

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: McGRAW-EDISON

Report Number: P640067

Luminaire Tested: GWS-SA5D-727-U-SL2-W

Issue Date: 1/10/2023

Test Information

Test Method: LM-79-2019
Report Number: P640067
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2209-782-27)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/10/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: McGRAW-EDISON
Catalog Number: GWS-SA5D-727-U-SL2-W
Description: GALLEON WALL SLIM LUMINAIRE. (5) LIGHTSQUARES WITH 16 LEDS EACH AND TYPE II SPILL LIGHT ELIMINATOR OPTICS
Light Source: (80) 2700K CCT, 70 CRI LEDS
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 24688.2 lumens
Efficiency: N/A
Efficacy: 120.7 lumens/watt
Luminous Opening: Rectangular (W 1.5' x L: 1' x H: 0')
IES Classification: Type II - Short
BUG Rating: B3 - U0 - G4


Input Watts (W): 204.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 0
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT



REPORT NUMBER: P640067
 CATALOG NUMBER: GWS-SA5D-727-U-SL2-W

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 8.7 fc
 Type II - Short - N/A

REPORT NUMBER: P640067
CATALOG NUMBER: GWS-SA5D-727-U-SL2-W

Luminous Intensity Polar Plot



— Vertical Plane Through 66-Deg Lateral - - - Horizontal Cone Through 67.5-Deg Vertical

REPORT NUMBER: P640067

CATALOG NUMBER: GWS-SA5D-727-U-SL2-W

FLUX DISTRIBUTION:

| | | Downward | Upward | Total |
|--------------------|-----------|----------|--------|---------|
| House Side | Lumens | 5009.8 | 0.0 | 5009.8 |
| | % Fixture | 20.3 | 0.0 | 20.3 |
| Street Side | Lumens | 19678.4 | 0.0 | 19678.4 |
| | % Fixture | 79.7 | 0.0 | 79.7 |
| Total | Lumens | 24688.2 | 0.0 | 24688.2 |
| | % Fixture | 100.0 | 0.0 | 100.0 |

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|---------|-----------|
| 0°-10° | 478.8 | 1.9 |
| 10°-20° | 1176.7 | 4.8 |
| 20°-30° | 1617.3 | 6.6 |
| 30°-40° | 2211.2 | 9.0 |
| 40°-50° | 3350.5 | 13.6 |
| 50°-60° | 5208.5 | 21.1 |
| 60°-70° | 6341.2 | 25.7 |
| 70°-80° | 3862.8 | 15.6 |
| 80°-90° | 441.2 | 1.8 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-90° | 24688.2 | 100.0 |
| 0°-180° | 24688.2 | 100.0 |

Coefficient of Utilization




REPORT NUMBER: P640067

CATALOG NUMBER: GWS-SA5D-727-U-SL2-W

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

| Zone | Lumens | % Fixture | Zone Rating/Lumen Limit | | |
|----------------|--------|-----------|-------------------------|------|----------|
| | | | B | U | G |
| FL (0°-30°) | 1934.4 | 7.8 | | | |
| FM (30°-60°) | 8999.8 | 36.5 | | | |
| FH (60°-80°) | 8377.3 | 33.9 | | | G4/12000 |
| FVH (80°-90°) | 366.8 | 1.5 | | | G3/500 |
| BL (0°-30°) | 1338.4 | 5.4 | B3/2500 | | |
| BM (30°-60°) | 1770.4 | 7.2 | B2/2500 | | |
| BH (60°-80°) | 1826.7 | 7.4 | B3/2500 | | G3/2500 |
| BVH (80°-90°) | 74.4 | 0.3 | | | G1/100 |
| UL (90°-100°) | 0.0 | 0.0 | | U0/0 | |
| UH (100°-180°) | 0.0 | 0.0 | | U0/0 | |

BUG Rating: B3-U0-G4
 Type II Short





REPORT NUMBER: P640067
 CATALOG NUMBER: GWS-SA5D-727-U-SL2-W

CANDELA DISTRIBUTION (FULL):

| | 0° | 5° | 15° | 25° | 35° | 45° | 55° | 65° | 66° | 75° | 85° |
|-------|--------|--------|--------|--------|---------|---------|---------|---------|---------|---------|---------|
| 0° | 5455.4 | 5455.4 | 5455.4 | 5455.4 | 5455.4 | 5455.4 | 5455.4 | 5455.4 | 5455.4 | 5455.4 | 5455.4 |
| 2.5° | 5109.6 | 5127.6 | 5116.8 | 5185.2 | 5188.8 | 5275.3 | 5323.9 | 5365.3 | 5368.9 | 5423.0 | 5459.0 |
| 5° | 4760.2 | 4771.0 | 4771.0 | 4835.8 | 4879.1 | 4994.3 | 5106.0 | 5224.9 | 5233.9 | 5363.5 | 5462.6 |
| 7.5° | 4477.4 | 4488.2 | 4481.0 | 4567.5 | 4623.3 | 4751.2 | 4893.5 | 5075.4 | 5093.4 | 5302.3 | 5475.2 |
| 10° | 4255.9 | 4252.3 | 4270.3 | 4349.5 | 4421.6 | 4574.7 | 4733.2 | 4940.3 | 4967.3 | 5232.1 | 5489.6 |
| 12.5° | 4104.6 | 4108.2 | 4119.0 | 4201.9 | 4279.3 | 4430.6 | 4594.5 | 4819.6 | 4848.4 | 5151.0 | 5482.4 |
| 15° | 4032.6 | 4025.4 | 4034.4 | 4110.0 | 4183.8 | 4317.1 | 4486.4 | 4718.8 | 4747.6 | 5079.0 | 5484.2 |
| 17.5° | 4016.3 | 4010.9 | 4009.1 | 4063.2 | 4119.0 | 4243.3 | 4405.4 | 4641.3 | 4671.9 | 5032.1 | 5495.0 |
| 20° | 4066.8 | 4059.6 | 4039.8 | 4063.2 | 4086.6 | 4191.1 | 4347.7 | 4585.5 | 4619.7 | 5001.5 | 5516.6 |
| 22.5° | 4205.5 | 4192.9 | 4162.2 | 4133.4 | 4102.8 | 4165.8 | 4311.7 | 4544.1 | 4578.3 | 4981.7 | 5538.2 |
| 25° | 4416.2 | 4405.4 | 4373.0 | 4308.1 | 4196.5 | 4185.6 | 4304.5 | 4526.0 | 4560.3 | 4967.3 | 5547.2 |
| 27.5° | 4706.2 | 4689.9 | 4657.5 | 4563.9 | 4382.0 | 4259.5 | 4331.5 | 4524.2 | 4556.7 | 4951.1 | 5538.2 |
| 30° | 5050.2 | 5039.3 | 5021.3 | 4907.9 | 4664.7 | 4416.2 | 4392.8 | 4538.7 | 4563.9 | 4942.1 | 5520.2 |
| 32.5° | 5399.6 | 5388.8 | 5403.2 | 5349.1 | 5050.2 | 4675.5 | 4526.0 | 4578.3 | 4596.3 | 4940.3 | 5504.0 |
| 35° | 5707.5 | 5720.1 | 5824.6 | 5833.6 | 5540.0 | 5026.7 | 4736.8 | 4670.1 | 4673.7 | 4976.3 | 5511.2 |
| 37.5° | 6029.9 | 6078.6 | 6215.4 | 6332.5 | 6087.6 | 5491.4 | 5050.2 | 4843.0 | 4839.4 | 5068.2 | 5556.3 |
| 40° | 6456.8 | 6478.4 | 6653.1 | 6872.8 | 6719.7 | 6129.0 | 5495.0 | 5125.8 | 5100.6 | 5255.5 | 5676.9 |
| 42.5° | 6872.8 | 6925.1 | 7204.2 | 7456.4 | 7405.9 | 6847.6 | 6055.1 | 5549.0 | 5504.0 | 5586.9 | 5925.5 |
| 45° | 7402.3 | 7452.8 | 7766.1 | 8090.3 | 8182.2 | 7659.9 | 6772.0 | 6150.6 | 6105.6 | 6085.8 | 6381.1 |
| 47.5° | 7931.8 | 7984.1 | 8265.0 | 8733.3 | 9055.7 | 8675.7 | 7704.9 | 6944.9 | 6871.0 | 6793.6 | 7069.1 |
| 50° | 8288.4 | 8349.7 | 8618.0 | 9180.0 | 9936.4 | 9943.6 | 8810.8 | 7985.9 | 7892.2 | 7769.7 | 8038.1 |
| 52.5° | 8275.8 | 8315.5 | 8571.2 | 9219.6 | 10570.4 | 11400.7 | 10291.2 | 9311.4 | 9235.8 | 8969.2 | 9203.4 |
| 55° | 7625.7 | 7685.1 | 7942.6 | 8753.1 | 10638.8 | 12782.1 | 12466.9 | 10874.8 | 10739.7 | 10262.4 | 10520.0 |
| 57.5° | 6319.9 | 6370.3 | 6629.7 | 7629.3 | 10031.9 | 13489.9 | 15229.7 | 12866.7 | 12681.2 | 11670.8 | 11968.0 |
| 60° | 4771.0 | 4709.8 | 4832.2 | 5707.5 | 8580.2 | 13507.9 | 17668.3 | 15568.3 | 15258.5 | 13176.5 | 13425.1 |
| 62.5° | 3580.5 | 3519.3 | 3546.3 | 3793.0 | 5817.4 | 12416.5 | 19058.7 | 19264.1 | 18752.6 | 14876.7 | 14828.1 |
| 65° | 2829.5 | 2795.2 | 2872.7 | 3042.0 | 3391.4 | 9455.5 | 19069.6 | 23260.6 | 22938.2 | 16847.1 | 16267.1 |
| 67.5° | 2305.3 | 2283.7 | 2363.0 | 2676.4 | 2750.2 | 5080.8 | 17099.2 | 25126.5 | 25252.6 | 19004.7 | 17601.7 |
| 70° | 1856.9 | 1824.5 | 1948.7 | 2361.2 | 2557.5 | 3074.4 | 12249.0 | 24175.5 | 24379.1 | 20290.7 | 17225.3 |
| 72.5° | 1282.4 | 1284.2 | 1347.2 | 1912.7 | 2469.2 | 2654.8 | 6928.7 | 20130.4 | 20571.6 | 19125.4 | 15143.3 |
| 75° | 864.5 | 871.7 | 889.7 | 1262.5 | 2274.7 | 2575.5 | 3692.2 | 15240.5 | 15552.1 | 15807.8 | 12517.3 |
| 77.5° | 522.3 | 525.9 | 567.3 | 763.6 | 1568.7 | 2404.4 | 2501.7 | 11047.7 | 11292.6 | 10420.9 | 7758.9 |
| 80° | 302.6 | 315.2 | 353.0 | 511.5 | 1059.0 | 1806.5 | 1936.1 | 6773.8 | 7051.1 | 4632.3 | 2465.6 |
| 82.5° | 133.3 | 142.3 | 192.7 | 297.2 | 617.8 | 1536.3 | 1511.1 | 2676.4 | 2636.7 | 1291.4 | 855.5 |
| 85° | 23.4 | 28.8 | 41.4 | 93.7 | 226.9 | 810.5 | 1172.5 | 1181.5 | 1111.3 | 489.9 | 354.8 |
| 87.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 5.4 | 176.5 | 317.0 | 315.2 | 138.7 | 122.5 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P640067
 CATALOG NUMBER: GWS-SA5D-727-U-SL2-W

CANDELA DISTRIBUTION (continued):

| | 90° | 95° | 105° | 115° | 125° | 135° | 145° | 155° | 165° | 175° | 180° |
|-------|---------|---------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 5455.4 | 5455.4 | 5455.4 | 5455.4 | 5455.4 | 5455.4 | 5455.4 | 5455.4 | 5455.4 | 5455.4 | 5455.4 |
| 2.5° | 5482.4 | 5433.8 | 5477.0 | 5482.4 | 5473.4 | 5466.2 | 5412.2 | 5365.3 | 5359.9 | 5309.5 | 5309.5 |
| 5° | 5502.2 | 5457.2 | 5478.8 | 5437.4 | 5372.5 | 5305.9 | 5190.6 | 5111.4 | 5075.4 | 5010.5 | 5010.5 |
| 7.5° | 5529.2 | 5482.4 | 5457.2 | 5354.5 | 5203.2 | 5057.4 | 4871.8 | 4717.0 | 4653.9 | 4562.1 | 4558.5 |
| 10° | 5554.4 | 5495.0 | 5408.6 | 5208.6 | 4967.3 | 4735.0 | 4464.8 | 4245.1 | 4095.6 | 3985.7 | 3985.7 |
| 12.5° | 5552.6 | 5475.2 | 5304.1 | 5008.7 | 4675.5 | 4338.7 | 3978.5 | 3647.1 | 3449.0 | 3277.9 | 3267.1 |
| 15° | 5549.0 | 5442.8 | 5170.8 | 4776.4 | 4335.1 | 3868.7 | 3378.8 | 2946.5 | 2653.0 | 2485.5 | 2471.0 |
| 17.5° | 5545.4 | 5401.4 | 5021.3 | 4511.6 | 3920.9 | 3285.1 | 2638.5 | 2170.3 | 1925.3 | 1822.7 | 1826.3 |
| 20° | 5545.4 | 5354.5 | 4861.0 | 4207.3 | 3443.6 | 2586.3 | 1936.1 | 1595.7 | 1534.5 | 1539.9 | 1545.3 |
| 22.5° | 5529.2 | 5296.9 | 4682.7 | 3875.9 | 2912.3 | 1901.9 | 1428.2 | 1313.0 | 1345.4 | 1395.8 | 1403.0 |
| 25° | 5491.4 | 5201.4 | 4475.6 | 3508.5 | 2280.1 | 1385.0 | 1165.3 | 1143.7 | 1203.1 | 1266.1 | 1284.2 |
| 27.5° | 5432.0 | 5091.6 | 4243.3 | 3078.0 | 1678.6 | 1113.1 | 1024.8 | 1023.0 | 1069.8 | 1116.7 | 1132.9 |
| 30° | 5368.9 | 4969.1 | 3998.3 | 2598.9 | 1215.7 | 969.0 | 934.7 | 934.7 | 958.2 | 987.0 | 983.4 |
| 32.5° | 5295.1 | 4844.8 | 3735.4 | 2100.0 | 990.6 | 887.9 | 877.1 | 871.7 | 875.3 | 886.1 | 886.1 |
| 35° | 5232.1 | 4735.0 | 3465.2 | 1572.3 | 887.9 | 842.9 | 832.1 | 819.5 | 814.1 | 806.9 | 810.5 |
| 37.5° | 5208.6 | 4648.5 | 3186.1 | 1185.1 | 837.5 | 810.5 | 792.5 | 774.5 | 761.8 | 758.2 | 756.4 |
| 40° | 5246.5 | 4612.5 | 2906.9 | 976.2 | 801.5 | 776.3 | 756.4 | 733.0 | 722.2 | 722.2 | 722.2 |
| 42.5° | 5394.2 | 4639.5 | 2622.3 | 882.5 | 776.3 | 747.4 | 718.6 | 697.0 | 693.4 | 697.0 | 698.8 |
| 45° | 5664.3 | 4744.0 | 2327.0 | 835.7 | 754.6 | 718.6 | 684.4 | 668.2 | 668.2 | 671.8 | 671.8 |
| 47.5° | 6147.0 | 5017.7 | 2035.2 | 806.9 | 733.0 | 695.2 | 659.2 | 643.0 | 641.2 | 644.8 | 644.8 |
| 50° | 6982.7 | 5511.2 | 1772.2 | 787.1 | 716.8 | 677.2 | 641.2 | 619.6 | 614.2 | 612.4 | 612.4 |
| 52.5° | 8036.3 | 6366.7 | 1604.7 | 772.7 | 697.0 | 657.4 | 621.4 | 592.5 | 581.7 | 576.3 | 576.3 |
| 55° | 9309.6 | 7506.8 | 1604.7 | 761.8 | 671.8 | 634.0 | 592.5 | 563.7 | 547.5 | 540.3 | 540.3 |
| 57.5° | 10752.3 | 8834.2 | 1882.1 | 752.8 | 652.0 | 607.0 | 561.9 | 533.1 | 515.1 | 504.3 | 504.3 |
| 60° | 12220.1 | 10237.2 | 2568.3 | 740.2 | 634.0 | 572.7 | 527.7 | 500.7 | 477.3 | 464.7 | 462.9 |
| 62.5° | 13742.0 | 11782.5 | 3472.4 | 747.4 | 621.4 | 540.3 | 491.7 | 461.1 | 441.3 | 428.7 | 426.8 |
| 65° | 15136.1 | 13254.0 | 4263.1 | 803.3 | 623.2 | 511.5 | 450.3 | 423.2 | 407.0 | 390.8 | 389.0 |
| 67.5° | 16319.3 | 14066.2 | 3708.4 | 916.7 | 661.0 | 477.3 | 408.8 | 381.8 | 367.4 | 356.6 | 354.8 |
| 70° | 15490.9 | 12827.1 | 2103.6 | 987.0 | 713.2 | 441.3 | 362.0 | 344.0 | 329.6 | 322.4 | 320.6 |
| 72.5° | 13246.7 | 10860.4 | 1406.6 | 871.7 | 650.2 | 394.4 | 318.8 | 304.4 | 293.6 | 284.6 | 282.8 |
| 75° | 10730.7 | 8612.6 | 1075.2 | 715.0 | 506.1 | 320.6 | 273.8 | 263.0 | 252.1 | 243.1 | 241.3 |
| 77.5° | 6348.7 | 4976.3 | 792.5 | 565.5 | 356.6 | 250.3 | 226.9 | 217.9 | 207.1 | 199.9 | 198.1 |
| 80° | 2026.2 | 1729.0 | 502.5 | 389.0 | 235.9 | 192.7 | 174.7 | 167.5 | 156.7 | 147.7 | 145.9 |
| 82.5° | 772.7 | 668.2 | 266.6 | 198.1 | 156.7 | 131.5 | 117.1 | 109.9 | 102.7 | 93.7 | 91.9 |
| 85° | 342.2 | 320.6 | 147.7 | 106.3 | 84.6 | 64.8 | 57.6 | 54.0 | 45.0 | 37.8 | 36.0 |
| 87.5° | 120.7 | 120.7 | 63.0 | 30.6 | 18.0 | 9.0 | 5.4 | 1.8 | 0.0 | 0.0 | 0.0 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



LM-79-2008: Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGRAW-EDISON

Report Number: SP1-1908-441-1-R4

Test Date: 08/20/2019

Luminaire Tested: SA1C-727-U-5WQ

Test Information

Test Method: LM-79-2008
 Report Number: SP1-1908-441-1-R4
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 10/28/2024
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: McGRAW-EDISON
 Catalog Number: **SA1C-727-U-5WQ**
 Description: McGRAW EDISON ROADWAY AND AREA LUMINAIRE

THIS IS A REVISION OF SP1-1908-441-1-R3. TO UPDATE THE CATALOG NUMBER.TESTED IN
 SITU. (1) 70 CRI, 2700K, 1050MA LIGHTSQUARE WITH 16 LEDS AND TYPE V WIDE OPTICS.

Spectral Parameters

CCT (K): 2741
 CIE u': 0.2605
 CIE v': 0.5272
 Duv: 0.0005
 CIE x: 0.4573
 CIE y: 0.4113
 CIE z: 0.1313
 Peak Wavelength (nm): 602
 Dominant Wavelength (nm): 583
 Purity: 61.2

| | | | |
|-----------|------|------|-------|
| CRI (Ra): | 71.5 | | |
| R1: | 69.2 | R9: | -16.1 |
| R2: | 79.4 | R10: | 51.4 |
| R3: | 87.8 | R11: | 63.1 |
| R4: | 69.4 | R12: | 42.0 |
| R5: | 66.4 | R13: | 70.2 |
| R6: | 69.8 | R14: | 92.4 |
| R7: | 79.8 | | |
| R8: | 50.1 | | |

Rf: 69.9
 Rg: 98.3



Test Conditions

Stabilization Time: 56M
 Operation Time: 12H
 Room Temperature (°C) / RH%: 25.3./42%
 Sphere Temperature (°C): 25.7

REPORT NUMBER: SP1-1908-441-1-R4

| Measurement and Test Equipment | | | |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument | Identification Number | Calibration Date | Calibration Due Date |
| Photometer | IN0058 | 6/28/2019 | 12/28/2019 |
| Power Meter | IN0071 | 12/5/2018 | 12/5/2019 |
| AC Power Source | IN0063 | 12/5/2018 | 12/5/2019 |
| DC Power Source | IN0208 | 12/5/2018 | 12/5/2019 |
| Sphere Thermometer | IN0085 | 12/5/2018 | 12/5/2019 |
| Room Thermometer | IN0046 | 12/5/2018 | 12/5/2019 |

REPORT NUMBER: SP1-1908-441-1-R4

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 2700K 4-step quadrangle

REPORT NUMBER: SP1-1908-441-1-R4

Photopic Flux vs. Wavelength



Photopic Lumens: 6211.7

| λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) |
|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|
| 360 | 2044 | 0.0 | 490 | 7179 | 1.0 | 620 | 118034 | 30.7 | 750 | 8362 | 0.0 | 880 | 3128 | 0.0 |
| 365 | 2016 | 0.0 | 495 | 10476 | 1.9 | 625 | 111884 | 24.7 | 755 | 7635 | 0.0 | 885 | 3110 | 0.0 |
| 370 | 2020 | 0.0 | 500 | 15549 | 3.4 | 630 | 106119 | 19.2 | 760 | 6582 | 0.0 | 890 | 2632 | 0.0 |
| 375 | 2137 | 0.0 | 505 | 22477 | 6.3 | 635 | 99706 | 15.0 | 765 | 5777 | 0.0 | 895 | 2709 | 0.0 |
| 380 | 2046 | 0.0 | 510 | 30417 | 10.4 | 640 | 92142 | 11.0 | 770 | 5474 | 0.0 | 900 | 2016 | 0.0 |
| 385 | 1925 | 0.0 | 515 | 39274 | 16.3 | 645 | 84987 | 8.2 | 775 | 4977 | 0.0 | 905 | 1748 | 0.0 |
| 390 | 1893 | 0.0 | 520 | 47282 | 22.9 | 650 | 78016 | 5.7 | 780 | 4723 | 0.0 | 910 | 2046 | 0.0 |
| 395 | 1695 | 0.0 | 525 | 55413 | 29.7 | 655 | 71541 | 4.1 | 785 | 4219 | 0.0 | 915 | 1844 | 0.0 |
| 400 | 1633 | 0.0 | 530 | 62377 | 36.7 | 660 | 64863 | 2.7 | 790 | 3969 | 0.0 | 920 | 2734 | 0.0 |
| 405 | 2065 | 0.0 | 535 | 68520 | 42.5 | 665 | 58485 | 1.9 | 795 | 4122 | 0.0 | 925 | 2307 | 0.0 |
| 410 | 3449 | 0.0 | 540 | 73435 | 47.8 | 670 | 51641 | 1.1 | 800 | 2864 | 0.0 | 930 | 2039 | 0.0 |
| 415 | 7117 | 0.0 | 545 | 78677 | 52.4 | 675 | 46030 | 0.8 | 805 | 3151 | 0.0 | 935 | 1784 | 0.0 |
| 420 | 13992 | 0.0 | 550 | 83331 | 56.6 | 680 | 40590 | 0.5 | 810 | 3022 | 0.0 | 940 | 2464 | 0.0 |
| 425 | 25176 | 0.1 | 555 | 89120 | 60.9 | 685 | 35691 | 0.3 | 815 | 3471 | 0.0 | 945 | 2794 | 0.0 |
| 430 | 38151 | 0.3 | 560 | 94613 | 64.3 | 690 | 31631 | 0.2 | 820 | 2749 | 0.0 | 950 | 3090 | 0.0 |
| 435 | 49673 | 0.6 | 565 | 99818 | 66.4 | 695 | 27437 | 0.1 | 825 | 2729 | 0.0 | 955 | 1866 | 0.0 |
| 440 | 57273 | 0.9 | 570 | 106526 | 69.3 | 700 | 24589 | 0.1 | 830 | 2282 | 0.0 | 960 | 3110 | 0.0 |
| 445 | 54802 | 1.1 | 575 | 111610 | 69.4 | 705 | 21832 | 0.0 | 835 | 3140 | 0.0 | 965 | 3880 | 0.0 |
| 450 | 39184 | 1.0 | 580 | 117163 | 69.6 | 710 | 19500 | 0.0 | 840 | 2365 | 0.0 | 970 | 3243 | 0.0 |
| 455 | 22506 | 0.8 | 585 | 122201 | 67.9 | 715 | 17870 | 0.0 | 845 | 3024 | 0.0 | 975 | 2014 | 0.0 |
| 460 | 13692 | 0.6 | 590 | 125662 | 65.0 | 720 | 15924 | 0.0 | 850 | 2510 | 0.0 | 980 | 1688 | 0.0 |
| 465 | 9446 | 0.5 | 595 | 127415 | 60.4 | 725 | 14268 | 0.0 | 855 | 2739 | 0.0 | 985 | 2827 | 0.0 |
| 470 | 6698 | 0.4 | 600 | 129155 | 55.7 | 730 | 12438 | 0.0 | 860 | 3515 | 0.0 | 990 | 4172 | 0.0 |
| 475 | 5328 | 0.4 | 605 | 128057 | 49.6 | 735 | 11255 | 0.0 | 865 | 3600 | 0.0 | 995 | 3177 | 0.0 |
| 480 | 5081 | 0.5 | 610 | 126031 | 43.3 | 740 | 9951 | 0.0 | 870 | 3609 | 0.0 | 1000 | 3241 | 0.0 |
| 485 | 5579 | 0.7 | 615 | 123059 | 37.1 | 745 | 8870 | 0.0 | 875 | 3208 | 0.0 | | | |

REPORT NUMBER: SP1-1908-441-1-R4

Scotopic Flux vs. Wavelength



Scotopic Lumens: 6474.3

S/P: 1.04

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 2044 | 0.0 | 490 | 7179 | 6.0 | 620 | 118034 | 0.1 | 750 | 8362 | 0.0 | 880 | 3128 | 0.0 |
| 365 | 2016 | 0.0 | 495 | 10476 | 8.6 | 625 | 111884 | 0.1 | 755 | 7635 | 0.0 | 885 | 3110 | 0.0 |
| 370 | 2020 | 0.0 | 500 | 15549 | 12.5 | 630 | 106119 | 0.0 | 760 | 6582 | 0.0 | 890 | 2632 | 0.0 |
| 375 | 2137 | 0.0 | 505 | 22477 | 17.3 | 635 | 99706 | 0.0 | 765 | 5777 | 0.0 | 895 | 2709 | 0.0 |
| 380 | 2046 | 0.0 | 510 | 30417 | 21.8 | 640 | 92142 | 0.0 | 770 | 5474 | 0.0 | 900 | 2016 | 0.0 |
| 385 | 1925 | 0.0 | 515 | 39274 | 25.7 | 645 | 84987 | 0.0 | 775 | 4977 | 0.0 | 905 | 1748 | 0.0 |
| 390 | 1893 | 0.0 | 520 | 47282 | 27.5 | 650 | 78016 | 0.0 | 780 | 4723 | 0.0 | 910 | 2046 | 0.0 |
| 395 | 1695 | 0.0 | 525 | 55413 | 28.1 | 655 | 71541 | 0.0 | 785 | 4219 | 0.0 | 915 | 1844 | 0.0 |
| 400 | 1633 | 0.0 | 530 | 62377 | 27.0 | 660 | 64863 | 0.0 | 790 | 3969 | 0.0 | 920 | 2734 | 0.0 |
| 405 | 2065 | 0.0 | 535 | 68520 | 24.7 | 665 | 58485 | 0.0 | 795 | 4122 | 0.0 | 925 | 2307 | 0.0 |
| 410 | 3449 | 0.1 | 540 | 73435 | 21.5 | 670 | 51641 | 0.0 | 800 | 2864 | 0.0 | 930 | 2039 | 0.0 |
| 415 | 7117 | 0.5 | 545 | 78677 | 18.3 | 675 | 46030 | 0.0 | 805 | 3151 | 0.0 | 935 | 1784 | 0.0 |
| 420 | 13992 | 1.6 | 550 | 83331 | 15.0 | 680 | 40590 | 0.0 | 810 | 3022 | 0.0 | 940 | 2464 | 0.0 |
| 425 | 25176 | 3.9 | 555 | 89120 | 12.0 | 685 | 35691 | 0.0 | 815 | 3471 | 0.0 | 945 | 2794 | 0.0 |
| 430 | 38151 | 8.1 | 560 | 94613 | 9.3 | 690 | 31631 | 0.0 | 820 | 2749 | 0.0 | 950 | 3090 | 0.0 |
| 435 | 49673 | 13.3 | 565 | 99818 | 7.0 | 695 | 27437 | 0.0 | 825 | 2729 | 0.0 | 955 | 1866 | 0.0 |
| 440 | 57273 | 19.1 | 570 | 106526 | 5.2 | 700 | 24589 | 0.0 | 830 | 2282 | 0.0 | 960 | 3110 | 0.0 |
| 445 | 54802 | 21.6 | 575 | 111610 | 3.7 | 705 | 21832 | 0.0 | 835 | 3140 | 0.0 | 965 | 3880 | 0.0 |
| 450 | 39184 | 18.1 | 580 | 117163 | 2.6 | 710 | 19500 | 0.0 | 840 | 2365 | 0.0 | 970 | 3243 | 0.0 |
| 455 | 22506 | 11.8 | 585 | 122201 | 1.8 | 715 | 17870 | 0.0 | 845 | 3024 | 0.0 | 975 | 2014 | 0.0 |
| 460 | 13692 | 8.1 | 590 | 125662 | 1.2 | 720 | 15924 | 0.0 | 850 | 2510 | 0.0 | 980 | 1688 | 0.0 |
| 465 | 9446 | 6.2 | 595 | 127415 | 0.8 | 725 | 14268 | 0.0 | 855 | 2739 | 0.0 | 985 | 2827 | 0.0 |
| 470 | 6698 | 4.8 | 600 | 129155 | 0.5 | 730 | 12438 | 0.0 | 860 | 3515 | 0.0 | 990 | 4172 | 0.0 |
| 475 | 5328 | 4.1 | 605 | 128057 | 0.4 | 735 | 11255 | 0.0 | 865 | 3600 | 0.0 | 995 | 3177 | 0.0 |
| 480 | 5081 | 4.1 | 610 | 126031 | 0.2 | 740 | 9951 | 0.0 | 870 | 3609 | 0.0 | 1000 | 3241 | 0.0 |
| 485 | 5579 | 4.6 | 615 | 123059 | 0.1 | 745 | 8870 | 0.0 | 875 | 3208 | 0.0 | | | |

REPORT NUMBER: SP1-1908-441-1-R4

Melanopic Flux vs. Wavelength



Melanopic Lumens: 2145.7 M/P: 0.35

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 2044 | 0.0 | 490 | 7179 | 11.1 | 620 | 118034 | 1.5 | 750 | 8362 | 0.0 | 880 | 3128 | 0.0 |
| 365 | 2016 | 0.0 | 495 | 10476 | 16.9 | 625 | 111884 | 0.9 | 755 | 7635 | 0.0 | 885 | 3110 | 0.0 |
| 370 | 2020 | 0.0 | 500 | 15549 | 26.0 | 630 | 106119 | 0.6 | 760 | 6582 | 0.0 | 890 | 2632 | 0.0 |
| 375 | 2137 | 0.0 | 505 | 22477 | 38.2 | 635 | 99706 | 0.4 | 765 | 5777 | 0.0 | 895 | 2709 | 0.0 |
| 380 | 2046 | 0.0 | 510 | 30417 | 51.6 | 640 | 92142 | 0.2 | 770 | 5474 | 0.0 | 900 | 2016 | 0.0 |
| 385 | 1925 | 0.0 | 515 | 39274 | 65.1 | 645 | 84987 | 0.1 | 775 | 4977 | 0.0 | 905 | 1748 | 0.0 |
| 390 | 1893 | 0.0 | 520 | 47282 | 75.2 | 650 | 78016 | 0.1 | 780 | 4723 | 0.0 | 910 | 2046 | 0.0 |
| 395 | 1695 | 0.0 | 525 | 55413 | 82.9 | 655 | 71541 | 0.1 | 785 | 4219 | 0.0 | 915 | 1844 | 0.0 |
| 400 | 1633 | 0.0 | 530 | 62377 | 86.0 | 660 | 64863 | 0.0 | 790 | 3969 | 0.0 | 920 | 2734 | 0.0 |
| 405 | 2065 | 0.1 | 535 | 68520 | 85.4 | 665 | 58485 | 0.0 | 795 | 4122 | 0.0 | 925 | 2307 | 0.0 |
| 410 | 3449 | 0.2 | 540 | 73435 | 81.1 | 670 | 51641 | 0.0 | 800 | 2864 | 0.0 | 930 | 2039 | 0.0 |
| 415 | 7117 | 0.7 | 545 | 78677 | 75.4 | 675 | 46030 | 0.0 | 805 | 3151 | 0.0 | 935 | 1784 | 0.0 |
| 420 | 13992 | 2.3 | 550 | 83331 | 68.1 | 680 | 40590 | 0.0 | 810 | 3022 | 0.0 | 940 | 2464 | 0.0 |
| 425 | 25176 | 6.2 | 555 | 89120 | 60.9 | 685 | 35691 | 0.0 | 815 | 3471 | 0.0 | 945 | 2794 | 0.0 |
| 430 | 38151 | 13.0 | 560 | 94613 | 52.9 | 690 | 31631 | 0.0 | 820 | 2749 | 0.0 | 950 | 3090 | 0.0 |
| 435 | 49673 | 22.2 | 565 | 99818 | 44.8 | 695 | 27437 | 0.0 | 825 | 2729 | 0.0 | 955 | 1866 | 0.0 |
| 440 | 57273 | 32.0 | 570 | 106526 | 37.6 | 700 | 24589 | 0.0 | 830 | 2282 | 0.0 | 960 | 3110 | 0.0 |
| 445 | 54802 | 36.7 | 575 | 111610 | 30.4 | 705 | 21832 | 0.0 | 835 | 3140 | 0.0 | 965 | 3880 | 0.0 |
| 450 | 39184 | 30.4 | 580 | 117163 | 24.1 | 710 | 19500 | 0.0 | 840 | 2365 | 0.0 | 970 | 3243 | 0.0 |
| 455 | 22506 | 19.7 | 585 | 122201 | 18.7 | 715 | 17870 | 0.0 | 845 | 3024 | 0.0 | 975 | 2014 | 0.0 |
| 460 | 13692 | 13.2 | 590 | 125662 | 14.0 | 720 | 15924 | 0.0 | 850 | 2510 | 0.0 | 980 | 1688 | 0.0 |
| 465 | 9446 | 10.0 | 595 | 127415 | 10.2 | 725 | 14268 | 0.0 | 855 | 2739 | 0.0 | 985 | 2827 | 0.0 |
| 470 | 6698 | 7.7 | 600 | 129155 | 7.3 | 730 | 12438 | 0.0 | 860 | 3515 | 0.0 | 990 | 4172 | 0.0 |
| 475 | 5328 | 6.7 | 605 | 128057 | 5.0 | 735 | 11255 | 0.0 | 865 | 3600 | 0.0 | 995 | 3177 | 0.0 |
| 480 | 5081 | 6.9 | 610 | 126031 | 3.4 | 740 | 9951 | 0.0 | 870 | 3609 | 0.0 | 1000 | 3241 | 0.0 |
| 485 | 5579 | 8.1 | 615 | 123059 | 2.3 | 745 | 8870 | 0.0 | 875 | 3208 | 0.0 | | | |

REPORT NUMBER: SP1-1908-441-1-R4

TM-30-18

Summary

$R_f = 69.9$
 $R_g = 98.3$
 CIE $R_a = 71.5$
 $R_9 = -16.1$



Color Vector Graphics



REPORT NUMBER: SP1-1908-441-1-R4

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)

| | | | |
|------------|------------|------------|------------|
| CES01 = 86 | CES26 = 54 | CES51 = 77 | CES76 = 48 |
| CES02 = 63 | CES27 = 74 | CES52 = 80 | CES77 = 75 |
| CES03 = 31 | CES28 = 80 | CES53 = 66 | CES78 = 56 |
| CES04 = 71 | CES29 = 44 | CES54 = 77 | CES79 = 81 |
| CES05 = 50 | CES30 = 46 | CES55 = 74 | CES80 = 80 |
| CES06 = 52 | CES31 = 50 | CES56 = 63 | CES81 = 73 |
| CES07 = 42 | CES32 = 49 | CES57 = 60 | CES82 = 91 |
| CES08 = 41 | CES33 = 53 | CES58 = 63 | CES83 = 84 |
| CES09 = 29 | CES34 = 66 | CES59 = 85 | CES84 = 90 |
| CES10 = 77 | CES35 = 82 | CES60 = 89 | CES85 = 87 |
| CES11 = 60 | CES36 = 78 | CES61 = 85 | CES86 = 65 |
| CES12 = 66 | CES37 = 75 | CES62 = 69 | CES87 = 78 |
| CES13 = 43 | CES38 = 53 | CES63 = 68 | CES88 = 73 |
| CES14 = 74 | CES39 = 91 | CES64 = 68 | CES89 = 68 |
| CES15 = 71 | CES40 = 85 | CES65 = 65 | CES90 = 68 |
| CES16 = 48 | CES41 = 76 | CES66 = 62 | CES91 = 91 |
| CES17 = 50 | CES42 = 76 | CES67 = 60 | CES92 = 71 |
| CES18 = 57 | CES43 = 65 | CES68 = 68 | CES93 = 82 |
| CES19 = 73 | CES44 = 98 | CES69 = 77 | CES94 = 57 |
| CES20 = 67 | CES45 = 75 | CES70 = 60 | CES95 = 78 |
| CES21 = 88 | CES46 = 70 | CES71 = 57 | CES96 = 80 |
| CES22 = 80 | CES47 = 63 | CES72 = 86 | CES97 = 79 |
| CES23 = 92 | CES48 = 51 | CES73 = 52 | CES98 = 71 |
| CES24 = 91 | CES49 = 68 | CES74 = 90 | CES99 = 64 |
| CES25 = 73 | CES50 = 77 | CES75 = 58 | |



REPORT NUMBER: SP1-1908-441-1-R4

TM-30-18

Color Rendition by Hue-Angle Bin



REPORT NUMBER: SP1-1908-441-1-R4

TM-30-18

Measure Comparisons



(END OF REPORT)