

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: McGRAW-EDISON

Report Number: P640100

Luminaire Tested: GWS-SA5D-727-U-T4FT-W

Issue Date: 1/10/2023

Test Information

Test Method: LM-79-2019
Report Number: P640100
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2209-782-54)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/10/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: McGRAW-EDISON
Catalog Number: GWS-SA5D-727-U-T4FT-W
Description: GALLEON WALL SLIM LUMINAIRE. (5) LIGHTSQUARES WITH 16 LEDS EACH AND TYPE IV FORWARD THROW OPTICS
Light Source: (80) 2700K CCT, 70 CRI LEDS
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 24266.8 lumens
Efficiency: N/A
Efficacy: 118.6 lumens/watt
Luminous Opening: Rectangular (W 1.5' x L: 1' x H: 0')
IES Classification: Type IV - Short
BUG Rating: B3 - U0 - G4


Input Watts (W): 204.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 0
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT



REPORT NUMBER: P640100
 CATALOG NUMBER: GWS-SA5D-727-U-T4FT-W

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 6 fc
 Type IV - Short - N/A

REPORT NUMBER: P640100
CATALOG NUMBER: GWS-SA5D-727-U-T4FT-W

Luminous Intensity Polar Plot



— Vertical Plane Through 36-Deg Lateral - - - Horizontal Cone Through 72.5-Deg Vertical

REPORT NUMBER: P640100

CATALOG NUMBER: GWS-SA5D-727-U-T4FT-W

FLUX DISTRIBUTION:

| | | Downward | Upward | Total |
|--------------------|-----------|----------|--------|---------|
| House Side | Lumens | 5594.5 | 0.0 | 5594.5 |
| | % Fixture | 23.1 | 0.0 | 23.1 |
| Street Side | Lumens | 18672.3 | 0.0 | 18672.3 |
| | % Fixture | 76.9 | 0.0 | 76.9 |
| Total | Lumens | 24266.8 | 0.0 | 24266.8 |
| | % Fixture | 100.0 | 0.0 | 100.0 |

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|---------|-----------|
| 0°-10° | 332.0 | 1.4 |
| 10°-20° | 936.6 | 3.9 |
| 20°-30° | 1551.2 | 6.4 |
| 30°-40° | 2323.0 | 9.6 |
| 40°-50° | 3389.1 | 14.0 |
| 50°-60° | 4823.7 | 19.9 |
| 60°-70° | 6094.4 | 25.1 |
| 70°-80° | 4342.8 | 17.9 |
| 80°-90° | 474.1 | 2.0 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-90° | 24266.8 | 100.0 |
| 0°-180° | 24266.8 | 100.0 |

Coefficient of Utilization



REPORT NUMBER: P640100


CATALOG NUMBER: GWS-SA5D-727-U-T4FT-W

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

| Zone | Lumens | % Fixture | Zone Rating/Lumen Limit | | |
|----------------|--------|-----------|-------------------------|------|----------|
| | | | B | U | G |
| FL (0°-30°) | 1354.7 | 5.6 | | | |
| FM (30°-60°) | 7776.9 | 32.0 | | | |
| FH (60°-80°) | 9200.3 | 37.9 | | | G4/12000 |
| FVH (80°-90°) | 340.3 | 1.4 | | | G3/500 |
| BL (0°-30°) | 1465.0 | 6.0 | B3/2500 | | |
| BM (30°-60°) | 2758.9 | 11.4 | B3/5000 | | |
| BH (60°-80°) | 1236.8 | 5.1 | B3/2500 | | G3/2500 |
| BVH (80°-90°) | 133.8 | 0.6 | | | G2/225 |
| UL (90°-100°) | 0.0 | 0.0 | | U0/0 | |
| UH (100°-180°) | 0.0 | 0.0 | | U0/0 | |

BUG Rating: B3-U0-G4

Type IV Short





REPORT NUMBER: P640100

CATALOG NUMBER: GWS-SA5D-727-U-T4FT-W

CANDELA DISTRIBUTION (FULL):

| | 0° | 5° | 15° | 25° | 35° | 36° | 45° | 55° | 65° | 75° | 85° |
|-------|---------|---------|---------|---------|---------|---------|---------|---------|--------|--------|---------|
| 0° | 3551.6 | 3551.6 | 3551.6 | 3551.6 | 3551.6 | 3551.6 | 3551.6 | 3551.6 | 3551.6 | 3551.6 | 3551.6 |
| 2.5° | 3240.0 | 3234.6 | 3223.8 | 3256.2 | 3288.6 | 3285.0 | 3330.0 | 3373.3 | 3420.1 | 3468.7 | 3533.5 |
| 5° | 2980.6 | 2977.0 | 2968.0 | 3016.7 | 3065.3 | 3063.5 | 3137.3 | 3207.6 | 3303.0 | 3407.5 | 3537.1 |
| 7.5° | 2721.3 | 2712.3 | 2724.9 | 2786.1 | 2854.6 | 2861.8 | 2962.6 | 3077.9 | 3216.6 | 3373.3 | 3557.0 |
| 10° | 2492.6 | 2490.8 | 2496.2 | 2564.6 | 2667.3 | 2674.5 | 2804.1 | 2964.4 | 3148.1 | 3357.0 | 3602.0 |
| 12.5° | 2433.1 | 2429.5 | 2415.1 | 2449.3 | 2526.8 | 2537.6 | 2679.9 | 2876.2 | 3101.3 | 3366.1 | 3663.2 |
| 15° | 2530.4 | 2521.4 | 2471.0 | 2454.8 | 2492.6 | 2501.6 | 2622.2 | 2824.0 | 3074.3 | 3382.3 | 3740.7 |
| 17.5° | 2697.9 | 2692.5 | 2597.0 | 2530.4 | 2555.6 | 2562.8 | 2652.9 | 2814.9 | 3067.1 | 3414.7 | 3836.1 |
| 20° | 2942.8 | 2919.4 | 2769.9 | 2669.1 | 2669.1 | 2679.9 | 2733.9 | 2854.6 | 3076.1 | 3454.3 | 3944.2 |
| 22.5° | 3267.0 | 3220.2 | 3009.5 | 2872.6 | 2836.6 | 2851.0 | 2874.4 | 2953.6 | 3113.9 | 3520.9 | 4079.2 |
| 25° | 3630.8 | 3587.6 | 3337.2 | 3144.5 | 3094.1 | 3099.5 | 3079.7 | 3094.1 | 3196.8 | 3612.8 | 4246.7 |
| 27.5° | 4018.0 | 3989.2 | 3722.6 | 3477.7 | 3398.5 | 3398.5 | 3328.2 | 3294.0 | 3312.0 | 3717.2 | 4434.0 |
| 30° | 4363.8 | 4324.2 | 4099.1 | 3830.7 | 3726.3 | 3726.3 | 3593.0 | 3519.1 | 3475.9 | 3845.1 | 4684.4 |
| 32.5° | 4545.7 | 4522.3 | 4372.8 | 4167.5 | 4039.6 | 4019.8 | 3904.5 | 3818.1 | 3717.2 | 4034.2 | 5023.0 |
| 35° | 4783.4 | 4778.0 | 4688.0 | 4527.7 | 4365.6 | 4336.8 | 4257.5 | 4189.1 | 4014.4 | 4270.2 | 5473.2 |
| 37.5° | 5082.4 | 5073.4 | 5059.0 | 4963.5 | 4769.0 | 4763.6 | 4693.4 | 4610.5 | 4383.6 | 4610.5 | 6018.9 |
| 40° | 5417.4 | 5401.2 | 5383.2 | 5381.4 | 5264.3 | 5244.5 | 5239.1 | 5145.4 | 4828.5 | 5021.2 | 6588.0 |
| 42.5° | 5878.4 | 5822.6 | 5653.3 | 5729.0 | 5815.4 | 5797.4 | 5865.8 | 5725.4 | 5383.2 | 5509.2 | 7126.5 |
| 45° | 6445.7 | 6308.9 | 5973.9 | 5995.5 | 6213.4 | 6249.4 | 6487.2 | 6453.0 | 5993.7 | 6072.9 | 7693.8 |
| 47.5° | 6786.1 | 6667.3 | 6355.7 | 6337.7 | 6609.6 | 6654.7 | 7171.5 | 7236.4 | 6651.1 | 6751.9 | 8394.4 |
| 50° | 7065.3 | 6982.4 | 6726.7 | 6751.9 | 7040.1 | 7085.1 | 7850.5 | 7989.2 | 7270.6 | 7447.1 | 9208.5 |
| 52.5° | 7402.1 | 7283.2 | 7085.1 | 7204.0 | 7557.0 | 7611.0 | 8605.1 | 8754.6 | 7828.9 | 8210.7 | 10051.3 |
| 55° | 7591.2 | 7542.6 | 7546.2 | 7728.1 | 8171.1 | 8244.9 | 9395.8 | 9370.6 | 8340.4 | 8864.5 | 10685.3 |
| 57.5° | 8027.0 | 8009.0 | 8174.7 | 8243.1 | 8887.9 | 8983.3 | 10186.4 | 9970.3 | 8805.0 | 9370.6 | 10989.6 |
| 60° | 8796.0 | 8751.0 | 8895.1 | 8999.6 | 9774.0 | 9909.1 | 11068.9 | 10557.4 | 9120.2 | 9747.0 | 10887.0 |
| 62.5° | 9876.6 | 9820.8 | 9826.2 | 9991.9 | 10960.8 | 11103.1 | 12050.4 | 11047.3 | 9217.5 | 9804.6 | 10236.8 |
| 65° | 11220.2 | 11139.1 | 11047.3 | 11272.4 | 12536.7 | 12655.6 | 13118.4 | 11403.9 | 8985.1 | 9249.9 | 8878.9 |
| 67.5° | 12637.6 | 12570.9 | 12462.9 | 12934.7 | 14577.2 | 14649.3 | 14316.1 | 11373.3 | 8248.5 | 7765.9 | 6227.8 |
| 70° | 12720.4 | 12736.6 | 13248.1 | 14955.4 | 17240.9 | 17258.9 | 15448.9 | 10757.3 | 6679.9 | 5033.8 | 3103.1 |
| 72.5° | 11866.7 | 11839.7 | 12506.1 | 15324.6 | 19384.1 | 19445.3 | 15983.8 | 8715.0 | 4127.9 | 2510.6 | 1455.2 |
| 75° | 9638.9 | 9685.7 | 10386.3 | 13408.4 | 16614.1 | 16668.2 | 13030.2 | 5138.2 | 1961.3 | 1228.3 | 931.1 |
| 77.5° | 4149.5 | 4410.6 | 5792.0 | 9446.2 | 11899.1 | 11731.7 | 6715.9 | 2081.9 | 1046.4 | 875.3 | 713.2 |
| 80° | 1197.7 | 1300.3 | 2063.9 | 4491.7 | 7130.1 | 7004.1 | 2658.3 | 779.8 | 729.4 | 657.4 | 511.5 |
| 82.5° | 387.2 | 428.6 | 756.4 | 1788.4 | 3195.0 | 3191.4 | 1008.6 | 461.1 | 477.3 | 446.6 | 329.6 |
| 85° | 108.1 | 124.3 | 232.3 | 542.1 | 988.7 | 968.9 | 291.8 | 217.9 | 253.9 | 257.5 | 163.9 |
| 87.5° | 0.0 | 0.0 | 1.8 | 3.6 | 3.6 | 3.6 | 7.2 | 32.4 | 73.8 | 93.7 | 66.6 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P640100
 CATALOG NUMBER: GWS-SA5D-727-U-T4FT-W

CANDELA DISTRIBUTION (continued):

| | 90° | 95° | 105° | 115° | 125° | 135° | 145° | 155° | 165° | 175° | 180° |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 3551.6 | 3551.6 | 3551.6 | 3551.6 | 3551.6 | 3551.6 | 3551.6 | 3551.6 | 3551.6 | 3551.6 | 3551.6 |
| 2.5° | 3573.2 | 3567.8 | 3641.6 | 3699.2 | 3753.3 | 3789.3 | 3800.1 | 3807.3 | 3821.7 | 3828.9 | 3821.7 |
| 5° | 3598.4 | 3625.4 | 3747.9 | 3837.9 | 3910.0 | 3953.2 | 3955.0 | 3951.4 | 3962.2 | 3953.2 | 3947.8 |
| 7.5° | 3652.4 | 3704.6 | 3859.5 | 3955.0 | 4001.8 | 4003.6 | 3960.4 | 3910.0 | 3884.7 | 3863.1 | 3855.9 |
| 10° | 3724.5 | 3801.9 | 3971.2 | 4034.2 | 4019.8 | 3953.2 | 3857.7 | 3778.5 | 3733.5 | 3701.0 | 3693.8 |
| 12.5° | 3823.5 | 3910.0 | 4070.2 | 4068.4 | 3978.4 | 3859.5 | 3747.9 | 3652.4 | 3587.6 | 3549.8 | 3537.1 |
| 15° | 3917.2 | 4027.0 | 4142.3 | 4057.6 | 3915.4 | 3771.3 | 3627.2 | 3499.3 | 3412.9 | 3353.4 | 3342.6 |
| 17.5° | 4032.4 | 4149.5 | 4194.5 | 4023.4 | 3836.1 | 3650.6 | 3457.9 | 3290.4 | 3173.3 | 3103.1 | 3097.7 |
| 20° | 4165.7 | 4270.2 | 4219.7 | 3964.0 | 3733.5 | 3490.3 | 3229.2 | 3041.9 | 2915.8 | 2847.4 | 2852.8 |
| 22.5° | 4320.6 | 4396.2 | 4226.9 | 3882.9 | 3591.2 | 3263.4 | 2971.6 | 2791.5 | 2706.9 | 2670.9 | 2672.7 |
| 25° | 4486.3 | 4534.9 | 4214.3 | 3773.1 | 3373.3 | 2986.0 | 2706.9 | 2624.0 | 2616.8 | 2607.8 | 2611.4 |
| 27.5° | 4682.6 | 4671.8 | 4176.5 | 3618.2 | 3079.7 | 2663.7 | 2521.4 | 2543.0 | 2571.8 | 2568.2 | 2571.8 |
| 30° | 4945.5 | 4842.9 | 4127.9 | 3403.9 | 2730.3 | 2393.5 | 2411.5 | 2472.8 | 2510.6 | 2514.2 | 2525.0 |
| 32.5° | 5246.3 | 5032.0 | 4050.4 | 3112.1 | 2397.1 | 2242.2 | 2308.9 | 2382.7 | 2427.7 | 2436.7 | 2451.1 |
| 35° | 5604.7 | 5248.1 | 3913.6 | 2748.3 | 2157.6 | 2152.2 | 2213.4 | 2263.8 | 2312.5 | 2316.1 | 2316.1 |
| 37.5° | 6017.1 | 5464.2 | 3695.6 | 2346.7 | 2009.9 | 2074.7 | 2132.4 | 2143.2 | 2155.8 | 2145.0 | 2150.4 |
| 40° | 6395.3 | 5673.1 | 3385.9 | 1981.1 | 1889.2 | 2006.3 | 2054.9 | 2018.9 | 1979.3 | 1952.3 | 1957.7 |
| 42.5° | 6712.3 | 5815.4 | 2975.2 | 1725.3 | 1766.8 | 1945.1 | 1982.9 | 1909.1 | 1831.6 | 1781.2 | 1788.4 |
| 45° | 7068.9 | 5946.9 | 2492.6 | 1552.5 | 1662.3 | 1901.8 | 1927.1 | 1831.6 | 1732.6 | 1656.9 | 1646.1 |
| 47.5° | 7560.6 | 6215.2 | 2063.9 | 1431.8 | 1588.5 | 1878.4 | 1919.9 | 1790.2 | 1660.5 | 1547.1 | 1534.4 |
| 50° | 8167.5 | 6595.2 | 1705.5 | 1352.5 | 1554.3 | 1865.8 | 1918.1 | 1745.2 | 1590.3 | 1457.0 | 1448.0 |
| 52.5° | 8830.3 | 6966.2 | 1440.8 | 1291.3 | 1520.0 | 1828.0 | 1909.1 | 1694.7 | 1516.4 | 1372.4 | 1361.5 |
| 55° | 9271.5 | 7112.1 | 1262.5 | 1233.7 | 1464.2 | 1768.6 | 1873.0 | 1646.1 | 1404.8 | 1273.3 | 1257.1 |
| 57.5° | 9401.2 | 6924.8 | 1138.2 | 1181.5 | 1392.2 | 1685.7 | 1804.6 | 1543.4 | 1336.3 | 1231.9 | 1219.3 |
| 60° | 9177.9 | 6453.0 | 1060.8 | 1138.2 | 1312.9 | 1579.5 | 1685.7 | 1484.0 | 1282.3 | 1188.7 | 1179.6 |
| 62.5° | 8547.5 | 5725.4 | 1001.4 | 1093.2 | 1231.9 | 1467.8 | 1610.1 | 1412.0 | 1222.9 | 1149.0 | 1136.4 |
| 65° | 7279.6 | 4695.2 | 952.7 | 1046.4 | 1154.4 | 1361.5 | 1527.2 | 1339.9 | 1158.0 | 1102.2 | 1087.8 |
| 67.5° | 5091.4 | 3297.6 | 900.5 | 990.5 | 1077.0 | 1258.9 | 1440.8 | 1273.3 | 1091.4 | 1050.0 | 1035.6 |
| 70° | 2489.0 | 1748.8 | 837.5 | 925.7 | 994.1 | 1154.4 | 1354.3 | 1192.3 | 1003.2 | 979.7 | 959.9 |
| 72.5° | 1185.1 | 977.9 | 763.6 | 837.5 | 880.7 | 1015.8 | 1210.3 | 1075.2 | 898.7 | 848.3 | 814.0 |
| 75° | 794.2 | 695.2 | 666.4 | 733.0 | 743.8 | 851.9 | 1037.4 | 927.5 | 792.4 | 734.8 | 706.0 |
| 77.5° | 601.5 | 531.3 | 560.1 | 619.5 | 597.9 | 700.6 | 853.7 | 826.7 | 715.0 | 662.8 | 648.4 |
| 80° | 423.2 | 387.2 | 444.8 | 480.9 | 464.7 | 596.1 | 769.0 | 707.8 | 588.9 | 531.3 | 520.5 |
| 82.5° | 266.5 | 259.3 | 327.8 | 333.2 | 338.6 | 471.9 | 632.1 | 556.5 | 457.5 | 376.4 | 349.4 |
| 85° | 133.3 | 147.7 | 196.3 | 196.3 | 194.5 | 243.1 | 360.2 | 313.4 | 246.7 | 196.3 | 190.9 |
| 87.5° | 45.0 | 63.0 | 84.6 | 68.4 | 52.2 | 41.4 | 46.8 | 57.6 | 61.2 | 59.4 | 59.4 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



LM-79-2008: Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGRAW-EDISON

Report Number: SP1-1908-441-1-R4

Test Date: 08/20/2019


Luminaire Tested: SA1C-727-U-5WQ

REPORT NUMBER: SP1-1908-441-1-R4

| Measurement and Test Equipment | | | |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument | Identification Number | Calibration Date | Calibration Due Date |
| Photometer | IN0058 | 6/28/2019 | 12/28/2019 |
| Power Meter | IN0071 | 12/5/2018 | 12/5/2019 |
| AC Power Source | IN0063 | 12/5/2018 | 12/5/2019 |
| DC Power Source | IN0208 | 12/5/2018 | 12/5/2019 |
| Sphere Thermometer | IN0085 | 12/5/2018 | 12/5/2019 |
| Room Thermometer | IN0046 | 12/5/2018 | 12/5/2019 |

REPORT NUMBER: SP1-1908-441-1-R4

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 2700K 4-step quadrangle

REPORT NUMBER: SP1-1908-441-1-R4

Photopic Flux vs. Wavelength



Photopic Lumens: 6211.7

| λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) |
|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|
| 360 | 2044 | 0.0 | 490 | 7179 | 1.0 | 620 | 118034 | 30.7 | 750 | 8362 | 0.0 | 880 | 3128 | 0.0 |
| 365 | 2016 | 0.0 | 495 | 10476 | 1.9 | 625 | 111884 | 24.7 | 755 | 7635 | 0.0 | 885 | 3110 | 0.0 |
| 370 | 2020 | 0.0 | 500 | 15549 | 3.4 | 630 | 106119 | 19.2 | 760 | 6582 | 0.0 | 890 | 2632 | 0.0 |
| 375 | 2137 | 0.0 | 505 | 22477 | 6.3 | 635 | 99706 | 15.0 | 765 | 5777 | 0.0 | 895 | 2709 | 0.0 |
| 380 | 2046 | 0.0 | 510 | 30417 | 10.4 | 640 | 92142 | 11.0 | 770 | 5474 | 0.0 | 900 | 2016 | 0.0 |
| 385 | 1925 | 0.0 | 515 | 39274 | 16.3 | 645 | 84987 | 8.2 | 775 | 4977 | 0.0 | 905 | 1748 | 0.0 |
| 390 | 1893 | 0.0 | 520 | 47282 | 22.9 | 650 | 78016 | 5.7 | 780 | 4723 | 0.0 | 910 | 2046 | 0.0 |
| 395 | 1695 | 0.0 | 525 | 55413 | 29.7 | 655 | 71541 | 4.1 | 785 | 4219 | 0.0 | 915 | 1844 | 0.0 |
| 400 | 1633 | 0.0 | 530 | 62377 | 36.7 | 660 | 64863 | 2.7 | 790 | 3969 | 0.0 | 920 | 2734 | 0.0 |
| 405 | 2065 | 0.0 | 535 | 68520 | 42.5 | 665 | 58485 | 1.9 | 795 | 4122 | 0.0 | 925 | 2307 | 0.0 |
| 410 | 3449 | 0.0 | 540 | 73435 | 47.8 | 670 | 51641 | 1.1 | 800 | 2864 | 0.0 | 930 | 2039 | 0.0 |
| 415 | 7117 | 0.0 | 545 | 78677 | 52.4 | 675 | 46030 | 0.8 | 805 | 3151 | 0.0 | 935 | 1784 | 0.0 |
| 420 | 13992 | 0.0 | 550 | 83331 | 56.6 | 680 | 40590 | 0.5 | 810 | 3022 | 0.0 | 940 | 2464 | 0.0 |
| 425 | 25176 | 0.1 | 555 | 89120 | 60.9 | 685 | 35691 | 0.3 | 815 | 3471 | 0.0 | 945 | 2794 | 0.0 |
| 430 | 38151 | 0.3 | 560 | 94613 | 64.3 | 690 | 31631 | 0.2 | 820 | 2749 | 0.0 | 950 | 3090 | 0.0 |
| 435 | 49673 | 0.6 | 565 | 99818 | 66.4 | 695 | 27437 | 0.1 | 825 | 2729 | 0.0 | 955 | 1866 | 0.0 |
| 440 | 57273 | 0.9 | 570 | 106526 | 69.3 | 700 | 24589 | 0.1 | 830 | 2282 | 0.0 | 960 | 3110 | 0.0 |
| 445 | 54802 | 1.1 | 575 | 111610 | 69.4 | 705 | 21832 | 0.0 | 835 | 3140 | 0.0 | 965 | 3880 | 0.0 |
| 450 | 39184 | 1.0 | 580 | 117163 | 69.6 | 710 | 19500 | 0.0 | 840 | 2365 | 0.0 | 970 | 3243 | 0.0 |
| 455 | 22506 | 0.8 | 585 | 122201 | 67.9 | 715 | 17870 | 0.0 | 845 | 3024 | 0.0 | 975 | 2014 | 0.0 |
| 460 | 13692 | 0.6 | 590 | 125662 | 65.0 | 720 | 15924 | 0.0 | 850 | 2510 | 0.0 | 980 | 1688 | 0.0 |
| 465 | 9446 | 0.5 | 595 | 127415 | 60.4 | 725 | 14268 | 0.0 | 855 | 2739 | 0.0 | 985 | 2827 | 0.0 |
| 470 | 6698 | 0.4 | 600 | 129155 | 55.7 | 730 | 12438 | 0.0 | 860 | 3515 | 0.0 | 990 | 4172 | 0.0 |
| 475 | 5328 | 0.4 | 605 | 128057 | 49.6 | 735 | 11255 | 0.0 | 865 | 3600 | 0.0 | 995 | 3177 | 0.0 |
| 480 | 5081 | 0.5 | 610 | 126031 | 43.3 | 740 | 9951 | 0.0 | 870 | 3609 | 0.0 | 1000 | 3241 | 0.0 |
| 485 | 5579 | 0.7 | 615 | 123059 | 37.1 | 745 | 8870 | 0.0 | 875 | 3208 | 0.0 | | | |

REPORT NUMBER: SP1-1908-441-1-R4

Scotopic Flux vs. Wavelength



Scotopic Lumens: 6474.3

S/P: 1.04

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 2044 | 0.0 | 490 | 7179 | 6.0 | 620 | 118034 | 0.1 | 750 | 8362 | 0.0 | 880 | 3128 | 0.0 |
| 365 | 2016 | 0.0 | 495 | 10476 | 8.6 | 625 | 111884 | 0.1 | 755 | 7635 | 0.0 | 885 | 3110 | 0.0 |
| 370 | 2020 | 0.0 | 500 | 15549 | 12.5 | 630 | 106119 | 0.0 | 760 | 6582 | 0.0 | 890 | 2632 | 0.0 |
| 375 | 2137 | 0.0 | 505 | 22477 | 17.3 | 635 | 99706 | 0.0 | 765 | 5777 | 0.0 | 895 | 2709 | 0.0 |
| 380 | 2046 | 0.0 | 510 | 30417 | 21.8 | 640 | 92142 | 0.0 | 770 | 5474 | 0.0 | 900 | 2016 | 0.0 |
| 385 | 1925 | 0.0 | 515 | 39274 | 25.7 | 645 | 84987 | 0.0 | 775 | 4977 | 0.0 | 905 | 1748 | 0.0 |
| 390 | 1893 | 0.0 | 520 | 47282 | 27.5 | 650 | 78016 | 0.0 | 780 | 4723 | 0.0 | 910 | 2046 | 0.0 |
| 395 | 1695 | 0.0 | 525 | 55413 | 28.1 | 655 | 71541 | 0.0 | 785 | 4219 | 0.0 | 915 | 1844 | 0.0 |
| 400 | 1633 | 0.0 | 530 | 62377 | 27.0 | 660 | 64863 | 0.0 | 790 | 3969 | 0.0 | 920 | 2734 | 0.0 |
| 405 | 2065 | 0.0 | 535 | 68520 | 24.7 | 665 | 58485 | 0.0 | 795 | 4122 | 0.0 | 925 | 2307 | 0.0 |
| 410 | 3449 | 0.1 | 540 | 73435 | 21.5 | 670 | 51641 | 0.0 | 800 | 2864 | 0.0 | 930 | 2039 | 0.0 |
| 415 | 7117 | 0.5 | 545 | 78677 | 18.3 | 675 | 46030 | 0.0 | 805 | 3151 | 0.0 | 935 | 1784 | 0.0 |
| 420 | 13992 | 1.6 | 550 | 83331 | 15.0 | 680 | 40590 | 0.0 | 810 | 3022 | 0.0 | 940 | 2464 | 0.0 |
| 425 | 25176 | 3.9 | 555 | 89120 | 12.0 | 685 | 35691 | 0.0 | 815 | 3471 | 0.0 | 945 | 2794 | 0.0 |
| 430 | 38151 | 8.1 | 560 | 94613 | 9.3 | 690 | 31631 | 0.0 | 820 | 2749 | 0.0 | 950 | 3090 | 0.0 |
| 435 | 49673 | 13.3 | 565 | 99818 | 7.0 | 695 | 27437 | 0.0 | 825 | 2729 | 0.0 | 955 | 1866 | 0.0 |
| 440 | 57273 | 19.1 | 570 | 106526 | 5.2 | 700 | 24589 | 0.0 | 830 | 2282 | 0.0 | 960 | 3110 | 0.0 |
| 445 | 54802 | 21.6 | 575 | 111610 | 3.7 | 705 | 21832 | 0.0 | 835 | 3140 | 0.0 | 965 | 3880 | 0.0 |
| 450 | 39184 | 18.1 | 580 | 117163 | 2.6 | 710 | 19500 | 0.0 | 840 | 2365 | 0.0 | 970 | 3243 | 0.0 |
| 455 | 22506 | 11.8 | 585 | 122201 | 1.8 | 715 | 17870 | 0.0 | 845 | 3024 | 0.0 | 975 | 2014 | 0.0 |
| 460 | 13692 | 8.1 | 590 | 125662 | 1.2 | 720 | 15924 | 0.0 | 850 | 2510 | 0.0 | 980 | 1688 | 0.0 |
| 465 | 9446 | 6.2 | 595 | 127415 | 0.8 | 725 | 14268 | 0.0 | 855 | 2739 | 0.0 | 985 | 2827 | 0.0 |
| 470 | 6698 | 4.8 | 600 | 129155 | 0.5 | 730 | 12438 | 0.0 | 860 | 3515 | 0.0 | 990 | 4172 | 0.0 |
| 475 | 5328 | 4.1 | 605 | 128057 | 0.4 | 735 | 11255 | 0.0 | 865 | 3600 | 0.0 | 995 | 3177 | 0.0 |
| 480 | 5081 | 4.1 | 610 | 126031 | 0.2 | 740 | 9951 | 0.0 | 870 | 3609 | 0.0 | 1000 | 3241 | 0.0 |
| 485 | 5579 | 4.6 | 615 | 123059 | 0.1 | 745 | 8870 | 0.0 | 875 | 3208 | 0.0 | | | |

REPORT NUMBER: SP1-1908-441-1-R4

Melanopic Flux vs. Wavelength



Melanopic Lumens: 2145.7 M/P: 0.35

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 2044 | 0.0 | 490 | 7179 | 11.1 | 620 | 118034 | 1.5 | 750 | 8362 | 0.0 | 880 | 3128 | 0.0 |
| 365 | 2016 | 0.0 | 495 | 10476 | 16.9 | 625 | 111884 | 0.9 | 755 | 7635 | 0.0 | 885 | 3110 | 0.0 |
| 370 | 2020 | 0.0 | 500 | 15549 | 26.0 | 630 | 106119 | 0.6 | 760 | 6582 | 0.0 | 890 | 2632 | 0.0 |
| 375 | 2137 | 0.0 | 505 | 22477 | 38.2 | 635 | 99706 | 0.4 | 765 | 5777 | 0.0 | 895 | 2709 | 0.0 |
| 380 | 2046 | 0.0 | 510 | 30417 | 51.6 | 640 | 92142 | 0.2 | 770 | 5474 | 0.0 | 900 | 2016 | 0.0 |
| 385 | 1925 | 0.0 | 515 | 39274 | 65.1 | 645 | 84987 | 0.1 | 775 | 4977 | 0.0 | 905 | 1748 | 0.0 |
| 390 | 1893 | 0.0 | 520 | 47282 | 75.2 | 650 | 78016 | 0.1 | 780 | 4723 | 0.0 | 910 | 2046 | 0.0 |
| 395 | 1695 | 0.0 | 525 | 55413 | 82.9 | 655 | 71541 | 0.1 | 785 | 4219 | 0.0 | 915 | 1844 | 0.0 |
| 400 | 1633 | 0.0 | 530 | 62377 | 86.0 | 660 | 64863 | 0.0 | 790 | 3969 | 0.0 | 920 | 2734 | 0.0 |
| 405 | 2065 | 0.1 | 535 | 68520 | 85.4 | 665 | 58485 | 0.0 | 795 | 4122 | 0.0 | 925 | 2307 | 0.0 |
| 410 | 3449 | 0.2 | 540 | 73435 | 81.1 | 670 | 51641 | 0.0 | 800 | 2864 | 0.0 | 930 | 2039 | 0.0 |
| 415 | 7117 | 0.7 | 545 | 78677 | 75.4 | 675 | 46030 | 0.0 | 805 | 3151 | 0.0 | 935 | 1784 | 0.0 |
| 420 | 13992 | 2.3 | 550 | 83331 | 68.1 | 680 | 40590 | 0.0 | 810 | 3022 | 0.0 | 940 | 2464 | 0.0 |
| 425 | 25176 | 6.2 | 555 | 89120 | 60.9 | 685 | 35691 | 0.0 | 815 | 3471 | 0.0 | 945 | 2794 | 0.0 |
| 430 | 38151 | 13.0 | 560 | 94613 | 52.9 | 690 | 31631 | 0.0 | 820 | 2749 | 0.0 | 950 | 3090 | 0.0 |
| 435 | 49673 | 22.2 | 565 | 99818 | 44.8 | 695 | 27437 | 0.0 | 825 | 2729 | 0.0 | 955 | 1866 | 0.0 |
| 440 | 57273 | 32.0 | 570 | 106526 | 37.6 | 700 | 24589 | 0.0 | 830 | 2282 | 0.0 | 960 | 3110 | 0.0 |
| 445 | 54802 | 36.7 | 575 | 111610 | 30.4 | 705 | 21832 | 0.0 | 835 | 3140 | 0.0 | 965 | 3880 | 0.0 |
| 450 | 39184 | 30.4 | 580 | 117163 | 24.1 | 710 | 19500 | 0.0 | 840 | 2365 | 0.0 | 970 | 3243 | 0.0 |
| 455 | 22506 | 19.7 | 585 | 122201 | 18.7 | 715 | 17870 | 0.0 | 845 | 3024 | 0.0 | 975 | 2014 | 0.0 |
| 460 | 13692 | 13.2 | 590 | 125662 | 14.0 | 720 | 15924 | 0.0 | 850 | 2510 | 0.0 | 980 | 1688 | 0.0 |
| 465 | 9446 | 10.0 | 595 | 127415 | 10.2 | 725 | 14268 | 0.0 | 855 | 2739 | 0.0 | 985 | 2827 | 0.0 |
| 470 | 6698 | 7.7 | 600 | 129155 | 7.3 | 730 | 12438 | 0.0 | 860 | 3515 | 0.0 | 990 | 4172 | 0.0 |
| 475 | 5328 | 6.7 | 605 | 128057 | 5.0 | 735 | 11255 | 0.0 | 865 | 3600 | 0.0 | 995 | 3177 | 0.0 |
| 480 | 5081 | 6.9 | 610 | 126031 | 3.4 | 740 | 9951 | 0.0 | 870 | 3609 | 0.0 | 1000 | 3241 | 0.0 |
| 485 | 5579 | 8.1 | 615 | 123059 | 2.3 | 745 | 8870 | 0.0 | 875 | 3208 | 0.0 | | | |

REPORT NUMBER: SP1-1908-441-1-R4


TM-30-18

Summary

$R_f = 69.9$
 $R_g = 98.3$
 $CIE R_a = 71.5$
 $R_9 = -16.1$



Color Vector Graphics



REPORT NUMBER: SP1-1908-441-1-R4

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)

| | | | |
|------------|------------|------------|------------|
| CES01 = 86 | CES26 = 54 | CES51 = 77 | CES76 = 48 |
| CES02 = 63 | CES27 = 74 | CES52 = 80 | CES77 = 75 |
| CES03 = 31 | CES28 = 80 | CES53 = 66 | CES78 = 56 |
| CES04 = 71 | CES29 = 44 | CES54 = 77 | CES79 = 81 |
| CES05 = 50 | CES30 = 46 | CES55 = 74 | CES80 = 80 |
| CES06 = 52 | CES31 = 50 | CES56 = 63 | CES81 = 73 |
| CES07 = 42 | CES32 = 49 | CES57 = 60 | CES82 = 91 |
| CES08 = 41 | CES33 = 53 | CES58 = 63 | CES83 = 84 |
| CES09 = 29 | CES34 = 66 | CES59 = 85 | CES84 = 90 |
| CES10 = 77 | CES35 = 82 | CES60 = 89 | CES85 = 87 |
| CES11 = 60 | CES36 = 78 | CES61 = 85 | CES86 = 65 |
| CES12 = 66 | CES37 = 75 | CES62 = 69 | CES87 = 78 |
| CES13 = 43 | CES38 = 53 | CES63 = 68 | CES88 = 73 |
| CES14 = 74 | CES39 = 91 | CES64 = 68 | CES89 = 68 |
| CES15 = 71 | CES40 = 85 | CES65 = 65 | CES90 = 68 |
| CES16 = 48 | CES41 = 76 | CES66 = 62 | CES91 = 91 |
| CES17 = 50 | CES42 = 76 | CES67 = 60 | CES92 = 71 |
| CES18 = 57 | CES43 = 65 | CES68 = 68 | CES93 = 82 |
| CES19 = 73 | CES44 = 98 | CES69 = 77 | CES94 = 57 |
| CES20 = 67 | CES45 = 75 | CES70 = 60 | CES95 = 78 |
| CES21 = 88 | CES46 = 70 | CES71 = 57 | CES96 = 80 |
| CES22 = 80 | CES47 = 63 | CES72 = 86 | CES97 = 79 |
| CES23 = 92 | CES48 = 51 | CES73 = 52 | CES98 = 71 |
| CES24 = 91 | CES49 = 68 | CES74 = 90 | CES99 = 64 |
| CES25 = 73 | CES50 = 77 | CES75 = 58 | |



REPORT NUMBER: SP1-1908-441-1-R4

TM-30-18

Color Rendition by Hue-Angle Bin



REPORT NUMBER: SP1-1908-441-1-R4

TM-30-18

Measure Comparisons



(END OF REPORT)