

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: McGRAW-EDISON

Report Number: P635668

Luminaire Tested: GWS-SA3E-730-U-SL3-W-GRSBK

Issue Date: 1/10/2023

**Test Information**

Test Method: LM-79-2019  
Report Number: P635668  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2209-782-32)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 1/10/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: McGRAW-EDISON  
Catalog Number: GWS-SA3E-730-U-SL3-W-GRSBK  
Description: GALLEON WALL SLIM LUMINAIRE. (3) LIGHTSQUARES WITH 16 LEDS EACH AND TYPE III SPILL LIGHT ELIMINATOR OPTICS W/ FACTORY INSTALLED GLARE SHIELD, BK  
Light Source: (48) 3000K CCT, 70 CRI LEDS  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 11713 lumens  
Efficiency: N/A  
Efficacy: 73.6 lumens/watt  
Luminous Opening: Rectangular (W 1.5' x L: 0.5' x H: 0')  
IES Classification: Type II - Short  
BUG Rating: B2 - U0 - G1  
  
Input Watts (W): 159.2  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 0  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 28.75 FT



REPORT NUMBER: P635668  
 CATALOG NUMBER: GWS-SA3E-730-U-SL3-W-GRSBK

### Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd  
 - - - 1/2 Max cd



Based on 20 foot mounting height. Maximum calculated value = 12.8 fc  
 Type II - Short - N/A

REPORT NUMBER: P635668  
CATALOG NUMBER: GWS-SA3E-730-U-SL3-W-GRSBK

### Luminous Intensity Polar Plot



— Vertical Plane Through 53-Deg Lateral    - - - Horizontal Cone Through 57.5-Deg Vertical

REPORT NUMBER: P635668

CATALOG NUMBER: GWS-SA3E-730-U-SL3-W-GRSBK

**FLUX DISTRIBUTION:**

|                    |           | Downward | Upward | Total   |
|--------------------|-----------|----------|--------|---------|
| <b>House Side</b>  | Lumens    | 1934.8   | 0.0    | 1934.8  |
|                    | % Fixture | 16.5     | 0.0    | 16.5    |
| <b>Street Side</b> | Lumens    | 9778.2   | 0.0    | 9778.2  |
|                    | % Fixture | 83.5     | 0.0    | 83.5    |
| <b>Total</b>       | Lumens    | 11713.0  | 0.0    | 11713.0 |
|                    | % Fixture | 100.0    | 0.0    | 100.0   |

**ZONAL LUMENS:**

| Zone      | Lumens  | % Fixture |
|-----------|---------|-----------|
| 0°-10°    | 439.6   | 3.8       |
| 10°-20°   | 965.1   | 8.2       |
| 20°-30°   | 1257.2  | 10.7      |
| 30°-40°   | 1823.6  | 15.6      |
| 40°-50°   | 2631.4  | 22.5      |
| 50°-60°   | 3182.4  | 27.2      |
| 60°-70°   | 1297.0  | 11.1      |
| 70°-80°   | 116.5   | 1.0       |
| 80°-90°   | 0.0     | 0.0       |
| 90°-100°  | 0.0     | 0.0       |
| 100°-110° | 0.0     | 0.0       |
| 110°-120° | 0.0     | 0.0       |
| 120°-130° | 0.0     | 0.0       |
| 130°-140° | 0.0     | 0.0       |
| 140°-150° | 0.0     | 0.0       |
| 150°-160° | 0.0     | 0.0       |
| 160°-170° | 0.0     | 0.0       |
| 170°-180° | 0.0     | 0.0       |
| 0°-90°    | 11713.0 | 100.0     |
| 0°-180°   | 11713.0 | 100.0     |

**Coefficient of Utilization**




REPORT NUMBER: P635668

CATALOG NUMBER: GWS-SA3E-730-U-SL3-W-GRSBK

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

| Zone           | Lumens | % Fixture | Zone Rating/Lumen Limit |      |         |
|----------------|--------|-----------|-------------------------|------|---------|
|                |        |           | B                       | U    | G       |
| FL (0°-30°)    | 1758.9 | 15.0      |                         |      |         |
| FM (30°-60°)   | 6739.4 | 57.5      |                         |      |         |
| FH (60°-80°)   | 1279.8 | 10.9      |                         |      | G1/1800 |
| FVH (80°-90°)  | 0.0    | 0.0       |                         |      | G0/10   |
| BL (0°-30°)    | 903.0  | 7.7       | B2/1000                 |      |         |
| BM (30°-60°)   | 898.1  | 7.7       | B1/1000                 |      |         |
| BH (60°-80°)   | 133.7  | 1.1       | B1/500                  |      | G1/500  |
| BVH (80°-90°)  | 0.0    | 0.0       |                         |      | G0/10   |
| UL (90°-100°)  | 0.0    | 0.0       |                         | U0/0 |         |
| UH (100°-180°) | 0.0    | 0.0       |                         | U0/0 |         |

**BUG Rating: B2-U0-G1**  
 Type II Short





REPORT NUMBER: P635668

CATALOG NUMBER: GWS-SA3E-730-U-SL3-W-GRSBK

**CANDELA DISTRIBUTION (FULL):**

|       | 0°     | 5°     | 15°    | 25°    | 35°    | 45°    | 53°    | 55°    | 65°    | 75°    | 85°    |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°    | 5138.0 | 5138.0 | 5138.0 | 5138.0 | 5138.0 | 5138.0 | 5138.0 | 5138.0 | 5138.0 | 5138.0 | 5138.0 |
| 2.5°  | 5066.2 | 5077.7 | 5097.8 | 5123.6 | 5140.9 | 5149.5 | 5149.5 | 5173.9 | 5158.1 | 5145.2 | 5130.8 |
| 5°    | 4849.4 | 4860.9 | 4888.2 | 4929.8 | 4971.5 | 5001.6 | 5036.1 | 5061.9 | 5072.0 | 5072.0 | 5047.5 |
| 7.5°  | 4543.7 | 4559.4 | 4576.7 | 4634.1 | 4724.5 | 4792.0 | 4850.9 | 4888.2 | 4942.7 | 4960.0 | 4925.5 |
| 10°   | 4214.9 | 4230.7 | 4269.5 | 4348.4 | 4451.8 | 4552.3 | 4652.8 | 4700.1 | 4793.4 | 4842.3 | 4803.5 |
| 12.5° | 3936.4 | 3943.6 | 3995.3 | 4090.0 | 4222.1 | 4359.9 | 4481.9 | 4530.7 | 4662.8 | 4736.0 | 4690.1 |
| 15°   | 3706.7 | 3711.0 | 3762.7 | 3867.5 | 4019.7 | 4189.1 | 4342.7 | 4392.9 | 4555.1 | 4665.7 | 4596.8 |
| 17.5° | 3533.0 | 3534.4 | 3578.9 | 3692.3 | 3851.7 | 4039.8 | 4222.1 | 4283.8 | 4493.4 | 4626.9 | 4523.6 |
| 20°   | 3445.4 | 3441.1 | 3472.7 | 3571.8 | 3722.5 | 3910.6 | 4125.9 | 4202.0 | 4459.0 | 4621.2 | 4467.6 |
| 22.5° | 3446.9 | 3436.8 | 3449.7 | 3520.1 | 3647.8 | 3824.4 | 4065.6 | 4151.7 | 4461.8 | 4645.6 | 4420.2 |
| 25°   | 3528.7 | 3514.3 | 3517.2 | 3554.5 | 3645.0 | 3805.8 | 4074.2 | 4166.1 | 4519.2 | 4727.4 | 4403.0 |
| 27.5° | 3666.5 | 3650.7 | 3650.7 | 3669.4 | 3718.2 | 3864.6 | 4181.9 | 4286.7 | 4672.9 | 4886.8 | 4438.9 |
| 30°   | 3844.5 | 3828.7 | 3823.0 | 3841.6 | 3881.8 | 4016.8 | 4421.6 | 4530.7 | 4935.6 | 5148.0 | 4553.7 |
| 32.5° | 4048.4 | 4029.7 | 4039.8 | 4065.6 | 4104.4 | 4291.0 | 4730.3 | 4875.3 | 5264.3 | 5499.8 | 4760.4 |
| 35°   | 4263.7 | 4247.9 | 4293.9 | 4349.8 | 4410.1 | 4671.4 | 5156.7 | 5283.0 | 5667.7 | 5937.6 | 5076.3 |
| 37.5° | 4469.0 | 4461.8 | 4558.0 | 4675.7 | 4800.6 | 5127.9 | 5590.2 | 5687.8 | 6013.7 | 6414.2 | 5462.4 |
| 40°   | 4674.3 | 4672.9 | 4838.0 | 5044.7 | 5244.2 | 5583.0 | 5919.0 | 5999.3 | 6224.7 | 6784.6 | 5832.8 |
| 42.5° | 4904.0 | 4904.0 | 5132.2 | 5407.9 | 5673.5 | 5967.8 | 6160.1 | 6196.0 | 6319.5 | 6998.5 | 6111.3 |
| 45°   | 5123.6 | 5136.6 | 5400.7 | 5720.8 | 6035.2 | 6267.8 | 6326.7 | 6329.5 | 6358.2 | 7124.9 | 6342.5 |
| 47.5° | 5297.3 | 5308.8 | 5624.7 | 5993.6 | 6332.4 | 6496.1 | 6504.7 | 6491.8 | 6460.2 | 7245.4 | 6520.5 |
| 50°   | 5438.0 | 5455.3 | 5785.4 | 6175.9 | 6536.3 | 6715.7 | 6781.7 | 6768.8 | 6688.4 | 7374.6 | 6645.4 |
| 52.5° | 5506.9 | 5531.3 | 5841.4 | 6266.4 | 6763.1 | 7091.8 | 7275.6 | 7305.7 | 7030.1 | 7446.4 | 6764.5 |
| 55°   | 4955.7 | 4991.6 | 5277.2 | 5858.7 | 6889.4 | 7673.2 | 7961.8 | 7956.1 | 7400.5 | 7660.3 | 7054.5 |
| 57.5° | 3742.6 | 3739.7 | 3976.6 | 4612.6 | 5884.5 | 7706.3 | 8383.9 | 8372.4 | 7746.5 | 7908.7 | 7351.7 |
| 60°   | 2548.2 | 2531.0 | 2594.1 | 2901.3 | 4114.4 | 6277.9 | 7630.2 | 7785.2 | 7501.0 | 7305.7 | 6242.0 |
| 62.5° | 2097.4 | 2081.6 | 2061.5 | 1976.8 | 2363.0 | 3910.6 | 5271.5 | 5506.9 | 5469.6 | 5077.7 | 3914.9 |
| 65°   | 1717.0 | 1729.9 | 1785.9 | 1750.0 | 1643.8 | 2005.5 | 2736.2 | 2875.5 | 2628.6 | 2212.2 | 1368.1 |
| 67.5° | 1266.2 | 1271.9 | 1345.2 | 1534.6 | 1477.2 | 1335.1 | 1287.7 | 1310.7 | 768.0  | 353.2  | 228.3  |
| 70°   | 747.9  | 752.3  | 819.7  | 1073.8 | 1198.7 | 1025.0 | 870.0  | 857.0  | 304.3  | 94.7   | 103.4  |
| 72.5° | 423.5  | 414.9  | 427.8  | 511.1  | 653.2  | 544.1  | 447.9  | 407.7  | 91.9   | 53.1   | 53.1   |
| 75°   | 201.0  | 195.2  | 168.0  | 157.9  | 143.6  | 91.9   | 57.4   | 48.8   | 23.0   | 21.5   | 21.5   |
| 77.5° | 1.4    | 4.3    | 2.9    | 4.3    | 4.3    | 2.9    | 1.4    | 1.4    | 4.3    | 4.3    | 5.7    |
| 80°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 82.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 85°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 87.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



REPORT NUMBER: P635668

CATALOG NUMBER: GWS-SA3E-730-U-SL3-W-GRSBK

**CANDELA DISTRIBUTION (continued):**

|       | 90°    | 95°    | 105°   | 115°   | 125°   | 135°   | 145°   | 155°   | 165°   | 175°   | 180°   |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°    | 5138.0 | 5138.0 | 5138.0 | 5138.0 | 5138.0 | 5138.0 | 5138.0 | 5138.0 | 5138.0 | 5138.0 | 5138.0 |
| 2.5°  | 5105.0 | 5061.9 | 5051.9 | 5049.0 | 5008.8 | 4965.7 | 4921.2 | 4904.0 | 4878.1 | 4862.4 | 4875.3 |
| 5°    | 5008.8 | 4947.1 | 4892.5 | 4842.3 | 4753.3 | 4655.6 | 4570.9 | 4516.4 | 4464.7 | 4430.2 | 4438.9 |
| 7.5°  | 4872.4 | 4792.0 | 4667.1 | 4539.3 | 4375.7 | 4229.3 | 4065.6 | 3965.1 | 3871.8 | 3820.1 | 3844.5 |
| 10°   | 4727.4 | 4621.2 | 4421.6 | 4204.9 | 3947.9 | 3718.2 | 3484.2 | 3293.3 | 3182.7 | 3077.9 | 3089.4 |
| 12.5° | 4585.3 | 4444.6 | 4146.0 | 3817.2 | 3492.8 | 3154.0 | 2800.8 | 2536.7 | 2355.8 | 2225.2 | 2205.1 |
| 15°   | 4453.2 | 4272.3 | 3877.5 | 3444.0 | 3001.8 | 2551.0 | 2100.3 | 1722.7 | 1513.1 | 1383.9 | 1375.3 |
| 17.5° | 4335.5 | 4111.5 | 3599.0 | 3053.5 | 2499.4 | 1922.3 | 1404.0 | 1121.2 | 1000.6 | 944.6  | 938.9  |
| 20°   | 4222.1 | 3949.3 | 3314.8 | 2657.3 | 1951.0 | 1349.5 | 969.0  | 838.4  | 799.6  | 776.7  | 779.5  |
| 22.5° | 4113.0 | 3772.7 | 3016.2 | 2218.0 | 1462.9 | 947.5  | 750.8  | 700.6  | 696.3  | 699.1  | 700.6  |
| 25°   | 4021.1 | 3610.5 | 2709.0 | 1794.5 | 1043.7 | 722.1  | 627.4  | 613.0  | 625.9  | 644.6  | 647.5  |
| 27.5° | 3973.7 | 3478.4 | 2408.9 | 1368.1 | 755.1  | 587.2  | 544.1  | 549.8  | 572.8  | 592.9  | 595.8  |
| 30°   | 3986.6 | 3379.4 | 2098.8 | 992.0  | 581.4  | 495.3  | 480.9  | 492.4  | 515.4  | 534.0  | 536.9  |
| 32.5° | 4078.5 | 3329.1 | 1781.6 | 722.1  | 478.1  | 432.1  | 426.4  | 435.0  | 455.1  | 469.4  | 470.9  |
| 35°   | 4260.8 | 3340.6 | 1480.1 | 552.7  | 410.6  | 384.7  | 383.3  | 389.0  | 399.1  | 409.1  | 410.6  |
| 37.5° | 4529.3 | 3433.9 | 1182.9 | 459.4  | 371.8  | 353.2  | 347.4  | 347.4  | 354.6  | 358.9  | 361.8  |
| 40°   | 4817.9 | 3574.6 | 947.5  | 406.3  | 344.5  | 324.4  | 313.0  | 308.7  | 314.4  | 320.1  | 321.6  |
| 42.5° | 5056.2 | 3715.3 | 769.5  | 368.9  | 323.0  | 295.7  | 281.4  | 278.5  | 285.7  | 295.7  | 298.6  |
| 45°   | 5238.5 | 3824.4 | 641.7  | 338.8  | 298.6  | 268.5  | 252.7  | 252.7  | 265.6  | 282.8  | 285.7  |
| 47.5° | 5405.0 | 3912.0 | 547.0  | 311.5  | 275.6  | 244.1  | 228.3  | 231.1  | 252.7  | 275.6  | 279.9  |
| 50°   | 5518.4 | 3982.3 | 476.6  | 287.1  | 257.0  | 224.0  | 209.6  | 215.3  | 241.2  | 268.5  | 272.8  |
| 52.5° | 5640.4 | 4068.5 | 430.7  | 265.6  | 239.7  | 208.2  | 195.2  | 199.5  | 228.3  | 258.4  | 264.1  |
| 55°   | 5977.8 | 4357.0 | 429.2  | 236.9  | 209.6  | 186.6  | 180.9  | 182.3  | 211.0  | 245.5  | 252.7  |
| 57.5° | 6253.4 | 4611.1 | 458.0  | 199.5  | 175.1  | 163.7  | 160.8  | 162.2  | 188.1  | 226.8  | 235.4  |
| 60°   | 5173.9 | 3583.2 | 379.0  | 165.1  | 146.4  | 143.6  | 139.3  | 142.1  | 166.5  | 201.0  | 208.2  |
| 62.5° | 3062.1 | 2048.6 | 180.9  | 126.3  | 124.9  | 122.0  | 117.7  | 123.5  | 146.4  | 176.6  | 180.9  |
| 65°   | 1046.5 | 607.3  | 114.8  | 103.4  | 106.2  | 101.9  | 97.6   | 103.4  | 123.5  | 140.7  | 142.1  |
| 67.5° | 201.0  | 160.8  | 91.9   | 86.1   | 87.6   | 79.0   | 77.5   | 83.3   | 94.7   | 97.6   | 96.2   |
| 70°   | 104.8  | 93.3   | 70.3   | 70.3   | 67.5   | 56.0   | 56.0   | 61.7   | 61.7   | 57.4   | 56.0   |
| 72.5° | 54.6   | 51.7   | 45.9   | 51.7   | 43.1   | 34.5   | 34.5   | 37.3   | 34.5   | 28.7   | 28.7   |
| 75°   | 21.5   | 21.5   | 20.1   | 25.8   | 18.7   | 15.8   | 14.4   | 17.2   | 12.9   | 10.0   | 10.0   |
| 77.5° | 5.7    | 5.7    | 5.7    | 7.2    | 4.3    | 4.3    | 2.9    | 2.9    | 1.4    | 0.0    | 0.0    |
| 80°   | 0.0    | 1.4    | 0.0    | 1.4    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 82.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 85°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 87.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



LM-79-2008: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGRAW-EDISON

Report Number: SP1-1908-441-2-R4

Test Date: 10/03/2019

Luminaire Tested: SA1C-730-U-5WQ

Data in this report applies to families of products SA1C-730-U-5WQ .

**Test Information**

Test Method: LM-79-2008  
 Report Number: SP1-1908-441-2-R4  
 Test Lab: COOPER LIGHTING SOLUTIONS  
 Photometer: SP1 - 76IN SPHERE  
 Measurement Geometry: 4π  
 Issue Date: 10/28/2024  
 Manufacturer: COOPER LIGHTING SOLUTIONS  
 Product Line: MCGRAW-EDISON  
 Catalog Number: **SA1C-730-U-5WQ**  
 Description: MCGRAW EDISON ROADWAY AND AREA LUMINAIRE

\*\*\*THIS IS A REVISION OF SP1-1908-441-2-R3. TO UPDATE THE CATALOG INFORMATION.\*\*\*TESTED IN SITU. (1) 70 CRI, 3000K, 1050MA LIGHTSQUARE WITH 16 LEDS AND TYPE V WIDE OPTICS.

**Spectral Parameters**

CCT (K): 2993  
 CIE u': 0.2508  
 CIE v': 0.5215  
 Duv: 0.0000  
 CIE x: 0.4374  
 CIE y: 0.4043  
 CIE z: 0.1583  
 Peak Wavelength (nm): 593  
 Dominant Wavelength (nm): 582  
 Purity: 53

|           |      |      |       |
|-----------|------|------|-------|
| CRI (Ra): | 71.8 |      |       |
| R1:       | 67.5 | R9:  | -38.3 |
| R2:       | 82.9 | R10: | 62.5  |
| R3:       | 94.7 | R11: | 63.7  |
| R4:       | 67.7 | R12: | 57.8  |
| R5:       | 67.9 | R13: | 70.4  |
| R6:       | 77.6 | R14: | 97.3  |
| R7:       | 76.0 |      |       |
| R8:       | 40.5 |      |       |

Rf: 75.7  
 Rg: 93.9



**Test Conditions**

Stabilization Time: 53M  
 Operation Time: 12H  
 Room Temperature (°C) / RH%: 25.0./44%  
 Sphere Temperature (°C): 25.7

REPORT NUMBER: SP1-1908-441-2-R4

| Measurement and Test Equipment |                       |                  |                      |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument                     | Identification Number | Calibration Date | Calibration Due Date |
| Photometer                     | IN0058                | 6/28/2019        | 12/28/2019           |
| Power Meter                    | IN0071                | 12/5/2018        | 12/5/2019            |
| AC Power Source                | IN0063                | 12/5/2018        | 12/5/2019            |
| DC Power Source                | IN0208                | 12/5/2018        | 12/5/2019            |
| Sphere Thermometer             | IN0085                | 12/5/2018        | 12/5/2019            |
| Room Thermometer               | IN0046                | 12/5/2018        | 12/5/2019            |

REPORT NUMBER: SP1-1908-441-2-R4

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 3000K 4-step quadrangle

REPORT NUMBER: SP1-1908-441-2-R4

**Photopic Flux vs. Wavelength**



#####

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360    | 2397          | NR            | 490    | 24908         | NR            | 620    | 118784        | NR            | 750    | 5037          | NR            | 880    | 2677          | NR            |
| 365    | 2084          | NR            | 495    | 30998         | NR            | 625    | 108951        | NR            | 755    | 4413          | NR            | 885    | 2940          | NR            |
| 370    | 2143          | NR            | 500    | 37103         | NR            | 630    | 99573         | NR            | 760    | 4189          | NR            | 890    | 3116          | NR            |
| 375    | 2413          | NR            | 505    | 42987         | NR            | 635    | 90444         | NR            | 765    | 3677          | NR            | 895    | 3345          | NR            |
| 380    | 2172          | NR            | 510    | 48702         | NR            | 640    | 80749         | NR            | 770    | 3366          | NR            | 900    | 2312          | NR            |
| 385    | 1997          | NR            | 515    | 53741         | NR            | 645    | 71664         | NR            | 775    | 3211          | NR            | 905    | 2829          | NR            |
| 390    | 1830          | NR            | 520    | 57283         | NR            | 650    | 63936         | NR            | 780    | 2682          | NR            | 910    | 2783          | NR            |
| 395    | 1861          | NR            | 525    | 61876         | NR            | 655    | 56611         | NR            | 785    | 2804          | NR            | 915    | 2662          | NR            |
| 400    | 1717          | NR            | 530    | 65398         | NR            | 660    | 49763         | NR            | 790    | 2581          | NR            | 920    | 3047          | NR            |
| 405    | 1761          | NR            | 535    | 69597         | NR            | 665    | 42891         | NR            | 795    | 2711          | NR            | 925    | 2256          | NR            |
| 410    | 2680          | NR            | 540    | 74214         | NR            | 670    | 36939         | NR            | 800    | 2609          | NR            | 930    | 2976          | NR            |
| 415    | 4374          | NR            | 545    | 79911         | NR            | 675    | 31946         | NR            | 805    | 2581          | NR            | 935    | 3503          | NR            |
| 420    | 8071          | NR            | 550    | 86153         | NR            | 680    | 27385         | NR            | 810    | 2404          | NR            | 940    | 4226          | NR            |
| 425    | 15169         | NR            | 555    | 93952         | NR            | 685    | 23504         | NR            | 815    | 2556          | NR            | 945    | 2930          | NR            |
| 430    | 26038         | NR            | 560    | 102904        | NR            | 690    | 20210         | NR            | 820    | 2742          | NR            | 950    | 2115          | NR            |
| 435    | 41316         | NR            | 565    | 112009        | NR            | 695    | 17459         | NR            | 825    | 2014          | NR            | 955    | 2634          | NR            |
| 440    | 59674         | NR            | 570    | 121662        | NR            | 700    | 15207         | NR            | 830    | 2488          | NR            | 960    | 4200          | NR            |
| 445    | 72751         | NR            | 575    | 130476        | NR            | 705    | 13322         | NR            | 835    | 2625          | NR            | 965    | 1982          | NR            |
| 450    | 65091         | NR            | 580    | 137926        | NR            | 710    | 11676         | NR            | 840    | 2754          | NR            | 970    | 3613          | NR            |
| 455    | 44894         | NR            | 585    | 143406        | NR            | 715    | 10626         | NR            | 845    | 2708          | NR            | 975    | 4034          | NR            |
| 460    | 32712         | NR            | 590    | 147039        | NR            | 720    | 9416          | NR            | 850    | 2608          | NR            | 980    | 3922          | NR            |
| 465    | 25296         | NR            | 595    | 147365        | NR            | 725    | 8333          | NR            | 855    | 2605          | NR            | 985    | 1909          | NR            |
| 470    | 19318         | NR            | 600    | 145800        | NR            | 730    | 7134          | NR            | 860    | 1765          | NR            | 990    | 3617          | NR            |
| 475    | 17265         | NR            | 605    | 141363        | NR            | 735    | 6437          | NR            | 865    | 2581          | NR            | 995    | 4767          | NR            |
| 480    | 18260         | NR            | 610    | 134199        | NR            | 740    | 5834          | NR            | 870    | 3016          | NR            | 1000   | 2528          | NR            |
| 485    | 20845         | NR            | 615    | 127683        | NR            | 745    | 5500          | NR            | 875    | 3952          | NR            |        |               |               |

REPORT NUMBER: SP1-1908-441-2-R4

Scotopic Flux vs. Wavelength



Scotopic Lumens: 8494.8

S/P: 1.23

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360    | 2397          | NR            | 490    | 24908         | NR            | 620    | 118784        | NR            | 750    | 5037          | NR            | 880    | 2677          | NR            |
| 365    | 2084          | NR            | 495    | 30998         | NR            | 625    | 108951        | NR            | 755    | 4413          | NR            | 885    | 2940          | NR            |
| 370    | 2143          | NR            | 500    | 37103         | NR            | 630    | 99573         | NR            | 760    | 4189          | NR            | 890    | 3116          | NR            |
| 375    | 2413          | NR            | 505    | 42987         | NR            | 635    | 90444         | NR            | 765    | 3677          | NR            | 895    | 3345          | NR            |
| 380    | 2172          | NR            | 510    | 48702         | NR            | 640    | 80749         | NR            | 770    | 3366          | NR            | 900    | 2312          | NR            |
| 385    | 1997          | NR            | 515    | 53741         | NR            | 645    | 71664         | NR            | 775    | 3211          | NR            | 905    | 2829          | NR            |
| 390    | 1830          | NR            | 520    | 57283         | NR            | 650    | 63936         | NR            | 780    | 2682          | NR            | 910    | 2783          | NR            |
| 395    | 1861          | NR            | 525    | 61876         | NR            | 655    | 56611         | NR            | 785    | 2804          | NR            | 915    | 2662          | NR            |
| 400    | 1717          | NR            | 530    | 65398         | NR            | 660    | 49763         | NR            | 790    | 2581          | NR            | 920    | 3047          | NR            |
| 405    | 1761          | NR            | 535    | 69597         | NR            | 665    | 42891         | NR            | 795    | 2711          | NR            | 925    | 2256          | NR            |
| 410    | 2680          | NR            | 540    | 74214         | NR            | 670    | 36939         | NR            | 800    | 2609          | NR            | 930    | 2976          | NR            |
| 415    | 4374          | NR            | 545    | 79911         | NR            | 675    | 31946         | NR            | 805    | 2581          | NR            | 935    | 3503          | NR            |
| 420    | 8071          | NR            | 550    | 86153         | NR            | 680    | 27385         | NR            | 810    | 2404          | NR            | 940    | 4226          | NR            |
| 425    | 15169         | NR            | 555    | 93952         | NR            | 685    | 23504         | NR            | 815    | 2556          | NR            | 945    | 2930          | NR            |
| 430    | 26038         | NR            | 560    | 102904        | NR            | 690    | 20210         | NR            | 820    | 2742          | NR            | 950    | 2115          | NR            |
| 435    | 41316         | NR            | 565    | 112009        | NR            | 695    | 17459         | NR            | 825    | 2014          | NR            | 955    | 2634          | NR            |
| 440    | 59674         | NR            | 570    | 121662        | NR            | 700    | 15207         | NR            | 830    | 2488          | NR            | 960    | 4200          | NR            |
| 445    | 72751         | NR            | 575    | 130476        | NR            | 705    | 13322         | NR            | 835    | 2625          | NR            | 965    | 1982          | NR            |
| 450    | 65091         | NR            | 580    | 137926        | NR            | 710    | 11676         | NR            | 840    | 2754          | NR            | 970    | 3613          | NR            |
| 455    | 44894         | NR            | 585    | 143406        | NR            | 715    | 10626         | NR            | 845    | 2708          | NR            | 975    | 4034          | NR            |
| 460    | 32712         | NR            | 590    | 147039        | NR            | 720    | 9416          | NR            | 850    | 2608          | NR            | 980    | 3922          | NR            |
| 465    | 25296         | NR            | 595    | 147365        | NR            | 725    | 8333          | NR            | 855    | 2605          | NR            | 985    | 1909          | NR            |
| 470    | 19318         | NR            | 600    | 145800        | NR            | 730    | 7134          | NR            | 860    | 1765          | NR            | 990    | 3617          | NR            |
| 475    | 17265         | NR            | 605    | 141363        | NR            | 735    | 6437          | NR            | 865    | 2581          | NR            | 995    | 4767          | NR            |
| 480    | 18260         | NR            | 610    | 134199        | NR            | 740    | 5834          | NR            | 870    | 3016          | NR            | 1000   | 2528          | NR            |
| 485    | 20845         | NR            | 615    | 127683        | NR            | 745    | 5500          | NR            | 875    | 3952          | NR            |        |               |               |

REPORT NUMBER: SP1-1908-441-2-R4

**Melanopic Flux vs. Wavelength**



**Melanopic Lumens: 3101.5 M/P: 0.45**

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360    | 2397          | NR            | 490    | 24908         | NR            | 620    | 118784        | NR            | 750    | 5037          | NR            | 880    | 2677          | NR            |
| 365    | 2084          | NR            | 495    | 30998         | NR            | 625    | 108951        | NR            | 755    | 4413          | NR            | 885    | 2940          | NR            |
| 370    | 2143          | NR            | 500    | 37103         | NR            | 630    | 99573         | NR            | 760    | 4189          | NR            | 890    | 3116          | NR            |
| 375    | 2413          | NR            | 505    | 42987         | NR            | 635    | 90444         | NR            | 765    | 3677          | NR            | 895    | 3345          | NR            |
| 380    | 2172          | NR            | 510    | 48702         | NR            | 640    | 80749         | NR            | 770    | 3366          | NR            | 900    | 2312          | NR            |
| 385    | 1997          | NR            | 515    | 53741         | NR            | 645    | 71664         | NR            | 775    | 3211          | NR            | 905    | 2829          | NR            |
| 390    | 1830          | NR            | 520    | 57283         | NR            | 650    | 63936         | NR            | 780    | 2682          | NR            | 910    | 2783          | NR            |
| 395    | 1861          | NR            | 525    | 61876         | NR            | 655    | 56611         | NR            | 785    | 2804          | NR            | 915    | 2662          | NR            |
| 400    | 1717          | NR            | 530    | 65398         | NR            | 660    | 49763         | NR            | 790    | 2581          | NR            | 920    | 3047          | NR            |
| 405    | 1761          | NR            | 535    | 69597         | NR            | 665    | 42891         | NR            | 795    | 2711          | NR            | 925    | 2256          | NR            |
| 410    | 2680          | NR            | 540    | 74214         | NR            | 670    | 36939         | NR            | 800    | 2609          | NR            | 930    | 2976          | NR            |
| 415    | 4374          | NR            | 545    | 79911         | NR            | 675    | 31946         | NR            | 805    | 2581          | NR            | 935    | 3503          | NR            |
| 420    | 8071          | NR            | 550    | 86153         | NR            | 680    | 27385         | NR            | 810    | 2404          | NR            | 940    | 4226          | NR            |
| 425    | 15169         | NR            | 555    | 93952         | NR            | 685    | 23504         | NR            | 815    | 2556          | NR            | 945    | 2930          | NR            |
| 430    | 26038         | NR            | 560    | 102904        | NR            | 690    | 20210         | NR            | 820    | 2742          | NR            | 950    | 2115          | NR            |
| 435    | 41316         | NR            | 565    | 112009        | NR            | 695    | 17459         | NR            | 825    | 2014          | NR            | 955    | 2634          | NR            |
| 440    | 59674         | NR            | 570    | 121662        | NR            | 700    | 15207         | NR            | 830    | 2488          | NR            | 960    | 4200          | NR            |
| 445    | 72751         | NR            | 575    | 130476        | NR            | 705    | 13322         | NR            | 835    | 2625          | NR            | 965    | 1982          | NR            |
| 450    | 65091         | NR            | 580    | 137926        | NR            | 710    | 11676         | NR            | 840    | 2754          | NR            | 970    | 3613          | NR            |
| 455    | 44894         | NR            | 585    | 143406        | NR            | 715    | 10626         | NR            | 845    | 2708          | NR            | 975    | 4034          | NR            |
| 460    | 32712         | NR            | 590    | 147039        | NR            | 720    | 9416          | NR            | 850    | 2608          | NR            | 980    | 3922          | NR            |
| 465    | 25296         | NR            | 595    | 147365        | NR            | 725    | 8333          | NR            | 855    | 2605          | NR            | 985    | 1909          | NR            |
| 470    | 19318         | NR            | 600    | 145800        | NR            | 730    | 7134          | NR            | 860    | 1765          | NR            | 990    | 3617          | NR            |
| 475    | 17265         | NR            | 605    | 141363        | NR            | 735    | 6437          | NR            | 865    | 2581          | NR            | 995    | 4767          | NR            |
| 480    | 18260         | NR            | 610    | 134199        | NR            | 740    | 5834          | NR            | 870    | 3016          | NR            | 1000   | 2528          | NR            |
| 485    | 20845         | NR            | 615    | 127683        | NR            | 745    | 5500          | NR            | 875    | 3952          | NR            |        |               |               |

REPORT NUMBER: SP1-1908-441-2-R4

TM-30-18

**Summary**

$R_f = 75.7$   
 $R_g = 93.9$   
 CIE  $R_a = 71.8$   
 $R_9 = -38.3$



**Color Vector Graphics**





REPORT NUMBER: SP1-1908-441-2-R4

TM-30-18

**Individual Sample Fidelity Index ( $R_{f,i}$ )**

|            |            |            |            |
|------------|------------|------------|------------|
| CES01 = 86 | CES26 = 67 | CES51 = 87 | CES76 = 63 |
| CES02 = 63 | CES27 = 88 | CES52 = 86 | CES77 = 80 |
| CES03 = 31 | CES28 = 87 | CES53 = 78 | CES78 = 67 |
| CES04 = 71 | CES29 = 66 | CES54 = 84 | CES79 = 87 |
| CES05 = 49 | CES30 = 73 | CES55 = 84 | CES80 = 86 |
| CES06 = 51 | CES31 = 70 | CES56 = 75 | CES81 = 71 |
| CES07 = 41 | CES32 = 65 | CES57 = 74 | CES82 = 94 |
| CES08 = 40 | CES33 = 73 | CES58 = 76 | CES83 = 90 |
| CES09 = 29 | CES34 = 79 | CES59 = 85 | CES84 = 89 |
| CES10 = 76 | CES35 = 89 | CES60 = 93 | CES85 = 77 |
| CES11 = 59 | CES36 = 97 | CES61 = 84 | CES86 = 61 |
| CES12 = 65 | CES37 = 87 | CES62 = 91 | CES87 = 78 |
| CES13 = 43 | CES38 = 81 | CES63 = 77 | CES88 = 77 |
| CES14 = 74 | CES39 = 95 | CES64 = 72 | CES89 = 67 |
| CES15 = 71 | CES40 = 92 | CES65 = 68 | CES90 = 76 |
| CES16 = 47 | CES41 = 88 | CES66 = 69 | CES91 = 89 |
| CES17 = 50 | CES42 = 89 | CES67 = 67 | CES92 = 58 |
| CES18 = 56 | CES43 = 79 | CES68 = 72 | CES93 = 74 |
| CES19 = 73 | CES44 = 99 | CES69 = 81 | CES94 = 49 |
| CES20 = 66 | CES45 = 85 | CES70 = 66 | CES95 = 68 |
| CES21 = 87 | CES46 = 80 | CES71 = 67 | CES96 = 76 |
| CES22 = 79 | CES47 = 82 | CES72 = 88 | CES97 = 82 |
| CES23 = 92 | CES48 = 69 | CES73 = 59 | CES98 = 75 |
| CES24 = 91 | CES49 = 80 | CES74 = 95 | CES99 = 62 |
| CES25 = 73 | CES50 = 87 | CES75 = 69 |            |



REPORT NUMBER: SP1-1908-441-2-R4

TM-30-18

Color Rendition by Hue-Angle Bin



REPORT NUMBER: SP1-1908-441-2-R4

TM-30-18

Measure Comparisons



(END OF REPORT)