

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: McGRAW-EDISON

Report Number: P636162

Luminaire Tested: GWS-SA3F-730-U-SL2-W

Issue Date: 1/10/2023

Test Information

Test Method: LM-79-2019
Report Number: P636162
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2209-782-27)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/10/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: McGRAW-EDISON
Catalog Number: GWS-SA3F-730-U-SL2-W
Description: GALLEON WALL SLIM LUMINAIRE. (3) LIGHTSQUARES WITH 16 LEDS EACH AND TYPE II SPILL LIGHT ELIMINATOR OPTICS
Light Source: (48) 3000K CCT, 70 CRI LEDS
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 21879.6 lumens
Efficiency: N/A
Efficacy: 119.4 lumens/watt
Luminous Opening: Rectangular (W 1.5' x L: 0.5' x H: 0')
IES Classification: Type II - Short
BUG Rating: B3 - U0 - G3


Input Watts (W): 183.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 0
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT



REPORT NUMBER: P636162
 CATALOG NUMBER: GWS-SA3F-730-U-SL2-W

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 7.7 fc
 Type II - Short - N/A

REPORT NUMBER: P636162
CATALOG NUMBER: GWS-SA3F-730-U-SL2-W

Luminous Intensity Polar Plot



— Vertical Plane Through 66-Deg Lateral - - - Horizontal Cone Through 67.5-Deg Vertical

REPORT NUMBER: P636162

CATALOG NUMBER: GWS-SA3F-730-U-SL2-W

FLUX DISTRIBUTION:

| | | Downward | Upward | Total |
|--------------------|-----------|----------|--------|---------|
| House Side | Lumens | 4439.9 | 0.0 | 4439.9 |
| | % Fixture | 20.3 | 0.0 | 20.3 |
| Street Side | Lumens | 17439.7 | 0.0 | 17439.7 |
| | % Fixture | 79.7 | 0.0 | 79.7 |
| Total | Lumens | 21879.6 | 0.0 | 21879.6 |
| | % Fixture | 100.0 | 0.0 | 100.0 |

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|---------|-----------|
| 0°-10° | 424.3 | 1.9 |
| 10°-20° | 1042.8 | 4.8 |
| 20°-30° | 1433.4 | 6.6 |
| 30°-40° | 1959.6 | 9.0 |
| 40°-50° | 2969.4 | 13.6 |
| 50°-60° | 4616.0 | 21.1 |
| 60°-70° | 5619.8 | 25.7 |
| 70°-80° | 3423.3 | 15.6 |
| 80°-90° | 391.0 | 1.8 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-90° | 21879.6 | 100.0 |
| 0°-180° | 21879.6 | 100.0 |

Coefficient of Utilization



REPORT NUMBER: P636162


CATALOG NUMBER: GWS-SA3F-730-U-SL2-W

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

| Zone | Lumens | % Fixture | Zone Rating/Lumen Limit | | |
|----------------|--------|-----------|-------------------------|------|---------|
| | | | B | U | G |
| FL (0°-30°) | 1714.4 | 7.8 | | | |
| FM (30°-60°) | 7975.9 | 36.5 | | | |
| FH (60°-80°) | 7424.3 | 33.9 | | | G3/7500 |
| FVH (80°-90°) | 325.1 | 1.5 | | | G3/500 |
| BL (0°-30°) | 1186.1 | 5.4 | B3/2500 | | |
| BM (30°-60°) | 1569.0 | 7.2 | B2/2500 | | |
| BH (60°-80°) | 1618.9 | 7.4 | B3/2500 | | G3/2500 |
| BVH (80°-90°) | 65.9 | 0.3 | | | G1/100 |
| UL (90°-100°) | 0.0 | 0.0 | | U0/0 | |
| UH (100°-180°) | 0.0 | 0.0 | | U0/0 | |

BUG Rating: B3-U0-G3

Type II Short





REPORT NUMBER: P636162
 CATALOG NUMBER: GWS-SA3F-730-U-SL2-W

CANDELA DISTRIBUTION (FULL):

| | 0° | 5° | 15° | 25° | 35° | 45° | 55° | 65° | 66° | 75° | 85° |
|-------|--------|--------|--------|--------|--------|---------|---------|---------|---------|---------|---------|
| 0° | 4834.8 | 4834.8 | 4834.8 | 4834.8 | 4834.8 | 4834.8 | 4834.8 | 4834.8 | 4834.8 | 4834.8 | 4834.8 |
| 2.5° | 4528.3 | 4544.3 | 4534.7 | 4595.3 | 4598.5 | 4675.2 | 4718.3 | 4755.0 | 4758.2 | 4806.0 | 4838.0 |
| 5° | 4218.7 | 4228.2 | 4228.2 | 4285.7 | 4324.0 | 4426.2 | 4525.1 | 4630.5 | 4638.4 | 4753.4 | 4841.2 |
| 7.5° | 3968.1 | 3977.6 | 3971.2 | 4047.9 | 4097.3 | 4210.7 | 4336.8 | 4498.0 | 4513.9 | 4699.1 | 4852.3 |
| 10° | 3771.7 | 3768.5 | 3784.5 | 3854.7 | 3918.6 | 4054.2 | 4194.7 | 4378.3 | 4402.2 | 4636.8 | 4865.1 |
| 12.5° | 3637.6 | 3640.8 | 3650.4 | 3723.8 | 3792.5 | 3926.6 | 4071.8 | 4271.3 | 4296.9 | 4565.0 | 4858.7 |
| 15° | 3573.8 | 3567.4 | 3575.4 | 3642.4 | 3707.9 | 3826.0 | 3976.0 | 4181.9 | 4207.5 | 4501.2 | 4860.3 |
| 17.5° | 3559.4 | 3554.6 | 3553.1 | 3600.9 | 3650.4 | 3760.6 | 3904.2 | 4113.3 | 4140.4 | 4459.7 | 4869.9 |
| 20° | 3604.1 | 3597.7 | 3580.2 | 3600.9 | 3621.7 | 3714.3 | 3853.1 | 4063.8 | 4094.2 | 4432.5 | 4889.0 |
| 22.5° | 3727.0 | 3715.9 | 3688.7 | 3663.2 | 3636.1 | 3691.9 | 3821.2 | 4027.1 | 4057.4 | 4415.0 | 4908.2 |
| 25° | 3913.8 | 3904.2 | 3875.5 | 3818.0 | 3719.1 | 3709.5 | 3814.8 | 4011.2 | 4041.5 | 4402.2 | 4916.2 |
| 27.5° | 4170.8 | 4156.4 | 4127.7 | 4044.7 | 3883.5 | 3774.9 | 3838.8 | 4009.6 | 4038.3 | 4387.8 | 4908.2 |
| 30° | 4475.6 | 4466.1 | 4450.1 | 4349.5 | 4134.1 | 3913.8 | 3893.0 | 4022.3 | 4044.7 | 4379.9 | 4892.2 |
| 32.5° | 4785.3 | 4775.7 | 4788.5 | 4740.6 | 4475.6 | 4143.6 | 4011.2 | 4057.4 | 4073.4 | 4378.3 | 4877.9 |
| 35° | 5058.2 | 5069.4 | 5162.0 | 5170.0 | 4909.8 | 4454.9 | 4197.9 | 4138.8 | 4142.0 | 4410.2 | 4884.3 |
| 37.5° | 5343.9 | 5387.0 | 5508.4 | 5612.1 | 5395.0 | 4866.7 | 4475.6 | 4292.1 | 4288.9 | 4491.6 | 4924.2 |
| 40° | 5722.2 | 5741.4 | 5896.2 | 6090.9 | 5955.3 | 5431.7 | 4869.9 | 4542.7 | 4520.3 | 4657.6 | 5031.1 |
| 42.5° | 6090.9 | 6137.2 | 6384.6 | 6608.1 | 6563.4 | 6068.6 | 5366.3 | 4917.8 | 4877.9 | 4951.3 | 5251.4 |
| 45° | 6560.2 | 6604.9 | 6882.6 | 7170.0 | 7251.4 | 6788.5 | 6001.6 | 5450.9 | 5411.0 | 5393.4 | 5655.2 |
| 47.5° | 7029.5 | 7075.8 | 7324.8 | 7739.8 | 8025.5 | 7688.7 | 6828.4 | 6154.8 | 6089.4 | 6020.7 | 6264.9 |
| 50° | 7345.5 | 7399.8 | 7637.6 | 8135.6 | 8806.0 | 8812.4 | 7808.4 | 7077.4 | 6994.4 | 6885.8 | 7123.7 |
| 52.5° | 7334.4 | 7369.5 | 7596.1 | 8170.7 | 9367.9 | 10103.7 | 9120.5 | 8252.2 | 8185.1 | 7948.9 | 8156.4 |
| 55° | 6758.1 | 6810.8 | 7039.1 | 7757.3 | 9428.5 | 11328.0 | 11048.6 | 9637.6 | 9517.9 | 9094.9 | 9323.2 |
| 57.5° | 5600.9 | 5645.6 | 5875.5 | 6761.3 | 8890.6 | 11955.2 | 13497.1 | 11403.0 | 11238.6 | 10343.1 | 10606.5 |
| 60° | 4228.2 | 4174.0 | 4282.5 | 5058.2 | 7604.1 | 11971.2 | 15658.3 | 13797.2 | 13522.7 | 11677.5 | 11897.8 |
| 62.5° | 3173.2 | 3118.9 | 3142.8 | 3361.5 | 5155.6 | 11003.9 | 16890.6 | 17072.5 | 16619.2 | 13184.3 | 13141.2 |
| 65° | 2507.6 | 2477.2 | 2545.9 | 2695.9 | 3005.6 | 8379.8 | 16900.1 | 20614.4 | 20328.7 | 14930.5 | 14416.5 |
| 67.5° | 2043.1 | 2023.9 | 2094.2 | 2371.9 | 2437.3 | 4502.8 | 15153.9 | 22268.0 | 22379.8 | 16842.7 | 15599.3 |
| 70° | 1645.6 | 1616.9 | 1727.0 | 2092.6 | 2266.5 | 2724.6 | 10855.5 | 21425.3 | 21605.6 | 17982.3 | 15265.7 |
| 72.5° | 1136.5 | 1138.1 | 1193.9 | 1695.1 | 2188.3 | 2352.7 | 6140.4 | 17840.3 | 18231.3 | 16949.6 | 13420.5 |
| 75° | 766.2 | 772.5 | 788.5 | 1118.9 | 2016.0 | 2282.5 | 3272.1 | 13506.7 | 13782.8 | 14009.5 | 11093.3 |
| 77.5° | 462.9 | 466.1 | 502.8 | 676.8 | 1390.3 | 2130.9 | 2217.1 | 9790.8 | 10007.9 | 9235.4 | 6876.3 |
| 80° | 268.2 | 279.3 | 312.8 | 453.3 | 938.5 | 1600.9 | 1715.9 | 6003.2 | 6249.0 | 4105.3 | 2185.1 |
| 82.5° | 118.1 | 126.1 | 170.8 | 263.4 | 547.5 | 1361.5 | 1339.2 | 2371.9 | 2336.8 | 1144.4 | 758.2 |
| 85° | 20.8 | 25.5 | 36.7 | 83.0 | 201.1 | 718.3 | 1039.1 | 1047.1 | 984.8 | 434.2 | 314.4 |
| 87.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 4.8 | 156.4 | 280.9 | 279.3 | 122.9 | 108.5 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P636162
 CATALOG NUMBER: GWS-SA3F-730-U-SL2-W

CANDELA DISTRIBUTION (continued):

| | 90° | 95° | 105° | 115° | 125° | 135° | 145° | 155° | 165° | 175° | 180° |
|-------|---------|---------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 4834.8 | 4834.8 | 4834.8 | 4834.8 | 4834.8 | 4834.8 | 4834.8 | 4834.8 | 4834.8 | 4834.8 | 4834.8 |
| 2.5° | 4858.7 | 4815.6 | 4853.9 | 4858.7 | 4850.7 | 4844.3 | 4796.5 | 4755.0 | 4750.2 | 4705.5 | 4705.5 |
| 5° | 4876.3 | 4836.4 | 4855.5 | 4818.8 | 4761.3 | 4702.3 | 4600.1 | 4529.9 | 4498.0 | 4440.5 | 4440.5 |
| 7.5° | 4900.2 | 4858.7 | 4836.4 | 4745.4 | 4611.3 | 4482.0 | 4317.6 | 4180.3 | 4124.5 | 4043.1 | 4039.9 |
| 10° | 4922.6 | 4869.9 | 4793.3 | 4616.1 | 4402.2 | 4196.3 | 3956.9 | 3762.2 | 3629.7 | 3532.3 | 3532.3 |
| 12.5° | 4921.0 | 4852.3 | 4700.7 | 4438.9 | 4143.6 | 3845.2 | 3525.9 | 3232.2 | 3056.6 | 2905.0 | 2895.4 |
| 15° | 4917.8 | 4823.6 | 4582.6 | 4233.0 | 3842.0 | 3428.6 | 2994.4 | 2611.3 | 2351.1 | 2202.7 | 2189.9 |
| 17.5° | 4914.6 | 4786.9 | 4450.1 | 3998.4 | 3474.8 | 2911.4 | 2338.4 | 1923.4 | 1706.3 | 1615.3 | 1618.5 |
| 20° | 4914.6 | 4745.4 | 4308.0 | 3728.6 | 3051.9 | 2292.1 | 1715.9 | 1414.2 | 1359.9 | 1364.7 | 1369.5 |
| 22.5° | 4900.2 | 4694.3 | 4150.0 | 3434.9 | 2581.0 | 1685.5 | 1265.8 | 1163.6 | 1192.3 | 1237.0 | 1243.4 |
| 25° | 4866.7 | 4609.7 | 3966.5 | 3109.3 | 2020.7 | 1227.4 | 1032.7 | 1013.6 | 1066.2 | 1122.1 | 1138.1 |
| 27.5° | 4814.0 | 4512.3 | 3760.6 | 2727.8 | 1487.6 | 986.4 | 908.2 | 906.6 | 948.1 | 989.6 | 1004.0 |
| 30° | 4758.2 | 4403.8 | 3543.5 | 2303.3 | 1077.4 | 858.7 | 828.4 | 828.4 | 849.2 | 874.7 | 871.5 |
| 32.5° | 4692.7 | 4293.7 | 3310.4 | 1861.1 | 877.9 | 786.9 | 777.3 | 772.5 | 775.7 | 785.3 | 785.3 |
| 35° | 4636.8 | 4196.3 | 3071.0 | 1393.4 | 786.9 | 747.0 | 737.4 | 726.3 | 721.5 | 715.1 | 718.3 |
| 37.5° | 4616.1 | 4119.7 | 2823.6 | 1050.3 | 742.2 | 718.3 | 702.3 | 686.3 | 675.2 | 672.0 | 670.4 |
| 40° | 4649.6 | 4087.8 | 2576.2 | 865.1 | 710.3 | 687.9 | 670.4 | 649.6 | 640.1 | 640.1 | 640.1 |
| 42.5° | 4780.5 | 4111.7 | 2324.0 | 782.1 | 687.9 | 662.4 | 636.9 | 617.7 | 614.5 | 617.7 | 619.3 |
| 45° | 5019.9 | 4204.3 | 2062.2 | 740.6 | 668.8 | 636.9 | 606.5 | 592.2 | 592.2 | 595.4 | 595.4 |
| 47.5° | 5447.7 | 4446.9 | 1803.7 | 715.1 | 649.6 | 616.1 | 584.2 | 569.8 | 568.2 | 571.4 | 571.4 |
| 50° | 6188.3 | 4884.3 | 1570.6 | 697.5 | 635.3 | 600.2 | 568.2 | 549.1 | 544.3 | 542.7 | 542.7 |
| 52.5° | 7122.1 | 5642.4 | 1422.2 | 684.8 | 617.7 | 582.6 | 550.7 | 525.1 | 515.6 | 510.8 | 510.8 |
| 55° | 8250.6 | 6652.8 | 1422.2 | 675.2 | 595.4 | 561.8 | 525.1 | 499.6 | 485.2 | 478.8 | 478.8 |
| 57.5° | 9529.1 | 7829.2 | 1668.0 | 667.2 | 577.8 | 537.9 | 498.0 | 472.5 | 456.5 | 446.9 | 446.9 |
| 60° | 10829.9 | 9072.6 | 2276.1 | 656.0 | 561.8 | 507.6 | 467.7 | 443.7 | 423.0 | 411.8 | 410.2 |
| 62.5° | 12178.7 | 10442.1 | 3077.4 | 662.4 | 550.7 | 478.8 | 435.8 | 408.6 | 391.1 | 379.9 | 378.3 |
| 65° | 13414.1 | 11746.1 | 3778.1 | 711.9 | 552.3 | 453.3 | 399.0 | 375.1 | 360.7 | 346.4 | 344.8 |
| 67.5° | 14462.8 | 12466.0 | 3286.5 | 812.4 | 585.8 | 423.0 | 362.3 | 338.4 | 325.6 | 316.0 | 314.4 |
| 70° | 13728.6 | 11367.9 | 1864.3 | 874.7 | 632.1 | 391.1 | 320.8 | 304.9 | 292.1 | 285.7 | 284.1 |
| 72.5° | 11739.8 | 9624.8 | 1246.6 | 772.5 | 576.2 | 349.6 | 282.5 | 269.8 | 260.2 | 252.2 | 250.6 |
| 75° | 9509.9 | 7632.8 | 952.9 | 633.7 | 448.5 | 284.1 | 242.6 | 233.0 | 223.5 | 215.5 | 213.9 |
| 77.5° | 5626.5 | 4410.2 | 702.3 | 501.2 | 316.0 | 221.9 | 201.1 | 193.1 | 183.6 | 177.2 | 175.6 |
| 80° | 1795.7 | 1532.3 | 445.3 | 344.8 | 209.1 | 170.8 | 154.8 | 148.4 | 138.9 | 130.9 | 129.3 |
| 82.5° | 684.8 | 592.2 | 236.2 | 175.6 | 138.9 | 116.5 | 103.8 | 97.4 | 91.0 | 83.0 | 81.4 |
| 85° | 303.3 | 284.1 | 130.9 | 94.2 | 75.0 | 57.5 | 51.1 | 47.9 | 39.9 | 33.5 | 31.9 |
| 87.5° | 106.9 | 106.9 | 55.9 | 27.1 | 16.0 | 8.0 | 4.8 | 1.6 | 0.0 | 0.0 | 0.0 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



LM-79-2008: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGRAW-EDISON

Report Number: SP1-1908-441-2-R4

Test Date: 10/03/2019

Luminaire Tested: SA1C-730-U-5WQ

Data in this report applies to families of products SA1C-730-U-5WQ .

Test Information

Test Method: LM-79-2008
 Report Number: SP1-1908-441-2-R4
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 10/28/2024
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: McGRAW-EDISON
 Catalog Number: **SA1C-730-U-5WQ**
 Description: McGRAW EDISON ROADWAY AND AREA LUMINAIRE

THIS IS A REVISION OF SP1-1908-441-2-R3. TO UPDATE THE CATALOG INFORMATION.TESTED IN SITU. (1) 70 CRI, 3000K, 1050MA LIGHTSQUARE WITH 16 LEDS AND TYPE V WIDE OPTICS.

Spectral Parameters

| | | | | | |
|---------------------------|--------|-----------|------|------|-------|
| CCT (K): | 2993 | CRI (Ra): | 71.8 | R9: | -38.3 |
| CIE u': | 0.2508 | R1: | 67.5 | R10: | 62.5 |
| CIE v': | 0.5215 | R2: | 82.9 | R11: | 63.7 |
| Duv: | 0.0000 | R3: | 94.7 | R12: | 57.8 |
| CIE x: | 0.4374 | R4: | 67.7 | R13: | 70.4 |
| CIE y: | 0.4043 | R5: | 67.9 | R14: | 97.3 |
| CIE z: | 0.1583 | R6: | 77.6 | | |
| Peak Wavelength (nm): | 593 | R7: | 76.0 | | |
| Dominant Wavelength (nm): | 582 | R8: | 40.5 | | |
| Purity: | 53 | | | | |
| Rf: | 75.7 | | | | |
| Rg: | 93.9 | | | | |



Test Conditions

Stabilization Time: 53M
 Operation Time: 12H
 Room Temperature (°C) / RH%: 25.0./44%
 Sphere Temperature (°C): 25.7

REPORT NUMBER: SP1-1908-441-2-R4

| Measurement and Test Equipment | | | |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument | Identification Number | Calibration Date | Calibration Due Date |
| Photometer | IN0058 | 6/28/2019 | 12/28/2019 |
| Power Meter | IN0071 | 12/5/2018 | 12/5/2019 |
| AC Power Source | IN0063 | 12/5/2018 | 12/5/2019 |
| DC Power Source | IN0208 | 12/5/2018 | 12/5/2019 |
| Sphere Thermometer | IN0085 | 12/5/2018 | 12/5/2019 |
| Room Thermometer | IN0046 | 12/5/2018 | 12/5/2019 |

REPORT NUMBER: SP1-1908-441-2-R4

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 3000K 4-step quadrangle

REPORT NUMBER: SP1-1908-441-2-R4

Photopic Flux vs. Wavelength



#####

| λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) |
|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|
| 360 | 2397 | NR | 490 | 24908 | NR | 620 | 118784 | NR | 750 | 5037 | NR | 880 | 2677 | NR |
| 365 | 2084 | NR | 495 | 30998 | NR | 625 | 108951 | NR | 755 | 4413 | NR | 885 | 2940 | NR |
| 370 | 2143 | NR | 500 | 37103 | NR | 630 | 99573 | NR | 760 | 4189 | NR | 890 | 3116 | NR |
| 375 | 2413 | NR | 505 | 42987 | NR | 635 | 90444 | NR | 765 | 3677 | NR | 895 | 3345 | NR |
| 380 | 2172 | NR | 510 | 48702 | NR | 640 | 80749 | NR | 770 | 3366 | NR | 900 | 2312 | NR |
| 385 | 1997 | NR | 515 | 53741 | NR | 645 | 71664 | NR | 775 | 3211 | NR | 905 | 2829 | NR |
| 390 | 1830 | NR | 520 | 57283 | NR | 650 | 63936 | NR | 780 | 2682 | NR | 910 | 2783 | NR |
| 395 | 1861 | NR | 525 | 61876 | NR | 655 | 56611 | NR | 785 | 2804 | NR | 915 | 2662 | NR |
| 400 | 1717 | NR | 530 | 65398 | NR | 660 | 49763 | NR | 790 | 2581 | NR | 920 | 3047 | NR |
| 405 | 1761 | NR | 535 | 69597 | NR | 665 | 42891 | NR | 795 | 2711 | NR | 925 | 2256 | NR |
| 410 | 2680 | NR | 540 | 74214 | NR | 670 | 36939 | NR | 800 | 2609 | NR | 930 | 2976 | NR |
| 415 | 4374 | NR | 545 | 79911 | NR | 675 | 31946 | NR | 805 | 2581 | NR | 935 | 3503 | NR |
| 420 | 8071 | NR | 550 | 86153 | NR | 680 | 27385 | NR | 810 | 2404 | NR | 940 | 4226 | NR |
| 425 | 15169 | NR | 555 | 93952 | NR | 685 | 23504 | NR | 815 | 2556 | NR | 945 | 2930 | NR |
| 430 | 26038 | NR | 560 | 102904 | NR | 690 | 20210 | NR | 820 | 2742 | NR | 950 | 2115 | NR |
| 435 | 41316 | NR | 565 | 112009 | NR | 695 | 17459 | NR | 825 | 2014 | NR | 955 | 2634 | NR |
| 440 | 59674 | NR | 570 | 121662 | NR | 700 | 15207 | NR | 830 | 2488 | NR | 960 | 4200 | NR |
| 445 | 72751 | NR | 575 | 130476 | NR | 705 | 13322 | NR | 835 | 2625 | NR | 965 | 1982 | NR |
| 450 | 65091 | NR | 580 | 137926 | NR | 710 | 11676 | NR | 840 | 2754 | NR | 970 | 3613 | NR |
| 455 | 44894 | NR | 585 | 143406 | NR | 715 | 10626 | NR | 845 | 2708 | NR | 975 | 4034 | NR |
| 460 | 32712 | NR | 590 | 147039 | NR | 720 | 9416 | NR | 850 | 2608 | NR | 980 | 3922 | NR |
| 465 | 25296 | NR | 595 | 147365 | NR | 725 | 8333 | NR | 855 | 2605 | NR | 985 | 1909 | NR |
| 470 | 19318 | NR | 600 | 145800 | NR | 730 | 7134 | NR | 860 | 1765 | NR | 990 | 3617 | NR |
| 475 | 17265 | NR | 605 | 141363 | NR | 735 | 6437 | NR | 865 | 2581 | NR | 995 | 4767 | NR |
| 480 | 18260 | NR | 610 | 134199 | NR | 740 | 5834 | NR | 870 | 3016 | NR | 1000 | 2528 | NR |
| 485 | 20845 | NR | 615 | 127683 | NR | 745 | 5500 | NR | 875 | 3952 | NR | | | |

REPORT NUMBER: SP1-1908-441-2-R4

Scotopic Flux vs. Wavelength



Scotopic Lumens: 8494.8

S/P: 1.23

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 2397 | NR | 490 | 24908 | NR | 620 | 118784 | NR | 750 | 5037 | NR | 880 | 2677 | NR |
| 365 | 2084 | NR | 495 | 30998 | NR | 625 | 108951 | NR | 755 | 4413 | NR | 885 | 2940 | NR |
| 370 | 2143 | NR | 500 | 37103 | NR | 630 | 99573 | NR | 760 | 4189 | NR | 890 | 3116 | NR |
| 375 | 2413 | NR | 505 | 42987 | NR | 635 | 90444 | NR | 765 | 3677 | NR | 895 | 3345 | NR |
| 380 | 2172 | NR | 510 | 48702 | NR | 640 | 80749 | NR | 770 | 3366 | NR | 900 | 2312 | NR |
| 385 | 1997 | NR | 515 | 53741 | NR | 645 | 71664 | NR | 775 | 3211 | NR | 905 | 2829 | NR |
| 390 | 1830 | NR | 520 | 57283 | NR | 650 | 63936 | NR | 780 | 2682 | NR | 910 | 2783 | NR |
| 395 | 1861 | NR | 525 | 61876 | NR | 655 | 56611 | NR | 785 | 2804 | NR | 915 | 2662 | NR |
| 400 | 1717 | NR | 530 | 65398 | NR | 660 | 49763 | NR | 790 | 2581 | NR | 920 | 3047 | NR |
| 405 | 1761 | NR | 535 | 69597 | NR | 665 | 42891 | NR | 795 | 2711 | NR | 925 | 2256 | NR |
| 410 | 2680 | NR | 540 | 74214 | NR | 670 | 36939 | NR | 800 | 2609 | NR | 930 | 2976 | NR |
| 415 | 4374 | NR | 545 | 79911 | NR | 675 | 31946 | NR | 805 | 2581 | NR | 935 | 3503 | NR |
| 420 | 8071 | NR | 550 | 86153 | NR | 680 | 27385 | NR | 810 | 2404 | NR | 940 | 4226 | NR |
| 425 | 15169 | NR | 555 | 93952 | NR | 685 | 23504 | NR | 815 | 2556 | NR | 945 | 2930 | NR |
| 430 | 26038 | NR | 560 | 102904 | NR | 690 | 20210 | NR | 820 | 2742 | NR | 950 | 2115 | NR |
| 435 | 41316 | NR | 565 | 112009 | NR | 695 | 17459 | NR | 825 | 2014 | NR | 955 | 2634 | NR |
| 440 | 59674 | NR | 570 | 121662 | NR | 700 | 15207 | NR | 830 | 2488 | NR | 960 | 4200 | NR |
| 445 | 72751 | NR | 575 | 130476 | NR | 705 | 13322 | NR | 835 | 2625 | NR | 965 | 1982 | NR |
| 450 | 65091 | NR | 580 | 137926 | NR | 710 | 11676 | NR | 840 | 2754 | NR | 970 | 3613 | NR |
| 455 | 44894 | NR | 585 | 143406 | NR | 715 | 10626 | NR | 845 | 2708 | NR | 975 | 4034 | NR |
| 460 | 32712 | NR | 590 | 147039 | NR | 720 | 9416 | NR | 850 | 2608 | NR | 980 | 3922 | NR |
| 465 | 25296 | NR | 595 | 147365 | NR | 725 | 8333 | NR | 855 | 2605 | NR | 985 | 1909 | NR |
| 470 | 19318 | NR | 600 | 145800 | NR | 730 | 7134 | NR | 860 | 1765 | NR | 990 | 3617 | NR |
| 475 | 17265 | NR | 605 | 141363 | NR | 735 | 6437 | NR | 865 | 2581 | NR | 995 | 4767 | NR |
| 480 | 18260 | NR | 610 | 134199 | NR | 740 | 5834 | NR | 870 | 3016 | NR | 1000 | 2528 | NR |
| 485 | 20845 | NR | 615 | 127683 | NR | 745 | 5500 | NR | 875 | 3952 | NR | | | |

REPORT NUMBER: SP1-1908-441-2-R4

Melanopic Flux vs. Wavelength



Melanopic Lumens: 3101.5 M/P: 0.45

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 2397 | NR | 490 | 24908 | NR | 620 | 118784 | NR | 750 | 5037 | NR | 880 | 2677 | NR |
| 365 | 2084 | NR | 495 | 30998 | NR | 625 | 108951 | NR | 755 | 4413 | NR | 885 | 2940 | NR |
| 370 | 2143 | NR | 500 | 37103 | NR | 630 | 99573 | NR | 760 | 4189 | NR | 890 | 3116 | NR |
| 375 | 2413 | NR | 505 | 42987 | NR | 635 | 90444 | NR | 765 | 3677 | NR | 895 | 3345 | NR |
| 380 | 2172 | NR | 510 | 48702 | NR | 640 | 80749 | NR | 770 | 3366 | NR | 900 | 2312 | NR |
| 385 | 1997 | NR | 515 | 53741 | NR | 645 | 71664 | NR | 775 | 3211 | NR | 905 | 2829 | NR |
| 390 | 1830 | NR | 520 | 57283 | NR | 650 | 63936 | NR | 780 | 2682 | NR | 910 | 2783 | NR |
| 395 | 1861 | NR | 525 | 61876 | NR | 655 | 56611 | NR | 785 | 2804 | NR | 915 | 2662 | NR |
| 400 | 1717 | NR | 530 | 65398 | NR | 660 | 49763 | NR | 790 | 2581 | NR | 920 | 3047 | NR |
| 405 | 1761 | NR | 535 | 69597 | NR | 665 | 42891 | NR | 795 | 2711 | NR | 925 | 2256 | NR |
| 410 | 2680 | NR | 540 | 74214 | NR | 670 | 36939 | NR | 800 | 2609 | NR | 930 | 2976 | NR |
| 415 | 4374 | NR | 545 | 79911 | NR | 675 | 31946 | NR | 805 | 2581 | NR | 935 | 3503 | NR |
| 420 | 8071 | NR | 550 | 86153 | NR | 680 | 27385 | NR | 810 | 2404 | NR | 940 | 4226 | NR |
| 425 | 15169 | NR | 555 | 93952 | NR | 685 | 23504 | NR | 815 | 2556 | NR | 945 | 2930 | NR |
| 430 | 26038 | NR | 560 | 102904 | NR | 690 | 20210 | NR | 820 | 2742 | NR | 950 | 2115 | NR |
| 435 | 41316 | NR | 565 | 112009 | NR | 695 | 17459 | NR | 825 | 2014 | NR | 955 | 2634 | NR |
| 440 | 59674 | NR | 570 | 121662 | NR | 700 | 15207 | NR | 830 | 2488 | NR | 960 | 4200 | NR |
| 445 | 72751 | NR | 575 | 130476 | NR | 705 | 13322 | NR | 835 | 2625 | NR | 965 | 1982 | NR |
| 450 | 65091 | NR | 580 | 137926 | NR | 710 | 11676 | NR | 840 | 2754 | NR | 970 | 3613 | NR |
| 455 | 44894 | NR | 585 | 143406 | NR | 715 | 10626 | NR | 845 | 2708 | NR | 975 | 4034 | NR |
| 460 | 32712 | NR | 590 | 147039 | NR | 720 | 9416 | NR | 850 | 2608 | NR | 980 | 3922 | NR |
| 465 | 25296 | NR | 595 | 147365 | NR | 725 | 8333 | NR | 855 | 2605 | NR | 985 | 1909 | NR |
| 470 | 19318 | NR | 600 | 145800 | NR | 730 | 7134 | NR | 860 | 1765 | NR | 990 | 3617 | NR |
| 475 | 17265 | NR | 605 | 141363 | NR | 735 | 6437 | NR | 865 | 2581 | NR | 995 | 4767 | NR |
| 480 | 18260 | NR | 610 | 134199 | NR | 740 | 5834 | NR | 870 | 3016 | NR | 1000 | 2528 | NR |
| 485 | 20845 | NR | 615 | 127683 | NR | 745 | 5500 | NR | 875 | 3952 | NR | | | |

REPORT NUMBER: SP1-1908-441-2-R4

TM-30-18

Summary

$R_f = 75.7$
 $R_g = 93.9$
 CIE $R_a = 71.8$
 $R_9 = -38.3$



Color Vector Graphics



REPORT NUMBER: SP1-1908-441-2-R4

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)

| | | | |
|------------|------------|------------|------------|
| CES01 = 86 | CES26 = 67 | CES51 = 87 | CES76 = 63 |
| CES02 = 63 | CES27 = 88 | CES52 = 86 | CES77 = 80 |
| CES03 = 31 | CES28 = 87 | CES53 = 78 | CES78 = 67 |
| CES04 = 71 | CES29 = 66 | CES54 = 84 | CES79 = 87 |
| CES05 = 49 | CES30 = 73 | CES55 = 84 | CES80 = 86 |
| CES06 = 51 | CES31 = 70 | CES56 = 75 | CES81 = 71 |
| CES07 = 41 | CES32 = 65 | CES57 = 74 | CES82 = 94 |
| CES08 = 40 | CES33 = 73 | CES58 = 76 | CES83 = 90 |
| CES09 = 29 | CES34 = 79 | CES59 = 85 | CES84 = 89 |
| CES10 = 76 | CES35 = 89 | CES60 = 93 | CES85 = 77 |
| CES11 = 59 | CES36 = 97 | CES61 = 84 | CES86 = 61 |
| CES12 = 65 | CES37 = 87 | CES62 = 91 | CES87 = 78 |
| CES13 = 43 | CES38 = 81 | CES63 = 77 | CES88 = 77 |
| CES14 = 74 | CES39 = 95 | CES64 = 72 | CES89 = 67 |
| CES15 = 71 | CES40 = 92 | CES65 = 68 | CES90 = 76 |
| CES16 = 47 | CES41 = 88 | CES66 = 69 | CES91 = 89 |
| CES17 = 50 | CES42 = 89 | CES67 = 67 | CES92 = 58 |
| CES18 = 56 | CES43 = 79 | CES68 = 72 | CES93 = 74 |
| CES19 = 73 | CES44 = 99 | CES69 = 81 | CES94 = 49 |
| CES20 = 66 | CES45 = 85 | CES70 = 66 | CES95 = 68 |
| CES21 = 87 | CES46 = 80 | CES71 = 67 | CES96 = 76 |
| CES22 = 79 | CES47 = 82 | CES72 = 88 | CES97 = 82 |
| CES23 = 92 | CES48 = 69 | CES73 = 59 | CES98 = 75 |
| CES24 = 91 | CES49 = 80 | CES74 = 95 | CES99 = 62 |
| CES25 = 73 | CES50 = 87 | CES75 = 69 | |



REPORT NUMBER: SP1-1908-441-2-R4

TM-30-18

Color Rendition by Hue-Angle Bin



REPORT NUMBER: SP1-1908-441-2-R4

TM-30-18

Measure Comparisons



(END OF REPORT)