

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: McGRAW-EDISON

Report Number: P636186

Luminaire Tested: GWS-SA3F-730-U-T3-W-GRSBK

Issue Date: 1/10/2023

Test Information

Test Method: LM-79-2019
Report Number: P636186
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2209-782-24)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/10/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: McGRAW-EDISON
Catalog Number: GWS-SA3F-730-U-T3-W-GRSBK
Description: GALLEON WALL SLIM LUMINAIRE. (3) LIGHTSQUARES WITH 16 LEDS EACH AND TYPE III OPTICS W/ FACTORY INSTALLED GLARE SHIELD, BK
Light Source: (48) 3000K CCT, 70 CRI LEDS
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 13749 lumens
Efficiency: N/A
Efficacy: 75.0 lumens/watt
Luminous Opening: Rectangular (W 1.5' x L: 0.5' x H: 0')
IES Classification: Type II - Short
BUG Rating: B3 - U0 - G1


Input Watts (W): 183.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 0
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT



REPORT NUMBER: P636186
 CATALOG NUMBER: GWS-SA3F-730-U-T3-W-GRSBK

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 20 foot mounting height. Maximum calculated value = 8.1 fc
 Type II - Short - N/A

REPORT NUMBER: P636186
CATALOG NUMBER: GWS-SA3F-730-U-T3-W-GRSBK

Luminous Intensity Polar Plot



— Vertical Plane Through 47-Deg Lateral - - - Horizontal Cone Through 57.5-Deg Vertical

REPORT NUMBER: P636186
 CATALOG NUMBER: GWS-SA3F-730-U-T3-W-GRSBK

FLUX DISTRIBUTION:

| | | Downward | Upward | Total |
|--------------------|-----------|----------|--------|---------|
| House Side | Lumens | 2982.8 | 0.0 | 2982.8 |
| | % Fixture | 21.7 | 0.0 | 21.7 |
| Street Side | Lumens | 10766.2 | 0.0 | 10766.2 |
| | % Fixture | 78.3 | 0.0 | 78.3 |
| Total | Lumens | 13749.0 | 0.0 | 13749.0 |
| | % Fixture | 100.0 | 0.0 | 100.0 |

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|---------|-----------|
| 0°-10° | 229.0 | 1.7 |
| 10°-20° | 772.6 | 5.6 |
| 20°-30° | 1434.6 | 10.4 |
| 30°-40° | 2296.5 | 16.7 |
| 40°-50° | 3357.0 | 24.4 |
| 50°-60° | 4143.1 | 30.1 |
| 60°-70° | 1384.4 | 10.1 |
| 70°-80° | 129.0 | 0.9 |
| 80°-90° | 2.7 | 0.0 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-90° | 13749.0 | 100.0 |
| 0°-180° | 13749.0 | 100.0 |

Coefficient of Utilization



REPORT NUMBER: P636186


CATALOG NUMBER: GWS-SA3F-730-U-T3-W-GRSBK

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

| Zone | Lumens | % Fixture | Zone Rating/Lumen Limit | | |
|----------------|--------|-----------|-------------------------|------|---------|
| | | | B | U | G |
| FL (0°-30°) | 1420.9 | 10.3 | | | |
| FM (30°-60°) | 8056.8 | 58.6 | | | |
| FH (60°-80°) | 1286.6 | 9.4 | | | G1/1800 |
| FVH (80°-90°) | 1.8 | 0.0 | | | G0/10 |
| BL (0°-30°) | 1015.3 | 7.4 | B3/2500 | | |
| BM (30°-60°) | 1739.9 | 12.7 | B2/2500 | | |
| BH (60°-80°) | 226.8 | 1.6 | B1/500 | | G1/500 |
| BVH (80°-90°) | 0.9 | 0.0 | | | G0/10 |
| UL (90°-100°) | 0.0 | 0.0 | | U0/0 | |
| UH (100°-180°) | 0.0 | 0.0 | | U0/0 | |

BUG Rating: B3-U0-G1

Type II Short





REPORT NUMBER: P636186

CATALOG NUMBER: GWS-SA3F-730-U-T3-W-GRSBK

CANDELA DISTRIBUTION (FULL):

| | 0° | 5° | 15° | 25° | 35° | 45° | 47° | 55° | 65° | 75° | 85° |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 2301.6 | 2301.6 | 2301.6 | 2301.6 | 2301.6 | 2301.6 | 2301.6 | 2301.6 | 2301.6 | 2301.6 | 2301.6 |
| 2.5° | 2325.5 | 2323.9 | 2322.3 | 2331.9 | 2328.7 | 2327.1 | 2330.3 | 2330.3 | 2330.3 | 2320.8 | 2301.6 |
| 5° | 2381.4 | 2381.4 | 2379.8 | 2389.4 | 2381.4 | 2376.6 | 2378.2 | 2378.2 | 2371.8 | 2354.3 | 2330.3 |
| 7.5° | 2469.2 | 2466.0 | 2462.8 | 2472.4 | 2464.4 | 2462.8 | 2466.0 | 2456.4 | 2445.2 | 2416.5 | 2383.0 |
| 10° | 2595.3 | 2595.3 | 2590.5 | 2600.1 | 2593.7 | 2590.5 | 2590.5 | 2584.1 | 2563.4 | 2518.7 | 2469.2 |
| 12.5° | 2769.3 | 2761.3 | 2750.1 | 2742.1 | 2738.9 | 2737.3 | 2738.9 | 2729.4 | 2707.0 | 2649.6 | 2580.9 |
| 15° | 2959.2 | 2952.8 | 2935.3 | 2922.5 | 2904.9 | 2901.7 | 2911.3 | 2903.3 | 2881.0 | 2802.8 | 2705.4 |
| 17.5° | 3198.6 | 3206.6 | 3161.9 | 3134.8 | 3083.7 | 3080.5 | 3083.7 | 3096.5 | 3080.5 | 2979.9 | 2837.9 |
| 20° | 3402.9 | 3409.3 | 3375.8 | 3356.6 | 3310.3 | 3289.6 | 3296.0 | 3316.7 | 3299.2 | 3181.1 | 2983.1 |
| 22.5° | 3621.6 | 3629.6 | 3594.5 | 3554.5 | 3533.8 | 3533.8 | 3557.7 | 3586.5 | 3562.5 | 3407.7 | 3149.1 |
| 25° | 3883.3 | 3889.7 | 3861.0 | 3808.3 | 3771.6 | 3817.9 | 3853.0 | 3929.6 | 3889.7 | 3679.0 | 3345.5 |
| 27.5° | 4183.4 | 4185.0 | 4143.5 | 4089.2 | 4070.1 | 4156.3 | 4191.4 | 4309.5 | 4293.5 | 3983.9 | 3553.0 |
| 30° | 4504.2 | 4505.8 | 4496.3 | 4459.5 | 4442.0 | 4555.3 | 4603.2 | 4774.0 | 4762.8 | 4362.2 | 3835.5 |
| 32.5° | 4837.8 | 4837.8 | 4855.4 | 4852.2 | 4872.9 | 5058.1 | 5134.7 | 5329.4 | 5318.3 | 4825.1 | 4186.6 |
| 35° | 5173.0 | 5174.6 | 5204.9 | 5281.5 | 5367.7 | 5613.5 | 5714.1 | 5950.3 | 5924.8 | 5378.9 | 4635.1 |
| 37.5° | 5554.5 | 5538.5 | 5580.0 | 5694.9 | 5886.5 | 6170.6 | 6266.3 | 6491.4 | 6462.7 | 5945.5 | 5220.9 |
| 40° | 6014.2 | 5985.4 | 5985.4 | 6119.5 | 6336.6 | 6663.8 | 6745.2 | 6856.9 | 6759.5 | 6403.6 | 5795.5 |
| 42.5° | 6521.7 | 6494.6 | 6459.5 | 6577.6 | 6759.5 | 7014.9 | 7082.0 | 7051.6 | 6971.8 | 6836.2 | 6449.9 |
| 45° | 7035.7 | 6994.2 | 7018.1 | 7089.9 | 7195.3 | 7316.6 | 7342.1 | 7201.7 | 7165.0 | 7203.3 | 6991.0 |
| 47.5° | 7426.7 | 7398.0 | 7457.0 | 7557.6 | 7643.8 | 7661.4 | 7643.8 | 7449.1 | 7445.9 | 7581.5 | 7366.1 |
| 50° | 7557.6 | 7560.8 | 7723.6 | 7943.9 | 8082.7 | 8097.1 | 8073.1 | 7849.7 | 7819.4 | 7859.3 | 7568.8 |
| 52.5° | 7570.4 | 7583.1 | 7821.0 | 8240.7 | 8619.0 | 8791.4 | 8772.2 | 8531.2 | 8234.4 | 8191.3 | 7875.2 |
| 55° | 7262.3 | 7337.3 | 7669.3 | 8282.2 | 9086.7 | 9637.3 | 9701.2 | 9239.9 | 8799.4 | 8762.7 | 8534.4 |
| 57.5° | 5805.1 | 5958.3 | 6358.9 | 7232.0 | 8564.8 | 9725.1 | 9891.1 | 9559.1 | 9133.0 | 8976.5 | 8357.3 |
| 60° | 3470.0 | 3659.9 | 4044.6 | 5115.5 | 6518.5 | 7993.3 | 8279.0 | 8325.3 | 8129.0 | 7677.3 | 6411.6 |
| 62.5° | 1489.2 | 1473.2 | 1947.3 | 2767.7 | 3877.0 | 5080.4 | 5209.7 | 5410.8 | 5581.6 | 5109.2 | 3891.3 |
| 65° | 510.8 | 555.4 | 772.5 | 1248.2 | 1940.9 | 2359.1 | 2474.0 | 2654.3 | 2896.9 | 2391.0 | 1425.3 |
| 67.5° | 316.0 | 335.2 | 445.3 | 737.4 | 1047.1 | 1031.1 | 980.0 | 951.3 | 925.7 | 633.7 | 391.0 |
| 70° | 229.8 | 245.8 | 312.8 | 507.6 | 703.9 | 494.8 | 429.4 | 348.0 | 386.3 | 355.9 | 277.7 |
| 72.5° | 154.8 | 167.6 | 215.5 | 308.1 | 360.7 | 241.0 | 223.5 | 253.8 | 306.5 | 292.1 | 226.6 |
| 75° | 92.6 | 100.6 | 122.9 | 150.0 | 146.8 | 124.5 | 126.1 | 178.8 | 234.6 | 218.7 | 161.2 |
| 77.5° | 63.8 | 67.0 | 81.4 | 97.4 | 71.8 | 38.3 | 35.1 | 49.5 | 79.8 | 79.8 | 54.3 |
| 80° | 16.0 | 20.7 | 20.7 | 12.8 | 11.2 | 9.6 | 9.6 | 14.4 | 22.3 | 16.0 | 8.0 |
| 82.5° | 1.6 | 1.6 | 1.6 | 1.6 | 1.6 | 1.6 | 1.6 | 3.2 | 3.2 | 3.2 | 3.2 |
| 85° | 0.0 | 0.0 | 1.6 | 1.6 | 1.6 | 1.6 | 1.6 | 1.6 | 3.2 | 3.2 | 3.2 |
| 87.5° | 0.0 | 0.0 | 1.6 | 1.6 | 1.6 | 1.6 | 1.6 | 1.6 | 1.6 | 3.2 | 3.2 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P636186

CATALOG NUMBER: GWS-SA3F-730-U-T3-W-GRSBK

CANDELA DISTRIBUTION (continued):

| | 90° | 95° | 105° | 115° | 125° | 135° | 145° | 155° | 165° | 175° | 180° |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 2301.6 | 2301.6 | 2301.6 | 2301.6 | 2301.6 | 2301.6 | 2301.6 | 2301.6 | 2301.6 | 2301.6 | 2301.6 |
| 2.5° | 2312.8 | 2293.6 | 2306.4 | 2303.2 | 2312.8 | 2316.0 | 2301.6 | 2298.4 | 2300.0 | 2280.8 | 2274.5 |
| 5° | 2335.1 | 2312.8 | 2319.2 | 2312.8 | 2323.9 | 2333.5 | 2328.7 | 2335.1 | 2343.1 | 2328.7 | 2322.3 |
| 7.5° | 2383.0 | 2360.7 | 2359.1 | 2349.5 | 2365.4 | 2371.8 | 2370.2 | 2387.8 | 2403.7 | 2394.2 | 2384.6 |
| 10° | 2466.0 | 2435.7 | 2432.5 | 2424.5 | 2429.3 | 2434.1 | 2416.5 | 2419.7 | 2434.1 | 2422.9 | 2418.1 |
| 12.5° | 2568.1 | 2531.4 | 2523.5 | 2504.3 | 2504.3 | 2480.4 | 2442.1 | 2434.1 | 2445.2 | 2437.3 | 2429.3 |
| 15° | 2678.3 | 2628.8 | 2616.0 | 2582.5 | 2550.6 | 2505.9 | 2466.0 | 2456.4 | 2464.4 | 2454.8 | 2448.4 |
| 17.5° | 2801.2 | 2745.3 | 2703.8 | 2644.8 | 2574.5 | 2521.9 | 2477.2 | 2456.4 | 2443.7 | 2424.5 | 2422.9 |
| 20° | 2922.5 | 2849.1 | 2778.8 | 2684.7 | 2592.1 | 2512.3 | 2438.9 | 2384.6 | 2338.3 | 2309.6 | 2298.4 |
| 22.5° | 3062.9 | 2954.4 | 2841.1 | 2708.6 | 2576.1 | 2454.8 | 2325.5 | 2233.0 | 2153.2 | 2126.0 | 2113.3 |
| 25° | 3213.0 | 3072.5 | 2903.3 | 2731.0 | 2521.9 | 2327.1 | 2151.6 | 2014.3 | 1909.0 | 1873.8 | 1859.5 |
| 27.5° | 3379.0 | 3185.8 | 2967.2 | 2726.2 | 2410.1 | 2145.2 | 1912.1 | 1741.4 | 1637.6 | 1605.7 | 1616.9 |
| 30° | 3589.7 | 3332.7 | 3047.0 | 2676.7 | 2242.5 | 1889.8 | 1616.9 | 1473.2 | 1395.0 | 1364.7 | 1366.3 |
| 32.5° | 3870.6 | 3543.4 | 3163.5 | 2571.3 | 2027.1 | 1599.3 | 1359.9 | 1254.5 | 1201.9 | 1162.0 | 1158.8 |
| 35° | 4272.8 | 3864.2 | 3272.0 | 2402.2 | 1765.3 | 1340.7 | 1166.8 | 1083.8 | 1010.3 | 964.1 | 972.0 |
| 37.5° | 4754.8 | 4268.0 | 3331.1 | 2173.9 | 1471.6 | 1139.6 | 1021.5 | 936.9 | 853.9 | 785.3 | 793.3 |
| 40° | 5326.2 | 4796.3 | 3326.3 | 1873.8 | 1203.5 | 1002.4 | 900.2 | 801.2 | 697.5 | 635.3 | 641.6 |
| 42.5° | 5963.1 | 5295.9 | 3222.6 | 1556.2 | 997.6 | 890.6 | 783.7 | 659.2 | 558.6 | 520.3 | 521.9 |
| 45° | 6515.3 | 5701.3 | 3040.6 | 1227.4 | 839.6 | 782.1 | 662.4 | 534.7 | 490.0 | 462.9 | 461.3 |
| 47.5° | 6923.9 | 5998.2 | 2780.4 | 965.6 | 711.9 | 683.1 | 544.3 | 478.8 | 443.7 | 421.4 | 418.2 |
| 50° | 7152.2 | 6101.9 | 2493.1 | 756.6 | 601.7 | 579.4 | 486.8 | 434.1 | 410.2 | 395.8 | 392.6 |
| 52.5° | 7458.6 | 6226.4 | 2287.2 | 596.9 | 504.4 | 474.0 | 448.5 | 403.8 | 387.9 | 376.7 | 371.9 |
| 55° | 7943.9 | 6467.5 | 2108.5 | 474.0 | 419.8 | 413.4 | 423.0 | 386.3 | 376.7 | 359.1 | 352.7 |
| 57.5° | 7487.4 | 5809.9 | 1637.6 | 367.1 | 354.3 | 378.3 | 408.6 | 368.7 | 344.8 | 328.8 | 322.4 |
| 60° | 5268.8 | 3862.6 | 823.6 | 295.3 | 316.0 | 354.3 | 384.7 | 333.6 | 309.6 | 312.8 | 309.6 |
| 62.5° | 2904.9 | 1932.9 | 370.3 | 247.4 | 274.5 | 312.8 | 328.8 | 288.9 | 272.9 | 300.1 | 304.9 |
| 65° | 949.7 | 657.6 | 213.9 | 191.5 | 217.1 | 255.4 | 284.1 | 274.5 | 271.3 | 303.3 | 312.8 |
| 67.5° | 292.1 | 217.1 | 145.2 | 137.3 | 150.0 | 188.3 | 239.4 | 296.9 | 319.2 | 328.8 | 333.6 |
| 70° | 218.7 | 170.8 | 124.5 | 116.5 | 122.9 | 143.7 | 202.7 | 247.4 | 233.0 | 234.6 | 231.4 |
| 72.5° | 175.6 | 135.7 | 106.9 | 102.2 | 102.2 | 99.0 | 106.9 | 134.1 | 151.6 | 159.6 | 159.6 |
| 75° | 122.9 | 95.8 | 81.4 | 75.0 | 59.1 | 47.9 | 43.1 | 43.1 | 38.3 | 36.7 | 35.1 |
| 77.5° | 41.5 | 35.1 | 31.9 | 25.5 | 17.6 | 14.4 | 12.8 | 11.2 | 8.0 | 4.8 | 3.2 |
| 80° | 6.4 | 4.8 | 3.2 | 3.2 | 3.2 | 1.6 | 1.6 | 1.6 | 0.0 | 0.0 | 0.0 |
| 82.5° | 3.2 | 3.2 | 3.2 | 3.2 | 3.2 | 1.6 | 1.6 | 0.0 | 0.0 | 0.0 | 0.0 |
| 85° | 3.2 | 3.2 | 3.2 | 3.2 | 3.2 | 1.6 | 1.6 | 0.0 | 0.0 | 0.0 | 0.0 |
| 87.5° | 3.2 | 3.2 | 3.2 | 3.2 | 1.6 | 1.6 | 1.6 | 0.0 | 0.0 | 0.0 | 0.0 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



LM-79-2008: Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGRAW-EDISON

Report Number: SP1-1908-441-2-R4

Test Date: 10/03/2019

Luminaire Tested: SA1C-730-U-5WQ

Data in this report applies to families of products SA1C-730-U-5WQ .

Test Information

Test Method: LM-79-2008
 Report Number: SP1-1908-441-2-R4
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 10/28/2024
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: McGRAW-EDISON
 Catalog Number: **SA1C-730-U-5WQ**
 Description: McGRAW EDISON ROADWAY AND AREA LUMINAIRE

THIS IS A REVISION OF SP1-1908-441-2-R3. TO UPDATE THE CATALOG INFORMATION.TESTED IN SITU. (1) 70 CRI, 3000K, 1050MA LIGHTSQUARE WITH 16 LEDS AND TYPE V WIDE OPTICS.

Spectral Parameters

CCT (K): 2993
 CIE u': 0.2508
 CIE v': 0.5215
 Duv: 0.0000
 CIE x: 0.4374
 CIE y: 0.4043
 CIE z: 0.1583
 Peak Wavelength (nm): 593
 Dominant Wavelength (nm): 582
 Purity: 53

| | | | |
|-----------|------|------|-------|
| CRI (Ra): | 71.8 | | |
| R1: | 67.5 | R9: | -38.3 |
| R2: | 82.9 | R10: | 62.5 |
| R3: | 94.7 | R11: | 63.7 |
| R4: | 67.7 | R12: | 57.8 |
| R5: | 67.9 | R13: | 70.4 |
| R6: | 77.6 | R14: | 97.3 |
| R7: | 76.0 | | |
| R8: | 40.5 | | |

Rf: 75.7
 Rg: 93.9



Test Conditions

Stabilization Time: 53M
 Operation Time: 12H
 Room Temperature (°C) / RH%: 25.0./44%
 Sphere Temperature (°C): 25.7

REPORT NUMBER: SP1-1908-441-2-R4

| Measurement and Test Equipment | | | |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument | Identification Number | Calibration Date | Calibration Due Date |
| Photometer | IN0058 | 6/28/2019 | 12/28/2019 |
| Power Meter | IN0071 | 12/5/2018 | 12/5/2019 |
| AC Power Source | IN0063 | 12/5/2018 | 12/5/2019 |
| DC Power Source | IN0208 | 12/5/2018 | 12/5/2019 |
| Sphere Thermometer | IN0085 | 12/5/2018 | 12/5/2019 |
| Room Thermometer | IN0046 | 12/5/2018 | 12/5/2019 |

REPORT NUMBER: SP1-1908-441-2-R4

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 3000K 4-step quadrangle

REPORT NUMBER: SP1-1908-441-2-R4

Photopic Flux vs. Wavelength



#####

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 2397 | NR | 490 | 24908 | NR | 620 | 118784 | NR | 750 | 5037 | NR | 880 | 2677 | NR |
| 365 | 2084 | NR | 495 | 30998 | NR | 625 | 108951 | NR | 755 | 4413 | NR | 885 | 2940 | NR |
| 370 | 2143 | NR | 500 | 37103 | NR | 630 | 99573 | NR | 760 | 4189 | NR | 890 | 3116 | NR |
| 375 | 2413 | NR | 505 | 42987 | NR | 635 | 90444 | NR | 765 | 3677 | NR | 895 | 3345 | NR |
| 380 | 2172 | NR | 510 | 48702 | NR | 640 | 80749 | NR | 770 | 3366 | NR | 900 | 2312 | NR |
| 385 | 1997 | NR | 515 | 53741 | NR | 645 | 71664 | NR | 775 | 3211 | NR | 905 | 2829 | NR |
| 390 | 1830 | NR | 520 | 57283 | NR | 650 | 63936 | NR | 780 | 2682 | NR | 910 | 2783 | NR |
| 395 | 1861 | NR | 525 | 61876 | NR | 655 | 56611 | NR | 785 | 2804 | NR | 915 | 2662 | NR |
| 400 | 1717 | NR | 530 | 65398 | NR | 660 | 49763 | NR | 790 | 2581 | NR | 920 | 3047 | NR |
| 405 | 1761 | NR | 535 | 69597 | NR | 665 | 42891 | NR | 795 | 2711 | NR | 925 | 2256 | NR |
| 410 | 2680 | NR | 540 | 74214 | NR | 670 | 36939 | NR | 800 | 2609 | NR | 930 | 2976 | NR |
| 415 | 4374 | NR | 545 | 79911 | NR | 675 | 31946 | NR | 805 | 2581 | NR | 935 | 3503 | NR |
| 420 | 8071 | NR | 550 | 86153 | NR | 680 | 27385 | NR | 810 | 2404 | NR | 940 | 4226 | NR |
| 425 | 15169 | NR | 555 | 93952 | NR | 685 | 23504 | NR | 815 | 2556 | NR | 945 | 2930 | NR |
| 430 | 26038 | NR | 560 | 102904 | NR | 690 | 20210 | NR | 820 | 2742 | NR | 950 | 2115 | NR |
| 435 | 41316 | NR | 565 | 112009 | NR | 695 | 17459 | NR | 825 | 2014 | NR | 955 | 2634 | NR |
| 440 | 59674 | NR | 570 | 121662 | NR | 700 | 15207 | NR | 830 | 2488 | NR | 960 | 4200 | NR |
| 445 | 72751 | NR | 575 | 130476 | NR | 705 | 13322 | NR | 835 | 2625 | NR | 965 | 1982 | NR |
| 450 | 65091 | NR | 580 | 137926 | NR | 710 | 11676 | NR | 840 | 2754 | NR | 970 | 3613 | NR |
| 455 | 44894 | NR | 585 | 143406 | NR | 715 | 10626 | NR | 845 | 2708 | NR | 975 | 4034 | NR |
| 460 | 32712 | NR | 590 | 147039 | NR | 720 | 9416 | NR | 850 | 2608 | NR | 980 | 3922 | NR |
| 465 | 25296 | NR | 595 | 147365 | NR | 725 | 8333 | NR | 855 | 2605 | NR | 985 | 1909 | NR |
| 470 | 19318 | NR | 600 | 145800 | NR | 730 | 7134 | NR | 860 | 1765 | NR | 990 | 3617 | NR |
| 475 | 17265 | NR | 605 | 141363 | NR | 735 | 6437 | NR | 865 | 2581 | NR | 995 | 4767 | NR |
| 480 | 18260 | NR | 610 | 134199 | NR | 740 | 5834 | NR | 870 | 3016 | NR | 1000 | 2528 | NR |
| 485 | 20845 | NR | 615 | 127683 | NR | 745 | 5500 | NR | 875 | 3952 | NR | | | |

REPORT NUMBER: SP1-1908-441-2-R4

Scotopic Flux vs. Wavelength



Scotopic Lumens: 8494.8

S/P: 1.23

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 2397 | NR | 490 | 24908 | NR | 620 | 118784 | NR | 750 | 5037 | NR | 880 | 2677 | NR |
| 365 | 2084 | NR | 495 | 30998 | NR | 625 | 108951 | NR | 755 | 4413 | NR | 885 | 2940 | NR |
| 370 | 2143 | NR | 500 | 37103 | NR | 630 | 99573 | NR | 760 | 4189 | NR | 890 | 3116 | NR |
| 375 | 2413 | NR | 505 | 42987 | NR | 635 | 90444 | NR | 765 | 3677 | NR | 895 | 3345 | NR |
| 380 | 2172 | NR | 510 | 48702 | NR | 640 | 80749 | NR | 770 | 3366 | NR | 900 | 2312 | NR |
| 385 | 1997 | NR | 515 | 53741 | NR | 645 | 71664 | NR | 775 | 3211 | NR | 905 | 2829 | NR |
| 390 | 1830 | NR | 520 | 57283 | NR | 650 | 63936 | NR | 780 | 2682 | NR | 910 | 2783 | NR |
| 395 | 1861 | NR | 525 | 61876 | NR | 655 | 56611 | NR | 785 | 2804 | NR | 915 | 2662 | NR |
| 400 | 1717 | NR | 530 | 65398 | NR | 660 | 49763 | NR | 790 | 2581 | NR | 920 | 3047 | NR |
| 405 | 1761 | NR | 535 | 69597 | NR | 665 | 42891 | NR | 795 | 2711 | NR | 925 | 2256 | NR |
| 410 | 2680 | NR | 540 | 74214 | NR | 670 | 36939 | NR | 800 | 2609 | NR | 930 | 2976 | NR |
| 415 | 4374 | NR | 545 | 79911 | NR | 675 | 31946 | NR | 805 | 2581 | NR | 935 | 3503 | NR |
| 420 | 8071 | NR | 550 | 86153 | NR | 680 | 27385 | NR | 810 | 2404 | NR | 940 | 4226 | NR |
| 425 | 15169 | NR | 555 | 93952 | NR | 685 | 23504 | NR | 815 | 2556 | NR | 945 | 2930 | NR |
| 430 | 26038 | NR | 560 | 102904 | NR | 690 | 20210 | NR | 820 | 2742 | NR | 950 | 2115 | NR |
| 435 | 41316 | NR | 565 | 112009 | NR | 695 | 17459 | NR | 825 | 2014 | NR | 955 | 2634 | NR |
| 440 | 59674 | NR | 570 | 121662 | NR | 700 | 15207 | NR | 830 | 2488 | NR | 960 | 4200 | NR |
| 445 | 72751 | NR | 575 | 130476 | NR | 705 | 13322 | NR | 835 | 2625 | NR | 965 | 1982 | NR |
| 450 | 65091 | NR | 580 | 137926 | NR | 710 | 11676 | NR | 840 | 2754 | NR | 970 | 3613 | NR |
| 455 | 44894 | NR | 585 | 143406 | NR | 715 | 10626 | NR | 845 | 2708 | NR | 975 | 4034 | NR |
| 460 | 32712 | NR | 590 | 147039 | NR | 720 | 9416 | NR | 850 | 2608 | NR | 980 | 3922 | NR |
| 465 | 25296 | NR | 595 | 147365 | NR | 725 | 8333 | NR | 855 | 2605 | NR | 985 | 1909 | NR |
| 470 | 19318 | NR | 600 | 145800 | NR | 730 | 7134 | NR | 860 | 1765 | NR | 990 | 3617 | NR |
| 475 | 17265 | NR | 605 | 141363 | NR | 735 | 6437 | NR | 865 | 2581 | NR | 995 | 4767 | NR |
| 480 | 18260 | NR | 610 | 134199 | NR | 740 | 5834 | NR | 870 | 3016 | NR | 1000 | 2528 | NR |
| 485 | 20845 | NR | 615 | 127683 | NR | 745 | 5500 | NR | 875 | 3952 | NR | | | |

REPORT NUMBER: SP1-1908-441-2-R4

Melanopic Flux vs. Wavelength



Melanopic Lumens: 3101.5 M/P: 0.45

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 2397 | NR | 490 | 24908 | NR | 620 | 118784 | NR | 750 | 5037 | NR | 880 | 2677 | NR |
| 365 | 2084 | NR | 495 | 30998 | NR | 625 | 108951 | NR | 755 | 4413 | NR | 885 | 2940 | NR |
| 370 | 2143 | NR | 500 | 37103 | NR | 630 | 99573 | NR | 760 | 4189 | NR | 890 | 3116 | NR |
| 375 | 2413 | NR | 505 | 42987 | NR | 635 | 90444 | NR | 765 | 3677 | NR | 895 | 3345 | NR |
| 380 | 2172 | NR | 510 | 48702 | NR | 640 | 80749 | NR | 770 | 3366 | NR | 900 | 2312 | NR |
| 385 | 1997 | NR | 515 | 53741 | NR | 645 | 71664 | NR | 775 | 3211 | NR | 905 | 2829 | NR |
| 390 | 1830 | NR | 520 | 57283 | NR | 650 | 63936 | NR | 780 | 2682 | NR | 910 | 2783 | NR |
| 395 | 1861 | NR | 525 | 61876 | NR | 655 | 56611 | NR | 785 | 2804 | NR | 915 | 2662 | NR |
| 400 | 1717 | NR | 530 | 65398 | NR | 660 | 49763 | NR | 790 | 2581 | NR | 920 | 3047 | NR |
| 405 | 1761 | NR | 535 | 69597 | NR | 665 | 42891 | NR | 795 | 2711 | NR | 925 | 2256 | NR |
| 410 | 2680 | NR | 540 | 74214 | NR | 670 | 36939 | NR | 800 | 2609 | NR | 930 | 2976 | NR |
| 415 | 4374 | NR | 545 | 79911 | NR | 675 | 31946 | NR | 805 | 2581 | NR | 935 | 3503 | NR |
| 420 | 8071 | NR | 550 | 86153 | NR | 680 | 27385 | NR | 810 | 2404 | NR | 940 | 4226 | NR |
| 425 | 15169 | NR | 555 | 93952 | NR | 685 | 23504 | NR | 815 | 2556 | NR | 945 | 2930 | NR |
| 430 | 26038 | NR | 560 | 102904 | NR | 690 | 20210 | NR | 820 | 2742 | NR | 950 | 2115 | NR |
| 435 | 41316 | NR | 565 | 112009 | NR | 695 | 17459 | NR | 825 | 2014 | NR | 955 | 2634 | NR |
| 440 | 59674 | NR | 570 | 121662 | NR | 700 | 15207 | NR | 830 | 2488 | NR | 960 | 4200 | NR |
| 445 | 72751 | NR | 575 | 130476 | NR | 705 | 13322 | NR | 835 | 2625 | NR | 965 | 1982 | NR |
| 450 | 65091 | NR | 580 | 137926 | NR | 710 | 11676 | NR | 840 | 2754 | NR | 970 | 3613 | NR |
| 455 | 44894 | NR | 585 | 143406 | NR | 715 | 10626 | NR | 845 | 2708 | NR | 975 | 4034 | NR |
| 460 | 32712 | NR | 590 | 147039 | NR | 720 | 9416 | NR | 850 | 2608 | NR | 980 | 3922 | NR |
| 465 | 25296 | NR | 595 | 147365 | NR | 725 | 8333 | NR | 855 | 2605 | NR | 985 | 1909 | NR |
| 470 | 19318 | NR | 600 | 145800 | NR | 730 | 7134 | NR | 860 | 1765 | NR | 990 | 3617 | NR |
| 475 | 17265 | NR | 605 | 141363 | NR | 735 | 6437 | NR | 865 | 2581 | NR | 995 | 4767 | NR |
| 480 | 18260 | NR | 610 | 134199 | NR | 740 | 5834 | NR | 870 | 3016 | NR | 1000 | 2528 | NR |
| 485 | 20845 | NR | 615 | 127683 | NR | 745 | 5500 | NR | 875 | 3952 | NR | | | |

REPORT NUMBER: SP1-1908-441-2-R4

TM-30-18

Summary

$R_f = 75.7$
 $R_g = 93.9$
 CIE $R_a = 71.8$
 $R_9 = -38.3$



Color Vector Graphics



REPORT NUMBER: SP1-1908-441-2-R4

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)

| | | | |
|------------|------------|------------|------------|
| CES01 = 86 | CES26 = 67 | CES51 = 87 | CES76 = 63 |
| CES02 = 63 | CES27 = 88 | CES52 = 86 | CES77 = 80 |
| CES03 = 31 | CES28 = 87 | CES53 = 78 | CES78 = 67 |
| CES04 = 71 | CES29 = 66 | CES54 = 84 | CES79 = 87 |
| CES05 = 49 | CES30 = 73 | CES55 = 84 | CES80 = 86 |
| CES06 = 51 | CES31 = 70 | CES56 = 75 | CES81 = 71 |
| CES07 = 41 | CES32 = 65 | CES57 = 74 | CES82 = 94 |
| CES08 = 40 | CES33 = 73 | CES58 = 76 | CES83 = 90 |
| CES09 = 29 | CES34 = 79 | CES59 = 85 | CES84 = 89 |
| CES10 = 76 | CES35 = 89 | CES60 = 93 | CES85 = 77 |
| CES11 = 59 | CES36 = 97 | CES61 = 84 | CES86 = 61 |
| CES12 = 65 | CES37 = 87 | CES62 = 91 | CES87 = 78 |
| CES13 = 43 | CES38 = 81 | CES63 = 77 | CES88 = 77 |
| CES14 = 74 | CES39 = 95 | CES64 = 72 | CES89 = 67 |
| CES15 = 71 | CES40 = 92 | CES65 = 68 | CES90 = 76 |
| CES16 = 47 | CES41 = 88 | CES66 = 69 | CES91 = 89 |
| CES17 = 50 | CES42 = 89 | CES67 = 67 | CES92 = 58 |
| CES18 = 56 | CES43 = 79 | CES68 = 72 | CES93 = 74 |
| CES19 = 73 | CES44 = 99 | CES69 = 81 | CES94 = 49 |
| CES20 = 66 | CES45 = 85 | CES70 = 66 | CES95 = 68 |
| CES21 = 87 | CES46 = 80 | CES71 = 67 | CES96 = 76 |
| CES22 = 79 | CES47 = 82 | CES72 = 88 | CES97 = 82 |
| CES23 = 92 | CES48 = 69 | CES73 = 59 | CES98 = 75 |
| CES24 = 91 | CES49 = 80 | CES74 = 95 | CES99 = 62 |
| CES25 = 73 | CES50 = 87 | CES75 = 69 | |



REPORT NUMBER: SP1-1908-441-2-R4

TM-30-18

Color Rendition by Hue-Angle Bin



REPORT NUMBER: SP1-1908-441-2-R4

TM-30-18

Measure Comparisons



(END OF REPORT)