

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: McGRAW-EDISON

Report Number: P641106

Luminaire Tested: GWS-SA5F-730-U-RW-W-GRSBK

Issue Date: 1/10/2023

Test Information

Test Method: LM-79-2019
Report Number: P641106
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2209-782-50)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/10/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: McGRAW-EDISON
Catalog Number: GWS-SA5F-730-U-RW-W-GRSBK
Description: GALLEON WALL SLIM LUMINAIRE. (5) LIGHTSQUARES WITH 16 LEDS EACH AND RECTANGULAR WIDE OPTICS W/ FACTORY INSTALLED GLARE SHIELD, BK
Light Source: (80) 3000K CCT, 70 CRI LEDS
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 24633.6 lumens
Efficiency: N/A
Efficacy: 79.4 lumens/watt
Luminous Opening: Rectangular (W 1.5' x L: 1' x H: 0')
IES Classification: Type V - Short
BUG Rating: B5 - U0 - G1


Input Watts (W): 310.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 0
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT



REPORT NUMBER: P641106
 CATALOG NUMBER: GWS-SA5F-730-U-RW-W-GRSBK

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 6.7 fc
 Type V - Short - N/A

REPORT NUMBER: P641106
CATALOG NUMBER: GWS-SA5F-730-U-RW-W-GRSBK

Luminous Intensity Polar Plot



— Vertical Plane Through 43-Deg Lateral - - - Horizontal Cone Through 50-Deg Vertical

REPORT NUMBER: P641106
 CATALOG NUMBER: GWS-SA5F-730-U-RW-W-GRSBK

FLUX DISTRIBUTION:

| | | Downward | Upward | Total |
|--------------------|-----------|----------|--------|---------|
| House Side | Lumens | 12316.5 | 0.0 | 12316.5 |
| | % Fixture | 50.0 | 0.0 | 50.0 |
| Street Side | Lumens | 12317.1 | 0.0 | 12317.1 |
| | % Fixture | 50.0 | 0.0 | 50.0 |
| Total | Lumens | 24633.6 | 0.0 | 24633.6 |
| | % Fixture | 100.0 | 0.0 | 100.0 |

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|---------|-----------|
| 0°-10° | 345.0 | 1.4 |
| 10°-20° | 1187.4 | 4.8 |
| 20°-30° | 2402.3 | 9.8 |
| 30°-40° | 4457.0 | 18.1 |
| 40°-50° | 7398.4 | 30.0 |
| 50°-60° | 7550.4 | 30.7 |
| 60°-70° | 1238.2 | 5.0 |
| 70°-80° | 54.2 | 0.2 |
| 80°-90° | 0.7 | 0.0 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-90° | 24633.6 | 100.0 |
| 0°-180° | 24633.6 | 100.0 |

Coefficient of Utilization



REPORT NUMBER: P641106


CATALOG NUMBER: GWS-SA5F-730-U-RW-W-GRSBK

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

| Zone | Lumens | % Fixture | Zone Rating/Lumen Limit | | |
|----------------|--------|-----------|-------------------------|------|---------|
| | | | B | U | G |
| FL (0°-30°) | 1984.6 | 8.1 | | | |
| FM (30°-60°) | 9726.5 | 39.5 | | | |
| FH (60°-80°) | 605.7 | 2.5 | | | G0/660 |
| FVH (80°-90°) | 0.3 | 0.0 | | | G0/10 |
| BL (0°-30°) | 1950.1 | 7.9 | B3/2500 | | |
| BM (30°-60°) | 9679.3 | 39.3 | B5 | | |
| BH (60°-80°) | 686.7 | 2.8 | B2/1000 | | G1/1800 |
| BVH (80°-90°) | 0.5 | 0.0 | | | G0/10 |
| UL (90°-100°) | 0.0 | 0.0 | | U0/0 | |
| UH (100°-180°) | 0.0 | 0.0 | | U0/0 | |

BUG Rating: B5-U0-G1

Type V Short





REPORT NUMBER: P641106

CATALOG NUMBER: GWS-SA5F-730-U-RW-W-GRSBK

CANDELA DISTRIBUTION (FULL):

| | 0° | 5° | 15° | 25° | 35° | 43° | 45° | 55° | 65° | 75° | 85° |
|-------|--------|--------|---------|---------|---------|---------|---------|---------|--------|--------|--------|
| 0° | 3503.7 | 3503.7 | 3503.7 | 3503.7 | 3503.7 | 3503.7 | 3503.7 | 3503.7 | 3503.7 | 3503.7 | 3503.7 |
| 2.5° | 3438.4 | 3446.5 | 3457.4 | 3468.3 | 3481.9 | 3495.6 | 3503.7 | 3528.3 | 3522.8 | 3544.6 | 3544.6 |
| 5° | 3400.2 | 3408.4 | 3422.0 | 3446.5 | 3476.5 | 3506.5 | 3528.3 | 3577.3 | 3604.5 | 3648.1 | 3664.5 |
| 7.5° | 3419.3 | 3430.2 | 3446.5 | 3484.7 | 3531.0 | 3577.3 | 3601.8 | 3680.8 | 3735.3 | 3817.1 | 3863.4 |
| 10° | 3481.9 | 3492.8 | 3520.1 | 3585.5 | 3645.4 | 3710.8 | 3740.8 | 3841.6 | 3928.8 | 4040.5 | 4105.9 |
| 12.5° | 3552.8 | 3566.4 | 3620.9 | 3719.0 | 3822.5 | 3909.7 | 3950.6 | 4062.3 | 4152.2 | 4277.5 | 4381.0 |
| 15° | 3626.3 | 3648.1 | 3732.6 | 3877.0 | 4024.1 | 4141.3 | 4184.9 | 4304.8 | 4394.7 | 4528.2 | 4645.3 |
| 17.5° | 3798.0 | 3822.5 | 3917.9 | 4073.2 | 4274.8 | 4411.0 | 4449.2 | 4574.5 | 4642.6 | 4732.5 | 4855.1 |
| 20° | 4013.2 | 4059.5 | 4176.7 | 4364.7 | 4585.4 | 4716.2 | 4743.4 | 4866.0 | 4860.6 | 4898.7 | 5005.0 |
| 22.5° | 4280.2 | 4312.9 | 4441.0 | 4664.4 | 4912.3 | 5056.7 | 5119.4 | 5171.1 | 5103.0 | 5070.3 | 5138.5 |
| 25° | 4558.1 | 4596.3 | 4735.2 | 4980.4 | 5258.3 | 5424.5 | 5476.3 | 5517.2 | 5408.2 | 5285.6 | 5293.8 |
| 27.5° | 4917.8 | 4945.0 | 5081.2 | 5342.8 | 5620.7 | 5808.7 | 5855.0 | 5925.8 | 5781.4 | 5585.3 | 5530.8 |
| 30° | 5345.5 | 5372.8 | 5517.2 | 5792.3 | 6067.5 | 6228.3 | 6299.1 | 6386.3 | 6228.3 | 5983.1 | 5920.4 |
| 32.5° | 5846.8 | 5874.1 | 6059.3 | 6342.7 | 6568.8 | 6743.2 | 6811.3 | 6903.9 | 6778.6 | 6503.4 | 6432.6 |
| 35° | 6446.2 | 6462.6 | 6680.5 | 6988.4 | 7228.2 | 7397.1 | 7443.4 | 7552.4 | 7413.4 | 7138.3 | 7100.1 |
| 37.5° | 7141.0 | 7160.1 | 7397.1 | 7754.0 | 7999.2 | 8187.2 | 8260.8 | 8290.7 | 8121.8 | 7813.9 | 7784.0 |
| 40° | 7903.8 | 7966.5 | 8198.1 | 8582.3 | 8857.4 | 9094.5 | 9159.9 | 9059.0 | 8822.0 | 8402.4 | 8347.9 |
| 42.5° | 8699.4 | 8753.9 | 9012.7 | 9429.6 | 9748.4 | 9990.8 | 9993.6 | 9775.6 | 9372.4 | 8792.0 | 8710.3 |
| 45° | 9361.5 | 9383.3 | 9718.4 | 10138.0 | 10530.3 | 10701.9 | 10718.3 | 10323.2 | 9715.7 | 9018.2 | 8843.8 |
| 47.5° | 9816.5 | 9851.9 | 10143.4 | 10546.6 | 10979.8 | 11135.1 | 11102.4 | 10609.3 | 9879.1 | 9165.3 | 8876.5 |
| 50° | 9821.9 | 9881.9 | 10197.9 | 10587.5 | 11007.1 | 11195.1 | 11148.8 | 10691.0 | 9971.8 | 9170.8 | 8797.5 |
| 52.5° | 8952.8 | 9050.9 | 9565.8 | 10129.8 | 10772.8 | 11094.3 | 11105.2 | 10797.3 | 9936.3 | 9083.6 | 8726.7 |
| 55° | 6754.1 | 6860.4 | 7508.8 | 8470.6 | 9712.9 | 10609.3 | 10764.6 | 10672.0 | 9895.5 | 9121.7 | 8852.0 |
| 57.5° | 3574.6 | 3492.8 | 3852.5 | 4806.1 | 6367.2 | 7952.9 | 8407.9 | 9149.0 | 9440.5 | 9168.0 | 9083.6 |
| 60° | 779.2 | 831.0 | 1106.2 | 1490.3 | 2484.8 | 3740.8 | 4184.9 | 5454.5 | 6963.9 | 7634.1 | 8119.1 |
| 62.5° | 335.1 | 329.7 | 343.3 | 389.6 | 569.4 | 948.1 | 1157.9 | 1890.8 | 2983.4 | 4097.7 | 4852.4 |
| 65° | 275.2 | 277.9 | 288.8 | 288.8 | 269.7 | 272.5 | 286.1 | 433.2 | 697.5 | 978.1 | 1313.2 |
| 67.5° | 207.1 | 209.8 | 228.9 | 234.3 | 220.7 | 196.2 | 193.4 | 163.5 | 171.6 | 215.2 | 223.4 |
| 70° | 130.8 | 130.8 | 141.7 | 147.1 | 147.1 | 136.2 | 133.5 | 117.2 | 114.4 | 130.8 | 147.1 |
| 72.5° | 70.8 | 70.8 | 76.3 | 79.0 | 76.3 | 73.6 | 73.6 | 70.8 | 68.1 | 79.0 | 100.8 |
| 75° | 30.0 | 30.0 | 32.7 | 32.7 | 30.0 | 30.0 | 30.0 | 30.0 | 30.0 | 35.4 | 54.5 |
| 77.5° | 5.4 | 8.2 | 10.9 | 8.2 | 5.4 | 5.4 | 5.4 | 8.2 | 8.2 | 10.9 | 16.3 |
| 80° | 2.7 | 2.7 | 5.4 | 2.7 | 0.0 | 0.0 | 0.0 | 0.0 | 2.7 | 2.7 | 2.7 |
| 82.5° | 2.7 | 2.7 | 2.7 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 2.7 |
| 85° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 87.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P641106

CATALOG NUMBER: GWS-SA5F-730-U-RW-W-GRSBK

CANDELA DISTRIBUTION (continued):

| | 90° | 95° | 105° | 115° | 125° | 135° | 145° | 155° | 165° | 175° | 180° |
|-------|--------|--------|--------|--------|---------|---------|---------|---------|---------|--------|--------|
| 0° | 3503.7 | 3503.7 | 3503.7 | 3503.7 | 3503.7 | 3503.7 | 3503.7 | 3503.7 | 3503.7 | 3503.7 | 3503.7 |
| 2.5° | 3563.7 | 3533.7 | 3544.6 | 3550.1 | 3541.9 | 3536.4 | 3506.5 | 3498.3 | 3484.7 | 3462.9 | 3457.4 |
| 5° | 3683.6 | 3659.0 | 3656.3 | 3640.0 | 3601.8 | 3555.5 | 3498.3 | 3473.8 | 3446.5 | 3419.3 | 3413.8 |
| 7.5° | 3885.2 | 3855.2 | 3836.1 | 3781.6 | 3694.5 | 3620.9 | 3525.5 | 3473.8 | 3438.4 | 3402.9 | 3394.8 |
| 10° | 4144.0 | 4108.6 | 4054.1 | 3953.3 | 3836.1 | 3729.9 | 3618.2 | 3550.1 | 3495.6 | 3446.5 | 3443.8 |
| 12.5° | 4419.2 | 4381.0 | 4283.0 | 4154.9 | 4013.2 | 3915.1 | 3773.5 | 3678.1 | 3596.4 | 3522.8 | 3514.6 |
| 15° | 4708.0 | 4661.7 | 4528.2 | 4375.6 | 4244.8 | 4144.0 | 3988.7 | 3836.1 | 3710.8 | 3604.5 | 3593.6 |
| 17.5° | 4928.7 | 4871.5 | 4713.4 | 4599.0 | 4492.7 | 4389.2 | 4214.8 | 4013.2 | 3847.0 | 3719.0 | 3689.0 |
| 20° | 5067.6 | 5013.1 | 4863.3 | 4800.6 | 4751.6 | 4678.0 | 4470.9 | 4261.2 | 4075.9 | 3917.9 | 3890.6 |
| 22.5° | 5201.1 | 5135.7 | 5005.0 | 5005.0 | 5043.1 | 5013.1 | 4789.7 | 4550.0 | 4332.0 | 4149.5 | 4108.6 |
| 25° | 5351.0 | 5299.2 | 5206.6 | 5282.9 | 5378.2 | 5375.5 | 5146.6 | 4846.9 | 4596.3 | 4391.9 | 4351.1 |
| 27.5° | 5568.9 | 5517.2 | 5484.5 | 5628.9 | 5748.7 | 5740.6 | 5489.9 | 5165.7 | 4901.4 | 4699.8 | 4661.7 |
| 30° | 5953.1 | 5904.0 | 5868.6 | 6043.0 | 6195.6 | 6138.4 | 5863.2 | 5549.9 | 5282.9 | 5054.0 | 5026.7 |
| 32.5° | 6465.3 | 6413.5 | 6367.2 | 6541.6 | 6677.8 | 6604.3 | 6342.7 | 6048.4 | 5740.6 | 5517.2 | 5462.7 |
| 35° | 7138.3 | 7029.3 | 6983.0 | 7190.0 | 7247.2 | 7165.5 | 6914.8 | 6656.0 | 6329.1 | 6073.0 | 6037.5 |
| 37.5° | 7833.0 | 7705.0 | 7672.3 | 7852.1 | 7944.7 | 7914.7 | 7620.5 | 7350.8 | 6996.6 | 6713.2 | 6672.4 |
| 40° | 8427.0 | 8309.8 | 8252.6 | 8533.2 | 8743.0 | 8762.1 | 8497.8 | 8168.1 | 7751.3 | 7457.0 | 7383.5 |
| 42.5° | 8775.7 | 8674.9 | 8661.3 | 9097.2 | 9440.5 | 9685.7 | 9369.6 | 9029.1 | 8590.4 | 8258.0 | 8198.1 |
| 45° | 8854.7 | 8789.3 | 8903.7 | 9475.9 | 10009.9 | 10456.7 | 10187.0 | 9827.4 | 9353.3 | 9001.8 | 8944.6 |
| 47.5° | 8846.5 | 8824.7 | 9029.1 | 9672.1 | 10347.7 | 10898.1 | 10764.6 | 10358.6 | 9900.9 | 9533.1 | 9478.6 |
| 50° | 8729.4 | 8732.1 | 9072.7 | 9770.1 | 10484.0 | 11018.0 | 10884.5 | 10508.5 | 10099.8 | 9737.5 | 9693.9 |
| 52.5° | 8683.1 | 8666.7 | 8990.9 | 9740.2 | 10622.9 | 10963.5 | 10663.8 | 10241.5 | 9786.5 | 9339.7 | 9274.3 |
| 55° | 8846.5 | 8805.7 | 9001.8 | 9715.7 | 10639.3 | 10933.5 | 10143.4 | 9228.0 | 8296.2 | 7767.6 | 7724.0 |
| 57.5° | 9091.7 | 9048.1 | 9140.8 | 9535.8 | 9786.5 | 9091.7 | 7465.2 | 5988.5 | 5029.5 | 4623.5 | 4446.4 |
| 60° | 8119.1 | 8089.1 | 8018.3 | 7541.5 | 6468.0 | 4879.6 | 3323.9 | 2119.7 | 1523.0 | 1231.5 | 1231.5 |
| 62.5° | 5037.6 | 4996.8 | 4612.6 | 3427.5 | 2490.2 | 1441.3 | 792.8 | 495.9 | 376.0 | 351.5 | 348.7 |
| 65° | 1414.0 | 1405.9 | 1163.4 | 822.8 | 523.1 | 324.2 | 286.1 | 291.5 | 286.1 | 277.9 | 275.2 |
| 67.5° | 212.5 | 234.3 | 234.3 | 190.7 | 182.5 | 204.3 | 239.8 | 256.1 | 242.5 | 228.9 | 223.4 |
| 70° | 136.2 | 147.1 | 141.7 | 122.6 | 130.8 | 152.6 | 171.6 | 174.4 | 166.2 | 152.6 | 149.8 |
| 72.5° | 95.4 | 106.3 | 87.2 | 79.0 | 81.7 | 89.9 | 98.1 | 98.1 | 95.4 | 89.9 | 84.5 |
| 75° | 57.2 | 57.2 | 40.9 | 38.1 | 38.1 | 40.9 | 40.9 | 46.3 | 46.3 | 43.6 | 40.9 |
| 77.5° | 19.1 | 21.8 | 13.6 | 10.9 | 10.9 | 10.9 | 13.6 | 16.3 | 16.3 | 13.6 | 10.9 |
| 80° | 2.7 | 5.4 | 2.7 | 2.7 | 2.7 | 2.7 | 2.7 | 2.7 | 5.4 | 5.4 | 2.7 |
| 82.5° | 2.7 | 2.7 | 2.7 | 0.0 | 0.0 | 0.0 | 0.0 | 2.7 | 2.7 | 2.7 | 2.7 |
| 85° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 2.7 | 2.7 |
| 87.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



LM-79-2008: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGRAW-EDISON

Report Number: SP1-1908-441-2-R4

Test Date: 10/03/2019

Luminaire Tested: SA1C-730-U-5WQ

Data in this report applies to families of products SA1C-730-U-5WQ .

Test Information

Test Method: LM-79-2008
 Report Number: SP1-1908-441-2-R4
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 10/28/2024
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: MCGRAW-EDISON
 Catalog Number: **SA1C-730-U-5WQ**
 Description: MCGRAW EDISON ROADWAY AND AREA LUMINAIRE

THIS IS A REVISION OF SP1-1908-441-2-R3. TO UPDATE THE CATALOG INFORMATION.TESTED IN SITU. (1) 70 CRI, 3000K, 1050MA LIGHTSQUARE WITH 16 LEDS AND TYPE V WIDE OPTICS.

Spectral Parameters

CCT (K): 2993
 CIE u': 0.2508
 CIE v': 0.5215
 Duv: 0.0000
 CIE x: 0.4374
 CIE y: 0.4043
 CIE z: 0.1583
 Peak Wavelength (nm): 593
 Dominant Wavelength (nm): 582
 Purity: 53

| | | | |
|-----------|------|------|-------|
| CRI (Ra): | 71.8 | | |
| R1: | 67.5 | R9: | -38.3 |
| R2: | 82.9 | R10: | 62.5 |
| R3: | 94.7 | R11: | 63.7 |
| R4: | 67.7 | R12: | 57.8 |
| R5: | 67.9 | R13: | 70.4 |
| R6: | 77.6 | R14: | 97.3 |
| R7: | 76.0 | | |
| R8: | 40.5 | | |

Rf: 75.7
 Rg: 93.9



Test Conditions

Stabilization Time: 53M
 Operation Time: 12H
 Room Temperature (°C) / RH%: 25.0./44%
 Sphere Temperature (°C): 25.7

REPORT NUMBER: SP1-1908-441-2-R4

| Measurement and Test Equipment | | | |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument | Identification Number | Calibration Date | Calibration Due Date |
| Photometer | IN0058 | 6/28/2019 | 12/28/2019 |
| Power Meter | IN0071 | 12/5/2018 | 12/5/2019 |
| AC Power Source | IN0063 | 12/5/2018 | 12/5/2019 |
| DC Power Source | IN0208 | 12/5/2018 | 12/5/2019 |
| Sphere Thermometer | IN0085 | 12/5/2018 | 12/5/2019 |
| Room Thermometer | IN0046 | 12/5/2018 | 12/5/2019 |

REPORT NUMBER: SP1-1908-441-2-R4

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 3000K 4-step quadrangle

REPORT NUMBER: SP1-1908-441-2-R4

Photopic Flux vs. Wavelength



#####

| λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) |
|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|
| 360 | 2397 | NR | 490 | 24908 | NR | 620 | 118784 | NR | 750 | 5037 | NR | 880 | 2677 | NR |
| 365 | 2084 | NR | 495 | 30998 | NR | 625 | 108951 | NR | 755 | 4413 | NR | 885 | 2940 | NR |
| 370 | 2143 | NR | 500 | 37103 | NR | 630 | 99573 | NR | 760 | 4189 | NR | 890 | 3116 | NR |
| 375 | 2413 | NR | 505 | 42987 | NR | 635 | 90444 | NR | 765 | 3677 | NR | 895 | 3345 | NR |
| 380 | 2172 | NR | 510 | 48702 | NR | 640 | 80749 | NR | 770 | 3366 | NR | 900 | 2312 | NR |
| 385 | 1997 | NR | 515 | 53741 | NR | 645 | 71664 | NR | 775 | 3211 | NR | 905 | 2829 | NR |
| 390 | 1830 | NR | 520 | 57283 | NR | 650 | 63936 | NR | 780 | 2682 | NR | 910 | 2783 | NR |
| 395 | 1861 | NR | 525 | 61876 | NR | 655 | 56611 | NR | 785 | 2804 | NR | 915 | 2662 | NR |
| 400 | 1717 | NR | 530 | 65398 | NR | 660 | 49763 | NR | 790 | 2581 | NR | 920 | 3047 | NR |
| 405 | 1761 | NR | 535 | 69597 | NR | 665 | 42891 | NR | 795 | 2711 | NR | 925 | 2256 | NR |
| 410 | 2680 | NR | 540 | 74214 | NR | 670 | 36939 | NR | 800 | 2609 | NR | 930 | 2976 | NR |
| 415 | 4374 | NR | 545 | 79911 | NR | 675 | 31946 | NR | 805 | 2581 | NR | 935 | 3503 | NR |
| 420 | 8071 | NR | 550 | 86153 | NR | 680 | 27385 | NR | 810 | 2404 | NR | 940 | 4226 | NR |
| 425 | 15169 | NR | 555 | 93952 | NR | 685 | 23504 | NR | 815 | 2556 | NR | 945 | 2930 | NR |
| 430 | 26038 | NR | 560 | 102904 | NR | 690 | 20210 | NR | 820 | 2742 | NR | 950 | 2115 | NR |
| 435 | 41316 | NR | 565 | 112009 | NR | 695 | 17459 | NR | 825 | 2014 | NR | 955 | 2634 | NR |
| 440 | 59674 | NR | 570 | 121662 | NR | 700 | 15207 | NR | 830 | 2488 | NR | 960 | 4200 | NR |
| 445 | 72751 | NR | 575 | 130476 | NR | 705 | 13322 | NR | 835 | 2625 | NR | 965 | 1982 | NR |
| 450 | 65091 | NR | 580 | 137926 | NR | 710 | 11676 | NR | 840 | 2754 | NR | 970 | 3613 | NR |
| 455 | 44894 | NR | 585 | 143406 | NR | 715 | 10626 | NR | 845 | 2708 | NR | 975 | 4034 | NR |
| 460 | 32712 | NR | 590 | 147039 | NR | 720 | 9416 | NR | 850 | 2608 | NR | 980 | 3922 | NR |
| 465 | 25296 | NR | 595 | 147365 | NR | 725 | 8333 | NR | 855 | 2605 | NR | 985 | 1909 | NR |
| 470 | 19318 | NR | 600 | 145800 | NR | 730 | 7134 | NR | 860 | 1765 | NR | 990 | 3617 | NR |
| 475 | 17265 | NR | 605 | 141363 | NR | 735 | 6437 | NR | 865 | 2581 | NR | 995 | 4767 | NR |
| 480 | 18260 | NR | 610 | 134199 | NR | 740 | 5834 | NR | 870 | 3016 | NR | 1000 | 2528 | NR |
| 485 | 20845 | NR | 615 | 127683 | NR | 745 | 5500 | NR | 875 | 3952 | NR | | | |

REPORT NUMBER: SP1-1908-441-2-R4

Scotopic Flux vs. Wavelength



Scotopic Lumens: 8494.8

S/P: 1.23

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 2397 | NR | 490 | 24908 | NR | 620 | 118784 | NR | 750 | 5037 | NR | 880 | 2677 | NR |
| 365 | 2084 | NR | 495 | 30998 | NR | 625 | 108951 | NR | 755 | 4413 | NR | 885 | 2940 | NR |
| 370 | 2143 | NR | 500 | 37103 | NR | 630 | 99573 | NR | 760 | 4189 | NR | 890 | 3116 | NR |
| 375 | 2413 | NR | 505 | 42987 | NR | 635 | 90444 | NR | 765 | 3677 | NR | 895 | 3345 | NR |
| 380 | 2172 | NR | 510 | 48702 | NR | 640 | 80749 | NR | 770 | 3366 | NR | 900 | 2312 | NR |
| 385 | 1997 | NR | 515 | 53741 | NR | 645 | 71664 | NR | 775 | 3211 | NR | 905 | 2829 | NR |
| 390 | 1830 | NR | 520 | 57283 | NR | 650 | 63936 | NR | 780 | 2682 | NR | 910 | 2783 | NR |
| 395 | 1861 | NR | 525 | 61876 | NR | 655 | 56611 | NR | 785 | 2804 | NR | 915 | 2662 | NR |
| 400 | 1717 | NR | 530 | 65398 | NR | 660 | 49763 | NR | 790 | 2581 | NR | 920 | 3047 | NR |
| 405 | 1761 | NR | 535 | 69597 | NR | 665 | 42891 | NR | 795 | 2711 | NR | 925 | 2256 | NR |
| 410 | 2680 | NR | 540 | 74214 | NR | 670 | 36939 | NR | 800 | 2609 | NR | 930 | 2976 | NR |
| 415 | 4374 | NR | 545 | 79911 | NR | 675 | 31946 | NR | 805 | 2581 | NR | 935 | 3503 | NR |
| 420 | 8071 | NR | 550 | 86153 | NR | 680 | 27385 | NR | 810 | 2404 | NR | 940 | 4226 | NR |
| 425 | 15169 | NR | 555 | 93952 | NR | 685 | 23504 | NR | 815 | 2556 | NR | 945 | 2930 | NR |
| 430 | 26038 | NR | 560 | 102904 | NR | 690 | 20210 | NR | 820 | 2742 | NR | 950 | 2115 | NR |
| 435 | 41316 | NR | 565 | 112009 | NR | 695 | 17459 | NR | 825 | 2014 | NR | 955 | 2634 | NR |
| 440 | 59674 | NR | 570 | 121662 | NR | 700 | 15207 | NR | 830 | 2488 | NR | 960 | 4200 | NR |
| 445 | 72751 | NR | 575 | 130476 | NR | 705 | 13322 | NR | 835 | 2625 | NR | 965 | 1982 | NR |
| 450 | 65091 | NR | 580 | 137926 | NR | 710 | 11676 | NR | 840 | 2754 | NR | 970 | 3613 | NR |
| 455 | 44894 | NR | 585 | 143406 | NR | 715 | 10626 | NR | 845 | 2708 | NR | 975 | 4034 | NR |
| 460 | 32712 | NR | 590 | 147039 | NR | 720 | 9416 | NR | 850 | 2608 | NR | 980 | 3922 | NR |
| 465 | 25296 | NR | 595 | 147365 | NR | 725 | 8333 | NR | 855 | 2605 | NR | 985 | 1909 | NR |
| 470 | 19318 | NR | 600 | 145800 | NR | 730 | 7134 | NR | 860 | 1765 | NR | 990 | 3617 | NR |
| 475 | 17265 | NR | 605 | 141363 | NR | 735 | 6437 | NR | 865 | 2581 | NR | 995 | 4767 | NR |
| 480 | 18260 | NR | 610 | 134199 | NR | 740 | 5834 | NR | 870 | 3016 | NR | 1000 | 2528 | NR |
| 485 | 20845 | NR | 615 | 127683 | NR | 745 | 5500 | NR | 875 | 3952 | NR | | | |

REPORT NUMBER: SP1-1908-441-2-R4

Melanopic Flux vs. Wavelength



Melanopic Lumens: 3101.5 M/P: 0.45

| λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) |
|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|
| 360 | 2397 | NR | 490 | 24908 | NR | 620 | 118784 | NR | 750 | 5037 | NR | 880 | 2677 | NR |
| 365 | 2084 | NR | 495 | 30998 | NR | 625 | 108951 | NR | 755 | 4413 | NR | 885 | 2940 | NR |
| 370 | 2143 | NR | 500 | 37103 | NR | 630 | 99573 | NR | 760 | 4189 | NR | 890 | 3116 | NR |
| 375 | 2413 | NR | 505 | 42987 | NR | 635 | 90444 | NR | 765 | 3677 | NR | 895 | 3345 | NR |
| 380 | 2172 | NR | 510 | 48702 | NR | 640 | 80749 | NR | 770 | 3366 | NR | 900 | 2312 | NR |
| 385 | 1997 | NR | 515 | 53741 | NR | 645 | 71664 | NR | 775 | 3211 | NR | 905 | 2829 | NR |
| 390 | 1830 | NR | 520 | 57283 | NR | 650 | 63936 | NR | 780 | 2682 | NR | 910 | 2783 | NR |
| 395 | 1861 | NR | 525 | 61876 | NR | 655 | 56611 | NR | 785 | 2804 | NR | 915 | 2662 | NR |
| 400 | 1717 | NR | 530 | 65398 | NR | 660 | 49763 | NR | 790 | 2581 | NR | 920 | 3047 | NR |
| 405 | 1761 | NR | 535 | 69597 | NR | 665 | 42891 | NR | 795 | 2711 | NR | 925 | 2256 | NR |
| 410 | 2680 | NR | 540 | 74214 | NR | 670 | 36939 | NR | 800 | 2609 | NR | 930 | 2976 | NR |
| 415 | 4374 | NR | 545 | 79911 | NR | 675 | 31946 | NR | 805 | 2581 | NR | 935 | 3503 | NR |
| 420 | 8071 | NR | 550 | 86153 | NR | 680 | 27385 | NR | 810 | 2404 | NR | 940 | 4226 | NR |
| 425 | 15169 | NR | 555 | 93952 | NR | 685 | 23504 | NR | 815 | 2556 | NR | 945 | 2930 | NR |
| 430 | 26038 | NR | 560 | 102904 | NR | 690 | 20210 | NR | 820 | 2742 | NR | 950 | 2115 | NR |
| 435 | 41316 | NR | 565 | 112009 | NR | 695 | 17459 | NR | 825 | 2014 | NR | 955 | 2634 | NR |
| 440 | 59674 | NR | 570 | 121662 | NR | 700 | 15207 | NR | 830 | 2488 | NR | 960 | 4200 | NR |
| 445 | 72751 | NR | 575 | 130476 | NR | 705 | 13322 | NR | 835 | 2625 | NR | 965 | 1982 | NR |
| 450 | 65091 | NR | 580 | 137926 | NR | 710 | 11676 | NR | 840 | 2754 | NR | 970 | 3613 | NR |
| 455 | 44894 | NR | 585 | 143406 | NR | 715 | 10626 | NR | 845 | 2708 | NR | 975 | 4034 | NR |
| 460 | 32712 | NR | 590 | 147039 | NR | 720 | 9416 | NR | 850 | 2608 | NR | 980 | 3922 | NR |
| 465 | 25296 | NR | 595 | 147365 | NR | 725 | 8333 | NR | 855 | 2605 | NR | 985 | 1909 | NR |
| 470 | 19318 | NR | 600 | 145800 | NR | 730 | 7134 | NR | 860 | 1765 | NR | 990 | 3617 | NR |
| 475 | 17265 | NR | 605 | 141363 | NR | 735 | 6437 | NR | 865 | 2581 | NR | 995 | 4767 | NR |
| 480 | 18260 | NR | 610 | 134199 | NR | 740 | 5834 | NR | 870 | 3016 | NR | 1000 | 2528 | NR |
| 485 | 20845 | NR | 615 | 127683 | NR | 745 | 5500 | NR | 875 | 3952 | NR | | | |

REPORT NUMBER: SP1-1908-441-2-R4

TM-30-18

Summary

$R_f = 75.7$
 $R_g = 93.9$
 CIE $R_a = 71.8$
 $R_9 = -38.3$



Color Vector Graphics



REPORT NUMBER: SP1-1908-441-2-R4

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)

| | | | |
|------------|------------|------------|------------|
| CES01 = 86 | CES26 = 67 | CES51 = 87 | CES76 = 63 |
| CES02 = 63 | CES27 = 88 | CES52 = 86 | CES77 = 80 |
| CES03 = 31 | CES28 = 87 | CES53 = 78 | CES78 = 67 |
| CES04 = 71 | CES29 = 66 | CES54 = 84 | CES79 = 87 |
| CES05 = 49 | CES30 = 73 | CES55 = 84 | CES80 = 86 |
| CES06 = 51 | CES31 = 70 | CES56 = 75 | CES81 = 71 |
| CES07 = 41 | CES32 = 65 | CES57 = 74 | CES82 = 94 |
| CES08 = 40 | CES33 = 73 | CES58 = 76 | CES83 = 90 |
| CES09 = 29 | CES34 = 79 | CES59 = 85 | CES84 = 89 |
| CES10 = 76 | CES35 = 89 | CES60 = 93 | CES85 = 77 |
| CES11 = 59 | CES36 = 97 | CES61 = 84 | CES86 = 61 |
| CES12 = 65 | CES37 = 87 | CES62 = 91 | CES87 = 78 |
| CES13 = 43 | CES38 = 81 | CES63 = 77 | CES88 = 77 |
| CES14 = 74 | CES39 = 95 | CES64 = 72 | CES89 = 67 |
| CES15 = 71 | CES40 = 92 | CES65 = 68 | CES90 = 76 |
| CES16 = 47 | CES41 = 88 | CES66 = 69 | CES91 = 89 |
| CES17 = 50 | CES42 = 89 | CES67 = 67 | CES92 = 58 |
| CES18 = 56 | CES43 = 79 | CES68 = 72 | CES93 = 74 |
| CES19 = 73 | CES44 = 99 | CES69 = 81 | CES94 = 49 |
| CES20 = 66 | CES45 = 85 | CES70 = 66 | CES95 = 68 |
| CES21 = 87 | CES46 = 80 | CES71 = 67 | CES96 = 76 |
| CES22 = 79 | CES47 = 82 | CES72 = 88 | CES97 = 82 |
| CES23 = 92 | CES48 = 69 | CES73 = 59 | CES98 = 75 |
| CES24 = 91 | CES49 = 80 | CES74 = 95 | CES99 = 62 |
| CES25 = 73 | CES50 = 87 | CES75 = 69 | |



REPORT NUMBER: SP1-1908-441-2-R4

TM-30-18

Color Rendition by Hue-Angle Bin



REPORT NUMBER: SP1-1908-441-2-R4

TM-30-18

Measure Comparisons



(END OF REPORT)