

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P386701

Luminaire Tested: **GWC-SA2B-827-U-SLR**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P386701
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1903-205-26)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: MCGRAW-EDISON
Catalog Number: GWC-SA2B-827-U-SLR
Description: GALLEON WALL LUMINAIRE
(2) 80 CRI, 2700K, 800mA LIGHTSQUARES WITH 16 LEDS EACH AND SPILL LIGHT
ELIMINATOR RIGHT OPTICS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7705 lumens
Efficiency: N/A
Efficacy: 90.6 lumens/watt
Luminous Opening: Rectangular (W 1' x L: 0.5' x H: 0')
IES Classification: Type IV - Medium
BUG Rating: B1 - U0 - G3

Input Watts (W): 85
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




REPORT NUMBER: P386701

CATALOG NUMBER: GWC-SA2B-827-U-SLR

Iso-Footcandle Lines of Horizontal Illumination

x Max cd


--- 1/2 Max cd



Based on 10 foot mounting height. Maximum calculated value = 23.5 fc
 Type IV - Medium - N/A

REPORT NUMBER: P386701
CATALOG NUMBER: GWC-SA2B-827-U-SLR

Luminous Intensity Polar Plot



— Vertical Plane Through 345-Deg Lateral - - - Horizontal Cone Through 67.5-Deg Vertical



REPORT NUMBER: P386701

CATALOG NUMBER: GWC-SA2B-827-U-SLR


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	1332.0	0.0	1332.0
	% Fixture	17.3	0.0	17.3
Street Side	Lumens	6373.0	0.0	6373.0
	% Fixture	82.7	0.0	82.7
Total	Lumens	7705.0	0.0	7705.0
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	181.2	2.4
10°-20°	376.3	4.9
20°-30°	535.3	6.9
30°-40°	771.3	10.0
40°-50°	1087.0	14.1
50°-60°	1511.1	19.6
60°-70°	1827.4	23.7
70°-80°	1123.2	14.6
80°-90°	292.3	3.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	7705.0	100.0
0°-180°	7705.0	100.0

Coefficient of Utilization




REPORT NUMBER: P386701

CATALOG NUMBER: GWC-SA2B-827-U-SLR

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	769.4	10.0			
FM (30°-60°)	2785.6	36.2			
FH (60°-80°)	2562.4	33.3			G2/5000
FVH (80°-90°)	255.6	3.3			G3/500
BL (0°-30°)	323.4	4.2	B1/500		
BM (30°-60°)	583.8	7.6	B1/1000		
BH (60°-80°)	388.2	5.0	B1/500		G1/500
BVH (80°-90°)	36.6	0.5			G1/100
UL (90°-100°)	0.0	0.0		U0/0	
UH (100°-180°)	0.0	0.0		U0/0	

BUG Rating: B1-U0-G3
 Type IV Medium





REPORT NUMBER: P386701

CATALOG NUMBER: GWC-SA2B-827-U-SLR

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	2347.4	2347.4	2347.4	2347.4	2347.4	2347.4	2347.4	2347.4	2347.4	2347.4	2347.4
2.5°	2514.7	2492.5	2458.9	2425.3	2400.4	2375.1	2346.5	2317.8	2285.2	2252.2	2232.8
5°	2473.1	2411.5	2331.4	2251.3	2198.3	2145.3	2085.2	2025.2	1965.7	1906.2	1874.2
7.5°	2285.8	2193.4	2089.2	1985.1	1908.1	1830.8	1747.6	1664.1	1590.2	1515.9	1470.0
10°	2101.6	1990.7	1871.1	1751.3	1652.7	1554.1	1470.7	1386.9	1331.1	1275.3	1233.1
12.5°	1969.4	1846.5	1714.9	1583.1	1484.5	1385.9	1333.0	1280.0	1233.8	1187.6	1138.9
15°	1917.0	1778.1	1643.5	1508.5	1418.9	1329.3	1270.4	1211.3	1149.4	1087.1	1027.4
17.5°	1963.2	1800.6	1654.3	1507.9	1390.6	1273.2	1190.9	1108.4	1026.7	945.1	875.8
20°	2107.4	1899.8	1708.5	1516.9	1360.7	1204.5	1094.2	983.6	878.9	774.1	695.6
22.5°	2309.8	2035.0	1785.2	1535.3	1333.6	1131.5	993.2	854.5	730.7	606.9	529.9
25°	2555.6	2214.3	1895.8	1576.9	1322.5	1067.7	897.7	727.6	597.0	466.1	411.3
27.5°	2814.7	2428.1	2033.2	1637.9	1324.3	1010.7	817.3	623.5	505.8	388.1	350.6
30°	3030.6	2672.4	2193.4	1714.0	1331.4	948.8	741.5	534.2	437.1	340.1	315.8
32.5°	3228.1	2842.7	2314.1	1785.2	1339.4	893.4	683.0	472.2	393.1	313.6	293.6
35°	3432.0	2994.0	2398.5	1802.7	1325.6	848.1	642.9	437.7	364.7	291.4	274.5
37.5°	3656.6	3157.6	2479.8	1801.8	1302.1	802.5	611.8	420.8	346.3	271.4	259.1
40°	3907.1	3338.4	2567.9	1797.5	1280.9	764.0	588.7	413.1	336.1	258.8	248.3
42.5°	4152.0	3510.9	2649.9	1788.9	1263.6	738.1	565.9	393.7	326.8	259.7	244.9
45°	4335.9	3661.5	2721.1	1780.3	1250.7	721.2	548.0	374.9	318.2	261.5	242.7
47.5°	4475.4	3812.8	2799.9	1786.7	1249.5	712.2	535.4	358.6	301.9	244.9	237.2
50°	4652.9	3994.6	2914.8	1835.1	1266.4	697.7	520.6	343.2	286.2	229.2	239.7
52.5°	4873.7	4253.9	3092.9	1931.5	1301.8	672.2	497.2	322.2	267.1	211.6	228.0
55°	5198.1	4586.3	3320.5	2054.4	1344.7	634.6	461.8	288.6	241.8	194.7	209.2
57.5°	5489.2	4922.1	3538.9	2155.5	1371.5	587.2	417.1	247.1	213.5	179.9	188.2
60°	5618.9	5095.2	3641.2	2186.9	1355.4	524.0	366.9	209.5	188.5	167.6	166.0
62.5°	5568.4	4985.3	3540.5	2095.7	1277.2	458.7	322.5	186.4	170.7	154.6	151.3
65°	5420.5	4639.6	3258.3	1877.0	1145.0	413.1	294.5	175.9	158.3	140.8	137.1
67.5°	5129.1	4147.7	2858.4	1569.2	977.2	385.1	278.5	171.9	150.6	129.1	124.8
70°	4606.0	3555.6	2397.9	1239.9	804.0	367.8	268.0	168.2	142.3	116.1	112.1
72.5°	3783.2	2850.7	1914.9	978.7	672.2	365.7	266.8	167.9	135.5	103.2	99.5
75°	2708.7	2165.3	1461.7	757.8	550.5	343.2	253.2	163.3	126.3	89.0	85.6
77.5°	1822.8	1498.7	1016.0	532.9	408.5	284.0	212.9	141.7	108.1	74.5	71.2
80°	1170.6	1037.2	680.8	324.4	264.9	205.5	152.2	98.9	78.9	58.5	55.8
82.5°	858.9	772.0	473.2	174.4	147.3	119.8	93.0	66.2	53.9	41.6	40.4
85°	545.9	601.9	348.4	94.9	77.6	60.4	49.9	39.4	31.1	22.8	22.8
87.5°	106.0	146.6	96.4	45.9	33.6	21.3	18.2	14.8	8.3	1.5	1.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P386701
 CATALOG NUMBER: GWC-SA2B-827-U-SLR

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P386701
 CATALOG NUMBER: GWC-SA2B-827-U-SLR

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	2347.4	2347.4	2347.4	2347.4	2347.4	2347.4	2347.4	2347.4	2347.4	2347.4	2347.4
2.5°	2213.1	2191.8	2170.6	2146.5	2122.2	2099.7	2076.9	2052.0	2056.6	2037.5	2018.4
5°	1842.2	1808.3	1774.1	1744.5	1714.9	1689.4	1663.5	1640.4	1660.4	1646.9	1633.3
7.5°	1423.8	1381.9	1339.7	1304.3	1268.9	1241.5	1213.7	1194.6	1214.4	1211.9	1209.4
10°	1190.9	1150.3	1109.3	1070.2	1031.1	997.8	964.2	935.9	930.9	916.8	902.3
12.5°	1089.9	1034.1	978.1	937.1	896.1	856.4	816.7	783.4	768.3	744.9	721.2
15°	967.6	901.7	835.8	789.2	742.4	703.9	665.1	636.4	626.9	608.7	590.5
17.5°	806.5	734.4	662.3	615.2	567.7	536.9	505.8	486.7	486.7	481.5	476.3
20°	617.0	552.7	488.3	452.2	416.2	399.9	383.2	375.2	377.7	378.0	378.0
22.5°	452.5	413.1	373.7	359.2	344.4	338.6	332.7	329.3	330.5	330.9	331.2
25°	356.4	341.3	325.9	318.5	310.8	307.1	303.4	302.2	305.0	305.3	305.3
27.5°	313.0	303.7	294.2	289.6	284.6	283.1	281.6	279.4	282.2	282.2	281.9
30°	291.1	281.3	271.4	265.5	259.7	260.3	260.6	260.0	261.8	263.1	264.0
32.5°	273.2	263.7	254.1	248.3	242.1	241.2	240.3	239.7	243.7	245.8	248.0
35°	257.2	246.8	236.3	230.7	225.2	223.0	220.9	219.3	223.0	225.8	228.6
37.5°	246.4	235.7	224.6	219.3	213.8	211.0	208.2	206.4	207.9	209.2	210.4
40°	237.8	226.7	215.3	209.2	203.0	200.2	197.5	195.9	196.8	197.2	197.5
42.5°	229.8	219.0	208.2	201.5	194.4	191.0	187.6	185.8	186.4	187.0	187.3
45°	224.0	213.2	202.1	194.1	185.8	182.1	178.4	176.2	176.5	176.5	176.5
47.5°	229.5	213.8	197.8	188.5	179.0	174.7	170.4	168.2	167.6	167.0	166.3
50°	249.8	223.0	195.9	184.2	172.2	167.6	162.7	160.2	158.6	158.0	157.4
52.5°	244.0	220.9	197.5	182.4	167.0	161.4	155.9	151.9	150.3	149.4	148.5
55°	223.3	208.9	194.1	175.9	157.7	152.8	147.6	144.8	142.0	141.4	140.8
57.5°	196.2	190.4	184.5	166.0	147.6	142.9	138.0	136.2	133.7	133.7	133.4
60°	164.2	172.8	181.4	160.2	138.6	133.4	128.2	126.6	125.7	125.4	125.1
62.5°	147.6	161.7	175.6	153.1	130.3	124.8	119.2	117.4	117.1	117.4	117.4
65°	133.4	137.7	142.0	131.5	121.1	115.5	109.7	107.8	108.4	109.4	110.3
67.5°	120.4	119.5	118.6	114.9	110.9	106.3	101.4	99.5	99.8	101.0	102.3
70°	108.1	106.9	105.4	102.6	99.8	95.8	91.8	90.6	90.3	91.8	93.0
72.5°	95.8	94.3	92.4	90.3	87.8	84.4	81.0	80.1	80.4	81.3	82.3
75°	82.3	81.0	79.5	77.6	75.5	72.4	69.3	68.7	69.3	70.2	71.2
77.5°	67.5	67.2	66.5	65.0	63.5	60.1	56.4	56.1	57.0	57.9	58.5
80°	52.7	53.0	53.3	52.1	50.8	47.1	43.1	42.8	43.7	44.7	45.6
82.5°	38.8	39.7	40.4	38.8	37.3	33.0	28.6	28.0	31.1	32.0	33.0
85°	22.5	23.7	25.0	23.7	22.5	18.2	13.9	13.6	16.3	17.9	19.4
87.5°	1.8	2.5	3.1	2.8	2.5	1.2	0.0	0.0	0.3	1.5	2.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P386701
 CATALOG NUMBER: GWC-SA2B-827-U-SLR

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P386701

CATALOG NUMBER: GWC-SA2B-827-U-SLR

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	2347.4	2347.4	2347.4	2347.4	2347.4	2347.4	2347.4	2347.4	2347.4	2347.4	2347.4
2.5°	2006.4	1994.4	1990.7	1987.0	1973.4	1959.5	1973.7	1987.6	1993.4	1999.3	1984.2
5°	1631.5	1629.3	1629.3	1629.0	1616.7	1604.0	1613.6	1622.8	1602.2	1581.6	1579.4
7.5°	1222.7	1235.9	1246.7	1257.2	1253.2	1249.2	1258.1	1267.0	1240.8	1214.4	1201.4
10°	905.4	908.1	919.9	931.6	934.3	936.8	947.9	958.7	938.3	918.0	909.1
12.5°	706.4	691.6	693.1	694.4	699.9	705.1	716.8	728.2	719.9	711.3	712.2
15°	572.1	553.3	545.6	537.6	543.7	549.9	558.2	566.2	566.5	566.5	574.5
17.5°	467.0	457.5	449.8	441.8	450.1	458.1	459.0	459.9	460.2	460.5	459.9
20°	382.6	387.2	384.8	382.3	385.4	388.1	390.6	392.8	390.0	386.9	379.2
22.5°	335.5	339.5	342.6	345.3	350.6	355.5	353.0	350.3	344.7	338.9	333.0
25°	308.1	310.8	313.9	317.0	321.3	325.3	321.0	316.7	312.7	308.7	304.7
27.5°	285.0	287.7	290.5	293.0	297.0	300.7	296.7	292.7	289.3	285.9	282.8
30°	266.2	268.0	270.2	272.3	276.0	279.4	276.0	272.3	269.9	267.1	264.9
32.5°	250.1	252.0	252.9	253.8	257.2	260.6	258.2	255.7	253.5	251.4	249.8
35°	232.6	236.3	236.9	237.5	240.9	244.3	242.7	240.9	238.4	236.0	233.2
37.5°	214.7	219.0	221.5	223.6	227.0	230.4	228.9	227.3	224.0	220.6	215.6
40°	199.6	201.5	206.1	210.4	215.9	221.2	218.1	214.7	209.5	204.2	201.8
42.5°	187.0	186.7	191.0	195.3	203.6	211.6	206.1	200.5	195.6	190.7	190.1
45°	175.9	175.0	177.1	179.3	188.2	196.8	191.3	185.4	182.7	179.9	179.9
47.5°	166.0	165.4	167.0	168.2	173.7	179.0	176.2	173.4	171.9	170.4	170.7
50°	157.1	156.5	158.0	159.3	161.4	163.3	163.9	164.2	163.3	162.3	163.0
52.5°	148.8	148.8	149.4	149.7	152.5	155.3	155.3	155.0	155.0	155.0	155.6
55°	141.7	142.3	142.3	142.3	146.6	150.6	149.4	148.2	148.5	148.5	149.1
57.5°	134.6	135.5	136.2	136.8	141.1	145.4	144.2	142.9	142.9	142.9	143.2
60°	126.6	127.8	129.1	130.3	134.6	138.9	137.7	136.2	136.5	136.8	137.1
62.5°	118.9	120.1	121.4	122.6	126.9	131.2	130.0	128.5	129.4	130.0	130.0
65°	111.5	112.4	113.7	114.9	118.9	122.9	121.7	120.4	121.7	122.6	123.2
67.5°	103.2	103.8	105.0	106.3	110.3	114.3	113.1	111.5	113.1	114.3	115.5
70°	93.6	94.3	95.8	97.0	101.0	105.0	103.5	102.0	103.5	105.0	106.3
72.5°	83.2	83.8	85.3	86.6	91.2	95.8	94.0	92.1	94.0	95.8	96.4
75°	71.8	72.4	74.2	75.8	80.4	85.0	83.5	81.6	83.2	84.7	85.0
77.5°	59.5	60.4	62.8	65.3	69.0	72.7	71.8	70.9	71.8	72.7	72.7
80°	46.5	47.4	50.5	53.3	55.4	57.6	57.9	58.2	58.5	58.8	58.5
82.5°	34.5	35.7	38.5	41.3	41.3	41.3	43.7	45.9	45.9	45.6	45.3
85°	21.3	22.8	25.3	27.7	26.2	24.6	28.6	32.3	32.3	32.0	31.4
87.5°	4.3	5.9	8.3	10.5	8.9	7.4	11.4	15.4	15.7	15.7	15.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P386701
 CATALOG NUMBER: GWC-SA2B-827-U-SLR

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P386701

CATALOG NUMBER: GWC-SA2B-827-U-SLR

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	2347.4	2347.4	2347.4	2347.4	2347.4	2347.4	2347.4	2347.4	2347.4	2347.4	2347.4
2.5°	1968.8	1992.8	2016.5	2022.7	2031.9	2035.9	2039.6	2069.8	2099.7	2134.8	2169.9
5°	1576.9	1594.8	1612.7	1615.4	1625.0	1629.9	1634.8	1671.5	1707.9	1756.8	1805.8
7.5°	1188.5	1192.8	1197.1	1196.5	1204.5	1215.3	1225.8	1264.9	1303.7	1356.4	1408.7
10°	900.1	910.0	919.5	928.5	946.0	966.4	986.4	1026.4	1066.5	1118.5	1170.3
12.5°	713.1	724.5	735.6	745.5	765.8	792.9	819.7	867.8	915.8	978.1	1040.0
15°	582.2	581.3	580.4	587.2	605.0	634.6	663.9	714.7	765.5	833.9	902.0
17.5°	459.3	454.7	450.1	455.3	471.9	496.3	520.3	563.4	606.3	672.5	738.7
20°	371.5	368.4	365.4	370.3	380.8	390.9	401.1	432.2	463.0	516.9	570.5
22.5°	326.8	326.5	325.9	328.7	333.6	338.9	343.8	358.9	373.7	408.5	443.0
25°	300.7	300.4	300.0	301.3	305.3	309.3	313.3	323.2	333.0	349.6	366.3
27.5°	279.7	279.1	278.5	278.8	279.7	285.9	291.7	296.3	300.7	312.1	323.2
30°	262.8	262.5	262.2	262.2	261.2	263.4	265.5	272.6	279.4	291.1	302.8
32.5°	248.3	246.8	245.2	241.8	239.7	242.7	245.8	253.2	260.6	271.4	282.2
35°	230.1	226.1	221.8	220.0	220.3	223.3	226.4	233.8	240.9	252.6	264.0
37.5°	210.4	209.2	207.6	207.3	208.2	211.3	214.4	220.9	227.0	238.7	250.1
40°	199.3	198.7	198.1	197.5	198.1	201.2	204.2	210.4	216.3	227.7	238.7
42.5°	189.5	189.1	188.8	188.8	189.1	192.5	195.9	202.1	207.9	218.1	228.3
45°	179.9	180.2	180.2	180.8	181.8	185.1	188.2	195.0	201.8	211.6	221.5
47.5°	171.0	171.9	172.5	174.1	175.0	178.7	182.1	189.5	196.8	209.2	221.2
50°	163.3	164.2	164.8	166.0	168.5	172.8	177.1	186.1	194.7	215.3	235.7
52.5°	156.2	157.1	158.0	159.3	162.3	167.3	172.2	183.3	194.1	218.1	242.1
55°	149.7	150.6	151.3	153.1	156.2	160.5	164.5	178.1	191.6	209.2	226.7
57.5°	143.6	144.5	145.1	146.3	147.9	152.5	156.8	171.3	185.8	198.1	210.1
60°	137.1	137.7	138.0	138.0	139.2	144.5	149.7	168.2	186.4	184.2	181.8
62.5°	130.0	130.6	130.9	130.0	131.5	137.1	142.6	166.7	190.7	175.9	161.1
65°	123.5	123.2	122.9	122.0	123.8	129.4	134.6	146.6	158.6	152.8	146.9
67.5°	116.4	115.5	114.6	113.4	115.2	120.1	124.8	128.8	132.8	133.4	134.0
70°	107.5	106.3	105.0	104.7	105.7	109.7	113.7	116.4	118.9	120.1	121.1
72.5°	97.0	96.1	95.2	94.6	94.9	98.3	101.4	103.8	106.3	107.2	107.8
75°	85.3	85.3	85.0	83.2	83.2	85.9	88.4	90.6	92.7	94.0	95.2
77.5°	72.7	73.0	73.0	70.5	70.2	73.0	75.5	77.3	78.9	80.1	81.0
80°	58.2	57.6	57.0	55.4	54.8	58.2	61.3	62.8	64.1	64.4	64.4
82.5°	44.7	43.4	41.9	38.5	38.8	42.5	45.9	47.1	48.4	48.4	48.4
85°	30.5	28.0	25.3	22.5	22.8	26.8	30.5	31.7	33.0	33.6	33.9
87.5°	14.5	12.0	9.2	7.1	7.1	10.5	13.6	14.2	14.8	16.0	17.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P386701
 CATALOG NUMBER: GWC-SA2B-827-U-SLR

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P386701

CATALOG NUMBER: GWC-SA2B-827-U-SLR

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	2347.4	2347.4	2347.4	2347.4	2347.4	2347.4	2347.4	2347.4	2347.4	2347.4	2347.4
2.5°	2196.7	2223.2	2250.7	2278.1	2309.5	2340.9	2377.6	2413.9	2445.0	2476.1	2502.0
5°	1848.0	1890.2	1939.8	1989.4	2052.6	2115.7	2193.0	2270.1	2338.8	2407.5	2487.2
7.5°	1463.9	1518.7	1583.4	1648.1	1729.7	1811.4	1911.5	2011.6	2108.6	2205.4	2328.0
10°	1227.9	1285.5	1349.3	1412.7	1495.9	1578.8	1684.8	1790.4	1899.5	2008.2	2146.8
12.5°	1104.1	1167.8	1223.9	1280.0	1347.4	1414.6	1517.2	1619.8	1747.9	1875.7	2009.1
15°	971.9	1041.5	1108.7	1175.8	1249.5	1322.8	1422.6	1522.4	1662.6	1802.7	1956.2
17.5°	812.0	885.4	967.3	1048.9	1145.0	1240.8	1368.7	1496.5	1662.6	1828.3	2009.1
20°	645.4	720.2	818.2	916.2	1035.7	1154.9	1320.6	1486.4	1710.0	1933.4	2164.1
22.5°	509.2	575.1	682.0	788.6	926.6	1064.6	1277.2	1489.4	1781.8	2073.8	2385.3
25°	412.8	459.3	564.4	669.1	828.4	987.6	1250.7	1513.5	1886.2	2258.7	2645.0
27.5°	353.6	384.1	482.1	579.8	753.8	927.6	1239.9	1552.0	2018.7	2485.4	2927.4
30°	324.1	345.3	428.2	510.8	687.6	864.4	1227.0	1589.6	2146.2	2702.6	3148.3
32.5°	299.4	316.4	387.2	457.8	630.3	802.8	1202.0	1601.0	2235.2	2869.5	3335.3
35°	278.5	292.7	354.3	415.9	585.3	754.7	1160.1	1565.5	2291.0	3016.5	3530.0
37.5°	261.5	272.6	329.6	386.6	546.5	706.4	1112.4	1518.4	2340.6	3162.8	3749.0
40°	248.3	257.8	311.1	364.4	509.5	654.6	1071.4	1487.9	2409.0	3330.1	3980.4
42.5°	240.9	253.2	295.1	336.7	474.4	612.1	1038.5	1464.8	2472.5	3479.8	4182.8
45°	239.1	256.6	286.8	317.0	448.2	579.5	1009.2	1438.6	2513.4	3588.2	4335.3
47.5°	236.0	250.4	280.3	310.2	435.3	560.0	993.5	1426.6	2554.4	3681.9	4461.9
50°	237.8	239.7	275.1	310.2	433.4	556.7	1011.3	1466.0	2643.1	3819.9	4606.7
52.5°	234.4	226.4	265.2	304.1	433.1	562.2	1062.8	1563.4	2807.9	4052.2	4763.5
55°	216.6	206.1	246.8	287.4	426.7	565.6	1124.1	1682.3	3029.1	4375.6	5045.3
57.5°	200.9	191.3	225.8	260.0	406.9	553.9	1187.2	1820.3	3262.9	4705.2	5362.9
60°	179.9	177.7	202.4	227.0	376.4	525.5	1239.3	1952.8	3420.0	4887.0	5485.2
62.5°	162.7	163.9	182.1	200.2	338.2	475.9	1256.6	2036.9	3415.7	4794.6	5362.0
65°	149.4	151.6	169.4	187.3	305.6	423.9	1199.9	1975.6	3242.9	4509.9	5118.3
67.5°	136.5	138.9	160.2	181.1	276.6	371.8	1058.2	1744.2	2932.1	4119.6	4808.4
70°	124.1	127.2	150.3	173.4	255.7	337.6	875.5	1413.4	2543.0	3672.3	4449.6
72.5°	110.9	114.0	138.6	163.3	242.4	321.3	713.8	1105.9	2063.7	3021.1	3806.0
75°	97.3	99.5	126.3	152.8	224.3	295.7	560.0	824.0	1579.4	2334.8	2874.8
77.5°	83.8	86.6	109.1	131.2	190.4	249.2	422.0	594.9	1158.9	1722.6	1999.3
80°	66.8	69.3	85.3	101.0	146.9	192.5	290.2	387.8	797.6	1207.3	1363.1
82.5°	51.1	53.9	64.7	75.2	104.7	134.3	175.9	217.5	529.9	841.9	854.9
85°	35.1	36.0	43.7	51.1	64.7	78.2	100.7	123.2	350.6	577.9	481.5
87.5°	17.6	17.6	22.8	28.0	34.8	41.6	53.3	64.7	112.1	159.6	91.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P386701
 CATALOG NUMBER: GWC-SA2B-827-U-SLR

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P386701

CATALOG NUMBER: GWC-SA2B-827-U-SLR

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	2347.4	2347.4	2347.4	2347.4	2347.4	2347.4	2347.4	2347.4	2347.4	2347.4	2347.4
2.5°	2535.0	2557.5	2580.3	2597.5	2615.1	2640.3	2665.6	2670.2	2675.2	2665.3	2655.4
5°	2567.6	2635.7	2704.1	2767.3	2830.4	2868.3	2906.2	2913.9	2921.6	2897.9	2873.8
7.5°	2446.6	2565.2	2683.8	2792.5	2901.3	2967.2	3033.4	3048.2	3063.3	3024.5	2985.7
10°	2284.8	2430.6	2576.3	2719.5	2862.8	2958.6	3054.4	3073.5	3092.6	3044.2	2995.8
12.5°	2159.8	2315.3	2470.9	2621.9	2773.1	2872.3	2971.5	2995.2	3018.9	2983.8	2948.4
15°	2121.3	2267.6	2413.9	2545.5	2677.3	2758.3	2839.7	2849.2	2859.1	2853.5	2848.0
17.5°	2191.2	2323.4	2455.8	2527.3	2599.1	2631.4	2664.1	2674.5	2685.3	2699.2	2713.4
20°	2360.6	2453.7	2547.0	2543.9	2540.5	2524.8	2508.8	2506.0	2503.3	2543.0	2583.0
22.5°	2613.5	2650.5	2687.8	2601.2	2514.7	2462.0	2409.0	2398.5	2387.7	2429.9	2472.5
25°	2888.0	2881.2	2874.2	2709.3	2544.2	2443.8	2343.4	2331.7	2320.0	2356.0	2392.4
27.5°	3159.7	3115.4	3071.0	2847.0	2623.1	2477.4	2331.7	2320.0	2308.3	2340.3	2372.3
30°	3359.0	3287.9	3216.7	2963.2	2709.7	2536.5	2363.4	2344.3	2324.9	2364.3	2403.8
32.5°	3514.6	3419.1	3323.6	3057.4	2791.3	2604.0	2416.7	2386.8	2356.9	2409.6	2462.3
35°	3669.9	3535.6	3400.9	3141.5	2881.9	2683.8	2485.4	2448.7	2412.1	2484.5	2556.9
37.5°	3865.2	3672.3	3479.2	3236.1	2993.1	2803.3	2613.2	2575.7	2538.1	2630.2	2722.6
40°	4077.1	3819.9	3562.7	3339.6	3116.6	2968.7	2820.6	2784.8	2748.8	2860.9	2973.0
42.5°	4253.3	3957.3	3661.2	3464.4	3267.2	3163.1	3058.7	3058.4	3057.8	3171.4	3285.1
45°	4396.6	4071.9	3746.9	3586.1	3425.0	3370.7	3316.5	3360.0	3403.4	3506.0	3608.9
47.5°	4503.5	4168.0	3832.2	3725.3	3618.4	3626.4	3634.4	3722.8	3811.3	3877.2	3943.4
50°	4573.1	4255.2	3936.9	3904.0	3871.0	3942.8	4014.9	4116.2	4217.9	4262.9	4307.8
52.5°	4674.4	4373.5	4072.2	4109.2	4146.1	4292.8	4439.4	4542.0	4644.6	4661.2	4678.1
55°	4908.9	4590.9	4272.7	4343.6	4414.7	4629.8	4845.1	4925.2	5005.3	5011.4	5017.6
57.5°	5241.9	4895.6	4549.4	4625.8	4702.2	4950.4	5199.0	5285.3	5371.9	5359.9	5347.5
60°	5491.1	5184.9	4878.4	4955.4	5032.4	5274.5	5516.7	5615.8	5715.4	5688.9	5662.4
62.5°	5506.5	5342.9	5179.0	5248.6	5318.6	5555.8	5793.0	5894.9	5996.9	5950.7	5904.5
65°	5261.6	5334.9	5408.2	5431.3	5454.4	5675.6	5897.1	5975.0	6053.3	6029.9	6006.5
67.5°	4924.3	5194.4	5464.9	5418.4	5371.9	5475.7	5579.5	5659.9	5740.3	5727.1	5713.5
70°	4587.6	4948.3	5309.0	5080.4	4851.6	4808.7	4765.9	4852.5	4939.4	4885.8	4831.8
72.5°	4014.3	4398.7	4783.5	4362.4	3941.3	3794.9	3648.6	3758.6	3868.6	3783.2	3697.6
75°	3151.1	3575.9	4001.0	3498.6	2996.1	2800.8	2605.5	2700.1	2794.7	2736.1	2677.3
77.5°	2345.8	2764.5	3183.1	2672.4	2161.3	2016.2	1870.8	1898.9	1927.2	1917.3	1907.2
80°	1591.1	1882.8	2174.9	1834.8	1494.7	1505.8	1517.2	1503.9	1490.4	1510.1	1529.8
82.5°	1015.4	1240.5	1466.0	1285.5	1105.0	1208.5	1312.0	1261.2	1210.0	1228.8	1247.9
85°	579.5	799.7	1020.3	951.0	881.3	941.7	1002.4	923.5	844.7	879.2	914.0
87.5°	152.8	442.4	732.2	664.8	597.3	519.1	440.8	336.4	232.0	338.9	445.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P386701
 CATALOG NUMBER: GWC-SA2B-827-U-SLR

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P386701

CATALOG NUMBER: GWC-SA2B-827-U-SLR

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	2347.4	2347.4	2347.4	2347.4	2347.4	2347.4	2347.4
2.5°	2650.2	2645.0	2626.2	2607.1	2578.7	2555.3	2514.7
5°	2840.6	2807.3	2750.0	2692.4	2628.3	2554.7	2473.1
7.5°	2908.0	2830.1	2720.1	2609.8	2510.7	2394.2	2285.8
10°	2879.4	2762.6	2619.7	2476.5	2356.0	2222.0	2101.6
12.5°	2824.6	2700.4	2543.0	2385.3	2248.2	2104.3	1969.4
15°	2749.1	2649.9	2502.3	2354.8	2216.8	2076.9	1917.0
17.5°	2666.5	2619.4	2512.8	2405.9	2286.4	2150.8	1963.2
20°	2600.0	2617.2	2574.7	2532.2	2436.4	2318.1	2107.4
22.5°	2555.0	2637.9	2670.5	2703.5	2645.9	2553.5	2309.8
25°	2529.8	2667.1	2776.5	2886.2	2860.6	2789.4	2555.6
27.5°	2540.8	2709.3	2879.1	3049.1	3072.9	3053.1	2814.7
30°	2574.1	2744.8	2951.5	3158.5	3253.1	3279.6	3030.6
32.5°	2629.6	2796.8	3022.0	3247.5	3390.5	3474.9	3228.1
35°	2713.4	2869.8	3104.6	3339.3	3524.2	3678.2	3432.0
37.5°	2857.2	2991.8	3208.4	3425.3	3664.9	3896.3	3656.6
40°	3067.9	3163.1	3346.1	3529.4	3831.0	4143.3	3907.1
42.5°	3333.8	3382.8	3527.8	3672.9	4004.4	4367.6	4152.0
45°	3621.8	3634.7	3725.9	3817.4	4141.8	4520.4	4335.9
47.5°	3899.1	3854.7	3891.0	3927.4	4247.2	4629.5	4475.4
50°	4184.3	4060.8	4041.7	4022.6	4352.5	4757.9	4652.9
52.5°	4474.5	4270.9	4195.4	4119.6	4478.2	4928.3	4873.7
55°	4758.5	4499.5	4397.8	4296.1	4670.4	5136.2	5198.1
57.5°	5054.0	4760.4	4666.1	4571.8	4952.9	5399.6	5489.2
60°	5371.9	5081.1	5005.6	4929.8	5304.1	5684.2	5618.9
62.5°	5673.5	5442.4	5402.7	5362.6	5659.3	5903.0	5568.4
65°	5874.9	5743.1	5780.0	5817.3	5927.9	5957.5	5420.5
67.5°	5740.3	5767.1	5923.3	6079.8	6003.7	5795.4	5129.1
70°	4992.3	5153.1	5523.1	5893.4	5724.6	5361.4	4606.0
72.5°	3878.1	4058.9	4608.2	5157.8	5002.2	4557.4	3783.2
75°	2881.2	3085.5	3691.7	4298.0	4082.0	3408.9	2708.7
77.5°	2043.9	2180.7	2779.3	3378.1	3026.0	2269.1	1822.8
80°	1487.9	1446.0	1779.6	2113.3	2054.7	1500.8	1170.6
82.5°	1145.7	1043.4	1200.5	1357.6	1349.0	1041.5	858.9
85°	873.0	832.1	971.0	1109.9	991.0	705.4	545.9
87.5°	508.9	572.4	735.9	899.8	675.3	214.1	106.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P386701
 CATALOG NUMBER: GWC-SA2B-827-U-SLR

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245982

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





--- HS — SS

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



u



110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
------	-----	-----	-----	-----	-----	-----	-----	-----	-----	-----	-----

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
------	-----	-----	-----	-----	-----	-----	-----	-----	-----	-----	-----

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
------	-----	-----	-----	-----	-----	-----	-----	-----	-----	-----	-----

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
------	-----	-----	-----	-----	-----	-----	-----	-----	-----	-----	-----

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
------	-----	-----	-----	-----	-----	-----	-----	-----	-----	-----	-----

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
------	-----	-----	-----	-----	-----	-----	-----	-----	-----	-----	-----

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
------	-----	-----	-----	-----	-----	-----	-----

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)