

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P386726

Luminaire Tested: **GWC-SA2B-830-U-SLL-HSS**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P386726  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1903-205-27)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: MCGRAW-EDISON  
Catalog Number: GWC-SA2B-830-U-SLL-HSS  
Description: GALLEON WALL LUMINAIRE  
(2) 80 CRI, 3000K, 800mA LIGHTSQUARES WITH 16 LEDS EACH AND SPILL LIGHT  
ELIMINATOR LEFT OPTICS WITH HOUSE SIDE SHIELD  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 7026 lumens  
Efficiency: N/A  
Efficacy: 82.7 lumens/watt  
Luminous Opening: Rectangular (W 1' x L: 0.5' x H: 0')  
IES Classification: Type III - Medium  
BUG Rating: B1 - U0 - G2


Input Watts (W): 85  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



REPORT NUMBER: P386726  
 CATALOG NUMBER: GWC-SA2B-830-U-SLL-HSS

### Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd  
 - - - 1/2 Max cd



Based on 10 foot mounting height. Maximum calculated value = 30.5 fc  
 Type III - Medium - N/A

REPORT NUMBER: P386726  
CATALOG NUMBER: GWC-SA2B-830-U-SLL-HSS

### Luminous Intensity Polar Plot



— Vertical Plane Through 75-Deg Lateral    - - - Horizontal Cone Through 67.5-Deg Vertical

REPORT NUMBER: P386726

CATALOG NUMBER: GWC-SA2B-830-U-SLL-HSS


**FLUX DISTRIBUTION:**

		Downward	Upward	Total
<b>House Side</b>	Lumens	1054.3	0.0	1054.3
	% Fixture	15.0	0.0	15.0
<b>Street Side</b>	Lumens	5971.7	0.0	5971.7
	% Fixture	85.0	0.0	85.0
<b>Total</b>	Lumens	7026.0	0.0	7026.0
	% Fixture	100.0	0.0	100.0

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	178.8	2.5
10°-20°	352.1	5.0
20°-30°	498.1	7.1
30°-40°	732.3	10.4
40°-50°	1052.5	15.0
50°-60°	1481.7	21.1
60°-70°	1730.5	24.6
70°-80°	882.8	12.6
80°-90°	117.3	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	7026.0	100.0
0°-180°	7026.0	100.0

**Coefficient of Utilization**




REPORT NUMBER: P386726

CATALOG NUMBER: GWC-SA2B-830-U-SLL-HSS

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	753.2	10.7			
FM (30°-60°)	2765.3	39.4			
FH (60°-80°)	2339.5	33.3			G2/5000
FVH (80°-90°)	113.7	1.6			G2/225
BL (0°-30°)	275.7	3.9	B1/500		
BM (30°-60°)	501.2	7.1	B1/1000		
BH (60°-80°)	273.9	3.9	B1/500		G1/500
BVH (80°-90°)	3.6	0.1			G0/10
UL (90°-100°)	0.0	0.0		U0/0	
UH (100°-180°)	0.0	0.0		U0/0	

**BUG Rating: B1-U0-G2**  
 Type III Medium





REPORT NUMBER: P386726

CATALOG NUMBER: GWC-SA2B-830-U-SLL-HSS

**CANDELA DISTRIBUTION (FULL):**

	0°	1°	5°	15°	25°	35°	45°	55°	65°	75°	85°
0°	2357.1	2357.1	2357.1	2357.1	2357.1	2357.1	2357.1	2357.1	2357.1	2357.1	2357.1
2.5°	2555.1	2559.1	2579.8	2627.7	2679.9	2683.9	2719.2	2682.9	2670.6	2612.1	2551.5
5°	2574.4	2589.8	2660.6	2801.4	2923.6	2962.9	2990.8	2919.6	2844.7	2701.6	2548.8
7.5°	2419.0	2444.6	2556.1	2820.4	3038.7	3135.3	3153.6	3042.1	2858.7	2623.0	2393.4
10°	2220.0	2249.3	2383.7	2708.6	3008.5	3173.9	3199.2	3053.1	2789.4	2495.9	2225.3
12.5°	2058.9	2093.2	2230.6	2582.8	2904.3	3087.3	3137.3	3016.1	2729.5	2405.7	2110.5
15°	1984.7	2023.9	2168.4	2501.6	2788.8	2932.9	2974.2	2921.9	2696.3	2391.4	2083.8
17.5°	2027.3	2069.9	2219.0	2508.5	2680.3	2741.9	2775.1	2796.4	2696.3	2477.6	2161.7
20°	2202.0	2247.9	2405.7	2579.4	2590.4	2567.5	2603.1	2678.0	2727.5	2641.3	2348.8
22.5°	2443.6	2497.6	2675.6	2700.9	2546.5	2459.6	2464.3	2581.8	2784.5	2849.0	2608.4
25°	2738.2	2804.1	2985.2	2882.0	2564.8	2395.4	2393.7	2502.5	2840.0	3057.0	2897.6
27.5°	3030.8	3103.3	3262.4	3103.0	2640.3	2383.7	2380.4	2478.6	2894.3	3242.1	3213.5
30°	3276.0	3346.6	3483.7	3263.1	2721.9	2411.0	2395.0	2504.2	2926.6	3362.2	3443.8
32.5°	3475.7	3532.3	3643.2	3373.2	2809.1	2463.9	2429.3	2572.8	2981.5	3463.8	3655.5
35°	3695.4	3755.0	3799.3	3478.1	2906.9	2540.2	2490.6	2681.6	3066.0	3566.9	3887.5
37.5°	3946.0	4005.3	4000.0	3573.9	3031.1	2666.3	2634.7	2854.0	3197.5	3669.1	4146.4
40°	4191.3	4251.9	4208.6	3678.8	3176.9	2874.3	2851.0	3113.0	3373.6	3799.9	4449.9
42.5°	4421.0	4486.5	4394.0	3778.0	3350.6	3136.6	3176.5	3446.5	3593.9	3961.0	4711.5
45°	4606.0	4672.9	4549.5	3874.5	3533.7	3454.8	3574.9	3815.9	3858.8	4097.1	4888.3
47.5°	4740.5	4803.7	4657.3	3971.0	3768.0	3843.9	4053.2	4203.3	4098.1	4215.3	5013.8
50°	4826.4	4875.6	4688.9	4091.8	4075.5	4297.8	4551.5	4624.7	4323.5	4321.8	5166.2
52.5°	4881.0	4903.3	4712.2	4218.0	4396.4	4792.1	5039.4	5062.3	4555.4	4439.0	5371.5
55°	5069.0	5087.0	4877.3	4370.7	4661.6	5225.1	5480.7	5459.4	4818.0	4668.3	5613.8
57.5°	5389.9	5408.8	5218.4	4590.4	4876.3	5492.7	5800.6	5838.8	5125.9	4990.5	5873.5
60°	5550.9	5586.2	5518.3	4868.6	5084.3	5663.8	6018.6	6140.7	5510.7	5415.1	6125.1
62.5°	5404.8	5456.1	5554.6	5177.2	5291.0	5758.0	6086.5	6248.9	5904.7	5910.1	6280.2
65°	5113.3	5154.2	5321.3	5346.3	5410.8	5746.3	5918.7	6097.8	6146.0	6364.7	6271.9
67.5°	4761.1	4776.4	4918.2	5359.6	5237.1	5396.2	5414.8	5547.3	5955.3	6525.8	6019.9
70°	4254.2	4262.6	4386.4	4913.9	4500.5	4535.5	4507.9	4534.8	5119.9	6133.4	5383.9
72.5°	3423.8	3444.8	3620.9	4080.8	3278.7	3177.9	3394.9	3382.9	3943.0	5181.8	3998.6
75°	2520.9	2557.1	2823.1	3287.0	2301.2	2081.5	2239.9	2282.2	2803.1	4008.3	2500.6
77.5°	1765.0	1792.0	2049.6	2416.3	1665.5	1488.4	1431.2	1481.4	1850.2	2899.6	1259.8
80°	1016.8	1026.8	1191.2	1395.2	1122.3	1284.1	1163.2	1197.9	1108.7	1290.0	541.8
82.5°	665.3	667.0	731.2	830.4	698.9	812.1	601.1	768.5	682.0	518.2	176.4
85°	359.5	361.5	424.0	589.4	395.7	223.7	131.5	269.9	421.7	118.8	48.3
87.5°	39.6	36.3	127.8	214.3	109.8	20.3	7.0	30.3	67.6	7.7	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P386726  
 CATALOG NUMBER: GWC-SA2B-830-U-SLL-HSS

**CANDELA DISTRIBUTION (continued):**

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	2357.1	2357.1	2357.1	2357.1	2357.1	2357.1	2357.1	2357.1	2357.1	2357.1	2357.1
2.5°	2520.5	2492.9	2424.0	2351.1	2292.5	2237.6	2182.4	2114.8	2062.5	2051.9	2034.6
5°	2466.6	2379.1	2234.6	2089.5	1972.7	1825.2	1731.7	1658.8	1587.6	1583.3	1569.0
7.5°	2278.2	2163.1	1959.7	1759.0	1594.6	1454.1	1312.3	1217.5	1142.9	1116.6	1101.0
10°	2097.2	1967.7	1713.7	1484.8	1338.0	1213.8	1114.0	1014.8	924.9	863.0	835.1
12.5°	1970.7	1827.6	1547.7	1350.3	1245.1	1127.3	1005.5	881.7	778.2	703.6	658.0
15°	1921.8	1769.0	1492.1	1297.0	1167.2	1018.1	862.4	720.9	606.1	538.5	497.6
17.5°	1980.0	1802.3	1487.8	1232.1	1050.7	865.4	693.3	526.2	418.0	366.8	340.5
20°	2127.8	1908.1	1486.1	1152.6	912.3	684.3	469.6	346.1	280.6	252.0	239.6
22.5°	2336.8	2043.2	1499.4	1074.0	768.2	488.9	324.2	254.3	220.7	205.4	198.4
25°	2605.7	2233.0	1537.0	1002.8	632.7	364.8	252.6	213.0	189.4	177.4	172.4
27.5°	2892.3	2451.3	1595.6	940.9	522.5	290.9	216.3	182.4	165.4	157.1	152.4
30°	3128.6	2704.2	1654.8	872.0	442.7	253.6	198.0	166.4	146.8	141.5	137.1
32.5°	3335.3	2895.6	1696.8	809.8	390.4	225.3	179.1	148.8	135.5	125.1	120.5
35°	3549.3	3055.0	1695.4	766.2	354.5	204.0	163.1	133.1	117.2	105.2	101.5
37.5°	3781.0	3235.1	1666.5	728.9	338.8	187.1	154.1	124.8	108.8	96.9	92.2
40°	4052.2	3424.2	1636.9	694.0	334.5	173.4	147.8	118.2	101.2	89.5	84.9
42.5°	4316.5	3594.6	1610.9	668.0	315.9	173.1	142.1	113.2	95.2	83.9	78.5
45°	4527.8	3753.3	1605.9	652.3	296.2	179.1	139.1	109.8	90.5	79.2	74.2
47.5°	4703.6	3925.7	1637.9	641.4	277.6	163.4	146.4	107.5	86.2	75.2	69.6
50°	4912.6	4137.4	1713.1	623.4	257.9	147.1	167.7	108.2	82.5	71.2	65.2
52.5°	5204.1	4430.3	1823.6	593.1	231.0	132.1	165.1	108.8	78.5	66.9	60.9
55°	5531.0	4796.1	1942.4	542.8	193.4	112.5	141.5	104.2	70.9	62.2	56.6
57.5°	5874.5	5127.9	2013.0	482.9	153.8	97.2	113.2	94.9	62.6	55.9	52.3
60°	5928.4	5254.1	1980.7	409.4	122.1	84.5	83.9	96.5	55.9	49.3	46.6
62.5°	5794.2	5095.6	1824.6	343.8	102.2	74.2	68.9	84.2	50.6	43.9	41.3
65°	5536.3	4667.3	1571.6	309.9	94.9	63.6	57.2	59.2	44.3	38.3	35.9
67.5°	5177.5	4095.5	1290.4	290.6	93.9	54.6	48.9	44.9	38.3	33.3	31.3
70°	4443.9	3411.8	1029.4	279.9	91.2	45.9	41.3	36.6	32.0	28.3	26.6
72.5°	3270.7	2417.7	800.8	268.3	91.9	36.6	35.9	30.3	25.6	22.0	21.3
75°	1889.8	1381.2	525.2	217.3	87.5	28.3	30.0	21.3	18.0	15.3	15.3
77.5°	1007.1	842.4	200.0	90.5	32.0	18.0	17.0	12.6	11.3	9.3	9.0
80°	439.0	370.8	60.2	25.3	17.6	9.7	6.3	5.7	5.0	4.0	3.7
82.5°	155.4	134.1	19.6	12.3	7.7	0.0	0.0	0.0	0.0	0.0	0.0
85°	35.3	25.3	0.0	3.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0





REPORT NUMBER: P386726  
 CATALOG NUMBER: GWC-SA2B-830-U-SLL-HSS

**CANDELA DISTRIBUTION (continued):**

	185°	195°	205°	215°	225°	235°	245°	255°	265°	270°	275°
0°	2357.1	2357.1	2357.1	2357.1	2357.1	2357.1	2357.1	2357.1	2357.1	2357.1	2357.1
2.5°	1999.3	1992.0	1948.7	1950.4	1958.0	1969.0	1943.1	1955.0	1987.3	2018.3	2029.9
5°	1546.0	1547.7	1521.4	1537.7	1552.3	1562.3	1520.4	1521.0	1546.7	1581.6	1599.9
7.5°	1089.4	1086.7	1088.0	1127.0	1154.6	1134.6	1150.3	1096.0	1099.3	1124.3	1105.7
10°	809.8	773.2	752.5	781.8	812.1	801.1	774.2	756.5	768.8	796.5	794.5
12.5°	636.4	583.8	552.8	531.9	556.8	536.2	535.5	520.2	503.6	506.6	550.8
15°	478.6	440.3	403.7	370.1	369.4	362.5	326.8	286.9	283.6	285.6	308.5
17.5°	329.2	316.2	301.2	272.3	264.6	235.3	200.7	184.7	176.7	180.4	188.0
20°	231.3	226.3	228.0	212.3	201.4	173.4	153.1	146.8	145.4	149.1	152.8
22.5°	191.7	182.7	181.7	174.7	163.8	143.4	132.5	128.8	127.1	130.5	133.1
25°	167.7	158.8	155.1	150.8	139.1	125.1	118.5	115.2	113.5	115.5	117.2
27.5°	147.8	139.5	136.1	133.1	121.8	111.8	106.5	103.5	102.2	102.8	104.5
30°	132.8	125.5	121.2	117.5	107.8	100.8	96.2	93.2	91.9	91.9	93.5
32.5°	117.2	113.2	109.2	104.5	95.5	90.9	86.2	82.9	81.5	81.9	83.2
35°	97.5	96.2	97.2	92.9	85.2	81.2	76.6	72.9	71.9	72.2	73.6
37.5°	86.5	80.5	84.2	81.9	77.5	72.2	66.2	62.9	61.2	62.2	62.9
40°	79.5	72.2	69.6	71.9	71.2	62.6	57.2	53.9	52.6	52.9	53.6
42.5°	73.6	64.9	58.9	58.6	62.6	54.6	48.9	45.9	44.3	44.3	44.9
45°	67.9	58.6	51.3	45.6	52.6	46.3	40.9	38.3	36.3	36.3	36.6
47.5°	63.6	53.3	44.6	37.3	39.6	37.9	33.6	31.0	29.0	29.0	29.3
50°	59.6	47.9	38.6	31.3	29.6	31.3	27.3	24.3	23.0	22.6	23.3
52.5°	55.2	42.6	33.0	26.6	23.3	23.6	21.3	19.3	17.6	17.6	18.3
55°	50.9	38.3	28.6	22.6	19.3	17.6	17.0	15.6	14.3	14.3	15.0
57.5°	46.6	33.6	24.3	18.6	15.3	14.0	14.0	13.0	12.0	12.0	12.6
60°	42.6	29.0	20.0	15.3	12.0	11.6	12.0	11.0	10.3	10.3	11.0
62.5°	37.9	24.6	16.3	12.6	9.7	9.3	10.3	9.7	9.0	9.0	9.7
65°	32.3	21.0	13.0	9.7	7.3	7.3	8.7	8.0	7.3	7.3	8.0
67.5°	27.3	17.6	10.0	7.0	5.3	5.7	7.3	6.7	6.3	6.3	7.0
70°	22.6	13.6	7.0	4.3	3.0	4.3	5.7	5.7	5.7	5.7	6.3
72.5°	17.0	9.3	4.0	1.7	1.3	3.0	4.7	5.3	5.0	5.0	6.0
75°	11.0	5.3	1.3	0.0	0.0	1.7	3.7	4.3	4.3	4.0	5.0
77.5°	6.3	1.7	0.0	0.0	0.0	0.0	2.3	2.0	1.7	1.3	2.3
80°	1.7	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P386726  
 CATALOG NUMBER: GWC-SA2B-830-U-SLL-HSS

**CANDELA DISTRIBUTION (continued):**

	285°	295°	305°	315°	325°	335°	345°	355°	359°	360°
0°	2357.1	2357.1	2357.1	2357.1	2357.1	2357.1	2357.1	2357.1	2357.1	2357.1
2.5°	2076.9	2116.1	2171.4	2230.0	2320.2	2391.7	2461.9	2522.2	2545.5	2555.1
5°	1643.8	1701.4	1782.3	1886.1	2048.9	2195.3	2343.8	2493.2	2558.1	2574.4
7.5°	1179.5	1253.1	1355.9	1486.1	1676.8	1866.5	2073.9	2293.2	2393.7	2419.0
10°	873.0	962.9	1080.7	1217.8	1399.9	1594.9	1820.9	2071.5	2186.4	2220.0
12.5°	619.4	740.9	898.6	1065.4	1223.2	1397.2	1625.9	1902.1	2022.6	2058.9
15°	363.8	481.3	668.0	891.3	1093.3	1269.7	1502.1	1815.3	1948.1	1984.7
17.5°	208.7	267.3	408.4	657.3	931.6	1175.9	1463.1	1836.9	1993.3	2027.3
20°	159.4	178.1	235.3	423.4	742.5	1083.7	1463.1	1959.4	2152.1	2202.0
22.5°	139.5	153.1	176.4	252.6	546.5	984.8	1480.1	2136.4	2388.4	2443.6
25°	123.8	136.1	156.1	190.0	372.8	867.4	1520.4	2353.8	2666.6	2738.2
27.5°	110.8	122.5	140.5	166.4	254.9	725.6	1574.6	2608.7	2973.5	3030.8
30°	99.2	110.2	126.5	144.8	196.7	564.8	1620.9	2849.0	3214.5	3276.0
32.5°	88.2	98.2	112.8	126.5	161.1	417.7	1625.9	3039.4	3414.5	3475.7
35°	77.9	86.9	100.2	110.8	133.5	329.8	1548.3	3204.5	3614.5	3695.4
37.5°	67.9	76.6	88.2	96.2	117.5	268.9	1429.8	3388.5	3871.1	3946.0
40°	58.6	66.2	78.2	83.5	111.2	206.7	1301.0	3581.6	4122.8	4191.3
42.5°	49.9	57.2	68.9	79.2	97.5	154.4	1161.9	3762.6	4349.1	4421.0
45°	41.6	49.3	60.9	83.9	80.9	115.5	1013.1	3882.8	4527.8	4606.0
47.5°	33.6	42.3	58.2	79.9	64.6	84.9	895.3	3996.6	4663.3	4740.5
50°	27.0	35.6	65.6	71.2	52.9	64.9	846.1	4098.5	4752.1	4826.4
52.5°	22.0	30.0	61.9	54.6	44.3	53.6	872.7	4263.6	4834.4	4881.0
55°	18.3	23.6	37.3	37.9	37.6	45.6	905.6	4500.5	5047.0	5069.0
57.5°	16.0	19.0	26.0	29.3	31.6	40.6	906.3	4840.7	5376.2	5389.9
60°	13.6	16.6	21.6	23.6	27.3	36.3	873.3	4959.5	5505.7	5550.9
62.5°	12.0	14.6	18.0	19.6	23.0	32.6	796.1	4787.4	5327.9	5404.8
65°	10.7	13.3	15.0	16.6	20.3	29.3	669.0	4443.3	5033.1	5113.3
67.5°	9.3	11.6	13.3	15.0	18.3	26.0	492.6	4043.6	4694.6	4761.1
70°	8.3	10.3	12.0	13.3	16.0	22.0	298.9	3431.1	4226.6	4254.2
72.5°	8.0	9.3	11.0	12.0	14.0	19.3	151.4	2521.5	3378.9	3423.8
75°	7.0	8.3	10.0	10.7	12.3	16.6	61.6	1656.2	2448.6	2520.9
77.5°	5.7	7.7	9.0	9.7	10.7	13.6	31.3	1058.4	1718.4	1765.0
80°	2.0	5.7	7.7	8.0	9.0	10.0	20.6	579.5	996.8	1016.8
82.5°	0.0	3.7	6.0	5.7	6.3	7.7	13.3	275.6	658.0	665.3
85°	0.0	1.7	4.7	3.7	2.7	5.3	4.7	60.2	345.1	359.5
87.5°	0.0	0.0	0.3	1.7	1.3	2.0	0.7	0.3	31.3	39.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245982

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



--- HS — SS

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



u



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)