

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: McGRAW-EDISON

Report Number: P631736

Luminaire Tested: GWS-SA2B-730-U-T3R-W-GRSWH

Issue Date: 1/10/2023

Test Information

Test Method: LM-79-2019
Report Number: P631736
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2209-782-17)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/10/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: McGRAW-EDISON
Catalog Number: GWS-SA2B-730-U-T3R-W-GRSWH
Description: GALLEON WALL SLIM LUMINAIRE. (2) LIGHTSQUARES WITH 16 LEDS EACH AND TYPE III ROADWAY OPTICS W/ FACTORY INSTALLED GLARE SHIELD, WH
Light Source: (32) 3000K CCT, 70 CRI LEDS
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5509.7 lumens
Efficiency: N/A
Efficacy: 118.7 lumens/watt
Luminous Opening: Rectangular (W 1' x L: 0.5' x H: 0')
IES Classification: Type II - Short
BUG Rating: B1 - U0 - G1

Input Watts (W): 46.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 0
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT




REPORT NUMBER: P631736

CATALOG NUMBER: GWS-SA2B-730-U-T3R-W-GRSWH

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 10 foot mounting height. Maximum calculated value = 13.8 fc
 Type II - Short - N/A

REPORT NUMBER: P631736
CATALOG NUMBER: GWS-SA2B-730-U-T3R-W-GRSWH

Luminous Intensity Polar Plot



— Vertical Plane Through 79-Deg Lateral - - - Horizontal Cone Through 57.5-Deg Vertical

REPORT NUMBER: P631736

CATALOG NUMBER: GWS-SA2B-730-U-T3R-W-GRSWH


FLUX DISTRIBUTION:

| | | Downward | Upward | Total |
|--------------------|-----------|----------|--------|--------|
| House Side | Lumens | 1637.8 | 0.0 | 1637.8 |
| | % Fixture | 29.7 | 0.0 | 29.7 |
| Street Side | Lumens | 3871.9 | 0.0 | 3871.9 |
| | % Fixture | 70.3 | 0.0 | 70.3 |
| Total | Lumens | 5509.7 | 0.0 | 5509.7 |
| | % Fixture | 100.0 | 0.0 | 100.0 |

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 126.5 | 2.3 |
| 10°-20° | 351.4 | 6.4 |
| 20°-30° | 595.7 | 10.8 |
| 30°-40° | 911.7 | 16.5 |
| 40°-50° | 1215.7 | 22.1 |
| 50°-60° | 1404.0 | 25.5 |
| 60°-70° | 729.6 | 13.2 |
| 70°-80° | 155.1 | 2.8 |
| 80°-90° | 20.1 | 0.4 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-90° | 5509.7 | 100.0 |
| 0°-180° | 5509.7 | 100.0 |

Coefficient of Utilization



REPORT NUMBER: P631736


CATALOG NUMBER: GWS-SA2B-730-U-T3R-W-GRSWH

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

| Zone | Lumens | % Fixture | Zone Rating/Lumen Limit | | |
|----------------|--------|-----------|-------------------------|------|--------|
| | | | B | U | G |
| FL (0°-30°) | 608.4 | 11.0 | | | |
| FM (30°-60°) | 2662.4 | 48.3 | | | |
| FH (60°-80°) | 594.1 | 10.8 | | | G0/660 |
| FVH (80°-90°) | 7.0 | 0.1 | | | G0/10 |
| BL (0°-30°) | 465.1 | 8.4 | B1/500 | | |
| BM (30°-60°) | 869.0 | 15.8 | B1/1000 | | |
| BH (60°-80°) | 290.6 | 5.3 | B1/500 | | G1/500 |
| BVH (80°-90°) | 13.1 | 0.2 | | | G1/100 |
| UL (90°-100°) | 0.0 | 0.0 | | U0/0 | |
| UH (100°-180°) | 0.0 | 0.0 | | U0/0 | |

BUG Rating: B1-U0-G1

Type II Short





REPORT NUMBER: P631736

CATALOG NUMBER: GWS-SA2B-730-U-T3R-W-GRSWH

CANDELA DISTRIBUTION (FULL):

| | 0° | 5° | 15° | 25° | 35° | 45° | 55° | 65° | 75° | 79° | 85° |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 1365.4 | 1365.4 | 1365.4 | 1365.4 | 1365.4 | 1365.4 | 1365.4 | 1365.4 | 1365.4 | 1365.4 | 1365.4 |
| 2.5° | 1303.3 | 1300.6 | 1301.5 | 1305.1 | 1318.6 | 1328.5 | 1338.9 | 1348.3 | 1357.3 | 1360.0 | 1362.3 |
| 5° | 1256.9 | 1251.9 | 1253.3 | 1259.1 | 1274.9 | 1291.6 | 1310.0 | 1332.5 | 1354.2 | 1361.4 | 1370.8 |
| 7.5° | 1224.0 | 1223.1 | 1225.3 | 1234.3 | 1251.0 | 1266.8 | 1290.6 | 1322.6 | 1360.0 | 1372.2 | 1388.9 |
| 10° | 1180.3 | 1178.5 | 1187.5 | 1206.0 | 1233.4 | 1258.7 | 1287.0 | 1324.9 | 1377.1 | 1395.2 | 1420.8 |
| 12.5° | 1145.6 | 1144.7 | 1154.2 | 1179.8 | 1215.0 | 1255.1 | 1294.3 | 1336.6 | 1400.1 | 1424.9 | 1456.4 |
| 15° | 1165.9 | 1161.8 | 1162.3 | 1180.3 | 1211.8 | 1259.1 | 1312.3 | 1357.8 | 1423.1 | 1454.6 | 1495.2 |
| 17.5° | 1224.9 | 1217.7 | 1212.3 | 1215.4 | 1233.4 | 1282.5 | 1339.8 | 1386.2 | 1449.7 | 1486.6 | 1536.2 |
| 20° | 1306.4 | 1302.4 | 1287.5 | 1277.6 | 1281.6 | 1324.9 | 1383.0 | 1426.2 | 1484.4 | 1525.8 | 1579.0 |
| 22.5° | 1415.9 | 1406.0 | 1385.7 | 1369.9 | 1357.8 | 1391.6 | 1445.2 | 1482.6 | 1532.6 | 1575.8 | 1631.2 |
| 25° | 1551.5 | 1537.1 | 1505.1 | 1480.3 | 1454.2 | 1488.9 | 1536.6 | 1565.0 | 1598.8 | 1638.9 | 1691.6 |
| 27.5° | 1689.8 | 1677.6 | 1642.0 | 1608.7 | 1576.3 | 1597.9 | 1654.6 | 1670.9 | 1667.3 | 1696.5 | 1741.6 |
| 30° | 1837.1 | 1821.8 | 1788.0 | 1752.0 | 1710.1 | 1724.0 | 1774.9 | 1783.0 | 1744.7 | 1769.1 | 1799.7 |
| 32.5° | 1992.5 | 1977.6 | 1948.4 | 1906.5 | 1859.2 | 1864.6 | 1878.5 | 1886.2 | 1849.7 | 1863.7 | 1887.1 |
| 35° | 2150.6 | 2136.7 | 2106.9 | 2065.5 | 2030.8 | 1997.9 | 1962.8 | 1993.4 | 1972.2 | 1999.3 | 1997.5 |
| 37.5° | 2295.2 | 2281.3 | 2262.8 | 2230.8 | 2171.4 | 2106.5 | 2025.4 | 2063.2 | 2096.1 | 2130.4 | 2124.5 |
| 40° | 2393.0 | 2383.5 | 2388.0 | 2383.1 | 2306.5 | 2178.1 | 2056.0 | 2097.5 | 2187.1 | 2245.7 | 2242.5 |
| 42.5° | 2477.2 | 2467.8 | 2493.9 | 2512.8 | 2422.7 | 2244.3 | 2070.9 | 2110.5 | 2245.2 | 2336.7 | 2332.2 |
| 45° | 2514.6 | 2511.9 | 2555.2 | 2615.1 | 2529.0 | 2314.6 | 2109.2 | 2137.6 | 2289.4 | 2406.5 | 2389.4 |
| 47.5° | 2470.0 | 2479.5 | 2564.6 | 2666.0 | 2617.3 | 2398.0 | 2187.6 | 2194.8 | 2347.0 | 2482.2 | 2434.0 |
| 50° | 2381.3 | 2402.0 | 2516.9 | 2667.3 | 2681.8 | 2492.1 | 2296.1 | 2278.1 | 2424.5 | 2562.8 | 2457.4 |
| 52.5° | 2252.0 | 2273.6 | 2461.0 | 2657.0 | 2718.7 | 2601.1 | 2440.7 | 2415.1 | 2522.3 | 2643.5 | 2461.5 |
| 55° | 1955.1 | 1984.4 | 2333.1 | 2633.6 | 2754.7 | 2700.2 | 2603.8 | 2551.6 | 2648.4 | 2754.3 | 2501.6 |
| 57.5° | 1696.1 | 1711.4 | 2021.3 | 2529.5 | 2761.9 | 2773.2 | 2720.1 | 2657.9 | 2773.7 | 2874.1 | 2546.6 |
| 60° | 1244.7 | 1248.3 | 1527.2 | 2093.0 | 2540.8 | 2730.9 | 2710.6 | 2618.2 | 2714.2 | 2778.2 | 2340.3 |
| 62.5° | 703.2 | 703.7 | 926.2 | 1397.0 | 1897.9 | 2225.9 | 2238.5 | 2156.9 | 2076.3 | 2095.2 | 1629.0 |
| 65° | 264.0 | 288.8 | 423.0 | 686.5 | 1094.2 | 1314.1 | 1366.3 | 1385.3 | 1251.0 | 1167.7 | 873.5 |
| 67.5° | 176.6 | 182.4 | 246.9 | 353.2 | 487.0 | 562.2 | 628.9 | 630.7 | 461.3 | 411.3 | 344.2 |
| 70° | 134.7 | 140.6 | 194.2 | 252.7 | 246.9 | 227.9 | 246.4 | 239.7 | 247.8 | 254.5 | 261.7 |
| 72.5° | 100.5 | 106.3 | 150.5 | 178.4 | 148.2 | 146.0 | 165.3 | 183.8 | 200.9 | 208.1 | 219.4 |
| 75° | 66.7 | 71.2 | 101.4 | 95.5 | 82.0 | 96.9 | 120.7 | 139.2 | 149.1 | 157.7 | 166.2 |
| 77.5° | 42.3 | 45.5 | 54.1 | 43.7 | 45.5 | 56.8 | 70.3 | 86.9 | 96.4 | 105.0 | 109.5 |
| 80° | 19.4 | 18.9 | 18.5 | 20.7 | 25.7 | 33.3 | 42.3 | 52.3 | 59.5 | 63.1 | 65.8 |
| 82.5° | 7.7 | 8.6 | 9.5 | 11.3 | 14.0 | 18.0 | 23.9 | 30.6 | 36.5 | 37.4 | 39.6 |
| 85° | 3.2 | 3.6 | 4.1 | 5.0 | 6.3 | 8.1 | 9.9 | 14.0 | 17.6 | 18.9 | 20.3 |
| 87.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.5 | 0.9 | 1.4 | 2.3 | 4.1 | 4.5 | 5.0 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P631736

CATALOG NUMBER: GWS-SA2B-730-U-T3R-W-GRSWH

CANDELA DISTRIBUTION (continued):

| | 90° | 95° | 105° | 115° | 125° | 135° | 145° | 155° | 165° | 175° | 180° |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 1365.4 | 1365.4 | 1365.4 | 1365.4 | 1365.4 | 1365.4 | 1365.4 | 1365.4 | 1365.4 | 1365.4 | 1365.4 |
| 2.5° | 1374.4 | 1368.6 | 1378.5 | 1385.3 | 1391.6 | 1384.8 | 1382.5 | 1376.7 | 1375.8 | 1375.8 | 1378.9 |
| 5° | 1387.1 | 1383.0 | 1393.4 | 1397.4 | 1397.0 | 1382.1 | 1373.1 | 1361.4 | 1355.5 | 1355.5 | 1356.4 |
| 7.5° | 1409.6 | 1407.3 | 1413.2 | 1406.9 | 1392.5 | 1362.3 | 1332.5 | 1307.8 | 1291.1 | 1282.5 | 1285.2 |
| 10° | 1447.0 | 1444.3 | 1439.3 | 1415.9 | 1374.4 | 1311.8 | 1251.0 | 1206.0 | 1178.9 | 1163.6 | 1164.5 |
| 12.5° | 1483.5 | 1479.0 | 1461.4 | 1409.6 | 1324.4 | 1224.9 | 1145.1 | 1094.7 | 1065.0 | 1046.9 | 1042.9 |
| 15° | 1523.6 | 1511.8 | 1474.0 | 1377.1 | 1242.9 | 1118.6 | 1035.2 | 980.7 | 948.7 | 937.9 | 937.5 |
| 17.5° | 1561.8 | 1541.1 | 1472.6 | 1319.5 | 1145.1 | 1007.3 | 923.5 | 889.7 | 884.3 | 889.3 | 890.6 |
| 20° | 1600.6 | 1567.2 | 1457.8 | 1239.7 | 1028.9 | 896.5 | 853.2 | 867.2 | 887.5 | 901.0 | 904.1 |
| 22.5° | 1640.7 | 1588.9 | 1424.0 | 1137.0 | 906.4 | 821.7 | 839.7 | 870.3 | 895.6 | 913.6 | 915.4 |
| 25° | 1685.7 | 1609.1 | 1373.5 | 1011.3 | 808.2 | 801.0 | 836.6 | 869.0 | 896.0 | 916.7 | 920.3 |
| 27.5° | 1711.4 | 1609.6 | 1302.8 | 882.1 | 763.1 | 792.9 | 828.9 | 859.5 | 886.6 | 909.1 | 913.1 |
| 30° | 1736.6 | 1597.4 | 1190.6 | 777.1 | 750.1 | 783.4 | 815.8 | 844.2 | 869.9 | 892.0 | 896.9 |
| 32.5° | 1772.2 | 1586.2 | 1061.4 | 716.7 | 742.4 | 774.4 | 801.0 | 826.2 | 846.0 | 855.9 | 858.6 |
| 35° | 1816.4 | 1571.8 | 924.0 | 690.6 | 737.4 | 767.2 | 790.6 | 804.1 | 778.4 | 773.0 | 778.9 |
| 37.5° | 1878.1 | 1558.2 | 787.0 | 679.3 | 734.3 | 764.5 | 785.2 | 750.5 | 719.0 | 706.4 | 710.9 |
| 40° | 1944.8 | 1550.6 | 694.2 | 670.3 | 735.6 | 767.2 | 762.7 | 711.3 | 665.8 | 639.2 | 638.3 |
| 42.5° | 2001.5 | 1538.9 | 634.7 | 664.5 | 739.3 | 777.5 | 732.0 | 676.6 | 609.1 | 593.3 | 593.7 |
| 45° | 2039.8 | 1509.1 | 603.2 | 658.2 | 742.4 | 779.8 | 717.6 | 628.9 | 580.7 | 570.8 | 570.3 |
| 47.5° | 2055.6 | 1455.1 | 582.9 | 648.3 | 742.0 | 761.3 | 688.3 | 609.1 | 560.9 | 558.2 | 560.0 |
| 50° | 2045.2 | 1366.3 | 562.2 | 628.9 | 731.1 | 742.0 | 654.6 | 591.5 | 547.3 | 562.2 | 573.0 |
| 52.5° | 2006.9 | 1251.5 | 537.4 | 602.3 | 711.8 | 719.9 | 637.4 | 580.7 | 537.4 | 557.3 | 565.8 |
| 55° | 1997.0 | 1158.2 | 505.9 | 567.6 | 682.9 | 680.7 | 619.4 | 575.3 | 530.7 | 523.0 | 524.4 |
| 57.5° | 1984.0 | 1067.2 | 453.6 | 505.4 | 610.0 | 613.6 | 602.3 | 569.0 | 513.1 | 510.9 | 513.1 |
| 60° | 1723.6 | 818.1 | 404.5 | 436.1 | 500.9 | 520.3 | 582.9 | 557.3 | 484.7 | 475.3 | 474.8 |
| 62.5° | 1125.8 | 495.5 | 359.9 | 380.2 | 408.1 | 430.7 | 531.6 | 523.5 | 453.6 | 447.8 | 451.8 |
| 65° | 605.5 | 353.2 | 327.5 | 339.7 | 355.0 | 372.1 | 440.6 | 466.3 | 409.9 | 389.2 | 389.7 |
| 67.5° | 309.5 | 300.5 | 303.2 | 311.7 | 323.5 | 332.0 | 355.4 | 378.0 | 349.6 | 332.0 | 331.6 |
| 70° | 264.9 | 272.1 | 276.1 | 281.1 | 288.8 | 287.4 | 289.7 | 293.7 | 291.5 | 282.9 | 282.5 |
| 72.5° | 225.7 | 237.0 | 237.9 | 238.8 | 241.5 | 235.2 | 231.1 | 224.3 | 224.8 | 226.1 | 226.6 |
| 75° | 171.6 | 182.4 | 185.2 | 183.8 | 186.5 | 178.4 | 173.0 | 166.2 | 158.1 | 156.8 | 157.7 |
| 77.5° | 111.7 | 120.3 | 124.3 | 123.4 | 124.8 | 118.5 | 115.8 | 108.6 | 99.1 | 95.5 | 95.5 |
| 80° | 67.6 | 72.5 | 75.7 | 76.6 | 77.9 | 73.4 | 68.9 | 62.6 | 58.6 | 54.5 | 54.5 |
| 82.5° | 41.0 | 44.1 | 46.4 | 46.4 | 47.8 | 42.8 | 39.2 | 34.7 | 32.9 | 29.3 | 29.3 |
| 85° | 20.7 | 23.0 | 23.9 | 23.4 | 22.5 | 18.5 | 17.1 | 14.9 | 14.0 | 12.2 | 12.2 |
| 87.5° | 5.0 | 6.3 | 6.3 | 4.5 | 4.5 | 2.3 | 1.4 | 0.5 | 0.0 | 0.0 | 0.0 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



LM-79-2008: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGRAW-EDISON

Report Number: SP1-1908-441-2-R4

Test Date: 10/03/2019

Luminaire Tested: SA1C-730-U-5WQ

Data in this report applies to families of products SA1C-730-U-5WQ .

Test Information

Test Method: LM-79-2008
 Report Number: SP1-1908-441-2-R4
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 10/28/2024
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: McGRAW-EDISON
 Catalog Number: **SA1C-730-U-5WQ**
 Description: McGRAW EDISON ROADWAY AND AREA LUMINAIRE

THIS IS A REVISION OF SP1-1908-441-2-R3. TO UPDATE THE CATALOG INFORMATION.TESTED IN SITU. (1) 70 CRI, 3000K, 1050MA LIGHTSQUARE WITH 16 LEDS AND TYPE V WIDE OPTICS.

Spectral Parameters

CCT (K): 2993
 CIE u': 0.2508
 CIE v': 0.5215
 Duv: 0.0000
 CIE x: 0.4374
 CIE y: 0.4043
 CIE z: 0.1583
 Peak Wavelength (nm): 593
 Dominant Wavelength (nm): 582
 Purity: 53

| | | | |
|-----------|------|------|-------|
| CRI (Ra): | 71.8 | | |
| R1: | 67.5 | R9: | -38.3 |
| R2: | 82.9 | R10: | 62.5 |
| R3: | 94.7 | R11: | 63.7 |
| R4: | 67.7 | R12: | 57.8 |
| R5: | 67.9 | R13: | 70.4 |
| R6: | 77.6 | R14: | 97.3 |
| R7: | 76.0 | | |
| R8: | 40.5 | | |

Rf: 75.7
 Rg: 93.9



Test Conditions

Stabilization Time: 53M
 Operation Time: 12H
 Room Temperature (°C) / RH%: 25.0./44%
 Sphere Temperature (°C): 25.7

REPORT NUMBER: SP1-1908-441-2-R4

| Measurement and Test Equipment | | | |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument | Identification Number | Calibration Date | Calibration Due Date |
| Photometer | IN0058 | 6/28/2019 | 12/28/2019 |
| Power Meter | IN0071 | 12/5/2018 | 12/5/2019 |
| AC Power Source | IN0063 | 12/5/2018 | 12/5/2019 |
| DC Power Source | IN0208 | 12/5/2018 | 12/5/2019 |
| Sphere Thermometer | IN0085 | 12/5/2018 | 12/5/2019 |
| Room Thermometer | IN0046 | 12/5/2018 | 12/5/2019 |

REPORT NUMBER: SP1-1908-441-2-R4

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 3000K 4-step quadrangle

REPORT NUMBER: SP1-1908-441-2-R4

Photopic Flux vs. Wavelength



#####

| λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) |
|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|
| 360 | 2397 | NR | 490 | 24908 | NR | 620 | 118784 | NR | 750 | 5037 | NR | 880 | 2677 | NR |
| 365 | 2084 | NR | 495 | 30998 | NR | 625 | 108951 | NR | 755 | 4413 | NR | 885 | 2940 | NR |
| 370 | 2143 | NR | 500 | 37103 | NR | 630 | 99573 | NR | 760 | 4189 | NR | 890 | 3116 | NR |
| 375 | 2413 | NR | 505 | 42987 | NR | 635 | 90444 | NR | 765 | 3677 | NR | 895 | 3345 | NR |
| 380 | 2172 | NR | 510 | 48702 | NR | 640 | 80749 | NR | 770 | 3366 | NR | 900 | 2312 | NR |
| 385 | 1997 | NR | 515 | 53741 | NR | 645 | 71664 | NR | 775 | 3211 | NR | 905 | 2829 | NR |
| 390 | 1830 | NR | 520 | 57283 | NR | 650 | 63936 | NR | 780 | 2682 | NR | 910 | 2783 | NR |
| 395 | 1861 | NR | 525 | 61876 | NR | 655 | 56611 | NR | 785 | 2804 | NR | 915 | 2662 | NR |
| 400 | 1717 | NR | 530 | 65398 | NR | 660 | 49763 | NR | 790 | 2581 | NR | 920 | 3047 | NR |
| 405 | 1761 | NR | 535 | 69597 | NR | 665 | 42891 | NR | 795 | 2711 | NR | 925 | 2256 | NR |
| 410 | 2680 | NR | 540 | 74214 | NR | 670 | 36939 | NR | 800 | 2609 | NR | 930 | 2976 | NR |
| 415 | 4374 | NR | 545 | 79911 | NR | 675 | 31946 | NR | 805 | 2581 | NR | 935 | 3503 | NR |
| 420 | 8071 | NR | 550 | 86153 | NR | 680 | 27385 | NR | 810 | 2404 | NR | 940 | 4226 | NR |
| 425 | 15169 | NR | 555 | 93952 | NR | 685 | 23504 | NR | 815 | 2556 | NR | 945 | 2930 | NR |
| 430 | 26038 | NR | 560 | 102904 | NR | 690 | 20210 | NR | 820 | 2742 | NR | 950 | 2115 | NR |
| 435 | 41316 | NR | 565 | 112009 | NR | 695 | 17459 | NR | 825 | 2014 | NR | 955 | 2634 | NR |
| 440 | 59674 | NR | 570 | 121662 | NR | 700 | 15207 | NR | 830 | 2488 | NR | 960 | 4200 | NR |
| 445 | 72751 | NR | 575 | 130476 | NR | 705 | 13322 | NR | 835 | 2625 | NR | 965 | 1982 | NR |
| 450 | 65091 | NR | 580 | 137926 | NR | 710 | 11676 | NR | 840 | 2754 | NR | 970 | 3613 | NR |
| 455 | 44894 | NR | 585 | 143406 | NR | 715 | 10626 | NR | 845 | 2708 | NR | 975 | 4034 | NR |
| 460 | 32712 | NR | 590 | 147039 | NR | 720 | 9416 | NR | 850 | 2608 | NR | 980 | 3922 | NR |
| 465 | 25296 | NR | 595 | 147365 | NR | 725 | 8333 | NR | 855 | 2605 | NR | 985 | 1909 | NR |
| 470 | 19318 | NR | 600 | 145800 | NR | 730 | 7134 | NR | 860 | 1765 | NR | 990 | 3617 | NR |
| 475 | 17265 | NR | 605 | 141363 | NR | 735 | 6437 | NR | 865 | 2581 | NR | 995 | 4767 | NR |
| 480 | 18260 | NR | 610 | 134199 | NR | 740 | 5834 | NR | 870 | 3016 | NR | 1000 | 2528 | NR |
| 485 | 20845 | NR | 615 | 127683 | NR | 745 | 5500 | NR | 875 | 3952 | NR | | | |

REPORT NUMBER: SP1-1908-441-2-R4

Scotopic Flux vs. Wavelength



Scotopic Lumens: 8494.8

S/P: 1.23

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 2397 | NR | 490 | 24908 | NR | 620 | 118784 | NR | 750 | 5037 | NR | 880 | 2677 | NR |
| 365 | 2084 | NR | 495 | 30998 | NR | 625 | 108951 | NR | 755 | 4413 | NR | 885 | 2940 | NR |
| 370 | 2143 | NR | 500 | 37103 | NR | 630 | 99573 | NR | 760 | 4189 | NR | 890 | 3116 | NR |
| 375 | 2413 | NR | 505 | 42987 | NR | 635 | 90444 | NR | 765 | 3677 | NR | 895 | 3345 | NR |
| 380 | 2172 | NR | 510 | 48702 | NR | 640 | 80749 | NR | 770 | 3366 | NR | 900 | 2312 | NR |
| 385 | 1997 | NR | 515 | 53741 | NR | 645 | 71664 | NR | 775 | 3211 | NR | 905 | 2829 | NR |
| 390 | 1830 | NR | 520 | 57283 | NR | 650 | 63936 | NR | 780 | 2682 | NR | 910 | 2783 | NR |
| 395 | 1861 | NR | 525 | 61876 | NR | 655 | 56611 | NR | 785 | 2804 | NR | 915 | 2662 | NR |
| 400 | 1717 | NR | 530 | 65398 | NR | 660 | 49763 | NR | 790 | 2581 | NR | 920 | 3047 | NR |
| 405 | 1761 | NR | 535 | 69597 | NR | 665 | 42891 | NR | 795 | 2711 | NR | 925 | 2256 | NR |
| 410 | 2680 | NR | 540 | 74214 | NR | 670 | 36939 | NR | 800 | 2609 | NR | 930 | 2976 | NR |
| 415 | 4374 | NR | 545 | 79911 | NR | 675 | 31946 | NR | 805 | 2581 | NR | 935 | 3503 | NR |
| 420 | 8071 | NR | 550 | 86153 | NR | 680 | 27385 | NR | 810 | 2404 | NR | 940 | 4226 | NR |
| 425 | 15169 | NR | 555 | 93952 | NR | 685 | 23504 | NR | 815 | 2556 | NR | 945 | 2930 | NR |
| 430 | 26038 | NR | 560 | 102904 | NR | 690 | 20210 | NR | 820 | 2742 | NR | 950 | 2115 | NR |
| 435 | 41316 | NR | 565 | 112009 | NR | 695 | 17459 | NR | 825 | 2014 | NR | 955 | 2634 | NR |
| 440 | 59674 | NR | 570 | 121662 | NR | 700 | 15207 | NR | 830 | 2488 | NR | 960 | 4200 | NR |
| 445 | 72751 | NR | 575 | 130476 | NR | 705 | 13322 | NR | 835 | 2625 | NR | 965 | 1982 | NR |
| 450 | 65091 | NR | 580 | 137926 | NR | 710 | 11676 | NR | 840 | 2754 | NR | 970 | 3613 | NR |
| 455 | 44894 | NR | 585 | 143406 | NR | 715 | 10626 | NR | 845 | 2708 | NR | 975 | 4034 | NR |
| 460 | 32712 | NR | 590 | 147039 | NR | 720 | 9416 | NR | 850 | 2608 | NR | 980 | 3922 | NR |
| 465 | 25296 | NR | 595 | 147365 | NR | 725 | 8333 | NR | 855 | 2605 | NR | 985 | 1909 | NR |
| 470 | 19318 | NR | 600 | 145800 | NR | 730 | 7134 | NR | 860 | 1765 | NR | 990 | 3617 | NR |
| 475 | 17265 | NR | 605 | 141363 | NR | 735 | 6437 | NR | 865 | 2581 | NR | 995 | 4767 | NR |
| 480 | 18260 | NR | 610 | 134199 | NR | 740 | 5834 | NR | 870 | 3016 | NR | 1000 | 2528 | NR |
| 485 | 20845 | NR | 615 | 127683 | NR | 745 | 5500 | NR | 875 | 3952 | NR | | | |

REPORT NUMBER: SP1-1908-441-2-R4

Melanopic Flux vs. Wavelength



Melanopic Lumens: 3101.5 M/P: 0.45

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 2397 | NR | 490 | 24908 | NR | 620 | 118784 | NR | 750 | 5037 | NR | 880 | 2677 | NR |
| 365 | 2084 | NR | 495 | 30998 | NR | 625 | 108951 | NR | 755 | 4413 | NR | 885 | 2940 | NR |
| 370 | 2143 | NR | 500 | 37103 | NR | 630 | 99573 | NR | 760 | 4189 | NR | 890 | 3116 | NR |
| 375 | 2413 | NR | 505 | 42987 | NR | 635 | 90444 | NR | 765 | 3677 | NR | 895 | 3345 | NR |
| 380 | 2172 | NR | 510 | 48702 | NR | 640 | 80749 | NR | 770 | 3366 | NR | 900 | 2312 | NR |
| 385 | 1997 | NR | 515 | 53741 | NR | 645 | 71664 | NR | 775 | 3211 | NR | 905 | 2829 | NR |
| 390 | 1830 | NR | 520 | 57283 | NR | 650 | 63936 | NR | 780 | 2682 | NR | 910 | 2783 | NR |
| 395 | 1861 | NR | 525 | 61876 | NR | 655 | 56611 | NR | 785 | 2804 | NR | 915 | 2662 | NR |
| 400 | 1717 | NR | 530 | 65398 | NR | 660 | 49763 | NR | 790 | 2581 | NR | 920 | 3047 | NR |
| 405 | 1761 | NR | 535 | 69597 | NR | 665 | 42891 | NR | 795 | 2711 | NR | 925 | 2256 | NR |
| 410 | 2680 | NR | 540 | 74214 | NR | 670 | 36939 | NR | 800 | 2609 | NR | 930 | 2976 | NR |
| 415 | 4374 | NR | 545 | 79911 | NR | 675 | 31946 | NR | 805 | 2581 | NR | 935 | 3503 | NR |
| 420 | 8071 | NR | 550 | 86153 | NR | 680 | 27385 | NR | 810 | 2404 | NR | 940 | 4226 | NR |
| 425 | 15169 | NR | 555 | 93952 | NR | 685 | 23504 | NR | 815 | 2556 | NR | 945 | 2930 | NR |
| 430 | 26038 | NR | 560 | 102904 | NR | 690 | 20210 | NR | 820 | 2742 | NR | 950 | 2115 | NR |
| 435 | 41316 | NR | 565 | 112009 | NR | 695 | 17459 | NR | 825 | 2014 | NR | 955 | 2634 | NR |
| 440 | 59674 | NR | 570 | 121662 | NR | 700 | 15207 | NR | 830 | 2488 | NR | 960 | 4200 | NR |
| 445 | 72751 | NR | 575 | 130476 | NR | 705 | 13322 | NR | 835 | 2625 | NR | 965 | 1982 | NR |
| 450 | 65091 | NR | 580 | 137926 | NR | 710 | 11676 | NR | 840 | 2754 | NR | 970 | 3613 | NR |
| 455 | 44894 | NR | 585 | 143406 | NR | 715 | 10626 | NR | 845 | 2708 | NR | 975 | 4034 | NR |
| 460 | 32712 | NR | 590 | 147039 | NR | 720 | 9416 | NR | 850 | 2608 | NR | 980 | 3922 | NR |
| 465 | 25296 | NR | 595 | 147365 | NR | 725 | 8333 | NR | 855 | 2605 | NR | 985 | 1909 | NR |
| 470 | 19318 | NR | 600 | 145800 | NR | 730 | 7134 | NR | 860 | 1765 | NR | 990 | 3617 | NR |
| 475 | 17265 | NR | 605 | 141363 | NR | 735 | 6437 | NR | 865 | 2581 | NR | 995 | 4767 | NR |
| 480 | 18260 | NR | 610 | 134199 | NR | 740 | 5834 | NR | 870 | 3016 | NR | 1000 | 2528 | NR |
| 485 | 20845 | NR | 615 | 127683 | NR | 745 | 5500 | NR | 875 | 3952 | NR | | | |

REPORT NUMBER: SP1-1908-441-2-R4

TM-30-18

Summary

$R_f = 75.7$
 $R_g = 93.9$
 CIE $R_a = 71.8$
 $R_9 = -38.3$



Color Vector Graphics



REPORT NUMBER: SP1-1908-441-2-R4

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)

| | | | |
|------------|------------|------------|------------|
| CES01 = 86 | CES26 = 67 | CES51 = 87 | CES76 = 63 |
| CES02 = 63 | CES27 = 88 | CES52 = 86 | CES77 = 80 |
| CES03 = 31 | CES28 = 87 | CES53 = 78 | CES78 = 67 |
| CES04 = 71 | CES29 = 66 | CES54 = 84 | CES79 = 87 |
| CES05 = 49 | CES30 = 73 | CES55 = 84 | CES80 = 86 |
| CES06 = 51 | CES31 = 70 | CES56 = 75 | CES81 = 71 |
| CES07 = 41 | CES32 = 65 | CES57 = 74 | CES82 = 94 |
| CES08 = 40 | CES33 = 73 | CES58 = 76 | CES83 = 90 |
| CES09 = 29 | CES34 = 79 | CES59 = 85 | CES84 = 89 |
| CES10 = 76 | CES35 = 89 | CES60 = 93 | CES85 = 77 |
| CES11 = 59 | CES36 = 97 | CES61 = 84 | CES86 = 61 |
| CES12 = 65 | CES37 = 87 | CES62 = 91 | CES87 = 78 |
| CES13 = 43 | CES38 = 81 | CES63 = 77 | CES88 = 77 |
| CES14 = 74 | CES39 = 95 | CES64 = 72 | CES89 = 67 |
| CES15 = 71 | CES40 = 92 | CES65 = 68 | CES90 = 76 |
| CES16 = 47 | CES41 = 88 | CES66 = 69 | CES91 = 89 |
| CES17 = 50 | CES42 = 89 | CES67 = 67 | CES92 = 58 |
| CES18 = 56 | CES43 = 79 | CES68 = 72 | CES93 = 74 |
| CES19 = 73 | CES44 = 99 | CES69 = 81 | CES94 = 49 |
| CES20 = 66 | CES45 = 85 | CES70 = 66 | CES95 = 68 |
| CES21 = 87 | CES46 = 80 | CES71 = 67 | CES96 = 76 |
| CES22 = 79 | CES47 = 82 | CES72 = 88 | CES97 = 82 |
| CES23 = 92 | CES48 = 69 | CES73 = 59 | CES98 = 75 |
| CES24 = 91 | CES49 = 80 | CES74 = 95 | CES99 = 62 |
| CES25 = 73 | CES50 = 87 | CES75 = 69 | |



REPORT NUMBER: SP1-1908-441-2-R4

TM-30-18

Color Rendition by Hue-Angle Bin



REPORT NUMBER: SP1-1908-441-2-R4

TM-30-18

Measure Comparisons



(END OF REPORT)