

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: McGRAW-EDISON

Report Number: P639146

Luminaire Tested: GWS-SA5B-730-U-SLR-W

Issue Date: 1/10/2023

Test Information

Test Method: LM-79-2019
Report Number: P639146
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2209-782-41)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/10/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: McGRAW-EDISON
Catalog Number: GWS-SA5B-730-U-SLR-W
Description: GALLEON WALL SLIM LUMINAIRE. (5) LIGHTSQUARES WITH 16 LEDS EACH AND
SPILL LIGHT ELIMINATOR RIGHT OPTICS
Light Source: (80) 3000K CCT, 70 CRI LEDS
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 15309.3 lumens
Efficiency: N/A
Efficacy: 132.3 lumens/watt
Luminous Opening: Rectangular (W 1.5' x L: 1' x H: 0')
IES Classification: Type III - Short
BUG Rating: B2 - U0 - G3


Input Watts (W): 115.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 0
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT



REPORT NUMBER: P639146
 CATALOG NUMBER: GWS-SA5B-730-U-SLR-W

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 4.6 fc
 Type III - Short - N/A

REPORT NUMBER: P639146
CATALOG NUMBER: GWS-SA5B-730-U-SLR-W

Luminous Intensity Polar Plot



— Vertical Plane Through 45-Deg Lateral - - - Horizontal Cone Through 62.5-Deg Vertical

REPORT NUMBER: P639146

CATALOG NUMBER: GWS-SA5B-730-U-SLR-W


FLUX DISTRIBUTION:

| | | Downward | Upward | Total |
|--------------------|-----------|----------|--------|---------|
| House Side | Lumens | 3653.1 | 0.0 | 3653.1 |
| | % Fixture | 23.9 | 0.0 | 23.9 |
| Street Side | Lumens | 11656.2 | 0.0 | 11656.2 |
| | % Fixture | 76.1 | 0.0 | 76.1 |
| Total | Lumens | 15309.3 | 0.0 | 15309.3 |
| | % Fixture | 100.0 | 0.0 | 100.0 |

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|---------|-----------|
| 0°-10° | 198.4 | 1.3 |
| 10°-20° | 622.1 | 4.1 |
| 20°-30° | 966.2 | 6.3 |
| 30°-40° | 1311.9 | 8.6 |
| 40°-50° | 2079.2 | 13.6 |
| 50°-60° | 3667.7 | 24.0 |
| 60°-70° | 4080.8 | 26.7 |
| 70°-80° | 2069.6 | 13.5 |
| 80°-90° | 313.4 | 2.0 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-90° | 15309.3 | 100.0 |
| 0°-180° | 15309.3 | 100.0 |

Coefficient of Utilization



REPORT NUMBER: P639146


CATALOG NUMBER: GWS-SA5B-730-U-SLR-W

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

| Zone | Lumens | % Fixture | Zone Rating/Lumen Limit | | |
|----------------|--------|-----------|-------------------------|------|---------|
| | | | B | U | G |
| FL (0°-30°) | 999.6 | 6.5 | | | |
| FM (30°-60°) | 5198.2 | 34.0 | | | |
| FH (60°-80°) | 5220.6 | 34.1 | | | G3/7500 |
| FVH (80°-90°) | 237.9 | 1.6 | | | G3/500 |
| BL (0°-30°) | 787.1 | 5.1 | B2/1000 | | |
| BM (30°-60°) | 1860.5 | 12.2 | B2/2500 | | |
| BH (60°-80°) | 929.9 | 6.1 | B2/1000 | | G2/1000 |
| BVH (80°-90°) | 75.5 | 0.5 | | | G1/100 |
| UL (90°-100°) | 0.0 | 0.0 | | U0/0 | |
| UH (100°-180°) | 0.0 | 0.0 | | U0/0 | |

BUG Rating: B2-U0-G3

Type III Short





REPORT NUMBER: P639146
 CATALOG NUMBER: GWS-SA5B-730-U-SLR-W

CANDELA DISTRIBUTION (FULL):

| | 0° | 1° | 5° | 15° | 25° | 35° | 45° | 55° | 65° | 75° | 85° |
|-------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|
| 0° | 2031.9 | 2031.9 | 2031.9 | 2031.9 | 2031.9 | 2031.9 | 2031.9 | 2031.9 | 2031.9 | 2031.9 | 2031.9 |
| 2.5° | 2183.7 | 2182.5 | 2204.6 | 2238.2 | 2269.5 | 2283.4 | 2306.6 | 2304.2 | 2285.7 | 2261.4 | 2253.2 |
| 5° | 2355.2 | 2359.9 | 2398.1 | 2472.3 | 2554.6 | 2589.4 | 2604.4 | 2598.6 | 2565.0 | 2522.1 | 2446.8 |
| 7.5° | 2510.6 | 2518.7 | 2577.8 | 2689.1 | 2791.1 | 2837.4 | 2874.5 | 2867.5 | 2818.9 | 2738.9 | 2627.6 |
| 10° | 2624.1 | 2633.4 | 2704.1 | 2835.1 | 2948.7 | 2989.3 | 3036.8 | 3039.1 | 2996.2 | 2888.4 | 2774.8 |
| 12.5° | 2737.7 | 2747.0 | 2813.1 | 2932.5 | 3006.6 | 3007.8 | 3035.6 | 3050.7 | 3053.0 | 3003.2 | 2889.6 |
| 15° | 2856.0 | 2864.1 | 2924.3 | 2991.6 | 2988.1 | 2923.2 | 2923.2 | 2952.2 | 3015.9 | 3051.8 | 2973.0 |
| 17.5° | 2956.8 | 2967.2 | 3013.6 | 2991.6 | 2888.4 | 2771.3 | 2757.4 | 2794.5 | 2905.8 | 3043.7 | 3035.6 |
| 20° | 3040.3 | 3048.4 | 3073.9 | 2927.8 | 2740.1 | 2587.1 | 2560.4 | 2603.3 | 2754.0 | 2993.9 | 3083.1 |
| 22.5° | 3120.2 | 3124.9 | 3111.0 | 2844.4 | 2580.1 | 2405.1 | 2372.6 | 2417.8 | 2580.1 | 2905.8 | 3123.7 |
| 25° | 3215.3 | 3210.6 | 3144.6 | 2757.4 | 2434.1 | 2261.4 | 2227.7 | 2278.7 | 2448.0 | 2788.7 | 3167.7 |
| 27.5° | 3325.4 | 3308.0 | 3173.5 | 2663.6 | 2321.6 | 2154.7 | 2131.5 | 2186.0 | 2343.6 | 2680.9 | 3202.5 |
| 30° | 3419.3 | 3385.7 | 3178.2 | 2580.1 | 2263.7 | 2109.5 | 2095.6 | 2146.6 | 2292.6 | 2607.9 | 3246.6 |
| 32.5° | 3523.6 | 3477.2 | 3204.8 | 2558.1 | 2296.1 | 2218.5 | 2237.0 | 2240.5 | 2306.6 | 2587.1 | 3312.6 |
| 35° | 3673.1 | 3612.8 | 3277.9 | 2621.8 | 2629.9 | 2760.9 | 2828.1 | 2737.7 | 2516.3 | 2633.4 | 3437.8 |
| 37.5° | 3899.1 | 3822.6 | 3426.2 | 2897.7 | 3319.6 | 3612.8 | 3775.1 | 3568.8 | 3153.8 | 2808.4 | 3626.7 |
| 40° | 4173.8 | 4076.5 | 3616.3 | 3407.7 | 3964.0 | 4433.5 | 4722.1 | 4419.5 | 3809.9 | 3245.4 | 3892.2 |
| 42.5° | 4557.5 | 4455.5 | 3984.9 | 3908.4 | 4561.0 | 5259.9 | 5636.6 | 5185.7 | 4388.3 | 3809.9 | 4317.6 |
| 45° | 5226.3 | 5127.7 | 4660.6 | 4410.3 | 5259.9 | 6277.5 | 6806.1 | 6179.0 | 4975.9 | 4376.7 | 5112.7 |
| 47.5° | 6461.8 | 6345.9 | 5664.4 | 4966.6 | 6057.3 | 7598.9 | 8338.4 | 7425.0 | 5586.7 | 5025.7 | 6447.9 |
| 50° | 7945.5 | 7834.2 | 6924.3 | 5625.0 | 6938.2 | 9011.8 | 10039.9 | 8888.9 | 6290.3 | 5815.1 | 8044.0 |
| 52.5° | 9730.4 | 9709.6 | 8722.0 | 6457.2 | 7855.0 | 10518.6 | 11928.0 | 10510.5 | 7061.1 | 6877.9 | 9852.1 |
| 55° | 11339.2 | 11543.2 | 11005.4 | 7726.4 | 9039.6 | 12411.4 | 13869.5 | 12279.2 | 8106.6 | 8635.1 | 11969.8 |
| 57.5° | 12206.2 | 12754.5 | 13580.9 | 10315.8 | 10762.0 | 14673.9 | 16265.3 | 14438.6 | 9903.1 | 11560.6 | 13933.2 |
| 60° | 11633.6 | 12254.9 | 13752.4 | 12265.3 | 12470.5 | 16486.7 | 18242.7 | 16253.7 | 11667.2 | 13591.3 | 13822.0 |
| 62.5° | 10680.9 | 11238.4 | 12570.2 | 11127.1 | 12734.7 | 16885.4 | 18289.0 | 16570.1 | 12368.5 | 12560.9 | 12485.5 |
| 65° | 9550.8 | 10112.9 | 11523.5 | 9713.0 | 11894.4 | 15938.4 | 16939.9 | 15639.4 | 11108.6 | 11348.5 | 11376.3 |
| 67.5° | 8049.8 | 8569.0 | 10005.1 | 8636.3 | 10842.0 | 14548.7 | 14868.6 | 14313.4 | 10230.0 | 10612.5 | 10212.6 |
| 70° | 6014.4 | 6482.7 | 7750.7 | 7018.2 | 9139.3 | 12738.2 | 12479.7 | 12562.0 | 9243.6 | 9623.8 | 8530.8 |
| 72.5° | 4110.1 | 4462.4 | 5549.6 | 5514.9 | 6998.5 | 10197.5 | 9837.1 | 10617.1 | 7720.6 | 8224.8 | 6503.6 |
| 75° | 2874.5 | 3149.2 | 4011.6 | 4357.0 | 5290.0 | 7558.3 | 7005.4 | 7946.6 | 6029.5 | 6749.3 | 4745.2 |
| 77.5° | 1764.1 | 1946.1 | 2533.7 | 3228.0 | 3403.0 | 5172.9 | 4351.2 | 5979.7 | 4234.1 | 4922.6 | 3165.4 |
| 80° | 882.1 | 970.1 | 1230.9 | 2029.5 | 2256.7 | 3048.4 | 2402.8 | 3471.4 | 2865.2 | 3048.4 | 1751.4 |
| 82.5° | 266.6 | 294.4 | 360.5 | 770.8 | 1169.5 | 1754.8 | 1419.9 | 2016.8 | 1564.7 | 1429.1 | 689.6 |
| 85° | 70.7 | 80.0 | 99.7 | 228.3 | 410.3 | 629.4 | 479.9 | 977.1 | 749.9 | 527.4 | 259.6 |
| 87.5° | 5.8 | 5.8 | 4.6 | 4.6 | 2.3 | 0.0 | 0.0 | 69.5 | 140.2 | 80.0 | 45.2 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P639146
 CATALOG NUMBER: GWS-SA5B-730-U-SLR-W

CANDELA DISTRIBUTION (continued):

| | 90° | 95° | 105° | 115° | 125° | 135° | 145° | 155° | 165° | 175° | 180° |
|-------|---------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 2031.9 | 2031.9 | 2031.9 | 2031.9 | 2031.9 | 2031.9 | 2031.9 | 2031.9 | 2031.9 | 2031.9 | 2031.9 |
| 2.5° | 2212.7 | 2208.0 | 2160.5 | 2125.7 | 2085.2 | 2045.8 | 2005.2 | 1969.3 | 1928.7 | 1888.1 | 1876.5 |
| 5° | 2391.2 | 2358.7 | 2257.9 | 2173.3 | 2089.8 | 2016.8 | 1953.0 | 1887.0 | 1833.7 | 1781.5 | 1761.8 |
| 7.5° | 2548.8 | 2492.0 | 2346.0 | 2217.3 | 2101.4 | 2011.0 | 1917.1 | 1820.9 | 1745.6 | 1671.4 | 1652.8 |
| 10° | 2691.4 | 2616.0 | 2431.7 | 2269.5 | 2140.8 | 2037.7 | 1927.5 | 1798.9 | 1689.9 | 1599.5 | 1575.2 |
| 12.5° | 2796.8 | 2714.6 | 2505.9 | 2319.3 | 2173.3 | 2057.4 | 1948.4 | 1834.8 | 1720.1 | 1603.0 | 1576.3 |
| 15° | 2880.3 | 2794.5 | 2567.3 | 2357.6 | 2174.4 | 2024.9 | 1919.4 | 1880.0 | 1844.1 | 1729.3 | 1680.7 |
| 17.5° | 2947.5 | 2857.1 | 2620.7 | 2380.7 | 2143.1 | 1926.4 | 1834.8 | 1892.8 | 1984.3 | 1912.5 | 1820.9 |
| 20° | 3009.0 | 2917.4 | 2661.2 | 2397.0 | 2073.6 | 1790.8 | 1739.8 | 1862.6 | 2000.6 | 1998.2 | 1915.9 |
| 22.5° | 3076.2 | 2986.9 | 2720.3 | 2406.2 | 1976.2 | 1652.8 | 1683.0 | 1818.6 | 1931.0 | 1964.6 | 1913.6 |
| 25° | 3162.0 | 3083.1 | 2802.6 | 2427.1 | 1866.1 | 1557.8 | 1641.2 | 1761.8 | 1855.7 | 1863.8 | 1833.7 |
| 27.5° | 3261.6 | 3202.5 | 2925.5 | 2475.8 | 1759.5 | 1509.1 | 1592.6 | 1681.8 | 1767.6 | 1771.1 | 1735.1 |
| 30° | 3370.6 | 3331.2 | 3039.1 | 2516.3 | 1679.5 | 1494.0 | 1530.0 | 1601.8 | 1656.3 | 1665.6 | 1634.3 |
| 32.5° | 3509.7 | 3474.9 | 3139.9 | 2489.7 | 1632.0 | 1490.6 | 1472.0 | 1509.1 | 1554.3 | 1554.3 | 1530.0 |
| 35° | 3700.9 | 3652.2 | 3246.6 | 2387.7 | 1574.0 | 1476.7 | 1410.6 | 1421.0 | 1440.7 | 1444.2 | 1430.3 |
| 37.5° | 3972.1 | 3892.2 | 3354.4 | 2186.0 | 1479.0 | 1426.8 | 1339.9 | 1327.1 | 1334.1 | 1343.4 | 1339.9 |
| 40° | 4308.3 | 4177.3 | 3512.0 | 1943.8 | 1365.4 | 1330.6 | 1266.9 | 1242.5 | 1236.7 | 1255.3 | 1262.2 |
| 42.5° | 4731.3 | 4530.8 | 3681.2 | 1717.7 | 1262.2 | 1220.5 | 1181.1 | 1160.2 | 1151.0 | 1182.3 | 1200.8 |
| 45° | 5407.1 | 5076.7 | 3843.5 | 1494.0 | 1204.3 | 1126.6 | 1100.0 | 1084.9 | 1089.5 | 1126.6 | 1149.8 |
| 47.5° | 6574.3 | 5910.1 | 3997.6 | 1352.6 | 1199.6 | 1059.4 | 1026.9 | 1030.4 | 1043.2 | 1082.6 | 1110.4 |
| 50° | 8050.9 | 7026.3 | 4100.8 | 1293.5 | 1213.6 | 1018.8 | 975.9 | 994.5 | 1014.2 | 1052.4 | 1084.9 |
| 52.5° | 9554.2 | 8066.0 | 3977.9 | 1261.1 | 1212.4 | 1020.0 | 928.4 | 984.1 | 993.3 | 1031.6 | 1066.3 |
| 55° | 10588.1 | 8181.9 | 3436.7 | 1211.2 | 1193.8 | 1066.3 | 891.3 | 979.4 | 985.2 | 1020.0 | 1051.3 |
| 57.5° | 10982.2 | 7785.5 | 2620.7 | 1225.1 | 1138.2 | 1102.3 | 875.1 | 947.0 | 988.7 | 1018.8 | 1051.3 |
| 60° | 10505.8 | 7037.9 | 1592.6 | 1261.1 | 1049.0 | 1100.0 | 885.5 | 887.9 | 959.7 | 1010.7 | 1043.2 |
| 62.5° | 9607.6 | 6078.2 | 1118.5 | 1159.1 | 984.1 | 1038.5 | 909.9 | 818.3 | 908.7 | 970.1 | 999.1 |
| 65° | 8578.3 | 4949.2 | 853.1 | 998.0 | 952.8 | 943.5 | 918.0 | 756.9 | 839.2 | 899.4 | 924.9 |
| 67.5° | 7506.2 | 3847.0 | 693.1 | 744.1 | 861.2 | 853.1 | 839.2 | 702.4 | 756.9 | 799.8 | 828.7 |
| 70° | 6155.8 | 2691.4 | 585.3 | 558.7 | 738.3 | 765.0 | 733.7 | 634.0 | 651.4 | 695.4 | 718.6 |
| 72.5° | 4503.0 | 1677.2 | 481.0 | 461.3 | 593.4 | 668.8 | 652.6 | 558.7 | 566.8 | 608.5 | 627.1 |
| 75° | 3238.5 | 959.7 | 386.0 | 380.2 | 453.2 | 572.6 | 540.1 | 481.0 | 490.3 | 521.6 | 534.3 |
| 77.5° | 2058.5 | 534.3 | 297.9 | 306.0 | 324.5 | 427.7 | 461.3 | 411.5 | 411.5 | 430.0 | 440.4 |
| 80° | 1102.3 | 306.0 | 217.9 | 221.4 | 227.2 | 326.9 | 363.9 | 318.7 | 318.7 | 306.0 | 318.7 |
| 82.5° | 449.7 | 176.2 | 149.5 | 139.1 | 151.8 | 223.7 | 255.0 | 202.8 | 212.1 | 191.2 | 195.9 |
| 85° | 148.4 | 88.1 | 74.2 | 73.0 | 71.9 | 98.5 | 122.9 | 100.8 | 120.5 | 76.5 | 80.0 |
| 87.5° | 19.7 | 16.2 | 9.3 | 7.0 | 8.1 | 3.5 | 7.0 | 8.1 | 8.1 | 5.8 | 5.8 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P639146
 CATALOG NUMBER: GWS-SA5B-730-U-SLR-W

CANDELA DISTRIBUTION (continued):

| | 185° | 195° | 205° | 215° | 225° | 235° | 245° | 255° | 265° | 270° | 275° |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 2031.9 | 2031.9 | 2031.9 | 2031.9 | 2031.9 | 2031.9 | 2031.9 | 2031.9 | 2031.9 | 2031.9 | 2031.9 |
| 2.5° | 1868.4 | 1859.2 | 1825.5 | 1833.7 | 1827.9 | 1818.6 | 1827.9 | 1810.5 | 1824.4 | 1829.0 | 1858.0 |
| 5° | 1746.7 | 1724.7 | 1692.2 | 1676.0 | 1672.5 | 1663.3 | 1664.4 | 1656.3 | 1658.6 | 1678.3 | 1710.8 |
| 7.5° | 1637.8 | 1616.9 | 1591.4 | 1579.8 | 1569.4 | 1559.0 | 1557.8 | 1556.6 | 1565.9 | 1583.3 | 1614.6 |
| 10° | 1559.0 | 1547.4 | 1536.9 | 1541.6 | 1536.9 | 1532.3 | 1524.2 | 1524.2 | 1539.3 | 1570.5 | 1608.8 |
| 12.5° | 1559.0 | 1556.6 | 1559.0 | 1572.9 | 1571.7 | 1572.9 | 1562.4 | 1568.2 | 1610.0 | 1663.3 | 1717.7 |
| 15° | 1642.4 | 1623.9 | 1623.9 | 1630.8 | 1628.5 | 1628.5 | 1628.5 | 1652.8 | 1747.9 | 1830.2 | 1888.1 |
| 17.5° | 1744.4 | 1689.9 | 1666.7 | 1663.3 | 1662.1 | 1662.1 | 1666.7 | 1718.9 | 1867.3 | 1954.2 | 1987.8 |
| 20° | 1815.1 | 1712.0 | 1673.7 | 1658.6 | 1659.8 | 1662.1 | 1676.0 | 1747.9 | 1911.3 | 1955.4 | 1947.2 |
| 22.5° | 1827.9 | 1694.6 | 1648.2 | 1626.2 | 1629.7 | 1632.0 | 1652.8 | 1729.3 | 1851.0 | 1858.0 | 1841.8 |
| 25° | 1768.7 | 1645.9 | 1596.0 | 1578.7 | 1583.3 | 1582.1 | 1600.7 | 1656.3 | 1743.2 | 1740.9 | 1731.7 |
| 27.5° | 1680.7 | 1568.2 | 1531.1 | 1519.5 | 1527.7 | 1518.4 | 1524.2 | 1567.1 | 1634.3 | 1632.0 | 1628.5 |
| 30° | 1590.2 | 1492.9 | 1459.3 | 1453.5 | 1463.9 | 1450.0 | 1451.2 | 1487.1 | 1533.5 | 1531.1 | 1530.0 |
| 32.5° | 1499.8 | 1417.5 | 1387.4 | 1387.4 | 1397.8 | 1382.8 | 1385.1 | 1416.4 | 1447.7 | 1438.4 | 1438.4 |
| 35° | 1414.1 | 1356.1 | 1331.8 | 1327.1 | 1335.3 | 1324.8 | 1329.5 | 1358.4 | 1370.0 | 1357.3 | 1349.2 |
| 37.5° | 1338.7 | 1313.2 | 1288.9 | 1272.7 | 1273.8 | 1275.0 | 1288.9 | 1310.9 | 1304.0 | 1285.4 | 1275.0 |
| 40° | 1269.2 | 1269.2 | 1246.0 | 1215.9 | 1212.4 | 1220.5 | 1243.7 | 1268.0 | 1248.3 | 1227.5 | 1214.7 |
| 42.5° | 1219.3 | 1229.8 | 1207.8 | 1177.6 | 1170.7 | 1184.6 | 1210.1 | 1227.5 | 1204.3 | 1181.1 | 1163.7 |
| 45° | 1173.0 | 1198.5 | 1183.4 | 1149.8 | 1140.5 | 1156.8 | 1189.2 | 1196.2 | 1164.9 | 1142.8 | 1130.1 |
| 47.5° | 1140.5 | 1175.3 | 1164.9 | 1132.4 | 1118.5 | 1141.7 | 1175.3 | 1174.1 | 1134.7 | 1111.6 | 1101.1 |
| 50° | 1117.3 | 1161.4 | 1160.2 | 1132.4 | 1117.3 | 1146.3 | 1176.5 | 1161.4 | 1118.5 | 1094.2 | 1083.7 |
| 52.5° | 1098.8 | 1160.2 | 1168.3 | 1152.1 | 1141.7 | 1167.2 | 1185.7 | 1156.8 | 1106.9 | 1081.4 | 1073.3 |
| 55° | 1090.7 | 1164.9 | 1170.7 | 1155.6 | 1146.3 | 1169.5 | 1185.7 | 1166.0 | 1106.9 | 1083.7 | 1076.8 |
| 57.5° | 1093.0 | 1159.1 | 1160.2 | 1139.4 | 1123.1 | 1152.1 | 1177.6 | 1171.8 | 1119.7 | 1093.0 | 1084.9 |
| 60° | 1079.1 | 1127.8 | 1130.1 | 1097.6 | 1079.1 | 1113.9 | 1159.1 | 1155.6 | 1113.9 | 1086.1 | 1071.0 |
| 62.5° | 1032.7 | 1075.6 | 1076.8 | 1046.6 | 1020.0 | 1069.8 | 1119.7 | 1118.5 | 1080.3 | 1052.4 | 1035.1 |
| 65° | 955.1 | 1000.3 | 1011.9 | 982.9 | 962.0 | 1015.3 | 1067.5 | 1065.2 | 1026.9 | 1001.4 | 984.1 |
| 67.5° | 858.9 | 907.6 | 929.6 | 909.9 | 901.8 | 950.4 | 999.1 | 998.0 | 966.7 | 942.3 | 927.3 |
| 70° | 741.8 | 782.4 | 819.5 | 819.5 | 813.7 | 869.3 | 921.5 | 916.8 | 887.9 | 869.3 | 857.7 |
| 72.5° | 644.4 | 675.7 | 687.3 | 698.9 | 716.3 | 774.3 | 818.3 | 821.8 | 800.9 | 791.6 | 800.9 |
| 75° | 548.2 | 567.9 | 578.4 | 569.1 | 599.2 | 659.5 | 717.5 | 723.3 | 701.2 | 686.2 | 689.6 |
| 77.5° | 450.9 | 472.9 | 483.3 | 462.5 | 460.2 | 536.7 | 607.4 | 620.1 | 601.6 | 578.4 | 585.3 |
| 80° | 325.7 | 354.7 | 372.1 | 358.2 | 353.5 | 387.1 | 484.5 | 498.4 | 481.0 | 462.5 | 472.9 |
| 82.5° | 199.4 | 215.6 | 220.2 | 234.1 | 263.1 | 277.0 | 311.8 | 358.2 | 345.4 | 329.2 | 358.2 |
| 85° | 78.8 | 93.9 | 104.3 | 118.2 | 137.9 | 163.4 | 192.4 | 229.5 | 208.6 | 201.7 | 237.6 |
| 87.5° | 4.6 | 1.2 | 0.0 | 2.3 | 19.7 | 38.2 | 82.3 | 113.6 | 95.0 | 102.0 | 122.9 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P639146
 CATALOG NUMBER: GWS-SA5B-730-U-SLR-W

CANDELA DISTRIBUTION (continued):

| | 285° | 295° | 305° | 315° | 325° | 335° | 345° | 355° | 359° | 360° |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|---------|---------|
| 0° | 2031.9 | 2031.9 | 2031.9 | 2031.9 | 2031.9 | 2031.9 | 2031.9 | 2031.9 | 2031.9 | 2031.9 |
| 2.5° | 1881.2 | 1911.3 | 1951.9 | 1985.5 | 2028.4 | 2068.9 | 2110.7 | 2152.4 | 2174.4 | 2183.7 |
| 5° | 1747.9 | 1803.5 | 1868.4 | 1940.3 | 2023.7 | 2111.8 | 2201.1 | 2292.6 | 2350.6 | 2355.2 |
| 7.5° | 1667.9 | 1747.9 | 1837.1 | 1927.5 | 2030.7 | 2152.4 | 2293.8 | 2435.2 | 2494.3 | 2510.6 |
| 10° | 1693.4 | 1782.7 | 1853.4 | 1938.0 | 2051.6 | 2203.4 | 2370.3 | 2536.1 | 2604.4 | 2624.1 |
| 12.5° | 1795.4 | 1812.8 | 1834.8 | 1912.5 | 2051.6 | 2247.4 | 2449.1 | 2646.2 | 2719.2 | 2737.7 |
| 15° | 1880.0 | 1796.6 | 1757.2 | 1839.5 | 2023.7 | 2285.7 | 2532.6 | 2750.5 | 2838.6 | 2856.0 |
| 17.5° | 1887.0 | 1743.2 | 1657.5 | 1731.7 | 1975.1 | 2312.4 | 2612.6 | 2866.4 | 2940.6 | 2956.8 |
| 20° | 1816.3 | 1686.5 | 1575.2 | 1620.4 | 1909.0 | 2323.9 | 2670.5 | 2951.0 | 3024.0 | 3040.3 |
| 22.5° | 1736.3 | 1640.1 | 1519.5 | 1517.2 | 1829.0 | 2336.7 | 2740.1 | 3031.0 | 3109.8 | 3120.2 |
| 25° | 1661.0 | 1576.3 | 1474.3 | 1441.9 | 1736.3 | 2361.0 | 2833.9 | 3151.5 | 3211.8 | 3215.3 |
| 27.5° | 1572.9 | 1508.0 | 1438.4 | 1407.1 | 1655.2 | 2407.4 | 2973.0 | 3295.2 | 3331.2 | 3325.4 |
| 30° | 1492.9 | 1444.2 | 1412.9 | 1403.6 | 1604.2 | 2442.2 | 3105.2 | 3436.7 | 3439.0 | 3419.3 |
| 32.5° | 1408.3 | 1389.7 | 1389.7 | 1419.9 | 1562.4 | 2434.1 | 3213.0 | 3574.6 | 3552.6 | 3523.6 |
| 35° | 1332.9 | 1336.4 | 1360.8 | 1431.5 | 1492.9 | 2352.9 | 3316.1 | 3747.3 | 3714.8 | 3673.1 |
| 37.5° | 1261.1 | 1287.7 | 1322.5 | 1390.9 | 1401.3 | 2232.4 | 3436.7 | 3991.9 | 3951.3 | 3899.1 |
| 40° | 1199.6 | 1240.2 | 1280.8 | 1314.4 | 1304.0 | 2060.8 | 3604.7 | 4279.3 | 4234.1 | 4173.8 |
| 42.5° | 1151.0 | 1190.4 | 1235.6 | 1239.1 | 1242.5 | 1882.3 | 3783.2 | 4631.7 | 4623.5 | 4557.5 |
| 45° | 1119.7 | 1145.2 | 1188.1 | 1182.3 | 1239.1 | 1685.3 | 3947.8 | 5169.5 | 5276.1 | 5226.3 |
| 47.5° | 1098.8 | 1118.5 | 1123.1 | 1147.5 | 1269.2 | 1509.1 | 4159.9 | 6221.9 | 6518.6 | 6461.8 |
| 50° | 1087.2 | 1106.9 | 1054.8 | 1149.8 | 1273.8 | 1395.5 | 4453.2 | 7543.3 | 8020.8 | 7945.5 |
| 52.5° | 1086.1 | 1081.4 | 1002.6 | 1174.1 | 1248.3 | 1326.0 | 4606.2 | 8507.6 | 9567.0 | 9730.4 |
| 55° | 1088.4 | 1030.4 | 975.9 | 1181.1 | 1197.3 | 1300.5 | 4093.8 | 8971.2 | 10993.8 | 11339.2 |
| 57.5° | 1067.5 | 974.8 | 991.0 | 1153.3 | 1101.1 | 1368.9 | 3026.3 | 8805.5 | 11564.1 | 12206.2 |
| 60° | 1028.1 | 921.5 | 1018.8 | 1077.9 | 1002.6 | 1251.8 | 2084.0 | 8066.0 | 10973.0 | 11633.6 |
| 62.5° | 971.3 | 884.4 | 1015.3 | 980.6 | 966.7 | 1024.6 | 1432.6 | 7030.9 | 10035.3 | 10680.9 |
| 65° | 907.6 | 854.2 | 960.9 | 886.7 | 894.8 | 788.2 | 1013.0 | 5862.6 | 8915.6 | 9550.8 |
| 67.5° | 839.2 | 835.7 | 880.9 | 789.3 | 755.7 | 624.7 | 738.3 | 4698.9 | 7477.2 | 8049.8 |
| 70° | 761.5 | 787.0 | 800.9 | 701.2 | 613.2 | 490.3 | 548.2 | 3286.0 | 5516.0 | 6014.4 |
| 72.5° | 683.9 | 686.2 | 705.9 | 609.7 | 459.0 | 392.9 | 411.5 | 1990.1 | 3747.3 | 4110.1 |
| 75° | 605.0 | 583.0 | 601.6 | 496.1 | 341.9 | 322.2 | 317.6 | 1229.8 | 2588.2 | 2874.5 |
| 77.5° | 520.4 | 496.1 | 471.7 | 373.2 | 274.7 | 249.2 | 243.4 | 689.6 | 1587.9 | 1764.1 |
| 80° | 423.1 | 390.6 | 352.4 | 273.5 | 200.5 | 178.5 | 177.3 | 336.1 | 791.6 | 882.1 |
| 82.5° | 329.2 | 267.7 | 257.3 | 170.4 | 124.0 | 109.0 | 115.9 | 128.7 | 238.8 | 266.6 |
| 85° | 230.7 | 194.7 | 136.8 | 68.4 | 55.6 | 45.2 | 44.0 | 38.2 | 63.7 | 70.7 |
| 87.5° | 128.7 | 84.6 | 44.0 | 8.1 | 9.3 | 10.4 | 8.1 | 5.8 | 5.8 | 5.8 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



LM-79-2008: Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGRAW-EDISON

Report Number: SP1-1908-441-2-R4

Test Date: 10/03/2019

Luminaire Tested: SA1C-730-U-5WQ

Data in this report applies to families of products SA1C-730-U-5WQ .

Test Information

Test Method: LM-79-2008
 Report Number: SP1-1908-441-2-R4
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 10/28/2024
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: McGRAW-EDISON
 Catalog Number: **SA1C-730-U-5WQ**
 Description: McGRAW EDISON ROADWAY AND AREA LUMINAIRE


THIS IS A REVISION OF SP1-1908-441-2-R3. TO UPDATE THE CATALOG INFORMATION.TESTED IN SITU. (1) 70 CRI, 3000K, 1050MA LIGHTSQUARE WITH 16 LEDS AND TYPE V WIDE OPTICS.

Spectral Parameters

CCT (K): 2993
 CIE u': 0.2508
 CIE v': 0.5215
 Duv: 0.0000
 CIE x: 0.4374
 CIE y: 0.4043
 CIE z: 0.1583
 Peak Wavelength (nm): 593
 Dominant Wavelength (nm): 582
 Purity: 53

| | | | |
|-----------|------|------|-------|
| CRI (Ra): | 71.8 | | |
| R1: | 67.5 | R9: | -38.3 |
| R2: | 82.9 | R10: | 62.5 |
| R3: | 94.7 | R11: | 63.7 |
| R4: | 67.7 | R12: | 57.8 |
| R5: | 67.9 | R13: | 70.4 |
| R6: | 77.6 | R14: | 97.3 |
| R7: | 76.0 | | |
| R8: | 40.5 | | |

Rf: 75.7
 Rg: 93.9



Test Conditions

Stabilization Time: 53M
 Operation Time: 12H
 Room Temperature (°C) / RH%: 25.0./44%
 Sphere Temperature (°C): 25.7

REPORT NUMBER: SP1-1908-441-2-R4

| Measurement and Test Equipment | | | |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument | Identification Number | Calibration Date | Calibration Due Date |
| Photometer | IN0058 | 6/28/2019 | 12/28/2019 |
| Power Meter | IN0071 | 12/5/2018 | 12/5/2019 |
| AC Power Source | IN0063 | 12/5/2018 | 12/5/2019 |
| DC Power Source | IN0208 | 12/5/2018 | 12/5/2019 |
| Sphere Thermometer | IN0085 | 12/5/2018 | 12/5/2019 |
| Room Thermometer | IN0046 | 12/5/2018 | 12/5/2019 |

REPORT NUMBER: SP1-1908-441-2-R4

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 3000K 4-step quadrangle

REPORT NUMBER: SP1-1908-441-2-R4

Photopic Flux vs. Wavelength



#####

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 2397 | NR | 490 | 24908 | NR | 620 | 118784 | NR | 750 | 5037 | NR | 880 | 2677 | NR |
| 365 | 2084 | NR | 495 | 30998 | NR | 625 | 108951 | NR | 755 | 4413 | NR | 885 | 2940 | NR |
| 370 | 2143 | NR | 500 | 37103 | NR | 630 | 99573 | NR | 760 | 4189 | NR | 890 | 3116 | NR |
| 375 | 2413 | NR | 505 | 42987 | NR | 635 | 90444 | NR | 765 | 3677 | NR | 895 | 3345 | NR |
| 380 | 2172 | NR | 510 | 48702 | NR | 640 | 80749 | NR | 770 | 3366 | NR | 900 | 2312 | NR |
| 385 | 1997 | NR | 515 | 53741 | NR | 645 | 71664 | NR | 775 | 3211 | NR | 905 | 2829 | NR |
| 390 | 1830 | NR | 520 | 57283 | NR | 650 | 63936 | NR | 780 | 2682 | NR | 910 | 2783 | NR |
| 395 | 1861 | NR | 525 | 61876 | NR | 655 | 56611 | NR | 785 | 2804 | NR | 915 | 2662 | NR |
| 400 | 1717 | NR | 530 | 65398 | NR | 660 | 49763 | NR | 790 | 2581 | NR | 920 | 3047 | NR |
| 405 | 1761 | NR | 535 | 69597 | NR | 665 | 42891 | NR | 795 | 2711 | NR | 925 | 2256 | NR |
| 410 | 2680 | NR | 540 | 74214 | NR | 670 | 36939 | NR | 800 | 2609 | NR | 930 | 2976 | NR |
| 415 | 4374 | NR | 545 | 79911 | NR | 675 | 31946 | NR | 805 | 2581 | NR | 935 | 3503 | NR |
| 420 | 8071 | NR | 550 | 86153 | NR | 680 | 27385 | NR | 810 | 2404 | NR | 940 | 4226 | NR |
| 425 | 15169 | NR | 555 | 93952 | NR | 685 | 23504 | NR | 815 | 2556 | NR | 945 | 2930 | NR |
| 430 | 26038 | NR | 560 | 102904 | NR | 690 | 20210 | NR | 820 | 2742 | NR | 950 | 2115 | NR |
| 435 | 41316 | NR | 565 | 112009 | NR | 695 | 17459 | NR | 825 | 2014 | NR | 955 | 2634 | NR |
| 440 | 59674 | NR | 570 | 121662 | NR | 700 | 15207 | NR | 830 | 2488 | NR | 960 | 4200 | NR |
| 445 | 72751 | NR | 575 | 130476 | NR | 705 | 13322 | NR | 835 | 2625 | NR | 965 | 1982 | NR |
| 450 | 65091 | NR | 580 | 137926 | NR | 710 | 11676 | NR | 840 | 2754 | NR | 970 | 3613 | NR |
| 455 | 44894 | NR | 585 | 143406 | NR | 715 | 10626 | NR | 845 | 2708 | NR | 975 | 4034 | NR |
| 460 | 32712 | NR | 590 | 147039 | NR | 720 | 9416 | NR | 850 | 2608 | NR | 980 | 3922 | NR |
| 465 | 25296 | NR | 595 | 147365 | NR | 725 | 8333 | NR | 855 | 2605 | NR | 985 | 1909 | NR |
| 470 | 19318 | NR | 600 | 145800 | NR | 730 | 7134 | NR | 860 | 1765 | NR | 990 | 3617 | NR |
| 475 | 17265 | NR | 605 | 141363 | NR | 735 | 6437 | NR | 865 | 2581 | NR | 995 | 4767 | NR |
| 480 | 18260 | NR | 610 | 134199 | NR | 740 | 5834 | NR | 870 | 3016 | NR | 1000 | 2528 | NR |
| 485 | 20845 | NR | 615 | 127683 | NR | 745 | 5500 | NR | 875 | 3952 | NR | | | |

REPORT NUMBER: SP1-1908-441-2-R4

Scotopic Flux vs. Wavelength



Scotopic Lumens: 8494.8

S/P: 1.23

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 2397 | NR | 490 | 24908 | NR | 620 | 118784 | NR | 750 | 5037 | NR | 880 | 2677 | NR |
| 365 | 2084 | NR | 495 | 30998 | NR | 625 | 108951 | NR | 755 | 4413 | NR | 885 | 2940 | NR |
| 370 | 2143 | NR | 500 | 37103 | NR | 630 | 99573 | NR | 760 | 4189 | NR | 890 | 3116 | NR |
| 375 | 2413 | NR | 505 | 42987 | NR | 635 | 90444 | NR | 765 | 3677 | NR | 895 | 3345 | NR |
| 380 | 2172 | NR | 510 | 48702 | NR | 640 | 80749 | NR | 770 | 3366 | NR | 900 | 2312 | NR |
| 385 | 1997 | NR | 515 | 53741 | NR | 645 | 71664 | NR | 775 | 3211 | NR | 905 | 2829 | NR |
| 390 | 1830 | NR | 520 | 57283 | NR | 650 | 63936 | NR | 780 | 2682 | NR | 910 | 2783 | NR |
| 395 | 1861 | NR | 525 | 61876 | NR | 655 | 56611 | NR | 785 | 2804 | NR | 915 | 2662 | NR |
| 400 | 1717 | NR | 530 | 65398 | NR | 660 | 49763 | NR | 790 | 2581 | NR | 920 | 3047 | NR |
| 405 | 1761 | NR | 535 | 69597 | NR | 665 | 42891 | NR | 795 | 2711 | NR | 925 | 2256 | NR |
| 410 | 2680 | NR | 540 | 74214 | NR | 670 | 36939 | NR | 800 | 2609 | NR | 930 | 2976 | NR |
| 415 | 4374 | NR | 545 | 79911 | NR | 675 | 31946 | NR | 805 | 2581 | NR | 935 | 3503 | NR |
| 420 | 8071 | NR | 550 | 86153 | NR | 680 | 27385 | NR | 810 | 2404 | NR | 940 | 4226 | NR |
| 425 | 15169 | NR | 555 | 93952 | NR | 685 | 23504 | NR | 815 | 2556 | NR | 945 | 2930 | NR |
| 430 | 26038 | NR | 560 | 102904 | NR | 690 | 20210 | NR | 820 | 2742 | NR | 950 | 2115 | NR |
| 435 | 41316 | NR | 565 | 112009 | NR | 695 | 17459 | NR | 825 | 2014 | NR | 955 | 2634 | NR |
| 440 | 59674 | NR | 570 | 121662 | NR | 700 | 15207 | NR | 830 | 2488 | NR | 960 | 4200 | NR |
| 445 | 72751 | NR | 575 | 130476 | NR | 705 | 13322 | NR | 835 | 2625 | NR | 965 | 1982 | NR |
| 450 | 65091 | NR | 580 | 137926 | NR | 710 | 11676 | NR | 840 | 2754 | NR | 970 | 3613 | NR |
| 455 | 44894 | NR | 585 | 143406 | NR | 715 | 10626 | NR | 845 | 2708 | NR | 975 | 4034 | NR |
| 460 | 32712 | NR | 590 | 147039 | NR | 720 | 9416 | NR | 850 | 2608 | NR | 980 | 3922 | NR |
| 465 | 25296 | NR | 595 | 147365 | NR | 725 | 8333 | NR | 855 | 2605 | NR | 985 | 1909 | NR |
| 470 | 19318 | NR | 600 | 145800 | NR | 730 | 7134 | NR | 860 | 1765 | NR | 990 | 3617 | NR |
| 475 | 17265 | NR | 605 | 141363 | NR | 735 | 6437 | NR | 865 | 2581 | NR | 995 | 4767 | NR |
| 480 | 18260 | NR | 610 | 134199 | NR | 740 | 5834 | NR | 870 | 3016 | NR | 1000 | 2528 | NR |
| 485 | 20845 | NR | 615 | 127683 | NR | 745 | 5500 | NR | 875 | 3952 | NR | | | |

REPORT NUMBER: SP1-1908-441-2-R4

Melanopic Flux vs. Wavelength



Melanopic Lumens: 3101.5 M/P: 0.45

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 2397 | NR | 490 | 24908 | NR | 620 | 118784 | NR | 750 | 5037 | NR | 880 | 2677 | NR |
| 365 | 2084 | NR | 495 | 30998 | NR | 625 | 108951 | NR | 755 | 4413 | NR | 885 | 2940 | NR |
| 370 | 2143 | NR | 500 | 37103 | NR | 630 | 99573 | NR | 760 | 4189 | NR | 890 | 3116 | NR |
| 375 | 2413 | NR | 505 | 42987 | NR | 635 | 90444 | NR | 765 | 3677 | NR | 895 | 3345 | NR |
| 380 | 2172 | NR | 510 | 48702 | NR | 640 | 80749 | NR | 770 | 3366 | NR | 900 | 2312 | NR |
| 385 | 1997 | NR | 515 | 53741 | NR | 645 | 71664 | NR | 775 | 3211 | NR | 905 | 2829 | NR |
| 390 | 1830 | NR | 520 | 57283 | NR | 650 | 63936 | NR | 780 | 2682 | NR | 910 | 2783 | NR |
| 395 | 1861 | NR | 525 | 61876 | NR | 655 | 56611 | NR | 785 | 2804 | NR | 915 | 2662 | NR |
| 400 | 1717 | NR | 530 | 65398 | NR | 660 | 49763 | NR | 790 | 2581 | NR | 920 | 3047 | NR |
| 405 | 1761 | NR | 535 | 69597 | NR | 665 | 42891 | NR | 795 | 2711 | NR | 925 | 2256 | NR |
| 410 | 2680 | NR | 540 | 74214 | NR | 670 | 36939 | NR | 800 | 2609 | NR | 930 | 2976 | NR |
| 415 | 4374 | NR | 545 | 79911 | NR | 675 | 31946 | NR | 805 | 2581 | NR | 935 | 3503 | NR |
| 420 | 8071 | NR | 550 | 86153 | NR | 680 | 27385 | NR | 810 | 2404 | NR | 940 | 4226 | NR |
| 425 | 15169 | NR | 555 | 93952 | NR | 685 | 23504 | NR | 815 | 2556 | NR | 945 | 2930 | NR |
| 430 | 26038 | NR | 560 | 102904 | NR | 690 | 20210 | NR | 820 | 2742 | NR | 950 | 2115 | NR |
| 435 | 41316 | NR | 565 | 112009 | NR | 695 | 17459 | NR | 825 | 2014 | NR | 955 | 2634 | NR |
| 440 | 59674 | NR | 570 | 121662 | NR | 700 | 15207 | NR | 830 | 2488 | NR | 960 | 4200 | NR |
| 445 | 72751 | NR | 575 | 130476 | NR | 705 | 13322 | NR | 835 | 2625 | NR | 965 | 1982 | NR |
| 450 | 65091 | NR | 580 | 137926 | NR | 710 | 11676 | NR | 840 | 2754 | NR | 970 | 3613 | NR |
| 455 | 44894 | NR | 585 | 143406 | NR | 715 | 10626 | NR | 845 | 2708 | NR | 975 | 4034 | NR |
| 460 | 32712 | NR | 590 | 147039 | NR | 720 | 9416 | NR | 850 | 2608 | NR | 980 | 3922 | NR |
| 465 | 25296 | NR | 595 | 147365 | NR | 725 | 8333 | NR | 855 | 2605 | NR | 985 | 1909 | NR |
| 470 | 19318 | NR | 600 | 145800 | NR | 730 | 7134 | NR | 860 | 1765 | NR | 990 | 3617 | NR |
| 475 | 17265 | NR | 605 | 141363 | NR | 735 | 6437 | NR | 865 | 2581 | NR | 995 | 4767 | NR |
| 480 | 18260 | NR | 610 | 134199 | NR | 740 | 5834 | NR | 870 | 3016 | NR | 1000 | 2528 | NR |
| 485 | 20845 | NR | 615 | 127683 | NR | 745 | 5500 | NR | 875 | 3952 | NR | | | |

REPORT NUMBER: SP1-1908-441-2-R4

TM-30-18

Summary

$R_f = 75.7$
 $R_g = 93.9$
 CIE $R_a = 71.8$
 $R_9 = -38.3$



Color Vector Graphics




REPORT NUMBER: SP1-1908-441-2-R4

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)


| | | | |
|------------|------------|------------|------------|
| CES01 = 86 | CES26 = 67 | CES51 = 87 | CES76 = 63 |
| CES02 = 63 | CES27 = 88 | CES52 = 86 | CES77 = 80 |
| CES03 = 31 | CES28 = 87 | CES53 = 78 | CES78 = 67 |
| CES04 = 71 | CES29 = 66 | CES54 = 84 | CES79 = 87 |
| CES05 = 49 | CES30 = 73 | CES55 = 84 | CES80 = 86 |
| CES06 = 51 | CES31 = 70 | CES56 = 75 | CES81 = 71 |
| CES07 = 41 | CES32 = 65 | CES57 = 74 | CES82 = 94 |
| CES08 = 40 | CES33 = 73 | CES58 = 76 | CES83 = 90 |
| CES09 = 29 | CES34 = 79 | CES59 = 85 | CES84 = 89 |
| CES10 = 76 | CES35 = 89 | CES60 = 93 | CES85 = 77 |
| CES11 = 59 | CES36 = 97 | CES61 = 84 | CES86 = 61 |
| CES12 = 65 | CES37 = 87 | CES62 = 91 | CES87 = 78 |
| CES13 = 43 | CES38 = 81 | CES63 = 77 | CES88 = 77 |
| CES14 = 74 | CES39 = 95 | CES64 = 72 | CES89 = 67 |
| CES15 = 71 | CES40 = 92 | CES65 = 68 | CES90 = 76 |
| CES16 = 47 | CES41 = 88 | CES66 = 69 | CES91 = 89 |
| CES17 = 50 | CES42 = 89 | CES67 = 67 | CES92 = 58 |
| CES18 = 56 | CES43 = 79 | CES68 = 72 | CES93 = 74 |
| CES19 = 73 | CES44 = 99 | CES69 = 81 | CES94 = 49 |
| CES20 = 66 | CES45 = 85 | CES70 = 66 | CES95 = 68 |
| CES21 = 87 | CES46 = 80 | CES71 = 67 | CES96 = 76 |
| CES22 = 79 | CES47 = 82 | CES72 = 88 | CES97 = 82 |
| CES23 = 92 | CES48 = 69 | CES73 = 59 | CES98 = 75 |
| CES24 = 91 | CES49 = 80 | CES74 = 95 | CES99 = 62 |
| CES25 = 73 | CES50 = 87 | CES75 = 69 | |



REPORT NUMBER: SP1-1908-441-2-R4

TM-30-18

Color Rendition by Hue-Angle Bin



REPORT NUMBER: SP1-1908-441-2-R4

TM-30-18

Measure Comparisons



(END OF REPORT)