

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: McGRAW-EDISON

Report Number: P629712

Luminaire Tested: GWS-SA1C-730-U-5MQ-W

Issue Date: 1/10/2023

Test Information

Test Method: LM-79-2019
Report Number: P629712
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2209-782-4)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/10/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: McGRAW-EDISON
Catalog Number: GWS-SA1C-730-U-5MQ-W
Description: GALLEON WALL SLIM LUMINAIRE. (1) LIGHTSQUARES WITH 16 LEDS EACH AND TYPE V MEDIUM OPTICS
Light Source: (16) 3000K CCT, 70 CRI LEDS
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4532.7 lumens
Efficiency: N/A
Efficacy: 132.9 lumens/watt
Luminous Opening: Rectangular (W 0.5' x L: 0.5' x H: 0')
IES Classification: Type V - Short
BUG Rating: B3 - U0 - G1


Input Watts (W): 34.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 0
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT



REPORT NUMBER: P629712
 CATALOG NUMBER: GWS-SA1C-730-U-5MQ-W

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 10 foot mounting height. Maximum calculated value = 4.7 fc
 Type V - Short - N/A

REPORT NUMBER: P629712
CATALOG NUMBER: GWS-SA1C-730-U-5MQ-W

Luminous Intensity Polar Plot



— Vertical Plane Through 45-Deg Lateral - - - Horizontal Cone Through 67.5-Deg Vertical

REPORT NUMBER: P629712

CATALOG NUMBER: GWS-SA1C-730-U-5MQ-W


FLUX DISTRIBUTION:

| | | Downward | Upward | Total |
|--------------------|-----------|----------|--------|--------|
| House Side | Lumens | 2266.3 | 0.0 | 2266.3 |
| | % Fixture | 50.0 | 0.0 | 50.0 |
| Street Side | Lumens | 2266.3 | 0.0 | 2266.3 |
| | % Fixture | 50.0 | 0.0 | 50.0 |
| Total | Lumens | 4532.7 | 0.0 | 4532.7 |
| | % Fixture | 100.0 | 0.0 | 100.0 |

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 44.9 | 1.0 |
| 10°-20° | 132.0 | 2.9 |
| 20°-30° | 227.6 | 5.0 |
| 30°-40° | 370.1 | 8.2 |
| 40°-50° | 623.2 | 13.7 |
| 50°-60° | 1104.1 | 24.4 |
| 60°-70° | 1578.3 | 34.8 |
| 70°-80° | 433.2 | 9.6 |
| 80°-90° | 19.4 | 0.4 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-90° | 4532.7 | 100.0 |
| 0°-180° | 4532.7 | 100.0 |

Coefficient of Utilization



REPORT NUMBER: P629712


CATALOG NUMBER: GWS-SA1C-730-U-5MQ-W

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

| Zone | Lumens | % Fixture | Zone Rating/Lumen Limit | | |
|----------------|--------|---------------------------------------|-------------------------|------|---------|
| | | | B | U | G |
| FL (0°-30°) | 202.2 | 4.5 | | | |
| FM (30°-60°) | 1048.7 | 23.1 | | | |
| FH (60°-80°) | 1005.7 | 22.2 | | | G1/1800 |
| FVH (80°-90°) | 9.7 | 0.2 | | | G0/10 |
| BL (0°-30°) | 202.2 | 4.5 | B1/500 | | |
| BM (30°-60°) | 1048.7 | 23.1 | B2/2500 | | |
| BH (60°-80°) | 1005.7 | 22.2 | B3/2500 | | G1/1800 |
| BVH (80°-90°) | 9.7 | 0.2 | | | G0/10 |
| UL (90°-100°) | 0.0 | 0.0 | | U0/0 | |
| UH (100°-180°) | 0.0 | 0.0 <td></td> <td>U0/0</td> <td></td> | | U0/0 | |

BUG Rating: B3-U0-G1

Type V Short





REPORT NUMBER: P629712
 CATALOG NUMBER: GWS-SA1C-730-U-5MQ-W

CANDELA DISTRIBUTION (FULL):

| | 0° | 5° | 15° | 25° | 35° | 45° | 55° | 65° | 75° | 85° | 90° |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 474.7 | 474.7 | 474.7 | 474.7 | 474.7 | 474.7 | 474.7 | 474.7 | 474.7 | 474.7 | 474.7 |
| 2.5° | 471.6 | 471.3 | 472.8 | 473.8 | 473.5 | 475.7 | 475.3 | 474.7 | 474.7 | 473.8 | 476.3 |
| 5° | 471.6 | 471.3 | 472.5 | 472.8 | 472.2 | 474.1 | 473.5 | 472.8 | 472.8 | 471.6 | 473.8 |
| 7.5° | 469.1 | 469.4 | 470.3 | 471.0 | 470.3 | 471.9 | 471.0 | 469.7 | 469.4 | 468.1 | 470.3 |
| 10° | 464.4 | 464.7 | 465.6 | 467.2 | 467.5 | 470.3 | 468.8 | 466.6 | 465.6 | 464.4 | 466.6 |
| 12.5° | 461.5 | 461.9 | 462.8 | 464.7 | 465.3 | 469.1 | 467.5 | 464.1 | 462.5 | 461.2 | 463.4 |
| 15° | 460.9 | 461.2 | 462.5 | 464.4 | 465.3 | 469.1 | 467.5 | 463.4 | 461.2 | 459.7 | 461.5 |
| 17.5° | 460.9 | 461.5 | 463.4 | 466.2 | 468.1 | 471.9 | 470.0 | 465.3 | 462.2 | 459.3 | 461.2 |
| 20° | 461.2 | 462.2 | 465.0 | 469.1 | 473.8 | 479.1 | 476.6 | 470.3 | 465.9 | 462.5 | 463.7 |
| 22.5° | 464.1 | 465.6 | 469.1 | 474.4 | 481.3 | 487.6 | 485.4 | 476.9 | 470.6 | 465.9 | 467.2 |
| 25° | 473.8 | 474.4 | 478.8 | 485.7 | 492.3 | 497.6 | 495.4 | 487.6 | 479.7 | 474.1 | 475.7 |
| 27.5° | 491.0 | 492.6 | 496.4 | 503.6 | 509.2 | 512.1 | 511.7 | 506.4 | 498.6 | 493.5 | 494.8 |
| 30° | 511.7 | 513.3 | 518.3 | 526.5 | 532.1 | 535.3 | 534.3 | 530.3 | 523.0 | 516.1 | 517.4 |
| 32.5° | 535.9 | 536.5 | 542.5 | 551.6 | 557.6 | 562.3 | 559.1 | 554.7 | 545.6 | 537.5 | 538.1 |
| 35° | 566.7 | 567.6 | 573.9 | 582.3 | 587.0 | 590.8 | 590.2 | 585.8 | 576.1 | 567.3 | 569.5 |
| 37.5° | 605.2 | 605.9 | 611.5 | 622.2 | 626.0 | 628.8 | 629.4 | 627.2 | 617.2 | 605.9 | 608.1 |
| 40° | 653.3 | 653.6 | 659.8 | 669.3 | 673.3 | 675.2 | 675.5 | 675.8 | 665.5 | 657.0 | 656.4 |
| 42.5° | 709.1 | 710.7 | 719.5 | 728.6 | 730.4 | 729.5 | 732.6 | 735.8 | 725.7 | 714.1 | 715.1 |
| 45° | 775.9 | 776.9 | 788.8 | 798.8 | 795.4 | 792.2 | 798.2 | 804.5 | 795.4 | 780.3 | 775.9 |
| 47.5° | 855.0 | 856.9 | 869.7 | 879.8 | 874.1 | 868.5 | 878.2 | 884.8 | 870.1 | 854.1 | 850.0 |
| 50° | 944.4 | 945.7 | 963.9 | 976.4 | 969.8 | 959.5 | 971.7 | 978.6 | 958.9 | 939.1 | 930.3 |
| 52.5° | 1050.2 | 1047.6 | 1071.8 | 1093.8 | 1089.7 | 1076.2 | 1086.2 | 1087.5 | 1058.0 | 1030.1 | 1021.3 |
| 55° | 1179.1 | 1176.6 | 1200.8 | 1224.9 | 1235.0 | 1231.5 | 1226.8 | 1219.3 | 1175.7 | 1145.9 | 1137.7 |
| 57.5° | 1329.4 | 1321.6 | 1355.4 | 1388.1 | 1410.0 | 1416.3 | 1396.2 | 1378.7 | 1344.2 | 1307.4 | 1298.0 |
| 60° | 1469.0 | 1468.7 | 1522.4 | 1578.8 | 1639.1 | 1664.2 | 1613.4 | 1565.7 | 1488.2 | 1421.3 | 1407.8 |
| 62.5° | 1508.2 | 1514.8 | 1602.7 | 1742.6 | 1891.4 | 1980.1 | 1846.2 | 1688.3 | 1538.7 | 1438.0 | 1420.1 |
| 65° | 1411.6 | 1427.9 | 1552.8 | 1773.7 | 2067.4 | 2284.5 | 1982.0 | 1691.2 | 1482.5 | 1357.0 | 1338.2 |
| 67.5° | 1040.4 | 1073.1 | 1238.4 | 1600.5 | 2052.3 | 2362.6 | 1957.9 | 1534.6 | 1287.7 | 1138.3 | 1112.3 |
| 70° | 513.3 | 544.4 | 675.5 | 1053.0 | 1688.7 | 2111.9 | 1694.0 | 1156.5 | 869.7 | 726.0 | 702.2 |
| 72.5° | 188.9 | 201.4 | 252.9 | 450.6 | 931.9 | 1560.0 | 1158.4 | 646.0 | 421.4 | 335.4 | 319.4 |
| 75° | 92.6 | 94.8 | 102.6 | 151.2 | 343.9 | 734.2 | 544.4 | 247.9 | 155.0 | 134.9 | 130.5 |
| 77.5° | 59.0 | 59.9 | 63.7 | 72.2 | 110.4 | 231.2 | 165.0 | 97.9 | 75.9 | 72.8 | 72.8 |
| 80° | 32.9 | 33.9 | 38.9 | 44.9 | 51.8 | 79.4 | 59.3 | 58.7 | 49.9 | 43.6 | 42.7 |
| 82.5° | 15.7 | 17.3 | 24.8 | 24.5 | 27.3 | 39.8 | 34.8 | 31.7 | 32.0 | 24.2 | 22.9 |
| 85° | 7.2 | 7.2 | 9.7 | 11.6 | 12.2 | 13.5 | 16.0 | 18.2 | 17.9 | 12.2 | 13.2 |
| 87.5° | 3.5 | 3.5 | 3.5 | 3.1 | 2.8 | 2.5 | 3.5 | 5.6 | 8.2 | 5.6 | 5.3 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



LM-79-2008: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGRAW-EDISON

Report Number: SP1-1908-441-2-R4

Test Date: 10/03/2019

Luminaire Tested: SA1C-730-U-5WQ

Data in this report applies to families of products SA1C-730-U-5WQ .

Test Information

Test Method: LM-79-2008
 Report Number: SP1-1908-441-2-R4
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 10/28/2024
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: McGRAW-EDISON
 Catalog Number: **SA1C-730-U-5WQ**
 Description: McGRAW EDISON ROADWAY AND AREA LUMINAIRE


THIS IS A REVISION OF SP1-1908-441-2-R3. TO UPDATE THE CATALOG INFORMATION.TESTED IN SITU. (1) 70 CRI, 3000K, 1050MA LIGHTSQUARE WITH 16 LEDS AND TYPE V WIDE OPTICS.

Spectral Parameters

CCT (K): 2993
 CIE u': 0.2508
 CIE v': 0.5215
 Duv: 0.0000
 CIE x: 0.4374
 CIE y: 0.4043
 CIE z: 0.1583
 Peak Wavelength (nm): 593
 Dominant Wavelength (nm): 582
 Purity: 53

| | | | |
|-----------|------|------|-------|
| CRI (Ra): | 71.8 | | |
| R1: | 67.5 | R9: | -38.3 |
| R2: | 82.9 | R10: | 62.5 |
| R3: | 94.7 | R11: | 63.7 |
| R4: | 67.7 | R12: | 57.8 |
| R5: | 67.9 | R13: | 70.4 |
| R6: | 77.6 | R14: | 97.3 |
| R7: | 76.0 | | |
| R8: | 40.5 | | |

Rf: 75.7
 Rg: 93.9



Test Conditions


Stabilization Time: 53M
 Operation Time: 12H
 Room Temperature (°C) / RH%: 25.0./44%
 Sphere Temperature (°C): 25.7

REPORT NUMBER: SP1-1908-441-2-R4

| Measurement and Test Equipment | | | |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument | Identification Number | Calibration Date | Calibration Due Date |
| Photometer | IN0058 | 6/28/2019 | 12/28/2019 |
| Power Meter | IN0071 | 12/5/2018 | 12/5/2019 |
| AC Power Source | IN0063 | 12/5/2018 | 12/5/2019 |
| DC Power Source | IN0208 | 12/5/2018 | 12/5/2019 |
| Sphere Thermometer | IN0085 | 12/5/2018 | 12/5/2019 |
| Room Thermometer | IN0046 | 12/5/2018 | 12/5/2019 |

REPORT NUMBER: SP1-1908-441-2-R4

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 3000K 4-step quadrangle

REPORT NUMBER: SP1-1908-441-2-R4

Photopic Flux vs. Wavelength



#####

| λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) |
|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|
| 360 | 2397 | NR | 490 | 24908 | NR | 620 | 118784 | NR | 750 | 5037 | NR | 880 | 2677 | NR |
| 365 | 2084 | NR | 495 | 30998 | NR | 625 | 108951 | NR | 755 | 4413 | NR | 885 | 2940 | NR |
| 370 | 2143 | NR | 500 | 37103 | NR | 630 | 99573 | NR | 760 | 4189 | NR | 890 | 3116 | NR |
| 375 | 2413 | NR | 505 | 42987 | NR | 635 | 90444 | NR | 765 | 3677 | NR | 895 | 3345 | NR |
| 380 | 2172 | NR | 510 | 48702 | NR | 640 | 80749 | NR | 770 | 3366 | NR | 900 | 2312 | NR |
| 385 | 1997 | NR | 515 | 53741 | NR | 645 | 71664 | NR | 775 | 3211 | NR | 905 | 2829 | NR |
| 390 | 1830 | NR | 520 | 57283 | NR | 650 | 63936 | NR | 780 | 2682 | NR | 910 | 2783 | NR |
| 395 | 1861 | NR | 525 | 61876 | NR | 655 | 56611 | NR | 785 | 2804 | NR | 915 | 2662 | NR |
| 400 | 1717 | NR | 530 | 65398 | NR | 660 | 49763 | NR | 790 | 2581 | NR | 920 | 3047 | NR |
| 405 | 1761 | NR | 535 | 69597 | NR | 665 | 42891 | NR | 795 | 2711 | NR | 925 | 2256 | NR |
| 410 | 2680 | NR | 540 | 74214 | NR | 670 | 36939 | NR | 800 | 2609 | NR | 930 | 2976 | NR |
| 415 | 4374 | NR | 545 | 79911 | NR | 675 | 31946 | NR | 805 | 2581 | NR | 935 | 3503 | NR |
| 420 | 8071 | NR | 550 | 86153 | NR | 680 | 27385 | NR | 810 | 2404 | NR | 940 | 4226 | NR |
| 425 | 15169 | NR | 555 | 93952 | NR | 685 | 23504 | NR | 815 | 2556 | NR | 945 | 2930 | NR |
| 430 | 26038 | NR | 560 | 102904 | NR | 690 | 20210 | NR | 820 | 2742 | NR | 950 | 2115 | NR |
| 435 | 41316 | NR | 565 | 112009 | NR | 695 | 17459 | NR | 825 | 2014 | NR | 955 | 2634 | NR |
| 440 | 59674 | NR | 570 | 121662 | NR | 700 | 15207 | NR | 830 | 2488 | NR | 960 | 4200 | NR |
| 445 | 72751 | NR | 575 | 130476 | NR | 705 | 13322 | NR | 835 | 2625 | NR | 965 | 1982 | NR |
| 450 | 65091 | NR | 580 | 137926 | NR | 710 | 11676 | NR | 840 | 2754 | NR | 970 | 3613 | NR |
| 455 | 44894 | NR | 585 | 143406 | NR | 715 | 10626 | NR | 845 | 2708 | NR | 975 | 4034 | NR |
| 460 | 32712 | NR | 590 | 147039 | NR | 720 | 9416 | NR | 850 | 2608 | NR | 980 | 3922 | NR |
| 465 | 25296 | NR | 595 | 147365 | NR | 725 | 8333 | NR | 855 | 2605 | NR | 985 | 1909 | NR |
| 470 | 19318 | NR | 600 | 145800 | NR | 730 | 7134 | NR | 860 | 1765 | NR | 990 | 3617 | NR |
| 475 | 17265 | NR | 605 | 141363 | NR | 735 | 6437 | NR | 865 | 2581 | NR | 995 | 4767 | NR |
| 480 | 18260 | NR | 610 | 134199 | NR | 740 | 5834 | NR | 870 | 3016 | NR | 1000 | 2528 | NR |
| 485 | 20845 | NR | 615 | 127683 | NR | 745 | 5500 | NR | 875 | 3952 | NR | | | |

REPORT NUMBER: SP1-1908-441-2-R4

Scotopic Flux vs. Wavelength



Scotopic Lumens: 8494.8

S/P: 1.23

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 2397 | NR | 490 | 24908 | NR | 620 | 118784 | NR | 750 | 5037 | NR | 880 | 2677 | NR |
| 365 | 2084 | NR | 495 | 30998 | NR | 625 | 108951 | NR | 755 | 4413 | NR | 885 | 2940 | NR |
| 370 | 2143 | NR | 500 | 37103 | NR | 630 | 99573 | NR | 760 | 4189 | NR | 890 | 3116 | NR |
| 375 | 2413 | NR | 505 | 42987 | NR | 635 | 90444 | NR | 765 | 3677 | NR | 895 | 3345 | NR |
| 380 | 2172 | NR | 510 | 48702 | NR | 640 | 80749 | NR | 770 | 3366 | NR | 900 | 2312 | NR |
| 385 | 1997 | NR | 515 | 53741 | NR | 645 | 71664 | NR | 775 | 3211 | NR | 905 | 2829 | NR |
| 390 | 1830 | NR | 520 | 57283 | NR | 650 | 63936 | NR | 780 | 2682 | NR | 910 | 2783 | NR |
| 395 | 1861 | NR | 525 | 61876 | NR | 655 | 56611 | NR | 785 | 2804 | NR | 915 | 2662 | NR |
| 400 | 1717 | NR | 530 | 65398 | NR | 660 | 49763 | NR | 790 | 2581 | NR | 920 | 3047 | NR |
| 405 | 1761 | NR | 535 | 69597 | NR | 665 | 42891 | NR | 795 | 2711 | NR | 925 | 2256 | NR |
| 410 | 2680 | NR | 540 | 74214 | NR | 670 | 36939 | NR | 800 | 2609 | NR | 930 | 2976 | NR |
| 415 | 4374 | NR | 545 | 79911 | NR | 675 | 31946 | NR | 805 | 2581 | NR | 935 | 3503 | NR |
| 420 | 8071 | NR | 550 | 86153 | NR | 680 | 27385 | NR | 810 | 2404 | NR | 940 | 4226 | NR |
| 425 | 15169 | NR | 555 | 93952 | NR | 685 | 23504 | NR | 815 | 2556 | NR | 945 | 2930 | NR |
| 430 | 26038 | NR | 560 | 102904 | NR | 690 | 20210 | NR | 820 | 2742 | NR | 950 | 2115 | NR |
| 435 | 41316 | NR | 565 | 112009 | NR | 695 | 17459 | NR | 825 | 2014 | NR | 955 | 2634 | NR |
| 440 | 59674 | NR | 570 | 121662 | NR | 700 | 15207 | NR | 830 | 2488 | NR | 960 | 4200 | NR |
| 445 | 72751 | NR | 575 | 130476 | NR | 705 | 13322 | NR | 835 | 2625 | NR | 965 | 1982 | NR |
| 450 | 65091 | NR | 580 | 137926 | NR | 710 | 11676 | NR | 840 | 2754 | NR | 970 | 3613 | NR |
| 455 | 44894 | NR | 585 | 143406 | NR | 715 | 10626 | NR | 845 | 2708 | NR | 975 | 4034 | NR |
| 460 | 32712 | NR | 590 | 147039 | NR | 720 | 9416 | NR | 850 | 2608 | NR | 980 | 3922 | NR |
| 465 | 25296 | NR | 595 | 147365 | NR | 725 | 8333 | NR | 855 | 2605 | NR | 985 | 1909 | NR |
| 470 | 19318 | NR | 600 | 145800 | NR | 730 | 7134 | NR | 860 | 1765 | NR | 990 | 3617 | NR |
| 475 | 17265 | NR | 605 | 141363 | NR | 735 | 6437 | NR | 865 | 2581 | NR | 995 | 4767 | NR |
| 480 | 18260 | NR | 610 | 134199 | NR | 740 | 5834 | NR | 870 | 3016 | NR | 1000 | 2528 | NR |
| 485 | 20845 | NR | 615 | 127683 | NR | 745 | 5500 | NR | 875 | 3952 | NR | | | |

REPORT NUMBER: SP1-1908-441-2-R4

Melanopic Flux vs. Wavelength



Melanopic Lumens: 3101.5 M/P: 0.45

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 2397 | NR | 490 | 24908 | NR | 620 | 118784 | NR | 750 | 5037 | NR | 880 | 2677 | NR |
| 365 | 2084 | NR | 495 | 30998 | NR | 625 | 108951 | NR | 755 | 4413 | NR | 885 | 2940 | NR |
| 370 | 2143 | NR | 500 | 37103 | NR | 630 | 99573 | NR | 760 | 4189 | NR | 890 | 3116 | NR |
| 375 | 2413 | NR | 505 | 42987 | NR | 635 | 90444 | NR | 765 | 3677 | NR | 895 | 3345 | NR |
| 380 | 2172 | NR | 510 | 48702 | NR | 640 | 80749 | NR | 770 | 3366 | NR | 900 | 2312 | NR |
| 385 | 1997 | NR | 515 | 53741 | NR | 645 | 71664 | NR | 775 | 3211 | NR | 905 | 2829 | NR |
| 390 | 1830 | NR | 520 | 57283 | NR | 650 | 63936 | NR | 780 | 2682 | NR | 910 | 2783 | NR |
| 395 | 1861 | NR | 525 | 61876 | NR | 655 | 56611 | NR | 785 | 2804 | NR | 915 | 2662 | NR |
| 400 | 1717 | NR | 530 | 65398 | NR | 660 | 49763 | NR | 790 | 2581 | NR | 920 | 3047 | NR |
| 405 | 1761 | NR | 535 | 69597 | NR | 665 | 42891 | NR | 795 | 2711 | NR | 925 | 2256 | NR |
| 410 | 2680 | NR | 540 | 74214 | NR | 670 | 36939 | NR | 800 | 2609 | NR | 930 | 2976 | NR |
| 415 | 4374 | NR | 545 | 79911 | NR | 675 | 31946 | NR | 805 | 2581 | NR | 935 | 3503 | NR |
| 420 | 8071 | NR | 550 | 86153 | NR | 680 | 27385 | NR | 810 | 2404 | NR | 940 | 4226 | NR |
| 425 | 15169 | NR | 555 | 93952 | NR | 685 | 23504 | NR | 815 | 2556 | NR | 945 | 2930 | NR |
| 430 | 26038 | NR | 560 | 102904 | NR | 690 | 20210 | NR | 820 | 2742 | NR | 950 | 2115 | NR |
| 435 | 41316 | NR | 565 | 112009 | NR | 695 | 17459 | NR | 825 | 2014 | NR | 955 | 2634 | NR |
| 440 | 59674 | NR | 570 | 121662 | NR | 700 | 15207 | NR | 830 | 2488 | NR | 960 | 4200 | NR |
| 445 | 72751 | NR | 575 | 130476 | NR | 705 | 13322 | NR | 835 | 2625 | NR | 965 | 1982 | NR |
| 450 | 65091 | NR | 580 | 137926 | NR | 710 | 11676 | NR | 840 | 2754 | NR | 970 | 3613 | NR |
| 455 | 44894 | NR | 585 | 143406 | NR | 715 | 10626 | NR | 845 | 2708 | NR | 975 | 4034 | NR |
| 460 | 32712 | NR | 590 | 147039 | NR | 720 | 9416 | NR | 850 | 2608 | NR | 980 | 3922 | NR |
| 465 | 25296 | NR | 595 | 147365 | NR | 725 | 8333 | NR | 855 | 2605 | NR | 985 | 1909 | NR |
| 470 | 19318 | NR | 600 | 145800 | NR | 730 | 7134 | NR | 860 | 1765 | NR | 990 | 3617 | NR |
| 475 | 17265 | NR | 605 | 141363 | NR | 735 | 6437 | NR | 865 | 2581 | NR | 995 | 4767 | NR |
| 480 | 18260 | NR | 610 | 134199 | NR | 740 | 5834 | NR | 870 | 3016 | NR | 1000 | 2528 | NR |
| 485 | 20845 | NR | 615 | 127683 | NR | 745 | 5500 | NR | 875 | 3952 | NR | | | |

REPORT NUMBER: SP1-1908-441-2-R4


TM-30-18

Summary

$R_f = 75.7$
 $R_g = 93.9$
 CIE $R_a = 71.8$
 $R_9 = -38.3$



Color Vector Graphics




REPORT NUMBER: SP1-1908-441-2-R4

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)

| | | | |
|------------|------------|------------|------------|
| CES01 = 86 | CES26 = 67 | CES51 = 87 | CES76 = 63 |
| CES02 = 63 | CES27 = 88 | CES52 = 86 | CES77 = 80 |
| CES03 = 31 | CES28 = 87 | CES53 = 78 | CES78 = 67 |
| CES04 = 71 | CES29 = 66 | CES54 = 84 | CES79 = 87 |
| CES05 = 49 | CES30 = 73 | CES55 = 84 | CES80 = 86 |
| CES06 = 51 | CES31 = 70 | CES56 = 75 | CES81 = 71 |
| CES07 = 41 | CES32 = 65 | CES57 = 74 | CES82 = 94 |
| CES08 = 40 | CES33 = 73 | CES58 = 76 | CES83 = 90 |
| CES09 = 29 | CES34 = 79 | CES59 = 85 | CES84 = 89 |
| CES10 = 76 | CES35 = 89 | CES60 = 93 | CES85 = 77 |
| CES11 = 59 | CES36 = 97 | CES61 = 84 | CES86 = 61 |
| CES12 = 65 | CES37 = 87 | CES62 = 91 | CES87 = 78 |
| CES13 = 43 | CES38 = 81 | CES63 = 77 | CES88 = 77 |
| CES14 = 74 | CES39 = 95 | CES64 = 72 | CES89 = 67 |
| CES15 = 71 | CES40 = 92 | CES65 = 68 | CES90 = 76 |
| CES16 = 47 | CES41 = 88 | CES66 = 69 | CES91 = 89 |
| CES17 = 50 | CES42 = 89 | CES67 = 67 | CES92 = 58 |
| CES18 = 56 | CES43 = 79 | CES68 = 72 | CES93 = 74 |
| CES19 = 73 | CES44 = 99 | CES69 = 81 | CES94 = 49 |
| CES20 = 66 | CES45 = 85 | CES70 = 66 | CES95 = 68 |
| CES21 = 87 | CES46 = 80 | CES71 = 67 | CES96 = 76 |
| CES22 = 79 | CES47 = 82 | CES72 = 88 | CES97 = 82 |
| CES23 = 92 | CES48 = 69 | CES73 = 59 | CES98 = 75 |
| CES24 = 91 | CES49 = 80 | CES74 = 95 | CES99 = 62 |
| CES25 = 73 | CES50 = 87 | CES75 = 69 | |



REPORT NUMBER: SP1-1908-441-2-R4

TM-30-18

Color Rendition by Hue-Angle Bin



REPORT NUMBER: SP1-1908-441-2-R4

TM-30-18

Measure Comparisons



(END OF REPORT)