

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: McGRAW-EDISON

Report Number: P637157

Luminaire Tested: GWS-SA4C-730-U-SL4-W-HSS

Issue Date: 1/10/2023

**Test Information**

Test Method: LM-79-2019  
Report Number: P637157  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2209-782-36)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 1/10/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: McGRAW-EDISON  
Catalog Number: GWS-SA4C-730-U-SL4-W-HSS  
Description: GALLEON WALL SLIM LUMINAIRE. (4) LIGHTSQUARES WITH 16 LEDS EACH AND TYPE IV SPILL LIGHT ELIMINATOR OPTICS WITH HOUSE SIDE SHIELD  
Light Source: (64) 3000K CCT, 70 CRI LEDS  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 13927.6 lumens  
Efficiency: N/A  
Efficacy: 108.4 lumens/watt  
Luminous Opening: Rectangular (W 1' x L: 1' x H: 0')  
IES Classification: Type IV - Short  
BUG Rating: B1 - U0 - G3  
  
Input Watts (W): 128.5  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 0  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 28.75 FT



REPORT NUMBER: P637157  
 CATALOG NUMBER: GWS-SA4C-730-U-SL4-W-HSS

### Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd  
 - - - 1/2 Max cd



Based on 20 foot mounting height. Maximum calculated value = 6.4 fc  
 Type IV - Short - N/A

REPORT NUMBER: P637157  
CATALOG NUMBER: GWS-SA4C-730-U-SL4-W-HSS

### Luminous Intensity Polar Plot



— Vertical Plane Through 40-Deg Lateral    - - - Horizontal Cone Through 70-Deg Vertical

REPORT NUMBER: P637157  
 CATALOG NUMBER: GWS-SA4C-730-U-SL4-W-HSS

**FLUX DISTRIBUTION:**

|                    |           | Downward | Upward | Total   |
|--------------------|-----------|----------|--------|---------|
| <b>House Side</b>  | Lumens    | 1138.9   | 0.0    | 1138.9  |
|                    | % Fixture | 8.2      | 0.0    | 8.2     |
| <b>Street Side</b> | Lumens    | 12788.7  | 0.0    | 12788.7 |
|                    | % Fixture | 91.8     | 0.0    | 91.8    |
| <b>Total</b>       | Lumens    | 13927.6  | 0.0    | 13927.6 |
|                    | % Fixture | 100.0    | 0.0    | 100.0   |

**ZONAL LUMENS:**

| Zone      | Lumens  | % Fixture |
|-----------|---------|-----------|
| 0°-10°    | 199.8   | 1.4       |
| 10°-20°   | 506.6   | 3.6       |
| 20°-30°   | 847.9   | 6.1       |
| 30°-40°   | 1331.7  | 9.6       |
| 40°-50°   | 2106.5  | 15.1      |
| 50°-60°   | 3072.8  | 22.1      |
| 60°-70°   | 3809.2  | 27.4      |
| 70°-80°   | 1927.2  | 13.8      |
| 80°-90°   | 125.8   | 0.9       |
| 90°-100°  | 0.0     | 0.0       |
| 100°-110° | 0.0     | 0.0       |
| 110°-120° | 0.0     | 0.0       |
| 120°-130° | 0.0     | 0.0       |
| 130°-140° | 0.0     | 0.0       |
| 140°-150° | 0.0     | 0.0       |
| 150°-160° | 0.0     | 0.0       |
| 160°-170° | 0.0     | 0.0       |
| 170°-180° | 0.0     | 0.0       |
| 0°-90°    | 13927.6 | 100.0     |
| 0°-180°   | 13927.6 | 100.0     |

**Coefficient of Utilization**



REPORT NUMBER: P637157


CATALOG NUMBER: GWS-SA4C-730-U-SL4-W-HSS

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

| Zone           | Lumens | % Fixture | Zone Rating/Lumen Limit |      |         |
|----------------|--------|-----------|-------------------------|------|---------|
|                |        |           | B                       | U    | G       |
| FL (0°-30°)    | 1190.6 | 8.5       |                         |      |         |
| FM (30°-60°)   | 5906.5 | 42.4      |                         |      |         |
| FH (60°-80°)   | 5574.1 | 40.0      |                         |      | G3/7500 |
| FVH (80°-90°)  | 117.5  | 0.8       |                         |      | G2/225  |
| BL (0°-30°)    | 363.7  | 2.6       | B1/500                  |      |         |
| BM (30°-60°)   | 604.5  | 4.3       | B1/1000                 |      |         |
| BH (60°-80°)   | 162.4  | 1.2       | B1/500                  |      | G1/500  |
| BVH (80°-90°)  | 8.3    | 0.1       |                         |      | G0/10   |
| UL (90°-100°)  | 0.0    | 0.0       |                         | U0/0 |         |
| UH (100°-180°) | 0.0    | 0.0       |                         | U0/0 |         |

**BUG Rating: B1-U0-G3**

Type IV Short





REPORT NUMBER: P637157

CATALOG NUMBER: GWS-SA4C-730-U-SL4-W-HSS

**CANDELA DISTRIBUTION (FULL):**

|       | 0°     | 5°     | 15°    | 25°    | 35°    | 40°    | 45°    | 55°    | 65°    | 75°    | 85°    |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°    | 2363.3 | 2363.3 | 2363.3 | 2363.3 | 2363.3 | 2363.3 | 2363.3 | 2363.3 | 2363.3 | 2363.3 | 2363.3 |
| 2.5°  | 2540.8 | 2549.6 | 2548.4 | 2552.2 | 2543.3 | 2529.4 | 2526.8 | 2507.8 | 2473.6 | 2430.5 | 2382.4 |
| 5°    | 2592.7 | 2602.8 | 2595.2 | 2591.4 | 2575.0 | 2559.8 | 2556.0 | 2535.7 | 2496.4 | 2438.1 | 2354.5 |
| 7.5°  | 2637.1 | 2639.6 | 2634.5 | 2625.7 | 2601.6 | 2581.3 | 2567.4 | 2539.5 | 2492.6 | 2434.3 | 2338.0 |
| 10°   | 2644.7 | 2643.4 | 2645.9 | 2647.2 | 2632.0 | 2614.3 | 2602.8 | 2564.8 | 2505.3 | 2443.2 | 2339.3 |
| 12.5° | 2635.8 | 2635.8 | 2652.3 | 2671.3 | 2671.3 | 2662.4 | 2651.0 | 2616.8 | 2547.1 | 2473.6 | 2364.6 |
| 15°   | 2647.2 | 2651.0 | 2682.7 | 2718.2 | 2729.6 | 2720.7 | 2715.6 | 2680.1 | 2607.9 | 2526.8 | 2410.2 |
| 17.5° | 2687.8 | 2691.6 | 2742.2 | 2795.5 | 2809.4 | 2799.3 | 2789.1 | 2753.6 | 2676.3 | 2587.6 | 2462.2 |
| 20°   | 2747.3 | 2757.4 | 2822.1 | 2890.5 | 2903.2 | 2890.5 | 2870.2 | 2820.8 | 2743.5 | 2653.5 | 2511.6 |
| 22.5° | 2856.3 | 2862.6 | 2932.3 | 3004.6 | 3010.9 | 2990.6 | 2960.2 | 2891.8 | 2810.7 | 2723.2 | 2567.4 |
| 25°   | 3000.8 | 3009.6 | 3079.3 | 3149.0 | 3132.5 | 3102.1 | 3060.3 | 2983.0 | 2890.5 | 2805.6 | 2638.3 |
| 27.5° | 3173.1 | 3183.2 | 3251.7 | 3312.5 | 3269.4 | 3233.9 | 3187.0 | 3090.7 | 2997.0 | 2919.7 | 2729.6 |
| 30°   | 3359.4 | 3368.2 | 3429.1 | 3483.6 | 3426.5 | 3384.7 | 3329.0 | 3230.1 | 3135.1 | 3076.8 | 2858.8 |
| 32.5° | 3539.3 | 3538.1 | 3596.3 | 3640.7 | 3582.4 | 3549.5 | 3498.8 | 3398.7 | 3322.6 | 3297.3 | 3051.4 |
| 35°   | 3706.6 | 3706.6 | 3754.7 | 3799.1 | 3757.3 | 3739.5 | 3692.7 | 3612.8 | 3569.7 | 3600.1 | 3308.7 |
| 37.5° | 3875.1 | 3866.3 | 3911.9 | 3961.3 | 3957.5 | 3958.8 | 3932.2 | 3894.1 | 3896.7 | 4004.4 | 3662.2 |
| 40°   | 4014.5 | 4010.7 | 4063.9 | 4128.6 | 4179.3 | 4219.8 | 4203.3 | 4217.3 | 4297.1 | 4498.6 | 4114.6 |
| 42.5° | 4126.0 | 4134.9 | 4203.3 | 4306.0 | 4434.0 | 4516.3 | 4527.7 | 4584.8 | 4790.1 | 5101.8 | 4625.3 |
| 45°   | 4254.0 | 4255.3 | 4350.3 | 4507.5 | 4711.5 | 4842.0 | 4887.6 | 5034.6 | 5326.1 | 5727.8 | 5185.4 |
| 47.5° | 4411.2 | 4396.0 | 4502.4 | 4722.9 | 5018.2 | 5210.8 | 5291.9 | 5475.6 | 5926.7 | 6338.6 | 5641.6 |
| 50°   | 4584.8 | 4556.9 | 4677.3 | 4977.6 | 5361.6 | 5602.3 | 5767.1 | 6035.7 | 6522.3 | 6840.4 | 5981.2 |
| 52.5° | 4786.3 | 4759.6 | 4896.5 | 5270.3 | 5773.4 | 6066.1 | 6277.8 | 6548.9 | 7033.0 | 7223.1 | 6184.0 |
| 55°   | 5042.2 | 5015.6 | 5160.1 | 5621.3 | 6260.0 | 6640.2 | 6861.9 | 7090.0 | 7508.2 | 7505.7 | 6331.0 |
| 57.5° | 5326.1 | 5289.3 | 5489.6 | 6064.9 | 6867.0 | 7262.4 | 7487.9 | 7599.5 | 7869.4 | 7724.9 | 6429.8 |
| 60°   | 5651.8 | 5618.8 | 5896.3 | 6593.3 | 7567.8 | 7934.0 | 8075.9 | 8030.3 | 8165.9 | 7854.2 | 6395.6 |
| 62.5° | 5945.7 | 5930.5 | 6275.2 | 7153.4 | 8235.6 | 8544.8 | 8584.1 | 8385.1 | 8383.9 | 7856.7 | 6165.0 |
| 65°   | 6251.1 | 6280.3 | 6792.2 | 7798.4 | 8907.2 | 9115.0 | 9047.9 | 8737.4 | 8471.3 | 7546.2 | 5483.2 |
| 67.5° | 6365.2 | 6450.1 | 7133.1 | 8381.3 | 9436.9 | 9599.1 | 9481.3 | 8913.6 | 8107.6 | 6502.1 | 4175.5 |
| 70°   | 5660.6 | 5820.3 | 6811.3 | 8414.3 | 9656.1 | 9810.7 | 9528.2 | 8439.6 | 6759.3 | 4307.2 | 2287.3 |
| 72.5° | 4304.7 | 4491.0 | 5675.8 | 6889.8 | 8684.2 | 9036.5 | 8553.7 | 6875.9 | 4356.7 | 1886.9 | 767.9  |
| 75°   | 2409.0 | 2610.5 | 4227.4 | 5188.0 | 5830.4 | 6152.3 | 5974.9 | 4411.2 | 1930.0 | 492.9  | 229.4  |
| 77.5° | 814.8  | 882.0  | 1966.7 | 3209.8 | 3848.5 | 3559.6 | 3013.4 | 2191.0 | 709.6  | 187.5  | 121.7  |
| 80°   | 482.8  | 508.2  | 732.4  | 1598.0 | 2025.0 | 1679.1 | 1325.5 | 809.7  | 361.2  | 100.1  | 84.9   |
| 82.5° | 144.5  | 171.1  | 404.2  | 593.1  | 793.3  | 494.2  | 418.2  | 462.5  | 187.5  | 54.5   | 71.0   |
| 85°   | 0.0    | 0.0    | 86.2   | 183.7  | 207.8  | 81.1   | 81.1   | 262.3  | 34.2   | 22.8   | 52.0   |
| 87.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 1.3    | 6.3    | 3.8    | 5.1    | 11.4   |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



REPORT NUMBER: P637157  
 CATALOG NUMBER: GWS-SA4C-730-U-SL4-W-HSS

**CANDELA DISTRIBUTION (continued):**

|       | 90°    | 95°    | 105°   | 115°   | 125°   | 135°   | 145°   | 155°   | 165°   | 175°   | 180°   |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°    | 2363.3 | 2363.3 | 2363.3 | 2363.3 | 2363.3 | 2363.3 | 2363.3 | 2363.3 | 2363.3 | 2363.3 | 2363.3 |
| 2.5°  | 2348.1 | 2303.8 | 2251.8 | 2202.4 | 2155.5 | 2094.7 | 2065.6 | 2030.1 | 1999.7 | 1983.2 | 1992.1 |
| 5°    | 2301.3 | 2231.6 | 2125.1 | 2017.4 | 1908.4 | 1805.8 | 1713.3 | 1651.2 | 1595.4 | 1566.3 | 1572.6 |
| 7.5°  | 2260.7 | 2166.9 | 2000.9 | 1824.8 | 1649.9 | 1473.8 | 1330.6 | 1219.1 | 1132.9 | 1097.4 | 1091.1 |
| 10°   | 2243.0 | 2125.1 | 1890.7 | 1637.2 | 1368.6 | 1131.6 | 928.9  | 805.9  | 718.5  | 675.4  | 683.0  |
| 12.5° | 2251.8 | 2103.6 | 1796.9 | 1453.5 | 1105.0 | 828.8  | 634.9  | 519.6  | 457.5  | 432.1  | 425.8  |
| 15°   | 2277.2 | 2098.5 | 1713.3 | 1265.9 | 852.8  | 579.1  | 438.5  | 391.6  | 378.9  | 376.4  | 376.4  |
| 17.5° | 2306.3 | 2099.8 | 1627.1 | 1075.9 | 647.5  | 429.6  | 375.1  | 366.2  | 362.4  | 359.9  | 361.2  |
| 20°   | 2335.5 | 2099.8 | 1528.3 | 883.2  | 486.6  | 371.3  | 357.4  | 351.0  | 347.2  | 345.9  | 345.9  |
| 22.5° | 2371.0 | 2099.8 | 1418.0 | 704.6  | 390.3  | 352.3  | 340.9  | 337.1  | 333.3  | 332.0  | 330.7  |
| 25°   | 2414.0 | 2101.0 | 1296.4 | 551.2  | 354.8  | 335.8  | 326.9  | 323.1  | 319.3  | 316.8  | 316.8  |
| 27.5° | 2476.1 | 2111.2 | 1162.0 | 429.6  | 334.5  | 320.6  | 313.0  | 309.2  | 305.4  | 301.6  | 301.6  |
| 30°   | 2566.1 | 2136.5 | 1011.2 | 354.8  | 315.5  | 304.1  | 296.5  | 294.0  | 290.2  | 286.4  | 285.1  |
| 32.5° | 2700.4 | 2180.9 | 855.4  | 318.1  | 297.8  | 286.4  | 277.5  | 275.0  | 271.2  | 267.4  | 266.1  |
| 35°   | 2888.0 | 2262.0 | 703.3  | 295.3  | 275.0  | 263.6  | 258.5  | 257.2  | 252.2  | 248.4  | 248.4  |
| 37.5° | 3163.0 | 2393.8 | 557.6  | 272.5  | 256.0  | 247.1  | 240.8  | 238.2  | 233.2  | 229.4  | 228.1  |
| 40°   | 3498.8 | 2564.8 | 433.4  | 254.7  | 238.2  | 229.4  | 223.0  | 219.2  | 212.9  | 207.8  | 205.3  |
| 42.5° | 3927.1 | 2773.9 | 342.1  | 235.7  | 221.8  | 212.9  | 207.8  | 200.2  | 191.3  | 183.7  | 182.5  |
| 45°   | 4373.1 | 2989.3 | 282.6  | 218.0  | 206.6  | 199.0  | 192.6  | 182.5  | 169.8  | 160.9  | 158.4  |
| 47.5° | 4715.3 | 3123.7 | 247.1  | 199.0  | 190.1  | 183.7  | 176.1  | 163.5  | 148.3  | 138.1  | 135.6  |
| 50°   | 4959.9 | 3143.9 | 220.5  | 181.2  | 176.1  | 169.8  | 158.4  | 143.2  | 126.7  | 116.6  | 114.0  |
| 52.5° | 5080.2 | 3052.7 | 199.0  | 164.7  | 160.9  | 154.6  | 140.7  | 124.2  | 106.4  | 96.3   | 93.8   |
| 55°   | 5134.7 | 2880.4 | 178.7  | 150.8  | 145.7  | 138.1  | 122.9  | 105.2  | 87.4   | 78.6   | 76.0   |
| 57.5° | 5113.2 | 2625.7 | 160.9  | 136.9  | 130.5  | 121.7  | 105.2  | 86.2   | 72.2   | 63.4   | 62.1   |
| 60°   | 4953.5 | 2268.3 | 143.2  | 122.9  | 115.3  | 105.2  | 88.7   | 71.0   | 58.3   | 52.0   | 50.7   |
| 62.5° | 4608.8 | 1824.8 | 125.5  | 106.4  | 101.4  | 91.2   | 76.0   | 58.3   | 48.2   | 44.4   | 43.1   |
| 65°   | 3903.0 | 1290.0 | 107.7  | 90.0   | 87.4   | 77.3   | 63.4   | 48.2   | 41.8   | 39.3   | 38.0   |
| 67.5° | 2805.6 | 784.4  | 91.2   | 77.3   | 74.8   | 65.9   | 53.2   | 41.8   | 38.0   | 36.7   | 36.7   |
| 70°   | 1410.4 | 371.3  | 72.2   | 63.4   | 63.4   | 54.5   | 45.6   | 38.0   | 36.7   | 35.5   | 35.5   |
| 72.5° | 479.0  | 158.4  | 54.5   | 49.4   | 52.0   | 46.9   | 39.3   | 35.5   | 35.5   | 35.5   | 35.5   |
| 75°   | 163.5  | 83.6   | 38.0   | 35.5   | 38.0   | 38.0   | 34.2   | 34.2   | 35.5   | 35.5   | 35.5   |
| 77.5° | 106.4  | 55.8   | 26.6   | 24.1   | 29.1   | 29.1   | 29.1   | 31.7   | 34.2   | 34.2   | 34.2   |
| 80°   | 87.4   | 30.4   | 17.7   | 16.5   | 21.5   | 21.5   | 24.1   | 29.1   | 31.7   | 31.7   | 31.7   |
| 82.5° | 74.8   | 19.0   | 10.1   | 11.4   | 15.2   | 16.5   | 20.3   | 24.1   | 27.9   | 29.1   | 29.1   |
| 85°   | 50.7   | 10.1   | 7.6    | 8.9    | 10.1   | 12.7   | 16.5   | 20.3   | 22.8   | 25.3   | 25.3   |
| 87.5° | 13.9   | 3.8    | 5.1    | 6.3    | 6.3    | 8.9    | 12.7   | 15.2   | 17.7   | 19.0   | 19.0   |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



LM-79-2008: Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGRAW-EDISON

Report Number: SP1-1908-441-2-R4

Test Date: 10/03/2019

Luminaire Tested: SA1C-730-U-5WQ

Data in this report applies to families of products SA1C-730-U-5WQ .

**Test Information**

Test Method: LM-79-2008  
 Report Number: SP1-1908-441-2-R4  
 Test Lab: COOPER LIGHTING SOLUTIONS  
 Photometer: SP1 - 76IN SPHERE  
 Measurement Geometry: 4π  
 Issue Date: 10/28/2024  
 Manufacturer: COOPER LIGHTING SOLUTIONS  
 Product Line: McGRAW-EDISON  
 Catalog Number: **SA1C-730-U-5WQ**  
 Description: McGRAW EDISON ROADWAY AND AREA LUMINAIRE

\*\*\*THIS IS A REVISION OF SP1-1908-441-2-R3. TO UPDATE THE CATALOG INFORMATION.\*\*\*TESTED IN SITU. (1) 70 CRI, 3000K, 1050MA LIGHTSQUARE WITH 16 LEDS AND TYPE V WIDE OPTICS.

**Spectral Parameters**

CCT (K): 2993  
 CIE u': 0.2508  
 CIE v': 0.5215  
 Duv: 0.0000  
 CIE x: 0.4374  
 CIE y: 0.4043  
 CIE z: 0.1583  
 Peak Wavelength (nm): 593  
 Dominant Wavelength (nm): 582  
 Purity: 53

|           |      |      |       |
|-----------|------|------|-------|
| CRI (Ra): | 71.8 |      |       |
| R1:       | 67.5 | R9:  | -38.3 |
| R2:       | 82.9 | R10: | 62.5  |
| R3:       | 94.7 | R11: | 63.7  |
| R4:       | 67.7 | R12: | 57.8  |
| R5:       | 67.9 | R13: | 70.4  |
| R6:       | 77.6 | R14: | 97.3  |
| R7:       | 76.0 |      |       |
| R8:       | 40.5 |      |       |

Rf: 75.7  
 Rg: 93.9



**Test Conditions**

Stabilization Time: 53M  
 Operation Time: 12H  
 Room Temperature (°C) / RH%: 25.0./44%  
 Sphere Temperature (°C): 25.7

REPORT NUMBER: SP1-1908-441-2-R4

| Measurement and Test Equipment |                       |                  |                      |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument                     | Identification Number | Calibration Date | Calibration Due Date |
| Photometer                     | IN0058                | 6/28/2019        | 12/28/2019           |
| Power Meter                    | IN0071                | 12/5/2018        | 12/5/2019            |
| AC Power Source                | IN0063                | 12/5/2018        | 12/5/2019            |
| DC Power Source                | IN0208                | 12/5/2018        | 12/5/2019            |
| Sphere Thermometer             | IN0085                | 12/5/2018        | 12/5/2019            |
| Room Thermometer               | IN0046                | 12/5/2018        | 12/5/2019            |

REPORT NUMBER: SP1-1908-441-2-R4

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 3000K 4-step quadrangle

REPORT NUMBER: SP1-1908-441-2-R4

**Photopic Flux vs. Wavelength**



#####

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360    | 2397          | NR            | 490    | 24908         | NR            | 620    | 118784        | NR            | 750    | 5037          | NR            | 880    | 2677          | NR            |
| 365    | 2084          | NR            | 495    | 30998         | NR            | 625    | 108951        | NR            | 755    | 4413          | NR            | 885    | 2940          | NR            |
| 370    | 2143          | NR            | 500    | 37103         | NR            | 630    | 99573         | NR            | 760    | 4189          | NR            | 890    | 3116          | NR            |
| 375    | 2413          | NR            | 505    | 42987         | NR            | 635    | 90444         | NR            | 765    | 3677          | NR            | 895    | 3345          | NR            |
| 380    | 2172          | NR            | 510    | 48702         | NR            | 640    | 80749         | NR            | 770    | 3366          | NR            | 900    | 2312          | NR            |
| 385    | 1997          | NR            | 515    | 53741         | NR            | 645    | 71664         | NR            | 775    | 3211          | NR            | 905    | 2829          | NR            |
| 390    | 1830          | NR            | 520    | 57283         | NR            | 650    | 63936         | NR            | 780    | 2682          | NR            | 910    | 2783          | NR            |
| 395    | 1861          | NR            | 525    | 61876         | NR            | 655    | 56611         | NR            | 785    | 2804          | NR            | 915    | 2662          | NR            |
| 400    | 1717          | NR            | 530    | 65398         | NR            | 660    | 49763         | NR            | 790    | 2581          | NR            | 920    | 3047          | NR            |
| 405    | 1761          | NR            | 535    | 69597         | NR            | 665    | 42891         | NR            | 795    | 2711          | NR            | 925    | 2256          | NR            |
| 410    | 2680          | NR            | 540    | 74214         | NR            | 670    | 36939         | NR            | 800    | 2609          | NR            | 930    | 2976          | NR            |
| 415    | 4374          | NR            | 545    | 79911         | NR            | 675    | 31946         | NR            | 805    | 2581          | NR            | 935    | 3503          | NR            |
| 420    | 8071          | NR            | 550    | 86153         | NR            | 680    | 27385         | NR            | 810    | 2404          | NR            | 940    | 4226          | NR            |
| 425    | 15169         | NR            | 555    | 93952         | NR            | 685    | 23504         | NR            | 815    | 2556          | NR            | 945    | 2930          | NR            |
| 430    | 26038         | NR            | 560    | 102904        | NR            | 690    | 20210         | NR            | 820    | 2742          | NR            | 950    | 2115          | NR            |
| 435    | 41316         | NR            | 565    | 112009        | NR            | 695    | 17459         | NR            | 825    | 2014          | NR            | 955    | 2634          | NR            |
| 440    | 59674         | NR            | 570    | 121662        | NR            | 700    | 15207         | NR            | 830    | 2488          | NR            | 960    | 4200          | NR            |
| 445    | 72751         | NR            | 575    | 130476        | NR            | 705    | 13322         | NR            | 835    | 2625          | NR            | 965    | 1982          | NR            |
| 450    | 65091         | NR            | 580    | 137926        | NR            | 710    | 11676         | NR            | 840    | 2754          | NR            | 970    | 3613          | NR            |
| 455    | 44894         | NR            | 585    | 143406        | NR            | 715    | 10626         | NR            | 845    | 2708          | NR            | 975    | 4034          | NR            |
| 460    | 32712         | NR            | 590    | 147039        | NR            | 720    | 9416          | NR            | 850    | 2608          | NR            | 980    | 3922          | NR            |
| 465    | 25296         | NR            | 595    | 147365        | NR            | 725    | 8333          | NR            | 855    | 2605          | NR            | 985    | 1909          | NR            |
| 470    | 19318         | NR            | 600    | 145800        | NR            | 730    | 7134          | NR            | 860    | 1765          | NR            | 990    | 3617          | NR            |
| 475    | 17265         | NR            | 605    | 141363        | NR            | 735    | 6437          | NR            | 865    | 2581          | NR            | 995    | 4767          | NR            |
| 480    | 18260         | NR            | 610    | 134199        | NR            | 740    | 5834          | NR            | 870    | 3016          | NR            | 1000   | 2528          | NR            |
| 485    | 20845         | NR            | 615    | 127683        | NR            | 745    | 5500          | NR            | 875    | 3952          | NR            |        |               |               |

REPORT NUMBER: SP1-1908-441-2-R4

Scotopic Flux vs. Wavelength



Scotopic Lumens: 8494.8

S/P: 1.23

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360    | 2397          | NR            | 490    | 24908         | NR            | 620    | 118784        | NR            | 750    | 5037          | NR            | 880    | 2677          | NR            |
| 365    | 2084          | NR            | 495    | 30998         | NR            | 625    | 108951        | NR            | 755    | 4413          | NR            | 885    | 2940          | NR            |
| 370    | 2143          | NR            | 500    | 37103         | NR            | 630    | 99573         | NR            | 760    | 4189          | NR            | 890    | 3116          | NR            |
| 375    | 2413          | NR            | 505    | 42987         | NR            | 635    | 90444         | NR            | 765    | 3677          | NR            | 895    | 3345          | NR            |
| 380    | 2172          | NR            | 510    | 48702         | NR            | 640    | 80749         | NR            | 770    | 3366          | NR            | 900    | 2312          | NR            |
| 385    | 1997          | NR            | 515    | 53741         | NR            | 645    | 71664         | NR            | 775    | 3211          | NR            | 905    | 2829          | NR            |
| 390    | 1830          | NR            | 520    | 57283         | NR            | 650    | 63936         | NR            | 780    | 2682          | NR            | 910    | 2783          | NR            |
| 395    | 1861          | NR            | 525    | 61876         | NR            | 655    | 56611         | NR            | 785    | 2804          | NR            | 915    | 2662          | NR            |
| 400    | 1717          | NR            | 530    | 65398         | NR            | 660    | 49763         | NR            | 790    | 2581          | NR            | 920    | 3047          | NR            |
| 405    | 1761          | NR            | 535    | 69597         | NR            | 665    | 42891         | NR            | 795    | 2711          | NR            | 925    | 2256          | NR            |
| 410    | 2680          | NR            | 540    | 74214         | NR            | 670    | 36939         | NR            | 800    | 2609          | NR            | 930    | 2976          | NR            |
| 415    | 4374          | NR            | 545    | 79911         | NR            | 675    | 31946         | NR            | 805    | 2581          | NR            | 935    | 3503          | NR            |
| 420    | 8071          | NR            | 550    | 86153         | NR            | 680    | 27385         | NR            | 810    | 2404          | NR            | 940    | 4226          | NR            |
| 425    | 15169         | NR            | 555    | 93952         | NR            | 685    | 23504         | NR            | 815    | 2556          | NR            | 945    | 2930          | NR            |
| 430    | 26038         | NR            | 560    | 102904        | NR            | 690    | 20210         | NR            | 820    | 2742          | NR            | 950    | 2115          | NR            |
| 435    | 41316         | NR            | 565    | 112009        | NR            | 695    | 17459         | NR            | 825    | 2014          | NR            | 955    | 2634          | NR            |
| 440    | 59674         | NR            | 570    | 121662        | NR            | 700    | 15207         | NR            | 830    | 2488          | NR            | 960    | 4200          | NR            |
| 445    | 72751         | NR            | 575    | 130476        | NR            | 705    | 13322         | NR            | 835    | 2625          | NR            | 965    | 1982          | NR            |
| 450    | 65091         | NR            | 580    | 137926        | NR            | 710    | 11676         | NR            | 840    | 2754          | NR            | 970    | 3613          | NR            |
| 455    | 44894         | NR            | 585    | 143406        | NR            | 715    | 10626         | NR            | 845    | 2708          | NR            | 975    | 4034          | NR            |
| 460    | 32712         | NR            | 590    | 147039        | NR            | 720    | 9416          | NR            | 850    | 2608          | NR            | 980    | 3922          | NR            |
| 465    | 25296         | NR            | 595    | 147365        | NR            | 725    | 8333          | NR            | 855    | 2605          | NR            | 985    | 1909          | NR            |
| 470    | 19318         | NR            | 600    | 145800        | NR            | 730    | 7134          | NR            | 860    | 1765          | NR            | 990    | 3617          | NR            |
| 475    | 17265         | NR            | 605    | 141363        | NR            | 735    | 6437          | NR            | 865    | 2581          | NR            | 995    | 4767          | NR            |
| 480    | 18260         | NR            | 610    | 134199        | NR            | 740    | 5834          | NR            | 870    | 3016          | NR            | 1000   | 2528          | NR            |
| 485    | 20845         | NR            | 615    | 127683        | NR            | 745    | 5500          | NR            | 875    | 3952          | NR            |        |               |               |

REPORT NUMBER: SP1-1908-441-2-R4

**Melanopic Flux vs. Wavelength**



**Melanopic Lumens: 3101.5 M/P: 0.45**

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360    | 2397          | NR            | 490    | 24908         | NR            | 620    | 118784        | NR            | 750    | 5037          | NR            | 880    | 2677          | NR            |
| 365    | 2084          | NR            | 495    | 30998         | NR            | 625    | 108951        | NR            | 755    | 4413          | NR            | 885    | 2940          | NR            |
| 370    | 2143          | NR            | 500    | 37103         | NR            | 630    | 99573         | NR            | 760    | 4189          | NR            | 890    | 3116          | NR            |
| 375    | 2413          | NR            | 505    | 42987         | NR            | 635    | 90444         | NR            | 765    | 3677          | NR            | 895    | 3345          | NR            |
| 380    | 2172          | NR            | 510    | 48702         | NR            | 640    | 80749         | NR            | 770    | 3366          | NR            | 900    | 2312          | NR            |
| 385    | 1997          | NR            | 515    | 53741         | NR            | 645    | 71664         | NR            | 775    | 3211          | NR            | 905    | 2829          | NR            |
| 390    | 1830          | NR            | 520    | 57283         | NR            | 650    | 63936         | NR            | 780    | 2682          | NR            | 910    | 2783          | NR            |
| 395    | 1861          | NR            | 525    | 61876         | NR            | 655    | 56611         | NR            | 785    | 2804          | NR            | 915    | 2662          | NR            |
| 400    | 1717          | NR            | 530    | 65398         | NR            | 660    | 49763         | NR            | 790    | 2581          | NR            | 920    | 3047          | NR            |
| 405    | 1761          | NR            | 535    | 69597         | NR            | 665    | 42891         | NR            | 795    | 2711          | NR            | 925    | 2256          | NR            |
| 410    | 2680          | NR            | 540    | 74214         | NR            | 670    | 36939         | NR            | 800    | 2609          | NR            | 930    | 2976          | NR            |
| 415    | 4374          | NR            | 545    | 79911         | NR            | 675    | 31946         | NR            | 805    | 2581          | NR            | 935    | 3503          | NR            |
| 420    | 8071          | NR            | 550    | 86153         | NR            | 680    | 27385         | NR            | 810    | 2404          | NR            | 940    | 4226          | NR            |
| 425    | 15169         | NR            | 555    | 93952         | NR            | 685    | 23504         | NR            | 815    | 2556          | NR            | 945    | 2930          | NR            |
| 430    | 26038         | NR            | 560    | 102904        | NR            | 690    | 20210         | NR            | 820    | 2742          | NR            | 950    | 2115          | NR            |
| 435    | 41316         | NR            | 565    | 112009        | NR            | 695    | 17459         | NR            | 825    | 2014          | NR            | 955    | 2634          | NR            |
| 440    | 59674         | NR            | 570    | 121662        | NR            | 700    | 15207         | NR            | 830    | 2488          | NR            | 960    | 4200          | NR            |
| 445    | 72751         | NR            | 575    | 130476        | NR            | 705    | 13322         | NR            | 835    | 2625          | NR            | 965    | 1982          | NR            |
| 450    | 65091         | NR            | 580    | 137926        | NR            | 710    | 11676         | NR            | 840    | 2754          | NR            | 970    | 3613          | NR            |
| 455    | 44894         | NR            | 585    | 143406        | NR            | 715    | 10626         | NR            | 845    | 2708          | NR            | 975    | 4034          | NR            |
| 460    | 32712         | NR            | 590    | 147039        | NR            | 720    | 9416          | NR            | 850    | 2608          | NR            | 980    | 3922          | NR            |
| 465    | 25296         | NR            | 595    | 147365        | NR            | 725    | 8333          | NR            | 855    | 2605          | NR            | 985    | 1909          | NR            |
| 470    | 19318         | NR            | 600    | 145800        | NR            | 730    | 7134          | NR            | 860    | 1765          | NR            | 990    | 3617          | NR            |
| 475    | 17265         | NR            | 605    | 141363        | NR            | 735    | 6437          | NR            | 865    | 2581          | NR            | 995    | 4767          | NR            |
| 480    | 18260         | NR            | 610    | 134199        | NR            | 740    | 5834          | NR            | 870    | 3016          | NR            | 1000   | 2528          | NR            |
| 485    | 20845         | NR            | 615    | 127683        | NR            | 745    | 5500          | NR            | 875    | 3952          | NR            |        |               |               |

REPORT NUMBER: SP1-1908-441-2-R4

TM-30-18

**Summary**

$R_f = 75.7$   
 $R_g = 93.9$   
 CIE  $R_a = 71.8$   
 $R_9 = -38.3$



**Color Vector Graphics**





REPORT NUMBER: SP1-1908-441-2-R4

TM-30-18

**Individual Sample Fidelity Index ( $R_{f,i}$ )**

|            |            |            |            |
|------------|------------|------------|------------|
| CES01 = 86 | CES26 = 67 | CES51 = 87 | CES76 = 63 |
| CES02 = 63 | CES27 = 88 | CES52 = 86 | CES77 = 80 |
| CES03 = 31 | CES28 = 87 | CES53 = 78 | CES78 = 67 |
| CES04 = 71 | CES29 = 66 | CES54 = 84 | CES79 = 87 |
| CES05 = 49 | CES30 = 73 | CES55 = 84 | CES80 = 86 |
| CES06 = 51 | CES31 = 70 | CES56 = 75 | CES81 = 71 |
| CES07 = 41 | CES32 = 65 | CES57 = 74 | CES82 = 94 |
| CES08 = 40 | CES33 = 73 | CES58 = 76 | CES83 = 90 |
| CES09 = 29 | CES34 = 79 | CES59 = 85 | CES84 = 89 |
| CES10 = 76 | CES35 = 89 | CES60 = 93 | CES85 = 77 |
| CES11 = 59 | CES36 = 97 | CES61 = 84 | CES86 = 61 |
| CES12 = 65 | CES37 = 87 | CES62 = 91 | CES87 = 78 |
| CES13 = 43 | CES38 = 81 | CES63 = 77 | CES88 = 77 |
| CES14 = 74 | CES39 = 95 | CES64 = 72 | CES89 = 67 |
| CES15 = 71 | CES40 = 92 | CES65 = 68 | CES90 = 76 |
| CES16 = 47 | CES41 = 88 | CES66 = 69 | CES91 = 89 |
| CES17 = 50 | CES42 = 89 | CES67 = 67 | CES92 = 58 |
| CES18 = 56 | CES43 = 79 | CES68 = 72 | CES93 = 74 |
| CES19 = 73 | CES44 = 99 | CES69 = 81 | CES94 = 49 |
| CES20 = 66 | CES45 = 85 | CES70 = 66 | CES95 = 68 |
| CES21 = 87 | CES46 = 80 | CES71 = 67 | CES96 = 76 |
| CES22 = 79 | CES47 = 82 | CES72 = 88 | CES97 = 82 |
| CES23 = 92 | CES48 = 69 | CES73 = 59 | CES98 = 75 |
| CES24 = 91 | CES49 = 80 | CES74 = 95 | CES99 = 62 |
| CES25 = 73 | CES50 = 87 | CES75 = 69 |            |



REPORT NUMBER: SP1-1908-441-2-R4

TM-30-18

Color Rendition by Hue-Angle Bin



REPORT NUMBER: SP1-1908-441-2-R4

TM-30-18

Measure Comparisons



(END OF REPORT)