

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: McGRAW-EDISON

Report Number: P635730

Luminaire Tested: GWS-SA3E-735-U-SLL-W-GRSWH

Issue Date: 1/10/2023

Test Information

Test Method: LM-79-2019
Report Number: P635730
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2209-782-39)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/10/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: McGRAW-EDISON
Catalog Number: GWS-SA3E-735-U-SLL-W-GRSWH
Description: GALLEON WALL SLIM LUMINAIRE. (3) LIGHTSQUARES WITH 16 LEDS EACH AND SPILL LIGHT ELIMINATOR LEFT OPTICS W/ FACTORY INSTALLED GLARE SHIELD, WH
Light Source: (48) 3500K CCT, 70 CRI LEDS
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 16883.1 lumens
Efficiency: N/A
Efficacy: 106.0 lumens/watt
Luminous Opening: Rectangular (W 1.5' x L: 0.5' x H: 0')
IES Classification: Type III - Short
BUG Rating: B3 - U0 - G3


Input Watts (W): 159.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 0
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT



REPORT NUMBER: P635730
 CATALOG NUMBER: GWS-SA3E-735-U-SLL-W-GRSWH

Iso-Footcandle Lines of Horizontal Illumination


× Max cd
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 6.6 fc
 Type III - Short - N/A

REPORT NUMBER: P635730
CATALOG NUMBER: GWS-SA3E-735-U-SLL-W-GRSWH

Luminous Intensity Polar Plot



— Vertical Plane Through 315-Deg Lateral - - - Horizontal Cone Through 60-Deg Vertical

REPORT NUMBER: P635730

CATALOG NUMBER: GWS-SA3E-735-U-SLL-W-GRSWH

FLUX DISTRIBUTION:

| | | Downward | Upward | Total |
|--------------------|-----------|----------|--------|---------|
| House Side | Lumens | 5775.6 | 0.0 | 5775.6 |
| | % Fixture | 34.2 | 0.0 | 34.2 |
| Street Side | Lumens | 11107.5 | 0.0 | 11107.5 |
| | % Fixture | 65.8 | 0.0 | 65.8 |
| Total | Lumens | 16883.1 | 0.0 | 16883.1 |
| | % Fixture | 100.0 | 0.0 | 100.0 |

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|---------|-----------|
| 0°-10° | 332.7 | 2.0 |
| 10°-20° | 1067.1 | 6.3 |
| 20°-30° | 1737.8 | 10.3 |
| 30°-40° | 2441.3 | 14.5 |
| 40°-50° | 3340.6 | 19.8 |
| 50°-60° | 4285.9 | 25.4 |
| 60°-70° | 2885.9 | 17.1 |
| 70°-80° | 721.5 | 4.3 |
| 80°-90° | 70.3 | 0.4 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-90° | 16883.1 | 100.0 |
| 0°-180° | 16883.1 | 100.0 |

Coefficient of Utilization



REPORT NUMBER: P635730


CATALOG NUMBER: GWS-SA3E-735-U-SLL-W-GRSWH

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

| Zone | Lumens | % Fixture | Zone Rating/Lumen Limit | | |
|----------------|--------|-----------|-------------------------|------|---------|
| | | | B | U | G |
| FL (0°-30°) | 1745.3 | 10.3 | | | |
| FM (30°-60°) | 6844.5 | 40.5 | | | |
| FH (60°-80°) | 2499.4 | 14.8 | | | G2/5000 |
| FVH (80°-90°) | 18.3 | 0.1 | | | G1/100 |
| BL (0°-30°) | 1392.3 | 8.2 | B3/2500 | | |
| BM (30°-60°) | 3223.2 | 19.1 | B3/5000 | | |
| BH (60°-80°) | 1108.0 | 6.6 | B3/2500 | | G3/2500 |
| BVH (80°-90°) | 52.1 | 0.3 | | | G1/100 |
| UL (90°-100°) | 0.0 | 0.0 | | U0/0 | |
| UH (100°-180°) | 0.0 | 0.0 | | U0/0 | |

BUG Rating: B3-U0-G3

Type III Short





REPORT NUMBER: P635730

CATALOG NUMBER: GWS-SA3E-735-U-SLL-W-GRSWH

CANDELA DISTRIBUTION (FULL):

| | 0° | 1° | 5° | 15° | 25° | 35° | 45° | 55° | 65° | 75° | 85° |
|-------|---------|---------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 3405.1 | 3405.1 | 3405.1 | 3405.1 | 3405.1 | 3405.1 | 3405.1 | 3405.1 | 3405.1 | 3405.1 | 3405.1 |
| 2.5° | 3602.6 | 3594.8 | 3587.1 | 3526.4 | 3510.9 | 3467.3 | 3436.2 | 3397.4 | 3341.4 | 3310.3 | 3283.9 |
| 5° | 3828.1 | 3815.6 | 3773.6 | 3649.3 | 3568.4 | 3479.8 | 3406.7 | 3325.8 | 3240.3 | 3184.4 | 3140.8 |
| 7.5° | 4041.1 | 4038.0 | 3966.4 | 3761.2 | 3630.6 | 3503.1 | 3403.6 | 3285.4 | 3162.6 | 3078.6 | 3022.6 |
| 10° | 4238.5 | 4215.2 | 4129.7 | 3862.3 | 3691.2 | 3545.1 | 3437.8 | 3307.2 | 3164.1 | 3050.6 | 2976.0 |
| 12.5° | 4412.7 | 4383.1 | 4265.0 | 3955.6 | 3744.1 | 3563.7 | 3447.1 | 3339.8 | 3245.0 | 3150.1 | 3064.6 |
| 15° | 4555.7 | 4520.0 | 4400.3 | 4042.6 | 3790.7 | 3552.9 | 3389.6 | 3305.6 | 3338.3 | 3380.3 | 3285.4 |
| 17.5° | 4689.5 | 4652.1 | 4506.0 | 4106.4 | 3804.7 | 3486.0 | 3248.1 | 3212.3 | 3377.2 | 3568.4 | 3524.9 |
| 20° | 4801.4 | 4759.4 | 4589.9 | 4137.5 | 3779.9 | 3358.5 | 3064.6 | 3126.8 | 3344.5 | 3573.1 | 3643.0 |
| 22.5° | 4922.7 | 4888.5 | 4684.8 | 4182.6 | 3748.8 | 3182.8 | 2910.7 | 3063.1 | 3288.5 | 3489.1 | 3594.8 |
| 25° | 5117.0 | 5075.1 | 4832.5 | 4261.9 | 3733.2 | 3018.0 | 2800.3 | 3000.9 | 3210.8 | 3392.7 | 3475.1 |
| 27.5° | 5398.5 | 5320.7 | 5034.6 | 4400.3 | 3750.3 | 2862.5 | 2730.3 | 2924.7 | 3120.6 | 3276.1 | 3342.9 |
| 30° | 5704.8 | 5611.5 | 5258.5 | 4543.3 | 3775.2 | 2767.6 | 2693.0 | 2837.6 | 2982.2 | 3137.7 | 3210.8 |
| 32.5° | 6067.1 | 5984.7 | 5498.0 | 4650.6 | 3722.3 | 2724.1 | 2665.0 | 2742.8 | 2857.8 | 2982.2 | 3042.9 |
| 35° | 6499.3 | 6351.6 | 5759.2 | 4737.7 | 3551.3 | 2660.4 | 2640.2 | 2638.6 | 2699.2 | 2820.5 | 2888.9 |
| 37.5° | 6964.2 | 6805.6 | 6081.1 | 4830.9 | 3285.4 | 2559.3 | 2581.1 | 2515.8 | 2571.7 | 2668.1 | 2745.9 |
| 40° | 7345.2 | 7178.8 | 6406.0 | 4958.4 | 2952.7 | 2400.7 | 2450.5 | 2380.5 | 2414.7 | 2514.2 | 2601.3 |
| 42.5° | 7718.3 | 7541.1 | 6709.2 | 5103.0 | 2630.8 | 2245.2 | 2270.1 | 2243.7 | 2254.5 | 2358.7 | 2480.0 |
| 45° | 8208.1 | 8009.1 | 7082.4 | 5205.7 | 2341.6 | 2122.4 | 2099.1 | 2054.0 | 2111.5 | 2246.8 | 2375.8 |
| 47.5° | 9026.0 | 8788.1 | 7693.4 | 5272.5 | 2131.7 | 2052.4 | 1945.1 | 1918.7 | 1990.2 | 2141.0 | 2274.8 |
| 50° | 9982.2 | 9777.0 | 8669.9 | 5269.4 | 1974.7 | 1993.3 | 1795.9 | 1772.5 | 1890.7 | 2043.1 | 2184.6 |
| 52.5° | 10765.8 | 10557.5 | 9504.9 | 5113.9 | 1845.6 | 1867.4 | 1708.8 | 1643.5 | 1805.2 | 1946.7 | 2088.2 |
| 55° | 11398.7 | 11163.9 | 9888.9 | 4464.0 | 1682.4 | 1666.8 | 1613.9 | 1494.2 | 1697.9 | 1850.3 | 1982.4 |
| 57.5° | 11058.2 | 10778.3 | 9424.0 | 3394.3 | 1514.4 | 1416.5 | 1450.7 | 1362.1 | 1551.7 | 1743.0 | 1870.5 |
| 60° | 9271.6 | 9019.7 | 7656.1 | 1806.7 | 1332.5 | 1183.2 | 1254.8 | 1268.8 | 1391.6 | 1613.9 | 1744.6 |
| 62.5° | 6368.7 | 6185.2 | 5188.6 | 1096.2 | 1051.1 | 950.0 | 1062.0 | 1163.0 | 1254.8 | 1442.9 | 1556.4 |
| 65° | 3115.9 | 3061.5 | 2595.1 | 702.8 | 735.4 | 768.1 | 880.1 | 1002.9 | 1138.2 | 1303.0 | 1422.7 |
| 67.5° | 858.3 | 864.5 | 786.8 | 548.9 | 580.0 | 670.1 | 758.8 | 856.7 | 992.0 | 1144.4 | 1265.7 |
| 70° | 377.8 | 384.1 | 396.5 | 422.9 | 482.0 | 564.4 | 656.2 | 757.2 | 881.6 | 1009.1 | 1125.7 |
| 72.5° | 262.8 | 269.0 | 287.6 | 321.9 | 374.7 | 452.5 | 539.5 | 635.9 | 765.0 | 872.3 | 968.7 |
| 75° | 161.7 | 166.4 | 183.5 | 213.0 | 248.8 | 307.9 | 393.4 | 482.0 | 595.5 | 693.5 | 779.0 |
| 77.5° | 85.5 | 82.4 | 93.3 | 113.5 | 144.6 | 175.7 | 233.2 | 289.2 | 370.1 | 449.4 | 520.9 |
| 80° | 46.6 | 45.1 | 51.3 | 62.2 | 71.5 | 96.4 | 135.3 | 172.6 | 219.2 | 264.3 | 303.2 |
| 82.5° | 20.2 | 18.7 | 20.2 | 26.4 | 32.7 | 46.6 | 68.4 | 94.8 | 121.3 | 152.4 | 177.3 |
| 85° | 0.0 | 0.0 | 0.0 | 1.6 | 7.8 | 12.4 | 23.3 | 34.2 | 49.8 | 68.4 | 84.0 |
| 87.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 6.2 | 14.0 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P635730

CATALOG NUMBER: GWS-SA3E-735-U-SLL-W-GRSWH

CANDELA DISTRIBUTION (continued):

| | 90° | 95° | 105° | 115° | 125° | 135° | 145° | 155° | 165° | 175° | 180° |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 3405.1 | 3405.1 | 3405.1 | 3405.1 | 3405.1 | 3405.1 | 3405.1 | 3405.1 | 3405.1 | 3405.1 | 3405.1 |
| 2.5° | 3268.3 | 3229.4 | 3226.3 | 3195.2 | 3198.3 | 3199.9 | 3168.8 | 3156.4 | 3167.2 | 3179.7 | 3173.5 |
| 5° | 3125.3 | 3084.8 | 3067.7 | 3038.2 | 3035.1 | 3021.1 | 3008.7 | 2993.1 | 3004.0 | 3014.9 | 3021.1 |
| 7.5° | 3000.9 | 2974.4 | 2963.6 | 2955.8 | 2958.9 | 2952.7 | 2927.8 | 2913.8 | 2912.3 | 2916.9 | 2923.1 |
| 10° | 2960.5 | 2938.7 | 2952.7 | 2974.4 | 2990.0 | 3000.9 | 2974.4 | 2951.1 | 2929.4 | 2920.0 | 2920.0 |
| 12.5° | 3047.5 | 3019.5 | 3047.5 | 3070.8 | 3101.9 | 3109.7 | 3080.2 | 3055.3 | 3047.5 | 3056.9 | 3075.5 |
| 15° | 3240.3 | 3175.0 | 3173.5 | 3187.5 | 3212.3 | 3224.8 | 3196.8 | 3184.4 | 3184.4 | 3243.4 | 3290.1 |
| 17.5° | 3433.1 | 3325.8 | 3280.8 | 3273.0 | 3288.5 | 3293.2 | 3269.9 | 3259.0 | 3287.0 | 3402.0 | 3489.1 |
| 20° | 3568.4 | 3437.8 | 3339.8 | 3321.2 | 3325.8 | 3327.4 | 3308.7 | 3301.0 | 3341.4 | 3481.3 | 3554.4 |
| 22.5° | 3554.4 | 3458.0 | 3338.3 | 3315.0 | 3322.7 | 3319.6 | 3302.5 | 3299.4 | 3332.1 | 3453.3 | 3487.5 |
| 25° | 3458.0 | 3383.4 | 3282.3 | 3266.8 | 3279.2 | 3277.6 | 3260.5 | 3252.8 | 3266.8 | 3347.6 | 3350.7 |
| 27.5° | 3347.6 | 3282.3 | 3195.2 | 3190.6 | 3210.8 | 3221.7 | 3192.1 | 3168.8 | 3164.1 | 3218.6 | 3206.1 |
| 30° | 3215.4 | 3167.2 | 3097.3 | 3100.4 | 3137.7 | 3143.9 | 3108.2 | 3074.0 | 3064.6 | 3094.2 | 3077.1 |
| 32.5° | 3058.4 | 3042.9 | 3005.5 | 3013.3 | 3049.1 | 3061.5 | 3024.2 | 2988.4 | 2977.6 | 2986.9 | 2951.1 |
| 35° | 2924.7 | 2918.5 | 2921.6 | 2935.6 | 2966.7 | 2976.0 | 2944.9 | 2916.9 | 2901.4 | 2868.7 | 2822.1 |
| 37.5° | 2786.3 | 2803.4 | 2848.5 | 2874.9 | 2892.0 | 2888.9 | 2871.8 | 2851.6 | 2826.7 | 2766.1 | 2708.6 |
| 40° | 2657.3 | 2700.8 | 2781.6 | 2811.2 | 2817.4 | 2819.0 | 2806.5 | 2789.4 | 2758.3 | 2677.5 | 2612.2 |
| 42.5° | 2557.7 | 2605.9 | 2713.2 | 2758.3 | 2761.4 | 2764.5 | 2752.1 | 2738.1 | 2694.6 | 2587.3 | 2523.5 |
| 45° | 2453.6 | 2517.3 | 2643.3 | 2697.7 | 2694.6 | 2693.0 | 2682.1 | 2675.9 | 2624.6 | 2500.2 | 2430.2 |
| 47.5° | 2364.9 | 2439.6 | 2574.8 | 2621.5 | 2619.9 | 2618.4 | 2610.6 | 2610.6 | 2559.3 | 2424.0 | 2344.7 |
| 50° | 2277.9 | 2363.4 | 2504.9 | 2543.7 | 2546.9 | 2543.7 | 2540.6 | 2545.3 | 2484.7 | 2340.1 | 2262.3 |
| 52.5° | 2183.0 | 2279.4 | 2427.1 | 2462.9 | 2481.6 | 2489.3 | 2489.3 | 2478.4 | 2406.9 | 2256.1 | 2170.6 |
| 55° | 2078.8 | 2170.6 | 2341.6 | 2389.8 | 2405.4 | 2419.4 | 2419.4 | 2397.6 | 2330.7 | 2178.4 | 2086.6 |
| 57.5° | 1949.8 | 2030.6 | 2165.9 | 2214.1 | 2251.4 | 2260.8 | 2260.8 | 2225.0 | 2170.6 | 2024.4 | 1949.8 |
| 60° | 1809.9 | 1879.8 | 1971.6 | 2022.9 | 2050.9 | 2032.2 | 2046.2 | 2036.9 | 1993.3 | 1858.1 | 1795.9 |
| 62.5° | 1623.3 | 1694.8 | 1795.9 | 1848.7 | 1861.2 | 1842.5 | 1861.2 | 1859.6 | 1800.5 | 1679.2 | 1604.6 |
| 65° | 1489.6 | 1559.5 | 1659.0 | 1727.4 | 1747.7 | 1743.0 | 1755.4 | 1736.8 | 1663.7 | 1548.6 | 1477.1 |
| 67.5° | 1331.0 | 1405.6 | 1520.7 | 1596.8 | 1638.8 | 1643.5 | 1660.6 | 1621.7 | 1547.1 | 1421.1 | 1331.0 |
| 70° | 1180.1 | 1243.9 | 1332.5 | 1404.0 | 1463.1 | 1492.7 | 1495.8 | 1439.8 | 1346.5 | 1242.3 | 1177.0 |
| 72.5° | 1021.5 | 1086.8 | 1194.1 | 1271.9 | 1346.5 | 1380.7 | 1380.7 | 1312.3 | 1211.2 | 1096.2 | 1026.2 |
| 75° | 828.7 | 889.4 | 987.3 | 1071.3 | 1156.8 | 1200.4 | 1198.8 | 1139.7 | 1027.8 | 918.9 | 845.8 |
| 77.5° | 561.3 | 606.4 | 668.6 | 732.3 | 744.8 | 779.0 | 796.1 | 721.5 | 659.3 | 600.2 | 534.9 |
| 80° | 326.5 | 354.5 | 388.7 | 424.5 | 432.3 | 443.1 | 415.1 | 387.2 | 354.5 | 315.6 | 286.1 |
| 82.5° | 191.2 | 209.9 | 227.0 | 255.0 | 259.7 | 262.8 | 237.9 | 225.5 | 199.0 | 175.7 | 157.0 |
| 85° | 93.3 | 99.5 | 115.1 | 129.1 | 122.8 | 119.7 | 108.8 | 96.4 | 85.5 | 76.2 | 66.9 |
| 87.5° | 18.7 | 18.7 | 28.0 | 26.4 | 21.8 | 18.7 | 10.9 | 14.0 | 3.1 | 3.1 | 0.0 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P635730

CATALOG NUMBER: GWS-SA3E-735-U-SLL-W-GRSWH

CANDELA DISTRIBUTION (continued):

| | 185° | 195° | 205° | 215° | 225° | 235° | 245° | 255° | 265° | 270° | 275° |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|---------|---------|
| 0° | 3405.1 | 3405.1 | 3405.1 | 3405.1 | 3405.1 | 3405.1 | 3405.1 | 3405.1 | 3405.1 | 3405.1 | 3405.1 |
| 2.5° | 3193.7 | 3220.1 | 3252.8 | 3296.3 | 3346.1 | 3398.9 | 3450.2 | 3489.1 | 3528.0 | 3585.5 | 3576.2 |
| 5° | 3030.4 | 3075.5 | 3126.8 | 3193.7 | 3274.5 | 3366.3 | 3468.9 | 3571.5 | 3681.9 | 3775.2 | 3815.6 |
| 7.5° | 2935.6 | 2985.3 | 3046.0 | 3133.0 | 3237.2 | 3349.2 | 3493.8 | 3660.1 | 3838.9 | 3961.8 | 4038.0 |
| 10° | 2935.6 | 2999.3 | 3078.6 | 3162.6 | 3254.3 | 3369.4 | 3548.2 | 3756.5 | 3986.7 | 4148.4 | 4237.0 |
| 12.5° | 3105.1 | 3168.8 | 3185.9 | 3182.8 | 3234.1 | 3361.6 | 3591.7 | 3857.6 | 4132.8 | 4303.9 | 4412.7 |
| 15° | 3369.4 | 3391.1 | 3262.1 | 3143.9 | 3151.7 | 3305.6 | 3611.9 | 3938.5 | 4258.8 | 4464.0 | 4582.2 |
| 17.5° | 3546.6 | 3489.1 | 3259.0 | 3052.2 | 3008.7 | 3210.8 | 3611.9 | 4016.2 | 4392.5 | 4624.2 | 4734.5 |
| 20° | 3560.6 | 3417.6 | 3179.7 | 2963.6 | 2851.6 | 3084.8 | 3587.1 | 4075.3 | 4521.5 | 4778.1 | 4896.3 |
| 22.5° | 3437.8 | 3296.3 | 3095.7 | 2887.4 | 2722.6 | 2932.5 | 3546.6 | 4120.4 | 4631.9 | 4922.7 | 5068.8 |
| 25° | 3297.9 | 3179.7 | 3010.2 | 2809.6 | 2633.9 | 2778.5 | 3509.3 | 4196.6 | 4785.9 | 5118.6 | 5266.3 |
| 27.5° | 3161.0 | 3061.5 | 2907.6 | 2744.3 | 2584.2 | 2644.8 | 3486.0 | 4308.5 | 4969.3 | 5396.9 | 5524.4 |
| 30° | 3027.3 | 2937.1 | 2797.2 | 2682.1 | 2557.7 | 2557.7 | 3465.8 | 4437.6 | 5211.9 | 5709.4 | 5836.9 |
| 32.5° | 2892.0 | 2806.5 | 2693.0 | 2621.5 | 2542.2 | 2523.5 | 3409.8 | 4558.8 | 5462.2 | 6051.5 | 6182.1 |
| 35° | 2766.1 | 2680.6 | 2593.5 | 2564.0 | 2534.4 | 2497.1 | 3271.4 | 4653.7 | 5706.3 | 6451.1 | 6563.1 |
| 37.5° | 2647.9 | 2565.5 | 2500.2 | 2492.4 | 2495.5 | 2425.6 | 3053.7 | 4733.0 | 6011.1 | 6860.0 | 6919.1 |
| 40° | 2545.3 | 2453.6 | 2402.3 | 2400.7 | 2416.3 | 2310.5 | 2778.5 | 4846.5 | 6359.4 | 7206.8 | 7181.9 |
| 42.5° | 2453.6 | 2357.2 | 2295.0 | 2309.0 | 2299.6 | 2195.5 | 2509.5 | 4950.7 | 6662.6 | 7531.7 | 7482.0 |
| 45° | 2363.4 | 2270.1 | 2183.0 | 2203.2 | 2192.4 | 2123.9 | 2281.0 | 5026.9 | 6998.4 | 7922.0 | 7928.2 |
| 47.5° | 2276.3 | 2184.6 | 2097.5 | 2072.6 | 2071.1 | 2102.2 | 2105.3 | 5051.7 | 7545.7 | 8550.2 | 8408.7 |
| 50° | 2195.5 | 2103.7 | 2013.5 | 1929.6 | 1962.2 | 2058.6 | 1974.7 | 5033.1 | 8365.1 | 9243.6 | 8848.7 |
| 52.5° | 2111.5 | 2024.4 | 1924.9 | 1774.1 | 1859.6 | 1954.5 | 1858.1 | 4966.2 | 8865.8 | 9856.3 | 9619.9 |
| 55° | 2015.1 | 1932.7 | 1797.4 | 1613.9 | 1718.1 | 1738.3 | 1738.3 | 4319.4 | 9078.8 | 10462.6 | 10608.8 |
| 57.5° | 1886.0 | 1777.2 | 1562.6 | 1414.9 | 1508.2 | 1430.5 | 1610.8 | 3022.6 | 8727.4 | 10271.4 | 10838.9 |
| 60° | 1739.9 | 1623.3 | 1396.3 | 1290.5 | 1318.5 | 1181.7 | 1372.9 | 1895.4 | 7233.2 | 8739.9 | 9722.5 |
| 62.5° | 1547.1 | 1439.8 | 1251.7 | 1169.3 | 1111.7 | 964.0 | 1105.5 | 1198.8 | 4958.4 | 6490.0 | 7160.1 |
| 65° | 1418.0 | 1299.9 | 1131.9 | 1023.1 | 904.9 | 775.9 | 733.9 | 786.8 | 2666.6 | 3632.2 | 4084.6 |
| 67.5° | 1265.7 | 1149.0 | 990.4 | 853.6 | 758.8 | 665.5 | 592.4 | 573.7 | 914.3 | 1209.7 | 1309.2 |
| 70° | 1121.1 | 1009.1 | 876.9 | 749.4 | 654.6 | 562.9 | 491.3 | 440.0 | 422.9 | 419.8 | 413.6 |
| 72.5° | 973.3 | 869.2 | 758.8 | 640.6 | 536.4 | 452.5 | 388.7 | 329.6 | 304.8 | 297.0 | 289.2 |
| 75° | 797.6 | 715.2 | 604.8 | 477.3 | 393.4 | 315.6 | 265.9 | 227.0 | 205.2 | 197.5 | 188.1 |
| 77.5° | 513.1 | 475.8 | 379.4 | 307.9 | 237.9 | 188.1 | 161.7 | 136.8 | 122.8 | 119.7 | 111.9 |
| 80° | 273.7 | 255.0 | 209.9 | 177.3 | 141.5 | 115.1 | 101.1 | 87.1 | 79.3 | 76.2 | 73.1 |
| 82.5° | 152.4 | 138.4 | 116.6 | 102.6 | 82.4 | 70.0 | 62.2 | 56.0 | 51.3 | 49.8 | 48.2 |
| 85° | 68.4 | 59.1 | 46.6 | 43.5 | 38.9 | 35.8 | 34.2 | 31.1 | 29.5 | 28.0 | 26.4 |
| 87.5° | 3.1 | 6.2 | 7.8 | 6.2 | 6.2 | 9.3 | 10.9 | 10.9 | 9.3 | 9.3 | 7.8 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P635730

CATALOG NUMBER: GWS-SA3E-735-U-SLL-W-GRSWH

CANDELA DISTRIBUTION (continued):

| | 285° | 295° | 305° | 315° | 325° | 335° | 345° | 355° | 359° | 360° |
|-------|--------|--------|---------|---------|---------|--------|--------|---------|---------|---------|
| 0° | 3405.1 | 3405.1 | 3405.1 | 3405.1 | 3405.1 | 3405.1 | 3405.1 | 3405.1 | 3405.1 | 3405.1 |
| 2.5° | 3633.7 | 3680.4 | 3685.0 | 3700.6 | 3680.4 | 3675.7 | 3643.0 | 3624.4 | 3607.3 | 3602.6 |
| 5° | 3916.7 | 4010.0 | 4047.3 | 4073.7 | 4048.9 | 4036.4 | 3964.9 | 3890.3 | 3848.3 | 3828.1 |
| 7.5° | 4207.4 | 4347.4 | 4420.5 | 4453.1 | 4456.2 | 4400.3 | 4277.4 | 4137.5 | 4067.5 | 4041.1 |
| 10° | 4467.1 | 4639.7 | 4736.1 | 4798.3 | 4776.5 | 4708.1 | 4540.2 | 4350.5 | 4261.9 | 4238.5 |
| 12.5° | 4659.9 | 4824.7 | 4899.4 | 4939.8 | 4938.2 | 4900.9 | 4742.3 | 4537.1 | 4436.0 | 4412.7 |
| 15° | 4784.3 | 4882.3 | 4886.9 | 4896.3 | 4922.7 | 4972.4 | 4890.0 | 4700.3 | 4588.4 | 4555.7 |
| 17.5° | 4882.3 | 4843.4 | 4770.3 | 4745.4 | 4804.5 | 4942.9 | 4992.7 | 4838.7 | 4717.4 | 4689.5 |
| 20° | 4944.5 | 4748.5 | 4619.5 | 4571.3 | 4639.7 | 4865.2 | 5054.8 | 4963.1 | 4837.2 | 4801.4 |
| 22.5° | 4992.7 | 4659.9 | 4451.6 | 4418.9 | 4490.4 | 4781.2 | 5118.6 | 5110.8 | 4972.4 | 4922.7 |
| 25° | 5068.8 | 4600.8 | 4333.4 | 4310.1 | 4376.9 | 4740.8 | 5204.1 | 5311.4 | 5188.6 | 5117.0 |
| 27.5° | 5188.6 | 4594.6 | 4272.8 | 4265.0 | 4356.7 | 4776.5 | 5326.9 | 5605.3 | 5451.3 | 5398.5 |
| 30° | 5354.9 | 4653.7 | 4286.7 | 4302.3 | 4414.2 | 4905.6 | 5518.2 | 5941.1 | 5787.2 | 5704.8 |
| 32.5° | 5594.4 | 4812.3 | 4499.8 | 4566.6 | 4649.0 | 5112.4 | 5798.1 | 6305.0 | 6188.3 | 6067.1 |
| 35° | 5910.0 | 5247.7 | 5129.5 | 5414.0 | 5336.3 | 5564.8 | 6135.5 | 6746.5 | 6605.0 | 6499.3 |
| 37.5° | 6331.4 | 6140.1 | 6249.0 | 6640.8 | 6452.7 | 6420.0 | 6547.5 | 7147.7 | 7069.9 | 6964.2 |
| 40° | 6922.2 | 6961.1 | 7161.7 | 7676.3 | 7404.2 | 7194.3 | 7052.8 | 7449.3 | 7475.8 | 7345.2 |
| 42.5° | 7314.1 | 7492.9 | 7976.4 | 8561.1 | 8186.3 | 7684.1 | 7475.8 | 7834.9 | 7836.5 | 7718.3 |
| 45° | 7460.2 | 7928.2 | 8938.9 | 9612.1 | 8985.5 | 7964.0 | 7709.0 | 8358.9 | 8343.4 | 8208.1 |
| 47.5° | 7407.3 | 8295.2 | 9938.7 | 10968.0 | 10011.7 | 8163.0 | 7676.3 | 9105.3 | 9231.2 | 9026.0 |
| 50° | 7297.0 | 8663.7 | 11106.4 | 12628.6 | 11271.2 | 8374.5 | 7626.6 | 9932.4 | 10140.8 | 9982.2 |
| 52.5° | 7408.9 | 9074.2 | 12487.1 | 14345.1 | 12850.9 | 8711.9 | 7962.4 | 10994.4 | 10957.1 | 10765.8 |
| 55° | 7763.4 | 9559.3 | 14164.8 | 16501.7 | 14586.1 | 9282.5 | 8825.4 | 12006.6 | 11627.2 | 11398.7 |
| 57.5° | 7746.3 | 9906.0 | 15635.7 | 18207.4 | 16095.9 | 9750.5 | 9125.5 | 12113.9 | 11347.4 | 11058.2 |
| 60° | 7031.1 | 9747.4 | 16195.4 | 19286.5 | 16551.5 | 9492.4 | 8138.1 | 10820.3 | 9574.8 | 9271.6 |
| 62.5° | 5247.7 | 8649.7 | 15110.1 | 17935.3 | 15262.5 | 8198.8 | 6119.9 | 7766.5 | 6880.3 | 6368.7 |
| 65° | 3356.9 | 6766.7 | 12703.2 | 14530.2 | 12580.4 | 6270.7 | 3644.6 | 4163.9 | 3262.1 | 3115.9 |
| 67.5° | 1428.9 | 4776.5 | 9874.9 | 9711.7 | 9411.6 | 4062.8 | 1407.1 | 1172.4 | 873.8 | 858.3 |
| 70° | 472.7 | 3249.7 | 6087.3 | 6477.5 | 5620.8 | 2798.7 | 464.9 | 393.4 | 391.8 | 377.8 |
| 72.5° | 309.4 | 1744.6 | 3426.9 | 3815.6 | 3616.6 | 1610.8 | 281.4 | 262.8 | 269.0 | 262.8 |
| 75° | 185.0 | 379.4 | 576.9 | 749.4 | 576.9 | 270.5 | 169.5 | 166.4 | 169.5 | 161.7 |
| 77.5° | 108.8 | 105.7 | 102.6 | 102.6 | 101.1 | 93.3 | 85.5 | 82.4 | 84.0 | 85.5 |
| 80° | 70.0 | 66.9 | 63.7 | 62.2 | 54.4 | 51.3 | 48.2 | 45.1 | 45.1 | 46.6 |
| 82.5° | 45.1 | 42.0 | 38.9 | 34.2 | 28.0 | 23.3 | 21.8 | 18.7 | 18.7 | 20.2 |
| 85° | 23.3 | 18.7 | 14.0 | 10.9 | 6.2 | 3.1 | 0.0 | 0.0 | 0.0 | 0.0 |
| 87.5° | 4.7 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |

LM-79-08: Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Report Prepared for

Cooper Lighting Solutions

All Brands

Data applicable to all product families using SA light engines

Report Number: SP1-2101-121-7

Luminaire Tested: IFLD-S-SA2A-735-U-T2

Test Date: 03/04/2021

Test Information

Test Method: LM-79-08
 Report Number: SP1-2101-121-7
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1
 Measurement Geometry: 4π
 Issue Date: 03/04/2021
 Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
 Product Line: STREETWORKS
 Catalog Number: **IFLD-S-SA2A-735-U-T2**
 Description: STREETWORKS INF FLOOD

PROGRAMMED @ 615mA.


Spectral Parameters

CCT (K): 3388
 CIE u': 0.2371
 CIE v': 0.5177
 Duv: 0.0032
 CIE x: 0.4153
 CIE y: 0.4030
 CIE z: 0.1817
 Peak Wavelength (nm): 590
 Dominant Wavelength (nm): 580
 Purity: 45.7
 Rf: 76.9
 Rg: 94.4

| | | | |
|-----------|------|------|-------|
| CRI (Ra): | 73.1 | | |
| R1: | 68.9 | R9: | -34.6 |
| R2: | 81.1 | R10: | 57.8 |
| R3: | 93.1 | R11: | 68.6 |
| R4: | 71.6 | R12: | 53.9 |
| R5: | 69.4 | R13: | 70.9 |
| R6: | 75.0 | R14: | 96.2 |
| R7: | 79.5 | | |
| R8: | 46.4 | | |

Test Conditions

Stabilization Time: 81M
 Operation Time: 12H
 Room Temperature (°C) / RH%: 25.0/30%
 Sphere Temperature (°C): 24.1




REPORT NUMBER: SP1-2101-121-7


| Measurement and Test Equipment | | | |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument | Identification Number | Calibration Date | Calibration Due Date |
| Photometer | IN0058 | 1/31/2021 | 7/31/2021 |
| Power Meter | IN0071 | 12/1/2020 | 12/1/2021 |
| AC Power Source | IN0063 | 12/1/2020 | 12/1/2021 |
| DC Power Source | IN0208 | 12/1/2020 | 12/1/2021 |
| Sphere Thermometer | IN0085 | 12/1/2020 | 12/1/2021 |
| Room Thermometer | IN0046 | 12/1/2020 | 12/1/2021 |

REPORT NUMBER: SP1-2101-121-7

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 3500K 4-step quadrangle

REPORT NUMBER: SP1-2101-121-7

Photopic Flux vs. Wavelength



#####

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 2672 | 0.0 | 490 | 34553 | 4.9 | 620 | 136720 | 35.6 | 750 | 5870 | 0.0 | 880 | 4216 | 0.0 |
| 365 | 2252 | 0.0 | 495 | 44336 | 8.0 | 625 | 126308 | 27.9 | 755 | 5421 | 0.0 | 885 | 4132 | 0.0 |
| 370 | 2217 | 0.0 | 500 | 54643 | 12.1 | 630 | 114625 | 20.7 | 760 | 5097 | 0.0 | 890 | 3992 | 0.0 |
| 375 | 2697 | 0.0 | 505 | 64676 | 18.1 | 635 | 103216 | 15.5 | 765 | 4626 | 0.0 | 895 | 3214 | 0.0 |
| 380 | 3039 | 0.0 | 510 | 73825 | 25.4 | 640 | 92605 | 11.1 | 770 | 3782 | 0.0 | 900 | 2580 | 0.0 |
| 385 | 2655 | 0.0 | 515 | 81872 | 33.9 | 645 | 83234 | 8.0 | 775 | 3506 | 0.0 | 905 | 1776 | 0.0 |
| 390 | 2357 | 0.0 | 520 | 88574 | 43.0 | 650 | 73263 | 5.4 | 780 | 3507 | 0.0 | 910 | 3995 | 0.0 |
| 395 | 2186 | 0.0 | 525 | 93289 | 50.1 | 655 | 64627 | 3.7 | 785 | 3267 | 0.0 | 915 | 4288 | 0.0 |
| 400 | 2015 | 0.0 | 530 | 98393 | 57.9 | 660 | 56614 | 2.4 | 790 | 2849 | 0.0 | 920 | 2446 | 0.0 |
| 405 | 2234 | 0.0 | 535 | 103269 | 64.0 | 665 | 49537 | 1.6 | 795 | 3037 | 0.0 | 925 | 3009 | 0.0 |
| 410 | 3412 | 0.0 | 540 | 107316 | 69.9 | 670 | 42866 | 0.9 | 800 | 2716 | 0.0 | 930 | 3026 | 0.0 |
| 415 | 6135 | 0.0 | 545 | 113101 | 75.3 | 675 | 36708 | 0.6 | 805 | 2648 | 0.0 | 935 | 4734 | 0.0 |
| 420 | 12146 | 0.0 | 550 | 120690 | 82.0 | 680 | 31814 | 0.4 | 810 | 3187 | 0.0 | 940 | 3719 | 0.0 |
| 425 | 23983 | 0.1 | 555 | 128583 | 87.8 | 685 | 27485 | 0.2 | 815 | 2931 | 0.0 | 945 | 1480 | 0.0 |
| 430 | 42142 | 0.3 | 560 | 137796 | 93.6 | 690 | 23698 | 0.1 | 820 | 2717 | 0.0 | 950 | 3450 | 0.0 |
| 435 | 68228 | 0.8 | 565 | 146577 | 97.5 | 695 | 20309 | 0.1 | 825 | 2236 | 0.0 | 955 | 5051 | 0.0 |
| 440 | 99323 | 1.6 | 570 | 154581 | 100.5 | 700 | 17890 | 0.1 | 830 | 2628 | 0.0 | 960 | 3176 | 0.0 |
| 445 | 115584 | 2.4 | 575 | 162633 | 101.2 | 705 | 15500 | 0.0 | 835 | 3140 | 0.0 | 965 | 5178 | 0.0 |
| 450 | 94997 | 2.5 | 580 | 168101 | 99.9 | 710 | 13699 | 0.0 | 840 | 3675 | 0.0 | 970 | 6385 | 0.0 |
| 455 | 61433 | 2.1 | 585 | 173145 | 96.2 | 715 | 12398 | 0.0 | 845 | 3283 | 0.0 | 975 | 3810 | 0.0 |
| 460 | 43373 | 1.8 | 590 | 174675 | 90.3 | 720 | 11147 | 0.0 | 850 | 3055 | 0.0 | 980 | 4322 | 0.0 |
| 465 | 32472 | 1.7 | 595 | 173724 | 82.3 | 725 | 9761 | 0.0 | 855 | 2932 | 0.0 | 985 | 4200 | 0.0 |
| 470 | 24257 | 1.5 | 600 | 171241 | 73.8 | 730 | 8651 | 0.0 | 860 | 3382 | 0.0 | 990 | 4661 | 0.0 |
| 475 | 21690 | 1.7 | 605 | 165134 | 64.0 | 735 | 7730 | 0.0 | 865 | 2605 | 0.0 | 995 | 6746 | 0.0 |
| 480 | 23173 | 2.2 | 610 | 156652 | 53.8 | 740 | 6847 | 0.0 | 870 | 3325 | 0.0 | 1000 | 4150 | 0.0 |
| 485 | 27564 | 3.3 | 615 | 147879 | 44.6 | 745 | 6124 | 0.0 | 875 | 3325 | 0.0 | | | |

REPORT NUMBER: SP1-2101-121-7

Scotopic Flux vs. Wavelength



Scotopic Lumens: 12126

S/P: 1.36

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 2672 | 0.0 | 490 | 34553 | 53.2 | 620 | 136720 | 1.7 | 750 | 5870 | 0.0 | 880 | 4216 | 0.0 |
| 365 | 2252 | 0.0 | 495 | 44336 | 71.7 | 625 | 126308 | 1.1 | 755 | 5421 | 0.0 | 885 | 4132 | 0.0 |
| 370 | 2217 | 0.0 | 500 | 54643 | 91.4 | 630 | 114625 | 0.6 | 760 | 5097 | 0.0 | 890 | 3992 | 0.0 |
| 375 | 2697 | 0.0 | 505 | 64676 | 110.0 | 635 | 103216 | 0.4 | 765 | 4626 | 0.0 | 895 | 3214 | 0.0 |
| 380 | 3039 | 0.0 | 510 | 73825 | 125.1 | 640 | 92605 | 0.2 | 770 | 3782 | 0.0 | 900 | 2580 | 0.0 |
| 385 | 2655 | 0.0 | 515 | 81872 | 135.7 | 645 | 83234 | 0.1 | 775 | 3506 | 0.0 | 905 | 1776 | 0.0 |
| 390 | 2357 | 0.0 | 520 | 88574 | 140.8 | 650 | 73263 | 0.1 | 780 | 3507 | 0.0 | 910 | 3995 | 0.0 |
| 395 | 2186 | 0.0 | 525 | 93289 | 139.6 | 655 | 64627 | 0.1 | 785 | 3267 | 0.0 | 915 | 4288 | 0.0 |
| 400 | 2015 | 0.0 | 530 | 98393 | 135.7 | 660 | 56614 | 0.0 | 790 | 2849 | 0.0 | 920 | 2446 | 0.0 |
| 405 | 2234 | 0.1 | 535 | 103269 | 128.7 | 665 | 49537 | 0.0 | 795 | 3037 | 0.0 | 925 | 3009 | 0.0 |
| 410 | 3412 | 0.2 | 540 | 107316 | 118.6 | 670 | 42866 | 0.0 | 800 | 2716 | 0.0 | 930 | 3026 | 0.0 |
| 415 | 6135 | 0.6 | 545 | 113101 | 108.4 | 675 | 36708 | 0.0 | 805 | 2648 | 0.0 | 935 | 4734 | 0.0 |
| 420 | 12146 | 2.0 | 550 | 120690 | 98.7 | 680 | 31814 | 0.0 | 810 | 3187 | 0.0 | 940 | 3719 | 0.0 |
| 425 | 23983 | 5.9 | 555 | 128583 | 87.9 | 685 | 27485 | 0.0 | 815 | 2931 | 0.0 | 945 | 1480 | 0.0 |
| 430 | 42142 | 14.3 | 560 | 137796 | 77.0 | 690 | 23698 | 0.0 | 820 | 2717 | 0.0 | 950 | 3450 | 0.0 |
| 435 | 68228 | 30.5 | 565 | 146577 | 65.8 | 695 | 20309 | 0.0 | 825 | 2236 | 0.0 | 955 | 5051 | 0.0 |
| 440 | 99323 | 55.5 | 570 | 154581 | 54.6 | 700 | 17890 | 0.0 | 830 | 2628 | 0.0 | 960 | 3176 | 0.0 |
| 445 | 115584 | 77.4 | 575 | 162633 | 44.3 | 705 | 15500 | 0.0 | 835 | 3140 | 0.0 | 965 | 5178 | 0.0 |
| 450 | 94997 | 73.6 | 580 | 168101 | 34.6 | 710 | 13699 | 0.0 | 840 | 3675 | 0.0 | 970 | 6385 | 0.0 |
| 455 | 61433 | 53.7 | 585 | 173145 | 26.5 | 715 | 12398 | 0.0 | 845 | 3283 | 0.0 | 975 | 3810 | 0.0 |
| 460 | 43373 | 41.9 | 590 | 174675 | 19.5 | 720 | 11147 | 0.0 | 850 | 3055 | 0.0 | 980 | 4322 | 0.0 |
| 465 | 32472 | 34.3 | 595 | 173724 | 13.9 | 725 | 9761 | 0.0 | 855 | 2932 | 0.0 | 985 | 4200 | 0.0 |
| 470 | 24257 | 27.9 | 600 | 171241 | 9.7 | 730 | 8651 | 0.0 | 860 | 3382 | 0.0 | 990 | 4661 | 0.0 |
| 475 | 21690 | 27.1 | 605 | 165134 | 6.5 | 735 | 7730 | 0.0 | 865 | 2605 | 0.0 | 995 | 6746 | 0.0 |
| 480 | 23173 | 31.3 | 610 | 156652 | 4.2 | 740 | 6847 | 0.0 | 870 | 3325 | 0.0 | 1000 | 4150 | 0.0 |
| 485 | 27564 | 40.0 | 615 | 147879 | 2.7 | 745 | 6124 | 0.0 | 875 | 3325 | 0.0 | | | |

REPORT NUMBER: SP1-2101-121-7

Melanopic Flux vs. Wavelength



Melanopic Lumens: 4490.7 M/P: 0.5

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 2672 | 0.0 | 490 | 34553 | 28.8 | 620 | 136720 | 0.1 | 750 | 5870 | 0.0 | 880 | 4216 | 0.0 |
| 365 | 2252 | 0.0 | 495 | 44336 | 36.6 | 625 | 126308 | 0.1 | 755 | 5421 | 0.0 | 885 | 4132 | 0.0 |
| 370 | 2217 | 0.0 | 500 | 54643 | 43.9 | 630 | 114625 | 0.0 | 760 | 5097 | 0.0 | 890 | 3992 | 0.0 |
| 375 | 2697 | 0.0 | 505 | 64676 | 49.6 | 635 | 103216 | 0.0 | 765 | 4626 | 0.0 | 895 | 3214 | 0.0 |
| 380 | 3039 | 0.0 | 510 | 73825 | 53.0 | 640 | 92605 | 0.0 | 770 | 3782 | 0.0 | 900 | 2580 | 0.0 |
| 385 | 2655 | 0.0 | 515 | 81872 | 53.5 | 645 | 83234 | 0.0 | 775 | 3506 | 0.0 | 905 | 1776 | 0.0 |
| 390 | 2357 | 0.0 | 520 | 88574 | 51.6 | 650 | 73263 | 0.0 | 780 | 3507 | 0.0 | 910 | 3995 | 0.0 |
| 395 | 2186 | 0.0 | 525 | 93289 | 47.3 | 655 | 64627 | 0.0 | 785 | 3267 | 0.0 | 915 | 4288 | 0.0 |
| 400 | 2015 | 0.0 | 530 | 98393 | 42.5 | 660 | 56614 | 0.0 | 790 | 2849 | 0.0 | 920 | 2446 | 0.0 |
| 405 | 2234 | 0.0 | 535 | 103269 | 37.2 | 665 | 49537 | 0.0 | 795 | 3037 | 0.0 | 925 | 3009 | 0.0 |
| 410 | 3412 | 0.1 | 540 | 107316 | 31.4 | 670 | 42866 | 0.0 | 800 | 2716 | 0.0 | 930 | 3026 | 0.0 |
| 415 | 6135 | 0.4 | 545 | 113101 | 26.3 | 675 | 36708 | 0.0 | 805 | 2648 | 0.0 | 935 | 4734 | 0.0 |
| 420 | 12146 | 1.4 | 550 | 120690 | 21.7 | 680 | 31814 | 0.0 | 810 | 3187 | 0.0 | 940 | 3719 | 0.0 |
| 425 | 23983 | 3.7 | 555 | 128583 | 17.3 | 685 | 27485 | 0.0 | 815 | 2931 | 0.0 | 945 | 1480 | 0.0 |
| 430 | 42142 | 8.9 | 560 | 137796 | 13.6 | 690 | 23698 | 0.0 | 820 | 2717 | 0.0 | 950 | 3450 | 0.0 |
| 435 | 68228 | 18.2 | 565 | 146577 | 10.3 | 695 | 20309 | 0.0 | 825 | 2236 | 0.0 | 955 | 5051 | 0.0 |
| 440 | 99323 | 33.2 | 570 | 154581 | 7.6 | 700 | 17890 | 0.0 | 830 | 2628 | 0.0 | 960 | 3176 | 0.0 |
| 445 | 115584 | 45.6 | 575 | 162633 | 5.4 | 705 | 15500 | 0.0 | 835 | 3140 | 0.0 | 965 | 5178 | 0.0 |
| 450 | 94997 | 43.8 | 580 | 168101 | 3.8 | 710 | 13699 | 0.0 | 840 | 3675 | 0.0 | 970 | 6385 | 0.0 |
| 455 | 61433 | 32.2 | 585 | 173145 | 2.6 | 715 | 12398 | 0.0 | 845 | 3283 | 0.0 | 975 | 3810 | 0.0 |
| 460 | 43373 | 25.6 | 590 | 174675 | 1.7 | 720 | 11147 | 0.0 | 850 | 3055 | 0.0 | 980 | 4322 | 0.0 |
| 465 | 32472 | 21.2 | 595 | 173724 | 1.1 | 725 | 9761 | 0.0 | 855 | 2932 | 0.0 | 985 | 4200 | 0.0 |
| 470 | 24257 | 17.4 | 600 | 171241 | 0.7 | 730 | 8651 | 0.0 | 860 | 3382 | 0.0 | 990 | 4661 | 0.0 |
| 475 | 21690 | 16.6 | 605 | 165134 | 0.5 | 735 | 7730 | 0.0 | 865 | 2605 | 0.0 | 995 | 6746 | 0.0 |
| 480 | 23173 | 18.6 | 610 | 156652 | 0.3 | 740 | 6847 | 0.0 | 870 | 3325 | 0.0 | 1000 | 4150 | 0.0 |
| 485 | 27564 | 22.7 | 615 | 147879 | 0.2 | 745 | 6124 | 0.0 | 875 | 3325 | 0.0 | | | |

Summary

$R_f = 76.9$
 $R_g = 94.4$
 $CIE R_a = 73.1$
 $R_g = -34.6$



Color Vector Graphics



Individual Sample Fidelity Index ($R_{f,i}$)

| | | | |
|------------|------------|------------|------------|
| CES01 = 86 | CES26 = 68 | CES51 = 90 | CES76 = 63 |
| CES02 = 62 | CES27 = 88 | CES52 = 89 | CES77 = 80 |
| CES03 = 31 | CES28 = 87 | CES53 = 80 | CES78 = 65 |
| CES04 = 70 | CES29 = 67 | CES54 = 84 | CES79 = 87 |
| CES05 = 48 | CES30 = 74 | CES55 = 84 | CES80 = 86 |
| CES06 = 51 | CES31 = 71 | CES56 = 75 | CES81 = 75 |
| CES07 = 40 | CES32 = 67 | CES57 = 74 | CES82 = 94 |
| CES08 = 39 | CES33 = 74 | CES58 = 76 | CES83 = 91 |
| CES09 = 29 | CES34 = 78 | CES59 = 87 | CES84 = 89 |
| CES10 = 75 | CES35 = 89 | CES60 = 93 | CES85 = 80 |
| CES11 = 58 | CES36 = 98 | CES61 = 86 | CES86 = 66 |
| CES12 = 64 | CES37 = 86 | CES62 = 89 | CES87 = 79 |
| CES13 = 43 | CES38 = 82 | CES63 = 77 | CES88 = 79 |
| CES14 = 74 | CES39 = 95 | CES64 = 74 | CES89 = 70 |
| CES15 = 71 | CES40 = 91 | CES65 = 68 | CES90 = 77 |
| CES16 = 47 | CES41 = 89 | CES66 = 71 | CES91 = 88 |
| CES17 = 50 | CES42 = 88 | CES67 = 69 | CES92 = 60 |
| CES18 = 56 | CES43 = 82 | CES68 = 74 | CES93 = 77 |
| CES19 = 72 | CES44 = 99 | CES69 = 82 | CES94 = 52 |
| CES20 = 65 | CES45 = 87 | CES70 = 67 | CES95 = 69 |
| CES21 = 86 | CES46 = 82 | CES71 = 66 | CES96 = 78 |
| CES22 = 79 | CES47 = 82 | CES72 = 88 | CES97 = 85 |
| CES23 = 92 | CES48 = 72 | CES73 = 59 | CES98 = 76 |
| CES24 = 91 | CES49 = 82 | CES74 = 97 | CES99 = 63 |
| CES25 = 72 | CES50 = 88 | CES75 = 66 | |



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)