

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: McGRAW-EDISON

Report Number: P635733

Luminaire Tested: GWS-SA3E-735-U-SLR-W-GRSBK

Issue Date: 1/10/2023

Test Information

Test Method: LM-79-2019
Report Number: P635733
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2209-782-42)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/10/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: McGRAW-EDISON
Catalog Number: GWS-SA3E-735-U-SLR-W-GRSBK
Description: GALLEON WALL SLIM LUMINAIRE. (3) LIGHTSQUARES WITH 16 LEDS EACH AND
SPILL LIGHT ELIMINATOR RIGHT OPTICS W/ FACTORY INSTALLED GLARE SHIELD, BK
Light Source: (48) 3500K CCT, 70 CRI LEDS
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 11571.6 lumens
Efficiency: N/A
Efficacy: 72.7 lumens/watt
Luminous Opening: Rectangular (W 1.5' x L: 0.5' x H: 0')
IES Classification: Type III - Short
BUG Rating: B2 - U0 - G1


Input Watts (W): 159.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 0
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT



REPORT NUMBER: P635733
 CATALOG NUMBER: GWS-SA3E-735-U-SLR-W-GRSBK

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 20 foot mounting height. Maximum calculated value = 9.1 fc
 Type III - Short - N/A

REPORT NUMBER: P635733
CATALOG NUMBER: GWS-SA3E-735-U-SLR-W-GRSBK

Luminous Intensity Polar Plot



— Vertical Plane Through 45-Deg Lateral - - - Horizontal Cone Through 57.5-Deg Vertical

REPORT NUMBER: P635733

CATALOG NUMBER: GWS-SA3E-735-U-SLR-W-GRSBK

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	2591.2	0.0	2591.2
	% Fixture	22.4	0.0	22.4
Street Side	Lumens	8980.4	0.0	8980.4
	% Fixture	77.6	0.0	77.6
Total	Lumens	11571.6	0.0	11571.6
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	200.1	1.7
10°-20°	647.3	5.6
20°-30°	1051.4	9.1
30°-40°	1624.6	14.0
40°-50°	2605.1	22.5
50°-60°	3560.4	30.8
60°-70°	1724.4	14.9
70°-80°	157.9	1.4
80°-90°	0.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	11571.6	100.0
0°-180°	11571.6	100.0

Coefficient of Utilization




REPORT NUMBER: P635733
 CATALOG NUMBER: GWS-SA3E-735-U-SLR-W-GRSBK

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	1132.1	9.8			
FM (30°-60°)	6159.8	53.2			
FH (60°-80°)	1688.1	14.6			G1/1800
FVH (80°-90°)	0.5	0.0			G0/10
BL (0°-30°)	766.7	6.6	B2/1000		
BM (30°-60°)	1630.3	14.1	B2/2500		
BH (60°-80°)	194.2	1.7	B1/500		G1/500
BVH (80°-90°)	0.0	0.0			G0/10
UL (90°-100°)	0.0	0.0		U0/0	
UH (100°-180°)	0.0	0.0		U0/0	

BUG Rating: B2-U0-G1
 Type III Short





REPORT NUMBER: P635733

CATALOG NUMBER: GWS-SA3E-735-U-SLR-W-GRSBK

CANDELA DISTRIBUTION (FULL):

	0°	1°	5°	15°	25°	35°	45°	55°	65°	75°	85°
0°	2033.8	2033.8	2033.8	2033.8	2033.8	2033.8	2033.8	2033.8	2033.8	2033.8	2033.8
2.5°	2203.3	2217.3	2240.6	2290.4	2332.4	2360.4	2372.8	2369.7	2352.6	2340.2	2315.3
5°	2439.7	2439.7	2484.8	2598.3	2685.3	2739.8	2767.8	2750.7	2716.4	2662.0	2578.1
7.5°	2646.5	2654.2	2730.4	2892.1	3024.3	3102.1	3147.2	3137.8	3077.2	2973.0	2805.1
10°	2808.2	2817.5	2918.6	3116.1	3271.5	3350.8	3417.7	3423.9	3357.1	3218.7	3025.9
12.5°	2965.2	2974.6	3080.3	3270.0	3406.8	3439.5	3498.6	3521.9	3504.8	3406.8	3206.2
15°	3134.7	3156.5	3246.7	3388.2	3445.7	3406.8	3445.7	3487.7	3545.2	3535.9	3355.5
17.5°	3301.1	3316.6	3408.4	3458.1	3394.4	3293.3	3312.0	3361.7	3492.3	3619.8	3503.2
20°	3455.0	3476.8	3553.0	3487.7	3294.9	3137.8	3139.4	3204.7	3403.7	3671.2	3654.1
22.5°	3616.7	3649.4	3703.8	3520.3	3203.1	3015.0	3022.8	3081.8	3333.7	3719.4	3825.1
25°	3828.2	3859.3	3895.1	3601.2	3173.6	2954.3	2983.9	3038.3	3333.7	3801.8	4036.6
27.5°	4114.3	4136.1	4137.6	3752.0	3224.9	2963.7	3025.9	3088.1	3433.3	3966.6	4319.6
30°	4473.5	4507.7	4462.6	3986.8	3385.1	3088.1	3179.8	3257.6	3647.8	4244.9	4736.3
32.5°	4910.4	4958.6	4898.0	4335.1	3719.4	3517.2	3683.6	3728.7	3989.9	4647.7	5209.0
35°	5423.6	5464.0	5398.7	4817.1	4499.9	4537.3	4838.9	4781.4	4677.2	5143.7	5761.0
37.5°	5986.4	6023.8	5897.8	5547.9	5653.7	5815.4	6297.4	6099.9	5764.1	5782.7	6359.6
40°	6502.7	6543.1	6345.6	6342.5	6560.2	6855.6	7437.2	7165.1	6707.9	6619.3	6920.9
42.5°	7037.6	7065.5	6886.7	6765.4	7259.9	7867.9	8483.6	8116.7	7333.0	7236.6	7623.8
45°	7801.0	7860.1	7541.4	6973.8	7889.7	9032.5	9890.8	9174.0	7759.0	7681.3	8699.8
47.5°	8923.7	8967.2	8317.3	7104.4	8475.9	10483.3	11649.4	10545.5	8133.8	7956.5	10170.7
50°	9852.0	9881.5	9031.0	7247.5	9099.4	12047.5	13653.7	12171.9	8555.2	8412.1	11543.7
52.5°	10536.1	10648.1	9968.6	7541.4	9918.8	13887.0	15872.6	14098.4	9212.9	9292.2	12681.9
55°	10677.6	10830.0	10609.2	7721.7	10640.3	15760.7	17922.0	15822.8	9869.1	9959.3	13064.4
57.5°	9383.9	9505.2	9688.7	6994.0	10623.2	16619.0	19111.5	16395.1	9570.5	8931.4	11632.3
60°	7029.8	7113.8	7446.5	5345.8	9769.6	15860.2	18184.8	15421.7	8368.6	6815.2	8863.0
62.5°	4168.7	4206.1	4627.4	3462.8	8108.9	13658.4	15081.2	13307.0	6613.1	4583.9	5428.2
65°	1600.0	1584.5	1906.3	1708.9	5963.1	10879.8	11217.2	10144.3	4537.3	2100.7	2069.6
67.5°	247.2	236.3	318.8	505.3	4300.9	7539.8	7401.4	7311.2	2842.4	489.8	427.6
70°	56.0	56.0	68.4	149.3	2627.8	4430.0	4740.9	4520.1	1819.3	104.2	56.0
72.5°	26.4	26.4	32.7	63.8	951.6	1825.5	2127.1	2094.5	590.9	34.2	20.2
75°	9.3	10.9	10.9	14.0	57.5	94.9	217.7	155.5	37.3	0.0	0.0
77.5°	3.1	3.1	3.1	3.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0
80°	1.6	1.6	1.6	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
82.5°	1.6	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P635733

CATALOG NUMBER: GWS-SA3E-735-U-SLR-W-GRSBK

CANDELA DISTRIBUTION (continued):

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	2033.8	2033.8	2033.8	2033.8	2033.8	2033.8	2033.8	2033.8	2033.8	2033.8	2033.8
2.5°	2260.9	2250.0	2209.5	2155.1	2102.2	2055.6	2007.4	1949.9	1907.9	1859.7	1844.1
5°	2512.7	2444.3	2333.9	2218.9	2113.1	2022.9	1935.9	1842.6	1774.2	1705.7	1682.4
7.5°	2725.8	2624.7	2445.9	2273.3	2128.7	2001.2	1875.2	1747.7	1648.2	1567.4	1542.5
10°	2917.0	2800.4	2561.0	2347.9	2166.0	2018.3	1865.9	1705.7	1576.7	1480.3	1457.0
12.5°	3081.8	2946.6	2658.9	2403.9	2181.6	2012.1	1864.3	1736.8	1620.2	1509.8	1480.3
15°	3220.2	3071.0	2741.3	2441.2	2158.2	1934.3	1805.3	1785.0	1775.7	1654.4	1596.9
17.5°	3355.5	3187.6	2808.2	2458.3	2092.9	1797.5	1704.2	1795.9	1893.9	1814.6	1741.5
20°	3497.0	3305.8	2876.6	2461.4	1984.1	1643.5	1628.0	1772.6	1897.0	1872.1	1803.7
22.5°	3663.4	3453.5	2962.1	2459.9	1847.2	1512.9	1572.0	1727.5	1828.6	1827.0	1772.6
25°	3904.4	3640.1	3077.2	2469.2	1698.0	1411.9	1509.8	1651.3	1733.7	1730.6	1685.5
27.5°	4162.5	3862.4	3226.5	2492.5	1570.5	1352.8	1436.7	1547.1	1618.7	1615.6	1576.7
30°	4524.8	4119.0	3369.5	2494.1	1478.7	1321.7	1355.9	1432.1	1500.5	1492.7	1463.2
32.5°	4964.9	4408.2	3489.2	2405.5	1421.2	1292.1	1271.9	1310.8	1363.7	1352.8	1345.0
35°	5496.6	4751.8	3591.9	2211.1	1332.6	1233.1	1178.6	1186.4	1223.7	1229.9	1226.8
37.5°	6103.1	5160.8	3719.4	1954.5	1212.8	1147.5	1074.4	1068.2	1090.0	1110.2	1125.8
40°	6701.7	5621.0	3892.0	1694.9	1104.0	1038.7	968.7	953.2	962.5	998.3	1030.9
42.5°	7375.0	6154.4	4078.6	1472.5	1029.4	919.0	852.1	822.6	849.0	906.5	945.4
45°	8345.2	6902.3	4260.5	1295.2	998.3	813.2	723.0	719.9	749.5	824.1	867.6
47.5°	9707.4	7869.4	4380.2	1156.9	996.7	730.8	623.5	642.2	676.4	749.5	799.2
50°	11035.3	9080.7	4248.0	1051.1	964.0	676.4	548.9	586.2	620.4	684.2	735.5
52.5°	11836.0	9732.2	3733.4	951.6	863.0	651.5	475.8	541.1	547.3	604.9	659.3
55°	11752.1	9310.8	2859.5	797.7	713.7	615.7	399.6	488.2	491.4	534.9	581.5
57.5°	10200.3	7993.8	1963.9	646.8	536.4	508.5	329.6	412.1	441.6	468.0	502.2
60°	7602.0	5832.5	875.4	525.6	340.5	343.6	281.4	311.0	356.1	387.2	416.7
62.5°	4479.7	3355.5	356.1	315.6	188.1	216.1	227.0	227.0	255.0	278.3	297.0
65°	1693.3	1174.0	144.6	158.6	98.0	101.1	133.7	164.8	186.6	206.8	231.7
67.5°	297.0	205.2	74.6	59.1	57.5	51.3	68.4	107.3	119.7	135.3	146.2
70°	49.8	42.0	31.1	29.5	26.4	28.0	45.1	76.2	84.0	88.6	93.3
72.5°	14.0	12.4	9.3	7.8	6.2	7.8	28.0	59.1	62.2	65.3	70.0
75°	0.0	0.0	0.0	0.0	0.0	0.0	10.9	42.0	45.1	46.6	51.3
77.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	9.3	12.4	15.5	12.4
80°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P635733

CATALOG NUMBER: GWS-SA3E-735-U-SLR-W-GRSBK

CANDELA DISTRIBUTION (continued):

	185°	195°	205°	215°	225°	235°	245°	255°	265°	270°	275°
0°	2033.8	2033.8	2033.8	2033.8	2033.8	2033.8	2033.8	2033.8	2033.8	2033.8	2033.8
2.5°	1834.8	1803.7	1786.6	1777.3	1777.3	1764.8	1750.8	1746.2	1766.4	1766.4	1800.6
5°	1652.9	1628.0	1600.0	1582.9	1556.5	1561.1	1545.6	1544.0	1564.2	1573.6	1609.3
7.5°	1526.9	1495.8	1478.7	1467.8	1453.8	1447.6	1433.6	1429.0	1439.9	1455.4	1489.6
10°	1443.0	1438.3	1436.7	1444.5	1444.5	1436.7	1424.3	1416.5	1419.6	1449.2	1488.1
12.5°	1464.7	1474.1	1477.2	1489.6	1495.8	1489.6	1480.3	1483.4	1503.6	1558.0	1615.6
15°	1559.6	1551.8	1548.7	1554.9	1559.6	1553.4	1550.3	1573.6	1643.5	1721.3	1786.6
17.5°	1660.7	1610.9	1589.1	1589.1	1592.2	1589.1	1592.2	1637.3	1750.8	1828.6	1876.8
20°	1712.0	1620.2	1586.0	1578.2	1584.5	1586.0	1596.9	1648.2	1772.6	1827.0	1837.9
22.5°	1696.4	1581.4	1542.5	1536.3	1542.5	1548.7	1559.6	1603.1	1719.7	1747.7	1743.1
25°	1618.7	1505.2	1474.1	1474.1	1488.1	1486.5	1491.2	1522.3	1618.7	1635.8	1628.0
27.5°	1520.7	1413.4	1387.0	1402.5	1415.0	1411.9	1413.4	1439.9	1511.4	1516.0	1508.3
30°	1421.2	1327.9	1303.0	1321.7	1338.8	1335.7	1337.2	1363.7	1408.8	1404.1	1393.2
32.5°	1320.1	1251.7	1233.1	1243.9	1270.4	1267.3	1273.5	1301.5	1318.6	1298.4	1285.9
35°	1226.8	1191.1	1177.1	1183.3	1203.5	1208.2	1219.1	1237.7	1237.7	1212.8	1191.1
37.5°	1139.8	1135.1	1125.8	1118.0	1136.6	1150.6	1166.2	1188.0	1156.9	1121.1	1100.9
40°	1058.9	1079.1	1066.7	1046.5	1057.3	1077.6	1108.7	1125.8	1088.4	1052.7	1018.5
42.5°	984.3	1018.5	1013.8	988.9	998.3	1016.9	1052.7	1066.7	1023.1	982.7	950.1
45°	912.7	960.9	964.0	933.0	942.3	960.9	1002.9	1007.6	951.6	908.1	884.7
47.5°	850.5	903.4	905.0	881.6	884.7	911.2	950.1	951.6	887.9	847.4	817.9
50°	791.5	852.1	856.8	836.5	839.7	870.8	903.4	897.2	828.8	786.8	760.4
52.5°	719.9	802.3	813.2	803.9	816.3	841.2	861.4	839.7	760.4	718.4	695.0
55°	642.2	749.5	772.8	766.6	780.6	800.8	805.4	791.5	691.9	650.0	628.2
57.5°	552.0	617.3	657.7	645.3	656.2	676.4	690.4	679.5	604.9	572.2	553.6
60°	457.1	500.7	510.0	489.8	480.5	516.2	548.9	534.9	471.1	450.9	429.2
62.5°	334.3	384.1	390.3	363.9	353.0	391.8	419.8	405.8	335.9	314.1	297.0
65°	267.4	314.1	326.5	301.7	295.4	325.0	342.1	307.9	258.1	234.8	216.1
67.5°	175.7	213.0	245.7	244.1	231.7	241.0	228.6	200.6	164.8	152.4	139.9
70°	108.8	130.6	150.8	158.6	157.0	153.9	136.8	116.6	105.7	101.1	94.9
72.5°	84.0	105.7	121.3	125.9	127.5	122.8	108.8	90.2	79.3	73.1	68.4
75°	62.2	79.3	91.7	98.0	101.1	98.0	84.0	71.5	60.6	56.0	51.3
77.5°	21.8	26.4	32.7	35.8	34.2	32.7	29.5	29.5	23.3	21.8	18.7
80°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P635733
 CATALOG NUMBER: GWS-SA3E-735-U-SLR-W-GRSBK

CANDELA DISTRIBUTION (continued):

	285°	295°	305°	315°	325°	335°	345°	355°	359°	360°
0°	2033.8	2033.8	2033.8	2033.8	2033.8	2033.8	2033.8	2033.8	2033.8	2033.8
2.5°	1839.5	1867.5	1918.8	1965.4	2015.2	2066.5	2122.5	2180.0	2206.4	2203.3
5°	1663.8	1724.4	1808.4	1900.1	2002.7	2113.1	2236.0	2361.9	2416.3	2439.7
7.5°	1553.4	1638.9	1749.3	1865.9	2001.2	2158.2	2343.3	2540.7	2620.0	2646.5
10°	1567.4	1666.9	1758.6	1872.1	2016.7	2220.4	2450.6	2685.3	2778.6	2808.2
12.5°	1680.9	1702.6	1727.5	1820.8	2002.7	2267.1	2548.5	2828.4	2935.7	2965.2
15°	1783.5	1682.4	1635.8	1721.3	1953.0	2299.7	2648.0	2982.3	3100.5	3134.7
17.5°	1788.2	1635.8	1531.6	1598.5	1872.1	2313.7	2746.0	3139.4	3268.4	3301.1
20°	1730.6	1584.5	1450.7	1452.3	1761.7	2310.6	2826.8	3280.9	3425.5	3455.0
22.5°	1646.7	1523.8	1385.4	1337.2	1643.5	2304.4	2915.5	3431.7	3588.8	3616.7
25°	1553.4	1446.1	1323.2	1250.2	1525.4	2310.6	3039.9	3629.2	3801.8	3828.2
27.5°	1452.3	1360.6	1275.0	1215.9	1425.9	2333.9	3189.1	3881.1	4086.3	4114.3
30°	1346.6	1278.1	1243.9	1208.2	1363.7	2340.2	3350.8	4175.0	4434.6	4473.5
32.5°	1242.4	1205.1	1206.6	1212.8	1304.6	2296.6	3498.6	4501.5	4848.2	4910.4
35°	1146.0	1135.1	1166.2	1197.3	1219.1	2184.7	3627.6	4887.1	5359.8	5423.6
37.5°	1063.6	1072.9	1111.8	1142.9	1125.8	2026.1	3798.7	5369.1	5932.0	5986.4
40°	984.3	1007.6	1052.7	1066.7	1054.2	1841.0	4003.9	5834.1	6428.0	6502.7
42.5°	911.2	928.3	992.0	995.1	1034.0	1652.9	4201.4	6334.7	6998.7	7037.6
45°	852.1	849.0	914.3	934.5	1060.5	1444.5	4394.2	7001.8	7745.0	7801.0
47.5°	794.6	791.5	807.0	898.7	1071.3	1251.7	4585.5	7978.3	8827.3	8923.7
50°	740.1	744.8	696.6	881.6	1012.3	1104.0	4672.5	8881.7	9811.5	9852.0
52.5°	691.9	674.8	590.9	825.7	886.3	964.0	4425.3	9292.2	10421.1	10536.1
55°	623.5	528.7	486.7	670.2	699.7	841.2	3624.5	9054.3	10473.9	10677.6
57.5°	533.3	415.2	413.6	494.5	494.5	780.6	2321.5	7735.7	9026.3	9383.9
60°	410.5	321.9	342.1	343.6	317.2	569.1	1303.0	5603.9	6673.7	7029.8
62.5°	292.3	245.7	258.1	205.2	181.9	284.6	625.1	3226.5	4119.0	4168.7
65°	195.9	166.4	135.3	113.5	112.0	121.3	258.1	1166.2	1418.1	1600.0
67.5°	129.1	101.1	71.5	71.5	80.9	80.9	98.0	192.8	270.6	247.2
70°	84.0	70.0	45.1	43.5	52.9	52.9	49.8	52.9	56.0	56.0
72.5°	62.2	52.9	26.4	23.3	29.5	31.1	28.0	26.4	26.4	26.4
75°	46.6	37.3	15.5	10.9	14.0	18.7	15.5	10.9	10.9	9.3
77.5°	18.7	14.0	6.2	4.7	7.8	10.9	9.3	4.7	3.1	3.1
80°	1.6	3.1	3.1	3.1	4.7	6.2	7.8	3.1	1.6	1.6
82.5°	0.0	1.6	1.6	1.6	3.1	4.7	6.2	3.1	1.6	1.6
85°	0.0	0.0	0.0	0.0	3.1	4.7	3.1	1.6	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	1.6	4.7	3.1	1.6	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)