

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: McGRAW-EDISON

Report Number: P640700

Luminaire Tested: GWS-SA5E-735-U-T3R-W-GRSBK

Issue Date: 1/10/2023

Test Information

Test Method: LM-79-2019
Report Number: P640700
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2209-782-16)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/10/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: McGRAW-EDISON
Catalog Number: GWS-SA5E-735-U-T3R-W-GRSBK
Description: GALLEON WALL SLIM LUMINAIRE. (5) LIGHTSQUARES WITH 16 LEDS EACH AND TYPE III ROADWAY OPTICS W/ FACTORY INSTALLED GLARE SHIELD, BK
Light Source: (80) 3500K CCT, 70 CRI LEDS
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 23222.4 lumens
Efficiency: N/A
Efficacy: 86.1 lumens/watt
Luminous Opening: Rectangular (W 1.5' x L: 1' x H: 0')
IES Classification: Type II - Short
BUG Rating: B3 - U0 - G2


Input Watts (W): 269.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 0
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT



REPORT NUMBER: P640700
 CATALOG NUMBER: GWS-SA5E-735-U-T3R-W-GRSBK

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 9.3 fc
 Type II - Short - N/A

REPORT NUMBER: P640700
CATALOG NUMBER: GWS-SA5E-735-U-T3R-W-GRSBK

Luminous Intensity Polar Plot



— Vertical Plane Through 38-Deg Lateral - - - Horizontal Cone Through 55-Deg Vertical

REPORT NUMBER: P640700
 CATALOG NUMBER: GWS-SA5E-735-U-T3R-W-GRSBK

FLUX DISTRIBUTION:

| | | Downward | Upward | Total |
|--------------------|-----------|----------|--------|---------|
| House Side | Lumens | 4524.5 | 0.0 | 4524.5 |
| | % Fixture | 19.5 | 0.0 | 19.5 |
| Street Side | Lumens | 18698.0 | 0.0 | 18698.0 |
| | % Fixture | 80.5 | 0.0 | 80.5 |
| Total | Lumens | 23222.4 | 0.0 | 23222.4 |
| | % Fixture | 100.0 | 0.0 | 100.0 |

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|---------|-----------|
| 0°-10° | 514.9 | 2.2 |
| 10°-20° | 1386.2 | 6.0 |
| 20°-30° | 2378.8 | 10.2 |
| 30°-40° | 3945.5 | 17.0 |
| 40°-50° | 5800.0 | 25.0 |
| 50°-60° | 6777.5 | 29.2 |
| 60°-70° | 2297.4 | 9.9 |
| 70°-80° | 117.5 | 0.5 |
| 80°-90° | 4.6 | 0.0 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-90° | 23222.4 | 100.0 |
| 0°-180° | 23222.4 | 100.0 |

Coefficient of Utilization




REPORT NUMBER: P640700

CATALOG NUMBER: GWS-SA5E-735-U-T3R-W-GRSBK

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

| Zone | Lumens | % Fixture | Zone Rating/Lumen Limit | | |
|----------------|---------|-----------|-------------------------|------|---------|
| | | | B | U | G |
| FL (0°-30°) | 2556.2 | 11.0 | | | |
| FM (30°-60°) | 14025.7 | 60.4 | | | |
| FH (60°-80°) | 2113.6 | 9.1 | | | G2/5000 |
| FVH (80°-90°) | 2.5 | 0.0 | | | G0/10 |
| BL (0°-30°) | 1723.8 | 7.4 | B3/2500 | | |
| BM (30°-60°) | 2497.3 | 10.8 | B2/2500 | | |
| BH (60°-80°) | 301.2 | 1.3 | B1/500 | | G1/500 |
| BVH (80°-90°) | 2.2 | 0.0 | | | G0/10 |
| UL (90°-100°) | 0.0 | 0.0 | | U0/0 | |
| UH (100°-180°) | 0.0 | 0.0 | | U0/0 | |

BUG Rating: B3-U0-G2
 Type II Short





REPORT NUMBER: P640700

CATALOG NUMBER: GWS-SA5E-735-U-T3R-W-GRSBK

CANDELA DISTRIBUTION (FULL):

| | 0° | 5° | 15° | 25° | 35° | 38° | 45° | 55° | 65° | 75° | 85° |
|-------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|
| 0° | 5568.9 | 5568.9 | 5568.9 | 5568.9 | 5568.9 | 5568.9 | 5568.9 | 5568.9 | 5568.9 | 5568.9 | 5568.9 |
| 2.5° | 5186.7 | 5176.1 | 5197.3 | 5239.8 | 5279.6 | 5292.9 | 5332.7 | 5388.4 | 5422.9 | 5505.2 | 5571.6 |
| 5° | 4953.1 | 4947.8 | 4969.0 | 5006.2 | 5059.3 | 5077.8 | 5138.9 | 5231.8 | 5324.7 | 5468.0 | 5608.7 |
| 7.5° | 4740.7 | 4738.1 | 4769.9 | 4852.2 | 4929.2 | 4953.1 | 5027.4 | 5141.6 | 5266.3 | 5486.6 | 5693.7 |
| 10° | 4462.0 | 4464.7 | 4525.7 | 4642.5 | 4783.2 | 4831.0 | 4950.4 | 5115.0 | 5276.9 | 5560.9 | 5847.6 |
| 12.5° | 4371.8 | 4377.1 | 4408.9 | 4499.2 | 4653.1 | 4714.2 | 4881.4 | 5130.9 | 5338.0 | 5667.1 | 6046.7 |
| 15° | 4592.1 | 4592.1 | 4565.6 | 4576.2 | 4645.2 | 4700.9 | 4876.1 | 5184.0 | 5441.5 | 5794.5 | 6243.1 |
| 17.5° | 5019.5 | 5003.5 | 4937.2 | 4846.9 | 4823.0 | 4841.6 | 4982.3 | 5298.2 | 5587.5 | 5943.2 | 6466.1 |
| 20° | 5598.1 | 5603.4 | 5473.4 | 5284.9 | 5133.6 | 5130.9 | 5215.9 | 5499.9 | 5797.2 | 6121.0 | 6707.6 |
| 22.5° | 6298.9 | 6277.6 | 6105.1 | 5847.6 | 5584.8 | 5563.6 | 5598.1 | 5807.8 | 6099.8 | 6402.4 | 7004.9 |
| 25° | 7111.1 | 7100.5 | 6856.3 | 6511.2 | 6163.5 | 6113.1 | 6113.1 | 6320.1 | 6532.5 | 6803.2 | 7360.6 |
| 27.5° | 7960.5 | 7960.5 | 7724.3 | 7326.1 | 6864.3 | 6774.0 | 6760.7 | 7004.9 | 7145.6 | 7198.7 | 7660.6 |
| 30° | 8833.8 | 8823.2 | 8589.6 | 8180.8 | 7687.1 | 7594.2 | 7557.0 | 7737.5 | 7838.4 | 7679.1 | 8034.8 |
| 32.5° | 9720.4 | 9739.0 | 9502.7 | 9123.1 | 8682.5 | 8621.5 | 8507.3 | 8507.3 | 8589.6 | 8366.6 | 8624.1 |
| 35° | 10673.3 | 10668.0 | 10482.2 | 10224.7 | 9847.8 | 9778.8 | 9590.3 | 9295.7 | 9420.4 | 9322.2 | 9439.0 |
| 37.5° | 11514.7 | 11554.6 | 11464.3 | 11273.2 | 10967.9 | 10898.9 | 10588.4 | 10054.8 | 10150.4 | 10304.3 | 10407.9 |
| 40° | 12369.5 | 12401.3 | 12491.6 | 12430.5 | 12045.6 | 11918.2 | 11366.1 | 10490.1 | 10596.3 | 11124.5 | 11421.8 |
| 42.5° | 13208.2 | 13224.2 | 13407.3 | 13508.2 | 12993.2 | 12770.3 | 11955.4 | 10755.6 | 10867.1 | 11766.9 | 12287.2 |
| 45° | 13741.8 | 13776.3 | 14078.9 | 14386.8 | 13829.4 | 13524.1 | 12467.7 | 11095.3 | 11143.1 | 12212.8 | 12926.9 |
| 47.5° | 13720.5 | 13800.2 | 14368.2 | 14928.3 | 14548.7 | 14219.6 | 13083.5 | 11639.5 | 11559.9 | 12632.2 | 13348.9 |
| 50° | 13293.2 | 13388.7 | 14203.6 | 15092.9 | 15066.3 | 14761.1 | 13768.3 | 12427.9 | 12178.3 | 13003.9 | 13402.0 |
| 52.5° | 12406.6 | 12682.7 | 13914.3 | 15114.1 | 15483.1 | 15329.1 | 14615.1 | 13489.6 | 13014.5 | 13537.4 | 13487.0 |
| 55° | 10490.1 | 10829.9 | 13035.7 | 14933.6 | 15860.0 | 15878.6 | 15504.3 | 14596.5 | 13922.3 | 14455.8 | 14009.9 |
| 57.5° | 7963.2 | 8233.9 | 10033.6 | 13293.2 | 15236.2 | 15541.5 | 15849.4 | 15180.5 | 14482.3 | 15082.2 | 14132.0 |
| 60° | 4799.1 | 5112.4 | 6282.9 | 9754.9 | 12305.8 | 12826.0 | 14033.8 | 13903.7 | 13062.3 | 13319.7 | 11589.1 |
| 62.5° | 1945.7 | 2110.2 | 2901.2 | 5375.1 | 7745.5 | 8231.3 | 9388.6 | 9585.0 | 9378.0 | 9115.2 | 7028.8 |
| 65° | 711.4 | 777.7 | 1162.6 | 2221.7 | 3562.2 | 3740.0 | 4350.5 | 4698.3 | 4984.9 | 4244.4 | 2614.6 |
| 67.5° | 440.6 | 483.1 | 756.5 | 1141.4 | 1295.3 | 1205.1 | 1226.3 | 1462.6 | 1396.2 | 862.7 | 467.2 |
| 70° | 326.5 | 361.0 | 591.9 | 791.0 | 522.9 | 403.5 | 273.4 | 292.0 | 262.8 | 230.9 | 228.3 |
| 72.5° | 225.6 | 257.5 | 443.3 | 467.2 | 201.7 | 143.3 | 100.9 | 140.7 | 159.3 | 156.6 | 161.9 |
| 75° | 148.6 | 172.5 | 278.7 | 183.2 | 50.4 | 39.8 | 34.5 | 74.3 | 95.6 | 95.6 | 98.2 |
| 77.5° | 87.6 | 100.9 | 98.2 | 37.2 | 10.6 | 10.6 | 8.0 | 13.3 | 21.2 | 23.9 | 29.2 |
| 80° | 10.6 | 8.0 | 5.3 | 5.3 | 5.3 | 5.3 | 5.3 | 5.3 | 8.0 | 8.0 | 8.0 |
| 82.5° | 2.7 | 2.7 | 2.7 | 5.3 | 5.3 | 5.3 | 5.3 | 5.3 | 5.3 | 8.0 | 8.0 |
| 85° | 0.0 | 0.0 | 2.7 | 2.7 | 5.3 | 5.3 | 5.3 | 5.3 | 5.3 | 8.0 | 8.0 |
| 87.5° | 0.0 | 0.0 | 2.7 | 2.7 | 5.3 | 5.3 | 5.3 | 5.3 | 5.3 | 8.0 | 8.0 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P640700

CATALOG NUMBER: GWS-SA5E-735-U-T3R-W-GRSBK

CANDELA DISTRIBUTION (continued):

| | 90° | 95° | 105° | 115° | 125° | 135° | 145° | 155° | 165° | 175° | 180° |
|-------|---------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 5568.9 | 5568.9 | 5568.9 | 5568.9 | 5568.9 | 5568.9 | 5568.9 | 5568.9 | 5568.9 | 5568.9 | 5568.9 |
| 2.5° | 5622.0 | 5603.4 | 5680.4 | 5736.1 | 5781.3 | 5802.5 | 5773.3 | 5770.6 | 5770.6 | 5712.2 | 5696.3 |
| 5° | 5688.4 | 5696.3 | 5805.2 | 5852.9 | 5860.9 | 5834.3 | 5768.0 | 5722.9 | 5696.3 | 5635.3 | 5600.8 |
| 7.5° | 5815.8 | 5842.3 | 5945.8 | 5937.9 | 5866.2 | 5744.1 | 5568.9 | 5433.5 | 5345.9 | 5250.4 | 5192.0 |
| 10° | 5998.9 | 6049.4 | 6113.1 | 6001.6 | 5773.3 | 5462.7 | 5101.7 | 4844.3 | 4690.3 | 4581.5 | 4515.1 |
| 12.5° | 6221.9 | 6272.3 | 6251.1 | 5988.3 | 5513.2 | 4958.4 | 4493.9 | 4122.3 | 3944.4 | 3846.2 | 3777.2 |
| 15° | 6447.5 | 6479.4 | 6341.3 | 5829.0 | 5054.0 | 4308.1 | 3790.5 | 3421.5 | 3203.8 | 3124.2 | 3065.8 |
| 17.5° | 6678.4 | 6670.5 | 6357.3 | 5515.8 | 4440.8 | 3575.5 | 3065.8 | 2813.7 | 2752.6 | 2739.3 | 2734.0 |
| 20° | 6920.0 | 6848.3 | 6293.6 | 5067.2 | 3702.9 | 2850.8 | 2561.5 | 2577.4 | 2688.9 | 2742.0 | 2752.6 |
| 22.5° | 7196.1 | 7015.6 | 6134.3 | 4459.4 | 2949.0 | 2375.7 | 2404.9 | 2561.5 | 2712.8 | 2784.5 | 2795.1 |
| 25° | 7490.7 | 7169.5 | 5868.9 | 3679.0 | 2325.2 | 2184.6 | 2357.1 | 2537.6 | 2699.5 | 2787.1 | 2797.7 |
| 27.5° | 7684.5 | 7206.7 | 5433.5 | 2893.3 | 1996.1 | 2110.2 | 2293.4 | 2465.9 | 2633.2 | 2728.7 | 2742.0 |
| 30° | 7894.2 | 7190.7 | 4841.6 | 2229.7 | 1884.6 | 2046.5 | 2205.8 | 2362.4 | 2516.4 | 2622.5 | 2633.2 |
| 32.5° | 8202.1 | 7180.1 | 4119.6 | 1810.3 | 1839.5 | 1996.1 | 2112.9 | 2243.0 | 2349.1 | 2410.2 | 2402.2 |
| 35° | 8605.5 | 7166.9 | 3278.2 | 1632.4 | 1812.9 | 1956.3 | 2049.2 | 2110.2 | 1993.4 | 1956.3 | 1964.2 |
| 37.5° | 9123.1 | 7198.7 | 2569.4 | 1558.1 | 1805.0 | 1945.7 | 2025.3 | 1850.1 | 1669.6 | 1600.6 | 1590.0 |
| 40° | 9696.5 | 7281.0 | 1958.9 | 1528.9 | 1831.5 | 1972.2 | 1935.1 | 1645.7 | 1422.8 | 1287.4 | 1258.2 |
| 42.5° | 10272.5 | 7371.2 | 1550.2 | 1518.3 | 1876.7 | 2046.5 | 1786.4 | 1497.1 | 1162.6 | 1085.6 | 1075.0 |
| 45° | 10699.8 | 7355.3 | 1340.5 | 1499.7 | 1916.5 | 2089.0 | 1746.6 | 1284.7 | 1037.9 | 1003.4 | 1006.0 |
| 47.5° | 10914.8 | 7180.1 | 1226.3 | 1457.3 | 1932.4 | 2046.5 | 1648.4 | 1197.1 | 952.9 | 990.1 | 1021.9 |
| 50° | 10800.7 | 6726.2 | 1120.2 | 1375.0 | 1897.9 | 1990.8 | 1491.8 | 1130.8 | 910.5 | 1064.4 | 1136.1 |
| 52.5° | 10662.7 | 6168.8 | 1003.4 | 1247.6 | 1815.6 | 1913.8 | 1430.7 | 1112.2 | 883.9 | 1027.2 | 1080.3 |
| 55° | 10845.8 | 5815.8 | 812.2 | 1051.1 | 1653.7 | 1733.3 | 1382.9 | 1109.5 | 822.9 | 799.0 | 791.0 |
| 57.5° | 10588.4 | 5112.4 | 581.3 | 756.5 | 1268.8 | 1372.3 | 1348.4 | 1091.0 | 730.0 | 727.3 | 737.9 |
| 60° | 8183.5 | 3118.9 | 398.2 | 480.4 | 777.7 | 875.9 | 1223.7 | 1043.2 | 629.1 | 578.7 | 581.3 |
| 62.5° | 4650.5 | 1327.2 | 273.4 | 297.3 | 398.2 | 472.5 | 934.3 | 947.6 | 581.3 | 552.1 | 581.3 |
| 65° | 1619.2 | 475.1 | 212.4 | 199.1 | 220.3 | 252.2 | 536.2 | 732.6 | 528.2 | 477.8 | 483.1 |
| 67.5° | 334.5 | 236.2 | 188.5 | 164.6 | 164.6 | 164.6 | 273.4 | 456.6 | 435.3 | 379.6 | 384.9 |
| 70° | 212.4 | 201.7 | 164.6 | 140.7 | 135.4 | 124.8 | 156.6 | 252.2 | 299.9 | 276.1 | 278.7 |
| 72.5° | 156.6 | 154.0 | 130.1 | 114.1 | 100.9 | 90.2 | 98.2 | 124.8 | 154.0 | 159.3 | 161.9 |
| 75° | 95.6 | 98.2 | 84.9 | 71.7 | 63.7 | 55.7 | 58.4 | 58.4 | 58.4 | 53.1 | 58.4 |
| 77.5° | 29.2 | 31.9 | 26.5 | 21.2 | 18.6 | 18.6 | 18.6 | 15.9 | 13.3 | 8.0 | 8.0 |
| 80° | 8.0 | 8.0 | 8.0 | 8.0 | 8.0 | 5.3 | 5.3 | 2.7 | 2.7 | 0.0 | 0.0 |
| 82.5° | 8.0 | 8.0 | 8.0 | 8.0 | 5.3 | 5.3 | 2.7 | 2.7 | 0.0 | 0.0 | 0.0 |
| 85° | 8.0 | 8.0 | 8.0 | 8.0 | 5.3 | 5.3 | 2.7 | 2.7 | 0.0 | 0.0 | 0.0 |
| 87.5° | 8.0 | 8.0 | 8.0 | 8.0 | 5.3 | 5.3 | 2.7 | 2.7 | 0.0 | 0.0 | 0.0 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |

LM-79-08: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

All Brands

Data applicable to all product families using SA light engines

Report Number: SP1-2101-121-7

Luminaire Tested: IFLD-S-SA2A-735-U-T2

Test Date: 03/04/2021

Test Information

Test Method: LM-79-08
 Report Number: SP1-2101-121-7
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1
 Measurement Geometry: 4π
 Issue Date: 03/04/2021
 Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
 Product Line: STREETWORKS
 Catalog Number: **IFLD-S-SA2A-735-U-T2**
 Description: STREETWORKS INF FLOOD

PROGRAMMED @ 615mA.

Spectral Parameters

| | | | | | |
|---------------------------|--------|-----------|------|------|-------|
| CCT (K): | 3388 | CRI (Ra): | 73.1 | R9: | -34.6 |
| CIE u': | 0.2371 | R1: | 68.9 | R10: | 57.8 |
| CIE v': | 0.5177 | R2: | 81.1 | R11: | 68.6 |
| Duv: | 0.0032 | R3: | 93.1 | R12: | 53.9 |
| CIE x: | 0.4153 | R4: | 71.6 | R13: | 70.9 |
| CIE y: | 0.4030 | R5: | 69.4 | R14: | 96.2 |
| CIE z: | 0.1817 | R6: | 75.0 | | |
| Peak Wavelength (nm): | 590 | R7: | 79.5 | | |
| Dominant Wavelength (nm): | 580 | R8: | 46.4 | | |
| Purity: | 45.7 | | | | |
| Rf: | 76.9 | | | | |
| Rg: | 94.4 | | | | |



Test Conditions

Stabilization Time: 81M
 Operation Time: 12H
 Room Temperature (°C) / RH%: 25.0/30%
 Sphere Temperature (°C): 24.1

REPORT NUMBER: SP1-2101-121-7

| Measurement and Test Equipment | | | |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument | Identification Number | Calibration Date | Calibration Due Date |
| Photometer | IN0058 | 1/31/2021 | 7/31/2021 |
| Power Meter | IN0071 | 12/1/2020 | 12/1/2021 |
| AC Power Source | IN0063 | 12/1/2020 | 12/1/2021 |
| DC Power Source | IN0208 | 12/1/2020 | 12/1/2021 |
| Sphere Thermometer | IN0085 | 12/1/2020 | 12/1/2021 |
| Room Thermometer | IN0046 | 12/1/2020 | 12/1/2021 |

REPORT NUMBER: SP1-2101-121-7

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 3500K 4-step quadrangle

REPORT NUMBER: SP1-2101-121-7

Photopic Flux vs. Wavelength



#####

| λ (nm) | Power (µW/nm) | Lumens (Φ/nm) | λ (nm) | Power (µW/nm) | Lumens (Φ/nm) | λ (nm) | Power (µW/nm) | Lumens (Φ/nm) | λ (nm) | Power (µW/nm) | Lumens (Φ/nm) | λ (nm) | Power (µW/nm) | Lumens (Φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 2672 | 0.0 | 490 | 34553 | 4.9 | 620 | 136720 | 35.6 | 750 | 5870 | 0.0 | 880 | 4216 | 0.0 |
| 365 | 2252 | 0.0 | 495 | 44336 | 8.0 | 625 | 126308 | 27.9 | 755 | 5421 | 0.0 | 885 | 4132 | 0.0 |
| 370 | 2217 | 0.0 | 500 | 54643 | 12.1 | 630 | 114625 | 20.7 | 760 | 5097 | 0.0 | 890 | 3992 | 0.0 |
| 375 | 2697 | 0.0 | 505 | 64676 | 18.1 | 635 | 103216 | 15.5 | 765 | 4626 | 0.0 | 895 | 3214 | 0.0 |
| 380 | 3039 | 0.0 | 510 | 73825 | 25.4 | 640 | 92605 | 11.1 | 770 | 3782 | 0.0 | 900 | 2580 | 0.0 |
| 385 | 2655 | 0.0 | 515 | 81872 | 33.9 | 645 | 83234 | 8.0 | 775 | 3506 | 0.0 | 905 | 1776 | 0.0 |
| 390 | 2357 | 0.0 | 520 | 88574 | 43.0 | 650 | 73263 | 5.4 | 780 | 3507 | 0.0 | 910 | 3995 | 0.0 |
| 395 | 2186 | 0.0 | 525 | 93289 | 50.1 | 655 | 64627 | 3.7 | 785 | 3267 | 0.0 | 915 | 4288 | 0.0 |
| 400 | 2015 | 0.0 | 530 | 98393 | 57.9 | 660 | 56614 | 2.4 | 790 | 2849 | 0.0 | 920 | 2446 | 0.0 |
| 405 | 2234 | 0.0 | 535 | 103269 | 64.0 | 665 | 49537 | 1.6 | 795 | 3037 | 0.0 | 925 | 3009 | 0.0 |
| 410 | 3412 | 0.0 | 540 | 107316 | 69.9 | 670 | 42866 | 0.9 | 800 | 2716 | 0.0 | 930 | 3026 | 0.0 |
| 415 | 6135 | 0.0 | 545 | 113101 | 75.3 | 675 | 36708 | 0.6 | 805 | 2648 | 0.0 | 935 | 4734 | 0.0 |
| 420 | 12146 | 0.0 | 550 | 120690 | 82.0 | 680 | 31814 | 0.4 | 810 | 3187 | 0.0 | 940 | 3719 | 0.0 |
| 425 | 23983 | 0.1 | 555 | 128583 | 87.8 | 685 | 27485 | 0.2 | 815 | 2931 | 0.0 | 945 | 1480 | 0.0 |
| 430 | 42142 | 0.3 | 560 | 137796 | 93.6 | 690 | 23698 | 0.1 | 820 | 2717 | 0.0 | 950 | 3450 | 0.0 |
| 435 | 68228 | 0.8 | 565 | 146577 | 97.5 | 695 | 20309 | 0.1 | 825 | 2236 | 0.0 | 955 | 5051 | 0.0 |
| 440 | 99323 | 1.6 | 570 | 154581 | 100.5 | 700 | 17890 | 0.1 | 830 | 2628 | 0.0 | 960 | 3176 | 0.0 |
| 445 | 115584 | 2.4 | 575 | 162633 | 101.2 | 705 | 15500 | 0.0 | 835 | 3140 | 0.0 | 965 | 5178 | 0.0 |
| 450 | 94997 | 2.5 | 580 | 168101 | 99.9 | 710 | 13699 | 0.0 | 840 | 3675 | 0.0 | 970 | 6385 | 0.0 |
| 455 | 61433 | 2.1 | 585 | 173145 | 96.2 | 715 | 12398 | 0.0 | 845 | 3283 | 0.0 | 975 | 3810 | 0.0 |
| 460 | 43373 | 1.8 | 590 | 174675 | 90.3 | 720 | 11147 | 0.0 | 850 | 3055 | 0.0 | 980 | 4322 | 0.0 |
| 465 | 32472 | 1.7 | 595 | 173724 | 82.3 | 725 | 9761 | 0.0 | 855 | 2932 | 0.0 | 985 | 4200 | 0.0 |
| 470 | 24257 | 1.5 | 600 | 171241 | 73.8 | 730 | 8651 | 0.0 | 860 | 3382 | 0.0 | 990 | 4661 | 0.0 |
| 475 | 21690 | 1.7 | 605 | 165134 | 64.0 | 735 | 7730 | 0.0 | 865 | 2605 | 0.0 | 995 | 6746 | 0.0 |
| 480 | 23173 | 2.2 | 610 | 156652 | 53.8 | 740 | 6847 | 0.0 | 870 | 3325 | 0.0 | 1000 | 4150 | 0.0 |
| 485 | 27564 | 3.3 | 615 | 147879 | 44.6 | 745 | 6124 | 0.0 | 875 | 3325 | 0.0 | | | |

REPORT NUMBER: SP1-2101-121-7

Scotopic Flux vs. Wavelength



Scotopic Lumens: 12126

S/P: 1.36

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 2672 | 0.0 | 490 | 34553 | 53.2 | 620 | 136720 | 1.7 | 750 | 5870 | 0.0 | 880 | 4216 | 0.0 |
| 365 | 2252 | 0.0 | 495 | 44336 | 71.7 | 625 | 126308 | 1.1 | 755 | 5421 | 0.0 | 885 | 4132 | 0.0 |
| 370 | 2217 | 0.0 | 500 | 54643 | 91.4 | 630 | 114625 | 0.6 | 760 | 5097 | 0.0 | 890 | 3992 | 0.0 |
| 375 | 2697 | 0.0 | 505 | 64676 | 110.0 | 635 | 103216 | 0.4 | 765 | 4626 | 0.0 | 895 | 3214 | 0.0 |
| 380 | 3039 | 0.0 | 510 | 73825 | 125.1 | 640 | 92605 | 0.2 | 770 | 3782 | 0.0 | 900 | 2580 | 0.0 |
| 385 | 2655 | 0.0 | 515 | 81872 | 135.7 | 645 | 83234 | 0.1 | 775 | 3506 | 0.0 | 905 | 1776 | 0.0 |
| 390 | 2357 | 0.0 | 520 | 88574 | 140.8 | 650 | 73263 | 0.1 | 780 | 3507 | 0.0 | 910 | 3995 | 0.0 |
| 395 | 2186 | 0.0 | 525 | 93289 | 139.6 | 655 | 64627 | 0.1 | 785 | 3267 | 0.0 | 915 | 4288 | 0.0 |
| 400 | 2015 | 0.0 | 530 | 98393 | 135.7 | 660 | 56614 | 0.0 | 790 | 2849 | 0.0 | 920 | 2446 | 0.0 |
| 405 | 2234 | 0.1 | 535 | 103269 | 128.7 | 665 | 49537 | 0.0 | 795 | 3037 | 0.0 | 925 | 3009 | 0.0 |
| 410 | 3412 | 0.2 | 540 | 107316 | 118.6 | 670 | 42866 | 0.0 | 800 | 2716 | 0.0 | 930 | 3026 | 0.0 |
| 415 | 6135 | 0.6 | 545 | 113101 | 108.4 | 675 | 36708 | 0.0 | 805 | 2648 | 0.0 | 935 | 4734 | 0.0 |
| 420 | 12146 | 2.0 | 550 | 120690 | 98.7 | 680 | 31814 | 0.0 | 810 | 3187 | 0.0 | 940 | 3719 | 0.0 |
| 425 | 23983 | 5.9 | 555 | 128583 | 87.9 | 685 | 27485 | 0.0 | 815 | 2931 | 0.0 | 945 | 1480 | 0.0 |
| 430 | 42142 | 14.3 | 560 | 137796 | 77.0 | 690 | 23698 | 0.0 | 820 | 2717 | 0.0 | 950 | 3450 | 0.0 |
| 435 | 68228 | 30.5 | 565 | 146577 | 65.8 | 695 | 20309 | 0.0 | 825 | 2236 | 0.0 | 955 | 5051 | 0.0 |
| 440 | 99323 | 55.5 | 570 | 154581 | 54.6 | 700 | 17890 | 0.0 | 830 | 2628 | 0.0 | 960 | 3176 | 0.0 |
| 445 | 115584 | 77.4 | 575 | 162633 | 44.3 | 705 | 15500 | 0.0 | 835 | 3140 | 0.0 | 965 | 5178 | 0.0 |
| 450 | 94997 | 73.6 | 580 | 168101 | 34.6 | 710 | 13699 | 0.0 | 840 | 3675 | 0.0 | 970 | 6385 | 0.0 |
| 455 | 61433 | 53.7 | 585 | 173145 | 26.5 | 715 | 12398 | 0.0 | 845 | 3283 | 0.0 | 975 | 3810 | 0.0 |
| 460 | 43373 | 41.9 | 590 | 174675 | 19.5 | 720 | 11147 | 0.0 | 850 | 3055 | 0.0 | 980 | 4322 | 0.0 |
| 465 | 32472 | 34.3 | 595 | 173724 | 13.9 | 725 | 9761 | 0.0 | 855 | 2932 | 0.0 | 985 | 4200 | 0.0 |
| 470 | 24257 | 27.9 | 600 | 171241 | 9.7 | 730 | 8651 | 0.0 | 860 | 3382 | 0.0 | 990 | 4661 | 0.0 |
| 475 | 21690 | 27.1 | 605 | 165134 | 6.5 | 735 | 7730 | 0.0 | 865 | 2605 | 0.0 | 995 | 6746 | 0.0 |
| 480 | 23173 | 31.3 | 610 | 156652 | 4.2 | 740 | 6847 | 0.0 | 870 | 3325 | 0.0 | 1000 | 4150 | 0.0 |
| 485 | 27564 | 40.0 | 615 | 147879 | 2.7 | 745 | 6124 | 0.0 | 875 | 3325 | 0.0 | | | |

REPORT NUMBER: SP1-2101-121-7

Melanopic Flux vs. Wavelength



Melanopic Lumens: 4490.7 M/P: 0.5




| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 2672 | 0.0 | 490 | 34553 | 28.8 | 620 | 136720 | 0.1 | 750 | 5870 | 0.0 | 880 | 4216 | 0.0 |
| 365 | 2252 | 0.0 | 495 | 44336 | 36.6 | 625 | 126308 | 0.1 | 755 | 5421 | 0.0 | 885 | 4132 | 0.0 |
| 370 | 2217 | 0.0 | 500 | 54643 | 43.9 | 630 | 114625 | 0.0 | 760 | 5097 | 0.0 | 890 | 3992 | 0.0 |
| 375 | 2697 | 0.0 | 505 | 64676 | 49.6 | 635 | 103216 | 0.0 | 765 | 4626 | 0.0 | 895 | 3214 | 0.0 |
| 380 | 3039 | 0.0 | 510 | 73825 | 53.0 | 640 | 92605 | 0.0 | 770 | 3782 | 0.0 | 900 | 2580 | 0.0 |
| 385 | 2655 | 0.0 | 515 | 81872 | 53.5 | 645 | 83234 | 0.0 | 775 | 3506 | 0.0 | 905 | 1776 | 0.0 |
| 390 | 2357 | 0.0 | 520 | 88574 | 51.6 | 650 | 73263 | 0.0 | 780 | 3507 | 0.0 | 910 | 3995 | 0.0 |
| 395 | 2186 | 0.0 | 525 | 93289 | 47.3 | 655 | 64627 | 0.0 | 785 | 3267 | 0.0 | 915 | 4288 | 0.0 |
| 400 | 2015 | 0.0 | 530 | 98393 | 42.5 | 660 | 56614 | 0.0 | 790 | 2849 | 0.0 | 920 | 2446 | 0.0 |
| 405 | 2234 | 0.0 | 535 | 103269 | 37.2 | 665 | 49537 | 0.0 | 795 | 3037 | 0.0 | 925 | 3009 | 0.0 |
| 410 | 3412 | 0.1 | 540 | 107316 | 31.4 | 670 | 42866 | 0.0 | 800 | 2716 | 0.0 | 930 | 3026 | 0.0 |
| 415 | 6135 | 0.4 | 545 | 113101 | 26.3 | 675 | 36708 | 0.0 | 805 | 2648 | 0.0 | 935 | 4734 | 0.0 |
| 420 | 12146 | 1.4 | 550 | 120690 | 21.7 | 680 | 31814 | 0.0 | 810 | 3187 | 0.0 | 940 | 3719 | 0.0 |
| 425 | 23983 | 3.7 | 555 | 128583 | 17.3 | 685 | 27485 | 0.0 | 815 | 2931 | 0.0 | 945 | 1480 | 0.0 |
| 430 | 42142 | 8.9 | 560 | 137796 | 13.6 | 690 | 23698 | 0.0 | 820 | 2717 | 0.0 | 950 | 3450 | 0.0 |
| 435 | 68228 | 18.2 | 565 | 146577 | 10.3 | 695 | 20309 | 0.0 | 825 | 2236 | 0.0 | 955 | 5051 | 0.0 |
| 440 | 99323 | 33.2 | 570 | 154581 | 7.6 | 700 | 17890 | 0.0 | 830 | 2628 | 0.0 | 960 | 3176 | 0.0 |
| 445 | 115584 | 45.6 | 575 | 162633 | 5.4 | 705 | 15500 | 0.0 | 835 | 3140 | 0.0 | 965 | 5178 | 0.0 |
| 450 | 94997 | 43.8 | 580 | 168101 | 3.8 | 710 | 13699 | 0.0 | 840 | 3675 | 0.0 | 970 | 6385 | 0.0 |
| 455 | 61433 | 32.2 | 585 | 173145 | 2.6 | 715 | 12398 | 0.0 | 845 | 3283 | 0.0 | 975 | 3810 | 0.0 |
| 460 | 43373 | 25.6 | 590 | 174675 | 1.7 | 720 | 11147 | 0.0 | 850 | 3055 | 0.0 | 980 | 4322 | 0.0 |
| 465 | 32472 | 21.2 | 595 | 173724 | 1.1 | 725 | 9761 | 0.0 | 855 | 2932 | 0.0 | 985 | 4200 | 0.0 |
| 470 | 24257 | 17.4 | 600 | 171241 | 0.7 | 730 | 8651 | 0.0 | 860 | 3382 | 0.0 | 990 | 4661 | 0.0 |
| 475 | 21690 | 16.6 | 605 | 165134 | 0.5 | 735 | 7730 | 0.0 | 865 | 2605 | 0.0 | 995 | 6746 | 0.0 |
| 480 | 23173 | 18.6 | 610 | 156652 | 0.3 | 740 | 6847 | 0.0 | 870 | 3325 | 0.0 | 1000 | 4150 | 0.0 |
| 485 | 27564 | 22.7 | 615 | 147879 | 0.2 | 745 | 6124 | 0.0 | 875 | 3325 | 0.0 | | | |

Summary

$R_f = 76.9$
 $R_g = 94.4$
 $CIE R_a = 73.1$
 $R_g = -34.6$



Color Vector Graphics



Individual Sample Fidelity Index ($R_{f,i}$)

| | | | |
|------------|------------|------------|------------|
| CES01 = 86 | CES26 = 68 | CES51 = 90 | CES76 = 63 |
| CES02 = 62 | CES27 = 88 | CES52 = 89 | CES77 = 80 |
| CES03 = 31 | CES28 = 87 | CES53 = 80 | CES78 = 65 |
| CES04 = 70 | CES29 = 67 | CES54 = 84 | CES79 = 87 |
| CES05 = 48 | CES30 = 74 | CES55 = 84 | CES80 = 86 |
| CES06 = 51 | CES31 = 71 | CES56 = 75 | CES81 = 75 |
| CES07 = 40 | CES32 = 67 | CES57 = 74 | CES82 = 94 |
| CES08 = 39 | CES33 = 74 | CES58 = 76 | CES83 = 91 |
| CES09 = 29 | CES34 = 78 | CES59 = 87 | CES84 = 89 |
| CES10 = 75 | CES35 = 89 | CES60 = 93 | CES85 = 80 |
| CES11 = 58 | CES36 = 98 | CES61 = 86 | CES86 = 66 |
| CES12 = 64 | CES37 = 86 | CES62 = 89 | CES87 = 79 |
| CES13 = 43 | CES38 = 82 | CES63 = 77 | CES88 = 79 |
| CES14 = 74 | CES39 = 95 | CES64 = 74 | CES89 = 70 |
| CES15 = 71 | CES40 = 91 | CES65 = 68 | CES90 = 77 |
| CES16 = 47 | CES41 = 89 | CES66 = 71 | CES91 = 88 |
| CES17 = 50 | CES42 = 88 | CES67 = 69 | CES92 = 60 |
| CES18 = 56 | CES43 = 82 | CES68 = 74 | CES93 = 77 |
| CES19 = 72 | CES44 = 99 | CES69 = 82 | CES94 = 52 |
| CES20 = 65 | CES45 = 87 | CES70 = 67 | CES95 = 69 |
| CES21 = 86 | CES46 = 82 | CES71 = 66 | CES96 = 78 |
| CES22 = 79 | CES47 = 82 | CES72 = 88 | CES97 = 85 |
| CES23 = 92 | CES48 = 72 | CES73 = 59 | CES98 = 76 |
| CES24 = 91 | CES49 = 82 | CES74 = 97 | CES99 = 63 |
| CES25 = 72 | CES50 = 88 | CES75 = 66 | |



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)