

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: McGRAW-EDISON

Report Number: P634234

Luminaire Tested: GWS-SA3B-735-U-SL2-W-GRSBK

Issue Date: 1/10/2023

Test Information

Test Method: LM-79-2019
Report Number: P634234
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2209-782-28)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/10/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: McGRAW-EDISON
Catalog Number: GWS-SA3B-735-U-SL2-W-GRSBK
Description: GALLEON WALL SLIM LUMINAIRE. (3) LIGHTSQUARES WITH 16 LEDS EACH AND TYPE II SPILL LIGHT ELIMINATOR OPTICS W/ FACTORY INSTALLED GLARE SHIELD, BK
Light Source: (48) 3500K CCT, 70 CRI LEDS
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6023.9 lumens
Efficiency: N/A
Efficacy: 88.2 lumens/watt
Luminous Opening: Rectangular (W 1.5' x L: 0.5' x H: 0')
IES Classification: Type II - Short
BUG Rating: B2 - U0 - G1


Input Watts (W): 68.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 0
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT



REPORT NUMBER: P634234
 CATALOG NUMBER: GWS-SA3B-735-U-SL2-W-GRSBK

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 10 foot mounting height. Maximum calculated value = 21.1 fc
 Type II - Short - N/A

REPORT NUMBER: P634234
CATALOG NUMBER: GWS-SA3B-735-U-SL2-W-GRSBK

Luminous Intensity Polar Plot



— Vertical Plane Through 50-Deg Lateral - - - Horizontal Cone Through 55-Deg Vertical

REPORT NUMBER: P634234

CATALOG NUMBER: GWS-SA3B-735-U-SL2-W-GRSBK


FLUX DISTRIBUTION:

| | | Downward | Upward | Total |
|--------------------|-----------|----------|--------|--------|
| House Side | Lumens | 1187.0 | 0.0 | 1187.0 |
| | % Fixture | 19.7 | 0.0 | 19.7 |
| Street Side | Lumens | 4836.9 | 0.0 | 4836.9 |
| | % Fixture | 80.3 | 0.0 | 80.3 |
| Total | Lumens | 6023.9 | 0.0 | 6023.9 |
| | % Fixture | 100.0 | 0.0 | 100.0 |

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 185.6 | 3.1 |
| 10°-20° | 456.8 | 7.6 |
| 20°-30° | 644.3 | 10.7 |
| 30°-40° | 953.4 | 15.8 |
| 40°-50° | 1375.4 | 22.8 |
| 50°-60° | 1622.4 | 26.9 |
| 60°-70° | 723.7 | 12.0 |
| 70°-80° | 62.2 | 1.0 |
| 80°-90° | 0.0 | 0.0 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-90° | 6023.9 | 100.0 |
| 0°-180° | 6023.9 | 100.0 |

Coefficient of Utilization




REPORT NUMBER: P634234

CATALOG NUMBER: GWS-SA3B-735-U-SL2-W-GRSBK

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

| Zone | Lumens | % Fixture | Zone Rating/Lumen Limit | | |
|----------------|--------|-----------|-------------------------|------|---------|
| | | | B | U | G |
| FL (0°-30°) | 777.7 | 12.9 | | | |
| FM (30°-60°) | 3380.4 | 56.1 | | | |
| FH (60°-80°) | 678.8 | 11.3 | | | G1/1800 |
| FVH (80°-90°) | 0.0 | 0.0 | | | G0/10 |
| BL (0°-30°) | 508.9 | 8.4 | B2/1000 | | |
| BM (30°-60°) | 570.9 | 9.5 | B1/1000 | | |
| BH (60°-80°) | 107.2 | 1.8 | B0/110 | | G0/110 |
| BVH (80°-90°) | 0.0 | 0.0 | | | G0/10 |
| UL (90°-100°) | 0.0 | 0.0 | | U0/0 | |
| UH (100°-180°) | 0.0 | 0.0 | | U0/0 | |

BUG Rating: B2-U0-G1
 Type II Short





REPORT NUMBER: P634234

CATALOG NUMBER: GWS-SA3B-735-U-SL2-W-GRSBK

CANDELA DISTRIBUTION (FULL):

| | 0° | 5° | 15° | 25° | 35° | 45° | 50° | 55° | 65° | 75° | 85° |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 2113.5 | 2113.5 | 2113.5 | 2113.5 | 2113.5 | 2113.5 | 2113.5 | 2113.5 | 2113.5 | 2113.5 | 2113.5 |
| 2.5° | 1963.5 | 1965.0 | 1965.7 | 1985.6 | 1992.9 | 2022.3 | 2037.8 | 2045.9 | 2067.2 | 2092.2 | 2112.8 |
| 5° | 1831.9 | 1829.7 | 1833.3 | 1858.3 | 1874.5 | 1917.9 | 1941.4 | 1957.6 | 2004.7 | 2063.5 | 2112.8 |
| 7.5° | 1717.1 | 1721.6 | 1726.0 | 1753.2 | 1777.4 | 1824.5 | 1858.3 | 1882.6 | 1948.1 | 2035.6 | 2118.7 |
| 10° | 1636.2 | 1636.2 | 1642.9 | 1673.8 | 1702.4 | 1760.5 | 1794.4 | 1825.2 | 1903.2 | 2010.6 | 2125.3 |
| 12.5° | 1576.7 | 1577.4 | 1585.5 | 1620.8 | 1653.9 | 1714.2 | 1749.5 | 1779.7 | 1865.7 | 1985.6 | 2126.8 |
| 15° | 1548.7 | 1546.5 | 1553.1 | 1590.7 | 1627.4 | 1684.0 | 1720.8 | 1750.2 | 1839.2 | 1971.6 | 2134.1 |
| 17.5° | 1541.4 | 1539.9 | 1545.1 | 1581.8 | 1619.3 | 1674.5 | 1710.5 | 1739.9 | 1835.5 | 1976.0 | 2156.2 |
| 20° | 1562.7 | 1559.8 | 1557.6 | 1589.2 | 1624.5 | 1678.9 | 1716.4 | 1749.5 | 1853.2 | 2000.3 | 2190.0 |
| 22.5° | 1613.5 | 1613.5 | 1608.3 | 1623.7 | 1647.3 | 1696.6 | 1735.5 | 1778.9 | 1899.5 | 2048.8 | 2240.0 |
| 25° | 1706.8 | 1699.5 | 1689.9 | 1696.6 | 1693.6 | 1724.5 | 1770.8 | 1831.1 | 1987.0 | 2129.0 | 2301.0 |
| 27.5° | 1813.5 | 1820.1 | 1803.9 | 1804.7 | 1778.9 | 1767.9 | 1821.6 | 1912.8 | 2117.2 | 2242.2 | 2391.5 |
| 30° | 1958.4 | 1953.2 | 1953.9 | 1951.7 | 1892.2 | 1840.0 | 1898.0 | 2019.4 | 2281.2 | 2415.0 | 2509.2 |
| 32.5° | 2071.6 | 2079.0 | 2103.2 | 2117.2 | 2039.2 | 1955.4 | 2017.2 | 2164.3 | 2468.0 | 2612.1 | 2653.3 |
| 35° | 2191.5 | 2204.7 | 2254.0 | 2299.6 | 2234.1 | 2137.8 | 2204.0 | 2356.2 | 2643.7 | 2807.0 | 2818.8 |
| 37.5° | 2318.0 | 2344.4 | 2403.3 | 2483.4 | 2473.1 | 2387.8 | 2448.1 | 2582.0 | 2782.0 | 2924.7 | 2955.5 |
| 40° | 2462.8 | 2488.6 | 2584.9 | 2700.4 | 2724.6 | 2705.5 | 2725.4 | 2803.3 | 2873.2 | 2929.8 | 3014.4 |
| 42.5° | 2621.7 | 2657.0 | 2779.0 | 2933.5 | 3024.7 | 3041.6 | 2995.3 | 2987.2 | 2912.9 | 2871.0 | 3001.9 |
| 45° | 2809.2 | 2850.4 | 2988.6 | 3188.7 | 3333.5 | 3356.3 | 3276.2 | 3172.5 | 2937.9 | 2827.6 | 2964.4 |
| 47.5° | 3019.5 | 3058.5 | 3196.0 | 3436.5 | 3652.0 | 3660.8 | 3521.1 | 3354.1 | 3012.2 | 2877.6 | 2993.0 |
| 50° | 3090.1 | 3114.4 | 3233.5 | 3515.9 | 3913.0 | 3980.7 | 3778.4 | 3558.6 | 3161.5 | 3024.7 | 3132.8 |
| 52.5° | 2847.4 | 2857.0 | 2960.7 | 3246.0 | 3860.1 | 4294.7 | 4154.2 | 3863.8 | 3426.9 | 3249.0 | 3348.2 |
| 55° | 2256.2 | 2240.7 | 2324.6 | 2586.4 | 3354.9 | 4230.7 | 4494.7 | 4343.2 | 3768.9 | 3512.2 | 3628.4 |
| 57.5° | 1578.2 | 1559.8 | 1540.6 | 1717.9 | 2503.3 | 3586.5 | 4141.7 | 4410.2 | 4094.7 | 3773.3 | 3930.7 |
| 60° | 1297.2 | 1279.6 | 1186.9 | 1105.3 | 1513.4 | 2575.3 | 3181.3 | 3686.5 | 4068.2 | 3760.1 | 3921.1 |
| 62.5° | 1120.7 | 1110.4 | 1072.9 | 961.9 | 890.6 | 1470.1 | 1992.2 | 2476.1 | 3121.7 | 2952.6 | 2961.4 |
| 65° | 880.3 | 877.3 | 903.1 | 914.8 | 787.6 | 813.3 | 1016.3 | 1286.9 | 1687.7 | 1591.4 | 1509.0 |
| 67.5° | 601.6 | 594.9 | 643.5 | 791.3 | 757.5 | 642.0 | 594.9 | 600.1 | 730.2 | 446.4 | 354.5 |
| 70° | 382.4 | 367.0 | 367.7 | 490.5 | 616.3 | 506.7 | 458.9 | 403.7 | 363.3 | 66.2 | 75.0 |
| 72.5° | 244.9 | 235.3 | 202.2 | 221.4 | 285.3 | 247.1 | 249.3 | 214.7 | 143.4 | 35.3 | 41.2 |
| 75° | 103.0 | 94.9 | 72.8 | 58.1 | 57.4 | 36.0 | 31.6 | 29.4 | 19.9 | 19.9 | 21.3 |
| 77.5° | 0.7 | 0.0 | 0.0 | 0.7 | 1.5 | 0.7 | 0.7 | 1.5 | 2.9 | 4.4 | 5.1 |
| 80° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.7 |
| 82.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 85° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 87.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P634234

CATALOG NUMBER: GWS-SA3B-735-U-SL2-W-GRSBK

CANDELA DISTRIBUTION (continued):

| | 90° | 95° | 105° | 115° | 125° | 135° | 145° | 155° | 165° | 175° | 180° |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 2113.5 | 2113.5 | 2113.5 | 2113.5 | 2113.5 | 2113.5 | 2113.5 | 2113.5 | 2113.5 | 2113.5 | 2113.5 |
| 2.5° | 2125.3 | 2107.6 | 2127.5 | 2134.8 | 2134.1 | 2134.8 | 2113.5 | 2098.8 | 2098.1 | 2079.7 | 2070.9 |
| 5° | 2133.4 | 2119.4 | 2134.1 | 2124.5 | 2101.8 | 2073.1 | 2034.8 | 2001.7 | 1987.0 | 1965.7 | 1955.4 |
| 7.5° | 2148.8 | 2134.1 | 2131.9 | 2093.7 | 2037.0 | 1976.7 | 1909.1 | 1848.8 | 1816.4 | 1777.4 | 1779.7 |
| 10° | 2159.8 | 2142.9 | 2114.3 | 2036.3 | 1942.2 | 1845.8 | 1745.1 | 1655.4 | 1598.7 | 1546.5 | 1537.7 |
| 12.5° | 2164.3 | 2139.3 | 2072.3 | 1954.7 | 1822.3 | 1696.6 | 1548.7 | 1420.8 | 1332.5 | 1264.1 | 1254.6 |
| 15° | 2172.4 | 2131.9 | 2018.7 | 1856.1 | 1674.5 | 1496.5 | 1308.3 | 1133.2 | 1016.3 | 937.6 | 944.2 |
| 17.5° | 2184.9 | 2123.8 | 1958.4 | 1745.8 | 1515.6 | 1264.1 | 1009.7 | 808.9 | 701.6 | 656.0 | 656.7 |
| 20° | 2202.5 | 2114.3 | 1892.2 | 1624.5 | 1325.2 | 1001.6 | 706.0 | 554.5 | 524.3 | 522.9 | 520.7 |
| 22.5° | 2226.0 | 2104.7 | 1821.6 | 1491.4 | 1099.4 | 701.6 | 469.9 | 422.9 | 435.4 | 459.6 | 464.0 |
| 25° | 2254.0 | 2092.9 | 1742.9 | 1341.4 | 853.1 | 460.4 | 352.3 | 344.9 | 375.1 | 407.4 | 414.8 |
| 27.5° | 2297.4 | 2087.0 | 1653.2 | 1170.7 | 598.6 | 330.2 | 288.3 | 292.7 | 319.9 | 347.1 | 353.7 |
| 30° | 2370.9 | 2098.1 | 1555.4 | 979.5 | 384.6 | 263.3 | 250.0 | 256.7 | 271.4 | 285.3 | 291.2 |
| 32.5° | 2470.9 | 2130.4 | 1460.5 | 770.7 | 274.3 | 228.7 | 225.8 | 229.4 | 235.3 | 243.4 | 245.6 |
| 35° | 2587.8 | 2186.3 | 1362.7 | 551.5 | 226.5 | 208.9 | 205.9 | 205.9 | 208.9 | 210.3 | 211.1 |
| 37.5° | 2684.2 | 2245.2 | 1270.8 | 367.0 | 203.0 | 193.4 | 189.0 | 186.8 | 186.1 | 187.5 | 188.3 |
| 40° | 2726.1 | 2269.4 | 1170.7 | 266.9 | 186.1 | 179.4 | 172.8 | 166.2 | 166.2 | 171.3 | 172.1 |
| 42.5° | 2696.7 | 2242.2 | 1055.3 | 220.6 | 174.3 | 164.7 | 154.4 | 148.5 | 151.5 | 156.6 | 158.1 |
| 45° | 2634.2 | 2175.3 | 928.1 | 194.9 | 162.5 | 150.0 | 138.3 | 134.6 | 137.5 | 144.1 | 145.6 |
| 47.5° | 2623.9 | 2131.2 | 775.8 | 178.0 | 150.0 | 137.5 | 125.0 | 121.3 | 125.0 | 130.2 | 131.6 |
| 50° | 2726.1 | 2169.4 | 606.7 | 163.3 | 138.3 | 124.3 | 114.0 | 110.3 | 112.5 | 115.5 | 116.9 |
| 52.5° | 2912.9 | 2311.3 | 489.8 | 149.3 | 124.3 | 111.0 | 104.4 | 100.0 | 100.0 | 103.0 | 103.7 |
| 55° | 3188.7 | 2559.2 | 422.9 | 133.1 | 108.1 | 100.7 | 94.9 | 90.5 | 90.5 | 91.9 | 92.7 |
| 57.5° | 3506.4 | 2859.2 | 438.3 | 111.8 | 94.9 | 91.2 | 86.0 | 82.4 | 83.8 | 83.8 | 83.8 |
| 60° | 3462.2 | 2837.1 | 469.2 | 94.1 | 83.8 | 82.4 | 78.0 | 76.5 | 80.2 | 77.2 | 75.7 |
| 62.5° | 2550.3 | 1959.8 | 245.6 | 77.2 | 72.1 | 70.6 | 67.7 | 70.6 | 75.7 | 67.7 | 64.7 |
| 65° | 1238.4 | 948.7 | 98.5 | 63.2 | 61.0 | 59.6 | 58.1 | 62.5 | 65.4 | 52.9 | 50.0 |
| 67.5° | 291.2 | 236.8 | 64.0 | 53.7 | 50.7 | 47.8 | 49.3 | 50.0 | 47.8 | 36.0 | 34.6 |
| 70° | 75.7 | 74.3 | 50.0 | 44.9 | 40.4 | 37.5 | 37.5 | 36.8 | 31.6 | 22.8 | 21.3 |
| 72.5° | 41.2 | 40.4 | 36.0 | 33.8 | 27.9 | 25.0 | 25.7 | 22.8 | 17.6 | 13.2 | 12.5 |
| 75° | 20.6 | 22.1 | 20.6 | 19.1 | 15.4 | 14.0 | 14.0 | 12.5 | 8.8 | 5.1 | 5.1 |
| 77.5° | 4.4 | 5.1 | 5.1 | 4.4 | 3.7 | 2.9 | 2.9 | 3.7 | 1.5 | 0.0 | 0.0 |
| 80° | 0.7 | 0.7 | 0.7 | 0.7 | 0.7 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 82.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 85° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 87.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |

LM-79-08: Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Report Prepared for

Cooper Lighting Solutions

All Brands

Data applicable to all product families using SA light engines

Report Number: SP1-2101-121-7

Luminaire Tested: IFLD-S-SA2A-735-U-T2

Test Date: 03/04/2021

Test Information

Test Method: LM-79-08
 Report Number: SP1-2101-121-7
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1
 Measurement Geometry: 4π
 Issue Date: 03/04/2021
 Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
 Product Line: STREETWORKS
 Catalog Number: **IFLD-S-SA2A-735-U-T2**
 Description: STREETWORKS INF FLOOD

PROGRAMMED @ 615mA.

Spectral Parameters

| | | | | | |
|---------------------------|--------|-----------|------|------|-------|
| CCT (K): | 3388 | CRI (Ra): | 73.1 | R9: | -34.6 |
| CIE u': | 0.2371 | R1: | 68.9 | R10: | 57.8 |
| CIE v': | 0.5177 | R2: | 81.1 | R11: | 68.6 |
| Duv: | 0.0032 | R3: | 93.1 | R12: | 53.9 |
| CIE x: | 0.4153 | R4: | 71.6 | R13: | 70.9 |
| CIE y: | 0.4030 | R5: | 69.4 | R14: | 96.2 |
| CIE z: | 0.1817 | R6: | 75.0 | | |
| Peak Wavelength (nm): | 590 | R7: | 79.5 | | |
| Dominant Wavelength (nm): | 580 | R8: | 46.4 | | |
| Purity: | 45.7 | | | | |
| Rf: | 76.9 | | | | |
| Rg: | 94.4 | | | | |



Test Conditions

Stabilization Time: 81M
 Operation Time: 12H
 Room Temperature (°C) / RH%: 25.0/30%
 Sphere Temperature (°C): 24.1

REPORT NUMBER: SP1-2101-121-7

| Measurement and Test Equipment | | | |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument | Identification Number | Calibration Date | Calibration Due Date |
| Photometer | IN0058 | 1/31/2021 | 7/31/2021 |
| Power Meter | IN0071 | 12/1/2020 | 12/1/2021 |
| AC Power Source | IN0063 | 12/1/2020 | 12/1/2021 |
| DC Power Source | IN0208 | 12/1/2020 | 12/1/2021 |
| Sphere Thermometer | IN0085 | 12/1/2020 | 12/1/2021 |
| Room Thermometer | IN0046 | 12/1/2020 | 12/1/2021 |

REPORT NUMBER: SP1-2101-121-7

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 3500K 4-step quadrangle

REPORT NUMBER: SP1-2101-121-7

Photopic Flux vs. Wavelength



#####

| λ (nm) | Power (µW/nm) | Lumens (Φ/nm) | λ (nm) | Power (µW/nm) | Lumens (Φ/nm) | λ (nm) | Power (µW/nm) | Lumens (Φ/nm) | λ (nm) | Power (µW/nm) | Lumens (Φ/nm) | λ (nm) | Power (µW/nm) | Lumens (Φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 2672 | 0.0 | 490 | 34553 | 4.9 | 620 | 136720 | 35.6 | 750 | 5870 | 0.0 | 880 | 4216 | 0.0 |
| 365 | 2252 | 0.0 | 495 | 44336 | 8.0 | 625 | 126308 | 27.9 | 755 | 5421 | 0.0 | 885 | 4132 | 0.0 |
| 370 | 2217 | 0.0 | 500 | 54643 | 12.1 | 630 | 114625 | 20.7 | 760 | 5097 | 0.0 | 890 | 3992 | 0.0 |
| 375 | 2697 | 0.0 | 505 | 64676 | 18.1 | 635 | 103216 | 15.5 | 765 | 4626 | 0.0 | 895 | 3214 | 0.0 |
| 380 | 3039 | 0.0 | 510 | 73825 | 25.4 | 640 | 92605 | 11.1 | 770 | 3782 | 0.0 | 900 | 2580 | 0.0 |
| 385 | 2655 | 0.0 | 515 | 81872 | 33.9 | 645 | 83234 | 8.0 | 775 | 3506 | 0.0 | 905 | 1776 | 0.0 |
| 390 | 2357 | 0.0 | 520 | 88574 | 43.0 | 650 | 73263 | 5.4 | 780 | 3507 | 0.0 | 910 | 3995 | 0.0 |
| 395 | 2186 | 0.0 | 525 | 93289 | 50.1 | 655 | 64627 | 3.7 | 785 | 3267 | 0.0 | 915 | 4288 | 0.0 |
| 400 | 2015 | 0.0 | 530 | 98393 | 57.9 | 660 | 56614 | 2.4 | 790 | 2849 | 0.0 | 920 | 2446 | 0.0 |
| 405 | 2234 | 0.0 | 535 | 103269 | 64.0 | 665 | 49537 | 1.6 | 795 | 3037 | 0.0 | 925 | 3009 | 0.0 |
| 410 | 3412 | 0.0 | 540 | 107316 | 69.9 | 670 | 42866 | 0.9 | 800 | 2716 | 0.0 | 930 | 3026 | 0.0 |
| 415 | 6135 | 0.0 | 545 | 113101 | 75.3 | 675 | 36708 | 0.6 | 805 | 2648 | 0.0 | 935 | 4734 | 0.0 |
| 420 | 12146 | 0.0 | 550 | 120690 | 82.0 | 680 | 31814 | 0.4 | 810 | 3187 | 0.0 | 940 | 3719 | 0.0 |
| 425 | 23983 | 0.1 | 555 | 128583 | 87.8 | 685 | 27485 | 0.2 | 815 | 2931 | 0.0 | 945 | 1480 | 0.0 |
| 430 | 42142 | 0.3 | 560 | 137796 | 93.6 | 690 | 23698 | 0.1 | 820 | 2717 | 0.0 | 950 | 3450 | 0.0 |
| 435 | 68228 | 0.8 | 565 | 146577 | 97.5 | 695 | 20309 | 0.1 | 825 | 2236 | 0.0 | 955 | 5051 | 0.0 |
| 440 | 99323 | 1.6 | 570 | 154581 | 100.5 | 700 | 17890 | 0.1 | 830 | 2628 | 0.0 | 960 | 3176 | 0.0 |
| 445 | 115584 | 2.4 | 575 | 162633 | 101.2 | 705 | 15500 | 0.0 | 835 | 3140 | 0.0 | 965 | 5178 | 0.0 |
| 450 | 94997 | 2.5 | 580 | 168101 | 99.9 | 710 | 13699 | 0.0 | 840 | 3675 | 0.0 | 970 | 6385 | 0.0 |
| 455 | 61433 | 2.1 | 585 | 173145 | 96.2 | 715 | 12398 | 0.0 | 845 | 3283 | 0.0 | 975 | 3810 | 0.0 |
| 460 | 43373 | 1.8 | 590 | 174675 | 90.3 | 720 | 11147 | 0.0 | 850 | 3055 | 0.0 | 980 | 4322 | 0.0 |
| 465 | 32472 | 1.7 | 595 | 173724 | 82.3 | 725 | 9761 | 0.0 | 855 | 2932 | 0.0 | 985 | 4200 | 0.0 |
| 470 | 24257 | 1.5 | 600 | 171241 | 73.8 | 730 | 8651 | 0.0 | 860 | 3382 | 0.0 | 990 | 4661 | 0.0 |
| 475 | 21690 | 1.7 | 605 | 165134 | 64.0 | 735 | 7730 | 0.0 | 865 | 2605 | 0.0 | 995 | 6746 | 0.0 |
| 480 | 23173 | 2.2 | 610 | 156652 | 53.8 | 740 | 6847 | 0.0 | 870 | 3325 | 0.0 | 1000 | 4150 | 0.0 |
| 485 | 27564 | 3.3 | 615 | 147879 | 44.6 | 745 | 6124 | 0.0 | 875 | 3325 | 0.0 | | | |

REPORT NUMBER: SP1-2101-121-7

Scotopic Flux vs. Wavelength



Scotopic Lumens: 12126

S/P: 1.36

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 2672 | 0.0 | 490 | 34553 | 53.2 | 620 | 136720 | 1.7 | 750 | 5870 | 0.0 | 880 | 4216 | 0.0 |
| 365 | 2252 | 0.0 | 495 | 44336 | 71.7 | 625 | 126308 | 1.1 | 755 | 5421 | 0.0 | 885 | 4132 | 0.0 |
| 370 | 2217 | 0.0 | 500 | 54643 | 91.4 | 630 | 114625 | 0.6 | 760 | 5097 | 0.0 | 890 | 3992 | 0.0 |
| 375 | 2697 | 0.0 | 505 | 64676 | 110.0 | 635 | 103216 | 0.4 | 765 | 4626 | 0.0 | 895 | 3214 | 0.0 |
| 380 | 3039 | 0.0 | 510 | 73825 | 125.1 | 640 | 92605 | 0.2 | 770 | 3782 | 0.0 | 900 | 2580 | 0.0 |
| 385 | 2655 | 0.0 | 515 | 81872 | 135.7 | 645 | 83234 | 0.1 | 775 | 3506 | 0.0 | 905 | 1776 | 0.0 |
| 390 | 2357 | 0.0 | 520 | 88574 | 140.8 | 650 | 73263 | 0.1 | 780 | 3507 | 0.0 | 910 | 3995 | 0.0 |
| 395 | 2186 | 0.0 | 525 | 93289 | 139.6 | 655 | 64627 | 0.1 | 785 | 3267 | 0.0 | 915 | 4288 | 0.0 |
| 400 | 2015 | 0.0 | 530 | 98393 | 135.7 | 660 | 56614 | 0.0 | 790 | 2849 | 0.0 | 920 | 2446 | 0.0 |
| 405 | 2234 | 0.1 | 535 | 103269 | 128.7 | 665 | 49537 | 0.0 | 795 | 3037 | 0.0 | 925 | 3009 | 0.0 |
| 410 | 3412 | 0.2 | 540 | 107316 | 118.6 | 670 | 42866 | 0.0 | 800 | 2716 | 0.0 | 930 | 3026 | 0.0 |
| 415 | 6135 | 0.6 | 545 | 113101 | 108.4 | 675 | 36708 | 0.0 | 805 | 2648 | 0.0 | 935 | 4734 | 0.0 |
| 420 | 12146 | 2.0 | 550 | 120690 | 98.7 | 680 | 31814 | 0.0 | 810 | 3187 | 0.0 | 940 | 3719 | 0.0 |
| 425 | 23983 | 5.9 | 555 | 128583 | 87.9 | 685 | 27485 | 0.0 | 815 | 2931 | 0.0 | 945 | 1480 | 0.0 |
| 430 | 42142 | 14.3 | 560 | 137796 | 77.0 | 690 | 23698 | 0.0 | 820 | 2717 | 0.0 | 950 | 3450 | 0.0 |
| 435 | 68228 | 30.5 | 565 | 146577 | 65.8 | 695 | 20309 | 0.0 | 825 | 2236 | 0.0 | 955 | 5051 | 0.0 |
| 440 | 99323 | 55.5 | 570 | 154581 | 54.6 | 700 | 17890 | 0.0 | 830 | 2628 | 0.0 | 960 | 3176 | 0.0 |
| 445 | 115584 | 77.4 | 575 | 162633 | 44.3 | 705 | 15500 | 0.0 | 835 | 3140 | 0.0 | 965 | 5178 | 0.0 |
| 450 | 94997 | 73.6 | 580 | 168101 | 34.6 | 710 | 13699 | 0.0 | 840 | 3675 | 0.0 | 970 | 6385 | 0.0 |
| 455 | 61433 | 53.7 | 585 | 173145 | 26.5 | 715 | 12398 | 0.0 | 845 | 3283 | 0.0 | 975 | 3810 | 0.0 |
| 460 | 43373 | 41.9 | 590 | 174675 | 19.5 | 720 | 11147 | 0.0 | 850 | 3055 | 0.0 | 980 | 4322 | 0.0 |
| 465 | 32472 | 34.3 | 595 | 173724 | 13.9 | 725 | 9761 | 0.0 | 855 | 2932 | 0.0 | 985 | 4200 | 0.0 |
| 470 | 24257 | 27.9 | 600 | 171241 | 9.7 | 730 | 8651 | 0.0 | 860 | 3382 | 0.0 | 990 | 4661 | 0.0 |
| 475 | 21690 | 27.1 | 605 | 165134 | 6.5 | 735 | 7730 | 0.0 | 865 | 2605 | 0.0 | 995 | 6746 | 0.0 |
| 480 | 23173 | 31.3 | 610 | 156652 | 4.2 | 740 | 6847 | 0.0 | 870 | 3325 | 0.0 | 1000 | 4150 | 0.0 |
| 485 | 27564 | 40.0 | 615 | 147879 | 2.7 | 745 | 6124 | 0.0 | 875 | 3325 | 0.0 | | | |

REPORT NUMBER: SP1-2101-121-7

Melanopic Flux vs. Wavelength



Melanopic Lumens: 4490.7 M/P: 0.5

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 2672 | 0.0 | 490 | 34553 | 28.8 | 620 | 136720 | 0.1 | 750 | 5870 | 0.0 | 880 | 4216 | 0.0 |
| 365 | 2252 | 0.0 | 495 | 44336 | 36.6 | 625 | 126308 | 0.1 | 755 | 5421 | 0.0 | 885 | 4132 | 0.0 |
| 370 | 2217 | 0.0 | 500 | 54643 | 43.9 | 630 | 114625 | 0.0 | 760 | 5097 | 0.0 | 890 | 3992 | 0.0 |
| 375 | 2697 | 0.0 | 505 | 64676 | 49.6 | 635 | 103216 | 0.0 | 765 | 4626 | 0.0 | 895 | 3214 | 0.0 |
| 380 | 3039 | 0.0 | 510 | 73825 | 53.0 | 640 | 92605 | 0.0 | 770 | 3782 | 0.0 | 900 | 2580 | 0.0 |
| 385 | 2655 | 0.0 | 515 | 81872 | 53.5 | 645 | 83234 | 0.0 | 775 | 3506 | 0.0 | 905 | 1776 | 0.0 |
| 390 | 2357 | 0.0 | 520 | 88574 | 51.6 | 650 | 73263 | 0.0 | 780 | 3507 | 0.0 | 910 | 3995 | 0.0 |
| 395 | 2186 | 0.0 | 525 | 93289 | 47.3 | 655 | 64627 | 0.0 | 785 | 3267 | 0.0 | 915 | 4288 | 0.0 |
| 400 | 2015 | 0.0 | 530 | 98393 | 42.5 | 660 | 56614 | 0.0 | 790 | 2849 | 0.0 | 920 | 2446 | 0.0 |
| 405 | 2234 | 0.0 | 535 | 103269 | 37.2 | 665 | 49537 | 0.0 | 795 | 3037 | 0.0 | 925 | 3009 | 0.0 |
| 410 | 3412 | 0.1 | 540 | 107316 | 31.4 | 670 | 42866 | 0.0 | 800 | 2716 | 0.0 | 930 | 3026 | 0.0 |
| 415 | 6135 | 0.4 | 545 | 113101 | 26.3 | 675 | 36708 | 0.0 | 805 | 2648 | 0.0 | 935 | 4734 | 0.0 |
| 420 | 12146 | 1.4 | 550 | 120690 | 21.7 | 680 | 31814 | 0.0 | 810 | 3187 | 0.0 | 940 | 3719 | 0.0 |
| 425 | 23983 | 3.7 | 555 | 128583 | 17.3 | 685 | 27485 | 0.0 | 815 | 2931 | 0.0 | 945 | 1480 | 0.0 |
| 430 | 42142 | 8.9 | 560 | 137796 | 13.6 | 690 | 23698 | 0.0 | 820 | 2717 | 0.0 | 950 | 3450 | 0.0 |
| 435 | 68228 | 18.2 | 565 | 146577 | 10.3 | 695 | 20309 | 0.0 | 825 | 2236 | 0.0 | 955 | 5051 | 0.0 |
| 440 | 99323 | 33.2 | 570 | 154581 | 7.6 | 700 | 17890 | 0.0 | 830 | 2628 | 0.0 | 960 | 3176 | 0.0 |
| 445 | 115584 | 45.6 | 575 | 162633 | 5.4 | 705 | 15500 | 0.0 | 835 | 3140 | 0.0 | 965 | 5178 | 0.0 |
| 450 | 94997 | 43.8 | 580 | 168101 | 3.8 | 710 | 13699 | 0.0 | 840 | 3675 | 0.0 | 970 | 6385 | 0.0 |
| 455 | 61433 | 32.2 | 585 | 173145 | 2.6 | 715 | 12398 | 0.0 | 845 | 3283 | 0.0 | 975 | 3810 | 0.0 |
| 460 | 43373 | 25.6 | 590 | 174675 | 1.7 | 720 | 11147 | 0.0 | 850 | 3055 | 0.0 | 980 | 4322 | 0.0 |
| 465 | 32472 | 21.2 | 595 | 173724 | 1.1 | 725 | 9761 | 0.0 | 855 | 2932 | 0.0 | 985 | 4200 | 0.0 |
| 470 | 24257 | 17.4 | 600 | 171241 | 0.7 | 730 | 8651 | 0.0 | 860 | 3382 | 0.0 | 990 | 4661 | 0.0 |
| 475 | 21690 | 16.6 | 605 | 165134 | 0.5 | 735 | 7730 | 0.0 | 865 | 2605 | 0.0 | 995 | 6746 | 0.0 |
| 480 | 23173 | 18.6 | 610 | 156652 | 0.3 | 740 | 6847 | 0.0 | 870 | 3325 | 0.0 | 1000 | 4150 | 0.0 |
| 485 | 27564 | 22.7 | 615 | 147879 | 0.2 | 745 | 6124 | 0.0 | 875 | 3325 | 0.0 | | | |

Summary

$R_f = 76.9$
 $R_g = 94.4$
 CIE $R_a = 73.1$
 $R_g = -34.6$



Color Vector Graphics



Individual Sample Fidelity Index ($R_{f,i}$)

| | | | |
|------------|------------|------------|------------|
| CES01 = 86 | CES26 = 68 | CES51 = 90 | CES76 = 63 |
| CES02 = 62 | CES27 = 88 | CES52 = 89 | CES77 = 80 |
| CES03 = 31 | CES28 = 87 | CES53 = 80 | CES78 = 65 |
| CES04 = 70 | CES29 = 67 | CES54 = 84 | CES79 = 87 |
| CES05 = 48 | CES30 = 74 | CES55 = 84 | CES80 = 86 |
| CES06 = 51 | CES31 = 71 | CES56 = 75 | CES81 = 75 |
| CES07 = 40 | CES32 = 67 | CES57 = 74 | CES82 = 94 |
| CES08 = 39 | CES33 = 74 | CES58 = 76 | CES83 = 91 |
| CES09 = 29 | CES34 = 78 | CES59 = 87 | CES84 = 89 |
| CES10 = 75 | CES35 = 89 | CES60 = 93 | CES85 = 80 |
| CES11 = 58 | CES36 = 98 | CES61 = 86 | CES86 = 66 |
| CES12 = 64 | CES37 = 86 | CES62 = 89 | CES87 = 79 |
| CES13 = 43 | CES38 = 82 | CES63 = 77 | CES88 = 79 |
| CES14 = 74 | CES39 = 95 | CES64 = 74 | CES89 = 70 |
| CES15 = 71 | CES40 = 91 | CES65 = 68 | CES90 = 77 |
| CES16 = 47 | CES41 = 89 | CES66 = 71 | CES91 = 88 |
| CES17 = 50 | CES42 = 88 | CES67 = 69 | CES92 = 60 |
| CES18 = 56 | CES43 = 82 | CES68 = 74 | CES93 = 77 |
| CES19 = 72 | CES44 = 99 | CES69 = 82 | CES94 = 52 |
| CES20 = 65 | CES45 = 87 | CES70 = 67 | CES95 = 69 |
| CES21 = 86 | CES46 = 82 | CES71 = 66 | CES96 = 78 |
| CES22 = 79 | CES47 = 82 | CES72 = 88 | CES97 = 85 |
| CES23 = 92 | CES48 = 72 | CES73 = 59 | CES98 = 76 |
| CES24 = 91 | CES49 = 82 | CES74 = 97 | CES99 = 63 |
| CES25 = 72 | CES50 = 88 | CES75 = 66 | |



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)