

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: McGRAW-EDISON

Report Number: P636713

Luminaire Tested: GWS-SA4B-735-U-SL3-W-GRSBK

Issue Date: 1/10/2023

Test Information

Test Method: LM-79-2019
Report Number: P636713
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2209-782-32)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/10/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: McGRAW-EDISON
Catalog Number: GWS-SA4B-735-U-SL3-W-GRSBK
Description: GALLEON WALL SLIM LUMINAIRE. (4) LIGHTSQUARES WITH 16 LEDS EACH AND TYPE III SPILL LIGHT ELIMINATOR OPTICS W/ FACTORY INSTALLED GLARE SHIELD, BK
Light Source: (64) 3500K CCT, 70 CRI LEDS
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8349.9 lumens
Efficiency: N/A
Efficacy: 88.5 lumens/watt
Luminous Opening: Rectangular (W 1' x L: 1' x H: 0')
IES Classification: Type II - Short
BUG Rating: B2 - U0 - G1


Input Watts (W): 94.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 0
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT



REPORT NUMBER: P636713
 CATALOG NUMBER: GWS-SA4B-735-U-SL3-W-GRSBK

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 10 foot mounting height. Maximum calculated value = 36.6 fc
 Type II - Short - N/A

REPORT NUMBER: P636713
CATALOG NUMBER: GWS-SA4B-735-U-SL3-W-GRSBK

Luminous Intensity Polar Plot



— Vertical Plane Through 53-Deg Lateral - - - Horizontal Cone Through 57.5-Deg Vertical

REPORT NUMBER: P636713
 CATALOG NUMBER: GWS-SA4B-735-U-SL3-W-GRSBK


FLUX DISTRIBUTION:

| | | Downward | Upward | Total |
|--------------------|-----------|----------|--------|--------|
| House Side | Lumens | 1379.3 | 0.0 | 1379.3 |
| | % Fixture | 16.5 | 0.0 | 16.5 |
| Street Side | Lumens | 6970.6 | 0.0 | 6970.6 |
| | % Fixture | 83.5 | 0.0 | 83.5 |
| Total | Lumens | 8349.9 | 0.0 | 8349.9 |
| | % Fixture | 100.0 | 0.0 | 100.0 |

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 313.4 | 3.8 |
| 10°-20° | 688.0 | 8.2 |
| 20°-30° | 896.3 | 10.7 |
| 30°-40° | 1300.0 | 15.6 |
| 40°-50° | 1875.9 | 22.5 |
| 50°-60° | 2268.7 | 27.2 |
| 60°-70° | 924.6 | 11.1 |
| 70°-80° | 83.1 | 1.0 |
| 80°-90° | 0.0 | 0.0 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-90° | 8349.9 | 100.0 |
| 0°-180° | 8349.9 | 100.0 |

Coefficient of Utilization



REPORT NUMBER: P636713


CATALOG NUMBER: GWS-SA4B-735-U-SL3-W-GRSBK

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

| Zone | Lumens | % Fixture | Zone Rating/Lumen Limit | | |
|----------------|--------|-----------|-------------------------|------|---------|
| | | | B | U | G |
| FL (0°-30°) | 1253.9 | 15.0 | | | |
| FM (30°-60°) | 4804.4 | 57.5 | | | |
| FH (60°-80°) | 912.4 | 10.9 | | | G1/1800 |
| FVH (80°-90°) | 0.0 | 0.0 | | | G0/10 |
| BL (0°-30°) | 643.7 | 7.7 | B2/1000 | | |
| BM (30°-60°) | 640.2 | 7.7 | B1/1000 | | |
| BH (60°-80°) | 95.3 | 1.1 | B0/110 | | G0/110 |
| BVH (80°-90°) | 0.0 | 0.0 | | | G0/10 |
| UL (90°-100°) | 0.0 | 0.0 | | U0/0 | |
| UH (100°-180°) | 0.0 | 0.0 | | U0/0 | |

BUG Rating: B2-U0-G1

Type II Short





REPORT NUMBER: P636713

CATALOG NUMBER: GWS-SA4B-735-U-SL3-W-GRSBK

CANDELA DISTRIBUTION (FULL):

| | 0° | 5° | 15° | 25° | 35° | 45° | 53° | 55° | 65° | 75° | 85° |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 3662.7 | 3662.7 | 3662.7 | 3662.7 | 3662.7 | 3662.7 | 3662.7 | 3662.7 | 3662.7 | 3662.7 | 3662.7 |
| 2.5° | 3611.6 | 3619.8 | 3634.1 | 3652.5 | 3664.8 | 3670.9 | 3670.9 | 3688.3 | 3677.1 | 3667.9 | 3657.6 |
| 5° | 3457.0 | 3465.2 | 3484.7 | 3514.3 | 3544.0 | 3565.5 | 3590.1 | 3608.5 | 3615.7 | 3615.7 | 3598.3 |
| 7.5° | 3239.1 | 3250.3 | 3262.6 | 3303.5 | 3368.0 | 3416.1 | 3458.1 | 3484.7 | 3523.6 | 3535.8 | 3511.3 |
| 10° | 3004.7 | 3016.0 | 3043.6 | 3099.9 | 3173.6 | 3245.2 | 3316.8 | 3350.6 | 3417.1 | 3451.9 | 3424.3 |
| 12.5° | 2806.2 | 2811.3 | 2848.1 | 2915.7 | 3009.8 | 3108.1 | 3195.0 | 3229.8 | 3324.0 | 3376.2 | 3343.4 |
| 15° | 2642.4 | 2645.5 | 2682.3 | 2757.0 | 2865.5 | 2986.3 | 3095.8 | 3131.6 | 3247.2 | 3326.0 | 3276.9 |
| 17.5° | 2518.6 | 2519.6 | 2551.3 | 2632.2 | 2745.8 | 2879.8 | 3009.8 | 3053.8 | 3203.2 | 3298.4 | 3224.7 |
| 20° | 2456.2 | 2453.1 | 2475.6 | 2546.2 | 2653.7 | 2787.7 | 2941.2 | 2995.5 | 3178.7 | 3294.3 | 3184.8 |
| 22.5° | 2457.2 | 2450.0 | 2459.2 | 2509.4 | 2600.5 | 2726.3 | 2898.3 | 2959.7 | 3180.7 | 3311.7 | 3151.0 |
| 25° | 2515.5 | 2505.3 | 2507.3 | 2533.9 | 2598.4 | 2713.0 | 2904.4 | 2969.9 | 3221.7 | 3370.1 | 3138.8 |
| 27.5° | 2613.8 | 2602.5 | 2602.5 | 2615.8 | 2650.6 | 2755.0 | 2981.2 | 3055.9 | 3331.2 | 3483.6 | 3164.3 |
| 30° | 2740.7 | 2729.4 | 2725.3 | 2738.6 | 2767.3 | 2863.5 | 3152.1 | 3229.8 | 3518.4 | 3669.9 | 3246.2 |
| 32.5° | 2886.0 | 2872.7 | 2879.8 | 2898.3 | 2925.9 | 3058.9 | 3372.1 | 3475.5 | 3752.8 | 3920.6 | 3393.6 |
| 35° | 3039.5 | 3028.2 | 3061.0 | 3100.9 | 3143.9 | 3330.1 | 3676.0 | 3766.1 | 4040.4 | 4232.8 | 3618.7 |
| 37.5° | 3185.8 | 3180.7 | 3249.3 | 3333.2 | 3422.2 | 3655.6 | 3985.1 | 4054.7 | 4287.0 | 4572.5 | 3894.0 |
| 40° | 3332.2 | 3331.2 | 3448.9 | 3596.2 | 3738.5 | 3980.0 | 4219.5 | 4276.8 | 4437.5 | 4836.6 | 4158.1 |
| 42.5° | 3495.9 | 3495.9 | 3658.6 | 3855.1 | 4044.5 | 4254.3 | 4391.4 | 4417.0 | 4505.0 | 4989.1 | 4356.6 |
| 45° | 3652.5 | 3661.7 | 3850.0 | 4078.2 | 4302.4 | 4468.2 | 4510.1 | 4512.2 | 4532.6 | 5079.1 | 4521.4 |
| 47.5° | 3776.3 | 3784.5 | 4009.7 | 4272.7 | 4514.2 | 4630.9 | 4637.0 | 4627.8 | 4605.3 | 5165.1 | 4648.3 |
| 50° | 3876.6 | 3888.9 | 4124.3 | 4402.7 | 4659.5 | 4787.5 | 4834.5 | 4825.3 | 4768.0 | 5257.2 | 4737.3 |
| 52.5° | 3925.8 | 3943.2 | 4164.2 | 4467.1 | 4821.2 | 5055.6 | 5186.6 | 5208.1 | 5011.6 | 5308.4 | 4822.3 |
| 55° | 3532.8 | 3558.4 | 3762.0 | 4176.5 | 4911.3 | 5470.1 | 5675.8 | 5671.7 | 5275.6 | 5460.9 | 5029.0 |
| 57.5° | 2668.0 | 2666.0 | 2834.8 | 3288.2 | 4194.9 | 5493.6 | 5976.6 | 5968.5 | 5522.3 | 5637.9 | 5240.8 |
| 60° | 1816.5 | 1804.3 | 1849.3 | 2068.3 | 2933.1 | 4475.3 | 5439.4 | 5549.9 | 5347.3 | 5208.1 | 4449.7 |
| 62.5° | 1495.2 | 1483.9 | 1469.6 | 1409.2 | 1684.5 | 2787.7 | 3757.9 | 3925.8 | 3899.1 | 3619.8 | 2790.8 |
| 65° | 1224.0 | 1233.2 | 1273.1 | 1247.5 | 1171.8 | 1429.7 | 1950.6 | 2049.9 | 1873.8 | 1577.1 | 975.3 |
| 67.5° | 902.6 | 906.7 | 958.9 | 1094.0 | 1053.1 | 951.8 | 918.0 | 934.4 | 547.5 | 251.8 | 162.7 |
| 70° | 533.2 | 536.3 | 584.4 | 765.5 | 854.5 | 730.7 | 620.2 | 611.0 | 217.0 | 67.5 | 73.7 |
| 72.5° | 301.9 | 295.8 | 305.0 | 364.3 | 465.6 | 387.9 | 319.3 | 290.6 | 65.5 | 37.9 | 37.9 |
| 75° | 143.3 | 139.2 | 119.7 | 112.6 | 102.3 | 65.5 | 40.9 | 34.8 | 16.4 | 15.4 | 15.4 |
| 77.5° | 1.0 | 3.1 | 2.0 | 3.1 | 3.1 | 2.0 | 1.0 | 1.0 | 3.1 | 3.1 | 4.1 |
| 80° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 82.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 85° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 87.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P636713
 CATALOG NUMBER: GWS-SA4B-735-U-SL3-W-GRSBK

CANDELA DISTRIBUTION (continued):

| | 90° | 95° | 105° | 115° | 125° | 135° | 145° | 155° | 165° | 175° | 180° |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 3662.7 | 3662.7 | 3662.7 | 3662.7 | 3662.7 | 3662.7 | 3662.7 | 3662.7 | 3662.7 | 3662.7 | 3662.7 |
| 2.5° | 3639.2 | 3608.5 | 3601.3 | 3599.3 | 3570.6 | 3539.9 | 3508.2 | 3495.9 | 3477.5 | 3466.2 | 3475.5 |
| 5° | 3570.6 | 3526.6 | 3487.7 | 3451.9 | 3388.5 | 3318.9 | 3258.5 | 3219.6 | 3182.8 | 3158.2 | 3164.3 |
| 7.5° | 3473.4 | 3416.1 | 3327.1 | 3236.0 | 3119.3 | 3014.9 | 2898.3 | 2826.6 | 2760.1 | 2723.3 | 2740.7 |
| 10° | 3370.1 | 3294.3 | 3152.1 | 2997.5 | 2814.3 | 2650.6 | 2483.8 | 2347.7 | 2268.9 | 2194.2 | 2202.4 |
| 12.5° | 3268.7 | 3168.4 | 2955.6 | 2721.2 | 2489.9 | 2248.4 | 1996.6 | 1808.3 | 1679.4 | 1586.3 | 1571.9 |
| 15° | 3174.6 | 3045.6 | 2764.2 | 2455.1 | 2139.9 | 1818.6 | 1497.2 | 1228.1 | 1078.7 | 986.6 | 980.4 |
| 17.5° | 3090.7 | 2931.0 | 2565.7 | 2176.8 | 1781.7 | 1370.3 | 1000.9 | 799.3 | 713.3 | 673.4 | 669.3 |
| 20° | 3009.8 | 2815.4 | 2363.0 | 1894.3 | 1390.8 | 962.0 | 690.8 | 597.7 | 570.0 | 553.7 | 555.7 |
| 22.5° | 2932.0 | 2689.5 | 2150.2 | 1581.2 | 1042.8 | 675.4 | 535.2 | 499.4 | 496.3 | 498.4 | 499.4 |
| 25° | 2866.5 | 2573.8 | 1931.2 | 1279.2 | 744.0 | 514.8 | 447.2 | 437.0 | 446.2 | 459.5 | 461.6 |
| 27.5° | 2832.8 | 2479.7 | 1717.3 | 975.3 | 538.3 | 418.6 | 387.9 | 392.0 | 408.3 | 422.7 | 424.7 |
| 30° | 2842.0 | 2409.1 | 1496.2 | 707.2 | 414.5 | 353.1 | 342.8 | 351.0 | 367.4 | 380.7 | 382.8 |
| 32.5° | 2907.5 | 2373.3 | 1270.0 | 514.8 | 340.8 | 308.0 | 303.9 | 310.1 | 324.4 | 334.7 | 335.7 |
| 35° | 3037.4 | 2381.4 | 1055.1 | 394.0 | 292.7 | 274.3 | 273.2 | 277.3 | 284.5 | 291.7 | 292.7 |
| 37.5° | 3228.8 | 2448.0 | 843.3 | 327.5 | 265.1 | 251.8 | 247.7 | 247.7 | 252.8 | 255.8 | 257.9 |
| 40° | 3434.5 | 2548.3 | 675.4 | 289.6 | 245.6 | 231.3 | 223.1 | 220.0 | 224.1 | 228.2 | 229.2 |
| 42.5° | 3604.4 | 2648.6 | 548.5 | 263.0 | 230.3 | 210.8 | 200.6 | 198.5 | 203.7 | 210.8 | 212.9 |
| 45° | 3734.4 | 2726.3 | 457.5 | 241.5 | 212.9 | 191.4 | 180.1 | 180.1 | 189.3 | 201.6 | 203.7 |
| 47.5° | 3853.1 | 2788.8 | 389.9 | 222.1 | 196.5 | 174.0 | 162.7 | 164.8 | 180.1 | 196.5 | 199.6 |
| 50° | 3933.9 | 2838.9 | 339.8 | 204.7 | 183.2 | 159.7 | 149.4 | 153.5 | 171.9 | 191.4 | 194.4 |
| 52.5° | 4020.9 | 2900.3 | 307.0 | 189.3 | 170.9 | 148.4 | 139.2 | 142.3 | 162.7 | 184.2 | 188.3 |
| 55° | 4261.4 | 3106.0 | 306.0 | 168.9 | 149.4 | 133.0 | 128.9 | 130.0 | 150.4 | 175.0 | 180.1 |
| 57.5° | 4457.9 | 3287.2 | 326.5 | 142.3 | 124.9 | 116.7 | 114.6 | 115.6 | 134.1 | 161.7 | 167.8 |
| 60° | 3688.3 | 2554.4 | 270.2 | 117.7 | 104.4 | 102.3 | 99.3 | 101.3 | 118.7 | 143.3 | 148.4 |
| 62.5° | 2182.9 | 1460.4 | 128.9 | 90.1 | 89.0 | 87.0 | 83.9 | 88.0 | 104.4 | 125.9 | 128.9 |
| 65° | 746.1 | 432.9 | 81.9 | 73.7 | 75.7 | 72.7 | 69.6 | 73.7 | 88.0 | 100.3 | 101.3 |
| 67.5° | 143.3 | 114.6 | 65.5 | 61.4 | 62.4 | 56.3 | 55.3 | 59.4 | 67.5 | 69.6 | 68.6 |
| 70° | 74.7 | 66.5 | 50.1 | 50.1 | 48.1 | 39.9 | 39.9 | 44.0 | 44.0 | 40.9 | 39.9 |
| 72.5° | 38.9 | 36.8 | 32.7 | 36.8 | 30.7 | 24.6 | 24.6 | 26.6 | 24.6 | 20.5 | 20.5 |
| 75° | 15.4 | 15.4 | 14.3 | 18.4 | 13.3 | 11.3 | 10.2 | 12.3 | 9.2 | 7.2 | 7.2 |
| 77.5° | 4.1 | 4.1 | 4.1 | 5.1 | 3.1 | 3.1 | 2.0 | 2.0 | 1.0 | 0.0 | 0.0 |
| 80° | 0.0 | 1.0 | 0.0 | 1.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 82.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 85° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 87.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |

LM-79-08: Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Report Prepared for

Cooper Lighting Solutions

All Brands

Data applicable to all product families using SA light engines

Report Number: SP1-2101-121-7

Luminaire Tested: IFLD-S-SA2A-735-U-T2

Test Date: 03/04/2021

Test Information

Test Method: LM-79-08
 Report Number: SP1-2101-121-7
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1
 Measurement Geometry: 4π
 Issue Date: 03/04/2021
 Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
 Product Line: STREETWORKS
 Catalog Number: **IFLD-S-SA2A-735-U-T2**
 Description: STREETWORKS INF FLOOD

PROGRAMMED @ 615mA.

Spectral Parameters

CCT (K): 3388
 CIE u': 0.2371
 CIE v': 0.5177
 Duv: 0.0032
 CIE x: 0.4153
 CIE y: 0.4030
 CIE z: 0.1817
 Peak Wavelength (nm): 590
 Dominant Wavelength (nm): 580
 Purity: 45.7

 Rf: 76.9
 Rg: 94.4

| | | | |
|-----------|------|------|-------|
| CRI (Ra): | 73.1 | | |
| R1: | 68.9 | R9: | -34.6 |
| R2: | 81.1 | R10: | 57.8 |
| R3: | 93.1 | R11: | 68.6 |
| R4: | 71.6 | R12: | 53.9 |
| R5: | 69.4 | R13: | 70.9 |
| R6: | 75.0 | R14: | 96.2 |
| R7: | 79.5 | | |
| R8: | 46.4 | | |

Test Conditions

Stabilization Time: 81M
 Operation Time: 12H
 Room Temperature (°C) / RH%: 25.0/30%
 Sphere Temperature (°C): 24.1



REPORT NUMBER: SP1-2101-121-7

| Measurement and Test Equipment | | | |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument | Identification Number | Calibration Date | Calibration Due Date |
| Photometer | IN0058 | 1/31/2021 | 7/31/2021 |
| Power Meter | IN0071 | 12/1/2020 | 12/1/2021 |
| AC Power Source | IN0063 | 12/1/2020 | 12/1/2021 |
| DC Power Source | IN0208 | 12/1/2020 | 12/1/2021 |
| Sphere Thermometer | IN0085 | 12/1/2020 | 12/1/2021 |
| Room Thermometer | IN0046 | 12/1/2020 | 12/1/2021 |

REPORT NUMBER: SP1-2101-121-7

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 3500K 4-step quadrangle

REPORT NUMBER: SP1-2101-121-7

Photopic Flux vs. Wavelength




#####

| λ (nm) | Power (µW/nm) | Lumens (Φ/nm) | λ (nm) | Power (µW/nm) | Lumens (Φ/nm) | λ (nm) | Power (µW/nm) | Lumens (Φ/nm) | λ (nm) | Power (µW/nm) | Lumens (Φ/nm) | λ (nm) | Power (µW/nm) | Lumens (Φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 2672 | 0.0 | 490 | 34553 | 4.9 | 620 | 136720 | 35.6 | 750 | 5870 | 0.0 | 880 | 4216 | 0.0 |
| 365 | 2252 | 0.0 | 495 | 44336 | 8.0 | 625 | 126308 | 27.9 | 755 | 5421 | 0.0 | 885 | 4132 | 0.0 |
| 370 | 2217 | 0.0 | 500 | 54643 | 12.1 | 630 | 114625 | 20.7 | 760 | 5097 | 0.0 | 890 | 3992 | 0.0 |
| 375 | 2697 | 0.0 | 505 | 64676 | 18.1 | 635 | 103216 | 15.5 | 765 | 4626 | 0.0 | 895 | 3214 | 0.0 |
| 380 | 3039 | 0.0 | 510 | 73825 | 25.4 | 640 | 92605 | 11.1 | 770 | 3782 | 0.0 | 900 | 2580 | 0.0 |
| 385 | 2655 | 0.0 | 515 | 81872 | 33.9 | 645 | 83234 | 8.0 | 775 | 3506 | 0.0 | 905 | 1776 | 0.0 |
| 390 | 2357 | 0.0 | 520 | 88574 | 43.0 | 650 | 73263 | 5.4 | 780 | 3507 | 0.0 | 910 | 3995 | 0.0 |
| 395 | 2186 | 0.0 | 525 | 93289 | 50.1 | 655 | 64627 | 3.7 | 785 | 3267 | 0.0 | 915 | 4288 | 0.0 |
| 400 | 2015 | 0.0 | 530 | 98393 | 57.9 | 660 | 56614 | 2.4 | 790 | 2849 | 0.0 | 920 | 2446 | 0.0 |
| 405 | 2234 | 0.0 | 535 | 103269 | 64.0 | 665 | 49537 | 1.6 | 795 | 3037 | 0.0 | 925 | 3009 | 0.0 |
| 410 | 3412 | 0.0 | 540 | 107316 | 69.9 | 670 | 42866 | 0.9 | 800 | 2716 | 0.0 | 930 | 3026 | 0.0 |
| 415 | 6135 | 0.0 | 545 | 113101 | 75.3 | 675 | 36708 | 0.6 | 805 | 2648 | 0.0 | 935 | 4734 | 0.0 |
| 420 | 12146 | 0.0 | 550 | 120690 | 82.0 | 680 | 31814 | 0.4 | 810 | 3187 | 0.0 | 940 | 3719 | 0.0 |
| 425 | 23983 | 0.1 | 555 | 128583 | 87.8 | 685 | 27485 | 0.2 | 815 | 2931 | 0.0 | 945 | 1480 | 0.0 |
| 430 | 42142 | 0.3 | 560 | 137796 | 93.6 | 690 | 23698 | 0.1 | 820 | 2717 | 0.0 | 950 | 3450 | 0.0 |
| 435 | 68228 | 0.8 | 565 | 146577 | 97.5 | 695 | 20309 | 0.1 | 825 | 2236 | 0.0 | 955 | 5051 | 0.0 |
| 440 | 99323 | 1.6 | 570 | 154581 | 100.5 | 700 | 17890 | 0.1 | 830 | 2628 | 0.0 | 960 | 3176 | 0.0 |
| 445 | 115584 | 2.4 | 575 | 162633 | 101.2 | 705 | 15500 | 0.0 | 835 | 3140 | 0.0 | 965 | 5178 | 0.0 |
| 450 | 94997 | 2.5 | 580 | 168101 | 99.9 | 710 | 13699 | 0.0 | 840 | 3675 | 0.0 | 970 | 6385 | 0.0 |
| 455 | 61433 | 2.1 | 585 | 173145 | 96.2 | 715 | 12398 | 0.0 | 845 | 3283 | 0.0 | 975 | 3810 | 0.0 |
| 460 | 43373 | 1.8 | 590 | 174675 | 90.3 | 720 | 11147 | 0.0 | 850 | 3055 | 0.0 | 980 | 4322 | 0.0 |
| 465 | 32472 | 1.7 | 595 | 173724 | 82.3 | 725 | 9761 | 0.0 | 855 | 2932 | 0.0 | 985 | 4200 | 0.0 |
| 470 | 24257 | 1.5 | 600 | 171241 | 73.8 | 730 | 8651 | 0.0 | 860 | 3382 | 0.0 | 990 | 4661 | 0.0 |
| 475 | 21690 | 1.7 | 605 | 165134 | 64.0 | 735 | 7730 | 0.0 | 865 | 2605 | 0.0 | 995 | 6746 | 0.0 |
| 480 | 23173 | 2.2 | 610 | 156652 | 53.8 | 740 | 6847 | 0.0 | 870 | 3325 | 0.0 | 1000 | 4150 | 0.0 |
| 485 | 27564 | 3.3 | 615 | 147879 | 44.6 | 745 | 6124 | 0.0 | 875 | 3325 | 0.0 | | | |

REPORT NUMBER: SP1-2101-121-7

Scotopic Flux vs. Wavelength



Scotopic Lumens: 12126

S/P: 1.36

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 2672 | 0.0 | 490 | 34553 | 53.2 | 620 | 136720 | 1.7 | 750 | 5870 | 0.0 | 880 | 4216 | 0.0 |
| 365 | 2252 | 0.0 | 495 | 44336 | 71.7 | 625 | 126308 | 1.1 | 755 | 5421 | 0.0 | 885 | 4132 | 0.0 |
| 370 | 2217 | 0.0 | 500 | 54643 | 91.4 | 630 | 114625 | 0.6 | 760 | 5097 | 0.0 | 890 | 3992 | 0.0 |
| 375 | 2697 | 0.0 | 505 | 64676 | 110.0 | 635 | 103216 | 0.4 | 765 | 4626 | 0.0 | 895 | 3214 | 0.0 |
| 380 | 3039 | 0.0 | 510 | 73825 | 125.1 | 640 | 92605 | 0.2 | 770 | 3782 | 0.0 | 900 | 2580 | 0.0 |
| 385 | 2655 | 0.0 | 515 | 81872 | 135.7 | 645 | 83234 | 0.1 | 775 | 3506 | 0.0 | 905 | 1776 | 0.0 |
| 390 | 2357 | 0.0 | 520 | 88574 | 140.8 | 650 | 73263 | 0.1 | 780 | 3507 | 0.0 | 910 | 3995 | 0.0 |
| 395 | 2186 | 0.0 | 525 | 93289 | 139.6 | 655 | 64627 | 0.1 | 785 | 3267 | 0.0 | 915 | 4288 | 0.0 |
| 400 | 2015 | 0.0 | 530 | 98393 | 135.7 | 660 | 56614 | 0.0 | 790 | 2849 | 0.0 | 920 | 2446 | 0.0 |
| 405 | 2234 | 0.1 | 535 | 103269 | 128.7 | 665 | 49537 | 0.0 | 795 | 3037 | 0.0 | 925 | 3009 | 0.0 |
| 410 | 3412 | 0.2 | 540 | 107316 | 118.6 | 670 | 42866 | 0.0 | 800 | 2716 | 0.0 | 930 | 3026 | 0.0 |
| 415 | 6135 | 0.6 | 545 | 113101 | 108.4 | 675 | 36708 | 0.0 | 805 | 2648 | 0.0 | 935 | 4734 | 0.0 |
| 420 | 12146 | 2.0 | 550 | 120690 | 98.7 | 680 | 31814 | 0.0 | 810 | 3187 | 0.0 | 940 | 3719 | 0.0 |
| 425 | 23983 | 5.9 | 555 | 128583 | 87.9 | 685 | 27485 | 0.0 | 815 | 2931 | 0.0 | 945 | 1480 | 0.0 |
| 430 | 42142 | 14.3 | 560 | 137796 | 77.0 | 690 | 23698 | 0.0 | 820 | 2717 | 0.0 | 950 | 3450 | 0.0 |
| 435 | 68228 | 30.5 | 565 | 146577 | 65.8 | 695 | 20309 | 0.0 | 825 | 2236 | 0.0 | 955 | 5051 | 0.0 |
| 440 | 99323 | 55.5 | 570 | 154581 | 54.6 | 700 | 17890 | 0.0 | 830 | 2628 | 0.0 | 960 | 3176 | 0.0 |
| 445 | 115584 | 77.4 | 575 | 162633 | 44.3 | 705 | 15500 | 0.0 | 835 | 3140 | 0.0 | 965 | 5178 | 0.0 |
| 450 | 94997 | 73.6 | 580 | 168101 | 34.6 | 710 | 13699 | 0.0 | 840 | 3675 | 0.0 | 970 | 6385 | 0.0 |
| 455 | 61433 | 53.7 | 585 | 173145 | 26.5 | 715 | 12398 | 0.0 | 845 | 3283 | 0.0 | 975 | 3810 | 0.0 |
| 460 | 43373 | 41.9 | 590 | 174675 | 19.5 | 720 | 11147 | 0.0 | 850 | 3055 | 0.0 | 980 | 4322 | 0.0 |
| 465 | 32472 | 34.3 | 595 | 173724 | 13.9 | 725 | 9761 | 0.0 | 855 | 2932 | 0.0 | 985 | 4200 | 0.0 |
| 470 | 24257 | 27.9 | 600 | 171241 | 9.7 | 730 | 8651 | 0.0 | 860 | 3382 | 0.0 | 990 | 4661 | 0.0 |
| 475 | 21690 | 27.1 | 605 | 165134 | 6.5 | 735 | 7730 | 0.0 | 865 | 2605 | 0.0 | 995 | 6746 | 0.0 |
| 480 | 23173 | 31.3 | 610 | 156652 | 4.2 | 740 | 6847 | 0.0 | 870 | 3325 | 0.0 | 1000 | 4150 | 0.0 |
| 485 | 27564 | 40.0 | 615 | 147879 | 2.7 | 745 | 6124 | 0.0 | 875 | 3325 | 0.0 | | | |

REPORT NUMBER: SP1-2101-121-7

Melanopic Flux vs. Wavelength



Melanopic Lumens: 4490.7 M/P: 0.5

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 2672 | 0.0 | 490 | 34553 | 28.8 | 620 | 136720 | 0.1 | 750 | 5870 | 0.0 | 880 | 4216 | 0.0 |
| 365 | 2252 | 0.0 | 495 | 44336 | 36.6 | 625 | 126308 | 0.1 | 755 | 5421 | 0.0 | 885 | 4132 | 0.0 |
| 370 | 2217 | 0.0 | 500 | 54643 | 43.9 | 630 | 114625 | 0.0 | 760 | 5097 | 0.0 | 890 | 3992 | 0.0 |
| 375 | 2697 | 0.0 | 505 | 64676 | 49.6 | 635 | 103216 | 0.0 | 765 | 4626 | 0.0 | 895 | 3214 | 0.0 |
| 380 | 3039 | 0.0 | 510 | 73825 | 53.0 | 640 | 92605 | 0.0 | 770 | 3782 | 0.0 | 900 | 2580 | 0.0 |
| 385 | 2655 | 0.0 | 515 | 81872 | 53.5 | 645 | 83234 | 0.0 | 775 | 3506 | 0.0 | 905 | 1776 | 0.0 |
| 390 | 2357 | 0.0 | 520 | 88574 | 51.6 | 650 | 73263 | 0.0 | 780 | 3507 | 0.0 | 910 | 3995 | 0.0 |
| 395 | 2186 | 0.0 | 525 | 93289 | 47.3 | 655 | 64627 | 0.0 | 785 | 3267 | 0.0 | 915 | 4288 | 0.0 |
| 400 | 2015 | 0.0 | 530 | 98393 | 42.5 | 660 | 56614 | 0.0 | 790 | 2849 | 0.0 | 920 | 2446 | 0.0 |
| 405 | 2234 | 0.0 | 535 | 103269 | 37.2 | 665 | 49537 | 0.0 | 795 | 3037 | 0.0 | 925 | 3009 | 0.0 |
| 410 | 3412 | 0.1 | 540 | 107316 | 31.4 | 670 | 42866 | 0.0 | 800 | 2716 | 0.0 | 930 | 3026 | 0.0 |
| 415 | 6135 | 0.4 | 545 | 113101 | 26.3 | 675 | 36708 | 0.0 | 805 | 2648 | 0.0 | 935 | 4734 | 0.0 |
| 420 | 12146 | 1.4 | 550 | 120690 | 21.7 | 680 | 31814 | 0.0 | 810 | 3187 | 0.0 | 940 | 3719 | 0.0 |
| 425 | 23983 | 3.7 | 555 | 128583 | 17.3 | 685 | 27485 | 0.0 | 815 | 2931 | 0.0 | 945 | 1480 | 0.0 |
| 430 | 42142 | 8.9 | 560 | 137796 | 13.6 | 690 | 23698 | 0.0 | 820 | 2717 | 0.0 | 950 | 3450 | 0.0 |
| 435 | 68228 | 18.2 | 565 | 146577 | 10.3 | 695 | 20309 | 0.0 | 825 | 2236 | 0.0 | 955 | 5051 | 0.0 |
| 440 | 99323 | 33.2 | 570 | 154581 | 7.6 | 700 | 17890 | 0.0 | 830 | 2628 | 0.0 | 960 | 3176 | 0.0 |
| 445 | 115584 | 45.6 | 575 | 162633 | 5.4 | 705 | 15500 | 0.0 | 835 | 3140 | 0.0 | 965 | 5178 | 0.0 |
| 450 | 94997 | 43.8 | 580 | 168101 | 3.8 | 710 | 13699 | 0.0 | 840 | 3675 | 0.0 | 970 | 6385 | 0.0 |
| 455 | 61433 | 32.2 | 585 | 173145 | 2.6 | 715 | 12398 | 0.0 | 845 | 3283 | 0.0 | 975 | 3810 | 0.0 |
| 460 | 43373 | 25.6 | 590 | 174675 | 1.7 | 720 | 11147 | 0.0 | 850 | 3055 | 0.0 | 980 | 4322 | 0.0 |
| 465 | 32472 | 21.2 | 595 | 173724 | 1.1 | 725 | 9761 | 0.0 | 855 | 2932 | 0.0 | 985 | 4200 | 0.0 |
| 470 | 24257 | 17.4 | 600 | 171241 | 0.7 | 730 | 8651 | 0.0 | 860 | 3382 | 0.0 | 990 | 4661 | 0.0 |
| 475 | 21690 | 16.6 | 605 | 165134 | 0.5 | 735 | 7730 | 0.0 | 865 | 2605 | 0.0 | 995 | 6746 | 0.0 |
| 480 | 23173 | 18.6 | 610 | 156652 | 0.3 | 740 | 6847 | 0.0 | 870 | 3325 | 0.0 | 1000 | 4150 | 0.0 |
| 485 | 27564 | 22.7 | 615 | 147879 | 0.2 | 745 | 6124 | 0.0 | 875 | 3325 | 0.0 | | | |

Summary

$R_f = 76.9$
 $R_g = 94.4$
 CIE $R_a = 73.1$
 $R_g = -34.6$



Color Vector Graphics



Individual Sample Fidelity Index ($R_{f,i}$)

| | | | |
|------------|------------|------------|------------|
| CES01 = 86 | CES26 = 68 | CES51 = 90 | CES76 = 63 |
| CES02 = 62 | CES27 = 88 | CES52 = 89 | CES77 = 80 |
| CES03 = 31 | CES28 = 87 | CES53 = 80 | CES78 = 65 |
| CES04 = 70 | CES29 = 67 | CES54 = 84 | CES79 = 87 |
| CES05 = 48 | CES30 = 74 | CES55 = 84 | CES80 = 86 |
| CES06 = 51 | CES31 = 71 | CES56 = 75 | CES81 = 75 |
| CES07 = 40 | CES32 = 67 | CES57 = 74 | CES82 = 94 |
| CES08 = 39 | CES33 = 74 | CES58 = 76 | CES83 = 91 |
| CES09 = 29 | CES34 = 78 | CES59 = 87 | CES84 = 89 |
| CES10 = 75 | CES35 = 89 | CES60 = 93 | CES85 = 80 |
| CES11 = 58 | CES36 = 98 | CES61 = 86 | CES86 = 66 |
| CES12 = 64 | CES37 = 86 | CES62 = 89 | CES87 = 79 |
| CES13 = 43 | CES38 = 82 | CES63 = 77 | CES88 = 79 |
| CES14 = 74 | CES39 = 95 | CES64 = 74 | CES89 = 70 |
| CES15 = 71 | CES40 = 91 | CES65 = 68 | CES90 = 77 |
| CES16 = 47 | CES41 = 89 | CES66 = 71 | CES91 = 88 |
| CES17 = 50 | CES42 = 88 | CES67 = 69 | CES92 = 60 |
| CES18 = 56 | CES43 = 82 | CES68 = 74 | CES93 = 77 |
| CES19 = 72 | CES44 = 99 | CES69 = 82 | CES94 = 52 |
| CES20 = 65 | CES45 = 87 | CES70 = 67 | CES95 = 69 |
| CES21 = 86 | CES46 = 82 | CES71 = 66 | CES96 = 78 |
| CES22 = 79 | CES47 = 82 | CES72 = 88 | CES97 = 85 |
| CES23 = 92 | CES48 = 72 | CES73 = 59 | CES98 = 76 |
| CES24 = 91 | CES49 = 82 | CES74 = 97 | CES99 = 63 |
| CES25 = 72 | CES50 = 88 | CES75 = 66 | |



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)