

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: McGRAW-EDISON

Report Number: P634739

Luminaire Tested: GWS-SA3C-735-U-SLL-W-GRSBK

Issue Date: 1/10/2023

**Test Information**

Test Method: LM-79-2019  
Report Number: P634739  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2209-782-38)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 1/10/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: McGRAW-EDISON  
Catalog Number: GWS-SA3C-735-U-SLL-W-GRSBK  
Description: GALLEON WALL SLIM LUMINAIRE. (3) LIGHTSQUARES WITH 16 LEDS EACH AND SPILL LIGHT ELIMINATOR LEFT OPTICS W/ FACTORY INSTALLED GLARE SHIELD, BK  
Light Source: (48) 3500K CCT, 70 CRI LEDS  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 7377.5 lumens  
Efficiency: N/A  
Efficacy: 79.3 lumens/watt  
Luminous Opening: Rectangular (W 1.5' x L: 0.5' x H: 0')  
IES Classification: Type III - Short  
BUG Rating: B2 - U0 - G1  
  
Input Watts (W): 93  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 0  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 28.75 FT



REPORT NUMBER: P634739  
 CATALOG NUMBER: GWS-SA3C-735-U-SLL-W-GRSBK

### Iso-Footcandle Lines of Horizontal Illumination


× Max cd  
 - - - 1/2 Max cd



Based on 10 foot mounting height. Maximum calculated value = 19.7 fc  
 Type III - Short - N/A

REPORT NUMBER: P634739  
CATALOG NUMBER: GWS-SA3C-735-U-SLL-W-GRSBK

### Luminous Intensity Polar Plot



— Vertical Plane Through 315-Deg Lateral    - - - Horizontal Cone Through 57.5-Deg Vertical

REPORT NUMBER: P634739

CATALOG NUMBER: GWS-SA3C-735-U-SLL-W-GRSBK


**FLUX DISTRIBUTION:**

|                    |           | Downward | Upward | Total  |
|--------------------|-----------|----------|--------|--------|
| <b>House Side</b>  | Lumens    | 1589.4   | 0.0    | 1589.4 |
|                    | % Fixture | 21.5     | 0.0    | 21.5   |
| <b>Street Side</b> | Lumens    | 5788.1   | 0.0    | 5788.1 |
|                    | % Fixture | 78.5     | 0.0    | 78.5   |
| <b>Total</b>       | Lumens    | 7377.5   | 0.0    | 7377.5 |
|                    | % Fixture | 100.0    | 0.0    | 100.0  |

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 123.9  | 1.7       |
| 10°-20°   | 407.7  | 5.5       |
| 20°-30°   | 661.6  | 9.0       |
| 30°-40°   | 1015.4 | 13.8      |
| 40°-50°   | 1621.7 | 22.0      |
| 50°-60°   | 2270.7 | 30.8      |
| 60°-70°   | 1164.3 | 15.8      |
| 70°-80°   | 112.1  | 1.5       |
| 80°-90°   | 0.0    | 0.0       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-90°    | 7377.5 | 100.0     |
| 0°-180°   | 7377.5 | 100.0     |

**Coefficient of Utilization**



REPORT NUMBER: P634739


CATALOG NUMBER: GWS-SA3C-735-U-SLL-W-GRSBK

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

| Zone           | Lumens | % Fixture | Zone Rating/Lumen Limit |      |         |
|----------------|--------|-----------|-------------------------|------|---------|
|                |        |           | B                       | U    | G       |
| FL (0°-30°)    | 730.4  | 9.9       |                         |      |         |
| FM (30°-60°)   | 3901.4 | 52.9      |                         |      |         |
| FH (60°-80°)   | 1156.3 | 15.7      |                         |      | G1/1800 |
| FVH (80°-90°)  | 0.0    | 0.0       |                         |      | G0/10   |
| BL (0°-30°)    | 462.8  | 6.3       | B1/500                  |      |         |
| BM (30°-60°)   | 1006.5 | 13.6      | B2/2500                 |      |         |
| BH (60°-80°)   | 120.0  | 1.6       | B1/500                  |      | G1/500  |
| BVH (80°-90°)  | 0.0    | 0.0       |                         |      | G0/10   |
| UL (90°-100°)  | 0.0    | 0.0       |                         | U0/0 |         |
| UH (100°-180°) | 0.0    | 0.0       |                         | U0/0 |         |

**BUG Rating: B2-U0-G1**

Type III Short





REPORT NUMBER: P634739  
 CATALOG NUMBER: GWS-SA3C-735-U-SLL-W-GRSBK

**CANDELA DISTRIBUTION (FULL):**

|       | 0°     | 1°     | 5°     | 15°    | 25°    | 35°    | 45°    | 55°    | 65°    | 75°    | 85°    |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°    | 1253.5 | 1253.5 | 1253.5 | 1253.5 | 1253.5 | 1253.5 | 1253.5 | 1253.5 | 1253.5 | 1253.5 | 1253.5 |
| 2.5°  | 1392.6 | 1389.7 | 1379.8 | 1346.3 | 1325.5 | 1293.0 | 1269.3 | 1238.8 | 1205.2 | 1184.5 | 1163.8 |
| 5°    | 1540.6 | 1532.7 | 1506.0 | 1429.1 | 1369.9 | 1305.8 | 1254.5 | 1198.3 | 1138.2 | 1098.7 | 1062.2 |
| 7.5°  | 1682.6 | 1670.7 | 1635.2 | 1505.0 | 1415.3 | 1323.6 | 1250.6 | 1168.7 | 1083.9 | 1024.7 | 979.4  |
| 10°   | 1821.6 | 1795.0 | 1738.8 | 1579.0 | 1457.7 | 1347.2 | 1261.4 | 1167.7 | 1068.1 | 993.2  | 942.9  |
| 12.5° | 1936.0 | 1916.3 | 1839.4 | 1649.0 | 1493.2 | 1352.2 | 1246.6 | 1159.9 | 1092.8 | 1042.5 | 996.1  |
| 15°   | 2034.7 | 2013.0 | 1940.0 | 1712.2 | 1523.8 | 1332.4 | 1184.5 | 1108.6 | 1119.4 | 1139.1 | 1099.7 |
| 17.5° | 2125.4 | 2102.7 | 2023.8 | 1764.4 | 1535.6 | 1284.1 | 1097.7 | 1061.2 | 1121.4 | 1195.4 | 1180.6 |
| 20°   | 2219.1 | 2193.5 | 2096.8 | 1806.8 | 1531.7 | 1208.2 | 1009.9 | 1020.8 | 1105.6 | 1190.4 | 1198.3 |
| 22.5° | 2328.6 | 2301.9 | 2189.5 | 1861.1 | 1528.7 | 1117.4 | 934.0  | 985.3  | 1076.0 | 1148.0 | 1161.8 |
| 25°   | 2473.6 | 2442.0 | 2318.7 | 1941.0 | 1536.6 | 1034.6 | 879.8  | 950.8  | 1025.7 | 1090.8 | 1098.7 |
| 27.5° | 2664.9 | 2624.5 | 2467.6 | 2039.6 | 1553.4 | 969.5  | 856.1  | 903.4  | 961.6  | 1019.8 | 1026.7 |
| 30°   | 2914.4 | 2863.1 | 2638.3 | 2125.4 | 1545.5 | 924.1  | 840.3  | 856.1  | 890.6  | 937.9  | 938.9  |
| 32.5° | 3206.4 | 3136.3 | 2829.6 | 2199.4 | 1477.4 | 890.6  | 818.6  | 807.8  | 815.6  | 852.1  | 859.0  |
| 35°   | 3549.6 | 3458.8 | 3040.7 | 2269.4 | 1353.2 | 825.5  | 779.2  | 742.7  | 739.7  | 757.5  | 774.2  |
| 37.5° | 3943.1 | 3834.6 | 3307.0 | 2359.2 | 1206.2 | 757.5  | 721.0  | 684.5  | 668.7  | 677.6  | 703.2  |
| 40°   | 4306.0 | 4185.7 | 3585.1 | 2467.6 | 1056.3 | 696.3  | 652.9  | 615.4  | 596.7  | 599.7  | 631.2  |
| 42.5° | 4732.1 | 4607.8 | 3925.3 | 2609.7 | 932.0  | 654.9  | 581.9  | 543.4  | 518.8  | 532.6  | 569.1  |
| 45°   | 5379.1 | 5238.1 | 4421.4 | 2732.9 | 833.4  | 645.0  | 519.8  | 465.5  | 453.7  | 477.4  | 520.7  |
| 47.5° | 6262.8 | 6090.2 | 5103.0 | 2807.9 | 749.6  | 653.9  | 476.4  | 402.4  | 405.4  | 432.0  | 475.4  |
| 50°   | 7139.6 | 6953.2 | 5891.0 | 2709.3 | 680.5  | 636.1  | 454.7  | 353.1  | 371.8  | 395.5  | 434.9  |
| 52.5° | 7742.2 | 7499.6 | 6274.6 | 2424.2 | 617.4  | 569.1  | 452.7  | 306.7  | 342.2  | 350.1  | 383.7  |
| 55°   | 7765.9 | 7467.0 | 6078.4 | 1911.4 | 531.6  | 480.3  | 432.0  | 268.3  | 309.7  | 312.6  | 341.2  |
| 57.5° | 6807.2 | 6537.0 | 5312.0 | 1312.7 | 472.4  | 352.1  | 344.2  | 234.7  | 254.5  | 279.1  | 296.9  |
| 60°   | 5178.9 | 4949.1 | 3972.7 | 601.6  | 359.0  | 223.9  | 235.7  | 202.2  | 190.3  | 226.8  | 244.6  |
| 62.5° | 3171.8 | 3024.9 | 2382.8 | 266.3  | 228.8  | 119.3  | 143.0  | 160.8  | 143.0  | 156.8  | 171.6  |
| 65°   | 1259.5 | 1194.4 | 904.4  | 113.4  | 93.7   | 60.2   | 65.1   | 93.7   | 100.6  | 110.5  | 124.3  |
| 67.5° | 219.0  | 207.1  | 151.9  | 50.3   | 38.5   | 36.5   | 31.6   | 43.4   | 61.1   | 68.1   | 78.9   |
| 70°   | 28.6   | 27.6   | 24.7   | 20.7   | 19.7   | 17.8   | 13.8   | 27.6   | 41.4   | 43.4   | 50.3   |
| 72.5° | 6.9    | 5.9    | 5.9    | 4.9    | 5.9    | 2.0    | 2.0    | 14.8   | 29.6   | 30.6   | 35.5   |
| 75°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 4.9    | 18.7   | 20.7   | 24.7   |
| 77.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 1.0    |
| 80°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 82.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 85°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 87.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



REPORT NUMBER: P634739

CATALOG NUMBER: GWS-SA3C-735-U-SLL-W-GRSBK

**CANDELA DISTRIBUTION (continued):**

|       | 90°    | 95°    | 105°   | 115°   | 125°   | 135°   | 145°   | 155°   | 165°   | 175°   | 180°   |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°    | 1253.5 | 1253.5 | 1253.5 | 1253.5 | 1253.5 | 1253.5 | 1253.5 | 1253.5 | 1253.5 | 1253.5 | 1253.5 |
| 2.5°  | 1147.0 | 1127.3 | 1120.4 | 1110.5 | 1097.7 | 1101.7 | 1083.9 | 1078.0 | 1086.9 | 1098.7 | 1095.7 |
| 5°    | 1042.5 | 1020.8 | 1006.0 | 983.3  | 979.4  | 970.5  | 964.6  | 956.7  | 966.5  | 980.4  | 983.3  |
| 7.5°  | 959.6  | 940.9  | 926.1  | 919.2  | 914.3  | 910.3  | 898.5  | 892.6  | 892.6  | 898.5  | 903.4  |
| 10°   | 924.1  | 910.3  | 907.4  | 909.3  | 917.2  | 916.2  | 905.4  | 897.5  | 887.6  | 882.7  | 888.6  |
| 12.5° | 973.4  | 950.8  | 946.8  | 947.8  | 957.7  | 956.7  | 944.8  | 935.0  | 933.0  | 935.0  | 953.7  |
| 15°   | 1057.3 | 1022.8 | 997.1  | 992.2  | 997.1  | 995.1  | 986.3  | 980.4  | 983.3  | 1011.9 | 1043.5 |
| 17.5° | 1132.2 | 1079.0 | 1032.6 | 1014.9 | 1013.9 | 1010.9 | 1002.0 | 1000.1 | 1014.9 | 1068.1 | 1114.5 |
| 20°   | 1153.9 | 1101.7 | 1035.6 | 1012.9 | 1008.0 | 1005.0 | 995.1  | 998.1  | 1016.8 | 1080.9 | 1120.4 |
| 22.5° | 1125.3 | 1075.0 | 1006.0 | 983.3  | 979.4  | 978.4  | 968.5  | 972.5  | 988.2  | 1044.5 | 1077.0 |
| 25°   | 1071.1 | 1028.7 | 956.7  | 937.0  | 937.0  | 935.0  | 926.1  | 928.1  | 937.9  | 987.3  | 1018.8 |
| 27.5° | 1005.0 | 964.6  | 904.4  | 884.7  | 887.6  | 890.6  | 879.8  | 876.8  | 884.7  | 931.0  | 949.8  |
| 30°   | 929.1  | 900.5  | 853.1  | 835.4  | 834.4  | 846.2  | 831.4  | 827.5  | 838.3  | 874.8  | 878.8  |
| 32.5° | 855.1  | 841.3  | 807.8  | 793.9  | 794.9  | 796.9  | 789.0  | 789.0  | 798.9  | 818.6  | 817.6  |
| 35°   | 783.1  | 774.2  | 768.3  | 758.4  | 757.5  | 753.5  | 753.5  | 755.5  | 766.3  | 773.2  | 760.4  |
| 37.5° | 714.1  | 722.9  | 729.8  | 720.0  | 712.1  | 712.1  | 712.1  | 721.0  | 730.8  | 727.9  | 706.2  |
| 40°   | 652.9  | 671.6  | 693.3  | 682.5  | 663.8  | 662.8  | 666.7  | 681.5  | 696.3  | 678.6  | 658.8  |
| 42.5° | 600.6  | 624.3  | 654.9  | 649.0  | 628.3  | 625.3  | 628.3  | 647.0  | 658.8  | 636.1  | 614.4  |
| 45°   | 549.4  | 578.9  | 615.4  | 615.4  | 592.7  | 589.8  | 590.8  | 615.4  | 622.3  | 595.7  | 568.1  |
| 47.5° | 506.0  | 538.5  | 577.0  | 577.0  | 558.2  | 552.3  | 557.2  | 582.9  | 587.8  | 550.3  | 524.7  |
| 50°   | 464.5  | 500.0  | 542.4  | 539.5  | 526.7  | 521.7  | 530.6  | 558.2  | 552.3  | 510.9  | 484.3  |
| 52.5° | 412.3  | 449.7  | 507.9  | 510.9  | 504.0  | 505.0  | 515.8  | 533.6  | 516.8  | 466.5  | 443.8  |
| 55°   | 364.9  | 403.4  | 461.6  | 477.4  | 477.4  | 476.4  | 481.3  | 495.1  | 481.3  | 421.1  | 393.5  |
| 57.5° | 313.6  | 346.2  | 394.5  | 398.5  | 401.4  | 390.6  | 397.5  | 416.2  | 409.3  | 358.0  | 342.2  |
| 60°   | 257.4  | 285.0  | 312.6  | 315.6  | 302.8  | 280.1  | 292.9  | 314.6  | 319.6  | 281.1  | 263.3  |
| 62.5° | 182.5  | 209.1  | 241.6  | 241.6  | 228.8  | 206.1  | 222.9  | 241.6  | 234.7  | 195.3  | 184.4  |
| 65°   | 136.1  | 160.8  | 185.4  | 196.3  | 185.4  | 169.6  | 182.5  | 196.3  | 185.4  | 152.9  | 137.1  |
| 67.5° | 87.8   | 104.5  | 119.3  | 128.2  | 130.2  | 128.2  | 134.1  | 130.2  | 117.4  | 95.7   | 86.8   |
| 70°   | 53.3   | 62.1   | 70.0   | 77.9   | 83.8   | 86.8   | 89.8   | 80.9   | 68.1   | 56.2   | 53.3   |
| 72.5° | 38.5   | 46.4   | 53.3   | 59.2   | 66.1   | 68.1   | 68.1   | 62.1   | 50.3   | 39.5   | 36.5   |
| 75°   | 26.6   | 33.5   | 39.5   | 43.4   | 49.3   | 51.3   | 51.3   | 46.4   | 37.5   | 28.6   | 25.6   |
| 77.5° | 1.0    | 6.9    | 6.9    | 5.9    | 7.9    | 9.9    | 9.9    | 11.8   | 10.8   | 7.9    | 6.9    |
| 80°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 82.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 85°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 87.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |





REPORT NUMBER: P634739

CATALOG NUMBER: GWS-SA3C-735-U-SLL-W-GRSBK

**CANDELA DISTRIBUTION (continued):**

|       | 185°   | 195°   | 205°   | 215°   | 225°   | 235°   | 245°   | 255°   | 265°   | 270°   | 275°   |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°    | 1253.5 | 1253.5 | 1253.5 | 1253.5 | 1253.5 | 1253.5 | 1253.5 | 1253.5 | 1253.5 | 1253.5 | 1253.5 |
| 2.5°  | 1101.7 | 1137.2 | 1147.0 | 1183.5 | 1216.1 | 1248.6 | 1288.1 | 1311.7 | 1347.2 | 1371.9 | 1385.7 |
| 5°    | 993.2  | 1022.8 | 1058.3 | 1112.5 | 1168.7 | 1230.9 | 1305.8 | 1370.9 | 1452.8 | 1512.9 | 1532.7 |
| 7.5°  | 914.3  | 952.7  | 994.2  | 1062.2 | 1139.1 | 1222.0 | 1327.5 | 1434.0 | 1559.3 | 1641.1 | 1693.4 |
| 10°   | 899.5  | 938.9  | 994.2  | 1061.2 | 1142.1 | 1236.8 | 1366.0 | 1504.1 | 1660.9 | 1760.5 | 1819.7 |
| 12.5° | 970.5  | 1012.9 | 1036.6 | 1067.1 | 1128.3 | 1233.8 | 1399.5 | 1575.1 | 1759.5 | 1868.0 | 1931.1 |
| 15°   | 1075.0 | 1112.5 | 1074.0 | 1035.6 | 1075.0 | 1202.3 | 1418.3 | 1634.2 | 1846.3 | 1971.5 | 2036.6 |
| 17.5° | 1147.0 | 1150.0 | 1066.2 | 984.3  | 995.1  | 1145.1 | 1425.2 | 1693.4 | 1939.0 | 2070.2 | 2138.2 |
| 20°   | 1140.1 | 1116.5 | 1031.6 | 940.9  | 907.4  | 1071.1 | 1417.3 | 1745.7 | 2032.7 | 2169.8 | 2236.9 |
| 22.5° | 1086.9 | 1059.3 | 987.3  | 898.5  | 833.4  | 983.3  | 1403.5 | 1793.0 | 2118.5 | 2274.3 | 2337.5 |
| 25°   | 1022.8 | 993.2  | 934.0  | 856.1  | 786.1  | 898.5  | 1392.6 | 1858.1 | 2227.0 | 2410.4 | 2459.8 |
| 27.5° | 947.8  | 922.2  | 871.9  | 815.6  | 766.3  | 834.4  | 1389.7 | 1943.9 | 2358.2 | 2576.1 | 2610.7 |
| 30°   | 874.8  | 851.1  | 811.7  | 779.2  | 758.4  | 796.9  | 1379.8 | 2035.7 | 2515.0 | 2766.5 | 2804.0 |
| 32.5° | 804.8  | 781.1  | 756.5  | 751.5  | 752.5  | 783.1  | 1346.3 | 2126.4 | 2701.4 | 3042.6 | 3070.3 |
| 35°   | 744.6  | 717.0  | 707.2  | 719.0  | 740.7  | 759.4  | 1251.6 | 2201.4 | 2901.6 | 3343.4 | 3366.1 |
| 37.5° | 687.4  | 659.8  | 658.8  | 687.4  | 711.1  | 722.9  | 1140.1 | 2275.3 | 3171.8 | 3649.2 | 3677.8 |
| 40°   | 635.2  | 607.5  | 617.4  | 651.9  | 670.7  | 676.6  | 1005.0 | 2387.8 | 3457.9 | 3971.7 | 3955.9 |
| 42.5° | 590.8  | 562.2  | 568.1  | 612.5  | 629.2  | 645.0  | 880.7  | 2481.5 | 3733.0 | 4277.4 | 4272.5 |
| 45°   | 547.4  | 525.7  | 521.7  | 570.1  | 584.9  | 648.0  | 790.0  | 2553.4 | 4087.1 | 4667.0 | 4674.9 |
| 47.5° | 505.0  | 488.2  | 489.2  | 509.9  | 546.4  | 662.8  | 713.1  | 2600.8 | 4600.9 | 5284.4 | 5147.3 |
| 50°   | 466.5  | 453.7  | 464.5  | 440.9  | 521.7  | 644.0  | 647.0  | 2590.9 | 5174.9 | 5876.2 | 5601.0 |
| 52.5° | 424.1  | 421.1  | 426.1  | 368.9  | 482.3  | 568.1  | 584.9  | 2459.8 | 5444.2 | 6280.6 | 6123.7 |
| 55°   | 380.7  | 379.7  | 340.3  | 294.9  | 403.4  | 453.7  | 501.0  | 2052.4 | 5435.3 | 6495.6 | 6685.9 |
| 57.5° | 329.4  | 321.5  | 258.4  | 240.6  | 313.6  | 315.6  | 456.6  | 1344.3 | 4816.9 | 5980.7 | 6375.2 |
| 60°   | 249.5  | 243.6  | 189.4  | 195.3  | 219.0  | 202.2  | 363.9  | 669.7  | 3599.9 | 4659.1 | 5103.9 |
| 62.5° | 172.6  | 164.7  | 141.0  | 150.9  | 141.0  | 115.4  | 222.9  | 331.4  | 2180.6 | 2942.0 | 3345.4 |
| 65°   | 126.2  | 117.4  | 96.7   | 82.8   | 66.1   | 66.1   | 84.8   | 127.2  | 844.2  | 1250.6 | 1508.0 |
| 67.5° | 77.9   | 74.0   | 57.2   | 41.4   | 40.4   | 43.4   | 44.4   | 63.1   | 136.1  | 217.0  | 265.3  |
| 70°   | 50.3   | 46.4   | 38.5   | 26.6   | 24.7   | 25.6   | 26.6   | 29.6   | 34.5   | 37.5   | 45.4   |
| 72.5° | 34.5   | 32.5   | 27.6   | 14.8   | 11.8   | 12.8   | 13.8   | 13.8   | 16.8   | 15.8   | 18.7   |
| 75°   | 24.7   | 22.7   | 19.7   | 6.9    | 3.9    | 4.9    | 5.9    | 4.9    | 5.9    | 3.9    | 4.9    |
| 77.5° | 6.9    | 6.9    | 4.9    | 1.0    | 0.0    | 1.0    | 2.0    | 2.0    | 1.0    | 0.0    | 0.0    |
| 80°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 1.0    | 1.0    | 0.0    | 0.0    | 0.0    |
| 82.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 85°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 87.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



REPORT NUMBER: P634739

CATALOG NUMBER: GWS-SA3C-735-U-SLL-W-GRSBK

**CANDELA DISTRIBUTION (continued):**

|       | 285°   | 295°   | 305°    | 315°    | 325°    | 335°   | 345°   | 355°   | 359°   | 360°   |
|-------|--------|--------|---------|---------|---------|--------|--------|--------|--------|--------|
| 0°    | 1253.5 | 1253.5 | 1253.5  | 1253.5  | 1253.5  | 1253.5 | 1253.5 | 1253.5 | 1253.5 | 1253.5 |
| 2.5°  | 1421.2 | 1443.9 | 1452.8  | 1440.0  | 1450.8  | 1433.0 | 1426.1 | 1399.5 | 1397.5 | 1392.6 |
| 5°    | 1612.5 | 1663.8 | 1694.4  | 1713.1  | 1691.4  | 1667.8 | 1632.3 | 1571.1 | 1552.4 | 1540.6 |
| 7.5°  | 1800.9 | 1880.8 | 1933.1  | 1957.7  | 1951.8  | 1903.5 | 1839.4 | 1736.8 | 1700.3 | 1682.6 |
| 10°   | 1964.6 | 2062.3 | 2125.4  | 2156.0  | 2143.2  | 2100.8 | 2009.0 | 1880.8 | 1832.5 | 1821.6 |
| 12.5° | 2079.1 | 2168.8 | 2212.2  | 2238.8  | 2239.8  | 2223.0 | 2136.3 | 2007.1 | 1949.9 | 1936.0 |
| 15°   | 2151.1 | 2189.5 | 2190.5  | 2206.3  | 2233.9  | 2271.4 | 2230.9 | 2116.5 | 2055.4 | 2034.7 |
| 17.5° | 2196.4 | 2154.0 | 2110.6  | 2114.6  | 2159.9  | 2259.5 | 2301.0 | 2213.2 | 2148.1 | 2125.4 |
| 20°   | 2229.0 | 2094.8 | 2014.0  | 2014.9  | 2061.3  | 2212.2 | 2349.3 | 2306.9 | 2239.8 | 2219.1 |
| 22.5° | 2249.7 | 2042.6 | 1927.2  | 1924.2  | 1973.5  | 2156.0 | 2393.7 | 2418.3 | 2352.2 | 2328.6 |
| 25°   | 2292.1 | 2017.9 | 1874.9  | 1891.7  | 1935.1  | 2138.2 | 2453.8 | 2566.3 | 2505.1 | 2473.6 |
| 27.5° | 2368.0 | 2042.6 | 1870.0  | 1908.4  | 1957.7  | 2190.5 | 2558.4 | 2763.5 | 2700.4 | 2664.9 |
| 30°   | 2499.2 | 2135.3 | 1945.9  | 1999.2  | 2058.3  | 2327.6 | 2733.9 | 3038.7 | 2948.0 | 2914.4 |
| 32.5° | 2710.3 | 2327.6 | 2180.6  | 2295.0  | 2352.2  | 2552.5 | 2997.3 | 3347.4 | 3273.4 | 3206.4 |
| 35°   | 3001.2 | 2766.5 | 2749.7  | 3016.0  | 3002.2  | 2978.5 | 3320.8 | 3726.1 | 3614.7 | 3549.6 |
| 37.5° | 3401.6 | 3472.6 | 3596.9  | 3861.2  | 3852.4  | 3671.9 | 3745.8 | 4084.1 | 4026.9 | 3943.1 |
| 40°   | 3901.7 | 4052.6 | 4263.6  | 4642.4  | 4524.0  | 4297.2 | 4267.6 | 4451.0 | 4404.7 | 4306.0 |
| 42.5° | 4196.6 | 4456.9 | 4859.3  | 5199.6  | 5104.9  | 4708.4 | 4674.9 | 4941.2 | 4839.6 | 4732.1 |
| 45°   | 4333.7 | 4786.4 | 5575.4  | 6036.0  | 5749.0  | 4981.6 | 4968.8 | 5580.3 | 5523.1 | 5379.1 |
| 47.5° | 4396.8 | 5118.7 | 6413.7  | 7111.0  | 6574.5  | 5221.3 | 5174.9 | 6507.4 | 6432.4 | 6262.8 |
| 50°   | 4466.8 | 5577.3 | 7423.6  | 8356.6  | 7571.6  | 5492.5 | 5526.1 | 7371.4 | 7339.8 | 7139.6 |
| 52.5° | 4620.7 | 6062.6 | 8667.3  | 9780.8  | 8780.7  | 5917.6 | 6128.7 | 8186.0 | 7973.0 | 7742.2 |
| 55°   | 4851.5 | 6591.2 | 9961.3  | 11235.6 | 10014.6 | 6488.7 | 6780.6 | 8619.0 | 8021.3 | 7765.9 |
| 57.5° | 4596.0 | 6723.4 | 10727.6 | 12251.4 | 10561.9 | 6490.6 | 6229.3 | 7868.4 | 7054.8 | 6807.2 |
| 60°   | 3647.2 | 6254.9 | 10432.7 | 12031.5 | 10095.4 | 5763.7 | 4769.6 | 6143.5 | 5344.6 | 5178.9 |
| 62.5° | 2465.7 | 5246.0 | 9184.1  | 10175.3 | 8640.7  | 4533.9 | 3099.8 | 3995.4 | 3308.9 | 3171.8 |
| 65°   | 1351.2 | 3913.5 | 7420.7  | 7697.8  | 6762.8  | 3166.9 | 1594.8 | 1733.9 | 1320.6 | 1259.5 |
| 67.5° | 372.8  | 2724.1 | 5460.0  | 5106.9  | 4744.9  | 2062.3 | 412.3  | 309.7  | 220.9  | 219.0  |
| 70°   | 93.7   | 1801.9 | 3271.5  | 3372.1  | 2909.5  | 1320.6 | 78.9   | 37.5   | 29.6   | 28.6   |
| 72.5° | 39.5   | 775.2  | 1552.4  | 1784.2  | 1489.3  | 611.5  | 28.6   | 10.8   | 8.9    | 6.9    |
| 75°   | 4.9    | 62.1   | 132.2   | 200.2   | 137.1   | 66.1   | 0.0    | 0.0    | 0.0    | 0.0    |
| 77.5° | 0.0    | 0.0    | 0.0     | 0.0     | 0.0     | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 80°   | 0.0    | 0.0    | 0.0     | 0.0     | 0.0     | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 82.5° | 0.0    | 0.0    | 0.0     | 0.0     | 0.0     | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 85°   | 0.0    | 0.0    | 0.0     | 0.0     | 0.0     | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 87.5° | 0.0    | 0.0    | 0.0     | 0.0     | 0.0     | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 90°   | 0.0    | 0.0    | 0.0     | 0.0     | 0.0     | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |

LM-79-08: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

All Brands

Data applicable to all product families using SA light engines

Report Number: SP1-2101-121-7

Luminaire Tested: IFLD-S-SA2A-735-U-T2

Test Date: 03/04/2021

**Test Information**

Test Method: LM-79-08  
 Report Number: SP1-2101-121-7  
 Test Lab: COOPER LIGHTING SOLUTIONS  
 Photometer: SP1  
 Measurement Geometry: 4π  
 Issue Date: 03/04/2021  
 Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
 Product Line: STREETWORKS  
 Catalog Number: **IFLD-S-SA2A-735-U-T2**  
 Description: STREETWORKS INF FLOOD

PROGRAMMED @ 615mA.

**Spectral Parameters**

|                           |        |           |      |      |       |
|---------------------------|--------|-----------|------|------|-------|
| CCT (K):                  | 3388   | CRI (Ra): | 73.1 | R9:  | -34.6 |
| CIE u':                   | 0.2371 | R1:       | 68.9 | R10: | 57.8  |
| CIE v':                   | 0.5177 | R2:       | 81.1 | R11: | 68.6  |
| Duv:                      | 0.0032 | R3:       | 93.1 | R12: | 53.9  |
| CIE x:                    | 0.4153 | R4:       | 71.6 | R13: | 70.9  |
| CIE y:                    | 0.4030 | R5:       | 69.4 | R14: | 96.2  |
| CIE z:                    | 0.1817 | R6:       | 75.0 |      |       |
| Peak Wavelength (nm):     | 590    | R7:       | 79.5 |      |       |
| Dominant Wavelength (nm): | 580    | R8:       | 46.4 |      |       |
| Purity:                   | 45.7   |           |      |      |       |
| Rf:                       | 76.9   |           |      |      |       |
| Rg:                       | 94.4   |           |      |      |       |



**Test Conditions**

Stabilization Time: 81M  
 Operation Time: 12H  
 Room Temperature (°C) / RH%: 25.0/30%  
 Sphere Temperature (°C): 24.1

REPORT NUMBER: SP1-2101-121-7

| Measurement and Test Equipment |                       |                  |                      |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument                     | Identification Number | Calibration Date | Calibration Due Date |
| Photometer                     | IN0058                | 1/31/2021        | 7/31/2021            |
| Power Meter                    | IN0071                | 12/1/2020        | 12/1/2021            |
| AC Power Source                | IN0063                | 12/1/2020        | 12/1/2021            |
| DC Power Source                | IN0208                | 12/1/2020        | 12/1/2021            |
| Sphere Thermometer             | IN0085                | 12/1/2020        | 12/1/2021            |
| Room Thermometer               | IN0046                | 12/1/2020        | 12/1/2021            |

REPORT NUMBER: SP1-2101-121-7

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



CCT = 3388K  
 CIE x = 0.4153  
 CIE y = 0.4030  
 Duv = 0.0032

Point lies inside the ANSI 3500K 4-step quadrangle

REPORT NUMBER: SP1-2101-121-7

**Photopic Flux vs. Wavelength**



#####

| λ (nm) | Power (µW/nm) | Lumens (Φ/nm) | λ (nm) | Power (µW/nm) | Lumens (Φ/nm) | λ (nm) | Power (µW/nm) | Lumens (Φ/nm) | λ (nm) | Power (µW/nm) | Lumens (Φ/nm) | λ (nm) | Power (µW/nm) | Lumens (Φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360    | 2672          | 0.0           | 490    | 34553         | 4.9           | 620    | 136720        | 35.6          | 750    | 5870          | 0.0           | 880    | 4216          | 0.0           |
| 365    | 2252          | 0.0           | 495    | 44336         | 8.0           | 625    | 126308        | 27.9          | 755    | 5421          | 0.0           | 885    | 4132          | 0.0           |
| 370    | 2217          | 0.0           | 500    | 54643         | 12.1          | 630    | 114625        | 20.7          | 760    | 5097          | 0.0           | 890    | 3992          | 0.0           |
| 375    | 2697          | 0.0           | 505    | 64676         | 18.1          | 635    | 103216        | 15.5          | 765    | 4626          | 0.0           | 895    | 3214          | 0.0           |
| 380    | 3039          | 0.0           | 510    | 73825         | 25.4          | 640    | 92605         | 11.1          | 770    | 3782          | 0.0           | 900    | 2580          | 0.0           |
| 385    | 2655          | 0.0           | 515    | 81872         | 33.9          | 645    | 83234         | 8.0           | 775    | 3506          | 0.0           | 905    | 1776          | 0.0           |
| 390    | 2357          | 0.0           | 520    | 88574         | 43.0          | 650    | 73263         | 5.4           | 780    | 3507          | 0.0           | 910    | 3995          | 0.0           |
| 395    | 2186          | 0.0           | 525    | 93289         | 50.1          | 655    | 64627         | 3.7           | 785    | 3267          | 0.0           | 915    | 4288          | 0.0           |
| 400    | 2015          | 0.0           | 530    | 98393         | 57.9          | 660    | 56614         | 2.4           | 790    | 2849          | 0.0           | 920    | 2446          | 0.0           |
| 405    | 2234          | 0.0           | 535    | 103269        | 64.0          | 665    | 49537         | 1.6           | 795    | 3037          | 0.0           | 925    | 3009          | 0.0           |
| 410    | 3412          | 0.0           | 540    | 107316        | 69.9          | 670    | 42866         | 0.9           | 800    | 2716          | 0.0           | 930    | 3026          | 0.0           |
| 415    | 6135          | 0.0           | 545    | 113101        | 75.3          | 675    | 36708         | 0.6           | 805    | 2648          | 0.0           | 935    | 4734          | 0.0           |
| 420    | 12146         | 0.0           | 550    | 120690        | 82.0          | 680    | 31814         | 0.4           | 810    | 3187          | 0.0           | 940    | 3719          | 0.0           |
| 425    | 23983         | 0.1           | 555    | 128583        | 87.8          | 685    | 27485         | 0.2           | 815    | 2931          | 0.0           | 945    | 1480          | 0.0           |
| 430    | 42142         | 0.3           | 560    | 137796        | 93.6          | 690    | 23698         | 0.1           | 820    | 2717          | 0.0           | 950    | 3450          | 0.0           |
| 435    | 68228         | 0.8           | 565    | 146577        | 97.5          | 695    | 20309         | 0.1           | 825    | 2236          | 0.0           | 955    | 5051          | 0.0           |
| 440    | 99323         | 1.6           | 570    | 154581        | 100.5         | 700    | 17890         | 0.1           | 830    | 2628          | 0.0           | 960    | 3176          | 0.0           |
| 445    | 115584        | 2.4           | 575    | 162633        | 101.2         | 705    | 15500         | 0.0           | 835    | 3140          | 0.0           | 965    | 5178          | 0.0           |
| 450    | 94997         | 2.5           | 580    | 168101        | 99.9          | 710    | 13699         | 0.0           | 840    | 3675          | 0.0           | 970    | 6385          | 0.0           |
| 455    | 61433         | 2.1           | 585    | 173145        | 96.2          | 715    | 12398         | 0.0           | 845    | 3283          | 0.0           | 975    | 3810          | 0.0           |
| 460    | 43373         | 1.8           | 590    | 174675        | 90.3          | 720    | 11147         | 0.0           | 850    | 3055          | 0.0           | 980    | 4322          | 0.0           |
| 465    | 32472         | 1.7           | 595    | 173724        | 82.3          | 725    | 9761          | 0.0           | 855    | 2932          | 0.0           | 985    | 4200          | 0.0           |
| 470    | 24257         | 1.5           | 600    | 171241        | 73.8          | 730    | 8651          | 0.0           | 860    | 3382          | 0.0           | 990    | 4661          | 0.0           |
| 475    | 21690         | 1.7           | 605    | 165134        | 64.0          | 735    | 7730          | 0.0           | 865    | 2605          | 0.0           | 995    | 6746          | 0.0           |
| 480    | 23173         | 2.2           | 610    | 156652        | 53.8          | 740    | 6847          | 0.0           | 870    | 3325          | 0.0           | 1000   | 4150          | 0.0           |
| 485    | 27564         | 3.3           | 615    | 147879        | 44.6          | 745    | 6124          | 0.0           | 875    | 3325          | 0.0           |        |               |               |

REPORT NUMBER: SP1-2101-121-7

**Scotopic Flux vs. Wavelength**



**Scotopic Lumens: 12126**

**S/P: 1.36**

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360    | 2672          | 0.0           | 490    | 34553         | 53.2          | 620    | 136720        | 1.7           | 750    | 5870          | 0.0           | 880    | 4216          | 0.0           |
| 365    | 2252          | 0.0           | 495    | 44336         | 71.7          | 625    | 126308        | 1.1           | 755    | 5421          | 0.0           | 885    | 4132          | 0.0           |
| 370    | 2217          | 0.0           | 500    | 54643         | 91.4          | 630    | 114625        | 0.6           | 760    | 5097          | 0.0           | 890    | 3992          | 0.0           |
| 375    | 2697          | 0.0           | 505    | 64676         | 110.0         | 635    | 103216        | 0.4           | 765    | 4626          | 0.0           | 895    | 3214          | 0.0           |
| 380    | 3039          | 0.0           | 510    | 73825         | 125.1         | 640    | 92605         | 0.2           | 770    | 3782          | 0.0           | 900    | 2580          | 0.0           |
| 385    | 2655          | 0.0           | 515    | 81872         | 135.7         | 645    | 83234         | 0.1           | 775    | 3506          | 0.0           | 905    | 1776          | 0.0           |
| 390    | 2357          | 0.0           | 520    | 88574         | 140.8         | 650    | 73263         | 0.1           | 780    | 3507          | 0.0           | 910    | 3995          | 0.0           |
| 395    | 2186          | 0.0           | 525    | 93289         | 139.6         | 655    | 64627         | 0.1           | 785    | 3267          | 0.0           | 915    | 4288          | 0.0           |
| 400    | 2015          | 0.0           | 530    | 98393         | 135.7         | 660    | 56614         | 0.0           | 790    | 2849          | 0.0           | 920    | 2446          | 0.0           |
| 405    | 2234          | 0.1           | 535    | 103269        | 128.7         | 665    | 49537         | 0.0           | 795    | 3037          | 0.0           | 925    | 3009          | 0.0           |
| 410    | 3412          | 0.2           | 540    | 107316        | 118.6         | 670    | 42866         | 0.0           | 800    | 2716          | 0.0           | 930    | 3026          | 0.0           |
| 415    | 6135          | 0.6           | 545    | 113101        | 108.4         | 675    | 36708         | 0.0           | 805    | 2648          | 0.0           | 935    | 4734          | 0.0           |
| 420    | 12146         | 2.0           | 550    | 120690        | 98.7          | 680    | 31814         | 0.0           | 810    | 3187          | 0.0           | 940    | 3719          | 0.0           |
| 425    | 23983         | 5.9           | 555    | 128583        | 87.9          | 685    | 27485         | 0.0           | 815    | 2931          | 0.0           | 945    | 1480          | 0.0           |
| 430    | 42142         | 14.3          | 560    | 137796        | 77.0          | 690    | 23698         | 0.0           | 820    | 2717          | 0.0           | 950    | 3450          | 0.0           |
| 435    | 68228         | 30.5          | 565    | 146577        | 65.8          | 695    | 20309         | 0.0           | 825    | 2236          | 0.0           | 955    | 5051          | 0.0           |
| 440    | 99323         | 55.5          | 570    | 154581        | 54.6          | 700    | 17890         | 0.0           | 830    | 2628          | 0.0           | 960    | 3176          | 0.0           |
| 445    | 115584        | 77.4          | 575    | 162633        | 44.3          | 705    | 15500         | 0.0           | 835    | 3140          | 0.0           | 965    | 5178          | 0.0           |
| 450    | 94997         | 73.6          | 580    | 168101        | 34.6          | 710    | 13699         | 0.0           | 840    | 3675          | 0.0           | 970    | 6385          | 0.0           |
| 455    | 61433         | 53.7          | 585    | 173145        | 26.5          | 715    | 12398         | 0.0           | 845    | 3283          | 0.0           | 975    | 3810          | 0.0           |
| 460    | 43373         | 41.9          | 590    | 174675        | 19.5          | 720    | 11147         | 0.0           | 850    | 3055          | 0.0           | 980    | 4322          | 0.0           |
| 465    | 32472         | 34.3          | 595    | 173724        | 13.9          | 725    | 9761          | 0.0           | 855    | 2932          | 0.0           | 985    | 4200          | 0.0           |
| 470    | 24257         | 27.9          | 600    | 171241        | 9.7           | 730    | 8651          | 0.0           | 860    | 3382          | 0.0           | 990    | 4661          | 0.0           |
| 475    | 21690         | 27.1          | 605    | 165134        | 6.5           | 735    | 7730          | 0.0           | 865    | 2605          | 0.0           | 995    | 6746          | 0.0           |
| 480    | 23173         | 31.3          | 610    | 156652        | 4.2           | 740    | 6847          | 0.0           | 870    | 3325          | 0.0           | 1000   | 4150          | 0.0           |
| 485    | 27564         | 40.0          | 615    | 147879        | 2.7           | 745    | 6124          | 0.0           | 875    | 3325          | 0.0           |        |               |               |



REPORT NUMBER: SP1-2101-121-7

**Melanopic Flux vs. Wavelength**



**Melanopic Lumens: 4490.7 M/P: 0.5**

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360    | 2672          | 0.0           | 490    | 34553         | 28.8          | 620    | 136720        | 0.1           | 750    | 5870          | 0.0           | 880    | 4216          | 0.0           |
| 365    | 2252          | 0.0           | 495    | 44336         | 36.6          | 625    | 126308        | 0.1           | 755    | 5421          | 0.0           | 885    | 4132          | 0.0           |
| 370    | 2217          | 0.0           | 500    | 54643         | 43.9          | 630    | 114625        | 0.0           | 760    | 5097          | 0.0           | 890    | 3992          | 0.0           |
| 375    | 2697          | 0.0           | 505    | 64676         | 49.6          | 635    | 103216        | 0.0           | 765    | 4626          | 0.0           | 895    | 3214          | 0.0           |
| 380    | 3039          | 0.0           | 510    | 73825         | 53.0          | 640    | 92605         | 0.0           | 770    | 3782          | 0.0           | 900    | 2580          | 0.0           |
| 385    | 2655          | 0.0           | 515    | 81872         | 53.5          | 645    | 83234         | 0.0           | 775    | 3506          | 0.0           | 905    | 1776          | 0.0           |
| 390    | 2357          | 0.0           | 520    | 88574         | 51.6          | 650    | 73263         | 0.0           | 780    | 3507          | 0.0           | 910    | 3995          | 0.0           |
| 395    | 2186          | 0.0           | 525    | 93289         | 47.3          | 655    | 64627         | 0.0           | 785    | 3267          | 0.0           | 915    | 4288          | 0.0           |
| 400    | 2015          | 0.0           | 530    | 98393         | 42.5          | 660    | 56614         | 0.0           | 790    | 2849          | 0.0           | 920    | 2446          | 0.0           |
| 405    | 2234          | 0.0           | 535    | 103269        | 37.2          | 665    | 49537         | 0.0           | 795    | 3037          | 0.0           | 925    | 3009          | 0.0           |
| 410    | 3412          | 0.1           | 540    | 107316        | 31.4          | 670    | 42866         | 0.0           | 800    | 2716          | 0.0           | 930    | 3026          | 0.0           |
| 415    | 6135          | 0.4           | 545    | 113101        | 26.3          | 675    | 36708         | 0.0           | 805    | 2648          | 0.0           | 935    | 4734          | 0.0           |
| 420    | 12146         | 1.4           | 550    | 120690        | 21.7          | 680    | 31814         | 0.0           | 810    | 3187          | 0.0           | 940    | 3719          | 0.0           |
| 425    | 23983         | 3.7           | 555    | 128583        | 17.3          | 685    | 27485         | 0.0           | 815    | 2931          | 0.0           | 945    | 1480          | 0.0           |
| 430    | 42142         | 8.9           | 560    | 137796        | 13.6          | 690    | 23698         | 0.0           | 820    | 2717          | 0.0           | 950    | 3450          | 0.0           |
| 435    | 68228         | 18.2          | 565    | 146577        | 10.3          | 695    | 20309         | 0.0           | 825    | 2236          | 0.0           | 955    | 5051          | 0.0           |
| 440    | 99323         | 33.2          | 570    | 154581        | 7.6           | 700    | 17890         | 0.0           | 830    | 2628          | 0.0           | 960    | 3176          | 0.0           |
| 445    | 115584        | 45.6          | 575    | 162633        | 5.4           | 705    | 15500         | 0.0           | 835    | 3140          | 0.0           | 965    | 5178          | 0.0           |
| 450    | 94997         | 43.8          | 580    | 168101        | 3.8           | 710    | 13699         | 0.0           | 840    | 3675          | 0.0           | 970    | 6385          | 0.0           |
| 455    | 61433         | 32.2          | 585    | 173145        | 2.6           | 715    | 12398         | 0.0           | 845    | 3283          | 0.0           | 975    | 3810          | 0.0           |
| 460    | 43373         | 25.6          | 590    | 174675        | 1.7           | 720    | 11147         | 0.0           | 850    | 3055          | 0.0           | 980    | 4322          | 0.0           |
| 465    | 32472         | 21.2          | 595    | 173724        | 1.1           | 725    | 9761          | 0.0           | 855    | 2932          | 0.0           | 985    | 4200          | 0.0           |
| 470    | 24257         | 17.4          | 600    | 171241        | 0.7           | 730    | 8651          | 0.0           | 860    | 3382          | 0.0           | 990    | 4661          | 0.0           |
| 475    | 21690         | 16.6          | 605    | 165134        | 0.5           | 735    | 7730          | 0.0           | 865    | 2605          | 0.0           | 995    | 6746          | 0.0           |
| 480    | 23173         | 18.6          | 610    | 156652        | 0.3           | 740    | 6847          | 0.0           | 870    | 3325          | 0.0           | 1000   | 4150          | 0.0           |
| 485    | 27564         | 22.7          | 615    | 147879        | 0.2           | 745    | 6124          | 0.0           | 875    | 3325          | 0.0           |        |               |               |

**Summary**

$R_f = 76.9$   
 $R_g = 94.4$   
 $CIE R_a = 73.1$   
 $R_g = -34.6$



**Color Vector Graphics**



**Individual Sample Fidelity Index ( $R_{f,i}$ )**


|            |            |            |            |
|------------|------------|------------|------------|
| CES01 = 86 | CES26 = 68 | CES51 = 90 | CES76 = 63 |
| CES02 = 62 | CES27 = 88 | CES52 = 89 | CES77 = 80 |
| CES03 = 31 | CES28 = 87 | CES53 = 80 | CES78 = 65 |
| CES04 = 70 | CES29 = 67 | CES54 = 84 | CES79 = 87 |
| CES05 = 48 | CES30 = 74 | CES55 = 84 | CES80 = 86 |
| CES06 = 51 | CES31 = 71 | CES56 = 75 | CES81 = 75 |
| CES07 = 40 | CES32 = 67 | CES57 = 74 | CES82 = 94 |
| CES08 = 39 | CES33 = 74 | CES58 = 76 | CES83 = 91 |
| CES09 = 29 | CES34 = 78 | CES59 = 87 | CES84 = 89 |
| CES10 = 75 | CES35 = 89 | CES60 = 93 | CES85 = 80 |
| CES11 = 58 | CES36 = 98 | CES61 = 86 | CES86 = 66 |
| CES12 = 64 | CES37 = 86 | CES62 = 89 | CES87 = 79 |
| CES13 = 43 | CES38 = 82 | CES63 = 77 | CES88 = 79 |
| CES14 = 74 | CES39 = 95 | CES64 = 74 | CES89 = 70 |
| CES15 = 71 | CES40 = 91 | CES65 = 68 | CES90 = 77 |
| CES16 = 47 | CES41 = 89 | CES66 = 71 | CES91 = 88 |
| CES17 = 50 | CES42 = 88 | CES67 = 69 | CES92 = 60 |
| CES18 = 56 | CES43 = 82 | CES68 = 74 | CES93 = 77 |
| CES19 = 72 | CES44 = 99 | CES69 = 82 | CES94 = 52 |
| CES20 = 65 | CES45 = 87 | CES70 = 67 | CES95 = 69 |
| CES21 = 86 | CES46 = 82 | CES71 = 66 | CES96 = 78 |
| CES22 = 79 | CES47 = 82 | CES72 = 88 | CES97 = 85 |
| CES23 = 92 | CES48 = 72 | CES73 = 59 | CES98 = 76 |
| CES24 = 91 | CES49 = 82 | CES74 = 97 | CES99 = 63 |
| CES25 = 72 | CES50 = 88 | CES75 = 66 |            |



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)