

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: McGRAW-EDISON

Report Number: P642170

Luminaire Tested: GWS-SA6C-735-U-SLR-W-HSS

Issue Date: 1/10/2023

Test Information

Test Method: LM-79-2019
Report Number: P642170
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2209-782-44)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/10/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: McGRAW-EDISON
Catalog Number: GWS-SA6C-735-U-SLR-W-HSS
Description: GALLEON WALL SLIM LUMINAIRE. (6) LIGHTSQUARES WITH 16 LEDS EACH AND
SPILL LIGHT ELIMINATOR RIGHT OPTICS WITH HOUSE SIDE SHIELD
Light Source: (96) 3500K CCT, 70 CRI LEDS
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 17380.1 lumens
Efficiency: N/A
Efficacy: 91.9 lumens/watt
Luminous Opening: Rectangular (W 2' x L: 1' x H: 0')
IES Classification: Type IV - Short
BUG Rating: B2 - U0 - G4


Input Watts (W): 189.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 0
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT



REPORT NUMBER: P642170
 CATALOG NUMBER: GWS-SA6C-735-U-SLR-W-HSS

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 5.6 fc
 Type IV - Short - N/A

REPORT NUMBER: P642170
CATALOG NUMBER: GWS-SA6C-735-U-SLR-W-HSS

Luminous Intensity Polar Plot



— Vertical Plane Through 45-Deg Lateral - - - Horizontal Cone Through 62.5-Deg Vertical

REPORT NUMBER: P642170
 CATALOG NUMBER: GWS-SA6C-735-U-SLR-W-HSS

FLUX DISTRIBUTION:

| | | Downward | Upward | Total |
|--------------------|-----------|----------|--------|---------|
| House Side | Lumens | 2144.7 | 0.0 | 2144.7 |
| | % Fixture | 12.3 | 0.0 | 12.3 |
| Street Side | Lumens | 15235.4 | 0.0 | 15235.4 |
| | % Fixture | 87.7 | 0.0 | 87.7 |
| Total | Lumens | 17380.1 | 0.0 | 17380.1 |
| | % Fixture | 100.0 | 0.0 | 100.0 |

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|---------|-----------|
| 0°-10° | 80.1 | 0.5 |
| 10°-20° | 303.0 | 1.7 |
| 20°-30° | 658.7 | 3.8 |
| 30°-40° | 1081.1 | 6.2 |
| 40°-50° | 1987.5 | 11.4 |
| 50°-60° | 4268.3 | 24.6 |
| 60°-70° | 5733.0 | 33.0 |
| 70°-80° | 2985.2 | 17.2 |
| 80°-90° | 283.0 | 1.6 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-90° | 17380.1 | 100.0 |
| 0°-180° | 17380.1 | 100.0 |

Coefficient of Utilization




REPORT NUMBER: P642170
 CATALOG NUMBER: GWS-SA6C-735-U-SLR-W-HSS

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

| Zone | Lumens | % Fixture | Zone Rating/Lumen Limit | | |
|----------------|--------|-----------|-------------------------|------|----------|
| | | | B | U | G |
| FL (0°-30°) | 734.2 | 4.2 | | | |
| FM (30°-60°) | 6100.2 | 35.1 | | | |
| FH (60°-80°) | 8130.6 | 46.8 | | | G4/12000 |
| FVH (80°-90°) | 270.4 | 1.6 | | | G3/500 |
| BL (0°-30°) | 307.6 | 1.8 | B1/500 | | |
| BM (30°-60°) | 1236.8 | 7.1 | B2/2500 | | |
| BH (60°-80°) | 587.7 | 3.4 | B2/1000 | | G2/1000 |
| BVH (80°-90°) | 12.6 | 0.1 | | | G1/100 |
| UL (90°-100°) | 0.0 | 0.0 | | U0/0 | |
| UH (100°-180°) | 0.0 | 0.0 | | U0/0 | |

BUG Rating: B2-U0-G4
 Type IV Short





REPORT NUMBER: P642170

CATALOG NUMBER: GWS-SA6C-735-U-SLR-W-HSS

CANDELA DISTRIBUTION (FULL):

| | 0° | 1° | 5° | 15° | 25° | 35° | 45° | 55° | 65° | 75° | 85° |
|-------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|
| 0° | 903.4 | 903.4 | 903.4 | 903.4 | 903.4 | 903.4 | 903.4 | 903.4 | 903.4 | 903.4 | 903.4 |
| 2.5° | 921.5 | 925.5 | 929.5 | 943.6 | 953.6 | 961.6 | 963.6 | 957.6 | 943.6 | 929.5 | 909.4 |
| 5° | 893.4 | 897.4 | 911.4 | 949.6 | 987.7 | 1017.8 | 1027.9 | 1021.8 | 987.7 | 943.6 | 897.4 |
| 7.5° | 891.4 | 899.4 | 933.5 | 1013.8 | 1096.1 | 1158.4 | 1174.4 | 1160.4 | 1096.1 | 1007.8 | 913.4 |
| 10° | 963.6 | 977.7 | 1027.9 | 1172.4 | 1323.0 | 1433.4 | 1477.6 | 1417.3 | 1315.0 | 1154.3 | 999.8 |
| 12.5° | 1152.3 | 1176.4 | 1272.8 | 1483.6 | 1716.5 | 1863.0 | 1923.2 | 1849.0 | 1688.4 | 1455.5 | 1210.6 |
| 15° | 1449.5 | 1485.6 | 1630.1 | 1945.3 | 2220.4 | 2350.9 | 2370.9 | 2328.8 | 2142.1 | 1885.1 | 1555.9 |
| 17.5° | 1869.0 | 1921.2 | 2146.1 | 2467.3 | 2666.0 | 2712.2 | 2706.2 | 2662.0 | 2525.5 | 2348.8 | 2037.7 |
| 20° | 2370.9 | 2433.2 | 2654.0 | 2919.0 | 2939.1 | 2884.9 | 2854.7 | 2828.7 | 2782.5 | 2752.4 | 2509.4 |
| 22.5° | 2876.8 | 2953.1 | 3184.0 | 3250.2 | 3069.6 | 2913.0 | 2838.7 | 2858.8 | 2927.0 | 3075.6 | 2977.2 |
| 25° | 3380.7 | 3453.0 | 3669.8 | 3491.1 | 3129.8 | 2868.8 | 2774.4 | 2822.6 | 2985.2 | 3306.4 | 3432.9 |
| 27.5° | 3968.9 | 4023.1 | 4151.6 | 3655.8 | 3139.8 | 2832.7 | 2740.3 | 2814.6 | 3013.3 | 3451.0 | 3932.8 |
| 30° | 4581.2 | 4613.4 | 4551.1 | 3699.9 | 3105.7 | 2778.5 | 2706.2 | 2814.6 | 3061.5 | 3547.4 | 4308.2 |
| 32.5° | 5030.9 | 5037.0 | 4834.2 | 3703.9 | 3087.6 | 2734.3 | 2674.1 | 2802.6 | 3107.7 | 3627.7 | 4671.6 |
| 35° | 5494.7 | 5464.6 | 5105.2 | 3764.2 | 3135.8 | 2750.4 | 2698.2 | 2836.7 | 3180.0 | 3722.0 | 4990.8 |
| 37.5° | 5964.5 | 5910.3 | 5408.4 | 3862.5 | 3260.3 | 2925.0 | 2892.9 | 3011.3 | 3296.4 | 3852.5 | 5342.1 |
| 40° | 6446.3 | 6372.0 | 5723.5 | 4011.1 | 3537.3 | 3519.3 | 3629.7 | 3615.6 | 3615.6 | 4019.1 | 5703.5 |
| 42.5° | 7034.5 | 6948.2 | 6189.3 | 4430.7 | 4183.8 | 4587.3 | 4888.4 | 4701.7 | 4356.4 | 4402.6 | 6173.2 |
| 45° | 7811.4 | 7737.1 | 6996.3 | 5233.7 | 5197.6 | 6125.1 | 6530.6 | 6161.2 | 5302.0 | 5287.9 | 6958.2 |
| 47.5° | 9054.1 | 9040.0 | 8283.2 | 6165.2 | 6438.2 | 8082.4 | 8865.4 | 8154.7 | 6380.0 | 6225.4 | 8443.8 |
| 50° | 10800.7 | 10758.5 | 9887.2 | 7257.3 | 7913.8 | 10507.6 | 11904.8 | 10720.4 | 7682.9 | 7319.6 | 10433.3 |
| 52.5° | 12768.1 | 12812.2 | 12133.7 | 8449.8 | 9481.7 | 13205.7 | 15151.0 | 13659.4 | 9098.3 | 8710.8 | 12936.7 |
| 55° | 14621.0 | 14874.0 | 14695.3 | 9845.1 | 11013.5 | 16184.9 | 18716.5 | 16883.6 | 10850.9 | 10531.7 | 15743.3 |
| 57.5° | 16070.5 | 16783.2 | 18035.9 | 11872.7 | 12814.2 | 19670.1 | 22697.5 | 20378.7 | 12896.6 | 13488.8 | 19563.7 |
| 60° | 16150.8 | 17094.4 | 20003.3 | 16114.7 | 15131.0 | 22659.3 | 26672.4 | 23793.6 | 16112.7 | 18509.7 | 22556.9 |
| 62.5° | 14940.3 | 15952.1 | 18722.5 | 18041.9 | 17654.5 | 25202.9 | 28712.1 | 26283.0 | 19276.6 | 21450.8 | 21669.6 |
| 65° | 13555.0 | 14576.9 | 17293.1 | 15855.7 | 17361.4 | 25094.5 | 28194.2 | 26341.2 | 19563.7 | 19451.2 | 20081.6 |
| 67.5° | 11461.2 | 12378.6 | 14837.9 | 14034.8 | 16002.3 | 23883.9 | 25801.1 | 24680.9 | 18023.9 | 18192.5 | 18473.6 |
| 70° | 8365.5 | 9248.8 | 11531.4 | 11571.6 | 13974.6 | 21701.7 | 22169.5 | 22014.9 | 16598.5 | 16777.2 | 15974.1 |
| 72.5° | 6042.8 | 6787.6 | 8757.0 | 9489.7 | 11156.0 | 18198.5 | 17875.3 | 18471.5 | 14241.6 | 14942.3 | 12830.3 |
| 75° | 4344.4 | 4902.5 | 6424.2 | 8255.1 | 8843.3 | 13514.9 | 12796.2 | 14305.9 | 11427.0 | 12866.4 | 9646.3 |
| 77.5° | 1762.6 | 1959.4 | 2527.5 | 5560.9 | 5811.9 | 9092.2 | 7833.5 | 10391.1 | 8146.7 | 8453.8 | 4675.6 |
| 80° | 72.3 | 80.3 | 104.4 | 2870.8 | 3985.0 | 5115.3 | 4191.8 | 5554.9 | 5380.3 | 3404.8 | 1104.2 |
| 82.5° | 8.0 | 8.0 | 18.1 | 827.1 | 1744.6 | 2822.6 | 1975.4 | 3200.0 | 2724.3 | 1443.4 | 501.9 |
| 85° | 2.0 | 2.0 | 4.0 | 94.4 | 409.5 | 451.7 | 267.0 | 981.7 | 1266.8 | 590.2 | 0.0 |
| 87.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 10.0 | 18.1 | 20.1 | 0.0 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P642170

CATALOG NUMBER: GWS-SA6C-735-U-SLR-W-HSS

CANDELA DISTRIBUTION (continued):

| | 90° | 95° | 105° | 115° | 125° | 135° | 145° | 155° | 165° | 175° | 180° |
|-------|---------|---------|--------|--------|-------|-------|-------|-------|-------|-------|-------|
| 0° | 903.4 | 903.4 | 903.4 | 903.4 | 903.4 | 903.4 | 903.4 | 903.4 | 903.4 | 903.4 | 903.4 |
| 2.5° | 909.4 | 899.4 | 887.3 | 875.3 | 869.3 | 853.2 | 847.2 | 843.2 | 839.2 | 841.2 | 841.2 |
| 5° | 879.3 | 857.2 | 831.1 | 805.0 | 791.0 | 774.9 | 766.9 | 762.9 | 764.9 | 772.9 | 772.9 |
| 7.5° | 875.3 | 833.1 | 776.9 | 742.8 | 726.7 | 714.7 | 706.7 | 702.6 | 704.7 | 714.7 | 718.7 |
| 10° | 941.5 | 867.3 | 766.9 | 708.7 | 690.6 | 678.6 | 670.5 | 664.5 | 660.5 | 668.5 | 670.5 |
| 12.5° | 1084.1 | 981.7 | 815.1 | 704.7 | 672.5 | 656.5 | 650.4 | 638.4 | 632.4 | 636.4 | 638.4 |
| 15° | 1379.2 | 1202.5 | 911.4 | 720.7 | 656.5 | 638.4 | 628.4 | 618.3 | 608.3 | 606.3 | 608.3 |
| 17.5° | 1764.6 | 1511.7 | 1058.0 | 758.9 | 644.4 | 622.3 | 608.3 | 594.2 | 580.2 | 578.2 | 576.2 |
| 20° | 2242.4 | 1891.1 | 1262.8 | 819.1 | 634.4 | 608.3 | 588.2 | 568.1 | 550.1 | 544.0 | 544.0 |
| 22.5° | 2678.1 | 2348.8 | 1525.7 | 893.4 | 620.3 | 588.2 | 564.1 | 540.0 | 520.0 | 509.9 | 507.9 |
| 25° | 3210.1 | 2834.7 | 1840.9 | 979.7 | 600.3 | 562.1 | 536.0 | 511.9 | 491.9 | 479.8 | 475.8 |
| 27.5° | 3746.1 | 3346.6 | 2198.3 | 1092.1 | 576.2 | 536.0 | 511.9 | 489.8 | 467.8 | 453.7 | 449.7 |
| 30° | 4266.1 | 3898.7 | 2599.8 | 1232.6 | 558.1 | 509.9 | 489.8 | 467.8 | 447.7 | 425.6 | 419.6 |
| 32.5° | 4824.2 | 4462.8 | 3049.5 | 1389.2 | 544.0 | 491.9 | 469.8 | 449.7 | 423.6 | 403.5 | 393.5 |
| 35° | 5362.2 | 5045.0 | 3545.3 | 1541.8 | 530.0 | 475.8 | 451.7 | 431.6 | 403.5 | 381.4 | 367.4 |
| 37.5° | 5904.2 | 5637.2 | 4063.3 | 1634.2 | 509.9 | 453.7 | 431.6 | 415.6 | 383.4 | 357.3 | 341.3 |
| 40° | 6478.4 | 6249.5 | 4623.4 | 1596.0 | 491.9 | 429.6 | 417.6 | 399.5 | 363.4 | 333.3 | 313.2 |
| 42.5° | 7108.8 | 6833.7 | 5193.6 | 1449.5 | 475.8 | 409.5 | 397.5 | 379.4 | 345.3 | 309.2 | 283.1 |
| 45° | 7901.8 | 7474.1 | 5661.3 | 1228.6 | 483.8 | 389.5 | 365.4 | 361.4 | 329.2 | 283.1 | 250.9 |
| 47.5° | 9264.9 | 8457.8 | 6024.7 | 1086.1 | 538.0 | 367.4 | 339.3 | 349.3 | 315.2 | 257.0 | 220.8 |
| 50° | 11350.7 | 10088.0 | 6364.0 | 1076.1 | 620.3 | 357.3 | 315.2 | 341.3 | 301.1 | 230.9 | 194.7 |
| 52.5° | 13338.2 | 11744.2 | 6580.8 | 1164.4 | 692.6 | 383.4 | 291.1 | 331.2 | 291.1 | 212.8 | 176.7 |
| 55° | 15239.4 | 12699.8 | 6193.3 | 1228.6 | 760.9 | 461.7 | 273.0 | 315.2 | 279.1 | 202.8 | 170.6 |
| 57.5° | 17289.1 | 13125.4 | 4876.4 | 1359.1 | 809.0 | 528.0 | 277.0 | 291.1 | 263.0 | 196.7 | 168.6 |
| 60° | 17901.4 | 12581.4 | 2943.1 | 1529.8 | 782.9 | 548.1 | 307.2 | 259.0 | 240.9 | 184.7 | 162.6 |
| 62.5° | 16949.8 | 11290.5 | 1736.5 | 1393.2 | 760.9 | 518.0 | 351.3 | 238.9 | 218.8 | 168.6 | 150.6 |
| 65° | 15526.5 | 9537.9 | 1132.3 | 1176.4 | 807.0 | 461.7 | 373.4 | 228.9 | 198.7 | 152.6 | 132.5 |
| 67.5° | 13900.3 | 7682.9 | 793.0 | 694.6 | 744.8 | 415.6 | 315.2 | 226.9 | 178.7 | 128.5 | 108.4 |
| 70° | 11708.1 | 5753.7 | 558.1 | 459.7 | 620.3 | 369.4 | 244.9 | 220.8 | 156.6 | 104.4 | 84.3 |
| 72.5° | 9046.1 | 3601.6 | 415.6 | 297.1 | 441.7 | 301.1 | 194.7 | 186.7 | 126.5 | 86.3 | 64.2 |
| 75° | 6671.1 | 2053.7 | 293.1 | 214.8 | 291.1 | 228.9 | 144.5 | 132.5 | 108.4 | 82.3 | 58.2 |
| 77.5° | 3483.1 | 1027.9 | 182.7 | 164.6 | 166.6 | 142.5 | 104.4 | 96.4 | 100.4 | 82.3 | 54.2 |
| 80° | 668.5 | 204.8 | 110.4 | 120.5 | 90.3 | 90.3 | 76.3 | 80.3 | 88.3 | 66.2 | 46.2 |
| 82.5° | 279.1 | 44.2 | 60.2 | 68.3 | 56.2 | 62.2 | 62.2 | 64.2 | 62.2 | 48.2 | 34.1 |
| 85° | 0.0 | 0.0 | 26.1 | 28.1 | 38.1 | 38.1 | 32.1 | 32.1 | 32.1 | 28.1 | 20.1 |
| 87.5° | 0.0 | 0.0 | 0.0 | 0.0 | 2.0 | 6.0 | 12.0 | 14.1 | 16.1 | 12.0 | 8.0 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P642170

CATALOG NUMBER: GWS-SA6C-735-U-SLR-W-HSS

CANDELA DISTRIBUTION (continued):

| | 185° | 195° | 205° | 215° | 225° | 235° | 245° | 255° | 265° | 270° | 275° |
|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|
| 0° | 903.4 | 903.4 | 903.4 | 903.4 | 903.4 | 903.4 | 903.4 | 903.4 | 903.4 | 903.4 | 903.4 |
| 2.5° | 839.2 | 835.1 | 841.2 | 845.2 | 849.2 | 849.2 | 845.2 | 841.2 | 835.1 | 841.2 | 835.1 |
| 5° | 774.9 | 780.9 | 791.0 | 795.0 | 799.0 | 791.0 | 787.0 | 774.9 | 764.9 | 766.9 | 762.9 |
| 7.5° | 724.7 | 730.8 | 742.8 | 750.8 | 750.8 | 746.8 | 734.8 | 722.7 | 706.7 | 706.7 | 704.7 |
| 10° | 678.6 | 686.6 | 700.6 | 710.7 | 714.7 | 710.7 | 698.6 | 682.6 | 668.5 | 668.5 | 662.5 |
| 12.5° | 640.4 | 650.4 | 666.5 | 680.6 | 684.6 | 680.6 | 668.5 | 652.5 | 636.4 | 636.4 | 632.4 |
| 15° | 608.3 | 620.3 | 638.4 | 654.5 | 660.5 | 654.5 | 640.4 | 620.3 | 604.3 | 606.3 | 600.3 |
| 17.5° | 578.2 | 588.2 | 612.3 | 630.4 | 636.4 | 630.4 | 612.3 | 586.2 | 570.1 | 574.2 | 570.1 |
| 20° | 544.0 | 556.1 | 580.2 | 600.3 | 606.3 | 600.3 | 580.2 | 552.1 | 536.0 | 536.0 | 538.0 |
| 22.5° | 507.9 | 520.0 | 544.0 | 558.1 | 566.1 | 560.1 | 540.0 | 513.9 | 497.9 | 497.9 | 499.9 |
| 25° | 475.8 | 481.8 | 499.9 | 513.9 | 515.9 | 509.9 | 493.9 | 473.8 | 461.7 | 467.8 | 469.8 |
| 27.5° | 445.7 | 445.7 | 453.7 | 461.7 | 459.7 | 453.7 | 447.7 | 431.6 | 429.6 | 435.6 | 441.7 |
| 30° | 413.6 | 403.5 | 399.5 | 393.5 | 391.5 | 389.5 | 395.5 | 395.5 | 399.5 | 407.5 | 413.6 |
| 32.5° | 385.5 | 365.4 | 347.3 | 329.2 | 319.2 | 327.2 | 343.3 | 357.3 | 371.4 | 383.4 | 389.5 |
| 35° | 353.3 | 321.2 | 291.1 | 267.0 | 250.9 | 263.0 | 289.1 | 315.2 | 339.3 | 355.3 | 365.4 |
| 37.5° | 321.2 | 275.0 | 238.9 | 208.8 | 196.7 | 206.8 | 234.9 | 271.0 | 307.2 | 327.2 | 341.3 |
| 40° | 287.1 | 228.9 | 186.7 | 162.6 | 150.6 | 160.6 | 188.7 | 224.8 | 273.0 | 299.1 | 317.2 |
| 42.5° | 253.0 | 188.7 | 150.6 | 126.5 | 120.5 | 126.5 | 148.6 | 184.7 | 236.9 | 269.0 | 293.1 |
| 45° | 218.8 | 156.6 | 120.5 | 102.4 | 96.4 | 102.4 | 120.5 | 150.6 | 202.8 | 238.9 | 267.0 |
| 47.5° | 188.7 | 132.5 | 100.4 | 84.3 | 80.3 | 86.3 | 100.4 | 126.5 | 170.6 | 206.8 | 238.9 |
| 50° | 164.6 | 116.4 | 86.3 | 72.3 | 68.3 | 74.3 | 86.3 | 106.4 | 144.5 | 176.7 | 210.8 |
| 52.5° | 148.6 | 108.4 | 76.3 | 62.2 | 60.2 | 64.2 | 74.3 | 90.3 | 122.5 | 150.6 | 182.7 |
| 55° | 144.5 | 108.4 | 70.3 | 56.2 | 54.2 | 58.2 | 66.2 | 78.3 | 106.4 | 130.5 | 158.6 |
| 57.5° | 148.6 | 116.4 | 66.2 | 48.2 | 46.2 | 50.2 | 58.2 | 68.3 | 92.3 | 112.4 | 138.5 |
| 60° | 148.6 | 118.4 | 58.2 | 38.1 | 36.1 | 40.2 | 48.2 | 60.2 | 82.3 | 98.4 | 120.5 |
| 62.5° | 134.5 | 108.4 | 48.2 | 30.1 | 26.1 | 30.1 | 40.2 | 50.2 | 72.3 | 88.3 | 106.4 |
| 65° | 116.4 | 92.3 | 40.2 | 22.1 | 18.1 | 22.1 | 32.1 | 42.2 | 62.2 | 76.3 | 96.4 |
| 67.5° | 94.4 | 70.3 | 30.1 | 16.1 | 12.0 | 16.1 | 24.1 | 34.1 | 52.2 | 66.2 | 86.3 |
| 70° | 70.3 | 50.2 | 24.1 | 14.1 | 12.0 | 14.1 | 22.1 | 32.1 | 46.2 | 60.2 | 80.3 |
| 72.5° | 52.2 | 34.1 | 20.1 | 14.1 | 10.0 | 14.1 | 20.1 | 30.1 | 44.2 | 58.2 | 76.3 |
| 75° | 44.2 | 28.1 | 18.1 | 12.0 | 10.0 | 12.0 | 18.1 | 28.1 | 40.2 | 54.2 | 72.3 |
| 77.5° | 42.2 | 26.1 | 16.1 | 10.0 | 8.0 | 10.0 | 16.1 | 24.1 | 36.1 | 50.2 | 70.3 |
| 80° | 36.1 | 22.1 | 14.1 | 8.0 | 6.0 | 8.0 | 14.1 | 20.1 | 28.1 | 38.1 | 54.2 |
| 82.5° | 28.1 | 18.1 | 10.0 | 4.0 | 2.0 | 4.0 | 10.0 | 12.0 | 18.1 | 22.1 | 32.1 |
| 85° | 18.1 | 10.0 | 4.0 | 0.0 | 0.0 | 0.0 | 4.0 | 8.0 | 8.0 | 10.0 | 16.1 |
| 87.5° | 8.0 | 2.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 2.0 | 4.0 | 6.0 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P642170
 CATALOG NUMBER: GWS-SA6C-735-U-SLR-W-HSS

CANDELA DISTRIBUTION (continued):

| | 285° | 295° | 305° | 315° | 325° | 335° | 345° | 355° | 359° | 360° |
|-------|-------|-------|-------|-------|-------|--------|--------|---------|---------|---------|
| 0° | 903.4 | 903.4 | 903.4 | 903.4 | 903.4 | 903.4 | 903.4 | 903.4 | 903.4 | 903.4 |
| 2.5° | 847.2 | 849.2 | 853.2 | 859.2 | 873.3 | 885.3 | 897.4 | 913.4 | 921.5 | 921.5 |
| 5° | 766.9 | 768.9 | 770.9 | 778.9 | 799.0 | 815.1 | 841.2 | 873.3 | 889.3 | 893.4 |
| 7.5° | 704.7 | 708.7 | 712.7 | 718.7 | 738.8 | 760.9 | 795.0 | 855.2 | 885.3 | 891.4 |
| 10° | 668.5 | 674.5 | 682.6 | 694.6 | 712.7 | 736.8 | 795.0 | 903.4 | 953.6 | 963.6 |
| 12.5° | 640.4 | 650.4 | 658.5 | 672.5 | 694.6 | 732.8 | 849.2 | 1039.9 | 1128.2 | 1152.3 |
| 15° | 612.3 | 624.4 | 636.4 | 650.4 | 674.5 | 746.8 | 953.6 | 1284.8 | 1431.4 | 1449.5 |
| 17.5° | 584.2 | 598.3 | 614.3 | 630.4 | 660.5 | 780.9 | 1118.2 | 1624.1 | 1828.9 | 1869.0 |
| 20° | 552.1 | 570.1 | 592.2 | 612.3 | 646.4 | 835.1 | 1347.1 | 2027.6 | 2284.6 | 2370.9 |
| 22.5° | 518.0 | 540.0 | 566.1 | 592.2 | 630.4 | 901.4 | 1624.1 | 2461.3 | 2820.6 | 2876.8 |
| 25° | 489.8 | 511.9 | 536.0 | 562.1 | 604.3 | 981.7 | 1959.4 | 2999.3 | 3326.5 | 3380.7 |
| 27.5° | 463.7 | 485.8 | 507.9 | 532.0 | 578.2 | 1086.1 | 2362.9 | 3571.4 | 3912.7 | 3968.9 |
| 30° | 435.6 | 461.7 | 483.8 | 507.9 | 554.1 | 1214.6 | 2828.7 | 4205.8 | 4529.1 | 4581.2 |
| 32.5° | 411.5 | 437.6 | 459.7 | 483.8 | 536.0 | 1355.1 | 3318.5 | 4768.0 | 5030.9 | 5030.9 |
| 35° | 391.5 | 419.6 | 435.6 | 467.8 | 522.0 | 1445.4 | 3782.2 | 5304.0 | 5502.7 | 5494.7 |
| 37.5° | 369.4 | 403.5 | 415.6 | 437.6 | 503.9 | 1455.5 | 4217.9 | 5870.1 | 6016.7 | 5964.5 |
| 40° | 347.3 | 383.4 | 401.5 | 413.6 | 483.8 | 1373.2 | 4695.7 | 6390.1 | 6514.5 | 6446.3 |
| 42.5° | 327.2 | 355.3 | 381.4 | 395.5 | 471.8 | 1228.6 | 5079.1 | 6946.2 | 7094.7 | 7034.5 |
| 45° | 307.2 | 331.2 | 347.3 | 373.4 | 479.8 | 1128.2 | 5408.4 | 7594.6 | 7855.6 | 7811.4 |
| 47.5° | 287.1 | 307.2 | 317.2 | 357.3 | 534.0 | 1082.1 | 5609.1 | 8598.4 | 9090.2 | 9054.1 |
| 50° | 265.0 | 289.1 | 289.1 | 353.3 | 614.3 | 1098.1 | 5783.8 | 10051.8 | 10812.7 | 10800.7 |
| 52.5° | 242.9 | 269.0 | 265.0 | 383.4 | 676.5 | 1172.4 | 5982.5 | 11334.7 | 12657.7 | 12768.1 |
| 55° | 220.8 | 244.9 | 248.9 | 443.7 | 712.7 | 1236.7 | 5213.6 | 11874.7 | 14233.6 | 14621.0 |
| 57.5° | 196.7 | 210.8 | 259.0 | 489.8 | 700.6 | 1423.4 | 3571.4 | 11973.1 | 15239.4 | 16070.5 |
| 60° | 170.6 | 182.7 | 293.1 | 479.8 | 662.5 | 1315.0 | 2248.5 | 11089.8 | 15096.8 | 16150.8 |
| 62.5° | 148.6 | 168.6 | 309.2 | 423.6 | 674.5 | 1140.3 | 1433.4 | 9451.6 | 13737.7 | 14940.3 |
| 65° | 130.5 | 162.6 | 281.1 | 383.4 | 682.6 | 772.9 | 967.6 | 7688.9 | 12410.7 | 13555.0 |
| 67.5° | 116.4 | 180.7 | 230.9 | 341.3 | 586.2 | 544.0 | 664.5 | 5974.5 | 10435.3 | 11461.2 |
| 70° | 106.4 | 184.7 | 188.7 | 293.1 | 453.7 | 349.3 | 437.6 | 4021.1 | 7193.1 | 8365.5 |
| 72.5° | 96.4 | 136.5 | 142.5 | 234.9 | 293.1 | 212.8 | 283.1 | 2300.7 | 5243.7 | 6042.8 |
| 75° | 92.3 | 92.3 | 98.4 | 152.6 | 162.6 | 154.6 | 182.7 | 1373.2 | 3760.2 | 4344.4 |
| 77.5° | 86.3 | 70.3 | 62.2 | 98.4 | 88.3 | 110.4 | 108.4 | 610.3 | 1630.1 | 1762.6 |
| 80° | 68.3 | 50.2 | 42.2 | 62.2 | 60.2 | 74.3 | 64.2 | 50.2 | 74.3 | 72.3 |
| 82.5° | 42.2 | 32.1 | 30.1 | 38.1 | 34.1 | 38.1 | 30.1 | 8.0 | 8.0 | 8.0 |
| 85° | 20.1 | 18.1 | 16.1 | 16.1 | 18.1 | 16.1 | 12.0 | 4.0 | 2.0 | 2.0 |
| 87.5° | 10.0 | 10.0 | 8.0 | 6.0 | 8.0 | 8.0 | 6.0 | 2.0 | 0.0 | 0.0 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |

LM-79-08: Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Report Prepared for

Cooper Lighting Solutions

All Brands

Data applicable to all product families using SA light engines

Report Number: SP1-2101-121-7

Luminaire Tested: IFLD-S-SA2A-735-U-T2

Test Date: 03/04/2021


Test Information

Test Method: LM-79-08
 Report Number: SP1-2101-121-7
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1
 Measurement Geometry: 4π
 Issue Date: 03/04/2021
 Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
 Product Line: STREETWORKS
 Catalog Number: **IFLD-S-SA2A-735-U-T2**
 Description: STREETWORKS INF FLOOD

PROGRAMMED @ 615mA.

Spectral Parameters

| | | | | | |
|---------------------------|--------|-----------|------|------|-------|
| CCT (K): | 3388 | CRI (Ra): | 73.1 | R9: | -34.6 |
| CIE u': | 0.2371 | R1: | 68.9 | R10: | 57.8 |
| CIE v': | 0.5177 | R2: | 81.1 | R11: | 68.6 |
| Duv: | 0.0032 | R3: | 93.1 | R12: | 53.9 |
| CIE x: | 0.4153 | R4: | 71.6 | R13: | 70.9 |
| CIE y: | 0.4030 | R5: | 69.4 | R14: | 96.2 |
| CIE z: | 0.1817 | R6: | 75.0 | | |
| Peak Wavelength (nm): | 590 | R7: | 79.5 | | |
| Dominant Wavelength (nm): | 580 | R8: | 46.4 | | |
| Purity: | 45.7 | | | | |
| Rf: | 76.9 | | | | |
| Rg: | 94.4 | | | | |



Test Conditions


Stabilization Time: 81M
 Operation Time: 12H
 Room Temperature (°C) / RH%: 25.0/30%
 Sphere Temperature (°C): 24.1

REPORT NUMBER: SP1-2101-121-7

| Measurement and Test Equipment | | | |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument | Identification Number | Calibration Date | Calibration Due Date |
| Photometer | IN0058 | 1/31/2021 | 7/31/2021 |
| Power Meter | IN0071 | 12/1/2020 | 12/1/2021 |
| AC Power Source | IN0063 | 12/1/2020 | 12/1/2021 |
| DC Power Source | IN0208 | 12/1/2020 | 12/1/2021 |
| Sphere Thermometer | IN0085 | 12/1/2020 | 12/1/2021 |
| Room Thermometer | IN0046 | 12/1/2020 | 12/1/2021 |

REPORT NUMBER: SP1-2101-121-7

CIE 1931 Chromaticity Diagram




CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 3500K 4-step quadrangle

REPORT NUMBER: SP1-2101-121-7

Photopic Flux vs. Wavelength



#####

| λ (nm) | Power (µW/nm) | Lumens (Φ/nm) | λ (nm) | Power (µW/nm) | Lumens (Φ/nm) | λ (nm) | Power (µW/nm) | Lumens (Φ/nm) | λ (nm) | Power (µW/nm) | Lumens (Φ/nm) | λ (nm) | Power (µW/nm) | Lumens (Φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 2672 | 0.0 | 490 | 34553 | 4.9 | 620 | 136720 | 35.6 | 750 | 5870 | 0.0 | 880 | 4216 | 0.0 |
| 365 | 2252 | 0.0 | 495 | 44336 | 8.0 | 625 | 126308 | 27.9 | 755 | 5421 | 0.0 | 885 | 4132 | 0.0 |
| 370 | 2217 | 0.0 | 500 | 54643 | 12.1 | 630 | 114625 | 20.7 | 760 | 5097 | 0.0 | 890 | 3992 | 0.0 |
| 375 | 2697 | 0.0 | 505 | 64676 | 18.1 | 635 | 103216 | 15.5 | 765 | 4626 | 0.0 | 895 | 3214 | 0.0 |
| 380 | 3039 | 0.0 | 510 | 73825 | 25.4 | 640 | 92605 | 11.1 | 770 | 3782 | 0.0 | 900 | 2580 | 0.0 |
| 385 | 2655 | 0.0 | 515 | 81872 | 33.9 | 645 | 83234 | 8.0 | 775 | 3506 | 0.0 | 905 | 1776 | 0.0 |
| 390 | 2357 | 0.0 | 520 | 88574 | 43.0 | 650 | 73263 | 5.4 | 780 | 3507 | 0.0 | 910 | 3995 | 0.0 |
| 395 | 2186 | 0.0 | 525 | 93289 | 50.1 | 655 | 64627 | 3.7 | 785 | 3267 | 0.0 | 915 | 4288 | 0.0 |
| 400 | 2015 | 0.0 | 530 | 98393 | 57.9 | 660 | 56614 | 2.4 | 790 | 2849 | 0.0 | 920 | 2446 | 0.0 |
| 405 | 2234 | 0.0 | 535 | 103269 | 64.0 | 665 | 49537 | 1.6 | 795 | 3037 | 0.0 | 925 | 3009 | 0.0 |
| 410 | 3412 | 0.0 | 540 | 107316 | 69.9 | 670 | 42866 | 0.9 | 800 | 2716 | 0.0 | 930 | 3026 | 0.0 |
| 415 | 6135 | 0.0 | 545 | 113101 | 75.3 | 675 | 36708 | 0.6 | 805 | 2648 | 0.0 | 935 | 4734 | 0.0 |
| 420 | 12146 | 0.0 | 550 | 120690 | 82.0 | 680 | 31814 | 0.4 | 810 | 3187 | 0.0 | 940 | 3719 | 0.0 |
| 425 | 23983 | 0.1 | 555 | 128583 | 87.8 | 685 | 27485 | 0.2 | 815 | 2931 | 0.0 | 945 | 1480 | 0.0 |
| 430 | 42142 | 0.3 | 560 | 137796 | 93.6 | 690 | 23698 | 0.1 | 820 | 2717 | 0.0 | 950 | 3450 | 0.0 |
| 435 | 68228 | 0.8 | 565 | 146577 | 97.5 | 695 | 20309 | 0.1 | 825 | 2236 | 0.0 | 955 | 5051 | 0.0 |
| 440 | 99323 | 1.6 | 570 | 154581 | 100.5 | 700 | 17890 | 0.1 | 830 | 2628 | 0.0 | 960 | 3176 | 0.0 |
| 445 | 115584 | 2.4 | 575 | 162633 | 101.2 | 705 | 15500 | 0.0 | 835 | 3140 | 0.0 | 965 | 5178 | 0.0 |
| 450 | 94997 | 2.5 | 580 | 168101 | 99.9 | 710 | 13699 | 0.0 | 840 | 3675 | 0.0 | 970 | 6385 | 0.0 |
| 455 | 61433 | 2.1 | 585 | 173145 | 96.2 | 715 | 12398 | 0.0 | 845 | 3283 | 0.0 | 975 | 3810 | 0.0 |
| 460 | 43373 | 1.8 | 590 | 174675 | 90.3 | 720 | 11147 | 0.0 | 850 | 3055 | 0.0 | 980 | 4322 | 0.0 |
| 465 | 32472 | 1.7 | 595 | 173724 | 82.3 | 725 | 9761 | 0.0 | 855 | 2932 | 0.0 | 985 | 4200 | 0.0 |
| 470 | 24257 | 1.5 | 600 | 171241 | 73.8 | 730 | 8651 | 0.0 | 860 | 3382 | 0.0 | 990 | 4661 | 0.0 |
| 475 | 21690 | 1.7 | 605 | 165134 | 64.0 | 735 | 7730 | 0.0 | 865 | 2605 | 0.0 | 995 | 6746 | 0.0 |
| 480 | 23173 | 2.2 | 610 | 156652 | 53.8 | 740 | 6847 | 0.0 | 870 | 3325 | 0.0 | 1000 | 4150 | 0.0 |
| 485 | 27564 | 3.3 | 615 | 147879 | 44.6 | 745 | 6124 | 0.0 | 875 | 3325 | 0.0 | | | |

REPORT NUMBER: SP1-2101-121-7

Scotopic Flux vs. Wavelength




Scotopic Lumens: 12126

S/P: 1.36

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 2672 | 0.0 | 490 | 34553 | 53.2 | 620 | 136720 | 1.7 | 750 | 5870 | 0.0 | 880 | 4216 | 0.0 |
| 365 | 2252 | 0.0 | 495 | 44336 | 71.7 | 625 | 126308 | 1.1 | 755 | 5421 | 0.0 | 885 | 4132 | 0.0 |
| 370 | 2217 | 0.0 | 500 | 54643 | 91.4 | 630 | 114625 | 0.6 | 760 | 5097 | 0.0 | 890 | 3992 | 0.0 |
| 375 | 2697 | 0.0 | 505 | 64676 | 110.0 | 635 | 103216 | 0.4 | 765 | 4626 | 0.0 | 895 | 3214 | 0.0 |
| 380 | 3039 | 0.0 | 510 | 73825 | 125.1 | 640 | 92605 | 0.2 | 770 | 3782 | 0.0 | 900 | 2580 | 0.0 |
| 385 | 2655 | 0.0 | 515 | 81872 | 135.7 | 645 | 83234 | 0.1 | 775 | 3506 | 0.0 | 905 | 1776 | 0.0 |
| 390 | 2357 | 0.0 | 520 | 88574 | 140.8 | 650 | 73263 | 0.1 | 780 | 3507 | 0.0 | 910 | 3995 | 0.0 |
| 395 | 2186 | 0.0 | 525 | 93289 | 139.6 | 655 | 64627 | 0.1 | 785 | 3267 | 0.0 | 915 | 4288 | 0.0 |
| 400 | 2015 | 0.0 | 530 | 98393 | 135.7 | 660 | 56614 | 0.0 | 790 | 2849 | 0.0 | 920 | 2446 | 0.0 |
| 405 | 2234 | 0.1 | 535 | 103269 | 128.7 | 665 | 49537 | 0.0 | 795 | 3037 | 0.0 | 925 | 3009 | 0.0 |
| 410 | 3412 | 0.2 | 540 | 107316 | 118.6 | 670 | 42866 | 0.0 | 800 | 2716 | 0.0 | 930 | 3026 | 0.0 |
| 415 | 6135 | 0.6 | 545 | 113101 | 108.4 | 675 | 36708 | 0.0 | 805 | 2648 | 0.0 | 935 | 4734 | 0.0 |
| 420 | 12146 | 2.0 | 550 | 120690 | 98.7 | 680 | 31814 | 0.0 | 810 | 3187 | 0.0 | 940 | 3719 | 0.0 |
| 425 | 23983 | 5.9 | 555 | 128583 | 87.9 | 685 | 27485 | 0.0 | 815 | 2931 | 0.0 | 945 | 1480 | 0.0 |
| 430 | 42142 | 14.3 | 560 | 137796 | 77.0 | 690 | 23698 | 0.0 | 820 | 2717 | 0.0 | 950 | 3450 | 0.0 |
| 435 | 68228 | 30.5 | 565 | 146577 | 65.8 | 695 | 20309 | 0.0 | 825 | 2236 | 0.0 | 955 | 5051 | 0.0 |
| 440 | 99323 | 55.5 | 570 | 154581 | 54.6 | 700 | 17890 | 0.0 | 830 | 2628 | 0.0 | 960 | 3176 | 0.0 |
| 445 | 115584 | 77.4 | 575 | 162633 | 44.3 | 705 | 15500 | 0.0 | 835 | 3140 | 0.0 | 965 | 5178 | 0.0 |
| 450 | 94997 | 73.6 | 580 | 168101 | 34.6 | 710 | 13699 | 0.0 | 840 | 3675 | 0.0 | 970 | 6385 | 0.0 |
| 455 | 61433 | 53.7 | 585 | 173145 | 26.5 | 715 | 12398 | 0.0 | 845 | 3283 | 0.0 | 975 | 3810 | 0.0 |
| 460 | 43373 | 41.9 | 590 | 174675 | 19.5 | 720 | 11147 | 0.0 | 850 | 3055 | 0.0 | 980 | 4322 | 0.0 |
| 465 | 32472 | 34.3 | 595 | 173724 | 13.9 | 725 | 9761 | 0.0 | 855 | 2932 | 0.0 | 985 | 4200 | 0.0 |
| 470 | 24257 | 27.9 | 600 | 171241 | 9.7 | 730 | 8651 | 0.0 | 860 | 3382 | 0.0 | 990 | 4661 | 0.0 |
| 475 | 21690 | 27.1 | 605 | 165134 | 6.5 | 735 | 7730 | 0.0 | 865 | 2605 | 0.0 | 995 | 6746 | 0.0 |
| 480 | 23173 | 31.3 | 610 | 156652 | 4.2 | 740 | 6847 | 0.0 | 870 | 3325 | 0.0 | 1000 | 4150 | 0.0 |
| 485 | 27564 | 40.0 | 615 | 147879 | 2.7 | 745 | 6124 | 0.0 | 875 | 3325 | 0.0 | | | |

REPORT NUMBER: SP1-2101-121-7

Melanopic Flux vs. Wavelength



Melanopic Lumens: 4490.7 M/P: 0.5

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 2672 | 0.0 | 490 | 34553 | 28.8 | 620 | 136720 | 0.1 | 750 | 5870 | 0.0 | 880 | 4216 | 0.0 |
| 365 | 2252 | 0.0 | 495 | 44336 | 36.6 | 625 | 126308 | 0.1 | 755 | 5421 | 0.0 | 885 | 4132 | 0.0 |
| 370 | 2217 | 0.0 | 500 | 54643 | 43.9 | 630 | 114625 | 0.0 | 760 | 5097 | 0.0 | 890 | 3992 | 0.0 |
| 375 | 2697 | 0.0 | 505 | 64676 | 49.6 | 635 | 103216 | 0.0 | 765 | 4626 | 0.0 | 895 | 3214 | 0.0 |
| 380 | 3039 | 0.0 | 510 | 73825 | 53.0 | 640 | 92605 | 0.0 | 770 | 3782 | 0.0 | 900 | 2580 | 0.0 |
| 385 | 2655 | 0.0 | 515 | 81872 | 53.5 | 645 | 83234 | 0.0 | 775 | 3506 | 0.0 | 905 | 1776 | 0.0 |
| 390 | 2357 | 0.0 | 520 | 88574 | 51.6 | 650 | 73263 | 0.0 | 780 | 3507 | 0.0 | 910 | 3995 | 0.0 |
| 395 | 2186 | 0.0 | 525 | 93289 | 47.3 | 655 | 64627 | 0.0 | 785 | 3267 | 0.0 | 915 | 4288 | 0.0 |
| 400 | 2015 | 0.0 | 530 | 98393 | 42.5 | 660 | 56614 | 0.0 | 790 | 2849 | 0.0 | 920 | 2446 | 0.0 |
| 405 | 2234 | 0.0 | 535 | 103269 | 37.2 | 665 | 49537 | 0.0 | 795 | 3037 | 0.0 | 925 | 3009 | 0.0 |
| 410 | 3412 | 0.1 | 540 | 107316 | 31.4 | 670 | 42866 | 0.0 | 800 | 2716 | 0.0 | 930 | 3026 | 0.0 |
| 415 | 6135 | 0.4 | 545 | 113101 | 26.3 | 675 | 36708 | 0.0 | 805 | 2648 | 0.0 | 935 | 4734 | 0.0 |
| 420 | 12146 | 1.4 | 550 | 120690 | 21.7 | 680 | 31814 | 0.0 | 810 | 3187 | 0.0 | 940 | 3719 | 0.0 |
| 425 | 23983 | 3.7 | 555 | 128583 | 17.3 | 685 | 27485 | 0.0 | 815 | 2931 | 0.0 | 945 | 1480 | 0.0 |
| 430 | 42142 | 8.9 | 560 | 137796 | 13.6 | 690 | 23698 | 0.0 | 820 | 2717 | 0.0 | 950 | 3450 | 0.0 |
| 435 | 68228 | 18.2 | 565 | 146577 | 10.3 | 695 | 20309 | 0.0 | 825 | 2236 | 0.0 | 955 | 5051 | 0.0 |
| 440 | 99323 | 33.2 | 570 | 154581 | 7.6 | 700 | 17890 | 0.0 | 830 | 2628 | 0.0 | 960 | 3176 | 0.0 |
| 445 | 115584 | 45.6 | 575 | 162633 | 5.4 | 705 | 15500 | 0.0 | 835 | 3140 | 0.0 | 965 | 5178 | 0.0 |
| 450 | 94997 | 43.8 | 580 | 168101 | 3.8 | 710 | 13699 | 0.0 | 840 | 3675 | 0.0 | 970 | 6385 | 0.0 |
| 455 | 61433 | 32.2 | 585 | 173145 | 2.6 | 715 | 12398 | 0.0 | 845 | 3283 | 0.0 | 975 | 3810 | 0.0 |
| 460 | 43373 | 25.6 | 590 | 174675 | 1.7 | 720 | 11147 | 0.0 | 850 | 3055 | 0.0 | 980 | 4322 | 0.0 |
| 465 | 32472 | 21.2 | 595 | 173724 | 1.1 | 725 | 9761 | 0.0 | 855 | 2932 | 0.0 | 985 | 4200 | 0.0 |
| 470 | 24257 | 17.4 | 600 | 171241 | 0.7 | 730 | 8651 | 0.0 | 860 | 3382 | 0.0 | 990 | 4661 | 0.0 |
| 475 | 21690 | 16.6 | 605 | 165134 | 0.5 | 735 | 7730 | 0.0 | 865 | 2605 | 0.0 | 995 | 6746 | 0.0 |
| 480 | 23173 | 18.6 | 610 | 156652 | 0.3 | 740 | 6847 | 0.0 | 870 | 3325 | 0.0 | 1000 | 4150 | 0.0 |
| 485 | 27564 | 22.7 | 615 | 147879 | 0.2 | 745 | 6124 | 0.0 | 875 | 3325 | 0.0 | | | |

Summary

$R_f = 76.9$
 $R_g = 94.4$
 $CIE R_a = 73.1$
 $R_g = -34.6$



Color Vector Graphics



Individual Sample Fidelity Index ($R_{f,i}$)

| | | | |
|------------|------------|------------|------------|
| CES01 = 86 | CES26 = 68 | CES51 = 90 | CES76 = 63 |
| CES02 = 62 | CES27 = 88 | CES52 = 89 | CES77 = 80 |
| CES03 = 31 | CES28 = 87 | CES53 = 80 | CES78 = 65 |
| CES04 = 70 | CES29 = 67 | CES54 = 84 | CES79 = 87 |
| CES05 = 48 | CES30 = 74 | CES55 = 84 | CES80 = 86 |
| CES06 = 51 | CES31 = 71 | CES56 = 75 | CES81 = 75 |
| CES07 = 40 | CES32 = 67 | CES57 = 74 | CES82 = 94 |
| CES08 = 39 | CES33 = 74 | CES58 = 76 | CES83 = 91 |
| CES09 = 29 | CES34 = 78 | CES59 = 87 | CES84 = 89 |
| CES10 = 75 | CES35 = 89 | CES60 = 93 | CES85 = 80 |
| CES11 = 58 | CES36 = 98 | CES61 = 86 | CES86 = 66 |
| CES12 = 64 | CES37 = 86 | CES62 = 89 | CES87 = 79 |
| CES13 = 43 | CES38 = 82 | CES63 = 77 | CES88 = 79 |
| CES14 = 74 | CES39 = 95 | CES64 = 74 | CES89 = 70 |
| CES15 = 71 | CES40 = 91 | CES65 = 68 | CES90 = 77 |
| CES16 = 47 | CES41 = 89 | CES66 = 71 | CES91 = 88 |
| CES17 = 50 | CES42 = 88 | CES67 = 69 | CES92 = 60 |
| CES18 = 56 | CES43 = 82 | CES68 = 74 | CES93 = 77 |
| CES19 = 72 | CES44 = 99 | CES69 = 82 | CES94 = 52 |
| CES20 = 65 | CES45 = 87 | CES70 = 67 | CES95 = 69 |
| CES21 = 86 | CES46 = 82 | CES71 = 66 | CES96 = 78 |
| CES22 = 79 | CES47 = 82 | CES72 = 88 | CES97 = 85 |
| CES23 = 92 | CES48 = 72 | CES73 = 59 | CES98 = 76 |
| CES24 = 91 | CES49 = 82 | CES74 = 97 | CES99 = 63 |
| CES25 = 72 | CES50 = 88 | CES75 = 66 | |



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)