

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: McGRAW-EDISON

Report Number: P635211

Luminaire Tested: GWS-SA3D-735-U-5NQ-W-GRSBK

Issue Date: 1/10/2023

**Test Information**

Test Method: LM-79-2019  
Report Number: P635211  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2209-782-8)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 1/10/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: McGRAW-EDISON  
Catalog Number: GWS-SA3D-735-U-5NQ-W-GRSBK  
Description: GALLEON WALL SLIM LUMINAIRE. (3) LIGHTSQUARES WITH 16 LEDS EACH AND TYPE V NARROW OPTICS W/ FACTORY INSTALLED GLARE SHIELD, BK  
Light Source: (48) 3500K CCT, 70 CRI LEDS  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 12213.7 lumens  
Efficiency: N/A  
Efficacy: 101.1 lumens/watt  
Luminous Opening: Rectangular (W 1.5' x L: 0.5' x H: 0')  
IES Classification: Type V - Short  
BUG Rating: B3 - U0 - G0  
  
Input Watts (W): 120.8  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 0  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 28.75 FT



REPORT NUMBER: P635211  
 CATALOG NUMBER: GWS-SA3D-735-U-5NQ-W-GRSBK

### Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd  
 - - - 1/2 Max cd



Based on 20 foot mounting height. Maximum calculated value = 5 fc  
 Type V - Short - N/A

REPORT NUMBER: P635211  
CATALOG NUMBER: GWS-SA3D-735-U-5NQ-W-GRSBK

### Luminous Intensity Polar Plot



— Vertical Plane Through 45-Deg Lateral    - - - Horizontal Cone Through 55-Deg Vertical

REPORT NUMBER: P635211

CATALOG NUMBER: GWS-SA3D-735-U-5NQ-W-GRSBK


**FLUX DISTRIBUTION:**

|                    |           | Downward | Upward | Total   |
|--------------------|-----------|----------|--------|---------|
| <b>House Side</b>  | Lumens    | 6106.9   | 0.0    | 6106.9  |
|                    | % Fixture | 50.0     | 0.0    | 50.0    |
| <b>Street Side</b> | Lumens    | 6106.9   | 0.0    | 6106.9  |
|                    | % Fixture | 50.0     | 0.0    | 50.0    |
| <b>Total</b>       | Lumens    | 12213.7  | 0.0    | 12213.7 |
|                    | % Fixture | 100.0    | 0.0    | 100.0   |

**ZONAL LUMENS:**

| Zone      | Lumens  | % Fixture |
|-----------|---------|-----------|
| 0°-10°    | 193.5   | 1.6       |
| 10°-20°   | 627.2   | 5.1       |
| 20°-30°   | 1214.6  | 9.9       |
| 30°-40°   | 2176.0  | 17.8      |
| 40°-50°   | 3648.3  | 29.9      |
| 50°-60°   | 3905.3  | 32.0      |
| 60°-70°   | 429.1   | 3.5       |
| 70°-80°   | 18.9    | 0.2       |
| 80°-90°   | 0.9     | 0.0       |
| 90°-100°  | 0.0     | 0.0       |
| 100°-110° | 0.0     | 0.0       |
| 110°-120° | 0.0     | 0.0       |
| 120°-130° | 0.0     | 0.0       |
| 130°-140° | 0.0     | 0.0       |
| 140°-150° | 0.0     | 0.0       |
| 150°-160° | 0.0     | 0.0       |
| 160°-170° | 0.0     | 0.0       |
| 170°-180° | 0.0     | 0.0       |
| 0°-90°    | 12213.7 | 100.0     |
| 0°-180°   | 12213.7 | 100.0     |

**Coefficient of Utilization**



REPORT NUMBER: P635211


CATALOG NUMBER: GWS-SA3D-735-U-5NQ-W-GRSBK

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

| Zone           | Lumens | % Fixture | Zone Rating/Lumen Limit |      |        |
|----------------|--------|-----------|-------------------------|------|--------|
|                |        |           | B                       | U    | G      |
| FL (0°-30°)    | 1017.6 | 8.3       |                         |      |        |
| FM (30°-60°)   | 4864.8 | 39.8      |                         |      |        |
| FH (60°-80°)   | 224.0  | 1.8       |                         |      | G0/660 |
| FVH (80°-90°)  | 0.4    | 0.0       |                         |      | G0/10  |
| BL (0°-30°)    | 1017.6 | 8.3       | B3/2500                 |      |        |
| BM (30°-60°)   | 4864.8 | 39.8      | B3/5000                 |      |        |
| BH (60°-80°)   | 224.0  | 1.8       | B1/500                  |      | G0/660 |
| BVH (80°-90°)  | 0.4    | 0.0       |                         |      | G0/10  |
| UL (90°-100°)  | 0.0    | 0.0       |                         | U0/0 |        |
| UH (100°-180°) | 0.0    | 0.0       |                         | U0/0 |        |

**BUG Rating: B3-U0-G0**

Type V Short





REPORT NUMBER: P635211  
 CATALOG NUMBER: GWS-SA3D-735-U-5NQ-W-GRSBK

**CANDELA DISTRIBUTION (FULL):**

|       | 0°     | 5°     | 15°    | 25°    | 35°    | 45°    | 55°    | 65°    | 75°    | 85°    | 90°    |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°    | 1974.7 | 1974.7 | 1974.7 | 1974.7 | 1974.7 | 1974.7 | 1974.7 | 1974.7 | 1974.7 | 1974.7 | 1974.7 |
| 2.5°  | 1971.0 | 1971.0 | 1976.0 | 1979.7 | 1979.7 | 1989.7 | 1985.9 | 1982.2 | 1982.2 | 1977.2 | 1987.2 |
| 5°    | 1999.6 | 1998.4 | 2003.4 | 2005.8 | 2000.9 | 2010.8 | 2004.6 | 2000.9 | 1998.4 | 1993.4 | 2003.4 |
| 7.5°  | 2030.7 | 2032.0 | 2033.2 | 2038.2 | 2035.7 | 2045.7 | 2040.7 | 2033.2 | 2030.7 | 2023.3 | 2033.2 |
| 10°   | 2068.1 | 2068.1 | 2070.5 | 2076.8 | 2078.0 | 2090.5 | 2085.5 | 2076.8 | 2069.3 | 2061.8 | 2071.8 |
| 12.5° | 2115.3 | 2116.6 | 2120.3 | 2129.0 | 2134.0 | 2147.7 | 2140.2 | 2122.8 | 2111.6 | 2102.9 | 2114.1 |
| 15°   | 2183.8 | 2182.5 | 2187.5 | 2200.0 | 2206.2 | 2216.1 | 2204.9 | 2181.3 | 2167.6 | 2157.7 | 2165.1 |
| 17.5° | 2258.4 | 2258.4 | 2260.9 | 2273.4 | 2282.1 | 2297.0 | 2283.3 | 2254.7 | 2242.3 | 2228.6 | 2236.0 |
| 20°   | 2340.6 | 2344.3 | 2346.8 | 2355.5 | 2370.4 | 2385.4 | 2374.2 | 2345.5 | 2331.9 | 2314.4 | 2323.1 |
| 22.5° | 2448.8 | 2445.1 | 2446.3 | 2461.3 | 2482.4 | 2497.4 | 2488.6 | 2455.0 | 2431.4 | 2417.7 | 2422.7 |
| 25°   | 2569.5 | 2568.3 | 2572.0 | 2594.4 | 2618.0 | 2634.2 | 2621.8 | 2578.2 | 2554.6 | 2530.9 | 2540.9 |
| 27.5° | 2717.6 | 2718.8 | 2721.3 | 2748.7 | 2786.0 | 2809.7 | 2778.6 | 2735.0 | 2702.7 | 2671.6 | 2679.0 |
| 30°   | 2893.0 | 2890.6 | 2898.0 | 2935.4 | 2990.1 | 3027.4 | 2991.3 | 2930.4 | 2884.3 | 2854.5 | 2858.2 |
| 32.5° | 3079.7 | 3082.2 | 3102.1 | 3161.8 | 3234.0 | 3299.9 | 3226.5 | 3145.6 | 3085.9 | 3029.9 | 3037.4 |
| 35°   | 3281.3 | 3287.5 | 3332.3 | 3420.6 | 3538.8 | 3627.2 | 3525.2 | 3392.0 | 3307.4 | 3235.2 | 3237.7 |
| 37.5° | 3518.9 | 3533.9 | 3596.1 | 3728.0 | 3897.2 | 4015.4 | 3866.1 | 3689.4 | 3579.9 | 3490.3 | 3484.1 |
| 40°   | 3831.3 | 3848.7 | 3933.3 | 4090.1 | 4295.4 | 4403.6 | 4230.7 | 4049.0 | 3913.4 | 3816.3 | 3801.4 |
| 42.5° | 4189.6 | 4212.0 | 4304.1 | 4464.6 | 4669.9 | 4743.3 | 4574.1 | 4421.1 | 4299.1 | 4184.6 | 4179.7 |
| 45°   | 4594.0 | 4606.5 | 4681.1 | 4804.3 | 4952.4 | 4969.8 | 4842.9 | 4758.3 | 4635.1 | 4528.1 | 4519.4 |
| 47.5° | 4973.5 | 4986.0 | 5037.0 | 5100.5 | 5135.3 | 5073.1 | 5050.7 | 5013.4 | 4854.1 | 4722.2 | 4694.8 |
| 50°   | 5262.2 | 5272.2 | 5335.6 | 5360.5 | 5263.5 | 5131.6 | 5175.1 | 5095.5 | 4922.5 | 4774.5 | 4732.1 |
| 52.5° | 5242.3 | 5267.2 | 5430.2 | 5572.1 | 5511.1 | 5404.1 | 5287.1 | 5115.4 | 4846.6 | 4643.8 | 4591.5 |
| 55°   | 4513.1 | 4546.7 | 4896.4 | 5363.0 | 5779.9 | 5825.9 | 5358.0 | 4804.3 | 4299.1 | 4001.7 | 3948.2 |
| 57.5° | 2900.5 | 2909.2 | 3336.0 | 3990.5 | 4930.0 | 5226.1 | 4443.5 | 3622.2 | 2993.8 | 2666.6 | 2644.2 |
| 60°   | 1066.4 | 1049.0 | 1371.2 | 1913.8 | 2839.5 | 3153.1 | 2615.6 | 1831.6 | 1306.5 | 1075.1 | 1056.4 |
| 62.5° | 256.3  | 258.8  | 321.0  | 481.6  | 890.9  | 1102.5 | 871.0  | 486.5  | 309.8  | 260.1  | 257.6  |
| 65°   | 129.4  | 126.9  | 128.2  | 138.1  | 190.4  | 227.7  | 186.6  | 131.9  | 126.9  | 128.2  | 126.9  |
| 67.5° | 83.4   | 82.1   | 84.6   | 85.9   | 84.6   | 79.6   | 78.4   | 80.9   | 80.9   | 82.1   | 79.6   |
| 70°   | 51.0   | 49.8   | 52.3   | 56.0   | 53.5   | 47.3   | 49.8   | 52.3   | 49.8   | 48.5   | 48.5   |
| 72.5° | 27.4   | 27.4   | 29.9   | 32.4   | 29.9   | 27.4   | 27.4   | 28.6   | 27.4   | 27.4   | 27.4   |
| 75°   | 12.4   | 12.4   | 13.7   | 14.9   | 12.4   | 12.4   | 12.4   | 12.4   | 12.4   | 12.4   | 12.4   |
| 77.5° | 3.7    | 3.7    | 5.0    | 5.0    | 3.7    | 3.7    | 3.7    | 3.7    | 5.0    | 5.0    | 5.0    |
| 80°   | 1.2    | 2.5    | 2.5    | 1.2    | 1.2    | 1.2    | 1.2    | 1.2    | 2.5    | 2.5    | 2.5    |
| 82.5° | 1.2    | 1.2    | 1.2    | 1.2    | 1.2    | 1.2    | 1.2    | 1.2    | 1.2    | 1.2    | 1.2    |
| 85°   | 1.2    | 1.2    | 1.2    | 0.0    | 0.0    | 0.0    | 0.0    | 1.2    | 1.2    | 1.2    | 1.2    |
| 87.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 1.2    | 1.2    | 1.2    | 1.2    |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |

LM-79-08: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

All Brands

Data applicable to all product families using SA light engines

Report Number: SP1-2101-121-7

Luminaire Tested: IFLD-S-SA2A-735-U-T2

Test Date: 03/04/2021



**Test Information**

Test Method: LM-79-08  
 Report Number: SP1-2101-121-7  
 Test Lab: COOPER LIGHTING SOLUTIONS  
 Photometer: SP1  
 Measurement Geometry: 4π  
 Issue Date: 03/04/2021  
 Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
 Product Line: STREETWORKS  
 Catalog Number: **IFLD-S-SA2A-735-U-T2**  
 Description: STREETWORKS INF FLOOD

PROGRAMMED @ 615mA.

**Spectral Parameters**

|                           |        |           |      |      |       |
|---------------------------|--------|-----------|------|------|-------|
| CCT (K):                  | 3388   | CRI (Ra): | 73.1 | R9:  | -34.6 |
| CIE u':                   | 0.2371 | R1:       | 68.9 | R10: | 57.8  |
| CIE v':                   | 0.5177 | R2:       | 81.1 | R11: | 68.6  |
| Duv:                      | 0.0032 | R3:       | 93.1 | R12: | 53.9  |
| CIE x:                    | 0.4153 | R4:       | 71.6 | R13: | 70.9  |
| CIE y:                    | 0.4030 | R5:       | 69.4 | R14: | 96.2  |
| CIE z:                    | 0.1817 | R6:       | 75.0 |      |       |
| Peak Wavelength (nm):     | 590    | R7:       | 79.5 |      |       |
| Dominant Wavelength (nm): | 580    | R8:       | 46.4 |      |       |
| Purity:                   | 45.7   |           |      |      |       |
| Rf:                       | 76.9   |           |      |      |       |
| Rg:                       | 94.4   |           |      |      |       |



**Test Conditions**

Stabilization Time: 81M  
 Operation Time: 12H  
 Room Temperature (°C) / RH%: 25.0/30%  
 Sphere Temperature (°C): 24.1

REPORT NUMBER: SP1-2101-121-7

| Measurement and Test Equipment |                       |                  |                      |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument                     | Identification Number | Calibration Date | Calibration Due Date |
| Photometer                     | IN0058                | 1/31/2021        | 7/31/2021            |
| Power Meter                    | IN0071                | 12/1/2020        | 12/1/2021            |
| AC Power Source                | IN0063                | 12/1/2020        | 12/1/2021            |
| DC Power Source                | IN0208                | 12/1/2020        | 12/1/2021            |
| Sphere Thermometer             | IN0085                | 12/1/2020        | 12/1/2021            |
| Room Thermometer               | IN0046                | 12/1/2020        | 12/1/2021            |

REPORT NUMBER: SP1-2101-121-7

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



CCT = 3388K  
 CIE x = 0.4153  
 CIE y = 0.4030  
 Duv = 0.0032

Point lies inside the ANSI 3500K 4-step quadrangle

REPORT NUMBER: SP1-2101-121-7

**Photopic Flux vs. Wavelength**



#####

| λ (nm) | Power (µW/nm) | Lumens (Φ/nm) | λ (nm) | Power (µW/nm) | Lumens (Φ/nm) | λ (nm) | Power (µW/nm) | Lumens (Φ/nm) | λ (nm) | Power (µW/nm) | Lumens (Φ/nm) | λ (nm) | Power (µW/nm) | Lumens (Φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360    | 2672          | 0.0           | 490    | 34553         | 4.9           | 620    | 136720        | 35.6          | 750    | 5870          | 0.0           | 880    | 4216          | 0.0           |
| 365    | 2252          | 0.0           | 495    | 44336         | 8.0           | 625    | 126308        | 27.9          | 755    | 5421          | 0.0           | 885    | 4132          | 0.0           |
| 370    | 2217          | 0.0           | 500    | 54643         | 12.1          | 630    | 114625        | 20.7          | 760    | 5097          | 0.0           | 890    | 3992          | 0.0           |
| 375    | 2697          | 0.0           | 505    | 64676         | 18.1          | 635    | 103216        | 15.5          | 765    | 4626          | 0.0           | 895    | 3214          | 0.0           |
| 380    | 3039          | 0.0           | 510    | 73825         | 25.4          | 640    | 92605         | 11.1          | 770    | 3782          | 0.0           | 900    | 2580          | 0.0           |
| 385    | 2655          | 0.0           | 515    | 81872         | 33.9          | 645    | 83234         | 8.0           | 775    | 3506          | 0.0           | 905    | 1776          | 0.0           |
| 390    | 2357          | 0.0           | 520    | 88574         | 43.0          | 650    | 73263         | 5.4           | 780    | 3507          | 0.0           | 910    | 3995          | 0.0           |
| 395    | 2186          | 0.0           | 525    | 93289         | 50.1          | 655    | 64627         | 3.7           | 785    | 3267          | 0.0           | 915    | 4288          | 0.0           |
| 400    | 2015          | 0.0           | 530    | 98393         | 57.9          | 660    | 56614         | 2.4           | 790    | 2849          | 0.0           | 920    | 2446          | 0.0           |
| 405    | 2234          | 0.0           | 535    | 103269        | 64.0          | 665    | 49537         | 1.6           | 795    | 3037          | 0.0           | 925    | 3009          | 0.0           |
| 410    | 3412          | 0.0           | 540    | 107316        | 69.9          | 670    | 42866         | 0.9           | 800    | 2716          | 0.0           | 930    | 3026          | 0.0           |
| 415    | 6135          | 0.0           | 545    | 113101        | 75.3          | 675    | 36708         | 0.6           | 805    | 2648          | 0.0           | 935    | 4734          | 0.0           |
| 420    | 12146         | 0.0           | 550    | 120690        | 82.0          | 680    | 31814         | 0.4           | 810    | 3187          | 0.0           | 940    | 3719          | 0.0           |
| 425    | 23983         | 0.1           | 555    | 128583        | 87.8          | 685    | 27485         | 0.2           | 815    | 2931          | 0.0           | 945    | 1480          | 0.0           |
| 430    | 42142         | 0.3           | 560    | 137796        | 93.6          | 690    | 23698         | 0.1           | 820    | 2717          | 0.0           | 950    | 3450          | 0.0           |
| 435    | 68228         | 0.8           | 565    | 146577        | 97.5          | 695    | 20309         | 0.1           | 825    | 2236          | 0.0           | 955    | 5051          | 0.0           |
| 440    | 99323         | 1.6           | 570    | 154581        | 100.5         | 700    | 17890         | 0.1           | 830    | 2628          | 0.0           | 960    | 3176          | 0.0           |
| 445    | 115584        | 2.4           | 575    | 162633        | 101.2         | 705    | 15500         | 0.0           | 835    | 3140          | 0.0           | 965    | 5178          | 0.0           |
| 450    | 94997         | 2.5           | 580    | 168101        | 99.9          | 710    | 13699         | 0.0           | 840    | 3675          | 0.0           | 970    | 6385          | 0.0           |
| 455    | 61433         | 2.1           | 585    | 173145        | 96.2          | 715    | 12398         | 0.0           | 845    | 3283          | 0.0           | 975    | 3810          | 0.0           |
| 460    | 43373         | 1.8           | 590    | 174675        | 90.3          | 720    | 11147         | 0.0           | 850    | 3055          | 0.0           | 980    | 4322          | 0.0           |
| 465    | 32472         | 1.7           | 595    | 173724        | 82.3          | 725    | 9761          | 0.0           | 855    | 2932          | 0.0           | 985    | 4200          | 0.0           |
| 470    | 24257         | 1.5           | 600    | 171241        | 73.8          | 730    | 8651          | 0.0           | 860    | 3382          | 0.0           | 990    | 4661          | 0.0           |
| 475    | 21690         | 1.7           | 605    | 165134        | 64.0          | 735    | 7730          | 0.0           | 865    | 2605          | 0.0           | 995    | 6746          | 0.0           |
| 480    | 23173         | 2.2           | 610    | 156652        | 53.8          | 740    | 6847          | 0.0           | 870    | 3325          | 0.0           | 1000   | 4150          | 0.0           |
| 485    | 27564         | 3.3           | 615    | 147879        | 44.6          | 745    | 6124          | 0.0           | 875    | 3325          | 0.0           |        |               |               |

REPORT NUMBER: SP1-2101-121-7

**Scotopic Flux vs. Wavelength**



**Scotopic Lumens: 12126**

**S/P: 1.36**

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360    | 2672          | 0.0           | 490    | 34553         | 53.2          | 620    | 136720        | 1.7           | 750    | 5870          | 0.0           | 880    | 4216          | 0.0           |
| 365    | 2252          | 0.0           | 495    | 44336         | 71.7          | 625    | 126308        | 1.1           | 755    | 5421          | 0.0           | 885    | 4132          | 0.0           |
| 370    | 2217          | 0.0           | 500    | 54643         | 91.4          | 630    | 114625        | 0.6           | 760    | 5097          | 0.0           | 890    | 3992          | 0.0           |
| 375    | 2697          | 0.0           | 505    | 64676         | 110.0         | 635    | 103216        | 0.4           | 765    | 4626          | 0.0           | 895    | 3214          | 0.0           |
| 380    | 3039          | 0.0           | 510    | 73825         | 125.1         | 640    | 92605         | 0.2           | 770    | 3782          | 0.0           | 900    | 2580          | 0.0           |
| 385    | 2655          | 0.0           | 515    | 81872         | 135.7         | 645    | 83234         | 0.1           | 775    | 3506          | 0.0           | 905    | 1776          | 0.0           |
| 390    | 2357          | 0.0           | 520    | 88574         | 140.8         | 650    | 73263         | 0.1           | 780    | 3507          | 0.0           | 910    | 3995          | 0.0           |
| 395    | 2186          | 0.0           | 525    | 93289         | 139.6         | 655    | 64627         | 0.1           | 785    | 3267          | 0.0           | 915    | 4288          | 0.0           |
| 400    | 2015          | 0.0           | 530    | 98393         | 135.7         | 660    | 56614         | 0.0           | 790    | 2849          | 0.0           | 920    | 2446          | 0.0           |
| 405    | 2234          | 0.1           | 535    | 103269        | 128.7         | 665    | 49537         | 0.0           | 795    | 3037          | 0.0           | 925    | 3009          | 0.0           |
| 410    | 3412          | 0.2           | 540    | 107316        | 118.6         | 670    | 42866         | 0.0           | 800    | 2716          | 0.0           | 930    | 3026          | 0.0           |
| 415    | 6135          | 0.6           | 545    | 113101        | 108.4         | 675    | 36708         | 0.0           | 805    | 2648          | 0.0           | 935    | 4734          | 0.0           |
| 420    | 12146         | 2.0           | 550    | 120690        | 98.7          | 680    | 31814         | 0.0           | 810    | 3187          | 0.0           | 940    | 3719          | 0.0           |
| 425    | 23983         | 5.9           | 555    | 128583        | 87.9          | 685    | 27485         | 0.0           | 815    | 2931          | 0.0           | 945    | 1480          | 0.0           |
| 430    | 42142         | 14.3          | 560    | 137796        | 77.0          | 690    | 23698         | 0.0           | 820    | 2717          | 0.0           | 950    | 3450          | 0.0           |
| 435    | 68228         | 30.5          | 565    | 146577        | 65.8          | 695    | 20309         | 0.0           | 825    | 2236          | 0.0           | 955    | 5051          | 0.0           |
| 440    | 99323         | 55.5          | 570    | 154581        | 54.6          | 700    | 17890         | 0.0           | 830    | 2628          | 0.0           | 960    | 3176          | 0.0           |
| 445    | 115584        | 77.4          | 575    | 162633        | 44.3          | 705    | 15500         | 0.0           | 835    | 3140          | 0.0           | 965    | 5178          | 0.0           |
| 450    | 94997         | 73.6          | 580    | 168101        | 34.6          | 710    | 13699         | 0.0           | 840    | 3675          | 0.0           | 970    | 6385          | 0.0           |
| 455    | 61433         | 53.7          | 585    | 173145        | 26.5          | 715    | 12398         | 0.0           | 845    | 3283          | 0.0           | 975    | 3810          | 0.0           |
| 460    | 43373         | 41.9          | 590    | 174675        | 19.5          | 720    | 11147         | 0.0           | 850    | 3055          | 0.0           | 980    | 4322          | 0.0           |
| 465    | 32472         | 34.3          | 595    | 173724        | 13.9          | 725    | 9761          | 0.0           | 855    | 2932          | 0.0           | 985    | 4200          | 0.0           |
| 470    | 24257         | 27.9          | 600    | 171241        | 9.7           | 730    | 8651          | 0.0           | 860    | 3382          | 0.0           | 990    | 4661          | 0.0           |
| 475    | 21690         | 27.1          | 605    | 165134        | 6.5           | 735    | 7730          | 0.0           | 865    | 2605          | 0.0           | 995    | 6746          | 0.0           |
| 480    | 23173         | 31.3          | 610    | 156652        | 4.2           | 740    | 6847          | 0.0           | 870    | 3325          | 0.0           | 1000   | 4150          | 0.0           |
| 485    | 27564         | 40.0          | 615    | 147879        | 2.7           | 745    | 6124          | 0.0           | 875    | 3325          | 0.0           |        |               |               |

REPORT NUMBER: SP1-2101-121-7

**Melanopic Flux vs. Wavelength**



**Melanopic Lumens: 4490.7 M/P: 0.5**

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360    | 2672          | 0.0           | 490    | 34553         | 28.8          | 620    | 136720        | 0.1           | 750    | 5870          | 0.0           | 880    | 4216          | 0.0           |
| 365    | 2252          | 0.0           | 495    | 44336         | 36.6          | 625    | 126308        | 0.1           | 755    | 5421          | 0.0           | 885    | 4132          | 0.0           |
| 370    | 2217          | 0.0           | 500    | 54643         | 43.9          | 630    | 114625        | 0.0           | 760    | 5097          | 0.0           | 890    | 3992          | 0.0           |
| 375    | 2697          | 0.0           | 505    | 64676         | 49.6          | 635    | 103216        | 0.0           | 765    | 4626          | 0.0           | 895    | 3214          | 0.0           |
| 380    | 3039          | 0.0           | 510    | 73825         | 53.0          | 640    | 92605         | 0.0           | 770    | 3782          | 0.0           | 900    | 2580          | 0.0           |
| 385    | 2655          | 0.0           | 515    | 81872         | 53.5          | 645    | 83234         | 0.0           | 775    | 3506          | 0.0           | 905    | 1776          | 0.0           |
| 390    | 2357          | 0.0           | 520    | 88574         | 51.6          | 650    | 73263         | 0.0           | 780    | 3507          | 0.0           | 910    | 3995          | 0.0           |
| 395    | 2186          | 0.0           | 525    | 93289         | 47.3          | 655    | 64627         | 0.0           | 785    | 3267          | 0.0           | 915    | 4288          | 0.0           |
| 400    | 2015          | 0.0           | 530    | 98393         | 42.5          | 660    | 56614         | 0.0           | 790    | 2849          | 0.0           | 920    | 2446          | 0.0           |
| 405    | 2234          | 0.0           | 535    | 103269        | 37.2          | 665    | 49537         | 0.0           | 795    | 3037          | 0.0           | 925    | 3009          | 0.0           |
| 410    | 3412          | 0.1           | 540    | 107316        | 31.4          | 670    | 42866         | 0.0           | 800    | 2716          | 0.0           | 930    | 3026          | 0.0           |
| 415    | 6135          | 0.4           | 545    | 113101        | 26.3          | 675    | 36708         | 0.0           | 805    | 2648          | 0.0           | 935    | 4734          | 0.0           |
| 420    | 12146         | 1.4           | 550    | 120690        | 21.7          | 680    | 31814         | 0.0           | 810    | 3187          | 0.0           | 940    | 3719          | 0.0           |
| 425    | 23983         | 3.7           | 555    | 128583        | 17.3          | 685    | 27485         | 0.0           | 815    | 2931          | 0.0           | 945    | 1480          | 0.0           |
| 430    | 42142         | 8.9           | 560    | 137796        | 13.6          | 690    | 23698         | 0.0           | 820    | 2717          | 0.0           | 950    | 3450          | 0.0           |
| 435    | 68228         | 18.2          | 565    | 146577        | 10.3          | 695    | 20309         | 0.0           | 825    | 2236          | 0.0           | 955    | 5051          | 0.0           |
| 440    | 99323         | 33.2          | 570    | 154581        | 7.6           | 700    | 17890         | 0.0           | 830    | 2628          | 0.0           | 960    | 3176          | 0.0           |
| 445    | 115584        | 45.6          | 575    | 162633        | 5.4           | 705    | 15500         | 0.0           | 835    | 3140          | 0.0           | 965    | 5178          | 0.0           |
| 450    | 94997         | 43.8          | 580    | 168101        | 3.8           | 710    | 13699         | 0.0           | 840    | 3675          | 0.0           | 970    | 6385          | 0.0           |
| 455    | 61433         | 32.2          | 585    | 173145        | 2.6           | 715    | 12398         | 0.0           | 845    | 3283          | 0.0           | 975    | 3810          | 0.0           |
| 460    | 43373         | 25.6          | 590    | 174675        | 1.7           | 720    | 11147         | 0.0           | 850    | 3055          | 0.0           | 980    | 4322          | 0.0           |
| 465    | 32472         | 21.2          | 595    | 173724        | 1.1           | 725    | 9761          | 0.0           | 855    | 2932          | 0.0           | 985    | 4200          | 0.0           |
| 470    | 24257         | 17.4          | 600    | 171241        | 0.7           | 730    | 8651          | 0.0           | 860    | 3382          | 0.0           | 990    | 4661          | 0.0           |
| 475    | 21690         | 16.6          | 605    | 165134        | 0.5           | 735    | 7730          | 0.0           | 865    | 2605          | 0.0           | 995    | 6746          | 0.0           |
| 480    | 23173         | 18.6          | 610    | 156652        | 0.3           | 740    | 6847          | 0.0           | 870    | 3325          | 0.0           | 1000   | 4150          | 0.0           |
| 485    | 27564         | 22.7          | 615    | 147879        | 0.2           | 745    | 6124          | 0.0           | 875    | 3325          | 0.0           |        |               |               |

**Summary**

$R_f = 76.9$   
 $R_g = 94.4$   
 $CIE R_a = 73.1$   
 $R_g = -34.6$



**Color Vector Graphics**



**Individual Sample Fidelity Index ( $R_{f,i}$ )**

|            |            |            |            |
|------------|------------|------------|------------|
| CES01 = 86 | CES26 = 68 | CES51 = 90 | CES76 = 63 |
| CES02 = 62 | CES27 = 88 | CES52 = 89 | CES77 = 80 |
| CES03 = 31 | CES28 = 87 | CES53 = 80 | CES78 = 65 |
| CES04 = 70 | CES29 = 67 | CES54 = 84 | CES79 = 87 |
| CES05 = 48 | CES30 = 74 | CES55 = 84 | CES80 = 86 |
| CES06 = 51 | CES31 = 71 | CES56 = 75 | CES81 = 75 |
| CES07 = 40 | CES32 = 67 | CES57 = 74 | CES82 = 94 |
| CES08 = 39 | CES33 = 74 | CES58 = 76 | CES83 = 91 |
| CES09 = 29 | CES34 = 78 | CES59 = 87 | CES84 = 89 |
| CES10 = 75 | CES35 = 89 | CES60 = 93 | CES85 = 80 |
| CES11 = 58 | CES36 = 98 | CES61 = 86 | CES86 = 66 |
| CES12 = 64 | CES37 = 86 | CES62 = 89 | CES87 = 79 |
| CES13 = 43 | CES38 = 82 | CES63 = 77 | CES88 = 79 |
| CES14 = 74 | CES39 = 95 | CES64 = 74 | CES89 = 70 |
| CES15 = 71 | CES40 = 91 | CES65 = 68 | CES90 = 77 |
| CES16 = 47 | CES41 = 89 | CES66 = 71 | CES91 = 88 |
| CES17 = 50 | CES42 = 88 | CES67 = 69 | CES92 = 60 |
| CES18 = 56 | CES43 = 82 | CES68 = 74 | CES93 = 77 |
| CES19 = 72 | CES44 = 99 | CES69 = 82 | CES94 = 52 |
| CES20 = 65 | CES45 = 87 | CES70 = 67 | CES95 = 69 |
| CES21 = 86 | CES46 = 82 | CES71 = 66 | CES96 = 78 |
| CES22 = 79 | CES47 = 82 | CES72 = 88 | CES97 = 85 |
| CES23 = 92 | CES48 = 72 | CES73 = 59 | CES98 = 76 |
| CES24 = 91 | CES49 = 82 | CES74 = 97 | CES99 = 63 |
| CES25 = 72 | CES50 = 88 | CES75 = 66 |            |





Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)