

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: McGRAW-EDISON

Report Number: P630824

Luminaire Tested: GWS-SA1E-740-U-SL2-W-GRSBK

Issue Date: 1/10/2023

**Test Information**

Test Method: LM-79-2019  
Report Number: P630824  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2209-782-28)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 1/10/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: McGRAW-EDISON  
Catalog Number: GWS-SA1E-740-U-SL2-W-GRSBK  
Description: GALLEON WALL SLIM LUMINAIRE. (1) LIGHTSQUARES WITH 16 LEDS EACH AND TYPE II SPILL LIGHT ELIMINATOR OPTICS W/ FACTORY INSTALLED GLARE SHIELD, BK  
Light Source: (16) 4000K CCT, 70 CRI LEDS  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 4449.5 lumens  
Efficiency: N/A  
Efficacy: 76.2 lumens/watt  
Luminous Opening: Rectangular (W 0.5' x L: 0.5' x H: 0')  
IES Classification: Type II - Short  
BUG Rating: B1 - U0 - G0  
  
Input Watts (W): 58.4  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 0  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 28.75 FT



REPORT NUMBER: P630824  
 CATALOG NUMBER: GWS-SA1E-740-U-SL2-W-GRSBK

### Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd  
 - - - 1/2 Max cd



Based on 10 foot mounting height. Maximum calculated value = 15.6 fc  
 Type II - Short - N/A

REPORT NUMBER: P630824  
CATALOG NUMBER: GWS-SA1E-740-U-SL2-W-GRSBK

### Luminous Intensity Polar Plot



— Vertical Plane Through 50-Deg Lateral    - - - Horizontal Cone Through 55-Deg Vertical

REPORT NUMBER: P630824

CATALOG NUMBER: GWS-SA1E-740-U-SL2-W-GRSBK


**FLUX DISTRIBUTION:**

|                    |           | Downward | Upward | Total  |
|--------------------|-----------|----------|--------|--------|
| <b>House Side</b>  | Lumens    | 876.8    | 0.0    | 876.8  |
|                    | % Fixture | 19.7     | 0.0    | 19.7   |
| <b>Street Side</b> | Lumens    | 3572.7   | 0.0    | 3572.7 |
|                    | % Fixture | 80.3     | 0.0    | 80.3   |
| <b>Total</b>       | Lumens    | 4449.5   | 0.0    | 4449.5 |
|                    | % Fixture | 100.0    | 0.0    | 100.0  |

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 137.1  | 3.1       |
| 10°-20°   | 337.4  | 7.6       |
| 20°-30°   | 475.9  | 10.7      |
| 30°-40°   | 704.2  | 15.8      |
| 40°-50°   | 1016.0 | 22.8      |
| 50°-60°   | 1198.4 | 26.9      |
| 60°-70°   | 534.6  | 12.0      |
| 70°-80°   | 46.0   | 1.0       |
| 80°-90°   | 0.0    | 0.0       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-90°    | 4449.5 | 100.0     |
| 0°-180°   | 4449.5 | 100.0     |

**Coefficient of Utilization**




REPORT NUMBER: P630824

CATALOG NUMBER: GWS-SA1E-740-U-SL2-W-GRSBK

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

| Zone           | Lumens | % Fixture | Zone Rating/Lumen Limit |      |        |
|----------------|--------|-----------|-------------------------|------|--------|
|                |        |           | B                       | U    | G      |
| FL (0°-30°)    | 574.4  | 12.9      |                         |      |        |
| FM (30°-60°)   | 2496.9 | 56.1      |                         |      |        |
| FH (60°-80°)   | 501.4  | 11.3      |                         |      | G0/660 |
| FVH (80°-90°)  | 0.0    | 0.0       |                         |      | G0/10  |
| BL (0°-30°)    | 375.9  | 8.4       | B1/500                  |      |        |
| BM (30°-60°)   | 421.7  | 9.5       | B1/1000                 |      |        |
| BH (60°-80°)   | 79.2   | 1.8       | B0/110                  |      | G0/110 |
| BVH (80°-90°)  | 0.0    | 0.0       |                         |      | G0/10  |
| UL (90°-100°)  | 0.0    | 0.0       |                         | U0/0 |        |
| UH (100°-180°) | 0.0    | 0.0       |                         | U0/0 |        |

**BUG Rating: B1-U0-G0**  
 Type II Short





REPORT NUMBER: P630824  
 CATALOG NUMBER: GWS-SA1E-740-U-SL2-W-GRSBK

**CANDELA DISTRIBUTION (FULL):**

|       | 0°     | 5°     | 15°    | 25°    | 35°    | 45°    | 50°    | 55°    | 65°    | 75°    | 85°    |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°    | 1561.1 | 1561.1 | 1561.1 | 1561.1 | 1561.1 | 1561.1 | 1561.1 | 1561.1 | 1561.1 | 1561.1 | 1561.1 |
| 2.5°  | 1450.3 | 1451.4 | 1452.0 | 1466.6 | 1472.0 | 1493.8 | 1505.2 | 1511.2 | 1526.9 | 1545.4 | 1560.6 |
| 5°    | 1353.1 | 1351.5 | 1354.2 | 1372.6 | 1384.6 | 1416.6 | 1434.0 | 1446.0 | 1480.7 | 1524.2 | 1560.6 |
| 7.5°  | 1268.4 | 1271.6 | 1274.9 | 1295.0 | 1312.9 | 1347.7 | 1372.6 | 1390.6 | 1438.9 | 1503.6 | 1564.9 |
| 10°   | 1208.6 | 1208.6 | 1213.5 | 1236.3 | 1257.5 | 1300.4 | 1325.4 | 1348.2 | 1405.8 | 1485.1 | 1569.8 |
| 12.5° | 1164.6 | 1165.1 | 1171.1 | 1197.2 | 1221.6 | 1266.2 | 1292.3 | 1314.5 | 1378.1 | 1466.6 | 1570.9 |
| 15°   | 1144.0 | 1142.3 | 1147.2 | 1174.9 | 1202.1 | 1243.9 | 1271.1 | 1292.8 | 1358.5 | 1456.3 | 1576.3 |
| 17.5° | 1138.5 | 1137.4 | 1141.2 | 1168.4 | 1196.1 | 1236.8 | 1263.5 | 1285.2 | 1355.8 | 1459.6 | 1592.6 |
| 20°   | 1154.3 | 1152.1 | 1150.5 | 1173.8 | 1199.9 | 1240.1 | 1267.8 | 1292.3 | 1368.8 | 1477.5 | 1617.6 |
| 22.5° | 1191.8 | 1191.8 | 1188.0 | 1199.4 | 1216.7 | 1253.1 | 1281.9 | 1314.0 | 1403.1 | 1513.3 | 1654.6 |
| 25°   | 1260.7 | 1255.3 | 1248.3 | 1253.1 | 1251.0 | 1273.8 | 1308.0 | 1352.5 | 1467.7 | 1572.5 | 1699.6 |
| 27.5° | 1339.5 | 1344.4 | 1332.4 | 1333.0 | 1314.0 | 1305.8 | 1345.5 | 1412.8 | 1563.8 | 1656.2 | 1766.5 |
| 30°   | 1446.5 | 1442.7 | 1443.3 | 1441.6 | 1397.6 | 1359.1 | 1402.0 | 1491.6 | 1685.0 | 1783.8 | 1853.4 |
| 32.5° | 1530.2 | 1535.6 | 1553.5 | 1563.8 | 1506.3 | 1444.3 | 1490.0 | 1598.6 | 1823.0 | 1929.4 | 1959.8 |
| 35°   | 1618.7 | 1628.5 | 1664.9 | 1698.6 | 1650.2 | 1579.1 | 1627.9 | 1740.4 | 1952.8 | 2073.4 | 2082.1 |
| 37.5° | 1712.1 | 1731.7 | 1775.1 | 1834.4 | 1826.8 | 1763.7 | 1808.3 | 1907.1 | 2054.9 | 2160.3 | 2183.1 |
| 40°   | 1819.1 | 1838.2 | 1909.3 | 1994.6 | 2012.5 | 1998.4 | 2013.1 | 2070.6 | 2122.2 | 2164.1 | 2226.5 |
| 42.5° | 1936.5 | 1962.6 | 2052.7 | 2166.8 | 2234.1 | 2246.6 | 2212.4 | 2206.4 | 2151.6 | 2120.6 | 2217.3 |
| 45°   | 2075.0 | 2105.4 | 2207.5 | 2355.3 | 2462.3 | 2479.1 | 2419.9 | 2343.3 | 2170.0 | 2088.6 | 2189.6 |
| 47.5° | 2230.3 | 2259.1 | 2360.7 | 2538.3 | 2697.5 | 2704.0 | 2600.8 | 2477.5 | 2224.9 | 2125.5 | 2210.8 |
| 50°   | 2282.5 | 2300.4 | 2388.4 | 2597.0 | 2890.3 | 2940.3 | 2790.9 | 2628.5 | 2335.2 | 2234.1 | 2314.0 |
| 52.5° | 2103.2 | 2110.3 | 2186.9 | 2397.6 | 2851.2 | 3172.2 | 3068.5 | 2853.9 | 2531.3 | 2399.8 | 2473.2 |
| 55°   | 1666.5 | 1655.1 | 1717.0 | 1910.4 | 2478.0 | 3125.0 | 3320.0 | 3208.1 | 2783.9 | 2594.3 | 2680.1 |
| 57.5° | 1165.7 | 1152.1 | 1138.0 | 1268.9 | 1849.0 | 2649.1 | 3059.3 | 3257.5 | 3024.5 | 2787.1 | 2903.4 |
| 60°   | 958.2  | 945.2  | 876.7  | 816.4  | 1117.9 | 1902.3 | 2349.8 | 2723.0 | 3004.9 | 2777.3 | 2896.3 |
| 62.5° | 827.8  | 820.2  | 792.5  | 710.5  | 657.8  | 1085.8 | 1471.5 | 1828.9 | 2305.8 | 2180.9 | 2187.4 |
| 65°   | 650.2  | 648.0  | 667.0  | 675.7  | 581.8  | 600.8  | 750.7  | 950.6  | 1246.6 | 1175.5 | 1114.6 |
| 67.5° | 444.3  | 439.4  | 475.3  | 584.5  | 559.5  | 474.2  | 439.4  | 443.2  | 539.4  | 329.7  | 261.8  |
| 70°   | 282.5  | 271.1  | 271.6  | 362.3  | 455.2  | 374.3  | 339.0  | 298.2  | 268.3  | 48.9   | 55.4   |
| 72.5° | 180.9  | 173.8  | 149.4  | 163.5  | 210.8  | 182.5  | 184.1  | 158.6  | 105.9  | 26.1   | 30.4   |
| 75°   | 76.0   | 70.1   | 53.8   | 42.9   | 42.4   | 26.6   | 23.4   | 21.7   | 14.7   | 14.7   | 15.8   |
| 77.5° | 0.5    | 0.0    | 0.0    | 0.5    | 1.1    | 0.5    | 0.5    | 1.1    | 2.2    | 3.3    | 3.8    |
| 80°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.5    |
| 82.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 85°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 87.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



REPORT NUMBER: P630824  
 CATALOG NUMBER: GWS-SA1E-740-U-SL2-W-GRSBK

**CANDELA DISTRIBUTION (continued):**

|       | 90°    | 95°    | 105°   | 115°   | 125°   | 135°   | 145°   | 155°   | 165°   | 175°   | 180°   |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°    | 1561.1 | 1561.1 | 1561.1 | 1561.1 | 1561.1 | 1561.1 | 1561.1 | 1561.1 | 1561.1 | 1561.1 | 1561.1 |
| 2.5°  | 1569.8 | 1556.8 | 1571.5 | 1576.9 | 1576.3 | 1576.9 | 1561.1 | 1550.3 | 1549.7 | 1536.1 | 1529.6 |
| 5°    | 1575.8 | 1565.5 | 1576.3 | 1569.3 | 1552.4 | 1531.3 | 1503.0 | 1478.6 | 1467.7 | 1452.0 | 1444.3 |
| 7.5°  | 1587.2 | 1576.3 | 1574.7 | 1546.5 | 1504.6 | 1460.1 | 1410.1 | 1365.6 | 1341.7 | 1312.9 | 1314.5 |
| 10°   | 1595.4 | 1582.9 | 1561.7 | 1504.1 | 1434.6 | 1363.4 | 1289.0 | 1222.7 | 1180.9 | 1142.3 | 1135.8 |
| 12.5° | 1598.6 | 1580.1 | 1530.7 | 1443.8 | 1346.0 | 1253.1 | 1144.0 | 1049.4 | 984.3  | 933.7  | 926.7  |
| 15°   | 1604.6 | 1574.7 | 1491.1 | 1371.0 | 1236.8 | 1105.4 | 966.3  | 837.1  | 750.7  | 692.6  | 697.5  |
| 17.5° | 1613.8 | 1568.7 | 1446.5 | 1289.5 | 1119.5 | 933.7  | 745.8  | 597.5  | 518.2  | 484.5  | 485.1  |
| 20°   | 1626.9 | 1561.7 | 1397.6 | 1199.9 | 978.8  | 739.8  | 521.5  | 409.6  | 387.3  | 386.2  | 384.6  |
| 22.5° | 1644.2 | 1554.6 | 1345.5 | 1101.6 | 812.1  | 518.2  | 347.1  | 312.3  | 321.6  | 339.5  | 342.8  |
| 25°   | 1664.9 | 1545.9 | 1287.4 | 990.8  | 630.1  | 340.0  | 260.2  | 254.8  | 277.0  | 300.9  | 306.4  |
| 27.5° | 1696.9 | 1541.6 | 1221.1 | 864.8  | 442.2  | 243.9  | 212.9  | 216.2  | 236.3  | 256.4  | 261.3  |
| 30°   | 1751.2 | 1549.7 | 1148.8 | 723.5  | 284.1  | 194.5  | 184.7  | 189.6  | 200.4  | 210.8  | 215.1  |
| 32.5° | 1825.1 | 1573.6 | 1078.8 | 569.3  | 202.6  | 168.9  | 166.8  | 169.5  | 173.8  | 179.8  | 181.4  |
| 35°   | 1911.5 | 1614.9 | 1006.5 | 407.4  | 167.3  | 154.3  | 152.1  | 152.1  | 154.3  | 155.4  | 155.9  |
| 37.5° | 1982.6 | 1658.4 | 938.6  | 271.1  | 149.9  | 142.9  | 139.6  | 138.0  | 137.4  | 138.5  | 139.1  |
| 40°   | 2013.6 | 1676.3 | 864.8  | 197.2  | 137.4  | 132.5  | 127.6  | 122.8  | 122.8  | 126.6  | 127.1  |
| 42.5° | 1991.9 | 1656.2 | 779.5  | 163.0  | 128.7  | 121.7  | 114.1  | 109.7  | 111.9  | 115.7  | 116.8  |
| 45°   | 1945.7 | 1606.8 | 685.5  | 143.9  | 120.0  | 110.8  | 102.1  | 99.4   | 101.6  | 106.5  | 107.6  |
| 47.5° | 1938.1 | 1574.2 | 573.1  | 131.5  | 110.8  | 101.6  | 92.3   | 89.6   | 92.3   | 96.1   | 97.2   |
| 50°   | 2013.6 | 1602.4 | 448.1  | 120.6  | 102.1  | 91.8   | 84.2   | 81.5   | 83.1   | 85.3   | 86.4   |
| 52.5° | 2151.6 | 1707.3 | 361.8  | 110.3  | 91.8   | 82.0   | 77.1   | 73.9   | 73.9   | 76.0   | 76.6   |
| 55°   | 2355.3 | 1890.3 | 312.3  | 98.3   | 79.8   | 74.4   | 70.1   | 66.8   | 66.8   | 67.9   | 68.4   |
| 57.5° | 2589.9 | 2111.9 | 323.7  | 82.6   | 70.1   | 67.4   | 63.6   | 60.8   | 61.9   | 61.9   | 61.9   |
| 60°   | 2557.3 | 2095.6 | 346.6  | 69.5   | 61.9   | 60.8   | 57.6   | 56.5   | 59.2   | 57.0   | 55.9   |
| 62.5° | 1883.8 | 1447.6 | 181.4  | 57.0   | 53.2   | 52.1   | 50.0   | 52.1   | 55.9   | 50.0   | 47.8   |
| 65°   | 914.7  | 700.7  | 72.8   | 46.7   | 45.1   | 44.0   | 42.9   | 46.2   | 48.3   | 39.1   | 36.9   |
| 67.5° | 215.1  | 174.9  | 47.3   | 39.7   | 37.5   | 35.3   | 36.4   | 36.9   | 35.3   | 26.6   | 25.5   |
| 70°   | 55.9   | 54.9   | 36.9   | 33.1   | 29.9   | 27.7   | 27.7   | 27.2   | 23.4   | 16.8   | 15.8   |
| 72.5° | 30.4   | 29.9   | 26.6   | 25.0   | 20.6   | 18.5   | 19.0   | 16.8   | 13.0   | 9.8    | 9.2    |
| 75°   | 15.2   | 16.3   | 15.2   | 14.1   | 11.4   | 10.3   | 10.3   | 9.2    | 6.5    | 3.8    | 3.8    |
| 77.5° | 3.3    | 3.8    | 3.8    | 3.3    | 2.7    | 2.2    | 2.2    | 2.7    | 1.1    | 0.0    | 0.0    |
| 80°   | 0.5    | 0.5    | 0.5    | 0.5    | 0.5    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 82.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 85°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 87.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



LM-79-08: Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Report Prepared for

Cooper Lighting Solutions

MCGRAW, INVUE, LUMARK AND STREETWORKS

DATA VALID FOR LUMINIAIRES UTILIZING SA LIGHT ENGINES

Report Number: SP1-2101-121-2

Luminaire Tested: IFLD-S-SA2A-740-U-T3R-HSS

Test Date: 03/05/2021

**Test Information**

Test Method: LM-79-08  
 Report Number: SP1-2101-121-2  
 Test Lab: COOPER LIGHTING SOLUTIONS  
 Photometer: SP1  
 Measurement Geometry: 4π  
 Issue Date: 03/05/2021  
 Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
 Product Line: STREETWORKS  
 Catalog Number: **IFLD-S-SA2A-740-U-T3R-HSS**  
 Description: STREETWORKS INF FLOOD

SHIELD, DRIVER PROGRAMMED @ 615mA.

**Spectral Parameters**

|                           |         |           |      |      |       |
|---------------------------|---------|-----------|------|------|-------|
| CCT (K):                  | 3905    | CRI (Ra): | 71.2 | R9:  | -29.7 |
| CIE u':                   | 0.2273  | R1:       | 68.9 | R10: | 46.2  |
| CIE v':                   | 0.5024  | R2:       | 77.0 | R11: | 68.8  |
| Duv:                      | -0.0008 | R3:       | 84.0 | R12: | 45.6  |
| CIE x:                    | 0.3841  | R4:       | 71.6 | R13: | 69.5  |
| CIE y:                    | 0.3774  | R5:       | 68.9 | R14: | 90.7  |
| CIE z:                    | 0.2385  | R6:       | 68.3 |      |       |
| Peak Wavelength (nm):     | 443     | R7:       | 78.7 |      |       |
| Dominant Wavelength (nm): | 579     | R8:       | 52.2 |      |       |
| Purity:                   | 28.7    |           |      |      |       |
| Rf:                       | 71.7    |           |      |      |       |
| Rg:                       | 96.9    |           |      |      |       |



**Test Conditions**

Stabilization Time: 211M  
 Operation Time: 12H  
 Room Temperature (°C) / RH%: 24.8/312%  
 Sphere Temperature (°C): 24.1

REPORT NUMBER: SP1-2101-121-2

| Measurement and Test Equipment |                       |                  |                      |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument                     | Identification Number | Calibration Date | Calibration Due Date |
| Photometer                     | IN0058                | 1/31/2021        | 7/31/2021            |
| Power Meter                    | IN0071                | 12/1/2020        | 12/1/2021            |
| AC Power Source                | IN0063                | 12/1/2020        | 12/1/2021            |
| DC Power Source                | IN0208                | 12/1/2020        | 12/1/2021            |
| Sphere Thermometer             | IN0085                | 12/1/2020        | 12/1/2021            |
| Room Thermometer               | IN0046                | 12/1/2020        | 12/1/2021            |

REPORT NUMBER: SP1-2101-121-2

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 4000K 4-step quadrangle

REPORT NUMBER: SP1-2101-121-2

**Photopic Flux vs. Wavelength**



#####

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360    | 2304          | 0.0           | 490    | 19043         | 2.7           | 620    | 97577         | 25.4          | 750    | 4830          | 0.0           | 880    | 3505          | 0.0           |
| 365    | 2150          | 0.0           | 495    | 26606         | 4.8           | 625    | 90158         | 19.9          | 755    | 4664          | 0.0           | 885    | 2991          | 0.0           |
| 370    | 2146          | 0.0           | 500    | 36376         | 8.0           | 630    | 82240         | 14.9          | 760    | 4006          | 0.0           | 890    | 2327          | 0.0           |
| 375    | 2332          | 0.0           | 505    | 47714         | 13.3          | 635    | 74361         | 11.2          | 765    | 3715          | 0.0           | 895    | 2775          | 0.0           |
| 380    | 2527          | 0.0           | 510    | 58741         | 20.2          | 640    | 66994         | 8.0           | 770    | 3696          | 0.0           | 900    | 2141          | 0.0           |
| 385    | 2304          | 0.0           | 515    | 68716         | 28.5          | 645    | 60405         | 5.8           | 775    | 3117          | 0.0           | 905    | 2421          | 0.0           |
| 390    | 2064          | 0.0           | 520    | 77136         | 37.4          | 650    | 53806         | 3.9           | 780    | 3062          | 0.0           | 910    | 2200          | 0.0           |
| 395    | 1856          | 0.0           | 525    | 83567         | 44.9          | 655    | 47610         | 2.7           | 785    | 2907          | 0.0           | 915    | 2716          | 0.0           |
| 400    | 1856          | 0.0           | 530    | 89283         | 52.6          | 660    | 42018         | 1.8           | 790    | 2655          | 0.0           | 920    | 2656          | 0.0           |
| 405    | 2374          | 0.0           | 535    | 94097         | 58.4          | 665    | 36742         | 1.2           | 795    | 2467          | 0.0           | 925    | 2671          | 0.0           |
| 410    | 4084          | 0.0           | 540    | 96845         | 63.1          | 670    | 32105         | 0.7           | 800    | 2609          | 0.0           | 930    | 3292          | 0.0           |
| 415    | 8543          | 0.0           | 545    | 100829        | 67.1          | 675    | 27946         | 0.5           | 805    | 2293          | 0.0           | 935    | 3188          | 0.0           |
| 420    | 18394         | 0.1           | 550    | 105648        | 71.8          | 680    | 24146         | 0.3           | 810    | 2188          | 0.0           | 940    | 1997          | 0.0           |
| 425    | 37987         | 0.2           | 555    | 110017        | 75.1          | 685    | 21191         | 0.2           | 815    | 2386          | 0.0           | 945    | 2623          | 0.0           |
| 430    | 67605         | 0.5           | 560    | 114586        | 77.9          | 690    | 18544         | 0.1           | 820    | 2712          | 0.0           | 950    | 2969          | 0.0           |
| 435    | 102160        | 1.2           | 565    | 118987        | 79.1          | 695    | 16058         | 0.1           | 825    | 2473          | 0.0           | 955    | 2277          | 0.0           |
| 440    | 135103        | 2.1           | 570    | 122326        | 79.5          | 700    | 14133         | 0.0           | 830    | 1969          | 0.0           | 960    | 4267          | 0.0           |
| 445    | 140126        | 2.9           | 575    | 125968        | 78.4          | 705    | 12309         | 0.0           | 835    | 1917          | 0.0           | 965    | 2034          | 0.0           |
| 450    | 102339        | 2.7           | 580    | 127613        | 75.8          | 710    | 11142         | 0.0           | 840    | 2248          | 0.0           | 970    | 3586          | 0.0           |
| 455    | 58751         | 2.0           | 585    | 129466        | 71.9          | 715    | 10143         | 0.0           | 845    | 2266          | 0.0           | 975    | 2505          | 0.0           |
| 460    | 36892         | 1.5           | 590    | 128813        | 66.6          | 720    | 9072          | 0.0           | 850    | 2558          | 0.0           | 980    | 2666          | 0.0           |
| 465    | 24637         | 1.3           | 595    | 126387        | 59.9          | 725    | 8130          | 0.0           | 855    | 2767          | 0.0           | 985    | 2934          | 0.0           |
| 470    | 16738         | 1.0           | 600    | 123477        | 53.2          | 730    | 7149          | 0.0           | 860    | 2826          | 0.0           | 990    | 4120          | 0.0           |
| 475    | 13456         | 1.1           | 605    | 118718        | 46.0          | 735    | 6311          | 0.0           | 865    | 2385          | 0.0           | 995    | 3858          | 0.0           |
| 480    | 13081         | 1.2           | 610    | 112091        | 38.5          | 740    | 5711          | 0.0           | 870    | 3194          | 0.0           | 1000   | 3405          | 0.0           |
| 485    | 14734         | 1.7           | 615    | 105039        | 31.7          | 745    | 5111          | 0.0           | 875    | 3189          | 0.0           |        |               |               |

REPORT NUMBER: SP1-2101-121-2

**Scotopic Flux vs. Wavelength**



**Scotopic Lumens: 10425.8 S/P: 1.47**

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360    | 2304          | 0.0           | 490    | 19043         | 29.3          | 620    | 97577         | 1.2           | 750    | 4830          | 0.0           | 880    | 3505          | 0.0           |
| 365    | 2150          | 0.0           | 495    | 26606         | 43.0          | 625    | 90158         | 0.8           | 755    | 4664          | 0.0           | 885    | 2991          | 0.0           |
| 370    | 2146          | 0.0           | 500    | 36376         | 60.8          | 630    | 82240         | 0.5           | 760    | 4006          | 0.0           | 890    | 2327          | 0.0           |
| 375    | 2332          | 0.0           | 505    | 47714         | 81.1          | 635    | 74361         | 0.3           | 765    | 3715          | 0.0           | 895    | 2775          | 0.0           |
| 380    | 2527          | 0.0           | 510    | 58741         | 99.6          | 640    | 66994         | 0.2           | 770    | 3696          | 0.0           | 900    | 2141          | 0.0           |
| 385    | 2304          | 0.0           | 515    | 68716         | 113.9         | 645    | 60405         | 0.1           | 775    | 3117          | 0.0           | 905    | 2421          | 0.0           |
| 390    | 2064          | 0.0           | 520    | 77136         | 122.6         | 650    | 53806         | 0.1           | 780    | 3062          | 0.0           | 910    | 2200          | 0.0           |
| 395    | 1856          | 0.0           | 525    | 83567         | 125.0         | 655    | 47610         | 0.0           | 785    | 2907          | 0.0           | 915    | 2716          | 0.0           |
| 400    | 1856          | 0.0           | 530    | 89283         | 123.1         | 660    | 42018         | 0.0           | 790    | 2655          | 0.0           | 920    | 2656          | 0.0           |
| 405    | 2374          | 0.1           | 535    | 94097         | 117.3         | 665    | 36742         | 0.0           | 795    | 2467          | 0.0           | 925    | 2671          | 0.0           |
| 410    | 4084          | 0.2           | 540    | 96845         | 107.0         | 670    | 32105         | 0.0           | 800    | 2609          | 0.0           | 930    | 3292          | 0.0           |
| 415    | 8543          | 0.9           | 545    | 100829        | 96.7          | 675    | 27946         | 0.0           | 805    | 2293          | 0.0           | 935    | 3188          | 0.0           |
| 420    | 18394         | 3.0           | 550    | 105648        | 86.4          | 680    | 24146         | 0.0           | 810    | 2188          | 0.0           | 940    | 1997          | 0.0           |
| 425    | 37987         | 9.3           | 555    | 110017        | 75.2          | 685    | 21191         | 0.0           | 815    | 2386          | 0.0           | 945    | 2623          | 0.0           |
| 430    | 67605         | 23.0          | 560    | 114586        | 64.0          | 690    | 18544         | 0.0           | 820    | 2712          | 0.0           | 950    | 2969          | 0.0           |
| 435    | 102160        | 45.7          | 565    | 118987        | 53.4          | 695    | 16058         | 0.0           | 825    | 2473          | 0.0           | 955    | 2277          | 0.0           |
| 440    | 135103        | 75.5          | 570    | 122326        | 43.2          | 700    | 14133         | 0.0           | 830    | 1969          | 0.0           | 960    | 4267          | 0.0           |
| 445    | 140126        | 93.8          | 575    | 125968        | 34.3          | 705    | 12309         | 0.0           | 835    | 1917          | 0.0           | 965    | 2034          | 0.0           |
| 450    | 102339        | 79.3          | 580    | 127613        | 26.3          | 710    | 11142         | 0.0           | 840    | 2248          | 0.0           | 970    | 3586          | 0.0           |
| 455    | 58751         | 51.3          | 585    | 129466        | 19.8          | 715    | 10143         | 0.0           | 845    | 2266          | 0.0           | 975    | 2505          | 0.0           |
| 460    | 36892         | 35.6          | 590    | 128813        | 14.3          | 720    | 9072          | 0.0           | 850    | 2558          | 0.0           | 980    | 2666          | 0.0           |
| 465    | 24637         | 26.0          | 595    | 126387        | 10.1          | 725    | 8130          | 0.0           | 855    | 2767          | 0.0           | 985    | 2934          | 0.0           |
| 470    | 16738         | 19.3          | 600    | 123477        | 7.0           | 730    | 7149          | 0.0           | 860    | 2826          | 0.0           | 990    | 4120          | 0.0           |
| 475    | 13456         | 16.8          | 605    | 118718        | 4.7           | 735    | 6311          | 0.0           | 865    | 2385          | 0.0           | 995    | 3858          | 0.0           |
| 480    | 13081         | 17.7          | 610    | 112091        | 3.0           | 740    | 5711          | 0.0           | 870    | 3194          | 0.0           | 1000   | 3405          | 0.0           |
| 485    | 14734         | 21.4          | 615    | 105039        | 1.9           | 745    | 5111          | 0.0           | 875    | 3189          | 0.0           |        |               |               |

REPORT NUMBER: SP1-2101-121-2

**Melanopic Flux vs. Wavelength**



**Melanopic Lumens: 3927.2 M/P: 0.55**

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360    | 2304          | 0.0           | 490    | 19043         | 15.8          | 620    | 97577         | 0.1           | 750    | 4830          | 0.0           | 880    | 3505          | 0.0           |
| 365    | 2150          | 0.0           | 495    | 26606         | 22.0          | 625    | 90158         | 0.0           | 755    | 4664          | 0.0           | 885    | 2991          | 0.0           |
| 370    | 2146          | 0.0           | 500    | 36376         | 29.2          | 630    | 82240         | 0.0           | 760    | 4006          | 0.0           | 890    | 2327          | 0.0           |
| 375    | 2332          | 0.0           | 505    | 47714         | 36.6          | 635    | 74361         | 0.0           | 765    | 3715          | 0.0           | 895    | 2775          | 0.0           |
| 380    | 2527          | 0.0           | 510    | 58741         | 42.2          | 640    | 66994         | 0.0           | 770    | 3696          | 0.0           | 900    | 2141          | 0.0           |
| 385    | 2304          | 0.0           | 515    | 68716         | 44.9          | 645    | 60405         | 0.0           | 775    | 3117          | 0.0           | 905    | 2421          | 0.0           |
| 390    | 2064          | 0.0           | 520    | 77136         | 44.9          | 650    | 53806         | 0.0           | 780    | 3062          | 0.0           | 910    | 2200          | 0.0           |
| 395    | 1856          | 0.0           | 525    | 83567         | 42.4          | 655    | 47610         | 0.0           | 785    | 2907          | 0.0           | 915    | 2716          | 0.0           |
| 400    | 1856          | 0.0           | 530    | 89283         | 38.6          | 660    | 42018         | 0.0           | 790    | 2655          | 0.0           | 920    | 2656          | 0.0           |
| 405    | 2374          | 0.0           | 535    | 94097         | 33.9          | 665    | 36742         | 0.0           | 795    | 2467          | 0.0           | 925    | 2671          | 0.0           |
| 410    | 4084          | 0.2           | 540    | 96845         | 28.3          | 670    | 32105         | 0.0           | 800    | 2609          | 0.0           | 930    | 3292          | 0.0           |
| 415    | 8543          | 0.6           | 545    | 100829        | 23.4          | 675    | 27946         | 0.0           | 805    | 2293          | 0.0           | 935    | 3188          | 0.0           |
| 420    | 18394         | 2.1           | 550    | 105648        | 19.0          | 680    | 24146         | 0.0           | 810    | 2188          | 0.0           | 940    | 1997          | 0.0           |
| 425    | 37987         | 5.9           | 555    | 110017        | 14.8          | 685    | 21191         | 0.0           | 815    | 2386          | 0.0           | 945    | 2623          | 0.0           |
| 430    | 67605         | 14.3          | 560    | 114586        | 11.3          | 690    | 18544         | 0.0           | 820    | 2712          | 0.0           | 950    | 2969          | 0.0           |
| 435    | 102160        | 27.3          | 565    | 118987        | 8.4           | 695    | 16058         | 0.0           | 825    | 2473          | 0.0           | 955    | 2277          | 0.0           |
| 440    | 135103        | 45.1          | 570    | 122326        | 6.0           | 700    | 14133         | 0.0           | 830    | 1969          | 0.0           | 960    | 4267          | 0.0           |
| 445    | 140126        | 55.3          | 575    | 125968        | 4.2           | 705    | 12309         | 0.0           | 835    | 1917          | 0.0           | 965    | 2034          | 0.0           |
| 450    | 102339        | 47.2          | 580    | 127613        | 2.9           | 710    | 11142         | 0.0           | 840    | 2248          | 0.0           | 970    | 3586          | 0.0           |
| 455    | 58751         | 30.8          | 585    | 129466        | 1.9           | 715    | 10143         | 0.0           | 845    | 2266          | 0.0           | 975    | 2505          | 0.0           |
| 460    | 36892         | 21.7          | 590    | 128813        | 1.3           | 720    | 9072          | 0.0           | 850    | 2558          | 0.0           | 980    | 2666          | 0.0           |
| 465    | 24637         | 16.1          | 595    | 126387        | 0.8           | 725    | 8130          | 0.0           | 855    | 2767          | 0.0           | 985    | 2934          | 0.0           |
| 470    | 16738         | 12.0          | 600    | 123477        | 0.5           | 730    | 7149          | 0.0           | 860    | 2826          | 0.0           | 990    | 4120          | 0.0           |
| 475    | 13456         | 10.3          | 605    | 118718        | 0.3           | 735    | 6311          | 0.0           | 865    | 2385          | 0.0           | 995    | 3858          | 0.0           |
| 480    | 13081         | 10.5          | 610    | 112091        | 0.2           | 740    | 5711          | 0.0           | 870    | 3194          | 0.0           | 1000   | 3405          | 0.0           |
| 485    | 14734         | 12.1          | 615    | 105039        | 0.1           | 745    | 5111          | 0.0           | 875    | 3189          | 0.0           |        |               |               |

**Summary**

$R_f = 71.7$   
 $R_g = 96.9$   
 CIE  $R_a = 71.2$   
 $R_g = -29.7$



**Color Vector Graphics**





**Individual Sample Fidelity Index ( $R_{f,i}$ )**

|            |            |            |            |
|------------|------------|------------|------------|
| CES01 = 85 | CES26 = 55 | CES51 = 86 | CES76 = 45 |
| CES02 = 61 | CES27 = 80 | CES52 = 87 | CES77 = 68 |
| CES03 = 30 | CES28 = 79 | CES53 = 74 | CES78 = 49 |
| CES04 = 70 | CES29 = 51 | CES54 = 81 | CES79 = 77 |
| CES05 = 47 | CES30 = 60 | CES55 = 80 | CES80 = 75 |
| CES06 = 50 | CES31 = 56 | CES56 = 69 | CES81 = 75 |
| CES07 = 40 | CES32 = 52 | CES57 = 67 | CES82 = 90 |
| CES08 = 39 | CES33 = 62 | CES58 = 69 | CES83 = 85 |
| CES09 = 29 | CES34 = 65 | CES59 = 86 | CES84 = 87 |
| CES10 = 74 | CES35 = 81 | CES60 = 91 | CES85 = 83 |
| CES11 = 57 | CES36 = 92 | CES61 = 85 | CES86 = 72 |
| CES12 = 63 | CES37 = 74 | CES62 = 81 | CES87 = 77 |
| CES13 = 42 | CES38 = 69 | CES63 = 72 | CES88 = 77 |
| CES14 = 74 | CES39 = 92 | CES64 = 69 | CES89 = 72 |
| CES15 = 71 | CES40 = 86 | CES65 = 64 | CES90 = 75 |
| CES16 = 46 | CES41 = 84 | CES66 = 63 | CES91 = 91 |
| CES17 = 49 | CES42 = 75 | CES67 = 60 | CES92 = 66 |
| CES18 = 56 | CES43 = 70 | CES68 = 67 | CES93 = 80 |
| CES19 = 72 | CES44 = 98 | CES69 = 77 | CES94 = 56 |
| CES20 = 65 | CES45 = 80 | CES70 = 57 | CES95 = 72 |
| CES21 = 86 | CES46 = 77 | CES71 = 53 | CES96 = 78 |
| CES22 = 78 | CES47 = 74 | CES72 = 84 | CES97 = 83 |
| CES23 = 92 | CES48 = 66 | CES73 = 47 | CES98 = 73 |
| CES24 = 91 | CES49 = 76 | CES74 = 96 | CES99 = 63 |
| CES25 = 72 | CES50 = 85 | CES75 = 52 |            |



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)