

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: McGRAW-EDISON

Report Number: P643210

Luminaire Tested: GWS-SA6E-740-U-SLL-W-GRSWH

Issue Date: 1/10/2023

Test Information

Test Method: LM-79-2019
Report Number: P643210
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2209-782-39)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/10/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: McGRAW-EDISON
Catalog Number: GWS-SAGE-740-U-SLL-W-GRSWH
Description: GALLEON WALL SLIM LUMINAIRE. (6) LIGHTSQUARES WITH 16 LEDS EACH AND SPILL LIGHT ELIMINATOR LEFT OPTICS W/ FACTORY INSTALLED GLARE SHIELD, WH
Light Source: (96) 4000K CCT, 70 CRI LEDS
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 34843.8 lumens
Efficiency: N/A
Efficacy: 107.6 lumens/watt
Luminous Opening: Rectangular (W 2' x L: 1' x H: 0')
IES Classification: Type III - Short
BUG Rating: B4 - U0 - G3


Input Watts (W): 323.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 0
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT



REPORT NUMBER: P643210
 CATALOG NUMBER: GWS-SA6E-740-U-SLL-W-GRSWH

Iso-Footcandle Lines of Horizontal Illumination


× Max cd
 - - - 1/2 Max cd



Based on 30 foot mounting height. Maximum calculated value = 9.4 fc
 Type III - Short - N/A

REPORT NUMBER: P643210
CATALOG NUMBER: GWS-SA6E-740-U-SLL-W-GRSWH

Luminous Intensity Polar Plot



— Vertical Plane Through 315-Deg Lateral - - - Horizontal Cone Through 60-Deg Vertical

REPORT NUMBER: P643210

CATALOG NUMBER: GWS-SA6E-740-U-SLL-W-GRSWH


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	11919.7	0.0	11919.7
	% Fixture	34.2	0.0	34.2
Street Side	Lumens	22924.1	0.0	22924.1
	% Fixture	65.8	0.0	65.8
Total	Lumens	34843.8	0.0	34843.8
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	686.6	2.0
10°-20°	2202.2	6.3
20°-30°	3586.6	10.3
30°-40°	5038.4	14.5
40°-50°	6894.5	19.8
50°-60°	8845.3	25.4
60°-70°	5956.0	17.1
70°-80°	1489.0	4.3
80°-90°	145.2	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	34843.8	100.0
0°-180°	34843.8	100.0

Coefficient of Utilization



REPORT NUMBER: P643210


CATALOG NUMBER: GWS-SA6E-740-U-SLL-W-GRSWH

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	3602.0	10.3			
FM (30°-60°)	14126.0	40.5			
FH (60°-80°)	5158.3	14.8			G3/7500
FVH (80°-90°)	37.7	0.1			G1/100
BL (0°-30°)	2873.4	8.2	B4/5000		
BM (30°-60°)	6652.2	19.1	B4/8500		
BH (60°-80°)	2286.7	6.6	B3/2500		G3/2500
BVH (80°-90°)	107.4	0.3			G2/225
UL (90°-100°)	0.0	0.0		U0/0	
UH (100°-180°)	0.0	0.0		U0/0	

BUG Rating: B4-U0-G3

Type III Short





REPORT NUMBER: P643210

CATALOG NUMBER: GWS-SA6E-740-U-SLL-W-GRSWH

CANDELA DISTRIBUTION (FULL):

	0°	1°	5°	15°	25°	35°	45°	55°	65°	75°	85°
0°	7027.6	7027.6	7027.6	7027.6	7027.6	7027.6	7027.6	7027.6	7027.6	7027.6	7027.6
2.5°	7435.2	7419.1	7403.1	7277.9	7245.8	7156.0	7091.8	7011.6	6896.1	6831.9	6777.3
5°	7900.5	7874.8	7788.1	7531.4	7364.6	7181.7	7030.8	6864.0	6687.5	6572.0	6482.1
7.5°	8340.1	8333.7	8186.1	7762.5	7492.9	7229.8	7024.4	6780.5	6527.0	6353.7	6238.2
10°	8747.6	8699.5	8523.0	7971.1	7618.1	7316.4	7095.0	6825.5	6530.2	6296.0	6142.0
12.5°	9107.0	9046.1	8802.2	8163.6	7727.2	7354.9	7114.3	6892.8	6697.1	6501.4	6324.9
15°	9402.3	9328.4	9081.4	8343.3	7823.4	7332.5	6995.5	6822.3	6889.6	6976.3	6780.5
17.5°	9678.2	9601.2	9299.6	8474.9	7852.3	7194.5	6703.5	6629.7	6969.9	7364.6	7274.7
20°	9909.3	9822.6	9472.9	8539.0	7801.0	6931.4	6324.9	6453.2	6902.5	7374.2	7518.6
22.5°	10159.6	10089.0	9668.6	8632.1	7736.8	6568.7	6007.2	6321.7	6787.0	7200.9	7419.1
25°	10560.7	10474.0	9973.5	8795.8	7704.7	6228.6	5779.3	6193.3	6626.5	7002.0	7172.0
27.5°	11141.5	10981.1	10390.6	9081.4	7740.0	5907.7	5634.9	6036.1	6440.4	6761.3	6899.3
30°	11773.7	11581.1	10852.7	9376.6	7791.4	5712.0	5557.9	5856.4	6154.8	6475.7	6626.5
32.5°	12521.4	12351.3	11346.9	9598.0	7682.3	5622.1	5500.2	5660.6	5898.1	6154.8	6279.9
35°	13413.5	13108.6	11886.0	9777.7	7329.3	5490.5	5448.8	5445.6	5570.8	5821.1	5962.2
37.5°	14372.9	14045.6	12550.2	9970.2	6780.5	5281.9	5326.9	5192.1	5307.6	5506.6	5667.0
40°	15159.1	14815.8	13220.9	10233.4	6093.8	4954.6	5057.3	4912.9	4983.5	5188.9	5368.6
42.5°	15929.3	15563.5	13846.7	10531.8	5429.6	4633.7	4685.1	4630.5	4653.0	4868.0	5118.3
45°	16940.1	16529.4	14616.8	10743.6	4832.7	4380.2	4332.1	4239.0	4357.8	4636.9	4903.3
47.5°	18628.0	18137.0	15877.9	10881.6	4399.5	4235.8	4014.4	3959.9	4107.5	4418.7	4694.7
50°	20601.5	20177.9	17893.2	10875.2	4075.4	4113.9	3706.3	3658.2	3902.1	4216.6	4508.6
52.5°	22218.8	21788.8	19616.4	10554.3	3809.0	3854.0	3526.6	3391.9	3725.6	4017.6	4309.6
55°	23524.9	23040.3	20409.0	9212.9	3472.1	3440.0	3330.9	3083.8	3504.2	3818.7	4091.4
57.5°	22822.1	22244.5	19449.5	7005.2	3125.5	2923.4	2994.0	2811.0	3202.5	3597.2	3860.4
60°	19135.0	18615.2	15800.9	3728.8	2750.1	2442.0	2589.6	2618.5	2872.0	3330.9	3600.5
62.5°	13143.9	12765.2	10708.3	2262.3	2169.3	1960.7	2191.7	2400.3	2589.6	2977.9	3212.2
65°	6430.8	6318.4	5355.8	1450.5	1517.8	1585.2	1816.3	2069.8	2349.0	2689.1	2936.2
67.5°	1771.3	1784.2	1623.7	1132.8	1196.9	1383.1	1566.0	1768.1	2047.3	2361.8	2612.1
70°	779.8	792.6	818.3	872.8	994.8	1164.9	1354.2	1562.8	1819.5	2082.6	2323.3
72.5°	542.3	555.2	593.7	664.3	773.4	933.8	1113.5	1312.5	1578.8	1800.2	1999.2
75°	333.7	343.4	378.7	439.6	513.4	635.4	811.9	994.8	1229.0	1431.2	1607.7
77.5°	176.5	170.1	192.5	234.3	298.4	362.6	481.3	596.9	763.7	927.4	1075.0
80°	96.3	93.1	105.9	128.4	147.6	199.0	279.2	356.2	452.5	545.5	625.7
82.5°	41.7	38.5	41.7	54.6	67.4	96.3	141.2	195.7	250.3	314.5	365.8
85°	0.0	0.0	0.0	3.2	16.0	25.7	48.1	70.6	102.7	141.2	173.3
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	12.8	28.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P643210

CATALOG NUMBER: GWS-SA6E-740-U-SLL-W-GRSWH

CANDELA DISTRIBUTION (continued):

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	7027.6	7027.6	7027.6	7027.6	7027.6	7027.6	7027.6	7027.6	7027.6	7027.6	7027.6
2.5°	6745.2	6665.0	6658.6	6594.4	6600.8	6604.0	6539.9	6514.2	6536.7	6562.3	6549.5
5°	6450.0	6366.6	6331.3	6270.3	6263.9	6235.0	6209.3	6177.2	6199.7	6222.2	6235.0
7.5°	6193.3	6138.7	6116.3	6100.2	6106.7	6093.8	6042.5	6013.6	6010.4	6020.0	6032.8
10°	6109.9	6064.9	6093.8	6138.7	6170.8	6193.3	6138.7	6090.6	6045.7	6026.4	6026.4
12.5°	6289.6	6231.8	6289.6	6337.7	6401.9	6417.9	6357.0	6305.6	6289.6	6308.8	6347.3
15°	6687.5	6552.7	6549.5	6578.4	6629.7	6655.4	6597.6	6572.0	6572.0	6693.9	6790.2
17.5°	7085.4	6864.0	6770.9	6754.9	6787.0	6796.6	6748.4	6726.0	6783.7	7021.2	7200.9
20°	7364.6	7095.0	6892.8	6854.3	6864.0	6867.2	6828.7	6812.6	6896.1	7184.9	7335.7
22.5°	7335.7	7136.7	6889.6	6841.5	6857.5	6851.1	6815.8	6809.4	6876.8	7127.1	7197.7
25°	7136.7	6982.7	6774.1	6742.0	6767.7	6764.5	6729.2	6713.1	6742.0	6908.9	6915.3
27.5°	6908.9	6774.1	6594.4	6584.8	6626.5	6649.0	6588.0	6539.9	6530.2	6642.5	6616.9
30°	6636.1	6536.7	6392.2	6398.7	6475.7	6488.5	6414.7	6344.1	6324.9	6385.8	6350.5
32.5°	6312.0	6279.9	6202.9	6219.0	6292.8	6318.4	6241.4	6167.6	6145.2	6164.4	6090.6
35°	6036.1	6023.2	6029.6	6058.5	6122.7	6142.0	6077.8	6020.0	5987.9	5920.5	5824.3
37.5°	5750.5	5785.8	5878.8	5933.4	5968.7	5962.2	5927.0	5885.2	5833.9	5708.7	5590.0
40°	5484.1	5574.0	5740.8	5801.8	5814.6	5817.8	5792.2	5756.9	5692.7	5525.8	5391.1
42.5°	5278.7	5378.2	5599.6	5692.7	5699.1	5705.5	5679.9	5651.0	5561.1	5339.7	5208.1
45°	5063.7	5195.3	5455.2	5567.5	5561.1	5557.9	5535.5	5522.6	5416.7	5160.0	5015.6
47.5°	4880.8	5034.9	5314.0	5410.3	5407.1	5403.9	5387.8	5387.8	5281.9	5002.8	4839.1
50°	4701.1	4877.6	5169.6	5249.9	5256.3	5249.9	5243.4	5253.1	5127.9	4829.5	4669.0
52.5°	4505.4	4704.3	5009.2	5083.0	5121.5	5137.5	5137.5	5115.1	4967.5	4656.2	4479.7
55°	4290.4	4479.7	4832.7	4932.2	4964.3	4993.1	4993.1	4948.2	4810.2	4495.8	4306.4
57.5°	4024.0	4190.9	4470.1	4569.6	4646.6	4665.8	4665.8	4592.0	4479.7	4178.1	4024.0
60°	3735.2	3879.6	4069.0	4174.9	4232.6	4194.1	4223.0	4203.7	4113.9	3834.7	3706.3
62.5°	3350.2	3497.8	3706.3	3815.5	3841.1	3802.6	3841.1	3837.9	3716.0	3465.7	3311.6
65°	3074.2	3218.6	3424.0	3565.2	3606.9	3597.2	3622.9	3584.4	3433.6	3196.1	3048.5
67.5°	2746.9	2900.9	3138.4	3295.6	3382.2	3391.9	3427.2	3346.9	3192.9	2933.0	2746.9
70°	2435.6	2567.2	2750.1	2897.7	3019.6	3080.6	3087.0	2971.5	2779.0	2564.0	2429.2
72.5°	2108.3	2243.1	2464.5	2624.9	2779.0	2849.6	2849.6	2708.4	2499.8	2262.3	2117.9
75°	1710.4	1835.5	2037.7	2211.0	2387.5	2477.3	2474.1	2352.2	2121.1	1896.5	1745.7
77.5°	1158.4	1251.5	1379.9	1511.4	1537.1	1607.7	1643.0	1489.0	1360.6	1238.7	1103.9
80°	673.9	731.6	802.2	876.0	892.1	914.6	856.8	799.0	731.6	651.4	590.4
82.5°	394.7	433.2	468.5	526.3	535.9	542.3	491.0	465.3	410.7	362.6	324.1
85°	192.5	205.4	237.5	266.3	253.5	247.1	224.6	199.0	176.5	157.2	138.0
87.5°	38.5	38.5	57.8	54.6	44.9	38.5	22.5	28.9	6.4	6.4	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P643210

CATALOG NUMBER: GWS-SA6E-740-U-SLL-W-GRSWH

CANDELA DISTRIBUTION (continued):

	185°	195°	205°	215°	225°	235°	245°	255°	265°	270°	275°
0°	7027.6	7027.6	7027.6	7027.6	7027.6	7027.6	7027.6	7027.6	7027.6	7027.6	7027.6
2.5°	6591.2	6645.8	6713.1	6803.0	6905.7	7014.8	7120.7	7200.9	7281.1	7399.9	7380.6
5°	6254.3	6347.3	6453.2	6591.2	6758.1	6947.4	7159.2	7371.0	7598.8	7791.4	7874.8
7.5°	6058.5	6161.2	6286.4	6466.1	6681.1	6912.1	7210.5	7553.9	7922.9	8176.4	8333.7
10°	6058.5	6190.1	6353.7	6527.0	6716.4	6953.8	7322.8	7752.8	8227.8	8561.5	8744.4
12.5°	6408.3	6539.9	6575.2	6568.7	6674.6	6937.8	7412.7	7961.4	8529.4	8882.4	9107.0
15°	6953.8	6998.7	6732.4	6488.5	6504.6	6822.3	7454.4	8128.3	8789.3	9212.9	9456.8
17.5°	7319.6	7200.9	6726.0	6299.2	6209.3	6626.5	7454.4	8288.7	9065.3	9543.4	9771.3
20°	7348.5	7053.3	6562.3	6116.3	5885.2	6366.6	7403.1	8410.7	9331.7	9861.1	10105.0
22.5°	7095.0	6803.0	6389.0	5959.0	5618.9	6052.1	7319.6	8503.7	9559.5	10159.6	10461.2
25°	6806.2	6562.3	6212.5	5798.6	5436.0	5734.4	7242.6	8661.0	9877.2	10563.9	10868.8
27.5°	6523.8	6318.4	6000.8	5663.8	5333.3	5458.4	7194.5	8892.0	10255.8	11138.3	11401.4
30°	6247.8	6061.7	5772.9	5535.5	5278.7	5278.7	7152.8	9158.4	10756.4	11783.3	12046.4
32.5°	5968.7	5792.2	5557.9	5410.3	5246.7	5208.1	7037.3	9408.7	11273.1	12489.3	12758.8
35°	5708.7	5532.2	5352.5	5291.6	5230.6	5153.6	6751.7	9604.4	11776.9	13314.0	13545.0
37.5°	5464.9	5294.8	5160.0	5144.0	5150.4	5006.0	6302.4	9768.1	12405.8	14157.9	14279.9
40°	5253.1	5063.7	4957.8	4954.6	4986.7	4768.5	5734.4	10002.3	13124.6	14873.5	14822.2
42.5°	5063.7	4864.8	4736.4	4765.3	4746.1	4531.1	5179.3	10217.3	13750.4	15544.2	15441.5
45°	4877.6	4685.1	4505.4	4547.1	4524.6	4383.4	4707.5	10374.6	14443.5	16349.7	16362.5
47.5°	4697.9	4508.6	4328.9	4277.5	4274.3	4338.5	4344.9	10425.9	15573.1	17646.1	17354.1
50°	4531.1	4341.7	4155.6	3982.3	4049.7	4248.7	4075.4	10387.4	17264.2	19077.3	18262.2
52.5°	4357.8	4178.1	3972.7	3661.4	3837.9	4033.7	3834.7	10249.4	18297.5	20341.6	19853.8
55°	4158.8	3988.7	3709.6	3330.9	3545.9	3587.6	3587.6	8914.5	18737.1	21593.1	21894.7
57.5°	3892.5	3667.8	3225.0	2920.2	3112.7	2952.2	3324.5	6238.2	18011.9	21198.4	22369.7
60°	3590.8	3350.2	2881.6	2663.4	2721.2	2438.8	2833.5	3911.7	14928.1	18037.6	20065.6
62.5°	3192.9	2971.5	2583.2	2413.1	2294.4	1989.6	2281.6	2474.1	10233.4	13394.2	14777.3
65°	2926.6	2682.7	2336.1	2111.5	1867.6	1601.3	1514.6	1623.7	5503.4	7496.1	8429.9
67.5°	2612.1	2371.4	2044.1	1761.7	1566.0	1373.4	1222.6	1184.1	1886.9	2496.6	2701.9
70°	2313.7	2082.6	1809.9	1546.7	1351.0	1161.6	1014.0	908.1	872.8	866.4	853.6
72.5°	2008.8	1793.8	1566.0	1322.1	1107.1	933.8	802.2	680.3	629.0	612.9	596.9
75°	1646.2	1476.1	1248.3	985.2	811.9	651.4	548.7	468.5	423.6	407.5	388.3
77.5°	1059.0	981.9	783.0	635.4	491.0	388.3	333.7	282.4	253.5	247.1	231.0
80°	564.8	526.3	433.2	365.8	292.0	237.5	208.6	179.7	163.7	157.2	150.8
82.5°	314.5	285.6	240.7	211.8	170.1	144.4	128.4	115.5	105.9	102.7	99.5
85°	141.2	121.9	96.3	89.9	80.2	73.8	70.6	64.2	61.0	57.8	54.6
87.5°	6.4	12.8	16.0	12.8	12.8	19.3	22.5	22.5	19.3	19.3	16.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P643210

CATALOG NUMBER: GWS-SA6E-740-U-SLL-W-GRSWH

CANDELA DISTRIBUTION (continued):

	285°	295°	305°	315°	325°	335°	345°	355°	359°	360°
0°	7027.6	7027.6	7027.6	7027.6	7027.6	7027.6	7027.6	7027.6	7027.6	7027.6
2.5°	7499.3	7595.6	7605.2	7637.3	7595.6	7586.0	7518.6	7480.1	7444.8	7435.2
5°	8083.4	8275.9	8352.9	8407.5	8356.1	8330.5	8182.8	8028.8	7942.2	7900.5
7.5°	8683.4	8972.3	9123.1	9190.5	9196.9	9081.4	8827.9	8539.0	8394.6	8340.1
10°	9219.3	9575.5	9774.5	9902.9	9857.9	9716.7	9370.2	8978.7	8795.8	8747.6
12.5°	9617.3	9957.4	10111.4	10194.9	10191.7	10114.6	9787.3	9363.7	9155.2	9107.0
15°	9874.0	10076.1	10085.8	10105.0	10159.6	10262.3	10092.2	9700.7	9469.6	9402.3
17.5°	10076.1	9995.9	9845.1	9793.7	9915.7	10201.3	10304.0	9986.3	9736.0	9678.2
20°	10204.5	9800.2	9533.8	9434.3	9575.5	10040.8	10432.3	10243.0	9983.1	9909.3
22.5°	10304.0	9617.3	9187.3	9119.9	9267.5	9867.6	10563.9	10547.9	10262.3	10159.6
25°	10461.2	9495.3	8943.4	8895.2	9033.2	9784.1	10740.4	10961.8	10708.3	10560.7
27.5°	10708.3	9482.5	8818.2	8802.2	8991.5	9857.9	10993.9	11568.3	11250.6	11141.5
30°	11051.7	9604.4	8847.1	8879.2	9110.2	10124.3	11388.6	12261.4	11943.8	11773.7
32.5°	11545.8	9931.7	9286.7	9424.7	9594.8	10551.1	11966.2	13012.3	12771.7	12521.4
35°	12197.3	10830.2	10586.4	11173.6	11013.2	11484.9	12662.6	13923.7	13631.7	13413.5
37.5°	13066.9	12672.2	12896.8	13705.5	13317.2	13249.8	13512.9	14751.6	14591.1	14372.9
40°	14286.3	14366.5	14780.5	15842.6	15281.1	14847.9	14555.8	15374.1	15428.7	15159.1
42.5°	15095.0	15464.0	16462.0	17668.5	16895.2	15858.7	15428.7	16170.0	16173.2	15929.3
45°	15396.6	16362.5	18448.3	19837.8	18544.6	16436.3	15910.0	17251.4	17219.3	16940.1
47.5°	15287.5	17119.8	20511.7	22636.0	20662.5	16847.0	15842.6	18791.7	19051.6	18628.0
50°	15059.7	17880.3	22921.6	26063.2	23261.8	17283.5	15740.0	20498.8	20928.8	20601.5
52.5°	15290.7	18727.5	25771.2	29605.9	26522.1	17979.8	16433.1	22690.6	22613.5	22218.8
55°	16022.3	19728.7	29233.6	34056.7	30103.3	19157.5	18214.1	24779.6	23996.6	23524.9
57.5°	15987.0	20444.3	32269.3	37576.9	33219.2	20123.4	18833.4	25001.0	23419.0	22822.1
60°	14510.9	20117.0	33424.5	39803.9	34159.4	19590.7	16795.7	22331.2	19760.8	19135.0
62.5°	10830.2	17851.4	31184.7	37015.4	31499.2	16920.9	12630.5	16028.8	14199.7	13143.9
65°	6928.1	13965.4	26217.2	29987.7	25963.7	12941.7	7521.8	8593.6	6732.4	6430.8
67.5°	2949.0	9857.9	20380.1	20043.2	19423.8	8385.0	2904.1	2419.6	1803.4	1771.3
70°	975.5	6706.7	12563.1	13368.5	11600.4	5776.1	959.5	811.9	808.7	779.8
72.5°	638.6	3600.5	7072.5	7874.8	7464.0	3324.5	580.8	542.3	555.2	542.3
75°	381.9	783.0	1190.5	1546.7	1190.5	558.4	349.8	343.4	349.8	333.7
77.5°	224.6	218.2	211.8	211.8	208.6	192.5	176.5	170.1	173.3	176.5
80°	144.4	138.0	131.6	128.4	112.3	105.9	99.5	93.1	93.1	96.3
82.5°	93.1	86.6	80.2	70.6	57.8	48.1	44.9	38.5	38.5	41.7
85°	48.1	38.5	28.9	22.5	12.8	6.4	0.0	0.0	0.0	0.0
87.5°	9.6	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)