

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: McGRAW-EDISON

Report Number: P631355

Luminaire Tested: GWS-SA1F-740-U-T4FT-W

Issue Date: 1/10/2023

Test Information

Test Method: LM-79-2019
Report Number: P631355
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2209-782-54)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/10/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: McGRAW-EDISON
Catalog Number: GWS-SA1F-740-U-T4FT-W
Description: GALLEON WALL SLIM LUMINAIRE. (1) LIGHTSQUARES WITH 16 LEDS EACH AND TYPE IV FORWARD THROW OPTICS
Light Source: (16) 4000K CCT, 70 CRI LEDS
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8137.7 lumens
Efficiency: N/A
Efficacy: 121.1 lumens/watt
Luminous Opening: Rectangular (W 0.5' x L: 0.5' x H: 0')
IES Classification: Type IV - Short
BUG Rating: B1 - U0 - G2


Input Watts (W): 67.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 0
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT



REPORT NUMBER: P631355
 CATALOG NUMBER: GWS-SA1F-740-U-T4FT-W

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 10 foot mounting height. Maximum calculated value = 12.7 fc
 Type IV - Short - N/A

REPORT NUMBER: P631355
CATALOG NUMBER: GWS-SA1F-740-U-T4FT-W

Luminous Intensity Polar Plot



— Vertical Plane Through 36-Deg Lateral - - - Horizontal Cone Through 72.5-Deg Vertical



REPORT NUMBER: P631355
 CATALOG NUMBER: GWS-SA1F-740-U-T4FT-W


FLUX DISTRIBUTION:

| | | Downward | Upward | Total |
|--------------------|-----------|----------|--------|--------|
| House Side | Lumens | 1876.1 | 0.0 | 1876.1 |
| | % Fixture | 23.1 | 0.0 | 23.1 |
| Street Side | Lumens | 6261.6 | 0.0 | 6261.6 |
| | % Fixture | 76.9 | 0.0 | 76.9 |
| Total | Lumens | 8137.7 | 0.0 | 8137.7 |
| | % Fixture | 100.0 | 0.0 | 100.0 |

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 111.3 | 1.4 |
| 10°-20° | 314.1 | 3.9 |
| 20°-30° | 520.2 | 6.4 |
| 30°-40° | 779.0 | 9.6 |
| 40°-50° | 1136.5 | 14.0 |
| 50°-60° | 1617.6 | 19.9 |
| 60°-70° | 2043.7 | 25.1 |
| 70°-80° | 1456.3 | 17.9 |
| 80°-90° | 159.0 | 2.0 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-90° | 8137.7 | 100.0 |
| 0°-180° | 8137.7 | 100.0 |

Coefficient of Utilization



REPORT NUMBER: P631355


CATALOG NUMBER: GWS-SA1F-740-U-T4FT-W

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

| Zone | Lumens | % Fixture | Zone Rating/Lumen Limit | | |
|----------------|--------|-----------|-------------------------|------|---------|
| | | | B | U | G |
| FL (0°-30°) | 454.3 | 5.6 | | | |
| FM (30°-60°) | 2607.9 | 32.0 | | | |
| FH (60°-80°) | 3085.3 | 37.9 | | | G2/5000 |
| FVH (80°-90°) | 114.1 | 1.4 | | | G2/225 |
| BL (0°-30°) | 491.3 | 6.0 | B1/500 | | |
| BM (30°-60°) | 925.2 | 11.4 | B1/1000 | | |
| BH (60°-80°) | 414.8 | 5.1 | B1/500 | | G1/500 |
| BVH (80°-90°) | 44.9 | 0.6 | | | G1/100 |
| UL (90°-100°) | 0.0 | 0.0 | | U0/0 | |
| UH (100°-180°) | 0.0 | 0.0 | | U0/0 | |

BUG Rating: B1-U0-G2

Type IV Short





REPORT NUMBER: P631355
 CATALOG NUMBER: GWS-SA1F-740-U-T4FT-W

CANDELA DISTRIBUTION (FULL):

| | 0° | 5° | 15° | 25° | 35° | 36° | 45° | 55° | 65° | 75° | 85° |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 1191.0 | 1191.0 | 1191.0 | 1191.0 | 1191.0 | 1191.0 | 1191.0 | 1191.0 | 1191.0 | 1191.0 | 1191.0 |
| 2.5° | 1086.5 | 1084.7 | 1081.1 | 1091.9 | 1102.8 | 1101.6 | 1116.7 | 1131.2 | 1146.9 | 1163.2 | 1184.9 |
| 5° | 999.5 | 998.3 | 995.3 | 1011.6 | 1027.9 | 1027.3 | 1052.1 | 1075.6 | 1107.6 | 1142.7 | 1186.2 |
| 7.5° | 912.6 | 909.5 | 913.8 | 934.3 | 957.3 | 959.7 | 993.5 | 1032.2 | 1078.7 | 1131.2 | 1192.8 |
| 10° | 835.9 | 835.3 | 837.1 | 860.0 | 894.4 | 896.9 | 940.3 | 994.1 | 1055.7 | 1125.8 | 1207.9 |
| 12.5° | 815.9 | 814.7 | 809.9 | 821.4 | 847.3 | 851.0 | 898.7 | 964.5 | 1040.0 | 1128.8 | 1228.4 |
| 15° | 848.5 | 845.5 | 828.6 | 823.2 | 835.9 | 838.9 | 879.4 | 947.0 | 1030.9 | 1134.2 | 1254.4 |
| 17.5° | 904.7 | 902.9 | 870.9 | 848.5 | 857.0 | 859.4 | 889.6 | 944.0 | 1028.5 | 1145.1 | 1286.4 |
| 20° | 986.9 | 979.0 | 928.9 | 895.1 | 895.1 | 898.7 | 916.8 | 957.3 | 1031.5 | 1158.4 | 1322.6 |
| 22.5° | 1095.6 | 1079.9 | 1009.2 | 963.3 | 951.2 | 956.1 | 963.9 | 990.5 | 1044.2 | 1180.7 | 1367.9 |
| 25° | 1217.6 | 1203.1 | 1119.1 | 1054.5 | 1037.6 | 1039.4 | 1032.8 | 1037.6 | 1072.0 | 1211.5 | 1424.1 |
| 27.5° | 1347.4 | 1337.7 | 1248.4 | 1166.2 | 1139.7 | 1139.7 | 1116.1 | 1104.6 | 1110.7 | 1246.6 | 1486.9 |
| 30° | 1463.4 | 1450.1 | 1374.6 | 1284.6 | 1249.6 | 1249.6 | 1204.9 | 1180.1 | 1165.6 | 1289.4 | 1570.9 |
| 32.5° | 1524.4 | 1516.5 | 1466.4 | 1397.5 | 1354.7 | 1348.0 | 1309.4 | 1280.4 | 1246.6 | 1352.8 | 1684.4 |
| 35° | 1604.1 | 1602.3 | 1572.1 | 1518.3 | 1464.0 | 1454.3 | 1427.7 | 1404.8 | 1346.2 | 1432.0 | 1835.4 |
| 37.5° | 1704.3 | 1701.3 | 1696.5 | 1664.5 | 1599.3 | 1597.4 | 1573.9 | 1546.1 | 1470.0 | 1546.1 | 2018.4 |
| 40° | 1816.7 | 1811.2 | 1805.2 | 1804.6 | 1765.3 | 1758.7 | 1756.9 | 1725.5 | 1619.2 | 1683.8 | 2209.2 |
| 42.5° | 1971.3 | 1952.6 | 1895.8 | 1921.2 | 1950.2 | 1944.1 | 1967.1 | 1920.0 | 1805.2 | 1847.5 | 2389.8 |
| 45° | 2161.5 | 2115.6 | 2003.3 | 2010.5 | 2083.6 | 2095.7 | 2175.4 | 2164.0 | 2009.9 | 2036.5 | 2580.1 |
| 47.5° | 2275.7 | 2235.8 | 2131.3 | 2125.3 | 2216.5 | 2231.6 | 2404.9 | 2426.7 | 2230.4 | 2264.2 | 2815.0 |
| 50° | 2369.3 | 2341.5 | 2255.8 | 2264.2 | 2360.8 | 2375.9 | 2632.6 | 2679.1 | 2438.1 | 2497.3 | 3088.0 |
| 52.5° | 2482.2 | 2442.4 | 2375.9 | 2415.8 | 2534.2 | 2552.3 | 2885.7 | 2935.8 | 2625.4 | 2753.4 | 3370.6 |
| 55° | 2545.6 | 2529.3 | 2530.5 | 2591.5 | 2740.1 | 2764.9 | 3150.8 | 3142.4 | 2796.9 | 2972.6 | 3583.2 |
| 57.5° | 2691.8 | 2685.8 | 2741.3 | 2764.3 | 2980.5 | 3012.5 | 3415.9 | 3343.5 | 2952.7 | 3142.4 | 3685.3 |
| 60° | 2949.7 | 2934.6 | 2982.9 | 3017.9 | 3277.6 | 3322.9 | 3711.9 | 3540.4 | 3058.4 | 3268.6 | 3650.9 |
| 62.5° | 3312.1 | 3293.3 | 3295.1 | 3350.7 | 3675.6 | 3723.4 | 4041.0 | 3704.6 | 3091.0 | 3287.9 | 3432.9 |
| 65° | 3762.6 | 3735.4 | 3704.6 | 3780.1 | 4204.1 | 4244.0 | 4399.2 | 3824.2 | 3013.1 | 3101.9 | 2977.5 |
| 67.5° | 4237.9 | 4215.6 | 4179.3 | 4337.6 | 4888.4 | 4912.5 | 4800.8 | 3813.9 | 2766.1 | 2604.2 | 2088.5 |
| 70° | 4265.7 | 4271.1 | 4442.7 | 5015.2 | 5781.6 | 5787.7 | 5180.7 | 3607.4 | 2240.0 | 1688.0 | 1040.6 |
| 72.5° | 3979.4 | 3970.4 | 4193.8 | 5139.0 | 6500.3 | 6520.8 | 5360.1 | 2922.5 | 1384.3 | 841.9 | 488.0 |
| 75° | 3232.3 | 3248.0 | 3483.0 | 4496.4 | 5571.4 | 5589.6 | 4369.6 | 1723.1 | 657.7 | 411.9 | 312.2 |
| 77.5° | 1391.5 | 1479.1 | 1942.3 | 3167.7 | 3990.3 | 3934.1 | 2252.1 | 698.2 | 350.9 | 293.5 | 239.2 |
| 80° | 401.6 | 436.1 | 692.1 | 1506.3 | 2391.0 | 2348.8 | 891.4 | 261.5 | 244.6 | 220.4 | 171.5 |
| 82.5° | 129.8 | 143.7 | 253.7 | 599.7 | 1071.4 | 1070.2 | 338.2 | 154.6 | 160.0 | 149.8 | 110.5 |
| 85° | 36.2 | 41.7 | 77.9 | 181.8 | 331.6 | 324.9 | 97.8 | 73.1 | 85.2 | 86.4 | 55.0 |
| 87.5° | 0.0 | 0.0 | 0.6 | 1.2 | 1.2 | 1.2 | 2.4 | 10.9 | 24.8 | 31.4 | 22.3 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P631355
 CATALOG NUMBER: GWS-SA1F-740-U-T4FT-W

CANDELA DISTRIBUTION (continued):

| | 90° | 95° | 105° | 115° | 125° | 135° | 145° | 155° | 165° | 175° | 180° |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 1191.0 | 1191.0 | 1191.0 | 1191.0 | 1191.0 | 1191.0 | 1191.0 | 1191.0 | 1191.0 | 1191.0 | 1191.0 |
| 2.5° | 1198.2 | 1196.4 | 1221.2 | 1240.5 | 1258.6 | 1270.7 | 1274.3 | 1276.7 | 1281.6 | 1284.0 | 1281.6 |
| 5° | 1206.7 | 1215.8 | 1256.8 | 1287.0 | 1311.2 | 1325.7 | 1326.3 | 1325.1 | 1328.7 | 1325.7 | 1323.9 |
| 7.5° | 1224.8 | 1242.3 | 1294.3 | 1326.3 | 1342.0 | 1342.6 | 1328.1 | 1311.2 | 1302.7 | 1295.5 | 1293.1 |
| 10° | 1249.0 | 1274.9 | 1331.7 | 1352.8 | 1348.0 | 1325.7 | 1293.7 | 1267.1 | 1252.0 | 1241.1 | 1238.7 |
| 12.5° | 1282.2 | 1311.2 | 1364.9 | 1364.3 | 1334.1 | 1294.3 | 1256.8 | 1224.8 | 1203.1 | 1190.4 | 1186.2 |
| 15° | 1313.6 | 1350.4 | 1389.1 | 1360.7 | 1313.0 | 1264.7 | 1216.4 | 1173.5 | 1144.5 | 1124.6 | 1120.9 |
| 17.5° | 1352.2 | 1391.5 | 1406.6 | 1349.2 | 1286.4 | 1224.2 | 1159.6 | 1103.4 | 1064.2 | 1040.6 | 1038.8 |
| 20° | 1396.9 | 1432.0 | 1415.1 | 1329.3 | 1252.0 | 1170.5 | 1082.9 | 1020.1 | 977.8 | 954.8 | 956.7 |
| 22.5° | 1448.9 | 1474.2 | 1417.5 | 1302.1 | 1204.3 | 1094.4 | 996.5 | 936.1 | 907.7 | 895.7 | 896.3 |
| 25° | 1504.4 | 1520.7 | 1413.2 | 1265.3 | 1131.2 | 1001.3 | 907.7 | 880.0 | 877.5 | 874.5 | 875.7 |
| 27.5° | 1570.3 | 1566.6 | 1400.6 | 1213.3 | 1032.8 | 893.2 | 845.5 | 852.8 | 862.4 | 861.2 | 862.4 |
| 30° | 1658.4 | 1624.0 | 1384.3 | 1141.5 | 915.6 | 802.6 | 808.7 | 829.2 | 841.9 | 843.1 | 846.7 |
| 32.5° | 1759.3 | 1687.4 | 1358.3 | 1043.6 | 803.9 | 751.9 | 774.3 | 799.0 | 814.1 | 817.1 | 822.0 |
| 35° | 1879.5 | 1759.9 | 1312.4 | 921.6 | 723.5 | 721.7 | 742.3 | 759.2 | 775.5 | 776.7 | 776.7 |
| 37.5° | 2017.8 | 1832.4 | 1239.3 | 786.9 | 674.0 | 695.8 | 715.1 | 718.7 | 722.9 | 719.3 | 721.1 |
| 40° | 2144.6 | 1902.4 | 1135.4 | 664.3 | 633.5 | 672.8 | 689.1 | 677.0 | 663.7 | 654.7 | 656.5 |
| 42.5° | 2250.9 | 1950.2 | 997.7 | 578.6 | 592.5 | 652.3 | 664.9 | 640.2 | 614.2 | 597.3 | 599.7 |
| 45° | 2370.5 | 1994.2 | 835.9 | 520.6 | 557.4 | 637.8 | 646.2 | 614.2 | 581.0 | 555.6 | 552.0 |
| 47.5° | 2535.4 | 2084.2 | 692.1 | 480.1 | 532.7 | 629.9 | 643.8 | 600.3 | 556.8 | 518.8 | 514.6 |
| 50° | 2738.9 | 2211.7 | 571.9 | 453.6 | 521.2 | 625.7 | 643.2 | 585.2 | 533.3 | 488.6 | 485.6 |
| 52.5° | 2961.2 | 2336.1 | 483.2 | 433.0 | 509.7 | 613.0 | 640.2 | 568.3 | 508.5 | 460.2 | 456.6 |
| 55° | 3109.1 | 2385.0 | 423.4 | 413.7 | 491.0 | 593.1 | 628.1 | 552.0 | 471.1 | 427.0 | 421.6 |
| 57.5° | 3152.6 | 2322.2 | 381.7 | 396.2 | 466.9 | 565.3 | 605.2 | 517.6 | 448.1 | 413.1 | 408.9 |
| 60° | 3077.7 | 2164.0 | 355.7 | 381.7 | 440.3 | 529.7 | 565.3 | 497.7 | 430.0 | 398.6 | 395.6 |
| 62.5° | 2866.3 | 1920.0 | 335.8 | 366.6 | 413.1 | 492.2 | 539.9 | 473.5 | 410.1 | 385.3 | 381.1 |
| 65° | 2441.2 | 1574.5 | 319.5 | 350.9 | 387.1 | 456.6 | 512.1 | 449.3 | 388.3 | 369.6 | 364.8 |
| 67.5° | 1707.4 | 1105.8 | 302.0 | 332.2 | 361.2 | 422.2 | 483.2 | 427.0 | 366.0 | 352.1 | 347.3 |
| 70° | 834.7 | 586.4 | 280.8 | 310.4 | 333.4 | 387.1 | 454.2 | 399.8 | 336.4 | 328.5 | 321.9 |
| 72.5° | 397.4 | 327.9 | 256.1 | 280.8 | 295.3 | 340.6 | 405.9 | 360.6 | 301.4 | 284.5 | 273.0 |
| 75° | 266.3 | 233.1 | 223.5 | 245.8 | 249.4 | 285.7 | 347.9 | 311.0 | 265.7 | 246.4 | 236.7 |
| 77.5° | 201.7 | 178.2 | 187.8 | 207.8 | 200.5 | 234.9 | 286.3 | 277.2 | 239.8 | 222.3 | 217.4 |
| 80° | 141.9 | 129.8 | 149.2 | 161.3 | 155.8 | 199.9 | 257.9 | 237.4 | 197.5 | 178.2 | 174.5 |
| 82.5° | 89.4 | 87.0 | 109.9 | 111.7 | 113.5 | 158.2 | 212.0 | 186.6 | 153.4 | 126.2 | 117.2 |
| 85° | 44.7 | 49.5 | 65.8 | 65.8 | 65.2 | 81.5 | 120.8 | 105.1 | 82.7 | 65.8 | 64.0 |
| 87.5° | 15.1 | 21.1 | 28.4 | 23.0 | 17.5 | 13.9 | 15.7 | 19.3 | 20.5 | 19.9 | 19.9 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |

LM-79-08: Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Report Prepared for

Cooper Lighting Solutions

MCGRAW, INVUE, LUMARK AND STREETWORKS

DATA VALID FOR LUMINAIRES UTILIZING SA LIGHT ENGINES

Report Number: SP1-2101-121-2

Luminaire Tested: IFLD-S-SA2A-740-U-T3R-HSS

Test Date: 03/05/2021

Test Information

Test Method: LM-79-08
 Report Number: SP1-2101-121-2
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1
 Measurement Geometry: 4π
 Issue Date: 03/05/2021
 Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
 Product Line: STREETWORKS
 Catalog Number: **IFLD-S-SA2A-740-U-T3R-HSS**
 Description: STREETWORKS INF FLOOD

SHIELD, DRIVER PROGRAMMED @ 615mA.

Spectral Parameters

| | | | | | |
|---------------------------|---------|-----------|------|------|-------|
| CCT (K): | 3905 | CRI (Ra): | 71.2 | R9: | -29.7 |
| CIE u': | 0.2273 | R1: | 68.9 | R10: | 46.2 |
| CIE v': | 0.5024 | R2: | 77.0 | R11: | 68.8 |
| Duv: | -0.0008 | R3: | 84.0 | R12: | 45.6 |
| CIE x: | 0.3841 | R4: | 71.6 | R13: | 69.5 |
| CIE y: | 0.3774 | R5: | 68.9 | R14: | 90.7 |
| CIE z: | 0.2385 | R6: | 68.3 | | |
| Peak Wavelength (nm): | 443 | R7: | 78.7 | | |
| Dominant Wavelength (nm): | 579 | R8: | 52.2 | | |
| Purity: | 28.7 | | | | |
| Rf: | 71.7 | | | | |
| Rg: | 96.9 | | | | |



Test Conditions

Stabilization Time: 211M
 Operation Time: 12H
 Room Temperature (°C) / RH%: 24.8/312%
 Sphere Temperature (°C): 24.1

REPORT NUMBER: SP1-2101-121-2

| Measurement and Test Equipment | | | |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument | Identification Number | Calibration Date | Calibration Due Date |
| Photometer | IN0058 | 1/31/2021 | 7/31/2021 |
| Power Meter | IN0071 | 12/1/2020 | 12/1/2021 |
| AC Power Source | IN0063 | 12/1/2020 | 12/1/2021 |
| DC Power Source | IN0208 | 12/1/2020 | 12/1/2021 |
| Sphere Thermometer | IN0085 | 12/1/2020 | 12/1/2021 |
| Room Thermometer | IN0046 | 12/1/2020 | 12/1/2021 |

REPORT NUMBER: SP1-2101-121-2

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



CCT = 3905K
 CIE x = 0.3841
 CIE y = 0.3774
 Duv = -0.0008

Point lies inside the ANSI 4000K 4-step quadrangle

REPORT NUMBER: SP1-2101-121-2

Photopic Flux vs. Wavelength



#####

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 2304 | 0.0 | 490 | 19043 | 2.7 | 620 | 97577 | 25.4 | 750 | 4830 | 0.0 | 880 | 3505 | 0.0 |
| 365 | 2150 | 0.0 | 495 | 26606 | 4.8 | 625 | 90158 | 19.9 | 755 | 4664 | 0.0 | 885 | 2991 | 0.0 |
| 370 | 2146 | 0.0 | 500 | 36376 | 8.0 | 630 | 82240 | 14.9 | 760 | 4006 | 0.0 | 890 | 2327 | 0.0 |
| 375 | 2332 | 0.0 | 505 | 47714 | 13.3 | 635 | 74361 | 11.2 | 765 | 3715 | 0.0 | 895 | 2775 | 0.0 |
| 380 | 2527 | 0.0 | 510 | 58741 | 20.2 | 640 | 66994 | 8.0 | 770 | 3696 | 0.0 | 900 | 2141 | 0.0 |
| 385 | 2304 | 0.0 | 515 | 68716 | 28.5 | 645 | 60405 | 5.8 | 775 | 3117 | 0.0 | 905 | 2421 | 0.0 |
| 390 | 2064 | 0.0 | 520 | 77136 | 37.4 | 650 | 53806 | 3.9 | 780 | 3062 | 0.0 | 910 | 2200 | 0.0 |
| 395 | 1856 | 0.0 | 525 | 83567 | 44.9 | 655 | 47610 | 2.7 | 785 | 2907 | 0.0 | 915 | 2716 | 0.0 |
| 400 | 1856 | 0.0 | 530 | 89283 | 52.6 | 660 | 42018 | 1.8 | 790 | 2655 | 0.0 | 920 | 2656 | 0.0 |
| 405 | 2374 | 0.0 | 535 | 94097 | 58.4 | 665 | 36742 | 1.2 | 795 | 2467 | 0.0 | 925 | 2671 | 0.0 |
| 410 | 4084 | 0.0 | 540 | 96845 | 63.1 | 670 | 32105 | 0.7 | 800 | 2609 | 0.0 | 930 | 3292 | 0.0 |
| 415 | 8543 | 0.0 | 545 | 100829 | 67.1 | 675 | 27946 | 0.5 | 805 | 2293 | 0.0 | 935 | 3188 | 0.0 |
| 420 | 18394 | 0.1 | 550 | 105648 | 71.8 | 680 | 24146 | 0.3 | 810 | 2188 | 0.0 | 940 | 1997 | 0.0 |
| 425 | 37987 | 0.2 | 555 | 110017 | 75.1 | 685 | 21191 | 0.2 | 815 | 2386 | 0.0 | 945 | 2623 | 0.0 |
| 430 | 67605 | 0.5 | 560 | 114586 | 77.9 | 690 | 18544 | 0.1 | 820 | 2712 | 0.0 | 950 | 2969 | 0.0 |
| 435 | 102160 | 1.2 | 565 | 118987 | 79.1 | 695 | 16058 | 0.1 | 825 | 2473 | 0.0 | 955 | 2277 | 0.0 |
| 440 | 135103 | 2.1 | 570 | 122326 | 79.5 | 700 | 14133 | 0.0 | 830 | 1969 | 0.0 | 960 | 4267 | 0.0 |
| 445 | 140126 | 2.9 | 575 | 125968 | 78.4 | 705 | 12309 | 0.0 | 835 | 1917 | 0.0 | 965 | 2034 | 0.0 |
| 450 | 102339 | 2.7 | 580 | 127613 | 75.8 | 710 | 11142 | 0.0 | 840 | 2248 | 0.0 | 970 | 3586 | 0.0 |
| 455 | 58751 | 2.0 | 585 | 129466 | 71.9 | 715 | 10143 | 0.0 | 845 | 2266 | 0.0 | 975 | 2505 | 0.0 |
| 460 | 36892 | 1.5 | 590 | 128813 | 66.6 | 720 | 9072 | 0.0 | 850 | 2558 | 0.0 | 980 | 2666 | 0.0 |
| 465 | 24637 | 1.3 | 595 | 126387 | 59.9 | 725 | 8130 | 0.0 | 855 | 2767 | 0.0 | 985 | 2934 | 0.0 |
| 470 | 16738 | 1.0 | 600 | 123477 | 53.2 | 730 | 7149 | 0.0 | 860 | 2826 | 0.0 | 990 | 4120 | 0.0 |
| 475 | 13456 | 1.1 | 605 | 118718 | 46.0 | 735 | 6311 | 0.0 | 865 | 2385 | 0.0 | 995 | 3858 | 0.0 |
| 480 | 13081 | 1.2 | 610 | 112091 | 38.5 | 740 | 5711 | 0.0 | 870 | 3194 | 0.0 | 1000 | 3405 | 0.0 |
| 485 | 14734 | 1.7 | 615 | 105039 | 31.7 | 745 | 5111 | 0.0 | 875 | 3189 | 0.0 | | | |

REPORT NUMBER: SP1-2101-121-2

Scotopic Flux vs. Wavelength



Scotopic Lumens: 10425.8 S/P: 1.47

| λ (nm) | Power (µW/nm) | Lumens (Φ/nm) | λ (nm) | Power (µW/nm) | Lumens (Φ/nm) | λ (nm) | Power (µW/nm) | Lumens (Φ/nm) | λ (nm) | Power (µW/nm) | Lumens (Φ/nm) | λ (nm) | Power (µW/nm) | Lumens (Φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 2304 | 0.0 | 490 | 19043 | 29.3 | 620 | 97577 | 1.2 | 750 | 4830 | 0.0 | 880 | 3505 | 0.0 |
| 365 | 2150 | 0.0 | 495 | 26606 | 43.0 | 625 | 90158 | 0.8 | 755 | 4664 | 0.0 | 885 | 2991 | 0.0 |
| 370 | 2146 | 0.0 | 500 | 36376 | 60.8 | 630 | 82240 | 0.5 | 760 | 4006 | 0.0 | 890 | 2327 | 0.0 |
| 375 | 2332 | 0.0 | 505 | 47714 | 81.1 | 635 | 74361 | 0.3 | 765 | 3715 | 0.0 | 895 | 2775 | 0.0 |
| 380 | 2527 | 0.0 | 510 | 58741 | 99.6 | 640 | 66994 | 0.2 | 770 | 3696 | 0.0 | 900 | 2141 | 0.0 |
| 385 | 2304 | 0.0 | 515 | 68716 | 113.9 | 645 | 60405 | 0.1 | 775 | 3117 | 0.0 | 905 | 2421 | 0.0 |
| 390 | 2064 | 0.0 | 520 | 77136 | 122.6 | 650 | 53806 | 0.1 | 780 | 3062 | 0.0 | 910 | 2200 | 0.0 |
| 395 | 1856 | 0.0 | 525 | 83567 | 125.0 | 655 | 47610 | 0.0 | 785 | 2907 | 0.0 | 915 | 2716 | 0.0 |
| 400 | 1856 | 0.0 | 530 | 89283 | 123.1 | 660 | 42018 | 0.0 | 790 | 2655 | 0.0 | 920 | 2656 | 0.0 |
| 405 | 2374 | 0.1 | 535 | 94097 | 117.3 | 665 | 36742 | 0.0 | 795 | 2467 | 0.0 | 925 | 2671 | 0.0 |
| 410 | 4084 | 0.2 | 540 | 96845 | 107.0 | 670 | 32105 | 0.0 | 800 | 2609 | 0.0 | 930 | 3292 | 0.0 |
| 415 | 8543 | 0.9 | 545 | 100829 | 96.7 | 675 | 27946 | 0.0 | 805 | 2293 | 0.0 | 935 | 3188 | 0.0 |
| 420 | 18394 | 3.0 | 550 | 105648 | 86.4 | 680 | 24146 | 0.0 | 810 | 2188 | 0.0 | 940 | 1997 | 0.0 |
| 425 | 37987 | 9.3 | 555 | 110017 | 75.2 | 685 | 21191 | 0.0 | 815 | 2386 | 0.0 | 945 | 2623 | 0.0 |
| 430 | 67605 | 23.0 | 560 | 114586 | 64.0 | 690 | 18544 | 0.0 | 820 | 2712 | 0.0 | 950 | 2969 | 0.0 |
| 435 | 102160 | 45.7 | 565 | 118987 | 53.4 | 695 | 16058 | 0.0 | 825 | 2473 | 0.0 | 955 | 2277 | 0.0 |
| 440 | 135103 | 75.5 | 570 | 122326 | 43.2 | 700 | 14133 | 0.0 | 830 | 1969 | 0.0 | 960 | 4267 | 0.0 |
| 445 | 140126 | 93.8 | 575 | 125968 | 34.3 | 705 | 12309 | 0.0 | 835 | 1917 | 0.0 | 965 | 2034 | 0.0 |
| 450 | 102339 | 79.3 | 580 | 127613 | 26.3 | 710 | 11142 | 0.0 | 840 | 2248 | 0.0 | 970 | 3586 | 0.0 |
| 455 | 58751 | 51.3 | 585 | 129466 | 19.8 | 715 | 10143 | 0.0 | 845 | 2266 | 0.0 | 975 | 2505 | 0.0 |
| 460 | 36892 | 35.6 | 590 | 128813 | 14.3 | 720 | 9072 | 0.0 | 850 | 2558 | 0.0 | 980 | 2666 | 0.0 |
| 465 | 24637 | 26.0 | 595 | 126387 | 10.1 | 725 | 8130 | 0.0 | 855 | 2767 | 0.0 | 985 | 2934 | 0.0 |
| 470 | 16738 | 19.3 | 600 | 123477 | 7.0 | 730 | 7149 | 0.0 | 860 | 2826 | 0.0 | 990 | 4120 | 0.0 |
| 475 | 13456 | 16.8 | 605 | 118718 | 4.7 | 735 | 6311 | 0.0 | 865 | 2385 | 0.0 | 995 | 3858 | 0.0 |
| 480 | 13081 | 17.7 | 610 | 112091 | 3.0 | 740 | 5711 | 0.0 | 870 | 3194 | 0.0 | 1000 | 3405 | 0.0 |
| 485 | 14734 | 21.4 | 615 | 105039 | 1.9 | 745 | 5111 | 0.0 | 875 | 3189 | 0.0 | | | |

REPORT NUMBER: SP1-2101-121-2

Melanopic Flux vs. Wavelength



Melanopic Lumens: 3927.2 M/P: 0.55

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 2304 | 0.0 | 490 | 19043 | 15.8 | 620 | 97577 | 0.1 | 750 | 4830 | 0.0 | 880 | 3505 | 0.0 |
| 365 | 2150 | 0.0 | 495 | 26606 | 22.0 | 625 | 90158 | 0.0 | 755 | 4664 | 0.0 | 885 | 2991 | 0.0 |
| 370 | 2146 | 0.0 | 500 | 36376 | 29.2 | 630 | 82240 | 0.0 | 760 | 4006 | 0.0 | 890 | 2327 | 0.0 |
| 375 | 2332 | 0.0 | 505 | 47714 | 36.6 | 635 | 74361 | 0.0 | 765 | 3715 | 0.0 | 895 | 2775 | 0.0 |
| 380 | 2527 | 0.0 | 510 | 58741 | 42.2 | 640 | 66994 | 0.0 | 770 | 3696 | 0.0 | 900 | 2141 | 0.0 |
| 385 | 2304 | 0.0 | 515 | 68716 | 44.9 | 645 | 60405 | 0.0 | 775 | 3117 | 0.0 | 905 | 2421 | 0.0 |
| 390 | 2064 | 0.0 | 520 | 77136 | 44.9 | 650 | 53806 | 0.0 | 780 | 3062 | 0.0 | 910 | 2200 | 0.0 |
| 395 | 1856 | 0.0 | 525 | 83567 | 42.4 | 655 | 47610 | 0.0 | 785 | 2907 | 0.0 | 915 | 2716 | 0.0 |
| 400 | 1856 | 0.0 | 530 | 89283 | 38.6 | 660 | 42018 | 0.0 | 790 | 2655 | 0.0 | 920 | 2656 | 0.0 |
| 405 | 2374 | 0.0 | 535 | 94097 | 33.9 | 665 | 36742 | 0.0 | 795 | 2467 | 0.0 | 925 | 2671 | 0.0 |
| 410 | 4084 | 0.2 | 540 | 96845 | 28.3 | 670 | 32105 | 0.0 | 800 | 2609 | 0.0 | 930 | 3292 | 0.0 |
| 415 | 8543 | 0.6 | 545 | 100829 | 23.4 | 675 | 27946 | 0.0 | 805 | 2293 | 0.0 | 935 | 3188 | 0.0 |
| 420 | 18394 | 2.1 | 550 | 105648 | 19.0 | 680 | 24146 | 0.0 | 810 | 2188 | 0.0 | 940 | 1997 | 0.0 |
| 425 | 37987 | 5.9 | 555 | 110017 | 14.8 | 685 | 21191 | 0.0 | 815 | 2386 | 0.0 | 945 | 2623 | 0.0 |
| 430 | 67605 | 14.3 | 560 | 114586 | 11.3 | 690 | 18544 | 0.0 | 820 | 2712 | 0.0 | 950 | 2969 | 0.0 |
| 435 | 102160 | 27.3 | 565 | 118987 | 8.4 | 695 | 16058 | 0.0 | 825 | 2473 | 0.0 | 955 | 2277 | 0.0 |
| 440 | 135103 | 45.1 | 570 | 122326 | 6.0 | 700 | 14133 | 0.0 | 830 | 1969 | 0.0 | 960 | 4267 | 0.0 |
| 445 | 140126 | 55.3 | 575 | 125968 | 4.2 | 705 | 12309 | 0.0 | 835 | 1917 | 0.0 | 965 | 2034 | 0.0 |
| 450 | 102339 | 47.2 | 580 | 127613 | 2.9 | 710 | 11142 | 0.0 | 840 | 2248 | 0.0 | 970 | 3586 | 0.0 |
| 455 | 58751 | 30.8 | 585 | 129466 | 1.9 | 715 | 10143 | 0.0 | 845 | 2266 | 0.0 | 975 | 2505 | 0.0 |
| 460 | 36892 | 21.7 | 590 | 128813 | 1.3 | 720 | 9072 | 0.0 | 850 | 2558 | 0.0 | 980 | 2666 | 0.0 |
| 465 | 24637 | 16.1 | 595 | 126387 | 0.8 | 725 | 8130 | 0.0 | 855 | 2767 | 0.0 | 985 | 2934 | 0.0 |
| 470 | 16738 | 12.0 | 600 | 123477 | 0.5 | 730 | 7149 | 0.0 | 860 | 2826 | 0.0 | 990 | 4120 | 0.0 |
| 475 | 13456 | 10.3 | 605 | 118718 | 0.3 | 735 | 6311 | 0.0 | 865 | 2385 | 0.0 | 995 | 3858 | 0.0 |
| 480 | 13081 | 10.5 | 610 | 112091 | 0.2 | 740 | 5711 | 0.0 | 870 | 3194 | 0.0 | 1000 | 3405 | 0.0 |
| 485 | 14734 | 12.1 | 615 | 105039 | 0.1 | 745 | 5111 | 0.0 | 875 | 3189 | 0.0 | | | |

Summary

$R_f = 71.7$
 $R_g = 96.9$
 CIE $R_a = 71.2$
 $R_g = -29.7$



Color Vector Graphics



Individual Sample Fidelity Index ($R_{f,i}$)

| | | | |
|------------|------------|------------|------------|
| CES01 = 85 | CES26 = 55 | CES51 = 86 | CES76 = 45 |
| CES02 = 61 | CES27 = 80 | CES52 = 87 | CES77 = 68 |
| CES03 = 30 | CES28 = 79 | CES53 = 74 | CES78 = 49 |
| CES04 = 70 | CES29 = 51 | CES54 = 81 | CES79 = 77 |
| CES05 = 47 | CES30 = 60 | CES55 = 80 | CES80 = 75 |
| CES06 = 50 | CES31 = 56 | CES56 = 69 | CES81 = 75 |
| CES07 = 40 | CES32 = 52 | CES57 = 67 | CES82 = 90 |
| CES08 = 39 | CES33 = 62 | CES58 = 69 | CES83 = 85 |
| CES09 = 29 | CES34 = 65 | CES59 = 86 | CES84 = 87 |
| CES10 = 74 | CES35 = 81 | CES60 = 91 | CES85 = 83 |
| CES11 = 57 | CES36 = 92 | CES61 = 85 | CES86 = 72 |
| CES12 = 63 | CES37 = 74 | CES62 = 81 | CES87 = 77 |
| CES13 = 42 | CES38 = 69 | CES63 = 72 | CES88 = 77 |
| CES14 = 74 | CES39 = 92 | CES64 = 69 | CES89 = 72 |
| CES15 = 71 | CES40 = 86 | CES65 = 64 | CES90 = 75 |
| CES16 = 46 | CES41 = 84 | CES66 = 63 | CES91 = 91 |
| CES17 = 49 | CES42 = 75 | CES67 = 60 | CES92 = 66 |
| CES18 = 56 | CES43 = 70 | CES68 = 67 | CES93 = 80 |
| CES19 = 72 | CES44 = 98 | CES69 = 77 | CES94 = 56 |
| CES20 = 65 | CES45 = 80 | CES70 = 57 | CES95 = 72 |
| CES21 = 86 | CES46 = 77 | CES71 = 53 | CES96 = 78 |
| CES22 = 78 | CES47 = 74 | CES72 = 84 | CES97 = 83 |
| CES23 = 92 | CES48 = 66 | CES73 = 47 | CES98 = 73 |
| CES24 = 91 | CES49 = 76 | CES74 = 96 | CES99 = 63 |
| CES25 = 72 | CES50 = 85 | CES75 = 52 | |



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)