

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: McGRAW-EDISON

Report Number: P638766

Luminaire Tested: GWS-SA4F-740-U-T2-W

Issue Date: 1/10/2023

Test Information

Test Method: LM-79-2019
Report Number: P638766
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2209-782-19)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/10/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: McGRAW-EDISON
Catalog Number: GWS-SA4F-740-U-T2-W
Description: GALLEON WALL SLIM LUMINAIRE. (4) LIGHTSQUARES WITH 16 LEDS EACH AND TYPE II OPTICS
Light Source: (64) 4000K CCT, 70 CRI LEDS
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 33757.5 lumens
Efficiency: N/A
Efficacy: 149.8 lumens/watt
Luminous Opening: Rectangular (W 1' x L: 1' x H: 0')
IES Classification: Type II - Medium
BUG Rating: B3 - U0 - G4


Input Watts (W): 225.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 0
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT



REPORT NUMBER: P638766
 CATALOG NUMBER: GWS-SA4F-740-U-T2-W

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 30 foot mounting height. Maximum calculated value = 6.3 fc
 Type II - Medium - N/A

REPORT NUMBER: P638766
CATALOG NUMBER: GWS-SA4F-740-U-T2-W

Luminous Intensity Polar Plot



— Vertical Plane Through 70-Deg Lateral - - - Horizontal Cone Through 70-Deg Vertical

REPORT NUMBER: P638766

CATALOG NUMBER: GWS-SA4F-740-U-T2-W

FLUX DISTRIBUTION:

| | | Downward | Upward | Total |
|--------------------|-----------|----------|--------|---------|
| House Side | Lumens | 6049.4 | 0.0 | 6049.4 |
| | % Fixture | 17.9 | 0.0 | 17.9 |
| Street Side | Lumens | 27708.1 | 0.0 | 27708.1 |
| | % Fixture | 82.1 | 0.0 | 82.1 |
| Total | Lumens | 33757.5 | 0.0 | 33757.5 |
| | % Fixture | 100.0 | 0.0 | 100.0 |

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|---------|-----------|
| 0°-10° | 400.1 | 1.2 |
| 10°-20° | 1301.6 | 3.9 |
| 20°-30° | 2305.9 | 6.8 |
| 30°-40° | 3470.4 | 10.3 |
| 40°-50° | 5250.3 | 15.6 |
| 50°-60° | 7521.4 | 22.3 |
| 60°-70° | 8314.0 | 24.6 |
| 70°-80° | 4691.8 | 13.9 |
| 80°-90° | 501.9 | 1.5 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-90° | 33757.5 | 100.0 |
| 0°-180° | 33757.5 | 100.0 |

Coefficient of Utilization




REPORT NUMBER: P638766

CATALOG NUMBER: GWS-SA4F-740-U-T2-W

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

| Zone | Lumens | % Fixture | Zone Rating/Lumen Limit | | |
|----------------|---------|-----------|-------------------------|------|----------|
| | | | B | U | G |
| FL (0°-30°) | 2620.6 | 7.8 | | | |
| FM (30°-60°) | 13560.4 | 40.2 | | | |
| FH (60°-80°) | 11172.3 | 33.1 | | | G4/12000 |
| FVH (80°-90°) | 354.8 | 1.1 | | | G3/500 |
| BL (0°-30°) | 1387.1 | 4.1 | B3/2500 | | |
| BM (30°-60°) | 2681.8 | 7.9 | B3/5000 | | |
| BH (60°-80°) | 1833.5 | 5.4 | B3/2500 | | G3/2500 |
| BVH (80°-90°) | 147.1 | 0.4 | | | G2/225 |
| UL (90°-100°) | 0.0 | 0.0 | | U0/0 | |
| UH (100°-180°) | 0.0 | 0.0 | | U0/0 | |

BUG Rating: B3-U0-G4
 Type II Medium





REPORT NUMBER: P638766
 CATALOG NUMBER: GWS-SA4F-740-U-T2-W

CANDELA DISTRIBUTION (FULL):

| | 0° | 5° | 15° | 25° | 35° | 45° | 55° | 65° | 70° | 75° | 85° |
|-------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|
| 0° | 3936.8 | 3936.8 | 3936.8 | 3936.8 | 3936.8 | 3936.8 | 3936.8 | 3936.8 | 3936.8 | 3936.8 | 3936.8 |
| 2.5° | 4361.2 | 4353.9 | 4358.8 | 4353.9 | 4327.1 | 4261.2 | 4207.6 | 4139.3 | 4092.9 | 4066.1 | 4002.7 |
| 5° | 4873.5 | 4866.1 | 4849.1 | 4824.7 | 4775.9 | 4685.6 | 4551.5 | 4402.7 | 4312.5 | 4244.2 | 4110.0 |
| 7.5° | 5241.8 | 5241.8 | 5239.3 | 5210.1 | 5175.9 | 5080.8 | 4922.2 | 4727.1 | 4595.4 | 4478.3 | 4258.8 |
| 10° | 5429.6 | 5441.8 | 5458.9 | 5500.3 | 5493.0 | 5441.8 | 5293.0 | 5083.2 | 4917.4 | 4780.8 | 4453.9 |
| 12.5° | 5532.0 | 5539.4 | 5568.6 | 5654.0 | 5741.8 | 5754.0 | 5666.2 | 5446.7 | 5266.2 | 5083.2 | 4671.0 |
| 15° | 5663.8 | 5666.2 | 5705.2 | 5807.7 | 5936.9 | 6066.2 | 6044.3 | 5824.7 | 5639.4 | 5436.9 | 4912.5 |
| 17.5° | 5766.2 | 5783.3 | 5854.0 | 5973.5 | 6134.5 | 6312.6 | 6419.9 | 6283.3 | 6054.0 | 5822.3 | 5175.9 |
| 20° | 5802.8 | 5815.0 | 5907.7 | 6090.6 | 6310.1 | 6561.4 | 6800.4 | 6763.8 | 6532.1 | 6258.9 | 5473.5 |
| 22.5° | 5934.5 | 5934.5 | 6002.8 | 6156.5 | 6415.0 | 6780.9 | 7168.7 | 7263.9 | 7059.0 | 6739.4 | 5793.0 |
| 25° | 6224.8 | 6215.0 | 6246.7 | 6310.1 | 6505.3 | 6956.5 | 7532.2 | 7817.5 | 7588.3 | 7229.7 | 6112.6 |
| 27.5° | 6622.4 | 6617.5 | 6615.0 | 6624.8 | 6690.6 | 7110.2 | 7839.5 | 8334.7 | 8105.4 | 7700.5 | 6397.9 |
| 30° | 7054.1 | 7039.5 | 7071.2 | 7041.9 | 7027.3 | 7293.1 | 8100.5 | 8798.1 | 8620.0 | 8166.3 | 6634.5 |
| 32.5° | 7641.9 | 7615.1 | 7607.8 | 7512.6 | 7454.1 | 7578.5 | 8310.3 | 9325.0 | 9183.5 | 8668.8 | 6900.4 |
| 35° | 8417.6 | 8393.2 | 8268.8 | 8117.6 | 7944.4 | 8002.9 | 8571.3 | 9839.6 | 9849.4 | 9298.1 | 7249.2 |
| 37.5° | 9200.6 | 9205.4 | 9107.9 | 8751.7 | 8573.7 | 8539.5 | 8968.8 | 10466.5 | 10676.3 | 10049.4 | 7700.5 |
| 40° | 9851.8 | 9881.1 | 9881.1 | 9505.5 | 9239.6 | 9207.9 | 9527.4 | 11210.4 | 11627.5 | 10971.4 | 8271.2 |
| 42.5° | 10347.0 | 10373.8 | 10459.2 | 10188.4 | 9907.9 | 10017.7 | 10205.5 | 11956.8 | 12705.6 | 12110.5 | 8993.2 |
| 45° | 10890.9 | 10912.9 | 10959.2 | 10803.1 | 10639.7 | 10932.4 | 10973.8 | 12849.6 | 13939.9 | 13388.6 | 9832.3 |
| 47.5° | 11612.9 | 11593.4 | 11598.3 | 11483.6 | 11356.8 | 11830.0 | 11820.2 | 13600.8 | 15132.6 | 14788.7 | 10742.1 |
| 50° | 12510.5 | 12547.1 | 12513.0 | 12286.1 | 12137.3 | 12569.1 | 12625.2 | 14432.6 | 16181.5 | 16174.1 | 11659.2 |
| 52.5° | 13374.0 | 13388.6 | 13569.1 | 13578.9 | 13274.0 | 13183.7 | 13330.1 | 15271.7 | 17066.9 | 17442.5 | 12539.8 |
| 55° | 13417.9 | 13474.0 | 14015.5 | 14405.7 | 14898.5 | 14174.0 | 14042.3 | 16071.7 | 17923.0 | 18684.1 | 13454.5 |
| 57.5° | 12483.7 | 12573.9 | 13493.5 | 14335.0 | 15705.8 | 15874.1 | 15261.9 | 17105.9 | 18779.2 | 19906.1 | 14513.1 |
| 60° | 10488.4 | 10676.3 | 11925.1 | 13213.0 | 15342.4 | 17096.2 | 17757.2 | 18510.9 | 19903.6 | 21154.9 | 15798.5 |
| 62.5° | 6698.0 | 6771.1 | 8522.5 | 10678.7 | 13705.7 | 16976.6 | 20474.4 | 20986.6 | 21615.9 | 22781.9 | 17779.1 |
| 65° | 3353.9 | 3588.0 | 4614.9 | 6373.6 | 9883.5 | 14959.4 | 21847.7 | 25521.1 | 24750.3 | 25567.4 | 20989.1 |
| 67.5° | 2275.7 | 2351.4 | 2870.9 | 3829.5 | 5795.5 | 10598.2 | 20996.4 | 29340.8 | 29114.0 | 29248.1 | 24411.2 |
| 70° | 1678.2 | 1726.9 | 2136.7 | 2712.4 | 3505.1 | 6017.4 | 16715.6 | 29053.0 | 30601.9 | 30553.1 | 24052.7 |
| 72.5° | 1224.5 | 1248.9 | 1558.6 | 2070.9 | 2597.7 | 3112.4 | 10207.9 | 23469.7 | 26713.8 | 28121.2 | 21035.4 |
| 75° | 890.3 | 919.6 | 1083.0 | 1548.9 | 2019.6 | 1941.6 | 5039.3 | 16952.2 | 20372.0 | 23079.4 | 17137.6 |
| 77.5° | 663.5 | 700.0 | 775.7 | 970.8 | 1414.7 | 1390.3 | 2178.2 | 11008.0 | 13176.4 | 15074.1 | 10410.4 |
| 80° | 478.1 | 485.4 | 529.3 | 622.0 | 897.6 | 814.7 | 1036.6 | 5739.4 | 6580.9 | 7210.2 | 4080.7 |
| 82.5° | 290.3 | 297.6 | 353.7 | 382.9 | 556.1 | 512.2 | 539.1 | 1858.6 | 2663.6 | 2827.0 | 1524.5 |
| 85° | 85.4 | 90.2 | 161.0 | 175.6 | 231.7 | 219.5 | 217.1 | 756.1 | 902.5 | 1153.7 | 600.0 |
| 87.5° | 0.0 | 0.0 | 0.0 | 0.0 | 2.4 | 14.6 | 26.8 | 134.2 | 202.5 | 280.5 | 146.4 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P638766
 CATALOG NUMBER: GWS-SA4F-740-U-T2-W

CANDELA DISTRIBUTION (continued):

| | 90° | 95° | 105° | 115° | 125° | 135° | 145° | 155° | 165° | 175° | 180° |
|-------|---------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 3936.8 | 3936.8 | 3936.8 | 3936.8 | 3936.8 | 3936.8 | 3936.8 | 3936.8 | 3936.8 | 3936.8 | 3936.8 |
| 2.5° | 3978.3 | 3922.2 | 3892.9 | 3841.7 | 3805.1 | 3768.5 | 3731.9 | 3697.8 | 3683.1 | 3661.2 | 3666.1 |
| 5° | 4049.0 | 3961.2 | 3873.4 | 3773.4 | 3688.0 | 3617.3 | 3553.9 | 3497.8 | 3473.4 | 3451.4 | 3461.2 |
| 7.5° | 4156.3 | 4024.6 | 3856.3 | 3673.4 | 3539.2 | 3441.7 | 3375.8 | 3336.8 | 3324.6 | 3307.5 | 3307.5 |
| 10° | 4292.9 | 4095.4 | 3800.2 | 3539.2 | 3378.3 | 3300.2 | 3270.9 | 3268.5 | 3280.7 | 3283.1 | 3278.2 |
| 12.5° | 4444.2 | 4163.7 | 3717.3 | 3380.7 | 3244.1 | 3219.7 | 3241.7 | 3283.1 | 3324.6 | 3346.5 | 3341.7 |
| 15° | 4600.3 | 4207.6 | 3575.8 | 3229.5 | 3146.5 | 3178.2 | 3249.0 | 3331.9 | 3412.4 | 3453.9 | 3451.4 |
| 17.5° | 4746.6 | 4217.3 | 3392.9 | 3083.1 | 3061.2 | 3141.7 | 3263.6 | 3392.9 | 3502.7 | 3561.2 | 3563.6 |
| 20° | 4910.1 | 4200.3 | 3205.1 | 2951.4 | 2975.8 | 3107.5 | 3268.5 | 3424.6 | 3553.9 | 3612.4 | 3627.0 |
| 22.5° | 5058.8 | 4141.7 | 3022.1 | 2827.0 | 2902.6 | 3066.0 | 3229.5 | 3375.8 | 3490.5 | 3546.6 | 3566.1 |
| 25° | 5193.0 | 4029.5 | 2822.1 | 2722.1 | 2846.5 | 3007.5 | 3131.9 | 3234.3 | 3314.8 | 3349.0 | 3375.8 |
| 27.5° | 5266.2 | 3861.2 | 2670.9 | 2639.2 | 2792.9 | 2924.6 | 2992.9 | 3024.6 | 3051.4 | 3041.6 | 3061.2 |
| 30° | 5280.8 | 3651.4 | 2539.2 | 2573.3 | 2712.4 | 2809.9 | 2824.6 | 2792.9 | 2746.5 | 2670.9 | 2688.0 |
| 32.5° | 5266.2 | 3410.0 | 2429.4 | 2502.6 | 2622.1 | 2680.6 | 2661.1 | 2578.2 | 2466.0 | 2348.9 | 2356.2 |
| 35° | 5271.1 | 3166.0 | 2339.2 | 2424.5 | 2517.2 | 2548.9 | 2500.2 | 2385.5 | 2266.0 | 2158.7 | 2153.8 |
| 37.5° | 5324.7 | 2961.2 | 2263.6 | 2348.9 | 2414.8 | 2419.7 | 2366.0 | 2246.5 | 2185.5 | 2105.0 | 2095.2 |
| 40° | 5473.5 | 2809.9 | 2195.3 | 2273.3 | 2314.8 | 2312.3 | 2251.4 | 2166.0 | 2207.5 | 2180.6 | 2173.3 |
| 42.5° | 5717.4 | 2717.2 | 2139.2 | 2192.8 | 2222.1 | 2227.0 | 2178.2 | 2124.5 | 2214.8 | 2180.6 | 2168.4 |
| 45° | 6110.1 | 2712.4 | 2100.1 | 2112.3 | 2158.7 | 2192.8 | 2158.7 | 2097.7 | 2131.8 | 1966.0 | 1934.3 |
| 47.5° | 6576.0 | 2795.3 | 2070.9 | 2041.6 | 2122.1 | 2183.1 | 2129.4 | 2031.8 | 1961.1 | 1809.9 | 1787.9 |
| 50° | 7137.0 | 2963.6 | 2044.0 | 1966.0 | 2068.4 | 2146.5 | 2092.8 | 1958.7 | 1851.3 | 1770.8 | 1758.6 |
| 52.5° | 7802.9 | 3185.6 | 2009.9 | 1880.6 | 1987.9 | 2127.0 | 2092.8 | 1951.3 | 1809.9 | 1736.7 | 1724.5 |
| 55° | 8500.5 | 3441.7 | 1970.9 | 1778.2 | 1897.7 | 2131.8 | 2109.9 | 1900.1 | 1778.2 | 1739.1 | 1729.4 |
| 57.5° | 9366.4 | 3749.0 | 1900.1 | 1658.6 | 1817.2 | 2087.9 | 2041.6 | 1870.8 | 1756.2 | 1724.5 | 1714.7 |
| 60° | 10490.9 | 4205.1 | 1766.0 | 1536.7 | 1724.5 | 2009.9 | 1980.6 | 1822.1 | 1697.7 | 1670.8 | 1663.5 |
| 62.5° | 12271.5 | 4978.3 | 1602.5 | 1419.6 | 1614.7 | 1846.5 | 1890.4 | 1729.4 | 1624.5 | 1622.0 | 1619.6 |
| 65° | 15174.1 | 5907.7 | 1409.8 | 1314.7 | 1500.1 | 1712.3 | 1770.8 | 1634.2 | 1548.9 | 1575.7 | 1573.3 |
| 67.5° | 17208.4 | 5988.2 | 1251.3 | 1205.0 | 1365.9 | 1565.9 | 1651.3 | 1536.7 | 1444.0 | 1495.2 | 1492.8 |
| 70° | 15761.9 | 4671.0 | 1114.7 | 1090.3 | 1222.0 | 1407.4 | 1522.0 | 1414.7 | 1322.0 | 1370.8 | 1361.1 |
| 72.5° | 13293.5 | 3580.7 | 985.4 | 970.8 | 1075.7 | 1241.5 | 1356.2 | 1292.8 | 1195.2 | 1195.2 | 1173.2 |
| 75° | 10683.6 | 2953.8 | 848.8 | 841.5 | 912.3 | 1073.2 | 1202.5 | 1095.2 | 1004.9 | 1000.1 | 985.4 |
| 77.5° | 6127.2 | 1936.7 | 712.2 | 707.4 | 729.3 | 897.6 | 934.2 | 912.3 | 844.0 | 812.2 | 802.5 |
| 80° | 2441.6 | 1007.4 | 561.0 | 529.3 | 551.3 | 658.6 | 736.6 | 700.0 | 641.5 | 602.5 | 580.5 |
| 82.5° | 946.4 | 504.9 | 395.1 | 346.4 | 378.1 | 475.6 | 534.2 | 522.0 | 483.0 | 395.1 | 370.8 |
| 85° | 385.4 | 246.4 | 236.6 | 200.0 | 219.5 | 256.1 | 307.3 | 265.9 | 219.5 | 156.1 | 148.8 |
| 87.5° | 102.4 | 90.2 | 87.8 | 53.7 | 41.5 | 12.2 | 2.4 | 0.0 | 0.0 | 0.0 | 0.0 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |

LM-79-08: Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Report Prepared for

Cooper Lighting Solutions

MCGRAW, INVUE, LUMARK AND STREETWORKS

DATA VALID FOR LUMINAIRES UTILIZING SA LIGHT ENGINES

Report Number: SP1-2101-121-2

Luminaire Tested: IFLD-S-SA2A-740-U-T3R-HSS

Test Date: 03/05/2021

Test Information

Test Method: LM-79-08
 Report Number: SP1-2101-121-2
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1
 Measurement Geometry: 4π
 Issue Date: 03/05/2021
 Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
 Product Line: STREETWORKS
 Catalog Number: **IFLD-S-SA2A-740-U-T3R-HSS**
 Description: STREETWORKS INF FLOOD

SHIELD, DRIVER PROGRAMMED @ 615mA.

Spectral Parameters

| | | | | | |
|---------------------------|---------|-----------|------|------|-------|
| CCT (K): | 3905 | CRI (Ra): | 71.2 | R9: | -29.7 |
| CIE u': | 0.2273 | R1: | 68.9 | R10: | 46.2 |
| CIE v': | 0.5024 | R2: | 77.0 | R11: | 68.8 |
| Duv: | -0.0008 | R3: | 84.0 | R12: | 45.6 |
| CIE x: | 0.3841 | R4: | 71.6 | R13: | 69.5 |
| CIE y: | 0.3774 | R5: | 68.9 | R14: | 90.7 |
| CIE z: | 0.2385 | R6: | 68.3 | | |
| Peak Wavelength (nm): | 443 | R7: | 78.7 | | |
| Dominant Wavelength (nm): | 579 | R8: | 52.2 | | |
| Purity: | 28.7 | | | | |
| Rf: | 71.7 | | | | |
| Rg: | 96.9 | | | | |



Test Conditions

Stabilization Time: 211M
 Operation Time: 12H
 Room Temperature (°C) / RH%: 24.8/312%
 Sphere Temperature (°C): 24.1

REPORT NUMBER: SP1-2101-121-2

| Measurement and Test Equipment | | | |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument | Identification Number | Calibration Date | Calibration Due Date |
| Photometer | IN0058 | 1/31/2021 | 7/31/2021 |
| Power Meter | IN0071 | 12/1/2020 | 12/1/2021 |
| AC Power Source | IN0063 | 12/1/2020 | 12/1/2021 |
| DC Power Source | IN0208 | 12/1/2020 | 12/1/2021 |
| Sphere Thermometer | IN0085 | 12/1/2020 | 12/1/2021 |
| Room Thermometer | IN0046 | 12/1/2020 | 12/1/2021 |

REPORT NUMBER: SP1-2101-121-2

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



CCT = 3905K
 CIE x = 0.3841
 CIE y = 0.3774
 Duv = -0.0008

Point lies inside the ANSI 4000K 4-step quadrangle

REPORT NUMBER: SP1-2101-121-2

Photopic Flux vs. Wavelength



#####

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 2304 | 0.0 | 490 | 19043 | 2.7 | 620 | 97577 | 25.4 | 750 | 4830 | 0.0 | 880 | 3505 | 0.0 |
| 365 | 2150 | 0.0 | 495 | 26606 | 4.8 | 625 | 90158 | 19.9 | 755 | 4664 | 0.0 | 885 | 2991 | 0.0 |
| 370 | 2146 | 0.0 | 500 | 36376 | 8.0 | 630 | 82240 | 14.9 | 760 | 4006 | 0.0 | 890 | 2327 | 0.0 |
| 375 | 2332 | 0.0 | 505 | 47714 | 13.3 | 635 | 74361 | 11.2 | 765 | 3715 | 0.0 | 895 | 2775 | 0.0 |
| 380 | 2527 | 0.0 | 510 | 58741 | 20.2 | 640 | 66994 | 8.0 | 770 | 3696 | 0.0 | 900 | 2141 | 0.0 |
| 385 | 2304 | 0.0 | 515 | 68716 | 28.5 | 645 | 60405 | 5.8 | 775 | 3117 | 0.0 | 905 | 2421 | 0.0 |
| 390 | 2064 | 0.0 | 520 | 77136 | 37.4 | 650 | 53806 | 3.9 | 780 | 3062 | 0.0 | 910 | 2200 | 0.0 |
| 395 | 1856 | 0.0 | 525 | 83567 | 44.9 | 655 | 47610 | 2.7 | 785 | 2907 | 0.0 | 915 | 2716 | 0.0 |
| 400 | 1856 | 0.0 | 530 | 89283 | 52.6 | 660 | 42018 | 1.8 | 790 | 2655 | 0.0 | 920 | 2656 | 0.0 |
| 405 | 2374 | 0.0 | 535 | 94097 | 58.4 | 665 | 36742 | 1.2 | 795 | 2467 | 0.0 | 925 | 2671 | 0.0 |
| 410 | 4084 | 0.0 | 540 | 96845 | 63.1 | 670 | 32105 | 0.7 | 800 | 2609 | 0.0 | 930 | 3292 | 0.0 |
| 415 | 8543 | 0.0 | 545 | 100829 | 67.1 | 675 | 27946 | 0.5 | 805 | 2293 | 0.0 | 935 | 3188 | 0.0 |
| 420 | 18394 | 0.1 | 550 | 105648 | 71.8 | 680 | 24146 | 0.3 | 810 | 2188 | 0.0 | 940 | 1997 | 0.0 |
| 425 | 37987 | 0.2 | 555 | 110017 | 75.1 | 685 | 21191 | 0.2 | 815 | 2386 | 0.0 | 945 | 2623 | 0.0 |
| 430 | 67605 | 0.5 | 560 | 114586 | 77.9 | 690 | 18544 | 0.1 | 820 | 2712 | 0.0 | 950 | 2969 | 0.0 |
| 435 | 102160 | 1.2 | 565 | 118987 | 79.1 | 695 | 16058 | 0.1 | 825 | 2473 | 0.0 | 955 | 2277 | 0.0 |
| 440 | 135103 | 2.1 | 570 | 122326 | 79.5 | 700 | 14133 | 0.0 | 830 | 1969 | 0.0 | 960 | 4267 | 0.0 |
| 445 | 140126 | 2.9 | 575 | 125968 | 78.4 | 705 | 12309 | 0.0 | 835 | 1917 | 0.0 | 965 | 2034 | 0.0 |
| 450 | 102339 | 2.7 | 580 | 127613 | 75.8 | 710 | 11142 | 0.0 | 840 | 2248 | 0.0 | 970 | 3586 | 0.0 |
| 455 | 58751 | 2.0 | 585 | 129466 | 71.9 | 715 | 10143 | 0.0 | 845 | 2266 | 0.0 | 975 | 2505 | 0.0 |
| 460 | 36892 | 1.5 | 590 | 128813 | 66.6 | 720 | 9072 | 0.0 | 850 | 2558 | 0.0 | 980 | 2666 | 0.0 |
| 465 | 24637 | 1.3 | 595 | 126387 | 59.9 | 725 | 8130 | 0.0 | 855 | 2767 | 0.0 | 985 | 2934 | 0.0 |
| 470 | 16738 | 1.0 | 600 | 123477 | 53.2 | 730 | 7149 | 0.0 | 860 | 2826 | 0.0 | 990 | 4120 | 0.0 |
| 475 | 13456 | 1.1 | 605 | 118718 | 46.0 | 735 | 6311 | 0.0 | 865 | 2385 | 0.0 | 995 | 3858 | 0.0 |
| 480 | 13081 | 1.2 | 610 | 112091 | 38.5 | 740 | 5711 | 0.0 | 870 | 3194 | 0.0 | 1000 | 3405 | 0.0 |
| 485 | 14734 | 1.7 | 615 | 105039 | 31.7 | 745 | 5111 | 0.0 | 875 | 3189 | 0.0 | | | |

REPORT NUMBER: SP1-2101-121-2

Scotopic Flux vs. Wavelength



Scotopic Lumens: 10425.8 S/P: 1.47

| λ (nm) | Power (µW/nm) | Lumens (Φ/nm) | λ (nm) | Power (µW/nm) | Lumens (Φ/nm) | λ (nm) | Power (µW/nm) | Lumens (Φ/nm) | λ (nm) | Power (µW/nm) | Lumens (Φ/nm) | λ (nm) | Power (µW/nm) | Lumens (Φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 2304 | 0.0 | 490 | 19043 | 29.3 | 620 | 97577 | 1.2 | 750 | 4830 | 0.0 | 880 | 3505 | 0.0 |
| 365 | 2150 | 0.0 | 495 | 26606 | 43.0 | 625 | 90158 | 0.8 | 755 | 4664 | 0.0 | 885 | 2991 | 0.0 |
| 370 | 2146 | 0.0 | 500 | 36376 | 60.8 | 630 | 82240 | 0.5 | 760 | 4006 | 0.0 | 890 | 2327 | 0.0 |
| 375 | 2332 | 0.0 | 505 | 47714 | 81.1 | 635 | 74361 | 0.3 | 765 | 3715 | 0.0 | 895 | 2775 | 0.0 |
| 380 | 2527 | 0.0 | 510 | 58741 | 99.6 | 640 | 66994 | 0.2 | 770 | 3696 | 0.0 | 900 | 2141 | 0.0 |
| 385 | 2304 | 0.0 | 515 | 68716 | 113.9 | 645 | 60405 | 0.1 | 775 | 3117 | 0.0 | 905 | 2421 | 0.0 |
| 390 | 2064 | 0.0 | 520 | 77136 | 122.6 | 650 | 53806 | 0.1 | 780 | 3062 | 0.0 | 910 | 2200 | 0.0 |
| 395 | 1856 | 0.0 | 525 | 83567 | 125.0 | 655 | 47610 | 0.0 | 785 | 2907 | 0.0 | 915 | 2716 | 0.0 |
| 400 | 1856 | 0.0 | 530 | 89283 | 123.1 | 660 | 42018 | 0.0 | 790 | 2655 | 0.0 | 920 | 2656 | 0.0 |
| 405 | 2374 | 0.1 | 535 | 94097 | 117.3 | 665 | 36742 | 0.0 | 795 | 2467 | 0.0 | 925 | 2671 | 0.0 |
| 410 | 4084 | 0.2 | 540 | 96845 | 107.0 | 670 | 32105 | 0.0 | 800 | 2609 | 0.0 | 930 | 3292 | 0.0 |
| 415 | 8543 | 0.9 | 545 | 100829 | 96.7 | 675 | 27946 | 0.0 | 805 | 2293 | 0.0 | 935 | 3188 | 0.0 |
| 420 | 18394 | 3.0 | 550 | 105648 | 86.4 | 680 | 24146 | 0.0 | 810 | 2188 | 0.0 | 940 | 1997 | 0.0 |
| 425 | 37987 | 9.3 | 555 | 110017 | 75.2 | 685 | 21191 | 0.0 | 815 | 2386 | 0.0 | 945 | 2623 | 0.0 |
| 430 | 67605 | 23.0 | 560 | 114586 | 64.0 | 690 | 18544 | 0.0 | 820 | 2712 | 0.0 | 950 | 2969 | 0.0 |
| 435 | 102160 | 45.7 | 565 | 118987 | 53.4 | 695 | 16058 | 0.0 | 825 | 2473 | 0.0 | 955 | 2277 | 0.0 |
| 440 | 135103 | 75.5 | 570 | 122326 | 43.2 | 700 | 14133 | 0.0 | 830 | 1969 | 0.0 | 960 | 4267 | 0.0 |
| 445 | 140126 | 93.8 | 575 | 125968 | 34.3 | 705 | 12309 | 0.0 | 835 | 1917 | 0.0 | 965 | 2034 | 0.0 |
| 450 | 102339 | 79.3 | 580 | 127613 | 26.3 | 710 | 11142 | 0.0 | 840 | 2248 | 0.0 | 970 | 3586 | 0.0 |
| 455 | 58751 | 51.3 | 585 | 129466 | 19.8 | 715 | 10143 | 0.0 | 845 | 2266 | 0.0 | 975 | 2505 | 0.0 |
| 460 | 36892 | 35.6 | 590 | 128813 | 14.3 | 720 | 9072 | 0.0 | 850 | 2558 | 0.0 | 980 | 2666 | 0.0 |
| 465 | 24637 | 26.0 | 595 | 126387 | 10.1 | 725 | 8130 | 0.0 | 855 | 2767 | 0.0 | 985 | 2934 | 0.0 |
| 470 | 16738 | 19.3 | 600 | 123477 | 7.0 | 730 | 7149 | 0.0 | 860 | 2826 | 0.0 | 990 | 4120 | 0.0 |
| 475 | 13456 | 16.8 | 605 | 118718 | 4.7 | 735 | 6311 | 0.0 | 865 | 2385 | 0.0 | 995 | 3858 | 0.0 |
| 480 | 13081 | 17.7 | 610 | 112091 | 3.0 | 740 | 5711 | 0.0 | 870 | 3194 | 0.0 | 1000 | 3405 | 0.0 |
| 485 | 14734 | 21.4 | 615 | 105039 | 1.9 | 745 | 5111 | 0.0 | 875 | 3189 | 0.0 | | | |

REPORT NUMBER: SP1-2101-121-2

Melanopic Flux vs. Wavelength



Melanopic Lumens: 3927.2 M/P: 0.55

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 2304 | 0.0 | 490 | 19043 | 15.8 | 620 | 97577 | 0.1 | 750 | 4830 | 0.0 | 880 | 3505 | 0.0 |
| 365 | 2150 | 0.0 | 495 | 26606 | 22.0 | 625 | 90158 | 0.0 | 755 | 4664 | 0.0 | 885 | 2991 | 0.0 |
| 370 | 2146 | 0.0 | 500 | 36376 | 29.2 | 630 | 82240 | 0.0 | 760 | 4006 | 0.0 | 890 | 2327 | 0.0 |
| 375 | 2332 | 0.0 | 505 | 47714 | 36.6 | 635 | 74361 | 0.0 | 765 | 3715 | 0.0 | 895 | 2775 | 0.0 |
| 380 | 2527 | 0.0 | 510 | 58741 | 42.2 | 640 | 66994 | 0.0 | 770 | 3696 | 0.0 | 900 | 2141 | 0.0 |
| 385 | 2304 | 0.0 | 515 | 68716 | 44.9 | 645 | 60405 | 0.0 | 775 | 3117 | 0.0 | 905 | 2421 | 0.0 |
| 390 | 2064 | 0.0 | 520 | 77136 | 44.9 | 650 | 53806 | 0.0 | 780 | 3062 | 0.0 | 910 | 2200 | 0.0 |
| 395 | 1856 | 0.0 | 525 | 83567 | 42.4 | 655 | 47610 | 0.0 | 785 | 2907 | 0.0 | 915 | 2716 | 0.0 |
| 400 | 1856 | 0.0 | 530 | 89283 | 38.6 | 660 | 42018 | 0.0 | 790 | 2655 | 0.0 | 920 | 2656 | 0.0 |
| 405 | 2374 | 0.0 | 535 | 94097 | 33.9 | 665 | 36742 | 0.0 | 795 | 2467 | 0.0 | 925 | 2671 | 0.0 |
| 410 | 4084 | 0.2 | 540 | 96845 | 28.3 | 670 | 32105 | 0.0 | 800 | 2609 | 0.0 | 930 | 3292 | 0.0 |
| 415 | 8543 | 0.6 | 545 | 100829 | 23.4 | 675 | 27946 | 0.0 | 805 | 2293 | 0.0 | 935 | 3188 | 0.0 |
| 420 | 18394 | 2.1 | 550 | 105648 | 19.0 | 680 | 24146 | 0.0 | 810 | 2188 | 0.0 | 940 | 1997 | 0.0 |
| 425 | 37987 | 5.9 | 555 | 110017 | 14.8 | 685 | 21191 | 0.0 | 815 | 2386 | 0.0 | 945 | 2623 | 0.0 |
| 430 | 67605 | 14.3 | 560 | 114586 | 11.3 | 690 | 18544 | 0.0 | 820 | 2712 | 0.0 | 950 | 2969 | 0.0 |
| 435 | 102160 | 27.3 | 565 | 118987 | 8.4 | 695 | 16058 | 0.0 | 825 | 2473 | 0.0 | 955 | 2277 | 0.0 |
| 440 | 135103 | 45.1 | 570 | 122326 | 6.0 | 700 | 14133 | 0.0 | 830 | 1969 | 0.0 | 960 | 4267 | 0.0 |
| 445 | 140126 | 55.3 | 575 | 125968 | 4.2 | 705 | 12309 | 0.0 | 835 | 1917 | 0.0 | 965 | 2034 | 0.0 |
| 450 | 102339 | 47.2 | 580 | 127613 | 2.9 | 710 | 11142 | 0.0 | 840 | 2248 | 0.0 | 970 | 3586 | 0.0 |
| 455 | 58751 | 30.8 | 585 | 129466 | 1.9 | 715 | 10143 | 0.0 | 845 | 2266 | 0.0 | 975 | 2505 | 0.0 |
| 460 | 36892 | 21.7 | 590 | 128813 | 1.3 | 720 | 9072 | 0.0 | 850 | 2558 | 0.0 | 980 | 2666 | 0.0 |
| 465 | 24637 | 16.1 | 595 | 126387 | 0.8 | 725 | 8130 | 0.0 | 855 | 2767 | 0.0 | 985 | 2934 | 0.0 |
| 470 | 16738 | 12.0 | 600 | 123477 | 0.5 | 730 | 7149 | 0.0 | 860 | 2826 | 0.0 | 990 | 4120 | 0.0 |
| 475 | 13456 | 10.3 | 605 | 118718 | 0.3 | 735 | 6311 | 0.0 | 865 | 2385 | 0.0 | 995 | 3858 | 0.0 |
| 480 | 13081 | 10.5 | 610 | 112091 | 0.2 | 740 | 5711 | 0.0 | 870 | 3194 | 0.0 | 1000 | 3405 | 0.0 |
| 485 | 14734 | 12.1 | 615 | 105039 | 0.1 | 745 | 5111 | 0.0 | 875 | 3189 | 0.0 | | | |

Summary

$R_f = 71.7$
 $R_g = 96.9$
 CIE $R_a = 71.2$
 $R_g = -29.7$



Color Vector Graphics



Individual Sample Fidelity Index ($R_{f,i}$)

| | | | |
|------------|------------|------------|------------|
| CES01 = 85 | CES26 = 55 | CES51 = 86 | CES76 = 45 |
| CES02 = 61 | CES27 = 80 | CES52 = 87 | CES77 = 68 |
| CES03 = 30 | CES28 = 79 | CES53 = 74 | CES78 = 49 |
| CES04 = 70 | CES29 = 51 | CES54 = 81 | CES79 = 77 |
| CES05 = 47 | CES30 = 60 | CES55 = 80 | CES80 = 75 |
| CES06 = 50 | CES31 = 56 | CES56 = 69 | CES81 = 75 |
| CES07 = 40 | CES32 = 52 | CES57 = 67 | CES82 = 90 |
| CES08 = 39 | CES33 = 62 | CES58 = 69 | CES83 = 85 |
| CES09 = 29 | CES34 = 65 | CES59 = 86 | CES84 = 87 |
| CES10 = 74 | CES35 = 81 | CES60 = 91 | CES85 = 83 |
| CES11 = 57 | CES36 = 92 | CES61 = 85 | CES86 = 72 |
| CES12 = 63 | CES37 = 74 | CES62 = 81 | CES87 = 77 |
| CES13 = 42 | CES38 = 69 | CES63 = 72 | CES88 = 77 |
| CES14 = 74 | CES39 = 92 | CES64 = 69 | CES89 = 72 |
| CES15 = 71 | CES40 = 86 | CES65 = 64 | CES90 = 75 |
| CES16 = 46 | CES41 = 84 | CES66 = 63 | CES91 = 91 |
| CES17 = 49 | CES42 = 75 | CES67 = 60 | CES92 = 66 |
| CES18 = 56 | CES43 = 70 | CES68 = 67 | CES93 = 80 |
| CES19 = 72 | CES44 = 98 | CES69 = 77 | CES94 = 56 |
| CES20 = 65 | CES45 = 80 | CES70 = 57 | CES95 = 72 |
| CES21 = 86 | CES46 = 77 | CES71 = 53 | CES96 = 78 |
| CES22 = 78 | CES47 = 74 | CES72 = 84 | CES97 = 83 |
| CES23 = 92 | CES48 = 66 | CES73 = 47 | CES98 = 73 |
| CES24 = 91 | CES49 = 76 | CES74 = 96 | CES99 = 63 |
| CES25 = 72 | CES50 = 85 | CES75 = 52 | |



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)