

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: McGRAW-EDISON

Report Number: P628860

Luminaire Tested: GWS-SA1A-740-U-SLR-W-GRSBK

Issue Date: 1/10/2023

Test Information

Test Method: LM-79-2019
Report Number: P628860
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2209-782-42)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/10/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: McGRAW-EDISON
Catalog Number: GWS-SA1A-740-U-SLR-W-GRSBK
Description: GALLEON WALL SLIM LUMINAIRE. (1) LIGHTSQUARES WITH 16 LEDS EACH AND SPILL LIGHT ELIMINATOR RIGHT OPTICS W/ FACTORY INSTALLED GLARE SHIELD, BK
Light Source: (16) 4000K CCT, 70 CRI LEDS
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1517.1 lumens
Efficiency: N/A
Efficacy: 77.0 lumens/watt
Luminous Opening: Rectangular (W 0.5' x L: 0.5' x H: 0')
IES Classification: Type III - Short
BUG Rating: B0 - U0 - G0


Input Watts (W): 19.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 0
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT



REPORT NUMBER: P628860
 CATALOG NUMBER: GWS-SA1A-740-U-SLR-W-GRSBK

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 10 foot mounting height. Maximum calculated value = 4.8 fc
 Type III - Short - N/A

REPORT NUMBER: P628860
CATALOG NUMBER: GWS-SA1A-740-U-SLR-W-GRSBK

Luminous Intensity Polar Plot



— Vertical Plane Through 45-Deg Lateral - - - Horizontal Cone Through 57.5-Deg Vertical

REPORT NUMBER: P628860
 CATALOG NUMBER: GWS-SA1A-740-U-SLR-W-GRSBK


FLUX DISTRIBUTION:

| | | Downward | Upward | Total |
|--------------------|-----------|----------|--------|--------|
| House Side | Lumens | 339.7 | 0.0 | 339.7 |
| | % Fixture | 22.4 | 0.0 | 22.4 |
| Street Side | Lumens | 1177.4 | 0.0 | 1177.4 |
| | % Fixture | 77.6 | 0.0 | 77.6 |
| Total | Lumens | 1517.1 | 0.0 | 1517.1 |
| | % Fixture | 100.0 | 0.0 | 100.0 |

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 26.2 | 1.7 |
| 10°-20° | 84.9 | 5.6 |
| 20°-30° | 137.8 | 9.1 |
| 30°-40° | 213.0 | 14.0 |
| 40°-50° | 341.5 | 22.5 |
| 50°-60° | 466.8 | 30.8 |
| 60°-70° | 226.1 | 14.9 |
| 70°-80° | 20.7 | 1.4 |
| 80°-90° | 0.1 | 0.0 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-90° | 1517.1 | 100.0 |
| 0°-180° | 1517.1 | 100.0 |

Coefficient of Utilization



REPORT NUMBER: P628860


CATALOG NUMBER: GWS-SA1A-740-U-SLR-W-GRSBK

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

| Zone | Lumens | % Fixture | Zone Rating/Lumen Limit | | |
|----------------|--------|-----------|-------------------------|------|--------|
| | | | B | U | G |
| FL (0°-30°) | 148.4 | 9.8 | | | |
| FM (30°-60°) | 807.6 | 53.2 | | | |
| FH (60°-80°) | 221.3 | 14.6 | | | G0/660 |
| FVH (80°-90°) | 0.1 | 0.0 | | | G0/10 |
| BL (0°-30°) | 100.5 | 6.6 | B0/110 | | |
| BM (30°-60°) | 213.7 | 14.1 | B0/220 | | |
| BH (60°-80°) | 25.5 | 1.7 | B0/110 | | G0/110 |
| BVH (80°-90°) | 0.0 | 0.0 | | | G0/10 |
| UL (90°-100°) | 0.0 | 0.0 | | U0/0 | |
| UH (100°-180°) | 0.0 | 0.0 | | U0/0 | |

BUG Rating: B0-U0-G0

Type III Short





REPORT NUMBER: P628860
 CATALOG NUMBER: GWS-SA1A-740-U-SLR-W-GRSBK

CANDELA DISTRIBUTION (FULL):

| | 0° | 1° | 5° | 15° | 25° | 35° | 45° | 55° | 65° | 75° | 85° |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 266.6 | 266.6 | 266.6 | 266.6 | 266.6 | 266.6 | 266.6 | 266.6 | 266.6 | 266.6 | 266.6 |
| 2.5° | 288.9 | 290.7 | 293.8 | 300.3 | 305.8 | 309.5 | 311.1 | 310.7 | 308.4 | 306.8 | 303.5 |
| 5° | 319.9 | 319.9 | 325.8 | 340.6 | 352.1 | 359.2 | 362.9 | 360.6 | 356.1 | 349.0 | 338.0 |
| 7.5° | 347.0 | 348.0 | 358.0 | 379.2 | 396.5 | 406.7 | 412.6 | 411.4 | 403.4 | 389.8 | 367.8 |
| 10° | 368.2 | 369.4 | 382.6 | 408.5 | 428.9 | 439.3 | 448.1 | 448.9 | 440.1 | 422.0 | 396.7 |
| 12.5° | 388.8 | 390.0 | 403.8 | 428.7 | 446.7 | 450.9 | 458.7 | 461.7 | 459.5 | 446.7 | 420.4 |
| 15° | 411.0 | 413.8 | 425.7 | 444.2 | 451.7 | 446.7 | 451.7 | 457.3 | 464.8 | 463.6 | 439.9 |
| 17.5° | 432.8 | 434.8 | 446.9 | 453.4 | 445.0 | 431.8 | 434.2 | 440.7 | 457.9 | 474.6 | 459.3 |
| 20° | 453.0 | 455.8 | 465.8 | 457.3 | 432.0 | 411.4 | 411.6 | 420.2 | 446.2 | 481.3 | 479.1 |
| 22.5° | 474.2 | 478.5 | 485.6 | 461.5 | 419.9 | 395.3 | 396.3 | 404.0 | 437.1 | 487.6 | 501.5 |
| 25° | 501.9 | 506.0 | 510.7 | 472.1 | 416.1 | 387.3 | 391.2 | 398.3 | 437.1 | 498.4 | 529.2 |
| 27.5° | 539.4 | 542.3 | 542.5 | 491.9 | 422.8 | 388.6 | 396.7 | 404.9 | 450.1 | 520.0 | 566.3 |
| 30° | 586.5 | 591.0 | 585.1 | 522.7 | 443.8 | 404.9 | 416.9 | 427.1 | 478.3 | 556.5 | 621.0 |
| 32.5° | 643.8 | 650.1 | 642.2 | 568.4 | 487.6 | 461.1 | 482.9 | 488.9 | 523.1 | 609.3 | 682.9 |
| 35° | 711.1 | 716.4 | 707.8 | 631.6 | 590.0 | 594.9 | 634.4 | 626.9 | 613.2 | 674.4 | 755.3 |
| 37.5° | 784.9 | 789.7 | 773.2 | 727.4 | 741.2 | 762.4 | 825.6 | 799.7 | 755.7 | 758.1 | 833.8 |
| 40° | 852.5 | 857.8 | 831.9 | 831.5 | 860.1 | 898.8 | 975.1 | 939.4 | 879.4 | 867.8 | 907.4 |
| 42.5° | 922.7 | 926.3 | 902.9 | 887.0 | 951.8 | 1031.5 | 1112.3 | 1064.1 | 961.4 | 948.8 | 999.5 |
| 45° | 1022.8 | 1030.5 | 988.7 | 914.3 | 1034.4 | 1184.2 | 1296.7 | 1202.8 | 1017.3 | 1007.1 | 1140.6 |
| 47.5° | 1169.9 | 1175.7 | 1090.4 | 931.4 | 1111.2 | 1374.4 | 1527.3 | 1382.6 | 1066.4 | 1043.1 | 1333.4 |
| 50° | 1291.6 | 1295.5 | 1184.0 | 950.2 | 1193.0 | 1579.5 | 1790.1 | 1595.8 | 1121.6 | 1102.9 | 1513.4 |
| 52.5° | 1381.3 | 1396.0 | 1306.9 | 988.7 | 1300.4 | 1820.7 | 2081.0 | 1848.4 | 1207.9 | 1218.3 | 1662.7 |
| 55° | 1399.9 | 1419.9 | 1390.9 | 1012.4 | 1395.0 | 2066.3 | 2349.7 | 2074.5 | 1293.9 | 1305.7 | 1712.8 |
| 57.5° | 1230.3 | 1246.2 | 1270.2 | 917.0 | 1392.8 | 2178.8 | 2505.6 | 2149.5 | 1254.7 | 1171.0 | 1525.1 |
| 60° | 921.6 | 932.7 | 976.3 | 700.9 | 1280.8 | 2079.4 | 2384.1 | 2021.9 | 1097.2 | 893.5 | 1162.0 |
| 62.5° | 546.5 | 551.4 | 606.7 | 454.0 | 1063.1 | 1790.7 | 1977.2 | 1744.6 | 867.0 | 601.0 | 711.7 |
| 65° | 209.8 | 207.7 | 249.9 | 224.0 | 781.8 | 1426.4 | 1470.6 | 1330.0 | 594.9 | 275.4 | 271.3 |
| 67.5° | 32.4 | 31.0 | 41.8 | 66.3 | 563.9 | 988.5 | 970.4 | 958.5 | 372.7 | 64.2 | 56.1 |
| 70° | 7.3 | 7.3 | 9.0 | 19.6 | 344.5 | 580.8 | 621.6 | 592.6 | 238.5 | 13.7 | 7.3 |
| 72.5° | 3.5 | 3.5 | 4.3 | 8.4 | 124.8 | 239.3 | 278.9 | 274.6 | 77.5 | 4.5 | 2.7 |
| 75° | 1.2 | 1.4 | 1.4 | 1.8 | 7.5 | 12.4 | 28.5 | 20.4 | 4.9 | 0.0 | 0.0 |
| 77.5° | 0.4 | 0.4 | 0.4 | 0.4 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 80° | 0.2 | 0.2 | 0.2 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 82.5° | 0.2 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 85° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 87.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P628860
 CATALOG NUMBER: GWS-SA1A-740-U-SLR-W-GRSBK

CANDELA DISTRIBUTION (continued):

| | 90° | 95° | 105° | 115° | 125° | 135° | 145° | 155° | 165° | 175° | 180° |
|-------|--------|--------|-------|-------|-------|-------|-------|-------|-------|-------|-------|
| 0° | 266.6 | 266.6 | 266.6 | 266.6 | 266.6 | 266.6 | 266.6 | 266.6 | 266.6 | 266.6 | 266.6 |
| 2.5° | 296.4 | 295.0 | 289.7 | 282.5 | 275.6 | 269.5 | 263.2 | 255.6 | 250.1 | 243.8 | 241.8 |
| 5° | 329.4 | 320.5 | 306.0 | 290.9 | 277.0 | 265.2 | 253.8 | 241.6 | 232.6 | 223.6 | 220.6 |
| 7.5° | 357.4 | 344.1 | 320.7 | 298.0 | 279.1 | 262.4 | 245.9 | 229.1 | 216.1 | 205.5 | 202.2 |
| 10° | 382.4 | 367.1 | 335.8 | 307.8 | 284.0 | 264.6 | 244.6 | 223.6 | 206.7 | 194.1 | 191.0 |
| 12.5° | 404.0 | 386.3 | 348.6 | 315.2 | 286.0 | 263.8 | 244.4 | 227.7 | 212.4 | 197.9 | 194.1 |
| 15° | 422.2 | 402.6 | 359.4 | 320.1 | 283.0 | 253.6 | 236.7 | 234.0 | 232.8 | 216.9 | 209.4 |
| 17.5° | 439.9 | 417.9 | 368.2 | 322.3 | 274.4 | 235.7 | 223.4 | 235.5 | 248.3 | 237.9 | 228.3 |
| 20° | 458.5 | 433.4 | 377.1 | 322.7 | 260.1 | 215.5 | 213.4 | 232.4 | 248.7 | 245.4 | 236.5 |
| 22.5° | 480.3 | 452.8 | 388.3 | 322.5 | 242.2 | 198.4 | 206.1 | 226.5 | 239.7 | 239.5 | 232.4 |
| 25° | 511.9 | 477.2 | 403.4 | 323.7 | 222.6 | 185.1 | 197.9 | 216.5 | 227.3 | 226.9 | 221.0 |
| 27.5° | 545.7 | 506.4 | 423.0 | 326.8 | 205.9 | 177.4 | 188.4 | 202.8 | 212.2 | 211.8 | 206.7 |
| 30° | 593.2 | 540.0 | 441.8 | 327.0 | 193.9 | 173.3 | 177.8 | 187.8 | 196.7 | 195.7 | 191.8 |
| 32.5° | 650.9 | 577.9 | 457.5 | 315.4 | 186.3 | 169.4 | 166.8 | 171.9 | 178.8 | 177.4 | 176.3 |
| 35° | 720.6 | 623.0 | 470.9 | 289.9 | 174.7 | 161.7 | 154.5 | 155.5 | 160.4 | 161.3 | 160.8 |
| 37.5° | 800.1 | 676.6 | 487.6 | 256.2 | 159.0 | 150.4 | 140.9 | 140.1 | 142.9 | 145.6 | 147.6 |
| 40° | 878.6 | 736.9 | 510.3 | 222.2 | 144.7 | 136.2 | 127.0 | 125.0 | 126.2 | 130.9 | 135.2 |
| 42.5° | 966.9 | 806.9 | 534.7 | 193.1 | 135.0 | 120.5 | 111.7 | 107.8 | 111.3 | 118.8 | 123.9 |
| 45° | 1094.1 | 904.9 | 558.6 | 169.8 | 130.9 | 106.6 | 94.8 | 94.4 | 98.3 | 108.0 | 113.8 |
| 47.5° | 1272.7 | 1031.7 | 574.3 | 151.7 | 130.7 | 95.8 | 81.7 | 84.2 | 88.7 | 98.3 | 104.8 |
| 50° | 1446.8 | 1190.5 | 556.9 | 137.8 | 126.4 | 88.7 | 72.0 | 76.9 | 81.3 | 89.7 | 96.4 |
| 52.5° | 1551.8 | 1275.9 | 489.5 | 124.8 | 113.1 | 85.4 | 62.4 | 70.9 | 71.8 | 79.3 | 86.4 |
| 55° | 1540.8 | 1220.7 | 374.9 | 104.6 | 93.6 | 80.7 | 52.4 | 64.0 | 64.4 | 70.1 | 76.2 |
| 57.5° | 1337.3 | 1048.0 | 257.5 | 84.8 | 70.3 | 66.7 | 43.2 | 54.0 | 57.9 | 61.4 | 65.8 |
| 60° | 996.7 | 764.7 | 114.8 | 68.9 | 44.6 | 45.1 | 36.9 | 40.8 | 46.7 | 50.8 | 54.6 |
| 62.5° | 587.3 | 439.9 | 46.7 | 41.4 | 24.7 | 28.3 | 29.8 | 29.8 | 33.4 | 36.5 | 38.9 |
| 65° | 222.0 | 153.9 | 19.0 | 20.8 | 12.8 | 13.3 | 17.5 | 21.6 | 24.5 | 27.1 | 30.4 |
| 67.5° | 38.9 | 26.9 | 9.8 | 7.7 | 7.5 | 6.7 | 9.0 | 14.1 | 15.7 | 17.7 | 19.2 |
| 70° | 6.5 | 5.5 | 4.1 | 3.9 | 3.5 | 3.7 | 5.9 | 10.0 | 11.0 | 11.6 | 12.2 |
| 72.5° | 1.8 | 1.6 | 1.2 | 1.0 | 0.8 | 1.0 | 3.7 | 7.7 | 8.2 | 8.6 | 9.2 |
| 75° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 1.4 | 5.5 | 5.9 | 6.1 | 6.7 |
| 77.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 1.2 | 1.6 | 2.0 | 1.6 |
| 80° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 82.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 85° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 87.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P628860

CATALOG NUMBER: GWS-SA1A-740-U-SLR-W-GRSBK

CANDELA DISTRIBUTION (continued):

| | 185° | 195° | 205° | 215° | 225° | 235° | 245° | 255° | 265° | 270° | 275° |
|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|
| 0° | 266.6 | 266.6 | 266.6 | 266.6 | 266.6 | 266.6 | 266.6 | 266.6 | 266.6 | 266.6 | 266.6 |
| 2.5° | 240.6 | 236.5 | 234.2 | 233.0 | 233.0 | 231.4 | 229.5 | 228.9 | 231.6 | 231.6 | 236.1 |
| 5° | 216.7 | 213.4 | 209.8 | 207.5 | 204.1 | 204.7 | 202.6 | 202.4 | 205.1 | 206.3 | 211.0 |
| 7.5° | 200.2 | 196.1 | 193.9 | 192.4 | 190.6 | 189.8 | 188.0 | 187.3 | 188.8 | 190.8 | 195.3 |
| 10° | 189.2 | 188.6 | 188.4 | 189.4 | 189.4 | 188.4 | 186.7 | 185.7 | 186.1 | 190.0 | 195.1 |
| 12.5° | 192.0 | 193.3 | 193.7 | 195.3 | 196.1 | 195.3 | 194.1 | 194.5 | 197.1 | 204.3 | 211.8 |
| 15° | 204.5 | 203.5 | 203.0 | 203.9 | 204.5 | 203.7 | 203.2 | 206.3 | 215.5 | 225.7 | 234.2 |
| 17.5° | 217.7 | 211.2 | 208.3 | 208.3 | 208.8 | 208.3 | 208.8 | 214.7 | 229.5 | 239.7 | 246.1 |
| 20° | 224.4 | 212.4 | 207.9 | 206.9 | 207.7 | 207.9 | 209.4 | 216.1 | 232.4 | 239.5 | 241.0 |
| 22.5° | 222.4 | 207.3 | 202.2 | 201.4 | 202.2 | 203.0 | 204.5 | 210.2 | 225.5 | 229.1 | 228.5 |
| 25° | 212.2 | 197.3 | 193.3 | 193.3 | 195.1 | 194.9 | 195.5 | 199.6 | 212.2 | 214.5 | 213.4 |
| 27.5° | 199.4 | 185.3 | 181.8 | 183.9 | 185.5 | 185.1 | 185.3 | 188.8 | 198.2 | 198.8 | 197.7 |
| 30° | 186.3 | 174.1 | 170.8 | 173.3 | 175.5 | 175.1 | 175.3 | 178.8 | 184.7 | 184.1 | 182.7 |
| 32.5° | 173.1 | 164.1 | 161.7 | 163.1 | 166.6 | 166.1 | 167.0 | 170.6 | 172.9 | 170.2 | 168.6 |
| 35° | 160.8 | 156.2 | 154.3 | 155.1 | 157.8 | 158.4 | 159.8 | 162.3 | 162.3 | 159.0 | 156.2 |
| 37.5° | 149.4 | 148.8 | 147.6 | 146.6 | 149.0 | 150.9 | 152.9 | 155.7 | 151.7 | 147.0 | 144.3 |
| 40° | 138.8 | 141.5 | 139.8 | 137.2 | 138.6 | 141.3 | 145.4 | 147.6 | 142.7 | 138.0 | 133.5 |
| 42.5° | 129.0 | 133.5 | 132.9 | 129.7 | 130.9 | 133.3 | 138.0 | 139.8 | 134.1 | 128.8 | 124.6 |
| 45° | 119.7 | 126.0 | 126.4 | 122.3 | 123.5 | 126.0 | 131.5 | 132.1 | 124.8 | 119.1 | 116.0 |
| 47.5° | 111.5 | 118.4 | 118.6 | 115.6 | 116.0 | 119.5 | 124.6 | 124.8 | 116.4 | 111.1 | 107.2 |
| 50° | 103.8 | 111.7 | 112.3 | 109.7 | 110.1 | 114.2 | 118.4 | 117.6 | 108.7 | 103.2 | 99.7 |
| 52.5° | 94.4 | 105.2 | 106.6 | 105.4 | 107.0 | 110.3 | 112.9 | 110.1 | 99.7 | 94.2 | 91.1 |
| 55° | 84.2 | 98.3 | 101.3 | 100.5 | 102.3 | 105.0 | 105.6 | 103.8 | 90.7 | 85.2 | 82.4 |
| 57.5° | 72.4 | 80.9 | 86.2 | 84.6 | 86.0 | 88.7 | 90.5 | 89.1 | 79.3 | 75.0 | 72.6 |
| 60° | 59.9 | 65.6 | 66.9 | 64.2 | 63.0 | 67.7 | 72.0 | 70.1 | 61.8 | 59.1 | 56.3 |
| 62.5° | 43.8 | 50.4 | 51.2 | 47.7 | 46.3 | 51.4 | 55.0 | 53.2 | 44.0 | 41.2 | 38.9 |
| 65° | 35.1 | 41.2 | 42.8 | 39.5 | 38.7 | 42.6 | 44.8 | 40.4 | 33.8 | 30.8 | 28.3 |
| 67.5° | 23.0 | 27.9 | 32.2 | 32.0 | 30.4 | 31.6 | 30.0 | 26.3 | 21.6 | 20.0 | 18.3 |
| 70° | 14.3 | 17.1 | 19.8 | 20.8 | 20.6 | 20.2 | 17.9 | 15.3 | 13.9 | 13.3 | 12.4 |
| 72.5° | 11.0 | 13.9 | 15.9 | 16.5 | 16.7 | 16.1 | 14.3 | 11.8 | 10.4 | 9.6 | 9.0 |
| 75° | 8.2 | 10.4 | 12.0 | 12.8 | 13.3 | 12.8 | 11.0 | 9.4 | 8.0 | 7.3 | 6.7 |
| 77.5° | 2.9 | 3.5 | 4.3 | 4.7 | 4.5 | 4.3 | 3.9 | 3.9 | 3.1 | 2.9 | 2.4 |
| 80° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 82.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 85° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 87.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P628860
 CATALOG NUMBER: GWS-SA1A-740-U-SLR-W-GRSBK

CANDELA DISTRIBUTION (continued):

| | 285° | 295° | 305° | 315° | 325° | 335° | 345° | 355° | 359° | 360° |
|-------|-------|-------|-------|-------|-------|-------|-------|--------|--------|--------|
| 0° | 266.6 | 266.6 | 266.6 | 266.6 | 266.6 | 266.6 | 266.6 | 266.6 | 266.6 | 266.6 |
| 2.5° | 241.2 | 244.8 | 251.6 | 257.7 | 264.2 | 270.9 | 278.3 | 285.8 | 289.3 | 288.9 |
| 5° | 218.1 | 226.1 | 237.1 | 249.1 | 262.6 | 277.0 | 293.1 | 309.7 | 316.8 | 319.9 |
| 7.5° | 203.7 | 214.9 | 229.3 | 244.6 | 262.4 | 283.0 | 307.2 | 333.1 | 343.5 | 347.0 |
| 10° | 205.5 | 218.5 | 230.6 | 245.4 | 264.4 | 291.1 | 321.3 | 352.1 | 364.3 | 368.2 |
| 12.5° | 220.4 | 223.2 | 226.5 | 238.7 | 262.6 | 297.2 | 334.1 | 370.8 | 384.9 | 388.8 |
| 15° | 233.8 | 220.6 | 214.5 | 225.7 | 256.0 | 301.5 | 347.2 | 391.0 | 406.5 | 411.0 |
| 17.5° | 234.4 | 214.5 | 200.8 | 209.6 | 245.4 | 303.3 | 360.0 | 411.6 | 428.5 | 432.8 |
| 20° | 226.9 | 207.7 | 190.2 | 190.4 | 231.0 | 302.9 | 370.6 | 430.1 | 449.1 | 453.0 |
| 22.5° | 215.9 | 199.8 | 181.6 | 175.3 | 215.5 | 302.1 | 382.2 | 449.9 | 470.5 | 474.2 |
| 25° | 203.7 | 189.6 | 173.5 | 163.9 | 200.0 | 302.9 | 398.5 | 475.8 | 498.4 | 501.9 |
| 27.5° | 190.4 | 178.4 | 167.2 | 159.4 | 186.9 | 306.0 | 418.1 | 508.8 | 535.7 | 539.4 |
| 30° | 176.5 | 167.6 | 163.1 | 158.4 | 178.8 | 306.8 | 439.3 | 547.4 | 581.4 | 586.5 |
| 32.5° | 162.9 | 158.0 | 158.2 | 159.0 | 171.0 | 301.1 | 458.7 | 590.2 | 635.6 | 643.8 |
| 35° | 150.2 | 148.8 | 152.9 | 157.0 | 159.8 | 286.4 | 475.6 | 640.7 | 702.7 | 711.1 |
| 37.5° | 139.4 | 140.7 | 145.8 | 149.8 | 147.6 | 265.6 | 498.0 | 703.9 | 777.7 | 784.9 |
| 40° | 129.0 | 132.1 | 138.0 | 139.8 | 138.2 | 241.4 | 524.9 | 764.9 | 842.8 | 852.5 |
| 42.5° | 119.5 | 121.7 | 130.1 | 130.5 | 135.6 | 216.7 | 550.8 | 830.5 | 917.6 | 922.7 |
| 45° | 111.7 | 111.3 | 119.9 | 122.5 | 139.0 | 189.4 | 576.1 | 918.0 | 1015.4 | 1022.8 |
| 47.5° | 104.2 | 103.8 | 105.8 | 117.8 | 140.5 | 164.1 | 601.2 | 1046.0 | 1157.3 | 1169.9 |
| 50° | 97.0 | 97.6 | 91.3 | 115.6 | 132.7 | 144.7 | 612.6 | 1164.4 | 1286.3 | 1291.6 |
| 52.5° | 90.7 | 88.5 | 77.5 | 108.2 | 116.2 | 126.4 | 580.2 | 1218.3 | 1366.3 | 1381.3 |
| 55° | 81.7 | 69.3 | 63.8 | 87.9 | 91.7 | 110.3 | 475.2 | 1187.1 | 1373.2 | 1399.9 |
| 57.5° | 69.9 | 54.4 | 54.2 | 64.8 | 64.8 | 102.3 | 304.4 | 1014.2 | 1183.4 | 1230.3 |
| 60° | 53.8 | 42.2 | 44.8 | 45.1 | 41.6 | 74.6 | 170.8 | 734.7 | 875.0 | 921.6 |
| 62.5° | 38.3 | 32.2 | 33.8 | 26.9 | 23.9 | 37.3 | 82.0 | 423.0 | 540.0 | 546.5 |
| 65° | 25.7 | 21.8 | 17.7 | 14.9 | 14.7 | 15.9 | 33.8 | 152.9 | 185.9 | 209.8 |
| 67.5° | 16.9 | 13.3 | 9.4 | 9.4 | 10.6 | 10.6 | 12.8 | 25.3 | 35.5 | 32.4 |
| 70° | 11.0 | 9.2 | 5.9 | 5.7 | 6.9 | 6.9 | 6.5 | 6.9 | 7.3 | 7.3 |
| 72.5° | 8.2 | 6.9 | 3.5 | 3.1 | 3.9 | 4.1 | 3.7 | 3.5 | 3.5 | 3.5 |
| 75° | 6.1 | 4.9 | 2.0 | 1.4 | 1.8 | 2.4 | 2.0 | 1.4 | 1.4 | 1.2 |
| 77.5° | 2.4 | 1.8 | 0.8 | 0.6 | 1.0 | 1.4 | 1.2 | 0.6 | 0.4 | 0.4 |
| 80° | 0.2 | 0.4 | 0.4 | 0.4 | 0.6 | 0.8 | 1.0 | 0.4 | 0.2 | 0.2 |
| 82.5° | 0.0 | 0.2 | 0.2 | 0.2 | 0.4 | 0.6 | 0.8 | 0.4 | 0.2 | 0.2 |
| 85° | 0.0 | 0.0 | 0.0 | 0.0 | 0.4 | 0.6 | 0.4 | 0.2 | 0.0 | 0.0 |
| 87.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.2 | 0.6 | 0.4 | 0.2 | 0.0 | 0.0 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |

LM-79-08: Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Report Prepared for

Cooper Lighting Solutions

MCGRAW, INVUE, LUMARK AND STREETWORKS

DATA VALID FOR LUMINAIRES UTILIZING SA LIGHT ENGINES

Report Number: SP1-2101-121-2

Luminaire Tested: IFLD-S-SA2A-740-U-T3R-HSS

Test Date: 03/05/2021

Test Information

Test Method: LM-79-08
 Report Number: SP1-2101-121-2
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1
 Measurement Geometry: 4π
 Issue Date: 03/05/2021
 Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
 Product Line: STREETWORKS
 Catalog Number: **IFLD-S-SA2A-740-U-T3R-HSS**
 Description: STREETWORKS INF FLOOD

SHIELD, DRIVER PROGRAMMED @ 615mA.

Spectral Parameters

| | | | | | |
|---------------------------|---------|-----------|------|------|-------|
| CCT (K): | 3905 | CRI (Ra): | 71.2 | R9: | -29.7 |
| CIE u': | 0.2273 | R1: | 68.9 | R10: | 46.2 |
| CIE v': | 0.5024 | R2: | 77.0 | R11: | 68.8 |
| Duv: | -0.0008 | R3: | 84.0 | R12: | 45.6 |
| CIE x: | 0.3841 | R4: | 71.6 | R13: | 69.5 |
| CIE y: | 0.3774 | R5: | 68.9 | R14: | 90.7 |
| CIE z: | 0.2385 | R6: | 68.3 | | |
| Peak Wavelength (nm): | 443 | R7: | 78.7 | | |
| Dominant Wavelength (nm): | 579 | R8: | 52.2 | | |
| Purity: | 28.7 | | | | |
| Rf: | 71.7 | | | | |
| Rg: | 96.9 | | | | |



Test Conditions

Stabilization Time: 211M
 Operation Time: 12H
 Room Temperature (°C) / RH%: 24.8/312%
 Sphere Temperature (°C): 24.1

REPORT NUMBER: SP1-2101-121-2

| Measurement and Test Equipment | | | |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument | Identification Number | Calibration Date | Calibration Due Date |
| Photometer | IN0058 | 1/31/2021 | 7/31/2021 |
| Power Meter | IN0071 | 12/1/2020 | 12/1/2021 |
| AC Power Source | IN0063 | 12/1/2020 | 12/1/2021 |
| DC Power Source | IN0208 | 12/1/2020 | 12/1/2021 |
| Sphere Thermometer | IN0085 | 12/1/2020 | 12/1/2021 |
| Room Thermometer | IN0046 | 12/1/2020 | 12/1/2021 |

REPORT NUMBER: SP1-2101-121-2

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 4000K 4-step quadrangle

REPORT NUMBER: SP1-2101-121-2

Photopic Flux vs. Wavelength



#####

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 2304 | 0.0 | 490 | 19043 | 2.7 | 620 | 97577 | 25.4 | 750 | 4830 | 0.0 | 880 | 3505 | 0.0 |
| 365 | 2150 | 0.0 | 495 | 26606 | 4.8 | 625 | 90158 | 19.9 | 755 | 4664 | 0.0 | 885 | 2991 | 0.0 |
| 370 | 2146 | 0.0 | 500 | 36376 | 8.0 | 630 | 82240 | 14.9 | 760 | 4006 | 0.0 | 890 | 2327 | 0.0 |
| 375 | 2332 | 0.0 | 505 | 47714 | 13.3 | 635 | 74361 | 11.2 | 765 | 3715 | 0.0 | 895 | 2775 | 0.0 |
| 380 | 2527 | 0.0 | 510 | 58741 | 20.2 | 640 | 66994 | 8.0 | 770 | 3696 | 0.0 | 900 | 2141 | 0.0 |
| 385 | 2304 | 0.0 | 515 | 68716 | 28.5 | 645 | 60405 | 5.8 | 775 | 3117 | 0.0 | 905 | 2421 | 0.0 |
| 390 | 2064 | 0.0 | 520 | 77136 | 37.4 | 650 | 53806 | 3.9 | 780 | 3062 | 0.0 | 910 | 2200 | 0.0 |
| 395 | 1856 | 0.0 | 525 | 83567 | 44.9 | 655 | 47610 | 2.7 | 785 | 2907 | 0.0 | 915 | 2716 | 0.0 |
| 400 | 1856 | 0.0 | 530 | 89283 | 52.6 | 660 | 42018 | 1.8 | 790 | 2655 | 0.0 | 920 | 2656 | 0.0 |
| 405 | 2374 | 0.0 | 535 | 94097 | 58.4 | 665 | 36742 | 1.2 | 795 | 2467 | 0.0 | 925 | 2671 | 0.0 |
| 410 | 4084 | 0.0 | 540 | 96845 | 63.1 | 670 | 32105 | 0.7 | 800 | 2609 | 0.0 | 930 | 3292 | 0.0 |
| 415 | 8543 | 0.0 | 545 | 100829 | 67.1 | 675 | 27946 | 0.5 | 805 | 2293 | 0.0 | 935 | 3188 | 0.0 |
| 420 | 18394 | 0.1 | 550 | 105648 | 71.8 | 680 | 24146 | 0.3 | 810 | 2188 | 0.0 | 940 | 1997 | 0.0 |
| 425 | 37987 | 0.2 | 555 | 110017 | 75.1 | 685 | 21191 | 0.2 | 815 | 2386 | 0.0 | 945 | 2623 | 0.0 |
| 430 | 67605 | 0.5 | 560 | 114586 | 77.9 | 690 | 18544 | 0.1 | 820 | 2712 | 0.0 | 950 | 2969 | 0.0 |
| 435 | 102160 | 1.2 | 565 | 118987 | 79.1 | 695 | 16058 | 0.1 | 825 | 2473 | 0.0 | 955 | 2277 | 0.0 |
| 440 | 135103 | 2.1 | 570 | 122326 | 79.5 | 700 | 14133 | 0.0 | 830 | 1969 | 0.0 | 960 | 4267 | 0.0 |
| 445 | 140126 | 2.9 | 575 | 125968 | 78.4 | 705 | 12309 | 0.0 | 835 | 1917 | 0.0 | 965 | 2034 | 0.0 |
| 450 | 102339 | 2.7 | 580 | 127613 | 75.8 | 710 | 11142 | 0.0 | 840 | 2248 | 0.0 | 970 | 3586 | 0.0 |
| 455 | 58751 | 2.0 | 585 | 129466 | 71.9 | 715 | 10143 | 0.0 | 845 | 2266 | 0.0 | 975 | 2505 | 0.0 |
| 460 | 36892 | 1.5 | 590 | 128813 | 66.6 | 720 | 9072 | 0.0 | 850 | 2558 | 0.0 | 980 | 2666 | 0.0 |
| 465 | 24637 | 1.3 | 595 | 126387 | 59.9 | 725 | 8130 | 0.0 | 855 | 2767 | 0.0 | 985 | 2934 | 0.0 |
| 470 | 16738 | 1.0 | 600 | 123477 | 53.2 | 730 | 7149 | 0.0 | 860 | 2826 | 0.0 | 990 | 4120 | 0.0 |
| 475 | 13456 | 1.1 | 605 | 118718 | 46.0 | 735 | 6311 | 0.0 | 865 | 2385 | 0.0 | 995 | 3858 | 0.0 |
| 480 | 13081 | 1.2 | 610 | 112091 | 38.5 | 740 | 5711 | 0.0 | 870 | 3194 | 0.0 | 1000 | 3405 | 0.0 |
| 485 | 14734 | 1.7 | 615 | 105039 | 31.7 | 745 | 5111 | 0.0 | 875 | 3189 | 0.0 | | | |

REPORT NUMBER: SP1-2101-121-2

Scotopic Flux vs. Wavelength



Scotopic Lumens: 10425.8 S/P: 1.47

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 2304 | 0.0 | 490 | 19043 | 29.3 | 620 | 97577 | 1.2 | 750 | 4830 | 0.0 | 880 | 3505 | 0.0 |
| 365 | 2150 | 0.0 | 495 | 26606 | 43.0 | 625 | 90158 | 0.8 | 755 | 4664 | 0.0 | 885 | 2991 | 0.0 |
| 370 | 2146 | 0.0 | 500 | 36376 | 60.8 | 630 | 82240 | 0.5 | 760 | 4006 | 0.0 | 890 | 2327 | 0.0 |
| 375 | 2332 | 0.0 | 505 | 47714 | 81.1 | 635 | 74361 | 0.3 | 765 | 3715 | 0.0 | 895 | 2775 | 0.0 |
| 380 | 2527 | 0.0 | 510 | 58741 | 99.6 | 640 | 66994 | 0.2 | 770 | 3696 | 0.0 | 900 | 2141 | 0.0 |
| 385 | 2304 | 0.0 | 515 | 68716 | 113.9 | 645 | 60405 | 0.1 | 775 | 3117 | 0.0 | 905 | 2421 | 0.0 |
| 390 | 2064 | 0.0 | 520 | 77136 | 122.6 | 650 | 53806 | 0.1 | 780 | 3062 | 0.0 | 910 | 2200 | 0.0 |
| 395 | 1856 | 0.0 | 525 | 83567 | 125.0 | 655 | 47610 | 0.0 | 785 | 2907 | 0.0 | 915 | 2716 | 0.0 |
| 400 | 1856 | 0.0 | 530 | 89283 | 123.1 | 660 | 42018 | 0.0 | 790 | 2655 | 0.0 | 920 | 2656 | 0.0 |
| 405 | 2374 | 0.1 | 535 | 94097 | 117.3 | 665 | 36742 | 0.0 | 795 | 2467 | 0.0 | 925 | 2671 | 0.0 |
| 410 | 4084 | 0.2 | 540 | 96845 | 107.0 | 670 | 32105 | 0.0 | 800 | 2609 | 0.0 | 930 | 3292 | 0.0 |
| 415 | 8543 | 0.9 | 545 | 100829 | 96.7 | 675 | 27946 | 0.0 | 805 | 2293 | 0.0 | 935 | 3188 | 0.0 |
| 420 | 18394 | 3.0 | 550 | 105648 | 86.4 | 680 | 24146 | 0.0 | 810 | 2188 | 0.0 | 940 | 1997 | 0.0 |
| 425 | 37987 | 9.3 | 555 | 110017 | 75.2 | 685 | 21191 | 0.0 | 815 | 2386 | 0.0 | 945 | 2623 | 0.0 |
| 430 | 67605 | 23.0 | 560 | 114586 | 64.0 | 690 | 18544 | 0.0 | 820 | 2712 | 0.0 | 950 | 2969 | 0.0 |
| 435 | 102160 | 45.7 | 565 | 118987 | 53.4 | 695 | 16058 | 0.0 | 825 | 2473 | 0.0 | 955 | 2277 | 0.0 |
| 440 | 135103 | 75.5 | 570 | 122326 | 43.2 | 700 | 14133 | 0.0 | 830 | 1969 | 0.0 | 960 | 4267 | 0.0 |
| 445 | 140126 | 93.8 | 575 | 125968 | 34.3 | 705 | 12309 | 0.0 | 835 | 1917 | 0.0 | 965 | 2034 | 0.0 |
| 450 | 102339 | 79.3 | 580 | 127613 | 26.3 | 710 | 11142 | 0.0 | 840 | 2248 | 0.0 | 970 | 3586 | 0.0 |
| 455 | 58751 | 51.3 | 585 | 129466 | 19.8 | 715 | 10143 | 0.0 | 845 | 2266 | 0.0 | 975 | 2505 | 0.0 |
| 460 | 36892 | 35.6 | 590 | 128813 | 14.3 | 720 | 9072 | 0.0 | 850 | 2558 | 0.0 | 980 | 2666 | 0.0 |
| 465 | 24637 | 26.0 | 595 | 126387 | 10.1 | 725 | 8130 | 0.0 | 855 | 2767 | 0.0 | 985 | 2934 | 0.0 |
| 470 | 16738 | 19.3 | 600 | 123477 | 7.0 | 730 | 7149 | 0.0 | 860 | 2826 | 0.0 | 990 | 4120 | 0.0 |
| 475 | 13456 | 16.8 | 605 | 118718 | 4.7 | 735 | 6311 | 0.0 | 865 | 2385 | 0.0 | 995 | 3858 | 0.0 |
| 480 | 13081 | 17.7 | 610 | 112091 | 3.0 | 740 | 5711 | 0.0 | 870 | 3194 | 0.0 | 1000 | 3405 | 0.0 |
| 485 | 14734 | 21.4 | 615 | 105039 | 1.9 | 745 | 5111 | 0.0 | 875 | 3189 | 0.0 | | | |

REPORT NUMBER: SP1-2101-121-2

Melanopic Flux vs. Wavelength



Melanopic Lumens: 3927.2 M/P: 0.55


| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 2304 | 0.0 | 490 | 19043 | 15.8 | 620 | 97577 | 0.1 | 750 | 4830 | 0.0 | 880 | 3505 | 0.0 |
| 365 | 2150 | 0.0 | 495 | 26606 | 22.0 | 625 | 90158 | 0.0 | 755 | 4664 | 0.0 | 885 | 2991 | 0.0 |
| 370 | 2146 | 0.0 | 500 | 36376 | 29.2 | 630 | 82240 | 0.0 | 760 | 4006 | 0.0 | 890 | 2327 | 0.0 |
| 375 | 2332 | 0.0 | 505 | 47714 | 36.6 | 635 | 74361 | 0.0 | 765 | 3715 | 0.0 | 895 | 2775 | 0.0 |
| 380 | 2527 | 0.0 | 510 | 58741 | 42.2 | 640 | 66994 | 0.0 | 770 | 3696 | 0.0 | 900 | 2141 | 0.0 |
| 385 | 2304 | 0.0 | 515 | 68716 | 44.9 | 645 | 60405 | 0.0 | 775 | 3117 | 0.0 | 905 | 2421 | 0.0 |
| 390 | 2064 | 0.0 | 520 | 77136 | 44.9 | 650 | 53806 | 0.0 | 780 | 3062 | 0.0 | 910 | 2200 | 0.0 |
| 395 | 1856 | 0.0 | 525 | 83567 | 42.4 | 655 | 47610 | 0.0 | 785 | 2907 | 0.0 | 915 | 2716 | 0.0 |
| 400 | 1856 | 0.0 | 530 | 89283 | 38.6 | 660 | 42018 | 0.0 | 790 | 2655 | 0.0 | 920 | 2656 | 0.0 |
| 405 | 2374 | 0.0 | 535 | 94097 | 33.9 | 665 | 36742 | 0.0 | 795 | 2467 | 0.0 | 925 | 2671 | 0.0 |
| 410 | 4084 | 0.2 | 540 | 96845 | 28.3 | 670 | 32105 | 0.0 | 800 | 2609 | 0.0 | 930 | 3292 | 0.0 |
| 415 | 8543 | 0.6 | 545 | 100829 | 23.4 | 675 | 27946 | 0.0 | 805 | 2293 | 0.0 | 935 | 3188 | 0.0 |
| 420 | 18394 | 2.1 | 550 | 105648 | 19.0 | 680 | 24146 | 0.0 | 810 | 2188 | 0.0 | 940 | 1997 | 0.0 |
| 425 | 37987 | 5.9 | 555 | 110017 | 14.8 | 685 | 21191 | 0.0 | 815 | 2386 | 0.0 | 945 | 2623 | 0.0 |
| 430 | 67605 | 14.3 | 560 | 114586 | 11.3 | 690 | 18544 | 0.0 | 820 | 2712 | 0.0 | 950 | 2969 | 0.0 |
| 435 | 102160 | 27.3 | 565 | 118987 | 8.4 | 695 | 16058 | 0.0 | 825 | 2473 | 0.0 | 955 | 2277 | 0.0 |
| 440 | 135103 | 45.1 | 570 | 122326 | 6.0 | 700 | 14133 | 0.0 | 830 | 1969 | 0.0 | 960 | 4267 | 0.0 |
| 445 | 140126 | 55.3 | 575 | 125968 | 4.2 | 705 | 12309 | 0.0 | 835 | 1917 | 0.0 | 965 | 2034 | 0.0 |
| 450 | 102339 | 47.2 | 580 | 127613 | 2.9 | 710 | 11142 | 0.0 | 840 | 2248 | 0.0 | 970 | 3586 | 0.0 |
| 455 | 58751 | 30.8 | 585 | 129466 | 1.9 | 715 | 10143 | 0.0 | 845 | 2266 | 0.0 | 975 | 2505 | 0.0 |
| 460 | 36892 | 21.7 | 590 | 128813 | 1.3 | 720 | 9072 | 0.0 | 850 | 2558 | 0.0 | 980 | 2666 | 0.0 |
| 465 | 24637 | 16.1 | 595 | 126387 | 0.8 | 725 | 8130 | 0.0 | 855 | 2767 | 0.0 | 985 | 2934 | 0.0 |
| 470 | 16738 | 12.0 | 600 | 123477 | 0.5 | 730 | 7149 | 0.0 | 860 | 2826 | 0.0 | 990 | 4120 | 0.0 |
| 475 | 13456 | 10.3 | 605 | 118718 | 0.3 | 735 | 6311 | 0.0 | 865 | 2385 | 0.0 | 995 | 3858 | 0.0 |
| 480 | 13081 | 10.5 | 610 | 112091 | 0.2 | 740 | 5711 | 0.0 | 870 | 3194 | 0.0 | 1000 | 3405 | 0.0 |
| 485 | 14734 | 12.1 | 615 | 105039 | 0.1 | 745 | 5111 | 0.0 | 875 | 3189 | 0.0 | | | |

Summary

$R_f = 71.7$
 $R_g = 96.9$
 CIE $R_a = 71.2$
 $R_g = -29.7$



Color Vector Graphics



Individual Sample Fidelity Index ($R_{f,i}$)

| | | | |
|------------|------------|------------|------------|
| CES01 = 85 | CES26 = 55 | CES51 = 86 | CES76 = 45 |
| CES02 = 61 | CES27 = 80 | CES52 = 87 | CES77 = 68 |
| CES03 = 30 | CES28 = 79 | CES53 = 74 | CES78 = 49 |
| CES04 = 70 | CES29 = 51 | CES54 = 81 | CES79 = 77 |
| CES05 = 47 | CES30 = 60 | CES55 = 80 | CES80 = 75 |
| CES06 = 50 | CES31 = 56 | CES56 = 69 | CES81 = 75 |
| CES07 = 40 | CES32 = 52 | CES57 = 67 | CES82 = 90 |
| CES08 = 39 | CES33 = 62 | CES58 = 69 | CES83 = 85 |
| CES09 = 29 | CES34 = 65 | CES59 = 86 | CES84 = 87 |
| CES10 = 74 | CES35 = 81 | CES60 = 91 | CES85 = 83 |
| CES11 = 57 | CES36 = 92 | CES61 = 85 | CES86 = 72 |
| CES12 = 63 | CES37 = 74 | CES62 = 81 | CES87 = 77 |
| CES13 = 42 | CES38 = 69 | CES63 = 72 | CES88 = 77 |
| CES14 = 74 | CES39 = 92 | CES64 = 69 | CES89 = 72 |
| CES15 = 71 | CES40 = 86 | CES65 = 64 | CES90 = 75 |
| CES16 = 46 | CES41 = 84 | CES66 = 63 | CES91 = 91 |
| CES17 = 49 | CES42 = 75 | CES67 = 60 | CES92 = 66 |
| CES18 = 56 | CES43 = 70 | CES68 = 67 | CES93 = 80 |
| CES19 = 72 | CES44 = 98 | CES69 = 77 | CES94 = 56 |
| CES20 = 65 | CES45 = 80 | CES70 = 57 | CES95 = 72 |
| CES21 = 86 | CES46 = 77 | CES71 = 53 | CES96 = 78 |
| CES22 = 78 | CES47 = 74 | CES72 = 84 | CES97 = 83 |
| CES23 = 92 | CES48 = 66 | CES73 = 47 | CES98 = 73 |
| CES24 = 91 | CES49 = 76 | CES74 = 96 | CES99 = 63 |
| CES25 = 72 | CES50 = 85 | CES75 = 52 | |



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)