

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: McGRAW-EDISON

Report Number: P632821

Luminaire Tested: GWS-SA2D-740-U-SLR-W

Issue Date: 1/10/2023

**Test Information**

Test Method: LM-79-2019  
Report Number: P632821  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2209-782-41)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 1/10/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: McGRAW-EDISON  
Catalog Number: GWS-SA2D-740-U-SLR-W  
Description: GALLEON WALL SLIM LUMINAIRE. (2) LIGHTSQUARES WITH 16 LEDS EACH AND  
SPILL LIGHT ELIMINATOR RIGHT OPTICS  
Light Source: (32) 4000K CCT, 70 CRI LEDS  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 11055.4 lumens  
Efficiency: N/A  
Efficacy: 134.7 lumens/watt  
Luminous Opening: Rectangular (W 1' x L: 0.5' x H: 0')  
IES Classification: Type III - Short  
BUG Rating: B2 - U0 - G2  
  
Input Watts (W): 82.1  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 0  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 28.75 FT



REPORT NUMBER: P632821  
 CATALOG NUMBER: GWS-SA2D-740-U-SLR-W

### Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd  
 - - - 1/2 Max cd



Based on 20 foot mounting height. Maximum calculated value = 5.2 fc  
 Type III - Short - N/A

REPORT NUMBER: P632821  
CATALOG NUMBER: GWS-SA2D-740-U-SLR-W

### Luminous Intensity Polar Plot



— Vertical Plane Through 45-Deg Lateral    - - - Horizontal Cone Through 62.5-Deg Vertical

REPORT NUMBER: P632821

CATALOG NUMBER: GWS-SA2D-740-U-SLR-W

**FLUX DISTRIBUTION:**

		Downward	Upward	Total
<b>House Side</b>	Lumens	2638.0	0.0	2638.0
	% Fixture	23.9	0.0	23.9
<b>Street Side</b>	Lumens	8417.4	0.0	8417.4
	% Fixture	76.1	0.0	76.1
<b>Total</b>	Lumens	11055.4	0.0	11055.4
	% Fixture	100.0	0.0	100.0

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	143.3	1.3
10°-20°	449.2	4.1
20°-30°	697.7	6.3
30°-40°	947.3	8.6
40°-50°	1501.5	13.6
50°-60°	2648.6	24.0
60°-70°	2946.9	26.7
70°-80°	1494.6	13.5
80°-90°	226.3	2.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	11055.4	100.0
0°-180°	11055.4	100.0

**Coefficient of Utilization**



REPORT NUMBER: P632821


CATALOG NUMBER: GWS-SA2D-740-U-SLR-W

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	721.8	6.5			
FM (30°-60°)	3753.8	34.0			
FH (60°-80°)	3770.0	34.1			G2/5000
FVH (80°-90°)	171.8	1.6			G2/225
BL (0°-30°)	568.4	5.1	B2/1000		
BM (30°-60°)	1343.6	12.2	B2/2500		
BH (60°-80°)	671.5	6.1	B2/1000		G2/1000
BVH (80°-90°)	54.5	0.5			G1/100
UL (90°-100°)	0.0	0.0		U0/0	
UH (100°-180°)	0.0	0.0		U0/0	

**BUG Rating: B2-U0-G2**

Type III Short





REPORT NUMBER: P632821  
 CATALOG NUMBER: GWS-SA2D-740-U-SLR-W

**CANDELA DISTRIBUTION (FULL):**

	0°	1°	5°	15°	25°	35°	45°	55°	65°	75°	85°
0°	1467.3	1467.3	1467.3	1467.3	1467.3	1467.3	1467.3	1467.3	1467.3	1467.3	1467.3
2.5°	1576.9	1576.1	1592.0	1616.3	1638.9	1648.9	1665.6	1664.0	1650.6	1633.0	1627.1
5°	1700.8	1704.2	1731.8	1785.3	1844.8	1869.9	1880.8	1876.6	1852.3	1821.3	1766.9
7.5°	1813.0	1818.8	1861.5	1941.9	2015.5	2049.0	2075.8	2070.8	2035.6	1977.9	1897.5
10°	1895.0	1901.7	1952.7	2047.3	2129.4	2158.6	2193.0	2194.6	2163.7	2085.8	2003.8
12.5°	1977.0	1983.7	2031.4	2117.6	2171.2	2172.0	2192.1	2203.0	2204.7	2168.7	2086.7
15°	2062.4	2068.3	2111.8	2160.3	2157.8	2110.9	2110.9	2131.9	2177.9	2203.8	2146.9
17.5°	2135.2	2142.7	2176.2	2160.3	2085.8	2001.3	1991.2	2018.0	2098.4	2198.0	2192.1
20°	2195.5	2201.3	2219.7	2114.3	1978.7	1868.2	1849.0	1879.9	1988.7	2162.0	2226.4
22.5°	2253.2	2256.6	2246.5	2054.0	1863.2	1736.8	1713.4	1746.0	1863.2	2098.4	2255.7
25°	2321.9	2318.5	2270.8	1991.2	1757.7	1633.0	1608.7	1645.6	1767.8	2013.8	2287.5
27.5°	2401.4	2388.8	2291.7	1923.4	1676.5	1556.0	1539.3	1578.6	1692.4	1936.0	2312.7
30°	2469.2	2444.9	2295.1	1863.2	1634.7	1523.4	1513.3	1550.1	1655.6	1883.3	2344.5
32.5°	2544.5	2511.0	2314.3	1847.3	1658.1	1602.0	1615.4	1617.9	1665.6	1868.2	2392.2
35°	2652.5	2609.0	2367.1	1893.3	1899.2	1993.8	2042.3	1977.0	1817.1	1901.7	2482.6
37.5°	2815.7	2760.5	2474.2	2092.5	2397.2	2609.0	2726.1	2577.2	2277.5	2028.1	2619.0
40°	3014.1	2943.8	2611.5	2460.8	2862.6	3201.6	3410.0	3191.5	2751.2	2343.6	2810.7
42.5°	3291.1	3217.5	2877.6	2822.4	3293.6	3798.3	4070.4	3744.8	3168.9	2751.2	3117.9
45°	3774.1	3702.9	3365.6	3184.8	3798.3	4533.2	4914.9	4462.1	3593.3	3160.5	3692.0
47.5°	4666.3	4582.6	4090.5	3586.6	4374.2	5487.4	6021.4	5361.9	4034.4	3629.3	4656.3
50°	5737.7	5657.3	5000.3	4062.0	5010.3	6507.7	7250.2	6419.0	4542.4	4199.3	5808.8
52.5°	7026.7	7011.6	6298.5	4663.0	5672.4	7595.9	8613.7	7590.0	5099.1	4966.8	7114.6
55°	8188.5	8335.8	7947.4	5579.5	6527.8	8962.7	10015.7	8867.3	5854.0	6235.7	8643.8
57.5°	8814.5	9210.5	9807.2	7449.4	7771.6	10596.5	11745.8	10426.6	7151.4	8348.3	10061.7
60°	8401.1	8849.7	9931.1	8857.2	9005.4	11905.6	13173.7	11737.4	8425.3	9814.8	9981.3
62.5°	7713.0	8115.6	9077.4	8035.3	9196.2	12193.6	13207.2	11965.9	8931.7	9070.7	9016.3
65°	6897.0	7302.9	8321.5	7014.1	8589.4	11509.7	12232.9	11293.8	8021.9	8195.2	8215.2
67.5°	5813.0	6188.0	7225.1	6236.6	7829.4	10506.1	10737.2	10336.2	7387.4	7663.7	7374.9
70°	4343.2	4681.4	5597.1	5068.1	6599.8	9198.7	9012.1	9071.5	6675.1	6949.7	6160.4
72.5°	2968.0	3222.5	4007.6	3982.5	5053.9	7364.0	7103.7	7667.0	5575.3	5939.4	4696.5
75°	2075.8	2274.2	2896.9	3146.3	3820.1	5458.1	5058.9	5738.5	4354.1	4873.9	3426.7
77.5°	1273.9	1405.3	1829.7	2331.1	2457.5	3735.6	3142.1	4318.1	3057.6	3554.8	2285.9
80°	637.0	700.6	888.9	1465.6	1629.7	2201.3	1735.1	2506.8	2069.1	2201.3	1264.7
82.5°	192.5	212.6	260.3	556.6	844.5	1267.2	1025.3	1456.4	1130.0	1032.0	498.0
85°	51.1	57.8	72.0	164.9	296.3	454.5	346.5	705.6	541.5	380.8	187.5
87.5°	4.2	4.2	3.3	3.3	1.7	0.0	0.0	50.2	101.3	57.8	32.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P632821  
 CATALOG NUMBER: GWS-SA2D-740-U-SLR-W

**CANDELA DISTRIBUTION (continued):**

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	1467.3	1467.3	1467.3	1467.3	1467.3	1467.3	1467.3	1467.3	1467.3	1467.3	1467.3
2.5°	1597.9	1594.5	1560.2	1535.1	1505.8	1477.3	1448.0	1422.1	1392.8	1363.5	1355.1
5°	1726.8	1703.3	1630.5	1569.4	1509.1	1456.4	1410.4	1362.7	1324.1	1286.5	1272.3
7.5°	1840.6	1799.6	1694.1	1601.2	1517.5	1452.2	1384.4	1314.9	1260.5	1207.0	1193.6
10°	1943.5	1889.1	1756.0	1638.9	1546.0	1471.5	1391.9	1299.0	1220.4	1155.1	1137.5
12.5°	2019.7	1960.3	1809.6	1674.9	1569.4	1485.7	1407.0	1325.0	1242.1	1157.6	1138.3
15°	2080.0	2018.0	1854.0	1702.5	1570.2	1462.3	1386.1	1357.6	1331.7	1248.8	1213.7
17.5°	2128.5	2063.2	1892.5	1719.2	1547.6	1391.1	1325.0	1366.8	1433.0	1381.1	1314.9
20°	2172.9	2106.8	1921.8	1730.9	1497.4	1293.2	1256.4	1345.1	1444.7	1443.0	1383.6
22.5°	2221.4	2157.0	1964.5	1737.6	1427.1	1193.6	1215.3	1313.3	1394.5	1418.7	1381.9
25°	2283.4	2226.4	2023.9	1752.7	1347.6	1124.9	1185.2	1272.3	1340.1	1345.9	1324.1
27.5°	2355.3	2312.7	2112.6	1787.9	1270.6	1089.8	1150.1	1214.5	1276.4	1279.0	1253.0
30°	2434.0	2405.6	2194.6	1817.1	1212.8	1078.9	1104.9	1156.7	1196.1	1202.8	1180.2
32.5°	2534.5	2509.4	2267.5	1797.9	1178.5	1076.4	1063.0	1089.8	1122.4	1122.4	1104.9
35°	2672.6	2637.4	2344.5	1724.2	1136.7	1066.3	1018.6	1026.2	1040.4	1042.9	1032.9
37.5°	2868.4	2810.7	2422.3	1578.6	1068.0	1030.4	967.6	958.4	963.4	970.1	967.6
40°	3111.2	3016.6	2536.1	1403.7	986.0	960.9	914.9	897.3	893.1	906.5	911.5
42.5°	3416.7	3271.9	2658.3	1240.4	911.5	881.4	852.9	837.8	831.2	853.7	867.1
45°	3904.6	3666.1	2775.5	1078.9	869.7	813.6	794.3	783.4	786.8	813.6	830.3
47.5°	4747.5	4267.9	2886.8	976.8	866.3	765.0	741.6	744.1	753.3	781.8	801.9
50°	5813.9	5074.0	2961.3	934.1	876.3	735.7	704.8	718.2	732.4	760.0	783.4
52.5°	6899.5	5824.7	2872.6	910.7	875.5	736.6	670.4	710.6	717.3	744.9	770.0
55°	7646.1	5908.4	2481.7	874.7	862.1	770.0	643.7	707.3	711.5	736.6	759.2
57.5°	7930.7	5622.2	1892.5	884.7	821.9	796.0	631.9	683.8	714.0	735.7	759.2
60°	7586.7	5082.3	1150.1	910.7	757.5	794.3	639.5	641.1	693.0	729.9	753.3
62.5°	6938.0	4389.3	807.7	837.0	710.6	750.0	657.1	590.9	656.2	700.6	721.5
65°	6194.7	3574.0	616.0	720.7	688.0	681.3	662.9	546.6	606.0	649.5	667.9
67.5°	5420.5	2778.0	500.5	537.4	621.9	616.0	606.0	507.2	546.6	577.5	598.5
70°	4445.4	1943.5	422.7	403.4	533.2	552.4	529.8	457.8	470.4	502.2	518.9
72.5°	3251.8	1211.2	347.4	333.1	428.5	483.0	471.2	403.4	409.3	439.4	452.8
75°	2338.6	693.0	278.7	274.5	327.3	413.5	390.0	347.4	354.1	376.7	385.9
77.5°	1486.5	385.9	215.1	221.0	234.4	308.9	333.1	297.1	297.1	310.5	318.1
80°	796.0	221.0	157.4	159.9	164.1	236.0	262.8	230.2	230.2	221.0	230.2
82.5°	324.8	127.2	108.0	100.4	109.6	161.5	184.1	146.5	153.2	138.1	141.5
85°	107.1	63.6	53.6	52.7	51.9	71.1	88.7	72.8	87.0	55.2	57.8
87.5°	14.2	11.7	6.7	5.0	5.9	2.5	5.0	5.9	5.9	4.2	4.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0





REPORT NUMBER: P632821  
 CATALOG NUMBER: GWS-SA2D-740-U-SLR-W

**CANDELA DISTRIBUTION (continued):**

	185°	195°	205°	215°	225°	235°	245°	255°	265°	270°	275°
0°	1467.3	1467.3	1467.3	1467.3	1467.3	1467.3	1467.3	1467.3	1467.3	1467.3	1467.3
2.5°	1349.3	1342.6	1318.3	1324.1	1320.0	1313.3	1320.0	1307.4	1317.5	1320.8	1341.7
5°	1261.4	1245.5	1222.0	1210.3	1207.8	1201.1	1201.9	1196.1	1197.8	1212.0	1235.4
7.5°	1182.7	1167.6	1149.2	1140.8	1133.3	1125.8	1124.9	1124.1	1130.8	1143.4	1166.0
10°	1125.8	1117.4	1109.9	1113.2	1109.9	1106.5	1100.7	1100.7	1111.5	1134.1	1161.8
12.5°	1125.8	1124.1	1125.8	1135.8	1135.0	1135.8	1128.3	1132.5	1162.6	1201.1	1240.4
15°	1186.0	1172.7	1172.7	1177.7	1176.0	1176.0	1176.0	1193.6	1262.2	1321.6	1363.5
17.5°	1259.7	1220.4	1203.6	1201.1	1200.3	1200.3	1203.6	1241.3	1348.4	1411.2	1435.5
20°	1310.8	1236.3	1208.6	1197.8	1198.6	1200.3	1210.3	1262.2	1380.2	1412.0	1406.2
22.5°	1320.0	1223.7	1190.2	1174.3	1176.8	1178.5	1193.6	1248.8	1336.7	1341.7	1330.0
25°	1277.3	1188.6	1152.6	1140.0	1143.4	1142.5	1155.9	1196.1	1258.9	1257.2	1250.5
27.5°	1213.7	1132.5	1105.7	1097.3	1103.2	1096.5	1100.7	1131.6	1180.2	1178.5	1176.0
30°	1148.4	1078.1	1053.8	1049.6	1057.1	1047.1	1047.9	1073.9	1107.4	1105.7	1104.9
32.5°	1083.1	1023.7	1001.9	1001.9	1009.4	998.6	1000.2	1022.8	1045.4	1038.7	1038.7
35°	1021.2	979.3	961.7	958.4	964.2	956.7	960.0	981.0	989.3	980.1	974.3
37.5°	966.7	948.3	930.8	919.0	919.9	920.7	930.8	946.7	941.6	928.2	920.7
40°	916.5	916.5	899.8	878.0	875.5	881.4	898.1	915.7	901.5	886.4	877.2
42.5°	880.5	888.1	872.2	850.4	845.4	855.4	873.8	886.4	869.7	852.9	840.4
45°	847.1	865.5	854.6	830.3	823.6	835.3	858.8	863.8	841.2	825.3	816.1
47.5°	823.6	848.7	841.2	817.8	807.7	824.5	848.7	847.9	819.4	802.7	795.2
50°	806.9	838.7	837.8	817.8	806.9	827.8	849.6	838.7	807.7	790.1	782.6
52.5°	793.5	837.8	843.7	832.0	824.5	842.9	856.3	835.3	799.3	780.9	775.1
55°	787.6	841.2	845.4	834.5	827.8	844.5	856.3	842.0	799.3	782.6	777.6
57.5°	789.3	837.0	837.8	822.8	811.1	832.0	850.4	846.2	808.6	789.3	783.4
60°	779.3	814.4	816.1	792.6	779.3	804.4	837.0	834.5	804.4	784.3	773.4
62.5°	745.8	776.7	777.6	755.8	736.6	772.6	808.6	807.7	780.1	760.0	747.4
65°	689.7	722.3	730.7	709.8	694.7	733.2	770.9	769.2	741.6	723.2	710.6
67.5°	620.2	655.4	671.3	657.1	651.2	686.3	721.5	720.7	698.1	680.5	669.6
70°	535.7	565.0	591.8	591.8	587.6	627.8	665.4	662.1	641.1	627.8	619.4
72.5°	465.4	488.0	496.3	504.7	517.3	559.1	590.9	593.4	578.4	571.7	578.4
75°	395.9	410.1	417.7	411.0	432.7	476.3	518.1	522.3	506.4	495.5	498.0
77.5°	325.6	341.5	349.0	334.0	332.3	387.5	438.6	447.8	434.4	417.7	422.7
80°	235.2	256.1	268.7	258.6	255.3	279.6	349.9	359.9	347.4	334.0	341.5
82.5°	144.0	155.7	159.0	169.1	190.0	200.0	225.2	258.6	249.4	237.7	258.6
85°	56.9	67.8	75.3	85.4	99.6	118.0	138.9	165.7	150.7	145.6	171.6
87.5°	3.3	0.8	0.0	1.7	14.2	27.6	59.4	82.0	68.6	73.7	88.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P632821  
 CATALOG NUMBER: GWS-SA2D-740-U-SLR-W

**CANDELA DISTRIBUTION (continued):**

	285°	295°	305°	315°	325°	335°	345°	355°	359°	360°
0°	1467.3	1467.3	1467.3	1467.3	1467.3	1467.3	1467.3	1467.3	1467.3	1467.3
2.5°	1358.5	1380.2	1409.5	1433.8	1464.8	1494.1	1524.2	1554.3	1570.2	1576.9
5°	1262.2	1302.4	1349.3	1401.2	1461.4	1525.0	1589.5	1655.6	1697.5	1700.8
7.5°	1204.5	1262.2	1326.7	1391.9	1466.4	1554.3	1656.4	1758.6	1801.2	1813.0
10°	1222.9	1287.3	1338.4	1399.5	1481.5	1591.2	1711.7	1831.4	1880.8	1895.0
12.5°	1296.5	1309.1	1325.0	1381.1	1481.5	1623.0	1768.6	1910.9	1963.6	1977.0
15°	1357.6	1297.4	1268.9	1328.3	1461.4	1650.6	1828.9	1986.2	2049.8	2062.4
17.5°	1362.7	1258.9	1196.9	1250.5	1426.3	1669.8	1886.6	2069.9	2123.5	2135.2
20°	1311.6	1217.8	1137.5	1170.1	1378.6	1678.2	1928.5	2131.0	2183.8	2195.5
22.5°	1253.8	1184.4	1097.3	1095.6	1320.8	1687.4	1978.7	2188.8	2245.7	2253.2
25°	1199.4	1138.3	1064.7	1041.2	1253.8	1705.0	2046.5	2275.8	2319.4	2321.9
27.5°	1135.8	1088.9	1038.7	1016.1	1195.2	1738.5	2146.9	2379.6	2405.6	2401.4
30°	1078.1	1042.9	1020.3	1013.6	1158.4	1763.6	2242.3	2481.7	2483.4	2469.2
32.5°	1017.0	1003.6	1003.6	1025.3	1128.3	1757.7	2320.2	2581.3	2565.4	2544.5
35°	962.6	965.1	982.6	1033.7	1078.1	1699.1	2394.7	2706.1	2682.6	2652.5
37.5°	910.7	929.9	955.0	1004.4	1011.9	1612.1	2481.7	2882.7	2853.4	2815.7
40°	866.3	895.6	924.9	949.2	941.6	1488.2	2603.1	3090.2	3057.6	3014.1
42.5°	831.2	859.6	892.3	894.8	897.3	1359.3	2732.0	3344.7	3338.8	3291.1
45°	808.6	827.0	857.9	853.7	894.8	1217.0	2850.9	3733.1	3810.1	3774.1
47.5°	793.5	807.7	811.1	828.6	916.5	1089.8	3004.0	4493.1	4707.3	4666.3
50°	785.1	799.3	761.7	830.3	919.9	1007.8	3215.8	5447.3	5792.1	5737.7
52.5°	784.3	780.9	724.0	847.9	901.5	957.5	3326.3	6143.6	6908.7	7026.7
55°	786.0	744.1	704.8	852.9	864.6	939.1	2956.3	6478.5	7939.0	8188.5
57.5°	770.9	703.9	715.6	832.8	795.2	988.5	2185.4	6358.8	8350.8	8814.5
60°	742.4	665.4	735.7	778.4	724.0	904.0	1504.9	5824.7	7924.0	8401.1
62.5°	701.4	638.6	733.2	708.1	698.1	739.9	1034.5	5077.3	7246.8	7713.0
65°	655.4	616.9	693.9	640.3	646.2	569.2	731.5	4233.6	6438.3	6897.0
67.5°	606.0	603.5	636.1	570.0	545.7	451.1	533.2	3393.2	5399.5	5813.0
70°	549.9	568.3	578.4	506.4	442.8	354.1	395.9	2372.9	3983.3	4343.2
72.5°	493.8	495.5	509.7	440.3	331.5	283.7	297.1	1437.1	2706.1	2968.0
75°	436.9	421.0	434.4	358.2	246.9	232.7	229.3	888.1	1869.0	2075.8
77.5°	375.8	358.2	340.7	269.5	198.4	180.0	175.8	498.0	1146.7	1273.9
80°	305.5	282.1	254.5	197.5	144.8	128.9	128.1	242.7	571.7	637.0
82.5°	237.7	193.3	185.8	123.0	89.6	78.7	83.7	92.9	172.4	192.5
85°	166.6	140.6	98.8	49.4	40.2	32.6	31.8	27.6	46.0	51.1
87.5°	92.9	61.1	31.8	5.9	6.7	7.5	5.9	4.2	4.2	4.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)