

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: McGRAW-EDISON

Report Number: P637755

Luminaire Tested: GWS-SA4D-740-U-SL2-W-GRSWH

Issue Date: 1/10/2023

Test Information

Test Method: LM-79-2019
Report Number: P637755
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2209-782-29)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/10/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: McGRAW-EDISON
Catalog Number: GWS-SA4D-740-U-SL2-W-GRSWH
Description: GALLEON WALL SLIM LUMINAIRE. (4) LIGHTSQUARES WITH 16 LEDS EACH AND TYPE II SPILL LIGHT ELIMINATOR OPTICS W/ FACTORY INSTALLED GLARE SHIELD, WH
Light Source: (64) 4000K CCT, 70 CRI LEDS
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 20857.6 lumens
Efficiency: N/A
Efficacy: 128.7 lumens/watt
Luminous Opening: Rectangular (W 1' x L: 1' x H: 0')
IES Classification: Type II - Short
BUG Rating: B3 - U0 - G3


Input Watts (W): 162.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 0
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT



REPORT NUMBER: P637755
 CATALOG NUMBER: GWS-SA4D-740-U-SL2-W-GRSWH

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 10.7 fc
 Type II - Short - N/A

REPORT NUMBER: P637755
CATALOG NUMBER: GWS-SA4D-740-U-SL2-W-GRSWH

Luminous Intensity Polar Plot



— Vertical Plane Through 53-Deg Lateral - - - Horizontal Cone Through 57.5-Deg Vertical

REPORT NUMBER: P637755

CATALOG NUMBER: GWS-SA4D-740-U-SL2-W-GRSWH


FLUX DISTRIBUTION:

| | | Downward | Upward | Total |
|--------------------|-----------|----------|--------|---------|
| House Side | Lumens | 6521.4 | 0.0 | 6521.4 |
| | % Fixture | 31.3 | 0.0 | 31.3 |
| Street Side | Lumens | 14336.2 | 0.0 | 14336.2 |
| | % Fixture | 68.7 | 0.0 | 68.7 |
| Total | Lumens | 20857.6 | 0.0 | 20857.6 |
| | % Fixture | 100.0 | 0.0 | 100.0 |

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|---------|-----------|
| 0°-10° | 602.3 | 2.9 |
| 10°-20° | 1580.2 | 7.6 |
| 20°-30° | 2328.1 | 11.2 |
| 30°-40° | 3258.8 | 15.6 |
| 40°-50° | 4283.9 | 20.5 |
| 50°-60° | 5022.9 | 24.1 |
| 60°-70° | 2959.0 | 14.2 |
| 70°-80° | 736.1 | 3.5 |
| 80°-90° | 86.4 | 0.4 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-90° | 20857.6 | 100.0 |
| 0°-180° | 20857.6 | 100.0 |

Coefficient of Utilization



REPORT NUMBER: P637755


CATALOG NUMBER: GWS-SA4D-740-U-SL2-W-GRSWH

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

| Zone | Lumens | % Fixture | Zone Rating/Lumen Limit | | |
|----------------|--------|-----------|-------------------------|------|---------|
| | | | B | U | G |
| FL (0°-30°) | 2535.9 | 12.2 | | | |
| FM (30°-60°) | 9331.9 | 44.7 | | | |
| FH (60°-80°) | 2439.5 | 11.7 | | | G2/5000 |
| FVH (80°-90°) | 28.9 | 0.1 | | | G1/100 |
| BL (0°-30°) | 1974.7 | 9.5 | B3/2500 | | |
| BM (30°-60°) | 3233.6 | 15.5 | B3/5000 | | |
| BH (60°-80°) | 1255.6 | 6.0 | B3/2500 | | G3/2500 |
| BVH (80°-90°) | 57.5 | 0.3 | | | G1/100 |
| UL (90°-100°) | 0.0 | 0.0 | | U0/0 | |
| UH (100°-180°) | 0.0 | 0.0 | | U0/0 | |

BUG Rating: B3-U0-G3

Type II Short





REPORT NUMBER: P637755

CATALOG NUMBER: GWS-SA4D-740-U-SL2-W-GRSWH

CANDELA DISTRIBUTION (FULL):

| | 0° | 5° | 15° | 25° | 35° | 45° | 53° | 55° | 65° | 75° | 85° |
|-------|--------|--------|--------|--------|---------|---------|---------|---------|---------|---------|---------|
| 0° | 6660.4 | 6660.4 | 6660.4 | 6660.4 | 6660.4 | 6660.4 | 6660.4 | 6660.4 | 6660.4 | 6660.4 | 6660.4 |
| 2.5° | 6277.7 | 6295.2 | 6298.8 | 6353.2 | 6356.7 | 6435.7 | 6488.4 | 6477.8 | 6532.2 | 6599.0 | 6651.6 |
| 5° | 5977.5 | 5979.3 | 5996.8 | 6061.8 | 6096.9 | 6200.5 | 6288.2 | 6288.2 | 6393.6 | 6530.5 | 6648.1 |
| 7.5° | 5730.0 | 5728.2 | 5744.0 | 5816.0 | 5873.9 | 5998.6 | 6117.9 | 6132.0 | 6279.5 | 6479.6 | 6670.9 |
| 10° | 5500.0 | 5512.3 | 5529.8 | 5617.6 | 5691.4 | 5845.8 | 5988.0 | 6010.9 | 6196.9 | 6444.5 | 6702.5 |
| 12.5° | 5352.5 | 5354.3 | 5380.6 | 5478.9 | 5573.7 | 5738.8 | 5888.0 | 5916.1 | 6130.2 | 6411.1 | 6725.3 |
| 15° | 5257.7 | 5259.5 | 5287.6 | 5396.4 | 5507.0 | 5673.8 | 5826.5 | 5858.1 | 6091.6 | 6405.8 | 6769.2 |
| 17.5° | 5215.6 | 5213.9 | 5240.2 | 5349.0 | 5470.2 | 5644.0 | 5807.2 | 5845.8 | 6109.2 | 6446.2 | 6846.5 |
| 20° | 5215.6 | 5217.4 | 5231.4 | 5329.7 | 5452.6 | 5636.9 | 5826.5 | 5873.9 | 6177.6 | 6537.5 | 6965.9 |
| 22.5° | 5289.3 | 5296.4 | 5303.4 | 5370.1 | 5466.7 | 5647.5 | 5877.4 | 5940.6 | 6325.1 | 6690.2 | 7122.1 |
| 25° | 5433.3 | 5435.1 | 5442.1 | 5496.5 | 5540.4 | 5677.3 | 5961.7 | 6056.5 | 6555.1 | 6913.2 | 7318.7 |
| 27.5° | 5626.4 | 5651.0 | 5658.0 | 5693.1 | 5693.1 | 5751.0 | 6093.4 | 6230.3 | 6865.8 | 7234.4 | 7569.7 |
| 30° | 5896.7 | 5905.5 | 5917.8 | 5956.4 | 5914.3 | 5889.7 | 6286.5 | 6462.0 | 7225.7 | 7622.4 | 7871.7 |
| 32.5° | 6133.7 | 6153.1 | 6219.8 | 6283.0 | 6207.5 | 6130.2 | 6570.9 | 6778.0 | 7571.5 | 8026.2 | 8193.0 |
| 35° | 6335.6 | 6383.0 | 6511.2 | 6651.6 | 6599.0 | 6521.7 | 6948.3 | 7164.2 | 7855.9 | 8315.8 | 8477.3 |
| 37.5° | 6579.6 | 6616.5 | 6792.1 | 7020.3 | 7067.7 | 7030.8 | 7408.2 | 7562.7 | 8045.5 | 8389.6 | 8631.8 |
| 40° | 6827.2 | 6883.3 | 7109.8 | 7425.8 | 7606.6 | 7632.9 | 7833.1 | 7936.6 | 8110.4 | 8245.6 | 8602.0 |
| 42.5° | 7080.0 | 7176.5 | 7487.2 | 7855.9 | 8177.2 | 8236.8 | 8191.2 | 8235.1 | 8089.4 | 8047.2 | 8463.3 |
| 45° | 7388.9 | 7503.0 | 7854.1 | 8324.6 | 8747.7 | 8840.7 | 8542.3 | 8501.9 | 8085.9 | 7971.8 | 8377.3 |
| 47.5° | 7754.1 | 7868.2 | 8203.5 | 8751.2 | 9291.9 | 9360.4 | 8902.2 | 8828.4 | 8208.8 | 8087.6 | 8493.1 |
| 50° | 8077.1 | 8156.1 | 8456.3 | 9069.0 | 9799.2 | 9839.6 | 9298.9 | 9209.4 | 8514.2 | 8408.9 | 8854.8 |
| 52.5° | 7748.8 | 7740.0 | 8056.0 | 8810.9 | 10062.6 | 10548.8 | 9909.8 | 9823.8 | 9104.1 | 8942.6 | 9414.8 |
| 55° | 6574.4 | 6474.3 | 6756.9 | 7499.5 | 9327.0 | 11179.1 | 11005.3 | 10833.2 | 9890.5 | 9479.7 | 9939.7 |
| 57.5° | 4806.6 | 4778.5 | 4847.0 | 5543.9 | 7471.4 | 10203.0 | 11675.9 | 11660.1 | 10569.9 | 9971.3 | 10462.8 |
| 60° | 3758.5 | 3716.4 | 3533.8 | 3553.1 | 5092.7 | 7970.0 | 10132.8 | 10598.0 | 10991.2 | 10266.2 | 10828.0 |
| 62.5° | 3337.2 | 3305.6 | 3210.8 | 2949.3 | 3033.5 | 5343.8 | 7427.6 | 7854.1 | 9604.4 | 9067.2 | 9300.7 |
| 65° | 2763.2 | 2754.4 | 2833.4 | 2822.9 | 2542.0 | 2951.0 | 4192.2 | 4622.3 | 6038.9 | 6114.4 | 6038.9 |
| 67.5° | 2008.3 | 1992.5 | 2192.6 | 2587.6 | 2447.2 | 2227.7 | 2336.6 | 2485.8 | 3096.7 | 2780.7 | 2503.4 |
| 70° | 1306.1 | 1283.3 | 1399.1 | 1869.6 | 2190.9 | 1941.6 | 1683.5 | 1659.0 | 1702.8 | 1058.6 | 1144.6 |
| 72.5° | 876.0 | 849.7 | 847.9 | 1028.7 | 1323.7 | 1307.9 | 1304.3 | 1292.1 | 1153.4 | 835.6 | 926.9 |
| 75° | 488.0 | 467.0 | 461.7 | 444.1 | 474.0 | 482.8 | 514.4 | 531.9 | 575.8 | 633.7 | 702.2 |
| 77.5° | 82.5 | 80.8 | 101.8 | 129.9 | 179.1 | 230.0 | 284.4 | 300.2 | 370.4 | 438.9 | 482.8 |
| 80° | 45.6 | 47.4 | 61.4 | 75.5 | 100.1 | 136.9 | 175.6 | 186.1 | 228.2 | 265.1 | 300.2 |
| 82.5° | 24.6 | 24.6 | 31.6 | 40.4 | 54.4 | 72.0 | 94.8 | 103.6 | 131.7 | 154.5 | 179.1 |
| 85° | 8.8 | 8.8 | 12.3 | 15.8 | 22.8 | 29.8 | 36.9 | 42.1 | 57.9 | 79.0 | 89.5 |
| 87.5° | 0.0 | 0.0 | 0.0 | 0.0 | 1.8 | 3.5 | 7.0 | 7.0 | 8.8 | 15.8 | 22.8 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P637755

CATALOG NUMBER: GWS-SA4D-740-U-SL2-W-GRSWH

CANDELA DISTRIBUTION (continued):

| | 90° | 95° | 105° | 115° | 125° | 135° | 145° | 155° | 165° | 175° | 180° |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 6660.4 | 6660.4 | 6660.4 | 6660.4 | 6660.4 | 6660.4 | 6660.4 | 6660.4 | 6660.4 | 6660.4 | 6660.4 |
| 2.5° | 6695.5 | 6648.1 | 6713.1 | 6742.9 | 6753.4 | 6760.5 | 6714.8 | 6683.2 | 6672.7 | 6639.3 | 6620.0 |
| 5° | 6720.1 | 6688.5 | 6749.9 | 6749.9 | 6706.0 | 6660.4 | 6567.4 | 6502.4 | 6456.8 | 6402.3 | 6393.6 |
| 7.5° | 6762.2 | 6739.4 | 6772.7 | 6704.3 | 6593.7 | 6470.8 | 6309.3 | 6182.9 | 6081.1 | 6014.4 | 6016.1 |
| 10° | 6818.4 | 6790.3 | 6764.0 | 6611.2 | 6409.4 | 6182.9 | 5935.4 | 5751.0 | 5582.5 | 5505.3 | 5463.1 |
| 12.5° | 6855.3 | 6814.9 | 6704.3 | 6451.5 | 6154.8 | 5851.1 | 5501.8 | 5227.9 | 4983.9 | 4873.3 | 4864.5 |
| 15° | 6900.9 | 6827.2 | 6606.0 | 6244.3 | 5831.8 | 5417.5 | 4968.1 | 4587.1 | 4257.1 | 4085.1 | 4076.3 |
| 17.5° | 6960.6 | 6839.5 | 6488.4 | 6007.3 | 5491.2 | 4880.3 | 4315.0 | 3835.8 | 3484.7 | 3351.3 | 3374.1 |
| 20° | 7044.9 | 6853.5 | 6354.9 | 5744.0 | 5068.1 | 4269.4 | 3565.4 | 3124.8 | 2989.6 | 2980.9 | 2963.3 |
| 22.5° | 7139.6 | 6862.3 | 6207.5 | 5449.1 | 4555.5 | 3618.1 | 2945.7 | 2757.9 | 2756.1 | 2800.0 | 2810.6 |
| 25° | 7246.7 | 6869.3 | 6040.7 | 5105.0 | 4000.8 | 2968.6 | 2605.2 | 2549.0 | 2592.9 | 2675.4 | 2685.9 |
| 27.5° | 7383.7 | 6883.3 | 5838.8 | 4727.6 | 3411.0 | 2564.8 | 2417.3 | 2403.3 | 2456.0 | 2533.2 | 2529.7 |
| 30° | 7585.5 | 6934.3 | 5624.6 | 4294.0 | 2805.3 | 2373.4 | 2303.2 | 2305.0 | 2326.0 | 2362.9 | 2368.2 |
| 32.5° | 7790.9 | 7013.3 | 5415.7 | 3805.9 | 2457.7 | 2264.6 | 2233.0 | 2229.5 | 2229.5 | 2245.3 | 2248.8 |
| 35° | 7985.8 | 7102.8 | 5189.3 | 3296.8 | 2289.2 | 2201.4 | 2180.3 | 2169.8 | 2164.5 | 2161.0 | 2155.8 |
| 37.5° | 8094.6 | 7146.7 | 4968.1 | 2794.8 | 2199.7 | 2159.3 | 2138.2 | 2124.2 | 2104.9 | 2090.8 | 2087.3 |
| 40° | 8047.2 | 7095.8 | 4711.8 | 2419.1 | 2145.2 | 2118.9 | 2094.3 | 2075.0 | 2048.7 | 2036.4 | 2029.4 |
| 42.5° | 7889.3 | 6937.8 | 4432.7 | 2241.8 | 2101.3 | 2075.0 | 2045.2 | 2013.6 | 1996.0 | 1985.5 | 1983.7 |
| 45° | 7722.5 | 6746.4 | 4095.6 | 2138.2 | 2059.2 | 2027.6 | 1992.5 | 1957.4 | 1938.1 | 1932.8 | 1931.1 |
| 47.5° | 7717.2 | 6651.6 | 3737.5 | 2055.7 | 2008.3 | 1976.7 | 1932.8 | 1897.7 | 1876.6 | 1869.6 | 1862.6 |
| 50° | 7948.9 | 6748.2 | 3333.7 | 1983.7 | 1955.6 | 1922.3 | 1873.1 | 1834.5 | 1808.2 | 1799.4 | 1797.6 |
| 52.5° | 8429.9 | 7111.6 | 2972.1 | 1911.7 | 1885.4 | 1846.8 | 1806.4 | 1767.8 | 1736.2 | 1720.4 | 1718.6 |
| 55° | 8949.6 | 7573.3 | 2747.4 | 1838.0 | 1802.9 | 1769.6 | 1732.7 | 1690.6 | 1655.4 | 1630.9 | 1627.4 |
| 57.5° | 9486.8 | 8077.1 | 2678.9 | 1745.0 | 1718.6 | 1695.8 | 1651.9 | 1606.3 | 1565.9 | 1543.1 | 1537.8 |
| 60° | 9929.2 | 8510.7 | 2807.1 | 1646.7 | 1632.6 | 1602.8 | 1562.4 | 1518.5 | 1490.4 | 1472.9 | 1469.4 |
| 62.5° | 8312.3 | 6929.0 | 2266.4 | 1539.6 | 1539.6 | 1508.0 | 1462.3 | 1430.7 | 1411.4 | 1399.1 | 1395.6 |
| 65° | 5275.3 | 4290.5 | 1546.6 | 1432.5 | 1430.7 | 1388.6 | 1350.0 | 1328.9 | 1320.1 | 1300.8 | 1297.3 |
| 67.5° | 2298.0 | 1960.9 | 1321.9 | 1323.7 | 1316.6 | 1271.0 | 1232.4 | 1216.6 | 1199.0 | 1177.9 | 1176.2 |
| 70° | 1192.0 | 1214.8 | 1183.2 | 1202.5 | 1190.2 | 1135.8 | 1098.9 | 1074.4 | 1037.5 | 1016.4 | 1018.2 |
| 72.5° | 962.0 | 986.6 | 1021.7 | 1051.5 | 1025.2 | 981.3 | 923.4 | 893.6 | 846.2 | 823.3 | 825.1 |
| 75° | 733.8 | 760.1 | 793.5 | 825.1 | 804.0 | 749.6 | 712.7 | 682.9 | 628.5 | 602.1 | 607.4 |
| 77.5° | 505.6 | 519.6 | 560.0 | 558.3 | 551.2 | 535.4 | 481.0 | 445.9 | 389.7 | 358.1 | 361.6 |
| 80° | 314.2 | 323.0 | 342.3 | 351.1 | 347.6 | 326.5 | 282.6 | 256.3 | 222.9 | 203.6 | 205.4 |
| 82.5° | 189.6 | 194.9 | 212.4 | 214.2 | 212.4 | 196.6 | 163.3 | 144.0 | 122.9 | 112.4 | 112.4 |
| 85° | 96.6 | 100.1 | 110.6 | 110.6 | 100.1 | 84.3 | 75.5 | 66.7 | 54.4 | 49.2 | 49.2 |
| 87.5° | 26.3 | 26.3 | 33.4 | 28.1 | 22.8 | 21.1 | 10.5 | 8.8 | 3.5 | 1.8 | 1.8 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |

LM-79-08: Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Report Prepared for

Cooper Lighting Solutions

MCGRAW, INVUE, LUMARK AND STREETWORKS

DATA VALID FOR LUMINAIRES UTILIZING SA LIGHT ENGINES

Report Number: SP1-2101-121-2

Luminaire Tested: IFLD-S-SA2A-740-U-T3R-HSS

Test Date: 03/05/2021


Test Information

Test Method: LM-79-08
 Report Number: SP1-2101-121-2
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1
 Measurement Geometry: 4π
 Issue Date: 03/05/2021
 Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
 Product Line: STREETWORKS
 Catalog Number: **IFLD-S-SA2A-740-U-T3R-HSS**
 Description: STREETWORKS INF FLOOD

SHIELD, DRIVER PROGRAMMED @ 615mA.

Spectral Parameters

| | | | | | |
|---------------------------|---------|-----------|------|------|-------|
| CCT (K): | 3905 | CRI (Ra): | 71.2 | R9: | -29.7 |
| CIE u': | 0.2273 | R1: | 68.9 | R10: | 46.2 |
| CIE v': | 0.5024 | R2: | 77.0 | R11: | 68.8 |
| Duv: | -0.0008 | R3: | 84.0 | R12: | 45.6 |
| CIE x: | 0.3841 | R4: | 71.6 | R13: | 69.5 |
| CIE y: | 0.3774 | R5: | 68.9 | R14: | 90.7 |
| CIE z: | 0.2385 | R6: | 68.3 | | |
| Peak Wavelength (nm): | 443 | R7: | 78.7 | | |
| Dominant Wavelength (nm): | 579 | R8: | 52.2 | | |
| Purity: | 28.7 | | | | |
| Rf: | 71.7 | | | | |
| Rg: | 96.9 | | | | |



Test Conditions

Stabilization Time: 211M
 Operation Time: 12H
 Room Temperature (°C) / RH%: 24.8/312%
 Sphere Temperature (°C): 24.1

REPORT NUMBER: SP1-2101-121-2

| Measurement and Test Equipment | | | |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument | Identification Number | Calibration Date | Calibration Due Date |
| Photometer | IN0058 | 1/31/2021 | 7/31/2021 |
| Power Meter | IN0071 | 12/1/2020 | 12/1/2021 |
| AC Power Source | IN0063 | 12/1/2020 | 12/1/2021 |
| DC Power Source | IN0208 | 12/1/2020 | 12/1/2021 |
| Sphere Thermometer | IN0085 | 12/1/2020 | 12/1/2021 |
| Room Thermometer | IN0046 | 12/1/2020 | 12/1/2021 |

REPORT NUMBER: SP1-2101-121-2

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 4000K 4-step quadrangle

REPORT NUMBER: SP1-2101-121-2

Photopic Flux vs. Wavelength



#####

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 2304 | 0.0 | 490 | 19043 | 2.7 | 620 | 97577 | 25.4 | 750 | 4830 | 0.0 | 880 | 3505 | 0.0 |
| 365 | 2150 | 0.0 | 495 | 26606 | 4.8 | 625 | 90158 | 19.9 | 755 | 4664 | 0.0 | 885 | 2991 | 0.0 |
| 370 | 2146 | 0.0 | 500 | 36376 | 8.0 | 630 | 82240 | 14.9 | 760 | 4006 | 0.0 | 890 | 2327 | 0.0 |
| 375 | 2332 | 0.0 | 505 | 47714 | 13.3 | 635 | 74361 | 11.2 | 765 | 3715 | 0.0 | 895 | 2775 | 0.0 |
| 380 | 2527 | 0.0 | 510 | 58741 | 20.2 | 640 | 66994 | 8.0 | 770 | 3696 | 0.0 | 900 | 2141 | 0.0 |
| 385 | 2304 | 0.0 | 515 | 68716 | 28.5 | 645 | 60405 | 5.8 | 775 | 3117 | 0.0 | 905 | 2421 | 0.0 |
| 390 | 2064 | 0.0 | 520 | 77136 | 37.4 | 650 | 53806 | 3.9 | 780 | 3062 | 0.0 | 910 | 2200 | 0.0 |
| 395 | 1856 | 0.0 | 525 | 83567 | 44.9 | 655 | 47610 | 2.7 | 785 | 2907 | 0.0 | 915 | 2716 | 0.0 |
| 400 | 1856 | 0.0 | 530 | 89283 | 52.6 | 660 | 42018 | 1.8 | 790 | 2655 | 0.0 | 920 | 2656 | 0.0 |
| 405 | 2374 | 0.0 | 535 | 94097 | 58.4 | 665 | 36742 | 1.2 | 795 | 2467 | 0.0 | 925 | 2671 | 0.0 |
| 410 | 4084 | 0.0 | 540 | 96845 | 63.1 | 670 | 32105 | 0.7 | 800 | 2609 | 0.0 | 930 | 3292 | 0.0 |
| 415 | 8543 | 0.0 | 545 | 100829 | 67.1 | 675 | 27946 | 0.5 | 805 | 2293 | 0.0 | 935 | 3188 | 0.0 |
| 420 | 18394 | 0.1 | 550 | 105648 | 71.8 | 680 | 24146 | 0.3 | 810 | 2188 | 0.0 | 940 | 1997 | 0.0 |
| 425 | 37987 | 0.2 | 555 | 110017 | 75.1 | 685 | 21191 | 0.2 | 815 | 2386 | 0.0 | 945 | 2623 | 0.0 |
| 430 | 67605 | 0.5 | 560 | 114586 | 77.9 | 690 | 18544 | 0.1 | 820 | 2712 | 0.0 | 950 | 2969 | 0.0 |
| 435 | 102160 | 1.2 | 565 | 118987 | 79.1 | 695 | 16058 | 0.1 | 825 | 2473 | 0.0 | 955 | 2277 | 0.0 |
| 440 | 135103 | 2.1 | 570 | 122326 | 79.5 | 700 | 14133 | 0.0 | 830 | 1969 | 0.0 | 960 | 4267 | 0.0 |
| 445 | 140126 | 2.9 | 575 | 125968 | 78.4 | 705 | 12309 | 0.0 | 835 | 1917 | 0.0 | 965 | 2034 | 0.0 |
| 450 | 102339 | 2.7 | 580 | 127613 | 75.8 | 710 | 11142 | 0.0 | 840 | 2248 | 0.0 | 970 | 3586 | 0.0 |
| 455 | 58751 | 2.0 | 585 | 129466 | 71.9 | 715 | 10143 | 0.0 | 845 | 2266 | 0.0 | 975 | 2505 | 0.0 |
| 460 | 36892 | 1.5 | 590 | 128813 | 66.6 | 720 | 9072 | 0.0 | 850 | 2558 | 0.0 | 980 | 2666 | 0.0 |
| 465 | 24637 | 1.3 | 595 | 126387 | 59.9 | 725 | 8130 | 0.0 | 855 | 2767 | 0.0 | 985 | 2934 | 0.0 |
| 470 | 16738 | 1.0 | 600 | 123477 | 53.2 | 730 | 7149 | 0.0 | 860 | 2826 | 0.0 | 990 | 4120 | 0.0 |
| 475 | 13456 | 1.1 | 605 | 118718 | 46.0 | 735 | 6311 | 0.0 | 865 | 2385 | 0.0 | 995 | 3858 | 0.0 |
| 480 | 13081 | 1.2 | 610 | 112091 | 38.5 | 740 | 5711 | 0.0 | 870 | 3194 | 0.0 | 1000 | 3405 | 0.0 |
| 485 | 14734 | 1.7 | 615 | 105039 | 31.7 | 745 | 5111 | 0.0 | 875 | 3189 | 0.0 | | | |

REPORT NUMBER: SP1-2101-121-2

Scotopic Flux vs. Wavelength



Scotopic Lumens: 10425.8 S/P: 1.47

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 2304 | 0.0 | 490 | 19043 | 29.3 | 620 | 97577 | 1.2 | 750 | 4830 | 0.0 | 880 | 3505 | 0.0 |
| 365 | 2150 | 0.0 | 495 | 26606 | 43.0 | 625 | 90158 | 0.8 | 755 | 4664 | 0.0 | 885 | 2991 | 0.0 |
| 370 | 2146 | 0.0 | 500 | 36376 | 60.8 | 630 | 82240 | 0.5 | 760 | 4006 | 0.0 | 890 | 2327 | 0.0 |
| 375 | 2332 | 0.0 | 505 | 47714 | 81.1 | 635 | 74361 | 0.3 | 765 | 3715 | 0.0 | 895 | 2775 | 0.0 |
| 380 | 2527 | 0.0 | 510 | 58741 | 99.6 | 640 | 66994 | 0.2 | 770 | 3696 | 0.0 | 900 | 2141 | 0.0 |
| 385 | 2304 | 0.0 | 515 | 68716 | 113.9 | 645 | 60405 | 0.1 | 775 | 3117 | 0.0 | 905 | 2421 | 0.0 |
| 390 | 2064 | 0.0 | 520 | 77136 | 122.6 | 650 | 53806 | 0.1 | 780 | 3062 | 0.0 | 910 | 2200 | 0.0 |
| 395 | 1856 | 0.0 | 525 | 83567 | 125.0 | 655 | 47610 | 0.0 | 785 | 2907 | 0.0 | 915 | 2716 | 0.0 |
| 400 | 1856 | 0.0 | 530 | 89283 | 123.1 | 660 | 42018 | 0.0 | 790 | 2655 | 0.0 | 920 | 2656 | 0.0 |
| 405 | 2374 | 0.1 | 535 | 94097 | 117.3 | 665 | 36742 | 0.0 | 795 | 2467 | 0.0 | 925 | 2671 | 0.0 |
| 410 | 4084 | 0.2 | 540 | 96845 | 107.0 | 670 | 32105 | 0.0 | 800 | 2609 | 0.0 | 930 | 3292 | 0.0 |
| 415 | 8543 | 0.9 | 545 | 100829 | 96.7 | 675 | 27946 | 0.0 | 805 | 2293 | 0.0 | 935 | 3188 | 0.0 |
| 420 | 18394 | 3.0 | 550 | 105648 | 86.4 | 680 | 24146 | 0.0 | 810 | 2188 | 0.0 | 940 | 1997 | 0.0 |
| 425 | 37987 | 9.3 | 555 | 110017 | 75.2 | 685 | 21191 | 0.0 | 815 | 2386 | 0.0 | 945 | 2623 | 0.0 |
| 430 | 67605 | 23.0 | 560 | 114586 | 64.0 | 690 | 18544 | 0.0 | 820 | 2712 | 0.0 | 950 | 2969 | 0.0 |
| 435 | 102160 | 45.7 | 565 | 118987 | 53.4 | 695 | 16058 | 0.0 | 825 | 2473 | 0.0 | 955 | 2277 | 0.0 |
| 440 | 135103 | 75.5 | 570 | 122326 | 43.2 | 700 | 14133 | 0.0 | 830 | 1969 | 0.0 | 960 | 4267 | 0.0 |
| 445 | 140126 | 93.8 | 575 | 125968 | 34.3 | 705 | 12309 | 0.0 | 835 | 1917 | 0.0 | 965 | 2034 | 0.0 |
| 450 | 102339 | 79.3 | 580 | 127613 | 26.3 | 710 | 11142 | 0.0 | 840 | 2248 | 0.0 | 970 | 3586 | 0.0 |
| 455 | 58751 | 51.3 | 585 | 129466 | 19.8 | 715 | 10143 | 0.0 | 845 | 2266 | 0.0 | 975 | 2505 | 0.0 |
| 460 | 36892 | 35.6 | 590 | 128813 | 14.3 | 720 | 9072 | 0.0 | 850 | 2558 | 0.0 | 980 | 2666 | 0.0 |
| 465 | 24637 | 26.0 | 595 | 126387 | 10.1 | 725 | 8130 | 0.0 | 855 | 2767 | 0.0 | 985 | 2934 | 0.0 |
| 470 | 16738 | 19.3 | 600 | 123477 | 7.0 | 730 | 7149 | 0.0 | 860 | 2826 | 0.0 | 990 | 4120 | 0.0 |
| 475 | 13456 | 16.8 | 605 | 118718 | 4.7 | 735 | 6311 | 0.0 | 865 | 2385 | 0.0 | 995 | 3858 | 0.0 |
| 480 | 13081 | 17.7 | 610 | 112091 | 3.0 | 740 | 5711 | 0.0 | 870 | 3194 | 0.0 | 1000 | 3405 | 0.0 |
| 485 | 14734 | 21.4 | 615 | 105039 | 1.9 | 745 | 5111 | 0.0 | 875 | 3189 | 0.0 | | | |

REPORT NUMBER: SP1-2101-121-2

Melanopic Flux vs. Wavelength



Melanopic Lumens: 3927.2 M/P: 0.55


| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 2304 | 0.0 | 490 | 19043 | 15.8 | 620 | 97577 | 0.1 | 750 | 4830 | 0.0 | 880 | 3505 | 0.0 |
| 365 | 2150 | 0.0 | 495 | 26606 | 22.0 | 625 | 90158 | 0.0 | 755 | 4664 | 0.0 | 885 | 2991 | 0.0 |
| 370 | 2146 | 0.0 | 500 | 36376 | 29.2 | 630 | 82240 | 0.0 | 760 | 4006 | 0.0 | 890 | 2327 | 0.0 |
| 375 | 2332 | 0.0 | 505 | 47714 | 36.6 | 635 | 74361 | 0.0 | 765 | 3715 | 0.0 | 895 | 2775 | 0.0 |
| 380 | 2527 | 0.0 | 510 | 58741 | 42.2 | 640 | 66994 | 0.0 | 770 | 3696 | 0.0 | 900 | 2141 | 0.0 |
| 385 | 2304 | 0.0 | 515 | 68716 | 44.9 | 645 | 60405 | 0.0 | 775 | 3117 | 0.0 | 905 | 2421 | 0.0 |
| 390 | 2064 | 0.0 | 520 | 77136 | 44.9 | 650 | 53806 | 0.0 | 780 | 3062 | 0.0 | 910 | 2200 | 0.0 |
| 395 | 1856 | 0.0 | 525 | 83567 | 42.4 | 655 | 47610 | 0.0 | 785 | 2907 | 0.0 | 915 | 2716 | 0.0 |
| 400 | 1856 | 0.0 | 530 | 89283 | 38.6 | 660 | 42018 | 0.0 | 790 | 2655 | 0.0 | 920 | 2656 | 0.0 |
| 405 | 2374 | 0.0 | 535 | 94097 | 33.9 | 665 | 36742 | 0.0 | 795 | 2467 | 0.0 | 925 | 2671 | 0.0 |
| 410 | 4084 | 0.2 | 540 | 96845 | 28.3 | 670 | 32105 | 0.0 | 800 | 2609 | 0.0 | 930 | 3292 | 0.0 |
| 415 | 8543 | 0.6 | 545 | 100829 | 23.4 | 675 | 27946 | 0.0 | 805 | 2293 | 0.0 | 935 | 3188 | 0.0 |
| 420 | 18394 | 2.1 | 550 | 105648 | 19.0 | 680 | 24146 | 0.0 | 810 | 2188 | 0.0 | 940 | 1997 | 0.0 |
| 425 | 37987 | 5.9 | 555 | 110017 | 14.8 | 685 | 21191 | 0.0 | 815 | 2386 | 0.0 | 945 | 2623 | 0.0 |
| 430 | 67605 | 14.3 | 560 | 114586 | 11.3 | 690 | 18544 | 0.0 | 820 | 2712 | 0.0 | 950 | 2969 | 0.0 |
| 435 | 102160 | 27.3 | 565 | 118987 | 8.4 | 695 | 16058 | 0.0 | 825 | 2473 | 0.0 | 955 | 2277 | 0.0 |
| 440 | 135103 | 45.1 | 570 | 122326 | 6.0 | 700 | 14133 | 0.0 | 830 | 1969 | 0.0 | 960 | 4267 | 0.0 |
| 445 | 140126 | 55.3 | 575 | 125968 | 4.2 | 705 | 12309 | 0.0 | 835 | 1917 | 0.0 | 965 | 2034 | 0.0 |
| 450 | 102339 | 47.2 | 580 | 127613 | 2.9 | 710 | 11142 | 0.0 | 840 | 2248 | 0.0 | 970 | 3586 | 0.0 |
| 455 | 58751 | 30.8 | 585 | 129466 | 1.9 | 715 | 10143 | 0.0 | 845 | 2266 | 0.0 | 975 | 2505 | 0.0 |
| 460 | 36892 | 21.7 | 590 | 128813 | 1.3 | 720 | 9072 | 0.0 | 850 | 2558 | 0.0 | 980 | 2666 | 0.0 |
| 465 | 24637 | 16.1 | 595 | 126387 | 0.8 | 725 | 8130 | 0.0 | 855 | 2767 | 0.0 | 985 | 2934 | 0.0 |
| 470 | 16738 | 12.0 | 600 | 123477 | 0.5 | 730 | 7149 | 0.0 | 860 | 2826 | 0.0 | 990 | 4120 | 0.0 |
| 475 | 13456 | 10.3 | 605 | 118718 | 0.3 | 735 | 6311 | 0.0 | 865 | 2385 | 0.0 | 995 | 3858 | 0.0 |
| 480 | 13081 | 10.5 | 610 | 112091 | 0.2 | 740 | 5711 | 0.0 | 870 | 3194 | 0.0 | 1000 | 3405 | 0.0 |
| 485 | 14734 | 12.1 | 615 | 105039 | 0.1 | 745 | 5111 | 0.0 | 875 | 3189 | 0.0 | | | |

Summary

$R_f = 71.7$
 $R_g = 96.9$
 CIE $R_a = 71.2$
 $R_g = -29.7$



Color Vector Graphics



Individual Sample Fidelity Index ($R_{f,i}$)

| | | | |
|------------|------------|------------|------------|
| CES01 = 85 | CES26 = 55 | CES51 = 86 | CES76 = 45 |
| CES02 = 61 | CES27 = 80 | CES52 = 87 | CES77 = 68 |
| CES03 = 30 | CES28 = 79 | CES53 = 74 | CES78 = 49 |
| CES04 = 70 | CES29 = 51 | CES54 = 81 | CES79 = 77 |
| CES05 = 47 | CES30 = 60 | CES55 = 80 | CES80 = 75 |
| CES06 = 50 | CES31 = 56 | CES56 = 69 | CES81 = 75 |
| CES07 = 40 | CES32 = 52 | CES57 = 67 | CES82 = 90 |
| CES08 = 39 | CES33 = 62 | CES58 = 69 | CES83 = 85 |
| CES09 = 29 | CES34 = 65 | CES59 = 86 | CES84 = 87 |
| CES10 = 74 | CES35 = 81 | CES60 = 91 | CES85 = 83 |
| CES11 = 57 | CES36 = 92 | CES61 = 85 | CES86 = 72 |
| CES12 = 63 | CES37 = 74 | CES62 = 81 | CES87 = 77 |
| CES13 = 42 | CES38 = 69 | CES63 = 72 | CES88 = 77 |
| CES14 = 74 | CES39 = 92 | CES64 = 69 | CES89 = 72 |
| CES15 = 71 | CES40 = 86 | CES65 = 64 | CES90 = 75 |
| CES16 = 46 | CES41 = 84 | CES66 = 63 | CES91 = 91 |
| CES17 = 49 | CES42 = 75 | CES67 = 60 | CES92 = 66 |
| CES18 = 56 | CES43 = 70 | CES68 = 67 | CES93 = 80 |
| CES19 = 72 | CES44 = 98 | CES69 = 77 | CES94 = 56 |
| CES20 = 65 | CES45 = 80 | CES70 = 57 | CES95 = 72 |
| CES21 = 86 | CES46 = 77 | CES71 = 53 | CES96 = 78 |
| CES22 = 78 | CES47 = 74 | CES72 = 84 | CES97 = 83 |
| CES23 = 92 | CES48 = 66 | CES73 = 47 | CES98 = 73 |
| CES24 = 91 | CES49 = 76 | CES74 = 96 | CES99 = 63 |
| CES25 = 72 | CES50 = 85 | CES75 = 52 | |



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)