

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: McGRAW-EDISON

Report Number: P637788

Luminaire Tested: GWS-SA4D-740-U-T3R-W

Issue Date: 1/10/2023

Test Information

Test Method: LM-79-2019
Report Number: P637788
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2209-782-15)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/10/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: McGRAW-EDISON
Catalog Number: GWS-SA4D-740-U-T3R-W
Description: GALLEON WALL SLIM LUMINAIRE. (4) LIGHTSQUARES WITH 16 LEDS EACH AND TYPE III ROADWAY OPTICS
Light Source: (64) 4000K CCT, 70 CRI LEDS
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 24895.4 lumens
Efficiency: N/A
Efficacy: 153.6 lumens/watt
Luminous Opening: Rectangular (W 1' x L: 1' x H: 0')
IES Classification: Type III - Medium
BUG Rating: B3 - U0 - G4


Input Watts (W): 162.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 0
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT



REPORT NUMBER: P637788
 CATALOG NUMBER: GWS-SA4D-740-U-T3R-W

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 6.7 fc
 Type III - Medium - N/A

REPORT NUMBER: P637788
CATALOG NUMBER: GWS-SA4D-740-U-T3R-W

Luminous Intensity Polar Plot



— Vertical Plane Through 56-Deg Lateral - - - Horizontal Cone Through 70-Deg Vertical

REPORT NUMBER: P637788

CATALOG NUMBER: GWS-SA4D-740-U-T3R-W


FLUX DISTRIBUTION:

| | | Downward | Upward | Total |
|--------------------|-----------|----------|--------|---------|
| House Side | Lumens | 4786.2 | 0.0 | 4786.2 |
| | % Fixture | 19.2 | 0.0 | 19.2 |
| Street Side | Lumens | 20109.2 | 0.0 | 20109.2 |
| | % Fixture | 80.8 | 0.0 | 80.8 |
| Total | Lumens | 24895.4 | 0.0 | 24895.4 |
| | % Fixture | 100.0 | 0.0 | 100.0 |

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|---------|-----------|
| 0°-10° | 371.9 | 1.5 |
| 10°-20° | 1007.6 | 4.0 |
| 20°-30° | 1665.8 | 6.7 |
| 30°-40° | 2490.6 | 10.0 |
| 40°-50° | 3706.4 | 14.9 |
| 50°-60° | 5269.4 | 21.2 |
| 60°-70° | 6526.3 | 26.2 |
| 70°-80° | 3603.6 | 14.5 |
| 80°-90° | 253.8 | 1.0 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-90° | 24895.4 | 100.0 |
| 0°-180° | 24895.4 | 100.0 |

Coefficient of Utilization




REPORT NUMBER: P637788

CATALOG NUMBER: GWS-SA4D-740-U-T3R-W

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

| Zone | Lumens | % Fixture | Zone Rating/Lumen Limit | | |
|----------------|--------|-----------|-------------------------|------|----------|
| | | | B | U | G |
| FL (0°-30°) | 1749.6 | 7.0 | | | |
| FM (30°-60°) | 9325.4 | 37.5 | | | |
| FH (60°-80°) | 8857.8 | 35.6 | | | G4/12000 |
| FVH (80°-90°) | 176.4 | 0.7 | | | G2/225 |
| BL (0°-30°) | 1295.7 | 5.2 | B3/2500 | | |
| BM (30°-60°) | 2141.0 | 8.6 | B2/2500 | | |
| BH (60°-80°) | 1272.1 | 5.1 | B3/2500 | | G3/2500 |
| BVH (80°-90°) | 77.4 | 0.3 | | | G1/100 |
| UL (90°-100°) | 0.0 | 0.0 | | U0/0 | |
| UH (100°-180°) | 0.0 | 0.0 | | U0/0 | |

BUG Rating: B3-U0-G4
 Type III Medium





REPORT NUMBER: P637788

CATALOG NUMBER: GWS-SA4D-740-U-T3R-W

CANDELA DISTRIBUTION (FULL):

| | 0° | 5° | 15° | 25° | 35° | 45° | 55° | 56° | 65° | 75° | 85° |
|-------|--------|--------|--------|---------|---------|---------|---------|---------|---------|---------|---------|
| 0° | 4018.5 | 4018.5 | 4018.5 | 4018.5 | 4018.5 | 4018.5 | 4018.5 | 4018.5 | 4018.5 | 4018.5 | 4018.5 |
| 2.5° | 3760.4 | 3739.4 | 3763.9 | 3776.2 | 3807.8 | 3853.5 | 3893.9 | 3895.6 | 3916.7 | 3967.6 | 4016.7 |
| 5° | 3590.1 | 3579.6 | 3586.6 | 3623.5 | 3656.9 | 3714.8 | 3776.2 | 3781.5 | 3841.2 | 3941.3 | 4039.6 |
| 7.5° | 3458.5 | 3444.4 | 3470.8 | 3518.2 | 3560.3 | 3625.3 | 3706.0 | 3713.0 | 3797.3 | 3948.3 | 4099.3 |
| 10° | 3268.9 | 3258.3 | 3307.5 | 3370.7 | 3462.0 | 3569.1 | 3676.2 | 3684.9 | 3795.5 | 3993.9 | 4204.6 |
| 12.5° | 3186.4 | 3186.4 | 3207.4 | 3267.1 | 3367.2 | 3509.4 | 3670.9 | 3684.9 | 3823.6 | 4064.1 | 4339.8 |
| 15° | 3314.5 | 3323.3 | 3305.7 | 3302.2 | 3342.6 | 3477.8 | 3677.9 | 3699.0 | 3876.3 | 4136.1 | 4473.2 |
| 17.5° | 3572.6 | 3581.4 | 3535.7 | 3463.7 | 3423.4 | 3507.6 | 3704.3 | 3727.1 | 3932.5 | 4215.1 | 4617.1 |
| 20° | 3934.2 | 3944.8 | 3844.7 | 3734.1 | 3595.4 | 3593.7 | 3755.2 | 3776.2 | 4004.5 | 4301.1 | 4769.9 |
| 22.5° | 4357.3 | 4364.3 | 4237.9 | 4062.4 | 3850.0 | 3753.4 | 3842.9 | 3864.0 | 4097.5 | 4420.5 | 4934.9 |
| 25° | 4847.1 | 4868.2 | 4715.5 | 4460.9 | 4173.0 | 3972.9 | 3988.7 | 4013.2 | 4264.3 | 4580.3 | 5129.8 |
| 27.5° | 5370.3 | 5396.6 | 5221.1 | 4940.2 | 4543.4 | 4215.1 | 4176.5 | 4197.6 | 4441.6 | 4678.6 | 5233.4 |
| 30° | 5905.7 | 5925.0 | 5749.5 | 5428.2 | 4941.9 | 4489.0 | 4334.5 | 4346.8 | 4518.8 | 4726.0 | 5338.7 |
| 32.5° | 6500.9 | 6485.1 | 6316.5 | 5946.1 | 5401.9 | 4817.3 | 4482.0 | 4478.5 | 4604.9 | 4820.8 | 5489.7 |
| 35° | 7059.1 | 7082.0 | 6902.9 | 6493.9 | 5907.5 | 5222.8 | 4703.2 | 4689.1 | 4787.4 | 4975.3 | 5702.1 |
| 37.5° | 7735.0 | 7728.0 | 7513.8 | 7071.4 | 6414.9 | 5610.8 | 5013.9 | 4989.3 | 5024.4 | 5215.8 | 5998.8 |
| 40° | 8217.8 | 8267.0 | 8128.3 | 7715.7 | 7008.2 | 6088.3 | 5377.3 | 5322.9 | 5331.7 | 5512.5 | 6395.5 |
| 42.5° | 8612.8 | 8658.5 | 8672.5 | 8409.2 | 7687.6 | 6678.2 | 5830.2 | 5775.8 | 5781.1 | 6037.4 | 6883.6 |
| 45° | 8916.5 | 8978.0 | 9176.4 | 9099.1 | 8453.1 | 7359.4 | 6442.9 | 6386.8 | 6390.3 | 6674.7 | 7473.5 |
| 47.5° | 9041.2 | 9107.9 | 9509.9 | 9694.3 | 9265.9 | 8173.9 | 7204.9 | 7122.3 | 7134.6 | 7448.9 | 8147.6 |
| 50° | 9000.8 | 9090.3 | 9634.6 | 10152.5 | 9947.1 | 9002.6 | 8116.0 | 8058.1 | 8010.7 | 8467.1 | 8879.7 |
| 52.5° | 8653.2 | 8751.5 | 9622.3 | 10443.9 | 10503.6 | 9785.5 | 9057.0 | 9023.6 | 9013.1 | 9548.5 | 9697.8 |
| 55° | 7629.7 | 7794.7 | 9199.2 | 10521.1 | 10939.0 | 10522.9 | 10077.0 | 10020.8 | 10075.2 | 10707.2 | 10524.6 |
| 57.5° | 7062.7 | 7185.5 | 8370.6 | 10435.1 | 11295.3 | 11225.1 | 11095.2 | 11100.5 | 11161.9 | 11966.0 | 11527.1 |
| 60° | 6739.6 | 6883.6 | 7910.6 | 10199.9 | 11637.7 | 12078.3 | 12160.8 | 12160.8 | 12271.4 | 13323.0 | 12545.3 |
| 62.5° | 6311.3 | 6457.0 | 7480.5 | 9746.9 | 11953.7 | 13082.5 | 13500.3 | 13495.1 | 13539.0 | 14778.4 | 13540.7 |
| 65° | 5442.3 | 5577.4 | 6616.7 | 9032.4 | 12108.2 | 14188.5 | 15022.4 | 15006.6 | 14918.8 | 16074.0 | 14199.1 |
| 67.5° | 3951.8 | 4079.9 | 5068.3 | 7673.6 | 11551.7 | 15080.3 | 16590.1 | 16597.2 | 16072.2 | 16890.3 | 14234.2 |
| 70° | 2605.3 | 2693.0 | 3258.3 | 4984.1 | 9394.1 | 14695.9 | 17246.7 | 17267.8 | 16249.6 | 16381.2 | 12668.2 |
| 72.5° | 1625.7 | 1687.1 | 2034.7 | 2972.2 | 5551.1 | 11632.4 | 15561.4 | 15619.3 | 14618.6 | 14395.7 | 10408.8 |
| 75° | 1079.7 | 1121.8 | 1353.5 | 1732.7 | 2568.4 | 6295.5 | 11829.0 | 12015.1 | 11716.7 | 11284.8 | 7252.3 |
| 77.5° | 649.6 | 684.7 | 862.0 | 1100.7 | 1137.6 | 2459.6 | 6904.7 | 7385.7 | 7427.8 | 5891.7 | 3037.1 |
| 80° | 296.7 | 337.1 | 475.8 | 628.5 | 605.7 | 856.7 | 2435.0 | 2547.3 | 3005.5 | 1871.4 | 958.5 |
| 82.5° | 175.6 | 193.1 | 316.0 | 312.5 | 258.1 | 416.1 | 876.0 | 898.9 | 763.7 | 684.7 | 409.0 |
| 85° | 70.2 | 82.5 | 133.4 | 117.6 | 94.8 | 135.2 | 330.0 | 345.8 | 331.8 | 298.4 | 151.0 |
| 87.5° | 0.0 | 0.0 | 0.0 | 0.0 | 1.8 | 3.5 | 29.8 | 31.6 | 45.6 | 82.5 | 45.6 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P637788
 CATALOG NUMBER: GWS-SA4D-740-U-T3R-W

CANDELA DISTRIBUTION (continued):

| | 90° | 95° | 105° | 115° | 125° | 135° | 145° | 155° | 165° | 175° | 180° |
|-------|---------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 4018.5 | 4018.5 | 4018.5 | 4018.5 | 4018.5 | 4018.5 | 4018.5 | 4018.5 | 4018.5 | 4018.5 | 4018.5 |
| 2.5° | 4048.3 | 4037.8 | 4090.5 | 4130.9 | 4148.4 | 4166.0 | 4150.2 | 4144.9 | 4144.9 | 4109.8 | 4092.2 |
| 5° | 4092.2 | 4097.5 | 4169.5 | 4202.8 | 4202.8 | 4188.8 | 4146.7 | 4116.8 | 4106.3 | 4060.6 | 4048.3 |
| 7.5° | 4174.7 | 4197.6 | 4264.3 | 4262.5 | 4213.4 | 4136.1 | 4030.8 | 3950.0 | 3876.3 | 3844.7 | 3825.4 |
| 10° | 4309.9 | 4339.8 | 4385.4 | 4311.7 | 4174.7 | 3971.1 | 3748.1 | 3572.6 | 3467.3 | 3383.0 | 3383.0 |
| 12.5° | 4464.4 | 4492.5 | 4483.7 | 4313.4 | 4030.8 | 3649.8 | 3328.6 | 3126.7 | 2979.2 | 2902.0 | 2902.0 |
| 15° | 4618.9 | 4641.7 | 4546.9 | 4232.7 | 3730.6 | 3223.2 | 2872.1 | 2629.8 | 2501.7 | 2429.7 | 2429.7 |
| 17.5° | 4775.2 | 4773.4 | 4573.3 | 4046.6 | 3339.1 | 2751.0 | 2406.9 | 2219.0 | 2175.2 | 2162.9 | 2161.1 |
| 20° | 4926.1 | 4885.8 | 4539.9 | 3735.9 | 2884.4 | 2275.2 | 2057.5 | 2069.8 | 2134.8 | 2162.9 | 2166.4 |
| 22.5° | 5096.4 | 4996.4 | 4441.6 | 3339.1 | 2368.3 | 1945.2 | 1959.2 | 2061.0 | 2155.8 | 2198.0 | 2203.2 |
| 25° | 5270.2 | 5091.2 | 4276.6 | 2873.9 | 1936.4 | 1824.0 | 1932.9 | 2047.0 | 2154.1 | 2208.5 | 2213.8 |
| 27.5° | 5340.4 | 5091.2 | 3995.7 | 2334.9 | 1706.4 | 1773.1 | 1892.5 | 2003.1 | 2115.5 | 2178.7 | 2191.0 |
| 30° | 5398.4 | 5047.3 | 3602.4 | 1848.6 | 1611.6 | 1724.0 | 1827.5 | 1929.4 | 2040.0 | 2117.2 | 2131.3 |
| 32.5° | 5479.1 | 5008.6 | 3126.7 | 1553.7 | 1567.7 | 1676.6 | 1748.5 | 1834.6 | 1934.6 | 1985.6 | 1980.3 |
| 35° | 5573.9 | 4949.0 | 2552.6 | 1413.2 | 1530.9 | 1636.2 | 1687.1 | 1738.0 | 1692.4 | 1690.6 | 1695.9 |
| 37.5° | 5709.1 | 4896.3 | 2052.3 | 1350.0 | 1506.3 | 1608.1 | 1650.2 | 1541.4 | 1478.2 | 1451.9 | 1441.3 |
| 40° | 5904.0 | 4875.2 | 1618.6 | 1313.2 | 1502.8 | 1606.3 | 1576.5 | 1408.0 | 1321.9 | 1230.7 | 1228.9 |
| 42.5° | 6149.8 | 4859.4 | 1337.7 | 1295.6 | 1515.1 | 1646.7 | 1474.7 | 1320.2 | 1142.9 | 1102.5 | 1099.0 |
| 45° | 6465.8 | 4834.8 | 1197.3 | 1292.1 | 1544.9 | 1678.3 | 1464.1 | 1199.1 | 1077.9 | 1060.4 | 1060.4 |
| 47.5° | 6846.7 | 4796.2 | 1134.1 | 1292.1 | 1578.3 | 1664.3 | 1432.5 | 1172.7 | 1048.1 | 1067.4 | 1079.7 |
| 50° | 7283.9 | 4747.1 | 1100.7 | 1288.6 | 1611.6 | 1664.3 | 1365.8 | 1167.5 | 1041.1 | 1141.1 | 1181.5 |
| 52.5° | 7750.8 | 4690.9 | 1077.9 | 1274.5 | 1634.4 | 1666.0 | 1369.3 | 1185.0 | 1048.1 | 1158.7 | 1192.0 |
| 55° | 8267.0 | 4682.1 | 1046.3 | 1244.7 | 1641.5 | 1620.4 | 1378.1 | 1223.6 | 1058.6 | 1049.8 | 1051.6 |
| 57.5° | 8918.3 | 4787.4 | 1023.5 | 1200.8 | 1613.4 | 1527.3 | 1395.7 | 1251.7 | 1046.3 | 1048.1 | 1060.4 |
| 60° | 9599.5 | 4985.8 | 1042.8 | 1158.7 | 1555.4 | 1439.6 | 1408.0 | 1237.7 | 986.6 | 958.5 | 962.1 |
| 62.5° | 10178.8 | 5136.8 | 1058.6 | 1139.4 | 1471.2 | 1362.3 | 1395.7 | 1206.1 | 953.3 | 946.3 | 962.1 |
| 65° | 10421.1 | 5012.2 | 1020.0 | 1099.0 | 1348.3 | 1267.5 | 1369.3 | 1165.7 | 925.2 | 898.9 | 900.6 |
| 67.5° | 10152.5 | 4427.5 | 944.5 | 1009.5 | 1209.6 | 1146.4 | 1327.2 | 1113.0 | 886.6 | 855.0 | 847.9 |
| 70° | 8672.5 | 3253.1 | 814.6 | 867.3 | 1041.1 | 1004.2 | 1262.3 | 1044.6 | 825.1 | 802.3 | 786.5 |
| 72.5° | 6988.9 | 2303.3 | 675.9 | 689.9 | 816.3 | 846.2 | 1149.9 | 958.5 | 754.9 | 689.9 | 667.1 |
| 75° | 4864.7 | 1446.6 | 563.5 | 549.5 | 589.9 | 646.0 | 897.1 | 795.3 | 651.3 | 582.8 | 561.8 |
| 77.5° | 2092.6 | 742.6 | 440.6 | 433.6 | 393.2 | 447.7 | 688.2 | 663.6 | 546.0 | 467.0 | 454.7 |
| 80° | 700.5 | 430.1 | 317.8 | 305.5 | 261.6 | 314.2 | 484.5 | 530.2 | 428.4 | 345.8 | 324.8 |
| 82.5° | 351.1 | 249.3 | 201.9 | 182.6 | 175.6 | 198.4 | 286.2 | 330.0 | 296.7 | 238.8 | 201.9 |
| 85° | 172.0 | 142.2 | 110.6 | 108.8 | 91.3 | 86.0 | 119.4 | 140.4 | 133.4 | 98.3 | 93.0 |
| 87.5° | 63.2 | 56.2 | 35.1 | 28.1 | 17.6 | 12.3 | 7.0 | 7.0 | 5.3 | 5.3 | 5.3 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |

LM-79-08: Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Report Prepared for

Cooper Lighting Solutions

MCGRAW, INVUE, LUMARK AND STREETWORKS

DATA VALID FOR LUMINAIRES UTILIZING SA LIGHT ENGINES

Report Number: SP1-2101-121-2

Luminaire Tested: IFLD-S-SA2A-740-U-T3R-HSS

Test Date: 03/05/2021

Test Information

Test Method: LM-79-08
 Report Number: SP1-2101-121-2
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1
 Measurement Geometry: 4π
 Issue Date: 03/05/2021
 Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
 Product Line: STREETWORKS
 Catalog Number: **IFLD-S-SA2A-740-U-T3R-HSS**
 Description: STREETWORKS INF FLOOD

SHIELD, DRIVER PROGRAMMED @ 615mA.

Spectral Parameters

| | | | | | |
|---------------------------|---------|-----------|------|------|-------|
| CCT (K): | 3905 | CRI (Ra): | 71.2 | R9: | -29.7 |
| CIE u': | 0.2273 | R1: | 68.9 | R10: | 46.2 |
| CIE v': | 0.5024 | R2: | 77.0 | R11: | 68.8 |
| Duv: | -0.0008 | R3: | 84.0 | R12: | 45.6 |
| CIE x: | 0.3841 | R4: | 71.6 | R13: | 69.5 |
| CIE y: | 0.3774 | R5: | 68.9 | R14: | 90.7 |
| CIE z: | 0.2385 | R6: | 68.3 | | |
| Peak Wavelength (nm): | 443 | R7: | 78.7 | | |
| Dominant Wavelength (nm): | 579 | R8: | 52.2 | | |
| Purity: | 28.7 | | | | |
| Rf: | 71.7 | | | | |
| Rg: | 96.9 | | | | |



Test Conditions

| | |
|------------------------------|-----------|
| Stabilization Time: | 211M |
| Operation Time: | 12H |
| Room Temperature (°C) / RH%: | 24.8/312% |
| Sphere Temperature (°C): | 24.1 |

REPORT NUMBER: SP1-2101-121-2

| Measurement and Test Equipment | | | |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument | Identification Number | Calibration Date | Calibration Due Date |
| Photometer | IN0058 | 1/31/2021 | 7/31/2021 |
| Power Meter | IN0071 | 12/1/2020 | 12/1/2021 |
| AC Power Source | IN0063 | 12/1/2020 | 12/1/2021 |
| DC Power Source | IN0208 | 12/1/2020 | 12/1/2021 |
| Sphere Thermometer | IN0085 | 12/1/2020 | 12/1/2021 |
| Room Thermometer | IN0046 | 12/1/2020 | 12/1/2021 |

REPORT NUMBER: SP1-2101-121-2

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 4000K 4-step quadrangle

REPORT NUMBER: SP1-2101-121-2

Photopic Flux vs. Wavelength



#####

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 2304 | 0.0 | 490 | 19043 | 2.7 | 620 | 97577 | 25.4 | 750 | 4830 | 0.0 | 880 | 3505 | 0.0 |
| 365 | 2150 | 0.0 | 495 | 26606 | 4.8 | 625 | 90158 | 19.9 | 755 | 4664 | 0.0 | 885 | 2991 | 0.0 |
| 370 | 2146 | 0.0 | 500 | 36376 | 8.0 | 630 | 82240 | 14.9 | 760 | 4006 | 0.0 | 890 | 2327 | 0.0 |
| 375 | 2332 | 0.0 | 505 | 47714 | 13.3 | 635 | 74361 | 11.2 | 765 | 3715 | 0.0 | 895 | 2775 | 0.0 |
| 380 | 2527 | 0.0 | 510 | 58741 | 20.2 | 640 | 66994 | 8.0 | 770 | 3696 | 0.0 | 900 | 2141 | 0.0 |
| 385 | 2304 | 0.0 | 515 | 68716 | 28.5 | 645 | 60405 | 5.8 | 775 | 3117 | 0.0 | 905 | 2421 | 0.0 |
| 390 | 2064 | 0.0 | 520 | 77136 | 37.4 | 650 | 53806 | 3.9 | 780 | 3062 | 0.0 | 910 | 2200 | 0.0 |
| 395 | 1856 | 0.0 | 525 | 83567 | 44.9 | 655 | 47610 | 2.7 | 785 | 2907 | 0.0 | 915 | 2716 | 0.0 |
| 400 | 1856 | 0.0 | 530 | 89283 | 52.6 | 660 | 42018 | 1.8 | 790 | 2655 | 0.0 | 920 | 2656 | 0.0 |
| 405 | 2374 | 0.0 | 535 | 94097 | 58.4 | 665 | 36742 | 1.2 | 795 | 2467 | 0.0 | 925 | 2671 | 0.0 |
| 410 | 4084 | 0.0 | 540 | 96845 | 63.1 | 670 | 32105 | 0.7 | 800 | 2609 | 0.0 | 930 | 3292 | 0.0 |
| 415 | 8543 | 0.0 | 545 | 100829 | 67.1 | 675 | 27946 | 0.5 | 805 | 2293 | 0.0 | 935 | 3188 | 0.0 |
| 420 | 18394 | 0.1 | 550 | 105648 | 71.8 | 680 | 24146 | 0.3 | 810 | 2188 | 0.0 | 940 | 1997 | 0.0 |
| 425 | 37987 | 0.2 | 555 | 110017 | 75.1 | 685 | 21191 | 0.2 | 815 | 2386 | 0.0 | 945 | 2623 | 0.0 |
| 430 | 67605 | 0.5 | 560 | 114586 | 77.9 | 690 | 18544 | 0.1 | 820 | 2712 | 0.0 | 950 | 2969 | 0.0 |
| 435 | 102160 | 1.2 | 565 | 118987 | 79.1 | 695 | 16058 | 0.1 | 825 | 2473 | 0.0 | 955 | 2277 | 0.0 |
| 440 | 135103 | 2.1 | 570 | 122326 | 79.5 | 700 | 14133 | 0.0 | 830 | 1969 | 0.0 | 960 | 4267 | 0.0 |
| 445 | 140126 | 2.9 | 575 | 125968 | 78.4 | 705 | 12309 | 0.0 | 835 | 1917 | 0.0 | 965 | 2034 | 0.0 |
| 450 | 102339 | 2.7 | 580 | 127613 | 75.8 | 710 | 11142 | 0.0 | 840 | 2248 | 0.0 | 970 | 3586 | 0.0 |
| 455 | 58751 | 2.0 | 585 | 129466 | 71.9 | 715 | 10143 | 0.0 | 845 | 2266 | 0.0 | 975 | 2505 | 0.0 |
| 460 | 36892 | 1.5 | 590 | 128813 | 66.6 | 720 | 9072 | 0.0 | 850 | 2558 | 0.0 | 980 | 2666 | 0.0 |
| 465 | 24637 | 1.3 | 595 | 126387 | 59.9 | 725 | 8130 | 0.0 | 855 | 2767 | 0.0 | 985 | 2934 | 0.0 |
| 470 | 16738 | 1.0 | 600 | 123477 | 53.2 | 730 | 7149 | 0.0 | 860 | 2826 | 0.0 | 990 | 4120 | 0.0 |
| 475 | 13456 | 1.1 | 605 | 118718 | 46.0 | 735 | 6311 | 0.0 | 865 | 2385 | 0.0 | 995 | 3858 | 0.0 |
| 480 | 13081 | 1.2 | 610 | 112091 | 38.5 | 740 | 5711 | 0.0 | 870 | 3194 | 0.0 | 1000 | 3405 | 0.0 |
| 485 | 14734 | 1.7 | 615 | 105039 | 31.7 | 745 | 5111 | 0.0 | 875 | 3189 | 0.0 | | | |

REPORT NUMBER: SP1-2101-121-2

Scotopic Flux vs. Wavelength



Scotopic Lumens: 10425.8 S/P: 1.47

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 2304 | 0.0 | 490 | 19043 | 29.3 | 620 | 97577 | 1.2 | 750 | 4830 | 0.0 | 880 | 3505 | 0.0 |
| 365 | 2150 | 0.0 | 495 | 26606 | 43.0 | 625 | 90158 | 0.8 | 755 | 4664 | 0.0 | 885 | 2991 | 0.0 |
| 370 | 2146 | 0.0 | 500 | 36376 | 60.8 | 630 | 82240 | 0.5 | 760 | 4006 | 0.0 | 890 | 2327 | 0.0 |
| 375 | 2332 | 0.0 | 505 | 47714 | 81.1 | 635 | 74361 | 0.3 | 765 | 3715 | 0.0 | 895 | 2775 | 0.0 |
| 380 | 2527 | 0.0 | 510 | 58741 | 99.6 | 640 | 66994 | 0.2 | 770 | 3696 | 0.0 | 900 | 2141 | 0.0 |
| 385 | 2304 | 0.0 | 515 | 68716 | 113.9 | 645 | 60405 | 0.1 | 775 | 3117 | 0.0 | 905 | 2421 | 0.0 |
| 390 | 2064 | 0.0 | 520 | 77136 | 122.6 | 650 | 53806 | 0.1 | 780 | 3062 | 0.0 | 910 | 2200 | 0.0 |
| 395 | 1856 | 0.0 | 525 | 83567 | 125.0 | 655 | 47610 | 0.0 | 785 | 2907 | 0.0 | 915 | 2716 | 0.0 |
| 400 | 1856 | 0.0 | 530 | 89283 | 123.1 | 660 | 42018 | 0.0 | 790 | 2655 | 0.0 | 920 | 2656 | 0.0 |
| 405 | 2374 | 0.1 | 535 | 94097 | 117.3 | 665 | 36742 | 0.0 | 795 | 2467 | 0.0 | 925 | 2671 | 0.0 |
| 410 | 4084 | 0.2 | 540 | 96845 | 107.0 | 670 | 32105 | 0.0 | 800 | 2609 | 0.0 | 930 | 3292 | 0.0 |
| 415 | 8543 | 0.9 | 545 | 100829 | 96.7 | 675 | 27946 | 0.0 | 805 | 2293 | 0.0 | 935 | 3188 | 0.0 |
| 420 | 18394 | 3.0 | 550 | 105648 | 86.4 | 680 | 24146 | 0.0 | 810 | 2188 | 0.0 | 940 | 1997 | 0.0 |
| 425 | 37987 | 9.3 | 555 | 110017 | 75.2 | 685 | 21191 | 0.0 | 815 | 2386 | 0.0 | 945 | 2623 | 0.0 |
| 430 | 67605 | 23.0 | 560 | 114586 | 64.0 | 690 | 18544 | 0.0 | 820 | 2712 | 0.0 | 950 | 2969 | 0.0 |
| 435 | 102160 | 45.7 | 565 | 118987 | 53.4 | 695 | 16058 | 0.0 | 825 | 2473 | 0.0 | 955 | 2277 | 0.0 |
| 440 | 135103 | 75.5 | 570 | 122326 | 43.2 | 700 | 14133 | 0.0 | 830 | 1969 | 0.0 | 960 | 4267 | 0.0 |
| 445 | 140126 | 93.8 | 575 | 125968 | 34.3 | 705 | 12309 | 0.0 | 835 | 1917 | 0.0 | 965 | 2034 | 0.0 |
| 450 | 102339 | 79.3 | 580 | 127613 | 26.3 | 710 | 11142 | 0.0 | 840 | 2248 | 0.0 | 970 | 3586 | 0.0 |
| 455 | 58751 | 51.3 | 585 | 129466 | 19.8 | 715 | 10143 | 0.0 | 845 | 2266 | 0.0 | 975 | 2505 | 0.0 |
| 460 | 36892 | 35.6 | 590 | 128813 | 14.3 | 720 | 9072 | 0.0 | 850 | 2558 | 0.0 | 980 | 2666 | 0.0 |
| 465 | 24637 | 26.0 | 595 | 126387 | 10.1 | 725 | 8130 | 0.0 | 855 | 2767 | 0.0 | 985 | 2934 | 0.0 |
| 470 | 16738 | 19.3 | 600 | 123477 | 7.0 | 730 | 7149 | 0.0 | 860 | 2826 | 0.0 | 990 | 4120 | 0.0 |
| 475 | 13456 | 16.8 | 605 | 118718 | 4.7 | 735 | 6311 | 0.0 | 865 | 2385 | 0.0 | 995 | 3858 | 0.0 |
| 480 | 13081 | 17.7 | 610 | 112091 | 3.0 | 740 | 5711 | 0.0 | 870 | 3194 | 0.0 | 1000 | 3405 | 0.0 |
| 485 | 14734 | 21.4 | 615 | 105039 | 1.9 | 745 | 5111 | 0.0 | 875 | 3189 | 0.0 | | | |

REPORT NUMBER: SP1-2101-121-2

Melanopic Flux vs. Wavelength



Melanopic Lumens: 3927.2 M/P: 0.55

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 2304 | 0.0 | 490 | 19043 | 15.8 | 620 | 97577 | 0.1 | 750 | 4830 | 0.0 | 880 | 3505 | 0.0 |
| 365 | 2150 | 0.0 | 495 | 26606 | 22.0 | 625 | 90158 | 0.0 | 755 | 4664 | 0.0 | 885 | 2991 | 0.0 |
| 370 | 2146 | 0.0 | 500 | 36376 | 29.2 | 630 | 82240 | 0.0 | 760 | 4006 | 0.0 | 890 | 2327 | 0.0 |
| 375 | 2332 | 0.0 | 505 | 47714 | 36.6 | 635 | 74361 | 0.0 | 765 | 3715 | 0.0 | 895 | 2775 | 0.0 |
| 380 | 2527 | 0.0 | 510 | 58741 | 42.2 | 640 | 66994 | 0.0 | 770 | 3696 | 0.0 | 900 | 2141 | 0.0 |
| 385 | 2304 | 0.0 | 515 | 68716 | 44.9 | 645 | 60405 | 0.0 | 775 | 3117 | 0.0 | 905 | 2421 | 0.0 |
| 390 | 2064 | 0.0 | 520 | 77136 | 44.9 | 650 | 53806 | 0.0 | 780 | 3062 | 0.0 | 910 | 2200 | 0.0 |
| 395 | 1856 | 0.0 | 525 | 83567 | 42.4 | 655 | 47610 | 0.0 | 785 | 2907 | 0.0 | 915 | 2716 | 0.0 |
| 400 | 1856 | 0.0 | 530 | 89283 | 38.6 | 660 | 42018 | 0.0 | 790 | 2655 | 0.0 | 920 | 2656 | 0.0 |
| 405 | 2374 | 0.0 | 535 | 94097 | 33.9 | 665 | 36742 | 0.0 | 795 | 2467 | 0.0 | 925 | 2671 | 0.0 |
| 410 | 4084 | 0.2 | 540 | 96845 | 28.3 | 670 | 32105 | 0.0 | 800 | 2609 | 0.0 | 930 | 3292 | 0.0 |
| 415 | 8543 | 0.6 | 545 | 100829 | 23.4 | 675 | 27946 | 0.0 | 805 | 2293 | 0.0 | 935 | 3188 | 0.0 |
| 420 | 18394 | 2.1 | 550 | 105648 | 19.0 | 680 | 24146 | 0.0 | 810 | 2188 | 0.0 | 940 | 1997 | 0.0 |
| 425 | 37987 | 5.9 | 555 | 110017 | 14.8 | 685 | 21191 | 0.0 | 815 | 2386 | 0.0 | 945 | 2623 | 0.0 |
| 430 | 67605 | 14.3 | 560 | 114586 | 11.3 | 690 | 18544 | 0.0 | 820 | 2712 | 0.0 | 950 | 2969 | 0.0 |
| 435 | 102160 | 27.3 | 565 | 118987 | 8.4 | 695 | 16058 | 0.0 | 825 | 2473 | 0.0 | 955 | 2277 | 0.0 |
| 440 | 135103 | 45.1 | 570 | 122326 | 6.0 | 700 | 14133 | 0.0 | 830 | 1969 | 0.0 | 960 | 4267 | 0.0 |
| 445 | 140126 | 55.3 | 575 | 125968 | 4.2 | 705 | 12309 | 0.0 | 835 | 1917 | 0.0 | 965 | 2034 | 0.0 |
| 450 | 102339 | 47.2 | 580 | 127613 | 2.9 | 710 | 11142 | 0.0 | 840 | 2248 | 0.0 | 970 | 3586 | 0.0 |
| 455 | 58751 | 30.8 | 585 | 129466 | 1.9 | 715 | 10143 | 0.0 | 845 | 2266 | 0.0 | 975 | 2505 | 0.0 |
| 460 | 36892 | 21.7 | 590 | 128813 | 1.3 | 720 | 9072 | 0.0 | 850 | 2558 | 0.0 | 980 | 2666 | 0.0 |
| 465 | 24637 | 16.1 | 595 | 126387 | 0.8 | 725 | 8130 | 0.0 | 855 | 2767 | 0.0 | 985 | 2934 | 0.0 |
| 470 | 16738 | 12.0 | 600 | 123477 | 0.5 | 730 | 7149 | 0.0 | 860 | 2826 | 0.0 | 990 | 4120 | 0.0 |
| 475 | 13456 | 10.3 | 605 | 118718 | 0.3 | 735 | 6311 | 0.0 | 865 | 2385 | 0.0 | 995 | 3858 | 0.0 |
| 480 | 13081 | 10.5 | 610 | 112091 | 0.2 | 740 | 5711 | 0.0 | 870 | 3194 | 0.0 | 1000 | 3405 | 0.0 |
| 485 | 14734 | 12.1 | 615 | 105039 | 0.1 | 745 | 5111 | 0.0 | 875 | 3189 | 0.0 | | | |

Summary

$R_f = 71.7$
 $R_g = 96.9$
 CIE $R_a = 71.2$
 $R_g = -29.7$



Color Vector Graphics



Individual Sample Fidelity Index ($R_{f,i}$)

| | | | |
|------------|------------|------------|------------|
| CES01 = 85 | CES26 = 55 | CES51 = 86 | CES76 = 45 |
| CES02 = 61 | CES27 = 80 | CES52 = 87 | CES77 = 68 |
| CES03 = 30 | CES28 = 79 | CES53 = 74 | CES78 = 49 |
| CES04 = 70 | CES29 = 51 | CES54 = 81 | CES79 = 77 |
| CES05 = 47 | CES30 = 60 | CES55 = 80 | CES80 = 75 |
| CES06 = 50 | CES31 = 56 | CES56 = 69 | CES81 = 75 |
| CES07 = 40 | CES32 = 52 | CES57 = 67 | CES82 = 90 |
| CES08 = 39 | CES33 = 62 | CES58 = 69 | CES83 = 85 |
| CES09 = 29 | CES34 = 65 | CES59 = 86 | CES84 = 87 |
| CES10 = 74 | CES35 = 81 | CES60 = 91 | CES85 = 83 |
| CES11 = 57 | CES36 = 92 | CES61 = 85 | CES86 = 72 |
| CES12 = 63 | CES37 = 74 | CES62 = 81 | CES87 = 77 |
| CES13 = 42 | CES38 = 69 | CES63 = 72 | CES88 = 77 |
| CES14 = 74 | CES39 = 92 | CES64 = 69 | CES89 = 72 |
| CES15 = 71 | CES40 = 86 | CES65 = 64 | CES90 = 75 |
| CES16 = 46 | CES41 = 84 | CES66 = 63 | CES91 = 91 |
| CES17 = 49 | CES42 = 75 | CES67 = 60 | CES92 = 66 |
| CES18 = 56 | CES43 = 70 | CES68 = 67 | CES93 = 80 |
| CES19 = 72 | CES44 = 98 | CES69 = 77 | CES94 = 56 |
| CES20 = 65 | CES45 = 80 | CES70 = 57 | CES95 = 72 |
| CES21 = 86 | CES46 = 77 | CES71 = 53 | CES96 = 78 |
| CES22 = 78 | CES47 = 74 | CES72 = 84 | CES97 = 83 |
| CES23 = 92 | CES48 = 66 | CES73 = 47 | CES98 = 73 |
| CES24 = 91 | CES49 = 76 | CES74 = 96 | CES99 = 63 |
| CES25 = 72 | CES50 = 85 | CES75 = 52 | |



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)