

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: McGRAW-EDISON

Report Number: P637792

Luminaire Tested: GWS-SA4D-740-U-T4W-W

Issue Date: 1/10/2023

**Test Information**

Test Method: LM-79-2019  
Report Number: P637792  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2209-782-52)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 1/10/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: McGRAW-EDISON  
Catalog Number: GWS-SA4D-740-U-T4W-W  
Description: GALLEON WALL SLIM LUMINAIRE. (4) LIGHTSQUARES WITH 16 LEDS EACH AND TYPE IV WIDE OPTICS  
Light Source: (64) 4000K CCT, 70 CRI LEDS  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 24279.2 lumens  
Efficiency: N/A  
Efficacy: 149.8 lumens/watt  
Luminous Opening: Rectangular (W 1' x L: 1' x H: 0')  
IES Classification: Type III - Short  
BUG Rating: B3 - U0 - G4  
  
Input Watts (W): 162.1  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 0  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 28.75 FT



REPORT NUMBER: P637792  
 CATALOG NUMBER: GWS-SA4D-740-U-T4W-W

### Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd  
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 4.8 fc  
 Type III - Short - N/A

REPORT NUMBER: P637792  
CATALOG NUMBER: GWS-SA4D-740-U-T4W-W

### Luminous Intensity Polar Plot



— Vertical Plane Through 47-Deg Lateral    - - - Horizontal Cone Through 67.5-Deg Vertical

REPORT NUMBER: P637792

CATALOG NUMBER: GWS-SA4D-740-U-T4W-W

**FLUX DISTRIBUTION:**

|                    |           | Downward | Upward | Total   |
|--------------------|-----------|----------|--------|---------|
| <b>House Side</b>  | Lumens    | 5533.4   | 0.0    | 5533.4  |
|                    | % Fixture | 22.8     | 0.0    | 22.8    |
| <b>Street Side</b> | Lumens    | 18745.8  | 0.0    | 18745.8 |
|                    | % Fixture | 77.2     | 0.0    | 77.2    |
| <b>Total</b>       | Lumens    | 24279.2  | 0.0    | 24279.2 |
|                    | % Fixture | 100.0    | 0.0    | 100.0   |

**ZONAL LUMENS:**

| Zone      | Lumens  | % Fixture |
|-----------|---------|-----------|
| 0°-10°    | 246.0   | 1.0       |
| 10°-20°   | 819.5   | 3.4       |
| 20°-30°   | 1393.0  | 5.7       |
| 30°-40°   | 2040.5  | 8.4       |
| 40°-50°   | 3109.0  | 12.8      |
| 50°-60°   | 5562.7  | 22.9      |
| 60°-70°   | 7422.8  | 30.6      |
| 70°-80°   | 3356.8  | 13.8      |
| 80°-90°   | 328.9   | 1.4       |
| 90°-100°  | 0.0     | 0.0       |
| 100°-110° | 0.0     | 0.0       |
| 110°-120° | 0.0     | 0.0       |
| 120°-130° | 0.0     | 0.0       |
| 130°-140° | 0.0     | 0.0       |
| 140°-150° | 0.0     | 0.0       |
| 150°-160° | 0.0     | 0.0       |
| 160°-170° | 0.0     | 0.0       |
| 170°-180° | 0.0     | 0.0       |
| 0°-90°    | 24279.2 | 100.0     |
| 0°-180°   | 24279.2 | 100.0     |

**Coefficient of Utilization**



REPORT NUMBER: P637792


CATALOG NUMBER: GWS-SA4D-740-U-T4W-W

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

| Zone           | Lumens | % Fixture | Zone Rating/Lumen Limit |      |          |
|----------------|--------|-----------|-------------------------|------|----------|
|                |        |           | B                       | U    | G        |
| FL (0°-30°)    | 1324.1 | 5.5       |                         |      |          |
| FM (30°-60°)   | 8060.9 | 33.2      |                         |      |          |
| FH (60°-80°)   | 9165.1 | 37.7      |                         |      | G4/12000 |
| FVH (80°-90°)  | 195.6  | 0.8       |                         |      | G2/225   |
| BL (0°-30°)    | 1134.4 | 4.7       | B3/2500                 |      |          |
| BM (30°-60°)   | 2651.3 | 10.9      | B3/5000                 |      |          |
| BH (60°-80°)   | 1614.5 | 6.6       | B3/2500                 |      | G3/2500  |
| BVH (80°-90°)  | 133.2  | 0.5       |                         |      | G2/225   |
| UL (90°-100°)  | 0.0    | 0.0       |                         | U0/0 |          |
| UH (100°-180°) | 0.0    | 0.0       |                         | U0/0 |          |

**BUG Rating: B3-U0-G4**

Type III Short





REPORT NUMBER: P637792  
 CATALOG NUMBER: GWS-SA4D-740-U-T4W-W

**CANDELA DISTRIBUTION (FULL):**

|       | 0°      | 5°      | 15°     | 25°     | 35°     | 45°     | 47°     | 55°     | 65°     | 75°     | 85°     |
|-------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|
| 0°    | 2406.8  | 2406.8  | 2406.8  | 2406.8  | 2406.8  | 2406.8  | 2406.8  | 2406.8  | 2406.8  | 2406.8  | 2406.8  |
| 2.5°  | 2566.6  | 2575.4  | 2573.6  | 2559.6  | 2550.8  | 2535.0  | 2536.7  | 2512.2  | 2475.3  | 2450.7  | 2422.6  |
| 5°    | 2793.1  | 2807.1  | 2789.5  | 2766.7  | 2731.6  | 2680.7  | 2675.4  | 2619.3  | 2549.0  | 2499.9  | 2449.0  |
| 7.5°  | 2989.7  | 2998.5  | 2977.4  | 2938.8  | 2887.9  | 2819.4  | 2807.1  | 2740.4  | 2652.6  | 2575.4  | 2501.6  |
| 10°   | 3142.4  | 3152.9  | 3124.9  | 3073.9  | 3007.2  | 2938.8  | 2930.0  | 2861.5  | 2768.5  | 2677.2  | 2584.1  |
| 12.5° | 3272.3  | 3275.8  | 3246.0  | 3177.5  | 3105.5  | 3035.3  | 3026.5  | 2963.3  | 2877.3  | 2784.3  | 2682.5  |
| 15°   | 3347.8  | 3349.6  | 3312.7  | 3237.2  | 3168.7  | 3107.3  | 3102.0  | 3047.6  | 2968.6  | 2880.8  | 2772.0  |
| 17.5° | 3342.5  | 3346.0  | 3319.7  | 3253.0  | 3193.3  | 3156.5  | 3151.2  | 3116.1  | 3054.6  | 2975.6  | 2866.8  |
| 20°   | 3277.6  | 3281.1  | 3263.5  | 3219.6  | 3188.0  | 3177.5  | 3179.3  | 3168.7  | 3131.9  | 3066.9  | 2956.3  |
| 22.5° | 3226.7  | 3231.9  | 3216.1  | 3184.5  | 3181.0  | 3205.6  | 3210.9  | 3216.1  | 3198.6  | 3140.7  | 3033.6  |
| 25°   | 3251.2  | 3260.0  | 3235.4  | 3191.6  | 3198.6  | 3253.0  | 3263.5  | 3281.1  | 3267.0  | 3217.9  | 3124.9  |
| 27.5° | 3421.5  | 3426.8  | 3363.6  | 3274.1  | 3253.0  | 3310.9  | 3326.7  | 3354.8  | 3344.3  | 3298.6  | 3226.7  |
| 30°   | 3816.5  | 3813.0  | 3677.8  | 3458.4  | 3370.6  | 3393.4  | 3405.7  | 3446.1  | 3449.6  | 3419.8  | 3351.3  |
| 32.5° | 4373.0  | 4355.5  | 4146.6  | 3797.2  | 3542.7  | 3486.5  | 3500.5  | 3555.0  | 3595.3  | 3563.7  | 3470.7  |
| 35°   | 4961.1  | 4945.3  | 4715.4  | 4306.3  | 3860.4  | 3665.6  | 3649.8  | 3691.9  | 3753.3  | 3665.6  | 3532.1  |
| 37.5° | 5521.2  | 5496.6  | 5261.3  | 4755.7  | 4251.9  | 3979.8  | 3957.0  | 3914.8  | 3878.0  | 3709.4  | 3607.6  |
| 40°   | 6142.6  | 6114.5  | 5909.1  | 5336.8  | 4683.8  | 4220.3  | 4162.4  | 3995.6  | 3962.2  | 3855.2  | 3804.2  |
| 42.5° | 6806.2  | 6806.2  | 6635.9  | 6072.4  | 5205.2  | 4564.4  | 4488.9  | 4237.9  | 4273.0  | 4202.7  | 4143.1  |
| 45°   | 7469.8  | 7489.1  | 7353.9  | 6813.2  | 5902.1  | 5213.9  | 5092.8  | 4736.4  | 4820.7  | 4789.1  | 4759.3  |
| 47.5° | 8035.1  | 8071.9  | 8045.6  | 7569.9  | 6755.3  | 6003.9  | 5819.6  | 5449.2  | 5630.0  | 5705.5  | 5789.8  |
| 50°   | 8644.2  | 8684.6  | 8658.3  | 8470.5  | 7754.2  | 6960.7  | 6795.7  | 6413.0  | 6723.7  | 6950.2  | 7225.8  |
| 52.5° | 9548.3  | 9606.3  | 9386.8  | 9314.9  | 8967.3  | 8047.4  | 7899.9  | 7464.5  | 8028.1  | 8403.7  | 9018.2  |
| 55°   | 10312.0 | 10310.3 | 10233.0 | 10398.0 | 10269.9 | 9376.3  | 9213.0  | 8818.0  | 9537.8  | 9936.3  | 10835.2 |
| 57.5° | 10666.6 | 10708.8 | 10973.8 | 11440.8 | 11697.1 | 11000.2 | 10843.9 | 10440.2 | 11158.2 | 11365.3 | 12336.1 |
| 60°   | 10849.2 | 10901.9 | 11414.5 | 12337.9 | 13027.8 | 12773.3 | 12711.8 | 12197.5 | 12601.2 | 12576.6 | 13601.9 |
| 62.5° | 10592.9 | 10698.2 | 11521.6 | 12748.7 | 13977.6 | 14555.1 | 14535.8 | 13758.1 | 13828.3 | 13587.8 | 14386.6 |
| 65°   | 9416.7  | 9530.8  | 10822.9 | 12543.3 | 14520.0 | 15910.4 | 15915.7 | 15171.3 | 14771.1 | 14079.4 | 14254.9 |
| 67.5° | 6734.2  | 6897.5  | 8495.0  | 11223.1 | 14328.7 | 16642.5 | 16703.9 | 15812.1 | 14992.3 | 13644.0 | 12871.6 |
| 70°   | 3670.8  | 3790.2  | 5041.9  | 8158.0  | 12604.7 | 16466.9 | 16581.0 | 15503.1 | 14016.2 | 11802.5 | 9908.2  |
| 72.5° | 1667.8  | 1706.4  | 2345.4  | 4476.6  | 8610.9  | 14174.2 | 14651.7 | 13835.4 | 11511.0 | 8718.0  | 6300.6  |
| 75°   | 763.7   | 781.2   | 1021.7  | 2141.8  | 4499.4  | 9485.2  | 9820.5  | 10305.0 | 8010.5  | 5505.4  | 3284.6  |
| 77.5° | 479.3   | 484.5   | 581.1   | 979.6   | 2243.6  | 4734.7  | 5087.5  | 6135.6  | 4690.8  | 2724.6  | 1372.8  |
| 80°   | 282.6   | 287.9   | 361.6   | 530.2   | 1053.3  | 2166.3  | 2501.6  | 2426.1  | 2205.0  | 1176.2  | 625.0   |
| 82.5° | 142.2   | 147.5   | 208.9   | 302.0   | 574.1   | 862.0   | 1014.7  | 1020.0  | 821.6   | 637.3   | 352.9   |
| 85°   | 50.9    | 52.7    | 68.5    | 119.4   | 244.0   | 284.4   | 317.8   | 388.0   | 402.0   | 370.4   | 170.3   |
| 87.5° | 0.0     | 0.0     | 1.8     | 3.5     | 7.0     | 28.1    | 29.8    | 56.2    | 117.6   | 131.7   | 68.5    |
| 90°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |



REPORT NUMBER: P637792  
 CATALOG NUMBER: GWS-SA4D-740-U-T4W-W

**CANDELA DISTRIBUTION (continued):**

|       | 90°     | 95°     | 105°   | 115°   | 125°   | 135°   | 145°   | 155°   | 165°   | 175°   | 180°   |
|-------|---------|---------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°    | 2406.8  | 2406.8  | 2406.8 | 2406.8 | 2406.8 | 2406.8 | 2406.8 | 2406.8 | 2406.8 | 2406.8 | 2406.8 |
| 2.5°  | 2413.9  | 2387.5  | 2378.7 | 2370.0 | 2355.9 | 2350.7 | 2340.1 | 2329.6 | 2329.6 | 2319.1 | 2313.8 |
| 5°    | 2426.1  | 2391.0  | 2368.2 | 2357.7 | 2348.9 | 2354.2 | 2354.2 | 2357.7 | 2370.0 | 2362.9 | 2366.5 |
| 7.5°  | 2470.0  | 2429.7  | 2398.1 | 2389.3 | 2389.3 | 2410.3 | 2424.4 | 2441.9 | 2464.8 | 2468.3 | 2468.3 |
| 10°   | 2547.3  | 2499.9  | 2466.5 | 2461.3 | 2470.0 | 2499.9 | 2520.9 | 2542.0 | 2570.1 | 2571.9 | 2575.4 |
| 12.5° | 2631.5  | 2584.1  | 2550.8 | 2557.8 | 2566.6 | 2605.2 | 2628.0 | 2645.6 | 2673.7 | 2673.7 | 2671.9 |
| 15°   | 2719.3  | 2666.7  | 2638.6 | 2652.6 | 2678.9 | 2722.8 | 2726.3 | 2728.1 | 2742.1 | 2738.6 | 2736.9 |
| 17.5° | 2810.6  | 2754.4  | 2733.4 | 2754.4 | 2782.5 | 2803.6 | 2786.0 | 2761.5 | 2756.2 | 2749.2 | 2745.7 |
| 20°   | 2900.1  | 2842.2  | 2833.4 | 2849.2 | 2858.0 | 2840.5 | 2786.0 | 2740.4 | 2719.3 | 2708.8 | 2705.3 |
| 22.5° | 2977.4  | 2928.2  | 2923.0 | 2923.0 | 2879.1 | 2817.6 | 2736.9 | 2675.4 | 2647.3 | 2633.3 | 2629.8 |
| 25°   | 3068.7  | 3023.0  | 3014.3 | 2966.9 | 2854.5 | 2742.1 | 2633.3 | 2577.1 | 2554.3 | 2547.3 | 2549.0 |
| 27.5° | 3175.8  | 3144.2  | 3116.1 | 2980.9 | 2784.3 | 2608.7 | 2485.8 | 2461.3 | 2452.5 | 2461.3 | 2466.5 |
| 30°   | 3307.4  | 3275.8  | 3212.6 | 2963.3 | 2671.9 | 2434.9 | 2317.3 | 2315.5 | 2341.9 | 2364.7 | 2368.2 |
| 32.5° | 3414.5  | 3400.5  | 3296.9 | 2907.2 | 2513.9 | 2243.6 | 2143.5 | 2150.5 | 2197.9 | 2229.5 | 2234.8 |
| 35°   | 3498.8  | 3521.6  | 3367.1 | 2814.1 | 2326.1 | 2062.8 | 1983.8 | 1987.3 | 2013.6 | 2057.5 | 2059.2 |
| 37.5° | 3618.2  | 3695.4  | 3430.3 | 2671.9 | 2110.2 | 1906.5 | 1834.5 | 1808.2 | 1804.7 | 1817.0 | 1820.5 |
| 40°   | 3858.7  | 3974.5  | 3476.0 | 2464.8 | 1901.2 | 1766.1 | 1685.3 | 1634.4 | 1590.5 | 1557.2 | 1546.6 |
| 42.5° | 4222.1  | 4355.5  | 3502.3 | 2213.7 | 1715.2 | 1627.4 | 1536.1 | 1471.1 | 1393.9 | 1323.7 | 1299.1 |
| 45°   | 4889.2  | 4933.1  | 3502.3 | 1946.9 | 1550.1 | 1497.5 | 1406.2 | 1328.9 | 1230.6 | 1148.1 | 1130.6 |
| 47.5° | 5956.5  | 5816.1  | 3505.8 | 1688.8 | 1404.4 | 1383.4 | 1304.4 | 1216.6 | 1107.7 | 1039.3 | 1028.7 |
| 50°   | 7564.6  | 7071.3  | 3577.8 | 1474.6 | 1283.3 | 1286.8 | 1228.9 | 1132.3 | 1034.0 | 983.1  | 974.3  |
| 52.5° | 9386.8  | 8617.9  | 3770.9 | 1316.7 | 1181.5 | 1207.8 | 1176.2 | 1083.2 | 995.4  | 951.5  | 942.7  |
| 55°   | 11100.2 | 10039.9 | 3935.9 | 1204.3 | 1095.5 | 1141.1 | 1139.3 | 1053.3 | 974.3  | 930.4  | 925.2  |
| 57.5° | 12557.3 | 11014.2 | 3911.3 | 1113.0 | 1021.7 | 1079.7 | 1106.0 | 1034.0 | 960.3  | 923.4  | 918.1  |
| 60°   | 13463.2 | 11530.3 | 3562.0 | 1028.7 | 965.5  | 1035.8 | 1086.7 | 1028.7 | 967.3  | 958.5  | 960.3  |
| 62.5° | 13856.4 | 11435.5 | 2891.4 | 965.5  | 928.7  | 1014.7 | 1107.7 | 1065.6 | 1032.3 | 1053.3 | 1065.6 |
| 65°   | 13245.5 | 10621.0 | 2127.7 | 918.1  | 893.6  | 1020.0 | 1156.9 | 1123.5 | 1032.3 | 1046.3 | 1051.6 |
| 67.5° | 11549.7 | 9041.0  | 1537.8 | 870.7  | 849.7  | 1035.8 | 1227.1 | 1114.8 | 972.6  | 972.6  | 962.0  |
| 70°   | 8323.0  | 6502.5  | 1116.5 | 823.3  | 805.8  | 1012.9 | 1230.6 | 1055.1 | 904.1  | 898.8  | 872.5  |
| 72.5° | 5008.5  | 3835.8  | 870.7  | 770.7  | 739.1  | 898.8  | 1153.4 | 984.9  | 837.4  | 793.5  | 761.9  |
| 75°   | 2601.7  | 1922.3  | 730.3  | 712.7  | 633.7  | 761.9  | 1055.1 | 876.0  | 716.3  | 677.6  | 660.1  |
| 77.5° | 1114.8  | 898.8   | 626.7  | 635.5  | 526.7  | 640.8  | 851.4  | 758.4  | 635.5  | 586.3  | 570.5  |
| 80°   | 549.5   | 510.9   | 495.1  | 509.1  | 421.3  | 495.1  | 733.8  | 663.6  | 538.9  | 482.8  | 459.9  |
| 82.5° | 314.2   | 298.4   | 356.4  | 361.6  | 300.2  | 414.3  | 619.7  | 561.8  | 445.9  | 384.5  | 347.6  |
| 85°   | 145.7   | 156.2   | 215.9  | 217.7  | 186.1  | 284.4  | 405.5  | 316.0  | 237.0  | 196.6  | 187.8  |
| 87.5° | 57.9    | 68.5    | 94.8   | 93.0   | 54.4   | 52.7   | 35.1   | 19.3   | 15.8   | 14.0   | 12.3   |
| 90°   | 0.0     | 0.0     | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



LM-79-08: Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Report Prepared for

Cooper Lighting Solutions

MCGRAW, INVUE, LUMARK AND STREETWORKS

DATA VALID FOR LUMINAIRES UTILIZING SA LIGHT ENGINES

Report Number: SP1-2101-121-2

Luminaire Tested: IFLD-S-SA2A-740-U-T3R-HSS

Test Date: 03/05/2021

**Test Information**

Test Method: LM-79-08  
 Report Number: SP1-2101-121-2  
 Test Lab: COOPER LIGHTING SOLUTIONS  
 Photometer: SP1  
 Measurement Geometry: 4π  
 Issue Date: 03/05/2021  
 Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
 Product Line: STREETWORKS  
 Catalog Number: **IFLD-S-SA2A-740-U-T3R-HSS**  
 Description: STREETWORKS INF FLOOD

SHIELD, DRIVER PROGRAMMED @ 615mA.

**Spectral Parameters**

|                           |         |           |      |      |       |
|---------------------------|---------|-----------|------|------|-------|
| CCT (K):                  | 3905    | CRI (Ra): | 71.2 | R9:  | -29.7 |
| CIE u':                   | 0.2273  | R1:       | 68.9 | R10: | 46.2  |
| CIE v':                   | 0.5024  | R2:       | 77.0 | R11: | 68.8  |
| Duv:                      | -0.0008 | R3:       | 84.0 | R12: | 45.6  |
| CIE x:                    | 0.3841  | R4:       | 71.6 | R13: | 69.5  |
| CIE y:                    | 0.3774  | R5:       | 68.9 | R14: | 90.7  |
| CIE z:                    | 0.2385  | R6:       | 68.3 |      |       |
| Peak Wavelength (nm):     | 443     | R7:       | 78.7 |      |       |
| Dominant Wavelength (nm): | 579     | R8:       | 52.2 |      |       |
| Purity:                   | 28.7    |           |      |      |       |
| Rf:                       | 71.7    |           |      |      |       |
| Rg:                       | 96.9    |           |      |      |       |



**Test Conditions**

Stabilization Time: 211M  
 Operation Time: 12H  
 Room Temperature (°C) / RH%: 24.8/312%  
 Sphere Temperature (°C): 24.1

REPORT NUMBER: SP1-2101-121-2

| Measurement and Test Equipment |                       |                  |                      |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument                     | Identification Number | Calibration Date | Calibration Due Date |
| Photometer                     | IN0058                | 1/31/2021        | 7/31/2021            |
| Power Meter                    | IN0071                | 12/1/2020        | 12/1/2021            |
| AC Power Source                | IN0063                | 12/1/2020        | 12/1/2021            |
| DC Power Source                | IN0208                | 12/1/2020        | 12/1/2021            |
| Sphere Thermometer             | IN0085                | 12/1/2020        | 12/1/2021            |
| Room Thermometer               | IN0046                | 12/1/2020        | 12/1/2021            |

REPORT NUMBER: SP1-2101-121-2

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 4000K 4-step quadrangle

REPORT NUMBER: SP1-2101-121-2

**Photopic Flux vs. Wavelength**



#####

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360    | 2304          | 0.0           | 490    | 19043         | 2.7           | 620    | 97577         | 25.4          | 750    | 4830          | 0.0           | 880    | 3505          | 0.0           |
| 365    | 2150          | 0.0           | 495    | 26606         | 4.8           | 625    | 90158         | 19.9          | 755    | 4664          | 0.0           | 885    | 2991          | 0.0           |
| 370    | 2146          | 0.0           | 500    | 36376         | 8.0           | 630    | 82240         | 14.9          | 760    | 4006          | 0.0           | 890    | 2327          | 0.0           |
| 375    | 2332          | 0.0           | 505    | 47714         | 13.3          | 635    | 74361         | 11.2          | 765    | 3715          | 0.0           | 895    | 2775          | 0.0           |
| 380    | 2527          | 0.0           | 510    | 58741         | 20.2          | 640    | 66994         | 8.0           | 770    | 3696          | 0.0           | 900    | 2141          | 0.0           |
| 385    | 2304          | 0.0           | 515    | 68716         | 28.5          | 645    | 60405         | 5.8           | 775    | 3117          | 0.0           | 905    | 2421          | 0.0           |
| 390    | 2064          | 0.0           | 520    | 77136         | 37.4          | 650    | 53806         | 3.9           | 780    | 3062          | 0.0           | 910    | 2200          | 0.0           |
| 395    | 1856          | 0.0           | 525    | 83567         | 44.9          | 655    | 47610         | 2.7           | 785    | 2907          | 0.0           | 915    | 2716          | 0.0           |
| 400    | 1856          | 0.0           | 530    | 89283         | 52.6          | 660    | 42018         | 1.8           | 790    | 2655          | 0.0           | 920    | 2656          | 0.0           |
| 405    | 2374          | 0.0           | 535    | 94097         | 58.4          | 665    | 36742         | 1.2           | 795    | 2467          | 0.0           | 925    | 2671          | 0.0           |
| 410    | 4084          | 0.0           | 540    | 96845         | 63.1          | 670    | 32105         | 0.7           | 800    | 2609          | 0.0           | 930    | 3292          | 0.0           |
| 415    | 8543          | 0.0           | 545    | 100829        | 67.1          | 675    | 27946         | 0.5           | 805    | 2293          | 0.0           | 935    | 3188          | 0.0           |
| 420    | 18394         | 0.1           | 550    | 105648        | 71.8          | 680    | 24146         | 0.3           | 810    | 2188          | 0.0           | 940    | 1997          | 0.0           |
| 425    | 37987         | 0.2           | 555    | 110017        | 75.1          | 685    | 21191         | 0.2           | 815    | 2386          | 0.0           | 945    | 2623          | 0.0           |
| 430    | 67605         | 0.5           | 560    | 114586        | 77.9          | 690    | 18544         | 0.1           | 820    | 2712          | 0.0           | 950    | 2969          | 0.0           |
| 435    | 102160        | 1.2           | 565    | 118987        | 79.1          | 695    | 16058         | 0.1           | 825    | 2473          | 0.0           | 955    | 2277          | 0.0           |
| 440    | 135103        | 2.1           | 570    | 122326        | 79.5          | 700    | 14133         | 0.0           | 830    | 1969          | 0.0           | 960    | 4267          | 0.0           |
| 445    | 140126        | 2.9           | 575    | 125968        | 78.4          | 705    | 12309         | 0.0           | 835    | 1917          | 0.0           | 965    | 2034          | 0.0           |
| 450    | 102339        | 2.7           | 580    | 127613        | 75.8          | 710    | 11142         | 0.0           | 840    | 2248          | 0.0           | 970    | 3586          | 0.0           |
| 455    | 58751         | 2.0           | 585    | 129466        | 71.9          | 715    | 10143         | 0.0           | 845    | 2266          | 0.0           | 975    | 2505          | 0.0           |
| 460    | 36892         | 1.5           | 590    | 128813        | 66.6          | 720    | 9072          | 0.0           | 850    | 2558          | 0.0           | 980    | 2666          | 0.0           |
| 465    | 24637         | 1.3           | 595    | 126387        | 59.9          | 725    | 8130          | 0.0           | 855    | 2767          | 0.0           | 985    | 2934          | 0.0           |
| 470    | 16738         | 1.0           | 600    | 123477        | 53.2          | 730    | 7149          | 0.0           | 860    | 2826          | 0.0           | 990    | 4120          | 0.0           |
| 475    | 13456         | 1.1           | 605    | 118718        | 46.0          | 735    | 6311          | 0.0           | 865    | 2385          | 0.0           | 995    | 3858          | 0.0           |
| 480    | 13081         | 1.2           | 610    | 112091        | 38.5          | 740    | 5711          | 0.0           | 870    | 3194          | 0.0           | 1000   | 3405          | 0.0           |
| 485    | 14734         | 1.7           | 615    | 105039        | 31.7          | 745    | 5111          | 0.0           | 875    | 3189          | 0.0           |        |               |               |

REPORT NUMBER: SP1-2101-121-2

Scotopic Flux vs. Wavelength



Scotopic Lumens: 10425.8 S/P: 1.47

| λ (nm) | Power (µW/nm) | Lumens (Φ/nm) | λ (nm) | Power (µW/nm) | Lumens (Φ/nm) | λ (nm) | Power (µW/nm) | Lumens (Φ/nm) | λ (nm) | Power (µW/nm) | Lumens (Φ/nm) | λ (nm) | Power (µW/nm) | Lumens (Φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360    | 2304          | 0.0           | 490    | 19043         | 29.3          | 620    | 97577         | 1.2           | 750    | 4830          | 0.0           | 880    | 3505          | 0.0           |
| 365    | 2150          | 0.0           | 495    | 26606         | 43.0          | 625    | 90158         | 0.8           | 755    | 4664          | 0.0           | 885    | 2991          | 0.0           |
| 370    | 2146          | 0.0           | 500    | 36376         | 60.8          | 630    | 82240         | 0.5           | 760    | 4006          | 0.0           | 890    | 2327          | 0.0           |
| 375    | 2332          | 0.0           | 505    | 47714         | 81.1          | 635    | 74361         | 0.3           | 765    | 3715          | 0.0           | 895    | 2775          | 0.0           |
| 380    | 2527          | 0.0           | 510    | 58741         | 99.6          | 640    | 66994         | 0.2           | 770    | 3696          | 0.0           | 900    | 2141          | 0.0           |
| 385    | 2304          | 0.0           | 515    | 68716         | 113.9         | 645    | 60405         | 0.1           | 775    | 3117          | 0.0           | 905    | 2421          | 0.0           |
| 390    | 2064          | 0.0           | 520    | 77136         | 122.6         | 650    | 53806         | 0.1           | 780    | 3062          | 0.0           | 910    | 2200          | 0.0           |
| 395    | 1856          | 0.0           | 525    | 83567         | 125.0         | 655    | 47610         | 0.0           | 785    | 2907          | 0.0           | 915    | 2716          | 0.0           |
| 400    | 1856          | 0.0           | 530    | 89283         | 123.1         | 660    | 42018         | 0.0           | 790    | 2655          | 0.0           | 920    | 2656          | 0.0           |
| 405    | 2374          | 0.1           | 535    | 94097         | 117.3         | 665    | 36742         | 0.0           | 795    | 2467          | 0.0           | 925    | 2671          | 0.0           |
| 410    | 4084          | 0.2           | 540    | 96845         | 107.0         | 670    | 32105         | 0.0           | 800    | 2609          | 0.0           | 930    | 3292          | 0.0           |
| 415    | 8543          | 0.9           | 545    | 100829        | 96.7          | 675    | 27946         | 0.0           | 805    | 2293          | 0.0           | 935    | 3188          | 0.0           |
| 420    | 18394         | 3.0           | 550    | 105648        | 86.4          | 680    | 24146         | 0.0           | 810    | 2188          | 0.0           | 940    | 1997          | 0.0           |
| 425    | 37987         | 9.3           | 555    | 110017        | 75.2          | 685    | 21191         | 0.0           | 815    | 2386          | 0.0           | 945    | 2623          | 0.0           |
| 430    | 67605         | 23.0          | 560    | 114586        | 64.0          | 690    | 18544         | 0.0           | 820    | 2712          | 0.0           | 950    | 2969          | 0.0           |
| 435    | 102160        | 45.7          | 565    | 118987        | 53.4          | 695    | 16058         | 0.0           | 825    | 2473          | 0.0           | 955    | 2277          | 0.0           |
| 440    | 135103        | 75.5          | 570    | 122326        | 43.2          | 700    | 14133         | 0.0           | 830    | 1969          | 0.0           | 960    | 4267          | 0.0           |
| 445    | 140126        | 93.8          | 575    | 125968        | 34.3          | 705    | 12309         | 0.0           | 835    | 1917          | 0.0           | 965    | 2034          | 0.0           |
| 450    | 102339        | 79.3          | 580    | 127613        | 26.3          | 710    | 11142         | 0.0           | 840    | 2248          | 0.0           | 970    | 3586          | 0.0           |
| 455    | 58751         | 51.3          | 585    | 129466        | 19.8          | 715    | 10143         | 0.0           | 845    | 2266          | 0.0           | 975    | 2505          | 0.0           |
| 460    | 36892         | 35.6          | 590    | 128813        | 14.3          | 720    | 9072          | 0.0           | 850    | 2558          | 0.0           | 980    | 2666          | 0.0           |
| 465    | 24637         | 26.0          | 595    | 126387        | 10.1          | 725    | 8130          | 0.0           | 855    | 2767          | 0.0           | 985    | 2934          | 0.0           |
| 470    | 16738         | 19.3          | 600    | 123477        | 7.0           | 730    | 7149          | 0.0           | 860    | 2826          | 0.0           | 990    | 4120          | 0.0           |
| 475    | 13456         | 16.8          | 605    | 118718        | 4.7           | 735    | 6311          | 0.0           | 865    | 2385          | 0.0           | 995    | 3858          | 0.0           |
| 480    | 13081         | 17.7          | 610    | 112091        | 3.0           | 740    | 5711          | 0.0           | 870    | 3194          | 0.0           | 1000   | 3405          | 0.0           |
| 485    | 14734         | 21.4          | 615    | 105039        | 1.9           | 745    | 5111          | 0.0           | 875    | 3189          | 0.0           |        |               |               |

REPORT NUMBER: SP1-2101-121-2

**Melanopic Flux vs. Wavelength**



**Melanopic Lumens: 3927.2 M/P: 0.55**

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360    | 2304          | 0.0           | 490    | 19043         | 15.8          | 620    | 97577         | 0.1           | 750    | 4830          | 0.0           | 880    | 3505          | 0.0           |
| 365    | 2150          | 0.0           | 495    | 26606         | 22.0          | 625    | 90158         | 0.0           | 755    | 4664          | 0.0           | 885    | 2991          | 0.0           |
| 370    | 2146          | 0.0           | 500    | 36376         | 29.2          | 630    | 82240         | 0.0           | 760    | 4006          | 0.0           | 890    | 2327          | 0.0           |
| 375    | 2332          | 0.0           | 505    | 47714         | 36.6          | 635    | 74361         | 0.0           | 765    | 3715          | 0.0           | 895    | 2775          | 0.0           |
| 380    | 2527          | 0.0           | 510    | 58741         | 42.2          | 640    | 66994         | 0.0           | 770    | 3696          | 0.0           | 900    | 2141          | 0.0           |
| 385    | 2304          | 0.0           | 515    | 68716         | 44.9          | 645    | 60405         | 0.0           | 775    | 3117          | 0.0           | 905    | 2421          | 0.0           |
| 390    | 2064          | 0.0           | 520    | 77136         | 44.9          | 650    | 53806         | 0.0           | 780    | 3062          | 0.0           | 910    | 2200          | 0.0           |
| 395    | 1856          | 0.0           | 525    | 83567         | 42.4          | 655    | 47610         | 0.0           | 785    | 2907          | 0.0           | 915    | 2716          | 0.0           |
| 400    | 1856          | 0.0           | 530    | 89283         | 38.6          | 660    | 42018         | 0.0           | 790    | 2655          | 0.0           | 920    | 2656          | 0.0           |
| 405    | 2374          | 0.0           | 535    | 94097         | 33.9          | 665    | 36742         | 0.0           | 795    | 2467          | 0.0           | 925    | 2671          | 0.0           |
| 410    | 4084          | 0.2           | 540    | 96845         | 28.3          | 670    | 32105         | 0.0           | 800    | 2609          | 0.0           | 930    | 3292          | 0.0           |
| 415    | 8543          | 0.6           | 545    | 100829        | 23.4          | 675    | 27946         | 0.0           | 805    | 2293          | 0.0           | 935    | 3188          | 0.0           |
| 420    | 18394         | 2.1           | 550    | 105648        | 19.0          | 680    | 24146         | 0.0           | 810    | 2188          | 0.0           | 940    | 1997          | 0.0           |
| 425    | 37987         | 5.9           | 555    | 110017        | 14.8          | 685    | 21191         | 0.0           | 815    | 2386          | 0.0           | 945    | 2623          | 0.0           |
| 430    | 67605         | 14.3          | 560    | 114586        | 11.3          | 690    | 18544         | 0.0           | 820    | 2712          | 0.0           | 950    | 2969          | 0.0           |
| 435    | 102160        | 27.3          | 565    | 118987        | 8.4           | 695    | 16058         | 0.0           | 825    | 2473          | 0.0           | 955    | 2277          | 0.0           |
| 440    | 135103        | 45.1          | 570    | 122326        | 6.0           | 700    | 14133         | 0.0           | 830    | 1969          | 0.0           | 960    | 4267          | 0.0           |
| 445    | 140126        | 55.3          | 575    | 125968        | 4.2           | 705    | 12309         | 0.0           | 835    | 1917          | 0.0           | 965    | 2034          | 0.0           |
| 450    | 102339        | 47.2          | 580    | 127613        | 2.9           | 710    | 11142         | 0.0           | 840    | 2248          | 0.0           | 970    | 3586          | 0.0           |
| 455    | 58751         | 30.8          | 585    | 129466        | 1.9           | 715    | 10143         | 0.0           | 845    | 2266          | 0.0           | 975    | 2505          | 0.0           |
| 460    | 36892         | 21.7          | 590    | 128813        | 1.3           | 720    | 9072          | 0.0           | 850    | 2558          | 0.0           | 980    | 2666          | 0.0           |
| 465    | 24637         | 16.1          | 595    | 126387        | 0.8           | 725    | 8130          | 0.0           | 855    | 2767          | 0.0           | 985    | 2934          | 0.0           |
| 470    | 16738         | 12.0          | 600    | 123477        | 0.5           | 730    | 7149          | 0.0           | 860    | 2826          | 0.0           | 990    | 4120          | 0.0           |
| 475    | 13456         | 10.3          | 605    | 118718        | 0.3           | 735    | 6311          | 0.0           | 865    | 2385          | 0.0           | 995    | 3858          | 0.0           |
| 480    | 13081         | 10.5          | 610    | 112091        | 0.2           | 740    | 5711          | 0.0           | 870    | 3194          | 0.0           | 1000   | 3405          | 0.0           |
| 485    | 14734         | 12.1          | 615    | 105039        | 0.1           | 745    | 5111          | 0.0           | 875    | 3189          | 0.0           |        |               |               |

**Summary**

$R_f = 71.7$   
 $R_g = 96.9$   
 CIE  $R_a = 71.2$   
 $R_g = -29.7$



**Color Vector Graphics**





**Individual Sample Fidelity Index ( $R_{f,i}$ )**


|            |            |            |            |
|------------|------------|------------|------------|
| CES01 = 85 | CES26 = 55 | CES51 = 86 | CES76 = 45 |
| CES02 = 61 | CES27 = 80 | CES52 = 87 | CES77 = 68 |
| CES03 = 30 | CES28 = 79 | CES53 = 74 | CES78 = 49 |
| CES04 = 70 | CES29 = 51 | CES54 = 81 | CES79 = 77 |
| CES05 = 47 | CES30 = 60 | CES55 = 80 | CES80 = 75 |
| CES06 = 50 | CES31 = 56 | CES56 = 69 | CES81 = 75 |
| CES07 = 40 | CES32 = 52 | CES57 = 67 | CES82 = 90 |
| CES08 = 39 | CES33 = 62 | CES58 = 69 | CES83 = 85 |
| CES09 = 29 | CES34 = 65 | CES59 = 86 | CES84 = 87 |
| CES10 = 74 | CES35 = 81 | CES60 = 91 | CES85 = 83 |
| CES11 = 57 | CES36 = 92 | CES61 = 85 | CES86 = 72 |
| CES12 = 63 | CES37 = 74 | CES62 = 81 | CES87 = 77 |
| CES13 = 42 | CES38 = 69 | CES63 = 72 | CES88 = 77 |
| CES14 = 74 | CES39 = 92 | CES64 = 69 | CES89 = 72 |
| CES15 = 71 | CES40 = 86 | CES65 = 64 | CES90 = 75 |
| CES16 = 46 | CES41 = 84 | CES66 = 63 | CES91 = 91 |
| CES17 = 49 | CES42 = 75 | CES67 = 60 | CES92 = 66 |
| CES18 = 56 | CES43 = 70 | CES68 = 67 | CES93 = 80 |
| CES19 = 72 | CES44 = 98 | CES69 = 77 | CES94 = 56 |
| CES20 = 65 | CES45 = 80 | CES70 = 57 | CES95 = 72 |
| CES21 = 86 | CES46 = 77 | CES71 = 53 | CES96 = 78 |
| CES22 = 78 | CES47 = 74 | CES72 = 84 | CES97 = 83 |
| CES23 = 92 | CES48 = 66 | CES73 = 47 | CES98 = 73 |
| CES24 = 91 | CES49 = 76 | CES74 = 96 | CES99 = 63 |
| CES25 = 72 | CES50 = 85 | CES75 = 52 |            |



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)