

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: McGRAW-EDISON

Report Number: P635839

Luminaire Tested: GWS-SA3E-750-U-SLL-W-GRSBK

Issue Date: 1/10/2023

Test Information

Test Method: LM-79-2019
Report Number: P635839
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2209-782-38)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/10/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: McGRAW-EDISON
Catalog Number: GWS-SA3E-750-U-SLL-W-GRSBK
Description: GALLEON WALL SLIM LUMINAIRE. (3) LIGHTSQUARES WITH 16 LEDS EACH AND SPILL LIGHT ELIMINATOR LEFT OPTICS W/ FACTORY INSTALLED GLARE SHIELD, BK
Light Source: (48) 5000K CCT, 70 CRI LEDS
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 12062.5 lumens
Efficiency: N/A
Efficacy: 75.8 lumens/watt
Luminous Opening: Rectangular (W 1.5' x L: 0.5' x H: 0')
IES Classification: Type III - Short
BUG Rating: B2 - U0 - G2


Input Watts (W): 159.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 0
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT



REPORT NUMBER: P635839
 CATALOG NUMBER: GWS-SA3E-750-U-SLL-W-GRSBK

Iso-Footcandle Lines of Horizontal Illumination


× Max cd
 - - - 1/2 Max cd



Based on 20 foot mounting height. Maximum calculated value = 8 fc
 Type III - Short - N/A

REPORT NUMBER: P635839
CATALOG NUMBER: GWS-SA3E-750-U-SLL-W-GRSBK

Luminous Intensity Polar Plot



— Vertical Plane Through 315-Deg Lateral - - - Horizontal Cone Through 57.5-Deg Vertical

REPORT NUMBER: P635839

CATALOG NUMBER: GWS-SA3E-750-U-SLL-W-GRSBK

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	2598.7	0.0	2598.7
	% Fixture	21.5	0.0	21.5
Street Side	Lumens	9463.8	0.0	9463.8
	% Fixture	78.5	0.0	78.5
Total	Lumens	12062.5	0.0	12062.5
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	202.6	1.7
10°-20°	666.6	5.5
20°-30°	1081.8	9.0
30°-40°	1660.3	13.8
40°-50°	2651.6	22.0
50°-60°	3712.7	30.8
60°-70°	1903.6	15.8
70°-80°	183.3	1.5
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	12062.5	100.0
0°-180°	12062.5	100.0

Coefficient of Utilization




REPORT NUMBER: P635839
 CATALOG NUMBER: GWS-SA3E-750-U-SLL-W-GRSBK

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	1194.3	9.9			
FM (30°-60°)	6378.9	52.9			
FH (60°-80°)	1890.6	15.7			G2/5000
FVH (80°-90°)	0.0	0.0			G0/10
BL (0°-30°)	756.7	6.3	B2/1000		
BM (30°-60°)	1645.7	13.6	B2/2500		
BH (60°-80°)	196.3	1.6	B1/500		G1/500
BVH (80°-90°)	0.0	0.0			G0/10
UL (90°-100°)	0.0	0.0		U0/0	
UH (100°-180°)	0.0	0.0		U0/0	

BUG Rating: B2-U0-G2
 Type III Short





REPORT NUMBER: P635839

CATALOG NUMBER: GWS-SA3E-750-U-SLL-W-GRSBK

CANDELA DISTRIBUTION (FULL):

	0°	1°	5°	15°	25°	35°	45°	55°	65°	75°	85°
0°	2049.6	2049.6	2049.6	2049.6	2049.6	2049.6	2049.6	2049.6	2049.6	2049.6	2049.6
2.5°	2277.0	2272.1	2256.0	2201.2	2167.3	2114.1	2075.4	2025.4	1970.6	1936.7	1902.9
5°	2518.9	2506.0	2462.4	2336.6	2239.9	2135.1	2051.2	1959.3	1860.9	1796.4	1736.8
7.5°	2751.1	2731.7	2673.7	2460.8	2314.1	2164.1	2044.8	1910.9	1772.2	1675.5	1601.3
10°	2978.4	2934.9	2843.0	2581.8	2383.4	2202.8	2062.5	1909.3	1746.4	1623.9	1541.6
12.5°	3165.5	3133.3	3007.5	2696.2	2441.5	2210.9	2038.3	1896.4	1786.7	1704.5	1628.7
15°	3326.8	3291.3	3172.0	2799.5	2491.4	2178.6	1936.7	1812.5	1830.3	1862.5	1798.0
17.5°	3475.1	3438.0	3309.0	2884.9	2510.8	2099.6	1794.8	1735.1	1833.5	1954.5	1930.3
20°	3628.3	3586.4	3428.4	2954.3	2504.3	1975.4	1651.3	1669.0	1807.7	1946.4	1959.3
22.5°	3807.3	3763.8	3579.9	3043.0	2499.5	1827.1	1527.1	1611.0	1759.3	1877.1	1899.6
25°	4044.4	3992.8	3791.2	3173.6	2512.4	1691.6	1438.4	1554.5	1677.1	1783.5	1796.4
27.5°	4357.2	4291.1	4034.7	3334.8	2539.8	1585.2	1399.7	1477.1	1572.3	1667.4	1678.7
30°	4765.2	4681.3	4313.7	3475.1	2526.9	1511.0	1373.9	1399.7	1456.2	1533.6	1535.2
32.5°	5242.5	5128.0	4626.5	3596.1	2415.7	1456.2	1338.4	1320.7	1333.6	1393.3	1404.6
35°	5803.7	5655.3	4971.6	3710.6	2212.5	1349.7	1273.9	1214.3	1209.4	1238.5	1265.9
37.5°	6447.1	6269.7	5407.0	3857.3	1972.2	1238.5	1178.8	1119.1	1093.3	1107.8	1149.8
40°	7040.6	6843.8	5861.8	4034.7	1727.1	1138.5	1067.5	1006.3	975.6	980.5	1032.1
42.5°	7737.2	7534.0	6418.1	4266.9	1523.9	1070.8	951.4	888.5	848.2	870.8	930.5
45°	8795.0	8564.4	7229.2	4468.5	1362.6	1054.6	849.8	761.1	741.8	780.5	851.4
47.5°	10239.9	9957.7	8343.5	4591.0	1225.6	1069.1	778.9	657.9	662.8	706.3	777.3
50°	11673.5	11368.7	9632.0	4429.8	1112.7	1040.1	743.4	577.3	607.9	646.6	711.2
52.5°	12658.8	12262.1	10259.3	3963.7	1009.5	930.5	740.2	501.5	559.6	572.5	627.3
55°	12697.5	12208.9	9938.4	3125.2	869.2	785.3	706.3	438.6	506.4	511.2	558.0
57.5°	11130.1	10688.2	8685.4	2146.4	772.4	575.7	562.8	383.8	416.0	456.4	485.4
60°	8467.7	8092.0	6495.5	983.7	587.0	366.1	385.4	330.6	311.2	370.9	399.9
62.5°	5186.1	4945.8	3896.0	435.4	374.1	195.1	233.8	262.9	233.8	256.4	280.6
65°	2059.3	1952.8	1478.7	185.4	153.2	98.4	106.4	153.2	164.5	180.6	203.2
67.5°	358.0	338.6	248.3	82.2	62.9	59.7	51.6	71.0	100.0	111.3	129.0
70°	46.8	45.2	40.3	33.9	32.3	29.0	22.6	45.2	67.7	71.0	82.2
72.5°	11.3	9.7	9.7	8.1	9.7	3.2	3.2	24.2	48.4	50.0	58.1
75°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	8.1	30.6	33.9	40.3
77.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	1.6
80°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P635839

CATALOG NUMBER: GWS-SA3E-750-U-SLL-W-GRSBK

CANDELA DISTRIBUTION (continued):

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	2049.6	2049.6	2049.6	2049.6	2049.6	2049.6	2049.6	2049.6	2049.6	2049.6	2049.6
2.5°	1875.4	1843.2	1831.9	1815.8	1794.8	1801.3	1772.2	1762.6	1777.1	1796.4	1791.6
5°	1704.5	1669.0	1644.8	1607.7	1601.3	1586.8	1577.1	1564.2	1580.3	1602.9	1607.7
7.5°	1569.0	1538.4	1514.2	1502.9	1494.9	1488.4	1469.1	1459.4	1459.4	1469.1	1477.1
10°	1511.0	1488.4	1483.6	1486.8	1499.7	1498.1	1480.4	1467.5	1451.3	1443.3	1452.9
12.5°	1591.6	1554.5	1548.1	1549.7	1565.8	1564.2	1544.9	1528.7	1525.5	1528.7	1559.4
15°	1728.7	1672.3	1630.3	1622.3	1630.3	1627.1	1612.6	1602.9	1607.7	1654.5	1706.1
17.5°	1851.2	1764.2	1688.4	1659.4	1657.7	1652.9	1638.4	1635.2	1659.4	1746.4	1822.2
20°	1886.7	1801.3	1693.2	1656.1	1648.1	1643.2	1627.1	1631.9	1662.6	1767.4	1831.9
22.5°	1840.0	1757.7	1644.8	1607.7	1601.3	1599.7	1583.6	1590.0	1615.8	1707.7	1760.9
25°	1751.3	1681.9	1564.2	1532.0	1532.0	1528.7	1514.2	1517.4	1533.6	1614.2	1665.8
27.5°	1643.2	1577.1	1478.7	1446.5	1451.3	1456.2	1438.4	1433.6	1446.5	1522.3	1552.9
30°	1519.1	1472.3	1394.9	1365.9	1364.2	1383.6	1359.4	1353.0	1370.7	1430.4	1436.8
32.5°	1398.1	1375.5	1320.7	1298.1	1299.7	1303.0	1290.1	1290.1	1306.2	1338.4	1336.8
35°	1280.4	1265.9	1256.2	1240.1	1238.5	1232.0	1232.0	1235.2	1253.0	1264.3	1243.3
37.5°	1167.5	1182.0	1193.3	1177.2	1164.3	1164.3	1164.3	1178.8	1194.9	1190.1	1154.6
40°	1067.5	1098.2	1133.6	1115.9	1085.3	1083.7	1090.1	1114.3	1138.5	1109.5	1077.2
42.5°	982.1	1020.8	1070.8	1061.1	1027.2	1022.4	1027.2	1057.9	1077.2	1040.1	1004.6
45°	898.2	946.6	1006.3	1006.3	969.2	964.3	965.9	1006.3	1017.5	974.0	928.8
47.5°	827.3	880.5	943.4	943.4	912.7	903.0	911.1	953.0	961.1	899.8	857.9
50°	759.5	817.6	886.9	882.1	861.1	853.1	867.6	912.7	903.0	835.3	791.8
52.5°	674.1	735.3	830.5	835.3	824.0	825.6	843.4	872.4	845.0	762.8	725.7
55°	596.7	659.5	754.7	780.5	780.5	778.9	786.9	809.5	786.9	688.6	643.4
57.5°	512.8	566.0	645.0	651.5	656.3	638.6	649.9	680.5	669.2	585.4	559.6
60°	420.9	466.0	511.2	516.0	495.1	458.0	478.9	514.4	522.5	459.6	430.6
62.5°	298.3	341.9	395.1	395.1	374.1	337.0	364.4	395.1	383.8	319.3	301.6
65°	222.5	262.9	303.2	320.9	303.2	277.4	298.3	320.9	303.2	250.0	224.1
67.5°	143.5	170.9	195.1	209.6	212.9	209.6	219.3	212.9	191.9	156.4	141.9
70°	87.1	101.6	114.5	127.4	137.1	141.9	146.7	132.2	111.3	91.9	87.1
72.5°	62.9	75.8	87.1	96.8	108.0	111.3	111.3	101.6	82.2	64.5	59.7
75°	43.5	54.8	64.5	71.0	80.6	83.9	83.9	75.8	61.3	46.8	41.9
77.5°	1.6	11.3	11.3	9.7	12.9	16.1	16.1	19.4	17.7	12.9	11.3
80°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P635839

CATALOG NUMBER: GWS-SA3E-750-U-SLL-W-GRSBK

CANDELA DISTRIBUTION (continued):

	185°	195°	205°	215°	225°	235°	245°	255°	265°	270°	275°
0°	2049.6	2049.6	2049.6	2049.6	2049.6	2049.6	2049.6	2049.6	2049.6	2049.6	2049.6
2.5°	1801.3	1859.3	1875.4	1935.1	1988.3	2041.5	2106.0	2144.7	2202.8	2243.1	2265.7
5°	1623.9	1672.3	1730.3	1819.0	1910.9	2012.5	2135.1	2241.5	2375.3	2473.7	2506.0
7.5°	1494.9	1557.8	1625.5	1736.8	1862.5	1998.0	2170.5	2344.7	2549.5	2683.3	2768.8
10°	1470.7	1535.2	1625.5	1735.1	1867.4	2022.2	2233.4	2459.2	2715.6	2878.5	2975.2
12.5°	1586.8	1656.1	1694.8	1744.8	1844.8	2017.3	2288.3	2575.3	2876.9	3054.2	3157.4
15°	1757.7	1819.0	1756.1	1693.2	1757.7	1965.7	2318.9	2672.1	3018.8	3223.6	3330.0
17.5°	1875.4	1880.3	1743.2	1609.4	1627.1	1872.2	2330.2	2768.8	3170.3	3384.8	3496.1
20°	1864.2	1825.4	1686.8	1538.4	1483.6	1751.3	2317.3	2854.3	3323.5	3547.7	3657.3
22.5°	1777.1	1731.9	1614.2	1469.1	1362.6	1607.7	2294.7	2931.7	3463.8	3718.6	3821.8
25°	1672.3	1623.9	1527.1	1399.7	1285.2	1469.1	2277.0	3038.1	3641.2	3941.2	4021.8
27.5°	1549.7	1507.8	1425.5	1333.6	1253.0	1364.2	2272.1	3178.4	3855.7	4212.1	4268.5
30°	1430.4	1391.7	1327.2	1273.9	1240.1	1303.0	2256.0	3328.4	4112.1	4523.3	4584.6
32.5°	1315.9	1277.2	1236.9	1228.8	1230.4	1280.4	2201.2	3476.7	4416.9	4974.8	5020.0
35°	1217.5	1172.4	1156.2	1175.6	1211.1	1241.7	2046.4	3599.3	4744.2	5466.7	5503.8
37.5°	1124.0	1078.8	1077.2	1124.0	1162.7	1182.0	1864.2	3720.2	5186.1	5966.6	6013.3
40°	1038.5	993.4	1009.5	1065.9	1096.6	1106.2	1643.2	3904.1	5653.7	6493.9	6468.1
42.5°	965.9	919.2	928.8	1001.4	1028.8	1054.6	1440.0	4057.3	6103.6	6993.8	6985.7
45°	895.0	859.5	853.1	932.1	956.3	1059.5	1291.7	4175.0	6682.6	7630.8	7643.7
47.5°	825.6	798.2	799.8	833.7	893.4	1083.7	1165.9	4252.4	7522.7	8640.2	8416.1
50°	762.8	741.8	759.5	720.8	853.1	1053.0	1057.9	4236.3	8461.2	9607.8	9157.9
52.5°	693.4	688.6	696.6	603.1	788.6	928.8	956.3	4021.8	8901.5	10269.0	10012.5
55°	622.5	620.8	556.3	482.2	659.5	741.8	819.2	3355.8	8887.0	10620.5	10931.7
57.5°	538.6	525.7	422.5	393.5	512.8	516.0	746.6	2198.0	7875.9	9778.7	10423.8
60°	408.0	398.3	309.6	319.3	358.0	330.6	595.0	1094.9	5885.9	7617.9	8345.1
62.5°	282.2	269.3	230.6	246.7	230.6	188.7	364.4	541.8	3565.4	4810.3	5469.9
65°	206.4	191.9	158.0	135.5	108.0	108.0	138.7	208.0	1380.4	2044.8	2465.6
67.5°	127.4	120.9	93.5	67.7	66.1	71.0	72.6	103.2	222.5	354.8	433.8
70°	82.2	75.8	62.9	43.5	40.3	41.9	43.5	48.4	56.4	61.3	74.2
72.5°	56.4	53.2	45.2	24.2	19.4	21.0	22.6	22.6	27.4	25.8	30.6
75°	40.3	37.1	32.3	11.3	6.5	8.1	9.7	8.1	9.7	6.5	8.1
77.5°	11.3	11.3	8.1	1.6	0.0	1.6	3.2	3.2	1.6	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0	0.0	1.6	1.6	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P635839

CATALOG NUMBER: GWS-SA3E-750-U-SLL-W-GRSBK

CANDELA DISTRIBUTION (continued):

	285°	295°	305°	315°	325°	335°	345°	355°	359°	360°
0°	2049.6	2049.6	2049.6	2049.6	2049.6	2049.6	2049.6	2049.6	2049.6	2049.6
2.5°	2323.7	2360.8	2375.3	2354.4	2372.1	2343.1	2331.8	2288.3	2285.0	2277.0
5°	2636.6	2720.4	2770.4	2801.1	2765.6	2726.9	2668.8	2568.9	2538.2	2518.9
7.5°	2944.6	3075.2	3160.7	3201.0	3191.3	3112.3	3007.5	2839.8	2780.1	2751.1
10°	3212.3	3371.9	3475.1	3525.1	3504.2	3434.8	3284.8	3075.2	2996.2	2978.4
12.5°	3399.3	3546.1	3617.0	3660.6	3662.2	3634.8	3492.9	3281.6	3188.1	3165.5
15°	3517.1	3579.9	3581.6	3607.4	3652.5	3713.8	3647.7	3460.6	3360.6	3326.8
17.5°	3591.2	3521.9	3450.9	3457.4	3531.6	3694.4	3762.2	3618.6	3512.2	3475.1
20°	3644.4	3425.1	3292.9	3294.5	3370.3	3617.0	3841.2	3771.8	3662.2	3628.3
22.5°	3678.3	3339.7	3151.0	3146.2	3226.8	3525.1	3913.7	3954.1	3846.0	3807.3
25°	3747.7	3299.4	3065.5	3092.9	3163.9	3496.1	4012.1	4196.0	4096.0	4044.4
27.5°	3871.8	3339.7	3057.5	3120.4	3201.0	3581.6	4183.0	4518.5	4415.3	4357.2
30°	4086.3	3491.2	3181.6	3268.7	3365.5	3805.7	4470.1	4968.4	4820.0	4765.2
32.5°	4431.4	3805.7	3565.4	3752.5	3846.0	4173.4	4900.7	5473.1	5352.2	5242.5
35°	4907.1	4523.3	4495.9	4931.3	4908.7	4870.0	5429.6	6092.4	5910.1	5803.7
37.5°	5561.8	5677.9	5881.1	6313.3	6298.8	6003.7	6124.6	6677.7	6584.2	6447.1
40°	6379.4	6626.1	6971.2	7590.4	7396.9	7026.0	6977.7	7277.6	7201.8	7040.6
42.5°	6861.6	7287.3	7945.2	8501.6	8346.7	7698.5	7643.7	8079.1	7913.0	7737.2
45°	7085.7	7825.9	9116.0	9869.0	9399.8	8145.2	8124.2	9124.0	9030.5	8795.0
47.5°	7188.9	8369.3	10486.7	11626.7	10749.5	8537.0	8461.2	10639.8	10517.3	10239.9
50°	7303.4	9119.2	12137.9	13663.4	12379.8	8980.5	9035.3	12052.5	12000.9	11673.5
52.5°	7555.0	9912.6	14171.4	15992.0	14356.9	9675.5	10020.6	13384.5	13036.1	12658.8
55°	7932.3	10776.9	16287.1	18370.6	16374.2	10609.2	11086.5	14092.4	13115.2	12697.5
57.5°	7514.7	10993.0	17540.1	20031.5	17269.2	10612.4	10185.1	12865.2	11534.8	11130.1
60°	5963.3	10227.0	17057.9	19671.9	16506.4	9424.0	7798.5	10044.8	8738.6	8467.7
62.5°	4031.5	8577.3	15016.4	16637.1	14127.9	7413.1	5068.4	6532.6	5410.2	5186.1
65°	2209.2	6398.7	12133.1	12586.2	11057.5	5178.0	2607.6	2834.9	2159.3	2059.3
67.5°	609.6	4454.0	8927.3	8350.0	7758.2	3371.9	674.1	506.4	361.2	358.0
70°	153.2	2946.2	5348.9	5513.4	4757.1	2159.3	129.0	61.3	48.4	46.8
72.5°	64.5	1267.5	2538.2	2917.2	2435.0	999.8	46.8	17.7	14.5	11.3
75°	8.1	101.6	216.1	327.4	224.1	108.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)