

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: McGRAW-EDISON

Report Number: P635843

Luminaire Tested: GWS-SA3E-750-U-SLR-W-GRSBK

Issue Date: 1/10/2023

Test Information

Test Method: LM-79-2019
Report Number: P635843
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2209-782-42)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/10/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: McGRAW-EDISON
Catalog Number: GWS-SA3E-750-U-SLR-W-GRSBK
Description: GALLEON WALL SLIM LUMINAIRE. (3) LIGHTSQUARES WITH 16 LEDS EACH AND SPILL LIGHT ELIMINATOR RIGHT OPTICS W/ FACTORY INSTALLED GLARE SHIELD, BK
Light Source: (48) 5000K CCT, 70 CRI LEDS
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 12001.2 lumens
Efficiency: N/A
Efficacy: 75.4 lumens/watt
Luminous Opening: Rectangular (W 1.5' x L: 0.5' x H: 0')
IES Classification: Type III - Short
BUG Rating: B2 - U0 - G1


Input Watts (W): 159.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 0
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT



REPORT NUMBER: P635843
 CATALOG NUMBER: GWS-SA3E-750-U-SLR-W-GRSBK

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 20 foot mounting height. Maximum calculated value = 9.4 fc
 Type III - Short - N/A

REPORT NUMBER: P635843
CATALOG NUMBER: GWS-SA3E-750-U-SLR-W-GRSBK

Luminous Intensity Polar Plot



— Vertical Plane Through 45-Deg Lateral - - - Horizontal Cone Through 57.5-Deg Vertical

REPORT NUMBER: P635843

CATALOG NUMBER: GWS-SA3E-750-U-SLR-W-GRSBK

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	2687.4	0.0	2687.4
	% Fixture	22.4	0.0	22.4
Street Side	Lumens	9313.8	0.0	9313.8
	% Fixture	77.6	0.0	77.6
Total	Lumens	12001.2	0.0	12001.2
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	207.5	1.7
10°-20°	671.3	5.6
20°-30°	1090.5	9.1
30°-40°	1684.9	14.0
40°-50°	2701.8	22.5
50°-60°	3692.6	30.8
60°-70°	1788.4	14.9
70°-80°	163.8	1.4
80°-90°	0.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	12001.2	100.0
0°-180°	12001.2	100.0

Coefficient of Utilization



REPORT NUMBER: P635843


CATALOG NUMBER: GWS-SA3E-750-U-SLR-W-GRSBK

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	1174.1	9.8			
FM (30°-60°)	6388.5	53.2			
FH (60°-80°)	1750.8	14.6			G1/1800
FVH (80°-90°)	0.5	0.0			G0/10
BL (0°-30°)	795.2	6.6	B2/1000		
BM (30°-60°)	1690.8	14.1	B2/2500		
BH (60°-80°)	201.4	1.7	B1/500		G1/500
BVH (80°-90°)	0.0	0.0			G0/10
UL (90°-100°)	0.0	0.0		U0/0	
UH (100°-180°)	0.0	0.0		U0/0	

BUG Rating: B2-U0-G1

Type III Short





REPORT NUMBER: P635843

CATALOG NUMBER: GWS-SA3E-750-U-SLR-W-GRSBK

CANDELA DISTRIBUTION (FULL):

	0°	1°	5°	15°	25°	35°	45°	55°	65°	75°	85°
0°	2109.3	2109.3	2109.3	2109.3	2109.3	2109.3	2109.3	2109.3	2109.3	2109.3	2109.3
2.5°	2285.1	2299.6	2323.8	2375.4	2419.0	2448.0	2460.9	2457.7	2439.9	2427.0	2401.2
5°	2530.2	2530.2	2577.0	2694.7	2785.0	2841.5	2870.5	2852.8	2817.3	2760.8	2673.8
7.5°	2744.7	2752.8	2831.8	2999.5	3136.6	3217.2	3264.0	3254.3	3191.4	3083.4	2909.2
10°	2912.4	2922.1	3026.9	3231.7	3393.0	3475.3	3544.6	3551.0	3481.7	3338.2	3138.2
12.5°	3075.3	3085.0	3194.6	3391.4	3533.3	3567.2	3628.5	3652.6	3634.9	3533.3	3325.3
15°	3251.1	3273.7	3367.2	3514.0	3573.6	3533.3	3573.6	3617.2	3676.8	3667.2	3480.1
17.5°	3423.6	3439.8	3534.9	3586.5	3520.4	3415.6	3434.9	3486.5	3622.0	3754.2	3633.3
20°	3583.3	3605.9	3684.9	3617.2	3417.2	3254.3	3255.9	3323.7	3530.1	3807.5	3789.7
22.5°	3751.0	3784.9	3841.3	3651.0	3322.0	3126.9	3135.0	3196.3	3457.5	3857.4	3967.1
25°	3970.3	4002.6	4039.7	3734.9	3291.4	3064.0	3094.7	3151.1	3457.5	3942.9	4186.4
27.5°	4267.1	4289.6	4291.2	3891.3	3344.6	3073.7	3138.2	3202.7	3560.7	4113.9	4479.9
30°	4639.6	4675.1	4628.3	4134.8	3510.7	3202.7	3297.9	3378.5	3783.3	4402.5	4912.1
32.5°	5092.7	5142.7	5079.8	4496.1	3857.4	3647.8	3820.4	3867.1	4138.0	4820.2	5402.4
35°	5624.9	5666.8	5599.1	4996.0	4667.0	4705.7	5018.6	4958.9	4850.8	5334.6	5974.8
37.5°	6208.7	6247.4	6116.8	5753.9	5863.6	6031.3	6531.2	6326.4	5978.1	5997.4	6595.7
40°	6744.1	6786.0	6581.2	6578.0	6803.7	7110.2	7713.3	7431.1	6957.0	6865.0	7177.9
42.5°	7298.8	7327.9	7142.4	7016.6	7529.4	8160.0	8798.6	8418.0	7605.2	7505.3	7906.8
45°	8090.6	8151.9	7821.3	7232.7	8182.6	9367.9	10258.0	9514.6	8047.1	7966.5	9022.7
47.5°	9255.0	9300.1	8626.0	7368.2	8790.5	10872.5	12081.9	10937.0	8435.7	8251.9	10548.3
50°	10217.7	10248.4	9366.2	7516.5	9437.2	12494.8	14160.6	12623.8	8872.8	8724.4	11972.3
52.5°	10927.3	11043.4	10338.7	7821.3	10287.1	14402.5	16461.9	14621.9	9554.9	9637.2	13152.7
55°	11074.0	11232.1	11003.1	8008.4	11035.3	16345.8	18587.3	16410.3	10235.5	10329.0	13549.4
57.5°	9732.3	9858.1	10048.4	7253.7	11017.6	17236.0	19821.0	17003.7	9925.8	9263.0	12064.2
60°	7290.8	7377.9	7723.0	5544.3	10132.2	16449.0	18859.9	15994.2	8679.3	7068.2	9192.1
62.5°	4323.5	4362.2	4799.2	3591.4	8409.9	14165.5	15641.0	13801.0	6858.6	4754.1	5629.7
65°	1659.4	1643.3	1977.1	1772.3	6184.5	11283.7	11633.6	10520.9	4705.7	2178.7	2146.4
67.5°	256.4	245.1	330.6	524.1	4460.6	7819.7	7676.2	7582.7	2947.9	508.0	443.5
70°	58.1	58.1	71.0	154.8	2725.4	4594.4	4917.0	4688.0	1886.8	108.0	58.1
72.5°	27.4	27.4	33.9	66.1	986.9	1893.2	2206.1	2172.2	612.8	35.5	21.0
75°	9.7	11.3	11.3	14.5	59.7	98.4	225.8	161.3	38.7	0.0	0.0
77.5°	3.2	3.2	3.2	3.2	0.0	0.0	0.0	0.0	0.0	0.0	0.0
80°	1.6	1.6	1.6	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
82.5°	1.6	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P635843

CATALOG NUMBER: GWS-SA3E-750-U-SLR-W-GRSBK

CANDELA DISTRIBUTION (continued):

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	2109.3	2109.3	2109.3	2109.3	2109.3	2109.3	2109.3	2109.3	2109.3	2109.3	2109.3
2.5°	2344.8	2333.5	2291.6	2235.1	2180.3	2131.9	2081.9	2022.3	1978.7	1928.7	1912.6
5°	2606.0	2535.1	2420.6	2301.2	2191.6	2098.1	2007.7	1911.0	1840.0	1769.1	1744.9
7.5°	2827.0	2722.1	2536.7	2357.7	2207.7	2075.5	1944.8	1812.6	1709.4	1625.5	1599.7
10°	3025.3	2904.4	2656.0	2435.1	2246.4	2093.2	1935.2	1769.1	1635.2	1535.2	1511.0
12.5°	3196.3	3056.0	2757.6	2493.1	2262.5	2086.8	1933.6	1801.3	1680.4	1565.9	1535.2
15°	3339.8	3185.0	2843.1	2531.9	2238.4	2006.1	1872.3	1851.3	1841.6	1715.9	1656.2
17.5°	3480.1	3305.9	2912.4	2549.6	2170.6	1864.2	1767.5	1862.6	1964.2	1882.0	1806.2
20°	3626.8	3428.5	2983.4	2552.8	2057.7	1704.6	1688.4	1838.4	1967.4	1941.6	1870.7
22.5°	3799.4	3581.7	3072.1	2551.2	1915.8	1569.1	1630.4	1791.6	1896.5	1894.9	1838.4
25°	4049.4	3775.2	3191.4	2560.9	1761.0	1464.3	1565.9	1712.6	1798.1	1794.9	1748.1
27.5°	4317.1	4005.8	3346.2	2585.1	1628.8	1403.0	1490.1	1604.6	1678.8	1675.5	1635.2
30°	4692.8	4271.9	3494.6	2586.7	1533.6	1370.7	1406.2	1485.2	1556.2	1548.1	1517.5
32.5°	5149.2	4571.8	3618.8	2494.8	1474.0	1340.1	1319.1	1359.5	1414.3	1403.0	1394.9
35°	5700.7	4928.2	3725.2	2293.2	1382.0	1278.8	1222.4	1230.4	1269.2	1275.6	1272.4
37.5°	6329.6	5352.4	3857.4	2027.1	1257.9	1190.1	1114.3	1107.9	1130.5	1151.4	1167.6
40°	6950.5	5829.7	4036.5	1757.8	1145.0	1077.2	1004.7	988.6	998.2	1035.3	1069.2
42.5°	7648.8	6382.8	4230.0	1527.2	1067.6	953.1	883.7	853.1	880.5	940.2	980.5
45°	8655.1	7158.5	4418.6	1343.3	1035.3	843.4	749.9	746.7	777.3	854.7	899.9
47.5°	10067.7	8161.6	4542.8	1199.8	1033.7	757.9	646.7	666.0	701.5	777.3	828.9
50°	11444.9	9417.8	4405.7	1090.1	999.8	701.5	569.3	608.0	643.4	709.6	762.8
52.5°	12275.5	10093.5	3872.0	986.9	895.0	675.7	493.5	561.2	567.7	627.3	683.8
55°	12188.4	9656.5	2965.7	827.3	740.2	638.6	414.4	506.4	509.6	554.7	603.1
57.5°	10579.0	8290.6	2036.8	670.9	556.4	527.3	341.9	427.4	458.0	485.4	520.9
60°	7884.2	6049.0	907.9	545.1	353.2	356.4	291.9	322.5	369.3	401.5	432.2
62.5°	4646.0	3480.1	369.3	327.4	195.1	224.2	235.4	235.4	264.5	288.7	308.0
65°	1756.2	1217.5	150.0	164.5	101.6	104.8	138.7	170.9	193.5	214.5	240.3
67.5°	308.0	212.9	77.4	61.3	59.7	53.2	71.0	111.3	124.2	140.3	151.6
70°	51.6	43.5	32.3	30.6	27.4	29.0	46.8	79.0	87.1	91.9	96.8
72.5°	14.5	12.9	9.7	8.1	6.5	8.1	29.0	61.3	64.5	67.7	72.6
75°	0.0	0.0	0.0	0.0	0.0	0.0	11.3	43.5	46.8	48.4	53.2
77.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	9.7	12.9	16.1	12.9
80°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P635843

CATALOG NUMBER: GWS-SA3E-750-U-SLR-W-GRSBK

CANDELA DISTRIBUTION (continued):

	185°	195°	205°	215°	225°	235°	245°	255°	265°	270°	275°
0°	2109.3	2109.3	2109.3	2109.3	2109.3	2109.3	2109.3	2109.3	2109.3	2109.3	2109.3
2.5°	1902.9	1870.7	1852.9	1843.3	1843.3	1830.4	1815.8	1811.0	1832.0	1832.0	1867.4
5°	1714.2	1688.4	1659.4	1641.7	1614.3	1619.1	1603.0	1601.4	1622.3	1632.0	1669.1
7.5°	1583.6	1551.4	1533.6	1522.3	1507.8	1501.4	1486.9	1482.0	1493.3	1509.4	1544.9
10°	1496.5	1491.7	1490.1	1498.1	1498.1	1490.1	1477.2	1469.1	1472.3	1503.0	1543.3
12.5°	1519.1	1528.8	1532.0	1544.9	1551.4	1544.9	1535.2	1538.5	1559.4	1615.9	1675.5
15°	1617.5	1609.4	1606.2	1612.6	1617.5	1611.0	1607.8	1632.0	1704.6	1785.2	1852.9
17.5°	1722.3	1670.7	1648.1	1648.1	1651.3	1648.1	1651.3	1698.1	1815.8	1896.5	1946.5
20°	1775.5	1680.4	1644.9	1636.8	1643.3	1644.9	1656.2	1709.4	1838.4	1894.9	1906.1
22.5°	1759.4	1640.1	1599.7	1593.3	1599.7	1606.2	1617.5	1662.6	1783.6	1812.6	1807.8
25°	1678.8	1561.0	1528.8	1528.8	1543.3	1541.7	1546.5	1578.8	1678.8	1696.5	1688.4
27.5°	1577.2	1465.9	1438.5	1454.6	1467.5	1464.3	1465.9	1493.3	1567.5	1572.3	1564.3
30°	1474.0	1377.2	1351.4	1370.7	1388.5	1385.3	1386.9	1414.3	1461.1	1456.2	1444.9
32.5°	1369.1	1298.2	1278.8	1290.1	1317.5	1314.3	1320.8	1349.8	1367.5	1346.6	1333.7
35°	1272.4	1235.3	1220.8	1227.2	1248.2	1253.0	1264.3	1283.7	1283.7	1257.9	1235.3
37.5°	1182.1	1177.2	1167.6	1159.5	1178.8	1193.4	1209.5	1232.1	1199.8	1162.7	1141.8
40°	1098.2	1119.2	1106.3	1085.3	1096.6	1117.6	1149.8	1167.6	1128.9	1091.8	1056.3
42.5°	1020.8	1056.3	1051.4	1025.6	1035.3	1054.7	1091.8	1106.3	1061.1	1019.2	985.3
45°	946.6	996.6	999.8	967.6	977.3	996.6	1040.2	1045.0	986.9	941.8	917.6
47.5°	882.1	936.9	938.6	914.4	917.6	945.0	985.3	986.9	920.8	878.9	848.3
50°	820.8	883.7	888.6	867.6	870.8	903.1	936.9	930.5	859.5	816.0	788.6
52.5°	746.7	832.1	843.4	833.7	846.6	872.4	893.4	870.8	788.6	745.0	720.9
55°	666.0	777.3	801.5	795.0	809.5	830.5	835.4	820.8	717.6	674.1	651.5
57.5°	572.5	640.2	682.1	669.2	680.5	701.5	716.0	704.7	627.3	593.5	574.1
60°	474.1	519.3	528.9	508.0	498.3	535.4	569.3	554.7	488.6	467.7	445.1
62.5°	346.7	398.3	404.8	377.4	366.1	406.4	435.4	420.9	348.3	325.8	308.0
65°	277.4	325.8	338.7	312.9	306.4	337.0	354.8	319.3	267.7	243.5	224.2
67.5°	182.2	220.9	254.8	253.2	240.3	250.0	237.1	208.0	170.9	158.0	145.1
70°	112.9	135.5	156.4	164.5	162.9	159.7	141.9	120.9	109.7	104.8	98.4
72.5°	87.1	109.7	125.8	130.6	132.2	127.4	112.9	93.5	82.2	75.8	71.0
75°	64.5	82.2	95.1	101.6	104.8	101.6	87.1	74.2	62.9	58.1	53.2
77.5°	22.6	27.4	33.9	37.1	35.5	33.9	30.6	30.6	24.2	22.6	19.4
80°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P635843
 CATALOG NUMBER: GWS-SA3E-750-U-SLR-W-GRSBK

CANDELA DISTRIBUTION (continued):

	285°	295°	305°	315°	325°	335°	345°	355°	359°	360°
0°	2109.3	2109.3	2109.3	2109.3	2109.3	2109.3	2109.3	2109.3	2109.3	2109.3
2.5°	1907.8	1936.8	1990.0	2038.4	2090.0	2143.2	2201.3	2260.9	2288.3	2285.1
5°	1725.5	1788.4	1875.5	1970.7	2077.1	2191.6	2319.0	2449.6	2506.1	2530.2
7.5°	1611.0	1699.7	1814.2	1935.2	2075.5	2238.4	2430.3	2635.1	2717.3	2744.7
10°	1625.5	1728.8	1823.9	1941.6	2091.6	2302.9	2541.5	2785.0	2881.8	2912.4
12.5°	1743.3	1765.8	1791.6	1888.4	2077.1	2351.2	2643.1	2933.4	3044.7	3075.3
15°	1849.7	1744.9	1696.5	1785.2	2025.5	2385.1	2746.3	3093.1	3215.6	3251.1
17.5°	1854.5	1696.5	1588.5	1657.8	1941.6	2399.6	2847.9	3255.9	3389.8	3423.6
20°	1794.9	1643.3	1504.6	1506.2	1827.1	2396.4	2931.8	3402.7	3552.7	3583.3
22.5°	1707.8	1580.4	1436.9	1386.9	1704.6	2389.9	3023.7	3559.1	3722.0	3751.0
25°	1611.0	1499.8	1372.4	1296.6	1582.0	2396.4	3152.7	3763.9	3942.9	3970.3
27.5°	1506.2	1411.1	1322.4	1261.1	1478.8	2420.6	3307.5	4025.2	4238.0	4267.1
30°	1396.6	1325.6	1290.1	1253.0	1414.3	2427.0	3475.3	4330.0	4599.3	4639.6
32.5°	1288.5	1249.8	1251.4	1257.9	1353.0	2381.9	3628.5	4668.6	5028.2	5092.7
35°	1188.5	1177.2	1209.5	1241.7	1264.3	2265.8	3762.3	5068.5	5558.8	5624.9
37.5°	1103.0	1112.7	1153.0	1185.3	1167.6	2101.3	3939.7	5568.5	6152.2	6208.7
40°	1020.8	1045.0	1091.8	1106.3	1093.4	1909.4	4152.6	6050.6	6666.7	6744.1
42.5°	945.0	962.7	1028.9	1032.1	1072.4	1714.2	4357.4	6569.9	7258.5	7298.8
45°	883.7	880.5	948.2	969.2	1099.8	1498.1	4557.3	7261.7	8032.6	8090.6
47.5°	824.1	820.8	837.0	932.1	1111.1	1298.2	4755.7	8274.5	9155.0	9255.0
50°	767.6	772.5	722.5	914.4	1049.8	1145.0	4846.0	9211.4	10175.8	10217.7
52.5°	717.6	699.9	612.8	856.3	919.2	999.8	4589.6	9637.2	10807.9	10927.3
55°	646.7	548.3	504.8	695.1	725.7	872.4	3759.1	9390.4	10862.8	11074.0
57.5°	553.1	430.6	429.0	512.8	512.8	809.5	2407.7	8022.9	9361.4	9732.3
60°	425.7	333.8	354.8	356.4	329.0	590.2	1351.4	5812.0	6921.5	7290.8
62.5°	303.2	254.8	267.7	212.9	188.7	295.1	648.3	3346.2	4271.9	4323.5
65°	203.2	172.6	140.3	117.7	116.1	125.8	267.7	1209.5	1470.7	1659.4
67.5°	133.8	104.8	74.2	74.2	83.9	83.9	101.6	200.0	280.6	256.4
70°	87.1	72.6	46.8	45.2	54.8	54.8	51.6	54.8	58.1	58.1
72.5°	64.5	54.8	27.4	24.2	30.6	32.3	29.0	27.4	27.4	27.4
75°	48.4	38.7	16.1	11.3	14.5	19.4	16.1	11.3	11.3	9.7
77.5°	19.4	14.5	6.5	4.8	8.1	11.3	9.7	4.8	3.2	3.2
80°	1.6	3.2	3.2	3.2	4.8	6.5	8.1	3.2	1.6	1.6
82.5°	0.0	1.6	1.6	1.6	3.2	4.8	6.5	3.2	1.6	1.6
85°	0.0	0.0	0.0	0.0	3.2	4.8	3.2	1.6	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	1.6	4.8	3.2	1.6	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)