

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: McGRAW-EDISON

Report Number: P640779

Luminaire Tested: GWS-SA5E-750-U-SL2-W-GRSBK

Issue Date: 1/10/2023

Test Information

Test Method: LM-79-2019
Report Number: P640779
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2209-782-28)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/10/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: McGRAW-EDISON
Catalog Number: GWS-SA5E-750-U-SL2-W-GRSBK
Description: GALLEON WALL SLIM LUMINAIRE. (5) LIGHTSQUARES WITH 16 LEDS EACH AND TYPE II SPILL LIGHT ELIMINATOR OPTICS W/ FACTORY INSTALLED GLARE SHIELD, BK
Light Source: (80) 5000K CCT, 70 CRI LEDS
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 22548.6 lumens
Efficiency: N/A
Efficacy: 83.6 lumens/watt
Luminous Opening: Rectangular (W 1.5' x L: 1' x H: 0')
IES Classification: Type II - Short
BUG Rating: B3 - U0 - G2


Input Watts (W): 269.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 0
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT



REPORT NUMBER: P640779
 CATALOG NUMBER: GWS-SA5E-750-U-SL2-W-GRSBK

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 12.7 fc
 Type II - Short - N/A

REPORT NUMBER: P640779
CATALOG NUMBER: GWS-SA5E-750-U-SL2-W-GRSBK

Luminous Intensity Polar Plot



— Vertical Plane Through 50-Deg Lateral - - - Horizontal Cone Through 55-Deg Vertical

REPORT NUMBER: P640779
 CATALOG NUMBER: GWS-SA5E-750-U-SL2-W-GRSBK


FLUX DISTRIBUTION:

| | | Downward | Upward | Total |
|--------------------|-----------|----------|--------|---------|
| House Side | Lumens | 4443.1 | 0.0 | 4443.1 |
| | % Fixture | 19.7 | 0.0 | 19.7 |
| Street Side | Lumens | 18105.5 | 0.0 | 18105.5 |
| | % Fixture | 80.3 | 0.0 | 80.3 |
| Total | Lumens | 22548.6 | 0.0 | 22548.6 |
| | % Fixture | 100.0 | 0.0 | 100.0 |

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|---------|-----------|
| 0°-10° | 694.8 | 3.1 |
| 10°-20° | 1709.7 | 7.6 |
| 20°-30° | 2411.6 | 10.7 |
| 30°-40° | 3568.7 | 15.8 |
| 40°-50° | 5148.5 | 22.8 |
| 50°-60° | 6073.1 | 26.9 |
| 60°-70° | 2709.1 | 12.0 |
| 70°-80° | 232.9 | 1.0 |
| 80°-90° | 0.1 | 0.0 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-90° | 22548.6 | 100.0 |
| 0°-180° | 22548.6 | 100.0 |

Coefficient of Utilization




REPORT NUMBER: P640779

CATALOG NUMBER: GWS-SA5E-750-U-SL2-W-GRSBK

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

| Zone | Lumens | % Fixture | Zone Rating/Lumen Limit | | |
|----------------|---------|-----------|-------------------------|------|---------|
| | | | B | U | G |
| FL (0°-30°) | 2911.1 | 12.9 | | | |
| FM (30°-60°) | 12653.5 | 56.1 | | | |
| FH (60°-80°) | 2540.8 | 11.3 | | | G2/5000 |
| FVH (80°-90°) | 0.0 | 0.0 | | | G0/10 |
| BL (0°-30°) | 1905.0 | 8.4 | B3/2500 | | |
| BM (30°-60°) | 2136.8 | 9.5 | B2/2500 | | |
| BH (60°-80°) | 401.2 | 1.8 | B1/500 | | G1/500 |
| BVH (80°-90°) | 0.1 | 0.0 | | | G0/10 |
| UL (90°-100°) | 0.0 | 0.0 | | U0/0 | |
| UH (100°-180°) | 0.0 | 0.0 | | U0/0 | |

BUG Rating: B3-U0-G2
 Type II Short





REPORT NUMBER: P640779

CATALOG NUMBER: GWS-SA5E-750-U-SL2-W-GRSBK

CANDELA DISTRIBUTION (FULL):

| | 0° | 5° | 15° | 25° | 35° | 45° | 50° | 55° | 65° | 75° | 85° |
|-------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|
| 0° | 7911.3 | 7911.3 | 7911.3 | 7911.3 | 7911.3 | 7911.3 | 7911.3 | 7911.3 | 7911.3 | 7911.3 | 7911.3 |
| 2.5° | 7349.7 | 7355.3 | 7358.0 | 7432.3 | 7459.9 | 7570.0 | 7627.8 | 7658.1 | 7737.9 | 7831.5 | 7908.5 |
| 5° | 6857.0 | 6848.8 | 6862.5 | 6956.1 | 7016.7 | 7179.1 | 7267.2 | 7327.7 | 7503.9 | 7724.1 | 7908.5 |
| 7.5° | 6427.6 | 6444.1 | 6460.6 | 6562.5 | 6653.3 | 6829.5 | 6956.1 | 7047.0 | 7291.9 | 7619.5 | 7930.6 |
| 10° | 6124.8 | 6124.8 | 6149.6 | 6265.2 | 6372.5 | 6590.0 | 6716.6 | 6832.2 | 7124.0 | 7525.9 | 7955.3 |
| 12.5° | 5901.8 | 5904.6 | 5934.9 | 6067.0 | 6190.9 | 6416.6 | 6548.7 | 6661.6 | 6983.6 | 7432.3 | 7960.9 |
| 15° | 5797.2 | 5789.0 | 5813.7 | 5954.1 | 6091.8 | 6303.7 | 6441.4 | 6551.5 | 6884.5 | 7380.0 | 7988.4 |
| 17.5° | 5769.7 | 5764.2 | 5783.5 | 5921.1 | 6061.5 | 6267.9 | 6402.8 | 6512.9 | 6870.8 | 7396.5 | 8071.0 |
| 20° | 5849.5 | 5838.5 | 5830.3 | 5948.6 | 6080.7 | 6284.4 | 6424.8 | 6548.7 | 6936.8 | 7487.4 | 8197.6 |
| 22.5° | 6039.5 | 6039.5 | 6020.2 | 6078.0 | 6166.1 | 6350.5 | 6496.4 | 6658.8 | 7110.3 | 7669.1 | 8384.8 |
| 25° | 6389.1 | 6361.5 | 6325.7 | 6350.5 | 6339.5 | 6455.1 | 6628.5 | 6854.3 | 7437.8 | 7969.1 | 8613.2 |
| 27.5° | 6788.2 | 6813.0 | 6752.4 | 6755.2 | 6658.8 | 6617.5 | 6818.5 | 7159.8 | 7925.1 | 8393.0 | 8951.8 |
| 30° | 7330.5 | 7311.2 | 7314.0 | 7305.7 | 7082.7 | 6887.3 | 7104.8 | 7559.0 | 8538.9 | 9039.9 | 9392.3 |
| 32.5° | 7754.4 | 7781.9 | 7872.8 | 7925.1 | 7633.3 | 7319.5 | 7550.7 | 8101.2 | 9238.1 | 9777.6 | 9931.8 |
| 35° | 8203.1 | 8252.6 | 8437.1 | 8607.7 | 8362.7 | 8002.1 | 8249.9 | 8819.7 | 9896.0 | 10507.1 | 10551.2 |
| 37.5° | 8676.6 | 8775.7 | 8995.9 | 9295.9 | 9257.4 | 8938.1 | 9163.8 | 9664.8 | 10413.5 | 10947.5 | 11063.2 |
| 40° | 9218.8 | 9315.2 | 9675.8 | 10108.0 | 10198.8 | 10127.2 | 10201.6 | 10493.3 | 10754.9 | 10966.8 | 11283.4 |
| 42.5° | 9813.4 | 9945.6 | 10402.5 | 10980.6 | 11321.9 | 11385.2 | 11211.8 | 11181.5 | 10903.5 | 10746.6 | 11236.6 |
| 45° | 10515.4 | 10669.5 | 11187.0 | 11935.8 | 12478.1 | 12563.4 | 12263.3 | 11875.2 | 10997.1 | 10584.2 | 11096.2 |
| 47.5° | 11302.6 | 11448.5 | 11963.3 | 12863.4 | 13670.0 | 13703.0 | 13180.0 | 12555.1 | 11275.1 | 10771.4 | 11203.5 |
| 50° | 11566.9 | 11657.7 | 12103.7 | 13160.7 | 14647.2 | 14900.4 | 14143.4 | 13320.4 | 11833.9 | 11321.9 | 11726.6 |
| 52.5° | 10658.5 | 10694.3 | 11082.4 | 12150.5 | 14449.0 | 16075.9 | 15550.1 | 14462.8 | 12827.7 | 12161.5 | 12533.1 |
| 55° | 8445.3 | 8387.5 | 8701.3 | 9681.3 | 12557.9 | 15836.4 | 16824.6 | 16257.5 | 14107.7 | 13147.0 | 13581.9 |
| 57.5° | 5907.3 | 5838.5 | 5766.9 | 6430.3 | 9370.2 | 13425.0 | 15503.3 | 16508.0 | 15327.1 | 14124.2 | 14713.3 |
| 60° | 4855.8 | 4789.7 | 4442.9 | 4137.3 | 5665.1 | 9640.0 | 11908.2 | 13799.4 | 15228.0 | 14074.6 | 14677.5 |
| 62.5° | 4195.1 | 4156.6 | 4016.2 | 3600.6 | 3333.5 | 5502.7 | 7457.1 | 9268.4 | 11685.3 | 11052.2 | 11085.2 |
| 65° | 3295.0 | 3284.0 | 3380.3 | 3424.4 | 2948.2 | 3044.5 | 3804.3 | 4817.3 | 6317.5 | 5956.9 | 5648.6 |
| 67.5° | 2251.7 | 2226.9 | 2408.6 | 2961.9 | 2835.3 | 2403.1 | 2226.9 | 2246.2 | 2733.4 | 1670.9 | 1326.8 |
| 70° | 1431.4 | 1373.6 | 1376.4 | 1836.1 | 2306.8 | 1896.6 | 1717.7 | 1511.2 | 1359.8 | 247.7 | 280.8 |
| 72.5° | 916.7 | 880.9 | 757.0 | 828.6 | 1068.1 | 924.9 | 933.2 | 803.8 | 536.8 | 132.1 | 154.2 |
| 75° | 385.4 | 355.1 | 272.5 | 217.5 | 214.7 | 134.9 | 118.4 | 110.1 | 74.3 | 74.3 | 79.8 |
| 77.5° | 2.8 | 0.0 | 0.0 | 2.8 | 5.5 | 2.8 | 2.8 | 5.5 | 11.0 | 16.5 | 19.3 |
| 80° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 2.8 |
| 82.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 85° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 87.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P640779

CATALOG NUMBER: GWS-SA5E-750-U-SL2-W-GRSBK

CANDELA DISTRIBUTION (continued):

| | 90° | 95° | 105° | 115° | 125° | 135° | 145° | 155° | 165° | 175° | 180° |
|-------|---------|---------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 7911.3 | 7911.3 | 7911.3 | 7911.3 | 7911.3 | 7911.3 | 7911.3 | 7911.3 | 7911.3 | 7911.3 | 7911.3 |
| 2.5° | 7955.3 | 7889.3 | 7963.6 | 7991.1 | 7988.4 | 7991.1 | 7911.3 | 7856.2 | 7853.5 | 7784.7 | 7751.6 |
| 5° | 7985.6 | 7933.3 | 7988.4 | 7952.6 | 7867.3 | 7759.9 | 7616.8 | 7492.9 | 7437.8 | 7358.0 | 7319.5 |
| 7.5° | 8043.4 | 7988.4 | 7980.1 | 7837.0 | 7625.0 | 7399.3 | 7146.0 | 6920.3 | 6799.2 | 6653.3 | 6661.6 |
| 10° | 8084.7 | 8021.4 | 7914.1 | 7622.3 | 7269.9 | 6909.3 | 6532.2 | 6196.4 | 5984.4 | 5789.0 | 5755.9 |
| 12.5° | 8101.2 | 8007.6 | 7757.2 | 7316.7 | 6821.2 | 6350.5 | 5797.2 | 5318.2 | 4987.9 | 4731.9 | 4696.1 |
| 15° | 8131.5 | 7980.1 | 7556.2 | 6947.9 | 6267.9 | 5601.8 | 4897.1 | 4241.9 | 3804.3 | 3509.7 | 3534.5 |
| 17.5° | 8178.3 | 7949.8 | 7330.5 | 6534.9 | 5673.3 | 4731.9 | 3779.5 | 3028.0 | 2626.1 | 2455.4 | 2458.2 |
| 20° | 8244.4 | 7914.1 | 7082.7 | 6080.7 | 4960.4 | 3749.2 | 2642.6 | 2075.5 | 1962.7 | 1957.2 | 1948.9 |
| 22.5° | 8332.5 | 7878.3 | 6818.5 | 5582.5 | 4115.3 | 2626.1 | 1759.0 | 1582.8 | 1629.6 | 1720.4 | 1737.0 |
| 25° | 8437.1 | 7834.2 | 6523.9 | 5021.0 | 3193.1 | 1723.2 | 1318.6 | 1291.0 | 1403.9 | 1525.0 | 1552.5 |
| 27.5° | 8599.5 | 7812.2 | 6188.1 | 4382.3 | 2240.7 | 1236.0 | 1079.1 | 1095.6 | 1197.4 | 1299.3 | 1324.1 |
| 30° | 8874.8 | 7853.5 | 5822.0 | 3666.6 | 1439.7 | 985.5 | 935.9 | 960.7 | 1015.8 | 1068.1 | 1090.1 |
| 32.5° | 9249.1 | 7974.6 | 5466.9 | 2884.8 | 1026.8 | 856.1 | 845.1 | 858.8 | 880.9 | 911.1 | 919.4 |
| 35° | 9686.8 | 8183.8 | 5100.8 | 2064.5 | 847.8 | 781.8 | 770.8 | 770.8 | 781.8 | 787.3 | 790.0 |
| 37.5° | 10047.4 | 8404.0 | 4756.7 | 1373.6 | 759.7 | 724.0 | 707.4 | 699.2 | 696.4 | 701.9 | 704.7 |
| 40° | 10204.3 | 8494.9 | 4382.3 | 999.2 | 696.4 | 671.7 | 646.9 | 622.1 | 622.1 | 641.4 | 644.1 |
| 42.5° | 10094.2 | 8393.0 | 3950.1 | 825.8 | 652.4 | 616.6 | 578.1 | 556.0 | 567.1 | 586.3 | 591.8 |
| 45° | 9860.2 | 8142.5 | 3473.9 | 729.5 | 608.3 | 561.6 | 517.5 | 503.7 | 514.8 | 539.5 | 545.0 |
| 47.5° | 9821.7 | 7977.4 | 2904.1 | 666.2 | 561.6 | 514.8 | 468.0 | 454.2 | 468.0 | 487.2 | 492.7 |
| 50° | 10204.3 | 8120.5 | 2271.0 | 611.1 | 517.5 | 465.2 | 426.7 | 412.9 | 421.2 | 432.2 | 437.7 |
| 52.5° | 10903.5 | 8651.8 | 1833.3 | 558.8 | 465.2 | 415.7 | 390.9 | 374.4 | 374.4 | 385.4 | 388.1 |
| 55° | 11935.8 | 9579.4 | 1582.8 | 498.2 | 404.6 | 377.1 | 355.1 | 338.6 | 338.6 | 344.1 | 346.8 |
| 57.5° | 13124.9 | 10702.6 | 1640.6 | 418.4 | 355.1 | 341.3 | 322.1 | 308.3 | 313.8 | 313.8 | 313.8 |
| 60° | 12959.8 | 10620.0 | 1756.2 | 352.3 | 313.8 | 308.3 | 291.8 | 286.3 | 300.0 | 289.0 | 283.5 |
| 62.5° | 9546.4 | 7336.0 | 919.4 | 289.0 | 269.8 | 264.3 | 253.2 | 264.3 | 283.5 | 253.2 | 242.2 |
| 65° | 4635.6 | 3551.0 | 368.9 | 236.7 | 228.5 | 223.0 | 217.5 | 234.0 | 245.0 | 198.2 | 187.2 |
| 67.5° | 1090.1 | 886.4 | 239.5 | 200.9 | 189.9 | 178.9 | 184.4 | 187.2 | 178.9 | 134.9 | 129.4 |
| 70° | 283.5 | 278.0 | 187.2 | 167.9 | 151.4 | 140.4 | 140.4 | 137.6 | 118.4 | 85.3 | 79.8 |
| 72.5° | 154.2 | 151.4 | 134.9 | 126.6 | 104.6 | 93.6 | 96.3 | 85.3 | 66.1 | 49.5 | 46.8 |
| 75° | 77.1 | 82.6 | 77.1 | 71.6 | 57.8 | 52.3 | 52.3 | 46.8 | 33.0 | 19.3 | 19.3 |
| 77.5° | 16.5 | 19.3 | 19.3 | 16.5 | 13.8 | 11.0 | 11.0 | 13.8 | 5.5 | 0.0 | 0.0 |
| 80° | 2.8 | 2.8 | 2.8 | 2.8 | 2.8 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 82.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 85° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 87.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



LM-79-2008: Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGRAW-EDISON

Report Number: SP1-1908-441-4-R4

Test Date: 10/02/2019

Luminaire Tested: SA1C-750-U-5WQ

Data in this report applies to families of products SA1C-760-U-5WQ .

Test Information

Test Method: LM-79-2008
 Report Number: SP1-1908-441-4-R4
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 10/28/2024
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: MCGRAW-EDISON
 Catalog Number: **SA1C-750-U-5WQ**
 Description: MCGRAW EDISON ROADWAY AND AREA LUMINAIRE

THIS IS A REVISION OF SP1-1908-441-4-R3. TO UPDATE THE CATALOG INFORMATION.TESTED IN SITU. ROADWAY AND AREA LUMINAIRE. (1) 70 CRI, 5000K, 1050MA LIGHTSQUARE WITH 16 LEDS AND TYPE V WIDE OPTICS.

Spectral Parameters

CCT (K): 4884
 CIE u': 0.2101
 CIE v': 0.4904
 Duv: 0.0037
 CIE x: 0.3493
 CIE y: 0.3624
 CIE z: 0.2884
 Peak Wavelength (nm): 444
 Dominant Wavelength (nm): 571
 Purity: 13.7
 Rf: 74.9
 Rg: 96.3

| | | | |
|-----------|------|------|-------|
| CRI (Ra): | 73.5 | | |
| R1: | 70.5 | R9: | -28.4 |
| R2: | 77.7 | R10: | 48.6 |
| R3: | 84.6 | R11: | 73.2 |
| R4: | 74.7 | R12: | 50.7 |
| R5: | 71.9 | R13: | 71.2 |
| R6: | 70.7 | R14: | 91.4 |
| R7: | 81.2 | | |
| R8: | 56.9 | | |



Test Conditions

Stabilization Time: 240M
 Operation Time: 12H
 Room Temperature (°C) / RH%: 25.0./44%
 Sphere Temperature (°C): 25.7

REPORT NUMBER: SP1-1908-441-4-R4

| Measurement and Test Equipment | | | |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument | Identification Number | Calibration Date | Calibration Due Date |
| Photometer | IN0058 | 6/28/2019 | 12/28/2019 |
| Power Meter | IN0071 | 12/5/2018 | 12/5/2019 |
| AC Power Source | IN0063 | 12/5/2018 | 12/5/2019 |
| DC Power Source | IN0208 | 12/5/2018 | 12/5/2019 |
| Sphere Thermometer | IN0085 | 12/5/2018 | 12/5/2019 |
| Room Thermometer | IN0046 | 12/5/2018 | 12/5/2019 |

REPORT NUMBER: SP1-1908-441-4-R4

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 5000K 4-step quadrangle

REPORT NUMBER: SP1-1908-441-4-R4

Photopic Flux vs. Wavelength



#####

| λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) |
|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|
| 360 | 2945 | NR | 490 | 37941 | NR | 620 | 88803 | NR | 750 | 3908 | NR | 880 | 2997 | NR |
| 365 | 2596 | NR | 495 | 48525 | NR | 625 | 80578 | NR | 755 | 3988 | NR | 885 | 2927 | NR |
| 370 | 2732 | NR | 500 | 60609 | NR | 630 | 73127 | NR | 760 | 3335 | NR | 890 | 2649 | NR |
| 375 | 2894 | NR | 505 | 72036 | NR | 635 | 66244 | NR | 765 | 3438 | NR | 895 | 2828 | NR |
| 380 | 2822 | NR | 510 | 82168 | NR | 640 | 59440 | NR | 770 | 3427 | NR | 900 | 1407 | NR |
| 385 | 2394 | NR | 515 | 90898 | NR | 645 | 52864 | NR | 775 | 2759 | NR | 905 | 2224 | NR |
| 390 | 2370 | NR | 520 | 97142 | NR | 650 | 47085 | NR | 780 | 2340 | NR | 910 | 2905 | NR |
| 395 | 2267 | NR | 525 | 103255 | NR | 655 | 41789 | NR | 785 | 2412 | NR | 915 | 3350 | NR |
| 400 | 2262 | NR | 530 | 106697 | NR | 660 | 37064 | NR | 790 | 1999 | NR | 920 | 3114 | NR |
| 405 | 3000 | NR | 535 | 110081 | NR | 665 | 32299 | NR | 795 | 2054 | NR | 925 | 2834 | NR |
| 410 | 5324 | NR | 540 | 112494 | NR | 670 | 28142 | NR | 800 | 2331 | NR | 930 | 2271 | NR |
| 415 | 10725 | NR | 545 | 115513 | NR | 675 | 24505 | NR | 805 | 2648 | NR | 935 | 2228 | NR |
| 420 | 22128 | NR | 550 | 117203 | NR | 680 | 21162 | NR | 810 | 2485 | NR | 940 | 2833 | NR |
| 425 | 44095 | NR | 555 | 119753 | NR | 685 | 18400 | NR | 815 | 2409 | NR | 945 | 2941 | NR |
| 430 | 77002 | NR | 560 | 122602 | NR | 690 | 16065 | NR | 820 | 2221 | NR | 950 | 2323 | NR |
| 435 | 119881 | NR | 565 | 124314 | NR | 695 | 13860 | NR | 825 | 1562 | NR | 955 | 1667 | NR |
| 440 | 164454 | NR | 570 | 126775 | NR | 700 | 12177 | NR | 830 | 2249 | NR | 960 | 749 | NR |
| 445 | 179997 | NR | 575 | 127511 | NR | 705 | 10757 | NR | 835 | 2573 | NR | 965 | 2669 | NR |
| 450 | 142822 | NR | 580 | 127577 | NR | 710 | 9601 | NR | 840 | 2764 | NR | 970 | 3968 | NR |
| 455 | 90008 | NR | 585 | 126153 | NR | 715 | 8944 | NR | 845 | 3109 | NR | 975 | 3886 | NR |
| 460 | 60557 | NR | 590 | 123678 | NR | 720 | 7947 | NR | 850 | 2963 | NR | 980 | 2788 | NR |
| 465 | 43305 | NR | 595 | 119774 | NR | 725 | 7062 | NR | 855 | 2336 | NR | 985 | 3496 | NR |
| 470 | 31089 | NR | 600 | 115733 | NR | 730 | 6004 | NR | 860 | 2118 | NR | 990 | 2913 | NR |
| 475 | 26278 | NR | 605 | 109231 | NR | 735 | 5594 | NR | 865 | 3144 | NR | 995 | 4659 | NR |
| 480 | 27060 | NR | 610 | 102408 | NR | 740 | 5165 | NR | 870 | 3069 | NR | 1000 | 1308 | NR |
| 485 | 30698 | NR | 615 | 96015 | NR | 745 | 4687 | NR | 875 | 3311 | NR | | | |

REPORT NUMBER: SP1-1908-441-4-R4

Scotopic Flux vs. Wavelength



Scotopic Lumens: 13493.5 S/P: 1.77

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 2945 | NR | 490 | 37941 | NR | 620 | 88803 | NR | 750 | 3908 | NR | 880 | 2997 | NR |
| 365 | 2596 | NR | 495 | 48525 | NR | 625 | 80578 | NR | 755 | 3988 | NR | 885 | 2927 | NR |
| 370 | 2732 | NR | 500 | 60609 | NR | 630 | 73127 | NR | 760 | 3335 | NR | 890 | 2649 | NR |
| 375 | 2894 | NR | 505 | 72036 | NR | 635 | 66244 | NR | 765 | 3438 | NR | 895 | 2828 | NR |
| 380 | 2822 | NR | 510 | 82168 | NR | 640 | 59440 | NR | 770 | 3427 | NR | 900 | 1407 | NR |
| 385 | 2394 | NR | 515 | 90898 | NR | 645 | 52864 | NR | 775 | 2759 | NR | 905 | 2224 | NR |
| 390 | 2370 | NR | 520 | 97142 | NR | 650 | 47085 | NR | 780 | 2340 | NR | 910 | 2905 | NR |
| 395 | 2267 | NR | 525 | 103255 | NR | 655 | 41789 | NR | 785 | 2412 | NR | 915 | 3350 | NR |
| 400 | 2262 | NR | 530 | 106697 | NR | 660 | 37064 | NR | 790 | 1999 | NR | 920 | 3114 | NR |
| 405 | 3000 | NR | 535 | 110081 | NR | 665 | 32299 | NR | 795 | 2054 | NR | 925 | 2834 | NR |
| 410 | 5324 | NR | 540 | 112494 | NR | 670 | 28142 | NR | 800 | 2331 | NR | 930 | 2271 | NR |
| 415 | 10725 | NR | 545 | 115513 | NR | 675 | 24505 | NR | 805 | 2648 | NR | 935 | 2228 | NR |
| 420 | 22128 | NR | 550 | 117203 | NR | 680 | 21162 | NR | 810 | 2485 | NR | 940 | 2833 | NR |
| 425 | 44095 | NR | 555 | 119753 | NR | 685 | 18400 | NR | 815 | 2409 | NR | 945 | 2941 | NR |
| 430 | 77002 | NR | 560 | 122602 | NR | 690 | 16065 | NR | 820 | 2221 | NR | 950 | 2323 | NR |
| 435 | 119881 | NR | 565 | 124314 | NR | 695 | 13860 | NR | 825 | 1562 | NR | 955 | 1667 | NR |
| 440 | 164454 | NR | 570 | 126775 | NR | 700 | 12177 | NR | 830 | 2249 | NR | 960 | 749 | NR |
| 445 | 179997 | NR | 575 | 127511 | NR | 705 | 10757 | NR | 835 | 2573 | NR | 965 | 2669 | NR |
| 450 | 142822 | NR | 580 | 127577 | NR | 710 | 9601 | NR | 840 | 2764 | NR | 970 | 3968 | NR |
| 455 | 90008 | NR | 585 | 126153 | NR | 715 | 8944 | NR | 845 | 3109 | NR | 975 | 3886 | NR |
| 460 | 60557 | NR | 590 | 123678 | NR | 720 | 7947 | NR | 850 | 2963 | NR | 980 | 2788 | NR |
| 465 | 43305 | NR | 595 | 119774 | NR | 725 | 7062 | NR | 855 | 2336 | NR | 985 | 3496 | NR |
| 470 | 31089 | NR | 600 | 115733 | NR | 730 | 6004 | NR | 860 | 2118 | NR | 990 | 2913 | NR |
| 475 | 26278 | NR | 605 | 109231 | NR | 735 | 5594 | NR | 865 | 3144 | NR | 995 | 4659 | NR |
| 480 | 27060 | NR | 610 | 102408 | NR | 740 | 5165 | NR | 870 | 3069 | NR | 1000 | 1308 | NR |
| 485 | 30698 | NR | 615 | 96015 | NR | 745 | 4687 | NR | 875 | 3311 | NR | | | |

REPORT NUMBER: SP1-1908-441-4-R4

Melanopic Flux vs. Wavelength



Melanopic Lumens: 5378.9

M/P: 0.71

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 2945 | NR | 490 | 37941 | NR | 620 | 88803 | NR | 750 | 3908 | NR | 880 | 2997 | NR |
| 365 | 2596 | NR | 495 | 48525 | NR | 625 | 80578 | NR | 755 | 3988 | NR | 885 | 2927 | NR |
| 370 | 2732 | NR | 500 | 60609 | NR | 630 | 73127 | NR | 760 | 3335 | NR | 890 | 2649 | NR |
| 375 | 2894 | NR | 505 | 72036 | NR | 635 | 66244 | NR | 765 | 3438 | NR | 895 | 2828 | NR |
| 380 | 2822 | NR | 510 | 82168 | NR | 640 | 59440 | NR | 770 | 3427 | NR | 900 | 1407 | NR |
| 385 | 2394 | NR | 515 | 90898 | NR | 645 | 52864 | NR | 775 | 2759 | NR | 905 | 2224 | NR |
| 390 | 2370 | NR | 520 | 97142 | NR | 650 | 47085 | NR | 780 | 2340 | NR | 910 | 2905 | NR |
| 395 | 2267 | NR | 525 | 103255 | NR | 655 | 41789 | NR | 785 | 2412 | NR | 915 | 3350 | NR |
| 400 | 2262 | NR | 530 | 106697 | NR | 660 | 37064 | NR | 790 | 1999 | NR | 920 | 3114 | NR |
| 405 | 3000 | NR | 535 | 110081 | NR | 665 | 32299 | NR | 795 | 2054 | NR | 925 | 2834 | NR |
| 410 | 5324 | NR | 540 | 112494 | NR | 670 | 28142 | NR | 800 | 2331 | NR | 930 | 2271 | NR |
| 415 | 10725 | NR | 545 | 115513 | NR | 675 | 24505 | NR | 805 | 2648 | NR | 935 | 2228 | NR |
| 420 | 22128 | NR | 550 | 117203 | NR | 680 | 21162 | NR | 810 | 2485 | NR | 940 | 2833 | NR |
| 425 | 44095 | NR | 555 | 119753 | NR | 685 | 18400 | NR | 815 | 2409 | NR | 945 | 2941 | NR |
| 430 | 77002 | NR | 560 | 122602 | NR | 690 | 16065 | NR | 820 | 2221 | NR | 950 | 2323 | NR |
| 435 | 119881 | NR | 565 | 124314 | NR | 695 | 13860 | NR | 825 | 1562 | NR | 955 | 1667 | NR |
| 440 | 164454 | NR | 570 | 126775 | NR | 700 | 12177 | NR | 830 | 2249 | NR | 960 | 749 | NR |
| 445 | 179997 | NR | 575 | 127511 | NR | 705 | 10757 | NR | 835 | 2573 | NR | 965 | 2669 | NR |
| 450 | 142822 | NR | 580 | 127577 | NR | 710 | 9601 | NR | 840 | 2764 | NR | 970 | 3968 | NR |
| 455 | 90008 | NR | 585 | 126153 | NR | 715 | 8944 | NR | 845 | 3109 | NR | 975 | 3886 | NR |
| 460 | 60557 | NR | 590 | 123678 | NR | 720 | 7947 | NR | 850 | 2963 | NR | 980 | 2788 | NR |
| 465 | 43305 | NR | 595 | 119774 | NR | 725 | 7062 | NR | 855 | 2336 | NR | 985 | 3496 | NR |
| 470 | 31089 | NR | 600 | 115733 | NR | 730 | 6004 | NR | 860 | 2118 | NR | 990 | 2913 | NR |
| 475 | 26278 | NR | 605 | 109231 | NR | 735 | 5594 | NR | 865 | 3144 | NR | 995 | 4659 | NR |
| 480 | 27060 | NR | 610 | 102408 | NR | 740 | 5165 | NR | 870 | 3069 | NR | 1000 | 1308 | NR |
| 485 | 30698 | NR | 615 | 96015 | NR | 745 | 4687 | NR | 875 | 3311 | NR | | | |

REPORT NUMBER: SP1-1908-441-4-R4


TM-30-18

Summary

$R_f = 74.9$
 $R_g = 96.3$
 $CIE R_a = 73.5$
 $R_g = -28.4$



Color Vector Graphics



REPORT NUMBER: SP1-1908-441-4-R4

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)

| | | | |
|------------|------------|------------|------------|
| CES01 = 85 | CES26 = 61 | CES51 = 90 | CES76 = 52 |
| CES02 = 60 | CES27 = 84 | CES52 = 91 | CES77 = 71 |
| CES03 = 30 | CES28 = 81 | CES53 = 79 | CES78 = 54 |
| CES04 = 69 | CES29 = 58 | CES54 = 83 | CES79 = 80 |
| CES05 = 46 | CES30 = 67 | CES55 = 83 | CES80 = 77 |
| CES06 = 50 | CES31 = 63 | CES56 = 73 | CES81 = 77 |
| CES07 = 39 | CES32 = 59 | CES57 = 72 | CES82 = 90 |
| CES08 = 38 | CES33 = 69 | CES58 = 73 | CES83 = 86 |
| CES09 = 29 | CES34 = 69 | CES59 = 88 | CES84 = 88 |
| CES10 = 73 | CES35 = 83 | CES60 = 93 | CES85 = 84 |
| CES11 = 56 | CES36 = 95 | CES61 = 88 | CES86 = 75 |
| CES12 = 61 | CES37 = 78 | CES62 = 85 | CES87 = 78 |
| CES13 = 41 | CES38 = 76 | CES63 = 77 | CES88 = 79 |
| CES14 = 74 | CES39 = 93 | CES64 = 74 | CES89 = 75 |
| CES15 = 70 | CES40 = 86 | CES65 = 67 | CES90 = 77 |
| CES16 = 46 | CES41 = 87 | CES66 = 69 | CES91 = 89 |
| CES17 = 49 | CES42 = 78 | CES67 = 67 | CES92 = 66 |
| CES18 = 55 | CES43 = 75 | CES68 = 73 | CES93 = 80 |
| CES19 = 71 | CES44 = 99 | CES69 = 81 | CES94 = 57 |
| CES20 = 64 | CES45 = 83 | CES70 = 63 | CES95 = 71 |
| CES21 = 85 | CES46 = 81 | CES71 = 60 | CES96 = 78 |
| CES22 = 77 | CES47 = 80 | CES72 = 86 | CES97 = 85 |
| CES23 = 91 | CES48 = 72 | CES73 = 53 | CES98 = 75 |
| CES24 = 90 | CES49 = 81 | CES74 = 96 | CES99 = 62 |
| CES25 = 71 | CES50 = 89 | CES75 = 58 | |



REPORT NUMBER: SP1-1908-441-4-R4

TM-30-18

Color Rendition by Hue-Angle Bin



REPORT NUMBER: SP1-1908-441-4-R4

TM-30-18

Measure Comparisons



(END OF REPORT)