

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: McGRAW-EDISON

Report Number: P643765

Luminaire Tested: GWS-SA6F-750-U-SLR-W-HSS

Issue Date: 1/10/2023

Test Information

Test Method: LM-79-2019
Report Number: P643765
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2209-782-44)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/10/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: McGRAW-EDISON
Catalog Number: GWS-SAGF-750-U-SLR-W-HSS
Description: GALLEON WALL SLIM LUMINAIRE. (6) LIGHTSQUARES WITH 16 LEDS EACH AND
SPILL LIGHT ELIMINATOR RIGHT OPTICS WITH HOUSE SIDE SHIELD
Light Source: (96) 5000K CCT, 70 CRI LEDS
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 31594.9 lumens
Efficiency: N/A
Efficacy: 84.8 lumens/watt
Luminous Opening: Rectangular (W 2' x L: 1' x H: 0')
IES Classification: Type IV - Short
BUG Rating: B3 - U0 - G5


Input Watts (W): 372.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 0
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT



REPORT NUMBER: P643765
 CATALOG NUMBER: GWS-SA6F-750-U-SLR-W-HSS

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 30 foot mounting height. Maximum calculated value = 7.1 fc
 Type IV - Short - N/A

REPORT NUMBER: P643765
CATALOG NUMBER: GWS-SA6F-750-U-SLR-W-HSS

Luminous Intensity Polar Plot



— Vertical Plane Through 45-Deg Lateral - - - Horizontal Cone Through 62.5-Deg Vertical

REPORT NUMBER: P643765
 CATALOG NUMBER: GWS-SA6F-750-U-SLR-W-HSS


FLUX DISTRIBUTION:

| | | Downward | Upward | Total |
|--------------------|-----------|----------|--------|---------|
| House Side | Lumens | 3898.8 | 0.0 | 3898.8 |
| | % Fixture | 12.3 | 0.0 | 12.3 |
| Street Side | Lumens | 27696.1 | 0.0 | 27696.1 |
| | % Fixture | 87.7 | 0.0 | 87.7 |
| Total | Lumens | 31594.9 | 0.0 | 31594.9 |
| | % Fixture | 100.0 | 0.0 | 100.0 |

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|---------|-----------|
| 0°-10° | 145.7 | 0.5 |
| 10°-20° | 550.8 | 1.7 |
| 20°-30° | 1197.4 | 3.8 |
| 30°-40° | 1965.4 | 6.2 |
| 40°-50° | 3613.1 | 11.4 |
| 50°-60° | 7759.2 | 24.6 |
| 60°-70° | 10421.9 | 33.0 |
| 70°-80° | 5426.8 | 17.2 |
| 80°-90° | 514.5 | 1.6 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-90° | 31594.9 | 100.0 |
| 0°-180° | 31594.9 | 100.0 |

Coefficient of Utilization



REPORT NUMBER: P643765


CATALOG NUMBER: GWS-SA6F-750-U-SLR-W-HSS

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

| Zone | Lumens | % Fixture | Zone Rating/Lumen Limit | | |
|----------------|---------|-----------|-------------------------|------|---------|
| | | | B | U | G |
| FL (0°-30°) | 1334.7 | 4.2 | | | |
| FM (30°-60°) | 11089.4 | 35.1 | | | |
| FH (60°-80°) | 14780.4 | 46.8 | | | G5 |
| FVH (80°-90°) | 491.6 | 1.6 | | | G3/500 |
| BL (0°-30°) | 559.2 | 1.8 | B2/1000 | | |
| BM (30°-60°) | 2248.3 | 7.1 | B2/2500 | | |
| BH (60°-80°) | 1068.3 | 3.4 | B3/2500 | | G3/2500 |
| BVH (80°-90°) | 22.9 | 0.1 | | | G1/100 |
| UL (90°-100°) | 0.0 | 0.0 | | U0/0 | |
| UH (100°-180°) | 0.0 | 0.0 | | U0/0 | |

BUG Rating: B3-U0-G5

Type IV Short





REPORT NUMBER: P643765

CATALOG NUMBER: GWS-SA6F-750-U-SLR-W-HSS

CANDELA DISTRIBUTION (FULL):

| | 0° | 1° | 5° | 15° | 25° | 35° | 45° | 55° | 65° | 75° | 85° |
|-------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|
| 0° | 1642.3 | 1642.3 | 1642.3 | 1642.3 | 1642.3 | 1642.3 | 1642.3 | 1642.3 | 1642.3 | 1642.3 | 1642.3 |
| 2.5° | 1675.1 | 1682.4 | 1689.7 | 1715.3 | 1733.5 | 1748.1 | 1751.8 | 1740.8 | 1715.3 | 1689.7 | 1653.2 |
| 5° | 1624.0 | 1631.3 | 1656.9 | 1726.2 | 1795.6 | 1850.3 | 1868.5 | 1857.6 | 1795.6 | 1715.3 | 1631.3 |
| 7.5° | 1620.4 | 1635.0 | 1697.0 | 1843.0 | 1992.6 | 2105.8 | 2135.0 | 2109.4 | 1992.6 | 1832.0 | 1660.5 |
| 10° | 1751.8 | 1777.3 | 1868.5 | 2131.3 | 2405.0 | 2605.7 | 2686.0 | 2576.5 | 2390.4 | 2098.5 | 1817.4 |
| 12.5° | 2094.8 | 2138.6 | 2313.8 | 2697.0 | 3120.3 | 3386.7 | 3496.2 | 3361.2 | 3069.2 | 2645.9 | 2200.6 |
| 15° | 2634.9 | 2700.6 | 2963.4 | 3536.4 | 4036.3 | 4273.6 | 4310.1 | 4233.4 | 3894.0 | 3426.9 | 2828.4 |
| 17.5° | 3397.7 | 3492.6 | 3901.3 | 4485.2 | 4846.5 | 4930.5 | 4919.5 | 4839.2 | 4591.1 | 4269.9 | 3704.2 |
| 20° | 4310.1 | 4423.2 | 4824.6 | 5306.4 | 5342.9 | 5244.3 | 5189.6 | 5142.1 | 5058.2 | 5003.5 | 4561.9 |
| 22.5° | 5229.7 | 5368.4 | 5788.1 | 5908.5 | 5580.1 | 5295.4 | 5160.4 | 5196.9 | 5321.0 | 5591.0 | 5412.2 |
| 25° | 6145.8 | 6277.1 | 6671.3 | 6346.5 | 5689.6 | 5215.1 | 5043.6 | 5131.2 | 5426.8 | 6010.7 | 6240.6 |
| 27.5° | 7215.1 | 7313.6 | 7547.2 | 6645.7 | 5707.8 | 5149.4 | 4981.6 | 5116.6 | 5477.9 | 6273.5 | 7149.4 |
| 30° | 8328.2 | 8386.5 | 8273.4 | 6726.0 | 5645.8 | 5050.9 | 4919.5 | 5116.6 | 5565.5 | 6448.7 | 7831.8 |
| 32.5° | 9145.6 | 9156.6 | 8788.0 | 6733.3 | 5612.9 | 4970.6 | 4861.1 | 5094.7 | 5649.4 | 6594.6 | 8492.4 |
| 35° | 9988.7 | 9933.9 | 9280.7 | 6842.8 | 5700.5 | 4999.8 | 4904.9 | 5156.7 | 5780.8 | 6766.2 | 9072.6 |
| 37.5° | 10842.7 | 10744.1 | 9831.7 | 7021.6 | 5926.8 | 5317.3 | 5258.9 | 5474.2 | 5992.5 | 7003.4 | 9711.3 |
| 40° | 11718.5 | 11583.5 | 10404.7 | 7291.7 | 6430.4 | 6397.6 | 6598.3 | 6572.7 | 6572.7 | 7306.3 | 10368.2 |
| 42.5° | 12787.8 | 12630.9 | 11251.4 | 8054.4 | 7605.6 | 8339.1 | 8886.5 | 8547.1 | 7919.4 | 8003.3 | 11222.2 |
| 45° | 14200.2 | 14065.2 | 12718.5 | 9514.2 | 9448.5 | 11134.6 | 11871.8 | 11200.3 | 9638.3 | 9612.8 | 12649.2 |
| 47.5° | 16459.2 | 16433.7 | 15057.8 | 11207.6 | 11703.9 | 14692.9 | 16116.2 | 14824.3 | 11598.1 | 11317.1 | 15349.8 |
| 50° | 19634.3 | 19557.7 | 17973.8 | 13192.9 | 14386.3 | 19101.5 | 21641.5 | 19488.3 | 13966.6 | 13306.1 | 18966.4 |
| 52.5° | 23210.8 | 23291.1 | 22057.6 | 15360.7 | 17236.6 | 24006.4 | 27542.8 | 24831.2 | 16539.5 | 15835.2 | 23517.4 |
| 55° | 26579.3 | 27039.1 | 26714.3 | 17897.1 | 20021.1 | 29422.2 | 34024.3 | 30692.3 | 19725.5 | 19145.3 | 28619.4 |
| 57.5° | 29214.2 | 30509.8 | 32787.1 | 21583.1 | 23294.7 | 35757.8 | 41261.2 | 37046.0 | 23444.4 | 24521.0 | 35564.3 |
| 60° | 29360.2 | 31075.5 | 36363.6 | 29294.5 | 27506.3 | 41191.9 | 48487.2 | 43253.8 | 29290.9 | 33648.4 | 41005.7 |
| 62.5° | 27159.6 | 28998.9 | 34035.2 | 32798.0 | 32093.7 | 45815.8 | 52195.1 | 47779.2 | 35042.5 | 38994.9 | 39392.7 |
| 65° | 24641.4 | 26499.0 | 31436.8 | 28823.7 | 31560.8 | 45618.7 | 51253.5 | 47885.0 | 35564.3 | 35360.0 | 36505.9 |
| 67.5° | 20835.0 | 22502.8 | 26973.4 | 25513.6 | 29090.1 | 43418.1 | 46903.3 | 44866.9 | 32765.2 | 33071.7 | 33582.7 |
| 70° | 15207.5 | 16813.2 | 20962.7 | 21035.7 | 25404.1 | 39451.1 | 40301.4 | 40020.4 | 30174.0 | 30498.8 | 29039.0 |
| 72.5° | 10985.0 | 12338.9 | 15919.1 | 17251.2 | 20280.3 | 33082.7 | 32495.1 | 33579.0 | 25889.5 | 27163.2 | 23323.9 |
| 75° | 7897.5 | 8912.1 | 11678.4 | 15006.7 | 16076.0 | 24568.4 | 23261.9 | 26006.3 | 20772.9 | 23389.6 | 17535.8 |
| 77.5° | 3204.3 | 3561.9 | 4594.7 | 10109.1 | 10565.3 | 16528.6 | 14240.3 | 18889.8 | 14809.7 | 15368.0 | 8499.7 |
| 80° | 131.4 | 146.0 | 189.8 | 5218.8 | 7244.3 | 9298.9 | 7620.1 | 10098.2 | 9780.7 | 6189.5 | 2007.2 |
| 82.5° | 14.6 | 14.6 | 32.8 | 1503.6 | 3171.4 | 5131.2 | 3591.1 | 5817.3 | 4952.4 | 2624.0 | 912.4 |
| 85° | 3.6 | 3.6 | 7.3 | 171.5 | 744.5 | 821.1 | 485.4 | 1784.6 | 2302.8 | 1073.0 | 0.0 |
| 87.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 18.2 | 32.8 | 36.5 | 0.0 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P643765
 CATALOG NUMBER: GWS-SA6F-750-U-SLR-W-HSS

CANDELA DISTRIBUTION (continued):

| | 90° | 95° | 105° | 115° | 125° | 135° | 145° | 155° | 165° | 175° | 180° |
|-------|---------|---------|---------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 1642.3 | 1642.3 | 1642.3 | 1642.3 | 1642.3 | 1642.3 | 1642.3 | 1642.3 | 1642.3 | 1642.3 | 1642.3 |
| 2.5° | 1653.2 | 1635.0 | 1613.1 | 1591.2 | 1580.2 | 1551.0 | 1540.1 | 1532.8 | 1525.5 | 1529.1 | 1529.1 |
| 5° | 1598.5 | 1558.3 | 1510.9 | 1463.4 | 1437.9 | 1408.7 | 1394.1 | 1386.8 | 1390.5 | 1405.1 | 1405.1 |
| 7.5° | 1591.2 | 1514.5 | 1412.4 | 1350.3 | 1321.1 | 1299.2 | 1284.6 | 1277.3 | 1281.0 | 1299.2 | 1306.5 |
| 10° | 1711.6 | 1576.6 | 1394.1 | 1288.3 | 1255.4 | 1233.5 | 1218.9 | 1208.0 | 1200.7 | 1215.3 | 1218.9 |
| 12.5° | 1970.7 | 1784.6 | 1481.7 | 1281.0 | 1222.6 | 1193.4 | 1182.4 | 1160.5 | 1149.6 | 1156.9 | 1160.5 |
| 15° | 2507.2 | 2186.0 | 1656.9 | 1310.2 | 1193.4 | 1160.5 | 1142.3 | 1124.0 | 1105.8 | 1102.1 | 1105.8 |
| 17.5° | 3207.9 | 2748.1 | 1923.3 | 1379.5 | 1171.5 | 1131.3 | 1105.8 | 1080.3 | 1054.7 | 1051.1 | 1047.4 |
| 20° | 4076.5 | 3437.8 | 2295.5 | 1489.0 | 1153.2 | 1105.8 | 1069.3 | 1032.8 | 1000.0 | 989.0 | 989.0 |
| 22.5° | 4868.4 | 4269.9 | 2773.6 | 1624.0 | 1127.7 | 1069.3 | 1025.5 | 981.7 | 945.2 | 927.0 | 923.3 |
| 25° | 5835.5 | 5153.1 | 3346.6 | 1781.0 | 1091.2 | 1021.9 | 974.4 | 930.6 | 894.1 | 872.2 | 864.9 |
| 27.5° | 6810.0 | 6083.7 | 3996.2 | 1985.3 | 1047.4 | 974.4 | 930.6 | 890.5 | 850.3 | 824.8 | 817.5 |
| 30° | 7755.2 | 7087.3 | 4726.1 | 2240.8 | 1014.6 | 927.0 | 890.5 | 850.3 | 813.8 | 773.7 | 762.7 |
| 32.5° | 8769.7 | 8112.8 | 5543.6 | 2525.5 | 989.0 | 894.1 | 854.0 | 817.5 | 770.0 | 733.5 | 715.3 |
| 35° | 9747.8 | 9171.2 | 6445.0 | 2802.8 | 963.5 | 864.9 | 821.1 | 784.6 | 733.5 | 693.4 | 667.9 |
| 37.5° | 10733.2 | 10247.8 | 7386.6 | 2970.7 | 927.0 | 824.8 | 784.6 | 755.4 | 697.1 | 649.6 | 620.4 |
| 40° | 11776.9 | 11360.9 | 8404.8 | 2901.3 | 894.1 | 781.0 | 759.1 | 726.2 | 660.6 | 605.8 | 569.3 |
| 42.5° | 12922.9 | 12422.9 | 9441.2 | 2634.9 | 864.9 | 744.5 | 722.6 | 689.8 | 627.7 | 562.0 | 514.6 |
| 45° | 14364.4 | 13587.1 | 10291.6 | 2233.5 | 879.5 | 708.0 | 664.2 | 656.9 | 598.5 | 514.6 | 456.2 |
| 47.5° | 16842.4 | 15375.3 | 10952.1 | 1974.4 | 978.1 | 667.9 | 616.8 | 635.0 | 573.0 | 467.1 | 401.4 |
| 50° | 20634.3 | 18338.7 | 11568.9 | 1956.1 | 1127.7 | 649.6 | 573.0 | 620.4 | 547.4 | 419.7 | 354.0 |
| 52.5° | 24247.3 | 21349.6 | 11963.0 | 2116.7 | 1259.1 | 697.1 | 529.2 | 602.2 | 529.2 | 386.8 | 321.2 |
| 55° | 27703.3 | 23086.7 | 11258.7 | 2233.5 | 1383.2 | 839.4 | 496.3 | 573.0 | 507.3 | 368.6 | 310.2 |
| 57.5° | 31429.5 | 23860.4 | 8864.6 | 2470.7 | 1470.7 | 959.8 | 503.6 | 529.2 | 478.1 | 357.7 | 306.6 |
| 60° | 32542.6 | 22871.4 | 5350.2 | 2780.9 | 1423.3 | 996.3 | 558.4 | 470.8 | 437.9 | 335.8 | 295.6 |
| 62.5° | 30812.7 | 20524.8 | 3156.8 | 2532.8 | 1383.2 | 941.6 | 638.7 | 434.3 | 397.8 | 306.6 | 273.7 |
| 65° | 28225.2 | 17338.8 | 2058.3 | 2138.6 | 1467.1 | 839.4 | 678.8 | 416.0 | 361.3 | 277.4 | 240.9 |
| 67.5° | 25269.1 | 13966.6 | 1441.6 | 1262.7 | 1354.0 | 755.4 | 573.0 | 412.4 | 324.8 | 233.6 | 197.1 |
| 70° | 21283.9 | 10459.5 | 1014.6 | 835.7 | 1127.7 | 671.5 | 445.2 | 401.4 | 284.7 | 189.8 | 153.3 |
| 72.5° | 16444.6 | 6547.2 | 755.4 | 540.1 | 802.9 | 547.4 | 354.0 | 339.4 | 229.9 | 156.9 | 116.8 |
| 75° | 12127.3 | 3733.4 | 532.8 | 390.5 | 529.2 | 416.0 | 262.8 | 240.9 | 197.1 | 149.6 | 105.8 |
| 77.5° | 6331.9 | 1868.5 | 332.1 | 299.3 | 302.9 | 259.1 | 189.8 | 175.2 | 182.5 | 149.6 | 98.5 |
| 80° | 1215.3 | 372.2 | 200.7 | 219.0 | 164.2 | 164.2 | 138.7 | 146.0 | 160.6 | 120.4 | 83.9 |
| 82.5° | 507.3 | 80.3 | 109.5 | 124.1 | 102.2 | 113.1 | 113.1 | 116.8 | 113.1 | 87.6 | 62.0 |
| 85° | 0.0 | 0.0 | 47.4 | 51.1 | 69.3 | 69.3 | 58.4 | 58.4 | 58.4 | 51.1 | 36.5 |
| 87.5° | 0.0 | 0.0 | 0.0 | 0.0 | 3.6 | 10.9 | 21.9 | 25.5 | 29.2 | 21.9 | 14.6 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P643765

CATALOG NUMBER: GWS-SA6F-750-U-SLR-W-HSS

CANDELA DISTRIBUTION (continued):

| | 185° | 195° | 205° | 215° | 225° | 235° | 245° | 255° | 265° | 270° | 275° |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 1642.3 | 1642.3 | 1642.3 | 1642.3 | 1642.3 | 1642.3 | 1642.3 | 1642.3 | 1642.3 | 1642.3 | 1642.3 |
| 2.5° | 1525.5 | 1518.2 | 1529.1 | 1536.4 | 1543.7 | 1543.7 | 1536.4 | 1529.1 | 1518.2 | 1529.1 | 1518.2 |
| 5° | 1408.7 | 1419.7 | 1437.9 | 1445.2 | 1452.5 | 1437.9 | 1430.6 | 1408.7 | 1390.5 | 1394.1 | 1386.8 |
| 7.5° | 1317.5 | 1328.4 | 1350.3 | 1364.9 | 1364.9 | 1357.6 | 1335.7 | 1313.8 | 1284.6 | 1284.6 | 1281.0 |
| 10° | 1233.5 | 1248.1 | 1273.7 | 1291.9 | 1299.2 | 1291.9 | 1270.0 | 1240.8 | 1215.3 | 1215.3 | 1204.3 |
| 12.5° | 1164.2 | 1182.4 | 1211.6 | 1237.2 | 1244.5 | 1237.2 | 1215.3 | 1186.1 | 1156.9 | 1156.9 | 1149.6 |
| 15° | 1105.8 | 1127.7 | 1160.5 | 1189.7 | 1200.7 | 1189.7 | 1164.2 | 1127.7 | 1098.5 | 1102.1 | 1091.2 |
| 17.5° | 1051.1 | 1069.3 | 1113.1 | 1145.9 | 1156.9 | 1145.9 | 1113.1 | 1065.7 | 1036.5 | 1043.8 | 1036.5 |
| 20° | 989.0 | 1010.9 | 1054.7 | 1091.2 | 1102.1 | 1091.2 | 1054.7 | 1003.6 | 974.4 | 974.4 | 978.1 |
| 22.5° | 923.3 | 945.2 | 989.0 | 1014.6 | 1029.2 | 1018.2 | 981.7 | 934.3 | 905.1 | 905.1 | 908.7 |
| 25° | 864.9 | 875.9 | 908.7 | 934.3 | 937.9 | 927.0 | 897.8 | 861.3 | 839.4 | 850.3 | 854.0 |
| 27.5° | 810.2 | 810.2 | 824.8 | 839.4 | 835.7 | 824.8 | 813.8 | 784.6 | 781.0 | 791.9 | 802.9 |
| 30° | 751.8 | 733.5 | 726.2 | 715.3 | 711.7 | 708.0 | 719.0 | 719.0 | 726.2 | 740.8 | 751.8 |
| 32.5° | 700.7 | 664.2 | 631.4 | 598.5 | 580.3 | 594.9 | 624.1 | 649.6 | 675.2 | 697.1 | 708.0 |
| 35° | 642.3 | 583.9 | 529.2 | 485.4 | 456.2 | 478.1 | 525.5 | 573.0 | 616.8 | 646.0 | 664.2 |
| 37.5° | 583.9 | 500.0 | 434.3 | 379.5 | 357.7 | 375.9 | 427.0 | 492.7 | 558.4 | 594.9 | 620.4 |
| 40° | 521.9 | 416.0 | 339.4 | 295.6 | 273.7 | 292.0 | 343.1 | 408.7 | 496.3 | 543.8 | 576.6 |
| 42.5° | 459.8 | 343.1 | 273.7 | 229.9 | 219.0 | 229.9 | 270.1 | 335.8 | 430.6 | 489.0 | 532.8 |
| 45° | 397.8 | 284.7 | 219.0 | 186.1 | 175.2 | 186.1 | 219.0 | 273.7 | 368.6 | 434.3 | 485.4 |
| 47.5° | 343.1 | 240.9 | 182.5 | 153.3 | 146.0 | 156.9 | 182.5 | 229.9 | 310.2 | 375.9 | 434.3 |
| 50° | 299.3 | 211.7 | 156.9 | 131.4 | 124.1 | 135.0 | 156.9 | 193.4 | 262.8 | 321.2 | 383.2 |
| 52.5° | 270.1 | 197.1 | 138.7 | 113.1 | 109.5 | 116.8 | 135.0 | 164.2 | 222.6 | 273.7 | 332.1 |
| 55° | 262.8 | 197.1 | 127.7 | 102.2 | 98.5 | 105.8 | 120.4 | 142.3 | 193.4 | 237.2 | 288.3 |
| 57.5° | 270.1 | 211.7 | 120.4 | 87.6 | 83.9 | 91.2 | 105.8 | 124.1 | 167.9 | 204.4 | 251.8 |
| 60° | 270.1 | 215.3 | 105.8 | 69.3 | 65.7 | 73.0 | 87.6 | 109.5 | 149.6 | 178.8 | 219.0 |
| 62.5° | 244.5 | 197.1 | 87.6 | 54.7 | 47.4 | 54.7 | 73.0 | 91.2 | 131.4 | 160.6 | 193.4 |
| 65° | 211.7 | 167.9 | 73.0 | 40.1 | 32.8 | 40.1 | 58.4 | 76.6 | 113.1 | 138.7 | 175.2 |
| 67.5° | 171.5 | 127.7 | 54.7 | 29.2 | 21.9 | 29.2 | 43.8 | 62.0 | 94.9 | 120.4 | 156.9 |
| 70° | 127.7 | 91.2 | 43.8 | 25.5 | 21.9 | 25.5 | 40.1 | 58.4 | 83.9 | 109.5 | 146.0 |
| 72.5° | 94.9 | 62.0 | 36.5 | 25.5 | 18.2 | 25.5 | 36.5 | 54.7 | 80.3 | 105.8 | 138.7 |
| 75° | 80.3 | 51.1 | 32.8 | 21.9 | 18.2 | 21.9 | 32.8 | 51.1 | 73.0 | 98.5 | 131.4 |
| 77.5° | 76.6 | 47.4 | 29.2 | 18.2 | 14.6 | 18.2 | 29.2 | 43.8 | 65.7 | 91.2 | 127.7 |
| 80° | 65.7 | 40.1 | 25.5 | 14.6 | 10.9 | 14.6 | 25.5 | 36.5 | 51.1 | 69.3 | 98.5 |
| 82.5° | 51.1 | 32.8 | 18.2 | 7.3 | 3.6 | 7.3 | 18.2 | 21.9 | 32.8 | 40.1 | 58.4 |
| 85° | 32.8 | 18.2 | 7.3 | 0.0 | 0.0 | 0.0 | 7.3 | 14.6 | 14.6 | 18.2 | 29.2 |
| 87.5° | 14.6 | 3.6 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 3.6 | 7.3 | 10.9 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P643765

CATALOG NUMBER: GWS-SA6F-750-U-SLR-W-HSS

CANDELA DISTRIBUTION (continued):

| | 285° | 295° | 305° | 315° | 325° | 335° | 345° | 355° | 359° | 360° |
|-------|--------|--------|--------|--------|--------|--------|---------|---------|---------|---------|
| 0° | 1642.3 | 1642.3 | 1642.3 | 1642.3 | 1642.3 | 1642.3 | 1642.3 | 1642.3 | 1642.3 | 1642.3 |
| 2.5° | 1540.1 | 1543.7 | 1551.0 | 1562.0 | 1587.5 | 1609.4 | 1631.3 | 1660.5 | 1675.1 | 1675.1 |
| 5° | 1394.1 | 1397.8 | 1401.4 | 1416.0 | 1452.5 | 1481.7 | 1529.1 | 1587.5 | 1616.7 | 1624.0 |
| 7.5° | 1281.0 | 1288.3 | 1295.6 | 1306.5 | 1343.0 | 1383.2 | 1445.2 | 1554.7 | 1609.4 | 1620.4 |
| 10° | 1215.3 | 1226.2 | 1240.8 | 1262.7 | 1295.6 | 1339.4 | 1445.2 | 1642.3 | 1733.5 | 1751.8 |
| 12.5° | 1164.2 | 1182.4 | 1197.0 | 1222.6 | 1262.7 | 1332.1 | 1543.7 | 1890.4 | 2051.0 | 2094.8 |
| 15° | 1113.1 | 1135.0 | 1156.9 | 1182.4 | 1226.2 | 1357.6 | 1733.5 | 2335.7 | 2602.1 | 2634.9 |
| 17.5° | 1062.0 | 1087.5 | 1116.7 | 1145.9 | 1200.7 | 1419.7 | 2032.8 | 2952.4 | 3324.7 | 3397.7 |
| 20° | 1003.6 | 1036.5 | 1076.6 | 1113.1 | 1175.1 | 1518.2 | 2448.8 | 3686.0 | 4153.1 | 4310.1 |
| 22.5° | 941.6 | 981.7 | 1029.2 | 1076.6 | 1145.9 | 1638.6 | 2952.4 | 4474.3 | 5127.5 | 5229.7 |
| 25° | 890.5 | 930.6 | 974.4 | 1021.9 | 1098.5 | 1784.6 | 3561.9 | 5452.3 | 6047.2 | 6145.8 |
| 27.5° | 843.0 | 883.2 | 923.3 | 967.1 | 1051.1 | 1974.4 | 4295.5 | 6492.5 | 7112.9 | 7215.1 |
| 30° | 791.9 | 839.4 | 879.5 | 923.3 | 1007.3 | 2207.9 | 5142.1 | 7645.7 | 8233.3 | 8328.2 |
| 32.5° | 748.1 | 795.6 | 835.7 | 879.5 | 974.4 | 2463.4 | 6032.6 | 8667.6 | 9145.6 | 9145.6 |
| 35° | 711.7 | 762.7 | 791.9 | 850.3 | 948.9 | 2627.6 | 6875.7 | 9642.0 | 10003.3 | 9988.7 |
| 37.5° | 671.5 | 733.5 | 755.4 | 795.6 | 916.0 | 2645.9 | 7667.6 | 10671.1 | 10937.5 | 10842.7 |
| 40° | 631.4 | 697.1 | 729.9 | 751.8 | 879.5 | 2496.3 | 8536.2 | 11616.3 | 11842.6 | 11718.5 |
| 42.5° | 594.9 | 646.0 | 693.4 | 719.0 | 857.6 | 2233.5 | 9233.2 | 12627.3 | 12897.3 | 12787.8 |
| 45° | 558.4 | 602.2 | 631.4 | 678.8 | 872.2 | 2051.0 | 9831.7 | 13806.0 | 14280.5 | 14200.2 |
| 47.5° | 521.9 | 558.4 | 576.6 | 649.6 | 970.8 | 1967.1 | 10196.7 | 15630.8 | 16524.9 | 16459.2 |
| 50° | 481.7 | 525.5 | 525.5 | 642.3 | 1116.7 | 1996.3 | 10514.2 | 18273.0 | 19656.2 | 19634.3 |
| 52.5° | 441.6 | 489.0 | 481.7 | 697.1 | 1229.9 | 2131.3 | 10875.5 | 20605.1 | 23010.1 | 23210.8 |
| 55° | 401.4 | 445.2 | 452.5 | 806.5 | 1295.6 | 2248.1 | 9477.7 | 21586.8 | 25874.9 | 26579.3 |
| 57.5° | 357.7 | 383.2 | 470.8 | 890.5 | 1273.7 | 2587.5 | 6492.5 | 21765.6 | 27703.3 | 29214.2 |
| 60° | 310.2 | 332.1 | 532.8 | 872.2 | 1204.3 | 2390.4 | 4087.4 | 20159.8 | 27444.2 | 29360.2 |
| 62.5° | 270.1 | 306.6 | 562.0 | 770.0 | 1226.2 | 2072.9 | 2605.7 | 17181.8 | 24973.5 | 27159.6 |
| 65° | 237.2 | 295.6 | 510.9 | 697.1 | 1240.8 | 1405.1 | 1759.1 | 13977.6 | 22561.2 | 24641.4 |
| 67.5° | 211.7 | 328.5 | 419.7 | 620.4 | 1065.7 | 989.0 | 1208.0 | 10860.9 | 18970.1 | 20835.0 |
| 70° | 193.4 | 335.8 | 343.1 | 532.8 | 824.8 | 635.0 | 795.6 | 7309.9 | 13076.1 | 15207.5 |
| 72.5° | 175.2 | 248.2 | 259.1 | 427.0 | 532.8 | 386.8 | 514.6 | 4182.3 | 9532.5 | 10985.0 |
| 75° | 167.9 | 167.9 | 178.8 | 277.4 | 295.6 | 281.0 | 332.1 | 2496.3 | 6835.5 | 7897.5 |
| 77.5° | 156.9 | 127.7 | 113.1 | 178.8 | 160.6 | 200.7 | 197.1 | 1109.4 | 2963.4 | 3204.3 |
| 80° | 124.1 | 91.2 | 76.6 | 113.1 | 109.5 | 135.0 | 116.8 | 91.2 | 135.0 | 131.4 |
| 82.5° | 76.6 | 58.4 | 54.7 | 69.3 | 62.0 | 69.3 | 54.7 | 14.6 | 14.6 | 14.6 |
| 85° | 36.5 | 32.8 | 29.2 | 29.2 | 32.8 | 29.2 | 21.9 | 7.3 | 3.6 | 3.6 |
| 87.5° | 18.2 | 18.2 | 14.6 | 10.9 | 14.6 | 14.6 | 10.9 | 3.6 | 0.0 | 0.0 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



LM-79-2008: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGRAW-EDISON

Report Number: SP1-1908-441-4-R4

Test Date: 10/02/2019

Luminaire Tested: SA1C-750-U-5WQ

Data in this report applies to families of products SA1C-760-U-5WQ .


Test Information

Test Method: LM-79-2008
 Report Number: SP1-1908-441-4-R4
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 10/28/2024
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: McGRAW-EDISON
 Catalog Number: **SA1C-750-U-5WQ**
 Description: McGRAW EDISON ROADWAY AND AREA LUMINAIRE

THIS IS A REVISION OF SP1-1908-441-4-R3. TO UPDATE THE CATALOG INFORMATION.TESTED IN SITU. ROADWAY AND AREA LUMINAIRE. (1) 70 CRI, 5000K, 1050MA LIGHTSQUARE WITH 16 LEDS AND TYPE V WIDE OPTICS.

Spectral Parameters

| | | | | | |
|---------------------------|--------|-----------|------|------|-------|
| CCT (K): | 4884 | CRI (Ra): | 73.5 | R9: | -28.4 |
| CIE u': | 0.2101 | R1: | 70.5 | R10: | 48.6 |
| CIE v': | 0.4904 | R2: | 77.7 | R11: | 73.2 |
| Duv: | 0.0037 | R3: | 84.6 | R12: | 50.7 |
| CIE x: | 0.3493 | R4: | 74.7 | R13: | 71.2 |
| CIE y: | 0.3624 | R5: | 71.9 | R14: | 91.4 |
| CIE z: | 0.2884 | R6: | 70.7 | | |
| Peak Wavelength (nm): | 444 | R7: | 81.2 | | |
| Dominant Wavelength (nm): | 571 | R8: | 56.9 | | |
| Purity: | 13.7 | | | | |
| Rf: | 74.9 | | | | |
| Rg: | 96.3 | | | | |



Test Conditions

Stabilization Time: 240M
 Operation Time: 12H
 Room Temperature (°C) / RH%: 25.0./44%
 Sphere Temperature (°C): 25.7

REPORT NUMBER: SP1-1908-441-4-R4

| Measurement and Test Equipment | | | |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument | Identification Number | Calibration Date | Calibration Due Date |
| Photometer | IN0058 | 6/28/2019 | 12/28/2019 |
| Power Meter | IN0071 | 12/5/2018 | 12/5/2019 |
| AC Power Source | IN0063 | 12/5/2018 | 12/5/2019 |
| DC Power Source | IN0208 | 12/5/2018 | 12/5/2019 |
| Sphere Thermometer | IN0085 | 12/5/2018 | 12/5/2019 |
| Room Thermometer | IN0046 | 12/5/2018 | 12/5/2019 |

REPORT NUMBER: SP1-1908-441-4-R4

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 5000K 4-step quadrangle

REPORT NUMBER: SP1-1908-441-4-R4

Photopic Flux vs. Wavelength



#####

| λ (nm) | Power (μ W/nm) | Lumens (ϕ /nm) | λ (nm) | Power (μ W/nm) | Lumens (ϕ /nm) | λ (nm) | Power (μ W/nm) | Lumens (ϕ /nm) | λ (nm) | Power (μ W/nm) | Lumens (ϕ /nm) | λ (nm) | Power (μ W/nm) | Lumens (ϕ /nm) |
|-------------------|------------------------|-------------------------|-------------------|------------------------|-------------------------|-------------------|------------------------|-------------------------|-------------------|------------------------|-------------------------|-------------------|------------------------|-------------------------|
| 360 | 2945 | NR | 490 | 37941 | NR | 620 | 88803 | NR | 750 | 3908 | NR | 880 | 2997 | NR |
| 365 | 2596 | NR | 495 | 48525 | NR | 625 | 80578 | NR | 755 | 3988 | NR | 885 | 2927 | NR |
| 370 | 2732 | NR | 500 | 60609 | NR | 630 | 73127 | NR | 760 | 3335 | NR | 890 | 2649 | NR |
| 375 | 2894 | NR | 505 | 72036 | NR | 635 | 66244 | NR | 765 | 3438 | NR | 895 | 2828 | NR |
| 380 | 2822 | NR | 510 | 82168 | NR | 640 | 59440 | NR | 770 | 3427 | NR | 900 | 1407 | NR |
| 385 | 2394 | NR | 515 | 90898 | NR | 645 | 52864 | NR | 775 | 2759 | NR | 905 | 2224 | NR |
| 390 | 2370 | NR | 520 | 97142 | NR | 650 | 47085 | NR | 780 | 2340 | NR | 910 | 2905 | NR |
| 395 | 2267 | NR | 525 | 103255 | NR | 655 | 41789 | NR | 785 | 2412 | NR | 915 | 3350 | NR |
| 400 | 2262 | NR | 530 | 106697 | NR | 660 | 37064 | NR | 790 | 1999 | NR | 920 | 3114 | NR |
| 405 | 3000 | NR | 535 | 110081 | NR | 665 | 32299 | NR | 795 | 2054 | NR | 925 | 2834 | NR |
| 410 | 5324 | NR | 540 | 112494 | NR | 670 | 28142 | NR | 800 | 2331 | NR | 930 | 2271 | NR |
| 415 | 10725 | NR | 545 | 115513 | NR | 675 | 24505 | NR | 805 | 2648 | NR | 935 | 2228 | NR |
| 420 | 22128 | NR | 550 | 117203 | NR | 680 | 21162 | NR | 810 | 2485 | NR | 940 | 2833 | NR |
| 425 | 44095 | NR | 555 | 119753 | NR | 685 | 18400 | NR | 815 | 2409 | NR | 945 | 2941 | NR |
| 430 | 77002 | NR | 560 | 122602 | NR | 690 | 16065 | NR | 820 | 2221 | NR | 950 | 2323 | NR |
| 435 | 119881 | NR | 565 | 124314 | NR | 695 | 13860 | NR | 825 | 1562 | NR | 955 | 1667 | NR |
| 440 | 164454 | NR | 570 | 126775 | NR | 700 | 12177 | NR | 830 | 2249 | NR | 960 | 749 | NR |
| 445 | 179997 | NR | 575 | 127511 | NR | 705 | 10757 | NR | 835 | 2573 | NR | 965 | 2669 | NR |
| 450 | 142822 | NR | 580 | 127577 | NR | 710 | 9601 | NR | 840 | 2764 | NR | 970 | 3968 | NR |
| 455 | 90008 | NR | 585 | 126153 | NR | 715 | 8944 | NR | 845 | 3109 | NR | 975 | 3886 | NR |
| 460 | 60557 | NR | 590 | 123678 | NR | 720 | 7947 | NR | 850 | 2963 | NR | 980 | 2788 | NR |
| 465 | 43305 | NR | 595 | 119774 | NR | 725 | 7062 | NR | 855 | 2336 | NR | 985 | 3496 | NR |
| 470 | 31089 | NR | 600 | 115733 | NR | 730 | 6004 | NR | 860 | 2118 | NR | 990 | 2913 | NR |
| 475 | 26278 | NR | 605 | 109231 | NR | 735 | 5594 | NR | 865 | 3144 | NR | 995 | 4659 | NR |
| 480 | 27060 | NR | 610 | 102408 | NR | 740 | 5165 | NR | 870 | 3069 | NR | 1000 | 1308 | NR |
| 485 | 30698 | NR | 615 | 96015 | NR | 745 | 4687 | NR | 875 | 3311 | NR | | | |

REPORT NUMBER: SP1-1908-441-4-R4

Scotopic Flux vs. Wavelength




Scotopic Lumens: 13493.5 S/P: 1.77

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 2945 | NR | 490 | 37941 | NR | 620 | 88803 | NR | 750 | 3908 | NR | 880 | 2997 | NR |
| 365 | 2596 | NR | 495 | 48525 | NR | 625 | 80578 | NR | 755 | 3988 | NR | 885 | 2927 | NR |
| 370 | 2732 | NR | 500 | 60609 | NR | 630 | 73127 | NR | 760 | 3335 | NR | 890 | 2649 | NR |
| 375 | 2894 | NR | 505 | 72036 | NR | 635 | 66244 | NR | 765 | 3438 | NR | 895 | 2828 | NR |
| 380 | 2822 | NR | 510 | 82168 | NR | 640 | 59440 | NR | 770 | 3427 | NR | 900 | 1407 | NR |
| 385 | 2394 | NR | 515 | 90898 | NR | 645 | 52864 | NR | 775 | 2759 | NR | 905 | 2224 | NR |
| 390 | 2370 | NR | 520 | 97142 | NR | 650 | 47085 | NR | 780 | 2340 | NR | 910 | 2905 | NR |
| 395 | 2267 | NR | 525 | 103255 | NR | 655 | 41789 | NR | 785 | 2412 | NR | 915 | 3350 | NR |
| 400 | 2262 | NR | 530 | 106697 | NR | 660 | 37064 | NR | 790 | 1999 | NR | 920 | 3114 | NR |
| 405 | 3000 | NR | 535 | 110081 | NR | 665 | 32299 | NR | 795 | 2054 | NR | 925 | 2834 | NR |
| 410 | 5324 | NR | 540 | 112494 | NR | 670 | 28142 | NR | 800 | 2331 | NR | 930 | 2271 | NR |
| 415 | 10725 | NR | 545 | 115513 | NR | 675 | 24505 | NR | 805 | 2648 | NR | 935 | 2228 | NR |
| 420 | 22128 | NR | 550 | 117203 | NR | 680 | 21162 | NR | 810 | 2485 | NR | 940 | 2833 | NR |
| 425 | 44095 | NR | 555 | 119753 | NR | 685 | 18400 | NR | 815 | 2409 | NR | 945 | 2941 | NR |
| 430 | 77002 | NR | 560 | 122602 | NR | 690 | 16065 | NR | 820 | 2221 | NR | 950 | 2323 | NR |
| 435 | 119881 | NR | 565 | 124314 | NR | 695 | 13860 | NR | 825 | 1562 | NR | 955 | 1667 | NR |
| 440 | 164454 | NR | 570 | 126775 | NR | 700 | 12177 | NR | 830 | 2249 | NR | 960 | 749 | NR |
| 445 | 179997 | NR | 575 | 127511 | NR | 705 | 10757 | NR | 835 | 2573 | NR | 965 | 2669 | NR |
| 450 | 142822 | NR | 580 | 127577 | NR | 710 | 9601 | NR | 840 | 2764 | NR | 970 | 3968 | NR |
| 455 | 90008 | NR | 585 | 126153 | NR | 715 | 8944 | NR | 845 | 3109 | NR | 975 | 3886 | NR |
| 460 | 60557 | NR | 590 | 123678 | NR | 720 | 7947 | NR | 850 | 2963 | NR | 980 | 2788 | NR |
| 465 | 43305 | NR | 595 | 119774 | NR | 725 | 7062 | NR | 855 | 2336 | NR | 985 | 3496 | NR |
| 470 | 31089 | NR | 600 | 115733 | NR | 730 | 6004 | NR | 860 | 2118 | NR | 990 | 2913 | NR |
| 475 | 26278 | NR | 605 | 109231 | NR | 735 | 5594 | NR | 865 | 3144 | NR | 995 | 4659 | NR |
| 480 | 27060 | NR | 610 | 102408 | NR | 740 | 5165 | NR | 870 | 3069 | NR | 1000 | 1308 | NR |
| 485 | 30698 | NR | 615 | 96015 | NR | 745 | 4687 | NR | 875 | 3311 | NR | | | |

REPORT NUMBER: SP1-1908-441-4-R4

Melanopic Flux vs. Wavelength



Melanopic Lumens: 5378.9 M/P: 0.71

| λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) |
|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|
| 360 | 2945 | NR | 490 | 37941 | NR | 620 | 88803 | NR | 750 | 3908 | NR | 880 | 2997 | NR |
| 365 | 2596 | NR | 495 | 48525 | NR | 625 | 80578 | NR | 755 | 3988 | NR | 885 | 2927 | NR |
| 370 | 2732 | NR | 500 | 60609 | NR | 630 | 73127 | NR | 760 | 3335 | NR | 890 | 2649 | NR |
| 375 | 2894 | NR | 505 | 72036 | NR | 635 | 66244 | NR | 765 | 3438 | NR | 895 | 2828 | NR |
| 380 | 2822 | NR | 510 | 82168 | NR | 640 | 59440 | NR | 770 | 3427 | NR | 900 | 1407 | NR |
| 385 | 2394 | NR | 515 | 90898 | NR | 645 | 52864 | NR | 775 | 2759 | NR | 905 | 2224 | NR |
| 390 | 2370 | NR | 520 | 97142 | NR | 650 | 47085 | NR | 780 | 2340 | NR | 910 | 2905 | NR |
| 395 | 2267 | NR | 525 | 103255 | NR | 655 | 41789 | NR | 785 | 2412 | NR | 915 | 3350 | NR |
| 400 | 2262 | NR | 530 | 106697 | NR | 660 | 37064 | NR | 790 | 1999 | NR | 920 | 3114 | NR |
| 405 | 3000 | NR | 535 | 110081 | NR | 665 | 32299 | NR | 795 | 2054 | NR | 925 | 2834 | NR |
| 410 | 5324 | NR | 540 | 112494 | NR | 670 | 28142 | NR | 800 | 2331 | NR | 930 | 2271 | NR |
| 415 | 10725 | NR | 545 | 115513 | NR | 675 | 24505 | NR | 805 | 2648 | NR | 935 | 2228 | NR |
| 420 | 22128 | NR | 550 | 117203 | NR | 680 | 21162 | NR | 810 | 2485 | NR | 940 | 2833 | NR |
| 425 | 44095 | NR | 555 | 119753 | NR | 685 | 18400 | NR | 815 | 2409 | NR | 945 | 2941 | NR |
| 430 | 77002 | NR | 560 | 122602 | NR | 690 | 16065 | NR | 820 | 2221 | NR | 950 | 2323 | NR |
| 435 | 119881 | NR | 565 | 124314 | NR | 695 | 13860 | NR | 825 | 1562 | NR | 955 | 1667 | NR |
| 440 | 164454 | NR | 570 | 126775 | NR | 700 | 12177 | NR | 830 | 2249 | NR | 960 | 749 | NR |
| 445 | 179997 | NR | 575 | 127511 | NR | 705 | 10757 | NR | 835 | 2573 | NR | 965 | 2669 | NR |
| 450 | 142822 | NR | 580 | 127577 | NR | 710 | 9601 | NR | 840 | 2764 | NR | 970 | 3968 | NR |
| 455 | 90008 | NR | 585 | 126153 | NR | 715 | 8944 | NR | 845 | 3109 | NR | 975 | 3886 | NR |
| 460 | 60557 | NR | 590 | 123678 | NR | 720 | 7947 | NR | 850 | 2963 | NR | 980 | 2788 | NR |
| 465 | 43305 | NR | 595 | 119774 | NR | 725 | 7062 | NR | 855 | 2336 | NR | 985 | 3496 | NR |
| 470 | 31089 | NR | 600 | 115733 | NR | 730 | 6004 | NR | 860 | 2118 | NR | 990 | 2913 | NR |
| 475 | 26278 | NR | 605 | 109231 | NR | 735 | 5594 | NR | 865 | 3144 | NR | 995 | 4659 | NR |
| 480 | 27060 | NR | 610 | 102408 | NR | 740 | 5165 | NR | 870 | 3069 | NR | 1000 | 1308 | NR |
| 485 | 30698 | NR | 615 | 96015 | NR | 745 | 4687 | NR | 875 | 3311 | NR | | | |

REPORT NUMBER: SP1-1908-441-4-R4



TM-30-18

Summary

$R_f = 74.9$
 $R_g = 96.3$
 CIE $R_a = 73.5$
 $R_g = -28.4$



Color Vector Graphics



REPORT NUMBER: SP1-1908-441-4-R4

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)

| | | | |
|------------|------------|------------|------------|
| CES01 = 85 | CES26 = 61 | CES51 = 90 | CES76 = 52 |
| CES02 = 60 | CES27 = 84 | CES52 = 91 | CES77 = 71 |
| CES03 = 30 | CES28 = 81 | CES53 = 79 | CES78 = 54 |
| CES04 = 69 | CES29 = 58 | CES54 = 83 | CES79 = 80 |
| CES05 = 46 | CES30 = 67 | CES55 = 83 | CES80 = 77 |
| CES06 = 50 | CES31 = 63 | CES56 = 73 | CES81 = 77 |
| CES07 = 39 | CES32 = 59 | CES57 = 72 | CES82 = 90 |
| CES08 = 38 | CES33 = 69 | CES58 = 73 | CES83 = 86 |
| CES09 = 29 | CES34 = 69 | CES59 = 88 | CES84 = 88 |
| CES10 = 73 | CES35 = 83 | CES60 = 93 | CES85 = 84 |
| CES11 = 56 | CES36 = 95 | CES61 = 88 | CES86 = 75 |
| CES12 = 61 | CES37 = 78 | CES62 = 85 | CES87 = 78 |
| CES13 = 41 | CES38 = 76 | CES63 = 77 | CES88 = 79 |
| CES14 = 74 | CES39 = 93 | CES64 = 74 | CES89 = 75 |
| CES15 = 70 | CES40 = 86 | CES65 = 67 | CES90 = 77 |
| CES16 = 46 | CES41 = 87 | CES66 = 69 | CES91 = 89 |
| CES17 = 49 | CES42 = 78 | CES67 = 67 | CES92 = 66 |
| CES18 = 55 | CES43 = 75 | CES68 = 73 | CES93 = 80 |
| CES19 = 71 | CES44 = 99 | CES69 = 81 | CES94 = 57 |
| CES20 = 64 | CES45 = 83 | CES70 = 63 | CES95 = 71 |
| CES21 = 85 | CES46 = 81 | CES71 = 60 | CES96 = 78 |
| CES22 = 77 | CES47 = 80 | CES72 = 86 | CES97 = 85 |
| CES23 = 91 | CES48 = 72 | CES73 = 53 | CES98 = 75 |
| CES24 = 90 | CES49 = 81 | CES74 = 96 | CES99 = 62 |
| CES25 = 71 | CES50 = 89 | CES75 = 58 | |



REPORT NUMBER: SP1-1908-441-4-R4

TM-30-18



Color Rendition by Hue-Angle Bin



REPORT NUMBER: SP1-1908-441-4-R4

TM-30-18

Measure Comparisons



(END OF REPORT)