

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: McGRAW-EDISON

Report Number: P629406

Luminaire Tested: GWS-SA1B-750-U-SLL-W-GRSBK

Issue Date: 1/10/2023

Test Information

Test Method: LM-79-2019
Report Number: P629406
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2209-782-38)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/10/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: McGRAW-EDISON
Catalog Number: GWS-SA1B-750-U-SLL-W-GRSBK
Description: GALLEON WALL SLIM LUMINAIRE. (1) LIGHTSQUARES WITH 16 LEDS EACH AND SPILL LIGHT ELIMINATOR LEFT OPTICS W/ FACTORY INSTALLED GLARE SHIELD, BK
Light Source: (16) 5000K CCT, 70 CRI LEDS
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1965.9 lumens
Efficiency: N/A
Efficacy: 78.6 lumens/watt
Luminous Opening: Rectangular (W 0.5' x L: 0.5' x H: 0')
IES Classification: Type III - Short
BUG Rating: B1 - U0 - G0


Input Watts (W): 25
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 0
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT



REPORT NUMBER: P629406
 CATALOG NUMBER: GWS-SA1B-750-U-SLL-W-GRSBK

Iso-Footcandle Lines of Horizontal Illumination


× Max cd
 - - - 1/2 Max cd



Based on 10 foot mounting height. Maximum calculated value = 5.2 fc
 Type III - Short - N/A

REPORT NUMBER: P629406
CATALOG NUMBER: GWS-SA1B-750-U-SLL-W-GRSBK

Luminous Intensity Polar Plot



— Vertical Plane Through 315-Deg Lateral - - - Horizontal Cone Through 57.5-Deg Vertical

REPORT NUMBER: P629406
 CATALOG NUMBER: GWS-SA1B-750-U-SLL-W-GRSBK


FLUX DISTRIBUTION:

| | | Downward | Upward | Total |
|--------------------|-----------|----------|--------|--------|
| House Side | Lumens | 423.5 | 0.0 | 423.5 |
| | % Fixture | 21.5 | 0.0 | 21.5 |
| Street Side | Lumens | 1542.4 | 0.0 | 1542.4 |
| | % Fixture | 78.5 | 0.0 | 78.5 |
| Total | Lumens | 1965.9 | 0.0 | 1965.9 |
| | % Fixture | 100.0 | 0.0 | 100.0 |

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 33.0 | 1.7 |
| 10°-20° | 108.6 | 5.5 |
| 20°-30° | 176.3 | 9.0 |
| 30°-40° | 270.6 | 13.8 |
| 40°-50° | 432.1 | 22.0 |
| 50°-60° | 605.1 | 30.8 |
| 60°-70° | 310.2 | 15.8 |
| 70°-80° | 29.9 | 1.5 |
| 80°-90° | 0.0 | 0.0 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-90° | 1965.9 | 100.0 |
| 0°-180° | 1965.9 | 100.0 |

Coefficient of Utilization



REPORT NUMBER: P629406


CATALOG NUMBER: GWS-SA1B-750-U-SLL-W-GRSBK

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

| Zone | Lumens | % Fixture | Zone Rating/Lumen Limit | | |
|----------------|--------|-----------|-------------------------|------|--------|
| | | | B | U | G |
| FL (0°-30°) | 194.6 | 9.9 | | | |
| FM (30°-60°) | 1039.6 | 52.9 | | | |
| FH (60°-80°) | 308.1 | 15.7 | | | G0/660 |
| FVH (80°-90°) | 0.0 | 0.0 | | | G0/10 |
| BL (0°-30°) | 123.3 | 6.3 | B1/500 | | |
| BM (30°-60°) | 268.2 | 13.6 | B1/1000 | | |
| BH (60°-80°) | 32.0 | 1.6 | B0/110 | | G0/110 |
| BVH (80°-90°) | 0.0 | 0.0 | | | G0/10 |
| UL (90°-100°) | 0.0 | 0.0 | | U0/0 | |
| UH (100°-180°) | 0.0 | 0.0 | | U0/0 | |

BUG Rating: B1-U0-G0

Type III Short





REPORT NUMBER: P629406

CATALOG NUMBER: GWS-SA1B-750-U-SLL-W-GRSBK

CANDELA DISTRIBUTION (FULL):

| | 0° | 1° | 5° | 15° | 25° | 35° | 45° | 55° | 65° | 75° | 85° |
|-------|--------|--------|--------|-------|-------|-------|-------|-------|-------|-------|-------|
| 0° | 334.0 | 334.0 | 334.0 | 334.0 | 334.0 | 334.0 | 334.0 | 334.0 | 334.0 | 334.0 | 334.0 |
| 2.5° | 371.1 | 370.3 | 367.7 | 358.7 | 353.2 | 344.5 | 338.2 | 330.1 | 321.2 | 315.6 | 310.1 |
| 5° | 410.5 | 408.4 | 401.3 | 380.8 | 365.0 | 348.0 | 334.3 | 319.3 | 303.3 | 292.8 | 283.0 |
| 7.5° | 448.4 | 445.2 | 435.7 | 401.1 | 377.1 | 352.7 | 333.2 | 311.4 | 288.8 | 273.1 | 261.0 |
| 10° | 485.4 | 478.3 | 463.3 | 420.8 | 388.4 | 359.0 | 336.1 | 311.2 | 284.6 | 264.7 | 251.2 |
| 12.5° | 515.9 | 510.6 | 490.1 | 439.4 | 397.9 | 360.3 | 332.2 | 309.1 | 291.2 | 277.8 | 265.4 |
| 15° | 542.2 | 536.4 | 517.0 | 456.2 | 406.0 | 355.1 | 315.6 | 295.4 | 298.3 | 303.5 | 293.0 |
| 17.5° | 566.4 | 560.3 | 539.3 | 470.2 | 409.2 | 342.2 | 292.5 | 282.8 | 298.8 | 318.5 | 314.6 |
| 20° | 591.3 | 584.5 | 558.7 | 481.5 | 408.1 | 321.9 | 269.1 | 272.0 | 294.6 | 317.2 | 319.3 |
| 22.5° | 620.5 | 613.4 | 583.4 | 495.9 | 407.4 | 297.8 | 248.9 | 262.6 | 286.7 | 305.9 | 309.6 |
| 25° | 659.1 | 650.7 | 617.9 | 517.2 | 409.5 | 275.7 | 234.4 | 253.4 | 273.3 | 290.7 | 292.8 |
| 27.5° | 710.1 | 699.3 | 657.6 | 543.5 | 413.9 | 258.3 | 228.1 | 240.7 | 256.2 | 271.7 | 273.6 |
| 30° | 776.6 | 762.9 | 703.0 | 566.4 | 411.8 | 246.3 | 223.9 | 228.1 | 237.3 | 249.9 | 250.2 |
| 32.5° | 854.4 | 835.7 | 754.0 | 586.1 | 393.7 | 237.3 | 218.1 | 215.2 | 217.3 | 227.1 | 228.9 |
| 35° | 945.9 | 921.7 | 810.3 | 604.7 | 360.6 | 220.0 | 207.6 | 197.9 | 197.1 | 201.8 | 206.3 |
| 37.5° | 1050.7 | 1021.8 | 881.2 | 628.6 | 321.4 | 201.8 | 192.1 | 182.4 | 178.2 | 180.6 | 187.4 |
| 40° | 1147.4 | 1115.4 | 955.3 | 657.6 | 281.5 | 185.5 | 174.0 | 164.0 | 159.0 | 159.8 | 168.2 |
| 42.5° | 1261.0 | 1227.9 | 1046.0 | 695.4 | 248.4 | 174.5 | 155.1 | 144.8 | 138.2 | 141.9 | 151.6 |
| 45° | 1433.4 | 1395.8 | 1178.2 | 728.3 | 222.1 | 171.9 | 138.5 | 124.0 | 120.9 | 127.2 | 138.8 |
| 47.5° | 1668.9 | 1622.9 | 1359.8 | 748.2 | 199.7 | 174.2 | 126.9 | 107.2 | 108.0 | 115.1 | 126.7 |
| 50° | 1902.5 | 1852.8 | 1569.8 | 721.9 | 181.3 | 169.5 | 121.2 | 94.1 | 99.1 | 105.4 | 115.9 |
| 52.5° | 2063.1 | 1998.4 | 1672.0 | 646.0 | 164.5 | 151.6 | 120.6 | 81.7 | 91.2 | 93.3 | 102.2 |
| 55° | 2069.4 | 1989.8 | 1619.7 | 509.3 | 141.7 | 128.0 | 115.1 | 71.5 | 82.5 | 83.3 | 90.9 |
| 57.5° | 1813.9 | 1741.9 | 1415.5 | 349.8 | 125.9 | 93.8 | 91.7 | 62.5 | 67.8 | 74.4 | 79.1 |
| 60° | 1380.0 | 1318.8 | 1058.6 | 160.3 | 95.7 | 59.7 | 62.8 | 53.9 | 50.7 | 60.4 | 65.2 |
| 62.5° | 845.2 | 806.0 | 635.0 | 71.0 | 61.0 | 31.8 | 38.1 | 42.8 | 38.1 | 41.8 | 45.7 |
| 65° | 335.6 | 318.3 | 241.0 | 30.2 | 25.0 | 16.0 | 17.3 | 25.0 | 26.8 | 29.4 | 33.1 |
| 67.5° | 58.3 | 55.2 | 40.5 | 13.4 | 10.2 | 9.7 | 8.4 | 11.6 | 16.3 | 18.1 | 21.0 |
| 70° | 7.6 | 7.4 | 6.6 | 5.5 | 5.3 | 4.7 | 3.7 | 7.4 | 11.0 | 11.6 | 13.4 |
| 72.5° | 1.8 | 1.6 | 1.6 | 1.3 | 1.6 | 0.5 | 0.5 | 3.9 | 7.9 | 8.1 | 9.5 |
| 75° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 1.3 | 5.0 | 5.5 | 6.6 |
| 77.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.3 |
| 80° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 82.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 85° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 87.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P629406

CATALOG NUMBER: GWS-SA1B-750-U-SLL-W-GRSBK

CANDELA DISTRIBUTION (continued):

| | 90° | 95° | 105° | 115° | 125° | 135° | 145° | 155° | 165° | 175° | 180° |
|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|
| 0° | 334.0 | 334.0 | 334.0 | 334.0 | 334.0 | 334.0 | 334.0 | 334.0 | 334.0 | 334.0 | 334.0 |
| 2.5° | 305.7 | 300.4 | 298.6 | 295.9 | 292.5 | 293.6 | 288.8 | 287.3 | 289.6 | 292.8 | 292.0 |
| 5° | 277.8 | 272.0 | 268.1 | 262.0 | 261.0 | 258.6 | 257.0 | 254.9 | 257.6 | 261.2 | 262.0 |
| 7.5° | 255.7 | 250.7 | 246.8 | 244.9 | 243.6 | 242.6 | 239.4 | 237.8 | 237.8 | 239.4 | 240.7 |
| 10° | 246.3 | 242.6 | 241.8 | 242.3 | 244.4 | 244.2 | 241.3 | 239.2 | 236.5 | 235.2 | 236.8 |
| 12.5° | 259.4 | 253.4 | 252.3 | 252.6 | 255.2 | 254.9 | 251.8 | 249.1 | 248.6 | 249.1 | 254.1 |
| 15° | 281.7 | 272.5 | 265.7 | 264.4 | 265.7 | 265.2 | 262.8 | 261.2 | 262.0 | 269.6 | 278.1 |
| 17.5° | 301.7 | 287.5 | 275.2 | 270.4 | 270.2 | 269.4 | 267.0 | 266.5 | 270.4 | 284.6 | 297.0 |
| 20° | 307.5 | 293.6 | 276.0 | 269.9 | 268.6 | 267.8 | 265.2 | 266.0 | 271.0 | 288.0 | 298.6 |
| 22.5° | 299.9 | 286.5 | 268.1 | 262.0 | 261.0 | 260.7 | 258.1 | 259.1 | 263.3 | 278.3 | 287.0 |
| 25° | 285.4 | 274.1 | 254.9 | 249.7 | 249.7 | 249.1 | 246.8 | 247.3 | 249.9 | 263.1 | 271.5 |
| 27.5° | 267.8 | 257.0 | 241.0 | 235.7 | 236.5 | 237.3 | 234.4 | 233.6 | 235.7 | 248.1 | 253.1 |
| 30° | 247.6 | 239.9 | 227.3 | 222.6 | 222.3 | 225.5 | 221.6 | 220.5 | 223.4 | 233.1 | 234.2 |
| 32.5° | 227.9 | 224.2 | 215.2 | 211.6 | 211.8 | 212.4 | 210.3 | 210.3 | 212.9 | 218.1 | 217.9 |
| 35° | 208.7 | 206.3 | 204.7 | 202.1 | 201.8 | 200.8 | 200.8 | 201.3 | 204.2 | 206.0 | 202.6 |
| 37.5° | 190.3 | 192.6 | 194.5 | 191.9 | 189.8 | 189.8 | 189.8 | 192.1 | 194.7 | 194.0 | 188.2 |
| 40° | 174.0 | 179.0 | 184.8 | 181.9 | 176.9 | 176.6 | 177.7 | 181.6 | 185.5 | 180.8 | 175.6 |
| 42.5° | 160.1 | 166.4 | 174.5 | 172.9 | 167.4 | 166.6 | 167.4 | 172.4 | 175.6 | 169.5 | 163.7 |
| 45° | 146.4 | 154.3 | 164.0 | 164.0 | 158.0 | 157.2 | 157.4 | 164.0 | 165.8 | 158.7 | 151.4 |
| 47.5° | 134.8 | 143.5 | 153.7 | 153.7 | 148.8 | 147.2 | 148.5 | 155.3 | 156.6 | 146.6 | 139.8 |
| 50° | 123.8 | 133.2 | 144.5 | 143.8 | 140.3 | 139.0 | 141.4 | 148.8 | 147.2 | 136.1 | 129.0 |
| 52.5° | 109.9 | 119.8 | 135.3 | 136.1 | 134.3 | 134.6 | 137.5 | 142.2 | 137.7 | 124.3 | 118.3 |
| 55° | 97.2 | 107.5 | 123.0 | 127.2 | 127.2 | 126.9 | 128.3 | 131.9 | 128.3 | 112.2 | 104.9 |
| 57.5° | 83.6 | 92.2 | 105.1 | 106.2 | 107.0 | 104.1 | 105.9 | 110.9 | 109.1 | 95.4 | 91.2 |
| 60° | 68.6 | 76.0 | 83.3 | 84.1 | 80.7 | 74.6 | 78.1 | 83.8 | 85.2 | 74.9 | 70.2 |
| 62.5° | 48.6 | 55.7 | 64.4 | 64.4 | 61.0 | 54.9 | 59.4 | 64.4 | 62.5 | 52.0 | 49.1 |
| 65° | 36.3 | 42.8 | 49.4 | 52.3 | 49.4 | 45.2 | 48.6 | 52.3 | 49.4 | 40.7 | 36.5 |
| 67.5° | 23.4 | 27.9 | 31.8 | 34.2 | 34.7 | 34.2 | 35.7 | 34.7 | 31.3 | 25.5 | 23.1 |
| 70° | 14.2 | 16.6 | 18.7 | 20.8 | 22.3 | 23.1 | 23.9 | 21.6 | 18.1 | 15.0 | 14.2 |
| 72.5° | 10.2 | 12.4 | 14.2 | 15.8 | 17.6 | 18.1 | 18.1 | 16.6 | 13.4 | 10.5 | 9.7 |
| 75° | 7.1 | 8.9 | 10.5 | 11.6 | 13.1 | 13.7 | 13.7 | 12.4 | 10.0 | 7.6 | 6.8 |
| 77.5° | 0.3 | 1.8 | 1.8 | 1.6 | 2.1 | 2.6 | 2.6 | 3.2 | 2.9 | 2.1 | 1.8 |
| 80° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 82.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 85° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 87.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P629406

CATALOG NUMBER: GWS-SA1B-750-U-SLL-W-GRSBK

CANDELA DISTRIBUTION (continued):

| | 185° | 195° | 205° | 215° | 225° | 235° | 245° | 255° | 265° | 270° | 275° |
|-------|-------|-------|-------|-------|-------|-------|-------|-------|--------|--------|--------|
| 0° | 334.0 | 334.0 | 334.0 | 334.0 | 334.0 | 334.0 | 334.0 | 334.0 | 334.0 | 334.0 | 334.0 |
| 2.5° | 293.6 | 303.0 | 305.7 | 315.4 | 324.0 | 332.7 | 343.2 | 349.5 | 359.0 | 365.6 | 369.3 |
| 5° | 264.7 | 272.5 | 282.0 | 296.5 | 311.4 | 328.0 | 348.0 | 365.3 | 387.1 | 403.2 | 408.4 |
| 7.5° | 243.6 | 253.9 | 264.9 | 283.0 | 303.5 | 325.6 | 353.7 | 382.1 | 415.5 | 437.3 | 451.3 |
| 10° | 239.7 | 250.2 | 264.9 | 282.8 | 304.3 | 329.6 | 364.0 | 400.8 | 442.6 | 469.1 | 484.9 |
| 12.5° | 258.6 | 269.9 | 276.2 | 284.4 | 300.7 | 328.8 | 372.9 | 419.7 | 468.9 | 497.8 | 514.6 |
| 15° | 286.5 | 296.5 | 286.2 | 276.0 | 286.5 | 320.4 | 377.9 | 435.5 | 492.0 | 525.4 | 542.7 |
| 17.5° | 305.7 | 306.4 | 284.1 | 262.3 | 265.2 | 305.1 | 379.8 | 451.3 | 516.7 | 551.6 | 569.8 |
| 20° | 303.8 | 297.5 | 274.9 | 250.7 | 241.8 | 285.4 | 377.7 | 465.2 | 541.7 | 578.2 | 596.1 |
| 22.5° | 289.6 | 282.3 | 263.1 | 239.4 | 222.1 | 262.0 | 374.0 | 477.8 | 564.5 | 606.0 | 622.9 |
| 25° | 272.5 | 264.7 | 248.9 | 228.1 | 209.5 | 239.4 | 371.1 | 495.1 | 593.4 | 642.3 | 655.5 |
| 27.5° | 252.6 | 245.7 | 232.3 | 217.3 | 204.2 | 222.3 | 370.3 | 518.0 | 628.4 | 686.5 | 695.7 |
| 30° | 233.1 | 226.8 | 216.3 | 207.6 | 202.1 | 212.4 | 367.7 | 542.4 | 670.2 | 737.2 | 747.2 |
| 32.5° | 214.5 | 208.1 | 201.6 | 200.3 | 200.5 | 208.7 | 358.7 | 566.6 | 719.8 | 810.8 | 818.1 |
| 35° | 198.4 | 191.1 | 188.4 | 191.6 | 197.4 | 202.4 | 333.5 | 586.6 | 773.2 | 890.9 | 897.0 |
| 37.5° | 183.2 | 175.8 | 175.6 | 183.2 | 189.5 | 192.6 | 303.8 | 606.3 | 845.2 | 972.4 | 980.0 |
| 40° | 169.3 | 161.9 | 164.5 | 173.7 | 178.7 | 180.3 | 267.8 | 636.3 | 921.4 | 1058.3 | 1054.1 |
| 42.5° | 157.4 | 149.8 | 151.4 | 163.2 | 167.7 | 171.9 | 234.7 | 661.2 | 994.7 | 1139.8 | 1138.5 |
| 45° | 145.9 | 140.1 | 139.0 | 151.9 | 155.8 | 172.7 | 210.5 | 680.4 | 1089.1 | 1243.6 | 1245.7 |
| 47.5° | 134.6 | 130.1 | 130.4 | 135.9 | 145.6 | 176.6 | 190.0 | 693.0 | 1226.0 | 1408.2 | 1371.6 |
| 50° | 124.3 | 120.9 | 123.8 | 117.5 | 139.0 | 171.6 | 172.4 | 690.4 | 1379.0 | 1565.8 | 1492.5 |
| 52.5° | 113.0 | 112.2 | 113.5 | 98.3 | 128.5 | 151.4 | 155.8 | 655.5 | 1450.7 | 1673.6 | 1631.8 |
| 55° | 101.4 | 101.2 | 90.7 | 78.6 | 107.5 | 120.9 | 133.5 | 546.9 | 1448.4 | 1730.9 | 1781.6 |
| 57.5° | 87.8 | 85.7 | 68.9 | 64.1 | 83.6 | 84.1 | 121.7 | 358.2 | 1283.6 | 1593.7 | 1698.8 |
| 60° | 66.5 | 64.9 | 50.5 | 52.0 | 58.3 | 53.9 | 97.0 | 178.5 | 959.3 | 1241.5 | 1360.1 |
| 62.5° | 46.0 | 43.9 | 37.6 | 40.2 | 37.6 | 30.7 | 59.4 | 88.3 | 581.1 | 784.0 | 891.5 |
| 65° | 33.6 | 31.3 | 25.8 | 22.1 | 17.6 | 17.6 | 22.6 | 33.9 | 225.0 | 333.2 | 401.8 |
| 67.5° | 20.8 | 19.7 | 15.2 | 11.0 | 10.8 | 11.6 | 11.8 | 16.8 | 36.3 | 57.8 | 70.7 |
| 70° | 13.4 | 12.4 | 10.2 | 7.1 | 6.6 | 6.8 | 7.1 | 7.9 | 9.2 | 10.0 | 12.1 |
| 72.5° | 9.2 | 8.7 | 7.4 | 3.9 | 3.2 | 3.4 | 3.7 | 3.7 | 4.5 | 4.2 | 5.0 |
| 75° | 6.6 | 6.0 | 5.3 | 1.8 | 1.1 | 1.3 | 1.6 | 1.3 | 1.6 | 1.1 | 1.3 |
| 77.5° | 1.8 | 1.8 | 1.3 | 0.3 | 0.0 | 0.3 | 0.5 | 0.5 | 0.3 | 0.0 | 0.0 |
| 80° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.3 | 0.3 | 0.0 | 0.0 | 0.0 |
| 82.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 85° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 87.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P629406

CATALOG NUMBER: GWS-SA1B-750-U-SLL-W-GRSBK

CANDELA DISTRIBUTION (continued):

| | 285° | 295° | 305° | 315° | 325° | 335° | 345° | 355° | 359° | 360° |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 334.0 | 334.0 | 334.0 | 334.0 | 334.0 | 334.0 | 334.0 | 334.0 | 334.0 | 334.0 |
| 2.5° | 378.7 | 384.8 | 387.1 | 383.7 | 386.6 | 381.9 | 380.0 | 372.9 | 372.4 | 371.1 |
| 5° | 429.7 | 443.4 | 451.5 | 456.5 | 450.7 | 444.4 | 435.0 | 418.7 | 413.7 | 410.5 |
| 7.5° | 479.9 | 501.2 | 515.1 | 521.7 | 520.1 | 507.2 | 490.1 | 462.8 | 453.1 | 448.4 |
| 10° | 523.5 | 549.5 | 566.4 | 574.5 | 571.1 | 559.8 | 535.4 | 501.2 | 488.3 | 485.4 |
| 12.5° | 554.0 | 577.9 | 589.5 | 596.6 | 596.8 | 592.4 | 569.3 | 534.8 | 519.6 | 515.9 |
| 15° | 573.2 | 583.4 | 583.7 | 587.9 | 595.3 | 605.3 | 594.5 | 564.0 | 547.7 | 542.2 |
| 17.5° | 585.3 | 574.0 | 562.4 | 563.5 | 575.6 | 602.1 | 613.1 | 589.8 | 572.4 | 566.4 |
| 20° | 594.0 | 558.2 | 536.7 | 536.9 | 549.3 | 589.5 | 626.0 | 614.7 | 596.8 | 591.3 |
| 22.5° | 599.5 | 544.3 | 513.5 | 512.7 | 525.9 | 574.5 | 637.8 | 644.4 | 626.8 | 620.5 |
| 25° | 610.8 | 537.7 | 499.6 | 504.1 | 515.6 | 569.8 | 653.9 | 683.8 | 667.5 | 659.1 |
| 27.5° | 631.0 | 544.3 | 498.3 | 508.5 | 521.7 | 583.7 | 681.7 | 736.4 | 719.6 | 710.1 |
| 30° | 666.0 | 569.0 | 518.5 | 532.7 | 548.5 | 620.2 | 728.5 | 809.7 | 785.5 | 776.6 |
| 32.5° | 722.2 | 620.2 | 581.1 | 611.6 | 626.8 | 680.2 | 798.7 | 892.0 | 872.3 | 854.4 |
| 35° | 799.7 | 737.2 | 732.7 | 803.7 | 800.0 | 793.7 | 884.9 | 992.9 | 963.2 | 945.9 |
| 37.5° | 906.4 | 925.4 | 958.5 | 1028.9 | 1026.5 | 978.5 | 998.2 | 1088.3 | 1073.1 | 1050.7 |
| 40° | 1039.7 | 1079.9 | 1136.1 | 1237.1 | 1205.5 | 1145.1 | 1137.2 | 1186.1 | 1173.7 | 1147.4 |
| 42.5° | 1118.3 | 1187.7 | 1294.9 | 1385.6 | 1360.3 | 1254.7 | 1245.7 | 1316.7 | 1289.6 | 1261.0 |
| 45° | 1154.8 | 1275.4 | 1485.7 | 1608.4 | 1531.9 | 1327.5 | 1324.1 | 1487.0 | 1471.8 | 1433.4 |
| 47.5° | 1171.6 | 1364.0 | 1709.1 | 1894.9 | 1751.9 | 1391.3 | 1379.0 | 1734.0 | 1714.1 | 1668.9 |
| 50° | 1190.3 | 1486.2 | 1978.2 | 2226.8 | 2017.6 | 1463.6 | 1472.5 | 1964.3 | 1955.9 | 1902.5 |
| 52.5° | 1231.3 | 1615.5 | 2309.6 | 2606.3 | 2339.8 | 1576.9 | 1633.1 | 2181.3 | 2124.6 | 2063.1 |
| 55° | 1292.8 | 1756.4 | 2654.4 | 2994.0 | 2668.6 | 1729.0 | 1806.8 | 2296.7 | 2137.5 | 2069.4 |
| 57.5° | 1224.7 | 1791.6 | 2858.6 | 3264.7 | 2814.5 | 1729.6 | 1659.9 | 2096.7 | 1879.9 | 1813.9 |
| 60° | 971.9 | 1666.8 | 2780.0 | 3206.1 | 2690.2 | 1535.9 | 1271.0 | 1637.1 | 1424.2 | 1380.0 |
| 62.5° | 657.0 | 1397.9 | 2447.3 | 2711.4 | 2302.5 | 1208.2 | 826.0 | 1064.7 | 881.7 | 845.2 |
| 65° | 360.1 | 1042.8 | 1977.4 | 2051.3 | 1802.1 | 843.9 | 425.0 | 462.0 | 351.9 | 335.6 |
| 67.5° | 99.3 | 725.9 | 1454.9 | 1360.8 | 1264.4 | 549.5 | 109.9 | 82.5 | 58.9 | 58.3 |
| 70° | 25.0 | 480.2 | 871.8 | 898.6 | 775.3 | 351.9 | 21.0 | 10.0 | 7.9 | 7.6 |
| 72.5° | 10.5 | 206.6 | 413.7 | 475.4 | 396.8 | 162.9 | 7.6 | 2.9 | 2.4 | 1.8 |
| 75° | 1.3 | 16.6 | 35.2 | 53.4 | 36.5 | 17.6 | 0.0 | 0.0 | 0.0 | 0.0 |
| 77.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 80° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 82.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 85° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 87.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



LM-79-2008: Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGRAW-EDISON

Report Number: SP1-1908-441-4-R4

Test Date: 10/02/2019

Luminaire Tested: SA1C-750-U-5WQ

Data in this report applies to families of products SA1C-760-U-5WQ .

Test Information

Test Method: LM-79-2008
 Report Number: SP1-1908-441-4-R4
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 10/28/2024
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: McGRAW-EDISON
 Catalog Number: **SA1C-750-U-5WQ**
 Description: McGRAW EDISON ROADWAY AND AREA LUMINAIRE

THIS IS A REVISION OF SP1-1908-441-4-R3. TO UPDATE THE CATALOG INFORMATION.TESTED IN SITU. ROADWAY AND AREA LUMINAIRE. (1) 70 CRI, 5000K, 1050MA LIGHTSQUARE WITH 16 LEDS AND TYPE V WIDE OPTICS.

Spectral Parameters

| | | | | | |
|---------------------------|--------|-----------|------|------|-------|
| CCT (K): | 4884 | CRI (Ra): | 73.5 | R9: | -28.4 |
| CIE u': | 0.2101 | R1: | 70.5 | R10: | 48.6 |
| CIE v': | 0.4904 | R2: | 77.7 | R11: | 73.2 |
| Duv: | 0.0037 | R3: | 84.6 | R12: | 50.7 |
| CIE x: | 0.3493 | R4: | 74.7 | R13: | 71.2 |
| CIE y: | 0.3624 | R5: | 71.9 | R14: | 91.4 |
| CIE z: | 0.2884 | R6: | 70.7 | | |
| Peak Wavelength (nm): | 444 | R7: | 81.2 | | |
| Dominant Wavelength (nm): | 571 | R8: | 56.9 | | |
| Purity: | 13.7 | | | | |
| Rf: | 74.9 | | | | |
| Rg: | 96.3 | | | | |



Test Conditions

Stabilization Time: 240M
 Operation Time: 12H
 Room Temperature (°C) / RH%: 25.0./44%
 Sphere Temperature (°C): 25.7

REPORT NUMBER: SP1-1908-441-4-R4

| Measurement and Test Equipment | | | |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument | Identification Number | Calibration Date | Calibration Due Date |
| Photometer | IN0058 | 6/28/2019 | 12/28/2019 |
| Power Meter | IN0071 | 12/5/2018 | 12/5/2019 |
| AC Power Source | IN0063 | 12/5/2018 | 12/5/2019 |
| DC Power Source | IN0208 | 12/5/2018 | 12/5/2019 |
| Sphere Thermometer | IN0085 | 12/5/2018 | 12/5/2019 |
| Room Thermometer | IN0046 | 12/5/2018 | 12/5/2019 |

REPORT NUMBER: SP1-1908-441-4-R4

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 5000K 4-step quadrangle

REPORT NUMBER: SP1-1908-441-4-R4

Photopic Flux vs. Wavelength



#####

| λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) |
|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|
| 360 | 2945 | NR | 490 | 37941 | NR | 620 | 88803 | NR | 750 | 3908 | NR | 880 | 2997 | NR |
| 365 | 2596 | NR | 495 | 48525 | NR | 625 | 80578 | NR | 755 | 3988 | NR | 885 | 2927 | NR |
| 370 | 2732 | NR | 500 | 60609 | NR | 630 | 73127 | NR | 760 | 3335 | NR | 890 | 2649 | NR |
| 375 | 2894 | NR | 505 | 72036 | NR | 635 | 66244 | NR | 765 | 3438 | NR | 895 | 2828 | NR |
| 380 | 2822 | NR | 510 | 82168 | NR | 640 | 59440 | NR | 770 | 3427 | NR | 900 | 1407 | NR |
| 385 | 2394 | NR | 515 | 90898 | NR | 645 | 52864 | NR | 775 | 2759 | NR | 905 | 2224 | NR |
| 390 | 2370 | NR | 520 | 97142 | NR | 650 | 47085 | NR | 780 | 2340 | NR | 910 | 2905 | NR |
| 395 | 2267 | NR | 525 | 103255 | NR | 655 | 41789 | NR | 785 | 2412 | NR | 915 | 3350 | NR |
| 400 | 2262 | NR | 530 | 106697 | NR | 660 | 37064 | NR | 790 | 1999 | NR | 920 | 3114 | NR |
| 405 | 3000 | NR | 535 | 110081 | NR | 665 | 32299 | NR | 795 | 2054 | NR | 925 | 2834 | NR |
| 410 | 5324 | NR | 540 | 112494 | NR | 670 | 28142 | NR | 800 | 2331 | NR | 930 | 2271 | NR |
| 415 | 10725 | NR | 545 | 115513 | NR | 675 | 24505 | NR | 805 | 2648 | NR | 935 | 2228 | NR |
| 420 | 22128 | NR | 550 | 117203 | NR | 680 | 21162 | NR | 810 | 2485 | NR | 940 | 2833 | NR |
| 425 | 44095 | NR | 555 | 119753 | NR | 685 | 18400 | NR | 815 | 2409 | NR | 945 | 2941 | NR |
| 430 | 77002 | NR | 560 | 122602 | NR | 690 | 16065 | NR | 820 | 2221 | NR | 950 | 2323 | NR |
| 435 | 119881 | NR | 565 | 124314 | NR | 695 | 13860 | NR | 825 | 1562 | NR | 955 | 1667 | NR |
| 440 | 164454 | NR | 570 | 126775 | NR | 700 | 12177 | NR | 830 | 2249 | NR | 960 | 749 | NR |
| 445 | 179997 | NR | 575 | 127511 | NR | 705 | 10757 | NR | 835 | 2573 | NR | 965 | 2669 | NR |
| 450 | 142822 | NR | 580 | 127577 | NR | 710 | 9601 | NR | 840 | 2764 | NR | 970 | 3968 | NR |
| 455 | 90008 | NR | 585 | 126153 | NR | 715 | 8944 | NR | 845 | 3109 | NR | 975 | 3886 | NR |
| 460 | 60557 | NR | 590 | 123678 | NR | 720 | 7947 | NR | 850 | 2963 | NR | 980 | 2788 | NR |
| 465 | 43305 | NR | 595 | 119774 | NR | 725 | 7062 | NR | 855 | 2336 | NR | 985 | 3496 | NR |
| 470 | 31089 | NR | 600 | 115733 | NR | 730 | 6004 | NR | 860 | 2118 | NR | 990 | 2913 | NR |
| 475 | 26278 | NR | 605 | 109231 | NR | 735 | 5594 | NR | 865 | 3144 | NR | 995 | 4659 | NR |
| 480 | 27060 | NR | 610 | 102408 | NR | 740 | 5165 | NR | 870 | 3069 | NR | 1000 | 1308 | NR |
| 485 | 30698 | NR | 615 | 96015 | NR | 745 | 4687 | NR | 875 | 3311 | NR | | | |

REPORT NUMBER: SP1-1908-441-4-R4

Scotopic Flux vs. Wavelength



Scotopic Lumens: 13493.5 S/P: 1.77

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 2945 | NR | 490 | 37941 | NR | 620 | 88803 | NR | 750 | 3908 | NR | 880 | 2997 | NR |
| 365 | 2596 | NR | 495 | 48525 | NR | 625 | 80578 | NR | 755 | 3988 | NR | 885 | 2927 | NR |
| 370 | 2732 | NR | 500 | 60609 | NR | 630 | 73127 | NR | 760 | 3335 | NR | 890 | 2649 | NR |
| 375 | 2894 | NR | 505 | 72036 | NR | 635 | 66244 | NR | 765 | 3438 | NR | 895 | 2828 | NR |
| 380 | 2822 | NR | 510 | 82168 | NR | 640 | 59440 | NR | 770 | 3427 | NR | 900 | 1407 | NR |
| 385 | 2394 | NR | 515 | 90898 | NR | 645 | 52864 | NR | 775 | 2759 | NR | 905 | 2224 | NR |
| 390 | 2370 | NR | 520 | 97142 | NR | 650 | 47085 | NR | 780 | 2340 | NR | 910 | 2905 | NR |
| 395 | 2267 | NR | 525 | 103255 | NR | 655 | 41789 | NR | 785 | 2412 | NR | 915 | 3350 | NR |
| 400 | 2262 | NR | 530 | 106697 | NR | 660 | 37064 | NR | 790 | 1999 | NR | 920 | 3114 | NR |
| 405 | 3000 | NR | 535 | 110081 | NR | 665 | 32299 | NR | 795 | 2054 | NR | 925 | 2834 | NR |
| 410 | 5324 | NR | 540 | 112494 | NR | 670 | 28142 | NR | 800 | 2331 | NR | 930 | 2271 | NR |
| 415 | 10725 | NR | 545 | 115513 | NR | 675 | 24505 | NR | 805 | 2648 | NR | 935 | 2228 | NR |
| 420 | 22128 | NR | 550 | 117203 | NR | 680 | 21162 | NR | 810 | 2485 | NR | 940 | 2833 | NR |
| 425 | 44095 | NR | 555 | 119753 | NR | 685 | 18400 | NR | 815 | 2409 | NR | 945 | 2941 | NR |
| 430 | 77002 | NR | 560 | 122602 | NR | 690 | 16065 | NR | 820 | 2221 | NR | 950 | 2323 | NR |
| 435 | 119881 | NR | 565 | 124314 | NR | 695 | 13860 | NR | 825 | 1562 | NR | 955 | 1667 | NR |
| 440 | 164454 | NR | 570 | 126775 | NR | 700 | 12177 | NR | 830 | 2249 | NR | 960 | 749 | NR |
| 445 | 179997 | NR | 575 | 127511 | NR | 705 | 10757 | NR | 835 | 2573 | NR | 965 | 2669 | NR |
| 450 | 142822 | NR | 580 | 127577 | NR | 710 | 9601 | NR | 840 | 2764 | NR | 970 | 3968 | NR |
| 455 | 90008 | NR | 585 | 126153 | NR | 715 | 8944 | NR | 845 | 3109 | NR | 975 | 3886 | NR |
| 460 | 60557 | NR | 590 | 123678 | NR | 720 | 7947 | NR | 850 | 2963 | NR | 980 | 2788 | NR |
| 465 | 43305 | NR | 595 | 119774 | NR | 725 | 7062 | NR | 855 | 2336 | NR | 985 | 3496 | NR |
| 470 | 31089 | NR | 600 | 115733 | NR | 730 | 6004 | NR | 860 | 2118 | NR | 990 | 2913 | NR |
| 475 | 26278 | NR | 605 | 109231 | NR | 735 | 5594 | NR | 865 | 3144 | NR | 995 | 4659 | NR |
| 480 | 27060 | NR | 610 | 102408 | NR | 740 | 5165 | NR | 870 | 3069 | NR | 1000 | 1308 | NR |
| 485 | 30698 | NR | 615 | 96015 | NR | 745 | 4687 | NR | 875 | 3311 | NR | | | |

REPORT NUMBER: SP1-1908-441-4-R4

Melanopic Flux vs. Wavelength



Melanopic Lumens: 5378.9

M/P: 0.71

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 2945 | NR | 490 | 37941 | NR | 620 | 88803 | NR | 750 | 3908 | NR | 880 | 2997 | NR |
| 365 | 2596 | NR | 495 | 48525 | NR | 625 | 80578 | NR | 755 | 3988 | NR | 885 | 2927 | NR |
| 370 | 2732 | NR | 500 | 60609 | NR | 630 | 73127 | NR | 760 | 3335 | NR | 890 | 2649 | NR |
| 375 | 2894 | NR | 505 | 72036 | NR | 635 | 66244 | NR | 765 | 3438 | NR | 895 | 2828 | NR |
| 380 | 2822 | NR | 510 | 82168 | NR | 640 | 59440 | NR | 770 | 3427 | NR | 900 | 1407 | NR |
| 385 | 2394 | NR | 515 | 90898 | NR | 645 | 52864 | NR | 775 | 2759 | NR | 905 | 2224 | NR |
| 390 | 2370 | NR | 520 | 97142 | NR | 650 | 47085 | NR | 780 | 2340 | NR | 910 | 2905 | NR |
| 395 | 2267 | NR | 525 | 103255 | NR | 655 | 41789 | NR | 785 | 2412 | NR | 915 | 3350 | NR |
| 400 | 2262 | NR | 530 | 106697 | NR | 660 | 37064 | NR | 790 | 1999 | NR | 920 | 3114 | NR |
| 405 | 3000 | NR | 535 | 110081 | NR | 665 | 32299 | NR | 795 | 2054 | NR | 925 | 2834 | NR |
| 410 | 5324 | NR | 540 | 112494 | NR | 670 | 28142 | NR | 800 | 2331 | NR | 930 | 2271 | NR |
| 415 | 10725 | NR | 545 | 115513 | NR | 675 | 24505 | NR | 805 | 2648 | NR | 935 | 2228 | NR |
| 420 | 22128 | NR | 550 | 117203 | NR | 680 | 21162 | NR | 810 | 2485 | NR | 940 | 2833 | NR |
| 425 | 44095 | NR | 555 | 119753 | NR | 685 | 18400 | NR | 815 | 2409 | NR | 945 | 2941 | NR |
| 430 | 77002 | NR | 560 | 122602 | NR | 690 | 16065 | NR | 820 | 2221 | NR | 950 | 2323 | NR |
| 435 | 119881 | NR | 565 | 124314 | NR | 695 | 13860 | NR | 825 | 1562 | NR | 955 | 1667 | NR |
| 440 | 164454 | NR | 570 | 126775 | NR | 700 | 12177 | NR | 830 | 2249 | NR | 960 | 749 | NR |
| 445 | 179997 | NR | 575 | 127511 | NR | 705 | 10757 | NR | 835 | 2573 | NR | 965 | 2669 | NR |
| 450 | 142822 | NR | 580 | 127577 | NR | 710 | 9601 | NR | 840 | 2764 | NR | 970 | 3968 | NR |
| 455 | 90008 | NR | 585 | 126153 | NR | 715 | 8944 | NR | 845 | 3109 | NR | 975 | 3886 | NR |
| 460 | 60557 | NR | 590 | 123678 | NR | 720 | 7947 | NR | 850 | 2963 | NR | 980 | 2788 | NR |
| 465 | 43305 | NR | 595 | 119774 | NR | 725 | 7062 | NR | 855 | 2336 | NR | 985 | 3496 | NR |
| 470 | 31089 | NR | 600 | 115733 | NR | 730 | 6004 | NR | 860 | 2118 | NR | 990 | 2913 | NR |
| 475 | 26278 | NR | 605 | 109231 | NR | 735 | 5594 | NR | 865 | 3144 | NR | 995 | 4659 | NR |
| 480 | 27060 | NR | 610 | 102408 | NR | 740 | 5165 | NR | 870 | 3069 | NR | 1000 | 1308 | NR |
| 485 | 30698 | NR | 615 | 96015 | NR | 745 | 4687 | NR | 875 | 3311 | NR | | | |

REPORT NUMBER: SP1-1908-441-4-R4


TM-30-18

Summary

$R_f = 74.9$
 $R_g = 96.3$
 CIE $R_a = 73.5$
 $R_g = -28.4$



Color Vector Graphics



REPORT NUMBER: SP1-1908-441-4-R4

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)

| | | | |
|------------|------------|------------|------------|
| CES01 = 85 | CES26 = 61 | CES51 = 90 | CES76 = 52 |
| CES02 = 60 | CES27 = 84 | CES52 = 91 | CES77 = 71 |
| CES03 = 30 | CES28 = 81 | CES53 = 79 | CES78 = 54 |
| CES04 = 69 | CES29 = 58 | CES54 = 83 | CES79 = 80 |
| CES05 = 46 | CES30 = 67 | CES55 = 83 | CES80 = 77 |
| CES06 = 50 | CES31 = 63 | CES56 = 73 | CES81 = 77 |
| CES07 = 39 | CES32 = 59 | CES57 = 72 | CES82 = 90 |
| CES08 = 38 | CES33 = 69 | CES58 = 73 | CES83 = 86 |
| CES09 = 29 | CES34 = 69 | CES59 = 88 | CES84 = 88 |
| CES10 = 73 | CES35 = 83 | CES60 = 93 | CES85 = 84 |
| CES11 = 56 | CES36 = 95 | CES61 = 88 | CES86 = 75 |
| CES12 = 61 | CES37 = 78 | CES62 = 85 | CES87 = 78 |
| CES13 = 41 | CES38 = 76 | CES63 = 77 | CES88 = 79 |
| CES14 = 74 | CES39 = 93 | CES64 = 74 | CES89 = 75 |
| CES15 = 70 | CES40 = 86 | CES65 = 67 | CES90 = 77 |
| CES16 = 46 | CES41 = 87 | CES66 = 69 | CES91 = 89 |
| CES17 = 49 | CES42 = 78 | CES67 = 67 | CES92 = 66 |
| CES18 = 55 | CES43 = 75 | CES68 = 73 | CES93 = 80 |
| CES19 = 71 | CES44 = 99 | CES69 = 81 | CES94 = 57 |
| CES20 = 64 | CES45 = 83 | CES70 = 63 | CES95 = 71 |
| CES21 = 85 | CES46 = 81 | CES71 = 60 | CES96 = 78 |
| CES22 = 77 | CES47 = 80 | CES72 = 86 | CES97 = 85 |
| CES23 = 91 | CES48 = 72 | CES73 = 53 | CES98 = 75 |
| CES24 = 90 | CES49 = 81 | CES74 = 96 | CES99 = 62 |
| CES25 = 71 | CES50 = 89 | CES75 = 58 | |



REPORT NUMBER: SP1-1908-441-4-R4

TM-30-18

Color Rendition by Hue-Angle Bin



REPORT NUMBER: SP1-1908-441-4-R4

TM-30-18

Measure Comparisons



(END OF REPORT)