

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: McGRAW-EDISON

Report Number: P629411

Luminaire Tested: GWS-SA1B-750-U-SLR-W-GRSWH

Issue Date: 1/10/2023

Test Information

Test Method: LM-79-2019
Report Number: P629411
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2209-782-43)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/10/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: McGRAW-EDISON
Catalog Number: GWS-SA1B-750-U-SLR-W-GRSWH
Description: GALLEON WALL SLIM LUMINAIRE. (1) LIGHTSQUARES WITH 16 LEDS EACH AND SPILL LIGHT ELIMINATOR RIGHT OPTICS W/ FACTORY INSTALLED GLARE SHIELD, WH
Light Source: (16) 5000K CCT, 70 CRI LEDS
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2868.4 lumens
Efficiency: N/A
Efficacy: 114.7 lumens/watt
Luminous Opening: Rectangular (W 0.5' x L: 0.5' x H: 0')
IES Classification: Type III - Short
BUG Rating: B1 - U0 - G1


Input Watts (W): 25
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 0
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT



REPORT NUMBER: P629411
 CATALOG NUMBER: GWS-SA1B-750-U-SLR-W-GRSWH

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 10 foot mounting height. Maximum calculated value = 7.9 fc
 Type III - Short - N/A

REPORT NUMBER: P629411
CATALOG NUMBER: GWS-SA1B-750-U-SLR-W-GRSWH

Luminous Intensity Polar Plot



— Vertical Plane Through 45-Deg Lateral - - - Horizontal Cone Through 60-Deg Vertical

REPORT NUMBER: P629411

CATALOG NUMBER: GWS-SA1B-750-U-SLR-W-GRSWH


FLUX DISTRIBUTION:

| | | Downward | Upward | Total |
|--------------------|-----------|----------|--------|--------|
| House Side | Lumens | 1005.5 | 0.0 | 1005.5 |
| | % Fixture | 35.1 | 0.0 | 35.1 |
| Street Side | Lumens | 1862.9 | 0.0 | 1862.9 |
| | % Fixture | 64.9 | 0.0 | 64.9 |
| Total | Lumens | 2868.4 | 0.0 | 2868.4 |
| | % Fixture | 100.0 | 0.0 | 100.0 |

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 57.5 | 2.0 |
| 10°-20° | 181.7 | 6.3 |
| 20°-30° | 295.1 | 10.3 |
| 30°-40° | 416.2 | 14.5 |
| 40°-50° | 575.2 | 20.1 |
| 50°-60° | 740.4 | 25.8 |
| 60°-70° | 469.1 | 16.4 |
| 70°-80° | 120.4 | 4.2 |
| 80°-90° | 12.9 | 0.4 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-90° | 2868.4 | 100.0 |
| 0°-180° | 2868.4 | 100.0 |

Coefficient of Utilization



REPORT NUMBER: P629411


CATALOG NUMBER: GWS-SA1B-750-U-SLR-W-GRSWH

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

| Zone | Lumens | % Fixture | Zone Rating/Lumen Limit | | |
|----------------|--------|-----------|-------------------------|------|--------|
| | | | B | U | G |
| FL (0°-30°) | 291.3 | 10.2 | | | |
| FM (30°-60°) | 1172.4 | 40.9 | | | |
| FH (60°-80°) | 395.7 | 13.8 | | | G0/660 |
| FVH (80°-90°) | 3.5 | 0.1 | | | G0/10 |
| BL (0°-30°) | 243.0 | 8.5 | B1/500 | | |
| BM (30°-60°) | 559.3 | 19.5 | B1/1000 | | |
| BH (60°-80°) | 193.8 | 6.8 | B1/500 | | G1/500 |
| BVH (80°-90°) | 9.4 | 0.3 | | | G0/10 |
| UL (90°-100°) | 0.0 | 0.0 | | U0/0 | |
| UH (100°-180°) | 0.0 | 0.0 | | U0/0 | |

BUG Rating: B1-U0-G1

Type III Short





REPORT NUMBER: P629411
 CATALOG NUMBER: GWS-SA1B-750-U-SLR-W-GRSWH

CANDELA DISTRIBUTION (FULL):

| | 0° | 1° | 5° | 15° | 25° | 35° | 45° | 55° | 65° | 75° | 85° |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 589.3 | 589.3 | 589.3 | 589.3 | 589.3 | 589.3 | 589.3 | 589.3 | 589.3 | 589.3 | 589.3 |
| 2.5° | 616.3 | 620.5 | 623.2 | 628.2 | 637.1 | 642.1 | 647.6 | 641.6 | 643.1 | 642.3 | 632.6 |
| 5° | 652.9 | 657.9 | 664.7 | 679.4 | 696.0 | 705.2 | 713.8 | 712.5 | 704.4 | 690.7 | 681.0 |
| 7.5° | 687.0 | 692.8 | 704.6 | 728.6 | 753.0 | 767.2 | 777.7 | 770.9 | 764.0 | 742.5 | 718.0 |
| 10° | 713.8 | 717.2 | 733.3 | 765.3 | 793.7 | 809.8 | 822.6 | 821.1 | 811.6 | 787.4 | 754.6 |
| 12.5° | 739.1 | 741.4 | 758.8 | 790.8 | 816.3 | 823.4 | 833.9 | 837.4 | 834.2 | 816.1 | 783.7 |
| 15° | 766.1 | 770.6 | 786.6 | 811.1 | 822.6 | 815.3 | 819.0 | 828.4 | 837.4 | 837.4 | 807.7 |
| 17.5° | 791.4 | 795.3 | 811.6 | 822.1 | 811.1 | 791.6 | 792.7 | 804.8 | 826.1 | 848.4 | 829.5 |
| 20° | 813.7 | 817.4 | 833.4 | 823.4 | 788.5 | 760.1 | 759.3 | 774.0 | 808.4 | 855.5 | 852.9 |
| 22.5° | 838.1 | 843.4 | 856.8 | 824.5 | 767.4 | 731.4 | 731.2 | 746.4 | 792.9 | 862.6 | 879.7 |
| 25° | 872.8 | 881.0 | 887.8 | 833.7 | 756.1 | 712.8 | 716.2 | 730.7 | 787.9 | 874.2 | 919.4 |
| 27.5° | 924.4 | 930.9 | 930.4 | 852.9 | 755.6 | 705.2 | 712.3 | 729.1 | 796.9 | 894.7 | 961.2 |
| 30° | 980.1 | 983.5 | 978.0 | 879.7 | 767.7 | 709.9 | 720.4 | 740.4 | 819.5 | 928.6 | 1022.7 |
| 32.5° | 1041.8 | 1046.0 | 1035.5 | 919.9 | 795.8 | 744.8 | 768.0 | 777.7 | 851.3 | 977.4 | 1087.8 |
| 35° | 1112.8 | 1120.9 | 1099.1 | 973.0 | 878.6 | 872.3 | 906.0 | 893.3 | 918.8 | 1035.3 | 1157.5 |
| 37.5° | 1187.4 | 1187.7 | 1156.4 | 1051.6 | 1041.0 | 1051.8 | 1119.1 | 1079.7 | 1062.1 | 1099.7 | 1228.4 |
| 40° | 1250.8 | 1249.2 | 1201.1 | 1157.5 | 1182.4 | 1225.3 | 1306.5 | 1246.1 | 1199.8 | 1186.1 | 1287.3 |
| 42.5° | 1314.1 | 1308.3 | 1259.7 | 1224.8 | 1280.0 | 1368.0 | 1459.7 | 1385.6 | 1288.1 | 1264.7 | 1345.4 |
| 45° | 1395.1 | 1393.2 | 1334.6 | 1251.6 | 1368.0 | 1527.8 | 1649.5 | 1529.4 | 1340.4 | 1310.4 | 1442.1 |
| 47.5° | 1525.7 | 1516.8 | 1407.7 | 1249.5 | 1450.5 | 1740.7 | 1894.4 | 1710.5 | 1376.9 | 1311.5 | 1598.2 |
| 50° | 1653.4 | 1642.4 | 1494.9 | 1249.2 | 1535.7 | 1961.5 | 2183.5 | 1930.4 | 1414.3 | 1317.8 | 1757.0 |
| 52.5° | 1782.5 | 1782.5 | 1638.2 | 1278.9 | 1625.0 | 2208.0 | 2517.6 | 2204.6 | 1477.9 | 1400.3 | 1952.3 |
| 55° | 1859.2 | 1879.7 | 1799.3 | 1329.1 | 1729.7 | 2498.2 | 2848.0 | 2500.5 | 1576.2 | 1549.4 | 2132.6 |
| 57.5° | 1761.7 | 1800.1 | 1788.5 | 1294.1 | 1791.4 | 2711.3 | 3128.1 | 2725.0 | 1624.8 | 1567.0 | 2105.5 |
| 60° | 1435.5 | 1488.9 | 1515.4 | 1117.5 | 1730.4 | 2736.0 | 3186.8 | 2739.7 | 1524.4 | 1334.4 | 1803.5 |
| 62.5° | 954.3 | 998.2 | 1038.7 | 798.5 | 1498.1 | 2461.4 | 2818.5 | 2462.1 | 1273.1 | 995.8 | 1249.5 |
| 65° | 468.1 | 500.7 | 544.3 | 472.0 | 1170.4 | 2056.6 | 2197.5 | 1989.6 | 920.9 | 557.5 | 637.4 |
| 67.5° | 122.5 | 131.7 | 137.7 | 183.2 | 838.4 | 1477.6 | 1433.2 | 1455.3 | 591.6 | 182.1 | 166.6 |
| 70° | 63.6 | 64.1 | 63.9 | 75.7 | 566.7 | 939.1 | 987.7 | 913.8 | 412.9 | 76.2 | 65.7 |
| 72.5° | 45.5 | 45.7 | 44.9 | 51.0 | 273.6 | 538.0 | 557.5 | 551.4 | 216.3 | 45.2 | 44.9 |
| 75° | 29.7 | 30.0 | 29.4 | 30.0 | 41.3 | 61.2 | 56.5 | 59.4 | 36.0 | 28.6 | 28.6 |
| 77.5° | 17.6 | 17.9 | 17.6 | 18.1 | 17.6 | 17.6 | 16.3 | 16.3 | 15.5 | 15.5 | 15.8 |
| 80° | 11.8 | 11.8 | 11.6 | 12.1 | 11.0 | 11.0 | 10.5 | 10.3 | 9.5 | 9.2 | 9.2 |
| 82.5° | 7.1 | 7.4 | 7.1 | 7.1 | 6.6 | 6.6 | 6.0 | 5.8 | 5.0 | 5.0 | 4.7 |
| 85° | 3.7 | 3.7 | 3.4 | 3.4 | 2.9 | 2.6 | 2.1 | 2.1 | 1.6 | 1.3 | 1.3 |
| 87.5° | 0.5 | 0.5 | 0.3 | 0.3 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P629411
 CATALOG NUMBER: GWS-SA1B-750-U-SLR-W-GRSWH

CANDELA DISTRIBUTION (continued):

| | 90° | 95° | 105° | 115° | 125° | 135° | 145° | 155° | 165° | 175° | 180° |
|-------|--------|--------|-------|-------|-------|-------|-------|-------|-------|-------|-------|
| 0° | 589.3 | 589.3 | 589.3 | 589.3 | 589.3 | 589.3 | 589.3 | 589.3 | 589.3 | 589.3 | 589.3 |
| 2.5° | 630.0 | 624.7 | 616.9 | 609.2 | 602.1 | 594.8 | 586.4 | 577.7 | 570.3 | 562.7 | 558.8 |
| 5° | 668.1 | 657.3 | 636.8 | 618.7 | 602.4 | 589.0 | 574.5 | 562.2 | 550.6 | 541.2 | 536.4 |
| 7.5° | 702.5 | 685.7 | 654.7 | 626.0 | 604.0 | 585.6 | 565.6 | 547.2 | 531.7 | 520.1 | 515.7 |
| 10° | 734.3 | 714.4 | 673.6 | 637.4 | 611.6 | 591.1 | 566.7 | 541.7 | 521.2 | 505.9 | 502.3 |
| 12.5° | 760.1 | 737.2 | 688.6 | 646.5 | 616.1 | 594.0 | 572.4 | 550.9 | 530.6 | 510.9 | 507.8 |
| 15° | 783.0 | 755.9 | 699.9 | 652.3 | 614.5 | 586.4 | 568.2 | 565.6 | 565.6 | 543.3 | 537.0 |
| 17.5° | 802.7 | 773.0 | 709.1 | 655.0 | 604.5 | 563.8 | 552.7 | 575.6 | 601.3 | 585.3 | 571.1 |
| 20° | 825.3 | 789.3 | 716.7 | 655.0 | 586.1 | 535.1 | 534.1 | 573.0 | 611.1 | 611.3 | 596.3 |
| 22.5° | 848.1 | 808.2 | 725.7 | 652.6 | 560.9 | 502.0 | 521.4 | 562.4 | 596.3 | 610.8 | 600.6 |
| 25° | 885.2 | 834.5 | 739.9 | 650.8 | 531.4 | 479.4 | 510.1 | 548.5 | 577.2 | 592.4 | 585.8 |
| 27.5° | 932.2 | 869.2 | 761.4 | 653.6 | 502.3 | 466.0 | 498.1 | 530.4 | 556.4 | 569.8 | 565.1 |
| 30° | 984.8 | 909.1 | 784.5 | 658.6 | 481.2 | 459.2 | 483.6 | 509.6 | 532.7 | 546.2 | 544.0 |
| 32.5° | 1051.8 | 952.5 | 804.5 | 651.8 | 469.4 | 455.7 | 468.4 | 487.0 | 509.4 | 517.8 | 519.6 |
| 35° | 1132.0 | 1000.3 | 819.8 | 625.0 | 458.6 | 452.1 | 451.8 | 463.4 | 479.1 | 492.5 | 493.8 |
| 37.5° | 1205.8 | 1056.3 | 836.6 | 579.0 | 439.2 | 442.9 | 432.3 | 439.2 | 454.7 | 468.1 | 473.3 |
| 40° | 1278.9 | 1113.1 | 860.0 | 520.4 | 413.7 | 422.4 | 410.0 | 414.7 | 427.1 | 444.7 | 453.1 |
| 42.5° | 1349.9 | 1164.3 | 884.7 | 460.5 | 388.2 | 393.7 | 384.5 | 389.2 | 402.1 | 424.2 | 433.7 |
| 45° | 1427.1 | 1233.7 | 903.9 | 404.0 | 366.1 | 363.7 | 356.4 | 363.2 | 382.7 | 406.9 | 418.2 |
| 47.5° | 1573.3 | 1343.0 | 916.5 | 366.4 | 354.3 | 337.2 | 328.8 | 343.5 | 365.6 | 390.0 | 403.7 |
| 50° | 1751.7 | 1501.3 | 912.8 | 342.5 | 344.0 | 309.9 | 307.0 | 326.4 | 350.1 | 375.6 | 390.6 |
| 52.5° | 1893.1 | 1656.6 | 871.0 | 319.6 | 324.1 | 292.5 | 284.1 | 312.5 | 335.1 | 361.1 | 376.6 |
| 55° | 2001.1 | 1708.9 | 742.7 | 292.5 | 291.5 | 279.9 | 262.3 | 298.0 | 320.1 | 344.3 | 361.1 |
| 57.5° | 1913.1 | 1592.5 | 550.6 | 255.2 | 248.9 | 254.9 | 237.9 | 273.6 | 301.7 | 325.6 | 340.6 |
| 60° | 1587.7 | 1269.7 | 306.7 | 226.0 | 208.2 | 222.9 | 220.2 | 247.8 | 281.7 | 307.0 | 319.9 |
| 62.5° | 1077.8 | 845.5 | 181.9 | 178.7 | 168.7 | 189.8 | 203.7 | 221.8 | 255.2 | 275.7 | 287.8 |
| 65° | 537.2 | 410.8 | 120.9 | 133.8 | 135.1 | 156.1 | 182.4 | 202.4 | 230.2 | 251.3 | 263.4 |
| 67.5° | 155.9 | 127.7 | 92.0 | 102.2 | 116.4 | 133.3 | 154.3 | 177.9 | 205.0 | 230.0 | 244.2 |
| 70° | 67.3 | 68.1 | 73.1 | 85.2 | 99.1 | 116.4 | 137.5 | 160.6 | 183.5 | 202.6 | 213.4 |
| 72.5° | 47.6 | 49.4 | 54.9 | 67.3 | 80.4 | 97.0 | 118.0 | 140.3 | 156.9 | 176.4 | 187.7 |
| 75° | 30.5 | 31.8 | 36.3 | 45.7 | 55.5 | 71.5 | 91.5 | 112.0 | 129.0 | 143.0 | 153.8 |
| 77.5° | 16.8 | 17.1 | 20.8 | 26.3 | 32.9 | 43.1 | 57.8 | 73.9 | 86.5 | 94.4 | 104.1 |
| 80° | 9.7 | 9.7 | 11.6 | 15.0 | 18.9 | 25.2 | 33.4 | 41.3 | 48.9 | 53.9 | 58.6 |
| 82.5° | 5.3 | 5.3 | 6.0 | 8.1 | 10.3 | 13.9 | 18.7 | 22.6 | 27.3 | 30.0 | 33.1 |
| 85° | 1.6 | 1.6 | 2.1 | 2.9 | 3.7 | 5.3 | 7.4 | 9.5 | 11.6 | 13.4 | 15.2 |
| 87.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.3 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P629411

CATALOG NUMBER: GWS-SA1B-750-U-SLR-W-GRSWH

CANDELA DISTRIBUTION (continued):

| | 185° | 195° | 205° | 215° | 225° | 235° | 245° | 255° | 265° | 270° | 275° |
|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|
| 0° | 589.3 | 589.3 | 589.3 | 589.3 | 589.3 | 589.3 | 589.3 | 589.3 | 589.3 | 589.3 | 589.3 |
| 2.5° | 558.0 | 554.3 | 552.2 | 549.6 | 550.4 | 548.0 | 546.7 | 547.5 | 542.7 | 547.5 | 552.2 |
| 5° | 534.6 | 529.3 | 525.1 | 521.7 | 520.1 | 517.0 | 515.1 | 515.1 | 512.2 | 517.0 | 522.8 |
| 7.5° | 514.1 | 509.9 | 507.8 | 505.7 | 503.3 | 500.4 | 497.3 | 496.2 | 494.4 | 499.4 | 504.4 |
| 10° | 500.4 | 500.9 | 502.3 | 505.1 | 504.6 | 502.8 | 498.1 | 495.4 | 495.4 | 501.2 | 508.8 |
| 12.5° | 506.7 | 512.2 | 515.4 | 520.7 | 521.7 | 520.1 | 515.4 | 513.3 | 518.6 | 527.2 | 539.8 |
| 15° | 531.2 | 534.8 | 537.5 | 541.7 | 541.4 | 540.1 | 536.4 | 538.0 | 555.3 | 572.2 | 583.5 |
| 17.5° | 557.7 | 553.5 | 553.0 | 555.6 | 556.4 | 554.8 | 552.7 | 559.8 | 588.5 | 604.2 | 610.0 |
| 20° | 576.9 | 562.4 | 559.3 | 560.3 | 562.4 | 561.7 | 561.7 | 573.2 | 602.9 | 610.3 | 602.9 |
| 22.5° | 582.7 | 562.2 | 557.5 | 557.7 | 560.6 | 560.9 | 562.2 | 574.3 | 591.6 | 591.9 | 580.6 |
| 25° | 573.5 | 553.8 | 550.4 | 550.9 | 554.3 | 554.0 | 554.6 | 561.4 | 569.0 | 565.9 | 557.5 |
| 27.5° | 556.1 | 539.1 | 538.0 | 540.9 | 545.4 | 543.0 | 541.4 | 543.3 | 546.9 | 543.0 | 535.6 |
| 30° | 536.4 | 522.0 | 522.5 | 528.0 | 532.7 | 528.8 | 524.9 | 525.9 | 526.2 | 522.0 | 513.6 |
| 32.5° | 515.7 | 504.9 | 506.7 | 512.5 | 518.0 | 513.8 | 509.6 | 509.1 | 504.1 | 499.1 | 491.0 |
| 35° | 494.9 | 490.7 | 493.1 | 497.8 | 502.5 | 499.1 | 496.5 | 494.9 | 484.1 | 476.8 | 469.9 |
| 37.5° | 476.0 | 479.1 | 483.3 | 486.2 | 487.8 | 487.5 | 486.0 | 482.3 | 468.1 | 459.4 | 450.5 |
| 40° | 459.2 | 468.9 | 473.3 | 474.7 | 477.0 | 476.5 | 476.2 | 471.0 | 452.3 | 443.1 | 432.9 |
| 42.5° | 443.9 | 457.6 | 465.2 | 466.5 | 467.8 | 468.1 | 467.3 | 459.7 | 438.4 | 427.6 | 417.9 |
| 45° | 429.2 | 447.1 | 456.8 | 455.5 | 457.3 | 457.3 | 458.1 | 448.1 | 424.7 | 413.7 | 403.4 |
| 47.5° | 416.3 | 437.3 | 446.3 | 444.7 | 445.8 | 446.5 | 447.3 | 435.8 | 409.7 | 399.2 | 388.7 |
| 50° | 404.5 | 426.8 | 434.4 | 435.0 | 435.0 | 436.8 | 436.6 | 425.3 | 397.1 | 385.8 | 375.3 |
| 52.5° | 391.9 | 416.1 | 424.2 | 427.6 | 428.7 | 429.5 | 425.8 | 412.6 | 384.3 | 370.6 | 360.9 |
| 55° | 377.2 | 405.0 | 412.4 | 416.8 | 418.9 | 418.4 | 413.4 | 400.0 | 371.1 | 357.4 | 346.4 |
| 57.5° | 354.8 | 381.4 | 391.9 | 394.0 | 397.4 | 395.3 | 389.5 | 378.2 | 350.1 | 336.4 | 325.1 |
| 60° | 330.4 | 349.6 | 358.0 | 359.8 | 357.2 | 358.0 | 357.2 | 346.4 | 322.0 | 311.2 | 299.6 |
| 62.5° | 298.3 | 315.4 | 324.3 | 326.7 | 322.2 | 325.1 | 324.1 | 310.7 | 286.2 | 274.9 | 264.7 |
| 65° | 274.1 | 292.8 | 303.3 | 304.6 | 303.3 | 304.6 | 300.9 | 284.6 | 261.5 | 249.9 | 239.4 |
| 67.5° | 255.2 | 274.4 | 285.4 | 289.1 | 287.8 | 287.5 | 281.7 | 262.8 | 238.9 | 226.3 | 212.9 |
| 70° | 222.6 | 239.4 | 253.6 | 262.6 | 262.6 | 257.6 | 246.5 | 228.9 | 209.7 | 199.0 | 188.4 |
| 72.5° | 197.1 | 218.4 | 232.3 | 241.5 | 243.4 | 240.5 | 225.0 | 206.3 | 184.2 | 173.5 | 162.4 |
| 75° | 162.4 | 183.2 | 198.2 | 210.3 | 212.6 | 209.5 | 191.6 | 173.2 | 152.7 | 142.2 | 131.1 |
| 77.5° | 108.5 | 120.9 | 133.0 | 144.0 | 141.7 | 143.8 | 131.7 | 117.7 | 105.1 | 97.2 | 92.3 |
| 80° | 61.2 | 69.4 | 73.1 | 79.1 | 79.1 | 79.1 | 71.2 | 64.7 | 57.6 | 53.1 | 48.1 |
| 82.5° | 34.7 | 39.9 | 41.5 | 46.5 | 47.8 | 48.1 | 42.8 | 38.6 | 34.2 | 31.8 | 28.4 |
| 85° | 16.0 | 18.9 | 19.2 | 22.1 | 23.1 | 25.2 | 22.9 | 20.0 | 17.3 | 16.3 | 14.2 |
| 87.5° | 0.5 | 1.6 | 2.1 | 3.9 | 5.3 | 6.0 | 6.6 | 6.6 | 5.5 | 5.0 | 4.2 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P629411

CATALOG NUMBER: GWS-SA1B-750-U-SLR-W-GRSWH

CANDELA DISTRIBUTION (continued):

| | 285° | 295° | 305° | 315° | 325° | 335° | 345° | 355° | 359° | 360° |
|-------|-------|-------|-------|-------|-------|-------|-------|--------|--------|--------|
| 0° | 589.3 | 589.3 | 589.3 | 589.3 | 589.3 | 589.3 | 589.3 | 589.3 | 589.3 | 589.3 |
| 2.5° | 558.0 | 564.3 | 571.6 | 576.9 | 586.4 | 594.2 | 602.4 | 611.3 | 617.9 | 616.3 |
| 5° | 529.9 | 540.4 | 553.8 | 566.1 | 583.7 | 601.6 | 621.3 | 641.6 | 653.4 | 652.9 |
| 7.5° | 514.1 | 529.1 | 545.4 | 561.9 | 582.7 | 608.4 | 638.7 | 670.2 | 686.2 | 687.0 |
| 10° | 522.5 | 538.5 | 549.6 | 563.5 | 585.3 | 617.6 | 653.9 | 691.8 | 710.2 | 713.8 |
| 12.5° | 549.0 | 547.7 | 546.9 | 556.9 | 583.2 | 624.2 | 668.6 | 713.8 | 734.6 | 739.1 |
| 15° | 574.3 | 547.2 | 530.9 | 537.7 | 573.7 | 628.4 | 683.1 | 738.0 | 761.4 | 766.1 |
| 17.5° | 579.0 | 538.0 | 507.8 | 512.5 | 558.8 | 629.7 | 697.0 | 761.7 | 786.9 | 791.4 |
| 20° | 565.9 | 526.2 | 491.0 | 484.4 | 539.8 | 626.3 | 705.7 | 781.4 | 809.0 | 813.7 |
| 22.5° | 549.3 | 515.7 | 478.3 | 461.3 | 516.7 | 622.9 | 715.4 | 802.1 | 833.9 | 838.1 |
| 25° | 532.0 | 502.3 | 466.5 | 440.5 | 490.4 | 620.8 | 731.7 | 829.5 | 867.8 | 872.8 |
| 27.5° | 513.6 | 486.0 | 456.3 | 430.5 | 466.3 | 623.4 | 754.8 | 873.6 | 917.3 | 924.4 |
| 30° | 493.8 | 469.7 | 449.7 | 427.1 | 449.7 | 625.8 | 780.3 | 918.8 | 970.1 | 980.1 |
| 32.5° | 473.3 | 454.7 | 442.9 | 428.7 | 439.4 | 620.3 | 802.7 | 969.6 | 1033.2 | 1041.8 |
| 35° | 452.8 | 439.4 | 434.2 | 431.6 | 425.8 | 600.0 | 820.8 | 1020.8 | 1105.2 | 1112.8 |
| 37.5° | 433.7 | 423.7 | 422.1 | 425.0 | 404.8 | 566.9 | 841.8 | 1086.0 | 1175.9 | 1187.4 |
| 40° | 415.8 | 406.6 | 406.3 | 405.8 | 381.6 | 521.7 | 870.2 | 1152.2 | 1245.5 | 1250.8 |
| 42.5° | 399.2 | 387.7 | 389.8 | 383.5 | 362.7 | 472.8 | 897.0 | 1208.7 | 1310.4 | 1314.1 |
| 45° | 384.5 | 369.3 | 371.6 | 363.7 | 353.8 | 421.6 | 920.7 | 1275.5 | 1392.7 | 1395.1 |
| 47.5° | 370.3 | 354.0 | 347.5 | 346.9 | 352.2 | 374.3 | 943.8 | 1404.0 | 1521.5 | 1525.7 |
| 50° | 357.2 | 339.6 | 320.9 | 332.5 | 342.5 | 338.8 | 972.7 | 1541.7 | 1654.5 | 1653.4 |
| 52.5° | 344.6 | 321.4 | 294.9 | 317.2 | 317.2 | 312.5 | 964.6 | 1625.3 | 1764.3 | 1782.5 |
| 55° | 330.1 | 292.3 | 267.8 | 291.7 | 280.2 | 288.8 | 820.3 | 1652.6 | 1833.5 | 1859.2 |
| 57.5° | 301.5 | 256.3 | 235.0 | 247.8 | 230.5 | 267.8 | 589.3 | 1517.0 | 1716.0 | 1761.7 |
| 60° | 273.9 | 229.7 | 215.8 | 213.4 | 190.8 | 218.4 | 381.9 | 1187.7 | 1412.4 | 1435.5 |
| 62.5° | 241.5 | 206.8 | 195.0 | 176.9 | 153.5 | 159.0 | 231.3 | 781.6 | 949.1 | 954.3 |
| 65° | 217.1 | 187.4 | 164.8 | 143.2 | 125.6 | 115.4 | 136.7 | 376.9 | 474.4 | 468.1 |
| 67.5° | 186.3 | 160.6 | 139.0 | 123.5 | 109.1 | 96.2 | 90.9 | 112.0 | 126.7 | 122.5 |
| 70° | 165.8 | 141.1 | 120.4 | 105.7 | 92.3 | 79.4 | 70.2 | 66.0 | 64.7 | 63.6 |
| 72.5° | 143.0 | 121.4 | 99.9 | 85.7 | 73.1 | 61.2 | 52.8 | 47.8 | 46.5 | 45.5 |
| 75° | 114.1 | 93.8 | 74.1 | 60.7 | 49.7 | 41.3 | 35.7 | 31.5 | 30.8 | 29.7 |
| 77.5° | 75.4 | 60.2 | 44.2 | 36.0 | 29.4 | 25.0 | 21.3 | 18.7 | 18.1 | 17.6 |
| 80° | 41.5 | 34.7 | 27.1 | 21.8 | 17.6 | 15.2 | 13.9 | 12.4 | 12.1 | 11.8 |
| 82.5° | 24.7 | 20.8 | 15.5 | 12.4 | 10.3 | 9.2 | 8.4 | 7.6 | 7.4 | 7.1 |
| 85° | 12.4 | 9.7 | 6.8 | 5.8 | 5.3 | 4.7 | 4.7 | 3.9 | 3.7 | 3.7 |
| 87.5° | 3.2 | 2.6 | 1.6 | 1.3 | 1.3 | 1.3 | 1.1 | 0.8 | 0.8 | 0.5 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



LM-79-2008: Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGRAW-EDISON

Report Number: SP1-1908-441-4-R4

Test Date: 10/02/2019

Luminaire Tested: SA1C-750-U-5WQ

Data in this report applies to families of products SA1C-760-U-5WQ .

Test Information


Test Method: LM-79-2008
 Report Number: SP1-1908-441-4-R4
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 10/28/2024
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: McGRAW-EDISON
 Catalog Number: **SA1C-750-U-5WQ**
 Description: McGRAW EDISON ROADWAY AND AREA LUMINAIRE

THIS IS A REVISION OF SP1-1908-441-4-R3. TO UPDATE THE CATALOG INFORMATION.TESTED IN SITU. ROADWAY AND AREA LUMINAIRE. (1) 70 CRI, 5000K, 1050MA LIGHTSQUARE WITH 16 LEDS AND TYPE V WIDE OPTICS.

Spectral Parameters

CCT (K): 4884
 CIE u': 0.2101
 CIE v': 0.4904
 Duv: 0.0037
 CIE x: 0.3493
 CIE y: 0.3624
 CIE z: 0.2884
 Peak Wavelength (nm): 444
 Dominant Wavelength (nm): 571
 Purity: 13.7
 Rf: 74.9
 Rg: 96.3

| | | | |
|-----------|------|------|-------|
| CRI (Ra): | 73.5 | | |
| R1: | 70.5 | R9: | -28.4 |
| R2: | 77.7 | R10: | 48.6 |
| R3: | 84.6 | R11: | 73.2 |
| R4: | 74.7 | R12: | 50.7 |
| R5: | 71.9 | R13: | 71.2 |
| R6: | 70.7 | R14: | 91.4 |
| R7: | 81.2 | | |
| R8: | 56.9 | | |



Test Conditions

Stabilization Time: 240M
 Operation Time: 12H
 Room Temperature (°C) / RH%: 25.0./44%
 Sphere Temperature (°C): 25.7

REPORT NUMBER: SP1-1908-441-4-R4

| Measurement and Test Equipment | | | |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument | Identification Number | Calibration Date | Calibration Due Date |
| Photometer | IN0058 | 6/28/2019 | 12/28/2019 |
| Power Meter | IN0071 | 12/5/2018 | 12/5/2019 |
| AC Power Source | IN0063 | 12/5/2018 | 12/5/2019 |
| DC Power Source | IN0208 | 12/5/2018 | 12/5/2019 |
| Sphere Thermometer | IN0085 | 12/5/2018 | 12/5/2019 |
| Room Thermometer | IN0046 | 12/5/2018 | 12/5/2019 |

REPORT NUMBER: SP1-1908-441-4-R4

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 5000K 4-step quadrangle

REPORT NUMBER: SP1-1908-441-4-R4

Photopic Flux vs. Wavelength



#####

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 2945 | NR | 490 | 37941 | NR | 620 | 88803 | NR | 750 | 3908 | NR | 880 | 2997 | NR |
| 365 | 2596 | NR | 495 | 48525 | NR | 625 | 80578 | NR | 755 | 3988 | NR | 885 | 2927 | NR |
| 370 | 2732 | NR | 500 | 60609 | NR | 630 | 73127 | NR | 760 | 3335 | NR | 890 | 2649 | NR |
| 375 | 2894 | NR | 505 | 72036 | NR | 635 | 66244 | NR | 765 | 3438 | NR | 895 | 2828 | NR |
| 380 | 2822 | NR | 510 | 82168 | NR | 640 | 59440 | NR | 770 | 3427 | NR | 900 | 1407 | NR |
| 385 | 2394 | NR | 515 | 90898 | NR | 645 | 52864 | NR | 775 | 2759 | NR | 905 | 2224 | NR |
| 390 | 2370 | NR | 520 | 97142 | NR | 650 | 47085 | NR | 780 | 2340 | NR | 910 | 2905 | NR |
| 395 | 2267 | NR | 525 | 103255 | NR | 655 | 41789 | NR | 785 | 2412 | NR | 915 | 3350 | NR |
| 400 | 2262 | NR | 530 | 106697 | NR | 660 | 37064 | NR | 790 | 1999 | NR | 920 | 3114 | NR |
| 405 | 3000 | NR | 535 | 110081 | NR | 665 | 32299 | NR | 795 | 2054 | NR | 925 | 2834 | NR |
| 410 | 5324 | NR | 540 | 112494 | NR | 670 | 28142 | NR | 800 | 2331 | NR | 930 | 2271 | NR |
| 415 | 10725 | NR | 545 | 115513 | NR | 675 | 24505 | NR | 805 | 2648 | NR | 935 | 2228 | NR |
| 420 | 22128 | NR | 550 | 117203 | NR | 680 | 21162 | NR | 810 | 2485 | NR | 940 | 2833 | NR |
| 425 | 44095 | NR | 555 | 119753 | NR | 685 | 18400 | NR | 815 | 2409 | NR | 945 | 2941 | NR |
| 430 | 77002 | NR | 560 | 122602 | NR | 690 | 16065 | NR | 820 | 2221 | NR | 950 | 2323 | NR |
| 435 | 119881 | NR | 565 | 124314 | NR | 695 | 13860 | NR | 825 | 1562 | NR | 955 | 1667 | NR |
| 440 | 164454 | NR | 570 | 126775 | NR | 700 | 12177 | NR | 830 | 2249 | NR | 960 | 749 | NR |
| 445 | 179997 | NR | 575 | 127511 | NR | 705 | 10757 | NR | 835 | 2573 | NR | 965 | 2669 | NR |
| 450 | 142822 | NR | 580 | 127577 | NR | 710 | 9601 | NR | 840 | 2764 | NR | 970 | 3968 | NR |
| 455 | 90008 | NR | 585 | 126153 | NR | 715 | 8944 | NR | 845 | 3109 | NR | 975 | 3886 | NR |
| 460 | 60557 | NR | 590 | 123678 | NR | 720 | 7947 | NR | 850 | 2963 | NR | 980 | 2788 | NR |
| 465 | 43305 | NR | 595 | 119774 | NR | 725 | 7062 | NR | 855 | 2336 | NR | 985 | 3496 | NR |
| 470 | 31089 | NR | 600 | 115733 | NR | 730 | 6004 | NR | 860 | 2118 | NR | 990 | 2913 | NR |
| 475 | 26278 | NR | 605 | 109231 | NR | 735 | 5594 | NR | 865 | 3144 | NR | 995 | 4659 | NR |
| 480 | 27060 | NR | 610 | 102408 | NR | 740 | 5165 | NR | 870 | 3069 | NR | 1000 | 1308 | NR |
| 485 | 30698 | NR | 615 | 96015 | NR | 745 | 4687 | NR | 875 | 3311 | NR | | | |

REPORT NUMBER: SP1-1908-441-4-R4

Scotopic Flux vs. Wavelength



Scotopic Lumens: 13493.5 S/P: 1.77

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 2945 | NR | 490 | 37941 | NR | 620 | 88803 | NR | 750 | 3908 | NR | 880 | 2997 | NR |
| 365 | 2596 | NR | 495 | 48525 | NR | 625 | 80578 | NR | 755 | 3988 | NR | 885 | 2927 | NR |
| 370 | 2732 | NR | 500 | 60609 | NR | 630 | 73127 | NR | 760 | 3335 | NR | 890 | 2649 | NR |
| 375 | 2894 | NR | 505 | 72036 | NR | 635 | 66244 | NR | 765 | 3438 | NR | 895 | 2828 | NR |
| 380 | 2822 | NR | 510 | 82168 | NR | 640 | 59440 | NR | 770 | 3427 | NR | 900 | 1407 | NR |
| 385 | 2394 | NR | 515 | 90898 | NR | 645 | 52864 | NR | 775 | 2759 | NR | 905 | 2224 | NR |
| 390 | 2370 | NR | 520 | 97142 | NR | 650 | 47085 | NR | 780 | 2340 | NR | 910 | 2905 | NR |
| 395 | 2267 | NR | 525 | 103255 | NR | 655 | 41789 | NR | 785 | 2412 | NR | 915 | 3350 | NR |
| 400 | 2262 | NR | 530 | 106697 | NR | 660 | 37064 | NR | 790 | 1999 | NR | 920 | 3114 | NR |
| 405 | 3000 | NR | 535 | 110081 | NR | 665 | 32299 | NR | 795 | 2054 | NR | 925 | 2834 | NR |
| 410 | 5324 | NR | 540 | 112494 | NR | 670 | 28142 | NR | 800 | 2331 | NR | 930 | 2271 | NR |
| 415 | 10725 | NR | 545 | 115513 | NR | 675 | 24505 | NR | 805 | 2648 | NR | 935 | 2228 | NR |
| 420 | 22128 | NR | 550 | 117203 | NR | 680 | 21162 | NR | 810 | 2485 | NR | 940 | 2833 | NR |
| 425 | 44095 | NR | 555 | 119753 | NR | 685 | 18400 | NR | 815 | 2409 | NR | 945 | 2941 | NR |
| 430 | 77002 | NR | 560 | 122602 | NR | 690 | 16065 | NR | 820 | 2221 | NR | 950 | 2323 | NR |
| 435 | 119881 | NR | 565 | 124314 | NR | 695 | 13860 | NR | 825 | 1562 | NR | 955 | 1667 | NR |
| 440 | 164454 | NR | 570 | 126775 | NR | 700 | 12177 | NR | 830 | 2249 | NR | 960 | 749 | NR |
| 445 | 179997 | NR | 575 | 127511 | NR | 705 | 10757 | NR | 835 | 2573 | NR | 965 | 2669 | NR |
| 450 | 142822 | NR | 580 | 127577 | NR | 710 | 9601 | NR | 840 | 2764 | NR | 970 | 3968 | NR |
| 455 | 90008 | NR | 585 | 126153 | NR | 715 | 8944 | NR | 845 | 3109 | NR | 975 | 3886 | NR |
| 460 | 60557 | NR | 590 | 123678 | NR | 720 | 7947 | NR | 850 | 2963 | NR | 980 | 2788 | NR |
| 465 | 43305 | NR | 595 | 119774 | NR | 725 | 7062 | NR | 855 | 2336 | NR | 985 | 3496 | NR |
| 470 | 31089 | NR | 600 | 115733 | NR | 730 | 6004 | NR | 860 | 2118 | NR | 990 | 2913 | NR |
| 475 | 26278 | NR | 605 | 109231 | NR | 735 | 5594 | NR | 865 | 3144 | NR | 995 | 4659 | NR |
| 480 | 27060 | NR | 610 | 102408 | NR | 740 | 5165 | NR | 870 | 3069 | NR | 1000 | 1308 | NR |
| 485 | 30698 | NR | 615 | 96015 | NR | 745 | 4687 | NR | 875 | 3311 | NR | | | |

REPORT NUMBER: SP1-1908-441-4-R4

Melanopic Flux vs. Wavelength



Melanopic Lumens: 5378.9 M/P: 0.71

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 2945 | NR | 490 | 37941 | NR | 620 | 88803 | NR | 750 | 3908 | NR | 880 | 2997 | NR |
| 365 | 2596 | NR | 495 | 48525 | NR | 625 | 80578 | NR | 755 | 3988 | NR | 885 | 2927 | NR |
| 370 | 2732 | NR | 500 | 60609 | NR | 630 | 73127 | NR | 760 | 3335 | NR | 890 | 2649 | NR |
| 375 | 2894 | NR | 505 | 72036 | NR | 635 | 66244 | NR | 765 | 3438 | NR | 895 | 2828 | NR |
| 380 | 2822 | NR | 510 | 82168 | NR | 640 | 59440 | NR | 770 | 3427 | NR | 900 | 1407 | NR |
| 385 | 2394 | NR | 515 | 90898 | NR | 645 | 52864 | NR | 775 | 2759 | NR | 905 | 2224 | NR |
| 390 | 2370 | NR | 520 | 97142 | NR | 650 | 47085 | NR | 780 | 2340 | NR | 910 | 2905 | NR |
| 395 | 2267 | NR | 525 | 103255 | NR | 655 | 41789 | NR | 785 | 2412 | NR | 915 | 3350 | NR |
| 400 | 2262 | NR | 530 | 106697 | NR | 660 | 37064 | NR | 790 | 1999 | NR | 920 | 3114 | NR |
| 405 | 3000 | NR | 535 | 110081 | NR | 665 | 32299 | NR | 795 | 2054 | NR | 925 | 2834 | NR |
| 410 | 5324 | NR | 540 | 112494 | NR | 670 | 28142 | NR | 800 | 2331 | NR | 930 | 2271 | NR |
| 415 | 10725 | NR | 545 | 115513 | NR | 675 | 24505 | NR | 805 | 2648 | NR | 935 | 2228 | NR |
| 420 | 22128 | NR | 550 | 117203 | NR | 680 | 21162 | NR | 810 | 2485 | NR | 940 | 2833 | NR |
| 425 | 44095 | NR | 555 | 119753 | NR | 685 | 18400 | NR | 815 | 2409 | NR | 945 | 2941 | NR |
| 430 | 77002 | NR | 560 | 122602 | NR | 690 | 16065 | NR | 820 | 2221 | NR | 950 | 2323 | NR |
| 435 | 119881 | NR | 565 | 124314 | NR | 695 | 13860 | NR | 825 | 1562 | NR | 955 | 1667 | NR |
| 440 | 164454 | NR | 570 | 126775 | NR | 700 | 12177 | NR | 830 | 2249 | NR | 960 | 749 | NR |
| 445 | 179997 | NR | 575 | 127511 | NR | 705 | 10757 | NR | 835 | 2573 | NR | 965 | 2669 | NR |
| 450 | 142822 | NR | 580 | 127577 | NR | 710 | 9601 | NR | 840 | 2764 | NR | 970 | 3968 | NR |
| 455 | 90008 | NR | 585 | 126153 | NR | 715 | 8944 | NR | 845 | 3109 | NR | 975 | 3886 | NR |
| 460 | 60557 | NR | 590 | 123678 | NR | 720 | 7947 | NR | 850 | 2963 | NR | 980 | 2788 | NR |
| 465 | 43305 | NR | 595 | 119774 | NR | 725 | 7062 | NR | 855 | 2336 | NR | 985 | 3496 | NR |
| 470 | 31089 | NR | 600 | 115733 | NR | 730 | 6004 | NR | 860 | 2118 | NR | 990 | 2913 | NR |
| 475 | 26278 | NR | 605 | 109231 | NR | 735 | 5594 | NR | 865 | 3144 | NR | 995 | 4659 | NR |
| 480 | 27060 | NR | 610 | 102408 | NR | 740 | 5165 | NR | 870 | 3069 | NR | 1000 | 1308 | NR |
| 485 | 30698 | NR | 615 | 96015 | NR | 745 | 4687 | NR | 875 | 3311 | NR | | | |

REPORT NUMBER: SP1-1908-441-4-R4




TM-30-18

Summary

$R_f = 74.9$
 $R_g = 96.3$
 CIE $R_a = 73.5$
 $R_g = -28.4$



Color Vector Graphics



REPORT NUMBER: SP1-1908-441-4-R4

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)



| | | | |
|------------|------------|------------|------------|
| CES01 = 85 | CES26 = 61 | CES51 = 90 | CES76 = 52 |
| CES02 = 60 | CES27 = 84 | CES52 = 91 | CES77 = 71 |
| CES03 = 30 | CES28 = 81 | CES53 = 79 | CES78 = 54 |
| CES04 = 69 | CES29 = 58 | CES54 = 83 | CES79 = 80 |
| CES05 = 46 | CES30 = 67 | CES55 = 83 | CES80 = 77 |
| CES06 = 50 | CES31 = 63 | CES56 = 73 | CES81 = 77 |
| CES07 = 39 | CES32 = 59 | CES57 = 72 | CES82 = 90 |
| CES08 = 38 | CES33 = 69 | CES58 = 73 | CES83 = 86 |
| CES09 = 29 | CES34 = 69 | CES59 = 88 | CES84 = 88 |
| CES10 = 73 | CES35 = 83 | CES60 = 93 | CES85 = 84 |
| CES11 = 56 | CES36 = 95 | CES61 = 88 | CES86 = 75 |
| CES12 = 61 | CES37 = 78 | CES62 = 85 | CES87 = 78 |
| CES13 = 41 | CES38 = 76 | CES63 = 77 | CES88 = 79 |
| CES14 = 74 | CES39 = 93 | CES64 = 74 | CES89 = 75 |
| CES15 = 70 | CES40 = 86 | CES65 = 67 | CES90 = 77 |
| CES16 = 46 | CES41 = 87 | CES66 = 69 | CES91 = 89 |
| CES17 = 49 | CES42 = 78 | CES67 = 67 | CES92 = 66 |
| CES18 = 55 | CES43 = 75 | CES68 = 73 | CES93 = 80 |
| CES19 = 71 | CES44 = 99 | CES69 = 81 | CES94 = 57 |
| CES20 = 64 | CES45 = 83 | CES70 = 63 | CES95 = 71 |
| CES21 = 85 | CES46 = 81 | CES71 = 60 | CES96 = 78 |
| CES22 = 77 | CES47 = 80 | CES72 = 86 | CES97 = 85 |
| CES23 = 91 | CES48 = 72 | CES73 = 53 | CES98 = 75 |
| CES24 = 90 | CES49 = 81 | CES74 = 96 | CES99 = 62 |
| CES25 = 71 | CES50 = 89 | CES75 = 58 | |



REPORT NUMBER: SP1-1908-441-4-R4

TM-30-18

Color Rendition by Hue-Angle Bin



REPORT NUMBER: SP1-1908-441-4-R4

TM-30-18

Measure Comparisons



(END OF REPORT)