

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: McGRAW-EDISON

Report Number: P634338

Luminaire Tested: GWS-SA3B-750-U-AFL-W-GRSWH

Issue Date: 1/10/2023

Test Information

Test Method: LM-79-2019
Report Number: P634338
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2209-782-47)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/10/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: McGRAW-EDISON
Catalog Number: GWS-SA3B-750-U-AFL-W-GRSWH
Description: GALLEON WALL SLIM LUMINAIRE. (3) LIGHTSQUARES WITH 16 LEDS EACH AND AUTOMOTIVE FRONTLINE OPTICS W/ FACTORY INSTALLED GLARE SHIELD, WH
Light Source: (48) 5000K CCT, 70 CRI LEDS
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 9652.5 lumens
Efficiency: N/A
Efficacy: 141.3 lumens/watt
Luminous Opening: Rectangular (W 1.5' x L: 0.5' x H: 0')
IES Classification: Type II - Short
BUG Rating: B2 - U0 - G1

Input Watts (W): 68.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 0
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT




REPORT NUMBER: P634338

CATALOG NUMBER: GWS-SA3B-750-U-AFL-W-GRSWH

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 10 foot mounting height. Maximum calculated value = 35.1 fc
 Type II - Short - N/A

REPORT NUMBER: P634338
CATALOG NUMBER: GWS-SA3B-750-U-AFL-W-GRSWH

Luminous Intensity Polar Plot



— Vertical Plane Through 51-Deg Lateral - - - Horizontal Cone Through 52.5-Deg Vertical

REPORT NUMBER: P634338

CATALOG NUMBER: GWS-SA3B-750-U-AFL-W-GRSWH


FLUX DISTRIBUTION:

| | | Downward | Upward | Total |
|--------------------|-----------|----------|--------|--------|
| House Side | Lumens | 1880.7 | 0.0 | 1880.7 |
| | % Fixture | 19.5 | 0.0 | 19.5 |
| Street Side | Lumens | 7771.8 | 0.0 | 7771.8 |
| | % Fixture | 80.5 | 0.0 | 80.5 |
| Total | Lumens | 9652.5 | 0.0 | 9652.5 |
| | % Fixture | 100.0 | 0.0 | 100.0 |

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 268.2 | 2.8 |
| 10°-20° | 696.9 | 7.2 |
| 20°-30° | 1133.0 | 11.7 |
| 30°-40° | 1795.6 | 18.6 |
| 40°-50° | 2708.2 | 28.1 |
| 50°-60° | 2342.8 | 24.3 |
| 60°-70° | 531.1 | 5.5 |
| 70°-80° | 156.6 | 1.6 |
| 80°-90° | 20.2 | 0.2 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-90° | 9652.5 | 100.0 |
| 0°-180° | 9652.5 | 100.0 |

Coefficient of Utilization



REPORT NUMBER: P634338


CATALOG NUMBER: GWS-SA3B-750-U-AFL-W-GRSWH

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

| Zone | Lumens | % Fixture | Zone Rating/Lumen Limit | | |
|----------------|--------|-----------|-------------------------|------|--------|
| | | | B | U | G |
| FL (0°-30°) | 1440.7 | 14.9 | | | |
| FM (30°-60°) | 5905.5 | 61.2 | | | |
| FH (60°-80°) | 418.0 | 4.3 | | | G0/660 |
| FVH (80°-90°) | 7.6 | 0.1 | | | G0/10 |
| BL (0°-30°) | 657.4 | 6.8 | B2/1000 | | |
| BM (30°-60°) | 941.0 | 9.7 | B1/1000 | | |
| BH (60°-80°) | 269.7 | 2.8 | B1/500 | | G1/500 |
| BVH (80°-90°) | 12.6 | 0.1 | | | G1/100 |
| UL (90°-100°) | 0.0 | 0.0 | | U0/0 | |
| UH (100°-180°) | 0.0 | 0.0 | | U0/0 | |

BUG Rating: B2-U0-G1

Type II Short





REPORT NUMBER: P634338

CATALOG NUMBER: GWS-SA3B-750-U-AFL-W-GRSWH

CANDELA DISTRIBUTION (FULL):

| | 0° | 5° | 15° | 25° | 35° | 45° | 51° | 55° | 65° | 75° | 85° |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 2874.0 | 2874.0 | 2874.0 | 2874.0 | 2874.0 | 2874.0 | 2874.0 | 2874.0 | 2874.0 | 2874.0 | 2874.0 |
| 2.5° | 3202.8 | 3221.1 | 3192.9 | 3182.2 | 3164.6 | 3134.1 | 3099.0 | 3089.1 | 3013.6 | 2964.0 | 2908.4 |
| 5° | 3524.7 | 3534.6 | 3511.7 | 3488.8 | 3445.3 | 3391.2 | 3323.3 | 3308.8 | 3171.5 | 3057.9 | 2939.6 |
| 7.5° | 3596.4 | 3592.5 | 3612.4 | 3625.3 | 3620.0 | 3598.6 | 3538.4 | 3510.2 | 3346.2 | 3166.2 | 2991.5 |
| 10° | 3312.6 | 3291.3 | 3364.5 | 3451.4 | 3555.9 | 3676.4 | 3669.6 | 3667.3 | 3524.7 | 3311.8 | 3057.9 |
| 12.5° | 2936.6 | 2925.9 | 2985.4 | 3094.5 | 3292.0 | 3559.0 | 3658.9 | 3736.7 | 3685.6 | 3450.7 | 3131.8 |
| 15° | 2721.5 | 2717.7 | 2758.1 | 2836.7 | 2993.8 | 3330.9 | 3544.5 | 3698.6 | 3823.7 | 3599.4 | 3210.4 |
| 17.5° | 2682.6 | 2684.9 | 2698.6 | 2743.6 | 2856.5 | 3134.1 | 3381.3 | 3596.4 | 3931.2 | 3762.6 | 3308.8 |
| 20° | 2796.2 | 2811.5 | 2787.8 | 2794.7 | 2855.7 | 3063.2 | 3269.9 | 3493.4 | 3999.8 | 3926.6 | 3414.8 |
| 22.5° | 3048.7 | 3043.4 | 2991.5 | 2961.0 | 2961.7 | 3106.7 | 3257.7 | 3445.3 | 4044.8 | 4086.0 | 3510.9 |
| 25° | 3334.7 | 3328.6 | 3266.8 | 3199.0 | 3156.2 | 3224.9 | 3345.4 | 3496.4 | 4085.3 | 4231.7 | 3588.0 |
| 27.5° | 3672.6 | 3653.6 | 3584.9 | 3498.0 | 3403.4 | 3433.1 | 3514.7 | 3634.5 | 4147.8 | 4375.1 | 3639.1 |
| 30° | 3999.8 | 4022.0 | 3923.6 | 3820.6 | 3720.7 | 3702.4 | 3749.7 | 3858.0 | 4275.2 | 4542.9 | 3700.1 |
| 32.5° | 4433.8 | 4426.2 | 4317.1 | 4182.9 | 4040.3 | 4026.5 | 4063.9 | 4163.1 | 4504.0 | 4774.8 | 3793.1 |
| 35° | 4959.4 | 4960.9 | 4806.1 | 4624.5 | 4421.6 | 4385.0 | 4447.6 | 4543.7 | 4845.0 | 5089.0 | 3940.4 |
| 37.5° | 5505.5 | 5503.2 | 5368.2 | 5162.3 | 4885.4 | 4833.5 | 4905.2 | 4976.9 | 5271.3 | 5516.9 | 4169.2 |
| 40° | 5888.4 | 5903.7 | 5840.4 | 5732.0 | 5469.7 | 5343.0 | 5406.4 | 5455.9 | 5735.1 | 6020.4 | 4470.5 |
| 42.5° | 6105.8 | 6128.7 | 6142.4 | 6207.2 | 6069.2 | 5934.2 | 5911.3 | 5937.2 | 6149.3 | 6487.9 | 4753.4 |
| 45° | 6152.3 | 6182.8 | 6282.7 | 6523.0 | 6576.4 | 6538.3 | 6463.5 | 6401.0 | 6458.2 | 6819.7 | 4938.8 |
| 47.5° | 5947.1 | 6000.5 | 6214.1 | 6634.4 | 6946.3 | 7066.1 | 6982.9 | 6887.6 | 6636.7 | 6905.1 | 4919.7 |
| 50° | 5134.1 | 5196.6 | 5677.9 | 6407.1 | 6999.0 | 7435.3 | 7442.9 | 7301.8 | 6615.3 | 6658.8 | 4680.2 |
| 52.5° | 4064.7 | 4107.4 | 4382.7 | 5431.5 | 6482.6 | 7420.0 | 7725.1 | 7574.1 | 6512.3 | 6350.6 | 4380.5 |
| 55° | 2429.3 | 2498.0 | 2755.0 | 3583.4 | 5050.1 | 6576.4 | 7226.3 | 7299.5 | 6462.0 | 6092.1 | 4176.0 |
| 57.5° | 820.0 | 853.5 | 1099.1 | 1582.7 | 2976.2 | 4815.2 | 5583.3 | 5880.8 | 5866.3 | 5697.0 | 3777.1 |
| 60° | 390.5 | 398.2 | 447.7 | 600.3 | 1191.4 | 2516.3 | 3305.0 | 3648.2 | 3960.9 | 3992.2 | 2350.0 |
| 62.5° | 297.5 | 302.0 | 327.2 | 360.0 | 479.0 | 1060.2 | 1514.8 | 1777.2 | 1898.5 | 1629.2 | 855.8 |
| 65° | 248.7 | 252.5 | 271.5 | 292.1 | 325.7 | 459.2 | 581.2 | 670.5 | 604.1 | 470.6 | 408.1 |
| 67.5° | 207.5 | 210.5 | 225.0 | 247.1 | 270.0 | 307.4 | 322.6 | 331.8 | 347.8 | 390.5 | 375.3 |
| 70° | 162.5 | 165.5 | 180.8 | 199.8 | 222.0 | 231.1 | 245.6 | 254.8 | 286.8 | 341.7 | 340.2 |
| 72.5° | 125.1 | 128.9 | 137.3 | 149.5 | 167.8 | 177.0 | 193.0 | 203.7 | 222.0 | 266.2 | 284.5 |
| 75° | 91.5 | 93.8 | 101.4 | 105.3 | 107.5 | 105.3 | 121.3 | 133.5 | 157.9 | 174.7 | 179.2 |
| 77.5° | 37.4 | 42.0 | 40.4 | 40.4 | 48.1 | 58.0 | 66.4 | 74.0 | 90.8 | 100.7 | 101.4 |
| 80° | 15.3 | 16.8 | 19.8 | 22.1 | 26.7 | 34.3 | 39.7 | 42.7 | 50.3 | 56.4 | 61.0 |
| 82.5° | 9.2 | 9.9 | 11.4 | 12.2 | 15.3 | 19.8 | 22.9 | 25.2 | 31.3 | 37.4 | 39.7 |
| 85° | 4.6 | 4.6 | 5.3 | 6.1 | 7.6 | 9.2 | 10.7 | 12.2 | 16.0 | 19.8 | 22.1 |
| 87.5° | 0.8 | 0.8 | 0.8 | 1.5 | 2.3 | 3.1 | 3.8 | 4.6 | 5.3 | 6.1 | 7.6 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P634338

CATALOG NUMBER: GWS-SA3B-750-U-AFL-W-GRSWH

CANDELA DISTRIBUTION (continued):

| | 90° | 95° | 105° | 115° | 125° | 135° | 145° | 155° | 165° | 175° | 180° |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 2874.0 | 2874.0 | 2874.0 | 2874.0 | 2874.0 | 2874.0 | 2874.0 | 2874.0 | 2874.0 | 2874.0 | 2874.0 |
| 2.5° | 2875.6 | 2834.4 | 2786.3 | 2748.2 | 2703.9 | 2671.1 | 2624.6 | 2595.6 | 2568.2 | 2545.3 | 2528.5 |
| 5° | 2878.6 | 2809.2 | 2709.3 | 2620.8 | 2529.3 | 2442.3 | 2353.1 | 2280.6 | 2215.8 | 2161.6 | 2157.0 |
| 7.5° | 2896.2 | 2796.2 | 2639.9 | 2485.0 | 2306.5 | 2134.2 | 1961.8 | 1821.4 | 1714.7 | 1659.0 | 1647.5 |
| 10° | 2925.9 | 2794.7 | 2568.9 | 2321.8 | 2017.5 | 1739.8 | 1535.4 | 1428.6 | 1366.8 | 1344.7 | 1337.1 |
| 12.5° | 2957.2 | 2790.9 | 2478.2 | 2091.5 | 1668.9 | 1425.6 | 1313.5 | 1300.5 | 1311.9 | 1313.5 | 1312.7 |
| 15° | 2995.3 | 2788.6 | 2363.8 | 1821.4 | 1414.1 | 1279.9 | 1287.5 | 1315.0 | 1341.7 | 1347.8 | 1347.8 |
| 17.5° | 3041.8 | 2783.3 | 2208.2 | 1557.5 | 1254.7 | 1251.7 | 1292.1 | 1328.7 | 1353.9 | 1358.5 | 1358.5 |
| 20° | 3090.7 | 2769.5 | 2016.7 | 1342.4 | 1189.9 | 1234.1 | 1277.6 | 1305.8 | 1323.4 | 1329.5 | 1330.2 |
| 22.5° | 3124.2 | 2732.9 | 1796.3 | 1183.0 | 1149.5 | 1200.6 | 1231.8 | 1260.8 | 1260.8 | 1245.6 | 1241.0 |
| 25° | 3131.1 | 2654.4 | 1557.5 | 1073.9 | 1101.4 | 1148.7 | 1180.7 | 1164.0 | 1132.7 | 1120.5 | 1119.7 |
| 27.5° | 3105.9 | 2539.9 | 1321.8 | 996.1 | 1043.4 | 1090.7 | 1085.4 | 1061.0 | 1047.3 | 1035.0 | 1039.6 |
| 30° | 3075.4 | 2402.7 | 1117.4 | 932.1 | 976.3 | 1022.8 | 1004.5 | 996.1 | 986.2 | 972.5 | 975.6 |
| 32.5° | 3054.8 | 2249.3 | 960.3 | 882.5 | 931.3 | 938.9 | 951.9 | 951.1 | 942.0 | 916.1 | 914.5 |
| 35° | 3060.9 | 2094.5 | 855.0 | 842.1 | 893.9 | 890.9 | 915.3 | 910.7 | 847.4 | 811.6 | 809.3 |
| 37.5° | 3109.7 | 1945.8 | 793.3 | 810.0 | 834.4 | 853.5 | 874.9 | 820.0 | 797.8 | 775.0 | 776.5 |
| 40° | 3202.8 | 1807.7 | 759.7 | 792.5 | 798.6 | 826.8 | 777.2 | 776.5 | 766.6 | 746.0 | 745.2 |
| 42.5° | 3308.0 | 1691.0 | 736.8 | 784.1 | 775.7 | 781.1 | 728.4 | 734.5 | 733.8 | 720.8 | 717.0 |
| 45° | 3372.1 | 1583.5 | 718.5 | 752.8 | 755.1 | 701.7 | 685.7 | 692.6 | 696.4 | 689.5 | 688.8 |
| 47.5° | 3305.7 | 1459.9 | 699.4 | 704.8 | 724.6 | 665.9 | 646.0 | 646.8 | 653.7 | 654.4 | 651.4 |
| 50° | 3119.6 | 1321.8 | 676.6 | 663.6 | 650.6 | 628.5 | 610.2 | 606.4 | 613.2 | 620.1 | 622.4 |
| 52.5° | 2879.4 | 1189.9 | 638.4 | 618.6 | 588.1 | 588.1 | 579.7 | 567.5 | 576.6 | 585.8 | 588.8 |
| 55° | 2703.2 | 1092.3 | 584.3 | 562.1 | 528.6 | 540.0 | 538.5 | 527.8 | 540.0 | 546.9 | 549.2 |
| 57.5° | 2342.4 | 877.9 | 514.1 | 507.2 | 479.0 | 492.7 | 495.8 | 482.1 | 476.0 | 477.5 | 479.8 |
| 60° | 1390.5 | 566.7 | 463.8 | 463.0 | 437.8 | 453.8 | 463.0 | 449.3 | 431.0 | 433.2 | 436.3 |
| 62.5° | 623.9 | 433.2 | 400.4 | 397.4 | 396.6 | 417.2 | 427.1 | 414.2 | 388.2 | 390.5 | 393.6 |
| 65° | 392.8 | 374.5 | 347.8 | 347.8 | 360.0 | 377.6 | 385.2 | 374.5 | 344.8 | 340.9 | 344.0 |
| 67.5° | 364.6 | 348.6 | 321.1 | 315.8 | 321.9 | 336.4 | 337.1 | 316.5 | 299.0 | 295.9 | 295.9 |
| 70° | 327.2 | 315.0 | 288.3 | 277.6 | 275.4 | 274.6 | 272.3 | 267.0 | 255.5 | 252.5 | 254.0 |
| 72.5° | 270.8 | 262.4 | 245.6 | 234.2 | 228.1 | 227.3 | 218.1 | 213.6 | 203.7 | 202.1 | 201.4 |
| 75° | 179.2 | 181.5 | 181.5 | 180.0 | 174.7 | 172.4 | 162.5 | 157.9 | 146.4 | 141.9 | 141.1 |
| 77.5° | 106.0 | 108.3 | 111.4 | 112.1 | 111.4 | 111.4 | 102.2 | 96.9 | 85.4 | 79.3 | 77.8 |
| 80° | 64.8 | 66.4 | 67.9 | 70.2 | 67.1 | 64.8 | 56.4 | 51.1 | 45.8 | 42.0 | 41.2 |
| 82.5° | 42.0 | 43.5 | 44.2 | 45.8 | 44.2 | 41.2 | 34.3 | 31.3 | 27.5 | 24.4 | 23.6 |
| 85° | 23.6 | 24.4 | 25.9 | 25.9 | 23.6 | 21.4 | 17.5 | 15.3 | 13.0 | 11.4 | 11.4 |
| 87.5° | 8.4 | 8.4 | 8.4 | 9.2 | 7.6 | 6.9 | 4.6 | 3.1 | 2.3 | 2.3 | 2.3 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



LM-79-2008: Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGRAW-EDISON

Report Number: SP1-1908-441-4-R4

Test Date: 10/02/2019

Luminaire Tested: SA1C-750-U-5WQ

Data in this report applies to families of products SA1C-760-U-5WQ .

Test Information

Test Method: LM-79-2008
 Report Number: SP1-1908-441-4-R4
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 10/28/2024
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: MCGRAW-EDISON
 Catalog Number: **SA1C-750-U-5WQ**
 Description: MCGRAW EDISON ROADWAY AND AREA LUMINAIRE

THIS IS A REVISION OF SP1-1908-441-4-R3. TO UPDATE THE CATALOG INFORMATION.TESTED IN SITU. ROADWAY AND AREA LUMINAIRE. (1) 70 CRI, 5000K, 1050MA LIGHTSQUARE WITH 16 LEDS AND TYPE V WIDE OPTICS.

Spectral Parameters

| | | | | | |
|---------------------------|--------|-----------|------|------|-------|
| CCT (K): | 4884 | CRI (Ra): | 73.5 | R9: | -28.4 |
| CIE u': | 0.2101 | R1: | 70.5 | R10: | 48.6 |
| CIE v': | 0.4904 | R2: | 77.7 | R11: | 73.2 |
| Duv: | 0.0037 | R3: | 84.6 | R12: | 50.7 |
| CIE x: | 0.3493 | R4: | 74.7 | R13: | 71.2 |
| CIE y: | 0.3624 | R5: | 71.9 | R14: | 91.4 |
| CIE z: | 0.2884 | R6: | 70.7 | | |
| Peak Wavelength (nm): | 444 | R7: | 81.2 | | |
| Dominant Wavelength (nm): | 571 | R8: | 56.9 | | |
| Purity: | 13.7 | | | | |
| Rf: | 74.9 | | | | |
| Rg: | 96.3 | | | | |



Test Conditions

Stabilization Time: 240M
 Operation Time: 12H
 Room Temperature (°C) / RH%: 25.0./44%
 Sphere Temperature (°C): 25.7

REPORT NUMBER: SP1-1908-441-4-R4

| Measurement and Test Equipment | | | |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument | Identification Number | Calibration Date | Calibration Due Date |
| Photometer | IN0058 | 6/28/2019 | 12/28/2019 |
| Power Meter | IN0071 | 12/5/2018 | 12/5/2019 |
| AC Power Source | IN0063 | 12/5/2018 | 12/5/2019 |
| DC Power Source | IN0208 | 12/5/2018 | 12/5/2019 |
| Sphere Thermometer | IN0085 | 12/5/2018 | 12/5/2019 |
| Room Thermometer | IN0046 | 12/5/2018 | 12/5/2019 |

REPORT NUMBER: SP1-1908-441-4-R4

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 5000K 4-step quadrangle

REPORT NUMBER: SP1-1908-441-4-R4

Photopic Flux vs. Wavelength



#####

| λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) |
|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|
| 360 | 2945 | NR | 490 | 37941 | NR | 620 | 88803 | NR | 750 | 3908 | NR | 880 | 2997 | NR |
| 365 | 2596 | NR | 495 | 48525 | NR | 625 | 80578 | NR | 755 | 3988 | NR | 885 | 2927 | NR |
| 370 | 2732 | NR | 500 | 60609 | NR | 630 | 73127 | NR | 760 | 3335 | NR | 890 | 2649 | NR |
| 375 | 2894 | NR | 505 | 72036 | NR | 635 | 66244 | NR | 765 | 3438 | NR | 895 | 2828 | NR |
| 380 | 2822 | NR | 510 | 82168 | NR | 640 | 59440 | NR | 770 | 3427 | NR | 900 | 1407 | NR |
| 385 | 2394 | NR | 515 | 90898 | NR | 645 | 52864 | NR | 775 | 2759 | NR | 905 | 2224 | NR |
| 390 | 2370 | NR | 520 | 97142 | NR | 650 | 47085 | NR | 780 | 2340 | NR | 910 | 2905 | NR |
| 395 | 2267 | NR | 525 | 103255 | NR | 655 | 41789 | NR | 785 | 2412 | NR | 915 | 3350 | NR |
| 400 | 2262 | NR | 530 | 106697 | NR | 660 | 37064 | NR | 790 | 1999 | NR | 920 | 3114 | NR |
| 405 | 3000 | NR | 535 | 110081 | NR | 665 | 32299 | NR | 795 | 2054 | NR | 925 | 2834 | NR |
| 410 | 5324 | NR | 540 | 112494 | NR | 670 | 28142 | NR | 800 | 2331 | NR | 930 | 2271 | NR |
| 415 | 10725 | NR | 545 | 115513 | NR | 675 | 24505 | NR | 805 | 2648 | NR | 935 | 2228 | NR |
| 420 | 22128 | NR | 550 | 117203 | NR | 680 | 21162 | NR | 810 | 2485 | NR | 940 | 2833 | NR |
| 425 | 44095 | NR | 555 | 119753 | NR | 685 | 18400 | NR | 815 | 2409 | NR | 945 | 2941 | NR |
| 430 | 77002 | NR | 560 | 122602 | NR | 690 | 16065 | NR | 820 | 2221 | NR | 950 | 2323 | NR |
| 435 | 119881 | NR | 565 | 124314 | NR | 695 | 13860 | NR | 825 | 1562 | NR | 955 | 1667 | NR |
| 440 | 164454 | NR | 570 | 126775 | NR | 700 | 12177 | NR | 830 | 2249 | NR | 960 | 749 | NR |
| 445 | 179997 | NR | 575 | 127511 | NR | 705 | 10757 | NR | 835 | 2573 | NR | 965 | 2669 | NR |
| 450 | 142822 | NR | 580 | 127577 | NR | 710 | 9601 | NR | 840 | 2764 | NR | 970 | 3968 | NR |
| 455 | 90008 | NR | 585 | 126153 | NR | 715 | 8944 | NR | 845 | 3109 | NR | 975 | 3886 | NR |
| 460 | 60557 | NR | 590 | 123678 | NR | 720 | 7947 | NR | 850 | 2963 | NR | 980 | 2788 | NR |
| 465 | 43305 | NR | 595 | 119774 | NR | 725 | 7062 | NR | 855 | 2336 | NR | 985 | 3496 | NR |
| 470 | 31089 | NR | 600 | 115733 | NR | 730 | 6004 | NR | 860 | 2118 | NR | 990 | 2913 | NR |
| 475 | 26278 | NR | 605 | 109231 | NR | 735 | 5594 | NR | 865 | 3144 | NR | 995 | 4659 | NR |
| 480 | 27060 | NR | 610 | 102408 | NR | 740 | 5165 | NR | 870 | 3069 | NR | 1000 | 1308 | NR |
| 485 | 30698 | NR | 615 | 96015 | NR | 745 | 4687 | NR | 875 | 3311 | NR | | | |

REPORT NUMBER: SP1-1908-441-4-R4

Scotopic Flux vs. Wavelength



Scotopic Lumens: 13493.5 S/P: 1.77

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 2945 | NR | 490 | 37941 | NR | 620 | 88803 | NR | 750 | 3908 | NR | 880 | 2997 | NR |
| 365 | 2596 | NR | 495 | 48525 | NR | 625 | 80578 | NR | 755 | 3988 | NR | 885 | 2927 | NR |
| 370 | 2732 | NR | 500 | 60609 | NR | 630 | 73127 | NR | 760 | 3335 | NR | 890 | 2649 | NR |
| 375 | 2894 | NR | 505 | 72036 | NR | 635 | 66244 | NR | 765 | 3438 | NR | 895 | 2828 | NR |
| 380 | 2822 | NR | 510 | 82168 | NR | 640 | 59440 | NR | 770 | 3427 | NR | 900 | 1407 | NR |
| 385 | 2394 | NR | 515 | 90898 | NR | 645 | 52864 | NR | 775 | 2759 | NR | 905 | 2224 | NR |
| 390 | 2370 | NR | 520 | 97142 | NR | 650 | 47085 | NR | 780 | 2340 | NR | 910 | 2905 | NR |
| 395 | 2267 | NR | 525 | 103255 | NR | 655 | 41789 | NR | 785 | 2412 | NR | 915 | 3350 | NR |
| 400 | 2262 | NR | 530 | 106697 | NR | 660 | 37064 | NR | 790 | 1999 | NR | 920 | 3114 | NR |
| 405 | 3000 | NR | 535 | 110081 | NR | 665 | 32299 | NR | 795 | 2054 | NR | 925 | 2834 | NR |
| 410 | 5324 | NR | 540 | 112494 | NR | 670 | 28142 | NR | 800 | 2331 | NR | 930 | 2271 | NR |
| 415 | 10725 | NR | 545 | 115513 | NR | 675 | 24505 | NR | 805 | 2648 | NR | 935 | 2228 | NR |
| 420 | 22128 | NR | 550 | 117203 | NR | 680 | 21162 | NR | 810 | 2485 | NR | 940 | 2833 | NR |
| 425 | 44095 | NR | 555 | 119753 | NR | 685 | 18400 | NR | 815 | 2409 | NR | 945 | 2941 | NR |
| 430 | 77002 | NR | 560 | 122602 | NR | 690 | 16065 | NR | 820 | 2221 | NR | 950 | 2323 | NR |
| 435 | 119881 | NR | 565 | 124314 | NR | 695 | 13860 | NR | 825 | 1562 | NR | 955 | 1667 | NR |
| 440 | 164454 | NR | 570 | 126775 | NR | 700 | 12177 | NR | 830 | 2249 | NR | 960 | 749 | NR |
| 445 | 179997 | NR | 575 | 127511 | NR | 705 | 10757 | NR | 835 | 2573 | NR | 965 | 2669 | NR |
| 450 | 142822 | NR | 580 | 127577 | NR | 710 | 9601 | NR | 840 | 2764 | NR | 970 | 3968 | NR |
| 455 | 90008 | NR | 585 | 126153 | NR | 715 | 8944 | NR | 845 | 3109 | NR | 975 | 3886 | NR |
| 460 | 60557 | NR | 590 | 123678 | NR | 720 | 7947 | NR | 850 | 2963 | NR | 980 | 2788 | NR |
| 465 | 43305 | NR | 595 | 119774 | NR | 725 | 7062 | NR | 855 | 2336 | NR | 985 | 3496 | NR |
| 470 | 31089 | NR | 600 | 115733 | NR | 730 | 6004 | NR | 860 | 2118 | NR | 990 | 2913 | NR |
| 475 | 26278 | NR | 605 | 109231 | NR | 735 | 5594 | NR | 865 | 3144 | NR | 995 | 4659 | NR |
| 480 | 27060 | NR | 610 | 102408 | NR | 740 | 5165 | NR | 870 | 3069 | NR | 1000 | 1308 | NR |
| 485 | 30698 | NR | 615 | 96015 | NR | 745 | 4687 | NR | 875 | 3311 | NR | | | |

REPORT NUMBER: SP1-1908-441-4-R4

Melanopic Flux vs. Wavelength



Melanopic Lumens: 5378.9 M/P: 0.71

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 2945 | NR | 490 | 37941 | NR | 620 | 88803 | NR | 750 | 3908 | NR | 880 | 2997 | NR |
| 365 | 2596 | NR | 495 | 48525 | NR | 625 | 80578 | NR | 755 | 3988 | NR | 885 | 2927 | NR |
| 370 | 2732 | NR | 500 | 60609 | NR | 630 | 73127 | NR | 760 | 3335 | NR | 890 | 2649 | NR |
| 375 | 2894 | NR | 505 | 72036 | NR | 635 | 66244 | NR | 765 | 3438 | NR | 895 | 2828 | NR |
| 380 | 2822 | NR | 510 | 82168 | NR | 640 | 59440 | NR | 770 | 3427 | NR | 900 | 1407 | NR |
| 385 | 2394 | NR | 515 | 90898 | NR | 645 | 52864 | NR | 775 | 2759 | NR | 905 | 2224 | NR |
| 390 | 2370 | NR | 520 | 97142 | NR | 650 | 47085 | NR | 780 | 2340 | NR | 910 | 2905 | NR |
| 395 | 2267 | NR | 525 | 103255 | NR | 655 | 41789 | NR | 785 | 2412 | NR | 915 | 3350 | NR |
| 400 | 2262 | NR | 530 | 106697 | NR | 660 | 37064 | NR | 790 | 1999 | NR | 920 | 3114 | NR |
| 405 | 3000 | NR | 535 | 110081 | NR | 665 | 32299 | NR | 795 | 2054 | NR | 925 | 2834 | NR |
| 410 | 5324 | NR | 540 | 112494 | NR | 670 | 28142 | NR | 800 | 2331 | NR | 930 | 2271 | NR |
| 415 | 10725 | NR | 545 | 115513 | NR | 675 | 24505 | NR | 805 | 2648 | NR | 935 | 2228 | NR |
| 420 | 22128 | NR | 550 | 117203 | NR | 680 | 21162 | NR | 810 | 2485 | NR | 940 | 2833 | NR |
| 425 | 44095 | NR | 555 | 119753 | NR | 685 | 18400 | NR | 815 | 2409 | NR | 945 | 2941 | NR |
| 430 | 77002 | NR | 560 | 122602 | NR | 690 | 16065 | NR | 820 | 2221 | NR | 950 | 2323 | NR |
| 435 | 119881 | NR | 565 | 124314 | NR | 695 | 13860 | NR | 825 | 1562 | NR | 955 | 1667 | NR |
| 440 | 164454 | NR | 570 | 126775 | NR | 700 | 12177 | NR | 830 | 2249 | NR | 960 | 749 | NR |
| 445 | 179997 | NR | 575 | 127511 | NR | 705 | 10757 | NR | 835 | 2573 | NR | 965 | 2669 | NR |
| 450 | 142822 | NR | 580 | 127577 | NR | 710 | 9601 | NR | 840 | 2764 | NR | 970 | 3968 | NR |
| 455 | 90008 | NR | 585 | 126153 | NR | 715 | 8944 | NR | 845 | 3109 | NR | 975 | 3886 | NR |
| 460 | 60557 | NR | 590 | 123678 | NR | 720 | 7947 | NR | 850 | 2963 | NR | 980 | 2788 | NR |
| 465 | 43305 | NR | 595 | 119774 | NR | 725 | 7062 | NR | 855 | 2336 | NR | 985 | 3496 | NR |
| 470 | 31089 | NR | 600 | 115733 | NR | 730 | 6004 | NR | 860 | 2118 | NR | 990 | 2913 | NR |
| 475 | 26278 | NR | 605 | 109231 | NR | 735 | 5594 | NR | 865 | 3144 | NR | 995 | 4659 | NR |
| 480 | 27060 | NR | 610 | 102408 | NR | 740 | 5165 | NR | 870 | 3069 | NR | 1000 | 1308 | NR |
| 485 | 30698 | NR | 615 | 96015 | NR | 745 | 4687 | NR | 875 | 3311 | NR | | | |

REPORT NUMBER: SP1-1908-441-4-R4

TM-30-18

Summary

$R_f = 74.9$
 $R_g = 96.3$
 CIE $R_a = 73.5$
 $R_g = -28.4$



Color Vector Graphics



REPORT NUMBER: SP1-1908-441-4-R4

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)

| | | | |
|------------|------------|------------|------------|
| CES01 = 85 | CES26 = 61 | CES51 = 90 | CES76 = 52 |
| CES02 = 60 | CES27 = 84 | CES52 = 91 | CES77 = 71 |
| CES03 = 30 | CES28 = 81 | CES53 = 79 | CES78 = 54 |
| CES04 = 69 | CES29 = 58 | CES54 = 83 | CES79 = 80 |
| CES05 = 46 | CES30 = 67 | CES55 = 83 | CES80 = 77 |
| CES06 = 50 | CES31 = 63 | CES56 = 73 | CES81 = 77 |
| CES07 = 39 | CES32 = 59 | CES57 = 72 | CES82 = 90 |
| CES08 = 38 | CES33 = 69 | CES58 = 73 | CES83 = 86 |
| CES09 = 29 | CES34 = 69 | CES59 = 88 | CES84 = 88 |
| CES10 = 73 | CES35 = 83 | CES60 = 93 | CES85 = 84 |
| CES11 = 56 | CES36 = 95 | CES61 = 88 | CES86 = 75 |
| CES12 = 61 | CES37 = 78 | CES62 = 85 | CES87 = 78 |
| CES13 = 41 | CES38 = 76 | CES63 = 77 | CES88 = 79 |
| CES14 = 74 | CES39 = 93 | CES64 = 74 | CES89 = 75 |
| CES15 = 70 | CES40 = 86 | CES65 = 67 | CES90 = 77 |
| CES16 = 46 | CES41 = 87 | CES66 = 69 | CES91 = 89 |
| CES17 = 49 | CES42 = 78 | CES67 = 67 | CES92 = 66 |
| CES18 = 55 | CES43 = 75 | CES68 = 73 | CES93 = 80 |
| CES19 = 71 | CES44 = 99 | CES69 = 81 | CES94 = 57 |
| CES20 = 64 | CES45 = 83 | CES70 = 63 | CES95 = 71 |
| CES21 = 85 | CES46 = 81 | CES71 = 60 | CES96 = 78 |
| CES22 = 77 | CES47 = 80 | CES72 = 86 | CES97 = 85 |
| CES23 = 91 | CES48 = 72 | CES73 = 53 | CES98 = 75 |
| CES24 = 90 | CES49 = 81 | CES74 = 96 | CES99 = 62 |
| CES25 = 71 | CES50 = 89 | CES75 = 58 | |



REPORT NUMBER: SP1-1908-441-4-R4

TM-30-18

Color Rendition by Hue-Angle Bin



REPORT NUMBER: SP1-1908-441-4-R4

TM-30-18

Measure Comparisons



(END OF REPORT)