

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: McGRAW-EDISON

Report Number: P639311

Luminaire Tested: GWS-SA5B-750-U-SLR-W

Issue Date: 1/10/2023

Test Information

Test Method: LM-79-2019
Report Number: P639311
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2209-782-41)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/10/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: McGRAW-EDISON
Catalog Number: GWS-SA5B-750-U-SLR-W
Description: GALLEON WALL SLIM LUMINAIRE. (5) LIGHTSQUARES WITH 16 LEDS EACH AND
SPILL LIGHT ELIMINATOR RIGHT OPTICS
Light Source: (80) 5000K CCT, 70 CRI LEDS
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 17197.2 lumens
Efficiency: N/A
Efficacy: 148.6 lumens/watt
Luminous Opening: Rectangular (W 1.5' x L: 1' x H: 0')
IES Classification: Type III - Short
BUG Rating: B3 - U0 - G3


Input Watts (W): 115.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 0
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT



REPORT NUMBER: P639311
 CATALOG NUMBER: GWS-SA5B-750-U-SLR-W

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 5.2 fc
 Type III - Short - N/A

REPORT NUMBER: P639311
CATALOG NUMBER: GWS-SA5B-750-U-SLR-W

Luminous Intensity Polar Plot



— Vertical Plane Through 45-Deg Lateral - - - Horizontal Cone Through 62.5-Deg Vertical

REPORT NUMBER: P639311

CATALOG NUMBER: GWS-SA5B-750-U-SLR-W

FLUX DISTRIBUTION:

| | | Downward | Upward | Total |
|--------------------|-----------|----------|--------|---------|
| House Side | Lumens | 4103.6 | 0.0 | 4103.6 |
| | % Fixture | 23.9 | 0.0 | 23.9 |
| Street Side | Lumens | 13093.6 | 0.0 | 13093.6 |
| | % Fixture | 76.1 | 0.0 | 76.1 |
| Total | Lumens | 17197.2 | 0.0 | 17197.2 |
| | % Fixture | 100.0 | 0.0 | 100.0 |

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|---------|-----------|
| 0°-10° | 222.9 | 1.3 |
| 10°-20° | 698.8 | 4.1 |
| 20°-30° | 1085.4 | 6.3 |
| 30°-40° | 1473.6 | 8.6 |
| 40°-50° | 2335.6 | 13.6 |
| 50°-60° | 4120.0 | 24.0 |
| 60°-70° | 4584.1 | 26.7 |
| 70°-80° | 2324.9 | 13.5 |
| 80°-90° | 352.0 | 2.0 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-90° | 17197.2 | 100.0 |
| 0°-180° | 17197.2 | 100.0 |

Coefficient of Utilization



REPORT NUMBER: P639311


CATALOG NUMBER: GWS-SA5B-750-U-SLR-W

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

| Zone | Lumens | % Fixture | Zone Rating/Lumen Limit | | |
|----------------|--------|-----------|-------------------------|------|---------|
| | | | B | U | G |
| FL (0°-30°) | 1122.8 | 6.5 | | | |
| FM (30°-60°) | 5839.2 | 34.0 | | | |
| FH (60°-80°) | 5864.4 | 34.1 | | | G3/7500 |
| FVH (80°-90°) | 267.2 | 1.6 | | | G3/500 |
| BL (0°-30°) | 884.2 | 5.1 | B2/1000 | | |
| BM (30°-60°) | 2090.0 | 12.2 | B2/2500 | | |
| BH (60°-80°) | 1044.6 | 6.1 | B3/2500 | | G3/2500 |
| BVH (80°-90°) | 84.8 | 0.5 | | | G1/100 |
| UL (90°-100°) | 0.0 | 0.0 | | U0/0 | |
| UH (100°-180°) | 0.0 | 0.0 | | U0/0 | |

BUG Rating: B3-U0-G3

Type III Short





REPORT NUMBER: P639311
 CATALOG NUMBER: GWS-SA5B-750-U-SLR-W

CANDELA DISTRIBUTION (FULL):

| | 0° | 1° | 5° | 15° | 25° | 35° | 45° | 55° | 65° | 75° | 85° |
|-------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|
| 0° | 2282.4 | 2282.4 | 2282.4 | 2282.4 | 2282.4 | 2282.4 | 2282.4 | 2282.4 | 2282.4 | 2282.4 | 2282.4 |
| 2.5° | 2453.0 | 2451.7 | 2476.4 | 2514.2 | 2549.3 | 2565.0 | 2591.0 | 2588.4 | 2567.6 | 2540.2 | 2531.1 |
| 5° | 2645.7 | 2650.9 | 2693.9 | 2777.2 | 2869.6 | 2908.7 | 2925.6 | 2919.1 | 2881.3 | 2833.2 | 2748.5 |
| 7.5° | 2820.1 | 2829.3 | 2895.7 | 3020.7 | 3135.2 | 3187.3 | 3229.0 | 3221.2 | 3166.5 | 3076.6 | 2951.7 |
| 10° | 2947.7 | 2958.2 | 3037.6 | 3184.7 | 3312.3 | 3357.9 | 3411.3 | 3413.9 | 3365.7 | 3244.6 | 3117.0 |
| 12.5° | 3075.3 | 3085.8 | 3160.0 | 3294.1 | 3377.4 | 3378.7 | 3410.0 | 3426.9 | 3429.5 | 3373.5 | 3245.9 |
| 15° | 3208.1 | 3217.3 | 3285.0 | 3360.5 | 3356.6 | 3283.7 | 3283.7 | 3316.2 | 3387.8 | 3428.2 | 3339.6 |
| 17.5° | 3321.4 | 3333.1 | 3385.2 | 3360.5 | 3244.6 | 3113.1 | 3097.5 | 3139.1 | 3264.1 | 3419.1 | 3410.0 |
| 20° | 3415.2 | 3424.3 | 3452.9 | 3288.9 | 3077.9 | 2906.1 | 2876.1 | 2924.3 | 3093.6 | 3363.1 | 3463.3 |
| 22.5° | 3505.0 | 3510.2 | 3494.6 | 3195.1 | 2898.3 | 2701.7 | 2665.2 | 2716.0 | 2898.3 | 3264.1 | 3508.9 |
| 25° | 3611.8 | 3606.6 | 3532.3 | 3097.5 | 2734.2 | 2540.2 | 2502.5 | 2559.7 | 2749.8 | 3132.6 | 3558.4 |
| 27.5° | 3735.5 | 3715.9 | 3564.9 | 2992.0 | 2607.9 | 2420.4 | 2394.4 | 2455.6 | 2632.7 | 3011.5 | 3597.4 |
| 30° | 3840.9 | 3803.2 | 3570.1 | 2898.3 | 2542.8 | 2369.7 | 2354.0 | 2411.3 | 2575.4 | 2929.5 | 3646.9 |
| 32.5° | 3958.1 | 3906.0 | 3600.1 | 2873.5 | 2579.3 | 2492.0 | 2512.9 | 2516.8 | 2591.0 | 2906.1 | 3721.1 |
| 35° | 4126.1 | 4058.4 | 3682.1 | 2945.1 | 2954.3 | 3101.4 | 3176.9 | 3075.3 | 2826.7 | 2958.2 | 3861.8 |
| 37.5° | 4380.0 | 4294.0 | 3848.7 | 3255.0 | 3729.0 | 4058.4 | 4240.6 | 4008.9 | 3542.8 | 3154.8 | 4074.0 |
| 40° | 4688.5 | 4579.2 | 4062.3 | 3827.9 | 4452.9 | 4980.2 | 5304.4 | 4964.6 | 4279.7 | 3645.6 | 4372.1 |
| 42.5° | 5119.5 | 5004.9 | 4476.3 | 4390.4 | 5123.4 | 5908.5 | 6331.7 | 5825.2 | 4929.4 | 4279.7 | 4850.0 |
| 45° | 5870.8 | 5760.1 | 5235.4 | 4954.1 | 5908.5 | 7051.7 | 7645.4 | 6941.0 | 5589.5 | 4916.4 | 5743.2 |
| 47.5° | 7258.7 | 7128.5 | 6362.9 | 5579.1 | 6804.3 | 8536.0 | 9366.6 | 8340.7 | 6275.7 | 5645.5 | 7243.1 |
| 50° | 8925.3 | 8800.3 | 7778.2 | 6318.6 | 7793.8 | 10123.1 | 11278.0 | 9985.1 | 7066.0 | 6532.2 | 9035.9 |
| 52.5° | 10930.4 | 10906.9 | 9797.6 | 7253.5 | 8823.7 | 11815.7 | 13399.0 | 11806.6 | 7931.8 | 7726.1 | 11067.1 |
| 55° | 12737.5 | 12966.7 | 12362.6 | 8679.2 | 10154.4 | 13941.9 | 15579.8 | 13793.5 | 9106.2 | 9700.0 | 13445.8 |
| 57.5° | 13711.4 | 14327.3 | 15255.6 | 11587.9 | 12089.1 | 16483.4 | 18271.1 | 16219.1 | 11124.4 | 12986.2 | 15651.4 |
| 60° | 13068.3 | 13766.1 | 15448.3 | 13777.8 | 14008.3 | 18519.8 | 20492.3 | 18258.1 | 13106.0 | 15267.3 | 15526.4 |
| 62.5° | 11998.0 | 12624.3 | 14120.3 | 12499.3 | 14305.2 | 18967.6 | 20544.4 | 18613.5 | 13893.7 | 14109.9 | 14025.2 |
| 65° | 10728.5 | 11360.0 | 12944.6 | 10910.8 | 13361.2 | 17903.9 | 19028.8 | 17568.0 | 12478.4 | 12748.0 | 12779.2 |
| 67.5° | 9042.4 | 9625.7 | 11238.9 | 9701.3 | 12179.0 | 16342.8 | 16702.2 | 16078.5 | 11491.5 | 11921.2 | 11472.0 |
| 70° | 6756.1 | 7282.1 | 8706.5 | 7883.7 | 10266.3 | 14309.1 | 14018.7 | 14111.2 | 10383.5 | 10810.6 | 9582.8 |
| 72.5° | 4616.9 | 5012.7 | 6234.0 | 6195.0 | 7861.5 | 11455.1 | 11050.1 | 11926.4 | 8672.7 | 9239.0 | 7305.6 |
| 75° | 3229.0 | 3537.6 | 4506.2 | 4894.2 | 5942.4 | 8490.4 | 7869.3 | 8926.6 | 6773.0 | 7581.6 | 5330.4 |
| 77.5° | 1981.7 | 2186.1 | 2846.2 | 3626.1 | 3822.7 | 5810.9 | 4887.7 | 6717.1 | 4756.2 | 5529.6 | 3555.8 |
| 80° | 990.8 | 1089.8 | 1382.7 | 2279.8 | 2535.0 | 3424.3 | 2699.1 | 3899.5 | 3218.6 | 3424.3 | 1967.3 |
| 82.5° | 299.5 | 330.7 | 404.9 | 865.8 | 1313.7 | 1971.2 | 1595.0 | 2265.5 | 1757.7 | 1605.4 | 774.7 |
| 85° | 79.4 | 89.8 | 112.0 | 256.5 | 460.9 | 707.0 | 539.0 | 1097.6 | 842.4 | 592.4 | 291.6 |
| 87.5° | 6.5 | 6.5 | 5.2 | 5.2 | 2.6 | 0.0 | 0.0 | 78.1 | 157.5 | 89.8 | 50.8 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P639311
 CATALOG NUMBER: GWS-SA5B-750-U-SLR-W

CANDELA DISTRIBUTION (continued):

| | 90° | 95° | 105° | 115° | 125° | 135° | 145° | 155° | 165° | 175° | 180° |
|-------|---------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 2282.4 | 2282.4 | 2282.4 | 2282.4 | 2282.4 | 2282.4 | 2282.4 | 2282.4 | 2282.4 | 2282.4 | 2282.4 |
| 2.5° | 2485.5 | 2480.3 | 2426.9 | 2387.9 | 2342.3 | 2298.0 | 2252.5 | 2212.1 | 2166.5 | 2121.0 | 2108.0 |
| 5° | 2686.0 | 2649.6 | 2536.3 | 2441.3 | 2347.5 | 2265.5 | 2193.9 | 2119.7 | 2059.8 | 2001.2 | 1979.1 |
| 7.5° | 2863.1 | 2799.3 | 2635.3 | 2490.7 | 2360.5 | 2259.0 | 2153.5 | 2045.5 | 1960.8 | 1877.5 | 1856.7 |
| 10° | 3023.3 | 2938.6 | 2731.6 | 2549.3 | 2404.8 | 2288.9 | 2165.2 | 2020.7 | 1898.3 | 1796.8 | 1769.4 |
| 12.5° | 3141.7 | 3049.3 | 2814.9 | 2605.3 | 2441.3 | 2311.1 | 2188.7 | 2061.1 | 1932.2 | 1800.7 | 1770.7 |
| 15° | 3235.5 | 3139.1 | 2883.9 | 2648.3 | 2442.6 | 2274.6 | 2156.1 | 2111.9 | 2071.5 | 1942.6 | 1887.9 |
| 17.5° | 3311.0 | 3209.4 | 2943.8 | 2674.3 | 2407.4 | 2163.9 | 2061.1 | 2126.2 | 2229.0 | 2148.3 | 2045.5 |
| 20° | 3380.0 | 3277.2 | 2989.4 | 2692.6 | 2329.3 | 2011.6 | 1954.3 | 2092.3 | 2247.3 | 2244.7 | 2152.2 |
| 22.5° | 3455.5 | 3355.3 | 3055.8 | 2703.0 | 2219.9 | 1856.7 | 1890.5 | 2042.9 | 2169.1 | 2206.9 | 2149.6 |
| 25° | 3551.9 | 3463.3 | 3148.3 | 2726.4 | 2096.2 | 1749.9 | 1843.6 | 1979.1 | 2084.5 | 2093.6 | 2059.8 |
| 27.5° | 3663.8 | 3597.4 | 3286.3 | 2781.1 | 1976.4 | 1695.2 | 1789.0 | 1889.2 | 1985.6 | 1989.5 | 1949.1 |
| 30° | 3786.2 | 3742.0 | 3413.9 | 2826.7 | 1886.6 | 1678.3 | 1718.7 | 1799.4 | 1860.6 | 1871.0 | 1835.8 |
| 32.5° | 3942.5 | 3903.4 | 3527.1 | 2796.7 | 1833.2 | 1674.4 | 1653.5 | 1695.2 | 1746.0 | 1746.0 | 1718.7 |
| 35° | 4157.3 | 4102.6 | 3646.9 | 2682.1 | 1768.1 | 1658.8 | 1584.5 | 1596.3 | 1618.4 | 1622.3 | 1606.7 |
| 37.5° | 4462.0 | 4372.1 | 3768.0 | 2455.6 | 1661.4 | 1602.8 | 1505.1 | 1490.8 | 1498.6 | 1509.0 | 1505.1 |
| 40° | 4839.6 | 4692.4 | 3945.1 | 2183.5 | 1533.8 | 1494.7 | 1423.1 | 1395.8 | 1389.2 | 1410.1 | 1417.9 |
| 42.5° | 5314.8 | 5089.5 | 4135.2 | 1929.6 | 1417.9 | 1371.0 | 1326.7 | 1303.3 | 1292.9 | 1328.0 | 1348.9 |
| 45° | 6073.9 | 5702.8 | 4317.5 | 1678.3 | 1352.8 | 1265.6 | 1235.6 | 1218.7 | 1223.9 | 1265.6 | 1291.6 |
| 47.5° | 7385.0 | 6638.9 | 4490.6 | 1519.4 | 1347.6 | 1190.0 | 1153.6 | 1157.5 | 1171.8 | 1216.1 | 1247.3 |
| 50° | 9043.7 | 7892.8 | 4606.5 | 1453.0 | 1363.2 | 1144.5 | 1096.3 | 1117.1 | 1139.3 | 1182.2 | 1218.7 |
| 52.5° | 10732.5 | 9060.7 | 4468.5 | 1416.6 | 1361.9 | 1145.8 | 1042.9 | 1105.4 | 1115.8 | 1158.8 | 1197.8 |
| 55° | 11893.8 | 9190.9 | 3860.5 | 1360.6 | 1341.1 | 1197.8 | 1001.2 | 1100.2 | 1106.7 | 1145.8 | 1180.9 |
| 57.5° | 12336.5 | 8745.6 | 2943.8 | 1376.2 | 1278.6 | 1238.2 | 983.0 | 1063.7 | 1110.6 | 1144.5 | 1180.9 |
| 60° | 11801.4 | 7905.8 | 1789.0 | 1416.6 | 1178.3 | 1235.6 | 994.7 | 997.3 | 1078.1 | 1135.4 | 1171.8 |
| 62.5° | 10792.3 | 6827.7 | 1256.4 | 1302.0 | 1105.4 | 1166.6 | 1022.1 | 919.2 | 1020.8 | 1089.8 | 1122.3 |
| 65° | 9636.2 | 5559.6 | 958.3 | 1121.0 | 1070.3 | 1059.8 | 1031.2 | 850.2 | 942.7 | 1010.4 | 1039.0 |
| 67.5° | 8431.8 | 4321.4 | 778.6 | 835.9 | 967.4 | 958.3 | 942.7 | 789.0 | 850.2 | 898.4 | 930.9 |
| 70° | 6915.0 | 3023.3 | 657.5 | 627.6 | 829.4 | 859.3 | 824.2 | 712.2 | 731.7 | 781.2 | 807.2 |
| 72.5° | 5058.3 | 1884.0 | 540.3 | 518.2 | 666.6 | 751.3 | 733.0 | 627.6 | 636.7 | 683.6 | 704.4 |
| 75° | 3637.8 | 1078.1 | 433.6 | 427.1 | 509.1 | 643.2 | 606.7 | 540.3 | 550.7 | 585.9 | 600.2 |
| 77.5° | 2312.4 | 600.2 | 334.6 | 343.7 | 364.6 | 480.4 | 518.2 | 462.2 | 462.2 | 483.0 | 494.8 |
| 80° | 1238.2 | 343.7 | 244.8 | 248.7 | 255.2 | 367.2 | 408.8 | 358.1 | 358.1 | 343.7 | 358.1 |
| 82.5° | 505.2 | 197.9 | 168.0 | 156.2 | 170.6 | 251.3 | 286.4 | 227.9 | 238.3 | 214.8 | 220.0 |
| 85° | 166.7 | 99.0 | 83.3 | 82.0 | 80.7 | 110.7 | 138.0 | 113.3 | 135.4 | 85.9 | 89.8 |
| 87.5° | 22.1 | 18.2 | 10.4 | 7.8 | 9.1 | 3.9 | 7.8 | 9.1 | 9.1 | 6.5 | 6.5 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P639311
 CATALOG NUMBER: GWS-SA5B-750-U-SLR-W

CANDELA DISTRIBUTION (continued):

| | 185° | 195° | 205° | 215° | 225° | 235° | 245° | 255° | 265° | 270° | 275° |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 2282.4 | 2282.4 | 2282.4 | 2282.4 | 2282.4 | 2282.4 | 2282.4 | 2282.4 | 2282.4 | 2282.4 | 2282.4 |
| 2.5° | 2098.8 | 2088.4 | 2050.7 | 2059.8 | 2053.3 | 2042.9 | 2053.3 | 2033.7 | 2049.4 | 2054.6 | 2087.1 |
| 5° | 1962.1 | 1937.4 | 1900.9 | 1882.7 | 1878.8 | 1868.4 | 1869.7 | 1860.6 | 1863.2 | 1885.3 | 1921.8 |
| 7.5° | 1839.7 | 1816.3 | 1787.7 | 1774.6 | 1762.9 | 1751.2 | 1749.9 | 1748.6 | 1759.0 | 1778.5 | 1813.7 |
| 10° | 1751.2 | 1738.2 | 1726.5 | 1731.7 | 1726.5 | 1721.3 | 1712.1 | 1712.1 | 1729.1 | 1764.2 | 1807.2 |
| 12.5° | 1751.2 | 1748.6 | 1751.2 | 1766.8 | 1765.5 | 1766.8 | 1755.1 | 1761.6 | 1808.5 | 1868.4 | 1929.6 |
| 15° | 1844.9 | 1824.1 | 1824.1 | 1831.9 | 1829.3 | 1829.3 | 1829.3 | 1856.7 | 1963.4 | 2055.9 | 2121.0 |
| 17.5° | 1959.5 | 1898.3 | 1872.3 | 1868.4 | 1867.1 | 1867.1 | 1872.3 | 1930.9 | 2097.5 | 2195.2 | 2232.9 |
| 20° | 2038.9 | 1923.1 | 1880.1 | 1863.2 | 1864.5 | 1867.1 | 1882.7 | 1963.4 | 2147.0 | 2196.5 | 2187.4 |
| 22.5° | 2053.3 | 1903.5 | 1851.5 | 1826.7 | 1830.6 | 1833.2 | 1856.7 | 1942.6 | 2079.3 | 2087.1 | 2068.9 |
| 25° | 1986.9 | 1848.9 | 1792.9 | 1773.3 | 1778.5 | 1777.2 | 1798.1 | 1860.6 | 1958.2 | 1955.6 | 1945.2 |
| 27.5° | 1887.9 | 1761.6 | 1720.0 | 1706.9 | 1716.0 | 1705.6 | 1712.1 | 1760.3 | 1835.8 | 1833.2 | 1829.3 |
| 30° | 1786.4 | 1677.0 | 1639.2 | 1632.7 | 1644.4 | 1628.8 | 1630.1 | 1670.5 | 1722.6 | 1720.0 | 1718.7 |
| 32.5° | 1684.8 | 1592.4 | 1558.5 | 1558.5 | 1570.2 | 1553.3 | 1555.9 | 1591.1 | 1626.2 | 1615.8 | 1615.8 |
| 35° | 1588.4 | 1523.3 | 1496.0 | 1490.8 | 1499.9 | 1488.2 | 1493.4 | 1526.0 | 1539.0 | 1524.7 | 1515.5 |
| 37.5° | 1503.8 | 1475.2 | 1447.8 | 1429.6 | 1430.9 | 1432.2 | 1447.8 | 1472.6 | 1464.8 | 1443.9 | 1432.2 |
| 40° | 1425.7 | 1425.7 | 1399.7 | 1365.8 | 1361.9 | 1371.0 | 1397.1 | 1424.4 | 1402.3 | 1378.8 | 1364.5 |
| 42.5° | 1369.7 | 1381.4 | 1356.7 | 1322.8 | 1315.0 | 1330.7 | 1359.3 | 1378.8 | 1352.8 | 1326.7 | 1307.2 |
| 45° | 1317.6 | 1346.3 | 1329.3 | 1291.6 | 1281.2 | 1299.4 | 1335.9 | 1343.7 | 1308.5 | 1283.8 | 1269.5 |
| 47.5° | 1281.2 | 1320.2 | 1308.5 | 1272.1 | 1256.4 | 1282.5 | 1320.2 | 1318.9 | 1274.7 | 1248.6 | 1236.9 |
| 50° | 1255.1 | 1304.6 | 1303.3 | 1272.1 | 1255.1 | 1287.7 | 1321.5 | 1304.6 | 1256.4 | 1229.1 | 1217.4 |
| 52.5° | 1234.3 | 1303.3 | 1312.4 | 1294.2 | 1282.5 | 1311.1 | 1332.0 | 1299.4 | 1243.4 | 1214.8 | 1205.7 |
| 55° | 1225.2 | 1308.5 | 1315.0 | 1298.1 | 1287.7 | 1313.7 | 1332.0 | 1309.8 | 1243.4 | 1217.4 | 1209.6 |
| 57.5° | 1227.8 | 1302.0 | 1303.3 | 1279.9 | 1261.6 | 1294.2 | 1322.8 | 1316.3 | 1257.7 | 1227.8 | 1218.7 |
| 60° | 1212.2 | 1266.9 | 1269.5 | 1233.0 | 1212.2 | 1251.2 | 1302.0 | 1298.1 | 1251.2 | 1220.0 | 1203.1 |
| 62.5° | 1160.1 | 1208.3 | 1209.6 | 1175.7 | 1145.8 | 1201.8 | 1257.7 | 1256.4 | 1213.5 | 1182.2 | 1162.7 |
| 65° | 1072.9 | 1123.6 | 1136.7 | 1104.1 | 1080.7 | 1140.6 | 1199.1 | 1196.5 | 1153.6 | 1124.9 | 1105.4 |
| 67.5° | 964.8 | 1019.5 | 1044.2 | 1022.1 | 1013.0 | 1067.6 | 1122.3 | 1121.0 | 1085.9 | 1058.5 | 1041.6 |
| 70° | 833.3 | 878.9 | 920.5 | 920.5 | 914.0 | 976.5 | 1035.1 | 1029.9 | 997.3 | 976.5 | 963.5 |
| 72.5° | 723.9 | 759.1 | 772.1 | 785.1 | 804.6 | 869.7 | 919.2 | 923.1 | 899.7 | 889.3 | 899.7 |
| 75° | 615.8 | 638.0 | 649.7 | 639.3 | 673.1 | 740.8 | 805.9 | 812.5 | 787.7 | 770.8 | 774.7 |
| 77.5° | 506.5 | 531.2 | 542.9 | 519.5 | 516.9 | 602.8 | 682.3 | 696.6 | 675.7 | 649.7 | 657.5 |
| 80° | 365.9 | 398.4 | 417.9 | 402.3 | 397.1 | 434.9 | 544.2 | 559.9 | 540.3 | 519.5 | 531.2 |
| 82.5° | 223.9 | 242.2 | 247.4 | 263.0 | 295.6 | 311.2 | 350.2 | 402.3 | 388.0 | 369.8 | 402.3 |
| 85° | 88.5 | 105.5 | 117.2 | 132.8 | 154.9 | 183.6 | 216.1 | 257.8 | 234.4 | 226.5 | 266.9 |
| 87.5° | 5.2 | 1.3 | 0.0 | 2.6 | 22.1 | 43.0 | 92.4 | 127.6 | 106.8 | 114.6 | 138.0 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P639311
 CATALOG NUMBER: GWS-SA5B-750-U-SLR-W

CANDELA DISTRIBUTION (continued):

| | 285° | 295° | 305° | 315° | 325° | 335° | 345° | 355° | 359° | 360° |
|-------|--------|--------|--------|--------|--------|--------|--------|---------|---------|---------|
| 0° | 2282.4 | 2282.4 | 2282.4 | 2282.4 | 2282.4 | 2282.4 | 2282.4 | 2282.4 | 2282.4 | 2282.4 |
| 2.5° | 2113.2 | 2147.0 | 2192.6 | 2230.3 | 2278.5 | 2324.1 | 2371.0 | 2417.8 | 2442.6 | 2453.0 |
| 5° | 1963.4 | 2025.9 | 2098.8 | 2179.6 | 2273.3 | 2372.3 | 2472.5 | 2575.4 | 2640.5 | 2645.7 |
| 7.5° | 1873.6 | 1963.4 | 2063.7 | 2165.2 | 2281.1 | 2417.8 | 2576.7 | 2735.5 | 2801.9 | 2820.1 |
| 10° | 1902.2 | 2002.5 | 2081.9 | 2177.0 | 2304.6 | 2475.1 | 2662.6 | 2848.8 | 2925.6 | 2947.7 |
| 12.5° | 2016.8 | 2036.3 | 2061.1 | 2148.3 | 2304.6 | 2524.6 | 2751.1 | 2972.5 | 3054.5 | 3075.3 |
| 15° | 2111.9 | 2018.1 | 1973.8 | 2066.3 | 2273.3 | 2567.6 | 2844.9 | 3089.7 | 3188.6 | 3208.1 |
| 17.5° | 2119.7 | 1958.2 | 1861.9 | 1945.2 | 2218.6 | 2597.5 | 2934.7 | 3219.9 | 3303.2 | 3321.4 |
| 20° | 2040.2 | 1894.4 | 1769.4 | 1820.2 | 2144.4 | 2610.5 | 2999.8 | 3314.9 | 3396.9 | 3415.2 |
| 22.5° | 1950.4 | 1842.3 | 1706.9 | 1704.3 | 2054.6 | 2624.8 | 3077.9 | 3404.8 | 3493.3 | 3505.0 |
| 25° | 1865.8 | 1770.7 | 1656.2 | 1619.7 | 1950.4 | 2652.2 | 3183.4 | 3540.2 | 3607.9 | 3611.8 |
| 27.5° | 1766.8 | 1693.9 | 1615.8 | 1580.6 | 1859.3 | 2704.3 | 3339.6 | 3701.6 | 3742.0 | 3735.5 |
| 30° | 1677.0 | 1622.3 | 1587.1 | 1576.7 | 1802.0 | 2743.3 | 3488.1 | 3860.5 | 3863.1 | 3840.9 |
| 32.5° | 1581.9 | 1561.1 | 1561.1 | 1595.0 | 1755.1 | 2734.2 | 3609.2 | 4015.4 | 3990.7 | 3958.1 |
| 35° | 1497.3 | 1501.2 | 1528.6 | 1608.0 | 1677.0 | 2643.1 | 3725.0 | 4209.4 | 4172.9 | 4126.1 |
| 37.5° | 1416.6 | 1446.5 | 1485.6 | 1562.4 | 1574.1 | 2507.7 | 3860.5 | 4484.1 | 4438.5 | 4380.0 |
| 40° | 1347.6 | 1393.1 | 1438.7 | 1476.5 | 1464.8 | 2315.0 | 4049.2 | 4807.0 | 4756.2 | 4688.5 |
| 42.5° | 1292.9 | 1337.2 | 1387.9 | 1391.8 | 1395.8 | 2114.5 | 4249.8 | 5202.8 | 5193.7 | 5119.5 |
| 45° | 1257.7 | 1286.4 | 1334.6 | 1328.0 | 1391.8 | 1893.1 | 4434.6 | 5807.0 | 5926.7 | 5870.8 |
| 47.5° | 1234.3 | 1256.4 | 1261.6 | 1289.0 | 1425.7 | 1695.2 | 4672.9 | 6989.2 | 7322.5 | 7258.7 |
| 50° | 1221.3 | 1243.4 | 1184.8 | 1291.6 | 1430.9 | 1567.6 | 5002.3 | 8473.5 | 9009.9 | 8925.3 |
| 52.5° | 1220.0 | 1214.8 | 1126.2 | 1318.9 | 1402.3 | 1489.5 | 5174.2 | 9556.7 | 10746.8 | 10930.4 |
| 55° | 1222.6 | 1157.5 | 1096.3 | 1326.7 | 1345.0 | 1460.9 | 4598.7 | 10077.5 | 12349.5 | 12737.5 |
| 57.5° | 1199.1 | 1095.0 | 1113.2 | 1295.5 | 1236.9 | 1537.7 | 3399.5 | 9891.4 | 12990.1 | 13711.4 |
| 60° | 1154.9 | 1035.1 | 1144.5 | 1210.9 | 1126.2 | 1406.2 | 2341.0 | 9060.7 | 12326.1 | 13068.3 |
| 62.5° | 1091.1 | 993.4 | 1140.6 | 1101.5 | 1085.9 | 1151.0 | 1609.3 | 7898.0 | 11272.8 | 11998.0 |
| 65° | 1019.5 | 959.6 | 1079.4 | 996.0 | 1005.1 | 885.4 | 1138.0 | 6585.6 | 10015.0 | 10728.5 |
| 67.5° | 942.7 | 938.7 | 989.5 | 886.7 | 848.9 | 701.8 | 829.4 | 5278.3 | 8399.3 | 9042.4 |
| 70° | 855.4 | 884.1 | 899.7 | 787.7 | 688.8 | 550.7 | 615.8 | 3691.2 | 6196.3 | 6756.1 |
| 72.5° | 768.2 | 770.8 | 792.9 | 684.9 | 515.6 | 441.4 | 462.2 | 2235.5 | 4209.4 | 4616.9 |
| 75° | 679.6 | 654.9 | 675.7 | 557.3 | 384.1 | 362.0 | 356.8 | 1381.4 | 2907.4 | 3229.0 |
| 77.5° | 584.6 | 557.3 | 529.9 | 419.2 | 308.6 | 279.9 | 273.4 | 774.7 | 1783.8 | 1981.7 |
| 80° | 475.2 | 438.8 | 395.8 | 307.3 | 225.2 | 200.5 | 199.2 | 377.6 | 889.3 | 990.8 |
| 82.5° | 369.8 | 300.8 | 289.0 | 191.4 | 139.3 | 122.4 | 130.2 | 144.5 | 268.2 | 299.5 |
| 85° | 259.1 | 218.7 | 153.6 | 76.8 | 62.5 | 50.8 | 49.5 | 43.0 | 71.6 | 79.4 |
| 87.5° | 144.5 | 95.0 | 49.5 | 9.1 | 10.4 | 11.7 | 9.1 | 6.5 | 6.5 | 6.5 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



LM-79-2008: Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGRAW-EDISON

Report Number: SP1-1908-441-4-R4

Test Date: 10/02/2019

Luminaire Tested: SA1C-750-U-5WQ

Data in this report applies to families of products SA1C-760-U-5WQ .

Test Information

Test Method: LM-79-2008
 Report Number: SP1-1908-441-4-R4
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 10/28/2024
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: McGRAW-EDISON
 Catalog Number: **SA1C-750-U-5WQ**
 Description: McGRAW EDISON ROADWAY AND AREA LUMINAIRE

THIS IS A REVISION OF SP1-1908-441-4-R3. TO UPDATE THE CATALOG INFORMATION.TESTED IN SITU. ROADWAY AND AREA LUMINAIRE. (1) 70 CRI, 5000K, 1050MA LIGHTSQUARE WITH 16 LEDS AND TYPE V WIDE OPTICS.

Spectral Parameters

| | | | | | |
|---------------------------|--------|-----------|------|------|-------|
| CCT (K): | 4884 | CRI (Ra): | 73.5 | R9: | -28.4 |
| CIE u': | 0.2101 | R1: | 70.5 | R10: | 48.6 |
| CIE v': | 0.4904 | R2: | 77.7 | R11: | 73.2 |
| Duv: | 0.0037 | R3: | 84.6 | R12: | 50.7 |
| CIE x: | 0.3493 | R4: | 74.7 | R13: | 71.2 |
| CIE y: | 0.3624 | R5: | 71.9 | R14: | 91.4 |
| CIE z: | 0.2884 | R6: | 70.7 | | |
| Peak Wavelength (nm): | 444 | R7: | 81.2 | | |
| Dominant Wavelength (nm): | 571 | R8: | 56.9 | | |
| Purity: | 13.7 | | | | |
| Rf: | 74.9 | | | | |
| Rg: | 96.3 | | | | |



Test Conditions


Stabilization Time: 240M
 Operation Time: 12H
 Room Temperature (°C) / RH%: 25.0./44%
 Sphere Temperature (°C): 25.7

REPORT NUMBER: SP1-1908-441-4-R4

| Measurement and Test Equipment | | | |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument | Identification Number | Calibration Date | Calibration Due Date |
| Photometer | IN0058 | 6/28/2019 | 12/28/2019 |
| Power Meter | IN0071 | 12/5/2018 | 12/5/2019 |
| AC Power Source | IN0063 | 12/5/2018 | 12/5/2019 |
| DC Power Source | IN0208 | 12/5/2018 | 12/5/2019 |
| Sphere Thermometer | IN0085 | 12/5/2018 | 12/5/2019 |
| Room Thermometer | IN0046 | 12/5/2018 | 12/5/2019 |

REPORT NUMBER: SP1-1908-441-4-R4

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 5000K 4-step quadrangle

REPORT NUMBER: SP1-1908-441-4-R4

Photopic Flux vs. Wavelength



#####

| λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) |
|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|
| 360 | 2945 | NR | 490 | 37941 | NR | 620 | 88803 | NR | 750 | 3908 | NR | 880 | 2997 | NR |
| 365 | 2596 | NR | 495 | 48525 | NR | 625 | 80578 | NR | 755 | 3988 | NR | 885 | 2927 | NR |
| 370 | 2732 | NR | 500 | 60609 | NR | 630 | 73127 | NR | 760 | 3335 | NR | 890 | 2649 | NR |
| 375 | 2894 | NR | 505 | 72036 | NR | 635 | 66244 | NR | 765 | 3438 | NR | 895 | 2828 | NR |
| 380 | 2822 | NR | 510 | 82168 | NR | 640 | 59440 | NR | 770 | 3427 | NR | 900 | 1407 | NR |
| 385 | 2394 | NR | 515 | 90898 | NR | 645 | 52864 | NR | 775 | 2759 | NR | 905 | 2224 | NR |
| 390 | 2370 | NR | 520 | 97142 | NR | 650 | 47085 | NR | 780 | 2340 | NR | 910 | 2905 | NR |
| 395 | 2267 | NR | 525 | 103255 | NR | 655 | 41789 | NR | 785 | 2412 | NR | 915 | 3350 | NR |
| 400 | 2262 | NR | 530 | 106697 | NR | 660 | 37064 | NR | 790 | 1999 | NR | 920 | 3114 | NR |
| 405 | 3000 | NR | 535 | 110081 | NR | 665 | 32299 | NR | 795 | 2054 | NR | 925 | 2834 | NR |
| 410 | 5324 | NR | 540 | 112494 | NR | 670 | 28142 | NR | 800 | 2331 | NR | 930 | 2271 | NR |
| 415 | 10725 | NR | 545 | 115513 | NR | 675 | 24505 | NR | 805 | 2648 | NR | 935 | 2228 | NR |
| 420 | 22128 | NR | 550 | 117203 | NR | 680 | 21162 | NR | 810 | 2485 | NR | 940 | 2833 | NR |
| 425 | 44095 | NR | 555 | 119753 | NR | 685 | 18400 | NR | 815 | 2409 | NR | 945 | 2941 | NR |
| 430 | 77002 | NR | 560 | 122602 | NR | 690 | 16065 | NR | 820 | 2221 | NR | 950 | 2323 | NR |
| 435 | 119881 | NR | 565 | 124314 | NR | 695 | 13860 | NR | 825 | 1562 | NR | 955 | 1667 | NR |
| 440 | 164454 | NR | 570 | 126775 | NR | 700 | 12177 | NR | 830 | 2249 | NR | 960 | 749 | NR |
| 445 | 179997 | NR | 575 | 127511 | NR | 705 | 10757 | NR | 835 | 2573 | NR | 965 | 2669 | NR |
| 450 | 142822 | NR | 580 | 127577 | NR | 710 | 9601 | NR | 840 | 2764 | NR | 970 | 3968 | NR |
| 455 | 90008 | NR | 585 | 126153 | NR | 715 | 8944 | NR | 845 | 3109 | NR | 975 | 3886 | NR |
| 460 | 60557 | NR | 590 | 123678 | NR | 720 | 7947 | NR | 850 | 2963 | NR | 980 | 2788 | NR |
| 465 | 43305 | NR | 595 | 119774 | NR | 725 | 7062 | NR | 855 | 2336 | NR | 985 | 3496 | NR |
| 470 | 31089 | NR | 600 | 115733 | NR | 730 | 6004 | NR | 860 | 2118 | NR | 990 | 2913 | NR |
| 475 | 26278 | NR | 605 | 109231 | NR | 735 | 5594 | NR | 865 | 3144 | NR | 995 | 4659 | NR |
| 480 | 27060 | NR | 610 | 102408 | NR | 740 | 5165 | NR | 870 | 3069 | NR | 1000 | 1308 | NR |
| 485 | 30698 | NR | 615 | 96015 | NR | 745 | 4687 | NR | 875 | 3311 | NR | | | |

REPORT NUMBER: SP1-1908-441-4-R4

Scotopic Flux vs. Wavelength



Scotopic Lumens: 13493.5 S/P: 1.77

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 2945 | NR | 490 | 37941 | NR | 620 | 88803 | NR | 750 | 3908 | NR | 880 | 2997 | NR |
| 365 | 2596 | NR | 495 | 48525 | NR | 625 | 80578 | NR | 755 | 3988 | NR | 885 | 2927 | NR |
| 370 | 2732 | NR | 500 | 60609 | NR | 630 | 73127 | NR | 760 | 3335 | NR | 890 | 2649 | NR |
| 375 | 2894 | NR | 505 | 72036 | NR | 635 | 66244 | NR | 765 | 3438 | NR | 895 | 2828 | NR |
| 380 | 2822 | NR | 510 | 82168 | NR | 640 | 59440 | NR | 770 | 3427 | NR | 900 | 1407 | NR |
| 385 | 2394 | NR | 515 | 90898 | NR | 645 | 52864 | NR | 775 | 2759 | NR | 905 | 2224 | NR |
| 390 | 2370 | NR | 520 | 97142 | NR | 650 | 47085 | NR | 780 | 2340 | NR | 910 | 2905 | NR |
| 395 | 2267 | NR | 525 | 103255 | NR | 655 | 41789 | NR | 785 | 2412 | NR | 915 | 3350 | NR |
| 400 | 2262 | NR | 530 | 106697 | NR | 660 | 37064 | NR | 790 | 1999 | NR | 920 | 3114 | NR |
| 405 | 3000 | NR | 535 | 110081 | NR | 665 | 32299 | NR | 795 | 2054 | NR | 925 | 2834 | NR |
| 410 | 5324 | NR | 540 | 112494 | NR | 670 | 28142 | NR | 800 | 2331 | NR | 930 | 2271 | NR |
| 415 | 10725 | NR | 545 | 115513 | NR | 675 | 24505 | NR | 805 | 2648 | NR | 935 | 2228 | NR |
| 420 | 22128 | NR | 550 | 117203 | NR | 680 | 21162 | NR | 810 | 2485 | NR | 940 | 2833 | NR |
| 425 | 44095 | NR | 555 | 119753 | NR | 685 | 18400 | NR | 815 | 2409 | NR | 945 | 2941 | NR |
| 430 | 77002 | NR | 560 | 122602 | NR | 690 | 16065 | NR | 820 | 2221 | NR | 950 | 2323 | NR |
| 435 | 119881 | NR | 565 | 124314 | NR | 695 | 13860 | NR | 825 | 1562 | NR | 955 | 1667 | NR |
| 440 | 164454 | NR | 570 | 126775 | NR | 700 | 12177 | NR | 830 | 2249 | NR | 960 | 749 | NR |
| 445 | 179997 | NR | 575 | 127511 | NR | 705 | 10757 | NR | 835 | 2573 | NR | 965 | 2669 | NR |
| 450 | 142822 | NR | 580 | 127577 | NR | 710 | 9601 | NR | 840 | 2764 | NR | 970 | 3968 | NR |
| 455 | 90008 | NR | 585 | 126153 | NR | 715 | 8944 | NR | 845 | 3109 | NR | 975 | 3886 | NR |
| 460 | 60557 | NR | 590 | 123678 | NR | 720 | 7947 | NR | 850 | 2963 | NR | 980 | 2788 | NR |
| 465 | 43305 | NR | 595 | 119774 | NR | 725 | 7062 | NR | 855 | 2336 | NR | 985 | 3496 | NR |
| 470 | 31089 | NR | 600 | 115733 | NR | 730 | 6004 | NR | 860 | 2118 | NR | 990 | 2913 | NR |
| 475 | 26278 | NR | 605 | 109231 | NR | 735 | 5594 | NR | 865 | 3144 | NR | 995 | 4659 | NR |
| 480 | 27060 | NR | 610 | 102408 | NR | 740 | 5165 | NR | 870 | 3069 | NR | 1000 | 1308 | NR |
| 485 | 30698 | NR | 615 | 96015 | NR | 745 | 4687 | NR | 875 | 3311 | NR | | | |

REPORT NUMBER: SP1-1908-441-4-R4

Melanopic Flux vs. Wavelength



Melanopic Lumens: 5378.9 M/P: 0.71

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 2945 | NR | 490 | 37941 | NR | 620 | 88803 | NR | 750 | 3908 | NR | 880 | 2997 | NR |
| 365 | 2596 | NR | 495 | 48525 | NR | 625 | 80578 | NR | 755 | 3988 | NR | 885 | 2927 | NR |
| 370 | 2732 | NR | 500 | 60609 | NR | 630 | 73127 | NR | 760 | 3335 | NR | 890 | 2649 | NR |
| 375 | 2894 | NR | 505 | 72036 | NR | 635 | 66244 | NR | 765 | 3438 | NR | 895 | 2828 | NR |
| 380 | 2822 | NR | 510 | 82168 | NR | 640 | 59440 | NR | 770 | 3427 | NR | 900 | 1407 | NR |
| 385 | 2394 | NR | 515 | 90898 | NR | 645 | 52864 | NR | 775 | 2759 | NR | 905 | 2224 | NR |
| 390 | 2370 | NR | 520 | 97142 | NR | 650 | 47085 | NR | 780 | 2340 | NR | 910 | 2905 | NR |
| 395 | 2267 | NR | 525 | 103255 | NR | 655 | 41789 | NR | 785 | 2412 | NR | 915 | 3350 | NR |
| 400 | 2262 | NR | 530 | 106697 | NR | 660 | 37064 | NR | 790 | 1999 | NR | 920 | 3114 | NR |
| 405 | 3000 | NR | 535 | 110081 | NR | 665 | 32299 | NR | 795 | 2054 | NR | 925 | 2834 | NR |
| 410 | 5324 | NR | 540 | 112494 | NR | 670 | 28142 | NR | 800 | 2331 | NR | 930 | 2271 | NR |
| 415 | 10725 | NR | 545 | 115513 | NR | 675 | 24505 | NR | 805 | 2648 | NR | 935 | 2228 | NR |
| 420 | 22128 | NR | 550 | 117203 | NR | 680 | 21162 | NR | 810 | 2485 | NR | 940 | 2833 | NR |
| 425 | 44095 | NR | 555 | 119753 | NR | 685 | 18400 | NR | 815 | 2409 | NR | 945 | 2941 | NR |
| 430 | 77002 | NR | 560 | 122602 | NR | 690 | 16065 | NR | 820 | 2221 | NR | 950 | 2323 | NR |
| 435 | 119881 | NR | 565 | 124314 | NR | 695 | 13860 | NR | 825 | 1562 | NR | 955 | 1667 | NR |
| 440 | 164454 | NR | 570 | 126775 | NR | 700 | 12177 | NR | 830 | 2249 | NR | 960 | 749 | NR |
| 445 | 179997 | NR | 575 | 127511 | NR | 705 | 10757 | NR | 835 | 2573 | NR | 965 | 2669 | NR |
| 450 | 142822 | NR | 580 | 127577 | NR | 710 | 9601 | NR | 840 | 2764 | NR | 970 | 3968 | NR |
| 455 | 90008 | NR | 585 | 126153 | NR | 715 | 8944 | NR | 845 | 3109 | NR | 975 | 3886 | NR |
| 460 | 60557 | NR | 590 | 123678 | NR | 720 | 7947 | NR | 850 | 2963 | NR | 980 | 2788 | NR |
| 465 | 43305 | NR | 595 | 119774 | NR | 725 | 7062 | NR | 855 | 2336 | NR | 985 | 3496 | NR |
| 470 | 31089 | NR | 600 | 115733 | NR | 730 | 6004 | NR | 860 | 2118 | NR | 990 | 2913 | NR |
| 475 | 26278 | NR | 605 | 109231 | NR | 735 | 5594 | NR | 865 | 3144 | NR | 995 | 4659 | NR |
| 480 | 27060 | NR | 610 | 102408 | NR | 740 | 5165 | NR | 870 | 3069 | NR | 1000 | 1308 | NR |
| 485 | 30698 | NR | 615 | 96015 | NR | 745 | 4687 | NR | 875 | 3311 | NR | | | |

REPORT NUMBER: SP1-1908-441-4-R4

TM-30-18

Summary

$R_f = 74.9$
 $R_g = 96.3$
 CIE $R_a = 73.5$
 $R_g = -28.4$



Color Vector Graphics



REPORT NUMBER: SP1-1908-441-4-R4

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)

| | | | |
|------------|------------|------------|------------|
| CES01 = 85 | CES26 = 61 | CES51 = 90 | CES76 = 52 |
| CES02 = 60 | CES27 = 84 | CES52 = 91 | CES77 = 71 |
| CES03 = 30 | CES28 = 81 | CES53 = 79 | CES78 = 54 |
| CES04 = 69 | CES29 = 58 | CES54 = 83 | CES79 = 80 |
| CES05 = 46 | CES30 = 67 | CES55 = 83 | CES80 = 77 |
| CES06 = 50 | CES31 = 63 | CES56 = 73 | CES81 = 77 |
| CES07 = 39 | CES32 = 59 | CES57 = 72 | CES82 = 90 |
| CES08 = 38 | CES33 = 69 | CES58 = 73 | CES83 = 86 |
| CES09 = 29 | CES34 = 69 | CES59 = 88 | CES84 = 88 |
| CES10 = 73 | CES35 = 83 | CES60 = 93 | CES85 = 84 |
| CES11 = 56 | CES36 = 95 | CES61 = 88 | CES86 = 75 |
| CES12 = 61 | CES37 = 78 | CES62 = 85 | CES87 = 78 |
| CES13 = 41 | CES38 = 76 | CES63 = 77 | CES88 = 79 |
| CES14 = 74 | CES39 = 93 | CES64 = 74 | CES89 = 75 |
| CES15 = 70 | CES40 = 86 | CES65 = 67 | CES90 = 77 |
| CES16 = 46 | CES41 = 87 | CES66 = 69 | CES91 = 89 |
| CES17 = 49 | CES42 = 78 | CES67 = 67 | CES92 = 66 |
| CES18 = 55 | CES43 = 75 | CES68 = 73 | CES93 = 80 |
| CES19 = 71 | CES44 = 99 | CES69 = 81 | CES94 = 57 |
| CES20 = 64 | CES45 = 83 | CES70 = 63 | CES95 = 71 |
| CES21 = 85 | CES46 = 81 | CES71 = 60 | CES96 = 78 |
| CES22 = 77 | CES47 = 80 | CES72 = 86 | CES97 = 85 |
| CES23 = 91 | CES48 = 72 | CES73 = 53 | CES98 = 75 |
| CES24 = 90 | CES49 = 81 | CES74 = 96 | CES99 = 62 |
| CES25 = 71 | CES50 = 89 | CES75 = 58 | |



REPORT NUMBER: SP1-1908-441-4-R4

TM-30-18

Color Rendition by Hue-Angle Bin



REPORT NUMBER: SP1-1908-441-4-R4

TM-30-18

Measure Comparisons



(END OF REPORT)