

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: McGRAW-EDISON

Report Number: P629879

Luminaire Tested: GWS-SA1C-750-U-5WQ-W-GRSBK

Issue Date: 1/10/2023

**Test Information**

Test Method: LM-79-2019  
Report Number: P629879  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2209-782-2)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 1/10/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: McGRAW-EDISON  
Catalog Number: GWS-SA1C-750-U-5WQ-W-GRSBK  
Description: GALLEON WALL SLIM LUMINAIRE. (1) LIGHTSQUARES WITH 16 LEDS EACH AND TYPE V WIDE OPTICS W/ FACTORY INSTALLED GLARE SHIELD, BK  
Light Source: (16) 5000K CCT, 70 CRI LEDS  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 2587.4 lumens  
Efficiency: N/A  
Efficacy: 75.9 lumens/watt  
Luminous Opening: Rectangular (W 0.5' x L: 0.5' x H: 0')  
IES Classification: Type V - Short  
BUG Rating: B1 - U0 - G0  
  
Input Watts (W): 34.1  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 0  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 28.75 FT



REPORT NUMBER: P629879  
 CATALOG NUMBER: GWS-SA1C-750-U-5WQ-W-GRSBK

### Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd  
 - - - 1/2 Max cd



Based on 10 foot mounting height. Maximum calculated value = 3.7 fc  
 Type V - Short - N/A

REPORT NUMBER: P629879  
CATALOG NUMBER: GWS-SA1C-750-U-5WQ-W-GRSBK

### Luminous Intensity Polar Plot



— Vertical Plane Through 45-Deg Lateral    - - - Horizontal Cone Through 58-Deg Vertical

REPORT NUMBER: P629879

CATALOG NUMBER: GWS-SA1C-750-U-5WQ-W-GRSBK


**FLUX DISTRIBUTION:**

|                    |           | Downward | Upward | Total  |
|--------------------|-----------|----------|--------|--------|
| <b>House Side</b>  | Lumens    | 1293.7   | 0.0    | 1293.7 |
|                    | % Fixture | 50.0     | 0.0    | 50.0   |
| <b>Street Side</b> | Lumens    | 1293.7   | 0.0    | 1293.7 |
|                    | % Fixture | 50.0     | 0.0    | 50.0   |
| <b>Total</b>       | Lumens    | 2587.4   | 0.0    | 2587.4 |
|                    | % Fixture | 100.0    | 0.0    | 100.0  |

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 34.2   | 1.3       |
| 10°-20°   | 101.3  | 3.9       |
| 20°-30°   | 191.6  | 7.4       |
| 30°-40°   | 377.8  | 14.6      |
| 40°-50°   | 597.9  | 23.1      |
| 50°-60°   | 878.9  | 34.0      |
| 60°-70°   | 392.3  | 15.2      |
| 70°-80°   | 13.1   | 0.5       |
| 80°-90°   | 0.1    | 0.0       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-90°    | 2587.4 | 100.0     |
| 0°-180°   | 2587.4 | 100.0     |

**Coefficient of Utilization**




REPORT NUMBER: P629879

CATALOG NUMBER: GWS-SA1C-750-U-5WQ-W-GRSBK

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

| Zone           | Lumens | % Fixture | Zone Rating/Lumen Limit |      |        |
|----------------|--------|-----------|-------------------------|------|--------|
|                |        |           | B                       | U    | G      |
| FL (0°-30°)    | 163.6  | 6.3       |                         |      |        |
| FM (30°-60°)   | 927.4  | 35.8      |                         |      |        |
| FH (60°-80°)   | 202.7  | 7.8       |                         |      | G0/660 |
| FVH (80°-90°)  | 0.1    | 0.0       |                         |      | G0/10  |
| BL (0°-30°)    | 163.6  | 6.3       | B1/500                  |      |        |
| BM (30°-60°)   | 927.4  | 35.8      | B1/1000                 |      |        |
| BH (60°-80°)   | 202.7  | 7.8       | B1/500                  |      | G0/660 |
| BVH (80°-90°)  | 0.1    | 0.0       |                         |      | G0/10  |
| UL (90°-100°)  | 0.0    | 0.0       |                         | U0/0 |        |
| UH (100°-180°) | 0.0    | 0.0       |                         | U0/0 |        |

**BUG Rating: B1-U0-G0**  
 Type V Short





REPORT NUMBER: P629879  
 CATALOG NUMBER: GWS-SA1C-750-U-5WQ-W-GRSBK

**CANDELA DISTRIBUTION (FULL):**

|       | 0°     | 5°     | 15°    | 25°    | 35°    | 45°    | 55°    | 65°    | 75°   | 85°   | 90°   |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|-------|-------|-------|
| 0°    | 366.9  | 366.9  | 366.9  | 366.9  | 366.9  | 366.9  | 366.9  | 366.9  | 366.9 | 366.9 | 366.9 |
| 2.5°  | 363.4  | 364.1  | 364.8  | 365.2  | 365.5  | 366.6  | 366.9  | 365.9  | 365.9 | 363.8 | 366.2 |
| 5°    | 361.6  | 362.3  | 363.1  | 362.7  | 362.7  | 362.7  | 362.3  | 360.9  | 360.6 | 358.5 | 360.9 |
| 7.5°  | 358.5  | 359.2  | 359.2  | 358.1  | 357.4  | 357.4  | 357.1  | 355.3  | 354.9 | 352.8 | 355.3 |
| 10°   | 356.0  | 356.4  | 356.0  | 353.9  | 352.5  | 352.5  | 352.1  | 351.4  | 351.8 | 350.4 | 352.5 |
| 12.5° | 357.4  | 357.8  | 356.4  | 353.5  | 351.8  | 351.4  | 350.4  | 349.3  | 350.4 | 350.0 | 352.1 |
| 15°   | 362.0  | 362.3  | 359.9  | 356.4  | 354.9  | 354.9  | 352.1  | 349.3  | 350.7 | 351.1 | 353.5 |
| 17.5° | 367.6  | 367.6  | 364.5  | 361.3  | 361.6  | 361.6  | 357.1  | 352.1  | 352.5 | 353.9 | 356.4 |
| 20°   | 374.3  | 374.3  | 371.2  | 370.5  | 372.9  | 373.3  | 367.6  | 359.9  | 358.1 | 359.2 | 362.0 |
| 22.5° | 386.3  | 386.3  | 383.8  | 385.6  | 391.2  | 393.0  | 384.6  | 373.6  | 369.4 | 370.1 | 372.9 |
| 25°   | 405.0  | 405.0  | 404.3  | 408.5  | 416.6  | 420.5  | 409.2  | 394.8  | 387.7 | 386.7 | 389.8 |
| 27.5° | 436.4  | 436.7  | 435.7  | 442.0  | 452.2  | 456.8  | 441.3  | 422.3  | 413.8 | 412.0 | 415.2 |
| 30°   | 476.9  | 476.9  | 477.3  | 486.1  | 499.5  | 505.5  | 485.0  | 462.8  | 452.9 | 447.3 | 451.5 |
| 32.5° | 522.0  | 522.7  | 526.2  | 541.1  | 564.7  | 577.0  | 547.0  | 516.0  | 500.2 | 494.2 | 498.8 |
| 35°   | 596.4  | 589.7  | 585.5  | 596.4  | 630.6  | 646.8  | 608.4  | 572.1  | 560.1 | 559.4 | 571.0 |
| 37.5° | 670.1  | 666.2  | 657.4  | 668.6  | 699.3  | 706.7  | 664.4  | 634.1  | 625.6 | 630.2 | 641.9 |
| 40°   | 728.6  | 721.5  | 709.9  | 720.5  | 760.6  | 768.0  | 715.9  | 685.9  | 682.7 | 693.0 | 708.8 |
| 42.5° | 774.7  | 764.9  | 749.4  | 751.8  | 784.3  | 789.5  | 743.4  | 720.8  | 722.9 | 735.6 | 753.6 |
| 45°   | 795.5  | 787.8  | 774.0  | 773.0  | 793.4  | 793.8  | 757.5  | 745.8  | 751.5 | 761.3 | 775.4 |
| 47.5° | 804.4  | 800.8  | 793.1  | 791.3  | 802.9  | 800.1  | 777.6  | 772.6  | 777.9 | 780.7 | 788.8 |
| 50°   | 826.2  | 826.2  | 827.3  | 828.7  | 840.7  | 837.8  | 822.0  | 816.3  | 809.6 | 799.8 | 802.2 |
| 52.5° | 887.5  | 890.0  | 900.2  | 911.5  | 933.4  | 942.5  | 916.8  | 884.0  | 851.9 | 830.4 | 830.4 |
| 55°   | 998.2  | 1000.7 | 1012.7 | 1031.7 | 1071.9 | 1093.7 | 1033.8 | 961.6  | 917.5 | 888.2 | 892.1 |
| 57.5° | 1059.2 | 1062.0 | 1086.7 | 1138.1 | 1216.0 | 1253.1 | 1124.4 | 1017.2 | 955.6 | 922.1 | 924.9 |
| 58°   | 1055.3 | 1057.1 | 1084.9 | 1145.2 | 1231.9 | 1271.7 | 1130.7 | 1015.5 | 950.6 | 916.4 | 920.0 |
| 60°   | 937.6  | 935.1  | 979.5  | 1065.5 | 1187.8 | 1242.8 | 1067.7 | 927.0  | 851.6 | 816.7 | 818.4 |
| 62.5° | 613.0  | 614.4  | 652.8  | 742.7  | 837.8  | 889.7  | 745.8  | 641.2  | 580.5 | 559.4 | 554.1 |
| 65°   | 255.9  | 251.3  | 274.9  | 325.0  | 382.1  | 411.0  | 353.2  | 298.9  | 261.5 | 247.4 | 251.3 |
| 67.5° | 65.9   | 64.2   | 65.6   | 82.1   | 100.5  | 118.8  | 99.8   | 76.1   | 66.3  | 67.0  | 67.0  |
| 70°   | 37.4   | 35.2   | 28.6   | 26.4   | 25.7   | 25.7   | 25.7   | 25.7   | 29.6  | 34.9  | 36.0  |
| 72.5° | 28.2   | 26.4   | 20.8   | 18.0   | 15.9   | 14.8   | 15.5   | 18.0   | 21.5  | 26.1  | 26.8  |
| 75°   | 14.1   | 14.1   | 12.7   | 12.0   | 10.6   | 9.9    | 10.2   | 11.3   | 13.0  | 14.8  | 14.5  |
| 77.5° | 2.8    | 3.2    | 3.5    | 4.2    | 3.5    | 3.5    | 3.5    | 4.2    | 4.2   | 4.6   | 4.2   |
| 80°   | 0.4    | 0.4    | 0.4    | 0.4    | 0.4    | 0.4    | 0.4    | 0.4    | 0.4   | 0.4   | 0.4   |
| 82.5° | 0.0    | 0.4    | 0.4    | 0.0    | 0.0    | 0.0    | 0.0    | 0.4    | 0.4   | 0.4   | 0.4   |
| 85°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0   | 0.4   | 0.4   |
| 87.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   |

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



LM-79-2008: Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGRAW-EDISON

Report Number: SP1-1908-441-4-R4

Test Date: 10/02/2019

Luminaire Tested: SA1C-750-U-5WQ

Data in this report applies to families of products SA1C-760-U-5WQ .




**Test Information**

Test Method: LM-79-2008  
 Report Number: SP1-1908-441-4-R4  
 Test Lab: COOPER LIGHTING SOLUTIONS  
 Photometer: SP1 - 76IN SPHERE  
 Measurement Geometry: 4π  
 Issue Date: 10/28/2024  
 Manufacturer: COOPER LIGHTING SOLUTIONS  
 Product Line: McGRAW-EDISON  
 Catalog Number: **SA1C-750-U-5WQ**  
 Description: McGRAW EDISON ROADWAY AND AREA LUMINAIRE

\*\*\*THIS IS A REVISION OF SP1-1908-441-4-R3. TO UPDATE THE CATALOG INFORMATION.\*\*\*TESTED IN SITU. ROADWAY AND AREA LUMINAIRE. (1) 70 CRI, 5000K, 1050MA LIGHTSQUARE WITH 16 LEDS AND TYPE V WIDE OPTICS.

**Spectral Parameters**

|                           |        |           |      |      |       |
|---------------------------|--------|-----------|------|------|-------|
| CCT (K):                  | 4884   | CRI (Ra): | 73.5 | R9:  | -28.4 |
| CIE u':                   | 0.2101 | R1:       | 70.5 | R10: | 48.6  |
| CIE v':                   | 0.4904 | R2:       | 77.7 | R11: | 73.2  |
| Duv:                      | 0.0037 | R3:       | 84.6 | R12: | 50.7  |
| CIE x:                    | 0.3493 | R4:       | 74.7 | R13: | 71.2  |
| CIE y:                    | 0.3624 | R5:       | 71.9 | R14: | 91.4  |
| CIE z:                    | 0.2884 | R6:       | 70.7 |      |       |
| Peak Wavelength (nm):     | 444    | R7:       | 81.2 |      |       |
| Dominant Wavelength (nm): | 571    | R8:       | 56.9 |      |       |
| Purity:                   | 13.7   |           |      |      |       |
| Rf:                       | 74.9   |           |      |      |       |
| Rg:                       | 96.3   |           |      |      |       |



**Test Conditions**


Stabilization Time: 240M  
 Operation Time: 12H  
 Room Temperature (°C) / RH%: 25.0./44%  
 Sphere Temperature (°C): 25.7

REPORT NUMBER: SP1-1908-441-4-R4


| Measurement and Test Equipment |                       |                  |                      |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument                     | Identification Number | Calibration Date | Calibration Due Date |
| Photometer                     | IN0058                | 6/28/2019        | 12/28/2019           |
| Power Meter                    | IN0071                | 12/5/2018        | 12/5/2019            |
| AC Power Source                | IN0063                | 12/5/2018        | 12/5/2019            |
| DC Power Source                | IN0208                | 12/5/2018        | 12/5/2019            |
| Sphere Thermometer             | IN0085                | 12/5/2018        | 12/5/2019            |
| Room Thermometer               | IN0046                | 12/5/2018        | 12/5/2019            |

REPORT NUMBER: SP1-1908-441-4-R4

CIE 1931 Chromaticity Diagram




CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 5000K 4-step quadrangle

REPORT NUMBER: SP1-1908-441-4-R4

**Photopic Flux vs. Wavelength**




#####

| $\lambda$<br>(nm) | Power<br>( $\mu\text{W}/\text{nm}$ ) | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>( $\mu\text{W}/\text{nm}$ ) | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>( $\mu\text{W}/\text{nm}$ ) | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>( $\mu\text{W}/\text{nm}$ ) | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>( $\mu\text{W}/\text{nm}$ ) | Lumens<br>( $\phi/\text{nm}$ ) |
|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|
| 360               | 2945                                 | NR                             | 490               | 37941                                | NR                             | 620               | 88803                                | NR                             | 750               | 3908                                 | NR                             | 880               | 2997                                 | NR                             |
| 365               | 2596                                 | NR                             | 495               | 48525                                | NR                             | 625               | 80578                                | NR                             | 755               | 3988                                 | NR                             | 885               | 2927                                 | NR                             |
| 370               | 2732                                 | NR                             | 500               | 60609                                | NR                             | 630               | 73127                                | NR                             | 760               | 3335                                 | NR                             | 890               | 2649                                 | NR                             |
| 375               | 2894                                 | NR                             | 505               | 72036                                | NR                             | 635               | 66244                                | NR                             | 765               | 3438                                 | NR                             | 895               | 2828                                 | NR                             |
| 380               | 2822                                 | NR                             | 510               | 82168                                | NR                             | 640               | 59440                                | NR                             | 770               | 3427                                 | NR                             | 900               | 1407                                 | NR                             |
| 385               | 2394                                 | NR                             | 515               | 90898                                | NR                             | 645               | 52864                                | NR                             | 775               | 2759                                 | NR                             | 905               | 2224                                 | NR                             |
| 390               | 2370                                 | NR                             | 520               | 97142                                | NR                             | 650               | 47085                                | NR                             | 780               | 2340                                 | NR                             | 910               | 2905                                 | NR                             |
| 395               | 2267                                 | NR                             | 525               | 103255                               | NR                             | 655               | 41789                                | NR                             | 785               | 2412                                 | NR                             | 915               | 3350                                 | NR                             |
| 400               | 2262                                 | NR                             | 530               | 106697                               | NR                             | 660               | 37064                                | NR                             | 790               | 1999                                 | NR                             | 920               | 3114                                 | NR                             |
| 405               | 3000                                 | NR                             | 535               | 110081                               | NR                             | 665               | 32299                                | NR                             | 795               | 2054                                 | NR                             | 925               | 2834                                 | NR                             |
| 410               | 5324                                 | NR                             | 540               | 112494                               | NR                             | 670               | 28142                                | NR                             | 800               | 2331                                 | NR                             | 930               | 2271                                 | NR                             |
| 415               | 10725                                | NR                             | 545               | 115513                               | NR                             | 675               | 24505                                | NR                             | 805               | 2648                                 | NR                             | 935               | 2228                                 | NR                             |
| 420               | 22128                                | NR                             | 550               | 117203                               | NR                             | 680               | 21162                                | NR                             | 810               | 2485                                 | NR                             | 940               | 2833                                 | NR                             |
| 425               | 44095                                | NR                             | 555               | 119753                               | NR                             | 685               | 18400                                | NR                             | 815               | 2409                                 | NR                             | 945               | 2941                                 | NR                             |
| 430               | 77002                                | NR                             | 560               | 122602                               | NR                             | 690               | 16065                                | NR                             | 820               | 2221                                 | NR                             | 950               | 2323                                 | NR                             |
| 435               | 119881                               | NR                             | 565               | 124314                               | NR                             | 695               | 13860                                | NR                             | 825               | 1562                                 | NR                             | 955               | 1667                                 | NR                             |
| 440               | 164454                               | NR                             | 570               | 126775                               | NR                             | 700               | 12177                                | NR                             | 830               | 2249                                 | NR                             | 960               | 749                                  | NR                             |
| 445               | 179997                               | NR                             | 575               | 127511                               | NR                             | 705               | 10757                                | NR                             | 835               | 2573                                 | NR                             | 965               | 2669                                 | NR                             |
| 450               | 142822                               | NR                             | 580               | 127577                               | NR                             | 710               | 9601                                 | NR                             | 840               | 2764                                 | NR                             | 970               | 3968                                 | NR                             |
| 455               | 90008                                | NR                             | 585               | 126153                               | NR                             | 715               | 8944                                 | NR                             | 845               | 3109                                 | NR                             | 975               | 3886                                 | NR                             |
| 460               | 60557                                | NR                             | 590               | 123678                               | NR                             | 720               | 7947                                 | NR                             | 850               | 2963                                 | NR                             | 980               | 2788                                 | NR                             |
| 465               | 43305                                | NR                             | 595               | 119774                               | NR                             | 725               | 7062                                 | NR                             | 855               | 2336                                 | NR                             | 985               | 3496                                 | NR                             |
| 470               | 31089                                | NR                             | 600               | 115733                               | NR                             | 730               | 6004                                 | NR                             | 860               | 2118                                 | NR                             | 990               | 2913                                 | NR                             |
| 475               | 26278                                | NR                             | 605               | 109231                               | NR                             | 735               | 5594                                 | NR                             | 865               | 3144                                 | NR                             | 995               | 4659                                 | NR                             |
| 480               | 27060                                | NR                             | 610               | 102408                               | NR                             | 740               | 5165                                 | NR                             | 870               | 3069                                 | NR                             | 1000              | 1308                                 | NR                             |
| 485               | 30698                                | NR                             | 615               | 96015                                | NR                             | 745               | 4687                                 | NR                             | 875               | 3311                                 | NR                             |                   |                                      |                                |

REPORT NUMBER: SP1-1908-441-4-R4

Scotopic Flux vs. Wavelength




Scotopic Lumens: 13493.5 S/P: 1.77

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360    | 2945          | NR            | 490    | 37941         | NR            | 620    | 88803         | NR            | 750    | 3908          | NR            | 880    | 2997          | NR            |
| 365    | 2596          | NR            | 495    | 48525         | NR            | 625    | 80578         | NR            | 755    | 3988          | NR            | 885    | 2927          | NR            |
| 370    | 2732          | NR            | 500    | 60609         | NR            | 630    | 73127         | NR            | 760    | 3335          | NR            | 890    | 2649          | NR            |
| 375    | 2894          | NR            | 505    | 72036         | NR            | 635    | 66244         | NR            | 765    | 3438          | NR            | 895    | 2828          | NR            |
| 380    | 2822          | NR            | 510    | 82168         | NR            | 640    | 59440         | NR            | 770    | 3427          | NR            | 900    | 1407          | NR            |
| 385    | 2394          | NR            | 515    | 90898         | NR            | 645    | 52864         | NR            | 775    | 2759          | NR            | 905    | 2224          | NR            |
| 390    | 2370          | NR            | 520    | 97142         | NR            | 650    | 47085         | NR            | 780    | 2340          | NR            | 910    | 2905          | NR            |
| 395    | 2267          | NR            | 525    | 103255        | NR            | 655    | 41789         | NR            | 785    | 2412          | NR            | 915    | 3350          | NR            |
| 400    | 2262          | NR            | 530    | 106697        | NR            | 660    | 37064         | NR            | 790    | 1999          | NR            | 920    | 3114          | NR            |
| 405    | 3000          | NR            | 535    | 110081        | NR            | 665    | 32299         | NR            | 795    | 2054          | NR            | 925    | 2834          | NR            |
| 410    | 5324          | NR            | 540    | 112494        | NR            | 670    | 28142         | NR            | 800    | 2331          | NR            | 930    | 2271          | NR            |
| 415    | 10725         | NR            | 545    | 115513        | NR            | 675    | 24505         | NR            | 805    | 2648          | NR            | 935    | 2228          | NR            |
| 420    | 22128         | NR            | 550    | 117203        | NR            | 680    | 21162         | NR            | 810    | 2485          | NR            | 940    | 2833          | NR            |
| 425    | 44095         | NR            | 555    | 119753        | NR            | 685    | 18400         | NR            | 815    | 2409          | NR            | 945    | 2941          | NR            |
| 430    | 77002         | NR            | 560    | 122602        | NR            | 690    | 16065         | NR            | 820    | 2221          | NR            | 950    | 2323          | NR            |
| 435    | 119881        | NR            | 565    | 124314        | NR            | 695    | 13860         | NR            | 825    | 1562          | NR            | 955    | 1667          | NR            |
| 440    | 164454        | NR            | 570    | 126775        | NR            | 700    | 12177         | NR            | 830    | 2249          | NR            | 960    | 749           | NR            |
| 445    | 179997        | NR            | 575    | 127511        | NR            | 705    | 10757         | NR            | 835    | 2573          | NR            | 965    | 2669          | NR            |
| 450    | 142822        | NR            | 580    | 127577        | NR            | 710    | 9601          | NR            | 840    | 2764          | NR            | 970    | 3968          | NR            |
| 455    | 90008         | NR            | 585    | 126153        | NR            | 715    | 8944          | NR            | 845    | 3109          | NR            | 975    | 3886          | NR            |
| 460    | 60557         | NR            | 590    | 123678        | NR            | 720    | 7947          | NR            | 850    | 2963          | NR            | 980    | 2788          | NR            |
| 465    | 43305         | NR            | 595    | 119774        | NR            | 725    | 7062          | NR            | 855    | 2336          | NR            | 985    | 3496          | NR            |
| 470    | 31089         | NR            | 600    | 115733        | NR            | 730    | 6004          | NR            | 860    | 2118          | NR            | 990    | 2913          | NR            |
| 475    | 26278         | NR            | 605    | 109231        | NR            | 735    | 5594          | NR            | 865    | 3144          | NR            | 995    | 4659          | NR            |
| 480    | 27060         | NR            | 610    | 102408        | NR            | 740    | 5165          | NR            | 870    | 3069          | NR            | 1000   | 1308          | NR            |
| 485    | 30698         | NR            | 615    | 96015         | NR            | 745    | 4687          | NR            | 875    | 3311          | NR            |        |               |               |

REPORT NUMBER: SP1-1908-441-4-R4

**Melanopic Flux vs. Wavelength**



**Melanopic Lumens: 5378.9 M/P: 0.71**


| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360    | 2945          | NR            | 490    | 37941         | NR            | 620    | 88803         | NR            | 750    | 3908          | NR            | 880    | 2997          | NR            |
| 365    | 2596          | NR            | 495    | 48525         | NR            | 625    | 80578         | NR            | 755    | 3988          | NR            | 885    | 2927          | NR            |
| 370    | 2732          | NR            | 500    | 60609         | NR            | 630    | 73127         | NR            | 760    | 3335          | NR            | 890    | 2649          | NR            |
| 375    | 2894          | NR            | 505    | 72036         | NR            | 635    | 66244         | NR            | 765    | 3438          | NR            | 895    | 2828          | NR            |
| 380    | 2822          | NR            | 510    | 82168         | NR            | 640    | 59440         | NR            | 770    | 3427          | NR            | 900    | 1407          | NR            |
| 385    | 2394          | NR            | 515    | 90898         | NR            | 645    | 52864         | NR            | 775    | 2759          | NR            | 905    | 2224          | NR            |
| 390    | 2370          | NR            | 520    | 97142         | NR            | 650    | 47085         | NR            | 780    | 2340          | NR            | 910    | 2905          | NR            |
| 395    | 2267          | NR            | 525    | 103255        | NR            | 655    | 41789         | NR            | 785    | 2412          | NR            | 915    | 3350          | NR            |
| 400    | 2262          | NR            | 530    | 106697        | NR            | 660    | 37064         | NR            | 790    | 1999          | NR            | 920    | 3114          | NR            |
| 405    | 3000          | NR            | 535    | 110081        | NR            | 665    | 32299         | NR            | 795    | 2054          | NR            | 925    | 2834          | NR            |
| 410    | 5324          | NR            | 540    | 112494        | NR            | 670    | 28142         | NR            | 800    | 2331          | NR            | 930    | 2271          | NR            |
| 415    | 10725         | NR            | 545    | 115513        | NR            | 675    | 24505         | NR            | 805    | 2648          | NR            | 935    | 2228          | NR            |
| 420    | 22128         | NR            | 550    | 117203        | NR            | 680    | 21162         | NR            | 810    | 2485          | NR            | 940    | 2833          | NR            |
| 425    | 44095         | NR            | 555    | 119753        | NR            | 685    | 18400         | NR            | 815    | 2409          | NR            | 945    | 2941          | NR            |
| 430    | 77002         | NR            | 560    | 122602        | NR            | 690    | 16065         | NR            | 820    | 2221          | NR            | 950    | 2323          | NR            |
| 435    | 119881        | NR            | 565    | 124314        | NR            | 695    | 13860         | NR            | 825    | 1562          | NR            | 955    | 1667          | NR            |
| 440    | 164454        | NR            | 570    | 126775        | NR            | 700    | 12177         | NR            | 830    | 2249          | NR            | 960    | 749           | NR            |
| 445    | 179997        | NR            | 575    | 127511        | NR            | 705    | 10757         | NR            | 835    | 2573          | NR            | 965    | 2669          | NR            |
| 450    | 142822        | NR            | 580    | 127577        | NR            | 710    | 9601          | NR            | 840    | 2764          | NR            | 970    | 3968          | NR            |
| 455    | 90008         | NR            | 585    | 126153        | NR            | 715    | 8944          | NR            | 845    | 3109          | NR            | 975    | 3886          | NR            |
| 460    | 60557         | NR            | 590    | 123678        | NR            | 720    | 7947          | NR            | 850    | 2963          | NR            | 980    | 2788          | NR            |
| 465    | 43305         | NR            | 595    | 119774        | NR            | 725    | 7062          | NR            | 855    | 2336          | NR            | 985    | 3496          | NR            |
| 470    | 31089         | NR            | 600    | 115733        | NR            | 730    | 6004          | NR            | 860    | 2118          | NR            | 990    | 2913          | NR            |
| 475    | 26278         | NR            | 605    | 109231        | NR            | 735    | 5594          | NR            | 865    | 3144          | NR            | 995    | 4659          | NR            |
| 480    | 27060         | NR            | 610    | 102408        | NR            | 740    | 5165          | NR            | 870    | 3069          | NR            | 1000   | 1308          | NR            |
| 485    | 30698         | NR            | 615    | 96015         | NR            | 745    | 4687          | NR            | 875    | 3311          | NR            |        |               |               |

REPORT NUMBER: SP1-1908-441-4-R4





TM-30-18

**Summary**

$R_f = 74.9$   
 $R_g = 96.3$   
 CIE  $R_a = 73.5$   
 $R_g = -28.4$



**Color Vector Graphics**




REPORT NUMBER: SP1-1908-441-4-R4

TM-30-18

**Individual Sample Fidelity Index ( $R_{f,i}$ )**

|            |            |            |            |
|------------|------------|------------|------------|
| CES01 = 85 | CES26 = 61 | CES51 = 90 | CES76 = 52 |
| CES02 = 60 | CES27 = 84 | CES52 = 91 | CES77 = 71 |
| CES03 = 30 | CES28 = 81 | CES53 = 79 | CES78 = 54 |
| CES04 = 69 | CES29 = 58 | CES54 = 83 | CES79 = 80 |
| CES05 = 46 | CES30 = 67 | CES55 = 83 | CES80 = 77 |
| CES06 = 50 | CES31 = 63 | CES56 = 73 | CES81 = 77 |
| CES07 = 39 | CES32 = 59 | CES57 = 72 | CES82 = 90 |
| CES08 = 38 | CES33 = 69 | CES58 = 73 | CES83 = 86 |
| CES09 = 29 | CES34 = 69 | CES59 = 88 | CES84 = 88 |
| CES10 = 73 | CES35 = 83 | CES60 = 93 | CES85 = 84 |
| CES11 = 56 | CES36 = 95 | CES61 = 88 | CES86 = 75 |
| CES12 = 61 | CES37 = 78 | CES62 = 85 | CES87 = 78 |
| CES13 = 41 | CES38 = 76 | CES63 = 77 | CES88 = 79 |
| CES14 = 74 | CES39 = 93 | CES64 = 74 | CES89 = 75 |
| CES15 = 70 | CES40 = 86 | CES65 = 67 | CES90 = 77 |
| CES16 = 46 | CES41 = 87 | CES66 = 69 | CES91 = 89 |
| CES17 = 49 | CES42 = 78 | CES67 = 67 | CES92 = 66 |
| CES18 = 55 | CES43 = 75 | CES68 = 73 | CES93 = 80 |
| CES19 = 71 | CES44 = 99 | CES69 = 81 | CES94 = 57 |
| CES20 = 64 | CES45 = 83 | CES70 = 63 | CES95 = 71 |
| CES21 = 85 | CES46 = 81 | CES71 = 60 | CES96 = 78 |
| CES22 = 77 | CES47 = 80 | CES72 = 86 | CES97 = 85 |
| CES23 = 91 | CES48 = 72 | CES73 = 53 | CES98 = 75 |
| CES24 = 90 | CES49 = 81 | CES74 = 96 | CES99 = 62 |
| CES25 = 71 | CES50 = 89 | CES75 = 58 |            |








REPORT NUMBER: SP1-1908-441-4-R4

TM-30-18



Color Rendition by Hue-Angle Bin



REPORT NUMBER: SP1-1908-441-4-R4

TM-30-18

Measure Comparisons



(END OF REPORT)