

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: McGRAW-EDISON

Report Number: P630409

Luminaire Tested: GWS-SA1D-750-U-T2R-W-HSS

Issue Date: 1/10/2023

Test Information

Test Method: LM-79-2019
Report Number: P630409
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2209-782-14)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/10/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: McGRAW-EDISON
Catalog Number: GWS-SA1D-750-U-T2R-W-HSS
Description: GALLEON WALL SLIM LUMINAIRE. (1) LIGHTSQUARES WITH 16 LEDS EACH AND TYPE II ROADWAY OPTICS WITH HOUSE SIDE SHIELD
Light Source: (16) 5000K CCT, 70 CRI LEDS
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5002.4 lumens
Efficiency: N/A
Efficacy: 112.9 lumens/watt
Luminous Opening: Rectangular (W 0.5' x L: 0.5' x H: 0')
IES Classification: Type II - Short
BUG Rating: B0 - U0 - G1


Input Watts (W): 44.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 0
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT



REPORT NUMBER: P630409
 CATALOG NUMBER: GWS-SA1D-750-U-T2R-W-HSS

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 10 foot mounting height. Maximum calculated value = 15 fc
 Type II - Short - N/A

REPORT NUMBER: P630409
CATALOG NUMBER: GWS-SA1D-750-U-T2R-W-HSS

Luminous Intensity Polar Plot



— Vertical Plane Through 76-Deg Lateral - - - Horizontal Cone Through 65-Deg Vertical

REPORT NUMBER: P630409
 CATALOG NUMBER: GWS-SA1D-750-U-T2R-W-HSS


FLUX DISTRIBUTION:

| | | Downward | Upward | Total |
|--------------------|-----------|----------|--------|--------|
| House Side | Lumens | 276.6 | 0.0 | 276.6 |
| | % Fixture | 5.5 | 0.0 | 5.5 |
| Street Side | Lumens | 4725.8 | 0.0 | 4725.8 |
| | % Fixture | 94.5 | 0.0 | 94.5 |
| Total | Lumens | 5002.4 | 0.0 | 5002.4 |
| | % Fixture | 100.0 | 0.0 | 100.0 |

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 53.9 | 1.1 |
| 10°-20° | 204.4 | 4.1 |
| 20°-30° | 417.1 | 8.3 |
| 30°-40° | 741.8 | 14.8 |
| 40°-50° | 1096.6 | 21.9 |
| 50°-60° | 1255.5 | 25.1 |
| 60°-70° | 957.9 | 19.1 |
| 70°-80° | 268.3 | 5.4 |
| 80°-90° | 6.7 | 0.1 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-90° | 5002.4 | 100.0 |
| 0°-180° | 5002.4 | 100.0 |

Coefficient of Utilization




REPORT NUMBER: P630409

CATALOG NUMBER: GWS-SA1D-750-U-T2R-W-HSS

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

| Zone | Lumens | % Fixture | Zone Rating/Lumen Limit | | |
|----------------|--------|-----------|-------------------------|------|---------|
| | | | B | U | G |
| FL (0°-30°) | 596.5 | 11.9 | | | |
| FM (30°-60°) | 2957.5 | 59.1 | | | |
| FH (60°-80°) | 1165.4 | 23.3 | | | G1/1800 |
| FVH (80°-90°) | 6.4 | 0.1 | | | G0/10 |
| BL (0°-30°) | 78.9 | 1.6 | B0/110 | | |
| BM (30°-60°) | 136.5 | 2.7 | B0/220 | | |
| BH (60°-80°) | 60.8 | 1.2 | B0/110 | | G0/110 |
| BVH (80°-90°) | 0.4 | 0.0 | | | G0/10 |
| UL (90°-100°) | 0.0 | 0.0 | | U0/0 | |
| UH (100°-180°) | 0.0 | 0.0 | | U0/0 | |

BUG Rating: B0-U0-G1
 Type II Short





REPORT NUMBER: P630409

CATALOG NUMBER: GWS-SA1D-750-U-T2R-W-HSS

CANDELA DISTRIBUTION (FULL):

| | 0° | 5° | 15° | 25° | 35° | 45° | 55° | 65° | 75° | 76° | 85° |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 442.9 | 442.9 | 442.9 | 442.9 | 442.9 | 442.9 | 442.9 | 442.9 | 442.9 | 442.9 | 442.9 |
| 2.5° | 682.6 | 692.8 | 684.8 | 671.5 | 645.7 | 620.8 | 588.7 | 544.7 | 509.6 | 505.1 | 472.2 |
| 5° | 921.8 | 920.9 | 903.6 | 886.2 | 859.1 | 816.4 | 751.9 | 670.1 | 591.4 | 584.7 | 510.9 |
| 7.5° | 1064.1 | 1065.4 | 1055.7 | 1042.3 | 1015.6 | 971.6 | 904.5 | 805.7 | 690.6 | 677.2 | 563.8 |
| 10° | 1183.7 | 1183.3 | 1176.2 | 1169.9 | 1145.9 | 1116.6 | 1044.5 | 936.0 | 797.3 | 776.4 | 623.0 |
| 12.5° | 1273.5 | 1276.7 | 1280.2 | 1286.4 | 1276.2 | 1247.3 | 1179.3 | 1061.0 | 905.4 | 882.2 | 690.6 |
| 15° | 1344.7 | 1345.6 | 1358.9 | 1382.9 | 1391.4 | 1376.3 | 1314.5 | 1181.9 | 1012.1 | 992.1 | 768.4 |
| 17.5° | 1366.0 | 1367.8 | 1390.5 | 1434.5 | 1479.0 | 1487.4 | 1440.7 | 1303.8 | 1117.0 | 1095.7 | 844.0 |
| 20° | 1410.9 | 1415.0 | 1431.8 | 1470.5 | 1526.6 | 1571.9 | 1553.7 | 1427.0 | 1222.0 | 1193.9 | 921.4 |
| 22.5° | 1552.4 | 1554.6 | 1548.8 | 1553.7 | 1582.6 | 1635.1 | 1646.2 | 1546.1 | 1329.6 | 1299.8 | 1005.0 |
| 25° | 1795.6 | 1796.5 | 1756.0 | 1717.8 | 1696.0 | 1705.8 | 1730.2 | 1656.0 | 1436.3 | 1406.9 | 1082.8 |
| 27.5° | 2048.2 | 2051.3 | 2002.8 | 1937.9 | 1860.1 | 1815.6 | 1808.5 | 1756.5 | 1543.9 | 1511.4 | 1159.7 |
| 30° | 2286.1 | 2286.1 | 2234.9 | 2155.8 | 2051.7 | 1965.0 | 1913.9 | 1857.8 | 1659.1 | 1623.5 | 1238.4 |
| 32.5° | 2500.0 | 2498.2 | 2432.8 | 2347.0 | 2244.3 | 2149.1 | 2041.5 | 1963.7 | 1787.1 | 1747.6 | 1329.1 |
| 35° | 2676.5 | 2672.0 | 2597.8 | 2515.5 | 2405.7 | 2335.0 | 2214.9 | 2077.5 | 1925.9 | 1886.3 | 1422.5 |
| 37.5° | 2809.9 | 2805.0 | 2737.0 | 2649.8 | 2548.0 | 2502.2 | 2401.7 | 2214.0 | 2072.2 | 2036.2 | 1526.1 |
| 40° | 2882.4 | 2872.6 | 2825.5 | 2760.5 | 2675.2 | 2635.1 | 2593.3 | 2383.5 | 2244.3 | 2199.4 | 1648.4 |
| 42.5° | 2903.7 | 2892.2 | 2861.0 | 2830.8 | 2779.2 | 2747.6 | 2792.5 | 2574.7 | 2433.3 | 2394.6 | 1788.0 |
| 45° | 2840.6 | 2833.9 | 2831.2 | 2853.0 | 2862.4 | 2871.3 | 2982.0 | 2786.3 | 2641.8 | 2612.5 | 1963.7 |
| 47.5° | 2688.5 | 2686.7 | 2710.3 | 2801.0 | 2899.7 | 2993.5 | 3187.9 | 3047.3 | 2912.2 | 2880.6 | 2209.1 |
| 50° | 2407.5 | 2425.7 | 2491.5 | 2650.7 | 2848.1 | 3062.9 | 3380.4 | 3409.3 | 3349.7 | 3303.5 | 2529.3 |
| 52.5° | 1968.1 | 2003.3 | 2150.9 | 2392.8 | 2676.5 | 3043.3 | 3469.3 | 3699.2 | 3760.2 | 3712.1 | 2758.8 |
| 55° | 1544.4 | 1577.3 | 1708.9 | 2015.7 | 2394.1 | 2894.4 | 3473.3 | 3799.3 | 3932.2 | 3887.8 | 2913.9 |
| 57.5° | 1150.4 | 1180.6 | 1300.2 | 1593.7 | 2009.9 | 2601.3 | 3378.2 | 3854.9 | 4136.4 | 4107.9 | 3159.0 |
| 60° | 751.9 | 781.7 | 889.8 | 1146.4 | 1559.0 | 2174.5 | 3143.8 | 3843.3 | 4414.3 | 4411.6 | 3460.0 |
| 62.5° | 417.1 | 440.7 | 518.9 | 719.0 | 1088.1 | 1684.0 | 2775.7 | 3727.3 | 4683.3 | 4700.2 | 3708.1 |
| 65° | 213.4 | 228.6 | 276.1 | 395.3 | 658.6 | 1193.9 | 2291.4 | 3461.3 | 4807.8 | 4850.5 | 3773.5 |
| 67.5° | 139.6 | 144.5 | 156.1 | 205.4 | 352.6 | 751.1 | 1724.4 | 3034.9 | 4632.6 | 4682.4 | 3554.3 |
| 70° | 113.4 | 117.4 | 124.1 | 137.0 | 181.9 | 398.9 | 1132.6 | 2423.9 | 3870.9 | 3904.7 | 2830.3 |
| 72.5° | 83.2 | 88.5 | 101.4 | 109.8 | 131.2 | 218.8 | 589.2 | 1591.0 | 2658.3 | 2717.8 | 1778.7 |
| 75° | 61.4 | 64.5 | 75.1 | 86.7 | 107.2 | 138.3 | 225.4 | 836.4 | 1372.7 | 1338.0 | 747.1 |
| 77.5° | 36.9 | 39.1 | 48.0 | 55.6 | 76.5 | 86.3 | 78.7 | 309.0 | 417.5 | 392.6 | 180.5 |
| 80° | 18.2 | 20.5 | 31.6 | 41.8 | 48.9 | 34.7 | 32.9 | 86.3 | 92.9 | 92.9 | 45.4 |
| 82.5° | 6.2 | 8.0 | 16.9 | 27.6 | 24.0 | 13.3 | 15.6 | 22.2 | 24.9 | 26.2 | 13.3 |
| 85° | 0.0 | 0.0 | 4.0 | 8.0 | 3.6 | 1.8 | 4.0 | 4.9 | 6.2 | 6.7 | 4.4 |
| 87.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.4 | 1.3 | 1.8 | 1.8 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P630409
 CATALOG NUMBER: GWS-SA1D-750-U-T2R-W-HSS

CANDELA DISTRIBUTION (continued):

| | 90° | 95° | 105° | 115° | 125° | 135° | 145° | 155° | 165° | 175° | 180° |
|-------|--------|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|
| 0° | 442.9 | 442.9 | 442.9 | 442.9 | 442.9 | 442.9 | 442.9 | 442.9 | 442.9 | 442.9 | 442.9 |
| 2.5° | 454.5 | 433.6 | 402.0 | 373.5 | 351.7 | 331.3 | 315.7 | 303.3 | 301.0 | 293.9 | 294.8 |
| 5° | 474.9 | 437.1 | 378.9 | 333.9 | 302.4 | 281.0 | 263.2 | 249.9 | 244.1 | 238.3 | 233.9 |
| 7.5° | 506.5 | 451.8 | 370.0 | 315.3 | 278.4 | 245.5 | 217.9 | 195.7 | 185.0 | 178.3 | 173.9 |
| 10° | 545.2 | 472.2 | 370.4 | 304.2 | 249.5 | 199.2 | 161.4 | 137.0 | 125.4 | 121.8 | 121.4 |
| 12.5° | 591.4 | 498.0 | 374.0 | 285.9 | 207.7 | 148.1 | 119.6 | 108.5 | 104.9 | 101.8 | 101.8 |
| 15° | 640.3 | 526.9 | 374.0 | 252.6 | 158.3 | 115.6 | 103.6 | 96.5 | 92.0 | 90.3 | 89.4 |
| 17.5° | 691.9 | 554.1 | 365.1 | 206.8 | 121.4 | 101.8 | 92.0 | 85.4 | 81.8 | 79.2 | 78.3 |
| 20° | 747.1 | 579.9 | 342.8 | 158.3 | 104.1 | 91.2 | 81.8 | 75.1 | 71.6 | 68.9 | 68.9 |
| 22.5° | 803.1 | 603.9 | 306.8 | 121.8 | 92.0 | 80.9 | 72.0 | 65.8 | 62.3 | 59.6 | 59.6 |
| 25° | 855.1 | 619.9 | 260.6 | 100.5 | 83.2 | 72.0 | 64.0 | 57.8 | 53.8 | 52.0 | 51.1 |
| 27.5° | 903.6 | 630.1 | 209.4 | 88.5 | 74.7 | 64.5 | 56.0 | 50.2 | 47.1 | 45.8 | 44.9 |
| 30° | 953.8 | 632.8 | 160.1 | 80.5 | 67.6 | 56.9 | 48.9 | 44.5 | 41.8 | 40.0 | 40.0 |
| 32.5° | 1002.7 | 629.7 | 122.3 | 73.8 | 61.4 | 50.2 | 43.6 | 39.6 | 37.4 | 36.0 | 35.6 |
| 35° | 1052.5 | 615.4 | 99.2 | 68.0 | 55.1 | 44.0 | 38.7 | 35.6 | 34.2 | 32.5 | 32.5 |
| 37.5° | 1106.8 | 596.3 | 86.3 | 62.3 | 48.9 | 39.6 | 34.7 | 32.5 | 30.7 | 29.3 | 28.9 |
| 40° | 1174.4 | 574.1 | 79.2 | 57.4 | 43.1 | 35.6 | 31.1 | 28.9 | 27.6 | 26.2 | 25.8 |
| 42.5° | 1254.4 | 552.3 | 75.6 | 52.0 | 38.7 | 31.6 | 28.0 | 25.3 | 24.0 | 22.2 | 21.8 |
| 45° | 1367.8 | 547.4 | 71.6 | 46.2 | 34.7 | 28.5 | 24.5 | 21.8 | 20.0 | 18.7 | 18.2 |
| 47.5° | 1550.1 | 561.2 | 64.9 | 40.0 | 30.7 | 24.9 | 20.9 | 18.7 | 16.5 | 15.1 | 14.2 |
| 50° | 1731.1 | 557.6 | 58.3 | 34.7 | 27.1 | 21.3 | 17.8 | 15.6 | 13.3 | 12.0 | 11.6 |
| 52.5° | 1829.8 | 540.7 | 52.0 | 30.7 | 23.6 | 18.2 | 15.1 | 12.5 | 11.1 | 9.8 | 9.3 |
| 55° | 1919.2 | 534.1 | 45.8 | 26.7 | 20.0 | 16.0 | 12.5 | 10.2 | 9.3 | 8.0 | 7.6 |
| 57.5° | 2094.4 | 549.6 | 40.5 | 23.1 | 17.3 | 13.8 | 10.7 | 8.4 | 7.6 | 6.2 | 5.8 |
| 60° | 2277.6 | 551.4 | 34.7 | 20.0 | 15.1 | 11.6 | 8.4 | 6.7 | 5.8 | 4.4 | 4.0 |
| 62.5° | 2373.2 | 506.5 | 28.5 | 16.9 | 12.5 | 9.8 | 7.1 | 5.3 | 4.4 | 2.7 | 2.7 |
| 65° | 2293.2 | 409.5 | 24.0 | 13.8 | 9.8 | 7.6 | 5.3 | 4.0 | 2.7 | 1.3 | 0.4 |
| 67.5° | 2029.5 | 291.3 | 20.0 | 11.1 | 7.1 | 5.3 | 4.0 | 2.7 | 0.4 | 0.0 | 0.0 |
| 70° | 1486.1 | 166.3 | 15.6 | 8.0 | 5.3 | 3.6 | 2.7 | 1.3 | 0.0 | 0.0 | 0.0 |
| 72.5° | 913.4 | 88.9 | 11.6 | 5.3 | 4.0 | 2.7 | 2.2 | 0.9 | 0.0 | 0.0 | 0.0 |
| 75° | 346.4 | 42.7 | 7.1 | 3.6 | 3.1 | 2.2 | 1.3 | 0.4 | 0.0 | 0.0 | 0.0 |
| 77.5° | 93.8 | 20.9 | 4.0 | 2.7 | 2.2 | 1.3 | 0.9 | 0.0 | 0.0 | 0.0 | 0.0 |
| 80° | 24.5 | 9.8 | 2.7 | 1.8 | 1.3 | 0.9 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 82.5° | 8.4 | 4.4 | 1.3 | 1.3 | 0.9 | 0.4 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 85° | 3.6 | 1.8 | 0.9 | 0.9 | 0.4 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 87.5° | 1.3 | 0.4 | 0.4 | 0.4 | 0.4 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



LM-79-2008: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGRAW-EDISON

Report Number: SP1-1908-441-4-R4

Test Date: 10/02/2019

Luminaire Tested: SA1C-750-U-5WQ

Data in this report applies to families of products SA1C-760-U-5WQ .

Test Information

Test Method: LM-79-2008
 Report Number: SP1-1908-441-4-R4
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 10/28/2024
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: McGRAW-EDISON
 Catalog Number: **SA1C-750-U-5WQ**
 Description: McGRAW EDISON ROADWAY AND AREA LUMINAIRE

THIS IS A REVISION OF SP1-1908-441-4-R3. TO UPDATE THE CATALOG INFORMATION.TESTED IN SITU. ROADWAY AND AREA LUMINAIRE. (1) 70 CRI, 5000K, 1050MA LIGHTSQUARE WITH 16 LEDS AND TYPE V WIDE OPTICS.

Spectral Parameters

| | | | | | |
|---------------------------|--------|-----------|------|------|-------|
| CCT (K): | 4884 | CRI (Ra): | 73.5 | R9: | -28.4 |
| CIE u': | 0.2101 | R1: | 70.5 | R10: | 48.6 |
| CIE v': | 0.4904 | R2: | 77.7 | R11: | 73.2 |
| Duv: | 0.0037 | R3: | 84.6 | R12: | 50.7 |
| CIE x: | 0.3493 | R4: | 74.7 | R13: | 71.2 |
| CIE y: | 0.3624 | R5: | 71.9 | R14: | 91.4 |
| CIE z: | 0.2884 | R6: | 70.7 | | |
| Peak Wavelength (nm): | 444 | R7: | 81.2 | | |
| Dominant Wavelength (nm): | 571 | R8: | 56.9 | | |
| Purity: | 13.7 | | | | |
| Rf: | 74.9 | | | | |
| Rg: | 96.3 | | | | |



Test Conditions

Stabilization Time: 240M
 Operation Time: 12H
 Room Temperature (°C) / RH%: 25.0./44%
 Sphere Temperature (°C): 25.7

REPORT NUMBER: SP1-1908-441-4-R4

| Measurement and Test Equipment | | | |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument | Identification Number | Calibration Date | Calibration Due Date |
| Photometer | IN0058 | 6/28/2019 | 12/28/2019 |
| Power Meter | IN0071 | 12/5/2018 | 12/5/2019 |
| AC Power Source | IN0063 | 12/5/2018 | 12/5/2019 |
| DC Power Source | IN0208 | 12/5/2018 | 12/5/2019 |
| Sphere Thermometer | IN0085 | 12/5/2018 | 12/5/2019 |
| Room Thermometer | IN0046 | 12/5/2018 | 12/5/2019 |

REPORT NUMBER: SP1-1908-441-4-R4

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 5000K 4-step quadrangle

REPORT NUMBER: SP1-1908-441-4-R4

Photopic Flux vs. Wavelength



#####

| λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) |
|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|
| 360 | 2945 | NR | 490 | 37941 | NR | 620 | 88803 | NR | 750 | 3908 | NR | 880 | 2997 | NR |
| 365 | 2596 | NR | 495 | 48525 | NR | 625 | 80578 | NR | 755 | 3988 | NR | 885 | 2927 | NR |
| 370 | 2732 | NR | 500 | 60609 | NR | 630 | 73127 | NR | 760 | 3335 | NR | 890 | 2649 | NR |
| 375 | 2894 | NR | 505 | 72036 | NR | 635 | 66244 | NR | 765 | 3438 | NR | 895 | 2828 | NR |
| 380 | 2822 | NR | 510 | 82168 | NR | 640 | 59440 | NR | 770 | 3427 | NR | 900 | 1407 | NR |
| 385 | 2394 | NR | 515 | 90898 | NR | 645 | 52864 | NR | 775 | 2759 | NR | 905 | 2224 | NR |
| 390 | 2370 | NR | 520 | 97142 | NR | 650 | 47085 | NR | 780 | 2340 | NR | 910 | 2905 | NR |
| 395 | 2267 | NR | 525 | 103255 | NR | 655 | 41789 | NR | 785 | 2412 | NR | 915 | 3350 | NR |
| 400 | 2262 | NR | 530 | 106697 | NR | 660 | 37064 | NR | 790 | 1999 | NR | 920 | 3114 | NR |
| 405 | 3000 | NR | 535 | 110081 | NR | 665 | 32299 | NR | 795 | 2054 | NR | 925 | 2834 | NR |
| 410 | 5324 | NR | 540 | 112494 | NR | 670 | 28142 | NR | 800 | 2331 | NR | 930 | 2271 | NR |
| 415 | 10725 | NR | 545 | 115513 | NR | 675 | 24505 | NR | 805 | 2648 | NR | 935 | 2228 | NR |
| 420 | 22128 | NR | 550 | 117203 | NR | 680 | 21162 | NR | 810 | 2485 | NR | 940 | 2833 | NR |
| 425 | 44095 | NR | 555 | 119753 | NR | 685 | 18400 | NR | 815 | 2409 | NR | 945 | 2941 | NR |
| 430 | 77002 | NR | 560 | 122602 | NR | 690 | 16065 | NR | 820 | 2221 | NR | 950 | 2323 | NR |
| 435 | 119881 | NR | 565 | 124314 | NR | 695 | 13860 | NR | 825 | 1562 | NR | 955 | 1667 | NR |
| 440 | 164454 | NR | 570 | 126775 | NR | 700 | 12177 | NR | 830 | 2249 | NR | 960 | 749 | NR |
| 445 | 179997 | NR | 575 | 127511 | NR | 705 | 10757 | NR | 835 | 2573 | NR | 965 | 2669 | NR |
| 450 | 142822 | NR | 580 | 127577 | NR | 710 | 9601 | NR | 840 | 2764 | NR | 970 | 3968 | NR |
| 455 | 90008 | NR | 585 | 126153 | NR | 715 | 8944 | NR | 845 | 3109 | NR | 975 | 3886 | NR |
| 460 | 60557 | NR | 590 | 123678 | NR | 720 | 7947 | NR | 850 | 2963 | NR | 980 | 2788 | NR |
| 465 | 43305 | NR | 595 | 119774 | NR | 725 | 7062 | NR | 855 | 2336 | NR | 985 | 3496 | NR |
| 470 | 31089 | NR | 600 | 115733 | NR | 730 | 6004 | NR | 860 | 2118 | NR | 990 | 2913 | NR |
| 475 | 26278 | NR | 605 | 109231 | NR | 735 | 5594 | NR | 865 | 3144 | NR | 995 | 4659 | NR |
| 480 | 27060 | NR | 610 | 102408 | NR | 740 | 5165 | NR | 870 | 3069 | NR | 1000 | 1308 | NR |
| 485 | 30698 | NR | 615 | 96015 | NR | 745 | 4687 | NR | 875 | 3311 | NR | | | |

REPORT NUMBER: SP1-1908-441-4-R4

Scotopic Flux vs. Wavelength



Scotopic Lumens: 13493.5 S/P: 1.77

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 2945 | NR | 490 | 37941 | NR | 620 | 88803 | NR | 750 | 3908 | NR | 880 | 2997 | NR |
| 365 | 2596 | NR | 495 | 48525 | NR | 625 | 80578 | NR | 755 | 3988 | NR | 885 | 2927 | NR |
| 370 | 2732 | NR | 500 | 60609 | NR | 630 | 73127 | NR | 760 | 3335 | NR | 890 | 2649 | NR |
| 375 | 2894 | NR | 505 | 72036 | NR | 635 | 66244 | NR | 765 | 3438 | NR | 895 | 2828 | NR |
| 380 | 2822 | NR | 510 | 82168 | NR | 640 | 59440 | NR | 770 | 3427 | NR | 900 | 1407 | NR |
| 385 | 2394 | NR | 515 | 90898 | NR | 645 | 52864 | NR | 775 | 2759 | NR | 905 | 2224 | NR |
| 390 | 2370 | NR | 520 | 97142 | NR | 650 | 47085 | NR | 780 | 2340 | NR | 910 | 2905 | NR |
| 395 | 2267 | NR | 525 | 103255 | NR | 655 | 41789 | NR | 785 | 2412 | NR | 915 | 3350 | NR |
| 400 | 2262 | NR | 530 | 106697 | NR | 660 | 37064 | NR | 790 | 1999 | NR | 920 | 3114 | NR |
| 405 | 3000 | NR | 535 | 110081 | NR | 665 | 32299 | NR | 795 | 2054 | NR | 925 | 2834 | NR |
| 410 | 5324 | NR | 540 | 112494 | NR | 670 | 28142 | NR | 800 | 2331 | NR | 930 | 2271 | NR |
| 415 | 10725 | NR | 545 | 115513 | NR | 675 | 24505 | NR | 805 | 2648 | NR | 935 | 2228 | NR |
| 420 | 22128 | NR | 550 | 117203 | NR | 680 | 21162 | NR | 810 | 2485 | NR | 940 | 2833 | NR |
| 425 | 44095 | NR | 555 | 119753 | NR | 685 | 18400 | NR | 815 | 2409 | NR | 945 | 2941 | NR |
| 430 | 77002 | NR | 560 | 122602 | NR | 690 | 16065 | NR | 820 | 2221 | NR | 950 | 2323 | NR |
| 435 | 119881 | NR | 565 | 124314 | NR | 695 | 13860 | NR | 825 | 1562 | NR | 955 | 1667 | NR |
| 440 | 164454 | NR | 570 | 126775 | NR | 700 | 12177 | NR | 830 | 2249 | NR | 960 | 749 | NR |
| 445 | 179997 | NR | 575 | 127511 | NR | 705 | 10757 | NR | 835 | 2573 | NR | 965 | 2669 | NR |
| 450 | 142822 | NR | 580 | 127577 | NR | 710 | 9601 | NR | 840 | 2764 | NR | 970 | 3968 | NR |
| 455 | 90008 | NR | 585 | 126153 | NR | 715 | 8944 | NR | 845 | 3109 | NR | 975 | 3886 | NR |
| 460 | 60557 | NR | 590 | 123678 | NR | 720 | 7947 | NR | 850 | 2963 | NR | 980 | 2788 | NR |
| 465 | 43305 | NR | 595 | 119774 | NR | 725 | 7062 | NR | 855 | 2336 | NR | 985 | 3496 | NR |
| 470 | 31089 | NR | 600 | 115733 | NR | 730 | 6004 | NR | 860 | 2118 | NR | 990 | 2913 | NR |
| 475 | 26278 | NR | 605 | 109231 | NR | 735 | 5594 | NR | 865 | 3144 | NR | 995 | 4659 | NR |
| 480 | 27060 | NR | 610 | 102408 | NR | 740 | 5165 | NR | 870 | 3069 | NR | 1000 | 1308 | NR |
| 485 | 30698 | NR | 615 | 96015 | NR | 745 | 4687 | NR | 875 | 3311 | NR | | | |

REPORT NUMBER: SP1-1908-441-4-R4

Melanopic Flux vs. Wavelength



Melanopic Lumens: 5378.9 M/P: 0.71

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 2945 | NR | 490 | 37941 | NR | 620 | 88803 | NR | 750 | 3908 | NR | 880 | 2997 | NR |
| 365 | 2596 | NR | 495 | 48525 | NR | 625 | 80578 | NR | 755 | 3988 | NR | 885 | 2927 | NR |
| 370 | 2732 | NR | 500 | 60609 | NR | 630 | 73127 | NR | 760 | 3335 | NR | 890 | 2649 | NR |
| 375 | 2894 | NR | 505 | 72036 | NR | 635 | 66244 | NR | 765 | 3438 | NR | 895 | 2828 | NR |
| 380 | 2822 | NR | 510 | 82168 | NR | 640 | 59440 | NR | 770 | 3427 | NR | 900 | 1407 | NR |
| 385 | 2394 | NR | 515 | 90898 | NR | 645 | 52864 | NR | 775 | 2759 | NR | 905 | 2224 | NR |
| 390 | 2370 | NR | 520 | 97142 | NR | 650 | 47085 | NR | 780 | 2340 | NR | 910 | 2905 | NR |
| 395 | 2267 | NR | 525 | 103255 | NR | 655 | 41789 | NR | 785 | 2412 | NR | 915 | 3350 | NR |
| 400 | 2262 | NR | 530 | 106697 | NR | 660 | 37064 | NR | 790 | 1999 | NR | 920 | 3114 | NR |
| 405 | 3000 | NR | 535 | 110081 | NR | 665 | 32299 | NR | 795 | 2054 | NR | 925 | 2834 | NR |
| 410 | 5324 | NR | 540 | 112494 | NR | 670 | 28142 | NR | 800 | 2331 | NR | 930 | 2271 | NR |
| 415 | 10725 | NR | 545 | 115513 | NR | 675 | 24505 | NR | 805 | 2648 | NR | 935 | 2228 | NR |
| 420 | 22128 | NR | 550 | 117203 | NR | 680 | 21162 | NR | 810 | 2485 | NR | 940 | 2833 | NR |
| 425 | 44095 | NR | 555 | 119753 | NR | 685 | 18400 | NR | 815 | 2409 | NR | 945 | 2941 | NR |
| 430 | 77002 | NR | 560 | 122602 | NR | 690 | 16065 | NR | 820 | 2221 | NR | 950 | 2323 | NR |
| 435 | 119881 | NR | 565 | 124314 | NR | 695 | 13860 | NR | 825 | 1562 | NR | 955 | 1667 | NR |
| 440 | 164454 | NR | 570 | 126775 | NR | 700 | 12177 | NR | 830 | 2249 | NR | 960 | 749 | NR |
| 445 | 179997 | NR | 575 | 127511 | NR | 705 | 10757 | NR | 835 | 2573 | NR | 965 | 2669 | NR |
| 450 | 142822 | NR | 580 | 127577 | NR | 710 | 9601 | NR | 840 | 2764 | NR | 970 | 3968 | NR |
| 455 | 90008 | NR | 585 | 126153 | NR | 715 | 8944 | NR | 845 | 3109 | NR | 975 | 3886 | NR |
| 460 | 60557 | NR | 590 | 123678 | NR | 720 | 7947 | NR | 850 | 2963 | NR | 980 | 2788 | NR |
| 465 | 43305 | NR | 595 | 119774 | NR | 725 | 7062 | NR | 855 | 2336 | NR | 985 | 3496 | NR |
| 470 | 31089 | NR | 600 | 115733 | NR | 730 | 6004 | NR | 860 | 2118 | NR | 990 | 2913 | NR |
| 475 | 26278 | NR | 605 | 109231 | NR | 735 | 5594 | NR | 865 | 3144 | NR | 995 | 4659 | NR |
| 480 | 27060 | NR | 610 | 102408 | NR | 740 | 5165 | NR | 870 | 3069 | NR | 1000 | 1308 | NR |
| 485 | 30698 | NR | 615 | 96015 | NR | 745 | 4687 | NR | 875 | 3311 | NR | | | |

REPORT NUMBER: SP1-1908-441-4-R4

TM-30-18

Summary

$R_f = 74.9$
 $R_g = 96.3$
 CIE $R_a = 73.5$
 $R_g = -28.4$



Color Vector Graphics



REPORT NUMBER: SP1-1908-441-4-R4

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)

| | | | |
|------------|------------|------------|------------|
| CES01 = 85 | CES26 = 61 | CES51 = 90 | CES76 = 52 |
| CES02 = 60 | CES27 = 84 | CES52 = 91 | CES77 = 71 |
| CES03 = 30 | CES28 = 81 | CES53 = 79 | CES78 = 54 |
| CES04 = 69 | CES29 = 58 | CES54 = 83 | CES79 = 80 |
| CES05 = 46 | CES30 = 67 | CES55 = 83 | CES80 = 77 |
| CES06 = 50 | CES31 = 63 | CES56 = 73 | CES81 = 77 |
| CES07 = 39 | CES32 = 59 | CES57 = 72 | CES82 = 90 |
| CES08 = 38 | CES33 = 69 | CES58 = 73 | CES83 = 86 |
| CES09 = 29 | CES34 = 69 | CES59 = 88 | CES84 = 88 |
| CES10 = 73 | CES35 = 83 | CES60 = 93 | CES85 = 84 |
| CES11 = 56 | CES36 = 95 | CES61 = 88 | CES86 = 75 |
| CES12 = 61 | CES37 = 78 | CES62 = 85 | CES87 = 78 |
| CES13 = 41 | CES38 = 76 | CES63 = 77 | CES88 = 79 |
| CES14 = 74 | CES39 = 93 | CES64 = 74 | CES89 = 75 |
| CES15 = 70 | CES40 = 86 | CES65 = 67 | CES90 = 77 |
| CES16 = 46 | CES41 = 87 | CES66 = 69 | CES91 = 89 |
| CES17 = 49 | CES42 = 78 | CES67 = 67 | CES92 = 66 |
| CES18 = 55 | CES43 = 75 | CES68 = 73 | CES93 = 80 |
| CES19 = 71 | CES44 = 99 | CES69 = 81 | CES94 = 57 |
| CES20 = 64 | CES45 = 83 | CES70 = 63 | CES95 = 71 |
| CES21 = 85 | CES46 = 81 | CES71 = 60 | CES96 = 78 |
| CES22 = 77 | CES47 = 80 | CES72 = 86 | CES97 = 85 |
| CES23 = 91 | CES48 = 72 | CES73 = 53 | CES98 = 75 |
| CES24 = 90 | CES49 = 81 | CES74 = 96 | CES99 = 62 |
| CES25 = 71 | CES50 = 89 | CES75 = 58 | |



REPORT NUMBER: SP1-1908-441-4-R4

TM-30-18

Color Rendition by Hue-Angle Bin



REPORT NUMBER: SP1-1908-441-4-R4

TM-30-18

Measure Comparisons



(END OF REPORT)