

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: McGRAW-EDISON

Report Number: P637832

Luminaire Tested: GWS-SA4D-750-U-T2R-W-GRSBK

Issue Date: 1/10/2023

Test Information

Test Method: LM-79-2019
Report Number: P637832
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2209-782-12)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/10/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: McGRAW-EDISON
Catalog Number: GWS-SA4D-750-U-T2R-W-GRSBK
Description: GALLEON WALL SLIM LUMINAIRE. (4) LIGHTSQUARES WITH 16 LEDS EACH AND TYPE II ROADWAY OPTICS W/ FACTORY INSTALLED GLARE SHIELD, BK
Light Source: (64) 5000K CCT, 70 CRI LEDS
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 16792.3 lumens
Efficiency: N/A
Efficacy: 103.6 lumens/watt
Luminous Opening: Rectangular (W 1' x L: 1' x H: 0')
IES Classification: Type II - Short
BUG Rating: B2 - U0 - G1


Input Watts (W): 162.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 0
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT



REPORT NUMBER: P637832
 CATALOG NUMBER: GWS-SA4D-750-U-T2R-W-GRSBK

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 9.9 fc
 Type II - Short - N/A

REPORT NUMBER: P637832
CATALOG NUMBER: GWS-SA4D-750-U-T2R-W-GRSBK

Luminous Intensity Polar Plot



— Vertical Plane Through 58-Deg Lateral - - - Horizontal Cone Through 50-Deg Vertical

REPORT NUMBER: P637832
 CATALOG NUMBER: GWS-SA4D-750-U-T2R-W-GRSBK

FLUX DISTRIBUTION:

| | | Downward | Upward | Total |
|--------------------|-----------|----------|--------|---------|
| House Side | Lumens | 2352.0 | 0.0 | 2352.0 |
| | % Fixture | 14.0 | 0.0 | 14.0 |
| Street Side | Lumens | 14440.3 | 0.0 | 14440.3 |
| | % Fixture | 86.0 | 0.0 | 86.0 |
| Total | Lumens | 16792.3 | 0.0 | 16792.3 |
| | % Fixture | 100.0 | 0.0 | 100.0 |

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|---------|-----------|
| 0°-10° | 248.5 | 1.5 |
| 10°-20° | 983.7 | 5.9 |
| 20°-30° | 1990.5 | 11.9 |
| 30°-40° | 3521.5 | 21.0 |
| 40°-50° | 5133.6 | 30.6 |
| 50°-60° | 4114.7 | 24.5 |
| 60°-70° | 741.3 | 4.4 |
| 70°-80° | 58.4 | 0.3 |
| 80°-90° | 0.0 | 0.0 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-90° | 16792.3 | 100.0 |
| 0°-180° | 16792.3 | 100.0 |

Coefficient of Utilization



REPORT NUMBER: P637832


CATALOG NUMBER: GWS-SA4D-750-U-T2R-W-GRSBK

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

| Zone | Lumens | % Fixture | Zone Rating/Lumen Limit | | |
|----------------|---------|-----------|-------------------------|------|--------|
| | | | B | U | G |
| FL (0°-30°) | 2498.6 | 14.9 | | | |
| FM (30°-60°) | 11309.1 | 67.3 | | | |
| FH (60°-80°) | 632.6 | 3.8 | | | G0/660 |
| FVH (80°-90°) | 0.0 | 0.0 | | | G0/10 |
| BL (0°-30°) | 724.1 | 4.3 | B2/1000 | | |
| BM (30°-60°) | 1460.7 | 8.7 | B2/2500 | | |
| BH (60°-80°) | 167.2 | 1.0 | B1/500 | | G1/500 |
| BVH (80°-90°) | 0.0 | 0.0 | | | G0/10 |
| UL (90°-100°) | 0.0 | 0.0 | | U0/0 | |
| UH (100°-180°) | 0.0 | 0.0 | | U0/0 | |

BUG Rating: B2-U0-G1

Type II Short





REPORT NUMBER: P637832

CATALOG NUMBER: GWS-SA4D-750-U-T2R-W-GRSBK

CANDELA DISTRIBUTION (FULL):

| | 0° | 5° | 15° | 25° | 35° | 45° | 55° | 58° | 65° | 75° | 85° |
|-------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|
| 0° | 2005.8 | 2005.8 | 2005.8 | 2005.8 | 2005.8 | 2005.8 | 2005.8 | 2005.8 | 2005.8 | 2005.8 | 2005.8 |
| 2.5° | 2968.3 | 2921.6 | 2894.7 | 2873.1 | 2778.0 | 2627.1 | 2528.4 | 2476.3 | 2390.1 | 2244.6 | 2118.9 |
| 5° | 3873.4 | 3839.2 | 3776.4 | 3733.3 | 3611.2 | 3397.5 | 3176.6 | 3088.6 | 2892.9 | 2564.3 | 2269.8 |
| 7.5° | 4473.1 | 4448.0 | 4424.6 | 4367.2 | 4252.2 | 4058.3 | 3814.1 | 3722.5 | 3420.8 | 2953.9 | 2470.9 |
| 10° | 4934.6 | 4914.9 | 4887.9 | 4886.1 | 4796.3 | 4622.2 | 4383.3 | 4288.2 | 3961.3 | 3377.7 | 2707.9 |
| 12.5° | 5340.5 | 5324.3 | 5318.9 | 5369.2 | 5311.7 | 5182.4 | 4923.8 | 4805.3 | 4458.8 | 3810.5 | 2970.1 |
| 15° | 5618.8 | 5615.2 | 5638.5 | 5737.3 | 5769.6 | 5710.4 | 5493.1 | 5365.6 | 4966.9 | 4245.1 | 3259.2 |
| 17.5° | 5746.3 | 5757.1 | 5801.9 | 5972.5 | 6116.2 | 6166.5 | 5999.5 | 5891.7 | 5471.5 | 4685.0 | 3568.1 |
| 20° | 5963.6 | 5960.0 | 5986.9 | 6148.5 | 6324.5 | 6504.1 | 6453.8 | 6362.2 | 5981.5 | 5150.1 | 3911.1 |
| 22.5° | 6575.9 | 6523.8 | 6466.4 | 6491.5 | 6554.4 | 6764.5 | 6857.8 | 6811.1 | 6507.7 | 5627.8 | 4264.8 |
| 25° | 7516.9 | 7463.0 | 7278.0 | 7098.5 | 6979.9 | 7075.1 | 7202.6 | 7225.9 | 7030.2 | 6118.0 | 4634.7 |
| 27.5° | 8515.3 | 8466.8 | 8258.5 | 7989.1 | 7649.7 | 7484.5 | 7579.7 | 7626.4 | 7543.8 | 6701.6 | 5028.0 |
| 30° | 9450.8 | 9386.2 | 9158.1 | 8824.1 | 8430.9 | 8177.7 | 8069.9 | 8102.3 | 8150.7 | 7393.0 | 5489.5 |
| 32.5° | 10262.5 | 10214.0 | 9941.1 | 9589.1 | 9210.2 | 8946.2 | 8694.8 | 8748.7 | 8867.2 | 8238.7 | 6080.3 |
| 35° | 10950.3 | 10925.1 | 10636.0 | 10285.8 | 9885.4 | 9750.7 | 9535.2 | 9546.0 | 9664.5 | 9260.5 | 6800.4 |
| 37.5° | 11548.2 | 11505.1 | 11243.0 | 10917.9 | 10600.1 | 10578.5 | 10519.3 | 10524.7 | 10585.7 | 10451.0 | 7628.2 |
| 40° | 11925.3 | 11885.8 | 11699.1 | 11498.0 | 11271.7 | 11275.3 | 11582.3 | 11605.7 | 11535.7 | 11620.1 | 8502.7 |
| 42.5° | 12067.2 | 12038.5 | 11937.9 | 11939.7 | 11916.4 | 12022.3 | 12598.7 | 12641.8 | 12390.4 | 12537.7 | 9249.7 |
| 45° | 11821.2 | 11808.6 | 11815.8 | 12074.4 | 12354.5 | 12681.3 | 13430.1 | 13505.6 | 13150.0 | 13146.4 | 9833.3 |
| 47.5° | 11027.5 | 11002.3 | 11212.4 | 11652.4 | 12300.6 | 12936.3 | 13932.9 | 14049.7 | 13681.5 | 13494.8 | 10199.6 |
| 50° | 9472.4 | 9544.2 | 9876.4 | 10537.2 | 11523.1 | 12586.2 | 13927.5 | 14130.5 | 13701.3 | 13464.3 | 10138.6 |
| 52.5° | 6861.4 | 6847.1 | 7574.3 | 8482.9 | 9682.5 | 11465.6 | 13187.7 | 13484.0 | 13221.8 | 13164.4 | 10002.1 |
| 55° | 3733.3 | 3864.4 | 4354.6 | 5557.7 | 7055.4 | 9344.9 | 11498.0 | 12144.4 | 12447.9 | 13054.8 | 10248.1 |
| 57.5° | 1371.9 | 1429.4 | 1736.5 | 2587.6 | 3735.1 | 5810.9 | 8782.8 | 9757.9 | 10695.3 | 12749.6 | 10206.8 |
| 60° | 553.1 | 563.9 | 686.0 | 951.7 | 1569.5 | 2957.5 | 5268.6 | 6134.2 | 7017.6 | 9759.7 | 7832.9 |
| 62.5° | 402.2 | 416.6 | 465.1 | 556.7 | 793.7 | 1292.9 | 2271.6 | 2641.5 | 2887.5 | 4834.1 | 3859.0 |
| 65° | 325.0 | 335.8 | 375.3 | 416.6 | 524.3 | 694.9 | 732.7 | 705.7 | 702.1 | 1249.8 | 885.3 |
| 67.5° | 269.4 | 280.1 | 308.9 | 337.6 | 377.1 | 346.6 | 251.4 | 264.0 | 215.5 | 213.7 | 174.2 |
| 70° | 197.5 | 210.1 | 238.8 | 269.4 | 226.3 | 93.4 | 145.5 | 215.5 | 163.4 | 136.5 | 132.9 |
| 72.5° | 149.0 | 158.0 | 185.0 | 176.0 | 66.4 | 35.9 | 97.0 | 156.2 | 125.7 | 100.6 | 98.8 |
| 75° | 111.3 | 116.7 | 93.4 | 28.7 | 7.2 | 9.0 | 35.9 | 64.6 | 70.0 | 57.5 | 57.5 |
| 77.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 3.6 | 5.4 | 7.2 | 9.0 | 10.8 |
| 80° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 82.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 85° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 87.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P637832

CATALOG NUMBER: GWS-SA4D-750-U-T2R-W-GRSBK

CANDELA DISTRIBUTION (continued):

| | 90° | 95° | 105° | 115° | 125° | 135° | 145° | 155° | 165° | 175° | 180° |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 2005.8 | 2005.8 | 2005.8 | 2005.8 | 2005.8 | 2005.8 | 2005.8 | 2005.8 | 2005.8 | 2005.8 | 2005.8 |
| 2.5° | 2047.1 | 1971.7 | 1864.0 | 1774.2 | 1705.9 | 1639.5 | 1589.2 | 1538.9 | 1537.1 | 1512.0 | 1506.6 |
| 5° | 2133.3 | 1996.8 | 1799.3 | 1657.4 | 1571.2 | 1519.2 | 1483.3 | 1465.3 | 1456.3 | 1447.3 | 1443.8 |
| 7.5° | 2257.2 | 2061.5 | 1788.5 | 1637.7 | 1565.9 | 1531.7 | 1506.6 | 1495.8 | 1490.4 | 1483.3 | 1481.5 |
| 10° | 2409.8 | 2154.9 | 1828.0 | 1675.4 | 1612.6 | 1580.2 | 1553.3 | 1537.1 | 1528.2 | 1515.6 | 1512.0 |
| 12.5° | 2593.0 | 2269.8 | 1890.9 | 1738.3 | 1671.8 | 1628.7 | 1592.8 | 1569.5 | 1556.9 | 1540.7 | 1537.1 |
| 15° | 2790.5 | 2393.7 | 1960.9 | 1795.7 | 1716.7 | 1661.0 | 1616.1 | 1580.2 | 1556.9 | 1537.1 | 1531.7 |
| 17.5° | 2995.2 | 2519.4 | 2023.8 | 1835.2 | 1738.3 | 1671.8 | 1607.2 | 1558.7 | 1529.9 | 1504.8 | 1497.6 |
| 20° | 3225.1 | 2648.7 | 2065.1 | 1842.4 | 1731.1 | 1643.1 | 1567.7 | 1506.6 | 1477.9 | 1443.8 | 1436.6 |
| 22.5° | 3465.7 | 2769.0 | 2083.0 | 1826.2 | 1691.6 | 1589.2 | 1508.4 | 1445.5 | 1404.2 | 1368.3 | 1357.6 |
| 25° | 3699.2 | 2876.7 | 2074.0 | 1781.3 | 1632.3 | 1513.8 | 1431.2 | 1366.5 | 1321.6 | 1285.7 | 1276.8 |
| 27.5° | 3947.0 | 2966.5 | 2041.7 | 1714.9 | 1551.5 | 1431.2 | 1352.2 | 1296.5 | 1255.2 | 1215.7 | 1206.7 |
| 30° | 4225.3 | 3049.1 | 1989.6 | 1634.1 | 1456.3 | 1346.8 | 1285.7 | 1248.0 | 1203.1 | 1161.8 | 1149.3 |
| 32.5° | 4561.1 | 3122.7 | 1914.2 | 1537.1 | 1371.9 | 1273.2 | 1239.0 | 1210.3 | 1158.2 | 1115.1 | 1106.2 |
| 35° | 4945.4 | 3183.8 | 1819.1 | 1436.6 | 1289.3 | 1226.5 | 1219.3 | 1181.6 | 1113.3 | 1063.1 | 1052.3 |
| 37.5° | 5390.7 | 3243.1 | 1705.9 | 1337.8 | 1228.3 | 1204.9 | 1206.7 | 1142.1 | 1059.5 | 998.4 | 991.2 |
| 40° | 5870.2 | 3302.3 | 1580.2 | 1251.6 | 1172.6 | 1192.4 | 1176.2 | 1084.6 | 949.9 | 890.7 | 883.5 |
| 42.5° | 6369.4 | 3367.0 | 1452.7 | 1170.8 | 1125.9 | 1143.9 | 1120.5 | 969.7 | 872.7 | 842.2 | 838.6 |
| 45° | 6820.1 | 3444.2 | 1314.5 | 1090.0 | 1079.2 | 1073.8 | 1034.3 | 878.1 | 836.8 | 815.3 | 813.5 |
| 47.5° | 7145.1 | 3431.6 | 1167.2 | 1012.8 | 1028.9 | 1011.0 | 890.7 | 835.0 | 800.9 | 772.2 | 765.0 |
| 50° | 7085.9 | 3212.5 | 1014.6 | 926.6 | 964.3 | 948.1 | 800.9 | 784.7 | 754.2 | 723.7 | 712.9 |
| 52.5° | 6935.0 | 2914.4 | 881.7 | 835.0 | 894.3 | 856.6 | 739.8 | 723.7 | 696.7 | 657.2 | 644.7 |
| 55° | 7015.9 | 2634.3 | 777.5 | 761.4 | 822.4 | 709.3 | 671.6 | 646.5 | 617.7 | 574.6 | 569.2 |
| 57.5° | 6755.5 | 2149.5 | 624.9 | 635.7 | 727.3 | 605.2 | 589.0 | 549.5 | 501.0 | 472.3 | 468.7 |
| 60° | 4676.0 | 1154.6 | 391.5 | 404.0 | 526.1 | 508.2 | 527.9 | 492.0 | 432.8 | 405.8 | 400.4 |
| 62.5° | 2147.7 | 463.3 | 213.7 | 204.7 | 276.5 | 344.8 | 452.5 | 448.9 | 375.3 | 332.2 | 328.6 |
| 65° | 520.8 | 211.9 | 152.6 | 143.7 | 156.2 | 206.5 | 294.5 | 353.8 | 303.5 | 253.2 | 247.8 |
| 67.5° | 168.8 | 172.4 | 140.1 | 131.1 | 138.3 | 154.4 | 176.0 | 195.7 | 193.9 | 177.8 | 174.2 |
| 70° | 134.7 | 156.2 | 129.3 | 118.5 | 118.5 | 123.9 | 118.5 | 95.2 | 82.6 | 89.8 | 93.4 |
| 72.5° | 100.6 | 118.5 | 102.4 | 91.6 | 88.0 | 86.2 | 73.6 | 53.9 | 37.7 | 34.1 | 32.3 |
| 75° | 59.3 | 66.4 | 62.8 | 53.9 | 50.3 | 44.9 | 35.9 | 23.3 | 12.6 | 9.0 | 5.4 |
| 77.5° | 10.8 | 12.6 | 14.4 | 10.8 | 9.0 | 7.2 | 5.4 | 1.8 | 0.0 | 0.0 | 0.0 |
| 80° | 0.0 | 1.8 | 1.8 | 1.8 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 82.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 85° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 87.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



LM-79-2008: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGRAW-EDISON

Report Number: SP1-1908-441-4-R4

Test Date: 10/02/2019

Luminaire Tested: SA1C-750-U-5WQ

Data in this report applies to families of products SA1C-760-U-5WQ .

Test Information

Test Method: LM-79-2008
 Report Number: SP1-1908-441-4-R4
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 10/28/2024
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: MCGRAW-EDISON
 Catalog Number: **SA1C-750-U-5WQ**
 Description: MCGRAW EDISON ROADWAY AND AREA LUMINAIRE

THIS IS A REVISION OF SP1-1908-441-4-R3. TO UPDATE THE CATALOG INFORMATION.TESTED IN SITU. ROADWAY AND AREA LUMINAIRE. (1) 70 CRI, 5000K, 1050MA LIGHTSQUARE WITH 16 LEDS AND TYPE V WIDE OPTICS.

Spectral Parameters

CCT (K): 4884
 CIE u': 0.2101
 CIE v': 0.4904
 Duv: 0.0037
 CIE x: 0.3493
 CIE y: 0.3624
 CIE z: 0.2884
 Peak Wavelength (nm): 444
 Dominant Wavelength (nm): 571
 Purity: 13.7
 Rf: 74.9
 Rg: 96.3

| | | | |
|-----------|------|------|-------|
| CRI (Ra): | 73.5 | | |
| R1: | 70.5 | R9: | -28.4 |
| R2: | 77.7 | R10: | 48.6 |
| R3: | 84.6 | R11: | 73.2 |
| R4: | 74.7 | R12: | 50.7 |
| R5: | 71.9 | R13: | 71.2 |
| R6: | 70.7 | R14: | 91.4 |
| R7: | 81.2 | | |
| R8: | 56.9 | | |



Test Conditions

Stabilization Time: 240M
 Operation Time: 12H
 Room Temperature (°C) / RH%: 25.0./44%
 Sphere Temperature (°C): 25.7

REPORT NUMBER: SP1-1908-441-4-R4

| Measurement and Test Equipment | | | |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument | Identification Number | Calibration Date | Calibration Due Date |
| Photometer | IN0058 | 6/28/2019 | 12/28/2019 |
| Power Meter | IN0071 | 12/5/2018 | 12/5/2019 |
| AC Power Source | IN0063 | 12/5/2018 | 12/5/2019 |
| DC Power Source | IN0208 | 12/5/2018 | 12/5/2019 |
| Sphere Thermometer | IN0085 | 12/5/2018 | 12/5/2019 |
| Room Thermometer | IN0046 | 12/5/2018 | 12/5/2019 |

REPORT NUMBER: SP1-1908-441-4-R4

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 5000K 4-step quadrangle

REPORT NUMBER: SP1-1908-441-4-R4

Photopic Flux vs. Wavelength



#####

| λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) |
|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|
| 360 | 2945 | NR | 490 | 37941 | NR | 620 | 88803 | NR | 750 | 3908 | NR | 880 | 2997 | NR |
| 365 | 2596 | NR | 495 | 48525 | NR | 625 | 80578 | NR | 755 | 3988 | NR | 885 | 2927 | NR |
| 370 | 2732 | NR | 500 | 60609 | NR | 630 | 73127 | NR | 760 | 3335 | NR | 890 | 2649 | NR |
| 375 | 2894 | NR | 505 | 72036 | NR | 635 | 66244 | NR | 765 | 3438 | NR | 895 | 2828 | NR |
| 380 | 2822 | NR | 510 | 82168 | NR | 640 | 59440 | NR | 770 | 3427 | NR | 900 | 1407 | NR |
| 385 | 2394 | NR | 515 | 90898 | NR | 645 | 52864 | NR | 775 | 2759 | NR | 905 | 2224 | NR |
| 390 | 2370 | NR | 520 | 97142 | NR | 650 | 47085 | NR | 780 | 2340 | NR | 910 | 2905 | NR |
| 395 | 2267 | NR | 525 | 103255 | NR | 655 | 41789 | NR | 785 | 2412 | NR | 915 | 3350 | NR |
| 400 | 2262 | NR | 530 | 106697 | NR | 660 | 37064 | NR | 790 | 1999 | NR | 920 | 3114 | NR |
| 405 | 3000 | NR | 535 | 110081 | NR | 665 | 32299 | NR | 795 | 2054 | NR | 925 | 2834 | NR |
| 410 | 5324 | NR | 540 | 112494 | NR | 670 | 28142 | NR | 800 | 2331 | NR | 930 | 2271 | NR |
| 415 | 10725 | NR | 545 | 115513 | NR | 675 | 24505 | NR | 805 | 2648 | NR | 935 | 2228 | NR |
| 420 | 22128 | NR | 550 | 117203 | NR | 680 | 21162 | NR | 810 | 2485 | NR | 940 | 2833 | NR |
| 425 | 44095 | NR | 555 | 119753 | NR | 685 | 18400 | NR | 815 | 2409 | NR | 945 | 2941 | NR |
| 430 | 77002 | NR | 560 | 122602 | NR | 690 | 16065 | NR | 820 | 2221 | NR | 950 | 2323 | NR |
| 435 | 119881 | NR | 565 | 124314 | NR | 695 | 13860 | NR | 825 | 1562 | NR | 955 | 1667 | NR |
| 440 | 164454 | NR | 570 | 126775 | NR | 700 | 12177 | NR | 830 | 2249 | NR | 960 | 749 | NR |
| 445 | 179997 | NR | 575 | 127511 | NR | 705 | 10757 | NR | 835 | 2573 | NR | 965 | 2669 | NR |
| 450 | 142822 | NR | 580 | 127577 | NR | 710 | 9601 | NR | 840 | 2764 | NR | 970 | 3968 | NR |
| 455 | 90008 | NR | 585 | 126153 | NR | 715 | 8944 | NR | 845 | 3109 | NR | 975 | 3886 | NR |
| 460 | 60557 | NR | 590 | 123678 | NR | 720 | 7947 | NR | 850 | 2963 | NR | 980 | 2788 | NR |
| 465 | 43305 | NR | 595 | 119774 | NR | 725 | 7062 | NR | 855 | 2336 | NR | 985 | 3496 | NR |
| 470 | 31089 | NR | 600 | 115733 | NR | 730 | 6004 | NR | 860 | 2118 | NR | 990 | 2913 | NR |
| 475 | 26278 | NR | 605 | 109231 | NR | 735 | 5594 | NR | 865 | 3144 | NR | 995 | 4659 | NR |
| 480 | 27060 | NR | 610 | 102408 | NR | 740 | 5165 | NR | 870 | 3069 | NR | 1000 | 1308 | NR |
| 485 | 30698 | NR | 615 | 96015 | NR | 745 | 4687 | NR | 875 | 3311 | NR | | | |

REPORT NUMBER: SP1-1908-441-4-R4

Scotopic Flux vs. Wavelength



Scotopic Lumens: 13493.5 S/P: 1.77

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 2945 | NR | 490 | 37941 | NR | 620 | 88803 | NR | 750 | 3908 | NR | 880 | 2997 | NR |
| 365 | 2596 | NR | 495 | 48525 | NR | 625 | 80578 | NR | 755 | 3988 | NR | 885 | 2927 | NR |
| 370 | 2732 | NR | 500 | 60609 | NR | 630 | 73127 | NR | 760 | 3335 | NR | 890 | 2649 | NR |
| 375 | 2894 | NR | 505 | 72036 | NR | 635 | 66244 | NR | 765 | 3438 | NR | 895 | 2828 | NR |
| 380 | 2822 | NR | 510 | 82168 | NR | 640 | 59440 | NR | 770 | 3427 | NR | 900 | 1407 | NR |
| 385 | 2394 | NR | 515 | 90898 | NR | 645 | 52864 | NR | 775 | 2759 | NR | 905 | 2224 | NR |
| 390 | 2370 | NR | 520 | 97142 | NR | 650 | 47085 | NR | 780 | 2340 | NR | 910 | 2905 | NR |
| 395 | 2267 | NR | 525 | 103255 | NR | 655 | 41789 | NR | 785 | 2412 | NR | 915 | 3350 | NR |
| 400 | 2262 | NR | 530 | 106697 | NR | 660 | 37064 | NR | 790 | 1999 | NR | 920 | 3114 | NR |
| 405 | 3000 | NR | 535 | 110081 | NR | 665 | 32299 | NR | 795 | 2054 | NR | 925 | 2834 | NR |
| 410 | 5324 | NR | 540 | 112494 | NR | 670 | 28142 | NR | 800 | 2331 | NR | 930 | 2271 | NR |
| 415 | 10725 | NR | 545 | 115513 | NR | 675 | 24505 | NR | 805 | 2648 | NR | 935 | 2228 | NR |
| 420 | 22128 | NR | 550 | 117203 | NR | 680 | 21162 | NR | 810 | 2485 | NR | 940 | 2833 | NR |
| 425 | 44095 | NR | 555 | 119753 | NR | 685 | 18400 | NR | 815 | 2409 | NR | 945 | 2941 | NR |
| 430 | 77002 | NR | 560 | 122602 | NR | 690 | 16065 | NR | 820 | 2221 | NR | 950 | 2323 | NR |
| 435 | 119881 | NR | 565 | 124314 | NR | 695 | 13860 | NR | 825 | 1562 | NR | 955 | 1667 | NR |
| 440 | 164454 | NR | 570 | 126775 | NR | 700 | 12177 | NR | 830 | 2249 | NR | 960 | 749 | NR |
| 445 | 179997 | NR | 575 | 127511 | NR | 705 | 10757 | NR | 835 | 2573 | NR | 965 | 2669 | NR |
| 450 | 142822 | NR | 580 | 127577 | NR | 710 | 9601 | NR | 840 | 2764 | NR | 970 | 3968 | NR |
| 455 | 90008 | NR | 585 | 126153 | NR | 715 | 8944 | NR | 845 | 3109 | NR | 975 | 3886 | NR |
| 460 | 60557 | NR | 590 | 123678 | NR | 720 | 7947 | NR | 850 | 2963 | NR | 980 | 2788 | NR |
| 465 | 43305 | NR | 595 | 119774 | NR | 725 | 7062 | NR | 855 | 2336 | NR | 985 | 3496 | NR |
| 470 | 31089 | NR | 600 | 115733 | NR | 730 | 6004 | NR | 860 | 2118 | NR | 990 | 2913 | NR |
| 475 | 26278 | NR | 605 | 109231 | NR | 735 | 5594 | NR | 865 | 3144 | NR | 995 | 4659 | NR |
| 480 | 27060 | NR | 610 | 102408 | NR | 740 | 5165 | NR | 870 | 3069 | NR | 1000 | 1308 | NR |
| 485 | 30698 | NR | 615 | 96015 | NR | 745 | 4687 | NR | 875 | 3311 | NR | | | |

REPORT NUMBER: SP1-1908-441-4-R4

Melanopic Flux vs. Wavelength



Melanopic Lumens: 5378.9 M/P: 0.71

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 2945 | NR | 490 | 37941 | NR | 620 | 88803 | NR | 750 | 3908 | NR | 880 | 2997 | NR |
| 365 | 2596 | NR | 495 | 48525 | NR | 625 | 80578 | NR | 755 | 3988 | NR | 885 | 2927 | NR |
| 370 | 2732 | NR | 500 | 60609 | NR | 630 | 73127 | NR | 760 | 3335 | NR | 890 | 2649 | NR |
| 375 | 2894 | NR | 505 | 72036 | NR | 635 | 66244 | NR | 765 | 3438 | NR | 895 | 2828 | NR |
| 380 | 2822 | NR | 510 | 82168 | NR | 640 | 59440 | NR | 770 | 3427 | NR | 900 | 1407 | NR |
| 385 | 2394 | NR | 515 | 90898 | NR | 645 | 52864 | NR | 775 | 2759 | NR | 905 | 2224 | NR |
| 390 | 2370 | NR | 520 | 97142 | NR | 650 | 47085 | NR | 780 | 2340 | NR | 910 | 2905 | NR |
| 395 | 2267 | NR | 525 | 103255 | NR | 655 | 41789 | NR | 785 | 2412 | NR | 915 | 3350 | NR |
| 400 | 2262 | NR | 530 | 106697 | NR | 660 | 37064 | NR | 790 | 1999 | NR | 920 | 3114 | NR |
| 405 | 3000 | NR | 535 | 110081 | NR | 665 | 32299 | NR | 795 | 2054 | NR | 925 | 2834 | NR |
| 410 | 5324 | NR | 540 | 112494 | NR | 670 | 28142 | NR | 800 | 2331 | NR | 930 | 2271 | NR |
| 415 | 10725 | NR | 545 | 115513 | NR | 675 | 24505 | NR | 805 | 2648 | NR | 935 | 2228 | NR |
| 420 | 22128 | NR | 550 | 117203 | NR | 680 | 21162 | NR | 810 | 2485 | NR | 940 | 2833 | NR |
| 425 | 44095 | NR | 555 | 119753 | NR | 685 | 18400 | NR | 815 | 2409 | NR | 945 | 2941 | NR |
| 430 | 77002 | NR | 560 | 122602 | NR | 690 | 16065 | NR | 820 | 2221 | NR | 950 | 2323 | NR |
| 435 | 119881 | NR | 565 | 124314 | NR | 695 | 13860 | NR | 825 | 1562 | NR | 955 | 1667 | NR |
| 440 | 164454 | NR | 570 | 126775 | NR | 700 | 12177 | NR | 830 | 2249 | NR | 960 | 749 | NR |
| 445 | 179997 | NR | 575 | 127511 | NR | 705 | 10757 | NR | 835 | 2573 | NR | 965 | 2669 | NR |
| 450 | 142822 | NR | 580 | 127577 | NR | 710 | 9601 | NR | 840 | 2764 | NR | 970 | 3968 | NR |
| 455 | 90008 | NR | 585 | 126153 | NR | 715 | 8944 | NR | 845 | 3109 | NR | 975 | 3886 | NR |
| 460 | 60557 | NR | 590 | 123678 | NR | 720 | 7947 | NR | 850 | 2963 | NR | 980 | 2788 | NR |
| 465 | 43305 | NR | 595 | 119774 | NR | 725 | 7062 | NR | 855 | 2336 | NR | 985 | 3496 | NR |
| 470 | 31089 | NR | 600 | 115733 | NR | 730 | 6004 | NR | 860 | 2118 | NR | 990 | 2913 | NR |
| 475 | 26278 | NR | 605 | 109231 | NR | 735 | 5594 | NR | 865 | 3144 | NR | 995 | 4659 | NR |
| 480 | 27060 | NR | 610 | 102408 | NR | 740 | 5165 | NR | 870 | 3069 | NR | 1000 | 1308 | NR |
| 485 | 30698 | NR | 615 | 96015 | NR | 745 | 4687 | NR | 875 | 3311 | NR | | | |

REPORT NUMBER: SP1-1908-441-4-R4

TM-30-18

Summary

$R_f = 74.9$
 $R_g = 96.3$
 CIE $R_a = 73.5$
 $R_g = -28.4$



Color Vector Graphics



REPORT NUMBER: SP1-1908-441-4-R4

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)

| | | | |
|------------|------------|------------|------------|
| CES01 = 85 | CES26 = 61 | CES51 = 90 | CES76 = 52 |
| CES02 = 60 | CES27 = 84 | CES52 = 91 | CES77 = 71 |
| CES03 = 30 | CES28 = 81 | CES53 = 79 | CES78 = 54 |
| CES04 = 69 | CES29 = 58 | CES54 = 83 | CES79 = 80 |
| CES05 = 46 | CES30 = 67 | CES55 = 83 | CES80 = 77 |
| CES06 = 50 | CES31 = 63 | CES56 = 73 | CES81 = 77 |
| CES07 = 39 | CES32 = 59 | CES57 = 72 | CES82 = 90 |
| CES08 = 38 | CES33 = 69 | CES58 = 73 | CES83 = 86 |
| CES09 = 29 | CES34 = 69 | CES59 = 88 | CES84 = 88 |
| CES10 = 73 | CES35 = 83 | CES60 = 93 | CES85 = 84 |
| CES11 = 56 | CES36 = 95 | CES61 = 88 | CES86 = 75 |
| CES12 = 61 | CES37 = 78 | CES62 = 85 | CES87 = 78 |
| CES13 = 41 | CES38 = 76 | CES63 = 77 | CES88 = 79 |
| CES14 = 74 | CES39 = 93 | CES64 = 74 | CES89 = 75 |
| CES15 = 70 | CES40 = 86 | CES65 = 67 | CES90 = 77 |
| CES16 = 46 | CES41 = 87 | CES66 = 69 | CES91 = 89 |
| CES17 = 49 | CES42 = 78 | CES67 = 67 | CES92 = 66 |
| CES18 = 55 | CES43 = 75 | CES68 = 73 | CES93 = 80 |
| CES19 = 71 | CES44 = 99 | CES69 = 81 | CES94 = 57 |
| CES20 = 64 | CES45 = 83 | CES70 = 63 | CES95 = 71 |
| CES21 = 85 | CES46 = 81 | CES71 = 60 | CES96 = 78 |
| CES22 = 77 | CES47 = 80 | CES72 = 86 | CES97 = 85 |
| CES23 = 91 | CES48 = 72 | CES73 = 53 | CES98 = 75 |
| CES24 = 90 | CES49 = 81 | CES74 = 96 | CES99 = 62 |
| CES25 = 71 | CES50 = 89 | CES75 = 58 | |



REPORT NUMBER: SP1-1908-441-4-R4

TM-30-18

Color Rendition by Hue-Angle Bin



REPORT NUMBER: SP1-1908-441-4-R4

TM-30-18

Measure Comparisons



(END OF REPORT)