

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: McGRAW-EDISON

Report Number: P633406

Luminaire Tested: GWS-SA2E-760-U-RW-W-GRSBK

Issue Date: 1/10/2023

Test Information

Test Method: LM-79-2019
Report Number: P633406
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2209-782-50)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/10/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: McGRAW-EDISON
Catalog Number: GWS-SA2E-760-U-RW-W-GRSBK
Description: GALLEON WALL SLIM LUMINAIRE. (2) LIGHTSQUARES WITH 16 LEDS EACH AND RECTANGULAR WIDE OPTICS W/ FACTORY INSTALLED GLARE SHIELD, BK
Light Source: (32) 5700K CCT, 70 CRI LEDS
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 9540.9 lumens
Efficiency: N/A
Efficacy: 88.2 lumens/watt
Luminous Opening: Rectangular (W 1' x L: 0.5' x H: 0')
IES Classification: Type V - Short
BUG Rating: B3 - U0 - G0


Input Watts (W): 108.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 0
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT



REPORT NUMBER: P633406
 CATALOG NUMBER: GWS-SA2E-760-U-RW-W-GRSBK

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 10 foot mounting height. Maximum calculated value = 16.3 fc
 Type V - Short - N/A

REPORT NUMBER: P633406
CATALOG NUMBER: GWS-SA2E-760-U-RW-W-GRSBK

Luminous Intensity Polar Plot



— Vertical Plane Through 43-Deg Lateral - - - Horizontal Cone Through 50-Deg Vertical

REPORT NUMBER: P633406
 CATALOG NUMBER: GWS-SA2E-760-U-RW-W-GRSBK

FLUX DISTRIBUTION:

| | | Downward | Upward | Total |
|--------------------|-----------|----------|--------|--------|
| House Side | Lumens | 4770.3 | 0.0 | 4770.3 |
| | % Fixture | 50.0 | 0.0 | 50.0 |
| Street Side | Lumens | 4770.6 | 0.0 | 4770.6 |
| | % Fixture | 50.0 | 0.0 | 50.0 |
| Total | Lumens | 9540.9 | 0.0 | 9540.9 |
| | % Fixture | 100.0 | 0.0 | 100.0 |

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 133.6 | 1.4 |
| 10°-20° | 459.9 | 4.8 |
| 20°-30° | 930.4 | 9.8 |
| 30°-40° | 1726.3 | 18.1 |
| 40°-50° | 2865.5 | 30.0 |
| 50°-60° | 2924.4 | 30.7 |
| 60°-70° | 479.6 | 5.0 |
| 70°-80° | 21.0 | 0.2 |
| 80°-90° | 0.3 | 0.0 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-90° | 9540.9 | 100.0 |
| 0°-180° | 9540.9 | 100.0 |

Coefficient of Utilization



REPORT NUMBER: P633406


CATALOG NUMBER: GWS-SA2E-760-U-RW-W-GRSBK

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

| Zone | Lumens | % Fixture | Zone Rating/Lumen Limit | | |
|----------------|--------|-----------|-------------------------|------|--------|
| | | | B | U | G |
| FL (0°-30°) | 768.7 | 8.1 | | | |
| FM (30°-60°) | 3767.2 | 39.5 | | | |
| FH (60°-80°) | 234.6 | 2.5 | | | G0/660 |
| FVH (80°-90°) | 0.1 | 0.0 | | | G0/10 |
| BL (0°-30°) | 755.3 | 7.9 | B2/1000 | | |
| BM (30°-60°) | 3748.9 | 39.3 | B3/5000 | | |
| BH (60°-80°) | 266.0 | 2.8 | B1/500 | | G0/660 |
| BVH (80°-90°) | 0.2 | 0.0 | | | G0/10 |
| UL (90°-100°) | 0.0 | 0.0 | | U0/0 | |
| UH (100°-180°) | 0.0 | 0.0 | | U0/0 | |

BUG Rating: B3-U0-G0

Type V Short





REPORT NUMBER: P633406

CATALOG NUMBER: GWS-SA2E-760-U-RW-W-GRSBK

CANDELA DISTRIBUTION (FULL):

| | 0° | 5° | 15° | 25° | 35° | 43° | 45° | 55° | 65° | 75° | 85° |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 1357.0 | 1357.0 | 1357.0 | 1357.0 | 1357.0 | 1357.0 | 1357.0 | 1357.0 | 1357.0 | 1357.0 | 1357.0 |
| 2.5° | 1331.7 | 1334.9 | 1339.1 | 1343.3 | 1348.6 | 1353.9 | 1357.0 | 1366.5 | 1364.4 | 1372.9 | 1372.9 |
| 5° | 1316.9 | 1320.1 | 1325.4 | 1334.9 | 1346.5 | 1358.1 | 1366.5 | 1385.5 | 1396.1 | 1413.0 | 1419.3 |
| 7.5° | 1324.3 | 1328.6 | 1334.9 | 1349.7 | 1367.6 | 1385.5 | 1395.0 | 1425.6 | 1446.7 | 1478.4 | 1496.3 |
| 10° | 1348.6 | 1352.8 | 1363.4 | 1388.7 | 1411.9 | 1437.2 | 1448.8 | 1487.9 | 1521.7 | 1564.9 | 1590.3 |
| 12.5° | 1376.0 | 1381.3 | 1402.4 | 1440.4 | 1480.5 | 1514.3 | 1530.1 | 1573.4 | 1608.2 | 1656.7 | 1696.8 |
| 15° | 1404.5 | 1413.0 | 1445.7 | 1501.6 | 1558.6 | 1604.0 | 1620.9 | 1667.3 | 1702.1 | 1753.8 | 1799.2 |
| 17.5° | 1471.0 | 1480.5 | 1517.4 | 1577.6 | 1655.7 | 1708.4 | 1723.2 | 1771.8 | 1798.1 | 1833.0 | 1880.4 |
| 20° | 1554.4 | 1572.3 | 1617.7 | 1690.5 | 1776.0 | 1826.6 | 1837.2 | 1884.7 | 1882.6 | 1897.3 | 1938.5 |
| 22.5° | 1657.8 | 1670.4 | 1720.0 | 1806.6 | 1902.6 | 1958.5 | 1982.8 | 2002.9 | 1976.5 | 1963.8 | 1990.2 |
| 25° | 1765.4 | 1780.2 | 1834.0 | 1929.0 | 2036.6 | 2101.0 | 2121.0 | 2136.9 | 2094.7 | 2047.2 | 2050.3 |
| 27.5° | 1904.7 | 1915.3 | 1968.0 | 2069.3 | 2177.0 | 2249.8 | 2267.7 | 2295.2 | 2239.2 | 2163.2 | 2142.1 |
| 30° | 2070.4 | 2080.9 | 2136.9 | 2243.4 | 2350.0 | 2412.3 | 2439.7 | 2473.5 | 2412.3 | 2317.3 | 2293.0 |
| 32.5° | 2264.6 | 2275.1 | 2346.9 | 2456.6 | 2544.2 | 2611.7 | 2638.1 | 2674.0 | 2625.4 | 2518.9 | 2491.4 |
| 35° | 2496.7 | 2503.0 | 2587.5 | 2706.7 | 2799.6 | 2865.0 | 2882.9 | 2925.1 | 2871.3 | 2764.7 | 2750.0 |
| 37.5° | 2765.8 | 2773.2 | 2865.0 | 3003.2 | 3098.2 | 3171.0 | 3199.5 | 3211.1 | 3145.7 | 3026.4 | 3014.8 |
| 40° | 3061.3 | 3085.5 | 3175.2 | 3324.0 | 3430.6 | 3522.4 | 3547.7 | 3508.7 | 3416.9 | 3254.4 | 3233.3 |
| 42.5° | 3369.4 | 3390.5 | 3490.7 | 3652.2 | 3775.7 | 3869.6 | 3870.6 | 3786.2 | 3630.0 | 3405.3 | 3373.6 |
| 45° | 3625.8 | 3634.3 | 3764.1 | 3926.6 | 4078.5 | 4145.0 | 4151.3 | 3998.3 | 3763.0 | 3492.9 | 3425.3 |
| 47.5° | 3802.0 | 3815.8 | 3928.7 | 4084.8 | 4252.6 | 4312.8 | 4300.1 | 4109.1 | 3826.3 | 3549.8 | 3438.0 |
| 50° | 3804.1 | 3827.4 | 3949.8 | 4100.7 | 4263.2 | 4336.0 | 4318.1 | 4140.8 | 3862.2 | 3551.9 | 3407.4 |
| 52.5° | 3467.5 | 3505.5 | 3705.0 | 3923.4 | 4172.4 | 4296.9 | 4301.2 | 4181.9 | 3848.5 | 3518.2 | 3379.9 |
| 55° | 2615.9 | 2657.1 | 2908.2 | 3280.7 | 3761.9 | 4109.1 | 4169.3 | 4133.4 | 3832.6 | 3533.0 | 3428.5 |
| 57.5° | 1384.5 | 1352.8 | 1492.1 | 1861.4 | 2466.1 | 3080.3 | 3256.5 | 3543.5 | 3656.4 | 3550.9 | 3518.2 |
| 60° | 301.8 | 321.8 | 428.4 | 577.2 | 962.4 | 1448.8 | 1620.9 | 2112.6 | 2697.2 | 2956.8 | 3144.6 |
| 62.5° | 129.8 | 127.7 | 133.0 | 150.9 | 220.5 | 367.2 | 448.5 | 732.3 | 1155.5 | 1587.1 | 1879.4 |
| 65° | 106.6 | 107.6 | 111.9 | 111.9 | 104.5 | 105.5 | 110.8 | 167.8 | 270.1 | 378.8 | 508.6 |
| 67.5° | 80.2 | 81.3 | 88.6 | 90.8 | 85.5 | 76.0 | 74.9 | 63.3 | 66.5 | 83.4 | 86.5 |
| 70° | 50.7 | 50.7 | 54.9 | 57.0 | 57.0 | 52.8 | 51.7 | 45.4 | 44.3 | 50.7 | 57.0 |
| 72.5° | 27.4 | 27.4 | 29.5 | 30.6 | 29.5 | 28.5 | 28.5 | 27.4 | 26.4 | 30.6 | 39.0 |
| 75° | 11.6 | 11.6 | 12.7 | 12.7 | 11.6 | 11.6 | 11.6 | 11.6 | 11.6 | 13.7 | 21.1 |
| 77.5° | 2.1 | 3.2 | 4.2 | 3.2 | 2.1 | 2.1 | 2.1 | 3.2 | 3.2 | 4.2 | 6.3 |
| 80° | 1.1 | 1.1 | 2.1 | 1.1 | 0.0 | 0.0 | 0.0 | 0.0 | 1.1 | 1.1 | 1.1 |
| 82.5° | 1.1 | 1.1 | 1.1 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 1.1 |
| 85° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 87.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P633406

CATALOG NUMBER: GWS-SA2E-760-U-RW-W-GRSBK

CANDELA DISTRIBUTION (continued):

| | 90° | 95° | 105° | 115° | 125° | 135° | 145° | 155° | 165° | 175° | 180° |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 1357.0 | 1357.0 | 1357.0 | 1357.0 | 1357.0 | 1357.0 | 1357.0 | 1357.0 | 1357.0 | 1357.0 | 1357.0 |
| 2.5° | 1380.3 | 1368.6 | 1372.9 | 1375.0 | 1371.8 | 1369.7 | 1358.1 | 1354.9 | 1349.7 | 1341.2 | 1339.1 |
| 5° | 1426.7 | 1417.2 | 1416.1 | 1409.8 | 1395.0 | 1377.1 | 1354.9 | 1345.4 | 1334.9 | 1324.3 | 1322.2 |
| 7.5° | 1504.8 | 1493.2 | 1485.8 | 1464.7 | 1430.9 | 1402.4 | 1365.5 | 1345.4 | 1331.7 | 1318.0 | 1314.8 |
| 10° | 1605.0 | 1591.3 | 1570.2 | 1531.2 | 1485.8 | 1444.6 | 1401.4 | 1375.0 | 1353.9 | 1334.9 | 1333.8 |
| 12.5° | 1711.6 | 1696.8 | 1658.8 | 1609.2 | 1554.4 | 1516.4 | 1461.5 | 1424.6 | 1392.9 | 1364.4 | 1361.3 |
| 15° | 1823.5 | 1805.5 | 1753.8 | 1694.7 | 1644.1 | 1605.0 | 1544.9 | 1485.8 | 1437.2 | 1396.1 | 1391.9 |
| 17.5° | 1908.9 | 1886.8 | 1825.6 | 1781.2 | 1740.1 | 1700.0 | 1632.5 | 1554.4 | 1490.0 | 1440.4 | 1428.8 |
| 20° | 1962.8 | 1941.6 | 1883.6 | 1859.3 | 1840.3 | 1811.9 | 1731.7 | 1650.4 | 1578.6 | 1517.4 | 1506.9 |
| 22.5° | 2014.5 | 1989.1 | 1938.5 | 1938.5 | 1953.3 | 1941.6 | 1855.1 | 1762.3 | 1677.8 | 1607.1 | 1591.3 |
| 25° | 2072.5 | 2052.4 | 2016.6 | 2046.1 | 2083.0 | 2082.0 | 1993.4 | 1877.3 | 1780.2 | 1701.1 | 1685.2 |
| 27.5° | 2156.9 | 2136.9 | 2124.2 | 2180.1 | 2226.6 | 2223.4 | 2126.3 | 2000.7 | 1898.4 | 1820.3 | 1805.5 |
| 30° | 2305.7 | 2286.7 | 2273.0 | 2340.5 | 2399.6 | 2377.5 | 2270.9 | 2149.5 | 2046.1 | 1957.5 | 1946.9 |
| 32.5° | 2504.1 | 2484.0 | 2466.1 | 2533.6 | 2586.4 | 2557.9 | 2456.6 | 2342.6 | 2223.4 | 2136.9 | 2115.8 |
| 35° | 2764.7 | 2722.5 | 2704.6 | 2784.8 | 2806.9 | 2775.3 | 2678.2 | 2578.0 | 2451.3 | 2352.1 | 2338.4 |
| 37.5° | 3033.8 | 2984.2 | 2971.6 | 3041.2 | 3077.1 | 3065.5 | 2951.5 | 2847.0 | 2709.9 | 2600.1 | 2584.3 |
| 40° | 3263.9 | 3218.5 | 3196.3 | 3305.0 | 3386.3 | 3393.7 | 3291.3 | 3163.6 | 3002.2 | 2888.2 | 2859.7 |
| 42.5° | 3398.9 | 3359.9 | 3354.6 | 3523.5 | 3656.4 | 3751.4 | 3629.0 | 3497.1 | 3327.2 | 3198.4 | 3175.2 |
| 45° | 3429.5 | 3404.2 | 3448.5 | 3670.1 | 3877.0 | 4050.0 | 3945.6 | 3806.3 | 3622.6 | 3486.5 | 3464.4 |
| 47.5° | 3426.4 | 3417.9 | 3497.1 | 3746.1 | 4007.8 | 4221.0 | 4169.3 | 4012.0 | 3834.8 | 3692.3 | 3671.2 |
| 50° | 3381.0 | 3382.1 | 3514.0 | 3784.1 | 4060.6 | 4267.4 | 4215.7 | 4070.1 | 3911.8 | 3771.4 | 3754.6 |
| 52.5° | 3363.1 | 3356.7 | 3482.3 | 3772.5 | 4114.4 | 4246.3 | 4130.2 | 3966.7 | 3790.4 | 3617.4 | 3592.0 |
| 55° | 3426.4 | 3410.5 | 3486.5 | 3763.0 | 4120.7 | 4234.7 | 3928.7 | 3574.1 | 3213.2 | 3008.5 | 2991.6 |
| 57.5° | 3521.3 | 3504.5 | 3540.3 | 3693.3 | 3790.4 | 3521.3 | 2891.4 | 2319.4 | 1948.0 | 1790.7 | 1722.2 |
| 60° | 3144.6 | 3133.0 | 3105.6 | 2920.9 | 2505.1 | 1889.9 | 1287.4 | 821.0 | 589.9 | 477.0 | 477.0 |
| 62.5° | 1951.1 | 1935.3 | 1786.5 | 1327.5 | 964.5 | 558.2 | 307.1 | 192.1 | 145.6 | 136.1 | 135.1 |
| 65° | 547.7 | 544.5 | 450.6 | 318.7 | 202.6 | 125.6 | 110.8 | 112.9 | 110.8 | 107.6 | 106.6 |
| 67.5° | 82.3 | 90.8 | 90.8 | 73.9 | 70.7 | 79.1 | 92.9 | 99.2 | 93.9 | 88.6 | 86.5 |
| 70° | 52.8 | 57.0 | 54.9 | 47.5 | 50.7 | 59.1 | 66.5 | 67.5 | 64.4 | 59.1 | 58.0 |
| 72.5° | 36.9 | 41.2 | 33.8 | 30.6 | 31.7 | 34.8 | 38.0 | 38.0 | 36.9 | 34.8 | 32.7 |
| 75° | 22.2 | 22.2 | 15.8 | 14.8 | 14.8 | 15.8 | 15.8 | 17.9 | 17.9 | 16.9 | 15.8 |
| 77.5° | 7.4 | 8.4 | 5.3 | 4.2 | 4.2 | 4.2 | 5.3 | 6.3 | 6.3 | 5.3 | 4.2 |
| 80° | 1.1 | 2.1 | 1.1 | 1.1 | 1.1 | 1.1 | 1.1 | 1.1 | 2.1 | 2.1 | 1.1 |
| 82.5° | 1.1 | 1.1 | 1.1 | 0.0 | 0.0 | 0.0 | 0.0 | 1.1 | 1.1 | 1.1 | 1.1 |
| 85° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 1.1 | 1.1 |
| 87.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



LM-79-2008: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGRAW-EDISON

Report Number: SP1-1908-441-9-R4

Test Date: 10/23/2019

Luminaire Tested: SA1C-760-U-5WQ

Data in this report applies to families of products SA1C-760-U-5WQ .

Test Information

Test Method: LM-79-2008
 Report Number: SP1-1908-441-9-R4
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 10/28/2024
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: McGRAW-EDISON
 Catalog Number: **SA1C-760-U-5WQ**
 Description: McGRAW EDISON ROADWAY AND AREA LUMINAIRE

THIS IS A REVISION OF SP1-1908-441-4-R3. TO UPDATE THE CATALOG INFORMATION.TESTED IN SITU. ROADWAY AND AREA LUMINAIRE. (1) 70 CRI, 5000K, 1050MA LIGHTSQUARE WITH 16 LEDS AND TYPE V WIDE OPTICS.

Spectral Parameters

CCT (K): 5474
 CIE u': 0.2052
 CIE v': 0.4804
 Duv: 0.0025
 CIE x: 0.3330
 CIE y: 0.3466
 CIE z: 0.3204
 Peak Wavelength (nm): 442
 Dominant Wavelength (nm): 554
 Purity: 4.1

| | | | |
|-----------|------|------|-------|
| CRI (Ra): | 71.7 | | |
| R1: | 70.6 | R9: | -27.1 |
| R2: | 74.6 | R10: | 40.8 |
| R3: | 78.3 | R11: | 74.6 |
| R4: | 73.8 | R12: | 50.4 |
| R5: | 72.4 | R13: | 70.0 |
| R6: | 67.5 | R14: | 87.8 |
| R7: | 77.5 | | |
| R8: | 58.9 | | |

Rf: 72.1
 Rg: 97.2



Test Conditions

Stabilization Time: 240M
 Operation Time: 12H
 Room Temperature (°C) / RH%: 24.6/31%
 Sphere Temperature (°C): 25.9

REPORT NUMBER: SP1-1908-441-9-R4

| Measurement and Test Equipment | | | |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument | Identification Number | Calibration Date | Calibration Due Date |
| Photometer | IN0058 | 6/28/2019 | 12/28/2019 |
| Power Meter | IN0071 | 12/5/2018 | 12/5/2019 |
| AC Power Source | IN0063 | 12/5/2018 | 12/5/2019 |
| DC Power Source | IN0208 | 12/5/2018 | 12/5/2019 |
| Sphere Thermometer | IN0085 | 12/5/2018 | 12/5/2019 |
| Room Thermometer | IN0046 | 12/5/2018 | 12/5/2019 |

REPORT NUMBER: SP1-1908-441-9-R4

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 5700K 4-step quadrangle

REPORT NUMBER: SP1-1908-441-9-R4

Photopic Flux vs. Wavelength



#####

| λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) |
|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|
| 360 | 3540 | NR | 490 | 33363 | NR | 620 | 80193 | NR | 750 | 4663 | NR | 880 | 4678 | NR |
| 365 | 2862 | NR | 495 | 44177 | NR | 625 | 73091 | NR | 755 | 4147 | NR | 885 | 4128 | NR |
| 370 | 2865 | NR | 500 | 57019 | NR | 630 | 66269 | NR | 760 | 4040 | NR | 890 | 4504 | NR |
| 375 | 3254 | NR | 505 | 70030 | NR | 635 | 60012 | NR | 765 | 3474 | NR | 895 | 4371 | NR |
| 380 | 3076 | NR | 510 | 81972 | NR | 640 | 53914 | NR | 770 | 3469 | NR | 900 | 4082 | NR |
| 385 | 2904 | NR | 515 | 92590 | NR | 645 | 48385 | NR | 775 | 3181 | NR | 905 | 2982 | NR |
| 390 | 2689 | NR | 520 | 100305 | NR | 650 | 43219 | NR | 780 | 2969 | NR | 910 | 4351 | NR |
| 395 | 2619 | NR | 525 | 107452 | NR | 655 | 38562 | NR | 785 | 3132 | NR | 915 | 3365 | NR |
| 400 | 2679 | NR | 530 | 111373 | NR | 660 | 34110 | NR | 790 | 2507 | NR | 920 | 3430 | NR |
| 405 | 3515 | NR | 535 | 114505 | NR | 665 | 30085 | NR | 795 | 2968 | NR | 925 | 4264 | NR |
| 410 | 6934 | NR | 540 | 116408 | NR | 670 | 26205 | NR | 800 | 2758 | NR | 930 | 4095 | NR |
| 415 | 14943 | NR | 545 | 118700 | NR | 675 | 22906 | NR | 805 | 2872 | NR | 935 | 5048 | NR |
| 420 | 31939 | NR | 550 | 119209 | NR | 680 | 20058 | NR | 810 | 3094 | NR | 940 | 4074 | NR |
| 425 | 64701 | NR | 555 | 120742 | NR | 685 | 17413 | NR | 815 | 3222 | NR | 945 | 4949 | NR |
| 430 | 110939 | NR | 560 | 121594 | NR | 690 | 15447 | NR | 820 | 3238 | NR | 950 | 4387 | NR |
| 435 | 164597 | NR | 565 | 121913 | NR | 695 | 13398 | NR | 825 | 3524 | NR | 955 | 4978 | NR |
| 440 | 207696 | NR | 570 | 122147 | NR | 700 | 11777 | NR | 830 | 2921 | NR | 960 | 4706 | NR |
| 445 | 201830 | NR | 575 | 121605 | NR | 705 | 10412 | NR | 835 | 3595 | NR | 965 | 5083 | NR |
| 450 | 145410 | NR | 580 | 120248 | NR | 710 | 9544 | NR | 840 | 3016 | NR | 970 | 4522 | NR |
| 455 | 89594 | NR | 585 | 117717 | NR | 715 | 8940 | NR | 845 | 4032 | NR | 975 | 4740 | NR |
| 460 | 58321 | NR | 590 | 114359 | NR | 720 | 7897 | NR | 850 | 3579 | NR | 980 | 6122 | NR |
| 465 | 39318 | NR | 595 | 109974 | NR | 725 | 7045 | NR | 855 | 4571 | NR | 985 | 6450 | NR |
| 470 | 27693 | NR | 600 | 105269 | NR | 730 | 6483 | NR | 860 | 4485 | NR | 990 | 4875 | NR |
| 475 | 23081 | NR | 605 | 99453 | NR | 735 | 5838 | NR | 865 | 3978 | NR | 995 | 4764 | NR |
| 480 | 23002 | NR | 610 | 92921 | NR | 740 | 5261 | NR | 870 | 4298 | NR | 1000 | 3640 | NR |
| 485 | 26201 | NR | 615 | 86989 | NR | 745 | 4760 | NR | 875 | 4356 | NR | | | |

REPORT NUMBER: SP1-1908-441-9-R4

Scotopic Flux vs. Wavelength




Scotopic Lumens: 13759.3 S/P: 1.85

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 3540 | NR | 490 | 33363 | NR | 620 | 80193 | NR | 750 | 4663 | NR | 880 | 4678 | NR |
| 365 | 2862 | NR | 495 | 44177 | NR | 625 | 73091 | NR | 755 | 4147 | NR | 885 | 4128 | NR |
| 370 | 2865 | NR | 500 | 57019 | NR | 630 | 66269 | NR | 760 | 4040 | NR | 890 | 4504 | NR |
| 375 | 3254 | NR | 505 | 70030 | NR | 635 | 60012 | NR | 765 | 3474 | NR | 895 | 4371 | NR |
| 380 | 3076 | NR | 510 | 81972 | NR | 640 | 53914 | NR | 770 | 3469 | NR | 900 | 4082 | NR |
| 385 | 2904 | NR | 515 | 92590 | NR | 645 | 48385 | NR | 775 | 3181 | NR | 905 | 2982 | NR |
| 390 | 2689 | NR | 520 | 100305 | NR | 650 | 43219 | NR | 780 | 2969 | NR | 910 | 4351 | NR |
| 395 | 2619 | NR | 525 | 107452 | NR | 655 | 38562 | NR | 785 | 3132 | NR | 915 | 3365 | NR |
| 400 | 2679 | NR | 530 | 111373 | NR | 660 | 34110 | NR | 790 | 2507 | NR | 920 | 3430 | NR |
| 405 | 3515 | NR | 535 | 114505 | NR | 665 | 30085 | NR | 795 | 2968 | NR | 925 | 4264 | NR |
| 410 | 6934 | NR | 540 | 116408 | NR | 670 | 26205 | NR | 800 | 2758 | NR | 930 | 4095 | NR |
| 415 | 14943 | NR | 545 | 118700 | NR | 675 | 22906 | NR | 805 | 2872 | NR | 935 | 5048 | NR |
| 420 | 31939 | NR | 550 | 119209 | NR | 680 | 20058 | NR | 810 | 3094 | NR | 940 | 4074 | NR |
| 425 | 64701 | NR | 555 | 120742 | NR | 685 | 17413 | NR | 815 | 3222 | NR | 945 | 4949 | NR |
| 430 | 110939 | NR | 560 | 121594 | NR | 690 | 15447 | NR | 820 | 3238 | NR | 950 | 4387 | NR |
| 435 | 164597 | NR | 565 | 121913 | NR | 695 | 13398 | NR | 825 | 3524 | NR | 955 | 4978 | NR |
| 440 | 207696 | NR | 570 | 122147 | NR | 700 | 11777 | NR | 830 | 2921 | NR | 960 | 4706 | NR |
| 445 | 201830 | NR | 575 | 121605 | NR | 705 | 10412 | NR | 835 | 3595 | NR | 965 | 5083 | NR |
| 450 | 145410 | NR | 580 | 120248 | NR | 710 | 9544 | NR | 840 | 3016 | NR | 970 | 4522 | NR |
| 455 | 89594 | NR | 585 | 117717 | NR | 715 | 8940 | NR | 845 | 4032 | NR | 975 | 4740 | NR |
| 460 | 58321 | NR | 590 | 114359 | NR | 720 | 7897 | NR | 850 | 3579 | NR | 980 | 6122 | NR |
| 465 | 39318 | NR | 595 | 109974 | NR | 725 | 7045 | NR | 855 | 4571 | NR | 985 | 6450 | NR |
| 470 | 27693 | NR | 600 | 105269 | NR | 730 | 6483 | NR | 860 | 4485 | NR | 990 | 4875 | NR |
| 475 | 23081 | NR | 605 | 99453 | NR | 735 | 5838 | NR | 865 | 3978 | NR | 995 | 4764 | NR |
| 480 | 23002 | NR | 610 | 92921 | NR | 740 | 5261 | NR | 870 | 4298 | NR | 1000 | 3640 | NR |
| 485 | 26201 | NR | 615 | 86989 | NR | 745 | 4760 | NR | 875 | 4356 | NR | | | |

REPORT NUMBER: SP1-1908-441-9-R4

Melanopic Flux vs. Wavelength



Melanopic Lumens: 5527.6 M/P: 0.74

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 3540 | NR | 490 | 33363 | NR | 620 | 80193 | NR | 750 | 4663 | NR | 880 | 4678 | NR |
| 365 | 2862 | NR | 495 | 44177 | NR | 625 | 73091 | NR | 755 | 4147 | NR | 885 | 4128 | NR |
| 370 | 2865 | NR | 500 | 57019 | NR | 630 | 66269 | NR | 760 | 4040 | NR | 890 | 4504 | NR |
| 375 | 3254 | NR | 505 | 70030 | NR | 635 | 60012 | NR | 765 | 3474 | NR | 895 | 4371 | NR |
| 380 | 3076 | NR | 510 | 81972 | NR | 640 | 53914 | NR | 770 | 3469 | NR | 900 | 4082 | NR |
| 385 | 2904 | NR | 515 | 92590 | NR | 645 | 48385 | NR | 775 | 3181 | NR | 905 | 2982 | NR |
| 390 | 2689 | NR | 520 | 100305 | NR | 650 | 43219 | NR | 780 | 2969 | NR | 910 | 4351 | NR |
| 395 | 2619 | NR | 525 | 107452 | NR | 655 | 38562 | NR | 785 | 3132 | NR | 915 | 3365 | NR |
| 400 | 2679 | NR | 530 | 111373 | NR | 660 | 34110 | NR | 790 | 2507 | NR | 920 | 3430 | NR |
| 405 | 3515 | NR | 535 | 114505 | NR | 665 | 30085 | NR | 795 | 2968 | NR | 925 | 4264 | NR |
| 410 | 6934 | NR | 540 | 116408 | NR | 670 | 26205 | NR | 800 | 2758 | NR | 930 | 4095 | NR |
| 415 | 14943 | NR | 545 | 118700 | NR | 675 | 22906 | NR | 805 | 2872 | NR | 935 | 5048 | NR |
| 420 | 31939 | NR | 550 | 119209 | NR | 680 | 20058 | NR | 810 | 3094 | NR | 940 | 4074 | NR |
| 425 | 64701 | NR | 555 | 120742 | NR | 685 | 17413 | NR | 815 | 3222 | NR | 945 | 4949 | NR |
| 430 | 110939 | NR | 560 | 121594 | NR | 690 | 15447 | NR | 820 | 3238 | NR | 950 | 4387 | NR |
| 435 | 164597 | NR | 565 | 121913 | NR | 695 | 13398 | NR | 825 | 3524 | NR | 955 | 4978 | NR |
| 440 | 207696 | NR | 570 | 122147 | NR | 700 | 11777 | NR | 830 | 2921 | NR | 960 | 4706 | NR |
| 445 | 201830 | NR | 575 | 121605 | NR | 705 | 10412 | NR | 835 | 3595 | NR | 965 | 5083 | NR |
| 450 | 145410 | NR | 580 | 120248 | NR | 710 | 9544 | NR | 840 | 3016 | NR | 970 | 4522 | NR |
| 455 | 89594 | NR | 585 | 117717 | NR | 715 | 8940 | NR | 845 | 4032 | NR | 975 | 4740 | NR |
| 460 | 58321 | NR | 590 | 114359 | NR | 720 | 7897 | NR | 850 | 3579 | NR | 980 | 6122 | NR |
| 465 | 39318 | NR | 595 | 109974 | NR | 725 | 7045 | NR | 855 | 4571 | NR | 985 | 6450 | NR |
| 470 | 27693 | NR | 600 | 105269 | NR | 730 | 6483 | NR | 860 | 4485 | NR | 990 | 4875 | NR |
| 475 | 23081 | NR | 605 | 99453 | NR | 735 | 5838 | NR | 865 | 3978 | NR | 995 | 4764 | NR |
| 480 | 23002 | NR | 610 | 92921 | NR | 740 | 5261 | NR | 870 | 4298 | NR | 1000 | 3640 | NR |
| 485 | 26201 | NR | 615 | 86989 | NR | 745 | 4760 | NR | 875 | 4356 | NR | | | |

REPORT NUMBER: SP1-1908-441-9-R4


TM-30-18

Summary

$R_f = 72.1$
 $R_g = 97.2$
 CIE $R_a = 71.7$
 $R_g = -27.1$



Color Vector Graphics



REPORT NUMBER: SP1-1908-441-9-R4

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)

| | | | |
|------------|------------|------------|------------|
| CES01 = 85 | CES26 = 54 | CES51 = 88 | CES76 = 43 |
| CES02 = 59 | CES27 = 79 | CES52 = 90 | CES77 = 64 |
| CES03 = 30 | CES28 = 77 | CES53 = 77 | CES78 = 46 |
| CES04 = 69 | CES29 = 50 | CES54 = 81 | CES79 = 74 |
| CES05 = 46 | CES30 = 59 | CES55 = 80 | CES80 = 70 |
| CES06 = 50 | CES31 = 55 | CES56 = 70 | CES81 = 71 |
| CES07 = 38 | CES32 = 52 | CES57 = 68 | CES82 = 88 |
| CES08 = 38 | CES33 = 63 | CES58 = 70 | CES83 = 82 |
| CES09 = 29 | CES34 = 63 | CES59 = 88 | CES84 = 87 |
| CES10 = 72 | CES35 = 79 | CES60 = 92 | CES85 = 84 |
| CES11 = 55 | CES36 = 90 | CES61 = 88 | CES86 = 76 |
| CES12 = 61 | CES37 = 72 | CES62 = 81 | CES87 = 75 |
| CES13 = 41 | CES38 = 68 | CES63 = 75 | CES88 = 77 |
| CES14 = 74 | CES39 = 91 | CES64 = 72 | CES89 = 76 |
| CES15 = 70 | CES40 = 83 | CES65 = 65 | CES90 = 76 |
| CES16 = 46 | CES41 = 84 | CES66 = 66 | CES91 = 92 |
| CES17 = 48 | CES42 = 70 | CES67 = 64 | CES92 = 70 |
| CES18 = 55 | CES43 = 69 | CES68 = 71 | CES93 = 83 |
| CES19 = 70 | CES44 = 98 | CES69 = 80 | CES94 = 60 |
| CES20 = 64 | CES45 = 79 | CES70 = 58 | CES95 = 73 |
| CES21 = 85 | CES46 = 78 | CES71 = 55 | CES96 = 79 |
| CES22 = 77 | CES47 = 76 | CES72 = 84 | CES97 = 84 |
| CES23 = 91 | CES48 = 68 | CES73 = 47 | CES98 = 73 |
| CES24 = 90 | CES49 = 78 | CES74 = 94 | CES99 = 62 |
| CES25 = 71 | CES50 = 87 | CES75 = 51 | |



REPORT NUMBER: SP1-1908-441-9-R4

TM-30-18

Color Rendition by Hue-Angle Bin



REPORT NUMBER: SP1-1908-441-9-R4

TM-30-18

Measure Comparisons



(END OF REPORT)