

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: McGRAW-EDISON

Report Number: P635897

Luminaire Tested: GWS-SA3E-760-U-SLL-W

Issue Date: 1/10/2023

Test Information

Test Method: LM-79-2019
Report Number: P635897
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2209-782-37)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/10/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: McGRAW-EDISON
Catalog Number: GWS-SA3E-760-U-SLL-W
Description: GALLEON WALL SLIM LUMINAIRE. (3) LIGHTSQUARES WITH 16 LEDS EACH AND SPILL LIGHT ELIMINATOR LEFT OPTICS
Light Source: (48) 5700K CCT, 70 CRI LEDS
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 20794.7 lumens
Efficiency: N/A
Efficacy: 130.6 lumens/watt
Luminous Opening: Rectangular (W 1.5' x L: 0.5' x H: 0')
IES Classification: Type III - Short
BUG Rating: B3 - U0 - G3


Input Watts (W): 159.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 0
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT



REPORT NUMBER: P635897
 CATALOG NUMBER: GWS-SA3E-760-U-SLL-W

Iso-Footcandle Lines of Horizontal Illumination


× Max cd
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 5.5 fc
 Type III - Short - N/A

REPORT NUMBER: P635897
CATALOG NUMBER: GWS-SA3E-760-U-SLL-W

Luminous Intensity Polar Plot



— Vertical Plane Through 315-Deg Lateral - - - Horizontal Cone Through 62.5-Deg Vertical

REPORT NUMBER: P635897

CATALOG NUMBER: GWS-SA3E-760-U-SLL-W

FLUX DISTRIBUTION:

| | | Downward | Upward | Total |
|--------------------|-----------|----------|--------|---------|
| House Side | Lumens | 4972.0 | 0.0 | 4972.0 |
| | % Fixture | 23.9 | 0.0 | 23.9 |
| Street Side | Lumens | 15822.7 | 0.0 | 15822.7 |
| | % Fixture | 76.1 | 0.0 | 76.1 |
| Total | Lumens | 20794.7 | 0.0 | 20794.7 |
| | % Fixture | 100.0 | 0.0 | 100.0 |

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|---------|-----------|
| 0°-10° | 255.4 | 1.2 |
| 10°-20° | 830.1 | 4.0 |
| 20°-30° | 1306.8 | 6.3 |
| 30°-40° | 1791.2 | 8.6 |
| 40°-50° | 2794.8 | 13.4 |
| 50°-60° | 4818.8 | 23.2 |
| 60°-70° | 5584.3 | 26.9 |
| 70°-80° | 2947.7 | 14.2 |
| 80°-90° | 465.6 | 2.2 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-90° | 20794.7 | 100.0 |
| 0°-180° | 20794.7 | 100.0 |

Coefficient of Utilization



REPORT NUMBER: P635897


CATALOG NUMBER: GWS-SA3E-760-U-SLL-W

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

| Zone | Lumens | % Fixture | Zone Rating/Lumen Limit | | |
|----------------|--------|-----------|-------------------------|------|---------|
| | | | B | U | G |
| FL (0°-30°) | 1375.3 | 6.6 | | | |
| FM (30°-60°) | 6865.1 | 33.0 | | | |
| FH (60°-80°) | 7222.9 | 34.7 | | | G3/7500 |
| FVH (80°-90°) | 359.4 | 1.7 | | | G3/500 |
| BL (0°-30°) | 1017.0 | 4.9 | B3/2500 | | |
| BM (30°-60°) | 2539.7 | 12.2 | B3/5000 | | |
| BH (60°-80°) | 1309.2 | 6.3 | B3/2500 | | G3/2500 |
| BVH (80°-90°) | 106.2 | 0.5 | | | G2/225 |
| UL (90°-100°) | 0.0 | 0.0 | | U0/0 | |
| UH (100°-180°) | 0.0 | 0.0 | | U0/0 | |

BUG Rating: B3-U0-G3

Type III Short





REPORT NUMBER: P635897
 CATALOG NUMBER: GWS-SA3E-760-U-SLL-W

CANDELA DISTRIBUTION (FULL):

| | 0° | 2° | 5° | 15° | 25° | 35° | 45° | 55° | 65° | 75° | 85° |
|-------|---------|---------|---------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 2592.7 | 2592.7 | 2592.7 | 2592.7 | 2592.7 | 2592.7 | 2592.7 | 2592.7 | 2592.7 | 2592.7 | 2592.7 |
| 2.5° | 2816.9 | 2805.8 | 2789.9 | 2735.8 | 2702.4 | 2664.2 | 2624.5 | 2578.4 | 2525.9 | 2489.3 | 2452.7 |
| 5° | 3055.5 | 3038.0 | 2999.9 | 2871.0 | 2781.9 | 2684.9 | 2603.8 | 2511.5 | 2420.9 | 2358.9 | 2296.8 |
| 7.5° | 3284.6 | 3262.3 | 3203.5 | 3006.2 | 2861.5 | 2721.5 | 2599.0 | 2465.4 | 2330.2 | 2238.0 | 2164.8 |
| 10° | 3513.6 | 3467.5 | 3392.7 | 3135.1 | 2944.2 | 2781.9 | 2642.0 | 2478.1 | 2298.4 | 2172.8 | 2094.8 |
| 12.5° | 3688.6 | 3645.6 | 3564.5 | 3252.8 | 3026.9 | 2823.3 | 2665.8 | 2514.7 | 2362.0 | 2228.4 | 2148.9 |
| 15° | 3852.4 | 3796.7 | 3704.5 | 3362.5 | 3095.3 | 2821.7 | 2618.1 | 2486.1 | 2463.8 | 2430.4 | 2327.0 |
| 17.5° | 3970.1 | 3919.2 | 3823.8 | 3451.6 | 3133.5 | 2772.4 | 2486.1 | 2408.2 | 2508.4 | 2610.2 | 2511.5 |
| 20° | 4073.5 | 4014.7 | 3917.6 | 3513.6 | 3141.4 | 2662.7 | 2325.4 | 2327.0 | 2484.5 | 2624.5 | 2600.6 |
| 22.5° | 4161.0 | 4095.8 | 4009.9 | 3583.6 | 3138.2 | 2510.0 | 2185.5 | 2280.9 | 2438.4 | 2548.1 | 2551.3 |
| 25° | 4269.2 | 4215.1 | 4143.5 | 3687.0 | 3138.2 | 2354.1 | 2083.7 | 2225.2 | 2360.4 | 2452.7 | 2449.5 |
| 27.5° | 4401.2 | 4364.6 | 4305.7 | 3844.5 | 3166.9 | 2223.7 | 2026.4 | 2153.7 | 2260.2 | 2339.8 | 2338.2 |
| 30° | 4549.1 | 4515.7 | 4471.2 | 4011.5 | 3216.2 | 2126.6 | 1994.6 | 2064.6 | 2142.5 | 2206.2 | 2206.2 |
| 32.5° | 4700.2 | 4687.5 | 4639.8 | 4145.1 | 3178.0 | 2096.4 | 1967.6 | 1975.5 | 2016.9 | 2069.4 | 2064.6 |
| 35° | 4910.2 | 4897.4 | 4837.0 | 4248.5 | 3012.6 | 2053.5 | 1924.6 | 1884.9 | 1889.6 | 1923.0 | 1934.2 |
| 37.5° | 5217.1 | 5198.1 | 5109.0 | 4369.4 | 2762.9 | 1945.3 | 1854.6 | 1789.4 | 1775.1 | 1789.4 | 1810.1 |
| 40° | 5587.8 | 5559.1 | 5438.2 | 4533.2 | 2475.0 | 1799.0 | 1744.9 | 1690.8 | 1666.9 | 1671.7 | 1695.6 |
| 42.5° | 6052.2 | 5991.8 | 5818.4 | 4706.6 | 2190.2 | 1670.1 | 1622.4 | 1589.0 | 1562.0 | 1558.8 | 1604.9 |
| 45° | 6806.2 | 6640.7 | 6365.6 | 4860.9 | 1950.1 | 1601.7 | 1512.7 | 1488.8 | 1466.5 | 1479.3 | 1533.3 |
| 47.5° | 8123.2 | 7817.8 | 7281.7 | 4992.9 | 1803.7 | 1603.3 | 1425.2 | 1399.7 | 1398.1 | 1423.6 | 1484.0 |
| 50° | 9933.3 | 9492.7 | 8665.6 | 5081.9 | 1727.4 | 1622.4 | 1372.7 | 1331.3 | 1361.5 | 1387.0 | 1444.3 |
| 52.5° | 11667.0 | 10994.2 | 10009.6 | 5080.4 | 1694.0 | 1625.6 | 1387.0 | 1267.7 | 1361.5 | 1367.9 | 1422.0 |
| 55° | 13147.9 | 11929.5 | 10372.3 | 4558.6 | 1646.3 | 1612.9 | 1442.7 | 1218.4 | 1344.1 | 1367.9 | 1410.9 |
| 57.5° | 14324.9 | 12524.3 | 10345.2 | 3682.2 | 1791.0 | 1542.9 | 1476.1 | 1207.3 | 1293.2 | 1371.1 | 1420.4 |
| 60° | 14194.5 | 12252.3 | 9678.8 | 2260.2 | 1776.7 | 1418.8 | 1471.3 | 1227.9 | 1207.3 | 1328.1 | 1409.3 |
| 62.5° | 13327.6 | 11277.3 | 8531.9 | 1568.3 | 1668.5 | 1347.2 | 1393.4 | 1264.5 | 1127.7 | 1266.1 | 1355.2 |
| 65° | 12114.0 | 10019.2 | 7110.0 | 1202.5 | 1382.2 | 1350.4 | 1261.3 | 1239.1 | 1057.7 | 1167.5 | 1262.9 |
| 67.5° | 10509.1 | 8458.8 | 5613.2 | 952.8 | 963.9 | 1169.1 | 1145.2 | 1100.7 | 992.5 | 1080.0 | 1165.9 |
| 70° | 7900.5 | 6173.1 | 3862.0 | 766.7 | 730.1 | 976.6 | 1029.1 | 989.3 | 928.9 | 954.4 | 1045.0 |
| 72.5° | 5567.1 | 4030.6 | 2115.5 | 607.6 | 563.1 | 750.8 | 893.9 | 887.6 | 820.7 | 839.8 | 928.9 |
| 75° | 4137.1 | 2851.9 | 1321.8 | 480.4 | 458.1 | 537.6 | 749.2 | 768.3 | 712.6 | 734.9 | 803.3 |
| 77.5° | 2753.3 | 1846.7 | 734.9 | 356.3 | 356.3 | 392.9 | 558.3 | 647.4 | 606.0 | 623.5 | 671.2 |
| 80° | 1519.0 | 940.0 | 367.4 | 233.8 | 240.2 | 270.4 | 407.2 | 466.0 | 467.6 | 510.6 | 523.3 |
| 82.5° | 480.4 | 299.0 | 163.8 | 136.8 | 128.8 | 154.3 | 262.4 | 334.0 | 311.8 | 397.6 | 365.8 |
| 85° | 109.8 | 70.0 | 30.2 | 30.2 | 33.4 | 50.9 | 100.2 | 178.1 | 227.5 | 273.6 | 198.8 |
| 87.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 1.6 | 70.0 | 103.4 | 92.3 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P635897
 CATALOG NUMBER: GWS-SA3E-760-U-SLL-W

CANDELA DISTRIBUTION (continued):

| | 90° | 95° | 105° | 115° | 125° | 135° | 145° | 155° | 165° | 175° | 180° |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 2592.7 | 2592.7 | 2592.7 | 2592.7 | 2592.7 | 2592.7 | 2592.7 | 2592.7 | 2592.7 | 2592.7 | 2592.7 |
| 2.5° | 2430.4 | 2398.6 | 2389.1 | 2362.0 | 2358.9 | 2333.4 | 2323.9 | 2323.9 | 2335.0 | 2335.0 | 2346.1 |
| 5° | 2271.4 | 2231.6 | 2209.3 | 2177.5 | 2169.6 | 2150.5 | 2137.8 | 2139.3 | 2153.7 | 2163.2 | 2182.3 |
| 7.5° | 2131.4 | 2104.4 | 2088.5 | 2074.1 | 2071.0 | 2067.8 | 2053.5 | 2051.9 | 2056.6 | 2071.0 | 2085.3 |
| 10° | 2072.5 | 2053.5 | 2058.2 | 2069.4 | 2086.9 | 2096.4 | 2083.7 | 2077.3 | 2072.5 | 2082.1 | 2094.8 |
| 12.5° | 2129.8 | 2110.7 | 2120.3 | 2139.3 | 2163.2 | 2172.8 | 2168.0 | 2166.4 | 2171.2 | 2207.7 | 2234.8 |
| 15° | 2255.5 | 2218.9 | 2206.2 | 2214.1 | 2233.2 | 2242.7 | 2238.0 | 2244.3 | 2274.5 | 2370.0 | 2438.4 |
| 17.5° | 2411.3 | 2322.3 | 2271.4 | 2257.1 | 2265.0 | 2273.0 | 2273.0 | 2288.9 | 2341.4 | 2481.3 | 2567.2 |
| 20° | 2495.6 | 2379.5 | 2293.6 | 2258.6 | 2261.8 | 2269.8 | 2269.8 | 2292.0 | 2350.9 | 2500.4 | 2556.1 |
| 22.5° | 2473.4 | 2366.8 | 2261.8 | 2223.7 | 2225.2 | 2231.6 | 2231.6 | 2250.7 | 2303.2 | 2435.2 | 2460.6 |
| 25° | 2385.9 | 2292.0 | 2188.7 | 2155.3 | 2158.4 | 2169.6 | 2166.4 | 2177.5 | 2217.3 | 2325.4 | 2339.8 |
| 27.5° | 2280.9 | 2198.2 | 2096.4 | 2071.0 | 2085.3 | 2107.5 | 2088.5 | 2090.0 | 2126.6 | 2217.3 | 2218.9 |
| 30° | 2168.0 | 2099.6 | 2008.9 | 1989.8 | 2016.9 | 2028.0 | 2010.5 | 2010.5 | 2047.1 | 2109.1 | 2107.5 |
| 32.5° | 2045.5 | 2002.6 | 1937.3 | 1916.7 | 1946.9 | 1964.4 | 1942.1 | 1945.3 | 1973.9 | 2015.3 | 1999.4 |
| 35° | 1931.0 | 1908.7 | 1878.5 | 1864.2 | 1883.3 | 1899.2 | 1884.9 | 1891.2 | 1918.3 | 1929.4 | 1907.1 |
| 37.5° | 1821.2 | 1818.0 | 1821.2 | 1821.2 | 1826.0 | 1830.8 | 1821.2 | 1837.1 | 1861.0 | 1846.7 | 1821.2 |
| 40° | 1725.8 | 1738.5 | 1768.7 | 1760.8 | 1756.0 | 1760.8 | 1754.4 | 1781.5 | 1805.3 | 1779.9 | 1749.7 |
| 42.5° | 1646.3 | 1670.1 | 1716.3 | 1716.3 | 1706.7 | 1709.9 | 1706.7 | 1740.1 | 1757.6 | 1722.6 | 1689.2 |
| 45° | 1577.9 | 1612.9 | 1671.7 | 1679.7 | 1663.8 | 1663.8 | 1670.1 | 1711.5 | 1717.8 | 1670.1 | 1635.1 |
| 47.5° | 1530.2 | 1573.1 | 1639.9 | 1654.2 | 1630.4 | 1628.8 | 1646.3 | 1690.8 | 1690.8 | 1635.1 | 1595.4 |
| 50° | 1496.7 | 1544.5 | 1624.0 | 1643.1 | 1619.2 | 1612.9 | 1641.5 | 1684.4 | 1674.9 | 1608.1 | 1568.3 |
| 52.5° | 1474.5 | 1523.8 | 1622.4 | 1649.4 | 1633.5 | 1627.2 | 1655.8 | 1686.0 | 1662.2 | 1590.6 | 1549.2 |
| 55° | 1460.2 | 1514.2 | 1627.2 | 1649.4 | 1631.9 | 1620.8 | 1649.4 | 1676.5 | 1663.8 | 1581.1 | 1541.3 |
| 57.5° | 1468.1 | 1522.2 | 1620.8 | 1631.9 | 1611.3 | 1592.2 | 1625.6 | 1663.8 | 1659.0 | 1584.2 | 1544.5 |
| 60° | 1455.4 | 1504.7 | 1585.8 | 1589.0 | 1554.0 | 1523.8 | 1573.1 | 1630.4 | 1630.4 | 1573.1 | 1538.1 |
| 62.5° | 1396.5 | 1445.9 | 1517.4 | 1520.6 | 1480.8 | 1447.4 | 1504.7 | 1573.1 | 1571.5 | 1525.4 | 1488.8 |
| 65° | 1299.5 | 1345.6 | 1426.8 | 1434.7 | 1395.0 | 1360.0 | 1418.8 | 1482.4 | 1487.2 | 1445.9 | 1414.0 |
| 67.5° | 1192.9 | 1234.3 | 1294.7 | 1326.6 | 1293.2 | 1256.6 | 1310.6 | 1371.1 | 1369.5 | 1320.2 | 1286.8 |
| 70° | 1065.7 | 1103.9 | 1159.5 | 1186.6 | 1165.9 | 1130.9 | 1180.2 | 1212.0 | 1197.7 | 1173.9 | 1151.6 |
| 72.5° | 940.0 | 976.6 | 1029.1 | 1029.1 | 1006.8 | 973.4 | 987.8 | 1045.0 | 1062.5 | 1045.0 | 1030.7 |
| 75° | 808.0 | 839.8 | 876.4 | 884.4 | 835.1 | 774.6 | 841.4 | 890.7 | 911.4 | 903.5 | 886.0 |
| 77.5° | 672.8 | 696.7 | 750.8 | 736.4 | 644.2 | 612.4 | 666.5 | 739.6 | 753.9 | 749.2 | 725.3 |
| 80° | 518.5 | 532.8 | 590.1 | 561.5 | 489.9 | 469.2 | 493.1 | 550.3 | 553.5 | 537.6 | 507.4 |
| 82.5° | 348.3 | 367.4 | 405.6 | 349.9 | 348.3 | 329.3 | 310.2 | 316.5 | 345.2 | 342.0 | 321.3 |
| 85° | 178.1 | 187.7 | 224.3 | 210.0 | 179.7 | 155.9 | 147.9 | 157.5 | 141.6 | 128.8 | 111.3 |
| 87.5° | 74.8 | 81.1 | 111.3 | 62.0 | 19.1 | 0.0 | 0.0 | 9.5 | 14.3 | 20.7 | 22.3 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P635897
 CATALOG NUMBER: GWS-SA3E-760-U-SLL-W

CANDELA DISTRIBUTION (continued):

| | 185° | 195° | 205° | 215° | 225° | 235° | 245° | 255° | 265° | 270° | 275° |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|---------|---------|---------|
| 0° | 2592.7 | 2592.7 | 2592.7 | 2592.7 | 2592.7 | 2592.7 | 2592.7 | 2592.7 | 2592.7 | 2592.7 | 2592.7 |
| 2.5° | 2371.6 | 2389.1 | 2432.0 | 2486.1 | 2538.6 | 2592.7 | 2651.5 | 2688.1 | 2732.6 | 2789.9 | 2791.5 |
| 5° | 2206.2 | 2245.9 | 2308.0 | 2390.7 | 2476.6 | 2575.2 | 2689.7 | 2785.1 | 2899.7 | 2990.3 | 3026.9 |
| 7.5° | 2104.4 | 2161.6 | 2239.6 | 2344.5 | 2457.5 | 2579.9 | 2729.5 | 2890.1 | 3077.8 | 3198.7 | 3270.3 |
| 10° | 2113.9 | 2201.4 | 2279.3 | 2368.4 | 2470.2 | 2602.2 | 2794.7 | 3007.8 | 3238.4 | 3397.5 | 3486.6 |
| 12.5° | 2284.1 | 2376.3 | 2362.0 | 2357.3 | 2425.7 | 2586.3 | 2847.2 | 3127.1 | 3408.6 | 3567.7 | 3674.3 |
| 15° | 2498.8 | 2533.8 | 2398.6 | 2296.8 | 2338.2 | 2529.0 | 2875.8 | 3233.7 | 3550.2 | 3744.3 | 3849.2 |
| 17.5° | 2608.6 | 2538.6 | 2374.8 | 2222.1 | 2210.9 | 2441.6 | 2890.1 | 3341.8 | 3709.3 | 3903.3 | 4014.7 |
| 20° | 2557.7 | 2455.9 | 2317.5 | 2172.8 | 2093.2 | 2322.3 | 2882.2 | 3427.7 | 3854.0 | 4070.3 | 4161.0 |
| 22.5° | 2447.9 | 2358.9 | 2250.7 | 2112.3 | 1997.8 | 2191.8 | 2861.5 | 3513.6 | 3982.8 | 4200.8 | 4280.3 |
| 25° | 2328.6 | 2261.8 | 2172.8 | 2051.9 | 1943.7 | 2077.3 | 2847.2 | 3628.1 | 4130.8 | 4339.1 | 4390.0 |
| 27.5° | 2209.3 | 2160.0 | 2086.9 | 1993.0 | 1931.0 | 1997.8 | 2851.9 | 3777.7 | 4321.6 | 4518.9 | 4498.2 |
| 30° | 2091.6 | 2048.7 | 1997.8 | 1956.4 | 1929.4 | 1978.7 | 2839.2 | 3936.7 | 4531.6 | 4714.5 | 4592.0 |
| 32.5° | 1980.3 | 1940.5 | 1908.7 | 1915.1 | 1931.0 | 1986.7 | 2774.0 | 4081.5 | 4724.1 | 4879.9 | 4693.8 |
| 35° | 1884.9 | 1843.5 | 1843.5 | 1865.8 | 1924.6 | 1959.6 | 2605.4 | 4194.4 | 4937.2 | 5093.1 | 4838.6 |
| 37.5° | 1795.8 | 1759.2 | 1783.1 | 1819.6 | 1875.3 | 1886.4 | 2389.1 | 4304.1 | 5247.4 | 5393.7 | 5062.9 |
| 40° | 1717.8 | 1681.3 | 1724.2 | 1770.3 | 1799.0 | 1794.2 | 2169.6 | 4456.8 | 5613.2 | 5764.3 | 5360.3 |
| 42.5° | 1655.8 | 1622.4 | 1660.6 | 1719.4 | 1724.2 | 1729.0 | 2008.9 | 4603.2 | 6037.9 | 6230.4 | 5872.5 |
| 45° | 1604.9 | 1581.1 | 1600.1 | 1659.0 | 1659.0 | 1732.2 | 1908.7 | 4725.7 | 6677.3 | 7017.7 | 6812.5 |
| 47.5° | 1565.1 | 1550.8 | 1560.4 | 1579.5 | 1611.3 | 1789.4 | 1845.1 | 4819.5 | 7841.6 | 8509.7 | 8302.9 |
| 50° | 1542.9 | 1528.6 | 1541.3 | 1501.5 | 1597.0 | 1818.0 | 1824.4 | 4891.1 | 9376.6 | 10423.2 | 10167.1 |
| 52.5° | 1523.8 | 1519.0 | 1527.0 | 1434.7 | 1628.8 | 1799.0 | 1808.5 | 4795.6 | 10405.7 | 12306.4 | 12559.3 |
| 55° | 1517.4 | 1520.6 | 1482.4 | 1385.4 | 1666.9 | 1735.3 | 1760.8 | 4113.3 | 10685.6 | 13930.4 | 15500.3 |
| 57.5° | 1520.6 | 1511.1 | 1414.0 | 1390.2 | 1668.5 | 1608.1 | 1829.2 | 2934.6 | 10278.4 | 14636.6 | 18377.7 |
| 60° | 1509.5 | 1461.8 | 1331.3 | 1433.1 | 1595.4 | 1458.6 | 1779.9 | 1913.5 | 9204.8 | 14094.3 | 18544.7 |
| 62.5° | 1460.2 | 1390.2 | 1259.8 | 1457.0 | 1464.9 | 1369.5 | 1616.0 | 1474.5 | 7773.2 | 12933.1 | 16935.1 |
| 65° | 1388.6 | 1294.7 | 1199.3 | 1407.7 | 1332.9 | 1328.1 | 1215.2 | 1181.8 | 6251.0 | 11550.9 | 15408.1 |
| 67.5° | 1270.9 | 1177.0 | 1154.8 | 1294.7 | 1199.3 | 1177.0 | 976.6 | 979.8 | 4988.1 | 10078.0 | 13873.2 |
| 70° | 1137.3 | 1043.4 | 1060.9 | 1170.7 | 1067.3 | 978.2 | 790.5 | 816.0 | 3784.0 | 8396.7 | 11803.8 |
| 72.5° | 1049.8 | 924.1 | 925.7 | 1030.7 | 938.5 | 792.1 | 650.6 | 672.8 | 2401.8 | 6329.0 | 9384.5 |
| 75° | 886.0 | 814.4 | 779.4 | 835.1 | 796.9 | 617.2 | 547.2 | 542.4 | 1423.6 | 4536.4 | 7027.2 |
| 77.5° | 739.6 | 684.0 | 666.5 | 688.7 | 594.9 | 456.5 | 440.6 | 432.6 | 806.4 | 2906.0 | 4604.8 |
| 80° | 536.0 | 521.7 | 520.1 | 531.3 | 458.1 | 335.6 | 335.6 | 337.2 | 434.2 | 1577.9 | 2595.8 |
| 82.5° | 340.4 | 372.2 | 329.3 | 365.8 | 311.8 | 238.6 | 222.7 | 252.9 | 249.7 | 672.8 | 1094.3 |
| 85° | 141.6 | 194.1 | 181.3 | 192.5 | 147.9 | 130.4 | 140.0 | 151.1 | 144.7 | 259.3 | 426.3 |
| 87.5° | 27.0 | 31.8 | 35.0 | 33.4 | 33.4 | 41.4 | 46.1 | 55.7 | 55.7 | 74.8 | 128.8 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P635897
 CATALOG NUMBER: GWS-SA3E-760-U-SLL-W

CANDELA DISTRIBUTION (continued):

| | 285° | 295° | 305° | 315° | 325° | 335° | 345° | 355° | 358° | 360° |
|-------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|
| 0° | 2592.7 | 2592.7 | 2592.7 | 2592.7 | 2592.7 | 2592.7 | 2592.7 | 2592.7 | 2592.7 | 2592.7 |
| 2.5° | 2851.9 | 2898.1 | 2888.5 | 2909.2 | 2882.2 | 2891.7 | 2837.6 | 2823.3 | 2813.8 | 2816.9 |
| 5° | 3144.6 | 3238.4 | 3255.9 | 3290.9 | 3267.1 | 3267.1 | 3171.6 | 3100.1 | 3074.6 | 3055.5 |
| 7.5° | 3442.0 | 3577.2 | 3666.3 | 3675.9 | 3663.1 | 3637.7 | 3499.3 | 3370.5 | 3324.3 | 3284.6 |
| 10° | 3706.1 | 3868.3 | 3968.5 | 4016.3 | 3992.4 | 3952.6 | 3780.8 | 3604.3 | 3548.6 | 3513.6 |
| 12.5° | 3908.1 | 4051.2 | 4118.0 | 4149.9 | 4146.7 | 4132.4 | 3992.4 | 3801.5 | 3742.7 | 3688.6 |
| 15° | 4038.5 | 4110.1 | 4084.6 | 4083.1 | 4105.3 | 4162.6 | 4119.6 | 3970.1 | 3901.7 | 3852.4 |
| 17.5° | 4122.8 | 4054.4 | 3941.5 | 3889.0 | 3936.7 | 4071.9 | 4170.5 | 4086.2 | 4024.2 | 3970.1 |
| 20° | 4153.0 | 3909.7 | 3745.8 | 3648.8 | 3704.5 | 3900.1 | 4143.5 | 4170.5 | 4118.0 | 4073.5 |
| 22.5° | 4118.0 | 3733.1 | 3510.4 | 3395.9 | 3450.0 | 3683.8 | 4064.0 | 4238.9 | 4203.9 | 4161.0 |
| 25° | 4032.2 | 3548.6 | 3281.4 | 3178.0 | 3236.9 | 3475.4 | 3922.4 | 4302.6 | 4304.1 | 4269.2 |
| 27.5° | 3925.6 | 3378.4 | 3120.7 | 3023.7 | 3081.0 | 3303.7 | 3784.0 | 4358.2 | 4413.9 | 4401.2 |
| 30° | 3817.4 | 3276.6 | 3044.4 | 2976.0 | 3018.9 | 3216.2 | 3642.5 | 4415.5 | 4526.8 | 4549.1 |
| 32.5° | 3768.1 | 3325.9 | 3224.1 | 3254.4 | 3198.7 | 3267.1 | 3591.6 | 4496.6 | 4663.6 | 4700.2 |
| 35° | 3833.3 | 3763.3 | 4021.0 | 4140.3 | 3943.1 | 3683.8 | 3656.8 | 4619.1 | 4856.1 | 4910.2 |
| 37.5° | 4149.9 | 4700.2 | 5085.1 | 5505.0 | 5163.1 | 4592.0 | 3979.7 | 4827.5 | 5131.3 | 5217.1 |
| 40° | 4838.6 | 5517.8 | 6212.9 | 6755.3 | 6238.3 | 5470.1 | 4593.6 | 5137.6 | 5509.8 | 5587.8 |
| 42.5° | 5487.5 | 6284.4 | 7242.0 | 7943.4 | 7272.2 | 6187.4 | 5255.3 | 5659.3 | 6009.3 | 6052.2 |
| 45° | 6123.8 | 7036.8 | 8487.4 | 9462.4 | 8551.0 | 6869.8 | 5931.3 | 6540.5 | 6804.6 | 6806.2 |
| 47.5° | 6869.8 | 7884.6 | 10049.4 | 11438.0 | 10248.2 | 7625.3 | 6566.0 | 7935.5 | 8302.9 | 8123.2 |
| 50° | 7762.1 | 8727.6 | 11657.5 | 13736.4 | 12317.6 | 8554.2 | 7372.4 | 9635.8 | 10136.9 | 9933.3 |
| 52.5° | 8956.6 | 9656.5 | 13429.4 | 15977.5 | 14573.0 | 9612.0 | 8541.5 | 11881.7 | 12047.2 | 11667.0 |
| 55° | 10637.9 | 10997.4 | 15703.9 | 18745.2 | 17090.9 | 10914.7 | 10251.4 | 14700.3 | 14237.4 | 13147.9 |
| 57.5° | 14466.5 | 13119.2 | 18624.3 | 21902.5 | 19939.7 | 13281.5 | 13998.8 | 17808.3 | 16162.0 | 14324.9 |
| 60° | 17669.9 | 15696.0 | 21326.7 | 25036.0 | 22381.3 | 15890.0 | 17517.2 | 18349.1 | 16090.5 | 14194.5 |
| 62.5° | 16589.9 | 16352.9 | 22301.7 | 25381.1 | 23214.7 | 17173.6 | 16863.5 | 16986.0 | 15040.7 | 13327.6 |
| 65° | 14555.5 | 15085.2 | 21431.7 | 23744.4 | 22290.6 | 16023.6 | 15253.8 | 15726.2 | 13839.8 | 12114.0 |
| 67.5° | 13354.6 | 13744.3 | 19884.0 | 21124.7 | 20610.9 | 14779.8 | 14002.0 | 13660.0 | 11975.6 | 10509.1 |
| 70° | 12126.7 | 12449.6 | 17711.3 | 17836.9 | 17991.2 | 12712.0 | 11449.1 | 10431.1 | 8926.4 | 7900.5 |
| 72.5° | 10478.8 | 10496.3 | 14964.3 | 14235.8 | 14528.5 | 9947.6 | 9215.9 | 7798.7 | 6497.6 | 5567.1 |
| 75° | 8791.2 | 8310.9 | 11845.2 | 9950.8 | 10537.7 | 7738.2 | 7652.3 | 5877.2 | 4900.6 | 4137.1 |
| 77.5° | 6702.8 | 6141.3 | 8652.8 | 6543.7 | 7401.0 | 5153.5 | 5753.2 | 3986.0 | 3448.4 | 2753.3 |
| 80° | 4499.8 | 4149.9 | 4781.3 | 3693.4 | 4841.8 | 3551.8 | 3752.2 | 2258.6 | 1958.0 | 1519.0 |
| 82.5° | 2373.2 | 2026.4 | 2955.3 | 2190.2 | 2920.3 | 1951.7 | 1407.7 | 698.3 | 594.9 | 480.4 |
| 85° | 919.4 | 1064.1 | 1449.0 | 779.4 | 1132.5 | 696.7 | 407.2 | 173.4 | 144.7 | 109.8 |
| 87.5° | 178.1 | 275.2 | 151.1 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



LM-79-2008: Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGRAW-EDISON

Report Number: SP1-1908-441-9-R4

Test Date: 10/23/2019

Luminaire Tested: SA1C-760-U-5WQ

Data in this report applies to families of products SA1C-760-U-5WQ .

Test Information

Test Method: LM-79-2008
 Report Number: SP1-1908-441-9-R4
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 10/28/2024
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: McGRAW-EDISON
 Catalog Number: **SA1C-760-U-5WQ**
 Description: McGRAW EDISON ROADWAY AND AREA LUMINAIRE

THIS IS A REVISION OF SP1-1908-441-4-R3. TO UPDATE THE CATALOG INFORMATION.TESTED IN SITU. ROADWAY AND AREA LUMINAIRE. (1) 70 CRI, 5000K, 1050MA LIGHTSQUARE WITH 16 LEDS AND TYPE V WIDE OPTICS.

Spectral Parameters

CCT (K): 5474
 CIE u': 0.2052
 CIE v': 0.4804
 Duv: 0.0025
 CIE x: 0.3330
 CIE y: 0.3466
 CIE z: 0.3204
 Peak Wavelength (nm): 442
 Dominant Wavelength (nm): 554
 Purity: 4.1

| | | | |
|-----------|------|------|-------|
| CRI (Ra): | 71.7 | | |
| R1: | 70.6 | R9: | -27.1 |
| R2: | 74.6 | R10: | 40.8 |
| R3: | 78.3 | R11: | 74.6 |
| R4: | 73.8 | R12: | 50.4 |
| R5: | 72.4 | R13: | 70.0 |
| R6: | 67.5 | R14: | 87.8 |
| R7: | 77.5 | | |
| R8: | 58.9 | | |

Rf: 72.1
 Rg: 97.2



Test Conditions

Stabilization Time: 240M
 Operation Time: 12H
 Room Temperature (°C) / RH%: 24.6/31%
 Sphere Temperature (°C): 25.9

REPORT NUMBER: SP1-1908-441-9-R4

| Measurement and Test Equipment | | | |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument | Identification Number | Calibration Date | Calibration Due Date |
| Photometer | IN0058 | 6/28/2019 | 12/28/2019 |
| Power Meter | IN0071 | 12/5/2018 | 12/5/2019 |
| AC Power Source | IN0063 | 12/5/2018 | 12/5/2019 |
| DC Power Source | IN0208 | 12/5/2018 | 12/5/2019 |
| Sphere Thermometer | IN0085 | 12/5/2018 | 12/5/2019 |
| Room Thermometer | IN0046 | 12/5/2018 | 12/5/2019 |

REPORT NUMBER: SP1-1908-441-9-R4

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 5700K 4-step quadrangle

REPORT NUMBER: SP1-1908-441-9-R4

Photopic Flux vs. Wavelength



#####

| λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) |
|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|
| 360 | 3540 | NR | 490 | 33363 | NR | 620 | 80193 | NR | 750 | 4663 | NR | 880 | 4678 | NR |
| 365 | 2862 | NR | 495 | 44177 | NR | 625 | 73091 | NR | 755 | 4147 | NR | 885 | 4128 | NR |
| 370 | 2865 | NR | 500 | 57019 | NR | 630 | 66269 | NR | 760 | 4040 | NR | 890 | 4504 | NR |
| 375 | 3254 | NR | 505 | 70030 | NR | 635 | 60012 | NR | 765 | 3474 | NR | 895 | 4371 | NR |
| 380 | 3076 | NR | 510 | 81972 | NR | 640 | 53914 | NR | 770 | 3469 | NR | 900 | 4082 | NR |
| 385 | 2904 | NR | 515 | 92590 | NR | 645 | 48385 | NR | 775 | 3181 | NR | 905 | 2982 | NR |
| 390 | 2689 | NR | 520 | 100305 | NR | 650 | 43219 | NR | 780 | 2969 | NR | 910 | 4351 | NR |
| 395 | 2619 | NR | 525 | 107452 | NR | 655 | 38562 | NR | 785 | 3132 | NR | 915 | 3365 | NR |
| 400 | 2679 | NR | 530 | 111373 | NR | 660 | 34110 | NR | 790 | 2507 | NR | 920 | 3430 | NR |
| 405 | 3515 | NR | 535 | 114505 | NR | 665 | 30085 | NR | 795 | 2968 | NR | 925 | 4264 | NR |
| 410 | 6934 | NR | 540 | 116408 | NR | 670 | 26205 | NR | 800 | 2758 | NR | 930 | 4095 | NR |
| 415 | 14943 | NR | 545 | 118700 | NR | 675 | 22906 | NR | 805 | 2872 | NR | 935 | 5048 | NR |
| 420 | 31939 | NR | 550 | 119209 | NR | 680 | 20058 | NR | 810 | 3094 | NR | 940 | 4074 | NR |
| 425 | 64701 | NR | 555 | 120742 | NR | 685 | 17413 | NR | 815 | 3222 | NR | 945 | 4949 | NR |
| 430 | 110939 | NR | 560 | 121594 | NR | 690 | 15447 | NR | 820 | 3238 | NR | 950 | 4387 | NR |
| 435 | 164597 | NR | 565 | 121913 | NR | 695 | 13398 | NR | 825 | 3524 | NR | 955 | 4978 | NR |
| 440 | 207696 | NR | 570 | 122147 | NR | 700 | 11777 | NR | 830 | 2921 | NR | 960 | 4706 | NR |
| 445 | 201830 | NR | 575 | 121605 | NR | 705 | 10412 | NR | 835 | 3595 | NR | 965 | 5083 | NR |
| 450 | 145410 | NR | 580 | 120248 | NR | 710 | 9544 | NR | 840 | 3016 | NR | 970 | 4522 | NR |
| 455 | 89594 | NR | 585 | 117717 | NR | 715 | 8940 | NR | 845 | 4032 | NR | 975 | 4740 | NR |
| 460 | 58321 | NR | 590 | 114359 | NR | 720 | 7897 | NR | 850 | 3579 | NR | 980 | 6122 | NR |
| 465 | 39318 | NR | 595 | 109974 | NR | 725 | 7045 | NR | 855 | 4571 | NR | 985 | 6450 | NR |
| 470 | 27693 | NR | 600 | 105269 | NR | 730 | 6483 | NR | 860 | 4485 | NR | 990 | 4875 | NR |
| 475 | 23081 | NR | 605 | 99453 | NR | 735 | 5838 | NR | 865 | 3978 | NR | 995 | 4764 | NR |
| 480 | 23002 | NR | 610 | 92921 | NR | 740 | 5261 | NR | 870 | 4298 | NR | 1000 | 3640 | NR |
| 485 | 26201 | NR | 615 | 86989 | NR | 745 | 4760 | NR | 875 | 4356 | NR | | | |

REPORT NUMBER: SP1-1908-441-9-R4

Scotopic Flux vs. Wavelength



Scotopic Lumens: 13759.3 S/P: 1.85

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 3540 | NR | 490 | 33363 | NR | 620 | 80193 | NR | 750 | 4663 | NR | 880 | 4678 | NR |
| 365 | 2862 | NR | 495 | 44177 | NR | 625 | 73091 | NR | 755 | 4147 | NR | 885 | 4128 | NR |
| 370 | 2865 | NR | 500 | 57019 | NR | 630 | 66269 | NR | 760 | 4040 | NR | 890 | 4504 | NR |
| 375 | 3254 | NR | 505 | 70030 | NR | 635 | 60012 | NR | 765 | 3474 | NR | 895 | 4371 | NR |
| 380 | 3076 | NR | 510 | 81972 | NR | 640 | 53914 | NR | 770 | 3469 | NR | 900 | 4082 | NR |
| 385 | 2904 | NR | 515 | 92590 | NR | 645 | 48385 | NR | 775 | 3181 | NR | 905 | 2982 | NR |
| 390 | 2689 | NR | 520 | 100305 | NR | 650 | 43219 | NR | 780 | 2969 | NR | 910 | 4351 | NR |
| 395 | 2619 | NR | 525 | 107452 | NR | 655 | 38562 | NR | 785 | 3132 | NR | 915 | 3365 | NR |
| 400 | 2679 | NR | 530 | 111373 | NR | 660 | 34110 | NR | 790 | 2507 | NR | 920 | 3430 | NR |
| 405 | 3515 | NR | 535 | 114505 | NR | 665 | 30085 | NR | 795 | 2968 | NR | 925 | 4264 | NR |
| 410 | 6934 | NR | 540 | 116408 | NR | 670 | 26205 | NR | 800 | 2758 | NR | 930 | 4095 | NR |
| 415 | 14943 | NR | 545 | 118700 | NR | 675 | 22906 | NR | 805 | 2872 | NR | 935 | 5048 | NR |
| 420 | 31939 | NR | 550 | 119209 | NR | 680 | 20058 | NR | 810 | 3094 | NR | 940 | 4074 | NR |
| 425 | 64701 | NR | 555 | 120742 | NR | 685 | 17413 | NR | 815 | 3222 | NR | 945 | 4949 | NR |
| 430 | 110939 | NR | 560 | 121594 | NR | 690 | 15447 | NR | 820 | 3238 | NR | 950 | 4387 | NR |
| 435 | 164597 | NR | 565 | 121913 | NR | 695 | 13398 | NR | 825 | 3524 | NR | 955 | 4978 | NR |
| 440 | 207696 | NR | 570 | 122147 | NR | 700 | 11777 | NR | 830 | 2921 | NR | 960 | 4706 | NR |
| 445 | 201830 | NR | 575 | 121605 | NR | 705 | 10412 | NR | 835 | 3595 | NR | 965 | 5083 | NR |
| 450 | 145410 | NR | 580 | 120248 | NR | 710 | 9544 | NR | 840 | 3016 | NR | 970 | 4522 | NR |
| 455 | 89594 | NR | 585 | 117717 | NR | 715 | 8940 | NR | 845 | 4032 | NR | 975 | 4740 | NR |
| 460 | 58321 | NR | 590 | 114359 | NR | 720 | 7897 | NR | 850 | 3579 | NR | 980 | 6122 | NR |
| 465 | 39318 | NR | 595 | 109974 | NR | 725 | 7045 | NR | 855 | 4571 | NR | 985 | 6450 | NR |
| 470 | 27693 | NR | 600 | 105269 | NR | 730 | 6483 | NR | 860 | 4485 | NR | 990 | 4875 | NR |
| 475 | 23081 | NR | 605 | 99453 | NR | 735 | 5838 | NR | 865 | 3978 | NR | 995 | 4764 | NR |
| 480 | 23002 | NR | 610 | 92921 | NR | 740 | 5261 | NR | 870 | 4298 | NR | 1000 | 3640 | NR |
| 485 | 26201 | NR | 615 | 86989 | NR | 745 | 4760 | NR | 875 | 4356 | NR | | | |

REPORT NUMBER: SP1-1908-441-9-R4

Melanopic Flux vs. Wavelength



Melanopic Lumens: 5527.6 M/P: 0.74

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 3540 | NR | 490 | 33363 | NR | 620 | 80193 | NR | 750 | 4663 | NR | 880 | 4678 | NR |
| 365 | 2862 | NR | 495 | 44177 | NR | 625 | 73091 | NR | 755 | 4147 | NR | 885 | 4128 | NR |
| 370 | 2865 | NR | 500 | 57019 | NR | 630 | 66269 | NR | 760 | 4040 | NR | 890 | 4504 | NR |
| 375 | 3254 | NR | 505 | 70030 | NR | 635 | 60012 | NR | 765 | 3474 | NR | 895 | 4371 | NR |
| 380 | 3076 | NR | 510 | 81972 | NR | 640 | 53914 | NR | 770 | 3469 | NR | 900 | 4082 | NR |
| 385 | 2904 | NR | 515 | 92590 | NR | 645 | 48385 | NR | 775 | 3181 | NR | 905 | 2982 | NR |
| 390 | 2689 | NR | 520 | 100305 | NR | 650 | 43219 | NR | 780 | 2969 | NR | 910 | 4351 | NR |
| 395 | 2619 | NR | 525 | 107452 | NR | 655 | 38562 | NR | 785 | 3132 | NR | 915 | 3365 | NR |
| 400 | 2679 | NR | 530 | 111373 | NR | 660 | 34110 | NR | 790 | 2507 | NR | 920 | 3430 | NR |
| 405 | 3515 | NR | 535 | 114505 | NR | 665 | 30085 | NR | 795 | 2968 | NR | 925 | 4264 | NR |
| 410 | 6934 | NR | 540 | 116408 | NR | 670 | 26205 | NR | 800 | 2758 | NR | 930 | 4095 | NR |
| 415 | 14943 | NR | 545 | 118700 | NR | 675 | 22906 | NR | 805 | 2872 | NR | 935 | 5048 | NR |
| 420 | 31939 | NR | 550 | 119209 | NR | 680 | 20058 | NR | 810 | 3094 | NR | 940 | 4074 | NR |
| 425 | 64701 | NR | 555 | 120742 | NR | 685 | 17413 | NR | 815 | 3222 | NR | 945 | 4949 | NR |
| 430 | 110939 | NR | 560 | 121594 | NR | 690 | 15447 | NR | 820 | 3238 | NR | 950 | 4387 | NR |
| 435 | 164597 | NR | 565 | 121913 | NR | 695 | 13398 | NR | 825 | 3524 | NR | 955 | 4978 | NR |
| 440 | 207696 | NR | 570 | 122147 | NR | 700 | 11777 | NR | 830 | 2921 | NR | 960 | 4706 | NR |
| 445 | 201830 | NR | 575 | 121605 | NR | 705 | 10412 | NR | 835 | 3595 | NR | 965 | 5083 | NR |
| 450 | 145410 | NR | 580 | 120248 | NR | 710 | 9544 | NR | 840 | 3016 | NR | 970 | 4522 | NR |
| 455 | 89594 | NR | 585 | 117717 | NR | 715 | 8940 | NR | 845 | 4032 | NR | 975 | 4740 | NR |
| 460 | 58321 | NR | 590 | 114359 | NR | 720 | 7897 | NR | 850 | 3579 | NR | 980 | 6122 | NR |
| 465 | 39318 | NR | 595 | 109974 | NR | 725 | 7045 | NR | 855 | 4571 | NR | 985 | 6450 | NR |
| 470 | 27693 | NR | 600 | 105269 | NR | 730 | 6483 | NR | 860 | 4485 | NR | 990 | 4875 | NR |
| 475 | 23081 | NR | 605 | 99453 | NR | 735 | 5838 | NR | 865 | 3978 | NR | 995 | 4764 | NR |
| 480 | 23002 | NR | 610 | 92921 | NR | 740 | 5261 | NR | 870 | 4298 | NR | 1000 | 3640 | NR |
| 485 | 26201 | NR | 615 | 86989 | NR | 745 | 4760 | NR | 875 | 4356 | NR | | | |

REPORT NUMBER: SP1-1908-441-9-R4

TM-30-18

Summary

$R_f = 72.1$
 $R_g = 97.2$
 CIE $R_a = 71.7$
 $R_g = -27.1$



Color Vector Graphics



REPORT NUMBER: SP1-1908-441-9-R4

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)

| | | | |
|------------|------------|------------|------------|
| CES01 = 85 | CES26 = 54 | CES51 = 88 | CES76 = 43 |
| CES02 = 59 | CES27 = 79 | CES52 = 90 | CES77 = 64 |
| CES03 = 30 | CES28 = 77 | CES53 = 77 | CES78 = 46 |
| CES04 = 69 | CES29 = 50 | CES54 = 81 | CES79 = 74 |
| CES05 = 46 | CES30 = 59 | CES55 = 80 | CES80 = 70 |
| CES06 = 50 | CES31 = 55 | CES56 = 70 | CES81 = 71 |
| CES07 = 38 | CES32 = 52 | CES57 = 68 | CES82 = 88 |
| CES08 = 38 | CES33 = 63 | CES58 = 70 | CES83 = 82 |
| CES09 = 29 | CES34 = 63 | CES59 = 88 | CES84 = 87 |
| CES10 = 72 | CES35 = 79 | CES60 = 92 | CES85 = 84 |
| CES11 = 55 | CES36 = 90 | CES61 = 88 | CES86 = 76 |
| CES12 = 61 | CES37 = 72 | CES62 = 81 | CES87 = 75 |
| CES13 = 41 | CES38 = 68 | CES63 = 75 | CES88 = 77 |
| CES14 = 74 | CES39 = 91 | CES64 = 72 | CES89 = 76 |
| CES15 = 70 | CES40 = 83 | CES65 = 65 | CES90 = 76 |
| CES16 = 46 | CES41 = 84 | CES66 = 66 | CES91 = 92 |
| CES17 = 48 | CES42 = 70 | CES67 = 64 | CES92 = 70 |
| CES18 = 55 | CES43 = 69 | CES68 = 71 | CES93 = 83 |
| CES19 = 70 | CES44 = 98 | CES69 = 80 | CES94 = 60 |
| CES20 = 64 | CES45 = 79 | CES70 = 58 | CES95 = 73 |
| CES21 = 85 | CES46 = 78 | CES71 = 55 | CES96 = 79 |
| CES22 = 77 | CES47 = 76 | CES72 = 84 | CES97 = 84 |
| CES23 = 91 | CES48 = 68 | CES73 = 47 | CES98 = 73 |
| CES24 = 90 | CES49 = 78 | CES74 = 94 | CES99 = 62 |
| CES25 = 71 | CES50 = 87 | CES75 = 51 | |



REPORT NUMBER: SP1-1908-441-9-R4

TM-30-18

Color Rendition by Hue-Angle Bin



REPORT NUMBER: SP1-1908-441-9-R4

TM-30-18

Measure Comparisons



(END OF REPORT)