

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: McGRAW-EDISON

Report Number: P638356

Luminaire Tested: GWS-SA4E-760-U-RW-W-GRSBK

Issue Date: 1/10/2023

Test Information

Test Method: LM-79-2019
Report Number: P638356
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2209-782-50)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/10/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: McGRAW-EDISON
Catalog Number: GWS-SA4E-760-U-RW-W-GRSBK
Description: GALLEON WALL SLIM LUMINAIRE. (4) LIGHTSQUARES WITH 16 LEDS EACH AND RECTANGULAR WIDE OPTICS W/ FACTORY INSTALLED GLARE SHIELD, BK
Light Source: (64) 5700K CCT, 70 CRI LEDS
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 20010.7 lumens
Efficiency: N/A
Efficacy: 98.8 lumens/watt
Luminous Opening: Rectangular (W 1' x L: 1' x H: 0')
IES Classification: Type V - Short
BUG Rating: B4 - U0 - G0


Input Watts (W): 202.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 0
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT



REPORT NUMBER: P638356
 CATALOG NUMBER: GWS-SA4E-760-U-RW-W-GRSBK

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 5.5 fc
 Type V - Short - N/A

REPORT NUMBER: P638356
CATALOG NUMBER: GWS-SA4E-760-U-RW-W-GRSBK

Luminous Intensity Polar Plot



— Vertical Plane Through 43-Deg Lateral - - - Horizontal Cone Through 50-Deg Vertical

REPORT NUMBER: P638356
 CATALOG NUMBER: GWS-SA4E-760-U-RW-W-GRSBK


FLUX DISTRIBUTION:

| | | Downward | Upward | Total |
|--------------------|-----------|----------|--------|---------|
| House Side | Lumens | 10005.1 | 0.0 | 10005.1 |
| | % Fixture | 50.0 | 0.0 | 50.0 |
| Street Side | Lumens | 10005.6 | 0.0 | 10005.6 |
| | % Fixture | 50.0 | 0.0 | 50.0 |
| Total | Lumens | 20010.7 | 0.0 | 20010.7 |
| | % Fixture | 100.0 | 0.0 | 100.0 |

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|---------|-----------|
| 0°-10° | 280.3 | 1.4 |
| 10°-20° | 964.5 | 4.8 |
| 20°-30° | 1951.4 | 9.8 |
| 30°-40° | 3620.6 | 18.1 |
| 40°-50° | 6010.0 | 30.0 |
| 50°-60° | 6133.4 | 30.7 |
| 60°-70° | 1005.8 | 5.0 |
| 70°-80° | 44.0 | 0.2 |
| 80°-90° | 0.6 | 0.0 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-90° | 20010.7 | 100.0 |
| 0°-180° | 20010.7 | 100.0 |

Coefficient of Utilization




REPORT NUMBER: P638356
 CATALOG NUMBER: GWS-SA4E-760-U-RW-W-GRSBK

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

| Zone | Lumens | % Fixture | Zone Rating/Lumen Limit | | |
|----------------|--------|-----------|-------------------------|------|--------|
| | | | B | U | G |
| FL (0°-30°) | 1612.1 | 8.1 | | | |
| FM (30°-60°) | 7901.2 | 39.5 | | | |
| FH (60°-80°) | 492.0 | 2.5 | | | G0/660 |
| FVH (80°-90°) | 0.2 | 0.0 | | | G0/10 |
| BL (0°-30°) | 1584.1 | 7.9 | B3/2500 | | |
| BM (30°-60°) | 7862.8 | 39.3 | B4/8500 | | |
| BH (60°-80°) | 557.8 | 2.8 | B2/1000 | | G0/660 |
| BVH (80°-90°) | 0.4 | 0.0 | | | G0/10 |
| UL (90°-100°) | 0.0 | 0.0 | | U0/0 | |
| UH (100°-180°) | 0.0 | 0.0 | | U0/0 | |

BUG Rating: B4-U0-G0
 Type V Short





REPORT NUMBER: P638356

CATALOG NUMBER: GWS-SA4E-760-U-RW-W-GRSBK

CANDELA DISTRIBUTION (FULL):

| | 0° | 5° | 15° | 25° | 35° | 43° | 45° | 55° | 65° | 75° | 85° |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 2846.2 | 2846.2 | 2846.2 | 2846.2 | 2846.2 | 2846.2 | 2846.2 | 2846.2 | 2846.2 | 2846.2 | 2846.2 |
| 2.5° | 2793.1 | 2799.7 | 2808.6 | 2817.4 | 2828.5 | 2839.6 | 2846.2 | 2866.1 | 2861.7 | 2879.4 | 2879.4 |
| 5° | 2762.1 | 2768.7 | 2779.8 | 2799.7 | 2824.1 | 2848.4 | 2866.1 | 2906.0 | 2928.1 | 2963.5 | 2976.8 |
| 7.5° | 2777.6 | 2786.4 | 2799.7 | 2830.7 | 2868.3 | 2906.0 | 2925.9 | 2990.1 | 3034.3 | 3100.7 | 3138.4 |
| 10° | 2828.5 | 2837.4 | 2859.5 | 2912.6 | 2961.3 | 3014.4 | 3038.8 | 3120.6 | 3191.5 | 3282.2 | 3335.3 |
| 12.5° | 2886.0 | 2897.1 | 2941.4 | 3021.1 | 3105.2 | 3176.0 | 3209.2 | 3299.9 | 3373.0 | 3474.8 | 3558.9 |
| 15° | 2945.8 | 2963.5 | 3032.1 | 3149.4 | 3268.9 | 3364.1 | 3399.5 | 3496.9 | 3569.9 | 3678.4 | 3773.5 |
| 17.5° | 3085.2 | 3105.2 | 3182.6 | 3308.8 | 3472.5 | 3583.2 | 3614.2 | 3716.0 | 3771.3 | 3844.4 | 3944.0 |
| 20° | 3260.1 | 3297.7 | 3392.9 | 3545.6 | 3724.9 | 3831.1 | 3853.2 | 3952.8 | 3948.4 | 3979.4 | 4065.7 |
| 22.5° | 3477.0 | 3503.5 | 3607.6 | 3789.0 | 3990.4 | 4107.7 | 4158.6 | 4200.7 | 4145.4 | 4118.8 | 4174.1 |
| 25° | 3702.7 | 3733.7 | 3846.6 | 4045.8 | 4271.5 | 4406.5 | 4448.6 | 4481.8 | 4393.2 | 4293.7 | 4300.3 |
| 27.5° | 3994.9 | 4017.0 | 4127.7 | 4340.1 | 4565.9 | 4718.6 | 4756.2 | 4813.8 | 4696.5 | 4537.1 | 4492.8 |
| 30° | 4342.3 | 4364.5 | 4481.8 | 4705.3 | 4928.8 | 5059.4 | 5117.0 | 5187.8 | 5059.4 | 4860.2 | 4809.3 |
| 32.5° | 4749.6 | 4771.7 | 4922.2 | 5152.4 | 5336.1 | 5477.7 | 5533.1 | 5608.3 | 5506.5 | 5283.0 | 5225.4 |
| 35° | 5236.5 | 5249.8 | 5426.8 | 5676.9 | 5871.7 | 6008.9 | 6046.5 | 6135.1 | 6022.2 | 5798.6 | 5767.7 |
| 37.5° | 5800.9 | 5816.4 | 6008.9 | 6298.8 | 6498.0 | 6650.7 | 6710.5 | 6734.8 | 6597.6 | 6347.5 | 6323.2 |
| 40° | 6420.6 | 6471.5 | 6659.6 | 6971.7 | 7195.2 | 7387.7 | 7440.9 | 7359.0 | 7166.4 | 6825.6 | 6781.3 |
| 42.5° | 7066.8 | 7111.1 | 7321.3 | 7660.0 | 7918.9 | 8115.9 | 8118.1 | 7941.0 | 7613.5 | 7142.1 | 7075.7 |
| 45° | 7604.6 | 7622.3 | 7894.6 | 8235.4 | 8554.1 | 8693.5 | 8706.8 | 8385.9 | 7892.4 | 7325.8 | 7184.1 |
| 47.5° | 7974.2 | 8003.0 | 8239.8 | 8567.4 | 8919.3 | 9045.4 | 9018.9 | 8618.3 | 8025.1 | 7445.3 | 7210.7 |
| 50° | 7978.7 | 8027.4 | 8284.1 | 8600.6 | 8941.4 | 9094.1 | 9056.5 | 8684.7 | 8100.4 | 7449.7 | 7146.5 |
| 52.5° | 7272.7 | 7352.3 | 7770.6 | 8228.8 | 8751.1 | 9012.2 | 9021.1 | 8771.0 | 8071.6 | 7378.9 | 7089.0 |
| 55° | 5486.6 | 5572.9 | 6099.6 | 6880.9 | 7890.1 | 8618.3 | 8744.4 | 8669.2 | 8038.4 | 7409.9 | 7190.8 |
| 57.5° | 2903.7 | 2837.4 | 3129.5 | 3904.1 | 5172.3 | 6460.4 | 6830.0 | 7432.0 | 7668.8 | 7447.5 | 7378.9 |
| 60° | 633.0 | 675.0 | 898.6 | 1210.6 | 2018.5 | 3038.8 | 3399.5 | 4430.9 | 5657.0 | 6201.5 | 6595.4 |
| 62.5° | 272.2 | 267.8 | 278.9 | 316.5 | 462.6 | 770.2 | 940.6 | 1536.0 | 2423.5 | 3328.7 | 3941.8 |
| 65° | 223.5 | 225.7 | 234.6 | 234.6 | 219.1 | 221.3 | 232.4 | 351.9 | 566.6 | 794.5 | 1066.8 |
| 67.5° | 168.2 | 170.4 | 185.9 | 190.3 | 179.3 | 159.4 | 157.1 | 132.8 | 139.4 | 174.8 | 181.5 |
| 70° | 106.2 | 106.2 | 115.1 | 119.5 | 119.5 | 110.7 | 108.4 | 95.2 | 93.0 | 106.2 | 119.5 |
| 72.5° | 57.5 | 57.5 | 62.0 | 64.2 | 62.0 | 59.8 | 59.8 | 57.5 | 55.3 | 64.2 | 81.9 |
| 75° | 24.3 | 24.3 | 26.6 | 26.6 | 24.3 | 24.3 | 24.3 | 24.3 | 24.3 | 28.8 | 44.3 |
| 77.5° | 4.4 | 6.6 | 8.9 | 6.6 | 4.4 | 4.4 | 4.4 | 6.6 | 6.6 | 8.9 | 13.3 |
| 80° | 2.2 | 2.2 | 4.4 | 2.2 | 0.0 | 0.0 | 0.0 | 0.0 | 2.2 | 2.2 | 2.2 |
| 82.5° | 2.2 | 2.2 | 2.2 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 2.2 |
| 85° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 87.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P638356

CATALOG NUMBER: GWS-SA4E-760-U-RW-W-GRSBK

CANDELA DISTRIBUTION (continued):

| | 90° | 95° | 105° | 115° | 125° | 135° | 145° | 155° | 165° | 175° | 180° |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 2846.2 | 2846.2 | 2846.2 | 2846.2 | 2846.2 | 2846.2 | 2846.2 | 2846.2 | 2846.2 | 2846.2 | 2846.2 |
| 2.5° | 2894.9 | 2870.6 | 2879.4 | 2883.8 | 2877.2 | 2872.8 | 2848.4 | 2841.8 | 2830.7 | 2813.0 | 2808.6 |
| 5° | 2992.3 | 2972.4 | 2970.1 | 2956.9 | 2925.9 | 2888.3 | 2841.8 | 2821.9 | 2799.7 | 2777.6 | 2773.2 |
| 7.5° | 3156.1 | 3131.7 | 3116.2 | 3072.0 | 3001.1 | 2941.4 | 2863.9 | 2821.9 | 2793.1 | 2764.3 | 2757.7 |
| 10° | 3366.3 | 3337.5 | 3293.3 | 3211.4 | 3116.2 | 3029.9 | 2939.2 | 2883.8 | 2839.6 | 2799.7 | 2797.5 |
| 12.5° | 3589.8 | 3558.9 | 3479.2 | 3375.2 | 3260.1 | 3180.4 | 3065.3 | 2987.9 | 2921.5 | 2861.7 | 2855.1 |
| 15° | 3824.5 | 3786.8 | 3678.4 | 3554.4 | 3448.2 | 3366.3 | 3240.2 | 3116.2 | 3014.4 | 2928.1 | 2919.2 |
| 17.5° | 4003.7 | 3957.2 | 3828.9 | 3735.9 | 3649.6 | 3565.5 | 3423.9 | 3260.1 | 3125.1 | 3021.1 | 2996.7 |
| 20° | 4116.6 | 4072.3 | 3950.6 | 3899.7 | 3859.9 | 3800.1 | 3631.9 | 3461.5 | 3311.0 | 3182.6 | 3160.5 |
| 22.5° | 4225.0 | 4171.9 | 4065.7 | 4065.7 | 4096.7 | 4072.3 | 3890.8 | 3696.1 | 3519.0 | 3370.7 | 3337.5 |
| 25° | 4346.8 | 4304.7 | 4229.5 | 4291.4 | 4368.9 | 4366.7 | 4180.8 | 3937.3 | 3733.7 | 3567.7 | 3534.5 |
| 27.5° | 4523.8 | 4481.8 | 4455.2 | 4572.5 | 4669.9 | 4663.3 | 4459.6 | 4196.3 | 3981.6 | 3817.8 | 3786.8 |
| 30° | 4835.9 | 4796.1 | 4767.3 | 4908.9 | 5032.9 | 4986.4 | 4762.9 | 4508.3 | 4291.4 | 4105.5 | 4083.4 |
| 32.5° | 5252.0 | 5209.9 | 5172.3 | 5313.9 | 5424.6 | 5364.9 | 5152.4 | 4913.4 | 4663.3 | 4481.8 | 4437.5 |
| 35° | 5798.6 | 5710.1 | 5672.5 | 5840.7 | 5887.2 | 5820.8 | 5617.2 | 5406.9 | 5141.3 | 4933.3 | 4904.5 |
| 37.5° | 6363.0 | 6259.0 | 6232.4 | 6378.5 | 6453.8 | 6429.4 | 6190.4 | 5971.3 | 5683.6 | 5453.4 | 5420.2 |
| 40° | 6845.5 | 6750.3 | 6703.9 | 6931.8 | 7102.2 | 7117.7 | 6903.0 | 6635.2 | 6296.6 | 6057.6 | 5997.8 |
| 42.5° | 7128.8 | 7046.9 | 7035.8 | 7390.0 | 7668.8 | 7868.0 | 7611.3 | 7334.6 | 6978.3 | 6708.3 | 6659.6 |
| 45° | 7193.0 | 7139.9 | 7232.8 | 7697.6 | 8131.4 | 8494.4 | 8275.2 | 7983.1 | 7598.0 | 7312.5 | 7266.0 |
| 47.5° | 7186.3 | 7168.6 | 7334.6 | 7856.9 | 8405.8 | 8852.9 | 8744.4 | 8414.7 | 8042.9 | 7744.1 | 7699.8 |
| 50° | 7091.2 | 7093.4 | 7370.0 | 7936.6 | 8516.5 | 8950.3 | 8841.8 | 8536.4 | 8204.4 | 7910.1 | 7874.6 |
| 52.5° | 7053.5 | 7040.3 | 7303.6 | 7912.3 | 8629.4 | 8906.0 | 8662.6 | 8319.5 | 7949.9 | 7586.9 | 7533.8 |
| 55° | 7186.3 | 7153.1 | 7312.5 | 7892.4 | 8642.6 | 8881.7 | 8239.8 | 7496.2 | 6739.3 | 6309.9 | 6274.5 |
| 57.5° | 7385.5 | 7350.1 | 7425.4 | 7746.3 | 7949.9 | 7385.5 | 6064.2 | 4864.7 | 4085.6 | 3755.8 | 3612.0 |
| 60° | 6595.4 | 6571.1 | 6513.5 | 6126.2 | 5254.2 | 3963.9 | 2700.1 | 1721.9 | 1237.2 | 1000.4 | 1000.4 |
| 62.5° | 4092.3 | 4059.1 | 3747.0 | 2784.2 | 2022.9 | 1170.8 | 644.0 | 402.8 | 305.4 | 285.5 | 283.3 |
| 65° | 1148.7 | 1142.0 | 945.0 | 668.4 | 424.9 | 263.4 | 232.4 | 236.8 | 232.4 | 225.7 | 223.5 |
| 67.5° | 172.6 | 190.3 | 190.3 | 154.9 | 148.3 | 166.0 | 194.8 | 208.0 | 197.0 | 185.9 | 181.5 |
| 70° | 110.7 | 119.5 | 115.1 | 99.6 | 106.2 | 123.9 | 139.4 | 141.6 | 135.0 | 123.9 | 121.7 |
| 72.5° | 77.5 | 86.3 | 70.8 | 64.2 | 66.4 | 73.0 | 79.7 | 79.7 | 77.5 | 73.0 | 68.6 |
| 75° | 46.5 | 46.5 | 33.2 | 31.0 | 31.0 | 33.2 | 33.2 | 37.6 | 37.6 | 35.4 | 33.2 |
| 77.5° | 15.5 | 17.7 | 11.1 | 8.9 | 8.9 | 8.9 | 11.1 | 13.3 | 13.3 | 11.1 | 8.9 |
| 80° | 2.2 | 4.4 | 2.2 | 2.2 | 2.2 | 2.2 | 2.2 | 2.2 | 4.4 | 4.4 | 2.2 |
| 82.5° | 2.2 | 2.2 | 2.2 | 0.0 | 0.0 | 0.0 | 0.0 | 2.2 | 2.2 | 2.2 | 2.2 |
| 85° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 2.2 | 2.2 |
| 87.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



LM-79-2008: Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGRAW-EDISON

Report Number: SP1-1908-441-9-R4

Test Date: 10/23/2019

Luminaire Tested: SA1C-760-U-5WQ

Data in this report applies to families of products SA1C-760-U-5WQ .

Test Information

Test Method: LM-79-2008
 Report Number: SP1-1908-441-9-R4
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 10/28/2024
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: MCGRAW-EDISON
 Catalog Number: **SA1C-760-U-5WQ**
 Description: MCGRAW EDISON ROADWAY AND AREA LUMINAIRE

THIS IS A REVISION OF SP1-1908-441-4-R3. TO UPDATE THE CATALOG INFORMATION.TESTED IN SITU. ROADWAY AND AREA LUMINAIRE. (1) 70 CRI, 5000K, 1050MA LIGHTSQUARE WITH 16 LEDS AND TYPE V WIDE OPTICS.

Spectral Parameters

CCT (K): 5474
 CIE u': 0.2052
 CIE v': 0.4804
 Duv: 0.0025
 CIE x: 0.3330
 CIE y: 0.3466
 CIE z: 0.3204
 Peak Wavelength (nm): 442
 Dominant Wavelength (nm): 554
 Purity: 4.1

| | | | |
|-----------|------|------|-------|
| CRI (Ra): | 71.7 | | |
| R1: | 70.6 | R9: | -27.1 |
| R2: | 74.6 | R10: | 40.8 |
| R3: | 78.3 | R11: | 74.6 |
| R4: | 73.8 | R12: | 50.4 |
| R5: | 72.4 | R13: | 70.0 |
| R6: | 67.5 | R14: | 87.8 |
| R7: | 77.5 | | |
| R8: | 58.9 | | |

Rf: 72.1
 Rg: 97.2



Test Conditions
 Stabilization Time: 240M
 Operation Time: 12H
 Room Temperature (°C) / RH%: 24.6/31%
 Sphere Temperature (°C): 25.9

REPORT NUMBER: SP1-1908-441-9-R4

| Measurement and Test Equipment | | | |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument | Identification Number | Calibration Date | Calibration Due Date |
| Photometer | IN0058 | 6/28/2019 | 12/28/2019 |
| Power Meter | IN0071 | 12/5/2018 | 12/5/2019 |
| AC Power Source | IN0063 | 12/5/2018 | 12/5/2019 |
| DC Power Source | IN0208 | 12/5/2018 | 12/5/2019 |
| Sphere Thermometer | IN0085 | 12/5/2018 | 12/5/2019 |
| Room Thermometer | IN0046 | 12/5/2018 | 12/5/2019 |

REPORT NUMBER: SP1-1908-441-9-R4

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 5700K 4-step quadrangle

REPORT NUMBER: SP1-1908-441-9-R4

Photopic Flux vs. Wavelength



#####

| λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) |
|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|
| 360 | 3540 | NR | 490 | 33363 | NR | 620 | 80193 | NR | 750 | 4663 | NR | 880 | 4678 | NR |
| 365 | 2862 | NR | 495 | 44177 | NR | 625 | 73091 | NR | 755 | 4147 | NR | 885 | 4128 | NR |
| 370 | 2865 | NR | 500 | 57019 | NR | 630 | 66269 | NR | 760 | 4040 | NR | 890 | 4504 | NR |
| 375 | 3254 | NR | 505 | 70030 | NR | 635 | 60012 | NR | 765 | 3474 | NR | 895 | 4371 | NR |
| 380 | 3076 | NR | 510 | 81972 | NR | 640 | 53914 | NR | 770 | 3469 | NR | 900 | 4082 | NR |
| 385 | 2904 | NR | 515 | 92590 | NR | 645 | 48385 | NR | 775 | 3181 | NR | 905 | 2982 | NR |
| 390 | 2689 | NR | 520 | 100305 | NR | 650 | 43219 | NR | 780 | 2969 | NR | 910 | 4351 | NR |
| 395 | 2619 | NR | 525 | 107452 | NR | 655 | 38562 | NR | 785 | 3132 | NR | 915 | 3365 | NR |
| 400 | 2679 | NR | 530 | 111373 | NR | 660 | 34110 | NR | 790 | 2507 | NR | 920 | 3430 | NR |
| 405 | 3515 | NR | 535 | 114505 | NR | 665 | 30085 | NR | 795 | 2968 | NR | 925 | 4264 | NR |
| 410 | 6934 | NR | 540 | 116408 | NR | 670 | 26205 | NR | 800 | 2758 | NR | 930 | 4095 | NR |
| 415 | 14943 | NR | 545 | 118700 | NR | 675 | 22906 | NR | 805 | 2872 | NR | 935 | 5048 | NR |
| 420 | 31939 | NR | 550 | 119209 | NR | 680 | 20058 | NR | 810 | 3094 | NR | 940 | 4074 | NR |
| 425 | 64701 | NR | 555 | 120742 | NR | 685 | 17413 | NR | 815 | 3222 | NR | 945 | 4949 | NR |
| 430 | 110939 | NR | 560 | 121594 | NR | 690 | 15447 | NR | 820 | 3238 | NR | 950 | 4387 | NR |
| 435 | 164597 | NR | 565 | 121913 | NR | 695 | 13398 | NR | 825 | 3524 | NR | 955 | 4978 | NR |
| 440 | 207696 | NR | 570 | 122147 | NR | 700 | 11777 | NR | 830 | 2921 | NR | 960 | 4706 | NR |
| 445 | 201830 | NR | 575 | 121605 | NR | 705 | 10412 | NR | 835 | 3595 | NR | 965 | 5083 | NR |
| 450 | 145410 | NR | 580 | 120248 | NR | 710 | 9544 | NR | 840 | 3016 | NR | 970 | 4522 | NR |
| 455 | 89594 | NR | 585 | 117717 | NR | 715 | 8940 | NR | 845 | 4032 | NR | 975 | 4740 | NR |
| 460 | 58321 | NR | 590 | 114359 | NR | 720 | 7897 | NR | 850 | 3579 | NR | 980 | 6122 | NR |
| 465 | 39318 | NR | 595 | 109974 | NR | 725 | 7045 | NR | 855 | 4571 | NR | 985 | 6450 | NR |
| 470 | 27693 | NR | 600 | 105269 | NR | 730 | 6483 | NR | 860 | 4485 | NR | 990 | 4875 | NR |
| 475 | 23081 | NR | 605 | 99453 | NR | 735 | 5838 | NR | 865 | 3978 | NR | 995 | 4764 | NR |
| 480 | 23002 | NR | 610 | 92921 | NR | 740 | 5261 | NR | 870 | 4298 | NR | 1000 | 3640 | NR |
| 485 | 26201 | NR | 615 | 86989 | NR | 745 | 4760 | NR | 875 | 4356 | NR | | | |

REPORT NUMBER: SP1-1908-441-9-R4

Scotopic Flux vs. Wavelength



Scotopic Lumens: 13759.3 S/P: 1.85

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 3540 | NR | 490 | 33363 | NR | 620 | 80193 | NR | 750 | 4663 | NR | 880 | 4678 | NR |
| 365 | 2862 | NR | 495 | 44177 | NR | 625 | 73091 | NR | 755 | 4147 | NR | 885 | 4128 | NR |
| 370 | 2865 | NR | 500 | 57019 | NR | 630 | 66269 | NR | 760 | 4040 | NR | 890 | 4504 | NR |
| 375 | 3254 | NR | 505 | 70030 | NR | 635 | 60012 | NR | 765 | 3474 | NR | 895 | 4371 | NR |
| 380 | 3076 | NR | 510 | 81972 | NR | 640 | 53914 | NR | 770 | 3469 | NR | 900 | 4082 | NR |
| 385 | 2904 | NR | 515 | 92590 | NR | 645 | 48385 | NR | 775 | 3181 | NR | 905 | 2982 | NR |
| 390 | 2689 | NR | 520 | 100305 | NR | 650 | 43219 | NR | 780 | 2969 | NR | 910 | 4351 | NR |
| 395 | 2619 | NR | 525 | 107452 | NR | 655 | 38562 | NR | 785 | 3132 | NR | 915 | 3365 | NR |
| 400 | 2679 | NR | 530 | 111373 | NR | 660 | 34110 | NR | 790 | 2507 | NR | 920 | 3430 | NR |
| 405 | 3515 | NR | 535 | 114505 | NR | 665 | 30085 | NR | 795 | 2968 | NR | 925 | 4264 | NR |
| 410 | 6934 | NR | 540 | 116408 | NR | 670 | 26205 | NR | 800 | 2758 | NR | 930 | 4095 | NR |
| 415 | 14943 | NR | 545 | 118700 | NR | 675 | 22906 | NR | 805 | 2872 | NR | 935 | 5048 | NR |
| 420 | 31939 | NR | 550 | 119209 | NR | 680 | 20058 | NR | 810 | 3094 | NR | 940 | 4074 | NR |
| 425 | 64701 | NR | 555 | 120742 | NR | 685 | 17413 | NR | 815 | 3222 | NR | 945 | 4949 | NR |
| 430 | 110939 | NR | 560 | 121594 | NR | 690 | 15447 | NR | 820 | 3238 | NR | 950 | 4387 | NR |
| 435 | 164597 | NR | 565 | 121913 | NR | 695 | 13398 | NR | 825 | 3524 | NR | 955 | 4978 | NR |
| 440 | 207696 | NR | 570 | 122147 | NR | 700 | 11777 | NR | 830 | 2921 | NR | 960 | 4706 | NR |
| 445 | 201830 | NR | 575 | 121605 | NR | 705 | 10412 | NR | 835 | 3595 | NR | 965 | 5083 | NR |
| 450 | 145410 | NR | 580 | 120248 | NR | 710 | 9544 | NR | 840 | 3016 | NR | 970 | 4522 | NR |
| 455 | 89594 | NR | 585 | 117717 | NR | 715 | 8940 | NR | 845 | 4032 | NR | 975 | 4740 | NR |
| 460 | 58321 | NR | 590 | 114359 | NR | 720 | 7897 | NR | 850 | 3579 | NR | 980 | 6122 | NR |
| 465 | 39318 | NR | 595 | 109974 | NR | 725 | 7045 | NR | 855 | 4571 | NR | 985 | 6450 | NR |
| 470 | 27693 | NR | 600 | 105269 | NR | 730 | 6483 | NR | 860 | 4485 | NR | 990 | 4875 | NR |
| 475 | 23081 | NR | 605 | 99453 | NR | 735 | 5838 | NR | 865 | 3978 | NR | 995 | 4764 | NR |
| 480 | 23002 | NR | 610 | 92921 | NR | 740 | 5261 | NR | 870 | 4298 | NR | 1000 | 3640 | NR |
| 485 | 26201 | NR | 615 | 86989 | NR | 745 | 4760 | NR | 875 | 4356 | NR | | | |

REPORT NUMBER: SP1-1908-441-9-R4

Melanopic Flux vs. Wavelength



Melanopic Lumens: 5527.6 M/P: 0.74

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 3540 | NR | 490 | 33363 | NR | 620 | 80193 | NR | 750 | 4663 | NR | 880 | 4678 | NR |
| 365 | 2862 | NR | 495 | 44177 | NR | 625 | 73091 | NR | 755 | 4147 | NR | 885 | 4128 | NR |
| 370 | 2865 | NR | 500 | 57019 | NR | 630 | 66269 | NR | 760 | 4040 | NR | 890 | 4504 | NR |
| 375 | 3254 | NR | 505 | 70030 | NR | 635 | 60012 | NR | 765 | 3474 | NR | 895 | 4371 | NR |
| 380 | 3076 | NR | 510 | 81972 | NR | 640 | 53914 | NR | 770 | 3469 | NR | 900 | 4082 | NR |
| 385 | 2904 | NR | 515 | 92590 | NR | 645 | 48385 | NR | 775 | 3181 | NR | 905 | 2982 | NR |
| 390 | 2689 | NR | 520 | 100305 | NR | 650 | 43219 | NR | 780 | 2969 | NR | 910 | 4351 | NR |
| 395 | 2619 | NR | 525 | 107452 | NR | 655 | 38562 | NR | 785 | 3132 | NR | 915 | 3365 | NR |
| 400 | 2679 | NR | 530 | 111373 | NR | 660 | 34110 | NR | 790 | 2507 | NR | 920 | 3430 | NR |
| 405 | 3515 | NR | 535 | 114505 | NR | 665 | 30085 | NR | 795 | 2968 | NR | 925 | 4264 | NR |
| 410 | 6934 | NR | 540 | 116408 | NR | 670 | 26205 | NR | 800 | 2758 | NR | 930 | 4095 | NR |
| 415 | 14943 | NR | 545 | 118700 | NR | 675 | 22906 | NR | 805 | 2872 | NR | 935 | 5048 | NR |
| 420 | 31939 | NR | 550 | 119209 | NR | 680 | 20058 | NR | 810 | 3094 | NR | 940 | 4074 | NR |
| 425 | 64701 | NR | 555 | 120742 | NR | 685 | 17413 | NR | 815 | 3222 | NR | 945 | 4949 | NR |
| 430 | 110939 | NR | 560 | 121594 | NR | 690 | 15447 | NR | 820 | 3238 | NR | 950 | 4387 | NR |
| 435 | 164597 | NR | 565 | 121913 | NR | 695 | 13398 | NR | 825 | 3524 | NR | 955 | 4978 | NR |
| 440 | 207696 | NR | 570 | 122147 | NR | 700 | 11777 | NR | 830 | 2921 | NR | 960 | 4706 | NR |
| 445 | 201830 | NR | 575 | 121605 | NR | 705 | 10412 | NR | 835 | 3595 | NR | 965 | 5083 | NR |
| 450 | 145410 | NR | 580 | 120248 | NR | 710 | 9544 | NR | 840 | 3016 | NR | 970 | 4522 | NR |
| 455 | 89594 | NR | 585 | 117717 | NR | 715 | 8940 | NR | 845 | 4032 | NR | 975 | 4740 | NR |
| 460 | 58321 | NR | 590 | 114359 | NR | 720 | 7897 | NR | 850 | 3579 | NR | 980 | 6122 | NR |
| 465 | 39318 | NR | 595 | 109974 | NR | 725 | 7045 | NR | 855 | 4571 | NR | 985 | 6450 | NR |
| 470 | 27693 | NR | 600 | 105269 | NR | 730 | 6483 | NR | 860 | 4485 | NR | 990 | 4875 | NR |
| 475 | 23081 | NR | 605 | 99453 | NR | 735 | 5838 | NR | 865 | 3978 | NR | 995 | 4764 | NR |
| 480 | 23002 | NR | 610 | 92921 | NR | 740 | 5261 | NR | 870 | 4298 | NR | 1000 | 3640 | NR |
| 485 | 26201 | NR | 615 | 86989 | NR | 745 | 4760 | NR | 875 | 4356 | NR | | | |

REPORT NUMBER: SP1-1908-441-9-R4





TM-30-18

Summary

$R_f = 72.1$
 $R_g = 97.2$
 CIE $R_a = 71.7$
 $R_g = -27.1$



Color Vector Graphics



REPORT NUMBER: SP1-1908-441-9-R4

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)

| | | | |
|------------|------------|------------|------------|
| CES01 = 85 | CES26 = 54 | CES51 = 88 | CES76 = 43 |
| CES02 = 59 | CES27 = 79 | CES52 = 90 | CES77 = 64 |
| CES03 = 30 | CES28 = 77 | CES53 = 77 | CES78 = 46 |
| CES04 = 69 | CES29 = 50 | CES54 = 81 | CES79 = 74 |
| CES05 = 46 | CES30 = 59 | CES55 = 80 | CES80 = 70 |
| CES06 = 50 | CES31 = 55 | CES56 = 70 | CES81 = 71 |
| CES07 = 38 | CES32 = 52 | CES57 = 68 | CES82 = 88 |
| CES08 = 38 | CES33 = 63 | CES58 = 70 | CES83 = 82 |
| CES09 = 29 | CES34 = 63 | CES59 = 88 | CES84 = 87 |
| CES10 = 72 | CES35 = 79 | CES60 = 92 | CES85 = 84 |
| CES11 = 55 | CES36 = 90 | CES61 = 88 | CES86 = 76 |
| CES12 = 61 | CES37 = 72 | CES62 = 81 | CES87 = 75 |
| CES13 = 41 | CES38 = 68 | CES63 = 75 | CES88 = 77 |
| CES14 = 74 | CES39 = 91 | CES64 = 72 | CES89 = 76 |
| CES15 = 70 | CES40 = 83 | CES65 = 65 | CES90 = 76 |
| CES16 = 46 | CES41 = 84 | CES66 = 66 | CES91 = 92 |
| CES17 = 48 | CES42 = 70 | CES67 = 64 | CES92 = 70 |
| CES18 = 55 | CES43 = 69 | CES68 = 71 | CES93 = 83 |
| CES19 = 70 | CES44 = 98 | CES69 = 80 | CES94 = 60 |
| CES20 = 64 | CES45 = 79 | CES70 = 58 | CES95 = 73 |
| CES21 = 85 | CES46 = 78 | CES71 = 55 | CES96 = 79 |
| CES22 = 77 | CES47 = 76 | CES72 = 84 | CES97 = 84 |
| CES23 = 91 | CES48 = 68 | CES73 = 47 | CES98 = 73 |
| CES24 = 90 | CES49 = 78 | CES74 = 94 | CES99 = 62 |
| CES25 = 71 | CES50 = 87 | CES75 = 51 | |



REPORT NUMBER: SP1-1908-441-9-R4

TM-30-18

Color Rendition by Hue-Angle Bin



REPORT NUMBER: SP1-1908-441-9-R4

TM-30-18

Measure Comparisons



(END OF REPORT)