

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: McGRAW-EDISON

Report Number: P643816

Luminaire Tested: GWS-SA6F-760-U-SLL-W-HSS

Issue Date: 1/10/2023

Test Information

Test Method: LM-79-2019
Report Number: P643816
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2209-782-40)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/10/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: McGRAW-EDISON
Catalog Number: GWS-SAGF-760-U-SLL-W-HSS
Description: GALLEON WALL SLIM LUMINAIRE. (6) LIGHTSQUARES WITH 16 LEDS EACH AND
SPILL LIGHT ELIMINATOR LEFT OPTICS WITH HOUSE SIDE SHIELD
Light Source: (96) 5700K CCT, 70 CRI LEDS
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 30402.3 lumens
Efficiency: N/A
Efficacy: 81.6 lumens/watt
Luminous Opening: Rectangular (W 2' x L: 1' x H: 0')
IES Classification: Type III - Short
BUG Rating: B2 - U0 - G5


Input Watts (W): 372.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 0
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT



REPORT NUMBER: P643816
 CATALOG NUMBER: GWS-SA6F-760-U-SLL-W-HSS

Iso-Footcandle Lines of Horizontal Illumination


× Max cd
 - - - 1/2 Max cd



Based on 30 foot mounting height. Maximum calculated value = 6 fc
 Type III - Short - N/A

REPORT NUMBER: P643816
CATALOG NUMBER: GWS-SA6F-760-U-SLL-W-HSS

Luminous Intensity Polar Plot



— Vertical Plane Through 315-Deg Lateral - - - Horizontal Cone Through 62.5-Deg Vertical

REPORT NUMBER: P643816
 CATALOG NUMBER: GWS-SA6F-760-U-SLL-W-HSS

FLUX DISTRIBUTION:

| | | Downward | Upward | Total |
|--------------------|-----------|----------|--------|---------|
| House Side | Lumens | 3532.4 | 0.0 | 3532.4 |
| | % Fixture | 11.6 | 0.0 | 11.6 |
| Street Side | Lumens | 26870.0 | 0.0 | 26870.0 |
| | % Fixture | 88.4 | 0.0 | 88.4 |
| Total | Lumens | 30402.3 | 0.0 | 30402.3 |
| | % Fixture | 100.0 | 0.0 | 100.0 |

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|---------|-----------|
| 0°-10° | 136.1 | 0.4 |
| 10°-20° | 466.7 | 1.5 |
| 20°-30° | 1054.3 | 3.5 |
| 30°-40° | 1816.2 | 6.0 |
| 40°-50° | 3426.1 | 11.3 |
| 50°-60° | 7649.5 | 25.2 |
| 60°-70° | 10231.1 | 33.7 |
| 70°-80° | 5130.6 | 16.9 |
| 80°-90° | 491.8 | 1.6 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-90° | 30402.3 | 100.0 |
| 0°-180° | 30402.3 | 100.0 |

Coefficient of Utilization



REPORT NUMBER: P643816


CATALOG NUMBER: GWS-SA6F-760-U-SLL-W-HSS

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

| Zone | Lumens | % Fixture | Zone Rating/Lumen Limit | | |
|----------------|---------|-----------|-------------------------|------|---------|
| | | | B | U | G |
| FL (0°-30°) | 1138.6 | 3.7 | | | |
| FM (30°-60°) | 10808.9 | 35.6 | | | |
| FH (60°-80°) | 14463.4 | 47.6 | | | G5 |
| FVH (80°-90°) | 459.0 | 1.5 | | | G3/500 |
| BL (0°-30°) | 518.5 | 1.7 | B2/1000 | | |
| BM (30°-60°) | 2082.9 | 6.9 | B2/2500 | | |
| BH (60°-80°) | 898.3 | 3.0 | B2/1000 | | G2/1000 |
| BVH (80°-90°) | 32.7 | 0.1 | | | G1/100 |
| UL (90°-100°) | 0.0 | 0.0 | | U0/0 | |
| UH (100°-180°) | 0.0 | 0.0 | | U0/0 | |

BUG Rating: B2-U0-G5

Type III Short





REPORT NUMBER: P643816

CATALOG NUMBER: GWS-SA6F-760-U-SLL-W-HSS

CANDELA DISTRIBUTION (FULL):

| | 0° | 2° | 5° | 15° | 25° | 35° | 45° | 55° | 65° | 75° | 85° |
|-------|---------|---------|---------|---------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 1576.7 | 1576.7 | 1576.7 | 1576.7 | 1576.7 | 1576.7 | 1576.7 | 1576.7 | 1576.7 | 1576.7 | 1576.7 |
| 2.5° | 1558.7 | 1555.1 | 1547.9 | 1526.3 | 1508.3 | 1497.5 | 1475.9 | 1475.9 | 1472.3 | 1465.1 | 1450.7 |
| 5° | 1508.3 | 1493.9 | 1479.5 | 1439.9 | 1396.7 | 1371.5 | 1342.7 | 1339.1 | 1339.1 | 1331.9 | 1328.3 |
| 7.5° | 1429.1 | 1414.7 | 1396.7 | 1331.9 | 1292.3 | 1267.1 | 1241.9 | 1238.3 | 1227.5 | 1227.5 | 1227.5 |
| 10° | 1385.9 | 1364.3 | 1335.5 | 1263.5 | 1223.9 | 1202.3 | 1184.3 | 1173.5 | 1166.3 | 1155.5 | 1151.9 |
| 12.5° | 1479.5 | 1439.9 | 1378.7 | 1249.1 | 1195.1 | 1166.3 | 1144.7 | 1137.5 | 1115.9 | 1101.5 | 1090.7 |
| 15° | 1771.1 | 1673.9 | 1551.5 | 1281.5 | 1184.3 | 1141.1 | 1112.3 | 1097.9 | 1079.9 | 1054.7 | 1036.7 |
| 17.5° | 2249.9 | 2109.5 | 1904.3 | 1385.9 | 1173.5 | 1119.5 | 1083.5 | 1058.3 | 1033.1 | 1004.3 | 982.7 |
| 20° | 2912.2 | 2703.4 | 2458.7 | 1576.7 | 1173.5 | 1094.3 | 1051.1 | 1018.7 | 982.7 | 950.3 | 925.1 |
| 22.5° | 3754.6 | 3545.8 | 3128.2 | 1900.7 | 1187.9 | 1061.9 | 1011.5 | 968.3 | 925.1 | 896.3 | 867.5 |
| 25° | 4697.7 | 4402.5 | 4013.8 | 2293.1 | 1227.5 | 1018.7 | 964.7 | 921.5 | 881.9 | 846.0 | 813.6 |
| 27.5° | 5748.9 | 5428.5 | 4910.1 | 2851.0 | 1313.9 | 975.5 | 914.3 | 874.7 | 838.8 | 802.8 | 759.6 |
| 30° | 6717.2 | 6526.4 | 5997.2 | 3520.6 | 1454.3 | 946.7 | 874.7 | 838.8 | 802.8 | 756.0 | 716.4 |
| 32.5° | 7879.9 | 7541.6 | 7106.0 | 4283.7 | 1641.5 | 917.9 | 842.4 | 792.0 | 763.2 | 720.0 | 676.8 |
| 35° | 9049.9 | 8761.9 | 8189.5 | 5223.3 | 1850.3 | 889.1 | 802.8 | 756.0 | 730.8 | 680.4 | 633.6 |
| 37.5° | 10255.8 | 10191.0 | 9625.8 | 6263.6 | 2055.5 | 856.7 | 756.0 | 727.2 | 702.0 | 644.4 | 590.4 |
| 40° | 11443.7 | 11324.9 | 10803.0 | 7451.6 | 2181.5 | 820.8 | 716.4 | 698.4 | 669.6 | 604.8 | 543.6 |
| 42.5° | 12581.3 | 12491.3 | 11983.7 | 8589.1 | 2163.5 | 788.4 | 676.8 | 655.2 | 633.6 | 568.8 | 493.2 |
| 45° | 13978.0 | 13830.4 | 13189.6 | 9431.4 | 1979.9 | 824.4 | 637.2 | 601.2 | 597.6 | 536.4 | 442.8 |
| 47.5° | 16591.4 | 16105.4 | 15018.3 | 10079.4 | 1796.3 | 917.9 | 594.0 | 550.8 | 576.0 | 504.0 | 392.4 |
| 50° | 20252.4 | 19680.0 | 18106.9 | 10583.4 | 1792.7 | 1040.3 | 586.8 | 504.0 | 558.0 | 478.8 | 349.2 |
| 52.5° | 23931.4 | 22923.4 | 21012.0 | 10853.4 | 1925.9 | 1130.3 | 651.6 | 457.2 | 536.4 | 453.6 | 316.8 |
| 55° | 27455.6 | 25364.1 | 22228.7 | 9960.6 | 2030.3 | 1227.5 | 770.4 | 432.0 | 496.8 | 424.8 | 298.8 |
| 57.5° | 30814.2 | 27326.0 | 22757.9 | 7879.9 | 2379.5 | 1267.1 | 842.4 | 442.8 | 439.2 | 388.8 | 284.4 |
| 60° | 31275.0 | 27232.4 | 21688.7 | 4582.5 | 2624.2 | 1198.7 | 813.6 | 493.2 | 385.2 | 345.6 | 259.2 |
| 62.5° | 29532.7 | 25421.7 | 19251.7 | 2858.2 | 2437.1 | 1173.5 | 723.6 | 561.6 | 349.2 | 306.0 | 226.8 |
| 65° | 26886.8 | 22581.5 | 16051.5 | 1843.1 | 1846.7 | 1303.1 | 633.6 | 550.8 | 327.6 | 270.0 | 194.4 |
| 67.5° | 22750.7 | 18898.9 | 12646.1 | 1234.7 | 1043.9 | 1112.3 | 554.4 | 378.0 | 320.4 | 230.4 | 151.2 |
| 70° | 16605.8 | 13452.4 | 8232.7 | 824.4 | 622.8 | 889.1 | 464.4 | 270.0 | 302.4 | 190.8 | 108.0 |
| 72.5° | 12138.5 | 9039.1 | 4596.9 | 540.0 | 352.8 | 518.4 | 342.0 | 194.4 | 234.0 | 140.4 | 75.6 |
| 75° | 8736.7 | 6220.4 | 2624.2 | 345.6 | 234.0 | 284.4 | 223.2 | 133.2 | 151.2 | 111.6 | 68.4 |
| 77.5° | 4204.6 | 3031.0 | 1191.5 | 190.8 | 158.4 | 144.0 | 118.8 | 82.8 | 93.6 | 100.8 | 61.2 |
| 80° | 158.4 | 118.8 | 90.0 | 93.6 | 100.8 | 64.8 | 54.0 | 43.2 | 54.0 | 68.4 | 32.4 |
| 82.5° | 0.0 | 0.0 | 0.0 | 10.8 | 14.4 | 18.0 | 21.6 | 18.0 | 21.6 | 25.2 | 3.6 |
| 85° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 87.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P643816

CATALOG NUMBER: GWS-SA6F-760-U-SLL-W-HSS

CANDELA DISTRIBUTION (continued):

| | 90° | 95° | 105° | 115° | 125° | 135° | 145° | 155° | 165° | 175° | 180° |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 1576.7 | 1576.7 | 1576.7 | 1576.7 | 1576.7 | 1576.7 | 1576.7 | 1576.7 | 1576.7 | 1576.7 | 1576.7 |
| 2.5° | 1461.5 | 1454.3 | 1461.5 | 1468.7 | 1475.9 | 1483.1 | 1472.3 | 1479.5 | 1486.7 | 1468.7 | 1475.9 |
| 5° | 1346.3 | 1342.7 | 1364.3 | 1375.1 | 1389.5 | 1396.7 | 1389.5 | 1389.5 | 1385.9 | 1364.3 | 1364.3 |
| 7.5° | 1245.5 | 1249.1 | 1267.1 | 1292.3 | 1310.3 | 1321.1 | 1313.9 | 1310.3 | 1299.5 | 1267.1 | 1267.1 |
| 10° | 1169.9 | 1169.9 | 1198.7 | 1220.3 | 1245.5 | 1256.3 | 1249.1 | 1238.3 | 1227.5 | 1195.1 | 1191.5 |
| 12.5° | 1108.7 | 1108.7 | 1130.3 | 1166.3 | 1195.1 | 1209.5 | 1205.9 | 1191.5 | 1173.5 | 1141.1 | 1137.5 |
| 15° | 1051.1 | 1047.5 | 1079.9 | 1112.3 | 1151.9 | 1169.9 | 1162.7 | 1151.9 | 1119.5 | 1090.7 | 1083.5 |
| 17.5° | 993.5 | 989.9 | 1018.7 | 1061.9 | 1105.1 | 1130.3 | 1126.7 | 1101.5 | 1072.7 | 1036.7 | 1029.5 |
| 20° | 935.9 | 928.7 | 964.7 | 1007.9 | 1051.1 | 1076.3 | 1069.1 | 1047.5 | 1011.5 | 975.5 | 968.3 |
| 22.5° | 878.3 | 874.7 | 899.9 | 935.9 | 975.5 | 997.1 | 993.5 | 975.5 | 939.5 | 907.1 | 907.1 |
| 25° | 813.6 | 813.6 | 831.6 | 856.7 | 885.5 | 896.3 | 899.9 | 892.7 | 871.1 | 853.1 | 853.1 |
| 27.5° | 759.6 | 748.8 | 756.0 | 763.2 | 777.6 | 795.6 | 795.6 | 802.8 | 806.4 | 799.2 | 802.8 |
| 30° | 716.4 | 698.4 | 687.6 | 673.2 | 666.0 | 673.2 | 680.4 | 705.6 | 730.8 | 745.2 | 752.4 |
| 32.5° | 666.0 | 644.4 | 615.6 | 576.0 | 550.8 | 543.6 | 565.2 | 612.0 | 658.8 | 691.2 | 709.2 |
| 35° | 615.6 | 586.8 | 532.8 | 475.2 | 442.8 | 432.0 | 457.2 | 511.2 | 579.6 | 637.2 | 662.4 |
| 37.5° | 565.2 | 525.6 | 450.0 | 381.6 | 345.6 | 338.4 | 363.6 | 421.2 | 500.4 | 579.6 | 612.0 |
| 40° | 507.6 | 460.8 | 370.8 | 298.8 | 270.0 | 262.8 | 284.4 | 342.0 | 424.8 | 514.8 | 565.2 |
| 42.5° | 450.0 | 392.4 | 298.8 | 237.6 | 208.8 | 208.8 | 237.6 | 280.8 | 356.4 | 453.6 | 514.8 |
| 45° | 392.4 | 331.2 | 244.8 | 190.8 | 172.8 | 176.4 | 194.4 | 237.6 | 298.8 | 399.6 | 457.2 |
| 47.5° | 338.4 | 284.4 | 201.6 | 158.4 | 144.0 | 147.6 | 169.2 | 205.2 | 255.6 | 345.6 | 406.8 |
| 50° | 291.6 | 241.2 | 176.4 | 133.2 | 122.4 | 129.6 | 151.2 | 183.6 | 226.8 | 306.0 | 356.4 |
| 52.5° | 262.8 | 216.0 | 162.0 | 115.2 | 108.0 | 115.2 | 136.8 | 165.6 | 205.2 | 270.0 | 320.4 |
| 55° | 248.4 | 212.4 | 162.0 | 104.4 | 93.6 | 100.8 | 122.4 | 151.2 | 183.6 | 244.8 | 288.0 |
| 57.5° | 244.8 | 219.6 | 172.8 | 93.6 | 79.2 | 86.4 | 108.0 | 136.8 | 169.2 | 223.2 | 259.2 |
| 60° | 230.4 | 208.8 | 169.2 | 75.6 | 61.2 | 72.0 | 90.0 | 118.8 | 154.8 | 208.8 | 241.2 |
| 62.5° | 201.6 | 183.6 | 147.6 | 61.2 | 46.8 | 54.0 | 75.6 | 104.4 | 140.4 | 190.8 | 226.8 |
| 65° | 165.6 | 147.6 | 115.2 | 39.6 | 28.8 | 36.0 | 57.6 | 90.0 | 122.4 | 172.8 | 205.2 |
| 67.5° | 122.4 | 104.4 | 79.2 | 25.2 | 14.4 | 25.2 | 46.8 | 75.6 | 111.6 | 154.8 | 187.2 |
| 70° | 75.6 | 61.2 | 43.2 | 14.4 | 10.8 | 21.6 | 43.2 | 72.0 | 100.8 | 144.0 | 176.4 |
| 72.5° | 43.2 | 28.8 | 18.0 | 7.2 | 10.8 | 21.6 | 43.2 | 72.0 | 97.2 | 136.8 | 165.6 |
| 75° | 32.4 | 18.0 | 7.2 | 3.6 | 7.2 | 18.0 | 39.6 | 64.8 | 93.6 | 129.6 | 158.4 |
| 77.5° | 21.6 | 10.8 | 3.6 | 0.0 | 3.6 | 14.4 | 36.0 | 61.2 | 86.4 | 122.4 | 151.2 |
| 80° | 3.6 | 0.0 | 0.0 | 0.0 | 0.0 | 10.8 | 32.4 | 54.0 | 79.2 | 108.0 | 133.2 |
| 82.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 3.6 | 25.2 | 46.8 | 68.4 | 90.0 | 108.0 |
| 85° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 14.4 | 36.0 | 54.0 | 68.4 | 75.6 |
| 87.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 18.0 | 36.0 | 43.2 | 50.4 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P643816

CATALOG NUMBER: GWS-SA6F-760-U-SLL-W-HSS

CANDELA DISTRIBUTION (continued):

| | 185° | 195° | 205° | 215° | 225° | 235° | 245° | 255° | 265° | 270° | 275° |
|-------|--------|--------|--------|--------|--------|--------|--------|---------|---------|---------|---------|
| 0° | 1576.7 | 1576.7 | 1576.7 | 1576.7 | 1576.7 | 1576.7 | 1576.7 | 1576.7 | 1576.7 | 1576.7 | 1576.7 |
| 2.5° | 1472.3 | 1493.9 | 1493.9 | 1508.3 | 1526.3 | 1558.7 | 1576.7 | 1601.9 | 1619.9 | 1637.9 | 1645.1 |
| 5° | 1360.7 | 1364.3 | 1367.9 | 1375.1 | 1396.7 | 1432.7 | 1465.1 | 1504.7 | 1551.5 | 1587.5 | 1609.1 |
| 7.5° | 1267.1 | 1267.1 | 1267.1 | 1277.9 | 1299.5 | 1324.7 | 1357.1 | 1411.1 | 1465.1 | 1508.3 | 1544.3 |
| 10° | 1187.9 | 1198.7 | 1202.3 | 1220.3 | 1245.5 | 1277.9 | 1313.9 | 1360.7 | 1421.9 | 1479.5 | 1544.3 |
| 12.5° | 1137.5 | 1148.3 | 1166.3 | 1184.3 | 1209.5 | 1245.5 | 1285.1 | 1346.3 | 1472.3 | 1591.1 | 1727.9 |
| 15° | 1090.7 | 1105.1 | 1126.7 | 1151.9 | 1180.7 | 1220.3 | 1263.5 | 1389.5 | 1684.7 | 1907.9 | 2123.9 |
| 17.5° | 1040.3 | 1061.9 | 1090.7 | 1115.9 | 1151.9 | 1195.1 | 1249.1 | 1493.9 | 2073.5 | 2444.3 | 2811.4 |
| 20° | 975.5 | 1004.3 | 1036.7 | 1076.3 | 1119.5 | 1169.9 | 1249.1 | 1709.9 | 2635.0 | 3167.8 | 3653.8 |
| 22.5° | 914.3 | 943.1 | 982.7 | 1033.1 | 1083.5 | 1133.9 | 1267.1 | 2037.5 | 3358.6 | 4031.8 | 4647.3 |
| 25° | 863.9 | 899.9 | 939.5 | 982.7 | 1040.3 | 1097.9 | 1310.3 | 2498.3 | 4229.8 | 5097.3 | 5532.9 |
| 27.5° | 817.2 | 860.3 | 899.9 | 935.9 | 986.3 | 1051.1 | 1407.5 | 3113.8 | 5259.3 | 6141.2 | 6483.2 |
| 30° | 770.4 | 820.8 | 860.3 | 896.3 | 946.7 | 1015.1 | 1555.1 | 3898.6 | 6404.0 | 7260.8 | 7296.8 |
| 32.5° | 730.8 | 777.6 | 824.4 | 860.3 | 907.1 | 986.3 | 1760.3 | 4816.5 | 7577.6 | 8405.5 | 8067.1 |
| 35° | 687.6 | 741.6 | 784.8 | 824.4 | 874.7 | 961.1 | 1997.9 | 5806.5 | 8761.9 | 9456.6 | 8833.9 |
| 37.5° | 644.4 | 705.6 | 759.6 | 788.4 | 838.8 | 935.9 | 2170.7 | 6839.6 | 9971.4 | 10482.6 | 9507.0 |
| 40° | 604.8 | 673.2 | 734.4 | 763.2 | 788.4 | 903.5 | 2195.9 | 7897.9 | 11198.9 | 11494.1 | 10140.6 |
| 42.5° | 561.6 | 637.2 | 691.2 | 730.8 | 752.4 | 881.9 | 2044.7 | 8790.7 | 12228.5 | 12502.1 | 10968.6 |
| 45° | 514.8 | 604.8 | 648.0 | 676.8 | 720.0 | 896.3 | 1850.3 | 9481.8 | 13405.6 | 13877.2 | 12332.9 |
| 47.5° | 468.0 | 568.8 | 604.8 | 626.4 | 684.0 | 982.7 | 1778.3 | 9942.6 | 15345.9 | 16325.0 | 14633.1 |
| 50° | 424.8 | 536.4 | 576.0 | 572.4 | 676.8 | 1094.3 | 1857.5 | 10291.8 | 18261.7 | 19413.7 | 17786.6 |
| 52.5° | 378.0 | 500.4 | 547.2 | 532.8 | 730.8 | 1180.7 | 2015.9 | 10569.0 | 20504.4 | 23035.0 | 22023.5 |
| 55° | 338.4 | 460.8 | 504.0 | 500.4 | 831.6 | 1245.5 | 2138.3 | 9107.5 | 21433.1 | 26400.8 | 26796.8 |
| 57.5° | 309.6 | 417.6 | 453.6 | 514.8 | 896.3 | 1245.5 | 2473.1 | 6465.2 | 21451.1 | 28877.5 | 33132.4 |
| 60° | 284.4 | 378.0 | 403.2 | 565.2 | 871.1 | 1180.7 | 2447.9 | 3959.8 | 19770.0 | 28708.3 | 36501.8 |
| 62.5° | 262.8 | 342.0 | 374.4 | 579.6 | 770.4 | 1169.9 | 2210.3 | 2455.1 | 16861.4 | 26523.2 | 34057.6 |
| 65° | 244.8 | 313.2 | 360.0 | 532.8 | 698.4 | 1252.7 | 1490.3 | 1763.9 | 13675.6 | 24032.2 | 31253.4 |
| 67.5° | 226.8 | 288.0 | 381.6 | 435.6 | 633.6 | 1119.5 | 1076.3 | 1252.7 | 10734.6 | 21299.9 | 28679.5 |
| 70° | 212.4 | 273.6 | 403.2 | 356.4 | 554.4 | 874.7 | 763.2 | 950.3 | 8218.3 | 17772.2 | 25054.5 |
| 72.5° | 201.6 | 255.6 | 338.4 | 280.8 | 450.0 | 676.8 | 532.8 | 691.2 | 5370.9 | 13873.6 | 20425.2 |
| 75° | 190.8 | 234.0 | 248.4 | 226.8 | 334.8 | 442.8 | 403.2 | 464.4 | 3200.2 | 10140.6 | 15497.1 |
| 77.5° | 187.2 | 219.6 | 201.6 | 183.6 | 226.8 | 262.8 | 306.0 | 313.2 | 1562.3 | 5072.1 | 8121.1 |
| 80° | 165.6 | 198.0 | 172.8 | 151.2 | 154.8 | 172.8 | 226.8 | 208.8 | 356.4 | 1288.7 | 2167.1 |
| 82.5° | 129.6 | 154.8 | 144.0 | 126.0 | 126.0 | 126.0 | 151.2 | 140.4 | 115.2 | 579.6 | 979.1 |
| 85° | 90.0 | 108.0 | 108.0 | 100.8 | 97.2 | 97.2 | 93.6 | 90.0 | 32.4 | 36.0 | 54.0 |
| 87.5° | 61.2 | 75.6 | 79.2 | 75.6 | 64.8 | 57.6 | 50.4 | 43.2 | 14.4 | 0.0 | 7.2 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P643816

CATALOG NUMBER: GWS-SA6F-760-U-SLL-W-HSS

CANDELA DISTRIBUTION (continued):

| | 285° | 295° | 305° | 315° | 325° | 335° | 345° | 355° | 358° | 360° |
|-------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|
| 0° | 1576.7 | 1576.7 | 1576.7 | 1576.7 | 1576.7 | 1576.7 | 1576.7 | 1576.7 | 1576.7 | 1576.7 |
| 2.5° | 1670.3 | 1681.1 | 1681.1 | 1666.7 | 1655.9 | 1627.1 | 1598.3 | 1569.5 | 1562.3 | 1558.7 |
| 5° | 1670.3 | 1713.5 | 1735.1 | 1731.5 | 1706.3 | 1659.5 | 1598.3 | 1533.5 | 1515.5 | 1508.3 |
| 7.5° | 1645.1 | 1727.9 | 1792.7 | 1803.5 | 1756.7 | 1673.9 | 1562.3 | 1465.1 | 1439.9 | 1429.1 |
| 10° | 1702.7 | 1864.7 | 1994.3 | 2012.3 | 1958.3 | 1796.3 | 1616.3 | 1450.7 | 1411.1 | 1385.9 |
| 12.5° | 2012.3 | 2278.7 | 2437.1 | 2512.7 | 2408.3 | 2203.1 | 1904.3 | 1609.1 | 1519.1 | 1479.5 |
| 15° | 2638.6 | 3016.6 | 3319.0 | 3319.0 | 3221.8 | 2858.2 | 2480.3 | 2001.5 | 1879.1 | 1771.1 |
| 17.5° | 3441.4 | 3916.6 | 4183.0 | 4154.2 | 4006.6 | 3751.0 | 3297.4 | 2609.8 | 2361.5 | 2249.9 |
| 20° | 4355.7 | 4640.1 | 4701.3 | 4683.3 | 4618.5 | 4470.9 | 4157.8 | 3419.8 | 3085.0 | 2912.2 |
| 22.5° | 5147.7 | 5072.1 | 4982.1 | 4910.1 | 4892.1 | 4935.3 | 4892.1 | 4323.3 | 4060.6 | 3754.6 |
| 25° | 5684.1 | 5255.7 | 4985.7 | 4856.1 | 4917.3 | 5165.7 | 5435.7 | 5223.3 | 5014.5 | 4697.7 |
| 27.5° | 5975.6 | 5234.1 | 4845.3 | 4712.1 | 4816.5 | 5169.3 | 5756.1 | 6116.0 | 5900.1 | 5748.9 |
| 30° | 6134.0 | 5216.1 | 4755.3 | 4625.7 | 4784.1 | 5226.9 | 5979.2 | 6951.2 | 6958.4 | 6717.2 |
| 32.5° | 6360.8 | 5331.3 | 4773.3 | 4654.5 | 4866.9 | 5399.7 | 6260.0 | 7800.7 | 8009.5 | 7879.9 |
| 35° | 6616.4 | 5507.7 | 4856.1 | 4748.1 | 5010.9 | 5630.1 | 6573.2 | 8657.5 | 9093.1 | 9049.9 |
| 37.5° | 6857.6 | 5705.7 | 5050.5 | 4946.1 | 5230.5 | 5828.1 | 6875.6 | 9499.8 | 10104.6 | 10255.8 |
| 40° | 7109.6 | 5982.8 | 5648.1 | 5748.9 | 5907.3 | 6141.2 | 7145.6 | 10230.6 | 11216.9 | 11443.7 |
| 42.5° | 7703.5 | 6944.0 | 7455.2 | 7645.9 | 7667.5 | 7185.2 | 7735.9 | 11166.5 | 12311.3 | 12581.3 |
| 45° | 9028.3 | 8653.9 | 10119.0 | 10389.0 | 10248.6 | 8787.1 | 9157.9 | 12516.5 | 13841.2 | 13978.0 |
| 47.5° | 10702.2 | 10875.0 | 13765.6 | 14697.9 | 13855.6 | 10677.0 | 10882.2 | 15356.7 | 16641.8 | 16591.4 |
| 50° | 12653.3 | 13470.4 | 17905.3 | 20104.8 | 18088.9 | 13132.0 | 12869.2 | 18848.5 | 20407.2 | 20252.4 |
| 52.5° | 14960.7 | 16487.0 | 22880.2 | 26004.9 | 24097.0 | 15893.1 | 15785.1 | 23474.2 | 24424.6 | 23931.4 |
| 55° | 17865.7 | 19399.3 | 28603.9 | 32970.5 | 30256.2 | 19262.5 | 19633.2 | 28837.9 | 29021.5 | 27455.6 |
| 57.5° | 22199.9 | 23197.0 | 35349.9 | 40958.4 | 36685.4 | 23841.4 | 26530.4 | 35976.3 | 33780.4 | 30814.2 |
| 60° | 30069.0 | 28081.9 | 41869.1 | 49129.9 | 43525.0 | 30281.4 | 35627.1 | 40206.0 | 35364.3 | 31275.0 |
| 62.5° | 32808.5 | 32228.9 | 45951.3 | 52585.7 | 48125.6 | 35569.5 | 37992.2 | 37808.6 | 33312.4 | 29532.7 |
| 65° | 28657.9 | 31195.8 | 45220.5 | 50760.6 | 47535.2 | 34698.4 | 34093.6 | 35162.7 | 31001.4 | 26886.8 |
| 67.5° | 26472.8 | 28769.5 | 42452.3 | 45724.5 | 44263.0 | 31742.9 | 30389.4 | 30097.8 | 26026.5 | 22750.7 |
| 70° | 24269.8 | 26544.8 | 38438.5 | 38845.3 | 38164.9 | 26926.4 | 25148.1 | 23193.4 | 19453.3 | 16605.8 |
| 72.5° | 21620.3 | 22873.1 | 32869.7 | 30940.2 | 30169.8 | 21148.8 | 20774.4 | 17466.2 | 14582.7 | 12138.5 |
| 75° | 18855.7 | 18492.1 | 25626.9 | 21235.1 | 21811.1 | 16454.6 | 17545.4 | 12826.0 | 10684.2 | 8736.7 |
| 77.5° | 13715.2 | 13445.2 | 17163.8 | 12898.0 | 14284.0 | 10777.8 | 9683.4 | 5118.9 | 4874.1 | 4204.6 |
| 80° | 7653.1 | 9226.3 | 9269.5 | 7228.4 | 9017.5 | 7026.8 | 2422.7 | 169.2 | 108.0 | 158.4 |
| 82.5° | 3556.6 | 3967.0 | 5025.3 | 3351.4 | 5144.1 | 3481.0 | 500.4 | 0.0 | 0.0 | 0.0 |
| 85° | 1151.9 | 1684.7 | 1411.1 | 493.2 | 1245.5 | 1177.1 | 82.8 | 0.0 | 0.0 | 0.0 |
| 87.5° | 68.4 | 140.4 | 36.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



LM-79-2008: Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGRAW-EDISON

Report Number: SP1-1908-441-9-R4

Test Date: 10/23/2019

Luminaire Tested: SA1C-760-U-5WQ

Data in this report applies to families of products SA1C-760-U-5WQ .

Test Information

Test Method: LM-79-2008
 Report Number: SP1-1908-441-9-R4
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 10/28/2024
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: McGRAW-EDISON
 Catalog Number: **SA1C-760-U-5WQ**
 Description: McGRAW EDISON ROADWAY AND AREA LUMINAIRE

THIS IS A REVISION OF SP1-1908-441-4-R3. TO UPDATE THE CATALOG INFORMATION.TESTED IN SITU. ROADWAY AND AREA LUMINAIRE. (1) 70 CRI, 5000K, 1050MA LIGHTSQUARE WITH 16 LEDS AND TYPE V WIDE OPTICS.

Spectral Parameters

| | | | | | |
|---------------------------|--------|-----------|------|------|-------|
| CCT (K): | 5474 | CRI (Ra): | 71.7 | R9: | -27.1 |
| CIE u': | 0.2052 | R1: | 70.6 | R10: | 40.8 |
| CIE v': | 0.4804 | R2: | 74.6 | R11: | 74.6 |
| Duv: | 0.0025 | R3: | 78.3 | R12: | 50.4 |
| CIE x: | 0.3330 | R4: | 73.8 | R13: | 70.0 |
| CIE y: | 0.3466 | R5: | 72.4 | R14: | 87.8 |
| CIE z: | 0.3204 | R6: | 67.5 | | |
| Peak Wavelength (nm): | 442 | R7: | 77.5 | | |
| Dominant Wavelength (nm): | 554 | R8: | 58.9 | | |
| Purity: | 4.1 | | | | |
| Rf: | 72.1 | | | | |
| Rg: | 97.2 | | | | |



Test Conditions

Stabilization Time: 240M
 Operation Time: 12H
 Room Temperature (°C) / RH%: 24.6/31%
 Sphere Temperature (°C): 25.9

REPORT NUMBER: SP1-1908-441-9-R4

| Measurement and Test Equipment | | | |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument | Identification Number | Calibration Date | Calibration Due Date |
| Photometer | IN0058 | 6/28/2019 | 12/28/2019 |
| Power Meter | IN0071 | 12/5/2018 | 12/5/2019 |
| AC Power Source | IN0063 | 12/5/2018 | 12/5/2019 |
| DC Power Source | IN0208 | 12/5/2018 | 12/5/2019 |
| Sphere Thermometer | IN0085 | 12/5/2018 | 12/5/2019 |
| Room Thermometer | IN0046 | 12/5/2018 | 12/5/2019 |

REPORT NUMBER: SP1-1908-441-9-R4

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 5700K 4-step quadrangle

REPORT NUMBER: SP1-1908-441-9-R4

Photopic Flux vs. Wavelength



#####

| λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) |
|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|
| 360 | 3540 | NR | 490 | 33363 | NR | 620 | 80193 | NR | 750 | 4663 | NR | 880 | 4678 | NR |
| 365 | 2862 | NR | 495 | 44177 | NR | 625 | 73091 | NR | 755 | 4147 | NR | 885 | 4128 | NR |
| 370 | 2865 | NR | 500 | 57019 | NR | 630 | 66269 | NR | 760 | 4040 | NR | 890 | 4504 | NR |
| 375 | 3254 | NR | 505 | 70030 | NR | 635 | 60012 | NR | 765 | 3474 | NR | 895 | 4371 | NR |
| 380 | 3076 | NR | 510 | 81972 | NR | 640 | 53914 | NR | 770 | 3469 | NR | 900 | 4082 | NR |
| 385 | 2904 | NR | 515 | 92590 | NR | 645 | 48385 | NR | 775 | 3181 | NR | 905 | 2982 | NR |
| 390 | 2689 | NR | 520 | 100305 | NR | 650 | 43219 | NR | 780 | 2969 | NR | 910 | 4351 | NR |
| 395 | 2619 | NR | 525 | 107452 | NR | 655 | 38562 | NR | 785 | 3132 | NR | 915 | 3365 | NR |
| 400 | 2679 | NR | 530 | 111373 | NR | 660 | 34110 | NR | 790 | 2507 | NR | 920 | 3430 | NR |
| 405 | 3515 | NR | 535 | 114505 | NR | 665 | 30085 | NR | 795 | 2968 | NR | 925 | 4264 | NR |
| 410 | 6934 | NR | 540 | 116408 | NR | 670 | 26205 | NR | 800 | 2758 | NR | 930 | 4095 | NR |
| 415 | 14943 | NR | 545 | 118700 | NR | 675 | 22906 | NR | 805 | 2872 | NR | 935 | 5048 | NR |
| 420 | 31939 | NR | 550 | 119209 | NR | 680 | 20058 | NR | 810 | 3094 | NR | 940 | 4074 | NR |
| 425 | 64701 | NR | 555 | 120742 | NR | 685 | 17413 | NR | 815 | 3222 | NR | 945 | 4949 | NR |
| 430 | 110939 | NR | 560 | 121594 | NR | 690 | 15447 | NR | 820 | 3238 | NR | 950 | 4387 | NR |
| 435 | 164597 | NR | 565 | 121913 | NR | 695 | 13398 | NR | 825 | 3524 | NR | 955 | 4978 | NR |
| 440 | 207696 | NR | 570 | 122147 | NR | 700 | 11777 | NR | 830 | 2921 | NR | 960 | 4706 | NR |
| 445 | 201830 | NR | 575 | 121605 | NR | 705 | 10412 | NR | 835 | 3595 | NR | 965 | 5083 | NR |
| 450 | 145410 | NR | 580 | 120248 | NR | 710 | 9544 | NR | 840 | 3016 | NR | 970 | 4522 | NR |
| 455 | 89594 | NR | 585 | 117717 | NR | 715 | 8940 | NR | 845 | 4032 | NR | 975 | 4740 | NR |
| 460 | 58321 | NR | 590 | 114359 | NR | 720 | 7897 | NR | 850 | 3579 | NR | 980 | 6122 | NR |
| 465 | 39318 | NR | 595 | 109974 | NR | 725 | 7045 | NR | 855 | 4571 | NR | 985 | 6450 | NR |
| 470 | 27693 | NR | 600 | 105269 | NR | 730 | 6483 | NR | 860 | 4485 | NR | 990 | 4875 | NR |
| 475 | 23081 | NR | 605 | 99453 | NR | 735 | 5838 | NR | 865 | 3978 | NR | 995 | 4764 | NR |
| 480 | 23002 | NR | 610 | 92921 | NR | 740 | 5261 | NR | 870 | 4298 | NR | 1000 | 3640 | NR |
| 485 | 26201 | NR | 615 | 86989 | NR | 745 | 4760 | NR | 875 | 4356 | NR | | | |

REPORT NUMBER: SP1-1908-441-9-R4

Scotopic Flux vs. Wavelength



Scotopic Lumens: 13759.3 S/P: 1.85

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 3540 | NR | 490 | 33363 | NR | 620 | 80193 | NR | 750 | 4663 | NR | 880 | 4678 | NR |
| 365 | 2862 | NR | 495 | 44177 | NR | 625 | 73091 | NR | 755 | 4147 | NR | 885 | 4128 | NR |
| 370 | 2865 | NR | 500 | 57019 | NR | 630 | 66269 | NR | 760 | 4040 | NR | 890 | 4504 | NR |
| 375 | 3254 | NR | 505 | 70030 | NR | 635 | 60012 | NR | 765 | 3474 | NR | 895 | 4371 | NR |
| 380 | 3076 | NR | 510 | 81972 | NR | 640 | 53914 | NR | 770 | 3469 | NR | 900 | 4082 | NR |
| 385 | 2904 | NR | 515 | 92590 | NR | 645 | 48385 | NR | 775 | 3181 | NR | 905 | 2982 | NR |
| 390 | 2689 | NR | 520 | 100305 | NR | 650 | 43219 | NR | 780 | 2969 | NR | 910 | 4351 | NR |
| 395 | 2619 | NR | 525 | 107452 | NR | 655 | 38562 | NR | 785 | 3132 | NR | 915 | 3365 | NR |
| 400 | 2679 | NR | 530 | 111373 | NR | 660 | 34110 | NR | 790 | 2507 | NR | 920 | 3430 | NR |
| 405 | 3515 | NR | 535 | 114505 | NR | 665 | 30085 | NR | 795 | 2968 | NR | 925 | 4264 | NR |
| 410 | 6934 | NR | 540 | 116408 | NR | 670 | 26205 | NR | 800 | 2758 | NR | 930 | 4095 | NR |
| 415 | 14943 | NR | 545 | 118700 | NR | 675 | 22906 | NR | 805 | 2872 | NR | 935 | 5048 | NR |
| 420 | 31939 | NR | 550 | 119209 | NR | 680 | 20058 | NR | 810 | 3094 | NR | 940 | 4074 | NR |
| 425 | 64701 | NR | 555 | 120742 | NR | 685 | 17413 | NR | 815 | 3222 | NR | 945 | 4949 | NR |
| 430 | 110939 | NR | 560 | 121594 | NR | 690 | 15447 | NR | 820 | 3238 | NR | 950 | 4387 | NR |
| 435 | 164597 | NR | 565 | 121913 | NR | 695 | 13398 | NR | 825 | 3524 | NR | 955 | 4978 | NR |
| 440 | 207696 | NR | 570 | 122147 | NR | 700 | 11777 | NR | 830 | 2921 | NR | 960 | 4706 | NR |
| 445 | 201830 | NR | 575 | 121605 | NR | 705 | 10412 | NR | 835 | 3595 | NR | 965 | 5083 | NR |
| 450 | 145410 | NR | 580 | 120248 | NR | 710 | 9544 | NR | 840 | 3016 | NR | 970 | 4522 | NR |
| 455 | 89594 | NR | 585 | 117717 | NR | 715 | 8940 | NR | 845 | 4032 | NR | 975 | 4740 | NR |
| 460 | 58321 | NR | 590 | 114359 | NR | 720 | 7897 | NR | 850 | 3579 | NR | 980 | 6122 | NR |
| 465 | 39318 | NR | 595 | 109974 | NR | 725 | 7045 | NR | 855 | 4571 | NR | 985 | 6450 | NR |
| 470 | 27693 | NR | 600 | 105269 | NR | 730 | 6483 | NR | 860 | 4485 | NR | 990 | 4875 | NR |
| 475 | 23081 | NR | 605 | 99453 | NR | 735 | 5838 | NR | 865 | 3978 | NR | 995 | 4764 | NR |
| 480 | 23002 | NR | 610 | 92921 | NR | 740 | 5261 | NR | 870 | 4298 | NR | 1000 | 3640 | NR |
| 485 | 26201 | NR | 615 | 86989 | NR | 745 | 4760 | NR | 875 | 4356 | NR | | | |

REPORT NUMBER: SP1-1908-441-9-R4

Melanopic Flux vs. Wavelength



Melanopic Lumens: 5527.6 M/P: 0.74

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 3540 | NR | 490 | 33363 | NR | 620 | 80193 | NR | 750 | 4663 | NR | 880 | 4678 | NR |
| 365 | 2862 | NR | 495 | 44177 | NR | 625 | 73091 | NR | 755 | 4147 | NR | 885 | 4128 | NR |
| 370 | 2865 | NR | 500 | 57019 | NR | 630 | 66269 | NR | 760 | 4040 | NR | 890 | 4504 | NR |
| 375 | 3254 | NR | 505 | 70030 | NR | 635 | 60012 | NR | 765 | 3474 | NR | 895 | 4371 | NR |
| 380 | 3076 | NR | 510 | 81972 | NR | 640 | 53914 | NR | 770 | 3469 | NR | 900 | 4082 | NR |
| 385 | 2904 | NR | 515 | 92590 | NR | 645 | 48385 | NR | 775 | 3181 | NR | 905 | 2982 | NR |
| 390 | 2689 | NR | 520 | 100305 | NR | 650 | 43219 | NR | 780 | 2969 | NR | 910 | 4351 | NR |
| 395 | 2619 | NR | 525 | 107452 | NR | 655 | 38562 | NR | 785 | 3132 | NR | 915 | 3365 | NR |
| 400 | 2679 | NR | 530 | 111373 | NR | 660 | 34110 | NR | 790 | 2507 | NR | 920 | 3430 | NR |
| 405 | 3515 | NR | 535 | 114505 | NR | 665 | 30085 | NR | 795 | 2968 | NR | 925 | 4264 | NR |
| 410 | 6934 | NR | 540 | 116408 | NR | 670 | 26205 | NR | 800 | 2758 | NR | 930 | 4095 | NR |
| 415 | 14943 | NR | 545 | 118700 | NR | 675 | 22906 | NR | 805 | 2872 | NR | 935 | 5048 | NR |
| 420 | 31939 | NR | 550 | 119209 | NR | 680 | 20058 | NR | 810 | 3094 | NR | 940 | 4074 | NR |
| 425 | 64701 | NR | 555 | 120742 | NR | 685 | 17413 | NR | 815 | 3222 | NR | 945 | 4949 | NR |
| 430 | 110939 | NR | 560 | 121594 | NR | 690 | 15447 | NR | 820 | 3238 | NR | 950 | 4387 | NR |
| 435 | 164597 | NR | 565 | 121913 | NR | 695 | 13398 | NR | 825 | 3524 | NR | 955 | 4978 | NR |
| 440 | 207696 | NR | 570 | 122147 | NR | 700 | 11777 | NR | 830 | 2921 | NR | 960 | 4706 | NR |
| 445 | 201830 | NR | 575 | 121605 | NR | 705 | 10412 | NR | 835 | 3595 | NR | 965 | 5083 | NR |
| 450 | 145410 | NR | 580 | 120248 | NR | 710 | 9544 | NR | 840 | 3016 | NR | 970 | 4522 | NR |
| 455 | 89594 | NR | 585 | 117717 | NR | 715 | 8940 | NR | 845 | 4032 | NR | 975 | 4740 | NR |
| 460 | 58321 | NR | 590 | 114359 | NR | 720 | 7897 | NR | 850 | 3579 | NR | 980 | 6122 | NR |
| 465 | 39318 | NR | 595 | 109974 | NR | 725 | 7045 | NR | 855 | 4571 | NR | 985 | 6450 | NR |
| 470 | 27693 | NR | 600 | 105269 | NR | 730 | 6483 | NR | 860 | 4485 | NR | 990 | 4875 | NR |
| 475 | 23081 | NR | 605 | 99453 | NR | 735 | 5838 | NR | 865 | 3978 | NR | 995 | 4764 | NR |
| 480 | 23002 | NR | 610 | 92921 | NR | 740 | 5261 | NR | 870 | 4298 | NR | 1000 | 3640 | NR |
| 485 | 26201 | NR | 615 | 86989 | NR | 745 | 4760 | NR | 875 | 4356 | NR | | | |

REPORT NUMBER: SP1-1908-441-9-R4


TM-30-18

Summary

$R_f = 72.1$
 $R_g = 97.2$
 CIE $R_a = 71.7$
 $R_g = -27.1$



Color Vector Graphics



REPORT NUMBER: SP1-1908-441-9-R4

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)


| | | | |
|------------|------------|------------|------------|
| CES01 = 85 | CES26 = 54 | CES51 = 88 | CES76 = 43 |
| CES02 = 59 | CES27 = 79 | CES52 = 90 | CES77 = 64 |
| CES03 = 30 | CES28 = 77 | CES53 = 77 | CES78 = 46 |
| CES04 = 69 | CES29 = 50 | CES54 = 81 | CES79 = 74 |
| CES05 = 46 | CES30 = 59 | CES55 = 80 | CES80 = 70 |
| CES06 = 50 | CES31 = 55 | CES56 = 70 | CES81 = 71 |
| CES07 = 38 | CES32 = 52 | CES57 = 68 | CES82 = 88 |
| CES08 = 38 | CES33 = 63 | CES58 = 70 | CES83 = 82 |
| CES09 = 29 | CES34 = 63 | CES59 = 88 | CES84 = 87 |
| CES10 = 72 | CES35 = 79 | CES60 = 92 | CES85 = 84 |
| CES11 = 55 | CES36 = 90 | CES61 = 88 | CES86 = 76 |
| CES12 = 61 | CES37 = 72 | CES62 = 81 | CES87 = 75 |
| CES13 = 41 | CES38 = 68 | CES63 = 75 | CES88 = 77 |
| CES14 = 74 | CES39 = 91 | CES64 = 72 | CES89 = 76 |
| CES15 = 70 | CES40 = 83 | CES65 = 65 | CES90 = 76 |
| CES16 = 46 | CES41 = 84 | CES66 = 66 | CES91 = 92 |
| CES17 = 48 | CES42 = 70 | CES67 = 64 | CES92 = 70 |
| CES18 = 55 | CES43 = 69 | CES68 = 71 | CES93 = 83 |
| CES19 = 70 | CES44 = 98 | CES69 = 80 | CES94 = 60 |
| CES20 = 64 | CES45 = 79 | CES70 = 58 | CES95 = 73 |
| CES21 = 85 | CES46 = 78 | CES71 = 55 | CES96 = 79 |
| CES22 = 77 | CES47 = 76 | CES72 = 84 | CES97 = 84 |
| CES23 = 91 | CES48 = 68 | CES73 = 47 | CES98 = 73 |
| CES24 = 90 | CES49 = 78 | CES74 = 94 | CES99 = 62 |
| CES25 = 71 | CES50 = 87 | CES75 = 51 | |



REPORT NUMBER: SP1-1908-441-9-R4

TM-30-18

Color Rendition by Hue-Angle Bin



REPORT NUMBER: SP1-1908-441-9-R4

TM-30-18

Measure Comparisons



(END OF REPORT)