

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: McGRAW-EDISON

Report Number: P629976

Luminaire Tested: GWS-SA1C-760-U-T3R-W-GRSWH

Issue Date: 1/10/2023

Test Information

Test Method: LM-79-2019
Report Number: P629976
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2209-782-17)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/10/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: McGRAW-EDISON
Catalog Number: GWS-SA1C-760-U-T3R-W-GRSWH
Description: GALLEON WALL SLIM LUMINAIRE. (1) LIGHTSQUARES WITH 16 LEDS EACH AND TYPE III ROADWAY OPTICS W/ FACTORY INSTALLED GLARE SHIELD, WH
Light Source: (16) 5700K CCT, 70 CRI LEDS
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4251.6 lumens
Efficiency: N/A
Efficacy: 124.7 lumens/watt
Luminous Opening: Rectangular (W 0.5' x L: 0.5' x H: 0')
IES Classification: Type II - Short
BUG Rating: B1 - U0 - G1


Input Watts (W): 34.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 0
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT



REPORT NUMBER: P629976
 CATALOG NUMBER: GWS-SA1C-760-U-T3R-W-GRSWH

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 10 foot mounting height. Maximum calculated value = 10.6 fc
 Type II - Short - N/A

REPORT NUMBER: P629976
CATALOG NUMBER: GWS-SA1C-760-U-T3R-W-GRSWH

Luminous Intensity Polar Plot



— Vertical Plane Through 79-Deg Lateral - - - Horizontal Cone Through 57.5-Deg Vertical

REPORT NUMBER: P629976

CATALOG NUMBER: GWS-SA1C-760-U-T3R-W-GRSWH

FLUX DISTRIBUTION:

| | | Downward | Upward | Total |
|--------------------|-----------|----------|--------|--------|
| House Side | Lumens | 1263.8 | 0.0 | 1263.8 |
| | % Fixture | 29.7 | 0.0 | 29.7 |
| Street Side | Lumens | 2987.8 | 0.0 | 2987.8 |
| | % Fixture | 70.3 | 0.0 | 70.3 |
| Total | Lumens | 4251.6 | 0.0 | 4251.6 |
| | % Fixture | 100.0 | 0.0 | 100.0 |

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 97.6 | 2.3 |
| 10°-20° | 271.2 | 6.4 |
| 20°-30° | 459.6 | 10.8 |
| 30°-40° | 703.5 | 16.5 |
| 40°-50° | 938.1 | 22.1 |
| 50°-60° | 1083.4 | 25.5 |
| 60°-70° | 563.0 | 13.2 |
| 70°-80° | 119.7 | 2.8 |
| 80°-90° | 15.5 | 0.4 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-90° | 4251.6 | 100.0 |
| 0°-180° | 4251.6 | 100.0 |

Coefficient of Utilization



REPORT NUMBER: P629976


CATALOG NUMBER: GWS-SA1C-760-U-T3R-W-GRSWH

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

| Zone | Lumens | % Fixture | Zone Rating/Lumen Limit | | |
|----------------|--------|-----------|-------------------------|------|--------|
| | | | B | U | G |
| FL (0°-30°) | 469.5 | 11.0 | | | |
| FM (30°-60°) | 2054.5 | 48.3 | | | |
| FH (60°-80°) | 458.4 | 10.8 | | | G0/660 |
| FVH (80°-90°) | 5.4 | 0.1 | | | G0/10 |
| BL (0°-30°) | 358.9 | 8.4 | B1/500 | | |
| BM (30°-60°) | 670.6 | 15.8 | B1/1000 | | |
| BH (60°-80°) | 224.2 | 5.3 | B1/500 | | G1/500 |
| BVH (80°-90°) | 10.1 | 0.2 | | | G1/100 |
| UL (90°-100°) | 0.0 | 0.0 | | U0/0 | |
| UH (100°-180°) | 0.0 | 0.0 | | U0/0 | |

BUG Rating: B1-U0-G1

Type II Short





REPORT NUMBER: P629976

CATALOG NUMBER: GWS-SA1C-760-U-T3R-W-GRSWH

CANDELA DISTRIBUTION (FULL):

| | 0° | 5° | 15° | 25° | 35° | 45° | 55° | 65° | 75° | 79° | 85° |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 1053.6 | 1053.6 | 1053.6 | 1053.6 | 1053.6 | 1053.6 | 1053.6 | 1053.6 | 1053.6 | 1053.6 | 1053.6 |
| 2.5° | 1005.7 | 1003.6 | 1004.3 | 1007.1 | 1017.5 | 1025.1 | 1033.1 | 1040.4 | 1047.4 | 1049.5 | 1051.2 |
| 5° | 969.9 | 966.0 | 967.1 | 971.6 | 983.8 | 996.6 | 1010.9 | 1028.3 | 1045.0 | 1050.5 | 1057.8 |
| 7.5° | 944.5 | 943.8 | 945.5 | 952.5 | 965.3 | 977.5 | 995.9 | 1020.6 | 1049.5 | 1058.9 | 1071.7 |
| 10° | 910.8 | 909.4 | 916.3 | 930.6 | 951.8 | 971.3 | 993.2 | 1022.4 | 1062.7 | 1076.6 | 1096.4 |
| 12.5° | 884.0 | 883.3 | 890.6 | 910.4 | 937.5 | 968.5 | 998.7 | 1031.4 | 1080.4 | 1099.5 | 1123.9 |
| 15° | 899.6 | 896.5 | 896.9 | 910.8 | 935.1 | 971.6 | 1012.6 | 1047.7 | 1098.1 | 1122.5 | 1153.8 |
| 17.5° | 945.2 | 939.6 | 935.5 | 937.9 | 951.8 | 989.7 | 1033.8 | 1069.6 | 1118.7 | 1147.2 | 1185.4 |
| 20° | 1008.1 | 1005.0 | 993.5 | 985.9 | 989.0 | 1022.4 | 1067.2 | 1100.6 | 1145.4 | 1177.4 | 1218.4 |
| 22.5° | 1092.6 | 1084.9 | 1069.3 | 1057.1 | 1047.7 | 1073.8 | 1115.2 | 1144.0 | 1182.6 | 1216.0 | 1258.7 |
| 25° | 1197.2 | 1186.1 | 1161.4 | 1142.3 | 1122.1 | 1148.9 | 1185.7 | 1207.6 | 1233.7 | 1264.7 | 1305.3 |
| 27.5° | 1303.9 | 1294.5 | 1267.1 | 1241.4 | 1216.3 | 1233.0 | 1276.8 | 1289.3 | 1286.6 | 1309.1 | 1343.9 |
| 30° | 1417.6 | 1405.8 | 1379.7 | 1351.9 | 1319.6 | 1330.4 | 1369.6 | 1375.9 | 1346.3 | 1365.1 | 1388.8 |
| 32.5° | 1537.5 | 1526.1 | 1503.5 | 1471.1 | 1434.6 | 1438.8 | 1449.6 | 1455.5 | 1427.3 | 1438.1 | 1456.2 |
| 35° | 1659.6 | 1648.8 | 1625.8 | 1593.9 | 1567.1 | 1541.7 | 1514.6 | 1538.2 | 1521.9 | 1542.8 | 1541.4 |
| 37.5° | 1771.1 | 1760.4 | 1746.1 | 1721.4 | 1675.5 | 1625.5 | 1562.9 | 1592.1 | 1617.5 | 1643.9 | 1639.4 |
| 40° | 1846.6 | 1839.3 | 1842.7 | 1838.9 | 1779.8 | 1680.8 | 1586.6 | 1618.5 | 1687.7 | 1732.9 | 1730.5 |
| 42.5° | 1911.6 | 1904.3 | 1924.4 | 1939.0 | 1869.5 | 1731.9 | 1598.0 | 1628.6 | 1732.6 | 1803.1 | 1799.6 |
| 45° | 1940.4 | 1938.3 | 1971.7 | 2018.0 | 1951.6 | 1786.1 | 1627.6 | 1649.5 | 1766.6 | 1857.0 | 1843.8 |
| 47.5° | 1906.0 | 1913.3 | 1979.0 | 2057.2 | 2019.7 | 1850.4 | 1688.1 | 1693.6 | 1811.1 | 1915.4 | 1878.2 |
| 50° | 1837.5 | 1853.5 | 1942.2 | 2058.3 | 2069.4 | 1923.0 | 1771.8 | 1757.9 | 1870.9 | 1977.6 | 1896.3 |
| 52.5° | 1737.8 | 1754.5 | 1899.1 | 2050.3 | 2097.9 | 2007.2 | 1883.4 | 1863.6 | 1946.3 | 2039.9 | 1899.4 |
| 55° | 1508.7 | 1531.3 | 1800.3 | 2032.2 | 2125.7 | 2083.7 | 2009.3 | 1968.9 | 2043.7 | 2125.4 | 1930.3 |
| 57.5° | 1308.8 | 1320.6 | 1559.8 | 1951.9 | 2131.3 | 2140.0 | 2098.9 | 2051.0 | 2140.3 | 2217.8 | 1965.1 |
| 60° | 960.5 | 963.3 | 1178.4 | 1615.1 | 1960.6 | 2107.3 | 2091.6 | 2020.4 | 2094.4 | 2143.8 | 1805.9 |
| 62.5° | 542.6 | 543.0 | 714.7 | 1078.0 | 1464.5 | 1717.6 | 1727.3 | 1664.4 | 1602.2 | 1616.8 | 1257.0 |
| 65° | 203.7 | 222.8 | 326.4 | 529.8 | 844.4 | 1014.0 | 1054.3 | 1068.9 | 965.3 | 901.0 | 674.0 |
| 67.5° | 136.3 | 140.8 | 190.5 | 272.5 | 375.8 | 433.8 | 485.3 | 486.7 | 356.0 | 317.4 | 265.6 |
| 70° | 103.9 | 108.5 | 149.8 | 195.0 | 190.5 | 175.9 | 190.1 | 184.9 | 191.2 | 196.4 | 202.0 |
| 72.5° | 77.5 | 82.0 | 116.1 | 137.7 | 114.4 | 112.6 | 127.6 | 141.8 | 155.0 | 160.6 | 169.3 |
| 75° | 51.4 | 54.9 | 78.2 | 73.7 | 63.3 | 74.7 | 93.2 | 107.4 | 115.1 | 121.7 | 128.3 |
| 77.5° | 32.7 | 35.1 | 41.7 | 33.7 | 35.1 | 43.8 | 54.2 | 67.1 | 74.4 | 81.0 | 84.5 |
| 80° | 14.9 | 14.6 | 14.3 | 16.0 | 19.8 | 25.7 | 32.7 | 40.3 | 45.9 | 48.7 | 50.8 |
| 82.5° | 5.9 | 6.6 | 7.3 | 8.7 | 10.8 | 13.9 | 18.4 | 23.6 | 28.2 | 28.9 | 30.6 |
| 85° | 2.4 | 2.8 | 3.1 | 3.8 | 4.9 | 6.3 | 7.6 | 10.8 | 13.6 | 14.6 | 15.6 |
| 87.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.3 | 0.7 | 1.0 | 1.7 | 3.1 | 3.5 | 3.8 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P629976

CATALOG NUMBER: GWS-SA1C-760-U-T3R-W-GRSWH

CANDELA DISTRIBUTION (continued):

| | 90° | 95° | 105° | 115° | 125° | 135° | 145° | 155° | 165° | 175° | 180° |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 1053.6 | 1053.6 | 1053.6 | 1053.6 | 1053.6 | 1053.6 | 1053.6 | 1053.6 | 1053.6 | 1053.6 | 1053.6 |
| 2.5° | 1060.6 | 1056.1 | 1063.7 | 1068.9 | 1073.8 | 1068.6 | 1066.9 | 1062.3 | 1061.6 | 1061.6 | 1064.1 |
| 5° | 1070.3 | 1067.2 | 1075.2 | 1078.3 | 1078.0 | 1066.5 | 1059.6 | 1050.5 | 1046.0 | 1046.0 | 1046.7 |
| 7.5° | 1087.7 | 1086.0 | 1090.5 | 1085.6 | 1074.5 | 1051.2 | 1028.3 | 1009.1 | 996.3 | 989.7 | 991.8 |
| 10° | 1116.6 | 1114.5 | 1110.7 | 1092.6 | 1060.6 | 1012.3 | 965.3 | 930.6 | 909.7 | 897.9 | 898.6 |
| 12.5° | 1144.7 | 1141.2 | 1127.7 | 1087.7 | 1022.0 | 945.2 | 883.7 | 844.7 | 821.8 | 807.9 | 804.7 |
| 15° | 1175.7 | 1166.6 | 1137.4 | 1062.7 | 959.1 | 863.1 | 798.8 | 756.8 | 732.1 | 723.8 | 723.4 |
| 17.5° | 1205.2 | 1189.2 | 1136.4 | 1018.2 | 883.7 | 777.3 | 712.6 | 686.6 | 682.4 | 686.2 | 687.3 |
| 20° | 1235.1 | 1209.4 | 1124.9 | 956.7 | 794.0 | 691.8 | 658.4 | 669.2 | 684.8 | 695.2 | 697.7 |
| 22.5° | 1266.0 | 1226.1 | 1098.8 | 877.4 | 699.4 | 634.1 | 648.0 | 671.6 | 691.1 | 705.0 | 706.4 |
| 25° | 1300.8 | 1241.7 | 1059.9 | 780.4 | 623.6 | 618.1 | 645.5 | 670.6 | 691.4 | 707.4 | 710.2 |
| 27.5° | 1320.6 | 1242.1 | 1005.3 | 680.6 | 588.9 | 611.8 | 639.6 | 663.3 | 684.1 | 701.5 | 704.6 |
| 30° | 1340.1 | 1232.7 | 918.8 | 599.6 | 578.8 | 604.5 | 629.5 | 651.4 | 671.3 | 688.3 | 692.1 |
| 32.5° | 1367.5 | 1224.0 | 819.0 | 553.1 | 572.9 | 597.6 | 618.1 | 637.5 | 652.8 | 660.5 | 662.6 |
| 35° | 1401.6 | 1212.9 | 713.0 | 532.9 | 569.1 | 592.0 | 610.1 | 620.5 | 600.7 | 596.5 | 601.0 |
| 37.5° | 1449.2 | 1202.4 | 607.3 | 524.2 | 566.6 | 589.9 | 605.9 | 579.1 | 554.8 | 545.1 | 548.5 |
| 40° | 1500.7 | 1196.5 | 535.7 | 517.3 | 567.7 | 592.0 | 588.5 | 548.9 | 513.8 | 493.3 | 492.6 |
| 42.5° | 1544.5 | 1187.5 | 489.8 | 512.7 | 570.4 | 600.0 | 564.9 | 522.1 | 470.0 | 457.8 | 458.2 |
| 45° | 1574.0 | 1164.5 | 465.5 | 507.9 | 572.9 | 601.7 | 553.8 | 485.3 | 448.1 | 440.4 | 440.1 |
| 47.5° | 1586.2 | 1122.8 | 449.8 | 500.2 | 572.5 | 587.5 | 531.2 | 470.0 | 432.8 | 430.7 | 432.1 |
| 50° | 1578.2 | 1054.3 | 433.8 | 485.3 | 564.2 | 572.5 | 505.1 | 456.4 | 422.4 | 433.8 | 442.2 |
| 52.5° | 1548.7 | 965.7 | 414.7 | 464.8 | 549.2 | 555.5 | 491.9 | 448.1 | 414.7 | 430.0 | 436.6 |
| 55° | 1541.0 | 893.7 | 390.4 | 438.0 | 527.0 | 525.3 | 478.0 | 443.9 | 409.5 | 403.6 | 404.6 |
| 57.5° | 1530.9 | 823.5 | 350.1 | 390.0 | 470.7 | 473.5 | 464.8 | 439.0 | 395.9 | 394.2 | 395.9 |
| 60° | 1330.0 | 631.3 | 312.2 | 336.5 | 386.6 | 401.5 | 449.8 | 430.0 | 374.0 | 366.7 | 366.4 |
| 62.5° | 868.7 | 382.4 | 277.8 | 293.4 | 314.9 | 332.3 | 410.2 | 403.9 | 350.1 | 345.5 | 348.7 |
| 65° | 467.2 | 272.5 | 252.7 | 262.1 | 273.9 | 287.1 | 340.0 | 359.8 | 316.3 | 300.3 | 300.7 |
| 67.5° | 238.8 | 231.9 | 234.0 | 240.6 | 249.6 | 256.2 | 274.3 | 291.7 | 269.8 | 256.2 | 255.9 |
| 70° | 204.4 | 210.0 | 213.1 | 216.9 | 222.8 | 221.8 | 223.5 | 226.7 | 224.9 | 218.3 | 218.0 |
| 72.5° | 174.2 | 182.8 | 183.5 | 184.2 | 186.3 | 181.5 | 178.3 | 173.1 | 173.5 | 174.5 | 174.9 |
| 75° | 132.4 | 140.8 | 142.9 | 141.8 | 143.9 | 137.7 | 133.5 | 128.3 | 122.0 | 121.0 | 121.7 |
| 77.5° | 86.2 | 92.8 | 95.9 | 95.2 | 96.3 | 91.4 | 89.3 | 83.8 | 76.5 | 73.7 | 73.7 |
| 80° | 52.1 | 56.0 | 58.4 | 59.1 | 60.1 | 56.7 | 53.2 | 48.3 | 45.2 | 42.1 | 42.1 |
| 82.5° | 31.6 | 34.1 | 35.8 | 35.8 | 36.8 | 33.0 | 30.2 | 26.8 | 25.4 | 22.6 | 22.6 |
| 85° | 16.0 | 17.7 | 18.4 | 18.1 | 17.4 | 14.3 | 13.2 | 11.5 | 10.8 | 9.4 | 9.4 |
| 87.5° | 3.8 | 4.9 | 4.9 | 3.5 | 3.5 | 1.7 | 1.0 | 0.3 | 0.0 | 0.0 | 0.0 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



LM-79-2008: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGRAW-EDISON

Report Number: SP1-1908-441-9-R4

Test Date: 10/23/2019

Luminaire Tested: SA1C-760-U-5WQ

Data in this report applies to families of products SA1C-760-U-5WQ .

Test Information

Test Method: LM-79-2008
 Report Number: SP1-1908-441-9-R4
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 10/28/2024
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: McGRAW-EDISON
 Catalog Number: **SA1C-760-U-5WQ**
 Description: McGRAW EDISON ROADWAY AND AREA LUMINAIRE

THIS IS A REVISION OF SP1-1908-441-4-R3. TO UPDATE THE CATALOG INFORMATION.TESTED IN SITU. ROADWAY AND AREA LUMINAIRE. (1) 70 CRI, 5000K, 1050MA LIGHTSQUARE WITH 16 LEDS AND TYPE V WIDE OPTICS.

Spectral Parameters

| | | | | | |
|---------------------------|--------|-----------|------|------|-------|
| CCT (K): | 5474 | CRI (Ra): | 71.7 | R9: | -27.1 |
| CIE u': | 0.2052 | R1: | 70.6 | R10: | 40.8 |
| CIE v': | 0.4804 | R2: | 74.6 | R11: | 74.6 |
| Duv: | 0.0025 | R3: | 78.3 | R12: | 50.4 |
| CIE x: | 0.3330 | R4: | 73.8 | R13: | 70.0 |
| CIE y: | 0.3466 | R5: | 72.4 | R14: | 87.8 |
| CIE z: | 0.3204 | R6: | 67.5 | | |
| Peak Wavelength (nm): | 442 | R7: | 77.5 | | |
| Dominant Wavelength (nm): | 554 | R8: | 58.9 | | |
| Purity: | 4.1 | | | | |
| Rf: | 72.1 | | | | |
| Rg: | 97.2 | | | | |



Test Conditions

Stabilization Time: 240M
 Operation Time: 12H
 Room Temperature (°C) / RH%: 24.6/31%
 Sphere Temperature (°C): 25.9

REPORT NUMBER: SP1-1908-441-9-R4

| Measurement and Test Equipment | | | |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument | Identification Number | Calibration Date | Calibration Due Date |
| Photometer | IN0058 | 6/28/2019 | 12/28/2019 |
| Power Meter | IN0071 | 12/5/2018 | 12/5/2019 |
| AC Power Source | IN0063 | 12/5/2018 | 12/5/2019 |
| DC Power Source | IN0208 | 12/5/2018 | 12/5/2019 |
| Sphere Thermometer | IN0085 | 12/5/2018 | 12/5/2019 |
| Room Thermometer | IN0046 | 12/5/2018 | 12/5/2019 |

REPORT NUMBER: SP1-1908-441-9-R4

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 5700K 4-step quadrangle

REPORT NUMBER: SP1-1908-441-9-R4

Photopic Flux vs. Wavelength



#####

| λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) |
|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|
| 360 | 3540 | NR | 490 | 33363 | NR | 620 | 80193 | NR | 750 | 4663 | NR | 880 | 4678 | NR |
| 365 | 2862 | NR | 495 | 44177 | NR | 625 | 73091 | NR | 755 | 4147 | NR | 885 | 4128 | NR |
| 370 | 2865 | NR | 500 | 57019 | NR | 630 | 66269 | NR | 760 | 4040 | NR | 890 | 4504 | NR |
| 375 | 3254 | NR | 505 | 70030 | NR | 635 | 60012 | NR | 765 | 3474 | NR | 895 | 4371 | NR |
| 380 | 3076 | NR | 510 | 81972 | NR | 640 | 53914 | NR | 770 | 3469 | NR | 900 | 4082 | NR |
| 385 | 2904 | NR | 515 | 92590 | NR | 645 | 48385 | NR | 775 | 3181 | NR | 905 | 2982 | NR |
| 390 | 2689 | NR | 520 | 100305 | NR | 650 | 43219 | NR | 780 | 2969 | NR | 910 | 4351 | NR |
| 395 | 2619 | NR | 525 | 107452 | NR | 655 | 38562 | NR | 785 | 3132 | NR | 915 | 3365 | NR |
| 400 | 2679 | NR | 530 | 111373 | NR | 660 | 34110 | NR | 790 | 2507 | NR | 920 | 3430 | NR |
| 405 | 3515 | NR | 535 | 114505 | NR | 665 | 30085 | NR | 795 | 2968 | NR | 925 | 4264 | NR |
| 410 | 6934 | NR | 540 | 116408 | NR | 670 | 26205 | NR | 800 | 2758 | NR | 930 | 4095 | NR |
| 415 | 14943 | NR | 545 | 118700 | NR | 675 | 22906 | NR | 805 | 2872 | NR | 935 | 5048 | NR |
| 420 | 31939 | NR | 550 | 119209 | NR | 680 | 20058 | NR | 810 | 3094 | NR | 940 | 4074 | NR |
| 425 | 64701 | NR | 555 | 120742 | NR | 685 | 17413 | NR | 815 | 3222 | NR | 945 | 4949 | NR |
| 430 | 110939 | NR | 560 | 121594 | NR | 690 | 15447 | NR | 820 | 3238 | NR | 950 | 4387 | NR |
| 435 | 164597 | NR | 565 | 121913 | NR | 695 | 13398 | NR | 825 | 3524 | NR | 955 | 4978 | NR |
| 440 | 207696 | NR | 570 | 122147 | NR | 700 | 11777 | NR | 830 | 2921 | NR | 960 | 4706 | NR |
| 445 | 201830 | NR | 575 | 121605 | NR | 705 | 10412 | NR | 835 | 3595 | NR | 965 | 5083 | NR |
| 450 | 145410 | NR | 580 | 120248 | NR | 710 | 9544 | NR | 840 | 3016 | NR | 970 | 4522 | NR |
| 455 | 89594 | NR | 585 | 117717 | NR | 715 | 8940 | NR | 845 | 4032 | NR | 975 | 4740 | NR |
| 460 | 58321 | NR | 590 | 114359 | NR | 720 | 7897 | NR | 850 | 3579 | NR | 980 | 6122 | NR |
| 465 | 39318 | NR | 595 | 109974 | NR | 725 | 7045 | NR | 855 | 4571 | NR | 985 | 6450 | NR |
| 470 | 27693 | NR | 600 | 105269 | NR | 730 | 6483 | NR | 860 | 4485 | NR | 990 | 4875 | NR |
| 475 | 23081 | NR | 605 | 99453 | NR | 735 | 5838 | NR | 865 | 3978 | NR | 995 | 4764 | NR |
| 480 | 23002 | NR | 610 | 92921 | NR | 740 | 5261 | NR | 870 | 4298 | NR | 1000 | 3640 | NR |
| 485 | 26201 | NR | 615 | 86989 | NR | 745 | 4760 | NR | 875 | 4356 | NR | | | |

REPORT NUMBER: SP1-1908-441-9-R4

Scotopic Flux vs. Wavelength



Scotopic Lumens: 13759.3 S/P: 1.85

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 3540 | NR | 490 | 33363 | NR | 620 | 80193 | NR | 750 | 4663 | NR | 880 | 4678 | NR |
| 365 | 2862 | NR | 495 | 44177 | NR | 625 | 73091 | NR | 755 | 4147 | NR | 885 | 4128 | NR |
| 370 | 2865 | NR | 500 | 57019 | NR | 630 | 66269 | NR | 760 | 4040 | NR | 890 | 4504 | NR |
| 375 | 3254 | NR | 505 | 70030 | NR | 635 | 60012 | NR | 765 | 3474 | NR | 895 | 4371 | NR |
| 380 | 3076 | NR | 510 | 81972 | NR | 640 | 53914 | NR | 770 | 3469 | NR | 900 | 4082 | NR |
| 385 | 2904 | NR | 515 | 92590 | NR | 645 | 48385 | NR | 775 | 3181 | NR | 905 | 2982 | NR |
| 390 | 2689 | NR | 520 | 100305 | NR | 650 | 43219 | NR | 780 | 2969 | NR | 910 | 4351 | NR |
| 395 | 2619 | NR | 525 | 107452 | NR | 655 | 38562 | NR | 785 | 3132 | NR | 915 | 3365 | NR |
| 400 | 2679 | NR | 530 | 111373 | NR | 660 | 34110 | NR | 790 | 2507 | NR | 920 | 3430 | NR |
| 405 | 3515 | NR | 535 | 114505 | NR | 665 | 30085 | NR | 795 | 2968 | NR | 925 | 4264 | NR |
| 410 | 6934 | NR | 540 | 116408 | NR | 670 | 26205 | NR | 800 | 2758 | NR | 930 | 4095 | NR |
| 415 | 14943 | NR | 545 | 118700 | NR | 675 | 22906 | NR | 805 | 2872 | NR | 935 | 5048 | NR |
| 420 | 31939 | NR | 550 | 119209 | NR | 680 | 20058 | NR | 810 | 3094 | NR | 940 | 4074 | NR |
| 425 | 64701 | NR | 555 | 120742 | NR | 685 | 17413 | NR | 815 | 3222 | NR | 945 | 4949 | NR |
| 430 | 110939 | NR | 560 | 121594 | NR | 690 | 15447 | NR | 820 | 3238 | NR | 950 | 4387 | NR |
| 435 | 164597 | NR | 565 | 121913 | NR | 695 | 13398 | NR | 825 | 3524 | NR | 955 | 4978 | NR |
| 440 | 207696 | NR | 570 | 122147 | NR | 700 | 11777 | NR | 830 | 2921 | NR | 960 | 4706 | NR |
| 445 | 201830 | NR | 575 | 121605 | NR | 705 | 10412 | NR | 835 | 3595 | NR | 965 | 5083 | NR |
| 450 | 145410 | NR | 580 | 120248 | NR | 710 | 9544 | NR | 840 | 3016 | NR | 970 | 4522 | NR |
| 455 | 89594 | NR | 585 | 117717 | NR | 715 | 8940 | NR | 845 | 4032 | NR | 975 | 4740 | NR |
| 460 | 58321 | NR | 590 | 114359 | NR | 720 | 7897 | NR | 850 | 3579 | NR | 980 | 6122 | NR |
| 465 | 39318 | NR | 595 | 109974 | NR | 725 | 7045 | NR | 855 | 4571 | NR | 985 | 6450 | NR |
| 470 | 27693 | NR | 600 | 105269 | NR | 730 | 6483 | NR | 860 | 4485 | NR | 990 | 4875 | NR |
| 475 | 23081 | NR | 605 | 99453 | NR | 735 | 5838 | NR | 865 | 3978 | NR | 995 | 4764 | NR |
| 480 | 23002 | NR | 610 | 92921 | NR | 740 | 5261 | NR | 870 | 4298 | NR | 1000 | 3640 | NR |
| 485 | 26201 | NR | 615 | 86989 | NR | 745 | 4760 | NR | 875 | 4356 | NR | | | |

REPORT NUMBER: SP1-1908-441-9-R4

Melanopic Flux vs. Wavelength



Melanopic Lumens: 5527.6 M/P: 0.74

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 3540 | NR | 490 | 33363 | NR | 620 | 80193 | NR | 750 | 4663 | NR | 880 | 4678 | NR |
| 365 | 2862 | NR | 495 | 44177 | NR | 625 | 73091 | NR | 755 | 4147 | NR | 885 | 4128 | NR |
| 370 | 2865 | NR | 500 | 57019 | NR | 630 | 66269 | NR | 760 | 4040 | NR | 890 | 4504 | NR |
| 375 | 3254 | NR | 505 | 70030 | NR | 635 | 60012 | NR | 765 | 3474 | NR | 895 | 4371 | NR |
| 380 | 3076 | NR | 510 | 81972 | NR | 640 | 53914 | NR | 770 | 3469 | NR | 900 | 4082 | NR |
| 385 | 2904 | NR | 515 | 92590 | NR | 645 | 48385 | NR | 775 | 3181 | NR | 905 | 2982 | NR |
| 390 | 2689 | NR | 520 | 100305 | NR | 650 | 43219 | NR | 780 | 2969 | NR | 910 | 4351 | NR |
| 395 | 2619 | NR | 525 | 107452 | NR | 655 | 38562 | NR | 785 | 3132 | NR | 915 | 3365 | NR |
| 400 | 2679 | NR | 530 | 111373 | NR | 660 | 34110 | NR | 790 | 2507 | NR | 920 | 3430 | NR |
| 405 | 3515 | NR | 535 | 114505 | NR | 665 | 30085 | NR | 795 | 2968 | NR | 925 | 4264 | NR |
| 410 | 6934 | NR | 540 | 116408 | NR | 670 | 26205 | NR | 800 | 2758 | NR | 930 | 4095 | NR |
| 415 | 14943 | NR | 545 | 118700 | NR | 675 | 22906 | NR | 805 | 2872 | NR | 935 | 5048 | NR |
| 420 | 31939 | NR | 550 | 119209 | NR | 680 | 20058 | NR | 810 | 3094 | NR | 940 | 4074 | NR |
| 425 | 64701 | NR | 555 | 120742 | NR | 685 | 17413 | NR | 815 | 3222 | NR | 945 | 4949 | NR |
| 430 | 110939 | NR | 560 | 121594 | NR | 690 | 15447 | NR | 820 | 3238 | NR | 950 | 4387 | NR |
| 435 | 164597 | NR | 565 | 121913 | NR | 695 | 13398 | NR | 825 | 3524 | NR | 955 | 4978 | NR |
| 440 | 207696 | NR | 570 | 122147 | NR | 700 | 11777 | NR | 830 | 2921 | NR | 960 | 4706 | NR |
| 445 | 201830 | NR | 575 | 121605 | NR | 705 | 10412 | NR | 835 | 3595 | NR | 965 | 5083 | NR |
| 450 | 145410 | NR | 580 | 120248 | NR | 710 | 9544 | NR | 840 | 3016 | NR | 970 | 4522 | NR |
| 455 | 89594 | NR | 585 | 117717 | NR | 715 | 8940 | NR | 845 | 4032 | NR | 975 | 4740 | NR |
| 460 | 58321 | NR | 590 | 114359 | NR | 720 | 7897 | NR | 850 | 3579 | NR | 980 | 6122 | NR |
| 465 | 39318 | NR | 595 | 109974 | NR | 725 | 7045 | NR | 855 | 4571 | NR | 985 | 6450 | NR |
| 470 | 27693 | NR | 600 | 105269 | NR | 730 | 6483 | NR | 860 | 4485 | NR | 990 | 4875 | NR |
| 475 | 23081 | NR | 605 | 99453 | NR | 735 | 5838 | NR | 865 | 3978 | NR | 995 | 4764 | NR |
| 480 | 23002 | NR | 610 | 92921 | NR | 740 | 5261 | NR | 870 | 4298 | NR | 1000 | 3640 | NR |
| 485 | 26201 | NR | 615 | 86989 | NR | 745 | 4760 | NR | 875 | 4356 | NR | | | |


REPORT NUMBER: SP1-1908-441-9-R4

TM-30-18





Summary

$R_f = 72.1$
 $R_g = 97.2$
 CIE $R_a = 71.7$
 $R_g = -27.1$

Spectral Power Distribution Comparison



Color Vector Graphics



REPORT NUMBER: SP1-1908-441-9-R4

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)

| | | | |
|------------|------------|------------|------------|
| CES01 = 85 | CES26 = 54 | CES51 = 88 | CES76 = 43 |
| CES02 = 59 | CES27 = 79 | CES52 = 90 | CES77 = 64 |
| CES03 = 30 | CES28 = 77 | CES53 = 77 | CES78 = 46 |
| CES04 = 69 | CES29 = 50 | CES54 = 81 | CES79 = 74 |
| CES05 = 46 | CES30 = 59 | CES55 = 80 | CES80 = 70 |
| CES06 = 50 | CES31 = 55 | CES56 = 70 | CES81 = 71 |
| CES07 = 38 | CES32 = 52 | CES57 = 68 | CES82 = 88 |
| CES08 = 38 | CES33 = 63 | CES58 = 70 | CES83 = 82 |
| CES09 = 29 | CES34 = 63 | CES59 = 88 | CES84 = 87 |
| CES10 = 72 | CES35 = 79 | CES60 = 92 | CES85 = 84 |
| CES11 = 55 | CES36 = 90 | CES61 = 88 | CES86 = 76 |
| CES12 = 61 | CES37 = 72 | CES62 = 81 | CES87 = 75 |
| CES13 = 41 | CES38 = 68 | CES63 = 75 | CES88 = 77 |
| CES14 = 74 | CES39 = 91 | CES64 = 72 | CES89 = 76 |
| CES15 = 70 | CES40 = 83 | CES65 = 65 | CES90 = 76 |
| CES16 = 46 | CES41 = 84 | CES66 = 66 | CES91 = 92 |
| CES17 = 48 | CES42 = 70 | CES67 = 64 | CES92 = 70 |
| CES18 = 55 | CES43 = 69 | CES68 = 71 | CES93 = 83 |
| CES19 = 70 | CES44 = 98 | CES69 = 80 | CES94 = 60 |
| CES20 = 64 | CES45 = 79 | CES70 = 58 | CES95 = 73 |
| CES21 = 85 | CES46 = 78 | CES71 = 55 | CES96 = 79 |
| CES22 = 77 | CES47 = 76 | CES72 = 84 | CES97 = 84 |
| CES23 = 91 | CES48 = 68 | CES73 = 47 | CES98 = 73 |
| CES24 = 90 | CES49 = 78 | CES74 = 94 | CES99 = 62 |
| CES25 = 71 | CES50 = 87 | CES75 = 51 | |



REPORT NUMBER: SP1-1908-441-9-R4

TM-30-18

Color Rendition by Hue-Angle Bin



REPORT NUMBER: SP1-1908-441-9-R4

TM-30-18

Measure Comparisons



(END OF REPORT)