

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: McGRAW-EDISON

Report Number: P633487

Luminaire Tested: GWS-SA2E-827-U-T2R-W-GRSBK

Issue Date: 1/10/2023

Test Information

Test Method: LM-79-2019
Report Number: P633487
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2209-782-12)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/10/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: McGRAW-EDISON
Catalog Number: GWS-SA2E-827-U-T2R-W-GRSBK
Description: GALLEON WALL SLIM LUMINAIRE. (2) LIGHTSQUARES WITH 16 LEDS EACH AND TYPE II ROADWAY OPTICS W/ FACTORY INSTALLED GLARE SHIELD, BK
Light Source: (32) 2700K CCT, 80 CRI LEDS
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7190.2 lumens
Efficiency: N/A
Efficacy: 66.5 lumens/watt
Luminous Opening: Rectangular (W 1' x L: 0.5' x H: 0')
IES Classification: Type II - Short
BUG Rating: B1 - U0 - G0


Input Watts (W): 108.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 0
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT



REPORT NUMBER: P633487
 CATALOG NUMBER: GWS-SA2E-827-U-T2R-W-GRSBK

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 10 foot mounting height. Maximum calculated value = 26.4 fc
 Type II - Short - N/A

REPORT NUMBER: P633487
CATALOG NUMBER: GWS-SA2E-827-U-T2R-W-GRSBK

Luminous Intensity Polar Plot



— Vertical Plane Through 58-Deg Lateral - - - Horizontal Cone Through 50-Deg Vertical

REPORT NUMBER: P633487
 CATALOG NUMBER: GWS-SA2E-827-U-T2R-W-GRSBK


FLUX DISTRIBUTION:

| | | Downward | Upward | Total |
|--------------------|-----------|----------|--------|--------|
| House Side | Lumens | 1007.1 | 0.0 | 1007.1 |
| | % Fixture | 14.0 | 0.0 | 14.0 |
| Street Side | Lumens | 6183.1 | 0.0 | 6183.1 |
| | % Fixture | 86.0 | 0.0 | 86.0 |
| Total | Lumens | 7190.2 | 0.0 | 7190.2 |
| | % Fixture | 100.0 | 0.0 | 100.0 |

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 106.4 | 1.5 |
| 10°-20° | 421.2 | 5.9 |
| 20°-30° | 852.3 | 11.9 |
| 30°-40° | 1507.9 | 21.0 |
| 40°-50° | 2198.1 | 30.6 |
| 50°-60° | 1761.9 | 24.5 |
| 60°-70° | 317.4 | 4.4 |
| 70°-80° | 25.0 | 0.3 |
| 80°-90° | 0.0 | 0.0 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-90° | 7190.2 | 100.0 |
| 0°-180° | 7190.2 | 100.0 |

Coefficient of Utilization




REPORT NUMBER: P633487

CATALOG NUMBER: GWS-SA2E-827-U-T2R-W-GRSBK

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

| Zone | Lumens | % Fixture | Zone Rating/Lumen Limit | | |
|----------------|--------|-----------|-------------------------|------|--------|
| | | | B | U | G |
| FL (0°-30°) | 1069.9 | 14.9 | | | |
| FM (30°-60°) | 4842.4 | 67.3 | | | |
| FH (60°-80°) | 270.9 | 3.8 | | | G0/660 |
| FVH (80°-90°) | 0.0 | 0.0 | | | G0/10 |
| BL (0°-30°) | 310.0 | 4.3 | B1/500 | | |
| BM (30°-60°) | 625.4 | 8.7 | B1/1000 | | |
| BH (60°-80°) | 71.6 | 1.0 | B0/110 | | G0/110 |
| BVH (80°-90°) | 0.0 | 0.0 | | | G0/10 |
| UL (90°-100°) | 0.0 | 0.0 | | U0/0 | |
| UH (100°-180°) | 0.0 | 0.0 | | U0/0 | |

BUG Rating: B1-U0-G0
 Type II Short





REPORT NUMBER: P633487

CATALOG NUMBER: GWS-SA2E-827-U-T2R-W-GRSBK

CANDELA DISTRIBUTION (FULL):

| | 0° | 5° | 15° | 25° | 35° | 45° | 55° | 58° | 65° | 75° | 85° |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 858.9 | 858.9 | 858.9 | 858.9 | 858.9 | 858.9 | 858.9 | 858.9 | 858.9 | 858.9 | 858.9 |
| 2.5° | 1271.0 | 1251.0 | 1239.5 | 1230.2 | 1189.5 | 1124.9 | 1082.6 | 1060.3 | 1023.4 | 961.1 | 907.3 |
| 5° | 1658.5 | 1643.9 | 1617.0 | 1598.5 | 1546.3 | 1454.8 | 1360.2 | 1322.5 | 1238.7 | 1098.0 | 971.9 |
| 7.5° | 1915.3 | 1904.6 | 1894.6 | 1870.0 | 1820.7 | 1737.7 | 1633.1 | 1593.9 | 1464.7 | 1264.8 | 1058.0 |
| 10° | 2112.9 | 2104.5 | 2092.9 | 2092.2 | 2053.7 | 1979.1 | 1876.9 | 1836.1 | 1696.2 | 1446.3 | 1159.5 |
| 12.5° | 2286.7 | 2279.8 | 2277.5 | 2299.0 | 2274.4 | 2219.0 | 2108.3 | 2057.6 | 1909.2 | 1631.6 | 1271.8 |
| 15° | 2405.9 | 2404.3 | 2414.3 | 2456.6 | 2470.5 | 2445.1 | 2352.1 | 2297.5 | 2126.8 | 1817.7 | 1395.5 |
| 17.5° | 2460.5 | 2465.1 | 2484.3 | 2557.3 | 2618.9 | 2640.4 | 2568.9 | 2522.7 | 2342.8 | 2006.1 | 1527.8 |
| 20° | 2553.5 | 2552.0 | 2563.5 | 2632.7 | 2708.1 | 2784.9 | 2763.4 | 2724.2 | 2561.2 | 2205.2 | 1674.7 |
| 22.5° | 2815.7 | 2793.4 | 2768.8 | 2779.6 | 2806.5 | 2896.4 | 2936.4 | 2916.4 | 2786.5 | 2409.7 | 1826.1 |
| 25° | 3218.6 | 3195.5 | 3116.3 | 3039.4 | 2988.7 | 3029.5 | 3084.0 | 3094.0 | 3010.2 | 2619.6 | 1984.5 |
| 27.5° | 3646.1 | 3625.3 | 3536.2 | 3420.8 | 3275.5 | 3204.8 | 3245.5 | 3265.5 | 3230.1 | 2869.5 | 2152.9 |
| 30° | 4046.7 | 4019.0 | 3921.4 | 3778.4 | 3610.0 | 3501.6 | 3455.4 | 3469.3 | 3490.0 | 3165.5 | 2350.5 |
| 32.5° | 4394.2 | 4373.5 | 4256.6 | 4105.9 | 3943.7 | 3830.6 | 3723.0 | 3746.1 | 3796.8 | 3527.7 | 2603.5 |
| 35° | 4688.7 | 4678.0 | 4554.2 | 4404.2 | 4232.8 | 4175.1 | 4082.8 | 4087.5 | 4138.2 | 3965.2 | 2911.8 |
| 37.5° | 4944.8 | 4926.3 | 4814.1 | 4674.9 | 4538.8 | 4529.6 | 4504.2 | 4506.5 | 4532.6 | 4475.0 | 3266.3 |
| 40° | 5106.2 | 5089.3 | 5009.4 | 4923.2 | 4826.4 | 4827.9 | 4959.4 | 4969.4 | 4939.4 | 4975.5 | 3640.7 |
| 42.5° | 5167.0 | 5154.7 | 5111.6 | 5112.4 | 5102.4 | 5147.8 | 5394.6 | 5413.0 | 5305.4 | 5368.4 | 3960.6 |
| 45° | 5061.6 | 5056.3 | 5059.3 | 5170.1 | 5290.0 | 5429.9 | 5750.6 | 5782.9 | 5630.6 | 5629.1 | 4210.5 |
| 47.5° | 4721.8 | 4711.0 | 4801.0 | 4989.4 | 5266.9 | 5539.1 | 5965.9 | 6015.8 | 5858.2 | 5778.3 | 4367.3 |
| 50° | 4055.9 | 4086.7 | 4228.9 | 4511.9 | 4934.0 | 5389.2 | 5963.6 | 6050.4 | 5866.7 | 5765.2 | 4341.2 |
| 52.5° | 2938.0 | 2931.8 | 3243.2 | 3632.3 | 4145.9 | 4909.4 | 5646.8 | 5773.6 | 5661.4 | 5636.8 | 4282.8 |
| 55° | 1598.5 | 1654.7 | 1864.6 | 2379.7 | 3021.0 | 4001.3 | 4923.2 | 5200.0 | 5330.0 | 5589.9 | 4388.1 |
| 57.5° | 587.4 | 612.0 | 743.5 | 1108.0 | 1599.3 | 2488.1 | 3760.7 | 4178.2 | 4579.5 | 5459.2 | 4370.4 |
| 60° | 236.8 | 241.4 | 293.7 | 407.5 | 672.0 | 1266.4 | 2255.9 | 2626.5 | 3004.8 | 4179.0 | 3353.9 |
| 62.5° | 172.2 | 178.4 | 199.1 | 238.4 | 339.9 | 553.6 | 972.7 | 1131.0 | 1236.4 | 2069.9 | 1652.4 |
| 65° | 139.2 | 143.8 | 160.7 | 178.4 | 224.5 | 297.6 | 313.7 | 302.2 | 300.6 | 535.2 | 379.1 |
| 67.5° | 115.3 | 119.9 | 132.3 | 144.6 | 161.5 | 148.4 | 107.6 | 113.0 | 92.3 | 91.5 | 74.6 |
| 70° | 84.6 | 90.0 | 102.3 | 115.3 | 96.9 | 40.0 | 62.3 | 92.3 | 70.0 | 58.4 | 56.9 |
| 72.5° | 63.8 | 67.7 | 79.2 | 75.4 | 28.4 | 15.4 | 41.5 | 66.9 | 53.8 | 43.1 | 42.3 |
| 75° | 47.7 | 50.0 | 40.0 | 12.3 | 3.1 | 3.8 | 15.4 | 27.7 | 30.0 | 24.6 | 24.6 |
| 77.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 1.5 | 2.3 | 3.1 | 3.8 | 4.6 |
| 80° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 82.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 85° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 87.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P633487
 CATALOG NUMBER: GWS-SA2E-827-U-T2R-W-GRSBK

CANDELA DISTRIBUTION (continued):

| | 90° | 95° | 105° | 115° | 125° | 135° | 145° | 155° | 165° | 175° | 180° |
|-------|--------|--------|-------|-------|-------|-------|-------|-------|-------|-------|-------|
| 0° | 858.9 | 858.9 | 858.9 | 858.9 | 858.9 | 858.9 | 858.9 | 858.9 | 858.9 | 858.9 | 858.9 |
| 2.5° | 876.5 | 844.2 | 798.1 | 759.7 | 730.5 | 702.0 | 680.5 | 658.9 | 658.2 | 647.4 | 645.1 |
| 5° | 913.4 | 855.0 | 770.4 | 709.7 | 672.8 | 650.5 | 635.1 | 627.4 | 623.6 | 619.7 | 618.2 |
| 7.5° | 966.5 | 882.7 | 765.8 | 701.2 | 670.5 | 655.9 | 645.1 | 640.5 | 638.2 | 635.1 | 634.3 |
| 10° | 1031.9 | 922.7 | 782.7 | 717.4 | 690.5 | 676.6 | 665.1 | 658.2 | 654.3 | 648.9 | 647.4 |
| 12.5° | 1110.3 | 971.9 | 809.6 | 744.3 | 715.8 | 697.4 | 682.0 | 672.0 | 666.6 | 659.7 | 658.2 |
| 15° | 1194.9 | 1024.9 | 839.6 | 768.9 | 735.1 | 711.2 | 692.0 | 676.6 | 666.6 | 658.2 | 655.9 |
| 17.5° | 1282.5 | 1078.8 | 866.5 | 785.8 | 744.3 | 715.8 | 688.2 | 667.4 | 655.1 | 644.3 | 641.3 |
| 20° | 1380.9 | 1134.1 | 884.2 | 788.9 | 741.2 | 703.5 | 671.2 | 645.1 | 632.8 | 618.2 | 615.1 |
| 22.5° | 1484.0 | 1185.6 | 891.9 | 782.0 | 724.3 | 680.5 | 645.9 | 619.0 | 601.3 | 585.9 | 581.3 |
| 25° | 1583.9 | 1231.8 | 888.1 | 762.7 | 698.9 | 648.2 | 612.8 | 585.1 | 565.9 | 550.5 | 546.7 |
| 27.5° | 1690.0 | 1270.2 | 874.2 | 734.3 | 664.3 | 612.8 | 579.0 | 555.1 | 537.5 | 520.5 | 516.7 |
| 30° | 1809.2 | 1305.6 | 851.9 | 699.7 | 623.6 | 576.7 | 550.5 | 534.4 | 515.2 | 497.5 | 492.1 |
| 32.5° | 1953.0 | 1337.1 | 819.6 | 658.2 | 587.4 | 545.1 | 530.5 | 518.2 | 495.9 | 477.5 | 473.6 |
| 35° | 2117.5 | 1363.3 | 778.9 | 615.1 | 552.1 | 525.2 | 522.1 | 505.9 | 476.7 | 455.2 | 450.6 |
| 37.5° | 2308.2 | 1388.6 | 730.5 | 572.8 | 525.9 | 515.9 | 516.7 | 489.0 | 453.6 | 427.5 | 424.4 |
| 40° | 2513.5 | 1414.0 | 676.6 | 535.9 | 502.1 | 510.5 | 503.6 | 464.4 | 406.7 | 381.4 | 378.3 |
| 42.5° | 2727.3 | 1441.7 | 622.0 | 501.3 | 482.1 | 489.8 | 479.8 | 415.2 | 373.7 | 360.6 | 359.1 |
| 45° | 2920.3 | 1474.7 | 562.8 | 466.7 | 462.1 | 459.8 | 442.9 | 376.0 | 358.3 | 349.1 | 348.3 |
| 47.5° | 3059.4 | 1469.4 | 499.8 | 433.7 | 440.6 | 432.9 | 381.4 | 357.5 | 342.9 | 330.6 | 327.5 |
| 50° | 3034.1 | 1375.6 | 434.4 | 396.8 | 412.9 | 406.0 | 342.9 | 336.0 | 322.9 | 309.9 | 305.3 |
| 52.5° | 2969.5 | 1247.9 | 377.5 | 357.5 | 382.9 | 366.8 | 316.8 | 309.9 | 298.3 | 281.4 | 276.0 |
| 55° | 3004.1 | 1128.0 | 332.9 | 326.0 | 352.2 | 303.7 | 287.6 | 276.8 | 264.5 | 246.0 | 243.7 |
| 57.5° | 2892.6 | 920.4 | 267.6 | 272.2 | 311.4 | 259.1 | 252.2 | 235.3 | 214.5 | 202.2 | 200.7 |
| 60° | 2002.2 | 494.4 | 167.6 | 173.0 | 225.3 | 217.6 | 226.1 | 210.7 | 185.3 | 173.8 | 171.5 |
| 62.5° | 919.6 | 198.4 | 91.5 | 87.7 | 118.4 | 147.6 | 193.8 | 192.2 | 160.7 | 142.2 | 140.7 |
| 65° | 223.0 | 90.7 | 65.4 | 61.5 | 66.9 | 88.4 | 126.1 | 151.5 | 129.9 | 108.4 | 106.1 |
| 67.5° | 72.3 | 73.8 | 60.0 | 56.1 | 59.2 | 66.1 | 75.4 | 83.8 | 83.0 | 76.1 | 74.6 |
| 70° | 57.7 | 66.9 | 55.4 | 50.7 | 50.7 | 53.1 | 50.7 | 40.8 | 35.4 | 38.4 | 40.0 |
| 72.5° | 43.1 | 50.7 | 43.8 | 39.2 | 37.7 | 36.9 | 31.5 | 23.1 | 16.1 | 14.6 | 13.8 |
| 75° | 25.4 | 28.4 | 26.9 | 23.1 | 21.5 | 19.2 | 15.4 | 10.0 | 5.4 | 3.8 | 2.3 |
| 77.5° | 4.6 | 5.4 | 6.2 | 4.6 | 3.8 | 3.1 | 2.3 | 0.8 | 0.0 | 0.0 | 0.0 |
| 80° | 0.0 | 0.8 | 0.8 | 0.8 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 82.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 85° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 87.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Invue

Report Number: SP1-2407-157-9

Test Date: 10/03/2024

Luminaire Tested: EMM2-HTN-SA1A-827-U-5WQ

Data applicable to all product families utilizing light square engine

Test Information

Test Method: LM-79-2019
 Report Number: SP1-2407-157-9
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 10/03/2024
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: Invue
 Catalog Number: **EMM2-HTN-SA1A-827-U-5WQ**
 Description: Epic Modern Light Square 40W 5WQ Optic

Spectral Parameters

CCT (K): 2764
 CIE u': 0.2591
 CIE v': 0.5290
 Duv: 0.0020
 CIE x: 0.4581
 CIE y: 0.4156
 CIE z: 0.1263
 Peak Wavelength (nm): 603
 Dominant Wavelength (nm): 583
 Purity: 62.2537
 Rf: 84.7
 Rg: 94.6

| | | | |
|-----------|------|------|------|
| CRI (Ra): | 80.9 | | |
| R1: | 78.8 | R9: | -1.5 |
| R2: | 89.9 | R10: | 77.9 |
| R3: | 96.2 | R11: | 78.9 |
| R4: | 79.1 | R12: | 71.6 |
| R5: | 79.1 | R13: | 81.2 |
| R6: | 88.8 | R14: | 98.5 |
| R7: | 81.3 | R15: | 69.9 |
| R8: | 54.3 | | |



Test Conditions

Stabilization Time: 81M
 Operation Time: 2H 21M
 Sphere Temperature (°C): 25.2

REPORT NUMBER: SP1-2407-157-9

| Measurement and Test Equipment | | | |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument | Identification Number | Calibration Date | Calibration Due Date |
| Photometer | IN0058 | 6/18/2024 | 12/18/2024 |
| Power Meter | INXT2011004 | 2/8/2024 | 2/8/2025 |
| AC Power Source | IN0063 | 10/24/2023 | 10/24/2024 |
| DC Power Source | IN0208 | 10/24/2023 | 10/24/2024 |
| Sphere Thermometer | IN0085 | 10/24/2023 | 10/24/2024 |
| Room Thermometer | IN0046 | 10/24/2023 | 10/24/2024 |

REPORT NUMBER: SP1-2407-157-9

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



CCT = 2764K
 CIE x = 0.4581
 CIE y = 0.4156
 Duv = 0.0020

Point lies inside the ANSI 2700K 4-step quadrangle

REPORT NUMBER: SP1-2407-157-9

Photopic Flux vs. Wavelength



Photopic Lumens: 4337.9

| λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) |
|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|
| 360 | 0 | 0.0 | 490 | 18018 | 2.6 | 620 | 87426 | 22.8 | 750 | 2680 | 0.0 | 880 | 58 | 0.0 |
| 365 | 0 | 0.0 | 495 | 22295 | 3.9 | 625 | 83013 | 18.2 | 755 | 2287 | 0.0 | 885 | 46 | 0.0 |
| 370 | 0 | 0.0 | 500 | 26478 | 5.8 | 630 | 78077 | 14.1 | 760 | 1944 | 0.0 | 890 | 45 | 0.0 |
| 375 | 0 | 0.0 | 505 | 30524 | 8.5 | 635 | 72080 | 10.7 | 765 | 1653 | 0.0 | 895 | 41 | 0.0 |
| 380 | 0 | 0.0 | 510 | 33611 | 11.5 | 640 | 66249 | 7.9 | 770 | 1413 | 0.0 | 900 | 38 | 0.0 |
| 385 | 0 | 0.0 | 515 | 36490 | 15.2 | 645 | 59973 | 5.7 | 775 | 1198 | 0.0 | 905 | 33 | 0.0 |
| 390 | 0 | 0.0 | 520 | 38610 | 18.7 | 650 | 53972 | 3.9 | 780 | 1025 | 0.0 | 910 | 30 | 0.0 |
| 395 | 0 | 0.0 | 525 | 40511 | 21.9 | 655 | 48369 | 2.7 | 785 | 874 | 0.0 | 915 | 23 | 0.0 |
| 400 | 48 | 0.0 | 530 | 42223 | 24.9 | 660 | 42641 | 1.8 | 790 | 747 | 0.0 | 920 | 24 | 0.0 |
| 405 | 201 | 0.0 | 535 | 44137 | 27.6 | 665 | 37602 | 1.1 | 795 | 639 | 0.0 | 925 | 22 | 0.0 |
| 410 | 457 | 0.0 | 540 | 46032 | 30.0 | 670 | 32798 | 0.7 | 800 | 547 | 0.0 | 930 | 22 | 0.0 |
| 415 | 925 | 0.0 | 545 | 48553 | 32.5 | 675 | 28558 | 0.5 | 805 | 473 | 0.0 | 935 | 17 | 0.0 |
| 420 | 1816 | 0.0 | 550 | 51408 | 34.9 | 680 | 24782 | 0.3 | 810 | 401 | 0.0 | 940 | 13 | 0.0 |
| 425 | 3217 | 0.0 | 555 | 54711 | 37.4 | 685 | 21386 | 0.2 | 815 | 351 | 0.0 | 945 | 6 | 0.0 |
| 430 | 5520 | 0.0 | 560 | 58847 | 40.0 | 690 | 18413 | 0.1 | 820 | 307 | 0.0 | 950 | 10 | 0.0 |
| 435 | 9225 | 0.1 | 565 | 63386 | 42.4 | 695 | 15721 | 0.1 | 825 | 261 | 0.0 | 955 | 11 | 0.0 |
| 440 | 15522 | 0.2 | 570 | 68196 | 44.3 | 700 | 13432 | 0.0 | 830 | 228 | 0.0 | 960 | 8 | 0.0 |
| 445 | 27642 | 0.6 | 575 | 73613 | 46.0 | 705 | 11513 | 0.0 | 835 | 193 | 0.0 | 965 | 12 | 0.0 |
| 450 | 36602 | 0.9 | 580 | 79207 | 47.1 | 710 | 9780 | 0.0 | 840 | 174 | 0.0 | 970 | 3 | 0.0 |
| 455 | 28292 | 0.9 | 585 | 84248 | 47.0 | 715 | 8356 | 0.0 | 845 | 151 | 0.0 | 975 | 8 | 0.0 |
| 460 | 21166 | 0.9 | 590 | 88397 | 45.7 | 720 | 7161 | 0.0 | 850 | 123 | 0.0 | 980 | 2 | 0.0 |
| 465 | 19092 | 1.0 | 595 | 91428 | 43.4 | 725 | 6067 | 0.0 | 855 | 106 | 0.0 | 985 | 13 | 0.0 |
| 470 | 14951 | 0.9 | 600 | 93452 | 40.3 | 730 | 5164 | 0.0 | 860 | 95 | 0.0 | 990 | 16 | 0.0 |
| 475 | 12606 | 1.0 | 605 | 93959 | 36.4 | 735 | 4393 | 0.0 | 865 | 82 | 0.0 | 995 | 20 | 0.0 |
| 480 | 13323 | 1.3 | 610 | 93079 | 32.0 | 740 | 3694 | 0.0 | 870 | 77 | 0.0 | 1000 | 0 | 0.0 |
| 485 | 15164 | 1.8 | 615 | 90707 | 27.3 | 745 | 3157 | 0.0 | 875 | 65 | 0.0 | | | |

REPORT NUMBER: SP1-2407-157-9

Scotopic Flux vs. Wavelength



Scotopic Lumens: 5286.7

S/P: 1.22

| λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) |
|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|
| 360 | 0 | 0.0 | 490 | 18018 | 75.9 | 620 | 87426 | 0.4 | 750 | 2680 | 0.0 | 880 | 58 | 0.0 |
| 365 | 0 | 0.0 | 495 | 22295 | 93.2 | 625 | 83013 | 0.2 | 755 | 2287 | 0.0 | 885 | 46 | 0.0 |
| 370 | 0 | 0.0 | 500 | 26478 | 107.8 | 630 | 78077 | 0.1 | 760 | 1944 | 0.0 | 890 | 45 | 0.0 |
| 375 | 0 | 0.0 | 505 | 30524 | 118.7 | 635 | 72080 | 0.1 | 765 | 1653 | 0.0 | 895 | 41 | 0.0 |
| 380 | 0 | 0.0 | 510 | 33611 | 122.2 | 640 | 66249 | 0.1 | 770 | 1413 | 0.0 | 900 | 38 | 0.0 |
| 385 | 0 | 0.0 | 515 | 36490 | 120.8 | 645 | 59973 | 0.0 | 775 | 1198 | 0.0 | 905 | 33 | 0.0 |
| 390 | 0 | 0.0 | 520 | 38610 | 113.9 | 650 | 53972 | 0.0 | 780 | 1025 | 0.0 | 910 | 30 | 0.0 |
| 395 | 0 | 0.0 | 525 | 40511 | 104.1 | 655 | 48369 | 0.0 | 785 | 874 | 0.0 | 915 | 23 | 0.0 |
| 400 | 48 | 0.0 | 530 | 42223 | 92.4 | 660 | 42641 | 0.0 | 790 | 747 | 0.0 | 920 | 24 | 0.0 |
| 405 | 201 | 0.0 | 535 | 44137 | 80.5 | 665 | 37602 | 0.0 | 795 | 639 | 0.0 | 925 | 22 | 0.0 |
| 410 | 457 | 0.1 | 540 | 46032 | 68.2 | 670 | 32798 | 0.0 | 800 | 547 | 0.0 | 930 | 22 | 0.0 |
| 415 | 925 | 0.3 | 545 | 48553 | 57.1 | 675 | 28558 | 0.0 | 805 | 473 | 0.0 | 935 | 17 | 0.0 |
| 420 | 1816 | 1.1 | 550 | 51408 | 46.7 | 680 | 24782 | 0.0 | 810 | 401 | 0.0 | 940 | 13 | 0.0 |
| 425 | 3217 | 2.5 | 555 | 54711 | 37.4 | 685 | 21386 | 0.0 | 815 | 351 | 0.0 | 945 | 6 | 0.0 |
| 430 | 5520 | 5.9 | 560 | 58847 | 29.4 | 690 | 18413 | 0.0 | 820 | 307 | 0.0 | 950 | 10 | 0.0 |
| 435 | 9225 | 12.5 | 565 | 63386 | 22.5 | 695 | 15721 | 0.0 | 825 | 261 | 0.0 | 955 | 11 | 0.0 |
| 440 | 15522 | 26.3 | 570 | 68196 | 16.9 | 700 | 13432 | 0.0 | 830 | 228 | 0.0 | 960 | 8 | 0.0 |
| 445 | 27642 | 55.2 | 575 | 73613 | 12.4 | 705 | 11513 | 0.0 | 835 | 193 | 0.0 | 965 | 12 | 0.0 |
| 450 | 36602 | 85.4 | 580 | 79207 | 9.0 | 710 | 9780 | 0.0 | 840 | 174 | 0.0 | 970 | 3 | 0.0 |
| 455 | 28292 | 75.1 | 585 | 84248 | 6.3 | 715 | 8356 | 0.0 | 845 | 151 | 0.0 | 975 | 8 | 0.0 |
| 460 | 21166 | 63.2 | 590 | 88397 | 4.4 | 720 | 7161 | 0.0 | 850 | 123 | 0.0 | 980 | 2 | 0.0 |
| 465 | 19092 | 63.2 | 595 | 91428 | 3.0 | 725 | 6067 | 0.0 | 855 | 106 | 0.0 | 985 | 13 | 0.0 |
| 470 | 14951 | 54.2 | 600 | 93452 | 2.0 | 730 | 5164 | 0.0 | 860 | 95 | 0.0 | 990 | 16 | 0.0 |
| 475 | 12606 | 48.8 | 605 | 93959 | 1.3 | 735 | 4393 | 0.0 | 865 | 82 | 0.0 | 995 | 20 | 0.0 |
| 480 | 13323 | 54.2 | 610 | 93079 | 0.9 | 740 | 3694 | 0.0 | 870 | 77 | 0.0 | 1000 | 0 | 0.0 |
| 485 | 15164 | 63.3 | 615 | 90707 | 0.5 | 745 | 3157 | 0.0 | 875 | 65 | 0.0 | | | |

REPORT NUMBER: SP1-2407-157-9

Melanopic Flux vs. Wavelength



Melanopic Lumens: 9797

M/P: 2.26

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 0 | 0.0 | 490 | 18018 | 27.7 | 620 | 87426 | 1.1 | 750 | 2680 | 0.0 | 880 | 58 | 0.0 |
| 365 | 0 | 0.0 | 495 | 22295 | 36.0 | 625 | 83013 | 0.7 | 755 | 2287 | 0.0 | 885 | 46 | 0.0 |
| 370 | 0 | 0.0 | 500 | 26478 | 44.2 | 630 | 78077 | 0.4 | 760 | 1944 | 0.0 | 890 | 45 | 0.0 |
| 375 | 0 | 0.0 | 505 | 30524 | 51.8 | 635 | 72080 | 0.3 | 765 | 1653 | 0.0 | 895 | 41 | 0.0 |
| 380 | 0 | 0.0 | 510 | 33611 | 57.0 | 640 | 66249 | 0.2 | 770 | 1413 | 0.0 | 900 | 38 | 0.0 |
| 385 | 0 | 0.0 | 515 | 36490 | 60.5 | 645 | 59973 | 0.1 | 775 | 1198 | 0.0 | 905 | 33 | 0.0 |
| 390 | 0 | 0.0 | 520 | 38610 | 61.4 | 650 | 53972 | 0.1 | 780 | 1025 | 0.0 | 910 | 30 | 0.0 |
| 395 | 0 | 0.0 | 525 | 40511 | 60.6 | 655 | 48369 | 0.0 | 785 | 874 | 0.0 | 915 | 23 | 0.0 |
| 400 | 48 | 0.0 | 530 | 42223 | 58.2 | 660 | 42641 | 0.0 | 790 | 747 | 0.0 | 920 | 24 | 0.0 |
| 405 | 201 | 0.0 | 535 | 44137 | 55.0 | 665 | 37602 | 0.0 | 795 | 639 | 0.0 | 925 | 22 | 0.0 |
| 410 | 457 | 0.0 | 540 | 46032 | 50.9 | 670 | 32798 | 0.0 | 800 | 547 | 0.0 | 930 | 22 | 0.0 |
| 415 | 925 | 0.1 | 545 | 48553 | 46.6 | 675 | 28558 | 0.0 | 805 | 473 | 0.0 | 935 | 17 | 0.0 |
| 420 | 1816 | 0.3 | 550 | 51408 | 42.0 | 680 | 24782 | 0.0 | 810 | 401 | 0.0 | 940 | 13 | 0.0 |
| 425 | 3217 | 0.8 | 555 | 54711 | 37.4 | 685 | 21386 | 0.0 | 815 | 351 | 0.0 | 945 | 6 | 0.0 |
| 430 | 5520 | 1.9 | 560 | 58847 | 32.9 | 690 | 18413 | 0.0 | 820 | 307 | 0.0 | 950 | 10 | 0.0 |
| 435 | 9225 | 4.1 | 565 | 63386 | 28.4 | 695 | 15721 | 0.0 | 825 | 261 | 0.0 | 955 | 11 | 0.0 |
| 440 | 15522 | 8.7 | 570 | 68196 | 24.1 | 700 | 13432 | 0.0 | 830 | 228 | 0.0 | 960 | 8 | 0.0 |
| 445 | 27642 | 18.5 | 575 | 73613 | 20.0 | 705 | 11513 | 0.0 | 835 | 193 | 0.0 | 965 | 12 | 0.0 |
| 450 | 36602 | 28.3 | 580 | 79207 | 16.3 | 710 | 9780 | 0.0 | 840 | 174 | 0.0 | 970 | 3 | 0.0 |
| 455 | 28292 | 24.7 | 585 | 84248 | 12.9 | 715 | 8356 | 0.0 | 845 | 151 | 0.0 | 975 | 8 | 0.0 |
| 460 | 21166 | 20.4 | 590 | 88397 | 9.8 | 720 | 7161 | 0.0 | 850 | 123 | 0.0 | 980 | 2 | 0.0 |
| 465 | 19092 | 20.1 | 595 | 91428 | 7.3 | 725 | 6067 | 0.0 | 855 | 106 | 0.0 | 985 | 13 | 0.0 |
| 470 | 14951 | 17.2 | 600 | 93452 | 5.3 | 730 | 5164 | 0.0 | 860 | 95 | 0.0 | 990 | 16 | 0.0 |
| 475 | 12606 | 15.7 | 605 | 93959 | 3.7 | 735 | 4393 | 0.0 | 865 | 82 | 0.0 | 995 | 20 | 0.0 |
| 480 | 13323 | 18.0 | 610 | 93079 | 2.5 | 740 | 3694 | 0.0 | 870 | 77 | 0.0 | 1000 | 0 | 0.0 |
| 485 | 15164 | 21.9 | 615 | 90707 | 1.7 | 745 | 3157 | 0.0 | 875 | 65 | 0.0 | | | |

Summary

$R_f = 84.7$
 $R_g = 94.6$
 CIE $R_a = 80.9$
 $R_9 = -1.5$



Color Vector Graphics




Individual Sample Fidelity Index ($R_{f,i}$)

| | | | |
|------------|------------|------------|------------|
| CES01 = 86 | CES26 = 84 | CES51 = 95 | CES76 = 81 |
| CES02 = 63 | CES27 = 95 | CES52 = 94 | CES77 = 84 |
| CES03 = 31 | CES28 = 94 | CES53 = 89 | CES78 = 81 |
| CES04 = 71 | CES29 = 87 | CES54 = 91 | CES79 = 89 |
| CES05 = 50 | CES30 = 94 | CES55 = 90 | CES80 = 89 |
| CES06 = 52 | CES31 = 89 | CES56 = 86 | CES81 = 69 |
| CES07 = 43 | CES32 = 82 | CES57 = 85 | CES82 = 96 |
| CES08 = 41 | CES33 = 91 | CES58 = 86 | CES83 = 93 |
| CES09 = 29 | CES34 = 92 | CES59 = 91 | CES84 = 92 |
| CES10 = 77 | CES35 = 96 | CES60 = 94 | CES85 = 76 |
| CES11 = 60 | CES36 = 90 | CES61 = 89 | CES86 = 65 |
| CES12 = 66 | CES37 = 96 | CES62 = 94 | CES87 = 84 |
| CES13 = 44 | CES38 = 98 | CES63 = 87 | CES88 = 86 |
| CES14 = 74 | CES39 = 98 | CES64 = 82 | CES89 = 73 |
| CES15 = 72 | CES40 = 95 | CES65 = 78 | CES90 = 88 |
| CES16 = 48 | CES41 = 96 | CES66 = 81 | CES91 = 82 |
| CES17 = 50 | CES42 = 97 | CES67 = 80 | CES92 = 64 |
| CES18 = 57 | CES43 = 91 | CES68 = 83 | CES93 = 78 |
| CES19 = 73 | CES44 = 99 | CES69 = 88 | CES94 = 59 |
| CES20 = 67 | CES45 = 93 | CES70 = 80 | CES95 = 74 |
| CES21 = 87 | CES46 = 89 | CES71 = 79 | CES96 = 83 |
| CES22 = 79 | CES47 = 92 | CES72 = 92 | CES97 = 88 |
| CES23 = 92 | CES48 = 83 | CES73 = 75 | CES98 = 83 |
| CES24 = 91 | CES49 = 90 | CES74 = 91 | CES99 = 74 |
| CES25 = 72 | CES50 = 94 | CES75 = 81 | |



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)