

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: McGRAW-EDISON

Report Number: P635939

Luminaire Tested: GWS-SA3E-827-U-SL2-W-GRSBK

Issue Date: 1/10/2023

Test Information

Test Method: LM-79-2019
Report Number: P635939
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2209-782-28)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/10/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: McGRAW-EDISON
Catalog Number: GWS-SA3E-827-U-SL2-W-GRSBK
Description: GALLEON WALL SLIM LUMINAIRE. (3) LIGHTSQUARES WITH 16 LEDS EACH AND TYPE II SPILL LIGHT ELIMINATOR OPTICS W/ FACTORY INSTALLED GLARE SHIELD, BK
Light Source: (48) 2700K CCT, 80 CRI LEDS
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 9492.7 lumens
Efficiency: N/A
Efficacy: 59.6 lumens/watt
Luminous Opening: Rectangular (W 1.5' x L: 0.5' x H: 0')
IES Classification: Type II - Short
BUG Rating: B2 - U0 - G1


Input Watts (W): 159.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 0
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT



REPORT NUMBER: P635939
 CATALOG NUMBER: GWS-SA3E-827-U-SL2-W-GRSBK

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 10 foot mounting height. Maximum calculated value = 33.3 fc
 Type II - Short - N/A

REPORT NUMBER: P635939
CATALOG NUMBER: GWS-SA3E-827-U-SL2-W-GRSBK

Luminous Intensity Polar Plot



— Vertical Plane Through 50-Deg Lateral - - - Horizontal Cone Through 55-Deg Vertical

REPORT NUMBER: P635939
 CATALOG NUMBER: GWS-SA3E-827-U-SL2-W-GRSBK

FLUX DISTRIBUTION:

| | | Downward | Upward | Total |
|--------------------|-----------|----------|--------|--------|
| House Side | Lumens | 1870.5 | 0.0 | 1870.5 |
| | % Fixture | 19.7 | 0.0 | 19.7 |
| Street Side | Lumens | 7622.2 | 0.0 | 7622.2 |
| | % Fixture | 80.3 | 0.0 | 80.3 |
| Total | Lumens | 9492.7 | 0.0 | 9492.7 |
| | % Fixture | 100.0 | 0.0 | 100.0 |

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 292.5 | 3.1 |
| 10°-20° | 719.8 | 7.6 |
| 20°-30° | 1015.3 | 10.7 |
| 30°-40° | 1502.4 | 15.8 |
| 40°-50° | 2167.5 | 22.8 |
| 50°-60° | 2556.7 | 26.9 |
| 60°-70° | 1140.5 | 12.0 |
| 70°-80° | 98.0 | 1.0 |
| 80°-90° | 0.0 | 0.0 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-90° | 9492.7 | 100.0 |
| 0°-180° | 9492.7 | 100.0 |

Coefficient of Utilization




REPORT NUMBER: P635939

CATALOG NUMBER: GWS-SA3E-827-U-SL2-W-GRSBK

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

| Zone | Lumens | % Fixture | Zone Rating/Lumen Limit | | |
|----------------|--------|-----------|-------------------------|------|---------|
| | | | B | U | G |
| FL (0°-30°) | 1225.5 | 12.9 | | | |
| FM (30°-60°) | 5327.0 | 56.1 | | | |
| FH (60°-80°) | 1069.7 | 11.3 | | | G1/1800 |
| FVH (80°-90°) | 0.0 | 0.0 | | | G0/10 |
| BL (0°-30°) | 802.0 | 8.4 | B2/1000 | | |
| BM (30°-60°) | 899.6 | 9.5 | B1/1000 | | |
| BH (60°-80°) | 168.9 | 1.8 | B1/500 | | G1/500 |
| BVH (80°-90°) | 0.0 | 0.0 | | | G0/10 |
| UL (90°-100°) | 0.0 | 0.0 | | U0/0 | |
| UH (100°-180°) | 0.0 | 0.0 | | U0/0 | |

BUG Rating: B2-U0-G1
 Type II Short





REPORT NUMBER: P635939

CATALOG NUMBER: GWS-SA3E-827-U-SL2-W-GRSBK

CANDELA DISTRIBUTION (FULL):

| | 0° | 5° | 15° | 25° | 35° | 45° | 50° | 55° | 65° | 75° | 85° |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 3330.6 | 3330.6 | 3330.6 | 3330.6 | 3330.6 | 3330.6 | 3330.6 | 3330.6 | 3330.6 | 3330.6 | 3330.6 |
| 2.5° | 3094.2 | 3096.5 | 3097.6 | 3128.9 | 3140.5 | 3186.9 | 3211.2 | 3224.0 | 3257.6 | 3297.0 | 3329.4 |
| 5° | 2886.7 | 2883.2 | 2889.0 | 2928.4 | 2953.9 | 3022.3 | 3059.4 | 3084.9 | 3159.1 | 3251.8 | 3329.4 |
| 7.5° | 2705.9 | 2712.9 | 2719.8 | 2762.7 | 2801.0 | 2875.1 | 2928.4 | 2966.7 | 3069.8 | 3207.7 | 3338.7 |
| 10° | 2578.5 | 2578.5 | 2588.9 | 2637.6 | 2682.8 | 2774.3 | 2827.6 | 2876.3 | 2999.1 | 3168.3 | 3349.1 |
| 12.5° | 2484.6 | 2485.8 | 2498.5 | 2554.1 | 2606.3 | 2701.3 | 2756.9 | 2804.4 | 2940.0 | 3128.9 | 3351.4 |
| 15° | 2440.6 | 2437.1 | 2447.5 | 2506.6 | 2564.6 | 2653.8 | 2711.7 | 2758.1 | 2898.3 | 3106.9 | 3363.0 |
| 17.5° | 2429.0 | 2426.7 | 2434.8 | 2492.7 | 2551.8 | 2638.7 | 2695.5 | 2741.9 | 2892.5 | 3113.9 | 3397.8 |
| 20° | 2462.6 | 2457.9 | 2454.5 | 2504.3 | 2559.9 | 2645.7 | 2704.8 | 2756.9 | 2920.3 | 3152.1 | 3451.1 |
| 22.5° | 2542.5 | 2542.5 | 2534.4 | 2558.8 | 2595.8 | 2673.5 | 2734.9 | 2803.3 | 2993.3 | 3228.6 | 3529.9 |
| 25° | 2689.7 | 2678.1 | 2663.1 | 2673.5 | 2668.9 | 2717.5 | 2790.5 | 2885.6 | 3131.2 | 3354.9 | 3626.1 |
| 27.5° | 2857.8 | 2868.2 | 2842.7 | 2843.8 | 2803.3 | 2785.9 | 2870.5 | 3014.2 | 3336.4 | 3533.4 | 3768.6 |
| 30° | 3086.0 | 3077.9 | 3079.1 | 3075.6 | 2981.7 | 2899.5 | 2991.0 | 3182.2 | 3594.8 | 3805.7 | 3954.0 |
| 32.5° | 3264.5 | 3276.1 | 3314.3 | 3336.4 | 3213.5 | 3081.4 | 3178.8 | 3410.5 | 3889.1 | 4116.3 | 4181.2 |
| 35° | 3453.4 | 3474.3 | 3551.9 | 3623.8 | 3520.6 | 3368.8 | 3473.1 | 3713.0 | 4166.1 | 4423.4 | 4441.9 |
| 37.5° | 3652.7 | 3694.4 | 3787.2 | 3913.5 | 3897.3 | 3762.8 | 3857.8 | 4068.8 | 4384.0 | 4608.8 | 4657.5 |
| 40° | 3881.0 | 3921.6 | 4073.4 | 4255.3 | 4293.6 | 4263.5 | 4294.7 | 4417.6 | 4527.7 | 4616.9 | 4750.2 |
| 42.5° | 4131.3 | 4187.0 | 4379.3 | 4622.7 | 4766.4 | 4793.0 | 4720.0 | 4707.3 | 4590.2 | 4524.2 | 4730.5 |
| 45° | 4426.8 | 4491.7 | 4709.6 | 5024.8 | 5253.1 | 5289.0 | 5162.7 | 4999.3 | 4629.7 | 4455.8 | 4671.4 |
| 47.5° | 4758.3 | 4819.7 | 5036.4 | 5415.4 | 5754.9 | 5768.8 | 5548.6 | 5285.6 | 4746.7 | 4534.6 | 4716.6 |
| 50° | 4869.5 | 4907.8 | 5095.5 | 5540.5 | 6166.3 | 6272.9 | 5954.2 | 5607.7 | 4981.9 | 4766.4 | 4936.7 |
| 52.5° | 4487.1 | 4502.2 | 4665.6 | 5115.2 | 6082.9 | 6767.7 | 6546.4 | 6088.7 | 5400.3 | 5119.8 | 5276.3 |
| 55° | 3555.4 | 3531.0 | 3663.2 | 4075.7 | 5286.7 | 6666.9 | 7083.0 | 6844.2 | 5939.2 | 5534.7 | 5717.8 |
| 57.5° | 2486.9 | 2457.9 | 2427.8 | 2707.1 | 3944.8 | 5651.8 | 6526.7 | 6949.7 | 6452.5 | 5946.1 | 6194.1 |
| 60° | 2044.2 | 2016.4 | 1870.4 | 1741.8 | 2384.9 | 4058.3 | 5013.2 | 5809.4 | 6410.8 | 5925.3 | 6179.0 |
| 62.5° | 1766.1 | 1749.9 | 1690.8 | 1515.8 | 1403.4 | 2316.6 | 3139.4 | 3901.9 | 4919.4 | 4652.8 | 4666.7 |
| 65° | 1387.2 | 1382.5 | 1423.1 | 1441.6 | 1241.1 | 1281.7 | 1601.5 | 2028.0 | 2659.6 | 2507.8 | 2378.0 |
| 67.5° | 947.9 | 937.5 | 1014.0 | 1246.9 | 1193.6 | 1011.7 | 937.5 | 945.6 | 1150.7 | 703.4 | 558.6 |
| 70° | 602.6 | 578.3 | 579.4 | 773.0 | 971.1 | 798.5 | 723.1 | 636.2 | 572.5 | 104.3 | 118.2 |
| 72.5° | 385.9 | 370.8 | 318.7 | 348.8 | 449.6 | 389.4 | 392.9 | 338.4 | 226.0 | 55.6 | 64.9 |
| 75° | 162.2 | 149.5 | 114.7 | 91.6 | 90.4 | 56.8 | 49.8 | 46.4 | 31.3 | 31.3 | 33.6 |
| 77.5° | 1.2 | 0.0 | 0.0 | 1.2 | 2.3 | 1.2 | 1.2 | 2.3 | 4.6 | 7.0 | 8.1 |
| 80° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 1.2 |
| 82.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 85° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 87.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P635939

CATALOG NUMBER: GWS-SA3E-827-U-SL2-W-GRSBK

CANDELA DISTRIBUTION (continued):

| | 90° | 95° | 105° | 115° | 125° | 135° | 145° | 155° | 165° | 175° | 180° |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 3330.6 | 3330.6 | 3330.6 | 3330.6 | 3330.6 | 3330.6 | 3330.6 | 3330.6 | 3330.6 | 3330.6 | 3330.6 |
| 2.5° | 3349.1 | 3321.3 | 3352.6 | 3364.2 | 3363.0 | 3364.2 | 3330.6 | 3307.4 | 3306.2 | 3277.3 | 3263.4 |
| 5° | 3361.9 | 3339.8 | 3363.0 | 3347.9 | 3312.0 | 3266.8 | 3206.6 | 3154.4 | 3131.2 | 3097.6 | 3081.4 |
| 7.5° | 3386.2 | 3363.0 | 3359.5 | 3299.3 | 3210.0 | 3115.0 | 3008.4 | 2913.4 | 2862.4 | 2801.0 | 2804.4 |
| 10° | 3403.6 | 3376.9 | 3331.7 | 3208.9 | 3060.6 | 2908.7 | 2750.0 | 2608.6 | 2519.4 | 2437.1 | 2423.2 |
| 12.5° | 3410.5 | 3371.1 | 3265.7 | 3080.3 | 2871.7 | 2673.5 | 2440.6 | 2238.9 | 2099.9 | 1992.1 | 1977.0 |
| 15° | 3423.3 | 3359.5 | 3181.1 | 2925.0 | 2638.7 | 2358.3 | 2061.6 | 1785.8 | 1601.5 | 1477.5 | 1488.0 |
| 17.5° | 3443.0 | 3346.8 | 3086.0 | 2751.1 | 2388.4 | 1992.1 | 1591.1 | 1274.7 | 1105.6 | 1033.7 | 1034.9 |
| 20° | 3470.8 | 3331.7 | 2981.7 | 2559.9 | 2088.3 | 1578.4 | 1112.5 | 873.8 | 826.3 | 824.0 | 820.5 |
| 22.5° | 3507.9 | 3316.7 | 2870.5 | 2350.2 | 1732.5 | 1105.6 | 740.5 | 666.3 | 686.0 | 724.3 | 731.2 |
| 25° | 3551.9 | 3298.1 | 2746.5 | 2113.8 | 1344.3 | 725.4 | 555.1 | 543.5 | 591.0 | 642.0 | 653.6 |
| 27.5° | 3620.3 | 3288.8 | 2605.1 | 1844.9 | 943.3 | 520.3 | 454.3 | 461.2 | 504.1 | 547.0 | 557.4 |
| 30° | 3736.2 | 3306.2 | 2451.0 | 1543.6 | 606.1 | 414.9 | 394.0 | 404.4 | 427.6 | 449.6 | 458.9 |
| 32.5° | 3893.8 | 3357.2 | 2301.5 | 1214.5 | 432.3 | 360.4 | 355.8 | 361.6 | 370.8 | 383.6 | 387.1 |
| 35° | 4078.0 | 3445.3 | 2147.4 | 869.1 | 356.9 | 329.1 | 324.5 | 324.5 | 329.1 | 331.4 | 332.6 |
| 37.5° | 4229.8 | 3538.0 | 2002.5 | 578.3 | 319.8 | 304.8 | 297.8 | 294.4 | 293.2 | 295.5 | 296.7 |
| 40° | 4295.9 | 3576.2 | 1844.9 | 420.7 | 293.2 | 282.8 | 272.3 | 261.9 | 261.9 | 270.0 | 271.2 |
| 42.5° | 4249.5 | 3533.4 | 1663.0 | 347.7 | 274.7 | 259.6 | 243.4 | 234.1 | 238.7 | 246.8 | 249.2 |
| 45° | 4151.0 | 3427.9 | 1462.5 | 307.1 | 256.1 | 236.4 | 217.9 | 212.1 | 216.7 | 227.1 | 229.5 |
| 47.5° | 4134.8 | 3358.4 | 1222.6 | 280.4 | 236.4 | 216.7 | 197.0 | 191.2 | 197.0 | 205.1 | 207.4 |
| 50° | 4295.9 | 3418.6 | 956.1 | 257.3 | 217.9 | 195.8 | 179.6 | 173.8 | 177.3 | 181.9 | 184.3 |
| 52.5° | 4590.2 | 3642.3 | 771.8 | 235.2 | 195.8 | 175.0 | 164.6 | 157.6 | 157.6 | 162.2 | 163.4 |
| 55° | 5024.8 | 4032.8 | 666.3 | 209.8 | 170.4 | 158.8 | 149.5 | 142.5 | 142.5 | 144.9 | 146.0 |
| 57.5° | 5525.5 | 4505.7 | 690.7 | 176.1 | 149.5 | 143.7 | 135.6 | 129.8 | 132.1 | 132.1 | 132.1 |
| 60° | 5455.9 | 4470.9 | 739.4 | 148.3 | 132.1 | 129.8 | 122.8 | 120.5 | 126.3 | 121.7 | 119.4 |
| 62.5° | 4018.9 | 3088.4 | 387.1 | 121.7 | 113.6 | 111.3 | 106.6 | 111.3 | 119.4 | 106.6 | 102.0 |
| 65° | 1951.5 | 1494.9 | 155.3 | 99.7 | 96.2 | 93.9 | 91.6 | 98.5 | 103.1 | 83.4 | 78.8 |
| 67.5° | 458.9 | 373.2 | 100.8 | 84.6 | 80.0 | 75.3 | 77.6 | 78.8 | 75.3 | 56.8 | 54.5 |
| 70° | 119.4 | 117.0 | 78.8 | 70.7 | 63.7 | 59.1 | 59.1 | 57.9 | 49.8 | 35.9 | 33.6 |
| 72.5° | 64.9 | 63.7 | 56.8 | 53.3 | 44.0 | 39.4 | 40.6 | 35.9 | 27.8 | 20.9 | 19.7 |
| 75° | 32.4 | 34.8 | 32.4 | 30.1 | 24.3 | 22.0 | 22.0 | 19.7 | 13.9 | 8.1 | 8.1 |
| 77.5° | 7.0 | 8.1 | 8.1 | 7.0 | 5.8 | 4.6 | 4.6 | 5.8 | 2.3 | 0.0 | 0.0 |
| 80° | 1.2 | 1.2 | 1.2 | 1.2 | 1.2 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 82.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 85° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 87.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Invue

Report Number: SP1-2407-157-9

Test Date: 10/03/2024

Luminaire Tested: EMM2-HTN-SA1A-827-U-5WQ

Data applicable to all product families utilizing light square engine

Test Information

Test Method: LM-79-2019
 Report Number: SP1-2407-157-9
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 10/03/2024
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: Invue
 Catalog Number: **EMM2-HTN-SA1A-827-U-5WQ**
 Description: Epic Modern Light Square 40W 5WQ Optic

Spectral Parameters

CCT (K): 2764
 CIE u': 0.2591
 CIE v': 0.5290
 Duv: 0.0020
 CIE x: 0.4581
 CIE y: 0.4156
 CIE z: 0.1263
 Peak Wavelength (nm): 603
 Dominant Wavelength (nm): 583
 Purity: 62.2537
 Rf: 84.7
 Rg: 94.6

| | | | |
|-----------|------|------|------|
| CRI (Ra): | 80.9 | | |
| R1: | 78.8 | R9: | -1.5 |
| R2: | 89.9 | R10: | 77.9 |
| R3: | 96.2 | R11: | 78.9 |
| R4: | 79.1 | R12: | 71.6 |
| R5: | 79.1 | R13: | 81.2 |
| R6: | 88.8 | R14: | 98.5 |
| R7: | 81.3 | R15: | 69.9 |
| R8: | 54.3 | | |



Test Conditions

Stabilization Time: 81M
 Operation Time: 2H 21M
 Sphere Temperature (°C): 25.2

REPORT NUMBER: SP1-2407-157-9

| Measurement and Test Equipment | | | |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument | Identification Number | Calibration Date | Calibration Due Date |
| Photometer | IN0058 | 6/18/2024 | 12/18/2024 |
| Power Meter | INXT2011004 | 2/8/2024 | 2/8/2025 |
| AC Power Source | IN0063 | 10/24/2023 | 10/24/2024 |
| DC Power Source | IN0208 | 10/24/2023 | 10/24/2024 |
| Sphere Thermometer | IN0085 | 10/24/2023 | 10/24/2024 |
| Room Thermometer | IN0046 | 10/24/2023 | 10/24/2024 |

REPORT NUMBER: SP1-2407-157-9

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 2700K 4-step quadrangle

REPORT NUMBER: SP1-2407-157-9

Photopic Flux vs. Wavelength



Photopic Lumens: 4337.9

| λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) |
|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|
| 360 | 0 | 0.0 | 490 | 18018 | 2.6 | 620 | 87426 | 22.8 | 750 | 2680 | 0.0 | 880 | 58 | 0.0 |
| 365 | 0 | 0.0 | 495 | 22295 | 3.9 | 625 | 83013 | 18.2 | 755 | 2287 | 0.0 | 885 | 46 | 0.0 |
| 370 | 0 | 0.0 | 500 | 26478 | 5.8 | 630 | 78077 | 14.1 | 760 | 1944 | 0.0 | 890 | 45 | 0.0 |
| 375 | 0 | 0.0 | 505 | 30524 | 8.5 | 635 | 72080 | 10.7 | 765 | 1653 | 0.0 | 895 | 41 | 0.0 |
| 380 | 0 | 0.0 | 510 | 33611 | 11.5 | 640 | 66249 | 7.9 | 770 | 1413 | 0.0 | 900 | 38 | 0.0 |
| 385 | 0 | 0.0 | 515 | 36490 | 15.2 | 645 | 59973 | 5.7 | 775 | 1198 | 0.0 | 905 | 33 | 0.0 |
| 390 | 0 | 0.0 | 520 | 38610 | 18.7 | 650 | 53972 | 3.9 | 780 | 1025 | 0.0 | 910 | 30 | 0.0 |
| 395 | 0 | 0.0 | 525 | 40511 | 21.9 | 655 | 48369 | 2.7 | 785 | 874 | 0.0 | 915 | 23 | 0.0 |
| 400 | 48 | 0.0 | 530 | 42223 | 24.9 | 660 | 42641 | 1.8 | 790 | 747 | 0.0 | 920 | 24 | 0.0 |
| 405 | 201 | 0.0 | 535 | 44137 | 27.6 | 665 | 37602 | 1.1 | 795 | 639 | 0.0 | 925 | 22 | 0.0 |
| 410 | 457 | 0.0 | 540 | 46032 | 30.0 | 670 | 32798 | 0.7 | 800 | 547 | 0.0 | 930 | 22 | 0.0 |
| 415 | 925 | 0.0 | 545 | 48553 | 32.5 | 675 | 28558 | 0.5 | 805 | 473 | 0.0 | 935 | 17 | 0.0 |
| 420 | 1816 | 0.0 | 550 | 51408 | 34.9 | 680 | 24782 | 0.3 | 810 | 401 | 0.0 | 940 | 13 | 0.0 |
| 425 | 3217 | 0.0 | 555 | 54711 | 37.4 | 685 | 21386 | 0.2 | 815 | 351 | 0.0 | 945 | 6 | 0.0 |
| 430 | 5520 | 0.0 | 560 | 58847 | 40.0 | 690 | 18413 | 0.1 | 820 | 307 | 0.0 | 950 | 10 | 0.0 |
| 435 | 9225 | 0.1 | 565 | 63386 | 42.4 | 695 | 15721 | 0.1 | 825 | 261 | 0.0 | 955 | 11 | 0.0 |
| 440 | 15522 | 0.2 | 570 | 68196 | 44.3 | 700 | 13432 | 0.0 | 830 | 228 | 0.0 | 960 | 8 | 0.0 |
| 445 | 27642 | 0.6 | 575 | 73613 | 46.0 | 705 | 11513 | 0.0 | 835 | 193 | 0.0 | 965 | 12 | 0.0 |
| 450 | 36602 | 0.9 | 580 | 79207 | 47.1 | 710 | 9780 | 0.0 | 840 | 174 | 0.0 | 970 | 3 | 0.0 |
| 455 | 28292 | 0.9 | 585 | 84248 | 47.0 | 715 | 8356 | 0.0 | 845 | 151 | 0.0 | 975 | 8 | 0.0 |
| 460 | 21166 | 0.9 | 590 | 88397 | 45.7 | 720 | 7161 | 0.0 | 850 | 123 | 0.0 | 980 | 2 | 0.0 |
| 465 | 19092 | 1.0 | 595 | 91428 | 43.4 | 725 | 6067 | 0.0 | 855 | 106 | 0.0 | 985 | 13 | 0.0 |
| 470 | 14951 | 0.9 | 600 | 93452 | 40.3 | 730 | 5164 | 0.0 | 860 | 95 | 0.0 | 990 | 16 | 0.0 |
| 475 | 12606 | 1.0 | 605 | 93959 | 36.4 | 735 | 4393 | 0.0 | 865 | 82 | 0.0 | 995 | 20 | 0.0 |
| 480 | 13323 | 1.3 | 610 | 93079 | 32.0 | 740 | 3694 | 0.0 | 870 | 77 | 0.0 | 1000 | 0 | 0.0 |
| 485 | 15164 | 1.8 | 615 | 90707 | 27.3 | 745 | 3157 | 0.0 | 875 | 65 | 0.0 | | | |

REPORT NUMBER: SP1-2407-157-9

Scotopic Flux vs. Wavelength




Scotopic Lumens: 5286.7

S/P: 1.22

| λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) |
|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|
| 360 | 0 | 0.0 | 490 | 18018 | 75.9 | 620 | 87426 | 0.4 | 750 | 2680 | 0.0 | 880 | 58 | 0.0 |
| 365 | 0 | 0.0 | 495 | 22295 | 93.2 | 625 | 83013 | 0.2 | 755 | 2287 | 0.0 | 885 | 46 | 0.0 |
| 370 | 0 | 0.0 | 500 | 26478 | 107.8 | 630 | 78077 | 0.1 | 760 | 1944 | 0.0 | 890 | 45 | 0.0 |
| 375 | 0 | 0.0 | 505 | 30524 | 118.7 | 635 | 72080 | 0.1 | 765 | 1653 | 0.0 | 895 | 41 | 0.0 |
| 380 | 0 | 0.0 | 510 | 33611 | 122.2 | 640 | 66249 | 0.1 | 770 | 1413 | 0.0 | 900 | 38 | 0.0 |
| 385 | 0 | 0.0 | 515 | 36490 | 120.8 | 645 | 59973 | 0.0 | 775 | 1198 | 0.0 | 905 | 33 | 0.0 |
| 390 | 0 | 0.0 | 520 | 38610 | 113.9 | 650 | 53972 | 0.0 | 780 | 1025 | 0.0 | 910 | 30 | 0.0 |
| 395 | 0 | 0.0 | 525 | 40511 | 104.1 | 655 | 48369 | 0.0 | 785 | 874 | 0.0 | 915 | 23 | 0.0 |
| 400 | 48 | 0.0 | 530 | 42223 | 92.4 | 660 | 42641 | 0.0 | 790 | 747 | 0.0 | 920 | 24 | 0.0 |
| 405 | 201 | 0.0 | 535 | 44137 | 80.5 | 665 | 37602 | 0.0 | 795 | 639 | 0.0 | 925 | 22 | 0.0 |
| 410 | 457 | 0.1 | 540 | 46032 | 68.2 | 670 | 32798 | 0.0 | 800 | 547 | 0.0 | 930 | 22 | 0.0 |
| 415 | 925 | 0.3 | 545 | 48553 | 57.1 | 675 | 28558 | 0.0 | 805 | 473 | 0.0 | 935 | 17 | 0.0 |
| 420 | 1816 | 1.1 | 550 | 51408 | 46.7 | 680 | 24782 | 0.0 | 810 | 401 | 0.0 | 940 | 13 | 0.0 |
| 425 | 3217 | 2.5 | 555 | 54711 | 37.4 | 685 | 21386 | 0.0 | 815 | 351 | 0.0 | 945 | 6 | 0.0 |
| 430 | 5520 | 5.9 | 560 | 58847 | 29.4 | 690 | 18413 | 0.0 | 820 | 307 | 0.0 | 950 | 10 | 0.0 |
| 435 | 9225 | 12.5 | 565 | 63386 | 22.5 | 695 | 15721 | 0.0 | 825 | 261 | 0.0 | 955 | 11 | 0.0 |
| 440 | 15522 | 26.3 | 570 | 68196 | 16.9 | 700 | 13432 | 0.0 | 830 | 228 | 0.0 | 960 | 8 | 0.0 |
| 445 | 27642 | 55.2 | 575 | 73613 | 12.4 | 705 | 11513 | 0.0 | 835 | 193 | 0.0 | 965 | 12 | 0.0 |
| 450 | 36602 | 85.4 | 580 | 79207 | 9.0 | 710 | 9780 | 0.0 | 840 | 174 | 0.0 | 970 | 3 | 0.0 |
| 455 | 28292 | 75.1 | 585 | 84248 | 6.3 | 715 | 8356 | 0.0 | 845 | 151 | 0.0 | 975 | 8 | 0.0 |
| 460 | 21166 | 63.2 | 590 | 88397 | 4.4 | 720 | 7161 | 0.0 | 850 | 123 | 0.0 | 980 | 2 | 0.0 |
| 465 | 19092 | 63.2 | 595 | 91428 | 3.0 | 725 | 6067 | 0.0 | 855 | 106 | 0.0 | 985 | 13 | 0.0 |
| 470 | 14951 | 54.2 | 600 | 93452 | 2.0 | 730 | 5164 | 0.0 | 860 | 95 | 0.0 | 990 | 16 | 0.0 |
| 475 | 12606 | 48.8 | 605 | 93959 | 1.3 | 735 | 4393 | 0.0 | 865 | 82 | 0.0 | 995 | 20 | 0.0 |
| 480 | 13323 | 54.2 | 610 | 93079 | 0.9 | 740 | 3694 | 0.0 | 870 | 77 | 0.0 | 1000 | 0 | 0.0 |
| 485 | 15164 | 63.3 | 615 | 90707 | 0.5 | 745 | 3157 | 0.0 | 875 | 65 | 0.0 | | | |

REPORT NUMBER: SP1-2407-157-9

Melanopic Flux vs. Wavelength



Melanopic Lumens: 9797

M/P: 2.26

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 0 | 0.0 | 490 | 18018 | 27.7 | 620 | 87426 | 1.1 | 750 | 2680 | 0.0 | 880 | 58 | 0.0 |
| 365 | 0 | 0.0 | 495 | 22295 | 36.0 | 625 | 83013 | 0.7 | 755 | 2287 | 0.0 | 885 | 46 | 0.0 |
| 370 | 0 | 0.0 | 500 | 26478 | 44.2 | 630 | 78077 | 0.4 | 760 | 1944 | 0.0 | 890 | 45 | 0.0 |
| 375 | 0 | 0.0 | 505 | 30524 | 51.8 | 635 | 72080 | 0.3 | 765 | 1653 | 0.0 | 895 | 41 | 0.0 |
| 380 | 0 | 0.0 | 510 | 33611 | 57.0 | 640 | 66249 | 0.2 | 770 | 1413 | 0.0 | 900 | 38 | 0.0 |
| 385 | 0 | 0.0 | 515 | 36490 | 60.5 | 645 | 59973 | 0.1 | 775 | 1198 | 0.0 | 905 | 33 | 0.0 |
| 390 | 0 | 0.0 | 520 | 38610 | 61.4 | 650 | 53972 | 0.1 | 780 | 1025 | 0.0 | 910 | 30 | 0.0 |
| 395 | 0 | 0.0 | 525 | 40511 | 60.6 | 655 | 48369 | 0.0 | 785 | 874 | 0.0 | 915 | 23 | 0.0 |
| 400 | 48 | 0.0 | 530 | 42223 | 58.2 | 660 | 42641 | 0.0 | 790 | 747 | 0.0 | 920 | 24 | 0.0 |
| 405 | 201 | 0.0 | 535 | 44137 | 55.0 | 665 | 37602 | 0.0 | 795 | 639 | 0.0 | 925 | 22 | 0.0 |
| 410 | 457 | 0.0 | 540 | 46032 | 50.9 | 670 | 32798 | 0.0 | 800 | 547 | 0.0 | 930 | 22 | 0.0 |
| 415 | 925 | 0.1 | 545 | 48553 | 46.6 | 675 | 28558 | 0.0 | 805 | 473 | 0.0 | 935 | 17 | 0.0 |
| 420 | 1816 | 0.3 | 550 | 51408 | 42.0 | 680 | 24782 | 0.0 | 810 | 401 | 0.0 | 940 | 13 | 0.0 |
| 425 | 3217 | 0.8 | 555 | 54711 | 37.4 | 685 | 21386 | 0.0 | 815 | 351 | 0.0 | 945 | 6 | 0.0 |
| 430 | 5520 | 1.9 | 560 | 58847 | 32.9 | 690 | 18413 | 0.0 | 820 | 307 | 0.0 | 950 | 10 | 0.0 |
| 435 | 9225 | 4.1 | 565 | 63386 | 28.4 | 695 | 15721 | 0.0 | 825 | 261 | 0.0 | 955 | 11 | 0.0 |
| 440 | 15522 | 8.7 | 570 | 68196 | 24.1 | 700 | 13432 | 0.0 | 830 | 228 | 0.0 | 960 | 8 | 0.0 |
| 445 | 27642 | 18.5 | 575 | 73613 | 20.0 | 705 | 11513 | 0.0 | 835 | 193 | 0.0 | 965 | 12 | 0.0 |
| 450 | 36602 | 28.3 | 580 | 79207 | 16.3 | 710 | 9780 | 0.0 | 840 | 174 | 0.0 | 970 | 3 | 0.0 |
| 455 | 28292 | 24.7 | 585 | 84248 | 12.9 | 715 | 8356 | 0.0 | 845 | 151 | 0.0 | 975 | 8 | 0.0 |
| 460 | 21166 | 20.4 | 590 | 88397 | 9.8 | 720 | 7161 | 0.0 | 850 | 123 | 0.0 | 980 | 2 | 0.0 |
| 465 | 19092 | 20.1 | 595 | 91428 | 7.3 | 725 | 6067 | 0.0 | 855 | 106 | 0.0 | 985 | 13 | 0.0 |
| 470 | 14951 | 17.2 | 600 | 93452 | 5.3 | 730 | 5164 | 0.0 | 860 | 95 | 0.0 | 990 | 16 | 0.0 |
| 475 | 12606 | 15.7 | 605 | 93959 | 3.7 | 735 | 4393 | 0.0 | 865 | 82 | 0.0 | 995 | 20 | 0.0 |
| 480 | 13323 | 18.0 | 610 | 93079 | 2.5 | 740 | 3694 | 0.0 | 870 | 77 | 0.0 | 1000 | 0 | 0.0 |
| 485 | 15164 | 21.9 | 615 | 90707 | 1.7 | 745 | 3157 | 0.0 | 875 | 65 | 0.0 | | | |

Summary

$R_f = 84.7$
 $R_g = 94.6$
 CIE $R_a = 80.9$
 $R_9 = -1.5$



Color Vector Graphics



Individual Sample Fidelity Index ($R_{f,i}$)

| | | | |
|------------|------------|------------|------------|
| CES01 = 86 | CES26 = 84 | CES51 = 95 | CES76 = 81 |
| CES02 = 63 | CES27 = 95 | CES52 = 94 | CES77 = 84 |
| CES03 = 31 | CES28 = 94 | CES53 = 89 | CES78 = 81 |
| CES04 = 71 | CES29 = 87 | CES54 = 91 | CES79 = 89 |
| CES05 = 50 | CES30 = 94 | CES55 = 90 | CES80 = 89 |
| CES06 = 52 | CES31 = 89 | CES56 = 86 | CES81 = 69 |
| CES07 = 43 | CES32 = 82 | CES57 = 85 | CES82 = 96 |
| CES08 = 41 | CES33 = 91 | CES58 = 86 | CES83 = 93 |
| CES09 = 29 | CES34 = 92 | CES59 = 91 | CES84 = 92 |
| CES10 = 77 | CES35 = 96 | CES60 = 94 | CES85 = 76 |
| CES11 = 60 | CES36 = 90 | CES61 = 89 | CES86 = 65 |
| CES12 = 66 | CES37 = 96 | CES62 = 94 | CES87 = 84 |
| CES13 = 44 | CES38 = 98 | CES63 = 87 | CES88 = 86 |
| CES14 = 74 | CES39 = 98 | CES64 = 82 | CES89 = 73 |
| CES15 = 72 | CES40 = 95 | CES65 = 78 | CES90 = 88 |
| CES16 = 48 | CES41 = 96 | CES66 = 81 | CES91 = 82 |
| CES17 = 50 | CES42 = 97 | CES67 = 80 | CES92 = 64 |
| CES18 = 57 | CES43 = 91 | CES68 = 83 | CES93 = 78 |
| CES19 = 73 | CES44 = 99 | CES69 = 88 | CES94 = 59 |
| CES20 = 67 | CES45 = 93 | CES70 = 80 | CES95 = 74 |
| CES21 = 87 | CES46 = 89 | CES71 = 79 | CES96 = 83 |
| CES22 = 79 | CES47 = 92 | CES72 = 92 | CES97 = 88 |
| CES23 = 92 | CES48 = 83 | CES73 = 75 | CES98 = 83 |
| CES24 = 91 | CES49 = 90 | CES74 = 91 | CES99 = 74 |
| CES25 = 72 | CES50 = 94 | CES75 = 81 | |



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)