

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: McGRAW-EDISON

Report Number: P635953

Luminaire Tested: GWS-SA3E-827-U-SLR-W-GRSBK

Issue Date: 1/10/2023

**Test Information**

Test Method: LM-79-2019  
Report Number: P635953  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2209-782-42)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 1/10/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: McGRAW-EDISON  
Catalog Number: GWS-SA3E-827-U-SLR-W-GRSBK  
Description: GALLEON WALL SLIM LUMINAIRE. (3) LIGHTSQUARES WITH 16 LEDS EACH AND  
SPILL LIGHT ELIMINATOR RIGHT OPTICS W/ FACTORY INSTALLED GLARE SHIELD, BK  
Light Source: (48) 2700K CCT, 80 CRI LEDS  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 8624.7 lumens  
Efficiency: N/A  
Efficacy: 54.2 lumens/watt  
Luminous Opening: Rectangular (W 1.5' x L: 0.5' x H: 0')  
IES Classification: Type III - Short  
BUG Rating: B2 - U0 - G1  
  
Input Watts (W): 159.2  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 0  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 28.75 FT



REPORT NUMBER: P635953  
 CATALOG NUMBER: GWS-SA3E-827-U-SLR-W-GRSBK

### Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd  
 - - - 1/2 Max cd



Based on 10 foot mounting height. Maximum calculated value = 27 fc  
 Type III - Short - N/A

REPORT NUMBER: P635953  
CATALOG NUMBER: GWS-SA3E-827-U-SLR-W-GRSBK

### Luminous Intensity Polar Plot



— Vertical Plane Through 45-Deg Lateral    - - - Horizontal Cone Through 57.5-Deg Vertical

REPORT NUMBER: P635953  
 CATALOG NUMBER: GWS-SA3E-827-U-SLR-W-GRSBK


**FLUX DISTRIBUTION:**

|                    |           | Downward | Upward | Total  |
|--------------------|-----------|----------|--------|--------|
| <b>House Side</b>  | Lumens    | 1931.3   | 0.0    | 1931.3 |
|                    | % Fixture | 22.4     | 0.0    | 22.4   |
| <b>Street Side</b> | Lumens    | 6693.4   | 0.0    | 6693.4 |
|                    | % Fixture | 77.6     | 0.0    | 77.6   |
| <b>Total</b>       | Lumens    | 8624.7   | 0.0    | 8624.7 |
|                    | % Fixture | 100.0    | 0.0    | 100.0  |

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 149.1  | 1.7       |
| 10°-20°   | 482.4  | 5.6       |
| 20°-30°   | 783.7  | 9.1       |
| 30°-40°   | 1210.9 | 14.0      |
| 40°-50°   | 1941.6 | 22.5      |
| 50°-60°   | 2653.7 | 30.8      |
| 60°-70°   | 1285.3 | 14.9      |
| 70°-80°   | 117.7  | 1.4       |
| 80°-90°   | 0.3    | 0.0       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-90°    | 8624.7 | 100.0     |
| 0°-180°   | 8624.7 | 100.0     |

**Coefficient of Utilization**



REPORT NUMBER: P635953


CATALOG NUMBER: GWS-SA3E-827-U-SLR-W-GRSBK

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

| Zone           | Lumens | % Fixture | Zone Rating/Lumen Limit |      |         |
|----------------|--------|-----------|-------------------------|------|---------|
|                |        |           | B                       | U    | G       |
| FL (0°-30°)    | 843.8  | 9.8       |                         |      |         |
| FM (30°-60°)   | 4591.1 | 53.2      |                         |      |         |
| FH (60°-80°)   | 1258.2 | 14.6      |                         |      | G1/1800 |
| FVH (80°-90°)  | 0.3    | 0.0       |                         |      | G0/10   |
| BL (0°-30°)    | 571.5  | 6.6       | B2/1000                 |      |         |
| BM (30°-60°)   | 1215.1 | 14.1      | B2/2500                 |      |         |
| BH (60°-80°)   | 144.8  | 1.7       | B1/500                  |      | G1/500  |
| BVH (80°-90°)  | 0.0    | 0.0       |                         |      | G0/10   |
| UL (90°-100°)  | 0.0    | 0.0       |                         | U0/0 |         |
| UH (100°-180°) | 0.0    | 0.0       |                         | U0/0 |         |

**BUG Rating: B2-U0-G1**

Type III Short





REPORT NUMBER: P635953  
 CATALOG NUMBER: GWS-SA3E-827-U-SLR-W-GRSBK

**CANDELA DISTRIBUTION (FULL):**

|       | 0°     | 1°     | 5°     | 15°    | 25°    | 35°     | 45°     | 55°     | 65°    | 75°    | 85°    |
|-------|--------|--------|--------|--------|--------|---------|---------|---------|--------|--------|--------|
| 0°    | 1515.9 | 1515.9 | 1515.9 | 1515.9 | 1515.9 | 1515.9  | 1515.9  | 1515.9  | 1515.9 | 1515.9 | 1515.9 |
| 2.5°  | 1642.2 | 1652.6 | 1670.0 | 1707.1 | 1738.4 | 1759.3  | 1768.5  | 1766.2  | 1753.5 | 1744.2 | 1725.7 |
| 5°    | 1818.4 | 1818.4 | 1852.0 | 1936.6 | 2001.5 | 2042.0  | 2062.9  | 2050.2  | 2024.7 | 1984.1 | 1921.5 |
| 7.5°  | 1972.5 | 1978.3 | 2035.1 | 2155.6 | 2254.1 | 2312.1  | 2345.7  | 2338.7  | 2293.5 | 2215.9 | 2090.7 |
| 10°   | 2093.0 | 2100.0 | 2175.3 | 2322.5 | 2438.4 | 2497.5  | 2547.3  | 2552.0  | 2502.1 | 2399.0 | 2255.3 |
| 12.5° | 2210.1 | 2217.0 | 2295.8 | 2437.2 | 2539.2 | 2563.6  | 2607.6  | 2625.0  | 2612.2 | 2539.2 | 2389.7 |
| 15°   | 2336.4 | 2352.6 | 2419.9 | 2525.3 | 2568.2 | 2539.2  | 2568.2  | 2599.5  | 2642.4 | 2635.4 | 2501.0 |
| 17.5° | 2460.4 | 2472.0 | 2540.4 | 2577.5 | 2529.9 | 2454.6  | 2468.5  | 2505.6  | 2603.0 | 2698.0 | 2611.1 |
| 20°   | 2575.1 | 2591.4 | 2648.2 | 2599.5 | 2455.8 | 2338.7  | 2339.9  | 2388.6  | 2536.9 | 2736.2 | 2723.5 |
| 22.5° | 2695.7 | 2720.0 | 2760.6 | 2623.8 | 2387.4 | 2247.2  | 2253.0  | 2297.0  | 2484.8 | 2772.2 | 2851.0 |
| 25°   | 2853.3 | 2876.5 | 2903.1 | 2684.1 | 2365.4 | 2202.0  | 2224.0  | 2264.6  | 2484.8 | 2833.6 | 3008.6 |
| 27.5° | 3066.5 | 3082.8 | 3083.9 | 2796.5 | 2403.6 | 2208.9  | 2255.3  | 2301.6  | 2558.9 | 2956.4 | 3219.5 |
| 30°   | 3334.2 | 3359.7 | 3326.1 | 2971.5 | 2523.0 | 2301.6  | 2370.0  | 2428.0  | 2718.9 | 3163.9 | 3530.1 |
| 32.5° | 3659.9 | 3695.8 | 3650.6 | 3231.1 | 2772.2 | 2621.5  | 2745.5  | 2779.1  | 2973.8 | 3464.0 | 3882.4 |
| 35°   | 4042.4 | 4072.5 | 4023.8 | 3590.4 | 3354.0 | 3381.8  | 3606.6  | 3563.7  | 3486.1 | 3833.7 | 4293.8 |
| 37.5° | 4461.9 | 4489.7 | 4395.8 | 4135.1 | 4213.9 | 4334.4  | 4693.7  | 4546.5  | 4296.2 | 4310.1 | 4740.0 |
| 40°   | 4846.7 | 4876.8 | 4729.6 | 4727.3 | 4889.5 | 5109.7  | 5543.2  | 5340.4  | 4999.6 | 4933.6 | 5158.4 |
| 42.5° | 5245.3 | 5266.2 | 5132.9 | 5042.5 | 5411.1 | 5864.2  | 6323.1  | 6049.6  | 5465.5 | 5393.7 | 5682.2 |
| 45°   | 5814.4 | 5858.4 | 5620.8 | 5197.8 | 5880.4 | 6732.2  | 7372.0  | 6837.7  | 5783.1 | 5725.1 | 6484.2 |
| 47.5° | 6651.1 | 6683.6 | 6199.1 | 5295.2 | 6317.3 | 7813.5  | 8682.7  | 7859.9  | 6062.4 | 5930.3 | 7580.6 |
| 50°   | 7343.0 | 7365.0 | 6731.1 | 5401.8 | 6782.1 | 8979.4  | 10176.6 | 9072.1  | 6376.4 | 6269.8 | 8603.9 |
| 52.5° | 7852.9 | 7936.4 | 7429.9 | 5620.8 | 7392.8 | 10350.4 | 11830.4 | 10508.0 | 6866.7 | 6925.8 | 9452.3 |
| 55°   | 7958.4 | 8072.0 | 7907.4 | 5755.3 | 7930.6 | 11746.9 | 13357.9 | 11793.3 | 7355.7 | 7423.0 | 9737.4 |
| 57.5° | 6994.2 | 7084.6 | 7221.3 | 5212.9 | 7917.8 | 12386.7 | 14244.4 | 12219.8 | 7133.2 | 6656.9 | 8670.0 |
| 60°   | 5239.5 | 5302.1 | 5550.1 | 3984.4 | 7281.6 | 11821.1 | 13553.7 | 11494.3 | 6237.4 | 5079.6 | 6605.9 |
| 62.5° | 3107.1 | 3134.9 | 3449.0 | 2580.9 | 6043.8 | 10180.1 | 11240.5 | 9918.1  | 4928.9 | 3416.5 | 4045.8 |
| 65°   | 1192.5 | 1181.0 | 1420.9 | 1273.7 | 4444.5 | 8109.1  | 8360.5  | 7560.9  | 3381.8 | 1565.7 | 1542.5 |
| 67.5° | 184.3  | 176.2  | 237.6  | 376.7  | 3205.6 | 5619.7  | 5516.5  | 5449.3  | 2118.5 | 365.1  | 318.7  |
| 70°   | 41.7   | 41.7   | 51.0   | 111.3  | 1958.6 | 3301.8  | 3533.6  | 3369.0  | 1356.0 | 77.6   | 41.7   |
| 72.5° | 19.7   | 19.7   | 24.3   | 47.5   | 709.3  | 1360.6  | 1585.4  | 1561.1  | 440.4  | 25.5   | 15.1   |
| 75°   | 7.0    | 8.1    | 8.1    | 10.4   | 42.9   | 70.7    | 162.3   | 115.9   | 27.8   | 0.0    | 0.0    |
| 77.5° | 2.3    | 2.3    | 2.3    | 2.3    | 0.0    | 0.0     | 0.0     | 0.0     | 0.0    | 0.0    | 0.0    |
| 80°   | 1.2    | 1.2    | 1.2    | 0.0    | 0.0    | 0.0     | 0.0     | 0.0     | 0.0    | 0.0    | 0.0    |
| 82.5° | 1.2    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0     | 0.0     | 0.0     | 0.0    | 0.0    | 0.0    |
| 85°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0     | 0.0     | 0.0     | 0.0    | 0.0    | 0.0    |
| 87.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0     | 0.0     | 0.0     | 0.0    | 0.0    | 0.0    |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0     | 0.0     | 0.0     | 0.0    | 0.0    | 0.0    |



REPORT NUMBER: P635953  
 CATALOG NUMBER: GWS-SA3E-827-U-SLR-W-GRSBK

**CANDELA DISTRIBUTION (continued):**

|       | 90°    | 95°    | 105°   | 115°   | 125°   | 135°   | 145°   | 155°   | 165°   | 175°   | 180°   |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°    | 1515.9 | 1515.9 | 1515.9 | 1515.9 | 1515.9 | 1515.9 | 1515.9 | 1515.9 | 1515.9 | 1515.9 | 1515.9 |
| 2.5°  | 1685.1 | 1677.0 | 1646.8 | 1606.3 | 1566.9 | 1532.1 | 1496.2 | 1453.3 | 1422.0 | 1386.1 | 1374.5 |
| 5°    | 1872.8 | 1821.8 | 1739.6 | 1653.8 | 1575.0 | 1507.8 | 1442.9 | 1373.3 | 1322.3 | 1271.3 | 1254.0 |
| 7.5°  | 2031.6 | 1956.3 | 1823.0 | 1694.4 | 1586.6 | 1491.5 | 1397.7 | 1302.6 | 1228.5 | 1168.2 | 1149.7 |
| 10°   | 2174.2 | 2087.2 | 1908.8 | 1750.0 | 1614.4 | 1504.3 | 1390.7 | 1271.3 | 1175.2 | 1103.3 | 1085.9 |
| 12.5° | 2297.0 | 2196.2 | 1981.8 | 1791.7 | 1626.0 | 1499.7 | 1389.6 | 1294.5 | 1207.6 | 1125.3 | 1103.3 |
| 15°   | 2400.1 | 2288.9 | 2043.2 | 1819.5 | 1608.6 | 1441.7 | 1345.5 | 1330.5 | 1323.5 | 1233.1 | 1190.2 |
| 17.5° | 2501.0 | 2375.8 | 2093.0 | 1832.3 | 1559.9 | 1339.7 | 1270.2 | 1338.6 | 1411.6 | 1352.5 | 1298.0 |
| 20°   | 2606.4 | 2463.9 | 2144.0 | 1834.6 | 1478.8 | 1225.0 | 1213.4 | 1321.2 | 1413.9 | 1395.4 | 1344.4 |
| 22.5° | 2730.4 | 2574.0 | 2207.8 | 1833.4 | 1376.8 | 1127.6 | 1171.7 | 1287.6 | 1362.9 | 1361.7 | 1321.2 |
| 25°   | 2910.1 | 2713.1 | 2293.5 | 1840.4 | 1265.6 | 1052.3 | 1125.3 | 1230.8 | 1292.2 | 1289.9 | 1256.3 |
| 27.5° | 3102.5 | 2878.8 | 2404.8 | 1857.8 | 1170.5 | 1008.3 | 1070.9 | 1153.1 | 1206.4 | 1204.1 | 1175.2 |
| 30°   | 3372.5 | 3070.0 | 2511.4 | 1858.9 | 1102.1 | 985.1  | 1010.6 | 1067.4 | 1118.4 | 1112.6 | 1090.6 |
| 32.5° | 3700.5 | 3285.6 | 2600.6 | 1792.9 | 1059.3 | 963.1  | 948.0  | 977.0  | 1016.4 | 1008.3 | 1002.5 |
| 35°   | 4096.8 | 3541.7 | 2677.1 | 1648.0 | 993.2  | 919.0  | 878.5  | 884.3  | 912.1  | 916.7  | 914.4  |
| 37.5° | 4548.8 | 3846.5 | 2772.2 | 1456.8 | 904.0  | 855.3  | 800.8  | 796.2  | 812.4  | 827.5  | 839.1  |
| 40°   | 4995.0 | 4189.5 | 2900.8 | 1263.2 | 822.8  | 774.2  | 722.0  | 710.4  | 717.4  | 744.0  | 768.4  |
| 42.5° | 5496.8 | 4587.1 | 3039.9 | 1097.5 | 767.2  | 684.9  | 635.1  | 613.1  | 632.8  | 675.7  | 704.6  |
| 45°   | 6220.0 | 5144.5 | 3175.5 | 965.4  | 744.0  | 606.1  | 538.9  | 536.6  | 558.6  | 614.2  | 646.7  |
| 47.5° | 7235.2 | 5865.4 | 3264.7 | 862.2  | 742.9  | 544.7  | 464.7  | 478.6  | 504.1  | 558.6  | 595.7  |
| 50°   | 8224.9 | 6768.2 | 3166.2 | 783.4  | 718.5  | 504.1  | 409.1  | 436.9  | 462.4  | 509.9  | 548.2  |
| 52.5° | 8821.8 | 7253.8 | 2782.6 | 709.3  | 643.2  | 485.6  | 354.6  | 403.3  | 407.9  | 450.8  | 491.4  |
| 55°   | 8759.2 | 6939.7 | 2131.3 | 594.5  | 531.9  | 458.9  | 297.8  | 363.9  | 366.2  | 398.7  | 433.4  |
| 57.5° | 7602.6 | 5958.1 | 1463.7 | 482.1  | 399.8  | 379.0  | 245.7  | 307.1  | 329.1  | 348.8  | 374.3  |
| 60°   | 5666.0 | 4347.2 | 652.5  | 391.7  | 253.8  | 256.1  | 209.8  | 231.8  | 265.4  | 288.6  | 310.6  |
| 62.5° | 3338.9 | 2501.0 | 265.4  | 235.3  | 140.2  | 161.1  | 169.2  | 169.2  | 190.1  | 207.4  | 221.4  |
| 65°   | 1262.1 | 875.0  | 107.8  | 118.2  | 73.0   | 75.3   | 99.7   | 122.8  | 139.1  | 154.1  | 172.7  |
| 67.5° | 221.4  | 153.0  | 55.6   | 44.0   | 42.9   | 38.2   | 51.0   | 80.0   | 89.2   | 100.8  | 108.9  |
| 70°   | 37.1   | 31.3   | 23.2   | 22.0   | 19.7   | 20.9   | 33.6   | 56.8   | 62.6   | 66.1   | 69.5   |
| 72.5° | 10.4   | 9.3    | 7.0    | 5.8    | 4.6    | 5.8    | 20.9   | 44.0   | 46.4   | 48.7   | 52.2   |
| 75°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 8.1    | 31.3   | 33.6   | 34.8   | 38.2   |
| 77.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 7.0    | 9.3    | 11.6   | 9.3    |
| 80°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 82.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 85°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 87.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |





REPORT NUMBER: P635953  
 CATALOG NUMBER: GWS-SA3E-827-U-SLR-W-GRSBK

**CANDELA DISTRIBUTION (continued):**

|       | 185°   | 195°   | 205°   | 215°   | 225°   | 235°   | 245°   | 255°   | 265°   | 270°   | 275°   |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°    | 1515.9 | 1515.9 | 1515.9 | 1515.9 | 1515.9 | 1515.9 | 1515.9 | 1515.9 | 1515.9 | 1515.9 | 1515.9 |
| 2.5°  | 1367.5 | 1344.4 | 1331.6 | 1324.7 | 1324.7 | 1315.4 | 1305.0 | 1301.5 | 1316.5 | 1316.5 | 1342.0 |
| 5°    | 1231.9 | 1213.4 | 1192.5 | 1179.8 | 1160.1 | 1163.6 | 1152.0 | 1150.8 | 1165.9 | 1172.8 | 1199.5 |
| 7.5°  | 1138.1 | 1114.9 | 1102.1 | 1094.0 | 1083.6 | 1079.0 | 1068.5 | 1065.1 | 1073.2 | 1084.8 | 1110.3 |
| 10°   | 1075.5 | 1072.0 | 1070.9 | 1076.6 | 1076.6 | 1070.9 | 1061.6 | 1055.8 | 1058.1 | 1080.1 | 1109.1 |
| 12.5° | 1091.7 | 1098.7 | 1101.0 | 1110.3 | 1114.9 | 1110.3 | 1103.3 | 1105.6 | 1120.7 | 1161.3 | 1204.1 |
| 15°   | 1162.4 | 1156.6 | 1154.3 | 1158.9 | 1162.4 | 1157.8 | 1155.5 | 1172.8 | 1225.0 | 1282.9 | 1331.6 |
| 17.5° | 1237.7 | 1200.7 | 1184.4 | 1184.4 | 1186.7 | 1184.4 | 1186.7 | 1220.4 | 1305.0 | 1362.9 | 1398.8 |
| 20°   | 1276.0 | 1207.6 | 1182.1 | 1176.3 | 1181.0 | 1182.1 | 1190.2 | 1228.5 | 1321.2 | 1361.7 | 1369.9 |
| 22.5° | 1264.4 | 1178.6 | 1149.7 | 1145.0 | 1149.7 | 1154.3 | 1162.4 | 1194.9 | 1281.8 | 1302.6 | 1299.2 |
| 25°   | 1206.4 | 1121.8 | 1098.7 | 1098.7 | 1109.1 | 1107.9 | 1111.4 | 1134.6 | 1206.4 | 1219.2 | 1213.4 |
| 27.5° | 1133.4 | 1053.5 | 1033.8 | 1045.4 | 1054.6 | 1052.3 | 1053.5 | 1073.2 | 1126.5 | 1130.0 | 1124.2 |
| 30°   | 1059.3 | 989.7  | 971.2  | 985.1  | 997.8  | 995.5  | 996.7  | 1016.4 | 1050.0 | 1046.5 | 1038.4 |
| 32.5° | 983.9  | 932.9  | 919.0  | 927.1  | 946.8  | 944.5  | 949.2  | 970.0  | 982.8  | 967.7  | 958.4  |
| 35°   | 914.4  | 887.7  | 877.3  | 881.9  | 897.0  | 900.5  | 908.6  | 922.5  | 922.5  | 904.0  | 887.7  |
| 37.5° | 849.5  | 846.0  | 839.1  | 833.3  | 847.2  | 857.6  | 869.2  | 885.4  | 862.2  | 835.6  | 820.5  |
| 40°   | 789.2  | 804.3  | 795.0  | 780.0  | 788.1  | 803.1  | 826.3  | 839.1  | 811.3  | 784.6  | 759.1  |
| 42.5° | 733.6  | 759.1  | 755.6  | 737.1  | 744.0  | 757.9  | 784.6  | 795.0  | 762.6  | 732.4  | 708.1  |
| 45°   | 680.3  | 716.2  | 718.5  | 695.4  | 702.3  | 716.2  | 747.5  | 751.0  | 709.3  | 676.8  | 659.4  |
| 47.5° | 633.9  | 673.3  | 674.5  | 657.1  | 659.4  | 679.1  | 708.1  | 709.3  | 661.8  | 631.6  | 609.6  |
| 50°   | 589.9  | 635.1  | 638.6  | 623.5  | 625.8  | 649.0  | 673.3  | 668.7  | 617.7  | 586.4  | 566.7  |
| 52.5° | 536.6  | 598.0  | 606.1  | 599.2  | 608.4  | 627.0  | 642.0  | 625.8  | 566.7  | 535.4  | 518.0  |
| 55°   | 478.6  | 558.6  | 576.0  | 571.4  | 581.8  | 596.9  | 600.3  | 589.9  | 515.7  | 484.4  | 468.2  |
| 57.5° | 411.4  | 460.1  | 490.2  | 481.0  | 489.1  | 504.1  | 514.6  | 506.5  | 450.8  | 426.5  | 412.6  |
| 60°   | 340.7  | 373.2  | 380.1  | 365.1  | 358.1  | 384.8  | 409.1  | 398.7  | 351.2  | 336.1  | 319.9  |
| 62.5° | 249.2  | 286.3  | 290.9  | 271.2  | 263.1  | 292.1  | 312.9  | 302.5  | 250.3  | 234.1  | 221.4  |
| 65°   | 199.3  | 234.1  | 243.4  | 224.8  | 220.2  | 242.2  | 255.0  | 229.5  | 192.4  | 175.0  | 161.1  |
| 67.5° | 131.0  | 158.8  | 183.1  | 182.0  | 172.7  | 179.6  | 170.4  | 149.5  | 122.8  | 113.6  | 104.3  |
| 70°   | 81.1   | 97.4   | 112.4  | 118.2  | 117.1  | 114.7  | 102.0  | 86.9   | 78.8   | 75.3   | 70.7   |
| 72.5° | 62.6   | 78.8   | 90.4   | 93.9   | 95.0   | 91.6   | 81.1   | 67.2   | 59.1   | 54.5   | 51.0   |
| 75°   | 46.4   | 59.1   | 68.4   | 73.0   | 75.3   | 73.0   | 62.6   | 53.3   | 45.2   | 41.7   | 38.2   |
| 77.5° | 16.2   | 19.7   | 24.3   | 26.7   | 25.5   | 24.3   | 22.0   | 22.0   | 17.4   | 16.2   | 13.9   |
| 80°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 82.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 85°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 87.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



REPORT NUMBER: P635953

CATALOG NUMBER: GWS-SA3E-827-U-SLR-W-GRSBK

**CANDELA DISTRIBUTION (continued):**

|       | 285°   | 295°   | 305°   | 315°   | 325°   | 335°   | 345°   | 355°   | 359°   | 360°   |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°    | 1515.9 | 1515.9 | 1515.9 | 1515.9 | 1515.9 | 1515.9 | 1515.9 | 1515.9 | 1515.9 | 1515.9 |
| 2.5°  | 1371.0 | 1391.9 | 1430.1 | 1464.9 | 1502.0 | 1540.2 | 1581.9 | 1624.8 | 1644.5 | 1642.2 |
| 5°    | 1240.1 | 1285.3 | 1347.8 | 1416.2 | 1492.7 | 1575.0 | 1666.5 | 1760.4 | 1801.0 | 1818.4 |
| 7.5°  | 1157.8 | 1221.5 | 1303.8 | 1390.7 | 1491.5 | 1608.6 | 1746.5 | 1893.7 | 1952.8 | 1972.5 |
| 10°   | 1168.2 | 1242.4 | 1310.8 | 1395.4 | 1503.1 | 1655.0 | 1826.5 | 2001.5 | 2071.0 | 2093.0 |
| 12.5° | 1252.8 | 1269.0 | 1287.6 | 1357.1 | 1492.7 | 1689.7 | 1899.5 | 2108.1 | 2188.1 | 2210.1 |
| 15°   | 1329.3 | 1254.0 | 1219.2 | 1282.9 | 1455.6 | 1714.1 | 1973.7 | 2222.8 | 2310.9 | 2336.4 |
| 17.5° | 1332.8 | 1219.2 | 1141.5 | 1191.4 | 1395.4 | 1724.5 | 2046.7 | 2339.9 | 2436.1 | 2460.4 |
| 20°   | 1289.9 | 1181.0 | 1081.3 | 1082.4 | 1313.1 | 1722.2 | 2106.9 | 2445.3 | 2553.1 | 2575.1 |
| 22.5° | 1227.3 | 1135.8 | 1032.6 | 996.7  | 1225.0 | 1717.5 | 2173.0 | 2557.8 | 2674.8 | 2695.7 |
| 25°   | 1157.8 | 1077.8 | 986.3  | 931.8  | 1136.9 | 1722.2 | 2265.7 | 2704.9 | 2833.6 | 2853.3 |
| 27.5° | 1082.4 | 1014.1 | 950.3  | 906.3  | 1062.7 | 1739.6 | 2377.0 | 2892.7 | 3045.7 | 3066.5 |
| 30°   | 1003.6 | 952.6  | 927.1  | 900.5  | 1016.4 | 1744.2 | 2497.5 | 3111.7 | 3305.3 | 3334.2 |
| 32.5° | 926.0  | 898.2  | 899.3  | 904.0  | 972.3  | 1711.7 | 2607.6 | 3355.1 | 3613.6 | 3659.9 |
| 35°   | 854.1  | 846.0  | 869.2  | 892.4  | 908.6  | 1628.3 | 2703.8 | 3642.5 | 3994.8 | 4042.4 |
| 37.5° | 792.7  | 799.7  | 828.6  | 851.8  | 839.1  | 1510.1 | 2831.3 | 4001.8 | 4421.3 | 4461.9 |
| 40°   | 733.6  | 751.0  | 784.6  | 795.0  | 785.8  | 1372.2 | 2984.3 | 4348.3 | 4791.0 | 4846.7 |
| 42.5° | 679.1  | 691.9  | 739.4  | 741.7  | 770.7  | 1231.9 | 3131.4 | 4721.5 | 5216.4 | 5245.3 |
| 45°   | 635.1  | 632.8  | 681.5  | 696.5  | 790.4  | 1076.6 | 3275.1 | 5218.7 | 5772.6 | 5814.4 |
| 47.5° | 592.2  | 589.9  | 601.5  | 669.9  | 798.5  | 932.9  | 3417.7 | 5946.5 | 6579.3 | 6651.1 |
| 50°   | 551.7  | 555.1  | 519.2  | 657.1  | 754.5  | 822.8  | 3482.6 | 6619.8 | 7312.9 | 7343.0 |
| 52.5° | 515.7  | 503.0  | 440.4  | 615.4  | 660.6  | 718.5  | 3298.3 | 6925.8 | 7767.2 | 7852.9 |
| 55°   | 464.7  | 394.0  | 362.7  | 499.5  | 521.5  | 627.0  | 2701.5 | 6748.5 | 7806.6 | 7958.4 |
| 57.5° | 397.5  | 309.4  | 308.3  | 368.5  | 368.5  | 581.8  | 1730.3 | 5765.7 | 6727.6 | 6994.2 |
| 60°   | 306.0  | 239.9  | 255.0  | 256.1  | 236.4  | 424.2  | 971.2  | 4176.8 | 4974.1 | 5239.5 |
| 62.5° | 217.9  | 183.1  | 192.4  | 153.0  | 135.6  | 212.1  | 465.9  | 2404.8 | 3070.0 | 3107.1 |
| 65°   | 146.0  | 124.0  | 100.8  | 84.6   | 83.4   | 90.4   | 192.4  | 869.2  | 1056.9 | 1192.5 |
| 67.5° | 96.2   | 75.3   | 53.3   | 53.3   | 60.3   | 60.3   | 73.0   | 143.7  | 201.7  | 184.3  |
| 70°   | 62.6   | 52.2   | 33.6   | 32.5   | 39.4   | 39.4   | 37.1   | 39.4   | 41.7   | 41.7   |
| 72.5° | 46.4   | 39.4   | 19.7   | 17.4   | 22.0   | 23.2   | 20.9   | 19.7   | 19.7   | 19.7   |
| 75°   | 34.8   | 27.8   | 11.6   | 8.1    | 10.4   | 13.9   | 11.6   | 8.1    | 8.1    | 7.0    |
| 77.5° | 13.9   | 10.4   | 4.6    | 3.5    | 5.8    | 8.1    | 7.0    | 3.5    | 2.3    | 2.3    |
| 80°   | 1.2    | 2.3    | 2.3    | 2.3    | 3.5    | 4.6    | 5.8    | 2.3    | 1.2    | 1.2    |
| 82.5° | 0.0    | 1.2    | 1.2    | 1.2    | 2.3    | 3.5    | 4.6    | 2.3    | 1.2    | 1.2    |
| 85°   | 0.0    | 0.0    | 0.0    | 0.0    | 2.3    | 3.5    | 2.3    | 1.2    | 0.0    | 0.0    |
| 87.5° | 0.0    | 0.0    | 0.0    | 0.0    | 1.2    | 3.5    | 2.3    | 1.2    | 0.0    | 0.0    |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Invue

Report Number: SP1-2407-157-9

Test Date: 10/03/2024

Luminaire Tested: EMM2-HTN-SA1A-827-U-5WQ

Data applicable to all product families utilizing light square engine

**Test Information**

Test Method: LM-79-2019  
 Report Number: SP1-2407-157-9  
 Test Lab: COOPER LIGHTING SOLUTIONS  
 Photometer: SP1 - 76IN SPHERE  
 Measurement Geometry: 4π  
 Issue Date: 10/03/2024  
 Manufacturer: COOPER LIGHTING SOLUTIONS  
 Product Line: Invue  
 Catalog Number: **EMM2-HTN-SA1A-827-U-5WQ**  
 Description: Epic Modern Light Square 40W 5WQ Optic

**Spectral Parameters**

CCT (K): 2764  
 CIE u': 0.2591  
 CIE v': 0.5290  
 Duv: 0.0020  
 CIE x: 0.4581  
 CIE y: 0.4156  
 CIE z: 0.1263  
 Peak Wavelength (nm): 603  
 Dominant Wavelength (nm): 583  
 Purity: 62.2537  
 Rf: 84.7  
 Rg: 94.6

|           |      |      |      |
|-----------|------|------|------|
| CRI (Ra): | 80.9 |      |      |
| R1:       | 78.8 | R9:  | -1.5 |
| R2:       | 89.9 | R10: | 77.9 |
| R3:       | 96.2 | R11: | 78.9 |
| R4:       | 79.1 | R12: | 71.6 |
| R5:       | 79.1 | R13: | 81.2 |
| R6:       | 88.8 | R14: | 98.5 |
| R7:       | 81.3 | R15: | 69.9 |
| R8:       | 54.3 |      |      |



**Test Conditions**


Stabilization Time: 81M  
 Operation Time: 2H 21M  
 Sphere Temperature (°C): 25.2

REPORT NUMBER: SP1-2407-157-9


| Measurement and Test Equipment |                       |                  |                      |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument                     | Identification Number | Calibration Date | Calibration Due Date |
| Photometer                     | IN0058                | 6/18/2024        | 12/18/2024           |
| Power Meter                    | INXT2011004           | 2/8/2024         | 2/8/2025             |
| AC Power Source                | IN0063                | 10/24/2023       | 10/24/2024           |
| DC Power Source                | IN0208                | 10/24/2023       | 10/24/2024           |
| Sphere Thermometer             | IN0085                | 10/24/2023       | 10/24/2024           |
| Room Thermometer               | IN0046                | 10/24/2023       | 10/24/2024           |

REPORT NUMBER: SP1-2407-157-9

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 2700K 4-step quadrangle

REPORT NUMBER: SP1-2407-157-9

**Photopic Flux vs. Wavelength**




**Photopic Lumens: 4337.9**

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360    | 0             | 0.0           | 490    | 18018         | 2.6           | 620    | 87426         | 22.8          | 750    | 2680          | 0.0           | 880    | 58            | 0.0           |
| 365    | 0             | 0.0           | 495    | 22295         | 3.9           | 625    | 83013         | 18.2          | 755    | 2287          | 0.0           | 885    | 46            | 0.0           |
| 370    | 0             | 0.0           | 500    | 26478         | 5.8           | 630    | 78077         | 14.1          | 760    | 1944          | 0.0           | 890    | 45            | 0.0           |
| 375    | 0             | 0.0           | 505    | 30524         | 8.5           | 635    | 72080         | 10.7          | 765    | 1653          | 0.0           | 895    | 41            | 0.0           |
| 380    | 0             | 0.0           | 510    | 33611         | 11.5          | 640    | 66249         | 7.9           | 770    | 1413          | 0.0           | 900    | 38            | 0.0           |
| 385    | 0             | 0.0           | 515    | 36490         | 15.2          | 645    | 59973         | 5.7           | 775    | 1198          | 0.0           | 905    | 33            | 0.0           |
| 390    | 0             | 0.0           | 520    | 38610         | 18.7          | 650    | 53972         | 3.9           | 780    | 1025          | 0.0           | 910    | 30            | 0.0           |
| 395    | 0             | 0.0           | 525    | 40511         | 21.9          | 655    | 48369         | 2.7           | 785    | 874           | 0.0           | 915    | 23            | 0.0           |
| 400    | 48            | 0.0           | 530    | 42223         | 24.9          | 660    | 42641         | 1.8           | 790    | 747           | 0.0           | 920    | 24            | 0.0           |
| 405    | 201           | 0.0           | 535    | 44137         | 27.6          | 665    | 37602         | 1.1           | 795    | 639           | 0.0           | 925    | 22            | 0.0           |
| 410    | 457           | 0.0           | 540    | 46032         | 30.0          | 670    | 32798         | 0.7           | 800    | 547           | 0.0           | 930    | 22            | 0.0           |
| 415    | 925           | 0.0           | 545    | 48553         | 32.5          | 675    | 28558         | 0.5           | 805    | 473           | 0.0           | 935    | 17            | 0.0           |
| 420    | 1816          | 0.0           | 550    | 51408         | 34.9          | 680    | 24782         | 0.3           | 810    | 401           | 0.0           | 940    | 13            | 0.0           |
| 425    | 3217          | 0.0           | 555    | 54711         | 37.4          | 685    | 21386         | 0.2           | 815    | 351           | 0.0           | 945    | 6             | 0.0           |
| 430    | 5520          | 0.0           | 560    | 58847         | 40.0          | 690    | 18413         | 0.1           | 820    | 307           | 0.0           | 950    | 10            | 0.0           |
| 435    | 9225          | 0.1           | 565    | 63386         | 42.4          | 695    | 15721         | 0.1           | 825    | 261           | 0.0           | 955    | 11            | 0.0           |
| 440    | 15522         | 0.2           | 570    | 68196         | 44.3          | 700    | 13432         | 0.0           | 830    | 228           | 0.0           | 960    | 8             | 0.0           |
| 445    | 27642         | 0.6           | 575    | 73613         | 46.0          | 705    | 11513         | 0.0           | 835    | 193           | 0.0           | 965    | 12            | 0.0           |
| 450    | 36602         | 0.9           | 580    | 79207         | 47.1          | 710    | 9780          | 0.0           | 840    | 174           | 0.0           | 970    | 3             | 0.0           |
| 455    | 28292         | 0.9           | 585    | 84248         | 47.0          | 715    | 8356          | 0.0           | 845    | 151           | 0.0           | 975    | 8             | 0.0           |
| 460    | 21166         | 0.9           | 590    | 88397         | 45.7          | 720    | 7161          | 0.0           | 850    | 123           | 0.0           | 980    | 2             | 0.0           |
| 465    | 19092         | 1.0           | 595    | 91428         | 43.4          | 725    | 6067          | 0.0           | 855    | 106           | 0.0           | 985    | 13            | 0.0           |
| 470    | 14951         | 0.9           | 600    | 93452         | 40.3          | 730    | 5164          | 0.0           | 860    | 95            | 0.0           | 990    | 16            | 0.0           |
| 475    | 12606         | 1.0           | 605    | 93959         | 36.4          | 735    | 4393          | 0.0           | 865    | 82            | 0.0           | 995    | 20            | 0.0           |
| 480    | 13323         | 1.3           | 610    | 93079         | 32.0          | 740    | 3694          | 0.0           | 870    | 77            | 0.0           | 1000   | 0             | 0.0           |
| 485    | 15164         | 1.8           | 615    | 90707         | 27.3          | 745    | 3157          | 0.0           | 875    | 65            | 0.0           |        |               |               |

REPORT NUMBER: SP1-2407-157-9

**Scotopic Flux vs. Wavelength**



**Scotopic Lumens: 5286.7**


**S/P: 1.22**

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360    | 0             | 0.0           | 490    | 18018         | 75.9          | 620    | 87426         | 0.4           | 750    | 2680          | 0.0           | 880    | 58            | 0.0           |
| 365    | 0             | 0.0           | 495    | 22295         | 93.2          | 625    | 83013         | 0.2           | 755    | 2287          | 0.0           | 885    | 46            | 0.0           |
| 370    | 0             | 0.0           | 500    | 26478         | 107.8         | 630    | 78077         | 0.1           | 760    | 1944          | 0.0           | 890    | 45            | 0.0           |
| 375    | 0             | 0.0           | 505    | 30524         | 118.7         | 635    | 72080         | 0.1           | 765    | 1653          | 0.0           | 895    | 41            | 0.0           |
| 380    | 0             | 0.0           | 510    | 33611         | 122.2         | 640    | 66249         | 0.1           | 770    | 1413          | 0.0           | 900    | 38            | 0.0           |
| 385    | 0             | 0.0           | 515    | 36490         | 120.8         | 645    | 59973         | 0.0           | 775    | 1198          | 0.0           | 905    | 33            | 0.0           |
| 390    | 0             | 0.0           | 520    | 38610         | 113.9         | 650    | 53972         | 0.0           | 780    | 1025          | 0.0           | 910    | 30            | 0.0           |
| 395    | 0             | 0.0           | 525    | 40511         | 104.1         | 655    | 48369         | 0.0           | 785    | 874           | 0.0           | 915    | 23            | 0.0           |
| 400    | 48            | 0.0           | 530    | 42223         | 92.4          | 660    | 42641         | 0.0           | 790    | 747           | 0.0           | 920    | 24            | 0.0           |
| 405    | 201           | 0.0           | 535    | 44137         | 80.5          | 665    | 37602         | 0.0           | 795    | 639           | 0.0           | 925    | 22            | 0.0           |
| 410    | 457           | 0.1           | 540    | 46032         | 68.2          | 670    | 32798         | 0.0           | 800    | 547           | 0.0           | 930    | 22            | 0.0           |
| 415    | 925           | 0.3           | 545    | 48553         | 57.1          | 675    | 28558         | 0.0           | 805    | 473           | 0.0           | 935    | 17            | 0.0           |
| 420    | 1816          | 1.1           | 550    | 51408         | 46.7          | 680    | 24782         | 0.0           | 810    | 401           | 0.0           | 940    | 13            | 0.0           |
| 425    | 3217          | 2.5           | 555    | 54711         | 37.4          | 685    | 21386         | 0.0           | 815    | 351           | 0.0           | 945    | 6             | 0.0           |
| 430    | 5520          | 5.9           | 560    | 58847         | 29.4          | 690    | 18413         | 0.0           | 820    | 307           | 0.0           | 950    | 10            | 0.0           |
| 435    | 9225          | 12.5          | 565    | 63386         | 22.5          | 695    | 15721         | 0.0           | 825    | 261           | 0.0           | 955    | 11            | 0.0           |
| 440    | 15522         | 26.3          | 570    | 68196         | 16.9          | 700    | 13432         | 0.0           | 830    | 228           | 0.0           | 960    | 8             | 0.0           |
| 445    | 27642         | 55.2          | 575    | 73613         | 12.4          | 705    | 11513         | 0.0           | 835    | 193           | 0.0           | 965    | 12            | 0.0           |
| 450    | 36602         | 85.4          | 580    | 79207         | 9.0           | 710    | 9780          | 0.0           | 840    | 174           | 0.0           | 970    | 3             | 0.0           |
| 455    | 28292         | 75.1          | 585    | 84248         | 6.3           | 715    | 8356          | 0.0           | 845    | 151           | 0.0           | 975    | 8             | 0.0           |
| 460    | 21166         | 63.2          | 590    | 88397         | 4.4           | 720    | 7161          | 0.0           | 850    | 123           | 0.0           | 980    | 2             | 0.0           |
| 465    | 19092         | 63.2          | 595    | 91428         | 3.0           | 725    | 6067          | 0.0           | 855    | 106           | 0.0           | 985    | 13            | 0.0           |
| 470    | 14951         | 54.2          | 600    | 93452         | 2.0           | 730    | 5164          | 0.0           | 860    | 95            | 0.0           | 990    | 16            | 0.0           |
| 475    | 12606         | 48.8          | 605    | 93959         | 1.3           | 735    | 4393          | 0.0           | 865    | 82            | 0.0           | 995    | 20            | 0.0           |
| 480    | 13323         | 54.2          | 610    | 93079         | 0.9           | 740    | 3694          | 0.0           | 870    | 77            | 0.0           | 1000   | 0             | 0.0           |
| 485    | 15164         | 63.3          | 615    | 90707         | 0.5           | 745    | 3157          | 0.0           | 875    | 65            | 0.0           |        |               |               |



REPORT NUMBER: SP1-2407-157-9

**Melanopic Flux vs. Wavelength**




**Melanopic Lumens: 9797**

**M/P: 2.26**





| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360    | 0             | 0.0           | 490    | 18018         | 27.7          | 620    | 87426         | 1.1           | 750    | 2680          | 0.0           | 880    | 58            | 0.0           |
| 365    | 0             | 0.0           | 495    | 22295         | 36.0          | 625    | 83013         | 0.7           | 755    | 2287          | 0.0           | 885    | 46            | 0.0           |
| 370    | 0             | 0.0           | 500    | 26478         | 44.2          | 630    | 78077         | 0.4           | 760    | 1944          | 0.0           | 890    | 45            | 0.0           |
| 375    | 0             | 0.0           | 505    | 30524         | 51.8          | 635    | 72080         | 0.3           | 765    | 1653          | 0.0           | 895    | 41            | 0.0           |
| 380    | 0             | 0.0           | 510    | 33611         | 57.0          | 640    | 66249         | 0.2           | 770    | 1413          | 0.0           | 900    | 38            | 0.0           |
| 385    | 0             | 0.0           | 515    | 36490         | 60.5          | 645    | 59973         | 0.1           | 775    | 1198          | 0.0           | 905    | 33            | 0.0           |
| 390    | 0             | 0.0           | 520    | 38610         | 61.4          | 650    | 53972         | 0.1           | 780    | 1025          | 0.0           | 910    | 30            | 0.0           |
| 395    | 0             | 0.0           | 525    | 40511         | 60.6          | 655    | 48369         | 0.0           | 785    | 874           | 0.0           | 915    | 23            | 0.0           |
| 400    | 48            | 0.0           | 530    | 42223         | 58.2          | 660    | 42641         | 0.0           | 790    | 747           | 0.0           | 920    | 24            | 0.0           |
| 405    | 201           | 0.0           | 535    | 44137         | 55.0          | 665    | 37602         | 0.0           | 795    | 639           | 0.0           | 925    | 22            | 0.0           |
| 410    | 457           | 0.0           | 540    | 46032         | 50.9          | 670    | 32798         | 0.0           | 800    | 547           | 0.0           | 930    | 22            | 0.0           |
| 415    | 925           | 0.1           | 545    | 48553         | 46.6          | 675    | 28558         | 0.0           | 805    | 473           | 0.0           | 935    | 17            | 0.0           |
| 420    | 1816          | 0.3           | 550    | 51408         | 42.0          | 680    | 24782         | 0.0           | 810    | 401           | 0.0           | 940    | 13            | 0.0           |
| 425    | 3217          | 0.8           | 555    | 54711         | 37.4          | 685    | 21386         | 0.0           | 815    | 351           | 0.0           | 945    | 6             | 0.0           |
| 430    | 5520          | 1.9           | 560    | 58847         | 32.9          | 690    | 18413         | 0.0           | 820    | 307           | 0.0           | 950    | 10            | 0.0           |
| 435    | 9225          | 4.1           | 565    | 63386         | 28.4          | 695    | 15721         | 0.0           | 825    | 261           | 0.0           | 955    | 11            | 0.0           |
| 440    | 15522         | 8.7           | 570    | 68196         | 24.1          | 700    | 13432         | 0.0           | 830    | 228           | 0.0           | 960    | 8             | 0.0           |
| 445    | 27642         | 18.5          | 575    | 73613         | 20.0          | 705    | 11513         | 0.0           | 835    | 193           | 0.0           | 965    | 12            | 0.0           |
| 450    | 36602         | 28.3          | 580    | 79207         | 16.3          | 710    | 9780          | 0.0           | 840    | 174           | 0.0           | 970    | 3             | 0.0           |
| 455    | 28292         | 24.7          | 585    | 84248         | 12.9          | 715    | 8356          | 0.0           | 845    | 151           | 0.0           | 975    | 8             | 0.0           |
| 460    | 21166         | 20.4          | 590    | 88397         | 9.8           | 720    | 7161          | 0.0           | 850    | 123           | 0.0           | 980    | 2             | 0.0           |
| 465    | 19092         | 20.1          | 595    | 91428         | 7.3           | 725    | 6067          | 0.0           | 855    | 106           | 0.0           | 985    | 13            | 0.0           |
| 470    | 14951         | 17.2          | 600    | 93452         | 5.3           | 730    | 5164          | 0.0           | 860    | 95            | 0.0           | 990    | 16            | 0.0           |
| 475    | 12606         | 15.7          | 605    | 93959         | 3.7           | 735    | 4393          | 0.0           | 865    | 82            | 0.0           | 995    | 20            | 0.0           |
| 480    | 13323         | 18.0          | 610    | 93079         | 2.5           | 740    | 3694          | 0.0           | 870    | 77            | 0.0           | 1000   | 0             | 0.0           |
| 485    | 15164         | 21.9          | 615    | 90707         | 1.7           | 745    | 3157          | 0.0           | 875    | 65            | 0.0           |        |               |               |

**Summary**

$R_f = 84.7$   
 $R_g = 94.6$   
 CIE  $R_a = 80.9$   
 $R_g = -1.5$




**Color Vector Graphics**






**Individual Sample Fidelity Index ( $R_{f,i}$ )**



|            |            |            |            |
|------------|------------|------------|------------|
| CES01 = 86 | CES26 = 84 | CES51 = 95 | CES76 = 81 |
| CES02 = 63 | CES27 = 95 | CES52 = 94 | CES77 = 84 |
| CES03 = 31 | CES28 = 94 | CES53 = 89 | CES78 = 81 |
| CES04 = 71 | CES29 = 87 | CES54 = 91 | CES79 = 89 |
| CES05 = 50 | CES30 = 94 | CES55 = 90 | CES80 = 89 |
| CES06 = 52 | CES31 = 89 | CES56 = 86 | CES81 = 69 |
| CES07 = 43 | CES32 = 82 | CES57 = 85 | CES82 = 96 |
| CES08 = 41 | CES33 = 91 | CES58 = 86 | CES83 = 93 |
| CES09 = 29 | CES34 = 92 | CES59 = 91 | CES84 = 92 |
| CES10 = 77 | CES35 = 96 | CES60 = 94 | CES85 = 76 |
| CES11 = 60 | CES36 = 90 | CES61 = 89 | CES86 = 65 |
| CES12 = 66 | CES37 = 96 | CES62 = 94 | CES87 = 84 |
| CES13 = 44 | CES38 = 98 | CES63 = 87 | CES88 = 86 |
| CES14 = 74 | CES39 = 98 | CES64 = 82 | CES89 = 73 |
| CES15 = 72 | CES40 = 95 | CES65 = 78 | CES90 = 88 |
| CES16 = 48 | CES41 = 96 | CES66 = 81 | CES91 = 82 |
| CES17 = 50 | CES42 = 97 | CES67 = 80 | CES92 = 64 |
| CES18 = 57 | CES43 = 91 | CES68 = 83 | CES93 = 78 |
| CES19 = 73 | CES44 = 99 | CES69 = 88 | CES94 = 59 |
| CES20 = 67 | CES45 = 93 | CES70 = 80 | CES95 = 74 |
| CES21 = 87 | CES46 = 89 | CES71 = 79 | CES96 = 83 |
| CES22 = 79 | CES47 = 92 | CES72 = 92 | CES97 = 88 |
| CES23 = 92 | CES48 = 83 | CES73 = 75 | CES98 = 83 |
| CES24 = 91 | CES49 = 90 | CES74 = 91 | CES99 = 74 |
| CES25 = 72 | CES50 = 94 | CES75 = 81 |            |



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)