

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: McGRAW-EDISON

Report Number: P643359

Luminaire Tested: GWS-SA6E-827-U-AFL-W-HSS

Issue Date: 1/10/2023

Test Information

Test Method: LM-79-2019
Report Number: P643359
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2209-782-48)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/10/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: McGRAW-EDISON
Catalog Number: GWS-SAGE-827-U-AFL-W-HSS
Description: GALLEON WALL SLIM LUMINAIRE. (6) LIGHTSQUARES WITH 16 LEDS EACH AND AUTOMOTIVE FRONTLINE OPTICS WITH HOUSE SIDE SHIELD
Light Source: (96) 2700K CCT, 80 CRI LEDS
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 27595.8 lumens
Efficiency: N/A
Efficacy: 85.2 lumens/watt
Luminous Opening: Rectangular (W 2' x L: 1' x H: 0')
IES Classification: Type II - Short
BUG Rating: B2 - U0 - G2


Input Watts (W): 323.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 0
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT



REPORT NUMBER: P643359
 CATALOG NUMBER: GWS-SA6E-827-U-AFL-W-HSS

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 14.9 fc
 Type II - Short - N/A

REPORT NUMBER: P643359
CATALOG NUMBER: GWS-SA6E-827-U-AFL-W-HSS

Luminous Intensity Polar Plot



— Vertical Plane Through 55-Deg Lateral - - - Horizontal Cone Through 55-Deg Vertical

REPORT NUMBER: P643359
 CATALOG NUMBER: GWS-SA6E-827-U-AFL-W-HSS

FLUX DISTRIBUTION:

| | | Downward | Upward | Total |
|--------------------|-----------|----------|--------|---------|
| House Side | Lumens | 1702.8 | 0.0 | 1702.8 |
| | % Fixture | 6.2 | 0.0 | 6.2 |
| Street Side | Lumens | 25893.0 | 0.0 | 25893.0 |
| | % Fixture | 93.8 | 0.0 | 93.8 |
| Total | Lumens | 27595.8 | 0.0 | 27595.8 |
| | % Fixture | 100.0 | 0.0 | 100.0 |

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|---------|-----------|
| 0°-10° | 630.0 | 2.3 |
| 10°-20° | 1519.0 | 5.5 |
| 20°-30° | 2529.7 | 9.2 |
| 30°-40° | 4310.7 | 15.6 |
| 40°-50° | 7036.6 | 25.5 |
| 50°-60° | 7366.9 | 26.7 |
| 60°-70° | 3715.7 | 13.5 |
| 70°-80° | 469.4 | 1.7 |
| 80°-90° | 17.8 | 0.1 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-90° | 27595.8 | 100.0 |
| 0°-180° | 27595.8 | 100.0 |

Coefficient of Utilization



REPORT NUMBER: P643359


CATALOG NUMBER: GWS-SA6E-827-U-AFL-W-HSS

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

| Zone | Lumens | % Fixture | Zone Rating/Lumen Limit | | |
|----------------|---------|-----------|-------------------------|------|---------|
| | | | B | U | G |
| FL (0°-30°) | 3860.3 | 14.0 | | | |
| FM (30°-60°) | 18002.3 | 65.2 | | | |
| FH (60°-80°) | 4014.3 | 14.5 | | | G2/5000 |
| FVH (80°-90°) | 16.2 | 0.1 | | | G1/100 |
| BL (0°-30°) | 818.4 | 3.0 | B2/1000 | | |
| BM (30°-60°) | 711.9 | 2.6 | B1/1000 | | |
| BH (60°-80°) | 170.8 | 0.6 | B1/500 | | G1/500 |
| BVH (80°-90°) | 1.6 | 0.0 | | | G0/10 |
| UL (90°-100°) | 0.0 | 0.0 | | U0/0 | |
| UH (100°-180°) | 0.0 | 0.0 | | U0/0 | |

BUG Rating: B2-U0-G2

Type II Short





REPORT NUMBER: P643359

CATALOG NUMBER: GWS-SA6E-827-U-AFL-W-HSS

CANDELA DISTRIBUTION (FULL):

| | 0° | 5° | 15° | 25° | 35° | 45° | 55° | 56° | 65° | 75° | 85° |
|-------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|
| 0° | 7129.1 | 7129.1 | 7129.1 | 7129.1 | 7129.1 | 7129.1 | 7129.1 | 7129.1 | 7129.1 | 7129.1 | 7129.1 |
| 2.5° | 8311.0 | 8270.9 | 8332.3 | 8261.5 | 8141.2 | 8039.7 | 7907.6 | 7860.5 | 7648.1 | 7447.6 | 7254.2 |
| 5° | 9320.7 | 9332.5 | 9313.6 | 9214.6 | 9044.7 | 8856.0 | 8589.4 | 8530.4 | 8160.1 | 7777.9 | 7365.0 |
| 7.5° | 9570.8 | 9563.7 | 9603.8 | 9641.6 | 9613.2 | 9518.9 | 9228.7 | 9169.7 | 8709.7 | 8136.5 | 7534.9 |
| 10° | 8799.4 | 8804.1 | 8886.7 | 9141.4 | 9457.5 | 9785.5 | 9740.6 | 9707.6 | 9257.0 | 8542.2 | 7723.6 |
| 12.5° | 7709.5 | 7751.9 | 7839.2 | 8202.5 | 8738.0 | 9483.5 | 9945.9 | 9978.9 | 9759.5 | 8988.1 | 7945.4 |
| 15° | 7237.7 | 7247.1 | 7317.9 | 7537.3 | 7935.9 | 8856.0 | 9858.6 | 9950.6 | 10179.4 | 9436.3 | 8186.0 |
| 17.5° | 7225.9 | 7237.7 | 7268.3 | 7365.0 | 7624.5 | 8362.9 | 9577.9 | 9738.3 | 10495.5 | 9917.6 | 8473.8 |
| 20° | 7669.4 | 7662.3 | 7641.1 | 7589.2 | 7702.4 | 8200.2 | 9318.4 | 9495.3 | 10667.8 | 10387.0 | 8764.0 |
| 22.5° | 8473.8 | 8464.4 | 8370.0 | 8155.3 | 8063.3 | 8348.8 | 9191.0 | 9351.4 | 10771.6 | 10804.6 | 9002.2 |
| 25° | 9400.9 | 9467.0 | 9290.1 | 8964.5 | 8738.0 | 8728.6 | 9304.2 | 9417.4 | 10861.2 | 11175.0 | 9165.0 |
| 27.5° | 10417.7 | 10438.9 | 10287.9 | 9922.3 | 9594.4 | 9337.2 | 9632.1 | 9717.0 | 10960.3 | 11505.2 | 9257.0 |
| 30° | 11533.5 | 11526.5 | 11354.2 | 10929.6 | 10530.9 | 10160.6 | 10184.1 | 10217.2 | 11191.5 | 11882.7 | 9358.5 |
| 32.5° | 12927.8 | 12958.4 | 12651.7 | 12073.8 | 11594.9 | 11083.0 | 10906.0 | 10910.7 | 11609.0 | 12368.7 | 9511.8 |
| 35° | 14822.1 | 14746.6 | 14340.8 | 13517.5 | 12701.3 | 12149.3 | 11847.3 | 11821.3 | 12253.1 | 13022.1 | 9778.4 |
| 37.5° | 16626.8 | 16633.9 | 16209.2 | 15303.3 | 14272.4 | 13401.9 | 12974.9 | 12904.2 | 13158.9 | 13928.0 | 10221.9 |
| 40° | 17879.5 | 17903.1 | 17726.1 | 17251.9 | 16159.7 | 14928.3 | 14300.7 | 14227.6 | 14333.8 | 15074.5 | 10802.2 |
| 42.5° | 18542.4 | 18608.4 | 18658.0 | 18768.8 | 17940.8 | 16834.4 | 15869.5 | 15862.5 | 15751.6 | 16381.4 | 11474.6 |
| 45° | 18568.3 | 18667.4 | 18969.4 | 19726.6 | 19821.0 | 19009.5 | 17959.7 | 17801.6 | 17374.6 | 17780.4 | 12076.1 |
| 47.5° | 17542.1 | 17770.9 | 18412.6 | 19913.0 | 20903.8 | 21172.7 | 20132.4 | 20035.7 | 18837.3 | 18886.8 | 12526.7 |
| 50° | 15150.0 | 15388.3 | 16570.2 | 18957.6 | 21177.5 | 22890.1 | 22517.4 | 22316.9 | 20059.3 | 19618.1 | 12743.7 |
| 52.5° | 12696.6 | 12913.6 | 13715.7 | 16683.4 | 20042.7 | 23430.4 | 24527.4 | 24289.1 | 21156.2 | 19872.9 | 12654.1 |
| 55° | 8834.8 | 9124.9 | 9908.1 | 12470.1 | 17428.9 | 22378.2 | 25192.6 | 25143.1 | 22135.2 | 19712.5 | 12514.9 |
| 57.5° | 4331.3 | 4619.1 | 5399.9 | 7688.2 | 12911.2 | 19537.9 | 24175.8 | 24437.7 | 22720.3 | 19540.3 | 12401.7 |
| 60° | 1809.4 | 1927.4 | 2196.3 | 3373.5 | 7223.5 | 14765.5 | 21880.5 | 22243.8 | 22361.7 | 19306.7 | 12389.9 |
| 62.5° | 1049.8 | 1068.7 | 1097.0 | 1398.9 | 2809.7 | 8464.4 | 18150.8 | 18667.4 | 20476.8 | 18997.7 | 12203.5 |
| 65° | 792.7 | 799.7 | 787.9 | 858.7 | 1160.7 | 3210.7 | 13114.1 | 13817.1 | 17091.5 | 17789.8 | 11467.5 |
| 67.5° | 651.1 | 651.1 | 620.4 | 634.6 | 729.0 | 1203.1 | 7240.0 | 8221.4 | 12647.0 | 14621.6 | 9469.3 |
| 70° | 519.0 | 530.8 | 516.6 | 497.8 | 521.4 | 665.3 | 2576.1 | 3194.2 | 7365.0 | 8634.2 | 5522.6 |
| 72.5° | 394.0 | 394.0 | 417.6 | 403.4 | 386.9 | 417.6 | 898.8 | 1009.7 | 2955.9 | 3600.0 | 1993.4 |
| 75° | 304.3 | 313.8 | 330.3 | 316.1 | 292.5 | 247.7 | 431.7 | 457.7 | 891.7 | 837.5 | 445.9 |
| 77.5° | 155.7 | 158.1 | 210.0 | 231.2 | 217.0 | 151.0 | 188.7 | 207.6 | 290.2 | 259.5 | 165.1 |
| 80° | 94.4 | 99.1 | 118.0 | 181.6 | 143.9 | 80.2 | 77.8 | 82.6 | 136.8 | 118.0 | 68.4 |
| 82.5° | 40.1 | 42.5 | 66.1 | 66.1 | 59.0 | 30.7 | 30.7 | 30.7 | 66.1 | 61.3 | 28.3 |
| 85° | 0.0 | 0.0 | 11.8 | 9.4 | 9.4 | 11.8 | 11.8 | 11.8 | 16.5 | 23.6 | 14.2 |
| 87.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 2.4 | 7.1 | 7.1 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P643359

CATALOG NUMBER: GWS-SA6E-827-U-AFL-W-HSS

CANDELA DISTRIBUTION (continued):

| | 90° | 95° | 105° | 115° | 125° | 135° | 145° | 155° | 165° | 175° | 180° |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 7129.1 | 7129.1 | 7129.1 | 7129.1 | 7129.1 | 7129.1 | 7129.1 | 7129.1 | 7129.1 | 7129.1 | 7129.1 |
| 2.5° | 7129.1 | 6978.2 | 6775.3 | 6591.3 | 6343.6 | 6204.4 | 6010.9 | 5852.9 | 5718.4 | 5675.9 | 5657.1 |
| 5° | 7131.5 | 6872.0 | 6437.9 | 6003.9 | 5470.7 | 5050.8 | 4619.1 | 4277.0 | 3996.3 | 3906.6 | 3883.0 |
| 7.5° | 7178.7 | 6796.5 | 6093.5 | 5305.6 | 4413.8 | 3677.8 | 3019.6 | 2429.9 | 2156.2 | 2064.2 | 2045.3 |
| 10° | 7242.4 | 6732.8 | 5694.8 | 4468.1 | 3187.1 | 2241.1 | 1587.7 | 1210.2 | 1030.9 | 931.8 | 946.0 |
| 12.5° | 7324.9 | 6680.9 | 5253.7 | 3562.2 | 2109.0 | 1231.4 | 872.9 | 731.3 | 693.6 | 674.7 | 665.3 |
| 15° | 7435.8 | 6619.6 | 4706.4 | 2663.4 | 1292.8 | 792.7 | 672.3 | 634.6 | 620.4 | 611.0 | 608.6 |
| 17.5° | 7549.1 | 6548.8 | 4149.6 | 1873.1 | 858.7 | 658.2 | 603.9 | 585.1 | 575.6 | 568.5 | 566.2 |
| 20° | 7669.4 | 6428.5 | 3496.2 | 1290.4 | 677.1 | 592.1 | 556.7 | 535.5 | 523.7 | 511.9 | 509.6 |
| 22.5° | 7721.3 | 6235.0 | 2871.0 | 903.5 | 601.6 | 544.9 | 500.1 | 474.2 | 460.0 | 450.6 | 450.6 |
| 25° | 7671.7 | 5921.3 | 2224.6 | 686.5 | 547.3 | 493.0 | 448.2 | 419.9 | 408.1 | 398.7 | 398.7 |
| 27.5° | 7539.6 | 5517.9 | 1623.0 | 568.5 | 488.3 | 438.8 | 396.3 | 370.4 | 360.9 | 356.2 | 356.2 |
| 30° | 7393.4 | 5008.3 | 1144.2 | 488.3 | 422.3 | 382.2 | 346.8 | 330.3 | 327.9 | 323.2 | 323.2 |
| 32.5° | 7268.3 | 4531.8 | 787.9 | 429.4 | 372.7 | 332.6 | 309.0 | 302.0 | 304.3 | 299.6 | 302.0 |
| 35° | 7199.9 | 4064.7 | 585.1 | 382.2 | 332.6 | 294.9 | 283.1 | 283.1 | 283.1 | 280.7 | 280.7 |
| 37.5° | 7228.2 | 3604.7 | 476.5 | 349.1 | 297.2 | 268.9 | 257.1 | 261.9 | 266.6 | 266.6 | 266.6 |
| 40° | 7369.8 | 3196.6 | 422.3 | 318.5 | 266.6 | 245.3 | 235.9 | 243.0 | 250.1 | 254.8 | 254.8 |
| 42.5° | 7549.1 | 2866.3 | 382.2 | 292.5 | 245.3 | 221.8 | 217.0 | 224.1 | 231.2 | 235.9 | 235.9 |
| 45° | 7662.3 | 2533.7 | 342.1 | 259.5 | 224.1 | 195.8 | 195.8 | 205.2 | 202.9 | 205.2 | 205.2 |
| 47.5° | 7714.2 | 2269.4 | 302.0 | 224.1 | 191.1 | 169.9 | 172.2 | 176.9 | 172.2 | 176.9 | 176.9 |
| 50° | 7586.8 | 2002.9 | 266.6 | 186.4 | 158.1 | 148.6 | 153.3 | 151.0 | 151.0 | 160.4 | 160.4 |
| 52.5° | 7353.3 | 1804.7 | 235.9 | 158.1 | 134.5 | 132.1 | 136.8 | 127.4 | 129.7 | 129.7 | 127.4 |
| 55° | 7181.0 | 1691.5 | 210.0 | 136.8 | 115.6 | 118.0 | 115.6 | 99.1 | 89.6 | 80.2 | 77.8 |
| 57.5° | 7096.1 | 1646.6 | 191.1 | 122.7 | 103.8 | 103.8 | 94.4 | 68.4 | 51.9 | 40.1 | 35.4 |
| 60° | 7077.2 | 1592.4 | 172.2 | 106.2 | 92.0 | 87.3 | 68.4 | 40.1 | 25.9 | 18.9 | 16.5 |
| 62.5° | 6897.9 | 1460.3 | 155.7 | 84.9 | 80.2 | 70.8 | 42.5 | 23.6 | 14.2 | 9.4 | 7.1 |
| 65° | 6310.5 | 1200.8 | 139.2 | 66.1 | 61.3 | 51.9 | 25.9 | 14.2 | 7.1 | 2.4 | 0.0 |
| 67.5° | 5020.1 | 851.6 | 122.7 | 49.5 | 42.5 | 33.0 | 16.5 | 9.4 | 2.4 | 0.0 | 0.0 |
| 70° | 2894.6 | 460.0 | 101.4 | 35.4 | 28.3 | 21.2 | 11.8 | 4.7 | 0.0 | 0.0 | 0.0 |
| 72.5° | 967.2 | 214.7 | 77.8 | 23.6 | 21.2 | 16.5 | 7.1 | 2.4 | 0.0 | 0.0 | 0.0 |
| 75° | 212.3 | 127.4 | 51.9 | 16.5 | 14.2 | 11.8 | 4.7 | 0.0 | 0.0 | 0.0 | 0.0 |
| 77.5° | 80.2 | 89.6 | 25.9 | 11.8 | 9.4 | 7.1 | 2.4 | 0.0 | 0.0 | 0.0 | 0.0 |
| 80° | 30.7 | 59.0 | 11.8 | 7.1 | 7.1 | 2.4 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 82.5° | 16.5 | 23.6 | 7.1 | 4.7 | 4.7 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 85° | 9.4 | 11.8 | 4.7 | 2.4 | 2.4 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 87.5° | 4.7 | 2.4 | 2.4 | 2.4 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Invue

Report Number: SP1-2407-157-9

Test Date: 10/03/2024

Luminaire Tested: EMM2-HTN-SA1A-827-U-5WQ

Data applicable to all product families utilizing light square engine

Test Information

Test Method: LM-79-2019
 Report Number: SP1-2407-157-9
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 10/03/2024
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: Invue
 Catalog Number: **EMM2-HTN-SA1A-827-U-5WQ**
 Description: Epic Modern Light Square 40W 5WQ Optic

Spectral Parameters

CCT (K): 2764
 CIE u': 0.2591
 CIE v': 0.5290
 Duv: 0.0020
 CIE x: 0.4581
 CIE y: 0.4156
 CIE z: 0.1263
 Peak Wavelength (nm): 603
 Dominant Wavelength (nm): 583
 Purity: 62.2537
 Rf: 84.7
 Rg: 94.6

| | | | |
|-----------|------|------|------|
| CRI (Ra): | 80.9 | | |
| R1: | 78.8 | R9: | -1.5 |
| R2: | 89.9 | R10: | 77.9 |
| R3: | 96.2 | R11: | 78.9 |
| R4: | 79.1 | R12: | 71.6 |
| R5: | 79.1 | R13: | 81.2 |
| R6: | 88.8 | R14: | 98.5 |
| R7: | 81.3 | R15: | 69.9 |
| R8: | 54.3 | | |



Test Conditions

Stabilization Time: 81M
 Operation Time: 2H 21M
 Sphere Temperature (°C): 25.2

REPORT NUMBER: SP1-2407-157-9

| Measurement and Test Equipment | | | |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument | Identification Number | Calibration Date | Calibration Due Date |
| Photometer | IN0058 | 6/18/2024 | 12/18/2024 |
| Power Meter | INXT2011004 | 2/8/2024 | 2/8/2025 |
| AC Power Source | IN0063 | 10/24/2023 | 10/24/2024 |
| DC Power Source | IN0208 | 10/24/2023 | 10/24/2024 |
| Sphere Thermometer | IN0085 | 10/24/2023 | 10/24/2024 |
| Room Thermometer | IN0046 | 10/24/2023 | 10/24/2024 |

REPORT NUMBER: SP1-2407-157-9

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 2700K 4-step quadrangle

REPORT NUMBER: SP1-2407-157-9

Photopic Flux vs. Wavelength



Photopic Lumens: 4337.9

| λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) |
|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|
| 360 | 0 | 0.0 | 490 | 18018 | 2.6 | 620 | 87426 | 22.8 | 750 | 2680 | 0.0 | 880 | 58 | 0.0 |
| 365 | 0 | 0.0 | 495 | 22295 | 3.9 | 625 | 83013 | 18.2 | 755 | 2287 | 0.0 | 885 | 46 | 0.0 |
| 370 | 0 | 0.0 | 500 | 26478 | 5.8 | 630 | 78077 | 14.1 | 760 | 1944 | 0.0 | 890 | 45 | 0.0 |
| 375 | 0 | 0.0 | 505 | 30524 | 8.5 | 635 | 72080 | 10.7 | 765 | 1653 | 0.0 | 895 | 41 | 0.0 |
| 380 | 0 | 0.0 | 510 | 33611 | 11.5 | 640 | 66249 | 7.9 | 770 | 1413 | 0.0 | 900 | 38 | 0.0 |
| 385 | 0 | 0.0 | 515 | 36490 | 15.2 | 645 | 59973 | 5.7 | 775 | 1198 | 0.0 | 905 | 33 | 0.0 |
| 390 | 0 | 0.0 | 520 | 38610 | 18.7 | 650 | 53972 | 3.9 | 780 | 1025 | 0.0 | 910 | 30 | 0.0 |
| 395 | 0 | 0.0 | 525 | 40511 | 21.9 | 655 | 48369 | 2.7 | 785 | 874 | 0.0 | 915 | 23 | 0.0 |
| 400 | 48 | 0.0 | 530 | 42223 | 24.9 | 660 | 42641 | 1.8 | 790 | 747 | 0.0 | 920 | 24 | 0.0 |
| 405 | 201 | 0.0 | 535 | 44137 | 27.6 | 665 | 37602 | 1.1 | 795 | 639 | 0.0 | 925 | 22 | 0.0 |
| 410 | 457 | 0.0 | 540 | 46032 | 30.0 | 670 | 32798 | 0.7 | 800 | 547 | 0.0 | 930 | 22 | 0.0 |
| 415 | 925 | 0.0 | 545 | 48553 | 32.5 | 675 | 28558 | 0.5 | 805 | 473 | 0.0 | 935 | 17 | 0.0 |
| 420 | 1816 | 0.0 | 550 | 51408 | 34.9 | 680 | 24782 | 0.3 | 810 | 401 | 0.0 | 940 | 13 | 0.0 |
| 425 | 3217 | 0.0 | 555 | 54711 | 37.4 | 685 | 21386 | 0.2 | 815 | 351 | 0.0 | 945 | 6 | 0.0 |
| 430 | 5520 | 0.0 | 560 | 58847 | 40.0 | 690 | 18413 | 0.1 | 820 | 307 | 0.0 | 950 | 10 | 0.0 |
| 435 | 9225 | 0.1 | 565 | 63386 | 42.4 | 695 | 15721 | 0.1 | 825 | 261 | 0.0 | 955 | 11 | 0.0 |
| 440 | 15522 | 0.2 | 570 | 68196 | 44.3 | 700 | 13432 | 0.0 | 830 | 228 | 0.0 | 960 | 8 | 0.0 |
| 445 | 27642 | 0.6 | 575 | 73613 | 46.0 | 705 | 11513 | 0.0 | 835 | 193 | 0.0 | 965 | 12 | 0.0 |
| 450 | 36602 | 0.9 | 580 | 79207 | 47.1 | 710 | 9780 | 0.0 | 840 | 174 | 0.0 | 970 | 3 | 0.0 |
| 455 | 28292 | 0.9 | 585 | 84248 | 47.0 | 715 | 8356 | 0.0 | 845 | 151 | 0.0 | 975 | 8 | 0.0 |
| 460 | 21166 | 0.9 | 590 | 88397 | 45.7 | 720 | 7161 | 0.0 | 850 | 123 | 0.0 | 980 | 2 | 0.0 |
| 465 | 19092 | 1.0 | 595 | 91428 | 43.4 | 725 | 6067 | 0.0 | 855 | 106 | 0.0 | 985 | 13 | 0.0 |
| 470 | 14951 | 0.9 | 600 | 93452 | 40.3 | 730 | 5164 | 0.0 | 860 | 95 | 0.0 | 990 | 16 | 0.0 |
| 475 | 12606 | 1.0 | 605 | 93959 | 36.4 | 735 | 4393 | 0.0 | 865 | 82 | 0.0 | 995 | 20 | 0.0 |
| 480 | 13323 | 1.3 | 610 | 93079 | 32.0 | 740 | 3694 | 0.0 | 870 | 77 | 0.0 | 1000 | 0 | 0.0 |
| 485 | 15164 | 1.8 | 615 | 90707 | 27.3 | 745 | 3157 | 0.0 | 875 | 65 | 0.0 | | | |

REPORT NUMBER: SP1-2407-157-9

Scotopic Flux vs. Wavelength



Scotopic Lumens: 5286.7

S/P: 1.22

| λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) |
|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|
| 360 | 0 | 0.0 | 490 | 18018 | 75.9 | 620 | 87426 | 0.4 | 750 | 2680 | 0.0 | 880 | 58 | 0.0 |
| 365 | 0 | 0.0 | 495 | 22295 | 93.2 | 625 | 83013 | 0.2 | 755 | 2287 | 0.0 | 885 | 46 | 0.0 |
| 370 | 0 | 0.0 | 500 | 26478 | 107.8 | 630 | 78077 | 0.1 | 760 | 1944 | 0.0 | 890 | 45 | 0.0 |
| 375 | 0 | 0.0 | 505 | 30524 | 118.7 | 635 | 72080 | 0.1 | 765 | 1653 | 0.0 | 895 | 41 | 0.0 |
| 380 | 0 | 0.0 | 510 | 33611 | 122.2 | 640 | 66249 | 0.1 | 770 | 1413 | 0.0 | 900 | 38 | 0.0 |
| 385 | 0 | 0.0 | 515 | 36490 | 120.8 | 645 | 59973 | 0.0 | 775 | 1198 | 0.0 | 905 | 33 | 0.0 |
| 390 | 0 | 0.0 | 520 | 38610 | 113.9 | 650 | 53972 | 0.0 | 780 | 1025 | 0.0 | 910 | 30 | 0.0 |
| 395 | 0 | 0.0 | 525 | 40511 | 104.1 | 655 | 48369 | 0.0 | 785 | 874 | 0.0 | 915 | 23 | 0.0 |
| 400 | 48 | 0.0 | 530 | 42223 | 92.4 | 660 | 42641 | 0.0 | 790 | 747 | 0.0 | 920 | 24 | 0.0 |
| 405 | 201 | 0.0 | 535 | 44137 | 80.5 | 665 | 37602 | 0.0 | 795 | 639 | 0.0 | 925 | 22 | 0.0 |
| 410 | 457 | 0.1 | 540 | 46032 | 68.2 | 670 | 32798 | 0.0 | 800 | 547 | 0.0 | 930 | 22 | 0.0 |
| 415 | 925 | 0.3 | 545 | 48553 | 57.1 | 675 | 28558 | 0.0 | 805 | 473 | 0.0 | 935 | 17 | 0.0 |
| 420 | 1816 | 1.1 | 550 | 51408 | 46.7 | 680 | 24782 | 0.0 | 810 | 401 | 0.0 | 940 | 13 | 0.0 |
| 425 | 3217 | 2.5 | 555 | 54711 | 37.4 | 685 | 21386 | 0.0 | 815 | 351 | 0.0 | 945 | 6 | 0.0 |
| 430 | 5520 | 5.9 | 560 | 58847 | 29.4 | 690 | 18413 | 0.0 | 820 | 307 | 0.0 | 950 | 10 | 0.0 |
| 435 | 9225 | 12.5 | 565 | 63386 | 22.5 | 695 | 15721 | 0.0 | 825 | 261 | 0.0 | 955 | 11 | 0.0 |
| 440 | 15522 | 26.3 | 570 | 68196 | 16.9 | 700 | 13432 | 0.0 | 830 | 228 | 0.0 | 960 | 8 | 0.0 |
| 445 | 27642 | 55.2 | 575 | 73613 | 12.4 | 705 | 11513 | 0.0 | 835 | 193 | 0.0 | 965 | 12 | 0.0 |
| 450 | 36602 | 85.4 | 580 | 79207 | 9.0 | 710 | 9780 | 0.0 | 840 | 174 | 0.0 | 970 | 3 | 0.0 |
| 455 | 28292 | 75.1 | 585 | 84248 | 6.3 | 715 | 8356 | 0.0 | 845 | 151 | 0.0 | 975 | 8 | 0.0 |
| 460 | 21166 | 63.2 | 590 | 88397 | 4.4 | 720 | 7161 | 0.0 | 850 | 123 | 0.0 | 980 | 2 | 0.0 |
| 465 | 19092 | 63.2 | 595 | 91428 | 3.0 | 725 | 6067 | 0.0 | 855 | 106 | 0.0 | 985 | 13 | 0.0 |
| 470 | 14951 | 54.2 | 600 | 93452 | 2.0 | 730 | 5164 | 0.0 | 860 | 95 | 0.0 | 990 | 16 | 0.0 |
| 475 | 12606 | 48.8 | 605 | 93959 | 1.3 | 735 | 4393 | 0.0 | 865 | 82 | 0.0 | 995 | 20 | 0.0 |
| 480 | 13323 | 54.2 | 610 | 93079 | 0.9 | 740 | 3694 | 0.0 | 870 | 77 | 0.0 | 1000 | 0 | 0.0 |
| 485 | 15164 | 63.3 | 615 | 90707 | 0.5 | 745 | 3157 | 0.0 | 875 | 65 | 0.0 | | | |

REPORT NUMBER: SP1-2407-157-9

Melanopic Flux vs. Wavelength



Melanopic Lumens: 9797

M/P: 2.26

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 0 | 0.0 | 490 | 18018 | 27.7 | 620 | 87426 | 1.1 | 750 | 2680 | 0.0 | 880 | 58 | 0.0 |
| 365 | 0 | 0.0 | 495 | 22295 | 36.0 | 625 | 83013 | 0.7 | 755 | 2287 | 0.0 | 885 | 46 | 0.0 |
| 370 | 0 | 0.0 | 500 | 26478 | 44.2 | 630 | 78077 | 0.4 | 760 | 1944 | 0.0 | 890 | 45 | 0.0 |
| 375 | 0 | 0.0 | 505 | 30524 | 51.8 | 635 | 72080 | 0.3 | 765 | 1653 | 0.0 | 895 | 41 | 0.0 |
| 380 | 0 | 0.0 | 510 | 33611 | 57.0 | 640 | 66249 | 0.2 | 770 | 1413 | 0.0 | 900 | 38 | 0.0 |
| 385 | 0 | 0.0 | 515 | 36490 | 60.5 | 645 | 59973 | 0.1 | 775 | 1198 | 0.0 | 905 | 33 | 0.0 |
| 390 | 0 | 0.0 | 520 | 38610 | 61.4 | 650 | 53972 | 0.1 | 780 | 1025 | 0.0 | 910 | 30 | 0.0 |
| 395 | 0 | 0.0 | 525 | 40511 | 60.6 | 655 | 48369 | 0.0 | 785 | 874 | 0.0 | 915 | 23 | 0.0 |
| 400 | 48 | 0.0 | 530 | 42223 | 58.2 | 660 | 42641 | 0.0 | 790 | 747 | 0.0 | 920 | 24 | 0.0 |
| 405 | 201 | 0.0 | 535 | 44137 | 55.0 | 665 | 37602 | 0.0 | 795 | 639 | 0.0 | 925 | 22 | 0.0 |
| 410 | 457 | 0.0 | 540 | 46032 | 50.9 | 670 | 32798 | 0.0 | 800 | 547 | 0.0 | 930 | 22 | 0.0 |
| 415 | 925 | 0.1 | 545 | 48553 | 46.6 | 675 | 28558 | 0.0 | 805 | 473 | 0.0 | 935 | 17 | 0.0 |
| 420 | 1816 | 0.3 | 550 | 51408 | 42.0 | 680 | 24782 | 0.0 | 810 | 401 | 0.0 | 940 | 13 | 0.0 |
| 425 | 3217 | 0.8 | 555 | 54711 | 37.4 | 685 | 21386 | 0.0 | 815 | 351 | 0.0 | 945 | 6 | 0.0 |
| 430 | 5520 | 1.9 | 560 | 58847 | 32.9 | 690 | 18413 | 0.0 | 820 | 307 | 0.0 | 950 | 10 | 0.0 |
| 435 | 9225 | 4.1 | 565 | 63386 | 28.4 | 695 | 15721 | 0.0 | 825 | 261 | 0.0 | 955 | 11 | 0.0 |
| 440 | 15522 | 8.7 | 570 | 68196 | 24.1 | 700 | 13432 | 0.0 | 830 | 228 | 0.0 | 960 | 8 | 0.0 |
| 445 | 27642 | 18.5 | 575 | 73613 | 20.0 | 705 | 11513 | 0.0 | 835 | 193 | 0.0 | 965 | 12 | 0.0 |
| 450 | 36602 | 28.3 | 580 | 79207 | 16.3 | 710 | 9780 | 0.0 | 840 | 174 | 0.0 | 970 | 3 | 0.0 |
| 455 | 28292 | 24.7 | 585 | 84248 | 12.9 | 715 | 8356 | 0.0 | 845 | 151 | 0.0 | 975 | 8 | 0.0 |
| 460 | 21166 | 20.4 | 590 | 88397 | 9.8 | 720 | 7161 | 0.0 | 850 | 123 | 0.0 | 980 | 2 | 0.0 |
| 465 | 19092 | 20.1 | 595 | 91428 | 7.3 | 725 | 6067 | 0.0 | 855 | 106 | 0.0 | 985 | 13 | 0.0 |
| 470 | 14951 | 17.2 | 600 | 93452 | 5.3 | 730 | 5164 | 0.0 | 860 | 95 | 0.0 | 990 | 16 | 0.0 |
| 475 | 12606 | 15.7 | 605 | 93959 | 3.7 | 735 | 4393 | 0.0 | 865 | 82 | 0.0 | 995 | 20 | 0.0 |
| 480 | 13323 | 18.0 | 610 | 93079 | 2.5 | 740 | 3694 | 0.0 | 870 | 77 | 0.0 | 1000 | 0 | 0.0 |
| 485 | 15164 | 21.9 | 615 | 90707 | 1.7 | 745 | 3157 | 0.0 | 875 | 65 | 0.0 | | | |

Summary

$R_f = 84.7$
 $R_g = 94.6$
 CIE $R_a = 80.9$
 $R_9 = -1.5$



Color Vector Graphics



Individual Sample Fidelity Index ($R_{f,i}$)

| | | | |
|------------|------------|------------|------------|
| CES01 = 86 | CES26 = 84 | CES51 = 95 | CES76 = 81 |
| CES02 = 63 | CES27 = 95 | CES52 = 94 | CES77 = 84 |
| CES03 = 31 | CES28 = 94 | CES53 = 89 | CES78 = 81 |
| CES04 = 71 | CES29 = 87 | CES54 = 91 | CES79 = 89 |
| CES05 = 50 | CES30 = 94 | CES55 = 90 | CES80 = 89 |
| CES06 = 52 | CES31 = 89 | CES56 = 86 | CES81 = 69 |
| CES07 = 43 | CES32 = 82 | CES57 = 85 | CES82 = 96 |
| CES08 = 41 | CES33 = 91 | CES58 = 86 | CES83 = 93 |
| CES09 = 29 | CES34 = 92 | CES59 = 91 | CES84 = 92 |
| CES10 = 77 | CES35 = 96 | CES60 = 94 | CES85 = 76 |
| CES11 = 60 | CES36 = 90 | CES61 = 89 | CES86 = 65 |
| CES12 = 66 | CES37 = 96 | CES62 = 94 | CES87 = 84 |
| CES13 = 44 | CES38 = 98 | CES63 = 87 | CES88 = 86 |
| CES14 = 74 | CES39 = 98 | CES64 = 82 | CES89 = 73 |
| CES15 = 72 | CES40 = 95 | CES65 = 78 | CES90 = 88 |
| CES16 = 48 | CES41 = 96 | CES66 = 81 | CES91 = 82 |
| CES17 = 50 | CES42 = 97 | CES67 = 80 | CES92 = 64 |
| CES18 = 57 | CES43 = 91 | CES68 = 83 | CES93 = 78 |
| CES19 = 73 | CES44 = 99 | CES69 = 88 | CES94 = 59 |
| CES20 = 67 | CES45 = 93 | CES70 = 80 | CES95 = 74 |
| CES21 = 87 | CES46 = 89 | CES71 = 79 | CES96 = 83 |
| CES22 = 79 | CES47 = 92 | CES72 = 92 | CES97 = 88 |
| CES23 = 92 | CES48 = 83 | CES73 = 75 | CES98 = 83 |
| CES24 = 91 | CES49 = 90 | CES74 = 91 | CES99 = 74 |
| CES25 = 72 | CES50 = 94 | CES75 = 81 | |



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)