

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: McGRAW-EDISON

Report Number: P631497

Luminaire Tested: GWS-SA1F-827-U-SLL-W

Issue Date: 1/10/2023

**Test Information**

Test Method: LM-79-2019  
Report Number: P631497  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2209-782-37)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 1/10/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: McGRAW-EDISON  
Catalog Number: GWS-SA1F-827-U-SLL-W  
Description: GALLEON WALL SLIM LUMINAIRE. (1) LIGHTSQUARES WITH 16 LEDS EACH AND SPILL LIGHT ELIMINATOR LEFT OPTICS  
Light Source: (16) 2700K CCT, 80 CRI LEDS  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 5804.6 lumens  
Efficiency: N/A  
Efficacy: 86.4 lumens/watt  
Luminous Opening: Rectangular (W 0.5' x L: 0.5' x H: 0')  
IES Classification: Type III - Short  
BUG Rating: B1 - U0 - G2  
  
Input Watts (W): 67.2  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 0  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 28.75 FT



REPORT NUMBER: P631497  
 CATALOG NUMBER: GWS-SA1F-827-U-SLL-W

### Iso-Footcandle Lines of Horizontal Illumination


× Max cd  
 - - - 1/2 Max cd



Based on 10 foot mounting height. Maximum calculated value = 9.7 fc  
 Type III - Short - N/A

REPORT NUMBER: P631497  
CATALOG NUMBER: GWS-SA1F-827-U-SLL-W

### Luminous Intensity Polar Plot



— Vertical Plane Through 315-Deg Lateral    - - - Horizontal Cone Through 62.5-Deg Vertical

REPORT NUMBER: P631497

CATALOG NUMBER: GWS-SA1F-827-U-SLL-W


**FLUX DISTRIBUTION:**

|                    |           | Downward | Upward | Total  |
|--------------------|-----------|----------|--------|--------|
| <b>House Side</b>  | Lumens    | 1387.9   | 0.0    | 1387.9 |
|                    | % Fixture | 23.9     | 0.0    | 23.9   |
| <b>Street Side</b> | Lumens    | 4416.7   | 0.0    | 4416.7 |
|                    | % Fixture | 76.1     | 0.0    | 76.1   |
| <b>Total</b>       | Lumens    | 5804.6   | 0.0    | 5804.6 |
|                    | % Fixture | 100.0    | 0.0    | 100.0  |

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 71.3   | 1.2       |
| 10°-20°   | 231.7  | 4.0       |
| 20°-30°   | 364.8  | 6.3       |
| 30°-40°   | 500.0  | 8.6       |
| 40°-50°   | 780.1  | 13.4      |
| 50°-60°   | 1345.1 | 23.2      |
| 60°-70°   | 1558.8 | 26.9      |
| 70°-80°   | 822.8  | 14.2      |
| 80°-90°   | 130.0  | 2.2       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-90°    | 5804.6 | 100.0     |
| 0°-180°   | 5804.6 | 100.0     |

**Coefficient of Utilization**



REPORT NUMBER: P631497


CATALOG NUMBER: GWS-SA1F-827-U-SLL-W

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

| Zone           | Lumens | % Fixture | Zone Rating/Lumen Limit |      |         |
|----------------|--------|-----------|-------------------------|------|---------|
|                |        |           | B                       | U    | G       |
| FL (0°-30°)    | 383.9  | 6.6       |                         |      |         |
| FM (30°-60°)   | 1916.3 | 33.0      |                         |      |         |
| FH (60°-80°)   | 2016.2 | 34.7      |                         |      | G2/5000 |
| FVH (80°-90°)  | 100.3  | 1.7       |                         |      | G2/225  |
| BL (0°-30°)    | 283.9  | 4.9       | B1/500                  |      |         |
| BM (30°-60°)   | 708.9  | 12.2      | B1/1000                 |      |         |
| BH (60°-80°)   | 365.4  | 6.3       | B1/500                  |      | G1/500  |
| BVH (80°-90°)  | 29.7   | 0.5       |                         |      | G1/100  |
| UL (90°-100°)  | 0.0    | 0.0       |                         | U0/0 |         |
| UH (100°-180°) | 0.0    | 0.0       |                         | U0/0 |         |

**BUG Rating: B1-U0-G2**

Type III Short





REPORT NUMBER: P631497  
 CATALOG NUMBER: GWS-SA1F-827-U-SLL-W

**CANDELA DISTRIBUTION (FULL):**

|       | 0°     | 2°     | 5°     | 15°    | 25°   | 35°   | 45°   | 55°   | 65°   | 75°   | 85°   |
|-------|--------|--------|--------|--------|-------|-------|-------|-------|-------|-------|-------|
| 0°    | 723.7  | 723.7  | 723.7  | 723.7  | 723.7 | 723.7 | 723.7 | 723.7 | 723.7 | 723.7 | 723.7 |
| 2.5°  | 786.3  | 783.2  | 778.8  | 763.7  | 754.3 | 743.7 | 732.6 | 719.7 | 705.1 | 694.9 | 684.6 |
| 5°    | 852.9  | 848.0  | 837.4  | 801.4  | 776.5 | 749.5 | 726.8 | 701.1 | 675.8 | 658.4 | 641.1 |
| 7.5°  | 916.9  | 910.6  | 894.2  | 839.2  | 798.7 | 759.7 | 725.5 | 688.2 | 650.5 | 624.7 | 604.3 |
| 10°   | 980.8  | 967.9  | 947.0  | 875.1  | 821.8 | 776.5 | 737.5 | 691.7 | 641.6 | 606.5 | 584.7 |
| 12.5° | 1029.6 | 1017.6 | 995.0  | 908.0  | 844.9 | 788.1 | 744.1 | 702.0 | 659.3 | 622.0 | 599.8 |
| 15°   | 1075.4 | 1059.8 | 1034.1 | 938.6  | 864.0 | 787.6 | 730.8 | 694.0 | 687.7 | 678.4 | 649.6 |
| 17.5° | 1108.2 | 1094.0 | 1067.4 | 963.5  | 874.7 | 773.9 | 694.0 | 672.2 | 700.2 | 728.6 | 701.1 |
| 20°   | 1137.1 | 1120.6 | 1093.6 | 980.8  | 876.9 | 743.2 | 649.1 | 649.6 | 693.5 | 732.6 | 725.9 |
| 22.5° | 1161.5 | 1143.3 | 1119.3 | 1000.3 | 876.0 | 700.6 | 610.1 | 636.7 | 680.6 | 711.3 | 712.2 |
| 25°   | 1191.7 | 1176.6 | 1156.6 | 1029.2 | 876.0 | 657.1 | 581.6 | 621.2 | 658.9 | 684.6 | 683.8 |
| 27.5° | 1228.5 | 1218.3 | 1201.9 | 1073.1 | 884.0 | 620.7 | 565.7 | 601.2 | 630.9 | 653.1 | 652.7 |
| 30°   | 1269.8 | 1260.5 | 1248.1 | 1119.8 | 897.8 | 593.6 | 556.8 | 576.3 | 598.1 | 615.8 | 615.8 |
| 32.5° | 1312.0 | 1308.5 | 1295.1 | 1157.1 | 887.1 | 585.2 | 549.2 | 551.4 | 563.0 | 577.6 | 576.3 |
| 35°   | 1370.6 | 1367.1 | 1350.2 | 1185.9 | 840.9 | 573.2 | 537.2 | 526.1 | 527.5 | 536.8 | 539.9 |
| 37.5° | 1456.3 | 1451.0 | 1426.1 | 1219.7 | 771.2 | 543.0 | 517.7 | 499.5 | 495.5 | 499.5 | 505.3 |
| 40°   | 1559.8 | 1551.8 | 1518.0 | 1265.4 | 690.9 | 502.2 | 487.1 | 472.0 | 465.3 | 466.6 | 473.3 |
| 42.5° | 1689.4 | 1672.5 | 1624.1 | 1313.8 | 611.4 | 466.2 | 452.9 | 443.6 | 436.0 | 435.1 | 448.0 |
| 45°   | 1899.9 | 1853.7 | 1776.9 | 1356.9 | 544.3 | 447.1 | 422.2 | 415.6 | 409.4 | 412.9 | 428.0 |
| 47.5° | 2267.5 | 2182.2 | 2032.6 | 1393.7 | 503.5 | 447.5 | 397.8 | 390.7 | 390.3 | 397.4 | 414.2 |
| 50°   | 2772.8 | 2649.8 | 2418.9 | 1418.6 | 482.2 | 452.9 | 383.2 | 371.6 | 380.1 | 387.2 | 403.1 |
| 52.5° | 3256.7 | 3068.9 | 2794.1 | 1418.1 | 472.9 | 453.8 | 387.2 | 353.9 | 380.1 | 381.8 | 396.9 |
| 55°   | 3670.1 | 3330.0 | 2895.3 | 1272.5 | 459.5 | 450.2 | 402.7 | 340.1 | 375.2 | 381.8 | 393.8 |
| 57.5° | 3998.6 | 3496.0 | 2887.7 | 1027.9 | 499.9 | 430.7 | 412.0 | 337.0 | 361.0 | 382.7 | 396.5 |
| 60°   | 3962.2 | 3420.1 | 2701.7 | 630.9  | 495.9 | 396.0 | 410.7 | 342.8 | 337.0 | 370.7 | 393.4 |
| 62.5° | 3720.2 | 3147.9 | 2381.6 | 437.8  | 465.8 | 376.1 | 388.9 | 353.0 | 314.8 | 353.4 | 378.3 |
| 65°   | 3381.5 | 2796.7 | 1984.7 | 335.7  | 385.8 | 377.0 | 352.1 | 345.9 | 295.3 | 325.9 | 352.5 |
| 67.5° | 2933.5 | 2361.2 | 1566.9 | 266.0  | 269.1 | 326.3 | 319.7 | 307.2 | 277.1 | 301.5 | 325.4 |
| 70°   | 2205.3 | 1723.1 | 1078.0 | 214.0  | 203.8 | 272.6 | 287.3 | 276.2 | 259.3 | 266.4 | 291.7 |
| 72.5° | 1554.0 | 1125.1 | 590.5  | 169.6  | 157.2 | 209.6 | 249.5 | 247.7 | 229.1 | 234.4 | 259.3 |
| 75°   | 1154.8 | 796.1  | 369.0  | 134.1  | 127.9 | 150.1 | 209.1 | 214.5 | 198.9 | 205.1 | 224.2 |
| 77.5° | 768.6  | 515.5  | 205.1  | 99.5   | 99.5  | 109.7 | 155.8 | 180.7 | 169.2 | 174.0 | 187.4 |
| 80°   | 424.0  | 262.4  | 102.6  | 65.3   | 67.0  | 75.5  | 113.7 | 130.1 | 130.5 | 142.5 | 146.1 |
| 82.5° | 134.1  | 83.5   | 45.7   | 38.2   | 36.0  | 43.1  | 73.3  | 93.2  | 87.0  | 111.0 | 102.1 |
| 85°   | 30.6   | 19.5   | 8.4    | 8.4    | 9.3   | 14.2  | 28.0  | 49.7  | 63.5  | 76.4  | 55.5  |
| 87.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.4   | 19.5  | 28.9  | 25.8  |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |



REPORT NUMBER: P631497  
 CATALOG NUMBER: GWS-SA1F-827-U-SLL-W

**CANDELA DISTRIBUTION (continued):**

|       | 90°   | 95°   | 105°  | 115°  | 125°  | 135°  | 145°  | 155°  | 165°  | 175°  | 180°  |
|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|
| 0°    | 723.7 | 723.7 | 723.7 | 723.7 | 723.7 | 723.7 | 723.7 | 723.7 | 723.7 | 723.7 | 723.7 |
| 2.5°  | 678.4 | 669.5 | 666.9 | 659.3 | 658.4 | 651.3 | 648.7 | 648.7 | 651.8 | 651.8 | 654.9 |
| 5°    | 634.0 | 622.9 | 616.7 | 607.8 | 605.6 | 600.3 | 596.7 | 597.2 | 601.2 | 603.8 | 609.2 |
| 7.5°  | 595.0 | 587.4 | 583.0 | 579.0 | 578.1 | 577.2 | 573.2 | 572.8 | 574.1 | 578.1 | 582.1 |
| 10°   | 578.5 | 573.2 | 574.5 | 577.6 | 582.5 | 585.2 | 581.6 | 579.9 | 578.5 | 581.2 | 584.7 |
| 12.5° | 594.5 | 589.2 | 591.8 | 597.2 | 603.8 | 606.5 | 605.2 | 604.7 | 606.1 | 616.3 | 623.8 |
| 15°   | 629.6 | 619.4 | 615.8 | 618.0 | 623.4 | 626.0 | 624.7 | 626.5 | 634.9 | 661.6 | 680.6 |
| 17.5° | 673.1 | 648.2 | 634.0 | 630.0 | 632.3 | 634.5 | 634.5 | 638.9 | 653.6 | 692.6 | 716.6 |
| 20°   | 696.6 | 664.2 | 640.2 | 630.5 | 631.4 | 633.6 | 633.6 | 639.8 | 656.2 | 698.0 | 713.5 |
| 22.5° | 690.4 | 660.7 | 631.4 | 620.7 | 621.2 | 622.9 | 622.9 | 628.3 | 642.9 | 679.8 | 686.9 |
| 25°   | 666.0 | 639.8 | 610.9 | 601.6 | 602.5 | 605.6 | 604.7 | 607.8 | 618.9 | 649.1 | 653.1 |
| 27.5° | 636.7 | 613.6 | 585.2 | 578.1 | 582.1 | 588.3 | 583.0 | 583.4 | 593.6 | 618.9 | 619.4 |
| 30°   | 605.2 | 586.1 | 560.8 | 555.4 | 563.0 | 566.1 | 561.2 | 561.2 | 571.4 | 588.7 | 588.3 |
| 32.5° | 571.0 | 559.0 | 540.8 | 535.0 | 543.5 | 548.3 | 542.1 | 543.0 | 551.0 | 562.5 | 558.1 |
| 35°   | 539.0 | 532.8 | 524.4 | 520.4 | 525.7 | 530.1 | 526.1 | 527.9 | 535.5 | 538.6 | 532.4 |
| 37.5° | 508.4 | 507.5 | 508.4 | 508.4 | 509.7 | 511.0 | 508.4 | 512.8 | 519.5 | 515.5 | 508.4 |
| 40°   | 481.7 | 485.3 | 493.7 | 491.5 | 490.2 | 491.5 | 489.7 | 497.3 | 503.9 | 496.8 | 488.4 |
| 42.5° | 459.5 | 466.2 | 479.1 | 479.1 | 476.4 | 477.3 | 476.4 | 485.7 | 490.6 | 480.8 | 471.5 |
| 45°   | 440.4 | 450.2 | 466.6 | 468.9 | 464.4 | 464.4 | 466.2 | 477.7 | 479.5 | 466.2 | 456.4 |
| 47.5° | 427.1 | 439.1 | 457.8 | 461.8 | 455.1 | 454.7 | 459.5 | 472.0 | 472.0 | 456.4 | 445.3 |
| 50°   | 417.8 | 431.1 | 453.3 | 458.6 | 452.0 | 450.2 | 458.2 | 470.2 | 467.5 | 448.9 | 437.8 |
| 52.5° | 411.6 | 425.3 | 452.9 | 460.4 | 456.0 | 454.2 | 462.2 | 470.6 | 464.0 | 444.0 | 432.5 |
| 55°   | 407.6 | 422.7 | 454.2 | 460.4 | 455.5 | 452.4 | 460.4 | 468.0 | 464.4 | 441.3 | 430.2 |
| 57.5° | 409.8 | 424.9 | 452.4 | 455.5 | 449.8 | 444.4 | 453.8 | 464.4 | 463.1 | 442.2 | 431.1 |
| 60°   | 406.3 | 420.0 | 442.7 | 443.6 | 433.8 | 425.3 | 439.1 | 455.1 | 455.1 | 439.1 | 429.3 |
| 62.5° | 389.8 | 403.6 | 423.6 | 424.5 | 413.4 | 404.0 | 420.0 | 439.1 | 438.7 | 425.8 | 415.6 |
| 65°   | 362.7 | 375.6 | 398.3 | 400.5 | 389.4 | 379.6 | 396.0 | 413.8 | 415.1 | 403.6 | 394.7 |
| 67.5° | 333.0 | 344.5 | 361.4 | 370.3 | 361.0 | 350.8 | 365.9 | 382.7 | 382.3 | 368.5 | 359.2 |
| 70°   | 297.5 | 308.1 | 323.7 | 331.2 | 325.4 | 315.7 | 329.4 | 338.3 | 334.3 | 327.7 | 321.5 |
| 72.5° | 262.4 | 272.6 | 287.3 | 287.3 | 281.0 | 271.7 | 275.7 | 291.7 | 296.6 | 291.7 | 287.7 |
| 75°   | 225.5 | 234.4 | 244.6 | 246.9 | 233.1 | 216.2 | 234.9 | 248.6 | 254.4 | 252.2 | 247.3 |
| 77.5° | 187.8 | 194.5 | 209.6 | 205.6 | 179.8 | 170.9 | 186.0 | 206.5 | 210.5 | 209.1 | 202.5 |
| 80°   | 144.7 | 148.7 | 164.7 | 156.7 | 136.8 | 131.0 | 137.6 | 153.6 | 154.5 | 150.1 | 141.6 |
| 82.5° | 97.2  | 102.6 | 113.2 | 97.7  | 97.2  | 91.9  | 86.6  | 88.4  | 96.3  | 95.5  | 89.7  |
| 85°   | 49.7  | 52.4  | 62.6  | 58.6  | 50.2  | 43.5  | 41.3  | 44.0  | 39.5  | 36.0  | 31.1  |
| 87.5° | 20.9  | 22.6  | 31.1  | 17.3  | 5.3   | 0.0   | 0.0   | 2.7   | 4.0   | 5.8   | 6.2   |
| 90°   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |





REPORT NUMBER: P631497  
 CATALOG NUMBER: GWS-SA1F-827-U-SLL-W

**CANDELA DISTRIBUTION (continued):**

|       | 185°  | 195°  | 205°  | 215°  | 225°  | 235°  | 245°  | 255°   | 265°   | 270°   | 275°   |
|-------|-------|-------|-------|-------|-------|-------|-------|--------|--------|--------|--------|
| 0°    | 723.7 | 723.7 | 723.7 | 723.7 | 723.7 | 723.7 | 723.7 | 723.7  | 723.7  | 723.7  | 723.7  |
| 2.5°  | 662.0 | 666.9 | 678.9 | 694.0 | 708.6 | 723.7 | 740.1 | 750.4  | 762.8  | 778.8  | 779.2  |
| 5°    | 615.8 | 626.9 | 644.2 | 667.3 | 691.3 | 718.8 | 750.8 | 777.4  | 809.4  | 834.7  | 844.9  |
| 7.5°  | 587.4 | 603.4 | 625.1 | 654.5 | 686.0 | 720.2 | 761.9 | 806.7  | 859.1  | 892.9  | 912.9  |
| 10°   | 590.1 | 614.5 | 636.2 | 661.1 | 689.5 | 726.4 | 780.1 | 839.6  | 904.0  | 948.4  | 973.2  |
| 12.5° | 637.6 | 663.3 | 659.3 | 658.0 | 677.1 | 721.9 | 794.8 | 872.9  | 951.5  | 995.9  | 1025.6 |
| 15°   | 697.5 | 707.3 | 669.5 | 641.1 | 652.7 | 706.0 | 802.7 | 902.6  | 991.0  | 1045.2 | 1074.5 |
| 17.5° | 728.2 | 708.6 | 662.9 | 620.3 | 617.2 | 681.5 | 806.7 | 932.8  | 1035.4 | 1089.6 | 1120.6 |
| 20°   | 713.9 | 685.5 | 646.9 | 606.5 | 584.3 | 648.2 | 804.5 | 956.8  | 1075.8 | 1136.2 | 1161.5 |
| 22.5° | 683.3 | 658.4 | 628.3 | 589.6 | 557.7 | 611.8 | 798.7 | 980.8  | 1111.8 | 1172.6 | 1194.8 |
| 25°   | 650.0 | 631.4 | 606.5 | 572.8 | 542.6 | 579.9 | 794.8 | 1012.8 | 1153.1 | 1211.2 | 1225.4 |
| 27.5° | 616.7 | 602.9 | 582.5 | 556.3 | 539.0 | 557.7 | 796.1 | 1054.5 | 1206.3 | 1261.4 | 1255.6 |
| 30°   | 583.9 | 571.9 | 557.7 | 546.1 | 538.6 | 552.3 | 792.5 | 1098.9 | 1264.9 | 1316.0 | 1281.8 |
| 32.5° | 552.8 | 541.7 | 532.8 | 534.6 | 539.0 | 554.6 | 774.3 | 1139.3 | 1318.7 | 1362.2 | 1310.2 |
| 35°   | 526.1 | 514.6 | 514.6 | 520.8 | 537.2 | 547.0 | 727.3 | 1170.8 | 1378.2 | 1421.7 | 1350.6 |
| 37.5° | 501.3 | 491.1 | 497.7 | 507.9 | 523.5 | 526.6 | 666.9 | 1201.5 | 1464.7 | 1505.6 | 1413.2 |
| 40°   | 479.5 | 469.3 | 481.3 | 494.2 | 502.2 | 500.8 | 605.6 | 1244.1 | 1566.9 | 1609.0 | 1496.3 |
| 42.5° | 462.2 | 452.9 | 463.5 | 480.0 | 481.3 | 482.6 | 560.8 | 1284.9 | 1685.4 | 1739.1 | 1639.2 |
| 45°   | 448.0 | 441.3 | 446.7 | 463.1 | 463.1 | 483.5 | 532.8 | 1319.1 | 1863.9 | 1958.9 | 1901.6 |
| 47.5° | 436.9 | 432.9 | 435.6 | 440.9 | 449.8 | 499.5 | 515.0 | 1345.3 | 2188.9 | 2375.4 | 2317.7 |
| 50°   | 430.7 | 426.7 | 430.2 | 419.1 | 445.8 | 507.5 | 509.3 | 1365.3 | 2617.4 | 2909.5 | 2838.0 |
| 52.5° | 425.3 | 424.0 | 426.2 | 400.5 | 454.7 | 502.2 | 504.8 | 1338.6 | 2904.6 | 3435.2 | 3505.8 |
| 55°   | 423.6 | 424.5 | 413.8 | 386.7 | 465.3 | 484.4 | 491.5 | 1148.2 | 2982.8 | 3888.5 | 4326.7 |
| 57.5° | 424.5 | 421.8 | 394.7 | 388.1 | 465.8 | 448.9 | 510.6 | 819.2  | 2869.1 | 4085.7 | 5129.9 |
| 60°   | 421.4 | 408.0 | 371.6 | 400.0 | 445.3 | 407.1 | 496.8 | 534.1  | 2569.4 | 3934.2 | 5176.5 |
| 62.5° | 407.6 | 388.1 | 351.6 | 406.7 | 408.9 | 382.3 | 451.1 | 411.6  | 2169.8 | 3610.1 | 4727.2 |
| 65°   | 387.6 | 361.4 | 334.8 | 392.9 | 372.1 | 370.7 | 339.2 | 329.9  | 1744.9 | 3224.3 | 4301.0 |
| 67.5° | 354.8 | 328.6 | 322.3 | 361.4 | 334.8 | 328.6 | 272.6 | 273.5  | 1392.4 | 2813.2 | 3872.5 |
| 70°   | 317.5 | 291.3 | 296.1 | 326.8 | 297.9 | 273.1 | 220.7 | 227.8  | 1056.3 | 2343.9 | 3294.9 |
| 72.5° | 293.0 | 258.0 | 258.4 | 287.7 | 262.0 | 221.1 | 181.6 | 187.8  | 670.4  | 1766.7 | 2619.6 |
| 75°   | 247.3 | 227.3 | 217.6 | 233.1 | 222.4 | 172.3 | 152.7 | 151.4  | 397.4  | 1266.3 | 1961.6 |
| 77.5° | 206.5 | 190.9 | 186.0 | 192.3 | 166.1 | 127.4 | 123.0 | 120.8  | 225.1  | 811.2  | 1285.4 |
| 80°   | 149.6 | 145.6 | 145.2 | 148.3 | 127.9 | 93.7  | 93.7  | 94.1   | 121.2  | 440.4  | 724.6  |
| 82.5° | 95.0  | 103.9 | 91.9  | 102.1 | 87.0  | 66.6  | 62.2  | 70.6   | 69.7   | 187.8  | 305.5  |
| 85°   | 39.5  | 54.2  | 50.6  | 53.7  | 41.3  | 36.4  | 39.1  | 42.2   | 40.4   | 72.4   | 119.0  |
| 87.5° | 7.5   | 8.9   | 9.8   | 9.3   | 9.3   | 11.5  | 12.9  | 15.5   | 15.5   | 20.9   | 36.0   |
| 90°   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0    | 0.0    | 0.0    |



REPORT NUMBER: P631497  
 CATALOG NUMBER: GWS-SA1F-827-U-SLL-W

**CANDELA DISTRIBUTION (continued):**

|       | 285°   | 295°   | 305°   | 315°   | 325°   | 335°   | 345°   | 355°   | 358°   | 360°   |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°    | 723.7  | 723.7  | 723.7  | 723.7  | 723.7  | 723.7  | 723.7  | 723.7  | 723.7  | 723.7  |
| 2.5°  | 796.1  | 809.0  | 806.3  | 812.1  | 804.5  | 807.2  | 792.1  | 788.1  | 785.4  | 786.3  |
| 5°    | 877.8  | 904.0  | 908.9  | 918.6  | 912.0  | 912.0  | 885.3  | 865.3  | 858.2  | 852.9  |
| 7.5°  | 960.8  | 998.5  | 1023.4 | 1026.1 | 1022.5 | 1015.4 | 976.8  | 940.8  | 928.0  | 916.9  |
| 10°   | 1034.5 | 1079.8 | 1107.8 | 1121.1 | 1114.4 | 1103.3 | 1055.4 | 1006.1 | 990.6  | 980.8  |
| 12.5° | 1090.9 | 1130.9 | 1149.5 | 1158.4 | 1157.5 | 1153.5 | 1114.4 | 1061.2 | 1044.7 | 1029.6 |
| 15°   | 1127.3 | 1147.3 | 1140.2 | 1139.7 | 1146.0 | 1161.9 | 1149.9 | 1108.2 | 1089.1 | 1075.4 |
| 17.5° | 1150.8 | 1131.7 | 1100.2 | 1085.6 | 1098.9 | 1136.6 | 1164.2 | 1140.6 | 1123.3 | 1108.2 |
| 20°   | 1159.3 | 1091.3 | 1045.6 | 1018.5 | 1034.1 | 1088.7 | 1156.6 | 1164.2 | 1149.5 | 1137.1 |
| 22.5° | 1149.5 | 1042.1 | 979.9  | 947.9  | 963.0  | 1028.3 | 1134.4 | 1183.2 | 1173.5 | 1161.5 |
| 25°   | 1125.5 | 990.6  | 916.0  | 887.1  | 903.5  | 970.1  | 1094.9 | 1201.0 | 1201.5 | 1191.7 |
| 27.5° | 1095.8 | 943.0  | 871.1  | 844.0  | 860.0  | 922.2  | 1056.3 | 1216.5 | 1232.1 | 1228.5 |
| 30°   | 1065.6 | 914.6  | 849.8  | 830.7  | 842.7  | 897.8  | 1016.8 | 1232.5 | 1263.6 | 1269.8 |
| 32.5° | 1051.8 | 928.4  | 900.0  | 908.4  | 892.9  | 912.0  | 1002.5 | 1255.2 | 1301.8 | 1312.0 |
| 35°   | 1070.0 | 1050.5 | 1122.4 | 1155.7 | 1100.7 | 1028.3 | 1020.7 | 1289.4 | 1355.5 | 1370.6 |
| 37.5° | 1158.4 | 1312.0 | 1419.5 | 1536.7 | 1441.2 | 1281.8 | 1110.9 | 1347.5 | 1432.3 | 1456.3 |
| 40°   | 1350.6 | 1540.2 | 1734.2 | 1885.7 | 1741.4 | 1526.9 | 1282.3 | 1434.1 | 1538.0 | 1559.8 |
| 42.5° | 1531.8 | 1754.2 | 2021.5 | 2217.3 | 2029.9 | 1727.1 | 1467.0 | 1579.7 | 1677.4 | 1689.4 |
| 45°   | 1709.4 | 1964.2 | 2369.2 | 2641.3 | 2386.9 | 1917.6 | 1655.7 | 1825.7 | 1899.4 | 1899.9 |
| 47.5° | 1917.6 | 2200.9 | 2805.2 | 3192.8 | 2860.7 | 2128.5 | 1832.8 | 2215.1 | 2317.7 | 2267.5 |
| 50°   | 2166.7 | 2436.2 | 3254.0 | 3834.3 | 3438.3 | 2387.8 | 2057.9 | 2689.7 | 2829.6 | 2772.8 |
| 52.5° | 2500.1 | 2695.5 | 3748.7 | 4459.9 | 4067.9 | 2683.1 | 2384.3 | 3316.6 | 3362.8 | 3256.7 |
| 55°   | 2969.4 | 3069.8 | 4383.6 | 5232.5 | 4770.7 | 3046.7 | 2861.6 | 4103.4 | 3974.2 | 3670.1 |
| 57.5° | 4038.1 | 3662.1 | 5198.7 | 6113.8 | 5565.9 | 3707.4 | 3907.6 | 4971.0 | 4511.4 | 3998.6 |
| 60°   | 4932.4 | 4381.4 | 5953.1 | 6988.5 | 6247.5 | 4435.5 | 4889.7 | 5121.9 | 4491.5 | 3962.2 |
| 62.5° | 4630.9 | 4564.7 | 6225.3 | 7084.8 | 6480.1 | 4793.8 | 4707.2 | 4741.4 | 4198.4 | 3720.2 |
| 65°   | 4063.0 | 4210.9 | 5982.4 | 6628.0 | 6222.2 | 4472.8 | 4257.9 | 4389.8 | 3863.2 | 3381.5 |
| 67.5° | 3727.8 | 3836.6 | 5550.4 | 5896.7 | 5753.3 | 4125.6 | 3908.5 | 3813.0 | 3342.8 | 2933.5 |
| 70°   | 3385.0 | 3475.2 | 4943.9 | 4979.0 | 5022.0 | 3548.4 | 3195.9 | 2911.7 | 2491.7 | 2205.3 |
| 72.5° | 2925.0 | 2929.9 | 4177.1 | 3973.8 | 4055.5 | 2776.8 | 2572.5 | 2176.9 | 1813.7 | 1554.0 |
| 75°   | 2454.0 | 2319.9 | 3306.4 | 2777.6 | 2941.5 | 2160.0 | 2136.1 | 1640.6 | 1368.0 | 1154.8 |
| 77.5° | 1871.0 | 1714.3 | 2415.3 | 1826.6 | 2065.9 | 1438.5 | 1605.9 | 1112.7 | 962.6  | 768.6  |
| 80°   | 1256.1 | 1158.4 | 1334.7 | 1031.0 | 1351.5 | 991.4  | 1047.4 | 630.5  | 546.6  | 424.0  |
| 82.5° | 662.4  | 565.7  | 824.9  | 611.4  | 815.2  | 544.8  | 392.9  | 194.9  | 166.1  | 134.1  |
| 85°   | 256.6  | 297.0  | 404.5  | 217.6  | 316.1  | 194.5  | 113.7  | 48.4   | 40.4   | 30.6   |
| 87.5° | 49.7   | 76.8   | 42.2   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Invue

Report Number: SP1-2407-157-9

Test Date: 10/03/2024

Luminaire Tested: EMM2-HTN-SA1A-827-U-5WQ

Data applicable to all product families utilizing light square engine

**Test Information**

Test Method: LM-79-2019  
 Report Number: SP1-2407-157-9  
 Test Lab: COOPER LIGHTING SOLUTIONS  
 Photometer: SP1 - 76IN SPHERE  
 Measurement Geometry: 4π  
 Issue Date: 10/03/2024  
 Manufacturer: COOPER LIGHTING SOLUTIONS  
 Product Line: Invue  
 Catalog Number: **EMM2-HTN-SA1A-827-U-5WQ**  
 Description: Epic Modern Light Square 40W 5WQ Optic

**Spectral Parameters**

CCT (K): 2764  
 CIE u': 0.2591  
 CIE v': 0.5290  
 Duv: 0.0020  
 CIE x: 0.4581  
 CIE y: 0.4156  
 CIE z: 0.1263  
 Peak Wavelength (nm): 603  
 Dominant Wavelength (nm): 583  
 Purity: 62.2537  
 Rf: 84.7  
 Rg: 94.6

|           |      |      |      |
|-----------|------|------|------|
| CRI (Ra): | 80.9 |      |      |
| R1:       | 78.8 | R9:  | -1.5 |
| R2:       | 89.9 | R10: | 77.9 |
| R3:       | 96.2 | R11: | 78.9 |
| R4:       | 79.1 | R12: | 71.6 |
| R5:       | 79.1 | R13: | 81.2 |
| R6:       | 88.8 | R14: | 98.5 |
| R7:       | 81.3 | R15: | 69.9 |
| R8:       | 54.3 |      |      |



**Test Conditions**


Stabilization Time: 81M  
 Operation Time: 2H 21M  
 Sphere Temperature (°C): 25.2

REPORT NUMBER: SP1-2407-157-9


| Measurement and Test Equipment |                       |                  |                      |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument                     | Identification Number | Calibration Date | Calibration Due Date |
| Photometer                     | IN0058                | 6/18/2024        | 12/18/2024           |
| Power Meter                    | INXT2011004           | 2/8/2024         | 2/8/2025             |
| AC Power Source                | IN0063                | 10/24/2023       | 10/24/2024           |
| DC Power Source                | IN0208                | 10/24/2023       | 10/24/2024           |
| Sphere Thermometer             | IN0085                | 10/24/2023       | 10/24/2024           |
| Room Thermometer               | IN0046                | 10/24/2023       | 10/24/2024           |

REPORT NUMBER: SP1-2407-157-9

CIE 1931 Chromaticity Diagram




CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 2700K 4-step quadrangle

REPORT NUMBER: SP1-2407-157-9

**Photopic Flux vs. Wavelength**




**Photopic Lumens: 4337.9**

| $\lambda$<br>(nm) | Power<br>( $\mu\text{W}/\text{nm}$ ) | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>( $\mu\text{W}/\text{nm}$ ) | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>( $\mu\text{W}/\text{nm}$ ) | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>( $\mu\text{W}/\text{nm}$ ) | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>( $\mu\text{W}/\text{nm}$ ) | Lumens<br>( $\phi/\text{nm}$ ) |
|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|
| 360               | 0                                    | 0.0                            | 490               | 18018                                | 2.6                            | 620               | 87426                                | 22.8                           | 750               | 2680                                 | 0.0                            | 880               | 58                                   | 0.0                            |
| 365               | 0                                    | 0.0                            | 495               | 22295                                | 3.9                            | 625               | 83013                                | 18.2                           | 755               | 2287                                 | 0.0                            | 885               | 46                                   | 0.0                            |
| 370               | 0                                    | 0.0                            | 500               | 26478                                | 5.8                            | 630               | 78077                                | 14.1                           | 760               | 1944                                 | 0.0                            | 890               | 45                                   | 0.0                            |
| 375               | 0                                    | 0.0                            | 505               | 30524                                | 8.5                            | 635               | 72080                                | 10.7                           | 765               | 1653                                 | 0.0                            | 895               | 41                                   | 0.0                            |
| 380               | 0                                    | 0.0                            | 510               | 33611                                | 11.5                           | 640               | 66249                                | 7.9                            | 770               | 1413                                 | 0.0                            | 900               | 38                                   | 0.0                            |
| 385               | 0                                    | 0.0                            | 515               | 36490                                | 15.2                           | 645               | 59973                                | 5.7                            | 775               | 1198                                 | 0.0                            | 905               | 33                                   | 0.0                            |
| 390               | 0                                    | 0.0                            | 520               | 38610                                | 18.7                           | 650               | 53972                                | 3.9                            | 780               | 1025                                 | 0.0                            | 910               | 30                                   | 0.0                            |
| 395               | 0                                    | 0.0                            | 525               | 40511                                | 21.9                           | 655               | 48369                                | 2.7                            | 785               | 874                                  | 0.0                            | 915               | 23                                   | 0.0                            |
| 400               | 48                                   | 0.0                            | 530               | 42223                                | 24.9                           | 660               | 42641                                | 1.8                            | 790               | 747                                  | 0.0                            | 920               | 24                                   | 0.0                            |
| 405               | 201                                  | 0.0                            | 535               | 44137                                | 27.6                           | 665               | 37602                                | 1.1                            | 795               | 639                                  | 0.0                            | 925               | 22                                   | 0.0                            |
| 410               | 457                                  | 0.0                            | 540               | 46032                                | 30.0                           | 670               | 32798                                | 0.7                            | 800               | 547                                  | 0.0                            | 930               | 22                                   | 0.0                            |
| 415               | 925                                  | 0.0                            | 545               | 48553                                | 32.5                           | 675               | 28558                                | 0.5                            | 805               | 473                                  | 0.0                            | 935               | 17                                   | 0.0                            |
| 420               | 1816                                 | 0.0                            | 550               | 51408                                | 34.9                           | 680               | 24782                                | 0.3                            | 810               | 401                                  | 0.0                            | 940               | 13                                   | 0.0                            |
| 425               | 3217                                 | 0.0                            | 555               | 54711                                | 37.4                           | 685               | 21386                                | 0.2                            | 815               | 351                                  | 0.0                            | 945               | 6                                    | 0.0                            |
| 430               | 5520                                 | 0.0                            | 560               | 58847                                | 40.0                           | 690               | 18413                                | 0.1                            | 820               | 307                                  | 0.0                            | 950               | 10                                   | 0.0                            |
| 435               | 9225                                 | 0.1                            | 565               | 63386                                | 42.4                           | 695               | 15721                                | 0.1                            | 825               | 261                                  | 0.0                            | 955               | 11                                   | 0.0                            |
| 440               | 15522                                | 0.2                            | 570               | 68196                                | 44.3                           | 700               | 13432                                | 0.0                            | 830               | 228                                  | 0.0                            | 960               | 8                                    | 0.0                            |
| 445               | 27642                                | 0.6                            | 575               | 73613                                | 46.0                           | 705               | 11513                                | 0.0                            | 835               | 193                                  | 0.0                            | 965               | 12                                   | 0.0                            |
| 450               | 36602                                | 0.9                            | 580               | 79207                                | 47.1                           | 710               | 9780                                 | 0.0                            | 840               | 174                                  | 0.0                            | 970               | 3                                    | 0.0                            |
| 455               | 28292                                | 0.9                            | 585               | 84248                                | 47.0                           | 715               | 8356                                 | 0.0                            | 845               | 151                                  | 0.0                            | 975               | 8                                    | 0.0                            |
| 460               | 21166                                | 0.9                            | 590               | 88397                                | 45.7                           | 720               | 7161                                 | 0.0                            | 850               | 123                                  | 0.0                            | 980               | 2                                    | 0.0                            |
| 465               | 19092                                | 1.0                            | 595               | 91428                                | 43.4                           | 725               | 6067                                 | 0.0                            | 855               | 106                                  | 0.0                            | 985               | 13                                   | 0.0                            |
| 470               | 14951                                | 0.9                            | 600               | 93452                                | 40.3                           | 730               | 5164                                 | 0.0                            | 860               | 95                                   | 0.0                            | 990               | 16                                   | 0.0                            |
| 475               | 12606                                | 1.0                            | 605               | 93959                                | 36.4                           | 735               | 4393                                 | 0.0                            | 865               | 82                                   | 0.0                            | 995               | 20                                   | 0.0                            |
| 480               | 13323                                | 1.3                            | 610               | 93079                                | 32.0                           | 740               | 3694                                 | 0.0                            | 870               | 77                                   | 0.0                            | 1000              | 0                                    | 0.0                            |
| 485               | 15164                                | 1.8                            | 615               | 90707                                | 27.3                           | 745               | 3157                                 | 0.0                            | 875               | 65                                   | 0.0                            |                   |                                      |                                |

REPORT NUMBER: SP1-2407-157-9

**Scotopic Flux vs. Wavelength**



**Scotopic Lumens: 5286.7**


**S/P: 1.22**

| $\lambda$<br>(nm) | Power<br>( $\mu\text{W}/\text{nm}$ ) | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>( $\mu\text{W}/\text{nm}$ ) | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>( $\mu\text{W}/\text{nm}$ ) | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>( $\mu\text{W}/\text{nm}$ ) | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>( $\mu\text{W}/\text{nm}$ ) | Lumens<br>( $\phi/\text{nm}$ ) |
|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|
| 360               | 0                                    | 0.0                            | 490               | 18018                                | 75.9                           | 620               | 87426                                | 0.4                            | 750               | 2680                                 | 0.0                            | 880               | 58                                   | 0.0                            |
| 365               | 0                                    | 0.0                            | 495               | 22295                                | 93.2                           | 625               | 83013                                | 0.2                            | 755               | 2287                                 | 0.0                            | 885               | 46                                   | 0.0                            |
| 370               | 0                                    | 0.0                            | 500               | 26478                                | 107.8                          | 630               | 78077                                | 0.1                            | 760               | 1944                                 | 0.0                            | 890               | 45                                   | 0.0                            |
| 375               | 0                                    | 0.0                            | 505               | 30524                                | 118.7                          | 635               | 72080                                | 0.1                            | 765               | 1653                                 | 0.0                            | 895               | 41                                   | 0.0                            |
| 380               | 0                                    | 0.0                            | 510               | 33611                                | 122.2                          | 640               | 66249                                | 0.1                            | 770               | 1413                                 | 0.0                            | 900               | 38                                   | 0.0                            |
| 385               | 0                                    | 0.0                            | 515               | 36490                                | 120.8                          | 645               | 59973                                | 0.0                            | 775               | 1198                                 | 0.0                            | 905               | 33                                   | 0.0                            |
| 390               | 0                                    | 0.0                            | 520               | 38610                                | 113.9                          | 650               | 53972                                | 0.0                            | 780               | 1025                                 | 0.0                            | 910               | 30                                   | 0.0                            |
| 395               | 0                                    | 0.0                            | 525               | 40511                                | 104.1                          | 655               | 48369                                | 0.0                            | 785               | 874                                  | 0.0                            | 915               | 23                                   | 0.0                            |
| 400               | 48                                   | 0.0                            | 530               | 42223                                | 92.4                           | 660               | 42641                                | 0.0                            | 790               | 747                                  | 0.0                            | 920               | 24                                   | 0.0                            |
| 405               | 201                                  | 0.0                            | 535               | 44137                                | 80.5                           | 665               | 37602                                | 0.0                            | 795               | 639                                  | 0.0                            | 925               | 22                                   | 0.0                            |
| 410               | 457                                  | 0.1                            | 540               | 46032                                | 68.2                           | 670               | 32798                                | 0.0                            | 800               | 547                                  | 0.0                            | 930               | 22                                   | 0.0                            |
| 415               | 925                                  | 0.3                            | 545               | 48553                                | 57.1                           | 675               | 28558                                | 0.0                            | 805               | 473                                  | 0.0                            | 935               | 17                                   | 0.0                            |
| 420               | 1816                                 | 1.1                            | 550               | 51408                                | 46.7                           | 680               | 24782                                | 0.0                            | 810               | 401                                  | 0.0                            | 940               | 13                                   | 0.0                            |
| 425               | 3217                                 | 2.5                            | 555               | 54711                                | 37.4                           | 685               | 21386                                | 0.0                            | 815               | 351                                  | 0.0                            | 945               | 6                                    | 0.0                            |
| 430               | 5520                                 | 5.9                            | 560               | 58847                                | 29.4                           | 690               | 18413                                | 0.0                            | 820               | 307                                  | 0.0                            | 950               | 10                                   | 0.0                            |
| 435               | 9225                                 | 12.5                           | 565               | 63386                                | 22.5                           | 695               | 15721                                | 0.0                            | 825               | 261                                  | 0.0                            | 955               | 11                                   | 0.0                            |
| 440               | 15522                                | 26.3                           | 570               | 68196                                | 16.9                           | 700               | 13432                                | 0.0                            | 830               | 228                                  | 0.0                            | 960               | 8                                    | 0.0                            |
| 445               | 27642                                | 55.2                           | 575               | 73613                                | 12.4                           | 705               | 11513                                | 0.0                            | 835               | 193                                  | 0.0                            | 965               | 12                                   | 0.0                            |
| 450               | 36602                                | 85.4                           | 580               | 79207                                | 9.0                            | 710               | 9780                                 | 0.0                            | 840               | 174                                  | 0.0                            | 970               | 3                                    | 0.0                            |
| 455               | 28292                                | 75.1                           | 585               | 84248                                | 6.3                            | 715               | 8356                                 | 0.0                            | 845               | 151                                  | 0.0                            | 975               | 8                                    | 0.0                            |
| 460               | 21166                                | 63.2                           | 590               | 88397                                | 4.4                            | 720               | 7161                                 | 0.0                            | 850               | 123                                  | 0.0                            | 980               | 2                                    | 0.0                            |
| 465               | 19092                                | 63.2                           | 595               | 91428                                | 3.0                            | 725               | 6067                                 | 0.0                            | 855               | 106                                  | 0.0                            | 985               | 13                                   | 0.0                            |
| 470               | 14951                                | 54.2                           | 600               | 93452                                | 2.0                            | 730               | 5164                                 | 0.0                            | 860               | 95                                   | 0.0                            | 990               | 16                                   | 0.0                            |
| 475               | 12606                                | 48.8                           | 605               | 93959                                | 1.3                            | 735               | 4393                                 | 0.0                            | 865               | 82                                   | 0.0                            | 995               | 20                                   | 0.0                            |
| 480               | 13323                                | 54.2                           | 610               | 93079                                | 0.9                            | 740               | 3694                                 | 0.0                            | 870               | 77                                   | 0.0                            | 1000              | 0                                    | 0.0                            |
| 485               | 15164                                | 63.3                           | 615               | 90707                                | 0.5                            | 745               | 3157                                 | 0.0                            | 875               | 65                                   | 0.0                            |                   |                                      |                                |



REPORT NUMBER: SP1-2407-157-9

**Melanopic Flux vs. Wavelength**




**Melanopic Lumens: 9797**

**M/P: 2.26**





| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360    | 0             | 0.0           | 490    | 18018         | 27.7          | 620    | 87426         | 1.1           | 750    | 2680          | 0.0           | 880    | 58            | 0.0           |
| 365    | 0             | 0.0           | 495    | 22295         | 36.0          | 625    | 83013         | 0.7           | 755    | 2287          | 0.0           | 885    | 46            | 0.0           |
| 370    | 0             | 0.0           | 500    | 26478         | 44.2          | 630    | 78077         | 0.4           | 760    | 1944          | 0.0           | 890    | 45            | 0.0           |
| 375    | 0             | 0.0           | 505    | 30524         | 51.8          | 635    | 72080         | 0.3           | 765    | 1653          | 0.0           | 895    | 41            | 0.0           |
| 380    | 0             | 0.0           | 510    | 33611         | 57.0          | 640    | 66249         | 0.2           | 770    | 1413          | 0.0           | 900    | 38            | 0.0           |
| 385    | 0             | 0.0           | 515    | 36490         | 60.5          | 645    | 59973         | 0.1           | 775    | 1198          | 0.0           | 905    | 33            | 0.0           |
| 390    | 0             | 0.0           | 520    | 38610         | 61.4          | 650    | 53972         | 0.1           | 780    | 1025          | 0.0           | 910    | 30            | 0.0           |
| 395    | 0             | 0.0           | 525    | 40511         | 60.6          | 655    | 48369         | 0.0           | 785    | 874           | 0.0           | 915    | 23            | 0.0           |
| 400    | 48            | 0.0           | 530    | 42223         | 58.2          | 660    | 42641         | 0.0           | 790    | 747           | 0.0           | 920    | 24            | 0.0           |
| 405    | 201           | 0.0           | 535    | 44137         | 55.0          | 665    | 37602         | 0.0           | 795    | 639           | 0.0           | 925    | 22            | 0.0           |
| 410    | 457           | 0.0           | 540    | 46032         | 50.9          | 670    | 32798         | 0.0           | 800    | 547           | 0.0           | 930    | 22            | 0.0           |
| 415    | 925           | 0.1           | 545    | 48553         | 46.6          | 675    | 28558         | 0.0           | 805    | 473           | 0.0           | 935    | 17            | 0.0           |
| 420    | 1816          | 0.3           | 550    | 51408         | 42.0          | 680    | 24782         | 0.0           | 810    | 401           | 0.0           | 940    | 13            | 0.0           |
| 425    | 3217          | 0.8           | 555    | 54711         | 37.4          | 685    | 21386         | 0.0           | 815    | 351           | 0.0           | 945    | 6             | 0.0           |
| 430    | 5520          | 1.9           | 560    | 58847         | 32.9          | 690    | 18413         | 0.0           | 820    | 307           | 0.0           | 950    | 10            | 0.0           |
| 435    | 9225          | 4.1           | 565    | 63386         | 28.4          | 695    | 15721         | 0.0           | 825    | 261           | 0.0           | 955    | 11            | 0.0           |
| 440    | 15522         | 8.7           | 570    | 68196         | 24.1          | 700    | 13432         | 0.0           | 830    | 228           | 0.0           | 960    | 8             | 0.0           |
| 445    | 27642         | 18.5          | 575    | 73613         | 20.0          | 705    | 11513         | 0.0           | 835    | 193           | 0.0           | 965    | 12            | 0.0           |
| 450    | 36602         | 28.3          | 580    | 79207         | 16.3          | 710    | 9780          | 0.0           | 840    | 174           | 0.0           | 970    | 3             | 0.0           |
| 455    | 28292         | 24.7          | 585    | 84248         | 12.9          | 715    | 8356          | 0.0           | 845    | 151           | 0.0           | 975    | 8             | 0.0           |
| 460    | 21166         | 20.4          | 590    | 88397         | 9.8           | 720    | 7161          | 0.0           | 850    | 123           | 0.0           | 980    | 2             | 0.0           |
| 465    | 19092         | 20.1          | 595    | 91428         | 7.3           | 725    | 6067          | 0.0           | 855    | 106           | 0.0           | 985    | 13            | 0.0           |
| 470    | 14951         | 17.2          | 600    | 93452         | 5.3           | 730    | 5164          | 0.0           | 860    | 95            | 0.0           | 990    | 16            | 0.0           |
| 475    | 12606         | 15.7          | 605    | 93959         | 3.7           | 735    | 4393          | 0.0           | 865    | 82            | 0.0           | 995    | 20            | 0.0           |
| 480    | 13323         | 18.0          | 610    | 93079         | 2.5           | 740    | 3694          | 0.0           | 870    | 77            | 0.0           | 1000   | 0             | 0.0           |
| 485    | 15164         | 21.9          | 615    | 90707         | 1.7           | 745    | 3157          | 0.0           | 875    | 65            | 0.0           |        |               |               |

**Summary**

$R_f = 84.7$   
 $R_g = 94.6$   
 CIE  $R_a = 80.9$   
 $R_9 = -1.5$




**Color Vector Graphics**






**Individual Sample Fidelity Index ( $R_{f,i}$ )**



|            |            |            |            |
|------------|------------|------------|------------|
| CES01 = 86 | CES26 = 84 | CES51 = 95 | CES76 = 81 |
| CES02 = 63 | CES27 = 95 | CES52 = 94 | CES77 = 84 |
| CES03 = 31 | CES28 = 94 | CES53 = 89 | CES78 = 81 |
| CES04 = 71 | CES29 = 87 | CES54 = 91 | CES79 = 89 |
| CES05 = 50 | CES30 = 94 | CES55 = 90 | CES80 = 89 |
| CES06 = 52 | CES31 = 89 | CES56 = 86 | CES81 = 69 |
| CES07 = 43 | CES32 = 82 | CES57 = 85 | CES82 = 96 |
| CES08 = 41 | CES33 = 91 | CES58 = 86 | CES83 = 93 |
| CES09 = 29 | CES34 = 92 | CES59 = 91 | CES84 = 92 |
| CES10 = 77 | CES35 = 96 | CES60 = 94 | CES85 = 76 |
| CES11 = 60 | CES36 = 90 | CES61 = 89 | CES86 = 65 |
| CES12 = 66 | CES37 = 96 | CES62 = 94 | CES87 = 84 |
| CES13 = 44 | CES38 = 98 | CES63 = 87 | CES88 = 86 |
| CES14 = 74 | CES39 = 98 | CES64 = 82 | CES89 = 73 |
| CES15 = 72 | CES40 = 95 | CES65 = 78 | CES90 = 88 |
| CES16 = 48 | CES41 = 96 | CES66 = 81 | CES91 = 82 |
| CES17 = 50 | CES42 = 97 | CES67 = 80 | CES92 = 64 |
| CES18 = 57 | CES43 = 91 | CES68 = 83 | CES93 = 78 |
| CES19 = 73 | CES44 = 99 | CES69 = 88 | CES94 = 59 |
| CES20 = 67 | CES45 = 93 | CES70 = 80 | CES95 = 74 |
| CES21 = 87 | CES46 = 89 | CES71 = 79 | CES96 = 83 |
| CES22 = 79 | CES47 = 92 | CES72 = 92 | CES97 = 88 |
| CES23 = 92 | CES48 = 83 | CES73 = 75 | CES98 = 83 |
| CES24 = 91 | CES49 = 90 | CES74 = 91 | CES99 = 74 |
| CES25 = 72 | CES50 = 94 | CES75 = 81 |            |



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)